

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331979-840

Luminaire Tested: **S123DIP-S775D805U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331979-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D805U840-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 805 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6443.6 lumens  
Efficiency: N/A  
Efficacy: 140.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331979-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331979-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47	42				
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	40	35				
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34	30				
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25				
5	68	56	48	42	62	52	45	40	45	39	35	38	33	30	31	28	25	22				
6	63	51	42	37	58	47	40	34	40	35	30	34	30	26	28	25	22	19				
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	26	22	20	17				
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15				
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16	14				
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13237	13237	13237
5°	13299	13116	13207
10°	13210	13002	13083
15°	13056	12856	12880
20°	12875	12645	12657
25°	12634	12396	12371
30°	12367	12117	12026
35°	12089	11825	11671
40°	11797	11500	11323
45°	11478	11204	10930
50°	11156	10836	10535
55°	10736	10457	10141
60°	10312	10015	9698
65°	9938	9536	9235
70°	9385	8985	8585
75°	8576	8268	7918
80°	7736	7407	7345
85°	6780	6533	6274



TEST NUMBER: P331979-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.8	1.8
10°-20°	327.1	5.1
20°-30°	483.2	7.5
30°-40°	564.4	8.8
40°-50°	567.4	8.8
50°-60°	498.4	7.7
60°-70°	371.3	5.8
70°-80°	211.6	3.3
80°-90°	63.7	1.0
90°-100°	38.6	0.6
100°-110°	184.1	2.9
110°-120°	442.3	6.9
120°-130°	563.2	8.7
130°-140°	601.8	9.3
140°-150°	562.7	8.7
150°-160°	453.9	7.0
160°-170°	293.0	4.5
170°-180°	101.0	1.6
0°-30°	926.1	14.4
0°-40°	1490.5	23.1
0°-60°	2556.3	39.7
0°-90°	3202.9	49.7
90°-120°	665.1	10.3
90°-150°	2392.8	37.1
90°-180°	3241.0	50.3
0°-180°	6443.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1172	1167	1154	1161	1156	330
25°	1064	1057	1044	1044	1042	490
35°	920	913	900	894	888	575
45°	754	749	736	724	718	582
55°	572	570	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	221
85°	55	53	53	51	51	60
90°	1	9	19	22	24	5
95°	48	18	24	30	30	60
105°	235	240	173	41	35	249
115°	441	446	453	461	464	435
125°	622	628	632	633	635	555
135°	774	779	782	784	782	596
145°	894	899	901	902	902	559
155°	984	983	984	987	983	453
165°	1038	1036	1035	1041	1036	293
175°	1063	1059	1060	1064	1059	101
180°	1063	1063	1063	1063	1063	



TEST NUMBER: P331979-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1234.0	1233.2	1232.5	1231.7	1231.0	1229.6	1227.5	1225.5	1223.4	1221.3	1223.1
5°	1230.8	1229.6	1228.5	1227.3	1226.1	1224.3	1221.6	1219.1	1216.5	1213.9	1216.3
7.5°	1218.8	1217.6	1216.4	1215.3	1214.1	1212.1	1209.4	1206.8	1204.1	1201.4	1203.6
10°	1208.6	1207.4	1206.3	1205.1	1204.0	1201.8	1198.7	1195.7	1192.7	1189.6	1191.7
12.5°	1195.1	1194.1	1193.2	1192.1	1191.1	1189.2	1186.4	1183.5	1180.6	1177.7	1179.3
15°	1171.6	1170.6	1169.7	1168.8	1167.8	1165.9	1162.8	1159.7	1156.7	1153.7	1155.5
17.5°	1144.3	1143.1	1141.9	1140.6	1139.4	1137.3	1134.3	1131.1	1128.1	1125.1	1126.4
20°	1124.0	1122.6	1121.3	1119.8	1118.4	1116.1	1113.1	1110.0	1107.0	1103.9	1104.9
22.5°	1101.2	1099.7	1098.3	1096.9	1095.5	1093.3	1090.3	1087.2	1084.2	1081.1	1081.9
25°	1063.8	1062.4	1061.0	1059.6	1058.1	1055.9	1052.8	1049.8	1046.7	1043.7	1043.9
27.5°	1023.8	1022.4	1021.1	1019.7	1018.3	1016.0	1012.7	1009.5	1006.1	1002.8	1003.0
30°	995.0	993.8	992.7	991.5	990.3	988.1	984.8	981.5	978.3	974.9	974.9
32.5°	966.2	964.7	963.1	961.6	960.1	958.1	955.4	952.9	950.4	947.9	946.5
35°	920.0	918.6	917.2	915.7	914.3	912.1	909.0	905.9	902.9	899.9	898.5
37.5°	872.5	870.8	869.0	867.2	865.5	863.0	859.9	856.8	853.6	850.6	848.9
40°	839.6	838.2	836.8	835.4	833.9	831.6	828.3	825.1	821.7	818.4	816.6
42.5°	806.6	805.0	803.3	801.8	800.2	797.8	794.5	791.1	787.9	784.6	782.7
45°	754.0	753.0	752.0	751.1	750.1	748.2	745.1	742.0	739.0	736.0	733.2
47.5°	701.7	700.3	698.9	697.6	696.2	694.1	691.3	688.4	685.5	682.7	679.8
50°	666.2	665.0	663.8	662.7	661.5	659.3	656.3	653.3	650.2	647.1	644.6
52.5°	628.9	628.1	627.3	626.5	625.7	623.7	620.5	617.2	614.0	610.8	608.5
55°	572.1	571.8	571.6	571.4	571.1	569.5	566.4	563.4	560.3	557.2	554.7
57.5°	518.0	517.2	516.3	515.5	514.7	513.1	510.7	508.2	505.7	503.3	501.0
60°	479.0	478.8	478.6	478.3	478.1	476.6	473.7	470.9	468.1	465.2	463.1
62.5°	444.3	443.7	443.1	442.5	441.9	440.2	437.4	434.5	431.7	428.9	426.8
65°	390.2	389.0	387.8	386.7	385.5	383.7	381.3	379.0	376.7	374.4	372.4
67.5°	332.9	331.8	330.8	329.7	328.7	327.3	325.6	323.8	321.9	320.2	318.5
70°	298.2	296.8	295.4	294.0	292.6	291.1	289.7	288.3	286.9	285.5	283.9
72.5°	261.9	260.7	259.7	258.7	257.7	256.4	254.8	253.2	251.6	249.9	248.5
75°	206.2	205.2	204.3	203.4	202.5	201.6	200.9	200.2	199.4	198.8	197.6
77.5°	156.9	156.4	155.9	155.4	154.8	154.2	153.3	152.5	151.7	150.8	150.0
80°	124.8	124.1	123.4	122.7	122.0	121.4	120.9	120.5	120.0	119.5	119.3
82.5°	93.5	93.3	93.2	93.0	92.9	92.8	92.7	92.6	92.5	92.4	92.0
85°	54.9	54.5	54.0	53.6	53.1	52.9	52.9	52.9	52.9	52.9	52.4
87.5°	22.1	21.9	21.7	21.5	21.3	21.3	21.6	21.9	22.1	22.4	22.3
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.3	16.7	19.0	19.7
92.5°	14.6	14.2	13.7	13.2	12.7	13.3	15.0	16.8	18.5	20.2	21.3
95°	48.2	41.0	33.7	26.6	19.4	16.8	18.7	20.6	22.5	24.4	25.8
97.5°	96.7	93.6	90.4	87.2	83.9	75.9	63.3	50.7	38.1	25.4	26.9
100°	133.4	136.9	140.5	143.9	147.4	135.5	108.2	80.8	53.4	26.1	27.5
102.5°	175.1	177.6	180.2	182.7	185.2	171.6	141.7	111.7	81.8	51.9	47.6
105°	235.3	237.2	239.1	241.1	243.0	236.1	220.3	204.5	188.6	172.9	141.9
107.5°	298.7	300.3	301.8	303.4	304.9	306.9	309.4	311.9	314.4	316.9	294.2
110°	341.0	342.4	343.9	345.3	346.7	348.3	350.3	352.2	354.2	356.1	350.3



TEST NUMBER: P331979-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.5	382.7	384.1	385.3	386.6	388.1	390.1	392.0	393.9	395.9	396.0
115°	441.3	442.4	443.4	444.5	445.6	446.9	448.5	450.0	451.6	453.2	454.9
117.5°	499.3	500.6	501.9	503.2	504.4	505.5	506.3	507.2	508.0	508.8	510.2
120°	535.3	536.8	538.5	540.0	541.6	542.7	543.2	543.7	544.2	544.7	546.1
122.5°	571.9	573.2	574.5	575.8	577.1	578.0	578.8	579.5	580.1	580.8	581.8
125°	622.2	623.5	624.9	626.3	627.7	628.8	629.5	630.2	630.9	631.6	632.0
127.5°	670.8	672.2	673.6	675.0	676.4	677.5	678.3	679.2	680.0	680.9	681.5
130°	701.0	702.5	703.9	705.3	706.7	707.7	708.4	709.1	709.8	710.5	711.2
132.5°	730.1	731.5	733.0	734.4	735.8	736.7	737.3	737.8	738.4	739.0	739.7
135°	774.5	775.6	776.6	777.7	778.7	779.6	780.3	781.0	781.7	782.4	782.9
137.5°	812.4	813.7	815.1	816.4	817.7	818.6	819.0	819.4	819.7	820.1	821.0
140°	837.7	838.7	839.8	840.8	841.9	842.6	843.2	843.7	844.2	844.8	845.5
142.5°	861.0	862.1	863.1	864.2	865.3	866.1	866.6	867.1	867.6	868.2	868.7
145°	893.7	894.9	896.2	897.4	898.7	899.4	899.8	900.1	900.5	900.8	901.2
147.5°	924.5	925.3	926.1	927.0	927.8	928.4	928.7	929.0	929.4	929.7	930.1
150°	943.4	944.0	944.5	945.0	945.5	946.0	946.3	946.7	947.1	947.5	947.8
152.5°	960.5	960.8	961.0	961.3	961.5	961.7	961.9	962.1	962.4	962.6	963.2
155°	984.5	984.2	983.8	983.5	983.1	983.0	983.2	983.4	983.5	983.7	984.6
157.5°	1003.1	1003.1	1003.1	1003.0	1003.0	1002.9	1002.7	1002.6	1002.4	1002.2	1003.3
160°	1014.5	1014.3	1014.2	1014.0	1013.8	1013.6	1013.5	1013.3	1013.1	1012.9	1014.0
162.5°	1025.2	1024.8	1024.3	1023.9	1023.4	1023.1	1022.9	1022.8	1022.6	1022.4	1023.6
165°	1038.2	1037.6	1037.1	1036.6	1036.1	1035.7	1035.6	1035.4	1035.2	1035.0	1036.4
167.5°	1048.3	1047.6	1046.9	1046.2	1045.5	1045.1	1045.1	1045.1	1045.1	1045.1	1046.5
170°	1054.0	1053.3	1052.6	1051.9	1051.2	1050.9	1050.9	1050.9	1050.9	1050.9	1052.3
172.5°	1057.7	1056.9	1056.1	1055.2	1054.4	1054.1	1054.2	1054.3	1054.5	1054.6	1056.0
175°	1062.7	1061.8	1061.0	1060.1	1059.1	1058.8	1058.9	1059.1	1059.3	1059.6	1060.8
177.5°	1063.9	1063.3	1062.6	1061.9	1061.2	1060.9	1061.0	1061.2	1061.3	1061.4	1062.6
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P331979-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1225.1	1227.0	1228.8	1229.7	1229.5	1229.3	1229.1	1228.9
5°	1218.6	1220.9	1223.4	1224.3	1223.8	1223.4	1222.8	1222.3
7.5°	1205.7	1207.8	1209.9	1210.8	1210.5	1210.2	1209.9	1209.7
10°	1193.9	1195.9	1198.0	1198.9	1198.4	1197.9	1197.5	1197.0
12.5°	1180.8	1182.3	1184.0	1184.6	1184.3	1184.0	1183.8	1183.5
15°	1157.4	1159.2	1161.1	1161.3	1159.9	1158.5	1157.2	1155.8
17.5°	1127.7	1129.0	1130.3	1130.7	1130.2	1129.7	1129.2	1128.7
20°	1105.8	1106.7	1107.7	1107.8	1107.1	1106.4	1105.7	1105.0
22.5°	1082.6	1083.4	1084.1	1084.0	1083.2	1082.3	1081.4	1080.5
25°	1044.1	1044.4	1044.6	1044.4	1043.7	1043.0	1042.3	1041.6
27.5°	1003.2	1003.4	1003.6	1003.2	1002.4	1001.5	1000.6	999.7
30°	974.9	974.9	974.9	974.1	972.5	970.8	969.2	967.6
32.5°	945.2	943.9	942.6	941.5	940.6	939.7	938.8	938.0
35°	897.1	895.6	894.2	892.9	891.7	890.6	889.4	888.2
37.5°	847.2	845.5	843.8	842.6	841.8	841.1	840.3	839.6
40°	814.7	812.8	810.9	809.5	808.6	807.6	806.7	805.8
42.5°	780.8	778.9	777.1	775.7	774.8	773.8	772.8	771.9
45°	730.3	727.5	724.7	722.7	721.5	720.3	719.1	718.0
47.5°	677.1	674.4	671.6	669.6	668.6	667.6	666.6	665.5
50°	642.0	639.3	636.8	634.8	633.4	632.0	630.6	629.1
52.5°	606.3	604.1	601.9	600.2	598.7	597.3	595.9	594.5
55°	552.1	549.5	546.9	545.0	543.8	542.7	541.5	540.4
57.5°	498.7	496.4	494.1	492.3	490.9	489.6	488.2	486.9
60°	461.0	458.9	456.8	455.1	453.9	452.8	451.6	450.5
62.5°	424.6	422.5	420.4	419.0	418.2	417.4	416.6	415.8
65°	370.5	368.7	366.8	365.5	364.8	364.1	363.3	362.6
67.5°	316.9	315.3	313.6	312.3	311.3	310.3	309.3	308.3
70°	282.3	280.5	278.9	277.5	276.3	275.2	274.0	272.8
72.5°	247.0	245.6	244.2	243.1	242.5	241.9	241.3	240.7
75°	196.4	195.3	194.1	193.2	192.5	191.8	191.1	190.4
77.5°	149.2	148.3	147.5	147.2	147.2	147.2	147.2	147.2
80°	119.1	118.8	118.6	118.5	118.5	118.5	118.5	118.5
82.5°	91.6	91.2	90.7	90.4	90.3	90.1	89.9	89.7
85°	51.9	51.5	51.0	50.8	50.8	50.8	50.8	50.8
87.5°	22.3	22.2	22.2	22.2	22.3	22.3	22.4	22.5
90°	20.4	21.0	21.7	22.3	22.6	23.0	23.3	23.7
92.5°	22.4	23.5	24.7	25.3	25.5	25.8	26.0	26.3
95°	27.0	28.2	29.4	30.0	30.0	30.0	30.0	30.0
97.5°	28.3	29.6	31.0	31.8	32.0	32.2	32.3	32.5
100°	28.9	30.3	31.7	32.4	32.6	32.8	33.0	33.1
102.5°	43.2	38.9	34.5	32.5	32.8	33.1	33.4	33.8
105°	110.8	79.8	48.7	33.3	33.7	34.0	34.4	34.7
107.5°	271.4	248.6	225.8	202.7	179.4	155.9	132.5	109.1
110°	344.5	338.7	333.0	317.5	292.4	267.3	242.2	217.1





TEST NUMBER: P331979-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	396.1	396.2	396.3	393.6	388.4	383.0	377.8	372.5
115°	456.7	458.5	460.2	461.4	462.1	462.8	463.5	464.2
117.5°	511.6	513.0	514.3	515.1	515.3	515.4	515.5	515.7
120°	547.5	549.0	550.4	551.1	551.1	551.1	551.1	551.1
122.5°	582.7	583.7	584.7	585.2	585.4	585.5	585.7	585.8
125°	632.3	632.7	633.0	633.4	633.7	634.1	634.4	634.8
127.5°	682.0	682.6	683.1	683.2	682.9	682.6	682.2	681.9
130°	712.0	712.7	713.4	713.6	713.2	712.9	712.5	712.2
132.5°	740.3	741.0	741.7	741.8	741.4	740.9	740.4	739.9
135°	783.5	784.0	784.5	784.5	784.0	783.5	782.9	782.4
137.5°	821.8	822.6	823.5	823.7	823.4	823.0	822.7	822.3
140°	846.2	846.9	847.6	847.8	847.4	847.1	846.7	846.4
142.5°	869.3	869.8	870.4	870.4	869.9	869.4	869.0	868.5
145°	901.5	901.9	902.2	902.4	902.4	902.4	902.4	902.4
147.5°	930.4	930.8	931.1	930.9	930.1	929.3	928.5	927.7
150°	948.1	948.5	948.8	948.8	948.2	947.7	947.2	946.6
152.5°	963.8	964.4	965.1	965.0	964.2	963.4	962.6	961.8
155°	985.5	986.3	987.2	987.1	986.1	985.0	984.0	982.9
157.5°	1004.3	1005.3	1006.4	1006.2	1004.9	1003.5	1002.2	1000.8
160°	1015.0	1016.1	1017.1	1017.0	1015.8	1014.6	1013.4	1012.2
162.5°	1024.8	1026.0	1027.1	1027.2	1026.1	1025.0	1024.0	1022.9
165°	1037.8	1039.3	1040.7	1040.8	1039.6	1038.2	1037.0	1035.8
167.5°	1047.9	1049.4	1050.8	1050.8	1049.4	1047.9	1046.5	1045.1
170°	1053.6	1055.0	1056.4	1056.4	1055.0	1053.6	1052.3	1050.9
172.5°	1057.4	1058.8	1060.3	1060.2	1058.6	1057.1	1055.5	1054.0
175°	1062.0	1063.2	1064.4	1064.3	1063.0	1061.6	1060.2	1058.7
177.5°	1063.7	1064.8	1065.9	1065.8	1064.4	1063.0	1061.6	1060.2
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7

(END OF REPORT)