

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332354-840

Luminaire Tested: **S123RDIP-S1000D1195U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332354-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U840-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8817.5 lumens
Efficiency: N/A
Efficacy: 134.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	90	86	89	86	83	80	72	69	67	59	57	56	47	46	45	39
2	89	82	76	71	81	75	70	66	63	60	57	52	50	47	42	40	39	34
3	82	72	66	60	75	67	61	56	56	52	48	47	43	41	37	35	33	29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29	26
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	22
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	24	21	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17280	17280	17280	17280
5°	20599	17354	15282	17354
10°	25719	17254	13806	17254
15°	30190	17079	12590	17079
20°	33693	16814	11557	16814
25°	33155	16537	10922	16537
30°	23832	16281	10268	16281
35°	15912	15948	9843	15948
40°	11724	15548	9405	15548
45°	9834	14845	8977	14845
50°	8678	13924	8378	13924
55°	7610	12872	7557	12872
60°	6777	11866	6923	11866
65°	5952	10781	6441	10781
70°	4674	9819	5882	9819
75°	4117	8576	5373	8576
80°	3583	7283	5281	7283
85°	2878	5866	5595	5866



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	1.8
10°-20°	493.2	5.6
20°-30°	774.9	8.8
30°-40°	808.4	9.2
40°-50°	691.8	7.8
50°-60°	527.3	6.0
60°-70°	338.0	3.8
70°-80°	162.6	1.8
80°-90°	47.4	0.5
90°-100°	57.4	0.7
100°-110°	273.6	3.1
110°-120°	657.3	7.5
120°-130°	837.0	9.5
130°-140°	894.3	10.1
140°-150°	836.3	9.5
150°-160°	674.6	7.7
160°-170°	435.4	4.9
170°-180°	150.0	1.7
0°-30°	1426.0	16.2
0°-40°	2234.4	25.3
0°-60°	3453.6	39.2
0°-90°	4001.6	45.4
90°-120°	988.3	11.2
90°-150°	3555.9	40.3
90°-180°	4816.0	54.6
0°-180°	8817.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1605	1605	1605	1605	1605	
5°	1906	1606	1414	1606	1906	197
15°	2709	1533	1130	1533	2709	768
25°	2792	1392	920	1392	2792	1200
35°	1211	1214	749	1214	1211	794
45°	646	975	590	975	646	508
55°	406	686	403	686	406	367
65°	234	423	253	423	234	230
75°	99	206	129	206	99	106
85°	23	48	45	48	23	28
90°	35	1	35	1	35	17
95°	44	72	44	72	44	37
105°	52	350	52	350	52	118
115°	690	656	690	656	690	637
125°	943	924	943	924	943	842
135°	1163	1151	1163	1151	1163	897
145°	1341	1328	1341	1328	1341	837
155°	1461	1463	1461	1463	1461	674
165°	1539	1543	1539	1543	1539	435
175°	1573	1579	1573	1579	1573	150
180°	1579	1579	1579	1579	1579	



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1709.9	1712.0	1705.0	1703.8	1695.6	1693.3	1693.3	1681.8	1674.7	1665.4	1659.8
5°	1906.4	1917.4	1911.9	1899.6	1879.0	1874.1	1861.1	1840.5	1817.1	1788.2	1774.4
7.5°	2151.9	2166.9	2161.1	2142.0	2120.4	2102.9	2066.2	2031.9	1984.0	1941.9	1905.9
10°	2353.1	2337.3	2324.9	2306.4	2286.4	2254.1	2215.6	2162.7	2101.6	2053.5	1999.9
12.5°	2503.8	2501.1	2485.5	2466.4	2438.2	2407.5	2360.3	2295.8	2224.7	2155.3	2093.9
15°	2709.2	2713.2	2702.9	2683.0	2643.1	2588.9	2517.4	2490.6	2388.8	2313.3	2237.7
17.5°	2851.3	2850.4	2849.0	2821.5	2780.8	2742.1	2675.8	2605.4	2513.3	2406.7	2304.9
20°	2941.4	2934.6	2935.9	2905.0	2874.8	2830.0	2765.5	2663.1	2587.5	2464.5	2359.3
22.5°	2939.2	2937.8	2943.0	2932.4	2910.5	2876.3	2825.4	2739.0	2642.4	2518.3	2400.0
25°	2791.6	2786.1	2818.4	2827.3	2862.4	2868.5	2853.5	2806.0	2714.6	2586.8	2440.4
27.5°	2336.3	2333.3	2393.3	2468.3	2563.4	2637.4	2708.9	2743.4	2714.6	2623.1	2476.4
30°	1917.4	1982.1	2012.3	2120.8	2241.8	2386.1	2512.5	2632.8	2662.4	2622.5	2502.2
32.5°	1592.0	1648.3	1673.5	1766.8	1879.5	2048.5	2238.3	2408.5	2528.8	2559.3	2486.9
35°	1210.9	1211.6	1269.3	1310.6	1415.0	1588.9	1773.1	2001.2	2228.1	2399.8	2417.7
37.5°	966.2	969.7	1004.6	1045.7	1124.1	1216.0	1378.2	1567.9	1829.9	2093.7	2248.3
40°	834.4	840.5	866.7	907.2	963.5	1032.9	1159.4	1338.1	1556.6	1850.1	2089.9
42.5°	749.6	759.7	773.2	804.4	839.3	904.2	1006.5	1144.6	1343.3	1620.8	1897.5
45°	646.0	651.5	661.9	676.2	707.8	753.3	821.9	914.7	1079.6	1303.0	1579.9
47.5°	569.9	566.9	577.8	589.6	610.6	641.5	687.5	763.3	880.9	1060.2	1295.1
50°	518.2	517.5	525.0	534.0	553.9	576.6	614.4	671.5	764.9	913.3	1128.4
52.5°	469.8	472.4	477.8	488.9	503.3	521.6	555.5	596.6	676.9	805.1	984.4
55°	405.5	407.6	415.1	421.3	431.6	450.1	471.4	505.8	560.8	650.2	797.9
57.5°	351.0	350.1	357.4	358.9	370.5	385.7	402.1	428.9	468.7	535.1	634.6
60°	314.8	312.7	318.9	323.7	329.9	342.2	356.0	382.1	413.7	462.5	547.8
62.5°	281.8	280.8	285.4	290.1	295.3	306.5	318.1	338.1	363.1	404.2	471.9
65°	233.7	235.7	237.8	239.8	242.6	249.4	260.4	274.2	291.3	320.2	369.0
67.5°	183.6	185.7	186.4	190.7	196.5	200.9	207.5	219.7	231.8	256.1	283.9
70°	148.5	147.7	148.5	150.5	158.0	165.6	174.6	183.5	191.1	208.2	231.6
72.5°	127.5	126.3	128.2	128.6	132.2	134.3	140.0	148.3	158.0	169.8	186.5
75°	99.0	99.0	99.0	99.0	101.7	103.1	105.1	107.2	110.7	116.1	128.6
77.5°	73.1	73.2	74.2	74.9	75.4	76.2	77.6	79.6	80.8	83.7	89.1
80°	57.8	58.4	57.8	58.4	58.4	59.8	60.5	62.5	63.2	66.7	68.8
82.5°	43.4	43.0	43.4	44.1	44.1	45.5	45.6	47.2	47.3	49.1	51.1
85°	23.3	22.0	23.3	22.7	24.0	22.7	23.3	24.7	24.7	25.4	28.2
87.5°	12.5	13.5	12.3	12.7	12.6	13.0	12.8	12.6	13.5	12.8	12.6
90°	35.2	34.6	34.1	33.6	33.1	32.3	31.3	30.2	29.2	28.2	24.7
92.5°	39.0	38.7	38.4	38.0	37.7	36.8	35.0	33.3	31.7	30.0	27.5
95°	44.5	44.5	44.5	44.5	44.5	43.6	41.8	40.0	38.2	36.4	33.5
97.5°	48.4	48.1	47.9	47.6	47.3	46.2	44.0	41.9	39.9	37.8	56.6
100°	49.3	49.0	48.8	48.5	48.3	47.1	44.9	42.9	40.8	38.7	79.4
102.5°	50.2	49.8	49.3	48.8	48.4	51.3	57.8	64.2	70.7	77.2	121.6
105°	51.6	51.1	50.6	50.1	49.6	72.3	118.5	164.6	210.8	256.9	280.4
107.5°	162.2	196.9	231.7	266.5	301.2	335.6	369.4	403.2	437.1	471.0	467.3
110°	322.7	359.9	397.2	434.5	471.8	494.7	503.3	511.9	520.6	529.2	526.2



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	553.5	561.4	569.3	577.1	585.0	589.0	588.8	588.5	588.4	588.2	585.4
115°	689.8	688.8	687.8	686.7	685.7	683.9	681.3	678.6	676.1	673.5	671.2
117.5°	766.4	766.2	766.0	765.8	765.6	764.4	762.3	760.2	758.1	756.1	754.9
120°	818.9	818.9	818.9	818.9	818.9	817.9	815.8	813.7	811.6	809.5	808.8
122.5°	870.6	870.4	870.1	869.9	869.7	868.9	867.5	866.0	864.5	863.0	862.0
125°	943.3	942.8	942.3	941.7	941.2	940.7	940.2	939.7	939.2	938.6	937.6
127.5°	1013.2	1013.8	1014.3	1014.8	1015.3	1015.1	1014.3	1013.5	1012.7	1011.8	1010.6
130°	1058.3	1058.8	1059.3	1059.9	1060.4	1060.2	1059.0	1058.0	1057.0	1055.9	1054.9
132.5°	1099.5	1100.3	1101.1	1101.8	1102.5	1102.4	1101.4	1100.2	1099.2	1098.2	1097.3
135°	1162.8	1163.5	1164.3	1165.1	1165.9	1165.9	1165.1	1164.3	1163.5	1162.8	1161.6
137.5°	1222.0	1222.6	1223.1	1223.7	1224.2	1223.8	1222.5	1221.3	1220.0	1218.8	1218.2
140°	1257.8	1258.3	1258.8	1259.3	1259.8	1259.6	1258.5	1257.5	1256.5	1255.4	1254.7
142.5°	1290.6	1291.3	1292.0	1292.8	1293.5	1293.4	1292.6	1291.8	1291.0	1290.1	1289.4
145°	1341.0	1341.0	1341.0	1341.0	1341.0	1340.8	1340.3	1339.8	1339.2	1338.7	1338.2
147.5°	1378.6	1379.8	1381.0	1382.2	1383.4	1383.7	1383.2	1382.7	1382.2	1381.6	1381.1
150°	1406.7	1407.5	1408.4	1409.1	1409.9	1410.0	1409.5	1409.0	1408.5	1408.0	1407.4
152.5°	1429.3	1430.5	1431.7	1432.9	1434.1	1434.2	1433.3	1432.3	1431.4	1430.5	1430.2
155°	1460.8	1462.3	1463.9	1465.4	1466.9	1467.1	1465.8	1464.5	1463.2	1461.9	1461.7
157.5°	1487.2	1489.2	1491.3	1493.4	1495.4	1495.6	1494.0	1492.5	1491.0	1489.3	1489.7
160°	1504.1	1505.9	1507.8	1509.6	1511.5	1511.6	1510.0	1508.4	1506.9	1505.3	1505.6
162.5°	1520.0	1521.7	1523.3	1524.9	1526.5	1526.5	1524.7	1523.0	1521.2	1519.3	1519.6
165°	1539.3	1541.2	1543.0	1544.8	1546.6	1546.5	1544.4	1542.4	1540.2	1538.1	1538.4
167.5°	1553.2	1555.3	1557.3	1559.4	1561.6	1561.6	1559.4	1557.3	1555.3	1553.2	1553.2
170°	1561.7	1563.7	1565.8	1567.9	1569.9	1569.9	1567.9	1565.8	1563.7	1561.7	1561.7
172.5°	1566.3	1568.6	1570.9	1573.2	1575.5	1575.6	1573.5	1571.5	1569.3	1567.2	1567.0
175°	1573.4	1575.5	1577.5	1579.6	1581.7	1581.9	1580.0	1578.2	1576.4	1574.5	1574.3
177.5°	1575.5	1577.5	1579.6	1581.8	1583.8	1584.0	1582.4	1580.6	1579.0	1577.3	1577.1
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1657.6	1656.0	1648.3	1639.5	1627.9	1620.2	1614.2	1610.9	1601.0	1588.9	1580.6
5°	1760.0	1739.4	1717.5	1690.6	1665.9	1640.4	1624.7	1606.1	1583.4	1558.0	1540.1
7.5°	1869.8	1829.3	1785.7	1740.8	1696.4	1656.6	1621.3	1591.2	1555.1	1518.6	1493.1
10°	1953.9	1894.7	1833.6	1771.0	1713.9	1660.4	1619.1	1578.6	1535.3	1493.4	1461.8
12.5°	2030.2	1952.5	1882.0	1805.1	1732.1	1668.1	1608.7	1561.0	1508.9	1464.2	1428.3
15°	2127.0	2047.3	1962.1	1845.2	1748.4	1667.3	1595.1	1532.6	1469.4	1414.3	1379.3
17.5°	2217.5	2097.5	1983.0	1885.5	1759.6	1658.3	1570.2	1495.4	1426.0	1367.8	1324.6
20°	2254.8	2138.7	2014.3	1890.0	1766.3	1652.8	1550.4	1467.9	1395.8	1329.8	1290.0
22.5°	2277.3	2145.9	2014.9	1881.2	1749.7	1631.9	1530.7	1440.0	1361.7	1299.0	1249.8
25°	2303.6	2147.0	2002.7	1870.7	1736.7	1608.8	1488.5	1392.4	1307.9	1241.1	1188.9
27.5°	2321.0	2136.7	1966.1	1819.4	1683.4	1556.2	1445.9	1343.9	1258.2	1187.7	1131.7
30°	2324.3	2128.4	1938.0	1779.3	1641.1	1524.3	1407.4	1309.9	1219.2	1144.3	1092.1
32.5°	2328.6	2108.1	1900.1	1731.4	1590.0	1474.3	1368.5	1275.3	1182.3	1108.5	1055.2
35°	2310.6	2096.8	1842.5	1648.7	1507.1	1395.1	1299.6	1213.7	1122.3	1050.8	996.5
37.5°	2232.4	2052.1	1782.8	1555.5	1407.4	1303.7	1225.9	1151.0	1067.1	990.1	938.9
40°	2153.8	2008.1	1736.7	1498.8	1344.2	1237.7	1167.6	1106.5	1025.4	953.2	898.3
42.5°	2036.7	1948.2	1692.7	1439.5	1272.7	1170.1	1111.0	1053.7	982.5	909.2	857.6
45°	1821.9	1833.6	1602.7	1344.9	1173.8	1070.8	1015.0	975.2	912.0	851.5	798.6
47.5°	1552.5	1661.7	1496.9	1244.2	1069.4	972.7	924.0	889.3	846.7	787.3	739.0
50°	1376.5	1532.6	1412.3	1176.6	1004.1	907.9	859.7	831.5	794.5	747.7	701.7
52.5°	1214.4	1381.9	1310.0	1101.3	933.1	845.2	798.2	775.0	745.5	701.6	659.8
55°	990.3	1160.0	1143.6	987.5	826.8	747.7	712.0	685.9	665.9	633.0	600.0
57.5°	801.0	962.0	970.5	861.1	733.1	654.9	624.2	604.5	591.5	566.5	536.0
60°	681.8	829.5	858.4	775.9	665.9	597.2	566.9	551.2	540.9	520.9	497.6
62.5°	582.8	708.5	741.2	681.9	601.6	537.2	513.6	498.4	491.4	474.2	453.6
65°	446.1	550.5	582.1	549.1	507.2	455.7	436.4	423.3	417.2	407.6	392.4
67.5°	335.4	411.5	446.2	422.9	407.8	375.3	363.0	356.0	350.5	343.9	331.2
70°	269.4	325.8	361.5	355.3	343.0	325.8	316.8	312.0	306.5	301.0	290.0
72.5°	216.6	255.4	288.9	292.1	282.0	278.5	270.6	268.6	265.3	258.7	252.7
75°	143.6	170.5	193.8	202.8	206.8	210.3	206.8	206.2	205.5	200.0	196.5
77.5°	94.1	108.6	123.3	138.6	145.0	149.7	150.8	153.3	151.5	148.6	146.9
80°	72.2	75.6	85.9	99.0	109.3	113.4	116.1	117.5	116.8	116.1	113.4
82.5°	52.4	55.2	60.1	69.3	78.0	84.8	86.4	86.1	87.7	88.1	85.9
85°	28.2	28.9	30.2	31.6	36.5	44.0	46.0	47.5	48.8	48.8	44.6
87.5°	13.0	11.8	12.2	11.7	12.8	12.8	15.6	17.9	18.9	17.3	17.8
90°	21.4	18.0	14.6	11.6	9.0	6.4	3.7	1.2	3.7	6.4	9.0
92.5°	24.9	22.4	19.8	18.9	19.6	20.4	21.1	21.8	21.1	20.4	19.6
95°	30.6	27.8	24.9	28.8	39.5	50.2	60.9	71.6	60.9	50.2	39.5
97.5°	75.3	94.1	112.9	124.6	129.5	134.2	139.1	143.8	139.1	134.2	129.5
100°	120.1	160.8	201.4	219.1	213.9	208.7	203.5	198.2	203.5	208.7	213.9
102.5°	166.0	210.5	254.9	275.3	271.5	267.7	264.0	260.2	264.0	267.7	271.5
105°	303.9	327.3	350.8	361.1	358.2	355.4	352.5	349.6	352.5	355.4	358.2
107.5°	463.5	459.9	456.2	453.1	450.8	448.6	446.3	443.9	446.3	448.6	450.8
110°	523.4	520.6	517.7	515.2	513.1	511.0	509.0	506.9	509.0	511.0	513.1



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	582.6	579.7	576.8	574.4	572.6	570.7	568.8	566.9	568.8	570.7	572.6
115°	668.7	666.4	664.1	662.1	660.6	658.9	657.4	655.9	657.4	658.9	660.6
117.5°	753.7	752.5	751.2	749.7	747.8	745.8	743.9	741.9	743.9	745.8	747.8
120°	808.0	807.2	806.5	804.9	802.5	800.2	797.8	795.5	797.8	800.2	802.5
122.5°	861.1	860.1	859.1	857.7	855.7	853.7	851.8	849.9	851.8	853.7	855.7
125°	936.5	935.4	934.4	932.9	930.8	928.7	926.7	924.5	926.7	928.7	930.8
127.5°	1009.4	1008.0	1006.8	1005.1	1003.1	1001.0	998.9	996.8	998.9	1001.0	1003.1
130°	1053.9	1052.8	1051.8	1050.2	1048.1	1046.0	1044.0	1041.9	1044.0	1046.0	1048.1
132.5°	1096.5	1095.7	1094.8	1093.4	1091.3	1089.2	1087.1	1085.0	1087.1	1089.2	1091.3
135°	1160.6	1159.6	1158.5	1157.2	1155.7	1154.1	1152.6	1150.9	1152.6	1154.1	1155.7
137.5°	1217.7	1217.1	1216.5	1215.3	1213.3	1211.2	1209.3	1207.3	1209.3	1211.2	1213.3
140°	1253.8	1253.0	1252.2	1251.1	1249.5	1248.0	1246.4	1244.9	1246.4	1248.0	1249.5
142.5°	1288.6	1287.8	1287.0	1285.9	1284.2	1282.7	1281.1	1279.6	1281.1	1282.7	1284.2
145°	1337.7	1337.2	1336.7	1335.4	1333.6	1331.8	1330.0	1328.2	1330.0	1331.8	1333.6
147.5°	1380.6	1380.1	1379.6	1378.7	1377.5	1376.3	1375.1	1373.9	1375.1	1376.3	1377.5
150°	1406.8	1406.3	1405.8	1405.2	1404.4	1403.6	1402.8	1402.1	1402.8	1403.6	1404.4
152.5°	1429.9	1429.5	1429.2	1428.9	1428.5	1428.2	1427.7	1427.4	1427.7	1428.2	1428.5
155°	1461.4	1461.1	1460.9	1461.0	1461.5	1462.0	1462.6	1463.1	1462.6	1462.0	1461.5
157.5°	1489.9	1490.2	1490.4	1490.6	1490.6	1490.7	1490.7	1490.8	1490.7	1490.7	1490.6
160°	1505.8	1506.1	1506.3	1506.6	1506.9	1507.1	1507.4	1507.6	1507.4	1507.1	1506.9
162.5°	1519.9	1520.1	1520.5	1520.9	1521.6	1522.3	1523.0	1523.6	1523.0	1522.3	1521.6
165°	1538.6	1538.9	1539.2	1539.7	1540.5	1541.3	1542.1	1542.9	1542.1	1541.3	1540.5
167.5°	1553.2	1553.2	1553.2	1553.7	1554.8	1555.8	1556.8	1557.9	1556.8	1555.8	1554.8
170°	1561.7	1561.7	1561.7	1562.2	1563.2	1564.3	1565.3	1566.3	1565.3	1564.3	1563.2
172.5°	1566.8	1566.6	1566.4	1566.9	1568.2	1569.4	1570.7	1572.0	1570.7	1569.4	1568.2
175°	1574.0	1573.8	1573.5	1574.0	1575.3	1576.6	1577.9	1579.2	1577.9	1576.6	1575.3
177.5°	1576.9	1576.7	1576.5	1576.9	1578.0	1579.0	1580.0	1581.1	1580.0	1579.0	1578.0
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1577.9	1570.7	1565.8	1554.8	1547.7	1539.9	1532.3	1537.2	1536.7	1536.1	1536.1
5°	1525.0	1509.1	1494.8	1476.2	1464.5	1450.1	1439.1	1437.7	1440.5	1430.9	1425.3
7.5°	1472.5	1450.9	1430.5	1410.0	1388.3	1370.9	1360.1	1354.9	1348.0	1342.0	1335.8
10°	1435.6	1410.3	1390.3	1364.8	1341.5	1320.9	1307.9	1298.9	1294.0	1289.3	1280.3
12.5°	1397.8	1372.8	1347.5	1318.7	1296.5	1272.5	1262.7	1252.7	1243.5	1238.1	1225.9
15°	1342.2	1309.9	1283.1	1252.8	1228.1	1204.8	1191.0	1171.0	1168.3	1161.4	1149.1
17.5°	1286.6	1251.4	1214.5	1192.1	1164.2	1139.8	1118.9	1112.3	1092.6	1085.2	1074.4
20°	1242.5	1210.2	1182.0	1152.6	1112.0	1089.2	1072.8	1063.9	1048.0	1038.4	1031.6
22.5°	1204.6	1171.7	1139.2	1104.7	1071.3	1045.8	1033.8	1019.9	1011.2	997.7	990.3
25°	1150.4	1114.7	1075.5	1038.4	1014.4	995.1	975.9	963.5	951.2	944.9	931.2
27.5°	1087.5	1050.2	1013.5	985.3	955.8	936.9	919.4	908.4	893.5	883.1	875.6
30°	1052.9	1008.9	977.2	951.8	914.0	896.2	883.1	869.4	858.4	847.4	839.8
32.5°	1012.7	972.6	942.6	911.2	882.1	862.6	845.8	833.6	824.3	813.9	806.3
35°	949.8	916.1	885.1	853.5	832.2	812.3	792.4	782.0	773.2	763.6	756.7
37.5°	892.8	861.4	832.0	802.0	775.6	759.4	743.4	735.5	723.4	716.9	709.9
40°	857.7	826.8	795.2	766.3	738.8	726.4	712.0	700.3	689.3	684.5	676.9
42.5°	819.2	788.3	761.6	730.5	708.0	691.3	677.9	665.1	656.9	649.8	645.6
45°	762.1	734.7	708.5	677.6	656.3	641.9	626.7	615.1	607.5	602.7	595.1
47.5°	706.8	679.2	652.8	625.8	605.2	588.7	573.6	565.4	555.4	549.6	544.4
50°	666.6	641.9	613.7	589.0	568.4	551.9	539.5	529.2	520.3	512.7	509.3
52.5°	629.8	603.4	579.1	556.0	534.2	515.5	504.3	493.4	486.8	478.1	474.0
55°	569.1	543.6	523.0	500.3	479.0	463.2	449.5	439.8	432.9	423.3	417.9
57.5°	512.0	489.2	464.5	444.9	422.9	409.6	398.2	385.2	376.8	369.2	363.9
60°	473.5	447.4	426.1	407.6	388.3	371.1	360.8	350.5	341.5	334.0	329.2
62.5°	433.3	410.6	390.3	370.1	352.5	337.6	325.6	317.0	309.1	304.3	299.5
65°	371.8	354.0	333.4	316.8	300.3	289.3	279.7	272.2	266.6	263.2	259.1
67.5°	315.2	297.8	279.8	263.7	252.7	244.3	237.9	231.5	228.7	224.3	221.6
70°	278.3	260.4	244.7	232.3	221.3	215.1	211.0	206.2	203.4	197.9	195.2
72.5°	238.2	225.3	213.9	203.7	194.9	189.2	184.0	178.1	173.7	167.6	164.9
75°	187.6	175.9	167.0	160.2	154.6	147.0	139.5	133.3	131.3	129.2	128.6
77.5°	139.0	131.6	125.1	119.3	112.4	106.9	105.3	103.9	103.5	102.4	102.4
80°	109.3	102.4	97.6	90.7	86.5	86.5	86.5	85.2	85.9	85.9	85.9
82.5°	81.2	74.9	72.3	69.8	69.0	69.6	69.6	69.8	69.4	70.5	70.0
85°	41.9	42.6	44.0	43.3	44.0	44.0	45.3	44.6	45.3	44.0	45.3
87.5°	17.7	20.0	21.2	22.4	23.6	23.7	24.5	24.7	25.5	25.8	25.9
90°	11.6	14.6	18.0	21.4	24.7	28.2	29.2	30.2	31.3	32.3	33.1
92.5°	18.9	19.8	22.4	24.9	27.5	30.0	31.7	33.3	35.0	36.8	37.7
95°	28.8	24.9	27.8	30.6	33.5	36.4	38.2	40.0	41.8	43.6	44.5
97.5°	124.6	112.9	94.1	75.3	56.6	37.8	39.9	41.9	44.0	46.2	47.3
100°	219.1	201.4	160.8	120.1	79.4	38.7	40.8	42.9	44.9	47.1	48.3
102.5°	275.3	254.9	210.5	166.0	121.6	77.2	70.7	64.2	57.8	51.3	48.4
105°	361.1	350.8	327.3	303.9	280.4	256.9	210.8	164.6	118.5	72.3	49.6
107.5°	453.1	456.2	459.9	463.5	467.3	471.0	437.1	403.2	369.4	335.6	301.2
110°	515.2	517.7	520.6	523.4	526.2	529.2	520.6	511.9	503.3	494.7	471.8



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	574.4	576.8	579.7	582.6	585.4	588.2	588.4	588.5	588.8	589.0	585.0
115°	662.1	664.1	666.4	668.7	671.2	673.5	676.1	678.6	681.3	683.9	685.7
117.5°	749.7	751.2	752.5	753.7	754.9	756.1	758.1	760.2	762.3	764.4	765.6
120°	804.9	806.5	807.2	808.0	808.8	809.5	811.6	813.7	815.8	817.9	818.9
122.5°	857.7	859.1	860.1	861.1	862.0	863.0	864.5	866.0	867.5	868.9	869.7
125°	932.9	934.4	935.4	936.5	937.6	938.6	939.2	939.7	940.2	940.7	941.2
127.5°	1005.1	1006.8	1008.0	1009.4	1010.6	1011.8	1012.7	1013.5	1014.3	1015.1	1015.3
130°	1050.2	1051.8	1052.8	1053.9	1054.9	1055.9	1057.0	1058.0	1059.0	1060.2	1060.4
132.5°	1093.4	1094.8	1095.7	1096.5	1097.3	1098.2	1099.2	1100.2	1101.4	1102.4	1102.5
135°	1157.2	1158.5	1159.6	1160.6	1161.6	1162.8	1163.5	1164.3	1165.1	1165.9	1165.9
137.5°	1215.3	1216.5	1217.1	1217.7	1218.2	1218.8	1220.0	1221.3	1222.5	1223.8	1224.2
140°	1251.1	1252.2	1253.0	1253.8	1254.7	1255.4	1256.5	1257.5	1258.5	1259.6	1259.8
142.5°	1285.9	1287.0	1287.8	1288.6	1289.4	1290.1	1291.0	1291.8	1292.6	1293.4	1293.5
145°	1335.4	1336.7	1337.2	1337.7	1338.2	1338.7	1339.2	1339.8	1340.3	1340.8	1341.0
147.5°	1378.7	1379.6	1380.1	1380.6	1381.1	1381.6	1382.2	1382.7	1383.2	1383.7	1383.4
150°	1405.2	1405.8	1406.3	1406.8	1407.4	1408.0	1408.5	1409.0	1409.5	1410.0	1409.9
152.5°	1428.9	1429.2	1429.5	1429.9	1430.2	1430.5	1431.4	1432.3	1433.3	1434.2	1434.1
155°	1461.0	1460.9	1461.1	1461.4	1461.7	1461.9	1463.2	1464.5	1465.8	1467.1	1466.9
157.5°	1490.6	1490.4	1490.2	1489.9	1489.7	1489.3	1491.0	1492.5	1494.0	1495.6	1495.4
160°	1506.6	1506.3	1506.1	1505.8	1505.6	1505.3	1506.9	1508.4	1510.0	1511.6	1511.5
162.5°	1520.9	1520.5	1520.1	1519.9	1519.6	1519.3	1521.2	1523.0	1524.7	1526.5	1526.5
165°	1539.7	1539.2	1538.9	1538.6	1538.4	1538.1	1540.2	1542.4	1544.4	1546.5	1546.6
167.5°	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1555.3	1557.3	1559.4	1561.6	1561.6
170°	1562.2	1561.7	1561.7	1561.7	1561.7	1561.7	1563.7	1565.8	1567.9	1569.9	1569.9
172.5°	1566.9	1566.4	1566.6	1566.8	1567.0	1567.2	1569.3	1571.5	1573.5	1575.6	1575.5
175°	1574.0	1573.5	1573.8	1574.0	1574.3	1574.5	1576.4	1578.2	1580.0	1581.9	1581.7
177.5°	1576.9	1576.5	1576.7	1576.9	1577.1	1577.3	1579.0	1580.6	1582.4	1584.0	1583.8
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1529.5	1528.9	1529.5	1527.3	1529.5	1528.9	1529.5	1536.1	1536.1	1536.7	1537.2
5°	1423.3	1422.6	1420.6	1414.3	1420.6	1422.6	1423.3	1425.3	1430.9	1440.5	1437.7
7.5°	1330.5	1329.6	1323.5	1323.6	1323.5	1329.6	1330.5	1335.8	1342.0	1348.0	1354.9
10°	1275.6	1276.2	1268.0	1263.1	1268.0	1276.2	1275.6	1280.3	1289.3	1294.0	1298.9
12.5°	1222.2	1219.0	1212.4	1207.1	1212.4	1219.0	1222.2	1225.9	1238.1	1243.5	1252.7
15°	1151.9	1145.0	1128.4	1129.8	1128.4	1145.0	1151.9	1149.1	1161.4	1168.3	1171.0
17.5°	1068.9	1063.9	1063.6	1054.0	1063.6	1063.9	1068.9	1074.4	1085.2	1092.6	1112.3
20°	1020.6	1017.1	1018.4	1008.9	1018.4	1017.1	1020.6	1031.6	1038.4	1048.0	1063.9
22.5°	982.6	979.2	973.4	970.4	973.4	979.2	982.6	990.3	997.7	1011.2	1019.9
25°	927.1	921.6	916.1	919.6	916.1	921.6	927.1	931.2	944.9	951.2	963.5
27.5°	871.6	867.5	861.9	861.2	861.9	867.5	871.6	875.6	883.1	893.5	908.4
30°	836.4	832.2	829.5	826.1	829.5	832.2	836.4	839.8	847.4	858.4	869.4
32.5°	800.6	799.8	794.9	794.2	794.9	799.8	800.6	806.3	813.9	824.3	833.6
35°	753.9	749.8	748.4	749.1	748.4	749.8	753.9	756.7	763.6	773.2	782.0
37.5°	709.5	704.0	701.6	699.0	701.6	704.0	709.5	709.9	716.9	723.4	735.5
40°	677.6	672.2	670.8	669.3	670.8	672.2	677.6	676.9	684.5	689.3	700.3
42.5°	641.9	639.6	638.8	636.4	638.8	639.6	641.9	645.6	649.8	656.9	665.1
45°	593.1	592.4	588.2	589.7	588.2	592.4	593.1	595.1	602.7	607.5	615.1
47.5°	541.7	538.7	535.7	537.7	535.7	538.7	541.7	544.4	549.6	555.4	565.4
50°	506.5	505.1	499.0	500.3	499.0	505.1	506.5	509.3	512.7	520.3	529.2
52.5°	471.3	466.1	463.7	462.9	463.7	466.1	471.3	474.0	478.1	486.8	493.4
55°	413.0	406.9	404.1	402.7	404.1	406.9	413.0	417.9	423.3	432.9	439.8
57.5°	355.9	354.2	352.0	353.6	352.0	354.2	355.9	363.9	369.2	376.8	385.2
60°	322.3	322.3	322.3	321.6	322.3	322.3	322.3	329.2	334.0	341.5	350.5
62.5°	296.5	294.8	294.3	295.3	294.3	294.8	296.5	299.5	304.3	309.1	317.0
65°	257.0	256.3	253.6	252.9	253.6	256.3	257.0	259.1	263.2	266.6	272.2
67.5°	219.7	217.3	216.5	215.5	216.5	217.3	219.7	221.6	224.3	228.7	231.5
70°	191.8	190.4	186.2	186.9	186.2	190.4	191.8	195.2	197.9	203.4	206.2
72.5°	161.5	160.2	159.3	158.3	159.3	160.2	161.5	164.9	167.6	173.7	178.1
75°	127.8	127.1	126.4	129.2	126.4	127.1	127.8	128.6	129.2	131.3	133.3
77.5°	102.4	102.4	102.8	101.7	102.8	102.4	102.4	102.4	102.4	103.5	103.9
80°	85.9	85.9	85.2	85.2	85.2	85.9	85.9	85.9	85.9	85.9	85.2
82.5°	68.9	69.4	69.8	68.8	69.8	69.4	68.9	70.0	70.5	69.4	69.8
85°	45.3	44.6	46.0	45.3	46.0	44.6	45.3	45.3	44.0	45.3	44.6
87.5°	27.1	26.1	26.2	26.9	26.2	26.1	27.1	25.9	25.8	25.5	24.7
90°	33.6	34.1	34.6	35.2	34.6	34.1	33.6	33.1	32.3	31.3	30.2
92.5°	38.0	38.4	38.7	39.0	38.7	38.4	38.0	37.7	36.8	35.0	33.3
95°	44.5	44.5	44.5	44.5	44.5	44.5	44.5	44.5	43.6	41.8	40.0
97.5°	47.6	47.9	48.1	48.4	48.1	47.9	47.6	47.3	46.2	44.0	41.9
100°	48.5	48.8	49.0	49.3	49.0	48.8	48.5	48.3	47.1	44.9	42.9
102.5°	48.8	49.3	49.8	50.2	49.8	49.3	48.8	48.4	51.3	57.8	64.2
105°	50.1	50.6	51.1	51.6	51.1	50.6	50.1	49.6	72.3	118.5	164.6
107.5°	266.5	231.7	196.9	162.2	196.9	231.7	266.5	301.2	335.6	369.4	403.2
110°	434.5	397.2	359.9	322.7	359.9	397.2	434.5	471.8	494.7	503.3	511.9



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	577.1	569.3	561.4	553.5	561.4	569.3	577.1	585.0	589.0	588.8	588.5
115°	686.7	687.8	688.8	689.8	688.8	687.8	686.7	685.7	683.9	681.3	678.6
117.5°	765.8	766.0	766.2	766.4	766.2	766.0	765.8	765.6	764.4	762.3	760.2
120°	818.9	818.9	818.9	818.9	818.9	818.9	818.9	818.9	817.9	815.8	813.7
122.5°	869.9	870.1	870.4	870.6	870.4	870.1	869.9	869.7	868.9	867.5	866.0
125°	941.7	942.3	942.8	943.3	942.8	942.3	941.7	941.2	940.7	940.2	939.7
127.5°	1014.8	1014.3	1013.8	1013.2	1013.8	1014.3	1014.8	1015.3	1015.1	1014.3	1013.5
130°	1059.9	1059.3	1058.8	1058.3	1058.8	1059.3	1059.9	1060.4	1060.2	1059.0	1058.0
132.5°	1101.8	1101.1	1100.3	1099.5	1100.3	1101.1	1101.8	1102.5	1102.4	1101.4	1100.2
135°	1165.1	1164.3	1163.5	1162.8	1163.5	1164.3	1165.1	1165.9	1165.9	1165.1	1164.3
137.5°	1223.7	1223.1	1222.6	1222.0	1222.6	1223.1	1223.7	1224.2	1223.8	1222.5	1221.3
140°	1259.3	1258.8	1258.3	1257.8	1258.3	1258.8	1259.3	1259.8	1259.6	1258.5	1257.5
142.5°	1292.8	1292.0	1291.3	1290.6	1291.3	1292.0	1292.8	1293.5	1293.4	1292.6	1291.8
145°	1341.0	1341.0	1341.0	1341.0	1341.0	1341.0	1341.0	1341.0	1340.8	1340.3	1339.8
147.5°	1382.2	1381.0	1379.8	1378.6	1379.8	1381.0	1382.2	1383.4	1383.7	1383.2	1382.7
150°	1409.1	1408.4	1407.5	1406.7	1407.5	1408.4	1409.1	1409.9	1410.0	1409.5	1409.0
152.5°	1432.9	1431.7	1430.5	1429.3	1430.5	1431.7	1432.9	1434.1	1434.2	1433.3	1432.3
155°	1465.4	1463.9	1462.3	1460.8	1462.3	1463.9	1465.4	1466.9	1467.1	1465.8	1464.5
157.5°	1493.4	1491.3	1489.2	1487.2	1489.2	1491.3	1493.4	1495.4	1495.6	1494.0	1492.5
160°	1509.6	1507.8	1505.9	1504.1	1505.9	1507.8	1509.6	1511.5	1511.6	1510.0	1508.4
162.5°	1524.9	1523.3	1521.7	1520.0	1521.7	1523.3	1524.9	1526.5	1526.5	1524.7	1523.0
165°	1544.8	1543.0	1541.2	1539.3	1541.2	1543.0	1544.8	1546.6	1546.5	1544.4	1542.4
167.5°	1559.4	1557.3	1555.3	1553.2	1555.3	1557.3	1559.4	1561.6	1561.6	1559.4	1557.3
170°	1567.9	1565.8	1563.7	1561.7	1563.7	1565.8	1567.9	1569.9	1569.9	1567.9	1565.8
172.5°	1573.2	1570.9	1568.6	1566.3	1568.6	1570.9	1573.2	1575.5	1575.6	1573.5	1571.5
175°	1579.6	1577.5	1575.5	1573.4	1575.5	1577.5	1579.6	1581.7	1581.9	1580.0	1578.2
177.5°	1581.8	1579.6	1577.5	1575.5	1577.5	1579.6	1581.8	1583.8	1584.0	1582.4	1580.6
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1532.3	1539.9	1547.7	1554.8	1565.8	1570.7	1577.9	1580.6	1588.9	1601.0	1610.9
5°	1439.1	1450.1	1464.5	1476.2	1494.8	1509.1	1525.0	1540.1	1558.0	1583.4	1606.1
7.5°	1360.1	1370.9	1388.3	1410.0	1430.5	1450.9	1472.5	1493.1	1518.6	1555.1	1591.2
10°	1307.9	1320.9	1341.5	1364.8	1390.3	1410.3	1435.6	1461.8	1493.4	1535.3	1578.6
12.5°	1262.7	1272.5	1296.5	1318.7	1347.5	1372.8	1397.8	1428.3	1464.2	1508.9	1561.0
15°	1191.0	1204.8	1228.1	1252.8	1283.1	1309.9	1342.2	1379.3	1414.3	1469.4	1532.6
17.5°	1118.9	1139.8	1164.2	1192.1	1214.5	1251.4	1286.6	1324.6	1367.8	1426.0	1495.4
20°	1072.8	1089.2	1112.0	1152.6	1182.0	1210.2	1242.5	1290.0	1329.8	1395.8	1467.9
22.5°	1033.8	1045.8	1071.3	1104.7	1139.2	1171.7	1204.6	1249.8	1299.0	1361.7	1440.0
25°	975.9	995.1	1014.4	1038.4	1075.5	1114.7	1150.4	1188.9	1241.1	1307.9	1392.4
27.5°	919.4	936.9	955.8	985.3	1013.5	1050.2	1087.5	1131.7	1187.7	1258.2	1343.9
30°	883.1	896.2	914.0	951.8	977.2	1008.9	1052.9	1092.1	1144.3	1219.2	1309.9
32.5°	845.8	862.6	882.1	911.2	942.6	972.6	1012.7	1055.2	1108.5	1182.3	1275.3
35°	792.4	812.3	832.2	853.5	885.1	916.1	949.8	996.5	1050.8	1122.3	1213.7
37.5°	743.4	759.4	775.6	802.0	832.0	861.4	892.8	938.9	990.1	1067.1	1151.0
40°	712.0	726.4	738.8	766.3	795.2	826.8	857.7	898.3	953.2	1025.4	1106.5
42.5°	677.9	691.3	708.0	730.5	761.6	788.3	819.2	857.6	909.2	982.5	1053.7
45°	626.7	641.9	656.3	677.6	708.5	734.7	762.1	798.6	851.5	912.0	975.2
47.5°	573.6	588.7	605.2	625.8	652.8	679.2	706.8	739.0	787.3	846.7	889.3
50°	539.5	551.9	568.4	589.0	613.7	641.9	666.6	701.7	747.7	794.5	831.5
52.5°	504.3	515.5	534.2	556.0	579.1	603.4	629.8	659.8	701.6	745.5	775.0
55°	449.5	463.2	479.0	500.3	523.0	543.6	569.1	600.0	633.0	665.9	685.9
57.5°	398.2	409.6	422.9	444.9	464.5	489.2	512.0	536.0	566.5	591.5	604.5
60°	360.8	371.1	388.3	407.6	426.1	447.4	473.5	497.6	520.9	540.9	551.2
62.5°	325.6	337.6	352.5	370.1	390.3	410.6	433.3	453.6	474.2	491.4	498.4
65°	279.7	289.3	300.3	316.8	333.4	354.0	371.8	392.4	407.6	417.2	423.3
67.5°	237.9	244.3	252.7	263.7	279.8	297.8	315.2	331.2	343.9	350.5	356.0
70°	211.0	215.1	221.3	232.3	244.7	260.4	278.3	290.0	301.0	306.5	312.0
72.5°	184.0	189.2	194.9	203.7	213.9	225.3	238.2	252.7	258.7	265.3	268.6
75°	139.5	147.0	154.6	160.2	167.0	175.9	187.6	196.5	200.0	205.5	206.2
77.5°	105.3	106.9	112.4	119.3	125.1	131.6	139.0	146.9	148.6	151.5	153.3
80°	86.5	86.5	86.5	90.7	97.6	102.4	109.3	113.4	116.1	116.8	117.5
82.5°	69.6	69.6	69.0	69.8	72.3	74.9	81.2	85.9	88.1	87.7	86.1
85°	45.3	44.0	44.0	43.3	44.0	42.6	41.9	44.6	48.8	48.8	47.5
87.5°	24.5	23.7	23.6	22.4	21.2	20.0	17.7	17.8	17.3	18.9	17.9
90°	29.2	28.2	24.7	21.4	18.0	14.6	11.6	9.0	6.4	3.7	1.2
92.5°	31.7	30.0	27.5	24.9	22.4	19.8	18.9	19.6	20.4	21.1	21.8
95°	38.2	36.4	33.5	30.6	27.8	24.9	28.8	39.5	50.2	60.9	71.6
97.5°	39.9	37.8	56.6	75.3	94.1	112.9	124.6	129.5	134.2	139.1	143.8
100°	40.8	38.7	79.4	120.1	160.8	201.4	219.1	213.9	208.7	203.5	198.2
102.5°	70.7	77.2	121.6	166.0	210.5	254.9	275.3	271.5	267.7	264.0	260.2
105°	210.8	256.9	280.4	303.9	327.3	350.8	361.1	358.2	355.4	352.5	349.6
107.5°	437.1	471.0	467.3	463.5	459.9	456.2	453.1	450.8	448.6	446.3	443.9
110°	520.6	529.2	526.2	523.4	520.6	517.7	515.2	513.1	511.0	509.0	506.9



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	588.4	588.2	585.4	582.6	579.7	576.8	574.4	572.6	570.7	568.8	566.9
115°	676.1	673.5	671.2	668.7	666.4	664.1	662.1	660.6	658.9	657.4	655.9
117.5°	758.1	756.1	754.9	753.7	752.5	751.2	749.7	747.8	745.8	743.9	741.9
120°	811.6	809.5	808.8	808.0	807.2	806.5	804.9	802.5	800.2	797.8	795.5
122.5°	864.5	863.0	862.0	861.1	860.1	859.1	857.7	855.7	853.7	851.8	849.9
125°	939.2	938.6	937.6	936.5	935.4	934.4	932.9	930.8	928.7	926.7	924.5
127.5°	1012.7	1011.8	1010.6	1009.4	1008.0	1006.8	1005.1	1003.1	1001.0	998.9	996.8
130°	1057.0	1055.9	1054.9	1053.9	1052.8	1051.8	1050.2	1048.1	1046.0	1044.0	1041.9
132.5°	1099.2	1098.2	1097.3	1096.5	1095.7	1094.8	1093.4	1091.3	1089.2	1087.1	1085.0
135°	1163.5	1162.8	1161.6	1160.6	1159.6	1158.5	1157.2	1155.7	1154.1	1152.6	1150.9
137.5°	1220.0	1218.8	1218.2	1217.7	1217.1	1216.5	1215.3	1213.3	1211.2	1209.3	1207.3
140°	1256.5	1255.4	1254.7	1253.8	1253.0	1252.2	1251.1	1249.5	1248.0	1246.4	1244.9
142.5°	1291.0	1290.1	1289.4	1288.6	1287.8	1287.0	1285.9	1284.2	1282.7	1281.1	1279.6
145°	1339.2	1338.7	1338.2	1337.7	1337.2	1336.7	1335.4	1333.6	1331.8	1330.0	1328.2
147.5°	1382.2	1381.6	1381.1	1380.6	1380.1	1379.6	1378.7	1377.5	1376.3	1375.1	1373.9
150°	1408.5	1408.0	1407.4	1406.8	1406.3	1405.8	1405.2	1404.4	1403.6	1402.8	1402.1
152.5°	1431.4	1430.5	1430.2	1429.9	1429.5	1429.2	1428.9	1428.5	1428.2	1427.7	1427.4
155°	1463.2	1461.9	1461.7	1461.4	1461.1	1460.9	1461.0	1461.5	1462.0	1462.6	1463.1
157.5°	1491.0	1489.3	1489.7	1489.9	1490.2	1490.4	1490.6	1490.6	1490.7	1490.7	1490.8
160°	1506.9	1505.3	1505.6	1505.8	1506.1	1506.3	1506.6	1506.9	1507.1	1507.4	1507.6
162.5°	1521.2	1519.3	1519.6	1519.9	1520.1	1520.5	1520.9	1521.6	1522.3	1523.0	1523.6
165°	1540.2	1538.1	1538.4	1538.6	1538.9	1539.2	1539.7	1540.5	1541.3	1542.1	1542.9
167.5°	1555.3	1553.2	1553.2	1553.2	1553.2	1553.2	1553.7	1554.8	1555.8	1556.8	1557.9
170°	1563.7	1561.7	1561.7	1561.7	1561.7	1561.7	1562.2	1563.2	1564.3	1565.3	1566.3
172.5°	1569.3	1567.2	1567.0	1566.8	1566.6	1566.4	1566.9	1568.2	1569.4	1570.7	1572.0
175°	1576.4	1574.5	1574.3	1574.0	1573.8	1573.5	1574.0	1575.3	1576.6	1577.9	1579.2
177.5°	1579.0	1577.3	1577.1	1576.9	1576.7	1576.5	1576.9	1578.0	1579.0	1580.0	1581.1
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1614.2	1620.2	1627.9	1639.5	1648.3	1656.0	1657.6	1659.8	1665.4	1674.7	1681.8
5°	1624.7	1640.4	1665.9	1690.6	1717.5	1739.4	1760.0	1774.4	1788.2	1817.1	1840.5
7.5°	1621.3	1656.6	1696.4	1740.8	1785.7	1829.3	1869.8	1905.9	1941.9	1984.0	2031.9
10°	1619.1	1660.4	1713.9	1771.0	1833.6	1894.7	1953.9	1999.9	2053.5	2101.6	2162.7
12.5°	1608.7	1668.1	1732.1	1805.1	1882.0	1952.5	2030.2	2093.9	2155.3	2224.7	2295.8
15°	1595.1	1667.3	1748.4	1845.2	1962.1	2047.3	2127.0	2237.7	2313.3	2388.8	2490.6
17.5°	1570.2	1658.3	1759.6	1885.5	1983.0	2097.5	2217.5	2304.9	2406.7	2513.3	2605.4
20°	1550.4	1652.8	1766.3	1890.0	2014.3	2138.7	2254.8	2359.3	2464.5	2587.5	2663.1
22.5°	1530.7	1631.9	1749.7	1881.2	2014.9	2145.9	2277.3	2400.0	2518.3	2642.4	2739.0
25°	1488.5	1608.8	1736.7	1870.7	2002.7	2147.0	2303.6	2440.4	2586.8	2714.6	2806.0
27.5°	1445.9	1556.2	1683.4	1819.4	1966.1	2136.7	2321.0	2476.4	2623.1	2714.6	2743.4
30°	1407.4	1524.3	1641.1	1779.3	1938.0	2128.4	2324.3	2502.2	2622.5	2662.4	2632.8
32.5°	1368.5	1474.3	1590.0	1731.4	1900.1	2108.1	2328.6	2486.9	2559.3	2528.8	2408.5
35°	1299.6	1395.1	1507.1	1648.7	1842.5	2096.8	2310.6	2417.7	2399.8	2228.1	2001.2
37.5°	1225.9	1303.7	1407.4	1555.5	1782.8	2052.1	2232.4	2248.3	2093.7	1829.9	1567.9
40°	1167.6	1237.7	1344.2	1498.8	1736.7	2008.1	2153.8	2089.9	1850.1	1556.6	1338.1
42.5°	1111.0	1170.1	1272.7	1439.5	1692.7	1948.2	2036.7	1897.5	1620.8	1343.3	1144.6
45°	1015.0	1070.8	1173.8	1344.9	1602.7	1833.6	1821.9	1579.9	1303.0	1079.6	914.7
47.5°	924.0	972.7	1069.4	1244.2	1496.9	1661.7	1552.5	1295.1	1060.2	880.9	763.3
50°	859.7	907.9	1004.1	1176.6	1412.3	1532.6	1376.5	1128.4	913.3	764.9	671.5
52.5°	798.2	845.2	933.1	1101.3	1310.0	1381.9	1214.4	984.4	805.1	676.9	596.6
55°	712.0	747.7	826.8	987.5	1143.6	1160.0	990.3	797.9	650.2	560.8	505.8
57.5°	624.2	654.9	733.1	861.1	970.5	962.0	801.0	634.6	535.1	468.7	428.9
60°	566.9	597.2	665.9	775.9	858.4	829.5	681.8	547.8	462.5	413.7	382.1
62.5°	513.6	537.2	601.6	681.9	741.2	708.5	582.8	471.9	404.2	363.1	338.1
65°	436.4	455.7	507.2	549.1	582.1	550.5	446.1	369.0	320.2	291.3	274.2
67.5°	363.0	375.3	407.8	422.9	446.2	411.5	335.4	283.9	256.1	231.8	219.7
70°	316.8	325.8	343.0	355.3	361.5	325.8	269.4	231.6	208.2	191.1	183.5
72.5°	270.6	278.5	282.0	292.1	288.9	255.4	216.6	186.5	169.8	158.0	148.3
75°	206.8	210.3	206.8	202.8	193.8	170.5	143.6	128.6	116.1	110.7	107.2
77.5°	150.8	149.7	145.0	138.6	123.3	108.6	94.1	89.1	83.7	80.8	79.6
80°	116.1	113.4	109.3	99.0	85.9	75.6	72.2	68.8	66.7	63.2	62.5
82.5°	86.4	84.8	78.0	69.3	60.1	55.2	52.4	51.1	49.1	47.3	47.2
85°	46.0	44.0	36.5	31.6	30.2	28.9	28.2	28.2	25.4	24.7	24.7
87.5°	15.6	12.8	12.8	11.7	12.2	11.8	13.0	12.6	12.8	13.5	12.6
90°	3.7	6.4	9.0	11.6	14.6	18.0	21.4	24.7	28.2	29.2	30.2
92.5°	21.1	20.4	19.6	18.9	19.8	22.4	24.9	27.5	30.0	31.7	33.3
95°	60.9	50.2	39.5	28.8	24.9	27.8	30.6	33.5	36.4	38.2	40.0
97.5°	139.1	134.2	129.5	124.6	112.9	94.1	75.3	56.6	37.8	39.9	41.9
100°	203.5	208.7	213.9	219.1	201.4	160.8	120.1	79.4	38.7	40.8	42.9
102.5°	264.0	267.7	271.5	275.3	254.9	210.5	166.0	121.6	77.2	70.7	64.2
105°	352.5	355.4	358.2	361.1	350.8	327.3	303.9	280.4	256.9	210.8	164.6
107.5°	446.3	448.6	450.8	453.1	456.2	459.9	463.5	467.3	471.0	437.1	403.2
110°	509.0	511.0	513.1	515.2	517.7	520.6	523.4	526.2	529.2	520.6	511.9



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	568.8	570.7	572.6	574.4	576.8	579.7	582.6	585.4	588.2	588.4	588.5
115°	657.4	658.9	660.6	662.1	664.1	666.4	668.7	671.2	673.5	676.1	678.6
117.5°	743.9	745.8	747.8	749.7	751.2	752.5	753.7	754.9	756.1	758.1	760.2
120°	797.8	800.2	802.5	804.9	806.5	807.2	808.0	808.8	809.5	811.6	813.7
122.5°	851.8	853.7	855.7	857.7	859.1	860.1	861.1	862.0	863.0	864.5	866.0
125°	926.7	928.7	930.8	932.9	934.4	935.4	936.5	937.6	938.6	939.2	939.7
127.5°	998.9	1001.0	1003.1	1005.1	1006.8	1008.0	1009.4	1010.6	1011.8	1012.7	1013.5
130°	1044.0	1046.0	1048.1	1050.2	1051.8	1052.8	1053.9	1054.9	1055.9	1057.0	1058.0
132.5°	1087.1	1089.2	1091.3	1093.4	1094.8	1095.7	1096.5	1097.3	1098.2	1099.2	1100.2
135°	1152.6	1154.1	1155.7	1157.2	1158.5	1159.6	1160.6	1161.6	1162.8	1163.5	1164.3
137.5°	1209.3	1211.2	1213.3	1215.3	1216.5	1217.1	1217.7	1218.2	1218.8	1220.0	1221.3
140°	1246.4	1248.0	1249.5	1251.1	1252.2	1253.0	1253.8	1254.7	1255.4	1256.5	1257.5
142.5°	1281.1	1282.7	1284.2	1285.9	1287.0	1287.8	1288.6	1289.4	1290.1	1291.0	1291.8
145°	1330.0	1331.8	1333.6	1335.4	1336.7	1337.2	1337.7	1338.2	1338.7	1339.2	1339.8
147.5°	1375.1	1376.3	1377.5	1378.7	1379.6	1380.1	1380.6	1381.1	1381.6	1382.2	1382.7
150°	1402.8	1403.6	1404.4	1405.2	1405.8	1406.3	1406.8	1407.4	1408.0	1408.5	1409.0
152.5°	1427.7	1428.2	1428.5	1428.9	1429.2	1429.5	1429.9	1430.2	1430.5	1431.4	1432.3
155°	1462.6	1462.0	1461.5	1461.0	1460.9	1461.1	1461.4	1461.7	1461.9	1463.2	1464.5
157.5°	1490.7	1490.7	1490.6	1490.6	1490.4	1490.2	1489.9	1489.7	1489.3	1491.0	1492.5
160°	1507.4	1507.1	1506.9	1506.6	1506.3	1506.1	1505.8	1505.6	1505.3	1506.9	1508.4
162.5°	1523.0	1522.3	1521.6	1520.9	1520.5	1520.1	1519.9	1519.6	1519.3	1521.2	1523.0
165°	1542.1	1541.3	1540.5	1539.7	1539.2	1538.9	1538.6	1538.4	1538.1	1540.2	1542.4
167.5°	1556.8	1555.8	1554.8	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1555.3	1557.3
170°	1565.3	1564.3	1563.2	1562.2	1561.7	1561.7	1561.7	1561.7	1561.7	1563.7	1565.8
172.5°	1570.7	1569.4	1568.2	1566.9	1566.4	1566.6	1566.8	1567.0	1567.2	1569.3	1571.5
175°	1577.9	1576.6	1575.3	1574.0	1573.5	1573.8	1574.0	1574.3	1574.5	1576.4	1578.2
177.5°	1580.0	1579.0	1578.0	1576.9	1576.5	1576.7	1576.9	1577.1	1577.3	1579.0	1580.6
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1693.3	1693.3	1695.6	1703.8	1705.0	1712.0	1709.9
5°	1861.1	1874.1	1879.0	1899.6	1911.9	1917.4	1906.4
7.5°	2066.2	2102.9	2120.4	2142.0	2161.1	2166.9	2151.9
10°	2215.6	2254.1	2286.4	2306.4	2324.9	2337.3	2353.1
12.5°	2360.3	2407.5	2438.2	2466.4	2485.5	2501.1	2503.8
15°	2517.4	2588.9	2643.1	2683.0	2702.9	2713.2	2709.2
17.5°	2675.8	2742.1	2780.8	2821.5	2849.0	2850.4	2851.3
20°	2765.5	2830.0	2874.8	2905.0	2935.9	2934.6	2941.4
22.5°	2825.4	2876.3	2910.5	2932.4	2943.0	2937.8	2939.2
25°	2853.5	2868.5	2862.4	2827.3	2818.4	2786.1	2791.6
27.5°	2708.9	2637.4	2563.4	2468.3	2393.3	2333.3	2336.3
30°	2512.5	2386.1	2241.8	2120.8	2012.3	1982.1	1917.4
32.5°	2238.3	2048.5	1879.5	1766.8	1673.5	1648.3	1592.0
35°	1773.1	1588.9	1415.0	1310.6	1269.3	1211.6	1210.9
37.5°	1378.2	1216.0	1124.1	1045.7	1004.6	969.7	966.2
40°	1159.4	1032.9	963.5	907.2	866.7	840.5	834.4
42.5°	1006.5	904.2	839.3	804.4	773.2	759.7	749.6
45°	821.9	753.3	707.8	676.2	661.9	651.5	646.0
47.5°	687.5	641.5	610.6	589.6	577.8	566.9	569.9
50°	614.4	576.6	553.9	534.0	525.0	517.5	518.2
52.5°	555.5	521.6	503.3	488.9	477.8	472.4	469.8
55°	471.4	450.1	431.6	421.3	415.1	407.6	405.5
57.5°	402.1	385.7	370.5	358.9	357.4	350.1	351.0
60°	356.0	342.2	329.9	323.7	318.9	312.7	314.8
62.5°	318.1	306.5	295.3	290.1	285.4	280.8	281.8
65°	260.4	249.4	242.6	239.8	237.8	235.7	233.7
67.5°	207.5	200.9	196.5	190.7	186.4	185.7	183.6
70°	174.6	165.6	158.0	150.5	148.5	147.7	148.5
72.5°	140.0	134.3	132.2	128.6	128.2	126.3	127.5
75°	105.1	103.1	101.7	99.0	99.0	99.0	99.0
77.5°	77.6	76.2	75.4	74.9	74.2	73.2	73.1
80°	60.5	59.8	58.4	58.4	57.8	58.4	57.8
82.5°	45.6	45.5	44.1	44.1	43.4	43.0	43.4
85°	23.3	22.7	24.0	22.7	23.3	22.0	23.3
87.5°	12.8	13.0	12.6	12.7	12.3	13.5	12.5
90°	31.3	32.3	33.1	33.6	34.1	34.6	35.2
92.5°	35.0	36.8	37.7	38.0	38.4	38.7	39.0
95°	41.8	43.6	44.5	44.5	44.5	44.5	44.5
97.5°	44.0	46.2	47.3	47.6	47.9	48.1	48.4
100°	44.9	47.1	48.3	48.5	48.8	49.0	49.3
102.5°	57.8	51.3	48.4	48.8	49.3	49.8	50.2
105°	118.5	72.3	49.6	50.1	50.6	51.1	51.6
107.5°	369.4	335.6	301.2	266.5	231.7	196.9	162.2
110°	503.3	494.7	471.8	434.5	397.2	359.9	322.7



TEST NUMBER: P332354-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	588.8	589.0	585.0	577.1	569.3	561.4	553.5
115°	681.3	683.9	685.7	686.7	687.8	688.8	689.8
117.5°	762.3	764.4	765.6	765.8	766.0	766.2	766.4
120°	815.8	817.9	818.9	818.9	818.9	818.9	818.9
122.5°	867.5	868.9	869.7	869.9	870.1	870.4	870.6
125°	940.2	940.7	941.2	941.7	942.3	942.8	943.3
127.5°	1014.3	1015.1	1015.3	1014.8	1014.3	1013.8	1013.2
130°	1059.0	1060.2	1060.4	1059.9	1059.3	1058.8	1058.3
132.5°	1101.4	1102.4	1102.5	1101.8	1101.1	1100.3	1099.5
135°	1165.1	1165.9	1165.9	1165.1	1164.3	1163.5	1162.8
137.5°	1222.5	1223.8	1224.2	1223.7	1223.1	1222.6	1222.0
140°	1258.5	1259.6	1259.8	1259.3	1258.8	1258.3	1257.8
142.5°	1292.6	1293.4	1293.5	1292.8	1292.0	1291.3	1290.6
145°	1340.3	1340.8	1341.0	1341.0	1341.0	1341.0	1341.0
147.5°	1383.2	1383.7	1383.4	1382.2	1381.0	1379.8	1378.6
150°	1409.5	1410.0	1409.9	1409.1	1408.4	1407.5	1406.7
152.5°	1433.3	1434.2	1434.1	1432.9	1431.7	1430.5	1429.3
155°	1465.8	1467.1	1466.9	1465.4	1463.9	1462.3	1460.8
157.5°	1494.0	1495.6	1495.4	1493.4	1491.3	1489.2	1487.2
160°	1510.0	1511.6	1511.5	1509.6	1507.8	1505.9	1504.1
162.5°	1524.7	1526.5	1526.5	1524.9	1523.3	1521.7	1520.0
165°	1544.4	1546.5	1546.6	1544.8	1543.0	1541.2	1539.3
167.5°	1559.4	1561.6	1561.6	1559.4	1557.3	1555.3	1553.2
170°	1567.9	1569.9	1569.9	1567.9	1565.8	1563.7	1561.7
172.5°	1573.5	1575.6	1575.5	1573.2	1570.9	1568.6	1566.3
175°	1580.0	1581.9	1581.7	1579.6	1577.5	1575.5	1573.4
177.5°	1582.4	1584.0	1583.8	1581.8	1579.6	1577.5	1575.5
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2

(END OF REPORT)