

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332362

Luminaire Tested: **S123RDIP-S1165D365U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332362  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D365U835-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5886.1 lumens  
Efficiency: N/A  
Efficacy: 118.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	82	82	82	78																				
1	105	101	97	94	100	96	93	90	88	86	83	81	79	77	74	72	71	67																				
2	96	89	83	78	92	85	80	75	78	74	70	72	69	66	66	63	61	58																				
3	88	79	72	66	84	76	69	64	70	65	60	64	60	57	59	56	53	50																				
4	81	71	63	57	78	68	61	55	63	57	52	58	53	49	53	50	46	44																				
5	75	64	56	50	72	61	54	48	57	51	46	53	47	43	49	44	41	38																				
6	70	58	50	44	66	56	48	43	52	45	41	48	43	39	44	40	37	34																				
7	65	52	44	39	62	51	43	38	47	41	36	44	38	35	41	36	33	31																				
8	60	48	40	35	58	46	39	34	43	37	33	40	35	31	38	33	30	28																				
9	56	44	37	31	54	43	36	31	40	34	29	37	32	28	35	30	27	25																				
10	53	41	33	29	51	39	33	28	37	31	27	35	29	26	32	28	25	23																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	19763	19763	19763	19763
5°	23558	19847	17477	19847
10°	29415	19733	15789	19733
15°	34526	19531	14399	19531
20°	38533	19230	13216	19230
25°	37917	18912	12490	18912
30°	27256	18620	11742	18620
35°	18198	18239	11257	18239
40°	13408	17781	10756	17781
45°	11246	16978	10266	16978
50°	9923	15925	9582	15925
55°	8702	14720	8644	14720
60°	7750	13569	7918	13569
65°	6805	12332	7366	12332
70°	5344	11229	6729	11229
75°	4708	9807	6147	9807
80°	4091	8331	6044	8331
85°	3298	6694	6410	6694



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.6	3.1
10°-20°	564.1	9.6
20°-30°	886.2	15.1
30°-40°	924.6	15.7
40°-50°	791.2	13.4
50°-60°	603.1	10.2
60°-70°	386.5	6.6
70°-80°	186.0	3.2
80°-90°	50.6	0.9
90°-100°	97.2	1.7
100°-110°	275.1	4.7
110°-120°	270.6	4.6
120°-130°	215.9	3.7
130°-140°	170.2	2.9
140°-150°	127.0	2.2
150°-160°	88.5	1.5
160°-170°	52.0	0.9
170°-180°	16.9	0.3
0°-30°	1630.8	27.7
0°-40°	2555.4	43.4
0°-60°	3949.7	67.1
0°-90°	4572.7	77.7
90°-120°	642.9	10.9
90°-150°	1155.9	19.6
90°-180°	1313.0	22.3
0°-180°	5886.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1836	1836	1836	1836	1836	
5°	2180	1837	1618	1837	2180	225
15°	3098	1753	1292	1753	3098	879
25°	3193	1592	1052	1592	3193	1372
35°	1385	1388	857	1388	1385	908
45°	739	1115	674	1115	739	581
55°	464	784	461	784	464	419
65°	267	484	289	484	267	263
75°	113	236	148	236	113	121
85°	27	54	52	54	27	31
90°	10	1	10	1	10	6
95°	41	12	41	12	41	74
105°	450	41	450	41	450	443
115°	547	72	547	72	547	531
125°	431	101	431	101	431	391
135°	350	118	350	118	350	271
145°	273	135	273	135	273	174
155°	226	153	226	153	226	106
165°	198	167	198	167	198	56
175°	178	174	178	174	178	17
180°	175	175	175	175	175	



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1955.5	1958.0	1949.8	1948.6	1939.1	1936.6	1936.6	1923.4	1915.2	1904.6	1898.3
5°	2180.3	2192.9	2186.6	2172.4	2148.8	2143.3	2128.4	2104.8	2078.1	2045.1	2029.4
7.5°	2461.0	2478.2	2471.6	2449.7	2425.0	2405.1	2362.9	2323.8	2268.9	2220.8	2179.6
10°	2691.2	2673.1	2658.9	2637.7	2614.9	2578.0	2534.0	2473.4	2403.5	2348.5	2287.2
12.5°	2863.4	2860.5	2842.5	2820.7	2788.5	2753.4	2699.3	2625.6	2544.3	2464.8	2394.7
15°	3098.3	3103.0	3091.2	3068.4	3022.8	2960.7	2879.0	2848.4	2732.0	2645.6	2559.1
17.5°	3260.8	3259.9	3258.3	3226.7	3180.2	3136.0	3060.2	2979.6	2874.3	2752.5	2636.0
20°	3363.9	3356.1	3357.7	3322.3	3287.7	3236.6	3162.7	3045.6	2959.2	2818.5	2698.2
22.5°	3361.4	3359.9	3365.8	3353.7	3328.6	3289.4	3231.3	3132.4	3022.1	2880.1	2744.8
25°	3192.6	3186.3	3223.3	3233.5	3273.6	3280.6	3263.3	3209.1	3104.6	2958.4	2791.0
27.5°	2672.0	2668.5	2737.1	2822.9	2931.7	3016.2	3098.0	3137.4	3104.6	2999.9	2832.2
30°	2192.9	2266.7	2301.3	2425.5	2563.8	2728.9	2873.5	3011.0	3044.8	2999.3	2861.7
32.5°	1820.6	1885.1	1914.0	2020.6	2149.5	2342.8	2559.7	2754.5	2892.1	2926.9	2844.1
35°	1384.9	1385.7	1451.7	1498.8	1618.3	1817.2	2027.8	2288.7	2548.1	2744.6	2765.0
37.5°	1105.1	1109.0	1148.9	1195.9	1285.5	1390.7	1576.2	1793.1	2092.7	2394.4	2571.2
40°	954.2	961.2	991.1	1037.5	1101.9	1181.3	1325.9	1530.3	1780.2	2115.8	2390.1
42.5°	857.3	868.8	884.2	919.9	959.8	1034.2	1151.1	1309.0	1536.3	1853.6	2170.1
45°	738.8	745.1	756.9	773.4	809.5	861.4	940.0	1046.1	1234.8	1490.2	1806.9
47.5°	651.7	648.4	660.8	674.2	698.3	733.6	786.3	872.9	1007.5	1212.4	1481.1
50°	592.6	591.8	600.5	610.7	633.5	659.4	702.7	767.9	874.8	1044.6	1290.6
52.5°	537.3	540.3	546.4	559.1	575.6	596.6	635.4	682.4	774.2	920.7	1125.8
55°	463.7	466.1	474.7	481.8	493.6	514.8	539.2	578.5	641.4	743.5	912.5
57.5°	401.5	400.4	408.7	410.4	423.8	441.1	459.9	490.4	536.0	612.0	725.8
60°	360.0	357.6	364.7	370.2	377.3	391.4	407.1	437.0	473.2	529.0	626.4
62.5°	322.2	321.1	326.3	331.8	337.7	350.5	363.7	386.7	415.3	462.3	539.6
65°	267.2	269.6	271.9	274.3	277.4	285.3	297.9	313.6	333.3	366.3	422.1
67.5°	210.0	212.4	213.2	218.0	224.8	229.7	237.4	251.4	265.0	292.9	324.6
70°	169.8	169.0	169.8	172.1	180.8	189.4	199.6	209.9	218.5	238.1	264.9
72.5°	145.9	144.5	146.5	147.0	151.2	153.6	160.0	169.6	180.8	194.1	213.3
75°	113.2	113.2	113.2	113.2	116.3	117.9	120.3	122.6	126.5	132.8	147.0
77.5°	83.6	83.8	84.9	85.7	86.3	87.2	88.7	91.0	92.4	95.7	101.9
80°	66.0	66.8	66.0	66.8	66.8	68.4	69.2	71.5	72.3	76.2	78.6
82.5°	49.7	49.2	49.7	50.5	50.5	52.0	52.2	53.9	54.1	56.1	58.5
85°	26.7	25.2	26.7	25.9	27.5	25.9	26.7	28.3	28.3	29.1	32.2
87.5°	8.3	9.7	8.3	8.9	9.0	9.5	9.4	9.3	10.5	9.9	10.4
90°	10.2	10.6	10.2	9.9	10.2	9.5	9.2	8.8	8.5	8.8	7.8
92.5°	17.0	17.7	17.3	18.4	19.0	20.8	23.6	29.8	41.0	54.3	59.8
95°	41.0	42.4	44.9	48.1	54.8	67.5	86.2	127.2	170.0	209.6	186.6
97.5°	111.6	114.6	124.2	140.1	166.2	208.4	254.0	317.1	347.4	324.8	237.8
100°	221.6	221.2	235.0	260.8	296.5	346.7	388.0	416.6	404.3	334.7	226.2
102.5°	325.0	333.2	344.7	365.1	392.9	424.7	448.8	449.7	407.1	316.3	209.2
105°	449.5	451.3	462.6	476.0	492.3	501.4	494.7	459.4	385.5	284.1	188.4
107.5°	521.2	524.4	528.2	532.8	532.5	519.9	488.9	431.5	347.8	255.7	175.1
110°	550.6	551.3	552.0	549.2	539.3	514.5	470.0	405.0	324.1	239.6	170.0



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	556.5	556.4	553.7	544.9	526.8	495.0	445.1	378.7	303.4	228.8	167.1
115°	546.7	544.9	537.8	522.3	495.8	457.3	405.3	343.8	278.5	217.3	166.1
117.5°	515.4	513.0	502.9	485.1	457.4	418.3	371.7	318.6	263.4	210.5	166.7
120°	489.4	487.3	478.8	459.0	431.1	395.4	353.0	305.3	255.5	207.4	167.9
122.5°	465.1	462.4	453.1	435.3	410.5	377.3	338.0	294.9	249.0	205.5	169.8
125°	431.1	428.7	419.8	404.3	381.7	353.4	319.5	280.9	240.7	202.8	172.8
127.5°	403.1	400.9	392.9	379.6	359.5	333.7	303.1	268.8	233.3	201.6	176.2
130°	387.3	384.5	377.1	364.3	345.6	321.6	293.0	261.1	229.3	200.7	178.5
132.5°	371.8	369.8	363.2	350.5	332.9	310.0	283.3	254.1	225.7	200.4	180.2
135°	349.5	347.0	340.7	330.1	312.7	292.6	269.6	244.5	220.9	200.0	182.7
137.5°	326.0	324.3	319.0	308.2	293.7	276.2	256.4	235.8	216.7	199.2	184.4
140°	309.6	309.9	304.3	294.4	280.9	265.7	248.8	230.8	214.1	199.0	185.5
142.5°	294.3	294.6	289.6	280.8	269.3	256.1	241.4	226.0	211.9	198.4	186.4
145°	273.2	272.5	269.6	262.2	253.4	243.1	231.8	220.2	208.8	197.5	186.9
147.5°	255.8	255.5	252.8	247.8	241.1	233.8	224.7	215.4	205.9	196.2	186.9
150°	245.6	245.6	243.5	239.6	234.3	227.6	220.2	212.0	203.9	195.1	186.9
152.5°	237.1	237.1	235.8	232.2	228.1	222.5	215.9	208.9	201.6	193.7	186.1
155°	226.5	226.2	225.5	222.6	219.4	215.2	209.9	204.3	198.2	191.2	185.2
157.5°	216.8	216.9	216.3	214.2	211.5	208.1	204.0	199.3	194.4	189.0	184.0
160°	210.6	211.0	211.0	208.8	206.4	203.9	200.4	196.5	191.9	187.3	183.4
162.5°	205.0	205.3	205.3	203.5	201.9	199.7	196.4	193.1	189.3	185.6	182.3
165°	197.5	197.5	197.9	196.5	195.1	193.3	190.8	188.7	185.9	183.1	180.6
167.5°	190.5	190.5	190.8	189.8	189.2	187.9	186.5	184.9	182.6	180.5	178.9
170°	186.2	186.2	186.6	185.9	185.5	184.8	183.4	182.3	180.6	178.8	177.8
172.5°	182.3	182.6	183.2	182.5	182.4	182.0	180.9	180.1	178.6	177.4	176.9
175°	177.8	178.1	178.5	178.1	178.1	178.1	177.4	177.0	176.3	175.6	175.6
177.5°	175.1	175.1	175.7	175.4	175.7	175.7	175.4	175.1	174.9	174.6	174.9
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1895.8	1893.9	1885.1	1875.0	1861.8	1853.0	1846.1	1842.3	1831.0	1817.2	1807.7
5°	2012.9	1989.3	1964.1	1933.5	1905.2	1876.1	1858.0	1836.8	1810.9	1781.8	1761.4
7.5°	2138.3	2092.1	2042.3	1990.9	1940.1	1894.5	1854.3	1819.8	1778.5	1736.8	1707.6
10°	2234.5	2166.9	2097.0	2025.4	1960.2	1898.9	1851.7	1805.4	1755.9	1707.9	1671.8
12.5°	2321.9	2232.9	2152.3	2064.4	1981.0	1907.7	1839.8	1785.2	1725.7	1674.6	1633.4
15°	2432.6	2341.4	2243.9	2110.3	1999.5	1906.8	1824.2	1752.7	1680.4	1617.5	1577.4
17.5°	2536.0	2398.8	2267.8	2156.4	2012.4	1896.5	1795.8	1710.3	1630.9	1564.2	1514.9
20°	2578.8	2445.9	2303.7	2161.4	2019.9	1890.3	1773.1	1678.8	1596.3	1520.8	1475.3
22.5°	2604.5	2454.1	2304.3	2151.4	2001.1	1866.4	1750.5	1646.8	1557.3	1485.6	1429.4
25°	2634.6	2455.4	2290.3	2139.4	1986.1	1840.0	1702.4	1592.4	1495.7	1419.5	1359.7
27.5°	2654.4	2443.6	2248.5	2080.8	1925.3	1779.7	1653.7	1537.0	1439.0	1358.3	1294.2
30°	2658.1	2434.1	2216.4	2034.9	1876.9	1743.3	1609.7	1498.1	1394.3	1308.6	1248.9
32.5°	2663.2	2410.9	2173.0	1980.2	1818.4	1686.1	1565.0	1458.4	1352.2	1267.8	1206.8
35°	2642.4	2398.0	2107.2	1885.5	1723.6	1595.5	1486.3	1388.0	1283.5	1201.7	1139.7
37.5°	2553.1	2346.9	2039.0	1779.0	1609.7	1491.0	1402.0	1316.3	1220.5	1132.3	1073.8
40°	2463.2	2296.6	1986.1	1714.2	1537.4	1415.5	1335.4	1265.4	1172.7	1090.1	1027.3
42.5°	2329.3	2228.1	1935.8	1646.3	1455.6	1338.2	1270.6	1205.0	1123.6	1039.8	980.7
45°	2083.6	2097.0	1832.9	1538.1	1342.4	1224.5	1160.9	1115.3	1043.0	973.8	913.3
47.5°	1775.5	1900.5	1712.0	1422.9	1223.1	1112.5	1056.8	1017.0	968.3	900.4	845.2
50°	1574.3	1752.7	1615.2	1345.6	1148.3	1038.3	983.2	951.0	908.6	855.1	802.5
52.5°	1388.8	1580.4	1498.2	1259.4	1067.2	966.6	912.8	886.3	852.6	802.3	754.7
55°	1132.6	1326.7	1307.9	1129.4	945.5	855.1	814.3	784.4	761.6	723.9	686.2
57.5°	916.1	1100.2	1109.9	984.8	838.3	749.0	713.8	691.3	676.4	648.0	613.1
60°	779.7	948.7	981.7	887.4	761.6	683.0	648.4	630.3	618.6	595.8	569.0
62.5°	666.5	810.3	847.7	779.8	688.0	614.5	587.4	570.0	562.0	542.3	518.7
65°	510.1	629.6	665.7	628.0	580.0	521.1	499.1	484.2	477.1	466.1	448.8
67.5°	383.6	470.6	510.3	483.7	466.4	429.1	415.1	407.1	400.8	393.3	378.8
70°	308.1	372.5	413.4	406.3	392.2	372.5	362.3	356.8	350.5	344.3	331.7
72.5°	247.7	292.1	330.4	334.0	322.4	318.5	309.5	307.2	303.4	295.8	288.9
75°	164.3	194.9	221.6	231.9	236.6	240.5	236.6	235.8	235.0	228.7	224.8
77.5°	107.7	124.2	141.0	158.5	165.8	171.2	172.4	175.3	173.2	169.9	168.0
80°	82.5	86.5	98.2	113.2	125.0	129.7	132.8	134.4	133.6	132.8	129.7
82.5°	59.9	63.2	68.7	79.2	89.1	97.0	98.9	98.6	100.3	100.8	98.2
85°	32.2	33.0	34.6	36.2	41.7	50.3	52.7	54.2	55.8	55.8	51.1
87.5°	11.4	10.6	11.6	11.5	13.2	13.6	17.3	20.3	21.0	18.7	18.9
90°	6.7	5.7	4.6	3.9	3.2	2.1	1.4	0.7	1.4	2.1	3.2
92.5°	44.9	29.7	20.4	15.2	12.2	9.5	6.5	4.4	6.5	9.5	12.2
95°	128.6	76.0	45.9	32.2	23.0	17.0	13.1	12.0	13.1	17.0	23.0
97.5°	141.1	81.8	53.1	38.2	29.1	23.9	20.8	20.5	20.8	23.9	29.1
100°	133.2	80.9	56.2	42.4	33.9	29.0	26.5	26.2	26.5	29.0	33.9
102.5°	126.4	82.1	59.9	47.2	39.6	34.9	32.7	32.1	32.7	34.9	39.6
105°	121.6	85.2	66.1	55.1	48.4	44.2	42.1	41.0	42.1	44.2	48.4
107.5°	121.2	91.0	74.2	64.0	57.7	53.6	51.5	50.5	51.5	53.6	57.7
110°	122.6	95.8	79.9	70.0	64.0	60.1	58.3	57.2	58.3	60.1	64.0





TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	125.5	100.6	85.8	76.2	70.2	66.3	64.5	63.5	64.5	66.3	70.2
115°	130.0	108.5	95.1	85.5	79.5	76.0	73.9	72.4	73.9	76.0	79.5
117.5°	136.1	116.9	103.6	94.8	88.1	84.8	83.0	81.4	83.0	84.8	88.1
120°	140.6	122.3	109.5	100.7	94.0	90.5	88.7	87.6	88.7	90.5	94.0
122.5°	144.9	127.9	115.5	106.1	99.7	95.8	94.1	93.0	94.1	95.8	99.7
125°	151.6	136.1	123.7	114.1	107.4	103.5	101.4	100.7	101.4	103.5	107.4
127.5°	157.1	143.1	131.2	121.6	114.2	110.3	107.6	106.6	107.6	110.3	114.2
130°	160.8	147.4	135.7	126.2	118.7	114.5	111.3	110.3	111.3	114.5	118.7
132.5°	164.2	151.0	139.7	130.4	123.0	117.9	114.4	113.1	114.4	117.9	123.0
135°	168.6	156.5	145.6	136.1	128.6	123.3	119.4	118.0	119.4	123.3	128.6
137.5°	171.8	160.4	149.8	141.0	133.6	128.0	124.2	122.7	124.2	128.0	133.6
140°	173.5	162.9	152.7	143.8	136.8	131.1	127.6	125.8	127.6	131.1	136.8
142.5°	175.2	164.9	154.9	146.7	139.6	134.5	130.7	129.2	130.7	134.5	139.6
145°	177.0	167.5	158.3	150.2	144.2	138.9	135.7	134.6	135.7	138.9	144.2
147.5°	178.2	169.6	161.2	154.3	148.5	143.9	140.8	140.2	140.8	143.9	148.5
150°	178.5	171.0	162.9	156.5	151.6	147.0	144.2	143.8	144.2	147.0	151.6
152.5°	179.0	171.9	164.9	158.8	154.4	150.4	147.6	147.5	147.6	150.4	154.4
155°	179.2	173.5	167.5	162.6	158.7	155.1	153.0	153.0	153.0	155.1	158.7
157.5°	179.5	174.4	169.6	165.8	162.5	159.4	157.7	157.4	157.7	159.4	162.5
160°	179.5	175.3	171.0	167.5	165.0	162.2	160.8	160.8	160.8	162.2	165.0
162.5°	179.2	175.6	171.9	168.9	166.7	164.5	163.3	163.3	163.3	164.5	166.7
165°	178.5	176.0	173.2	170.7	169.3	167.5	166.8	167.1	166.8	167.5	169.3
167.5°	177.9	175.9	173.9	172.3	171.3	170.0	169.6	170.0	169.6	170.0	171.3
170°	177.0	175.6	173.9	173.2	172.4	171.4	171.0	171.7	171.0	171.4	172.4
172.5°	176.8	175.6	174.1	173.7	173.3	172.5	172.4	172.9	172.4	172.5	173.3
175°	176.0	175.3	174.6	174.2	174.2	173.5	173.9	174.2	173.9	173.5	174.2
177.5°	175.4	174.9	174.6	174.6	174.6	174.3	174.6	174.9	174.6	174.3	174.6
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1804.6	1796.4	1790.8	1778.2	1770.0	1761.2	1752.4	1758.1	1757.4	1756.8	1756.8
5°	1744.1	1726.0	1709.5	1688.3	1674.9	1658.4	1645.8	1644.2	1647.4	1636.4	1630.1
7.5°	1684.0	1659.3	1635.9	1612.5	1587.7	1567.9	1555.4	1549.6	1541.6	1534.8	1527.8
10°	1641.9	1612.8	1590.0	1560.9	1534.2	1510.6	1495.7	1485.5	1480.0	1474.5	1464.3
12.5°	1598.5	1570.1	1541.0	1508.1	1482.7	1455.3	1444.1	1432.7	1422.1	1416.0	1402.0
15°	1535.0	1498.1	1467.4	1432.8	1404.5	1377.8	1362.1	1339.3	1336.1	1328.3	1314.1
17.5°	1471.3	1431.2	1389.0	1363.3	1331.4	1303.6	1279.7	1272.0	1249.5	1241.0	1228.8
20°	1421.0	1384.1	1351.9	1318.1	1271.7	1245.8	1226.9	1216.7	1198.6	1187.6	1179.7
22.5°	1377.6	1340.1	1302.8	1263.4	1225.2	1196.1	1182.3	1166.4	1156.5	1141.1	1132.6
25°	1315.7	1274.8	1230.0	1187.6	1160.1	1138.1	1116.1	1101.9	1087.8	1080.7	1065.0
27.5°	1243.7	1201.0	1159.1	1126.9	1093.1	1071.4	1051.5	1038.9	1021.9	1010.0	1001.3
30°	1204.1	1153.8	1117.6	1088.6	1045.3	1024.9	1010.0	994.3	981.7	969.1	960.5
32.5°	1158.2	1112.3	1078.0	1042.0	1008.9	986.5	967.2	953.4	942.7	930.7	922.1
35°	1086.2	1047.7	1012.3	976.2	951.8	929.0	906.2	894.4	884.2	873.2	865.4
37.5°	1021.1	985.1	951.5	917.2	887.0	868.5	850.1	841.1	827.3	819.9	811.9
40°	980.9	945.5	909.4	876.4	844.9	830.8	814.3	800.9	788.3	782.8	774.2
42.5°	936.9	901.5	871.0	835.5	809.7	790.5	775.3	760.7	751.2	743.2	738.3
45°	871.6	840.2	810.3	775.0	750.6	734.1	716.8	703.4	694.8	689.3	680.6
47.5°	808.3	776.9	746.5	715.7	692.1	673.3	656.0	646.7	635.2	628.5	622.6
50°	762.4	734.1	701.9	673.6	650.0	631.1	617.0	605.2	595.0	586.3	582.4
52.5°	720.3	690.1	662.3	635.8	611.0	589.6	576.7	564.3	556.6	546.7	542.2
55°	650.8	621.7	598.1	572.2	547.8	529.7	514.0	503.0	495.2	484.2	477.9
57.5°	585.5	559.5	531.3	508.8	483.7	468.4	455.4	440.5	430.9	422.2	416.1
60°	541.5	511.7	487.3	466.1	444.1	424.4	412.6	400.8	390.6	382.0	376.5
62.5°	495.6	469.5	446.4	423.3	403.2	386.1	372.4	362.5	353.5	348.0	342.5
65°	425.2	404.8	381.2	362.3	343.5	330.9	319.9	311.2	305.0	301.0	296.3
67.5°	360.4	340.6	320.0	301.5	288.9	279.3	272.1	264.7	261.6	256.5	253.4
70°	318.3	297.9	279.8	265.7	253.1	246.0	241.3	235.8	232.6	226.4	223.2
72.5°	272.4	257.6	244.6	233.0	222.9	216.5	210.5	203.7	198.7	191.8	188.6
75°	214.6	201.2	191.0	183.1	176.8	168.2	159.6	152.5	150.1	147.8	147.0
77.5°	158.9	150.4	143.0	136.4	128.6	122.3	120.4	118.8	118.4	117.1	117.1
80°	125.0	117.1	111.6	103.7	99.0	99.0	99.0	97.5	98.2	98.2	98.2
82.5°	92.9	85.7	82.7	79.9	78.9	79.5	79.5	79.9	79.4	80.6	80.0
85°	47.9	48.7	50.3	49.5	50.3	50.3	51.9	51.1	51.9	50.3	51.9
87.5°	18.4	20.4	21.3	22.1	22.9	22.5	23.1	23.1	23.8	23.9	24.1
90°	3.9	4.6	5.7	6.7	7.8	8.8	8.5	8.8	9.2	9.5	10.2
92.5°	15.2	20.4	29.7	44.9	59.8	54.3	41.0	29.8	23.6	20.8	19.0
95°	32.2	45.9	76.0	128.6	186.6	209.6	170.0	127.2	86.2	67.5	54.8
97.5°	38.2	53.1	81.8	141.1	237.8	324.8	347.4	317.1	254.0	208.4	166.2
100°	42.4	56.2	80.9	133.2	226.2	334.7	404.3	416.6	388.0	346.7	296.5
102.5°	47.2	59.9	82.1	126.4	209.2	316.3	407.1	449.7	448.8	424.7	392.9
105°	55.1	66.1	85.2	121.6	188.4	284.1	385.5	459.4	494.7	501.4	492.3
107.5°	64.0	74.2	91.0	121.2	175.1	255.7	347.8	431.5	488.9	519.9	532.5
110°	70.0	79.9	95.8	122.6	170.0	239.6	324.1	405.0	470.0	514.5	539.3



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	76.2	85.8	100.6	125.5	167.1	228.8	303.4	378.7	445.1	495.0	526.8
115°	85.5	95.1	108.5	130.0	166.1	217.3	278.5	343.8	405.3	457.3	495.8
117.5°	94.8	103.6	116.9	136.1	166.7	210.5	263.4	318.6	371.7	418.3	457.4
120°	100.7	109.5	122.3	140.6	167.9	207.4	255.5	305.3	353.0	395.4	431.1
122.5°	106.1	115.5	127.9	144.9	169.8	205.5	249.0	294.9	338.0	377.3	410.5
125°	114.1	123.7	136.1	151.6	172.8	202.8	240.7	280.9	319.5	353.4	381.7
127.5°	121.6	131.2	143.1	157.1	176.2	201.6	233.3	268.8	303.1	333.7	359.5
130°	126.2	135.7	147.4	160.8	178.5	200.7	229.3	261.1	293.0	321.6	345.6
132.5°	130.4	139.7	151.0	164.2	180.2	200.4	225.7	254.1	283.3	310.0	332.9
135°	136.1	145.6	156.5	168.6	182.7	200.0	220.9	244.5	269.6	292.6	312.7
137.5°	141.0	149.8	160.4	171.8	184.4	199.2	216.7	235.8	256.4	276.2	293.7
140°	143.8	152.7	162.9	173.5	185.5	199.0	214.1	230.8	248.8	265.7	280.9
142.5°	146.7	154.9	164.9	175.2	186.4	198.4	211.9	226.0	241.4	256.1	269.3
145°	150.2	158.3	167.5	177.0	186.9	197.5	208.8	220.2	231.8	243.1	253.4
147.5°	154.3	161.2	169.6	178.2	186.9	196.2	205.9	215.4	224.7	233.8	241.1
150°	156.5	162.9	171.0	178.5	186.9	195.1	203.9	212.0	220.2	227.6	234.3
152.5°	158.8	164.9	171.9	179.0	186.1	193.7	201.6	208.9	215.9	222.5	228.1
155°	162.6	167.5	173.5	179.2	185.2	191.2	198.2	204.3	209.9	215.2	219.4
157.5°	165.8	169.6	174.4	179.5	184.0	189.0	194.4	199.3	204.0	208.1	211.5
160°	167.5	171.0	175.3	179.5	183.4	187.3	191.9	196.5	200.4	203.9	206.4
162.5°	168.9	171.9	175.6	179.2	182.3	185.6	189.3	193.1	196.4	199.7	201.9
165°	170.7	173.2	176.0	178.5	180.6	183.1	185.9	188.7	190.8	193.3	195.1
167.5°	172.3	173.9	175.9	177.9	178.9	180.5	182.6	184.9	186.5	187.9	189.2
170°	173.2	173.9	175.6	177.0	177.8	178.8	180.6	182.3	183.4	184.8	185.5
172.5°	173.7	174.1	175.6	176.8	176.9	177.4	178.6	180.1	180.9	182.0	182.4
175°	174.2	174.6	175.3	176.0	175.6	175.6	176.3	177.0	177.4	178.1	178.1
177.5°	174.6	174.6	174.9	175.4	174.9	174.6	174.9	175.1	175.4	175.7	175.7
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1749.3	1748.6	1749.3	1746.7	1749.3	1748.6	1749.3	1756.8	1756.8	1757.4	1758.1
5°	1627.7	1627.0	1624.6	1617.5	1624.6	1627.0	1627.7	1630.1	1636.4	1647.4	1644.2
7.5°	1521.6	1520.5	1513.6	1513.8	1513.6	1520.5	1521.6	1527.8	1534.8	1541.6	1549.6
10°	1458.8	1459.5	1450.1	1444.6	1450.1	1459.5	1458.8	1464.3	1474.5	1480.0	1485.5
12.5°	1397.8	1394.2	1386.6	1380.5	1386.6	1394.2	1397.8	1402.0	1416.0	1422.1	1432.7
15°	1317.3	1309.4	1290.6	1292.1	1290.6	1309.4	1317.3	1314.1	1328.3	1336.1	1339.3
17.5°	1222.5	1216.7	1216.4	1205.4	1216.4	1216.7	1222.5	1228.8	1241.0	1249.5	1272.0
20°	1167.2	1163.2	1164.8	1153.8	1164.8	1163.2	1167.2	1179.7	1187.6	1198.6	1216.7
22.5°	1123.8	1119.8	1113.2	1109.8	1113.2	1119.8	1123.8	1132.6	1141.1	1156.5	1166.4
25°	1060.3	1054.0	1047.7	1051.6	1047.7	1054.0	1060.3	1065.0	1080.7	1087.8	1101.9
27.5°	996.8	992.1	985.8	985.0	985.8	992.1	996.8	1001.3	1010.0	1021.9	1038.9
30°	956.5	951.8	948.7	944.7	948.7	951.8	956.5	960.5	969.1	981.7	994.3
32.5°	915.7	914.7	909.1	908.3	909.1	914.7	915.7	922.1	930.7	942.7	953.4
35°	862.2	857.5	855.9	856.7	855.9	857.5	862.2	865.4	873.2	884.2	894.4
37.5°	811.4	805.1	802.3	799.5	802.3	805.1	811.4	811.9	819.9	827.3	841.1
40°	775.0	768.7	767.1	765.5	767.1	768.7	775.0	774.2	782.8	788.3	800.9
42.5°	734.1	731.6	730.6	727.8	730.6	731.6	734.1	738.3	743.2	751.2	760.7
45°	678.3	677.5	672.8	674.4	672.8	677.5	678.3	680.6	689.3	694.8	703.4
47.5°	619.5	616.0	612.7	614.9	612.7	616.0	619.5	622.6	628.5	635.2	646.7
50°	579.3	577.7	570.6	572.2	570.6	577.7	579.3	582.4	586.3	595.0	605.2
52.5°	539.0	533.0	530.4	529.4	530.4	533.0	539.0	542.2	546.7	556.6	564.3
55°	472.4	465.3	462.1	460.6	462.1	465.3	472.4	477.9	484.2	495.2	503.0
57.5°	407.0	405.1	402.6	404.3	402.6	405.1	407.0	416.1	422.2	430.9	440.5
60°	368.6	368.6	368.6	367.8	368.6	368.6	368.6	376.5	382.0	390.6	400.8
62.5°	339.1	337.2	336.6	337.7	336.6	337.2	339.1	342.5	348.0	353.5	362.5
65°	294.0	293.2	290.0	289.2	290.0	293.2	294.0	296.3	301.0	305.0	311.2
67.5°	251.4	248.5	247.6	246.5	247.6	248.5	251.4	253.4	256.5	261.6	264.7
70°	219.3	217.7	213.0	213.8	213.0	217.7	219.3	223.2	226.4	232.6	235.8
72.5°	184.7	183.1	182.2	181.1	182.2	183.1	184.7	188.6	191.8	198.7	203.7
75°	146.2	145.4	144.6	147.8	144.6	145.4	146.2	147.0	147.8	150.1	152.5
77.5°	117.1	117.1	117.6	116.3	117.6	117.1	117.1	117.1	117.1	118.4	118.8
80°	98.2	98.2	97.5	97.5	97.5	98.2	98.2	98.2	98.2	98.2	97.5
82.5°	78.8	79.4	79.9	78.6	79.9	79.4	78.8	80.0	80.6	79.4	79.9
85°	51.9	51.1	52.7	51.9	52.7	51.1	51.9	51.9	50.3	51.9	51.1
87.5°	25.2	24.1	24.1	24.7	24.1	24.1	25.2	24.1	23.9	23.8	23.1
90°	9.9	10.2	10.6	10.2	10.6	10.2	9.9	10.2	9.5	9.2	8.8
92.5°	18.4	17.3	17.7	17.0	17.7	17.3	18.4	19.0	20.8	23.6	29.8
95°	48.1	44.9	42.4	41.0	42.4	44.9	48.1	54.8	67.5	86.2	127.2
97.5°	140.1	124.2	114.6	111.6	114.6	124.2	140.1	166.2	208.4	254.0	317.1
100°	260.8	235.0	221.2	221.6	221.2	235.0	260.8	296.5	346.7	388.0	416.6
102.5°	365.1	344.7	333.2	325.0	333.2	344.7	365.1	392.9	424.7	448.8	449.7
105°	476.0	462.6	451.3	449.5	451.3	462.6	476.0	492.3	501.4	494.7	459.4
107.5°	532.8	528.2	524.4	521.2	524.4	528.2	532.8	532.5	519.9	488.9	431.5
110°	549.2	552.0	551.3	550.6	551.3	552.0	549.2	539.3	514.5	470.0	405.0



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	544.9	553.7	556.4	556.5	556.4	553.7	544.9	526.8	495.0	445.1	378.7
115°	522.3	537.8	544.9	546.7	544.9	537.8	522.3	495.8	457.3	405.3	343.8
117.5°	485.1	502.9	513.0	515.4	513.0	502.9	485.1	457.4	418.3	371.7	318.6
120°	459.0	478.8	487.3	489.4	487.3	478.8	459.0	431.1	395.4	353.0	305.3
122.5°	435.3	453.1	462.4	465.1	462.4	453.1	435.3	410.5	377.3	338.0	294.9
125°	404.3	419.8	428.7	431.1	428.7	419.8	404.3	381.7	353.4	319.5	280.9
127.5°	379.6	392.9	400.9	403.1	400.9	392.9	379.6	359.5	333.7	303.1	268.8
130°	364.3	377.1	384.5	387.3	384.5	377.1	364.3	345.6	321.6	293.0	261.1
132.5°	350.5	363.2	369.8	371.8	369.8	363.2	350.5	332.9	310.0	283.3	254.1
135°	330.1	340.7	347.0	349.5	347.0	340.7	330.1	312.7	292.6	269.6	244.5
137.5°	308.2	319.0	324.3	326.0	324.3	319.0	308.2	293.7	276.2	256.4	235.8
140°	294.4	304.3	309.9	309.6	309.9	304.3	294.4	280.9	265.7	248.8	230.8
142.5°	280.8	289.6	294.6	294.3	294.6	289.6	280.8	269.3	256.1	241.4	226.0
145°	262.2	269.6	272.5	273.2	272.5	269.6	262.2	253.4	243.1	231.8	220.2
147.5°	247.8	252.8	255.5	255.8	255.5	252.8	247.8	241.1	233.8	224.7	215.4
150°	239.6	243.5	245.6	245.6	245.6	243.5	239.6	234.3	227.6	220.2	212.0
152.5°	232.2	235.8	237.1	237.1	237.1	235.8	232.2	228.1	222.5	215.9	208.9
155°	222.6	225.5	226.2	226.5	226.2	225.5	222.6	219.4	215.2	209.9	204.3
157.5°	214.2	216.3	216.9	216.8	216.9	216.3	214.2	211.5	208.1	204.0	199.3
160°	208.8	211.0	211.0	210.6	211.0	211.0	208.8	206.4	203.9	200.4	196.5
162.5°	203.5	205.3	205.3	205.0	205.3	205.3	203.5	201.9	199.7	196.4	193.1
165°	196.5	197.9	197.5	197.5	197.5	197.9	196.5	195.1	193.3	190.8	188.7
167.5°	189.8	190.8	190.5	190.5	190.5	190.8	189.8	189.2	187.9	186.5	184.9
170°	185.9	186.6	186.2	186.2	186.2	186.6	185.9	185.5	184.8	183.4	182.3
172.5°	182.5	183.2	182.6	182.3	182.6	183.2	182.5	182.4	182.0	180.9	180.1
175°	178.1	178.5	178.1	177.8	178.1	178.5	178.1	178.1	178.1	177.4	177.0
177.5°	175.4	175.7	175.1	175.1	175.1	175.7	175.4	175.7	175.7	175.4	175.1
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1752.4	1761.2	1770.0	1778.2	1790.8	1796.4	1804.6	1807.7	1817.2	1831.0	1842.3
5°	1645.8	1658.4	1674.9	1688.3	1709.5	1726.0	1744.1	1761.4	1781.8	1810.9	1836.8
7.5°	1555.4	1567.9	1587.7	1612.5	1635.9	1659.3	1684.0	1707.6	1736.8	1778.5	1819.8
10°	1495.7	1510.6	1534.2	1560.9	1590.0	1612.8	1641.9	1671.8	1707.9	1755.9	1805.4
12.5°	1444.1	1455.3	1482.7	1508.1	1541.0	1570.1	1598.5	1633.4	1674.6	1725.7	1785.2
15°	1362.1	1377.8	1404.5	1432.8	1467.4	1498.1	1535.0	1577.4	1617.5	1680.4	1752.7
17.5°	1279.7	1303.6	1331.4	1363.3	1389.0	1431.2	1471.3	1514.9	1564.2	1630.9	1710.3
20°	1226.9	1245.8	1271.7	1318.1	1351.9	1384.1	1421.0	1475.3	1520.8	1596.3	1678.8
22.5°	1182.3	1196.1	1225.2	1263.4	1302.8	1340.1	1377.6	1429.4	1485.6	1557.3	1646.8
25°	1116.1	1138.1	1160.1	1187.6	1230.0	1274.8	1315.7	1359.7	1419.5	1495.7	1592.4
27.5°	1051.5	1071.4	1093.1	1126.9	1159.1	1201.0	1243.7	1294.2	1358.3	1439.0	1537.0
30°	1010.0	1024.9	1045.3	1088.6	1117.6	1153.8	1204.1	1248.9	1308.6	1394.3	1498.1
32.5°	967.2	986.5	1008.9	1042.0	1078.0	1112.3	1158.2	1206.8	1267.8	1352.2	1458.4
35°	906.2	929.0	951.8	976.2	1012.3	1047.7	1086.2	1139.7	1201.7	1283.5	1388.0
37.5°	850.1	868.5	887.0	917.2	951.5	985.1	1021.1	1073.8	1132.3	1220.5	1316.3
40°	814.3	830.8	844.9	876.4	909.4	945.5	980.9	1027.3	1090.1	1172.7	1265.4
42.5°	775.3	790.5	809.7	835.5	871.0	901.5	936.9	980.7	1039.8	1123.6	1205.0
45°	716.8	734.1	750.6	775.0	810.3	840.2	871.6	913.3	973.8	1043.0	1115.3
47.5°	656.0	673.3	692.1	715.7	746.5	776.9	808.3	845.2	900.4	968.3	1017.0
50°	617.0	631.1	650.0	673.6	701.9	734.1	762.4	802.5	855.1	908.6	951.0
52.5°	576.7	589.6	611.0	635.8	662.3	690.1	720.3	754.7	802.3	852.6	886.3
55°	514.0	529.7	547.8	572.2	598.1	621.7	650.8	686.2	723.9	761.6	784.4
57.5°	455.4	468.4	483.7	508.8	531.3	559.5	585.5	613.1	648.0	676.4	691.3
60°	412.6	424.4	444.1	466.1	487.3	511.7	541.5	569.0	595.8	618.6	630.3
62.5°	372.4	386.1	403.2	423.3	446.4	469.5	495.6	518.7	542.3	562.0	570.0
65°	319.9	330.9	343.5	362.3	381.2	404.8	425.2	448.8	466.1	477.1	484.2
67.5°	272.1	279.3	288.9	301.5	320.0	340.6	360.4	378.8	393.3	400.8	407.1
70°	241.3	246.0	253.1	265.7	279.8	297.9	318.3	331.7	344.3	350.5	356.8
72.5°	210.5	216.5	222.9	233.0	244.6	257.6	272.4	288.9	295.8	303.4	307.2
75°	159.6	168.2	176.8	183.1	191.0	201.2	214.6	224.8	228.7	235.0	235.8
77.5°	120.4	122.3	128.6	136.4	143.0	150.4	158.9	168.0	169.9	173.2	175.3
80°	99.0	99.0	99.0	103.7	111.6	117.1	125.0	129.7	132.8	133.6	134.4
82.5°	79.5	79.5	78.9	79.9	82.7	85.7	92.9	98.2	100.8	100.3	98.6
85°	51.9	50.3	50.3	49.5	50.3	48.7	47.9	51.1	55.8	55.8	54.2
87.5°	23.1	22.5	22.9	22.1	21.3	20.4	18.4	18.9	18.7	21.0	20.3
90°	8.5	8.8	7.8	6.7	5.7	4.6	3.9	3.2	2.1	1.4	0.7
92.5°	41.0	54.3	59.8	44.9	29.7	20.4	15.2	12.2	9.5	6.5	4.4
95°	170.0	209.6	186.6	128.6	76.0	45.9	32.2	23.0	17.0	13.1	12.0
97.5°	347.4	324.8	237.8	141.1	81.8	53.1	38.2	29.1	23.9	20.8	20.5
100°	404.3	334.7	226.2	133.2	80.9	56.2	42.4	33.9	29.0	26.5	26.2
102.5°	407.1	316.3	209.2	126.4	82.1	59.9	47.2	39.6	34.9	32.7	32.1
105°	385.5	284.1	188.4	121.6	85.2	66.1	55.1	48.4	44.2	42.1	41.0
107.5°	347.8	255.7	175.1	121.2	91.0	74.2	64.0	57.7	53.6	51.5	50.5
110°	324.1	239.6	170.0	122.6	95.8	79.9	70.0	64.0	60.1	58.3	57.2



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	303.4	228.8	167.1	125.5	100.6	85.8	76.2	70.2	66.3	64.5	63.5
115°	278.5	217.3	166.1	130.0	108.5	95.1	85.5	79.5	76.0	73.9	72.4
117.5°	263.4	210.5	166.7	136.1	116.9	103.6	94.8	88.1	84.8	83.0	81.4
120°	255.5	207.4	167.9	140.6	122.3	109.5	100.7	94.0	90.5	88.7	87.6
122.5°	249.0	205.5	169.8	144.9	127.9	115.5	106.1	99.7	95.8	94.1	93.0
125°	240.7	202.8	172.8	151.6	136.1	123.7	114.1	107.4	103.5	101.4	100.7
127.5°	233.3	201.6	176.2	157.1	143.1	131.2	121.6	114.2	110.3	107.6	106.6
130°	229.3	200.7	178.5	160.8	147.4	135.7	126.2	118.7	114.5	111.3	110.3
132.5°	225.7	200.4	180.2	164.2	151.0	139.7	130.4	123.0	117.9	114.4	113.1
135°	220.9	200.0	182.7	168.6	156.5	145.6	136.1	128.6	123.3	119.4	118.0
137.5°	216.7	199.2	184.4	171.8	160.4	149.8	141.0	133.6	128.0	124.2	122.7
140°	214.1	199.0	185.5	173.5	162.9	152.7	143.8	136.8	131.1	127.6	125.8
142.5°	211.9	198.4	186.4	175.2	164.9	154.9	146.7	139.6	134.5	130.7	129.2
145°	208.8	197.5	186.9	177.0	167.5	158.3	150.2	144.2	138.9	135.7	134.6
147.5°	205.9	196.2	186.9	178.2	169.6	161.2	154.3	148.5	143.9	140.8	140.2
150°	203.9	195.1	186.9	178.5	171.0	162.9	156.5	151.6	147.0	144.2	143.8
152.5°	201.6	193.7	186.1	179.0	171.9	164.9	158.8	154.4	150.4	147.6	147.5
155°	198.2	191.2	185.2	179.2	173.5	167.5	162.6	158.7	155.1	153.0	153.0
157.5°	194.4	189.0	184.0	179.5	174.4	169.6	165.8	162.5	159.4	157.7	157.4
160°	191.9	187.3	183.4	179.5	175.3	171.0	167.5	165.0	162.2	160.8	160.8
162.5°	189.3	185.6	182.3	179.2	175.6	171.9	168.9	166.7	164.5	163.3	163.3
165°	185.9	183.1	180.6	178.5	176.0	173.2	170.7	169.3	167.5	166.8	167.1
167.5°	182.6	180.5	178.9	177.9	175.9	173.9	172.3	171.3	170.0	169.6	170.0
170°	180.6	178.8	177.8	177.0	175.6	173.9	173.2	172.4	171.4	171.0	171.7
172.5°	178.6	177.4	176.9	176.8	175.6	174.1	173.7	173.3	172.5	172.4	172.9
175°	176.3	175.6	175.6	176.0	175.3	174.6	174.2	174.2	173.5	173.9	174.2
177.5°	174.9	174.6	174.9	175.4	174.9	174.6	174.6	174.6	174.3	174.6	174.9
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1846.1	1853.0	1861.8	1875.0	1885.1	1893.9	1895.8	1898.3	1904.6	1915.2	1923.4
5°	1858.0	1876.1	1905.2	1933.5	1964.1	1989.3	2012.9	2029.4	2045.1	2078.1	2104.8
7.5°	1854.3	1894.5	1940.1	1990.9	2042.3	2092.1	2138.3	2179.6	2220.8	2268.9	2323.8
10°	1851.7	1898.9	1960.2	2025.4	2097.0	2166.9	2234.5	2287.2	2348.5	2403.5	2473.4
12.5°	1839.8	1907.7	1981.0	2064.4	2152.3	2232.9	2321.9	2394.7	2464.8	2544.3	2625.6
15°	1824.2	1906.8	1999.5	2110.3	2243.9	2341.4	2432.6	2559.1	2645.6	2732.0	2848.4
17.5°	1795.8	1896.5	2012.4	2156.4	2267.8	2398.8	2536.0	2636.0	2752.5	2874.3	2979.6
20°	1773.1	1890.3	2019.9	2161.4	2303.7	2445.9	2578.8	2698.2	2818.5	2959.2	3045.6
22.5°	1750.5	1866.4	2001.1	2151.4	2304.3	2454.1	2604.5	2744.8	2880.1	3022.1	3132.4
25°	1702.4	1840.0	1986.1	2139.4	2290.3	2455.4	2634.6	2791.0	2958.4	3104.6	3209.1
27.5°	1653.7	1779.7	1925.3	2080.8	2248.5	2443.6	2654.4	2832.2	2999.9	3104.6	3137.4
30°	1609.7	1743.3	1876.9	2034.9	2216.4	2434.1	2658.1	2861.7	2999.3	3044.8	3011.0
32.5°	1565.0	1686.1	1818.4	1980.2	2173.0	2410.9	2663.2	2844.1	2926.9	2892.1	2754.5
35°	1486.3	1595.5	1723.6	1885.5	2107.2	2398.0	2642.4	2765.0	2744.6	2548.1	2288.7
37.5°	1402.0	1491.0	1609.7	1779.0	2039.0	2346.9	2553.1	2571.2	2394.4	2092.7	1793.1
40°	1335.4	1415.5	1537.4	1714.2	1986.1	2296.6	2463.2	2390.1	2115.8	1780.2	1530.3
42.5°	1270.6	1338.2	1455.6	1646.3	1935.8	2228.1	2329.3	2170.1	1853.6	1536.3	1309.0
45°	1160.9	1224.5	1342.4	1538.1	1832.9	2097.0	2083.6	1806.9	1490.2	1234.8	1046.1
47.5°	1056.8	1112.5	1223.1	1422.9	1712.0	1900.5	1775.5	1481.1	1212.4	1007.5	872.9
50°	983.2	1038.3	1148.3	1345.6	1615.2	1752.7	1574.3	1290.6	1044.6	874.8	767.9
52.5°	912.8	966.6	1067.2	1259.4	1498.2	1580.4	1388.8	1125.8	920.7	774.2	682.4
55°	814.3	855.1	945.5	1129.4	1307.9	1326.7	1132.6	912.5	743.5	641.4	578.5
57.5°	713.8	749.0	838.3	984.8	1109.9	1100.2	916.1	725.8	612.0	536.0	490.4
60°	648.4	683.0	761.6	887.4	981.7	948.7	779.7	626.4	529.0	473.2	437.0
62.5°	587.4	614.5	688.0	779.8	847.7	810.3	666.5	539.6	462.3	415.3	386.7
65°	499.1	521.1	580.0	628.0	665.7	629.6	510.1	422.1	366.3	333.3	313.6
67.5°	415.1	429.1	466.4	483.7	510.3	470.6	383.6	324.6	292.9	265.0	251.4
70°	362.3	372.5	392.2	406.3	413.4	372.5	308.1	264.9	238.1	218.5	209.9
72.5°	309.5	318.5	322.4	334.0	330.4	292.1	247.7	213.3	194.1	180.8	169.6
75°	236.6	240.5	236.6	231.9	221.6	194.9	164.3	147.0	132.8	126.5	122.6
77.5°	172.4	171.2	165.8	158.5	141.0	124.2	107.7	101.9	95.7	92.4	91.0
80°	132.8	129.7	125.0	113.2	98.2	86.5	82.5	78.6	76.2	72.3	71.5
82.5°	98.9	97.0	89.1	79.2	68.7	63.2	59.9	58.5	56.1	54.1	53.9
85°	52.7	50.3	41.7	36.2	34.6	33.0	32.2	32.2	29.1	28.3	28.3
87.5°	17.3	13.6	13.2	11.5	11.6	10.6	11.4	10.4	9.9	10.5	9.3
90°	1.4	2.1	3.2	3.9	4.6	5.7	6.7	7.8	8.8	8.5	8.8
92.5°	6.5	9.5	12.2	15.2	20.4	29.7	44.9	59.8	54.3	41.0	29.8
95°	13.1	17.0	23.0	32.2	45.9	76.0	128.6	186.6	209.6	170.0	127.2
97.5°	20.8	23.9	29.1	38.2	53.1	81.8	141.1	237.8	324.8	347.4	317.1
100°	26.5	29.0	33.9	42.4	56.2	80.9	133.2	226.2	334.7	404.3	416.6
102.5°	32.7	34.9	39.6	47.2	59.9	82.1	126.4	209.2	316.3	407.1	449.7
105°	42.1	44.2	48.4	55.1	66.1	85.2	121.6	188.4	284.1	385.5	459.4
107.5°	51.5	53.6	57.7	64.0	74.2	91.0	121.2	175.1	255.7	347.8	431.5
110°	58.3	60.1	64.0	70.0	79.9	95.8	122.6	170.0	239.6	324.1	405.0





TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	64.5	66.3	70.2	76.2	85.8	100.6	125.5	167.1	228.8	303.4	378.7
115°	73.9	76.0	79.5	85.5	95.1	108.5	130.0	166.1	217.3	278.5	343.8
117.5°	83.0	84.8	88.1	94.8	103.6	116.9	136.1	166.7	210.5	263.4	318.6
120°	88.7	90.5	94.0	100.7	109.5	122.3	140.6	167.9	207.4	255.5	305.3
122.5°	94.1	95.8	99.7	106.1	115.5	127.9	144.9	169.8	205.5	249.0	294.9
125°	101.4	103.5	107.4	114.1	123.7	136.1	151.6	172.8	202.8	240.7	280.9
127.5°	107.6	110.3	114.2	121.6	131.2	143.1	157.1	176.2	201.6	233.3	268.8
130°	111.3	114.5	118.7	126.2	135.7	147.4	160.8	178.5	200.7	229.3	261.1
132.5°	114.4	117.9	123.0	130.4	139.7	151.0	164.2	180.2	200.4	225.7	254.1
135°	119.4	123.3	128.6	136.1	145.6	156.5	168.6	182.7	200.0	220.9	244.5
137.5°	124.2	128.0	133.6	141.0	149.8	160.4	171.8	184.4	199.2	216.7	235.8
140°	127.6	131.1	136.8	143.8	152.7	162.9	173.5	185.5	199.0	214.1	230.8
142.5°	130.7	134.5	139.6	146.7	154.9	164.9	175.2	186.4	198.4	211.9	226.0
145°	135.7	138.9	144.2	150.2	158.3	167.5	177.0	186.9	197.5	208.8	220.2
147.5°	140.8	143.9	148.5	154.3	161.2	169.6	178.2	186.9	196.2	205.9	215.4
150°	144.2	147.0	151.6	156.5	162.9	171.0	178.5	186.9	195.1	203.9	212.0
152.5°	147.6	150.4	154.4	158.8	164.9	171.9	179.0	186.1	193.7	201.6	208.9
155°	153.0	155.1	158.7	162.6	167.5	173.5	179.2	185.2	191.2	198.2	204.3
157.5°	157.7	159.4	162.5	165.8	169.6	174.4	179.5	184.0	189.0	194.4	199.3
160°	160.8	162.2	165.0	167.5	171.0	175.3	179.5	183.4	187.3	191.9	196.5
162.5°	163.3	164.5	166.7	168.9	171.9	175.6	179.2	182.3	185.6	189.3	193.1
165°	166.8	167.5	169.3	170.7	173.2	176.0	178.5	180.6	183.1	185.9	188.7
167.5°	169.6	170.0	171.3	172.3	173.9	175.9	177.9	178.9	180.5	182.6	184.9
170°	171.0	171.4	172.4	173.2	173.9	175.6	177.0	177.8	178.8	180.6	182.3
172.5°	172.4	172.5	173.3	173.7	174.1	175.6	176.8	176.9	177.4	178.6	180.1
175°	173.9	173.5	174.2	174.2	174.6	175.3	176.0	175.6	175.6	176.3	177.0
177.5°	174.6	174.3	174.6	174.6	174.6	174.9	175.4	174.9	174.6	174.9	175.1
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1936.6	1936.6	1939.1	1948.6	1949.8	1958.0	1955.5
5°	2128.4	2143.3	2148.8	2172.4	2186.6	2192.9	2180.3
7.5°	2362.9	2405.1	2425.0	2449.7	2471.6	2478.2	2461.0
10°	2534.0	2578.0	2614.9	2637.7	2658.9	2673.1	2691.2
12.5°	2699.3	2753.4	2788.5	2820.7	2842.5	2860.5	2863.4
15°	2879.0	2960.7	3022.8	3068.4	3091.2	3103.0	3098.3
17.5°	3060.2	3136.0	3180.2	3226.7	3258.3	3259.9	3260.8
20°	3162.7	3236.6	3287.7	3322.3	3357.7	3356.1	3363.9
22.5°	3231.3	3289.4	3328.6	3353.7	3365.8	3359.9	3361.4
25°	3263.3	3280.6	3273.6	3233.5	3223.3	3186.3	3192.6
27.5°	3098.0	3016.2	2931.7	2822.9	2737.1	2668.5	2672.0
30°	2873.5	2728.9	2563.8	2425.5	2301.3	2266.7	2192.9
32.5°	2559.7	2342.8	2149.5	2020.6	1914.0	1885.1	1820.6
35°	2027.8	1817.2	1618.3	1498.8	1451.7	1385.7	1384.9
37.5°	1576.2	1390.7	1285.5	1195.9	1148.9	1109.0	1105.1
40°	1325.9	1181.3	1101.9	1037.5	991.1	961.2	954.2
42.5°	1151.1	1034.2	959.8	919.9	884.2	868.8	857.3
45°	940.0	861.4	809.5	773.4	756.9	745.1	738.8
47.5°	786.3	733.6	698.3	674.2	660.8	648.4	651.7
50°	702.7	659.4	633.5	610.7	600.5	591.8	592.6
52.5°	635.4	596.6	575.6	559.1	546.4	540.3	537.3
55°	539.2	514.8	493.6	481.8	474.7	466.1	463.7
57.5°	459.9	441.1	423.8	410.4	408.7	400.4	401.5
60°	407.1	391.4	377.3	370.2	364.7	357.6	360.0
62.5°	363.7	350.5	337.7	331.8	326.3	321.1	322.2
65°	297.9	285.3	277.4	274.3	271.9	269.6	267.2
67.5°	237.4	229.7	224.8	218.0	213.2	212.4	210.0
70°	199.6	189.4	180.8	172.1	169.8	169.0	169.8
72.5°	160.0	153.6	151.2	147.0	146.5	144.5	145.9
75°	120.3	117.9	116.3	113.2	113.2	113.2	113.2
77.5°	88.7	87.2	86.3	85.7	84.9	83.8	83.6
80°	69.2	68.4	66.8	66.8	66.0	66.8	66.0
82.5°	52.2	52.0	50.5	50.5	49.7	49.2	49.7
85°	26.7	25.9	27.5	25.9	26.7	25.2	26.7
87.5°	9.4	9.5	9.0	8.9	8.3	9.7	8.3
90°	9.2	9.5	10.2	9.9	10.2	10.6	10.2
92.5°	23.6	20.8	19.0	18.4	17.3	17.7	17.0
95°	86.2	67.5	54.8	48.1	44.9	42.4	41.0
97.5°	254.0	208.4	166.2	140.1	124.2	114.6	111.6
100°	388.0	346.7	296.5	260.8	235.0	221.2	221.6
102.5°	448.8	424.7	392.9	365.1	344.7	333.2	325.0
105°	494.7	501.4	492.3	476.0	462.6	451.3	449.5
107.5°	488.9	519.9	532.5	532.8	528.2	524.4	521.2
110°	470.0	514.5	539.3	549.2	552.0	551.3	550.6



TEST NUMBER: P332362

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	445.1	495.0	526.8	544.9	553.7	556.4	556.5
115°	405.3	457.3	495.8	522.3	537.8	544.9	546.7
117.5°	371.7	418.3	457.4	485.1	502.9	513.0	515.4
120°	353.0	395.4	431.1	459.0	478.8	487.3	489.4
122.5°	338.0	377.3	410.5	435.3	453.1	462.4	465.1
125°	319.5	353.4	381.7	404.3	419.8	428.7	431.1
127.5°	303.1	333.7	359.5	379.6	392.9	400.9	403.1
130°	293.0	321.6	345.6	364.3	377.1	384.5	387.3
132.5°	283.3	310.0	332.9	350.5	363.2	369.8	371.8
135°	269.6	292.6	312.7	330.1	340.7	347.0	349.5
137.5°	256.4	276.2	293.7	308.2	319.0	324.3	326.0
140°	248.8	265.7	280.9	294.4	304.3	309.9	309.6
142.5°	241.4	256.1	269.3	280.8	289.6	294.6	294.3
145°	231.8	243.1	253.4	262.2	269.6	272.5	273.2
147.5°	224.7	233.8	241.1	247.8	252.8	255.5	255.8
150°	220.2	227.6	234.3	239.6	243.5	245.6	245.6
152.5°	215.9	222.5	228.1	232.2	235.8	237.1	237.1
155°	209.9	215.2	219.4	222.6	225.5	226.2	226.5
157.5°	204.0	208.1	211.5	214.2	216.3	216.9	216.8
160°	200.4	203.9	206.4	208.8	211.0	211.0	210.6
162.5°	196.4	199.7	201.9	203.5	205.3	205.3	205.0
165°	190.8	193.3	195.1	196.5	197.9	197.5	197.5
167.5°	186.5	187.9	189.2	189.8	190.8	190.5	190.5
170°	183.4	184.8	185.5	185.9	186.6	186.2	186.2
172.5°	180.9	182.0	182.4	182.5	183.2	182.6	182.3
175°	177.4	178.1	178.1	178.1	178.5	178.1	177.8
177.5°	175.4	175.7	175.7	175.4	175.7	175.1	175.1
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6

(END OF REPORT)