

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332364

Luminaire Tested: **S123RDIP-S1165D365U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332364  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D365U835-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5626.2 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332364

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332364

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78																												
1	105	100	96	93	100	96	92	89	88	85	82	80	78	76	73	72	70	67																												
2	96	88	82	77	91	84	79	74	77	73	69	71	67	64	65	62	60	57																												
3	88	78	71	65	83	75	68	63	69	63	59	63	59	55	58	54	51	48																												
4	80	69	61	55	77	67	59	54	61	55	51	57	52	48	52	48	45	42																												
5	74	62	54	48	71	60	52	47	55	49	44	51	46	42	47	43	39	37																												
6	69	56	48	42	65	54	46	41	50	44	39	46	41	37	43	38	35	32																												
7	64	51	43	37	61	49	42	36	46	39	35	42	37	33	39	35	31	29																												
8	59	47	39	33	57	45	38	32	42	36	31	39	34	30	36	32	28	26																												
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24																												
10	52	40	32	27	50	38	31	27	36	30	25	33	28	24	31	27	23	22																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332364

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.0	3.2
10°-20°	506.4	9.0
20°-30°	729.2	13.0
30°-40°	821.3	14.6
40°-50°	785.8	14.0
50°-60°	643.5	11.4
60°-70°	434.1	7.7
70°-80°	218.4	3.9
80°-90°	59.1	1.1
90°-100°	29.3	0.5
100°-110°	87.7	1.6
110°-120°	149.2	2.7
120°-130°	196.2	3.5
130°-140°	220.6	3.9
140°-150°	216.8	3.9
150°-160°	182.5	3.2
160°-170°	121.5	2.2
170°-180°	42.5	0.8
0°-30°	1417.6	25.2
0°-40°	2238.9	39.8
0°-60°	3668.1	65.2
0°-90°	4379.8	77.8
90°-120°	266.2	4.7
90°-150°	899.9	16.0
90°-180°	1246.0	22.1
0°-180°	5626.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	0	4	8	10	11	5
95°	21	23	26	28	28	23
105°	80	80	83	83	84	85
115°	150	151	150	151	150	149
125°	220	221	220	219	217	196
135°	285	287	287	286	285	220
145°	346	347	348	347	346	216
155°	396	396	396	398	395	182
165°	432	430	430	432	430	122
175°	449	448	447	449	447	43
180°	450	450	450	450	450	



TEST NUMBER: P332364

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.3	27.3	24.4	21.5	18.6	17.2	17.4	17.6	17.8	18.0	17.8
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.4	6.4	7.5	8.5	8.8
92.5°	8.6	9.1	9.6	10.2	10.7	11.2	11.8	12.4	13.0	13.6	13.8
95°	20.9	21.4	21.9	22.5	23.0	23.6	24.3	24.9	25.5	26.2	26.5
97.5°	37.0	37.4	37.9	38.3	38.7	39.1	39.6	40.0	40.5	40.9	41.3
100°	48.1	48.5	49.0	49.5	49.9	50.4	50.8	51.2	51.6	51.9	52.2
102.5°	60.8	61.1	61.3	61.6	61.9	62.3	62.8	63.4	63.9	64.4	64.6
105°	79.5	79.7	79.8	80.0	80.1	80.6	81.3	82.0	82.7	83.4	83.4
107.5°	101.3	101.4	101.5	101.6	101.7	101.8	102.1	102.4	102.7	103.0	103.2
110°	114.9	115.0	115.2	115.3	115.5	115.6	115.8	116.0	116.1	116.3	116.6



TEST NUMBER: P332364

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	129.0	129.1	129.2	129.3	129.4	129.4	129.5	129.5	129.5	129.6	129.9
115°	150.2	150.4	150.7	150.9	151.1	151.2	151.0	150.9	150.7	150.5	150.6
117.5°	171.5	171.7	171.9	172.0	172.2	172.1	171.9	171.7	171.5	171.3	171.3
120°	184.8	185.3	185.8	186.2	186.7	186.7	186.4	186.0	185.6	185.2	185.1
122.5°	198.7	199.0	199.4	199.7	200.1	200.1	199.9	199.7	199.5	199.3	199.1
125°	219.8	220.0	220.3	220.5	220.8	220.8	220.6	220.5	220.3	220.2	219.8
127.5°	239.3	239.8	240.3	240.8	241.3	241.5	241.3	241.1	241.0	240.8	240.4
130°	252.3	252.9	253.6	254.2	254.8	255.0	254.8	254.6	254.3	254.1	253.8
132.5°	265.3	266.0	266.6	267.2	267.8	268.1	267.9	267.7	267.5	267.4	267.0
135°	285.2	285.7	286.1	286.6	287.1	287.3	287.2	287.1	287.0	287.0	286.6
137.5°	303.6	304.0	304.3	304.7	305.1	305.4	305.6	305.8	306.0	306.2	305.9
140°	316.3	316.7	317.1	317.5	317.9	318.1	318.2	318.2	318.3	318.4	318.3
142.5°	327.9	328.3	328.7	329.1	329.4	329.7	329.9	330.0	330.1	330.3	330.2
145°	346.0	346.1	346.3	346.4	346.6	346.8	347.0	347.3	347.5	347.7	347.7
147.5°	361.8	362.1	362.4	362.7	362.9	363.2	363.4	363.6	363.8	364.1	364.1
150°	372.8	373.0	373.1	373.3	373.5	373.6	373.8	373.9	374.1	374.2	374.2
152.5°	381.9	382.1	382.3	382.5	382.8	382.9	383.0	383.1	383.2	383.3	383.4
155°	396.2	396.2	396.2	396.2	396.2	396.2	396.3	396.3	396.4	396.5	396.8
157.5°	408.3	408.2	408.1	408.0	407.9	407.9	408.0	408.0	408.1	408.2	408.5
160°	415.9	415.8	415.6	415.5	415.3	415.2	415.2	415.2	415.2	415.2	415.6
162.5°	422.7	422.5	422.3	422.1	421.8	421.8	421.8	421.9	422.0	422.0	422.4
165°	431.5	431.3	431.0	430.8	430.5	430.4	430.4	430.4	430.4	430.4	430.9
167.5°	438.5	438.2	437.9	437.5	437.2	437.1	437.2	437.2	437.3	437.4	437.8
170°	442.4	442.1	441.8	441.5	441.2	441.0	441.0	441.0	441.0	441.0	441.6
172.5°	445.6	445.2	444.9	444.6	444.3	444.1	444.1	444.1	444.1	444.1	444.6
175°	448.8	448.5	448.2	447.9	447.6	447.4	447.4	447.4	447.4	447.4	447.9
177.5°	450.1	449.9	449.6	449.4	449.1	449.0	449.0	449.0	449.0	449.0	449.4
180°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9



TEST NUMBER: P332364

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	17.6	17.4	17.2	16.9	16.7	16.4	16.2	16.0
90°	9.1	9.4	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	14.1	14.3	14.6	14.7	14.6	14.5	14.4	14.3
95°	26.8	27.1	27.4	27.6	27.6	27.6	27.6	27.6
97.5°	41.6	42.0	42.4	42.5	42.5	42.5	42.4	42.4
100°	52.4	52.7	52.9	53.1	53.2	53.4	53.6	53.7
102.5°	64.9	65.1	65.3	65.4	65.4	65.4	65.3	65.3
105°	83.4	83.4	83.4	83.5	83.6	83.8	84.0	84.1
107.5°	103.5	103.7	104.0	104.1	104.0	103.9	103.8	103.7
110°	116.9	117.2	117.5	117.6	117.4	117.3	117.1	117.0





TEST NUMBER: P332364

CATALOG NUMBER: S123RDIP-S1165D365U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	130.3	130.7	131.1	131.2	131.2	131.2	131.1	131.1
115°	150.7	150.8	150.9	150.9	150.8	150.7	150.6	150.5
117.5°	171.3	171.3	171.3	171.1	170.9	170.7	170.5	170.3
120°	185.0	184.9	184.9	184.7	184.6	184.4	184.3	184.1
122.5°	198.9	198.7	198.5	198.3	198.1	197.8	197.6	197.4
125°	219.5	219.2	218.9	218.6	218.3	218.0	217.6	217.3
127.5°	239.9	239.5	239.0	238.6	238.3	237.9	237.6	237.2
130°	253.5	253.1	252.8	252.4	251.9	251.3	250.8	250.2
132.5°	266.6	266.2	265.9	265.5	265.0	264.6	264.2	263.8
135°	286.3	286.0	285.7	285.5	285.3	285.1	285.0	284.8
137.5°	305.6	305.3	304.9	304.6	304.3	304.0	303.7	303.4
140°	318.2	318.2	318.1	317.8	317.2	316.7	316.1	315.6
142.5°	330.1	330.0	330.0	329.7	329.3	328.9	328.4	328.0
145°	347.6	347.5	347.4	347.2	346.9	346.6	346.3	346.0
147.5°	364.1	364.1	364.1	363.8	363.4	362.9	362.4	361.9
150°	374.2	374.2	374.2	374.0	373.5	373.1	372.6	372.1
152.5°	383.5	383.7	383.8	383.6	383.2	382.8	382.4	382.0
155°	397.1	397.4	397.8	397.6	397.1	396.5	396.0	395.4
157.5°	408.8	409.2	409.5	409.4	409.0	408.6	408.1	407.7
160°	416.0	416.4	416.8	416.8	416.5	416.2	415.9	415.6
162.5°	422.8	423.2	423.6	423.5	423.0	422.5	422.0	421.5
165°	431.4	431.8	432.3	432.3	431.7	431.2	430.6	430.1
167.5°	438.3	438.8	439.3	439.3	438.8	438.3	437.8	437.4
170°	442.1	442.7	443.2	443.2	442.7	442.1	441.6	441.0
172.5°	445.1	445.6	446.1	446.1	445.5	445.0	444.4	443.9
175°	448.3	448.8	449.3	449.2	448.7	448.1	447.6	447.0
177.5°	449.8	450.1	450.5	450.5	450.1	449.6	449.2	448.7
180°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9

(END OF REPORT)