

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332338-840

Luminaire Tested: **S123RDIP-S1000D585U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332338-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D585U840-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6140.2 lumens  
Efficiency: N/A  
Efficacy: 125.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61	56
2	93	86	80	75	88	82	76	72	72	68	65	64	61	59	56	54	52	48
3	86	77	69	64	80	72	66	61	65	60	56	57	54	50	51	48	45	42
4	79	68	61	55	74	65	58	52	58	52	48	52	47	44	46	42	40	37
5	73	61	53	47	68	58	51	46	52	46	42	47	42	39	42	38	35	32
6	67	55	47	42	63	53	45	40	47	42	37	43	38	34	38	34	31	29
7	62	50	42	37	59	48	41	36	43	37	33	39	34	31	35	31	28	26
8	58	46	38	33	55	44	37	32	40	34	30	36	31	27	32	28	25	23
9	54	42	35	30	51	40	33	29	37	31	27	33	28	25	30	26	23	21
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17280	17280	17280	17280
5°	20599	17354	15282	17354
10°	25719	17254	13806	17254
15°	30190	17079	12590	17079
20°	33693	16814	11557	16814
25°	33155	16537	10922	16537
30°	23832	16281	10268	16281
35°	15912	15948	9843	15948
40°	11724	15548	9405	15548
45°	9834	14845	8977	14845
50°	8678	13924	8378	13924
55°	7610	12872	7557	12872
60°	6777	11866	6923	11866
65°	5952	10781	6441	10781
70°	4674	9819	5882	9819
75°	4117	8576	5373	8576
80°	3583	7283	5281	7283
85°	2878	5866	5595	5866



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.9	2.6
10°-20°	493.2	8.0
20°-30°	774.9	12.6
30°-40°	808.4	13.2
40°-50°	691.8	11.3
50°-60°	527.3	8.6
60°-70°	338.0	5.5
70°-80°	162.6	2.6
80°-90°	45.2	0.7
90°-100°	158.3	2.6
100°-110°	448.4	7.3
110°-120°	441.1	7.2
120°-130°	351.8	5.7
130°-140°	277.4	4.5
140°-150°	207.0	3.4
150°-160°	144.3	2.4
160°-170°	84.8	1.4
170°-180°	27.6	0.4
0°-30°	1426.0	23.2
0°-40°	2234.4	36.4
0°-60°	3453.6	56.2
0°-90°	3999.4	65.1
90°-120°	1047.8	17.1
90°-150°	1884.1	30.7
90°-180°	2141.0	34.9
0°-180°	6140.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1605	1605	1605	1605	1605	
5°	1906	1606	1414	1606	1906	197
15°	2709	1533	1130	1533	2709	768
25°	2792	1392	920	1392	2792	1200
35°	1211	1214	749	1214	1211	794
45°	646	975	590	975	646	508
55°	406	686	403	686	406	367
65°	234	423	253	423	234	230
75°	99	206	129	206	99	106
85°	23	48	45	48	23	27
90°	17	1	17	1	17	10
95°	67	20	67	20	67	120
105°	733	67	733	67	733	723
115°	891	118	891	118	891	866
125°	703	164	703	164	703	637
135°	570	192	570	192	570	442
145°	445	219	445	219	445	283
155°	369	249	369	249	369	172
165°	322	272	322	272	322	92
175°	290	284	290	284	290	28
180°	285	285	285	285	285	



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1709.9	1712.0	1705.0	1703.8	1695.6	1693.3	1693.3	1681.8	1674.7	1665.4	1659.8
5°	1906.4	1917.4	1911.9	1899.6	1879.0	1874.1	1861.1	1840.5	1817.1	1788.2	1774.4
7.5°	2151.9	2166.9	2161.1	2142.0	2120.4	2102.9	2066.2	2031.9	1984.0	1941.9	1905.9
10°	2353.1	2337.3	2324.9	2306.4	2286.4	2254.1	2215.6	2162.7	2101.6	2053.5	1999.9
12.5°	2503.8	2501.1	2485.5	2466.4	2438.2	2407.5	2360.3	2295.8	2224.7	2155.3	2093.9
15°	2709.2	2713.2	2702.9	2683.0	2643.1	2588.9	2517.4	2490.6	2388.8	2313.3	2237.7
17.5°	2851.3	2850.4	2849.0	2821.5	2780.8	2742.1	2675.8	2605.4	2513.3	2406.7	2304.9
20°	2941.4	2934.6	2935.9	2905.0	2874.8	2830.0	2765.5	2663.1	2587.5	2464.5	2359.3
22.5°	2939.2	2937.8	2943.0	2932.4	2910.5	2876.3	2825.4	2739.0	2642.4	2518.3	2400.0
25°	2791.6	2786.1	2818.4	2827.3	2862.4	2868.5	2853.5	2806.0	2714.6	2586.8	2440.4
27.5°	2336.3	2333.3	2393.3	2468.3	2563.4	2637.4	2708.9	2743.4	2714.6	2623.1	2476.4
30°	1917.4	1982.1	2012.3	2120.8	2241.8	2386.1	2512.5	2632.8	2662.4	2622.5	2502.2
32.5°	1592.0	1648.3	1673.5	1766.8	1879.5	2048.5	2238.3	2408.5	2528.8	2559.3	2486.9
35°	1210.9	1211.6	1269.3	1310.6	1415.0	1588.9	1773.1	2001.2	2228.1	2399.8	2417.7
37.5°	966.2	969.7	1004.6	1045.7	1124.1	1216.0	1378.2	1567.9	1829.9	2093.7	2248.3
40°	834.4	840.5	866.7	907.2	963.5	1032.9	1159.4	1338.1	1556.6	1850.1	2089.9
42.5°	749.6	759.7	773.2	804.4	839.3	904.2	1006.5	1144.6	1343.3	1620.8	1897.5
45°	646.0	651.5	661.9	676.2	707.8	753.3	821.9	914.7	1079.6	1303.0	1579.9
47.5°	569.9	566.9	577.8	589.6	610.6	641.5	687.5	763.3	880.9	1060.2	1295.1
50°	518.2	517.5	525.0	534.0	553.9	576.6	614.4	671.5	764.9	913.3	1128.4
52.5°	469.8	472.4	477.8	488.9	503.3	521.6	555.5	596.6	676.9	805.1	984.4
55°	405.5	407.6	415.1	421.3	431.6	450.1	471.4	505.8	560.8	650.2	797.9
57.5°	351.0	350.1	357.4	358.9	370.5	385.7	402.1	428.9	468.7	535.1	634.6
60°	314.8	312.7	318.9	323.7	329.9	342.2	356.0	382.1	413.7	462.5	547.8
62.5°	281.8	280.8	285.4	290.1	295.3	306.5	318.1	338.1	363.1	404.2	471.9
65°	233.7	235.7	237.8	239.8	242.6	249.4	260.4	274.2	291.3	320.2	369.0
67.5°	183.6	185.7	186.4	190.7	196.5	200.9	207.5	219.7	231.8	256.1	283.9
70°	148.5	147.7	148.5	150.5	158.0	165.6	174.6	183.5	191.1	208.2	231.6
72.5°	127.5	126.3	128.2	128.6	132.2	134.3	140.0	148.3	158.0	169.8	186.5
75°	99.0	99.0	99.0	99.0	101.7	103.1	105.1	107.2	110.7	116.1	128.6
77.5°	73.1	73.2	74.2	74.9	75.4	76.2	77.6	79.6	80.8	83.7	89.1
80°	57.8	58.4	57.8	58.4	58.4	59.8	60.5	62.5	63.2	66.7	68.8
82.5°	43.4	43.0	43.4	44.1	44.1	45.5	45.6	47.2	47.3	49.1	51.1
85°	23.3	22.0	23.3	22.7	24.0	22.7	23.3	24.7	24.7	25.4	28.2
87.5°	8.9	10.1	8.9	9.3	9.4	9.7	9.6	9.5	10.5	10.0	10.2
90°	16.7	17.3	16.7	16.2	16.7	15.6	14.9	14.4	13.8	14.4	12.6
92.5°	27.8	28.8	28.2	30.0	31.0	34.0	38.5	48.5	66.9	88.6	97.5
95°	66.9	69.1	73.1	78.4	89.3	110.0	140.6	207.3	277.0	341.5	304.2
97.5°	181.9	186.8	202.4	228.3	270.8	339.7	414.0	516.9	566.3	529.4	387.5
100°	361.1	360.6	383.0	425.1	483.2	565.0	632.5	679.1	658.9	545.4	368.6
102.5°	529.8	543.0	561.8	595.1	640.4	692.3	731.5	733.1	663.6	515.5	341.0
105°	732.7	735.6	754.0	775.9	802.3	817.4	806.4	748.8	628.4	463.1	307.0
107.5°	849.5	854.7	861.0	868.4	867.9	847.4	797.0	703.4	566.9	416.8	285.4
110°	897.4	898.6	899.7	895.1	879.0	838.7	766.1	660.0	528.2	390.5	277.0



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	907.1	906.9	902.5	888.2	858.7	806.9	725.5	617.2	494.5	373.0	272.5
115°	891.1	888.2	876.7	851.3	808.1	745.4	660.7	560.5	453.9	354.3	270.7
117.5°	840.1	836.3	819.6	790.6	745.6	681.9	605.8	519.3	429.4	343.2	271.8
120°	797.8	794.3	780.5	748.2	702.8	644.5	575.4	497.7	416.5	338.1	273.6
122.5°	758.1	753.8	738.5	709.5	669.0	615.0	551.0	480.6	405.9	334.9	276.8
125°	702.8	698.7	684.3	658.9	622.1	576.0	520.7	457.9	392.2	330.6	281.7
127.5°	657.1	653.4	640.4	618.7	585.9	544.0	494.1	438.1	380.3	328.5	287.2
130°	631.3	626.7	614.6	593.9	563.3	524.1	477.5	425.7	373.9	327.2	290.8
132.5°	605.9	602.7	592.0	571.3	542.6	505.2	461.8	414.1	367.8	326.7	293.7
135°	569.7	565.6	555.2	538.0	509.8	477.0	439.5	398.6	360.0	326.0	297.8
137.5°	531.3	528.7	519.9	502.4	478.7	450.2	418.0	384.5	353.3	324.8	300.5
140°	504.5	505.1	495.9	479.8	457.9	433.1	405.5	376.2	349.0	324.3	302.4
142.5°	479.7	480.3	472.0	457.7	439.0	417.5	393.5	368.3	345.4	323.4	303.8
145°	445.2	444.1	439.5	427.4	413.0	396.3	377.9	358.8	340.4	321.9	304.7
147.5°	416.9	416.5	412.0	403.8	392.9	381.1	366.2	351.1	335.6	319.8	304.7
150°	400.3	400.3	396.9	390.5	381.9	370.9	358.8	345.6	332.3	317.9	304.7
152.5°	386.5	386.5	384.5	378.5	371.7	362.6	351.9	340.5	328.7	315.7	303.4
155°	369.2	368.6	367.5	362.8	357.7	350.8	342.1	333.0	323.2	311.6	301.8
157.5°	353.5	353.6	352.6	349.2	344.7	339.3	332.5	324.9	316.9	308.0	299.8
160°	343.3	343.9	343.9	340.4	336.4	332.3	326.6	320.2	312.8	305.3	298.9
162.5°	334.1	334.7	334.7	331.6	329.0	325.5	320.1	314.8	308.6	302.6	297.1
165°	321.9	321.9	322.6	320.2	317.9	315.1	311.0	307.6	303.0	298.4	294.4
167.5°	310.4	310.4	311.0	309.4	308.4	306.3	304.0	301.3	297.6	294.2	291.5
170°	303.6	303.6	304.2	303.0	302.4	301.2	298.9	297.2	294.4	291.4	289.7
172.5°	297.1	297.6	298.6	297.4	297.3	296.6	294.8	293.6	291.1	289.1	288.3
175°	289.7	290.3	290.8	290.3	290.3	290.3	289.1	288.6	287.4	286.3	286.3
177.5°	285.5	285.5	286.4	285.9	286.4	286.4	285.9	285.5	285.0	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1657.6	1656.0	1648.3	1639.5	1627.9	1620.2	1614.2	1610.9	1601.0	1588.9	1580.6
5°	1760.0	1739.4	1717.5	1690.6	1665.9	1640.4	1624.7	1606.1	1583.4	1558.0	1540.1
7.5°	1869.8	1829.3	1785.7	1740.8	1696.4	1656.6	1621.3	1591.2	1555.1	1518.6	1493.1
10°	1953.9	1894.7	1833.6	1771.0	1713.9	1660.4	1619.1	1578.6	1535.3	1493.4	1461.8
12.5°	2030.2	1952.5	1882.0	1805.1	1732.1	1668.1	1608.7	1561.0	1508.9	1464.2	1428.3
15°	2127.0	2047.3	1962.1	1845.2	1748.4	1667.3	1595.1	1532.6	1469.4	1414.3	1379.3
17.5°	2217.5	2097.5	1983.0	1885.5	1759.6	1658.3	1570.2	1495.4	1426.0	1367.8	1324.6
20°	2254.8	2138.7	2014.3	1890.0	1766.3	1652.8	1550.4	1467.9	1395.8	1329.8	1290.0
22.5°	2277.3	2145.9	2014.9	1881.2	1749.7	1631.9	1530.7	1440.0	1361.7	1299.0	1249.8
25°	2303.6	2147.0	2002.7	1870.7	1736.7	1608.8	1488.5	1392.4	1307.9	1241.1	1188.9
27.5°	2321.0	2136.7	1966.1	1819.4	1683.4	1556.2	1445.9	1343.9	1258.2	1187.7	1131.7
30°	2324.3	2128.4	1938.0	1779.3	1641.1	1524.3	1407.4	1309.9	1219.2	1144.3	1092.1
32.5°	2328.6	2108.1	1900.1	1731.4	1590.0	1474.3	1368.5	1275.3	1182.3	1108.5	1055.2
35°	2310.6	2096.8	1842.5	1648.7	1507.1	1395.1	1299.6	1213.7	1122.3	1050.8	996.5
37.5°	2232.4	2052.1	1782.8	1555.5	1407.4	1303.7	1225.9	1151.0	1067.1	990.1	938.9
40°	2153.8	2008.1	1736.7	1498.8	1344.2	1237.7	1167.6	1106.5	1025.4	953.2	898.3
42.5°	2036.7	1948.2	1692.7	1439.5	1272.7	1170.1	1111.0	1053.7	982.5	909.2	857.6
45°	1821.9	1833.6	1602.7	1344.9	1173.8	1070.8	1015.0	975.2	912.0	851.5	798.6
47.5°	1552.5	1661.7	1496.9	1244.2	1069.4	972.7	924.0	889.3	846.7	787.3	739.0
50°	1376.5	1532.6	1412.3	1176.6	1004.1	907.9	859.7	831.5	794.5	747.7	701.7
52.5°	1214.4	1381.9	1310.0	1101.3	933.1	845.2	798.2	775.0	745.5	701.6	659.8
55°	990.3	1160.0	1143.6	987.5	826.8	747.7	712.0	685.9	665.9	633.0	600.0
57.5°	801.0	962.0	970.5	861.1	733.1	654.9	624.2	604.5	591.5	566.5	536.0
60°	681.8	829.5	858.4	775.9	665.9	597.2	566.9	551.2	540.9	520.9	497.6
62.5°	582.8	708.5	741.2	681.9	601.6	537.2	513.6	498.4	491.4	474.2	453.6
65°	446.1	550.5	582.1	549.1	507.2	455.7	436.4	423.3	417.2	407.6	392.4
67.5°	335.4	411.5	446.2	422.9	407.8	375.3	363.0	356.0	350.5	343.9	331.2
70°	269.4	325.8	361.5	355.3	343.0	325.8	316.8	312.0	306.5	301.0	290.0
72.5°	216.6	255.4	288.9	292.1	282.0	278.5	270.6	268.6	265.3	258.7	252.7
75°	143.6	170.5	193.8	202.8	206.8	210.3	206.8	206.2	205.5	200.0	196.5
77.5°	94.1	108.6	123.3	138.6	145.0	149.7	150.8	153.3	151.5	148.6	146.9
80°	72.2	75.6	85.9	99.0	109.3	113.4	116.1	117.5	116.8	116.1	113.4
82.5°	52.4	55.2	60.1	69.3	78.0	84.8	86.4	86.1	87.7	88.1	85.9
85°	28.2	28.9	30.2	31.6	36.5	44.0	46.0	47.5	48.8	48.8	44.6
87.5°	11.0	10.1	10.8	10.6	12.0	12.2	15.3	17.8	18.6	16.7	17.0
90°	10.9	9.2	7.5	6.4	5.2	3.4	2.3	1.1	2.3	3.4	5.2
92.5°	73.1	48.4	33.3	24.7	19.9	15.5	10.6	7.2	10.6	15.5	19.9
95°	209.6	123.8	74.8	52.4	37.5	27.7	21.3	19.6	21.3	27.7	37.5
97.5°	230.0	133.3	86.5	62.2	47.5	39.0	34.0	33.4	34.0	39.0	47.5
100°	217.1	131.9	91.6	69.1	55.3	47.3	43.2	42.6	43.2	47.3	55.3
102.5°	206.1	133.7	97.6	77.0	64.5	57.0	53.3	52.3	53.3	57.0	64.5
105°	198.1	138.9	107.8	89.9	78.9	72.0	68.6	66.9	68.6	72.0	78.9
107.5°	197.5	148.2	121.0	104.4	94.1	87.4	84.0	82.2	84.0	87.4	94.1
110°	199.9	156.1	130.2	114.0	104.2	98.0	95.0	93.3	95.0	98.0	104.2





TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	204.5	163.9	139.9	124.2	114.4	108.1	105.2	103.4	105.2	108.1	114.4
115°	212.0	176.8	154.9	139.4	129.6	123.8	120.4	118.1	120.4	123.8	129.6
117.5°	221.9	190.6	168.8	154.5	143.5	138.3	135.3	132.7	135.3	138.3	143.5
120°	229.2	199.2	178.5	164.2	153.2	147.4	144.6	142.9	144.6	147.4	153.2
122.5°	236.2	208.5	188.2	172.9	162.4	156.2	153.3	151.6	153.3	156.2	162.4
125°	247.1	221.8	201.6	186.0	175.1	168.7	165.3	164.2	165.3	168.7	175.1
127.5°	256.1	233.3	213.8	198.2	186.1	179.8	175.4	173.7	175.4	179.8	186.1
130°	262.1	240.1	221.2	205.6	193.5	186.6	181.5	179.8	181.5	186.6	193.5
132.5°	267.6	246.2	227.6	212.6	200.5	192.2	186.5	184.3	186.5	192.2	200.5
135°	274.8	255.2	237.3	221.8	209.6	201.1	194.7	192.4	194.7	201.1	209.6
137.5°	280.0	261.4	244.2	229.8	217.8	208.6	202.4	200.0	202.4	208.6	217.8
140°	282.9	265.5	248.8	234.4	222.9	213.7	207.9	205.1	207.9	213.7	222.9
142.5°	285.6	268.7	252.6	239.0	227.5	219.2	213.0	210.6	213.0	219.2	227.5
145°	288.6	273.1	258.0	244.8	235.0	226.4	221.2	219.4	221.2	226.4	235.0
147.5°	290.4	276.5	262.8	251.5	242.1	234.6	229.4	228.4	229.4	234.6	242.1
150°	290.8	278.8	265.5	255.2	247.1	239.6	235.0	234.4	235.0	239.6	247.1
152.5°	291.9	280.1	268.7	258.8	251.8	245.2	240.5	240.4	240.5	245.2	251.8
155°	292.1	282.9	273.1	265.0	258.6	252.9	249.4	249.4	249.4	252.9	258.6
157.5°	292.7	284.3	276.5	270.2	264.9	259.7	257.0	256.5	257.0	259.7	264.9
160°	292.7	285.7	278.8	273.1	269.0	264.4	262.1	262.1	262.1	264.4	269.0
162.5°	292.2	286.2	280.1	275.3	271.8	268.1	266.2	266.2	266.2	268.1	271.8
165°	290.8	286.8	282.3	278.2	275.9	273.1	271.9	272.5	271.9	273.1	275.9
167.5°	289.9	286.7	283.4	280.8	279.2	277.0	276.5	277.2	276.5	277.0	279.2
170°	288.6	286.3	283.4	282.3	281.0	279.3	278.8	279.9	278.8	279.3	281.0
172.5°	288.1	286.3	283.9	283.2	282.5	281.2	281.0	281.8	281.0	281.2	282.5
175°	286.8	285.7	284.6	284.0	284.0	282.9	283.4	284.0	283.4	282.9	284.0
177.5°	285.9	285.0	284.6	284.6	284.6	284.1	284.6	285.0	284.6	284.1	284.6
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1577.9	1570.7	1565.8	1554.8	1547.7	1539.9	1532.3	1537.2	1536.7	1536.1	1536.1
5°	1525.0	1509.1	1494.8	1476.2	1464.5	1450.1	1439.1	1437.7	1440.5	1430.9	1425.3
7.5°	1472.5	1450.9	1430.5	1410.0	1388.3	1370.9	1360.1	1354.9	1348.0	1342.0	1335.8
10°	1435.6	1410.3	1390.3	1364.8	1341.5	1320.9	1307.9	1298.9	1294.0	1289.3	1280.3
12.5°	1397.8	1372.8	1347.5	1318.7	1296.5	1272.5	1262.7	1252.7	1243.5	1238.1	1225.9
15°	1342.2	1309.9	1283.1	1252.8	1228.1	1204.8	1191.0	1171.0	1168.3	1161.4	1149.1
17.5°	1286.6	1251.4	1214.5	1192.1	1164.2	1139.8	1118.9	1112.3	1092.6	1085.2	1074.4
20°	1242.5	1210.2	1182.0	1152.6	1112.0	1089.2	1072.8	1063.9	1048.0	1038.4	1031.6
22.5°	1204.6	1171.7	1139.2	1104.7	1071.3	1045.8	1033.8	1019.9	1011.2	997.7	990.3
25°	1150.4	1114.7	1075.5	1038.4	1014.4	995.1	975.9	963.5	951.2	944.9	931.2
27.5°	1087.5	1050.2	1013.5	985.3	955.8	936.9	919.4	908.4	893.5	883.1	875.6
30°	1052.9	1008.9	977.2	951.8	914.0	896.2	883.1	869.4	858.4	847.4	839.8
32.5°	1012.7	972.6	942.6	911.2	882.1	862.6	845.8	833.6	824.3	813.9	806.3
35°	949.8	916.1	885.1	853.5	832.2	812.3	792.4	782.0	773.2	763.6	756.7
37.5°	892.8	861.4	832.0	802.0	775.6	759.4	743.4	735.5	723.4	716.9	709.9
40°	857.7	826.8	795.2	766.3	738.8	726.4	712.0	700.3	689.3	684.5	676.9
42.5°	819.2	788.3	761.6	730.5	708.0	691.3	677.9	665.1	656.9	649.8	645.6
45°	762.1	734.7	708.5	677.6	656.3	641.9	626.7	615.1	607.5	602.7	595.1
47.5°	706.8	679.2	652.8	625.8	605.2	588.7	573.6	565.4	555.4	549.6	544.4
50°	666.6	641.9	613.7	589.0	568.4	551.9	539.5	529.2	520.3	512.7	509.3
52.5°	629.8	603.4	579.1	556.0	534.2	515.5	504.3	493.4	486.8	478.1	474.0
55°	569.1	543.6	523.0	500.3	479.0	463.2	449.5	439.8	432.9	423.3	417.9
57.5°	512.0	489.2	464.5	444.9	422.9	409.6	398.2	385.2	376.8	369.2	363.9
60°	473.5	447.4	426.1	407.6	388.3	371.1	360.8	350.5	341.5	334.0	329.2
62.5°	433.3	410.6	390.3	370.1	352.5	337.6	325.6	317.0	309.1	304.3	299.5
65°	371.8	354.0	333.4	316.8	300.3	289.3	279.7	272.2	266.6	263.2	259.1
67.5°	315.2	297.8	279.8	263.7	252.7	244.3	237.9	231.5	228.7	224.3	221.6
70°	278.3	260.4	244.7	232.3	221.3	215.1	211.0	206.2	203.4	197.9	195.2
72.5°	238.2	225.3	213.9	203.7	194.9	189.2	184.0	178.1	173.7	167.6	164.9
75°	187.6	175.9	167.0	160.2	154.6	147.0	139.5	133.3	131.3	129.2	128.6
77.5°	139.0	131.6	125.1	119.3	112.4	106.9	105.3	103.9	103.5	102.4	102.4
80°	109.3	102.4	97.6	90.7	86.5	86.5	86.5	85.2	85.9	85.9	85.9
82.5°	81.2	74.9	72.3	69.8	69.0	69.6	69.6	69.8	69.4	70.5	70.0
85°	41.9	42.6	44.0	43.3	44.0	44.0	45.3	44.6	45.3	44.0	45.3
87.5°	16.7	18.6	19.4	20.3	21.2	21.0	21.4	21.6	22.2	22.3	22.6
90°	6.4	7.5	9.2	10.9	12.6	14.4	13.8	14.4	14.9	15.6	16.7
92.5°	24.7	33.3	48.4	73.1	97.5	88.6	66.9	48.5	38.5	34.0	31.0
95°	52.4	74.8	123.8	209.6	304.2	341.5	277.0	207.3	140.6	110.0	89.3
97.5°	62.2	86.5	133.3	230.0	387.5	529.4	566.3	516.9	414.0	339.7	270.8
100°	69.1	91.6	131.9	217.1	368.6	545.4	658.9	679.1	632.5	565.0	483.2
102.5°	77.0	97.6	133.7	206.1	341.0	515.5	663.6	733.1	731.5	692.3	640.4
105°	89.9	107.8	138.9	198.1	307.0	463.1	628.4	748.8	806.4	817.4	802.3
107.5°	104.4	121.0	148.2	197.5	285.4	416.8	566.9	703.4	797.0	847.4	867.9
110°	114.0	130.2	156.1	199.9	277.0	390.5	528.2	660.0	766.1	838.7	879.0



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	124.2	139.9	163.9	204.5	272.5	373.0	494.5	617.2	725.5	806.9	858.7
115°	139.4	154.9	176.8	212.0	270.7	354.3	453.9	560.5	660.7	745.4	808.1
117.5°	154.5	168.8	190.6	221.9	271.8	343.2	429.4	519.3	605.8	681.9	745.6
120°	164.2	178.5	199.2	229.2	273.6	338.1	416.5	497.7	575.4	644.5	702.8
122.5°	172.9	188.2	208.5	236.2	276.8	334.9	405.9	480.6	551.0	615.0	669.0
125°	186.0	201.6	221.8	247.1	281.7	330.6	392.2	457.9	520.7	576.0	622.1
127.5°	198.2	213.8	233.3	256.1	287.2	328.5	380.3	438.1	494.1	544.0	585.9
130°	205.6	221.2	240.1	262.1	290.8	327.2	373.9	425.7	477.5	524.1	563.3
132.5°	212.6	227.6	246.2	267.6	293.7	326.7	367.8	414.1	461.8	505.2	542.6
135°	221.8	237.3	255.2	274.8	297.8	326.0	360.0	398.6	439.5	477.0	509.8
137.5°	229.8	244.2	261.4	280.0	300.5	324.8	353.3	384.5	418.0	450.2	478.7
140°	234.4	248.8	265.5	282.9	302.4	324.3	349.0	376.2	405.5	433.1	457.9
142.5°	239.0	252.6	268.7	285.6	303.8	323.4	345.4	368.3	393.5	417.5	439.0
145°	244.8	258.0	273.1	288.6	304.7	321.9	340.4	358.8	377.9	396.3	413.0
147.5°	251.5	262.8	276.5	290.4	304.7	319.8	335.6	351.1	366.2	381.1	392.9
150°	255.2	265.5	278.8	290.8	304.7	317.9	332.3	345.6	358.8	370.9	381.9
152.5°	258.8	268.7	280.1	291.9	303.4	315.7	328.7	340.5	351.9	362.6	371.7
155°	265.0	273.1	282.9	292.1	301.8	311.6	323.2	333.0	342.1	350.8	357.7
157.5°	270.2	276.5	284.3	292.7	299.8	308.0	316.9	324.9	332.5	339.3	344.7
160°	273.1	278.8	285.7	292.7	298.9	305.3	312.8	320.2	326.6	332.3	336.4
162.5°	275.3	280.1	286.2	292.2	297.1	302.6	308.6	314.8	320.1	325.5	329.0
165°	278.2	282.3	286.8	290.8	294.4	298.4	303.0	307.6	311.0	315.1	317.9
167.5°	280.8	283.4	286.7	289.9	291.5	294.2	297.6	301.3	304.0	306.3	308.4
170°	282.3	283.4	286.3	288.6	289.7	291.4	294.4	297.2	298.9	301.2	302.4
172.5°	283.2	283.9	286.3	288.1	288.3	289.1	291.1	293.6	294.8	296.6	297.3
175°	284.0	284.6	285.7	286.8	286.3	286.3	287.4	288.6	289.1	290.3	290.3
177.5°	284.6	284.6	285.0	285.9	285.0	284.6	285.0	285.5	285.9	286.4	286.4
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1529.5	1528.9	1529.5	1527.3	1529.5	1528.9	1529.5	1536.1	1536.1	1536.7	1537.2
5°	1423.3	1422.6	1420.6	1414.3	1420.6	1422.6	1423.3	1425.3	1430.9	1440.5	1437.7
7.5°	1330.5	1329.6	1323.5	1323.6	1323.5	1329.6	1330.5	1335.8	1342.0	1348.0	1354.9
10°	1275.6	1276.2	1268.0	1263.1	1268.0	1276.2	1275.6	1280.3	1289.3	1294.0	1298.9
12.5°	1222.2	1219.0	1212.4	1207.1	1212.4	1219.0	1222.2	1225.9	1238.1	1243.5	1252.7
15°	1151.9	1145.0	1128.4	1129.8	1128.4	1145.0	1151.9	1149.1	1161.4	1168.3	1171.0
17.5°	1068.9	1063.9	1063.6	1054.0	1063.6	1063.9	1068.9	1074.4	1085.2	1092.6	1112.3
20°	1020.6	1017.1	1018.4	1008.9	1018.4	1017.1	1020.6	1031.6	1038.4	1048.0	1063.9
22.5°	982.6	979.2	973.4	970.4	973.4	979.2	982.6	990.3	997.7	1011.2	1019.9
25°	927.1	921.6	916.1	919.6	916.1	921.6	927.1	931.2	944.9	951.2	963.5
27.5°	871.6	867.5	861.9	861.2	861.9	867.5	871.6	875.6	883.1	893.5	908.4
30°	836.4	832.2	829.5	826.1	829.5	832.2	836.4	839.8	847.4	858.4	869.4
32.5°	800.6	799.8	794.9	794.2	794.9	799.8	800.6	806.3	813.9	824.3	833.6
35°	753.9	749.8	748.4	749.1	748.4	749.8	753.9	756.7	763.6	773.2	782.0
37.5°	709.5	704.0	701.6	699.0	701.6	704.0	709.5	709.9	716.9	723.4	735.5
40°	677.6	672.2	670.8	669.3	670.8	672.2	677.6	676.9	684.5	689.3	700.3
42.5°	641.9	639.6	638.8	636.4	638.8	639.6	641.9	645.6	649.8	656.9	665.1
45°	593.1	592.4	588.2	589.7	588.2	592.4	593.1	595.1	602.7	607.5	615.1
47.5°	541.7	538.7	535.7	537.7	535.7	538.7	541.7	544.4	549.6	555.4	565.4
50°	506.5	505.1	499.0	500.3	499.0	505.1	506.5	509.3	512.7	520.3	529.2
52.5°	471.3	466.1	463.7	462.9	463.7	466.1	471.3	474.0	478.1	486.8	493.4
55°	413.0	406.9	404.1	402.7	404.1	406.9	413.0	417.9	423.3	432.9	439.8
57.5°	355.9	354.2	352.0	353.6	352.0	354.2	355.9	363.9	369.2	376.8	385.2
60°	322.3	322.3	322.3	321.6	322.3	322.3	322.3	329.2	334.0	341.5	350.5
62.5°	296.5	294.8	294.3	295.3	294.3	294.8	296.5	299.5	304.3	309.1	317.0
65°	257.0	256.3	253.6	252.9	253.6	256.3	257.0	259.1	263.2	266.6	272.2
67.5°	219.7	217.3	216.5	215.5	216.5	217.3	219.7	221.6	224.3	228.7	231.5
70°	191.8	190.4	186.2	186.9	186.2	190.4	191.8	195.2	197.9	203.4	206.2
72.5°	161.5	160.2	159.3	158.3	159.3	160.2	161.5	164.9	167.6	173.7	178.1
75°	127.8	127.1	126.4	129.2	126.4	127.1	127.8	128.6	129.2	131.3	133.3
77.5°	102.4	102.4	102.8	101.7	102.8	102.4	102.4	102.4	102.4	103.5	103.9
80°	85.9	85.9	85.2	85.2	85.2	85.9	85.9	85.9	85.9	85.9	85.2
82.5°	68.9	69.4	69.8	68.8	69.8	69.4	68.9	70.0	70.5	69.4	69.8
85°	45.3	44.6	46.0	45.3	46.0	44.6	45.3	45.3	44.0	45.3	44.6
87.5°	23.5	22.6	22.7	23.1	22.7	22.6	23.5	22.6	22.3	22.2	21.6
90°	16.2	16.7	17.3	16.7	17.3	16.7	16.2	16.7	15.6	14.9	14.4
92.5°	30.0	28.2	28.8	27.8	28.8	28.2	30.0	31.0	34.0	38.5	48.5
95°	78.4	73.1	69.1	66.9	69.1	73.1	78.4	89.3	110.0	140.6	207.3
97.5°	228.3	202.4	186.8	181.9	186.8	202.4	228.3	270.8	339.7	414.0	516.9
100°	425.1	383.0	360.6	361.1	360.6	383.0	425.1	483.2	565.0	632.5	679.1
102.5°	595.1	561.8	543.0	529.8	543.0	561.8	595.1	640.4	692.3	731.5	733.1
105°	775.9	754.0	735.6	732.7	735.6	754.0	775.9	802.3	817.4	806.4	748.8
107.5°	868.4	861.0	854.7	849.5	854.7	861.0	868.4	867.9	847.4	797.0	703.4
110°	895.1	899.7	898.6	897.4	898.6	899.7	895.1	879.0	838.7	766.1	660.0



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	888.2	902.5	906.9	907.1	906.9	902.5	888.2	858.7	806.9	725.5	617.2
115°	851.3	876.7	888.2	891.1	888.2	876.7	851.3	808.1	745.4	660.7	560.5
117.5°	790.6	819.6	836.3	840.1	836.3	819.6	790.6	745.6	681.9	605.8	519.3
120°	748.2	780.5	794.3	797.8	794.3	780.5	748.2	702.8	644.5	575.4	497.7
122.5°	709.5	738.5	753.8	758.1	753.8	738.5	709.5	669.0	615.0	551.0	480.6
125°	658.9	684.3	698.7	702.8	698.7	684.3	658.9	622.1	576.0	520.7	457.9
127.5°	618.7	640.4	653.4	657.1	653.4	640.4	618.7	585.9	544.0	494.1	438.1
130°	593.9	614.6	626.7	631.3	626.7	614.6	593.9	563.3	524.1	477.5	425.7
132.5°	571.3	592.0	602.7	605.9	602.7	592.0	571.3	542.6	505.2	461.8	414.1
135°	538.0	555.2	565.6	569.7	565.6	555.2	538.0	509.8	477.0	439.5	398.6
137.5°	502.4	519.9	528.7	531.3	528.7	519.9	502.4	478.7	450.2	418.0	384.5
140°	479.8	495.9	505.1	504.5	505.1	495.9	479.8	457.9	433.1	405.5	376.2
142.5°	457.7	472.0	480.3	479.7	480.3	472.0	457.7	439.0	417.5	393.5	368.3
145°	427.4	439.5	444.1	445.2	444.1	439.5	427.4	413.0	396.3	377.9	358.8
147.5°	403.8	412.0	416.5	416.9	416.5	412.0	403.8	392.9	381.1	366.2	351.1
150°	390.5	396.9	400.3	400.3	400.3	396.9	390.5	381.9	370.9	358.8	345.6
152.5°	378.5	384.5	386.5	386.5	386.5	384.5	378.5	371.7	362.6	351.9	340.5
155°	362.8	367.5	368.6	369.2	368.6	367.5	362.8	357.7	350.8	342.1	333.0
157.5°	349.2	352.6	353.6	353.5	353.6	352.6	349.2	344.7	339.3	332.5	324.9
160°	340.4	343.9	343.9	343.3	343.9	343.9	340.4	336.4	332.3	326.6	320.2
162.5°	331.6	334.7	334.7	334.1	334.7	334.7	331.6	329.0	325.5	320.1	314.8
165°	320.2	322.6	321.9	321.9	321.9	322.6	320.2	317.9	315.1	311.0	307.6
167.5°	309.4	311.0	310.4	310.4	310.4	311.0	309.4	308.4	306.3	304.0	301.3
170°	303.0	304.2	303.6	303.6	303.6	304.2	303.0	302.4	301.2	298.9	297.2
172.5°	297.4	298.6	297.6	297.1	297.6	298.6	297.4	297.3	296.6	294.8	293.6
175°	290.3	290.8	290.3	289.7	290.3	290.8	290.3	290.3	290.3	289.1	288.6
177.5°	285.9	286.4	285.5	285.5	285.5	286.4	285.9	286.4	286.4	285.9	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1532.3	1539.9	1547.7	1554.8	1565.8	1570.7	1577.9	1580.6	1588.9	1601.0	1610.9
5°	1439.1	1450.1	1464.5	1476.2	1494.8	1509.1	1525.0	1540.1	1558.0	1583.4	1606.1
7.5°	1360.1	1370.9	1388.3	1410.0	1430.5	1450.9	1472.5	1493.1	1518.6	1555.1	1591.2
10°	1307.9	1320.9	1341.5	1364.8	1390.3	1410.3	1435.6	1461.8	1493.4	1535.3	1578.6
12.5°	1262.7	1272.5	1296.5	1318.7	1347.5	1372.8	1397.8	1428.3	1464.2	1508.9	1561.0
15°	1191.0	1204.8	1228.1	1252.8	1283.1	1309.9	1342.2	1379.3	1414.3	1469.4	1532.6
17.5°	1118.9	1139.8	1164.2	1192.1	1214.5	1251.4	1286.6	1324.6	1367.8	1426.0	1495.4
20°	1072.8	1089.2	1112.0	1152.6	1182.0	1210.2	1242.5	1290.0	1329.8	1395.8	1467.9
22.5°	1033.8	1045.8	1071.3	1104.7	1139.2	1171.7	1204.6	1249.8	1299.0	1361.7	1440.0
25°	975.9	995.1	1014.4	1038.4	1075.5	1114.7	1150.4	1188.9	1241.1	1307.9	1392.4
27.5°	919.4	936.9	955.8	985.3	1013.5	1050.2	1087.5	1131.7	1187.7	1258.2	1343.9
30°	883.1	896.2	914.0	951.8	977.2	1008.9	1052.9	1092.1	1144.3	1219.2	1309.9
32.5°	845.8	862.6	882.1	911.2	942.6	972.6	1012.7	1055.2	1108.5	1182.3	1275.3
35°	792.4	812.3	832.2	853.5	885.1	916.1	949.8	996.5	1050.8	1122.3	1213.7
37.5°	743.4	759.4	775.6	802.0	832.0	861.4	892.8	938.9	990.1	1067.1	1151.0
40°	712.0	726.4	738.8	766.3	795.2	826.8	857.7	898.3	953.2	1025.4	1106.5
42.5°	677.9	691.3	708.0	730.5	761.6	788.3	819.2	857.6	909.2	982.5	1053.7
45°	626.7	641.9	656.3	677.6	708.5	734.7	762.1	798.6	851.5	912.0	975.2
47.5°	573.6	588.7	605.2	625.8	652.8	679.2	706.8	739.0	787.3	846.7	889.3
50°	539.5	551.9	568.4	589.0	613.7	641.9	666.6	701.7	747.7	794.5	831.5
52.5°	504.3	515.5	534.2	556.0	579.1	603.4	629.8	659.8	701.6	745.5	775.0
55°	449.5	463.2	479.0	500.3	523.0	543.6	569.1	600.0	633.0	665.9	685.9
57.5°	398.2	409.6	422.9	444.9	464.5	489.2	512.0	536.0	566.5	591.5	604.5
60°	360.8	371.1	388.3	407.6	426.1	447.4	473.5	497.6	520.9	540.9	551.2
62.5°	325.6	337.6	352.5	370.1	390.3	410.6	433.3	453.6	474.2	491.4	498.4
65°	279.7	289.3	300.3	316.8	333.4	354.0	371.8	392.4	407.6	417.2	423.3
67.5°	237.9	244.3	252.7	263.7	279.8	297.8	315.2	331.2	343.9	350.5	356.0
70°	211.0	215.1	221.3	232.3	244.7	260.4	278.3	290.0	301.0	306.5	312.0
72.5°	184.0	189.2	194.9	203.7	213.9	225.3	238.2	252.7	258.7	265.3	268.6
75°	139.5	147.0	154.6	160.2	167.0	175.9	187.6	196.5	200.0	205.5	206.2
77.5°	105.3	106.9	112.4	119.3	125.1	131.6	139.0	146.9	148.6	151.5	153.3
80°	86.5	86.5	86.5	90.7	97.6	102.4	109.3	113.4	116.1	116.8	117.5
82.5°	69.6	69.6	69.0	69.8	72.3	74.9	81.2	85.9	88.1	87.7	86.1
85°	45.3	44.0	44.0	43.3	44.0	42.6	41.9	44.6	48.8	48.8	47.5
87.5°	21.4	21.0	21.2	20.3	19.4	18.6	16.7	17.0	16.7	18.6	17.8
90°	13.8	14.4	12.6	10.9	9.2	7.5	6.4	5.2	3.4	2.3	1.1
92.5°	66.9	88.6	97.5	73.1	48.4	33.3	24.7	19.9	15.5	10.6	7.2
95°	277.0	341.5	304.2	209.6	123.8	74.8	52.4	37.5	27.7	21.3	19.6
97.5°	566.3	529.4	387.5	230.0	133.3	86.5	62.2	47.5	39.0	34.0	33.4
100°	658.9	545.4	368.6	217.1	131.9	91.6	69.1	55.3	47.3	43.2	42.6
102.5°	663.6	515.5	341.0	206.1	133.7	97.6	77.0	64.5	57.0	53.3	52.3
105°	628.4	463.1	307.0	198.1	138.9	107.8	89.9	78.9	72.0	68.6	66.9
107.5°	566.9	416.8	285.4	197.5	148.2	121.0	104.4	94.1	87.4	84.0	82.2
110°	528.2	390.5	277.0	199.9	156.1	130.2	114.0	104.2	98.0	95.0	93.3



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.5	373.0	272.5	204.5	163.9	139.9	124.2	114.4	108.1	105.2	103.4
115°	453.9	354.3	270.7	212.0	176.8	154.9	139.4	129.6	123.8	120.4	118.1
117.5°	429.4	343.2	271.8	221.9	190.6	168.8	154.5	143.5	138.3	135.3	132.7
120°	416.5	338.1	273.6	229.2	199.2	178.5	164.2	153.2	147.4	144.6	142.9
122.5°	405.9	334.9	276.8	236.2	208.5	188.2	172.9	162.4	156.2	153.3	151.6
125°	392.2	330.6	281.7	247.1	221.8	201.6	186.0	175.1	168.7	165.3	164.2
127.5°	380.3	328.5	287.2	256.1	233.3	213.8	198.2	186.1	179.8	175.4	173.7
130°	373.9	327.2	290.8	262.1	240.1	221.2	205.6	193.5	186.6	181.5	179.8
132.5°	367.8	326.7	293.7	267.6	246.2	227.6	212.6	200.5	192.2	186.5	184.3
135°	360.0	326.0	297.8	274.8	255.2	237.3	221.8	209.6	201.1	194.7	192.4
137.5°	353.3	324.8	300.5	280.0	261.4	244.2	229.8	217.8	208.6	202.4	200.0
140°	349.0	324.3	302.4	282.9	265.5	248.8	234.4	222.9	213.7	207.9	205.1
142.5°	345.4	323.4	303.8	285.6	268.7	252.6	239.0	227.5	219.2	213.0	210.6
145°	340.4	321.9	304.7	288.6	273.1	258.0	244.8	235.0	226.4	221.2	219.4
147.5°	335.6	319.8	304.7	290.4	276.5	262.8	251.5	242.1	234.6	229.4	228.4
150°	332.3	317.9	304.7	290.8	278.8	265.5	255.2	247.1	239.6	235.0	234.4
152.5°	328.7	315.7	303.4	291.9	280.1	268.7	258.8	251.8	245.2	240.5	240.4
155°	323.2	311.6	301.8	292.1	282.9	273.1	265.0	258.6	252.9	249.4	249.4
157.5°	316.9	308.0	299.8	292.7	284.3	276.5	270.2	264.9	259.7	257.0	256.5
160°	312.8	305.3	298.9	292.7	285.7	278.8	273.1	269.0	264.4	262.1	262.1
162.5°	308.6	302.6	297.1	292.2	286.2	280.1	275.3	271.8	268.1	266.2	266.2
165°	303.0	298.4	294.4	290.8	286.8	282.3	278.2	275.9	273.1	271.9	272.5
167.5°	297.6	294.2	291.5	289.9	286.7	283.4	280.8	279.2	277.0	276.5	277.2
170°	294.4	291.4	289.7	288.6	286.3	283.4	282.3	281.0	279.3	278.8	279.9
172.5°	291.1	289.1	288.3	288.1	286.3	283.9	283.2	282.5	281.2	281.0	281.8
175°	287.4	286.3	286.3	286.8	285.7	284.6	284.0	284.0	282.9	283.4	284.0
177.5°	285.0	284.6	285.0	285.9	285.0	284.6	284.6	284.6	284.1	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1614.2	1620.2	1627.9	1639.5	1648.3	1656.0	1657.6	1659.8	1665.4	1674.7	1681.8
5°	1624.7	1640.4	1665.9	1690.6	1717.5	1739.4	1760.0	1774.4	1788.2	1817.1	1840.5
7.5°	1621.3	1656.6	1696.4	1740.8	1785.7	1829.3	1869.8	1905.9	1941.9	1984.0	2031.9
10°	1619.1	1660.4	1713.9	1771.0	1833.6	1894.7	1953.9	1999.9	2053.5	2101.6	2162.7
12.5°	1608.7	1668.1	1732.1	1805.1	1882.0	1952.5	2030.2	2093.9	2155.3	2224.7	2295.8
15°	1595.1	1667.3	1748.4	1845.2	1962.1	2047.3	2127.0	2237.7	2313.3	2388.8	2490.6
17.5°	1570.2	1658.3	1759.6	1885.5	1983.0	2097.5	2217.5	2304.9	2406.7	2513.3	2605.4
20°	1550.4	1652.8	1766.3	1890.0	2014.3	2138.7	2254.8	2359.3	2464.5	2587.5	2663.1
22.5°	1530.7	1631.9	1749.7	1881.2	2014.9	2145.9	2277.3	2400.0	2518.3	2642.4	2739.0
25°	1488.5	1608.8	1736.7	1870.7	2002.7	2147.0	2303.6	2440.4	2586.8	2714.6	2806.0
27.5°	1445.9	1556.2	1683.4	1819.4	1966.1	2136.7	2321.0	2476.4	2623.1	2714.6	2743.4
30°	1407.4	1524.3	1641.1	1779.3	1938.0	2128.4	2324.3	2502.2	2622.5	2662.4	2632.8
32.5°	1368.5	1474.3	1590.0	1731.4	1900.1	2108.1	2328.6	2486.9	2559.3	2528.8	2408.5
35°	1299.6	1395.1	1507.1	1648.7	1842.5	2096.8	2310.6	2417.7	2399.8	2228.1	2001.2
37.5°	1225.9	1303.7	1407.4	1555.5	1782.8	2052.1	2232.4	2248.3	2093.7	1829.9	1567.9
40°	1167.6	1237.7	1344.2	1498.8	1736.7	2008.1	2153.8	2089.9	1850.1	1556.6	1338.1
42.5°	1111.0	1170.1	1272.7	1439.5	1692.7	1948.2	2036.7	1897.5	1620.8	1343.3	1144.6
45°	1015.0	1070.8	1173.8	1344.9	1602.7	1833.6	1821.9	1579.9	1303.0	1079.6	914.7
47.5°	924.0	972.7	1069.4	1244.2	1496.9	1661.7	1552.5	1295.1	1060.2	880.9	763.3
50°	859.7	907.9	1004.1	1176.6	1412.3	1532.6	1376.5	1128.4	913.3	764.9	671.5
52.5°	798.2	845.2	933.1	1101.3	1310.0	1381.9	1214.4	984.4	805.1	676.9	596.6
55°	712.0	747.7	826.8	987.5	1143.6	1160.0	990.3	797.9	650.2	560.8	505.8
57.5°	624.2	654.9	733.1	861.1	970.5	962.0	801.0	634.6	535.1	468.7	428.9
60°	566.9	597.2	665.9	775.9	858.4	829.5	681.8	547.8	462.5	413.7	382.1
62.5°	513.6	537.2	601.6	681.9	741.2	708.5	582.8	471.9	404.2	363.1	338.1
65°	436.4	455.7	507.2	549.1	582.1	550.5	446.1	369.0	320.2	291.3	274.2
67.5°	363.0	375.3	407.8	422.9	446.2	411.5	335.4	283.9	256.1	231.8	219.7
70°	316.8	325.8	343.0	355.3	361.5	325.8	269.4	231.6	208.2	191.1	183.5
72.5°	270.6	278.5	282.0	292.1	288.9	255.4	216.6	186.5	169.8	158.0	148.3
75°	206.8	210.3	206.8	202.8	193.8	170.5	143.6	128.6	116.1	110.7	107.2
77.5°	150.8	149.7	145.0	138.6	123.3	108.6	94.1	89.1	83.7	80.8	79.6
80°	116.1	113.4	109.3	99.0	85.9	75.6	72.2	68.8	66.7	63.2	62.5
82.5°	86.4	84.8	78.0	69.3	60.1	55.2	52.4	51.1	49.1	47.3	47.2
85°	46.0	44.0	36.5	31.6	30.2	28.9	28.2	28.2	25.4	24.7	24.7
87.5°	15.3	12.2	12.0	10.6	10.8	10.1	11.0	10.2	10.0	10.5	9.5
90°	2.3	3.4	5.2	6.4	7.5	9.2	10.9	12.6	14.4	13.8	14.4
92.5°	10.6	15.5	19.9	24.7	33.3	48.4	73.1	97.5	88.6	66.9	48.5
95°	21.3	27.7	37.5	52.4	74.8	123.8	209.6	304.2	341.5	277.0	207.3
97.5°	34.0	39.0	47.5	62.2	86.5	133.3	230.0	387.5	529.4	566.3	516.9
100°	43.2	47.3	55.3	69.1	91.6	131.9	217.1	368.6	545.4	658.9	679.1
102.5°	53.3	57.0	64.5	77.0	97.6	133.7	206.1	341.0	515.5	663.6	733.1
105°	68.6	72.0	78.9	89.9	107.8	138.9	198.1	307.0	463.1	628.4	748.8
107.5°	84.0	87.4	94.1	104.4	121.0	148.2	197.5	285.4	416.8	566.9	703.4
110°	95.0	98.0	104.2	114.0	130.2	156.1	199.9	277.0	390.5	528.2	660.0





TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	105.2	108.1	114.4	124.2	139.9	163.9	204.5	272.5	373.0	494.5	617.2
115°	120.4	123.8	129.6	139.4	154.9	176.8	212.0	270.7	354.3	453.9	560.5
117.5°	135.3	138.3	143.5	154.5	168.8	190.6	221.9	271.8	343.2	429.4	519.3
120°	144.6	147.4	153.2	164.2	178.5	199.2	229.2	273.6	338.1	416.5	497.7
122.5°	153.3	156.2	162.4	172.9	188.2	208.5	236.2	276.8	334.9	405.9	480.6
125°	165.3	168.7	175.1	186.0	201.6	221.8	247.1	281.7	330.6	392.2	457.9
127.5°	175.4	179.8	186.1	198.2	213.8	233.3	256.1	287.2	328.5	380.3	438.1
130°	181.5	186.6	193.5	205.6	221.2	240.1	262.1	290.8	327.2	373.9	425.7
132.5°	186.5	192.2	200.5	212.6	227.6	246.2	267.6	293.7	326.7	367.8	414.1
135°	194.7	201.1	209.6	221.8	237.3	255.2	274.8	297.8	326.0	360.0	398.6
137.5°	202.4	208.6	217.8	229.8	244.2	261.4	280.0	300.5	324.8	353.3	384.5
140°	207.9	213.7	222.9	234.4	248.8	265.5	282.9	302.4	324.3	349.0	376.2
142.5°	213.0	219.2	227.5	239.0	252.6	268.7	285.6	303.8	323.4	345.4	368.3
145°	221.2	226.4	235.0	244.8	258.0	273.1	288.6	304.7	321.9	340.4	358.8
147.5°	229.4	234.6	242.1	251.5	262.8	276.5	290.4	304.7	319.8	335.6	351.1
150°	235.0	239.6	247.1	255.2	265.5	278.8	290.8	304.7	317.9	332.3	345.6
152.5°	240.5	245.2	251.8	258.8	268.7	280.1	291.9	303.4	315.7	328.7	340.5
155°	249.4	252.9	258.6	265.0	273.1	282.9	292.1	301.8	311.6	323.2	333.0
157.5°	257.0	259.7	264.9	270.2	276.5	284.3	292.7	299.8	308.0	316.9	324.9
160°	262.1	264.4	269.0	273.1	278.8	285.7	292.7	298.9	305.3	312.8	320.2
162.5°	266.2	268.1	271.8	275.3	280.1	286.2	292.2	297.1	302.6	308.6	314.8
165°	271.9	273.1	275.9	278.2	282.3	286.8	290.8	294.4	298.4	303.0	307.6
167.5°	276.5	277.0	279.2	280.8	283.4	286.7	289.9	291.5	294.2	297.6	301.3
170°	278.8	279.3	281.0	282.3	283.4	286.3	288.6	289.7	291.4	294.4	297.2
172.5°	281.0	281.2	282.5	283.2	283.9	286.3	288.1	288.3	289.1	291.1	293.6
175°	283.4	282.9	284.0	284.0	284.6	285.7	286.8	286.3	286.3	287.4	288.6
177.5°	284.6	284.1	284.6	284.6	284.6	285.0	285.9	285.0	284.6	285.0	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1693.3	1693.3	1695.6	1703.8	1705.0	1712.0	1709.9
5°	1861.1	1874.1	1879.0	1899.6	1911.9	1917.4	1906.4
7.5°	2066.2	2102.9	2120.4	2142.0	2161.1	2166.9	2151.9
10°	2215.6	2254.1	2286.4	2306.4	2324.9	2337.3	2353.1
12.5°	2360.3	2407.5	2438.2	2466.4	2485.5	2501.1	2503.8
15°	2517.4	2588.9	2643.1	2683.0	2702.9	2713.2	2709.2
17.5°	2675.8	2742.1	2780.8	2821.5	2849.0	2850.4	2851.3
20°	2765.5	2830.0	2874.8	2905.0	2935.9	2934.6	2941.4
22.5°	2825.4	2876.3	2910.5	2932.4	2943.0	2937.8	2939.2
25°	2853.5	2868.5	2862.4	2827.3	2818.4	2786.1	2791.6
27.5°	2708.9	2637.4	2563.4	2468.3	2393.3	2333.3	2336.3
30°	2512.5	2386.1	2241.8	2120.8	2012.3	1982.1	1917.4
32.5°	2238.3	2048.5	1879.5	1766.8	1673.5	1648.3	1592.0
35°	1773.1	1588.9	1415.0	1310.6	1269.3	1211.6	1210.9
37.5°	1378.2	1216.0	1124.1	1045.7	1004.6	969.7	966.2
40°	1159.4	1032.9	963.5	907.2	866.7	840.5	834.4
42.5°	1006.5	904.2	839.3	804.4	773.2	759.7	749.6
45°	821.9	753.3	707.8	676.2	661.9	651.5	646.0
47.5°	687.5	641.5	610.6	589.6	577.8	566.9	569.9
50°	614.4	576.6	553.9	534.0	525.0	517.5	518.2
52.5°	555.5	521.6	503.3	488.9	477.8	472.4	469.8
55°	471.4	450.1	431.6	421.3	415.1	407.6	405.5
57.5°	402.1	385.7	370.5	358.9	357.4	350.1	351.0
60°	356.0	342.2	329.9	323.7	318.9	312.7	314.8
62.5°	318.1	306.5	295.3	290.1	285.4	280.8	281.8
65°	260.4	249.4	242.6	239.8	237.8	235.7	233.7
67.5°	207.5	200.9	196.5	190.7	186.4	185.7	183.6
70°	174.6	165.6	158.0	150.5	148.5	147.7	148.5
72.5°	140.0	134.3	132.2	128.6	128.2	126.3	127.5
75°	105.1	103.1	101.7	99.0	99.0	99.0	99.0
77.5°	77.6	76.2	75.4	74.9	74.2	73.2	73.1
80°	60.5	59.8	58.4	58.4	57.8	58.4	57.8
82.5°	45.6	45.5	44.1	44.1	43.4	43.0	43.4
85°	23.3	22.7	24.0	22.7	23.3	22.0	23.3
87.5°	9.6	9.7	9.4	9.3	8.9	10.1	8.9
90°	14.9	15.6	16.7	16.2	16.7	17.3	16.7
92.5°	38.5	34.0	31.0	30.0	28.2	28.8	27.8
95°	140.6	110.0	89.3	78.4	73.1	69.1	66.9
97.5°	414.0	339.7	270.8	228.3	202.4	186.8	181.9
100°	632.5	565.0	483.2	425.1	383.0	360.6	361.1
102.5°	731.5	692.3	640.4	595.1	561.8	543.0	529.8
105°	806.4	817.4	802.3	775.9	754.0	735.6	732.7
107.5°	797.0	847.4	867.9	868.4	861.0	854.7	849.5
110°	766.1	838.7	879.0	895.1	899.7	898.6	897.4



TEST NUMBER: P332338-840

CATALOG NUMBER: S123RDIP-S1000D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	725.5	806.9	858.7	888.2	902.5	906.9	907.1
115°	660.7	745.4	808.1	851.3	876.7	888.2	891.1
117.5°	605.8	681.9	745.6	790.6	819.6	836.3	840.1
120°	575.4	644.5	702.8	748.2	780.5	794.3	797.8
122.5°	551.0	615.0	669.0	709.5	738.5	753.8	758.1
125°	520.7	576.0	622.1	658.9	684.3	698.7	702.8
127.5°	494.1	544.0	585.9	618.7	640.4	653.4	657.1
130°	477.5	524.1	563.3	593.9	614.6	626.7	631.3
132.5°	461.8	505.2	542.6	571.3	592.0	602.7	605.9
135°	439.5	477.0	509.8	538.0	555.2	565.6	569.7
137.5°	418.0	450.2	478.7	502.4	519.9	528.7	531.3
140°	405.5	433.1	457.9	479.8	495.9	505.1	504.5
142.5°	393.5	417.5	439.0	457.7	472.0	480.3	479.7
145°	377.9	396.3	413.0	427.4	439.5	444.1	445.2
147.5°	366.2	381.1	392.9	403.8	412.0	416.5	416.9
150°	358.8	370.9	381.9	390.5	396.9	400.3	400.3
152.5°	351.9	362.6	371.7	378.5	384.5	386.5	386.5
155°	342.1	350.8	357.7	362.8	367.5	368.6	369.2
157.5°	332.5	339.3	344.7	349.2	352.6	353.6	353.5
160°	326.6	332.3	336.4	340.4	343.9	343.9	343.3
162.5°	320.1	325.5	329.0	331.6	334.7	334.7	334.1
165°	311.0	315.1	317.9	320.2	322.6	321.9	321.9
167.5°	304.0	306.3	308.4	309.4	311.0	310.4	310.4
170°	298.9	301.2	302.4	303.0	304.2	303.6	303.6
172.5°	294.8	296.6	297.3	297.4	298.6	297.6	297.1
175°	289.1	290.3	290.3	290.3	290.8	290.3	289.7
177.5°	285.9	286.4	286.4	285.9	286.4	285.5	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6

(END OF REPORT)