

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332371

Luminaire Tested: **S123RDIP-S1165D585U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332371
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D585U835-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6500.5 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332371

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332371

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	62	58
2	93	86	80	75	88	81	76	71	73	68	65	65	61	59	57	55	53	49
3	85	76	69	63	80	72	65	60	64	59	55	58	54	50	51	48	45	42
4	78	68	60	54	74	64	57	51	58	52	47	52	47	43	46	42	39	36
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35	32
6	67	55	46	41	63	52	44	39	47	41	36	42	37	33	38	34	31	28
7	62	49	41	36	58	47	40	35	43	37	32	39	34	30	35	31	27	25
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	25	22	20
10	50	38	31	26	48	36	30	25	33	28	24	30	25	22	28	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332371

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.0	2.8
10°-20°	506.4	7.8
20°-30°	729.2	11.2
30°-40°	821.3	12.6
40°-50°	785.8	12.1
50°-60°	643.5	9.9
60°-70°	434.1	6.7
70°-80°	218.4	3.4
80°-90°	60.0	0.9
90°-100°	156.8	2.4
100°-110°	444.0	6.8
110°-120°	436.8	6.7
120°-130°	348.4	5.4
130°-140°	274.7	4.2
140°-150°	205.0	3.2
150°-160°	142.9	2.2
160°-170°	83.9	1.3
170°-180°	27.3	0.4
0°-30°	1417.6	21.8
0°-40°	2238.9	34.4
0°-60°	3668.1	56.4
0°-90°	4380.7	67.4
90°-120°	1037.6	16.0
90°-150°	1865.7	28.7
90°-180°	2120.0	32.6
0°-180°	6500.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	1	7	14	16	16	5
95°	19	63	338	99	66	21
105°	66	98	459	802	726	70
115°	117	146	351	769	882	116
125°	163	192	327	593	696	144
135°	190	227	323	489	564	147
145°	217	249	319	401	441	136
155°	247	266	309	351	366	114
165°	270	278	296	313	319	76
175°	281	282	284	288	287	27
180°	282	282	282	282	282	



TEST NUMBER: P332371

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.4	27.6	24.7	22.0	19.1	17.8	18.2	18.5	18.9	19.2	18.8
90°	1.1	2.3	3.4	5.1	6.3	7.4	9.1	10.8	12.5	14.3	13.7
92.5°	7.1	10.5	15.3	19.7	24.5	33.0	47.9	72.4	96.5	87.7	66.2
95°	19.4	21.1	27.4	37.1	51.9	74.1	122.6	207.6	301.2	338.2	274.3
97.5°	33.1	33.7	38.6	47.0	61.6	85.7	132.0	227.8	383.7	524.2	560.8
100°	42.2	42.8	46.8	54.8	68.4	90.7	130.6	215.0	365.0	540.1	652.5
102.5°	51.8	52.8	56.4	63.9	76.2	96.6	132.4	204.1	337.7	510.5	657.1
105°	66.2	67.9	71.3	78.1	89.0	106.7	137.5	196.2	304.0	458.6	622.3
107.5°	81.4	83.2	86.5	93.2	103.4	119.8	146.8	195.6	282.6	412.7	561.4
110°	92.4	94.1	97.0	103.2	112.9	128.9	154.6	197.9	274.3	386.7	523.0



TEST NUMBER: P332371

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	102.4	104.2	107.0	113.3	123.0	138.5	162.3	202.5	269.8	369.4	489.7
115°	116.9	119.2	122.6	128.3	138.0	153.4	175.1	209.9	268.1	350.8	449.5
117.5°	131.4	134.0	136.9	142.1	153.0	167.2	188.7	219.7	269.1	339.8	425.2
120°	141.5	143.2	146.0	151.7	162.6	176.8	197.3	227.0	270.9	334.8	412.4
122.5°	150.1	151.8	154.7	160.8	171.2	186.4	206.5	233.9	274.1	331.6	401.9
125°	162.6	163.7	167.1	173.4	184.2	199.6	219.6	244.7	278.9	327.4	388.4
127.5°	172.0	173.7	178.0	184.3	196.3	211.7	231.0	253.6	284.4	325.3	376.6
130°	178.0	179.7	184.8	191.6	203.6	219.0	237.8	259.5	288.0	324.0	370.2
132.5°	182.5	184.7	190.3	198.5	210.5	225.4	243.8	265.0	290.8	323.5	364.2
135°	190.5	192.8	199.1	207.6	219.6	235.0	252.7	272.1	294.9	322.8	356.5
137.5°	198.0	200.4	206.6	215.7	227.6	241.8	258.8	277.3	297.6	321.6	349.8
140°	203.1	205.9	211.6	220.7	232.1	246.4	262.9	280.1	299.4	321.1	345.6
142.5°	208.5	210.9	217.1	225.3	236.7	250.1	266.1	282.8	300.8	320.2	342.0
145°	217.3	219.0	224.2	232.7	242.4	255.5	270.4	285.8	301.7	318.8	337.1
147.5°	226.2	227.2	232.3	239.7	249.0	260.2	273.8	287.6	301.7	316.7	332.3
150°	232.1	232.7	237.3	244.7	252.7	262.9	276.1	288.0	301.7	314.8	329.1
152.5°	238.1	238.2	242.8	249.3	256.3	266.1	277.4	289.0	300.4	312.6	325.5
155°	247.0	247.0	250.4	256.1	262.4	270.4	280.1	289.2	298.9	308.6	320.0
157.5°	254.0	254.5	257.2	262.3	267.6	273.8	281.5	289.8	296.9	305.0	313.8
160°	259.5	259.5	261.8	266.4	270.4	276.1	282.9	289.8	296.0	302.3	309.7
162.5°	263.6	263.6	265.5	269.1	272.6	277.4	283.4	289.3	294.2	299.6	305.6
165°	269.8	269.2	270.4	273.2	275.5	279.5	284.0	288.0	291.5	295.5	300.0
167.5°	274.5	273.8	274.3	276.5	278.1	280.6	283.9	287.1	288.7	291.3	294.7
170°	277.2	276.1	276.6	278.3	279.5	280.6	283.5	285.8	286.9	288.6	291.5
172.5°	279.0	278.3	278.5	279.7	280.4	281.1	283.5	285.3	285.5	286.3	288.3
175°	281.2	280.6	280.1	281.2	281.2	281.8	282.9	284.0	283.5	283.5	284.6
177.5°	282.2	281.8	281.3	281.8	281.8	281.8	282.2	283.1	282.2	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332371

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	18.6	18.5	18.3	18.3	17.9	17.7	17.5	17.1
90°	14.3	14.8	15.4	16.5	16.0	16.5	17.1	16.5
92.5°	48.0	38.1	33.7	30.7	29.7	27.9	28.5	27.5
95°	205.3	139.2	108.9	88.4	77.6	72.4	68.4	66.2
97.5°	511.9	410.0	336.4	268.2	226.1	200.4	185.0	180.1
100°	672.5	626.3	559.5	478.5	420.9	379.3	357.1	357.6
102.5°	725.9	724.4	685.5	634.1	589.3	556.3	537.7	524.6
105°	741.5	798.5	809.4	794.5	768.3	746.6	728.4	725.5
107.5°	696.5	789.2	839.1	859.4	859.9	852.6	846.4	841.2
110°	653.6	758.6	830.5	870.4	886.4	890.9	889.8	888.6



TEST NUMBER: P332371

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	611.2	718.4	799.0	850.3	879.5	893.7	898.0	898.2
115°	555.0	654.2	738.1	800.2	843.0	868.1	879.5	882.4
117.5°	514.2	599.9	675.2	738.3	782.9	811.6	828.1	831.9
120°	492.8	569.8	638.2	695.9	740.9	772.9	786.5	790.0
122.5°	475.9	545.6	609.0	662.5	702.6	731.3	746.4	750.7
125°	453.4	515.6	570.4	616.0	652.5	677.6	691.9	695.9
127.5°	433.8	489.3	538.7	580.2	612.7	634.1	647.0	650.7
130°	421.5	472.8	519.0	557.8	588.1	608.6	620.6	625.1
132.5°	410.1	457.3	500.3	537.3	565.7	586.2	596.8	600.0
135°	394.7	435.2	472.3	504.8	532.7	549.8	560.1	564.1
137.5°	380.7	413.9	445.8	474.0	497.5	514.8	523.5	526.1
140°	372.5	401.5	428.9	453.4	475.1	491.1	500.2	499.6
142.5°	364.7	389.7	413.4	434.7	453.2	467.4	475.6	475.0
145°	355.3	374.2	392.4	409.0	423.2	435.2	439.8	440.9
147.5°	347.7	362.6	377.4	389.1	399.9	408.0	412.4	412.8
150°	342.2	355.3	367.3	378.2	386.7	393.0	396.4	396.4
152.5°	337.2	348.5	359.1	368.1	374.8	380.7	382.7	382.7
155°	329.7	338.8	347.4	354.2	359.3	363.9	365.0	365.6
157.5°	321.7	329.3	336.0	341.3	345.8	349.2	350.1	350.0
160°	317.1	323.4	329.1	333.1	337.1	340.5	340.5	339.9
162.5°	311.7	317.0	322.3	325.8	328.4	331.4	331.4	330.8
165°	304.6	308.0	312.0	314.8	317.1	319.4	318.8	318.8
167.5°	298.4	301.0	303.3	305.4	306.4	308.0	307.4	307.4
170°	294.3	296.0	298.3	299.4	300.0	301.2	300.6	300.6
172.5°	290.7	291.9	293.7	294.4	294.5	295.7	294.7	294.2
175°	285.8	286.3	287.5	287.5	287.5	288.0	287.5	286.9
177.5°	282.7	283.1	283.6	283.6	283.1	283.6	282.7	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8

(END OF REPORT)