

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832011

Luminaire Tested: S123RDIP-S1165D805U835-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832011
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U835-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8179.0 lumens
Efficiency: N/A
Efficacy: 130.2 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832011

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-G

Luminous Intensity Polar Plot



TEST NUMBER: P832011

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	66	66	66	61		
1	101	97	94	90	95	91	88	85	80	78	75	69	68	66	60	59	58	58	58	58	58	58	58	53		
2	93	86	80	75	87	81	76	72	71	67	64	62	59	57	54	52	50	50	50	50	50	50	50	46		
3	86	77	70	64	80	72	66	61	64	59	55	56	52	50	49	46	44	44	44	44	44	44	44	40		
4	79	69	61	56	74	65	58	53	58	52	48	51	47	44	44	41	39	39	39	39	39	39	39	36		
5	73	62	54	49	68	59	52	47	52	47	43	46	42	39	41	37	35	35	35	35	35	35	35	32		
6	68	56	48	43	63	53	46	41	48	42	38	42	38	35	37	34	31	31	31	31	31	31	31	29		
7	63	51	44	38	59	49	42	37	44	38	34	39	35	31	35	31	28	28	28	28	28	28	28	26		
8	59	47	40	35	55	45	38	33	40	35	31	36	32	28	32	29	26	26	26	26	26	26	26	24		
9	55	43	36	31	52	41	35	30	37	32	28	34	29	26	30	27	24	24	24	24	24	24	24	22		
10	52	40	33	29	49	38	32	28	35	29	26	31	27	24	28	25	22	22	22	22	22	22	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	40341	40341	40341	40341	40341
5°	47900	46372	40595	32816	30467
10°	43399	47102	40392	26293	22556
15°	29881	40386	39965	21489	17842
20°	20787	31093	39163	18120	15683
25°	15841	23698	37996	16106	14454
30°	13789	18946	36535	14955	13389
35°	12661	15981	34467	13983	12418
40°	11552	14272	31760	13030	11529
45°	10432	13052	28841	12128	10644
50°	9470	12042	25396	11245	9547
55°	8565	11059	22088	10382	8190
60°	7675	10056	19186	9427	7741
65°	7083	8922	16514	8474	7317
70°	5756	7714	14411	7666	5948
75°	5049	6134	12206	6359	5240
80°	4575	5188	9998	5331	4953
85°	4174	4557	7595	4841	4557

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 30431 cd/sqm



TEST NUMBER: P832011

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	341.6	4.2
10°-20°	790.5	9.7
20°-30°	906.9	11.1
30°-40°	893.9	10.9
40°-50°	788.3	9.6
50°-60°	606.5	7.4
60°-70°	398.7	4.9
70°-80°	193.6	2.4
80°-90°	50.9	0.6
90°-100°	37.1	0.5
100°-110°	179.4	2.2
110°-120°	439.6	5.4
120°-130°	558.1	6.8
130°-140°	596.2	7.3
140°-150°	557.5	6.8
150°-160°	449.7	5.5
160°-170°	290.2	3.5
170°-180°	100.0	1.2
0°-30°	2039.0	24.9
0°-40°	2933.0	35.9
0°-60°	4327.8	52.9
0°-90°	4971.1	60.8
90°-120°	656.1	8.0
90°-150°	2367.9	29.0
90°-180°	3208.0	39.2
0°-180°	8179.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3748	3748	3748	3748	3748	
5°	4433	4292	3757	3037	2820	405
15°	2681	3624	3586	1928	1601	757
25°	1334	1995	3199	1356	1217	630
35°	964	1216	2623	1064	945	601
45°	685	857	1895	797	699	532
55°	456	589	1177	553	436	409
65°	278	350	648	333	287	273
75°	121	148	294	153	126	131
85°	34	37	62	39	37	36
90°	24	19	1	19	24	12
95°	30	24	48	24	30	25
105°	34	171	233	171	34	72
115°	460	449	437	449	460	432
125°	629	625	616	625	629	562
135°	775	775	767	775	775	598
145°	894	892	885	892	894	558
155°	973	974	975	974	973	449
165°	1026	1025	1028	1025	1026	290
175°	1048	1049	1052	1049	1048	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P832011

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8
2.5°	4153.4	4140.4	4127.3	4123.5	4119.6	4107.3	4095.1	4067.4	4039.7	4011.3	3982.9
5°	4433.1	4434.6	4436.2	4432.3	4428.5	4412.4	4396.2	4362.4	4328.6	4291.7	4254.9
7.5°	4347.1	4371.6	4396.2	4400.8	4405.4	4417.7	4430.0	4422.3	4414.7	4400.8	4387.0
10°	3970.6	3969.0	3967.5	3995.2	4022.8	4105.0	4187.2	4229.5	4271.8	4309.4	4347.1
12.5°	3355.9	3358.2	3360.6	3451.2	3541.9	3619.5	3697.1	3804.6	3912.2	4028.2	4144.2
15°	2681.4	2719.0	2756.7	2837.3	2918.0	3034.8	3151.6	3296.0	3440.5	3624.1	3807.7
17.5°	2202.0	2218.1	2234.2	2311.8	2389.4	2500.1	2610.7	2774.3	2938.0	3174.6	3411.3
20°	1814.7	1829.3	1843.9	1900.0	1956.1	2062.1	2168.1	2324.1	2480.1	2714.4	2948.7
22.5°	1515.1	1543.5	1571.9	1609.6	1647.2	1724.1	1800.9	1959.9	2119.0	2332.6	2546.2
25°	1333.8	1346.8	1359.9	1392.2	1424.4	1498.2	1571.9	1677.2	1782.5	1995.3	2208.1
27.5°	1210.8	1214.7	1218.5	1242.3	1266.2	1313.8	1361.4	1459.0	1556.6	1731.8	1906.9
30°	1109.4	1116.3	1123.3	1141.7	1160.1	1194.7	1229.3	1298.4	1367.6	1524.3	1681.0
32.5°	1031.1	1034.9	1038.7	1054.1	1069.5	1094.8	1120.2	1174.7	1229.3	1349.1	1469.0
35°	963.5	964.2	965.0	976.5	988.0	1012.6	1037.2	1082.5	1127.9	1216.2	1304.6
37.5°	886.6	892.0	897.4	905.8	914.3	935.8	957.3	994.2	1031.1	1104.1	1177.0
40°	822.1	826.7	831.3	841.3	851.3	868.2	885.1	918.9	952.7	1015.7	1078.7
42.5°	757.5	760.6	763.7	773.7	783.7	804.4	825.2	852.0	878.9	931.2	983.4
45°	685.3	693.0	700.7	711.4	722.2	739.9	757.5	785.2	812.9	857.4	902.0
47.5°	625.4	629.2	633.1	642.3	651.5	673.0	694.5	719.1	743.7	785.2	826.7
50°	565.5	567.0	568.5	577.0	585.4	604.7	623.9	652.3	680.7	719.1	757.5
52.5°	508.6	512.5	516.3	524.8	533.2	546.3	559.3	588.5	617.7	655.4	693.0
55°	456.4	458.7	461.0	467.1	473.3	488.6	504.0	529.4	554.7	589.3	623.9
57.5°	407.2	410.3	413.3	418.0	422.6	436.4	450.2	472.5	494.8	529.4	563.9
60°	356.5	360.3	364.2	369.6	374.9	385.7	396.4	416.4	436.4	467.1	497.9
62.5°	319.6	320.4	321.2	325.8	330.4	338.1	345.7	361.9	378.0	408.7	439.5
65°	278.1	280.4	282.7	285.0	287.3	293.5	299.6	313.5	327.3	350.3	373.4
67.5°	235.1	237.4	239.7	243.6	247.4	252.8	258.1	267.4	276.6	298.1	319.6
70°	182.9	182.9	182.9	189.0	195.1	204.4	213.6	220.5	227.4	245.1	262.8
72.5°	149.1	149.8	150.6	151.4	152.1	157.5	162.9	174.4	185.9	196.7	207.4
75°	121.4	122.2	122.9	123.7	124.5	126.0	127.5	131.4	135.2	147.5	159.8
77.5°	96.8	97.6	98.3	99.1	99.9	101.4	103.0	104.5	106.0	110.6	115.2
80°	73.8	74.5	75.3	76.1	76.8	77.6	78.4	79.9	81.4	83.7	86.0
82.5°	53.8	53.8	53.8	53.8	53.8	55.3	56.9	56.9	56.9	58.4	59.9
85°	33.8	33.8	33.8	34.6	35.3	35.3	35.3	36.1	36.9	36.9	36.9
87.5°	15.4	14.6	13.8	14.6	15.4	15.4	15.4	16.1	16.9	16.9	16.9
90°	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2	19.5	18.8	16.5
92.5°	26.6	26.4	26.2	26.1	25.9	25.2	24.0	22.8	21.5	20.3	18.8
95°	29.7	29.7	29.7	29.7	29.7	29.1	27.9	26.7	25.5	24.2	22.3
97.5°	32.1	31.9	31.7	31.5	31.4	30.6	29.2	27.8	26.4	25.0	33.9
100°	32.8	32.7	32.5	32.3	32.1	31.4	30.0	28.6	27.2	25.8	52.9
102.5°	33.6	33.3	32.9	32.6	32.2	34.9	40.7	46.4	52.1	57.9	88.1
105°	34.4	34.1	33.7	33.4	33.0	48.2	79.0	109.7	140.5	171.2	186.8
107.5°	81.3	104.1	126.8	149.6	172.3	197.1	223.9	250.6	277.4	304.1	301.5
110°	215.0	239.8	264.7	289.5	314.4	329.7	335.4	341.1	346.9	352.6	350.7



TEST NUMBER: P832011

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	407.3	407.7	408.0	408.4	408.7	408.1	406.5	405.0	403.4	401.8	399.9
115°	459.7	459.0	458.3	457.6	456.9	455.7	454.0	452.2	450.5	448.8	447.2
117.5°	501.9	501.7	501.6	501.4	501.2	500.4	499.0	497.7	496.3	494.9	494.0
120°	545.7	545.7	545.7	545.7	545.7	545.0	543.6	542.2	540.8	539.4	538.9
122.5°	588.7	588.5	588.3	588.2	588.0	587.5	586.6	585.7	584.9	584.0	583.3
125°	628.6	628.2	627.9	627.5	627.2	626.8	626.5	626.1	625.8	625.4	624.7
127.5°	667.7	668.0	668.3	668.7	669.0	669.0	668.4	667.9	667.4	666.9	666.0
130°	705.2	705.5	705.9	706.2	706.6	706.4	705.7	705.0	704.3	703.6	702.9
132.5°	739.6	740.1	740.6	741.1	741.7	741.6	740.9	740.2	739.5	738.8	738.3
135°	774.8	775.3	775.8	776.3	776.8	776.8	776.3	775.8	775.3	774.8	774.1
137.5°	808.4	808.7	809.1	809.4	809.8	809.5	808.6	807.8	806.9	806.0	805.7
140°	838.1	838.4	838.8	839.1	839.5	839.3	838.6	837.9	837.2	836.5	836.0
142.5°	865.4	866.0	866.5	867.0	867.5	867.5	867.0	866.5	866.0	865.4	864.9
145°	893.6	893.6	893.6	893.6	893.6	893.4	893.1	892.7	892.4	892.0	891.7
147.5°	913.9	914.8	915.7	916.5	917.4	917.7	917.3	917.0	916.6	916.3	915.9
150°	937.4	937.9	938.4	938.9	939.5	939.5	939.2	938.8	938.5	938.2	937.8
152.5°	956.1	957.0	957.9	958.7	959.6	959.7	959.0	958.3	957.6	956.9	956.7
155°	973.3	974.4	975.4	976.5	977.5	977.6	976.7	975.9	975.0	974.1	973.9
157.5°	988.2	989.6	991.0	992.4	993.7	993.9	992.9	991.8	990.8	989.8	989.9
160°	1002.3	1003.5	1004.7	1005.9	1007.1	1007.2	1006.2	1005.1	1004.1	1003.0	1003.2
162.5°	1015.6	1016.6	1017.6	1018.7	1019.7	1019.6	1018.4	1017.2	1016.0	1014.8	1014.9
165°	1025.7	1026.9	1028.1	1029.4	1030.6	1030.5	1029.1	1027.7	1026.3	1024.9	1025.1
167.5°	1033.5	1034.9	1036.3	1037.7	1039.1	1039.1	1037.7	1036.3	1034.9	1033.5	1033.5
170°	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1	1044.7	1043.3	1042.0	1040.6	1040.6
172.5°	1044.5	1046.0	1047.6	1049.2	1050.7	1050.8	1049.4	1048.0	1046.6	1045.3	1045.1
175°	1048.4	1049.8	1051.2	1052.6	1053.9	1054.0	1052.8	1051.6	1050.4	1049.2	1049.0
177.5°	1049.2	1050.9	1052.6	1054.4	1056.1	1056.3	1054.9	1053.5	1052.1	1050.7	1050.6
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P832011

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8
2.5°	3979.0	3975.2	3938.3	3901.4	3865.3	3829.2	3802.3	3775.4	3730.1	3684.8	3656.4
5°	4225.7	4196.5	4138.1	4079.7	3992.1	3904.5	3830.8	3757.0	3663.3	3569.5	3491.2
7.5°	4363.2	4339.4	4268.7	4198.0	4082.0	3966.0	3850.7	3735.5	3597.2	3458.9	3340.6
10°	4367.0	4387.0	4328.6	4270.2	4139.6	4009.0	3852.3	3695.5	3509.6	3323.7	3170.8
12.5°	4230.3	4316.3	4304.0	4291.7	4158.8	4025.9	3835.4	3644.8	3416.6	3188.5	2997.1
15°	3974.4	4141.1	4190.3	4239.5	4129.6	4019.8	3803.1	3586.4	3318.3	3050.2	2830.4
17.5°	3644.8	3878.4	4008.2	4138.1	4058.2	3978.3	3740.9	3503.5	3201.5	2899.6	2660.6
20°	3254.5	3560.3	3763.9	3967.5	3938.3	3909.1	3664.0	3418.9	3093.2	2767.4	2508.5
22.5°	2868.8	3191.5	3472.7	3753.9	3783.9	3813.9	3566.5	3319.1	2962.6	2606.1	2342.6
25°	2536.2	2864.2	3199.2	3534.2	3601.8	3669.4	3434.3	3199.2	2829.7	2460.1	2198.1
27.5°	2218.9	2530.8	2899.6	3268.4	3391.3	3514.2	3299.1	3084.0	2699.0	2314.1	2052.9
30°	1959.9	2238.8	2615.3	2991.8	3163.1	3334.4	3137.0	2939.5	2557.7	2175.8	1920.0
32.5°	1718.7	1968.4	2346.4	2724.4	2923.4	3122.4	2951.8	2781.3	2414.0	2046.8	1794.0
35°	1528.2	1751.7	2104.4	2457.0	2679.8	2902.6	2762.8	2623.0	2264.2	1905.4	1666.4
37.5°	1364.5	1552.0	1883.1	2214.2	2450.9	2687.5	2570.7	2454.0	2116.7	1779.4	1553.5
40°	1229.3	1379.9	1688.0	1996.0	2228.1	2460.1	2360.2	2260.3	1958.4	1656.5	1445.2
42.5°	1113.3	1243.1	1519.7	1796.3	2009.1	2221.9	2155.9	2089.8	1816.3	1542.8	1346.8
45°	1011.1	1120.2	1363.7	1607.3	1803.2	1999.1	1946.9	1894.6	1658.8	1422.9	1243.1
47.5°	920.4	1014.2	1231.6	1449.0	1625.0	1800.9	1752.5	1704.1	1508.9	1313.8	1150.1
50°	837.4	917.4	1098.7	1280.0	1438.3	1596.5	1556.6	1516.6	1355.3	1193.9	1052.6
52.5°	759.1	825.2	988.0	1150.9	1278.5	1406.0	1375.3	1344.5	1220.1	1095.6	967.3
55°	684.6	745.3	882.8	1020.3	1129.4	1238.5	1207.8	1177.0	1080.2	983.4	870.5
57.5°	616.9	670.0	781.4	892.8	979.6	1066.4	1051.8	1037.2	956.5	875.9	782.9
60°	545.5	593.1	689.2	785.2	855.1	925.0	908.1	891.2	833.6	776.0	696.1
62.5°	481.7	524.0	600.8	677.6	734.5	791.4	779.1	766.8	723.0	679.2	613.1
65°	414.9	456.4	518.6	580.8	625.4	670.0	659.2	648.4	615.4	582.4	529.4
67.5°	354.2	388.8	442.5	496.3	526.3	556.3	550.1	544.0	518.6	493.3	451.8
70°	292.7	322.7	367.2	411.8	432.6	453.3	455.6	457.9	434.9	411.8	381.1
72.5°	231.3	255.1	296.6	338.1	354.2	370.3	369.6	368.8	355.0	341.1	313.5
75°	177.5	195.1	227.4	259.7	273.5	287.3	290.4	293.5	280.4	267.4	252.0
77.5°	127.5	139.8	164.4	189.0	204.4	219.7	221.3	222.8	216.7	210.5	195.9
80°	89.9	93.7	109.1	124.5	140.6	156.7	159.0	161.3	155.2	149.1	139.8
82.5°	62.2	64.5	69.9	75.3	88.4	101.4	104.5	107.6	104.5	101.4	91.4
85°	37.6	38.4	40.7	43.0	49.2	55.3	58.4	61.5	59.9	58.4	53.0
87.5°	16.9	16.9	17.7	18.4	20.0	21.5	25.4	29.2	26.9	24.6	22.3
90°	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8	2.5	4.3	6.0
92.5°	17.2	15.6	14.1	13.8	14.9	15.9	16.9	18.0	16.9	15.9	14.9
95°	20.4	18.5	16.6	19.2	26.3	33.4	40.6	47.7	40.6	33.4	26.3
97.5°	42.7	51.6	60.5	67.3	72.2	77.1	81.9	86.8	81.9	77.1	72.2
100°	80.0	107.1	134.2	146.0	142.5	139.1	135.6	132.1	135.6	139.1	142.5
102.5°	118.3	148.5	178.8	192.8	190.5	188.2	186.0	183.7	186.0	188.2	190.5
105°	202.5	218.1	233.8	240.6	238.7	236.8	234.9	233.0	234.9	236.8	238.7
107.5°	298.9	296.3	293.7	291.6	290.0	288.5	286.9	285.4	286.9	288.5	290.0
110°	348.8	346.9	344.9	343.3	341.9	340.5	339.1	337.7	339.1	340.5	341.9



TEST NUMBER: P832011

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	398.0	396.1	394.2	392.6	391.4	390.2	389.0	387.8	389.0	390.2	391.4
115°	445.6	444.1	442.5	441.2	440.2	439.1	438.1	437.0	438.1	439.1	440.2
117.5°	493.1	492.3	491.4	490.4	489.1	487.9	486.7	485.5	486.7	487.9	489.1
120°	538.4	537.9	537.4	536.3	534.7	533.2	531.6	530.1	531.6	533.2	534.7
122.5°	582.6	581.9	581.2	580.3	579.0	577.8	576.6	575.4	576.6	577.8	579.0
125°	624.0	623.4	622.7	621.6	620.2	618.8	617.4	616.1	617.4	618.8	620.2
127.5°	665.1	664.3	663.4	662.3	660.9	659.5	658.1	656.7	658.1	659.5	660.9
130°	702.2	701.5	700.8	699.8	698.4	697.0	695.6	694.2	695.6	697.0	698.4
132.5°	737.8	737.2	736.7	735.8	734.4	733.0	731.6	730.2	731.6	733.0	734.4
135°	773.4	772.7	772.0	771.1	770.1	769.0	768.0	766.9	768.0	769.0	770.1
137.5°	805.3	805.0	804.6	803.8	802.4	801.0	799.6	798.2	799.6	801.0	802.4
140°	835.5	835.0	834.4	833.7	832.6	831.6	830.5	829.5	830.5	831.6	832.6
142.5°	864.4	863.9	863.4	862.6	861.5	860.5	859.5	858.4	859.5	860.5	861.5
145°	891.3	891.0	890.6	889.9	888.6	887.4	886.2	885.0	886.2	887.4	888.6
147.5°	915.6	915.2	914.9	914.3	913.4	912.5	911.7	910.8	911.7	912.5	913.4
150°	937.5	937.1	936.8	936.3	935.8	935.3	934.8	934.2	934.8	935.3	935.8
152.5°	956.6	956.4	956.2	956.0	955.9	955.7	955.5	955.4	955.5	955.7	955.9
155°	973.8	973.6	973.4	973.5	973.9	974.2	974.6	974.9	974.6	974.2	973.9
157.5°	990.1	990.3	990.4	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5
160°	1003.4	1003.6	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6	1004.4	1004.3	1004.1
162.5°	1015.1	1015.3	1015.5	1015.8	1016.3	1016.9	1017.4	1017.9	1017.4	1016.9	1016.3
165°	1025.3	1025.5	1025.6	1026.0	1026.5	1027.0	1027.5	1028.1	1027.5	1027.0	1026.5
167.5°	1033.5	1033.5	1033.5	1033.9	1034.6	1035.3	1036.0	1036.7	1036.0	1035.3	1034.6
170°	1040.6	1040.6	1040.6	1040.9	1041.6	1042.3	1043.0	1043.7	1043.0	1042.3	1041.6
172.5°	1044.9	1044.7	1044.6	1044.9	1045.8	1046.6	1047.5	1048.4	1047.5	1046.6	1045.8
175°	1048.8	1048.6	1048.5	1048.8	1049.7	1050.6	1051.4	1052.3	1051.4	1050.6	1049.7
177.5°	1050.4	1050.2	1050.0	1050.4	1051.3	1052.1	1053.0	1053.9	1053.0	1052.1	1051.3
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P832011

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8	3747.8
2.5°	3627.9	3584.1	3540.3	3508.8	3477.3	3438.2	3399.0	3397.4	3395.9	3366.7	3337.5
5°	3412.8	3336.7	3260.7	3186.1	3111.6	3037.1	2962.6	2945.7	2928.8	2903.4	2878.1
7.5°	3222.3	3100.9	2979.5	2884.2	2788.9	2714.4	2639.9	2589.2	2538.5	2499.3	2460.1
10°	3017.9	2867.3	2716.7	2601.5	2486.2	2405.6	2324.9	2266.5	2208.1	2180.4	2152.8
12.5°	2805.8	2642.2	2478.5	2365.6	2252.7	2155.9	2059.1	2006.0	1953.0	1914.6	1876.2
15°	2610.7	2434.7	2258.8	2139.0	2019.1	1928.4	1837.8	1784.8	1731.8	1693.3	1654.9
17.5°	2421.7	2244.2	2066.7	1945.3	1823.9	1741.7	1659.5	1608.1	1556.6	1532.8	1508.9
20°	2249.6	2070.6	1891.6	1777.1	1662.6	1581.9	1501.3	1473.6	1445.9	1423.7	1401.4
22.5°	2079.0	1906.9	1734.8	1625.0	1515.1	1456.7	1398.3	1376.0	1353.7	1336.8	1319.9
25°	1936.1	1764.8	1593.5	1497.4	1401.4	1356.1	1310.7	1296.1	1281.5	1264.6	1247.7
27.5°	1791.7	1628.8	1465.9	1389.1	1312.3	1275.4	1238.5	1220.1	1201.6	1187.8	1174.0
30°	1664.1	1513.6	1363.0	1299.2	1235.4	1203.2	1170.9	1150.9	1130.9	1117.9	1104.8
32.5°	1541.2	1407.5	1273.8	1219.3	1164.7	1133.2	1101.7	1082.5	1063.3	1048.0	1032.6
35°	1427.5	1311.5	1195.5	1145.5	1095.6	1064.1	1032.6	1013.4	994.2	978.8	963.5
37.5°	1327.6	1222.4	1117.1	1070.2	1023.4	995.7	968.1	948.1	928.1	912.0	895.8
40°	1233.9	1140.9	1048.0	1002.6	957.3	927.3	897.4	879.7	862.0	847.4	832.8
42.5°	1150.9	1065.6	980.4	935.8	891.2	862.8	834.4	813.6	792.9	784.4	776.0
45°	1063.3	988.0	912.7	869.7	826.7	796.7	766.8	749.1	731.4	723.7	716.1
47.5°	986.5	916.6	846.7	804.4	762.2	735.3	708.4	694.5	680.7	670.0	659.2
50°	911.2	843.6	776.0	735.3	694.5	671.5	648.4	631.5	614.6	607.0	599.3
52.5°	839.0	777.5	716.1	674.6	633.1	610.8	588.5	573.9	559.3	543.2	527.1
55°	757.5	703.8	650.0	613.1	576.2	553.2	530.1	513.2	496.3	479.4	462.5
57.5°	689.9	636.9	583.9	550.9	517.8	495.6	473.3	454.8	436.4	422.6	408.7
60°	616.2	570.1	524.0	491.7	459.4	437.9	416.4	398.7	381.1	374.2	367.2
62.5°	547.0	504.0	461.0	432.6	404.1	383.4	362.6	351.1	339.6	335.0	330.4
65°	476.3	439.5	402.6	376.5	350.3	332.7	315.0	309.6	304.2	300.4	296.6
67.5°	410.3	378.8	347.3	324.2	301.2	288.9	276.6	270.4	264.3	259.7	255.1
70°	350.3	322.7	295.0	275.1	255.1	243.6	232.0	226.6	221.3	212.8	204.4
72.5°	285.8	264.3	242.8	227.4	212.1	202.1	192.1	181.3	170.6	162.9	155.2
75°	236.6	215.1	193.6	179.0	164.4	152.9	141.4	137.5	133.7	131.4	129.1
77.5°	181.3	162.9	144.4	132.9	121.4	116.0	110.6	108.3	106.0	105.3	104.5
80°	130.6	115.2	99.9	93.7	87.6	86.0	84.5	83.0	81.4	80.7	79.9
82.5°	81.4	73.8	66.1	64.5	63.0	62.2	61.5	60.7	59.9	59.2	58.4
85°	47.6	44.6	41.5	40.7	40.0	39.2	38.4	38.4	38.4	38.4	38.4
87.5°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	19.2	18.4
90°	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2	20.8	21.5	22.1
92.5°	13.8	14.1	15.6	17.2	18.8	20.3	21.5	22.8	24.0	25.2	25.9
95°	19.2	16.6	18.5	20.4	22.3	24.2	25.5	26.7	27.9	29.1	29.7
97.5°	67.3	60.5	51.6	42.7	33.9	25.0	26.4	27.8	29.2	30.6	31.4
100°	146.0	134.2	107.1	80.0	52.9	25.8	27.2	28.6	30.0	31.4	32.1
102.5°	192.8	178.8	148.5	118.3	88.1	57.9	52.1	46.4	40.7	34.9	32.2
105°	240.6	233.8	218.1	202.5	186.8	171.2	140.5	109.7	79.0	48.2	33.0
107.5°	291.6	293.7	296.3	298.9	301.5	304.1	277.4	250.6	223.9	197.1	172.3
110°	343.3	344.9	346.9	348.8	350.7	352.6	346.9	341.1	335.4	329.7	314.4



TEST NUMBER: P832011

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	392.6	394.2	396.1	398.0	399.9	401.8	403.4	405.0	406.5	408.1	408.7
115°	441.2	442.5	444.1	445.6	447.2	448.8	450.5	452.2	454.0	455.7	456.9
117.5°	490.4	491.4	492.3	493.1	494.0	494.9	496.3	497.7	499.0	500.4	501.2
120°	536.3	537.4	537.9	538.4	538.9	539.4	540.8	542.2	543.6	545.0	545.7
122.5°	580.3	581.2	581.9	582.6	583.3	584.0	584.9	585.7	586.6	587.5	588.0
125°	621.6	622.7	623.4	624.0	624.7	625.4	625.8	626.1	626.5	626.8	627.2
127.5°	662.3	663.4	664.3	665.1	666.0	666.9	667.4	667.9	668.4	669.0	669.0
130°	699.8	700.8	701.5	702.2	702.9	703.6	704.3	705.0	705.7	706.4	706.6
132.5°	735.8	736.7	737.2	737.8	738.3	738.8	739.5	740.2	740.9	741.6	741.7
135°	771.1	772.0	772.7	773.4	774.1	774.8	775.3	775.8	776.3	776.8	776.8
137.5°	803.8	804.6	805.0	805.3	805.7	806.0	806.9	807.8	808.6	809.5	809.8
140°	833.7	834.4	835.0	835.5	836.0	836.5	837.2	837.9	838.6	839.3	839.5
142.5°	862.6	863.4	863.9	864.4	864.9	865.4	866.0	866.5	867.0	867.5	867.5
145°	889.9	890.6	891.0	891.3	891.7	892.0	892.4	892.7	893.1	893.4	893.6
147.5°	914.3	914.9	915.2	915.6	915.9	916.3	916.6	917.0	917.3	917.7	917.4
150°	936.3	936.8	937.1	937.5	937.8	938.2	938.5	938.8	939.2	939.5	939.5
152.5°	956.0	956.2	956.4	956.6	956.7	956.9	957.6	958.3	959.0	959.7	959.6
155°	973.5	973.4	973.6	973.8	973.9	974.1	975.0	975.9	976.7	977.6	977.5
157.5°	990.5	990.4	990.3	990.1	989.9	989.8	990.8	991.8	992.9	993.9	993.7
160°	1003.9	1003.7	1003.6	1003.4	1003.2	1003.0	1004.1	1005.1	1006.2	1007.2	1007.1
162.5°	1015.8	1015.5	1015.3	1015.1	1014.9	1014.8	1016.0	1017.2	1018.4	1019.6	1019.7
165°	1026.0	1025.6	1025.5	1025.3	1025.1	1024.9	1026.3	1027.7	1029.1	1030.5	1030.6
167.5°	1033.9	1033.5	1033.5	1033.5	1033.5	1033.5	1034.9	1036.3	1037.7	1039.1	1039.1
170°	1040.9	1040.6	1040.6	1040.6	1040.6	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1
172.5°	1044.9	1044.6	1044.7	1044.9	1045.1	1045.3	1046.6	1048.0	1049.4	1050.8	1050.7
175°	1048.8	1048.5	1048.6	1048.8	1049.0	1049.2	1050.4	1051.6	1052.8	1054.0	1053.9
177.5°	1050.4	1050.0	1050.2	1050.4	1050.6	1050.7	1052.1	1053.5	1054.9	1056.3	1056.1
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P832011

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3747.8	3747.8	3747.8	3747.8
2.5°	3329.8	3322.1	3319.1	3316.0
5°	2854.2	2830.4	2825.0	2819.7
7.5°	2450.1	2440.1	2407.1	2374.1
10°	2122.1	2091.3	2077.5	2063.7
12.5°	1847.8	1819.3	1814.7	1810.1
15°	1634.9	1615.0	1608.1	1601.1
17.5°	1495.1	1481.3	1472.8	1464.4
20°	1391.4	1381.4	1375.3	1369.1
22.5°	1312.3	1304.6	1300.0	1295.4
25°	1236.2	1224.7	1220.8	1217.0
27.5°	1164.0	1154.0	1150.1	1146.3
30°	1096.4	1087.9	1082.5	1077.2
32.5°	1022.6	1012.6	1009.5	1006.5
35°	957.3	951.2	948.1	945.0
37.5°	888.2	880.5	875.9	871.3
40°	829.0	825.2	822.9	820.5
42.5°	769.1	762.2	761.4	760.6
45°	709.1	702.2	700.7	699.2
47.5°	653.1	646.9	646.1	645.4
50°	590.8	582.4	576.2	570.1
52.5°	519.4	511.7	506.3	500.9
55°	454.1	445.6	441.0	436.4
57.5°	404.9	401.1	398.7	396.4
60°	364.9	362.6	361.1	359.6
62.5°	328.1	325.8	325.8	325.8
65°	294.3	292.0	289.6	287.3
67.5°	250.5	245.9	245.1	244.3
70°	197.5	190.5	189.8	189.0
72.5°	154.4	153.7	152.1	150.6
75°	127.5	126.0	126.0	126.0
77.5°	103.0	101.4	101.4	101.4
80°	79.1	78.4	79.1	79.9
82.5°	58.4	58.4	57.6	56.9
85°	37.6	36.9	36.9	36.9
87.5°	18.4	18.4	18.4	18.4
90°	22.4	22.8	23.1	23.5
92.5°	26.1	26.2	26.4	26.6
95°	29.7	29.7	29.7	29.7
97.5°	31.5	31.7	31.9	32.1
100°	32.3	32.5	32.7	32.8
102.5°	32.6	32.9	33.3	33.6
105°	33.4	33.7	34.1	34.4
107.5°	149.6	126.8	104.1	81.3
110°	289.5	264.7	239.8	215.0



TEST NUMBER: P832011

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	408.4	408.0	407.7	407.3
115°	457.6	458.3	459.0	459.7
117.5°	501.4	501.6	501.7	501.9
120°	545.7	545.7	545.7	545.7
122.5°	588.2	588.3	588.5	588.7
125°	627.5	627.9	628.2	628.6
127.5°	668.7	668.3	668.0	667.7
130°	706.2	705.9	705.5	705.2
132.5°	741.1	740.6	740.1	739.6
135°	776.3	775.8	775.3	774.8
137.5°	809.4	809.1	808.7	808.4
140°	839.1	838.8	838.4	838.1
142.5°	867.0	866.5	866.0	865.4
145°	893.6	893.6	893.6	893.6
147.5°	916.5	915.7	914.8	913.9
150°	938.9	938.4	937.9	937.4
152.5°	958.7	957.9	957.0	956.1
155°	976.5	975.4	974.4	973.3
157.5°	992.4	991.0	989.6	988.2
160°	1005.9	1004.7	1003.5	1002.3
162.5°	1018.7	1017.6	1016.6	1015.6
165°	1029.4	1028.1	1026.9	1025.7
167.5°	1037.7	1036.3	1034.9	1033.5
170°	1044.7	1043.3	1042.0	1040.6
172.5°	1049.2	1047.6	1046.0	1044.5
175°	1052.6	1051.2	1049.8	1048.4
177.5°	1054.4	1052.6	1050.9	1049.2
180°	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P832011

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.55	15.45	15.42	16.33	17.45	19.21	20.11	20.09	21.00	22.11
	3H	15.78	16.58	16.66	17.47	18.61	20.72	21.52	21.60	22.41	23.55
	4H	16.16	16.92	17.06	17.82	18.97	21.21	21.97	22.11	22.87	24.02
	6H	16.45	17.14	17.36	18.05	19.21	21.53	22.22	22.44	23.13	24.29
	8H	16.54	17.20	17.46	18.12	19.28	21.61	22.27	22.53	23.19	24.35
	12H	16.59	17.22	17.51	18.14	19.32	21.64	22.27	22.57	23.19	24.37
4H	2H	15.28	16.04	16.19	16.94	18.09	19.22	19.97	20.12	20.87	22.02
	3H	16.66	17.28	17.57	18.21	19.38	20.88	21.51	21.80	22.44	23.60
	4H	17.12	17.69	18.04	18.61	19.80	21.49	22.06	22.42	22.99	24.18
	6H	17.49	17.98	18.43	18.93	20.12	21.93	22.42	22.87	23.37	24.56
	8H	17.61	18.07	18.55	19.01	20.22	22.06	22.52	23.01	23.47	24.67
	12H	17.69	18.10	18.65	19.07	20.27	22.13	22.54	23.09	23.50	24.71
8H	4H	17.43	17.89	18.37	18.84	20.04	21.46	21.92	22.40	22.86	24.07
	6H	17.90	18.28	18.87	19.26	20.47	21.96	22.34	22.93	23.32	24.53
	8H	18.09	18.43	19.07	19.40	20.62	22.15	22.48	23.12	23.46	24.68
	12H	18.24	18.53	19.21	19.50	20.77	22.27	22.56	23.24	23.53	24.80
12H	4H	17.45	17.86	18.41	18.82	20.03	21.42	21.83	22.38	22.79	24.00
	6H	17.96	18.29	18.93	19.27	20.49	21.94	22.27	22.91	23.25	24.47
	8H	18.18	18.47	19.16	19.44	20.71	22.13	22.42	23.11	23.39	24.66