

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332345-840

Luminaire Tested: **S123RDIP-S1000D805U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332345-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7072.2 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332345-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332345-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	54	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	61	77	68	62	57	59	54	50	50	47	44	42	40	38	34
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	65	55	47	42	47	42	37	41	36	33	34	31	29	26
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	47	40	34	55	45	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	36	30	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	30	26	33	27	23	28	24	21	24	21	19	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18243	18243	18243
5°	18312	18058	18163
10°	18208	17832	17772
15°	18013	17415	17231
20°	17743	16893	16501
25°	17467	16308	15785
30°	17100	15632	14777
35°	16724	14954	13853
40°	16378	14155	12708
45°	15923	13370	11676
50°	15421	12476	10518
55°	14910	11453	9439
60°	14441	10357	8254
65°	13827	9172	7070
70°	13064	7701	5712
75°	11948	6059	5373
80°	10649	5362	4940
85°	8991	4755	4409



TEST NUMBER: P332345-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	2.3
10°-20°	442.8	6.3
20°-30°	637.6	9.0
30°-40°	718.2	10.2
40°-50°	687.1	9.7
50°-60°	562.6	8.0
60°-70°	379.6	5.4
70°-80°	191.0	2.7
80°-90°	53.5	0.8
90°-100°	38.6	0.5
100°-110°	184.1	2.6
110°-120°	442.3	6.3
120°-130°	563.2	8.0
130°-140°	601.8	8.5
140°-150°	562.7	8.0
150°-160°	453.9	6.4
160°-170°	293.0	4.1
170°-180°	101.0	1.4
0°-30°	1239.5	17.5
0°-40°	1957.7	27.7
0°-60°	3207.4	45.4
0°-90°	3831.5	54.2
90°-120°	665.1	9.4
90°-150°	2392.8	33.8
90°-180°	3241.0	45.8
0°-180°	7072.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1695	1695	1695	1695	1695	
5°	1695	1687	1671	1683	1681	161
15°	1616	1600	1563	1556	1546	455
25°	1471	1435	1373	1345	1329	676
35°	1273	1221	1138	1081	1054	796
45°	1046	982	878	802	767	807
55°	794	724	610	533	503	712
65°	543	466	360	296	278	537
75°	287	221	146	133	129	306
85°	73	44	38	36	36	82
90°	1	9	19	22	24	6
95°	48	18	24	30	30	60
105°	235	240	173	41	35	249
115°	441	446	453	461	464	435
125°	622	628	632	633	635	555
135°	774	779	782	784	782	596
145°	894	899	901	902	902	559
155°	984	983	984	987	983	453
165°	1038	1036	1035	1041	1036	293
175°	1063	1059	1060	1064	1059	101
180°	1063	1063	1063	1063	1063	



TEST NUMBER: P332345-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1700.2	1699.2	1698.3	1697.3	1696.3	1694.4	1691.4	1688.5	1685.6	1682.6	1685.3
5°	1694.8	1693.1	1691.6	1690.1	1688.6	1686.0	1682.3	1678.7	1675.1	1671.3	1674.1
7.5°	1679.0	1677.4	1675.8	1674.1	1672.4	1669.2	1664.5	1659.7	1655.0	1650.2	1651.7
10°	1665.9	1663.8	1661.5	1659.4	1657.3	1653.5	1648.0	1642.4	1637.0	1631.5	1631.8
12.5°	1647.2	1644.8	1642.4	1640.0	1637.6	1633.1	1626.4	1619.6	1613.0	1606.2	1606.0
15°	1616.4	1613.1	1609.6	1606.3	1603.0	1597.0	1588.4	1579.8	1571.3	1562.8	1561.3
17.5°	1577.6	1573.7	1569.8	1565.9	1562.0	1554.6	1543.7	1532.9	1522.0	1511.1	1507.8
20°	1549.0	1544.2	1539.2	1534.4	1529.4	1521.3	1509.6	1498.0	1486.4	1474.8	1470.9
22.5°	1517.1	1511.6	1505.9	1500.3	1494.7	1485.7	1473.3	1461.0	1448.7	1436.3	1431.4
25°	1470.7	1463.1	1455.4	1447.7	1440.2	1429.3	1415.2	1401.2	1387.2	1373.1	1366.7
27.5°	1414.3	1405.9	1397.5	1389.1	1380.6	1368.6	1352.9	1337.3	1321.6	1306.1	1297.1
30°	1375.8	1366.7	1357.6	1348.4	1339.2	1326.1	1309.0	1291.8	1274.8	1257.7	1247.3
32.5°	1337.4	1327.0	1316.6	1306.2	1295.9	1281.6	1263.5	1245.5	1227.3	1209.2	1197.9
35°	1272.7	1261.7	1250.7	1239.8	1228.8	1213.8	1194.9	1175.9	1157.0	1138.0	1124.9
37.5°	1207.3	1195.1	1182.9	1170.6	1158.4	1142.3	1122.1	1101.8	1081.6	1061.4	1046.4
40°	1165.6	1152.2	1138.6	1125.2	1111.8	1094.2	1072.6	1050.9	1029.2	1007.4	991.6
42.5°	1118.2	1104.8	1091.4	1077.9	1064.5	1046.6	1024.2	1001.8	979.4	956.9	939.6
45°	1046.0	1032.2	1018.4	1004.7	991.0	972.4	948.9	925.3	901.8	878.3	860.9
47.5°	973.7	958.6	943.5	928.4	913.3	894.0	870.5	847.0	823.4	799.9	781.0
50°	920.9	906.6	892.2	877.9	863.4	843.9	819.2	794.5	769.7	745.0	726.0
52.5°	873.6	858.1	842.4	826.9	811.3	791.2	766.8	742.3	717.8	693.3	673.6
55°	794.5	779.5	764.5	749.5	734.6	714.1	688.1	662.2	636.2	610.3	592.6
57.5°	721.3	705.0	688.7	672.4	656.1	634.9	608.7	582.7	556.6	530.6	513.8
60°	670.8	654.0	637.1	620.4	603.5	582.5	557.1	531.8	506.4	481.1	464.5
62.5°	620.2	603.4	586.5	569.8	553.0	531.9	506.5	481.2	455.9	430.5	415.0
65°	542.9	526.1	509.3	492.5	475.7	455.4	431.6	407.8	384.0	360.1	345.2
67.5°	465.6	448.7	431.7	414.8	397.8	377.8	355.0	332.1	309.3	286.4	275.3
70°	415.1	398.6	382.1	365.6	349.1	330.2	308.8	287.4	266.0	244.7	234.0
72.5°	364.5	348.3	332.0	315.8	299.5	281.7	262.3	242.9	223.4	204.0	195.2
75°	287.3	272.6	257.9	243.3	228.6	212.9	196.1	179.3	162.5	145.7	142.6
77.5°	216.9	203.6	190.4	177.1	163.9	151.8	141.0	130.2	119.4	108.6	106.9
80°	171.8	159.3	146.7	134.2	121.7	112.3	105.8	99.4	93.0	86.5	85.6
82.5°	129.0	118.2	107.3	96.4	85.6	78.8	75.7	72.8	69.8	66.8	65.8
85°	72.8	66.1	59.4	52.7	45.9	42.1	41.2	40.3	39.4	38.5	37.9
87.5°	26.6	24.2	21.9	19.5	17.2	16.3	16.8	17.2	17.7	18.1	18.0
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.3	16.7	19.0	19.7
92.5°	14.6	14.2	13.7	13.2	12.7	13.3	15.0	16.8	18.5	20.2	21.3
95°	48.2	41.0	33.7	26.6	19.4	16.8	18.7	20.6	22.5	24.4	25.8
97.5°	96.7	93.6	90.4	87.2	83.9	75.9	63.3	50.7	38.1	25.4	26.9
100°	133.4	136.9	140.5	143.9	147.4	135.5	108.2	80.8	53.4	26.1	27.5
102.5°	175.1	177.6	180.2	182.7	185.2	171.6	141.7	111.7	81.8	51.9	47.6
105°	235.3	237.2	239.1	241.1	243.0	236.1	220.3	204.5	188.6	172.9	141.9
107.5°	298.7	300.3	301.8	303.4	304.9	306.9	309.4	311.9	314.4	316.9	294.2
110°	341.0	342.4	343.9	345.3	346.7	348.3	350.3	352.2	354.2	356.1	350.3



TEST NUMBER: P332345-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.5	382.7	384.1	385.3	386.6	388.1	390.1	392.0	393.9	395.9	396.0
115°	441.3	442.4	443.4	444.5	445.6	446.9	448.5	450.0	451.6	453.2	454.9
117.5°	499.3	500.6	501.9	503.2	504.4	505.5	506.3	507.2	508.0	508.8	510.2
120°	535.3	536.8	538.5	540.0	541.6	542.7	543.2	543.7	544.2	544.7	546.1
122.5°	571.9	573.2	574.5	575.8	577.1	578.0	578.8	579.5	580.1	580.8	581.8
125°	622.2	623.5	624.9	626.3	627.7	628.8	629.5	630.2	630.9	631.6	632.0
127.5°	670.8	672.2	673.6	675.0	676.4	677.5	678.3	679.2	680.0	680.9	681.5
130°	701.0	702.5	703.9	705.3	706.7	707.7	708.4	709.1	709.8	710.5	711.2
132.5°	730.1	731.5	733.0	734.4	735.8	736.7	737.3	737.8	738.4	739.0	739.7
135°	774.5	775.6	776.6	777.7	778.7	779.6	780.3	781.0	781.7	782.4	782.9
137.5°	812.4	813.7	815.1	816.4	817.7	818.6	819.0	819.4	819.7	820.1	821.0
140°	837.7	838.7	839.8	840.8	841.9	842.6	843.2	843.7	844.2	844.8	845.5
142.5°	861.0	862.1	863.1	864.2	865.3	866.1	866.6	867.1	867.6	868.2	868.7
145°	893.7	894.9	896.2	897.4	898.7	899.4	899.8	900.1	900.5	900.8	901.2
147.5°	924.5	925.3	926.1	927.0	927.8	928.4	928.7	929.0	929.4	929.7	930.1
150°	943.4	944.0	944.5	945.0	945.5	946.0	946.3	946.7	947.1	947.5	947.8
152.5°	960.5	960.8	961.0	961.3	961.5	961.7	961.9	962.1	962.4	962.6	963.2
155°	984.5	984.2	983.8	983.5	983.1	983.0	983.2	983.4	983.5	983.7	984.6
157.5°	1003.1	1003.1	1003.1	1003.0	1003.0	1002.9	1002.7	1002.6	1002.4	1002.2	1003.3
160°	1014.5	1014.3	1014.2	1014.0	1013.8	1013.6	1013.5	1013.3	1013.1	1012.9	1014.0
162.5°	1025.2	1024.8	1024.3	1023.9	1023.4	1023.1	1022.9	1022.8	1022.6	1022.4	1023.6
165°	1038.2	1037.6	1037.1	1036.6	1036.1	1035.7	1035.6	1035.4	1035.2	1035.0	1036.4
167.5°	1048.3	1047.6	1046.9	1046.2	1045.5	1045.1	1045.1	1045.1	1045.1	1045.1	1046.5
170°	1054.0	1053.3	1052.6	1051.9	1051.2	1050.9	1050.9	1050.9	1050.9	1050.9	1052.3
172.5°	1057.7	1056.9	1056.1	1055.2	1054.4	1054.1	1054.2	1054.3	1054.5	1054.6	1056.0
175°	1062.7	1061.8	1061.0	1060.1	1059.1	1058.8	1058.9	1059.1	1059.3	1059.6	1060.8
177.5°	1063.9	1063.3	1062.6	1061.9	1061.2	1060.9	1061.0	1061.2	1061.3	1061.4	1062.6
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332345-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1688.0	1690.7	1693.3	1694.5	1693.9	1693.5	1693.0	1692.5
5°	1676.9	1679.6	1682.3	1683.4	1682.8	1682.2	1681.6	1681.0
7.5°	1653.3	1654.8	1656.3	1656.6	1655.5	1654.5	1653.5	1652.3
10°	1632.1	1632.4	1632.7	1632.1	1630.5	1629.0	1627.5	1626.0
12.5°	1605.8	1605.7	1605.5	1604.5	1602.8	1600.9	1599.2	1597.4
15°	1559.7	1558.2	1556.7	1554.8	1552.7	1550.5	1548.4	1546.3
17.5°	1504.6	1501.4	1498.1	1494.9	1491.8	1488.5	1485.4	1482.2
20°	1466.8	1462.9	1459.0	1455.1	1451.5	1447.7	1444.1	1440.5
22.5°	1426.4	1421.5	1416.5	1412.3	1409.0	1405.5	1402.1	1398.7
25°	1360.3	1353.8	1347.5	1342.5	1339.2	1335.8	1332.5	1329.1
27.5°	1288.2	1279.3	1270.3	1263.3	1258.2	1253.0	1247.9	1242.8
30°	1236.9	1226.5	1216.1	1208.5	1203.6	1198.7	1193.8	1188.9
32.5°	1186.5	1175.2	1163.8	1155.6	1150.4	1145.3	1140.1	1135.0
35°	1111.8	1098.6	1085.5	1076.2	1070.8	1065.2	1059.8	1054.2
37.5°	1031.6	1016.6	1001.8	990.9	984.1	977.3	970.6	963.8
40°	975.7	959.9	943.9	932.5	925.4	918.5	911.4	904.4
42.5°	922.2	904.8	887.5	875.7	869.4	863.1	856.8	850.5
45°	843.4	826.1	808.6	796.3	788.9	781.6	774.3	767.0
47.5°	762.0	743.2	724.2	711.4	704.9	698.4	691.9	685.3
50°	707.1	688.1	669.2	656.2	649.2	642.2	635.2	628.1
52.5°	654.0	634.3	614.6	601.6	595.3	589.1	582.8	576.4
55°	574.8	557.1	539.4	527.5	521.4	515.2	509.2	503.0
57.5°	497.1	480.3	463.6	452.6	447.5	442.2	437.1	431.8
60°	448.1	431.6	415.1	404.2	399.1	393.8	388.7	383.4
62.5°	399.4	384.0	368.4	357.9	352.5	347.1	341.6	336.2
65°	330.2	315.2	300.2	291.0	287.7	284.4	281.0	277.6
67.5°	264.1	252.9	241.8	234.3	230.8	227.1	223.5	219.9
70°	223.3	212.6	201.9	194.9	191.5	188.1	184.8	181.5
72.5°	186.5	177.7	169.1	164.0	162.6	161.2	159.8	158.3
75°	139.6	136.5	133.5	131.7	131.1	130.4	129.8	129.2
77.5°	105.3	103.6	102.0	100.9	100.3	99.7	99.1	98.5
80°	84.7	83.8	82.9	82.2	81.6	81.0	80.3	79.7
82.5°	64.9	64.0	63.1	62.6	62.5	62.4	62.2	62.1
85°	37.3	36.7	36.1	35.7	35.7	35.7	35.7	35.7
87.5°	17.9	17.8	17.7	17.6	17.4	17.2	17.0	16.9
90°	20.4	21.0	21.7	22.3	22.6	23.0	23.3	23.7
92.5°	22.4	23.5	24.7	25.3	25.5	25.8	26.0	26.3
95°	27.0	28.2	29.4	30.0	30.0	30.0	30.0	30.0
97.5°	28.3	29.6	31.0	31.8	32.0	32.2	32.3	32.5
100°	28.9	30.3	31.7	32.4	32.6	32.8	33.0	33.1
102.5°	43.2	38.9	34.5	32.5	32.8	33.1	33.4	33.8
105°	110.8	79.8	48.7	33.3	33.7	34.0	34.4	34.7
107.5°	271.4	248.6	225.8	202.7	179.4	155.9	132.5	109.1
110°	344.5	338.7	333.0	317.5	292.4	267.3	242.2	217.1



TEST NUMBER: P332345-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	396.1	396.2	396.3	393.6	388.4	383.0	377.8	372.5
115°	456.7	458.5	460.2	461.4	462.1	462.8	463.5	464.2
117.5°	511.6	513.0	514.3	515.1	515.3	515.4	515.5	515.7
120°	547.5	549.0	550.4	551.1	551.1	551.1	551.1	551.1
122.5°	582.7	583.7	584.7	585.2	585.4	585.5	585.7	585.8
125°	632.3	632.7	633.0	633.4	633.7	634.1	634.4	634.8
127.5°	682.0	682.6	683.1	683.2	682.9	682.6	682.2	681.9
130°	712.0	712.7	713.4	713.6	713.2	712.9	712.5	712.2
132.5°	740.3	741.0	741.7	741.8	741.4	740.9	740.4	739.9
135°	783.5	784.0	784.5	784.5	784.0	783.5	782.9	782.4
137.5°	821.8	822.6	823.5	823.7	823.4	823.0	822.7	822.3
140°	846.2	846.9	847.6	847.8	847.4	847.1	846.7	846.4
142.5°	869.3	869.8	870.4	870.4	869.9	869.4	869.0	868.5
145°	901.5	901.9	902.2	902.4	902.4	902.4	902.4	902.4
147.5°	930.4	930.8	931.1	930.9	930.1	929.3	928.5	927.7
150°	948.1	948.5	948.8	948.8	948.2	947.7	947.2	946.6
152.5°	963.8	964.4	965.1	965.0	964.2	963.4	962.6	961.8
155°	985.5	986.3	987.2	987.1	986.1	985.0	984.0	982.9
157.5°	1004.3	1005.3	1006.4	1006.2	1004.9	1003.5	1002.2	1000.8
160°	1015.0	1016.1	1017.1	1017.0	1015.8	1014.6	1013.4	1012.2
162.5°	1024.8	1026.0	1027.1	1027.2	1026.1	1025.0	1024.0	1022.9
165°	1037.8	1039.3	1040.7	1040.8	1039.6	1038.2	1037.0	1035.8
167.5°	1047.9	1049.4	1050.8	1050.8	1049.4	1047.9	1046.5	1045.1
170°	1053.6	1055.0	1056.4	1056.4	1055.0	1053.6	1052.3	1050.9
172.5°	1057.4	1058.8	1060.3	1060.2	1058.6	1057.1	1055.5	1054.0
175°	1062.0	1063.2	1064.4	1064.3	1063.0	1061.6	1060.2	1058.7
177.5°	1063.7	1064.8	1065.9	1065.8	1064.4	1063.0	1061.6	1060.2
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7

(END OF REPORT)