

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831879

Luminaire Tested: S123RDIP-S1000D805U840-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831879  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D805U840-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 805 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7586.5 lumens  
Efficiency: N/A  
Efficacy: 136.2 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 55.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831879

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P831879

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57	57	57	57	
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55	50	50	50	50	
2	92	85	79	75	86	80	75	71	70	66	63	60	57	55	51	49	48	44	44	44	44	
3	85	76	69	64	79	71	65	60	62	58	54	54	51	48	46	44	42	38	38	38	38	
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	34	34	34	34	
5	72	61	54	48	67	58	51	46	51	45	41	45	40	37	39	36	33	30	30	30	30	
6	67	56	48	42	62	52	45	40	46	41	37	41	37	33	36	32	30	27	27	27	27	
7	62	51	43	38	58	48	41	36	43	37	33	38	33	30	33	30	27	25	25	25	25	
8	58	46	39	34	54	44	37	33	39	34	30	35	30	27	31	27	25	22	22	22	22	
9	54	43	36	31	51	41	34	30	36	31	27	32	28	25	29	25	23	21	21	21	21	
10	51	40	33	28	48	38	31	27	34	29	25	30	26	23	27	23	21	19	19	19	19	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	35273	35273	35273	35273	35273
5°	41884	40548	35496	28694	26640
10°	37948	41185	35319	22990	19723
15°	26127	35313	34946	18790	15601
20°	18176	27188	34244	15844	13712
25°	13851	20721	33224	14082	12638
30°	12057	16566	31947	13075	11707
35°	11069	13975	30137	12226	10858
40°	10100	12479	27771	11394	10082
45°	9121	11412	25219	10605	9305
50°	8279	10530	22206	9833	8348
55°	7488	9670	19314	9077	7161
60°	6710	8794	16777	8243	6768
65°	6194	7801	14441	7409	6401
70°	5032	6744	12601	6703	5202
75°	4413	5365	10672	5560	4583
80°	3998	4537	8746	4661	4333
85°	3656	3977	6632	4236	3977

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 26609 cd/sqm



TEST NUMBER: P831879

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	298.7	3.9
10°-20°	691.2	9.1
20°-30°	793.0	10.5
30°-40°	781.7	10.3
40°-50°	689.3	9.1
50°-60°	530.3	7.0
60°-70°	348.6	4.6
70°-80°	169.3	2.2
80°-90°	44.8	0.6
90°-100°	37.5	0.5
100°-110°	181.1	2.4
110°-120°	444.0	5.9
120°-130°	563.6	7.4
130°-140°	602.1	7.9
140°-150°	563.0	7.4
150°-160°	454.1	6.0
160°-170°	293.1	3.9
170°-180°	101.0	1.3
0°-30°	1782.9	23.5
0°-40°	2564.6	33.8
0°-60°	3784.2	49.9
0°-90°	4347.0	57.3
90°-120°	662.5	8.7
90°-150°	2391.3	31.5
90°-180°	3240.0	42.7
0°-180°	7586.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3277	3277	3277	3277	3277	
5°	3876	3753	3285	2656	2466	354
15°	2345	3169	3136	1686	1400	662
25°	1166	1745	2797	1186	1064	551
35°	842	1064	2294	930	826	525
45°	599	750	1657	697	611	465
55°	399	515	1029	484	382	358
65°	243	306	567	291	251	238
75°	106	129	257	134	110	114
85°	30	32	54	34	32	31
90°	24	19	1	19	24	12
95°	30	24	48	24	30	25
105°	35	173	235	173	35	72
115°	464	453	441	453	464	437
125°	635	632	622	632	635	567
135°	782	782	774	782	782	604
145°	902	901	894	901	902	564
155°	983	984	984	984	983	453
165°	1036	1035	1038	1035	1036	293
175°	1059	1060	1063	1060	1059	101
180°	1063	1063	1063	1063	1063	



TEST NUMBER: P831879

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0
2.5°	3631.7	3620.3	3608.9	3605.5	3602.2	3591.4	3580.7	3556.5	3532.3	3507.5	3482.6
5°	3876.3	3877.6	3879.0	3875.6	3872.2	3858.1	3844.0	3814.5	3784.9	3752.7	3720.4
7.5°	3801.0	3822.5	3844.0	3848.1	3852.1	3862.8	3873.6	3866.9	3860.2	3848.1	3836.0
10°	3471.9	3470.5	3469.2	3493.4	3517.5	3589.4	3661.3	3698.3	3735.2	3768.1	3801.0
12.5°	2934.4	2936.4	2938.4	3017.7	3097.0	3164.8	3232.7	3326.7	3420.8	3522.2	3623.7
15°	2344.6	2377.5	2410.4	2481.0	2551.5	2653.6	2755.7	2882.0	3008.3	3168.9	3329.4
17.5°	1925.4	1939.5	1953.6	2021.4	2089.3	2186.0	2282.8	2425.9	2569.0	2775.9	2982.8
20°	1586.8	1599.6	1612.3	1661.4	1710.4	1803.1	1895.8	2032.2	2168.6	2373.5	2578.4
22.5°	1324.8	1349.6	1374.5	1407.4	1440.3	1507.5	1574.7	1713.8	1852.8	2039.6	2226.3
25°	1166.2	1177.7	1189.1	1217.3	1245.5	1310.0	1374.5	1466.5	1558.6	1744.7	1930.7
27.5°	1058.8	1062.1	1065.5	1086.3	1107.1	1148.8	1190.4	1275.7	1361.1	1514.2	1667.4
30°	970.1	976.1	982.2	998.3	1014.4	1044.6	1074.9	1135.3	1195.8	1332.8	1469.9
32.5°	901.6	904.9	908.3	921.7	935.1	957.3	979.5	1027.2	1074.9	1179.7	1284.5
35°	842.4	843.1	843.8	853.9	863.9	885.4	906.9	946.6	986.2	1063.5	1140.7
37.5°	775.3	780.0	784.7	792.1	799.4	818.3	837.1	869.3	901.6	965.4	1029.2
40°	718.8	722.9	726.9	735.6	744.4	759.1	773.9	803.5	833.0	888.1	943.2
42.5°	662.4	665.1	667.8	676.5	685.2	703.4	721.5	745.0	768.5	814.2	859.9
45°	599.2	606.0	612.7	622.1	631.5	646.9	662.4	686.6	710.8	749.7	788.7
47.5°	546.8	550.2	553.6	561.6	569.7	588.5	607.3	628.8	650.3	686.6	722.9
50°	494.4	495.8	497.1	504.5	511.9	528.7	545.5	570.4	595.2	628.8	662.4
52.5°	444.7	448.1	451.4	458.8	466.2	477.6	489.1	514.6	540.1	573.0	606.0
55°	399.0	401.1	403.1	408.5	413.8	427.3	440.7	462.9	485.0	515.3	545.5
57.5°	356.1	358.7	361.4	365.5	369.5	381.6	393.7	413.2	432.6	462.9	493.1
60°	311.7	315.1	318.4	323.1	327.8	337.2	346.6	364.1	381.6	408.5	435.3
62.5°	279.5	280.1	280.8	284.8	288.9	295.6	302.3	316.4	330.5	357.4	384.3
65°	243.2	245.2	247.2	249.2	251.3	256.6	262.0	274.1	286.2	306.3	326.5
67.5°	205.6	207.6	209.6	213.0	216.3	221.0	225.7	233.8	241.8	260.7	279.5
70°	159.9	159.9	159.9	165.3	170.6	178.7	186.8	192.8	198.9	214.3	229.8
72.5°	130.3	131.0	131.7	132.3	133.0	137.7	142.4	152.5	162.6	172.0	181.4
75°	106.1	106.8	107.5	108.2	108.8	110.2	111.5	114.9	118.2	129.0	139.7
77.5°	84.6	85.3	86.0	86.7	87.3	88.7	90.0	91.4	92.7	96.7	100.8
80°	64.5	65.2	65.8	66.5	67.2	67.9	68.5	69.9	71.2	73.2	75.2
82.5°	47.0	47.0	47.0	47.0	47.0	48.4	49.7	49.7	49.7	51.1	52.4
85°	29.6	29.6	29.6	30.2	30.9	30.9	30.9	31.6	32.2	32.2	32.2
87.5°	13.4	12.8	12.1	12.8	13.4	13.4	13.4	14.1	14.8	14.8	14.8
90°	23.7	23.3	23.0	22.6	22.3	21.8	21.1	20.4	19.6	18.9	16.7
92.5°	26.8	26.7	26.5	26.3	26.1	25.4	24.2	23.0	21.8	20.5	18.9
95°	30.0	30.0	30.0	30.0	30.0	29.4	28.2	26.9	25.7	24.5	22.5
97.5°	32.4	32.2	32.0	31.8	31.7	30.9	29.5	28.1	26.7	25.3	34.2
100°	33.2	33.0	32.8	32.6	32.5	31.7	30.3	28.9	27.5	26.1	53.4
102.5°	33.9	33.6	33.2	32.9	32.5	35.3	41.1	46.8	52.6	58.4	89.0
105°	34.7	34.4	34.0	33.7	33.3	48.7	79.7	110.8	141.8	172.9	188.7
107.5°	82.1	105.1	128.1	151.1	174.0	199.0	226.1	253.1	280.1	307.1	304.5
110°	217.1	242.2	267.3	292.4	317.5	332.9	338.7	344.5	350.3	356.1	354.1



TEST NUMBER: P831879

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	411.3	411.7	412.0	412.4	412.7	412.1	410.5	409.0	407.4	405.8	403.9
115°	464.2	463.5	462.8	462.1	461.4	460.2	458.4	456.7	454.9	453.2	451.6
117.5°	506.9	506.7	506.5	506.3	506.2	505.4	504.0	502.6	501.2	499.8	498.9
120°	551.1	551.1	551.1	551.1	551.1	550.4	549.0	547.6	546.2	544.8	544.2
122.5°	594.5	594.3	594.1	594.0	593.8	593.3	592.4	591.5	590.6	589.8	589.1
125°	634.8	634.4	634.1	633.7	633.4	633.0	632.7	632.3	632.0	631.6	630.9
127.5°	674.2	674.6	674.9	675.3	675.6	675.6	675.0	674.5	674.0	673.4	672.6
130°	712.1	712.5	712.8	713.2	713.5	713.4	712.7	712.0	711.3	710.6	709.9
132.5°	746.9	747.4	747.9	748.5	749.0	748.9	748.2	747.5	746.8	746.1	745.6
135°	782.4	782.9	783.5	784.0	784.5	784.5	784.0	783.5	782.9	782.4	781.7
137.5°	816.4	816.7	817.1	817.4	817.8	817.5	816.6	815.7	814.9	814.0	813.6
140°	846.4	846.7	847.1	847.4	847.8	847.6	846.9	846.2	845.5	844.8	844.2
142.5°	874.0	874.5	875.0	875.6	876.1	876.1	875.6	875.0	874.5	874.0	873.5
145°	902.4	902.4	902.4	902.4	902.4	902.2	901.9	901.5	901.2	900.8	900.5
147.5°	922.9	923.8	924.7	925.6	926.4	926.7	926.4	926.0	925.7	925.3	925.0
150°	946.6	947.1	947.7	948.2	948.7	948.8	948.5	948.1	947.8	947.4	947.1
152.5°	965.6	966.4	967.3	968.2	969.1	969.2	968.5	967.8	967.1	966.4	966.2
155°	982.9	984.0	985.0	986.1	987.1	987.2	986.4	985.5	984.6	983.7	983.6
157.5°	997.9	999.3	1000.7	1002.1	1003.6	1003.7	1002.7	1001.6	1000.6	999.5	999.7
160°	1012.1	1013.4	1014.6	1015.8	1017.1	1017.1	1016.1	1015.0	1014.0	1012.9	1013.1
162.5°	1025.6	1026.6	1027.7	1028.7	1029.8	1029.7	1028.5	1027.2	1026.0	1024.8	1025.0
165°	1035.8	1037.1	1038.3	1039.5	1040.7	1040.7	1039.3	1037.9	1036.4	1035.0	1035.2
167.5°	1043.7	1045.1	1046.5	1047.9	1049.3	1049.3	1047.9	1046.5	1045.1	1043.7	1043.7
170°	1050.8	1052.2	1053.6	1055.0	1056.4	1056.4	1055.0	1053.6	1052.2	1050.8	1050.8
172.5°	1054.8	1056.4	1057.9	1059.5	1061.1	1061.2	1059.8	1058.4	1057.0	1055.6	1055.4
175°	1058.7	1060.1	1061.5	1062.9	1064.3	1064.4	1063.2	1062.0	1060.7	1059.5	1059.3
177.5°	1059.5	1061.3	1063.0	1064.8	1066.5	1066.7	1065.3	1063.9	1062.5	1061.1	1060.9
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P831879

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0
2.5°	3479.2	3475.9	3443.6	3411.4	3379.8	3348.2	3324.7	3301.2	3261.6	3221.9	3197.1
5°	3694.9	3669.4	3618.3	3567.3	3490.7	3414.1	3349.6	3285.1	3203.1	3121.2	3052.7
7.5°	3815.1	3794.3	3732.5	3670.7	3569.3	3467.8	3367.1	3266.3	3145.4	3024.4	2921.0
10°	3818.5	3836.0	3784.9	3733.9	3619.7	3505.4	3368.4	3231.4	3068.8	2906.2	2772.5
12.5°	3698.9	3774.2	3763.4	3752.7	3636.4	3520.2	3353.6	3187.0	2987.5	2788.0	2620.7
15°	3475.2	3621.0	3664.0	3707.0	3610.9	3514.9	3325.4	3136.0	2901.5	2667.0	2474.9
17.5°	3187.0	3391.2	3504.8	3618.3	3548.4	3478.6	3271.0	3063.4	2799.4	2535.4	2326.4
20°	2845.7	3113.1	3291.1	3469.2	3443.6	3418.1	3203.8	2989.5	2704.7	2419.8	2193.4
22.5°	2508.5	2790.7	3036.5	3282.4	3308.6	3334.8	3118.5	2902.2	2590.5	2278.7	2048.3
25°	2217.6	2504.5	2797.4	3090.3	3149.4	3208.5	3002.9	2797.4	2474.2	2151.1	1922.0
27.5°	1940.2	2212.9	2535.4	2857.8	2965.3	3072.8	2884.7	2696.6	2360.0	2023.5	1795.0
30°	1713.8	1957.6	2286.8	2616.0	2765.8	2915.6	2743.0	2570.3	2236.4	1902.5	1678.8
32.5°	1502.8	1721.1	2051.7	2382.2	2556.2	2730.2	2581.1	2431.9	2110.8	1789.7	1568.7
35°	1336.2	1531.7	1840.1	2148.4	2343.2	2538.1	2415.8	2293.5	1979.8	1666.1	1457.1
37.5°	1193.1	1357.0	1646.6	1936.1	2143.0	2350.0	2247.8	2145.7	1850.8	1555.9	1358.4
40°	1074.9	1206.6	1475.9	1745.3	1948.2	2151.1	2063.8	1976.4	1712.4	1448.4	1263.7
42.5°	973.4	1087.0	1328.8	1570.7	1756.8	1942.8	1885.1	1827.3	1588.1	1349.0	1177.7
45°	884.1	979.5	1192.4	1405.4	1576.7	1748.0	1702.3	1656.7	1450.4	1244.2	1087.0
47.5°	804.8	886.8	1076.9	1267.0	1420.9	1574.7	1532.4	1490.0	1319.4	1148.8	1005.7
50°	732.3	802.1	960.7	1119.2	1257.6	1396.0	1361.1	1326.1	1185.1	1044.0	920.4
52.5°	663.7	721.5	863.9	1006.4	1117.9	1229.4	1202.5	1175.6	1066.8	958.0	845.8
55°	598.6	651.6	771.9	892.1	987.5	1082.9	1056.1	1029.2	944.5	859.9	761.1
57.5°	539.5	585.8	683.2	780.6	856.5	932.5	919.7	906.9	836.4	765.9	684.6
60°	477.0	518.6	602.6	686.6	747.7	808.8	794.1	779.3	728.9	678.5	608.6
62.5°	421.2	458.2	525.3	592.5	642.2	692.0	681.2	670.5	632.2	593.9	536.1
65°	362.8	399.0	453.5	507.9	546.8	585.8	576.4	567.0	538.1	509.2	462.9
67.5°	309.7	339.9	387.0	434.0	460.2	486.4	481.0	475.6	453.5	431.3	395.0
70°	256.0	282.2	321.1	360.1	378.2	396.4	398.4	400.4	380.2	360.1	333.2
72.5°	202.2	223.0	259.3	295.6	309.7	323.8	323.1	322.5	310.4	298.3	274.1
75°	155.2	170.6	198.9	227.1	239.2	251.3	253.9	256.6	245.2	233.8	220.4
77.5°	111.5	122.3	143.8	165.3	178.7	192.1	193.5	194.8	189.4	184.1	171.3
80°	78.6	82.0	95.4	108.8	122.9	137.0	139.1	141.1	135.7	130.3	122.3
82.5°	54.4	56.4	61.1	65.8	77.3	88.7	91.4	94.1	91.4	88.7	79.9
85°	32.9	33.6	35.6	37.6	43.0	48.4	51.1	53.7	52.4	51.1	46.4
87.5°	14.8	14.8	15.5	16.1	17.5	18.8	22.2	25.5	23.5	21.5	19.5
90°	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	17.4	15.8	14.2	13.9	15.0	16.1	17.1	18.2	17.1	16.1	15.0
95°	20.6	18.7	16.8	19.4	26.6	33.8	41.0	48.2	41.0	33.8	26.6
97.5°	43.2	52.1	61.1	68.0	72.9	77.8	82.7	87.6	82.7	77.8	72.9
100°	80.8	108.2	135.5	147.5	144.0	140.4	136.9	133.4	136.9	140.4	144.0
102.5°	119.5	150.0	180.5	194.7	192.4	190.1	187.8	185.5	187.8	190.1	192.4
105°	204.5	220.3	236.1	243.0	241.1	239.1	237.2	235.3	237.2	239.1	241.1
107.5°	301.9	299.2	296.6	294.5	292.9	291.3	289.7	288.2	289.7	291.3	292.9
110°	352.2	350.3	348.3	346.7	345.3	343.9	342.5	341.1	342.5	343.9	345.3





TEST NUMBER: P831879

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	401.9	400.0	398.1	396.5	395.3	394.1	392.8	391.6	392.8	394.1	395.3
115°	450.0	448.4	446.9	445.5	444.5	443.4	442.4	441.3	442.4	443.4	444.5
117.5°	498.0	497.1	496.2	495.2	494.0	492.7	491.5	490.3	491.5	492.7	494.0
120°	543.7	543.2	542.7	541.6	540.0	538.4	536.9	535.3	536.9	538.4	540.0
122.5°	588.4	587.7	587.0	586.0	584.8	583.5	582.3	581.1	582.3	583.5	584.8
125°	630.2	629.5	628.8	627.7	626.3	624.9	623.5	622.1	623.5	624.9	626.3
127.5°	671.7	670.8	669.9	668.8	667.4	666.0	664.6	663.2	664.6	666.0	667.4
130°	709.2	708.5	707.7	706.7	705.3	703.9	702.5	701.1	702.5	703.9	705.3
132.5°	745.0	744.5	744.0	743.0	741.6	740.2	738.8	737.4	738.8	740.2	741.6
135°	781.0	780.3	779.6	778.7	777.7	776.6	775.6	774.5	775.6	776.6	777.7
137.5°	813.3	812.9	812.6	811.7	810.3	808.9	807.5	806.1	807.5	808.9	810.3
140°	843.7	843.2	842.7	841.9	840.8	839.8	838.7	837.7	838.7	839.8	840.8
142.5°	872.9	872.4	871.9	871.1	870.0	869.0	867.9	866.9	867.9	869.0	870.0
145°	900.1	899.8	899.4	898.6	897.4	896.2	895.0	893.7	895.0	896.2	897.4
147.5°	924.6	924.2	923.9	923.3	922.4	921.5	920.7	919.8	920.7	921.5	922.4
150°	946.7	946.4	946.0	945.6	945.0	944.5	944.0	943.5	944.0	944.5	945.0
152.5°	966.0	965.8	965.7	965.5	965.3	965.1	965.0	964.8	965.0	965.1	965.3
155°	983.4	983.2	983.0	983.1	983.5	983.8	984.2	984.5	984.2	983.8	983.5
157.5°	999.9	1000.0	1000.2	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3
160°	1013.3	1013.5	1013.6	1013.8	1014.0	1014.2	1014.3	1014.5	1014.3	1014.2	1014.0
162.5°	1025.1	1025.3	1025.5	1025.8	1026.4	1026.9	1027.4	1027.9	1027.4	1026.9	1026.4
165°	1035.4	1035.6	1035.7	1036.1	1036.6	1037.1	1037.7	1038.2	1037.7	1037.1	1036.6
167.5°	1043.7	1043.7	1043.7	1044.1	1044.8	1045.5	1046.2	1046.9	1046.2	1045.5	1044.8
170°	1050.8	1050.8	1050.8	1051.2	1051.9	1052.6	1053.3	1054.0	1053.3	1052.6	1051.9
172.5°	1055.2	1055.0	1054.9	1055.2	1056.1	1057.0	1057.9	1058.7	1057.9	1057.0	1056.1
175°	1059.2	1059.0	1058.8	1059.2	1060.0	1060.9	1061.8	1062.7	1061.8	1060.9	1060.0
177.5°	1060.7	1060.6	1060.4	1060.7	1061.6	1062.5	1063.4	1064.3	1063.4	1062.5	1061.6
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P831879

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0	3277.0
2.5°	3172.2	3133.9	3095.6	3068.1	3040.6	3006.3	2972.0	2970.7	2969.4	2943.8	2918.3
5°	2984.1	2917.6	2851.1	2785.9	2720.8	2655.6	2590.5	2575.7	2560.9	2538.7	2516.6
7.5°	2817.5	2711.4	2605.2	2521.9	2438.6	2373.5	2308.3	2264.0	2219.6	2185.4	2151.1
10°	2638.8	2507.2	2375.5	2274.7	2173.9	2103.4	2032.9	1981.8	1930.7	1906.6	1882.4
12.5°	2453.4	2310.3	2167.2	2068.5	1969.7	1885.1	1800.4	1754.1	1707.7	1674.1	1640.5
15°	2282.8	2128.9	1975.1	1870.3	1765.5	1686.2	1606.9	1560.6	1514.2	1480.6	1447.1
17.5°	2117.5	1962.3	1807.1	1701.0	1594.9	1523.0	1451.1	1406.1	1361.1	1340.2	1319.4
20°	1967.0	1810.5	1654.0	1553.9	1453.8	1383.2	1312.7	1288.5	1264.3	1244.8	1225.4
22.5°	1817.9	1667.4	1516.9	1420.9	1324.8	1273.7	1222.7	1203.2	1183.7	1168.9	1154.2
25°	1692.9	1543.1	1393.3	1309.3	1225.4	1185.7	1146.1	1133.3	1120.6	1105.8	1091.0
27.5°	1566.6	1424.2	1281.8	1214.6	1147.4	1115.2	1082.9	1066.8	1050.7	1038.6	1026.5
30°	1455.1	1323.4	1191.8	1136.0	1080.3	1052.0	1023.8	1006.4	988.9	977.5	966.0
32.5°	1347.6	1230.7	1113.8	1066.1	1018.4	990.9	963.4	946.6	929.8	916.3	902.9
35°	1248.2	1146.8	1045.3	1001.7	958.0	930.4	902.9	886.1	869.3	855.9	842.4
37.5°	1160.9	1068.8	976.8	935.8	894.8	870.7	846.5	829.0	811.5	797.4	783.3
40°	1078.9	997.6	916.3	876.7	837.1	810.9	784.7	769.2	753.8	741.0	728.2
42.5°	1006.4	931.8	857.2	818.3	779.3	754.4	729.6	711.4	693.3	685.9	678.5
45°	929.8	863.9	798.1	760.5	722.9	696.7	670.5	655.0	639.6	632.8	626.1
47.5°	862.6	801.5	740.3	703.4	666.4	642.9	619.4	607.3	595.2	585.8	576.4
50°	796.8	737.6	678.5	642.9	607.3	587.2	567.0	552.2	537.4	530.7	524.0
52.5°	733.6	679.9	626.1	589.8	553.6	534.1	514.6	501.8	489.1	475.0	460.9
55°	662.4	615.4	568.3	536.1	503.8	483.7	463.5	448.8	434.0	419.2	404.4
57.5°	603.3	556.9	510.6	481.7	452.8	433.3	413.8	397.7	381.6	369.5	357.4
60°	538.8	498.5	458.2	430.0	401.7	382.9	364.1	348.7	333.2	327.2	321.1
62.5°	478.3	440.7	403.1	378.2	353.4	335.2	317.1	307.0	296.9	292.9	288.9
65°	416.5	384.3	352.0	329.2	306.3	290.9	275.4	270.7	266.0	262.7	259.3
67.5°	358.7	331.2	303.7	283.5	263.3	252.6	241.8	236.5	231.1	227.1	223.0
70°	306.3	282.2	258.0	240.5	223.0	213.0	202.9	198.2	193.5	186.1	178.7
72.5°	249.9	231.1	212.3	198.9	185.4	176.7	167.9	158.5	149.1	142.4	135.7
75°	206.9	188.1	169.3	156.5	143.8	133.7	123.6	120.3	116.9	114.9	112.9
77.5°	158.5	142.4	126.3	116.2	106.1	101.4	96.7	94.7	92.7	92.0	91.4
80°	114.2	100.8	87.3	82.0	76.6	75.2	73.9	72.6	71.2	70.5	69.9
82.5°	71.2	64.5	57.8	56.4	55.1	54.4	53.7	53.1	52.4	51.7	51.1
85°	41.7	39.0	36.3	35.6	34.9	34.3	33.6	33.6	33.6	33.6	33.6
87.5°	17.5	17.5	17.5	17.5	17.5	17.5	17.5	17.5	17.5	16.8	16.1
90°	7.8	9.8	12.1	14.4	16.7	18.9	19.6	20.4	21.1	21.8	22.3
92.5°	13.9	14.2	15.8	17.4	18.9	20.5	21.8	23.0	24.2	25.4	26.1
95°	19.4	16.8	18.7	20.6	22.5	24.5	25.7	26.9	28.2	29.4	30.0
97.5°	68.0	61.1	52.1	43.2	34.2	25.3	26.7	28.1	29.5	30.9	31.7
100°	147.5	135.5	108.2	80.8	53.4	26.1	27.5	28.9	30.3	31.7	32.5
102.5°	194.7	180.5	150.0	119.5	89.0	58.4	52.6	46.8	41.1	35.3	32.5
105°	243.0	236.1	220.3	204.5	188.7	172.9	141.8	110.8	79.7	48.7	33.3
107.5°	294.5	296.6	299.2	301.9	304.5	307.1	280.1	253.1	226.1	199.0	174.0
110°	346.7	348.3	350.3	352.2	354.1	356.1	350.3	344.5	338.7	332.9	317.5



TEST NUMBER: P831879

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	396.5	398.1	400.0	401.9	403.9	405.8	407.4	409.0	410.5	412.1	412.7
115°	445.5	446.9	448.4	450.0	451.6	453.2	454.9	456.7	458.4	460.2	461.4
117.5°	495.2	496.2	497.1	498.0	498.9	499.8	501.2	502.6	504.0	505.4	506.2
120°	541.6	542.7	543.2	543.7	544.2	544.8	546.2	547.6	549.0	550.4	551.1
122.5°	586.0	587.0	587.7	588.4	589.1	589.8	590.6	591.5	592.4	593.3	593.8
125°	627.7	628.8	629.5	630.2	630.9	631.6	632.0	632.3	632.7	633.0	633.4
127.5°	668.8	669.9	670.8	671.7	672.6	673.4	674.0	674.5	675.0	675.6	675.6
130°	706.7	707.7	708.5	709.2	709.9	710.6	711.3	712.0	712.7	713.4	713.5
132.5°	743.0	744.0	744.5	745.0	745.6	746.1	746.8	747.5	748.2	748.9	749.0
135°	778.7	779.6	780.3	781.0	781.7	782.4	782.9	783.5	784.0	784.5	784.5
137.5°	811.7	812.6	812.9	813.3	813.6	814.0	814.9	815.7	816.6	817.5	817.8
140°	841.9	842.7	843.2	843.7	844.2	844.8	845.5	846.2	846.9	847.6	847.8
142.5°	871.1	871.9	872.4	872.9	873.5	874.0	874.5	875.0	875.6	876.1	876.1
145°	898.6	899.4	899.8	900.1	900.5	900.8	901.2	901.5	901.9	902.2	902.4
147.5°	923.3	923.9	924.2	924.6	925.0	925.3	925.7	926.0	926.4	926.7	926.4
150°	945.6	946.0	946.4	946.7	947.1	947.4	947.8	948.1	948.5	948.8	948.7
152.5°	965.5	965.7	965.8	966.0	966.2	966.4	967.1	967.8	968.5	969.2	969.1
155°	983.1	983.0	983.2	983.4	983.6	983.7	984.6	985.5	986.4	987.2	987.1
157.5°	1000.3	1000.2	1000.0	999.9	999.7	999.5	1000.6	1001.6	1002.7	1003.7	1003.6
160°	1013.8	1013.6	1013.5	1013.3	1013.1	1012.9	1014.0	1015.0	1016.1	1017.1	1017.1
162.5°	1025.8	1025.5	1025.3	1025.1	1025.0	1024.8	1026.0	1027.2	1028.5	1029.7	1029.8
165°	1036.1	1035.7	1035.6	1035.4	1035.2	1035.0	1036.4	1037.9	1039.3	1040.7	1040.7
167.5°	1044.1	1043.7	1043.7	1043.7	1043.7	1043.7	1045.1	1046.5	1047.9	1049.3	1049.3
170°	1051.2	1050.8	1050.8	1050.8	1050.8	1050.8	1052.2	1053.6	1055.0	1056.4	1056.4
172.5°	1055.2	1054.9	1055.0	1055.2	1055.4	1055.6	1057.0	1058.4	1059.8	1061.2	1061.1
175°	1059.2	1058.8	1059.0	1059.2	1059.3	1059.5	1060.7	1062.0	1063.2	1064.4	1064.3
177.5°	1060.7	1060.4	1060.6	1060.7	1060.9	1061.1	1062.5	1063.9	1065.3	1066.7	1066.5
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P831879

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	3277.0	3277.0	3277.0	3277.0
2.5°	2911.6	2904.9	2902.2	2899.5
5°	2495.7	2474.9	2470.2	2465.5
7.5°	2142.4	2133.6	2104.7	2075.9
10°	1855.5	1828.6	1816.5	1804.5
12.5°	1615.7	1590.8	1586.8	1582.8
15°	1429.6	1412.1	1406.1	1400.0
17.5°	1307.3	1295.2	1287.8	1280.4
20°	1216.6	1207.9	1202.5	1197.1
22.5°	1147.4	1140.7	1136.7	1132.7
25°	1080.9	1070.8	1067.5	1064.1
27.5°	1017.8	1009.0	1005.7	1002.3
30°	958.7	951.3	946.6	941.9
32.5°	894.2	885.4	882.7	880.1
35°	837.1	831.7	829.0	826.3
37.5°	776.6	769.9	765.9	761.8
40°	724.9	721.5	719.5	717.5
42.5°	672.5	666.4	665.8	665.1
45°	620.1	614.0	612.7	611.3
47.5°	571.0	565.7	565.0	564.3
50°	516.6	509.2	503.8	498.5
52.5°	454.1	447.4	442.7	438.0
55°	397.0	389.6	385.6	381.6
57.5°	354.0	350.7	348.7	346.6
60°	319.1	317.1	315.7	314.4
62.5°	286.9	284.8	284.8	284.8
65°	257.3	255.3	253.3	251.3
67.5°	219.0	215.0	214.3	213.6
70°	172.7	166.6	165.9	165.3
72.5°	135.0	134.4	133.0	131.7
75°	111.5	110.2	110.2	110.2
77.5°	90.0	88.7	88.7	88.7
80°	69.2	68.5	69.2	69.9
82.5°	51.1	51.1	50.4	49.7
85°	32.9	32.2	32.2	32.2
87.5°	16.1	16.1	16.1	16.1
90°	22.6	23.0	23.3	23.7
92.5°	26.3	26.5	26.7	26.8
95°	30.0	30.0	30.0	30.0
97.5°	31.8	32.0	32.2	32.4
100°	32.6	32.8	33.0	33.2
102.5°	32.9	33.2	33.6	33.9
105°	33.7	34.0	34.4	34.7
107.5°	151.1	128.1	105.1	82.1
110°	292.4	267.3	242.2	217.1



TEST NUMBER: P831879

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	412.4	412.0	411.7	411.3
115°	462.1	462.8	463.5	464.2
117.5°	506.3	506.5	506.7	506.9
120°	551.1	551.1	551.1	551.1
122.5°	594.0	594.1	594.3	594.5
125°	633.7	634.1	634.4	634.8
127.5°	675.3	674.9	674.6	674.2
130°	713.2	712.8	712.5	712.1
132.5°	748.5	747.9	747.4	746.9
135°	784.0	783.5	782.9	782.4
137.5°	817.4	817.1	816.7	816.4
140°	847.4	847.1	846.7	846.4
142.5°	875.6	875.0	874.5	874.0
145°	902.4	902.4	902.4	902.4
147.5°	925.6	924.7	923.8	922.9
150°	948.2	947.7	947.1	946.6
152.5°	968.2	967.3	966.4	965.6
155°	986.1	985.0	984.0	982.9
157.5°	1002.1	1000.7	999.3	997.9
160°	1015.8	1014.6	1013.4	1012.1
162.5°	1028.7	1027.7	1026.6	1025.6
165°	1039.5	1038.3	1037.1	1035.8
167.5°	1047.9	1046.5	1045.1	1043.7
170°	1055.0	1053.6	1052.2	1050.8
172.5°	1059.5	1057.9	1056.4	1054.8
175°	1062.9	1061.5	1060.1	1058.7
177.5°	1064.8	1063.0	1061.3	1059.5
180°	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P831879

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.79	14.65	14.69	15.57	16.74	18.45	19.32	19.35	20.23	21.40
	3H	15.01	15.78	15.93	16.71	17.90	19.95	20.73	20.87	21.65	22.84
	4H	15.39	16.13	16.33	17.05	18.26	20.44	21.17	21.38	22.10	23.31
	6H	15.68	16.35	16.62	17.29	18.50	20.76	21.43	21.70	22.37	23.58
	8H	15.77	16.40	16.72	17.36	18.57	20.84	21.48	21.79	22.43	23.64
	12H	15.82	16.43	16.77	17.37	18.61	20.87	21.48	21.82	22.42	23.66
4H	2H	14.51	15.24	15.45	16.17	17.38	18.45	19.18	19.39	20.11	21.31
	3H	15.89	16.49	16.83	17.45	18.67	20.11	20.72	21.06	21.68	22.89
	4H	16.34	16.90	17.30	17.85	19.09	20.72	21.27	21.67	22.23	23.47
	6H	16.71	17.19	17.68	18.17	19.41	21.16	21.63	22.13	22.61	23.85
	8H	16.84	17.28	17.81	18.25	19.51	21.29	21.73	22.26	22.71	23.96
	12H	16.92	17.31	17.90	18.30	19.56	21.35	21.75	22.34	22.74	24.00
8H	4H	16.66	17.10	17.63	18.07	19.33	20.69	21.13	21.66	22.10	23.36
	6H	17.12	17.49	18.12	18.50	19.76	21.19	21.55	22.18	22.57	23.82
	8H	17.32	17.64	18.32	18.64	19.91	21.37	21.69	22.38	22.70	23.97
	12H	17.46	17.74	18.47	18.74	20.06	21.49	21.77	22.50	22.77	24.09
12H	4H	16.67	17.07	17.66	18.06	19.32	20.64	21.04	21.63	22.03	23.29
	6H	17.18	17.51	18.19	18.51	19.78	21.16	21.48	22.16	22.49	23.76
	8H	17.40	17.69	18.41	18.68	20.00	21.36	21.64	22.36	22.63	23.95