

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831908

Luminaire Tested: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831908
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8766.5 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831908

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831908

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57		
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55	50		
2	92	85	79	75	86	80	75	71	69	66	63	60	57	55	51	49	48	43		
3	85	76	69	63	79	71	65	60	62	58	54	54	51	48	46	44	42	38		
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	34		
5	72	61	54	48	67	58	51	46	51	45	41	45	40	37	39	36	33	30		
6	67	55	48	42	62	52	45	40	46	41	37	41	37	33	36	32	30	27		
7	62	51	43	38	58	48	41	36	43	37	33	38	33	30	33	30	27	25		
8	58	46	39	34	54	44	37	33	39	34	30	35	30	27	31	27	25	22		
9	54	43	36	31	51	41	34	30	36	31	27	32	28	25	29	25	23	21		
10	51	40	33	28	48	38	31	27	34	29	25	30	26	23	27	23	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	40739	40739	40739	40739	40739
5°	48372	46830	40995	33140	30767
10°	43827	47566	40791	26552	22778
15°	30175	40783	40360	21702	18018
20°	20992	31400	39550	18299	15837
25°	15997	23931	38371	16264	14596
30°	13926	19132	36896	15101	13520
35°	12786	16139	34807	14121	12540
40°	11665	14412	32073	13159	11643
45°	10535	13181	29125	12248	10749
50°	9562	12161	25648	11355	9640
55°	8649	11168	22308	10483	8270
60°	7750	10155	19375	9522	7817
65°	7154	9011	16677	8558	7391
70°	5813	7789	14552	7742	6008
75°	5099	6197	12327	6421	5290
80°	4618	5244	10098	5387	5002
85°	4211	4594	7669	4891	4594

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 30731 cd/sqm



TEST NUMBER: P831908

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.0	3.9
10°-20°	798.3	9.1
20°-30°	915.9	10.4
30°-40°	902.8	10.3
40°-50°	796.1	9.1
50°-60°	612.5	7.0
60°-70°	402.7	4.6
70°-80°	195.6	2.2
80°-90°	52.1	0.6
90°-100°	270.2	3.1
100°-110°	791.1	9.0
110°-120°	772.6	8.8
120°-130°	615.3	7.0
130°-140°	485.4	5.5
140°-150°	362.1	4.1
150°-160°	252.5	2.9
160°-170°	148.3	1.7
170°-180°	48.2	0.6
0°-30°	2059.1	23.5
0°-40°	2961.9	33.8
0°-60°	4370.5	49.9
0°-90°	5020.8	57.3
90°-120°	1833.9	20.9
90°-150°	3296.7	37.6
90°-180°	3746.0	42.7
0°-180°	8766.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3785	3785	3785	3785	3785	
5°	4477	4334	3794	3067	2848	409
15°	2708	3660	3622	1948	1617	764
25°	1347	2015	3231	1369	1229	636
35°	973	1228	2649	1075	954	607
45°	692	866	1913	805	706	537
55°	461	595	1189	559	441	413
65°	281	354	655	336	290	275
75°	123	149	296	154	127	132
85°	34	37	62	40	37	36
90°	29	25	2	25	29	17
95°	117	598	34	598	117	190
105°	1282	810	117	810	1282	1279
115°	1559	620	207	620	1559	1521
125°	1230	579	287	579	1230	1113
135°	997	570	337	570	997	773
145°	779	564	384	564	779	495
155°	646	545	436	545	646	301
165°	564	522	477	522	564	161
175°	507	501	497	501	507	49
180°	498	498	498	498	498	



TEST NUMBER: P831908

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8
2.5°	4194.4	4181.2	4168.0	4164.2	4160.3	4147.9	4135.5	4107.5	4079.6	4050.9	4022.2
5°	4476.8	4478.4	4479.9	4476.1	4472.2	4455.9	4439.6	4405.5	4371.3	4334.1	4296.8
7.5°	4389.9	4414.8	4439.6	4444.3	4448.9	4461.3	4473.7	4466.0	4458.2	4444.3	4430.3
10°	4009.8	4008.2	4006.7	4034.6	4062.5	4145.5	4228.6	4271.2	4313.9	4351.9	4389.9
12.5°	3389.1	3391.4	3393.7	3485.3	3576.8	3655.2	3733.5	3842.2	3950.8	4067.9	4185.1
15°	2707.8	2745.8	2783.9	2865.3	2946.8	3064.7	3182.7	3328.5	3474.4	3659.8	3845.3
17.5°	2223.7	2240.0	2256.3	2334.6	2413.0	2524.7	2636.4	2801.7	2967.0	3205.9	3444.9
20°	1832.6	1847.4	1862.1	1918.8	1975.4	2082.5	2189.5	2347.0	2504.5	2741.2	2977.8
22.5°	1530.0	1558.7	1587.5	1625.5	1663.5	1741.1	1818.7	1979.3	2139.9	2355.6	2571.3
25°	1346.9	1360.1	1373.3	1405.9	1438.5	1513.0	1587.5	1693.8	1800.0	2015.0	2229.9
27.5°	1222.8	1226.7	1230.5	1254.6	1278.7	1326.8	1374.9	1473.4	1571.9	1748.8	1925.7
30°	1120.4	1127.4	1134.3	1153.0	1171.6	1206.5	1241.4	1311.2	1381.1	1539.3	1697.6
32.5°	1041.2	1045.1	1049.0	1064.5	1080.0	1105.6	1131.2	1186.3	1241.4	1362.4	1483.5
35°	973.0	973.7	974.5	986.1	997.8	1022.6	1047.4	1093.2	1139.0	1228.2	1317.4
37.5°	895.4	900.8	906.2	914.8	923.3	945.0	966.7	1004.0	1041.2	1114.9	1188.7
40°	830.2	834.8	839.5	849.6	859.7	876.7	893.8	928.0	962.1	1025.7	1089.3
42.5°	765.0	768.1	771.2	781.3	791.4	812.3	833.3	860.5	887.6	940.4	993.1
45°	692.1	699.8	707.6	718.5	729.3	747.2	765.0	793.0	820.9	865.9	910.9
47.5°	631.6	635.4	639.3	648.6	657.9	679.7	701.4	726.2	751.1	793.0	834.8
50°	571.0	572.6	574.2	582.7	591.2	610.6	630.0	658.7	687.4	726.2	765.0
52.5°	513.6	517.5	521.4	529.9	538.5	551.7	564.8	594.3	623.8	661.8	699.8
55°	460.9	463.2	465.5	471.7	477.9	493.5	509.0	534.6	560.2	595.1	630.0
57.5°	411.2	414.3	417.4	422.1	426.7	440.7	454.7	477.2	499.7	534.6	569.5
60°	360.0	363.9	367.8	373.2	378.6	389.5	400.4	420.5	440.7	471.7	502.8
62.5°	322.8	323.5	324.3	329.0	333.6	341.4	349.1	365.4	381.7	412.8	443.8
65°	280.9	283.2	285.5	287.9	290.2	296.4	302.6	316.6	330.5	353.8	377.1
67.5°	237.4	239.7	242.1	246.0	249.8	255.3	260.7	270.0	279.3	301.0	322.8
70°	184.7	184.7	184.7	190.9	197.1	206.4	215.7	222.7	229.7	247.5	265.4
72.5°	150.5	151.3	152.1	152.8	153.6	159.1	164.5	176.1	187.8	198.6	209.5
75°	122.6	123.4	124.1	124.9	125.7	127.2	128.8	132.7	136.6	149.0	161.4
77.5°	97.8	98.5	99.3	100.1	100.9	102.4	104.0	105.5	107.1	111.7	116.4
80°	74.5	75.3	76.0	76.8	77.6	78.4	79.1	80.7	82.2	84.6	86.9
82.5°	54.3	54.3	54.3	54.3	54.3	55.9	57.4	57.4	57.4	59.0	60.5
85°	34.1	34.1	34.1	34.9	35.7	35.7	35.7	36.5	37.2	37.2	37.2
87.5°	15.5	14.7	14.0	14.7	15.5	15.5	15.5	16.3	17.1	17.1	17.1
90°	29.2	30.2	29.2	28.2	29.2	27.2	26.2	25.2	24.2	25.2	22.2
92.5°	53.4	55.4	54.4	58.5	60.5	67.5	77.6	99.8	140.1	187.5	207.7
95°	116.9	121.0	128.0	137.1	156.2	192.5	246.0	362.9	484.9	597.8	532.2
97.5°	239.9	251.0	275.2	313.5	381.0	495.9	629.0	833.6	950.6	919.3	686.5
100°	632.0	631.0	670.3	743.9	845.7	988.9	1106.8	1188.5	1153.2	954.6	645.1
102.5°	1001.0	1030.2	1061.5	1115.9	1189.5	1267.1	1323.5	1306.4	1163.3	889.1	584.7
105°	1282.2	1287.3	1319.5	1357.8	1404.2	1430.4	1411.2	1310.4	1099.8	810.5	537.3
107.5°	1465.7	1476.8	1489.9	1508.0	1514.1	1486.8	1408.2	1250.0	1009.0	740.9	503.0
110°	1570.5	1572.5	1574.5	1566.5	1538.2	1467.7	1340.7	1155.2	924.4	683.4	484.9



TEST NUMBER: P831908

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1591.7	1590.7	1580.6	1551.4	1493.9	1398.1	1252.0	1061.5	850.8	645.1	474.8
115°	1559.4	1554.4	1534.2	1489.9	1414.3	1304.4	1156.2	980.8	794.3	619.9	473.8
117.5°	1488.9	1481.8	1451.6	1402.2	1323.5	1209.6	1073.5	918.3	757.0	602.8	474.8
120°	1396.1	1390.1	1365.9	1309.4	1229.8	1128.0	1007.0	870.9	728.8	591.7	478.8
122.5°	1309.4	1301.4	1274.1	1224.8	1156.2	1063.5	953.6	833.6	705.6	584.7	485.9
125°	1229.8	1222.7	1197.5	1153.2	1088.7	1008.0	911.3	801.4	686.5	578.6	492.9
127.5°	1161.2	1155.2	1132.0	1093.7	1035.2	960.6	871.9	772.1	668.3	575.6	501.0
130°	1104.8	1096.7	1075.6	1039.3	985.9	917.3	835.7	744.9	654.2	572.6	509.1
132.5°	1049.4	1044.3	1026.2	989.9	940.5	876.0	801.4	719.7	641.1	571.6	515.1
135°	996.9	989.9	971.7	941.5	892.1	834.6	769.1	697.6	630.0	570.5	521.1
137.5°	941.5	935.4	920.3	889.1	846.7	795.3	736.9	676.4	619.9	568.5	525.2
140°	883.0	884.0	867.9	839.7	801.4	758.0	709.7	658.2	610.9	567.5	529.2
142.5°	828.6	829.6	815.5	791.3	760.1	723.8	683.4	641.1	602.8	565.5	532.2
145°	779.2	777.2	769.1	748.0	722.8	693.5	661.3	628.0	595.7	563.5	533.2
147.5°	736.9	735.9	727.8	712.7	692.5	671.3	644.1	616.9	588.7	560.5	533.2
150°	700.6	700.6	694.5	683.4	668.3	649.2	628.0	604.8	581.6	556.4	533.2
152.5°	670.3	670.3	667.3	657.2	646.1	631.0	612.9	593.7	573.6	551.4	530.2
155°	646.1	645.1	643.1	635.1	626.0	613.9	598.8	582.6	565.5	545.3	528.2
157.5°	623.0	623.0	620.9	614.9	606.8	596.8	584.7	570.5	556.4	540.3	525.2
160°	600.8	601.8	601.8	595.7	588.7	581.6	571.6	560.5	547.4	534.3	523.2
162.5°	580.6	581.6	581.6	576.6	572.6	566.5	557.4	548.4	538.3	528.2	519.1
165°	563.5	563.5	564.5	560.5	556.4	551.4	544.3	538.3	530.2	522.2	515.1
167.5°	546.4	546.4	547.4	544.3	542.3	538.3	534.3	529.2	522.2	516.1	511.1
170°	531.2	531.2	532.2	530.2	529.2	527.2	523.2	520.1	515.1	510.1	507.0
172.5°	517.1	518.1	520.1	518.1	518.1	517.1	514.1	512.1	508.0	505.0	504.0
175°	507.0	508.0	509.1	508.0	508.0	508.0	506.0	505.0	503.0	501.0	501.0
177.5°	500.0	500.0	502.0	501.0	502.0	502.0	501.0	500.0	499.0	498.0	499.0
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P831908

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8
2.5°	4018.3	4014.4	3977.2	3939.9	3903.5	3867.0	3839.8	3812.7	3766.9	3721.1	3692.4
5°	4267.4	4237.9	4178.9	4119.9	4031.5	3943.0	3868.5	3794.1	3699.4	3604.7	3525.6
7.5°	4406.2	4382.2	4310.8	4239.4	4122.3	4005.1	3888.7	3772.3	3632.7	3493.0	3373.5
10°	4410.1	4430.3	4371.3	4312.4	4180.5	4048.6	3890.3	3732.0	3544.2	3356.5	3202.1
12.5°	4272.0	4358.9	4346.5	4334.1	4199.8	4065.6	3873.2	3680.8	3450.3	3219.9	3026.7
15°	4013.6	4182.0	4231.7	4281.3	4170.4	4059.4	3840.6	3621.8	3351.0	3080.3	2858.3
17.5°	3680.8	3916.7	4047.8	4178.9	4098.2	4017.5	3777.8	3538.0	3233.1	2928.2	2686.9
20°	3286.6	3595.4	3801.0	4006.7	3977.2	3947.7	3700.2	3452.7	3123.7	2794.7	2533.3
22.5°	2897.1	3223.0	3507.0	3791.0	3821.2	3851.5	3601.6	3351.8	2991.8	2631.8	2365.7
25°	2561.2	2892.5	3230.8	3569.1	3637.3	3705.6	3468.2	3230.8	2857.6	2484.4	2219.8
27.5°	2240.7	2555.8	2928.2	3300.6	3424.7	3548.9	3331.6	3114.4	2725.7	2337.0	2073.2
30°	1979.3	2260.9	2641.1	3021.3	3194.3	3367.3	3167.9	2968.5	2582.9	2197.3	1938.9
32.5°	1735.6	1987.8	2369.5	2751.3	2952.2	3153.2	2980.9	2808.7	2437.8	2066.9	1811.7
35°	1543.2	1769.0	2125.1	2481.3	2706.3	2931.3	2790.1	2648.9	2286.5	1924.2	1682.9
37.5°	1378.0	1567.3	1901.7	2236.1	2475.1	2714.0	2596.1	2478.2	2137.6	1796.9	1568.8
40°	1241.4	1393.5	1704.6	2015.7	2250.1	2484.4	2383.5	2282.6	1977.7	1672.8	1459.4
42.5°	1124.3	1255.4	1534.7	1814.0	2028.9	2243.9	2177.1	2110.4	1834.2	1558.0	1360.1
45°	1021.1	1131.2	1377.2	1623.1	1821.0	2018.8	1966.1	1913.3	1675.1	1436.9	1255.4
47.5°	929.5	1024.2	1243.7	1463.3	1641.0	1818.7	1769.8	1720.9	1523.8	1326.8	1161.5
50°	845.7	926.4	1109.5	1292.6	1452.5	1612.3	1571.9	1531.6	1368.7	1205.7	1063.0
52.5°	766.6	833.3	997.8	1162.3	1291.1	1419.9	1388.8	1357.8	1232.1	1106.4	976.8
55°	691.3	752.6	891.5	1030.4	1140.5	1250.7	1219.7	1188.7	1090.9	993.1	879.1
57.5°	623.0	676.6	789.1	901.6	989.2	1076.9	1062.2	1047.4	966.0	884.5	790.6
60°	550.9	599.0	696.0	793.0	863.6	934.2	917.1	900.0	841.8	783.6	702.9
62.5°	486.5	529.2	606.7	684.3	741.7	799.2	786.7	774.3	730.1	685.9	619.2
65°	419.0	460.9	523.7	586.6	631.6	676.6	665.7	654.8	621.5	588.1	534.6
67.5°	357.7	392.6	446.9	501.2	531.5	561.7	555.5	549.3	523.7	498.1	456.2
70°	295.6	325.9	370.9	415.9	436.8	457.8	460.1	462.4	439.1	415.9	384.8
72.5°	233.5	257.6	299.5	341.4	357.7	374.0	373.2	372.4	358.5	344.5	316.6
75°	179.2	197.1	229.7	262.2	276.2	290.2	293.3	296.4	283.2	270.0	254.5
77.5°	128.8	141.2	166.0	190.9	206.4	221.9	223.5	225.0	218.8	212.6	197.8
80°	90.8	94.7	110.2	125.7	142.0	158.3	160.6	162.9	156.7	150.5	141.2
82.5°	62.8	65.2	70.6	76.0	89.2	102.4	105.5	108.6	105.5	102.4	92.3
85°	38.0	38.8	41.1	43.4	49.7	55.9	59.0	62.1	60.5	59.0	53.5
87.5°	17.1	17.1	17.8	18.6	20.2	21.7	25.6	29.5	27.2	24.8	22.5
90°	19.2	16.1	13.1	11.1	9.1	6.0	4.0	2.0	4.0	6.0	9.1
92.5°	155.2	101.8	69.6	51.4	41.3	32.3	22.2	15.1	22.2	32.3	41.3
95°	366.9	216.7	131.0	91.7	65.5	48.4	37.3	34.3	37.3	48.4	65.5
97.5°	408.3	233.9	149.2	105.8	79.6	64.5	55.4	54.4	55.4	64.5	79.6
100°	380.0	230.8	160.3	121.0	96.8	82.7	75.6	74.6	75.6	82.7	96.8
102.5°	355.8	234.9	173.4	138.1	116.9	103.8	97.8	95.8	97.8	103.8	116.9
105°	346.8	242.9	188.5	157.3	138.1	126.0	120.0	116.9	120.0	126.0	138.1
107.5°	344.7	256.0	207.7	178.4	160.3	148.2	142.1	139.1	142.1	148.2	160.3
110°	349.8	273.2	227.8	199.6	182.5	171.4	166.3	163.3	166.3	171.4	182.5



TEST NUMBER: P831908

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	359.9	290.3	249.0	221.8	204.6	193.5	188.5	185.5	188.5	193.5	204.6
115°	371.0	309.5	271.2	243.9	226.8	216.7	210.7	206.6	210.7	216.7	226.8
117.5°	385.1	329.6	291.3	266.1	247.0	237.9	232.9	227.8	232.9	237.9	247.0
120°	401.2	348.8	312.5	287.3	268.1	258.1	253.0	250.0	253.0	258.1	268.1
122.5°	416.3	368.9	333.7	306.4	288.3	277.2	272.2	269.1	272.2	277.2	288.3
125°	432.4	388.1	352.8	325.6	306.4	295.4	289.3	287.3	289.3	295.4	306.4
127.5°	445.5	405.2	371.0	343.7	322.6	311.5	304.4	301.4	304.4	311.5	322.6
130°	458.7	420.3	387.1	359.9	338.7	326.6	317.5	314.5	317.5	326.6	338.7
132.5°	470.7	433.5	401.2	375.0	353.8	338.7	328.6	324.6	328.6	338.7	353.8
135°	480.8	446.6	415.3	388.1	366.9	351.8	340.7	336.7	340.7	351.8	366.9
137.5°	488.9	455.6	425.4	400.2	379.0	362.9	351.8	347.8	351.8	362.9	379.0
140°	494.9	464.7	435.5	410.3	390.1	374.0	363.9	358.9	363.9	374.0	390.1
142.5°	501.0	471.8	443.5	420.3	400.2	386.1	375.0	371.0	375.0	386.1	400.2
145°	505.0	477.8	451.6	428.4	411.3	396.2	387.1	384.1	387.1	396.2	411.3
147.5°	508.0	482.8	458.7	438.5	421.4	408.3	399.2	397.2	399.2	408.3	421.4
150°	509.1	487.9	464.7	446.6	432.4	419.3	411.3	410.3	411.3	419.3	432.4
152.5°	511.1	490.9	471.8	454.6	442.5	431.4	423.4	423.4	423.4	431.4	442.5
155°	511.1	494.9	477.8	463.7	452.6	442.5	436.5	436.5	436.5	442.5	452.6
157.5°	512.1	497.0	482.8	471.8	461.7	452.6	447.6	446.6	447.6	452.6	461.7
160°	512.1	500.0	487.9	477.8	470.7	462.7	458.7	458.7	458.7	462.7	470.7
162.5°	511.1	501.0	490.9	482.8	476.8	470.7	467.7	467.7	467.7	470.7	476.8
165°	509.1	502.0	493.9	486.9	482.8	477.8	475.8	476.8	475.8	477.8	482.8
167.5°	508.0	502.0	495.9	490.9	487.9	483.9	482.8	483.9	482.8	483.9	487.9
170°	505.0	501.0	495.9	493.9	491.9	488.9	487.9	489.9	487.9	488.9	491.9
172.5°	504.0	501.0	497.0	495.9	494.9	492.9	492.9	493.9	492.9	492.9	494.9
175°	502.0	500.0	498.0	497.0	497.0	494.9	495.9	497.0	495.9	494.9	497.0
177.5°	501.0	499.0	498.0	498.0	498.0	497.0	498.0	499.0	498.0	497.0	498.0
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P831908

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8
2.5°	3663.7	3619.5	3575.3	3543.5	3511.6	3472.1	3432.5	3431.0	3429.4	3399.9	3370.4
5°	3446.5	3369.7	3292.8	3217.6	3142.3	3067.1	2991.8	2974.7	2957.7	2932.1	2906.5
7.5°	3254.0	3131.5	3008.9	2912.7	2816.5	2741.2	2665.9	2614.7	2563.5	2523.9	2484.4
10°	3047.7	2895.6	2743.5	2627.1	2510.8	2429.3	2347.8	2288.9	2229.9	2202.0	2174.0
12.5°	2833.5	2668.3	2503.0	2388.9	2274.9	2177.1	2079.4	2025.8	1972.3	1933.5	1894.7
15°	2636.4	2458.8	2281.1	2160.1	2039.0	1947.5	1855.9	1802.4	1748.8	1710.0	1671.2
17.5°	2445.6	2266.4	2087.1	1964.5	1841.9	1758.9	1675.9	1623.9	1571.9	1547.9	1523.8
20°	2271.8	2091.0	1910.2	1794.6	1679.0	1597.5	1516.1	1488.1	1460.2	1437.7	1415.2
22.5°	2099.5	1925.7	1751.9	1641.0	1530.0	1471.1	1412.1	1389.6	1367.1	1350.0	1333.0
25°	1955.2	1782.2	1609.2	1512.2	1415.2	1369.4	1323.7	1308.9	1294.2	1277.1	1260.0
27.5°	1809.4	1644.9	1480.4	1402.8	1325.2	1288.0	1250.7	1232.1	1213.5	1199.5	1185.5
30°	1680.6	1528.5	1376.4	1312.0	1247.6	1215.0	1182.4	1162.3	1142.1	1128.9	1115.7
32.5°	1556.4	1421.4	1286.4	1231.3	1176.2	1144.4	1112.6	1093.2	1073.8	1058.3	1042.8
35°	1441.6	1324.4	1207.3	1156.8	1106.4	1074.6	1042.8	1023.4	1004.0	988.5	973.0
37.5°	1340.7	1234.4	1128.1	1080.8	1033.5	1005.5	977.6	957.4	937.3	921.0	904.7
40°	1246.1	1152.2	1058.3	1012.5	966.7	936.5	906.2	888.4	870.5	855.8	841.1
42.5°	1162.3	1076.1	990.0	945.0	900.0	871.3	842.6	821.7	800.7	792.2	783.6
45°	1073.8	997.8	921.7	878.3	834.8	804.6	774.3	756.5	738.6	730.9	723.1
47.5°	996.2	925.6	855.0	812.3	769.7	742.5	715.4	701.4	687.4	676.6	665.7
50°	920.2	851.9	783.6	742.5	701.4	678.1	654.8	637.8	620.7	612.9	605.2
52.5°	847.3	785.2	723.1	681.2	639.3	616.8	594.3	579.6	564.8	548.5	532.3
55°	765.0	710.7	656.4	619.2	581.9	558.6	535.4	518.3	501.2	484.2	467.1
57.5°	696.7	643.2	589.7	556.3	522.9	500.4	477.9	459.3	440.7	426.7	412.8
60°	622.3	575.7	529.2	496.6	464.0	442.3	420.5	402.7	384.8	377.9	370.9
62.5°	552.4	509.0	465.5	436.8	408.1	387.2	366.2	354.6	342.9	338.3	333.6
65°	481.0	443.8	406.6	380.2	353.8	336.0	318.1	312.7	307.2	303.4	299.5
67.5°	414.3	382.5	350.7	327.4	304.1	291.7	279.3	273.1	266.9	262.2	257.6
70°	353.8	325.9	297.9	277.8	257.6	246.0	234.3	228.9	223.5	214.9	206.4
72.5°	288.6	266.9	245.2	229.7	214.1	204.1	194.0	183.1	172.2	164.5	156.7
75°	239.0	217.2	195.5	180.8	166.0	154.4	142.8	138.9	135.0	132.7	130.3
77.5°	183.1	164.5	145.9	134.2	122.6	117.2	111.7	109.4	107.1	106.3	105.5
80°	131.9	116.4	100.9	94.7	88.5	86.9	85.3	83.8	82.2	81.5	80.7
82.5°	82.2	74.5	66.7	65.2	63.6	62.8	62.1	61.3	60.5	59.7	59.0
85°	48.1	45.0	41.9	41.1	40.3	39.6	38.8	38.8	38.8	38.8	38.8
87.5°	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2	19.4	18.6
90°	11.1	13.1	16.1	19.2	22.2	25.2	24.2	25.2	26.2	27.2	29.2
92.5°	51.4	69.6	101.8	155.2	207.7	187.5	140.1	99.8	77.6	67.5	60.5
95°	91.7	131.0	216.7	366.9	532.2	597.8	484.9	362.9	246.0	192.5	156.2
97.5°	105.8	149.2	233.9	408.3	686.5	919.3	950.6	833.6	629.0	495.9	381.0
100°	121.0	160.3	230.8	380.0	645.1	954.6	1153.2	1188.5	1106.8	988.9	845.7
102.5°	138.1	173.4	234.9	355.8	584.7	889.1	1163.3	1306.4	1323.5	1267.1	1189.5
105°	157.3	188.5	242.9	346.8	537.3	810.5	1099.8	1310.4	1411.2	1430.4	1404.2
107.5°	178.4	207.7	256.0	344.7	503.0	740.9	1009.0	1250.0	1408.2	1486.8	1514.1
110°	199.6	227.8	273.2	349.8	484.9	683.4	924.4	1155.2	1340.7	1467.7	1538.2



TEST NUMBER: P831908

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	221.8	249.0	290.3	359.9	474.8	645.1	850.8	1061.5	1252.0	1398.1	1493.9
115°	243.9	271.2	309.5	371.0	473.8	619.9	794.3	980.8	1156.2	1304.4	1414.3
117.5°	266.1	291.3	329.6	385.1	474.8	602.8	757.0	918.3	1073.5	1209.6	1323.5
120°	287.3	312.5	348.8	401.2	478.8	591.7	728.8	870.9	1007.0	1128.0	1229.8
122.5°	306.4	333.7	368.9	416.3	485.9	584.7	705.6	833.6	953.6	1063.5	1156.2
125°	325.6	352.8	388.1	432.4	492.9	578.6	686.5	801.4	911.3	1008.0	1088.7
127.5°	343.7	371.0	405.2	445.5	501.0	575.6	668.3	772.1	871.9	960.6	1035.2
130°	359.9	387.1	420.3	458.7	509.1	572.6	654.2	744.9	835.7	917.3	985.9
132.5°	375.0	401.2	433.5	470.7	515.1	571.6	641.1	719.7	801.4	876.0	940.5
135°	388.1	415.3	446.6	480.8	521.1	570.5	630.0	697.6	769.1	834.6	892.1
137.5°	400.2	425.4	455.6	488.9	525.2	568.5	619.9	676.4	736.9	795.3	846.7
140°	410.3	435.5	464.7	494.9	529.2	567.5	610.9	658.2	709.7	758.0	801.4
142.5°	420.3	443.5	471.8	501.0	532.2	565.5	602.8	641.1	683.4	723.8	760.1
145°	428.4	451.6	477.8	505.0	533.2	563.5	595.7	628.0	661.3	693.5	722.8
147.5°	438.5	458.7	482.8	508.0	533.2	560.5	588.7	616.9	644.1	671.3	692.5
150°	446.6	464.7	487.9	509.1	533.2	556.4	581.6	604.8	628.0	649.2	668.3
152.5°	454.6	471.8	490.9	511.1	530.2	551.4	573.6	593.7	612.9	631.0	646.1
155°	463.7	477.8	494.9	511.1	528.2	545.3	565.5	582.6	598.8	613.9	626.0
157.5°	471.8	482.8	497.0	512.1	525.2	540.3	556.4	570.5	584.7	596.8	606.8
160°	477.8	487.9	500.0	512.1	523.2	534.3	547.4	560.5	571.6	581.6	588.7
162.5°	482.8	490.9	501.0	511.1	519.1	528.2	538.3	548.4	557.4	566.5	572.6
165°	486.9	493.9	502.0	509.1	515.1	522.2	530.2	538.3	544.3	551.4	556.4
167.5°	490.9	495.9	502.0	508.0	511.1	516.1	522.2	529.2	534.3	538.3	542.3
170°	493.9	495.9	501.0	505.0	507.0	510.1	515.1	520.1	523.2	527.2	529.2
172.5°	495.9	497.0	501.0	504.0	504.0	505.0	508.0	512.1	514.1	517.1	518.1
175°	497.0	498.0	500.0	502.0	501.0	501.0	503.0	505.0	506.0	508.0	508.0
177.5°	498.0	498.0	499.0	501.0	499.0	498.0	499.0	500.0	501.0	502.0	502.0
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0

TEST NUMBER: P831908

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3784.8	3784.8	3784.8	3784.8
2.5°	3362.7	3354.9	3351.8	3348.7
5°	2882.4	2858.3	2852.9	2847.5
7.5°	2474.3	2464.2	2430.8	2397.5
10°	2143.0	2112.0	2098.0	2084.0
12.5°	1866.0	1837.3	1832.6	1828.0
15°	1651.1	1630.9	1623.9	1616.9
17.5°	1509.9	1495.9	1487.4	1478.8
20°	1405.1	1395.0	1388.8	1382.6
22.5°	1325.2	1317.4	1312.8	1308.1
25°	1248.4	1236.8	1232.9	1229.0
27.5°	1175.5	1165.4	1161.5	1157.6
30°	1107.2	1098.6	1093.2	1087.8
32.5°	1032.7	1022.6	1019.5	1016.4
35°	966.7	960.5	957.4	954.3
37.5°	896.9	889.2	884.5	879.9
40°	837.2	833.3	831.0	828.6
42.5°	776.7	769.7	768.9	768.1
45°	716.1	709.2	707.6	706.1
47.5°	659.5	653.3	652.5	651.7
50°	596.7	588.1	581.9	575.7
52.5°	524.5	516.7	511.3	505.9
55°	458.5	450.0	445.4	440.7
57.5°	408.9	405.0	402.7	400.4
60°	368.5	366.2	364.7	363.1
62.5°	331.3	329.0	329.0	329.0
65°	297.2	294.8	292.5	290.2
67.5°	252.9	248.3	247.5	246.7
70°	199.4	192.4	191.6	190.9
72.5°	156.0	155.2	153.6	152.1
75°	128.8	127.2	127.2	127.2
77.5°	104.0	102.4	102.4	102.4
80°	79.9	79.1	79.9	80.7
82.5°	59.0	59.0	58.2	57.4
85°	38.0	37.2	37.2	37.2
87.5°	18.6	18.6	18.6	18.6
90°	28.2	29.2	30.2	29.2
92.5°	58.5	54.4	55.4	53.4
95°	137.1	128.0	121.0	116.9
97.5°	313.5	275.2	251.0	239.9
100°	743.9	670.3	631.0	632.0
102.5°	1115.9	1061.5	1030.2	1001.0
105°	1357.8	1319.5	1287.3	1282.2
107.5°	1508.0	1489.9	1476.8	1465.7
110°	1566.5	1574.5	1572.5	1570.5



TEST NUMBER: P831908

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1551.4	1580.6	1590.7	1591.7
115°	1489.9	1534.2	1554.4	1559.4
117.5°	1402.2	1451.6	1481.8	1488.9
120°	1309.4	1365.9	1390.1	1396.1
122.5°	1224.8	1274.1	1301.4	1309.4
125°	1153.2	1197.5	1222.7	1229.8
127.5°	1093.7	1132.0	1155.2	1161.2
130°	1039.3	1075.6	1096.7	1104.8
132.5°	989.9	1026.2	1044.3	1049.4
135°	941.5	971.7	989.9	996.9
137.5°	889.1	920.3	935.4	941.5
140°	839.7	867.9	884.0	883.0
142.5°	791.3	815.5	829.6	828.6
145°	748.0	769.1	777.2	779.2
147.5°	712.7	727.8	735.9	736.9
150°	683.4	694.5	700.6	700.6
152.5°	657.2	667.3	670.3	670.3
155°	635.1	643.1	645.1	646.1
157.5°	614.9	620.9	623.0	623.0
160°	595.7	601.8	601.8	600.8
162.5°	576.6	581.6	581.6	580.6
165°	560.5	564.5	563.5	563.5
167.5°	544.3	547.4	546.4	546.4
170°	530.2	532.2	531.2	531.2
172.5°	518.1	520.1	518.1	517.1
175°	508.0	509.1	508.0	507.0
177.5°	501.0	502.0	500.0	500.0
180°	498.0	498.0	498.0	498.0



TEST NUMBER: P831908

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.28	15.15	15.19	16.07	17.23	18.95	19.81	19.85	20.73	21.90
	3H	15.51	16.28	16.43	17.21	18.40	20.45	21.22	21.37	22.15	23.34
	4H	15.89	16.62	16.82	17.55	18.76	20.94	21.67	21.87	22.60	23.81
	6H	16.18	16.85	17.12	17.78	19.00	21.26	21.93	22.20	22.86	24.08
	8H	16.26	16.90	17.21	17.85	19.07	21.34	21.97	22.29	22.93	24.14
	12H	16.32	16.92	17.27	17.87	19.11	21.37	21.98	22.32	22.92	24.16
4H	2H	15.01	15.74	15.95	16.67	17.88	18.95	19.68	19.89	20.61	21.81
	3H	16.38	16.99	17.33	17.95	19.17	20.61	21.22	21.56	22.18	23.39
	4H	16.84	17.39	17.80	18.35	19.59	21.22	21.77	22.17	22.72	23.97
	6H	17.21	17.69	18.18	18.66	19.91	21.66	22.13	22.63	23.11	24.35
	8H	17.34	17.78	18.31	18.75	20.01	21.79	22.23	22.76	23.20	24.46
	12H	17.41	17.81	18.40	18.80	20.06	21.85	22.25	22.84	23.24	24.50
8H	4H	17.16	17.60	18.13	18.57	19.83	21.19	21.63	22.16	22.60	23.86
	6H	17.62	17.99	18.62	19.00	20.26	21.68	22.05	22.68	23.06	24.32
	8H	17.82	18.14	18.82	19.14	20.41	21.87	22.19	22.87	23.19	24.47
	12H	17.96	18.24	18.96	19.24	20.55	21.99	22.27	22.99	23.27	24.59
12H	4H	17.17	17.57	18.16	18.56	19.82	21.14	21.54	22.13	22.53	23.79
	6H	17.68	18.00	18.69	19.01	20.28	21.66	21.98	22.66	22.98	24.26
	8H	17.90	18.18	18.91	19.18	20.50	21.85	22.14	22.86	23.13	24.45