

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332262

Luminaire Tested: **S123RDIP-S340D1025U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332262
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1025U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4822.4 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332262

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332262

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	28	26	25	20
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13
6	60	48	40	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	14	13	10
8	51	39	32	27	45	35	29	25	28	24	20	22	18	16	15	13	12	9
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	10	8
10	44	33	26	21	39	30	24	19	24	19	16	18	15	13	13	11	10	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6184	6184	6184
5°	6207	6122	6158
10°	6172	6045	6025
15°	6107	5904	5841
20°	6015	5727	5593
25°	5922	5529	5352
30°	5797	5299	5009
35°	5670	5070	4696
40°	5552	4799	4308
45°	5398	4532	3958
50°	5228	4228	3565
55°	5054	3883	3200
60°	4895	3511	2799
65°	4689	3110	2397
70°	4428	2609	1936
75°	4051	2054	1822
80°	3608	1822	1674
85°	3051	1606	1494



TEST NUMBER: P332262

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	1.1
10°-20°	150.1	3.1
20°-30°	216.1	4.5
30°-40°	243.5	5.0
40°-50°	232.9	4.8
50°-60°	190.7	4.0
60°-70°	128.7	2.7
70°-80°	64.7	1.3
80°-90°	20.9	0.4
90°-100°	82.8	1.7
100°-110°	247.8	5.1
110°-120°	421.4	8.7
120°-130°	554.3	11.5
130°-140°	623.0	12.9
140°-150°	612.4	12.7
150°-160°	515.6	10.7
160°-170°	343.2	7.1
170°-180°	120.2	2.5
0°-30°	420.2	8.7
0°-40°	663.7	13.8
0°-60°	1087.3	22.5
0°-90°	1301.6	27.0
90°-120°	752.0	15.6
90°-150°	2541.8	52.7
90°-180°	3521.0	73.0
0°-180°	4822.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	574	574	574	574	574	
5°	574	572	567	570	570	54
15°	548	542	530	527	524	154
25°	499	486	466	456	451	229
35°	432	414	386	366	357	270
45°	355	333	298	272	260	273
55°	269	246	207	181	170	241
65°	184	158	122	100	94	182
75°	97	75	49	45	44	104
85°	25	15	13	12	12	28
90°	1	11	24	28	30	5
95°	59	66	74	78	78	66
105°	225	227	236	236	238	241
115°	424	427	425	426	425	420
125°	621	624	622	618	614	553
135°	806	811	810	807	805	621
145°	977	979	982	981	977	610
155°	1119	1119	1120	1123	1117	515
165°	1219	1216	1216	1221	1215	344
175°	1268	1264	1264	1269	1263	120
180°	1271	1271	1271	1271	1271	



TEST NUMBER: P332262

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	576.4	576.0	575.7	575.4	575.1	574.4	573.4	572.4	571.4	570.4	571.3
5°	574.5	574.0	573.5	573.0	572.4	571.6	570.3	569.1	567.8	566.6	567.5
7.5°	569.2	568.6	568.1	567.5	567.0	565.9	564.3	562.7	561.0	559.4	559.9
10°	564.7	564.0	563.3	562.6	561.8	560.5	558.7	556.8	554.9	553.1	553.2
12.5°	558.4	557.6	556.8	556.0	555.2	553.6	551.3	549.1	546.8	544.5	544.4
15°	548.0	546.8	545.7	544.5	543.4	541.4	538.5	535.6	532.7	529.8	529.3
17.5°	534.8	533.5	532.2	530.8	529.5	527.0	523.3	519.6	516.0	512.3	511.2
20°	525.1	523.5	521.8	520.2	518.5	515.7	511.8	507.8	503.9	500.0	498.6
22.5°	514.3	512.4	510.5	508.6	506.7	503.7	499.5	495.3	491.1	486.9	485.2
25°	498.6	496.0	493.4	490.8	488.2	484.5	479.8	475.0	470.2	465.5	463.3
27.5°	479.5	476.6	473.7	470.9	468.0	464.0	458.7	453.3	448.0	442.7	439.7
30°	466.4	463.3	460.2	457.1	454.0	449.5	443.7	437.9	432.1	426.3	422.8
32.5°	453.4	449.8	446.3	442.8	439.3	434.5	428.3	422.2	416.1	409.9	406.1
35°	431.5	427.7	424.0	420.3	416.6	411.5	405.1	398.6	392.2	385.8	381.4
37.5°	409.3	405.1	401.0	396.9	392.7	387.2	380.4	373.5	366.7	359.8	354.8
40°	395.1	390.6	386.0	381.5	376.9	370.9	363.6	356.2	348.9	341.5	336.2
42.5°	379.1	374.5	370.0	365.4	360.9	354.8	347.2	339.6	332.0	324.4	318.5
45°	354.6	349.9	345.3	340.6	335.9	329.6	321.7	313.7	305.7	297.7	291.8
47.5°	330.1	325.0	319.8	314.7	309.6	303.1	295.1	287.1	279.2	271.2	264.8
50°	312.2	307.3	302.5	297.6	292.7	286.1	277.7	269.3	260.9	252.5	246.1
52.5°	296.2	290.9	285.6	280.3	275.0	268.2	259.9	251.6	243.3	235.0	228.4
55°	269.3	264.2	259.2	254.1	249.0	242.1	233.3	224.5	215.7	206.9	200.9
57.5°	244.5	239.0	233.5	227.9	222.4	215.2	206.4	197.5	188.7	179.9	174.2
60°	227.4	221.7	216.0	210.3	204.6	197.5	188.9	180.3	171.7	163.1	157.5
62.5°	210.2	204.5	198.8	193.2	187.5	180.3	171.7	163.1	154.5	145.9	140.7
65°	184.1	178.4	172.7	167.0	161.3	154.4	146.3	138.2	130.2	122.1	117.0
67.5°	157.9	152.1	146.3	140.6	134.8	128.1	120.3	112.6	104.8	97.1	93.3
70°	140.7	135.1	129.5	123.9	118.4	111.9	104.7	97.4	90.2	82.9	79.3
72.5°	123.6	118.1	112.6	107.0	101.5	95.5	88.9	82.3	75.7	69.1	66.2
75°	97.4	92.4	87.4	82.5	77.5	72.2	66.5	60.8	55.1	49.4	48.4
77.5°	73.5	69.0	64.5	60.0	55.6	51.5	47.8	44.1	40.5	36.8	36.3
80°	58.2	54.0	49.8	45.5	41.3	38.1	35.9	33.7	31.5	29.4	29.0
82.5°	43.7	40.0	36.4	32.7	29.0	26.7	25.7	24.7	23.7	22.6	22.3
85°	24.7	22.4	20.1	17.9	15.6	14.3	14.0	13.7	13.4	13.0	12.8
87.5°	9.1	8.7	8.2	7.7	7.3	7.3	7.9	8.5	9.1	9.6	9.7
90°	1.0	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8
92.5°	24.2	25.7	27.2	28.7	30.2	31.8	33.4	35.0	36.7	38.3	39.0
95°	58.9	60.4	62.0	63.6	65.1	66.8	68.5	70.3	72.1	73.9	74.8
97.5°	104.6	105.8	106.9	108.1	109.2	110.4	111.7	113.0	114.3	115.6	116.6
100°	135.8	137.1	138.4	139.7	141.1	142.3	143.4	144.5	145.6	146.7	147.4
102.5°	171.7	172.5	173.3	174.1	174.9	176.0	177.5	178.9	180.4	181.9	182.5
105°	224.6	225.0	225.5	225.9	226.4	227.6	229.6	231.6	233.6	235.6	235.6
107.5°	286.1	286.4	286.6	286.9	287.2	287.7	288.5	289.3	290.1	290.9	291.6
110°	324.4	324.9	325.3	325.7	326.2	326.6	327.1	327.5	328.0	328.4	329.3



TEST NUMBER: P332262

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	364.3	364.6	364.9	365.1	365.4	365.6	365.7	365.8	365.9	365.9	367.0
115°	424.2	424.9	425.6	426.2	426.9	427.0	426.6	426.1	425.7	425.2	425.5
117.5°	484.5	485.0	485.4	485.9	486.3	486.2	485.7	485.1	484.5	483.9	483.9
120°	522.1	523.4	524.7	526.1	527.4	527.5	526.4	525.3	524.2	523.1	522.8
122.5°	561.2	562.2	563.1	564.1	565.1	565.3	564.7	564.1	563.6	563.0	562.4
125°	620.9	621.6	622.2	622.9	623.5	623.7	623.2	622.8	622.3	621.9	621.0
127.5°	676.0	677.4	678.8	680.2	681.7	682.1	681.6	681.2	680.7	680.2	678.9
130°	712.7	714.5	716.3	718.0	719.8	720.4	719.7	719.0	718.4	717.7	716.8
132.5°	749.5	751.2	753.0	754.8	756.6	757.2	756.7	756.2	755.7	755.2	754.2
135°	805.6	806.9	808.2	809.5	810.9	811.4	811.2	811.0	810.8	810.5	809.7
137.5°	857.5	858.6	859.7	860.8	861.9	862.7	863.3	863.9	864.5	865.0	864.1
140°	893.4	894.5	895.6	896.7	897.8	898.5	898.7	898.9	899.2	899.4	899.2
142.5°	926.1	927.2	928.4	929.5	930.6	931.3	931.7	932.1	932.5	932.9	932.7
145°	977.2	977.7	978.1	978.6	979.0	979.6	980.2	980.9	981.6	982.2	982.0
147.5°	1022.0	1022.8	1023.6	1024.4	1025.2	1025.9	1026.5	1027.1	1027.7	1028.4	1028.4
150°	1053.1	1053.6	1054.0	1054.4	1054.9	1055.3	1055.8	1056.2	1056.7	1057.1	1057.1
152.5°	1078.7	1079.3	1079.9	1080.5	1081.1	1081.6	1081.9	1082.1	1082.4	1082.7	1083.0
155°	1119.0	1119.0	1119.0	1119.0	1119.0	1119.1	1119.3	1119.5	1119.8	1120.0	1120.9
157.5°	1153.3	1153.1	1152.8	1152.5	1152.3	1152.2	1152.4	1152.6	1152.8	1152.9	1153.9
160°	1174.9	1174.4	1174.0	1173.6	1173.1	1172.9	1172.9	1172.9	1172.9	1172.9	1174.0
162.5°	1194.1	1193.4	1192.8	1192.2	1191.6	1191.4	1191.5	1191.7	1191.9	1192.1	1193.2
165°	1218.8	1218.1	1217.5	1216.8	1216.2	1215.8	1215.8	1215.8	1215.8	1215.8	1217.1
167.5°	1238.6	1237.7	1236.8	1235.9	1235.0	1234.7	1234.9	1235.0	1235.2	1235.4	1236.8
170°	1249.8	1248.9	1248.0	1247.1	1246.2	1245.8	1245.8	1245.8	1245.8	1245.8	1247.3
172.5°	1258.5	1257.7	1256.8	1255.9	1255.0	1254.5	1254.5	1254.5	1254.5	1254.5	1255.9
175°	1267.7	1266.8	1265.9	1265.1	1264.2	1263.7	1263.7	1263.7	1263.7	1263.7	1265.1
177.5°	1271.5	1270.8	1270.1	1269.4	1268.7	1268.3	1268.3	1268.3	1268.3	1268.3	1269.4
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P332262

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	572.2	573.1	574.1	574.4	574.3	574.1	573.9	573.8
5°	568.5	569.4	570.3	570.7	570.5	570.3	570.1	569.9
7.5°	560.5	561.0	561.5	561.6	561.2	560.9	560.5	560.2
10°	553.3	553.4	553.5	553.3	552.8	552.3	551.7	551.2
12.5°	544.4	544.3	544.3	543.9	543.3	542.7	542.1	541.5
15°	528.7	528.2	527.7	527.1	526.4	525.6	524.9	524.2
17.5°	510.1	509.0	507.9	506.8	505.7	504.6	503.6	502.5
20°	497.3	495.9	494.6	493.3	492.0	490.8	489.6	488.3
22.5°	483.6	481.9	480.2	478.8	477.6	476.5	475.3	474.2
25°	461.1	459.0	456.8	455.1	454.0	452.9	451.7	450.6
27.5°	436.7	433.7	430.7	428.3	426.5	424.8	423.1	421.3
30°	419.3	415.8	412.3	409.7	408.0	406.4	404.7	403.0
32.5°	402.2	398.4	394.5	391.7	390.0	388.3	386.5	384.8
35°	376.9	372.4	368.0	364.8	363.0	361.1	359.2	357.4
37.5°	349.7	344.6	339.6	335.9	333.6	331.3	329.0	326.7
40°	330.8	325.4	320.0	316.1	313.7	311.4	309.0	306.6
42.5°	312.6	306.8	300.9	296.9	294.7	292.6	290.5	288.3
45°	285.9	280.0	274.1	269.9	267.5	265.0	262.5	260.0
47.5°	258.3	251.9	245.5	241.2	239.0	236.8	234.5	232.3
50°	239.7	233.3	226.9	222.5	220.1	217.7	215.3	212.9
52.5°	221.7	215.0	208.4	204.0	201.8	199.7	197.6	195.4
55°	194.9	188.9	182.9	178.8	176.8	174.7	172.6	170.5
57.5°	168.5	162.8	157.2	153.4	151.7	149.9	148.2	146.4
60°	151.9	146.3	140.7	137.0	135.3	133.5	131.8	130.0
62.5°	135.4	130.2	124.9	121.3	119.5	117.7	115.8	114.0
65°	111.9	106.9	101.8	98.7	97.5	96.4	95.3	94.1
67.5°	89.5	85.7	81.9	79.4	78.2	77.0	75.8	74.6
70°	75.7	72.1	68.4	66.1	64.9	63.8	62.6	61.5
72.5°	63.2	60.3	57.3	55.6	55.1	54.6	54.2	53.7
75°	47.3	46.3	45.2	44.6	44.4	44.2	44.0	43.8
77.5°	35.7	35.1	34.6	34.2	34.0	33.8	33.6	33.4
80°	28.7	28.4	28.1	27.9	27.6	27.4	27.2	27.0
82.5°	22.0	21.7	21.4	21.2	21.2	21.1	21.1	21.1
85°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
87.5°	9.8	9.9	10.0	10.1	10.1	10.1	10.1	10.1
90°	25.7	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	39.8	40.5	41.2	41.4	41.1	40.9	40.6	40.3
95°	75.6	76.5	77.4	77.9	77.9	77.9	77.9	77.9
97.5°	117.6	118.7	119.7	120.1	120.1	120.0	119.9	119.8
100°	148.1	148.7	149.4	150.0	150.4	150.8	151.3	151.7
102.5°	183.2	183.9	184.5	184.8	184.7	184.6	184.6	184.5
105°	235.6	235.6	235.6	235.8	236.2	236.7	237.1	237.6
107.5°	292.3	293.0	293.7	293.9	293.7	293.4	293.1	292.9
110°	330.2	331.1	332.0	332.2	331.7	331.3	330.9	330.4



TEST NUMBER: P332262

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.1	369.1	370.2	370.7	370.6	370.5	370.4	370.3
115°	425.7	425.9	426.1	426.1	425.9	425.7	425.5	425.2
117.5°	483.8	483.8	483.8	483.4	482.8	482.2	481.6	480.9
120°	522.6	522.4	522.2	521.8	521.4	521.0	520.5	520.1
122.5°	561.8	561.3	560.7	560.1	559.5	558.8	558.2	557.6
125°	620.1	619.2	618.3	617.4	616.6	615.7	614.8	613.9
127.5°	677.7	676.5	675.2	674.1	673.1	672.0	671.0	670.0
130°	715.9	715.0	714.2	712.9	711.4	709.8	708.3	706.7
132.5°	753.1	752.1	751.0	749.9	748.7	747.5	746.3	745.1
135°	808.8	807.9	807.0	806.3	805.9	805.4	805.0	804.6
137.5°	863.2	862.3	861.3	860.4	859.6	858.7	857.9	857.1
140°	898.9	898.7	898.5	897.6	896.1	894.5	893.0	891.4
142.5°	932.5	932.3	932.0	931.3	930.1	928.9	927.7	926.5
145°	981.8	981.6	981.3	980.8	979.9	979.0	978.1	977.2
147.5°	1028.4	1028.4	1028.4	1027.7	1026.4	1025.0	1023.7	1022.4
150°	1057.1	1057.1	1057.1	1056.4	1055.1	1053.8	1052.4	1051.1
152.5°	1083.4	1083.7	1084.1	1083.7	1082.5	1081.4	1080.2	1079.1
155°	1121.8	1122.7	1123.5	1123.2	1121.7	1120.1	1118.5	1117.0
157.5°	1154.8	1155.7	1156.7	1156.5	1155.3	1154.0	1152.8	1151.5
160°	1175.1	1176.2	1177.3	1177.4	1176.6	1175.7	1174.8	1173.9
162.5°	1194.3	1195.4	1196.5	1196.3	1194.9	1193.5	1192.1	1190.7
165°	1218.5	1219.8	1221.1	1221.0	1219.5	1217.9	1216.4	1214.8
167.5°	1238.1	1239.5	1240.9	1240.9	1239.5	1238.1	1236.8	1235.4
170°	1248.9	1250.4	1252.0	1252.0	1250.4	1248.9	1247.3	1245.8
172.5°	1257.3	1258.7	1260.0	1260.0	1258.4	1256.9	1255.3	1253.7
175°	1266.4	1267.7	1269.1	1268.9	1267.4	1265.8	1264.3	1262.7
177.5°	1270.5	1271.5	1272.6	1272.5	1271.3	1270.0	1268.8	1267.5
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7

(END OF REPORT)