

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332388-840

Luminaire Tested: **S123RDIP-S1165D1195U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332388-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1195U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8564.5 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332388-840

CATALOG NUMBER: S123RDIP-S1165D1195U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332388-840

CATALOG NUMBER: S123RDIP-S1165D1195U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	58	55	52	50	46	44	42	38
3	82	73	66	60	76	68	62	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	42	47	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21068	21068	21068
5°	21149	20857	20977
10°	21029	20595	20525
15°	20803	20113	19900
20°	20492	19511	19057
25°	20173	18834	18231
30°	19750	18053	17066
35°	19316	17270	16000
40°	18916	16350	14677
45°	18389	15440	13484
50°	17811	14408	12149
55°	17220	13226	10903
60°	16678	11961	9535
65°	15969	10593	8166
70°	15087	8894	6593
75°	13795	6995	6209
80°	12298	6199	5709
85°	10387	5483	5101



TEST NUMBER: P332388-840

CATALOG NUMBER: S123RDIP-S1165D1195U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	2.1
10°-20°	511.4	6.0
20°-30°	736.4	8.6
30°-40°	829.4	9.7
40°-50°	793.5	9.3
50°-60°	649.8	7.6
60°-70°	438.4	5.1
70°-80°	220.6	2.6
80°-90°	62.8	0.7
90°-100°	97.3	1.1
100°-110°	291.2	3.4
110°-120°	495.4	5.8
120°-130°	651.6	7.6
130°-140°	732.3	8.6
140°-150°	719.9	8.4
150°-160°	606.0	7.1
160°-170°	403.4	4.7
170°-180°	141.3	1.6
0°-30°	1431.6	16.7
0°-40°	2261.0	26.4
0°-60°	3704.3	43.3
0°-90°	4426.1	51.7
90°-120°	883.9	10.3
90°-150°	2987.7	34.9
90°-180°	4138.0	48.3
0°-180°	8564.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1957	1957	1957	1957	1957	
5°	1957	1949	1930	1944	1941	186
15°	1867	1848	1805	1797	1786	526
25°	1698	1657	1586	1553	1535	781
35°	1470	1411	1314	1248	1218	920
45°	1208	1134	1014	927	886	932
55°	918	837	705	616	581	822
65°	627	538	416	342	321	620
75°	332	255	168	153	149	354
85°	84	51	44	41	41	94
90°	1	13	28	33	35	8
95°	69	78	87	91	92	78
105°	264	267	277	277	279	283
115°	499	502	500	501	500	493
125°	730	733	731	726	722	651
135°	947	953	953	948	946	729
145°	1149	1151	1155	1153	1149	717
155°	1315	1315	1316	1320	1313	605
165°	1433	1429	1429	1435	1428	404
175°	1490	1486	1485	1492	1484	141
180°	1494	1494	1494	1494	1494	



TEST NUMBER: P332388-840

CATALOG NUMBER: S123RDIP-S1165D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1963.7	1962.5	1961.4	1960.2	1959.1	1956.8	1953.5	1950.0	1946.7	1943.3	1946.4
5°	1957.3	1955.5	1953.8	1952.0	1950.3	1947.2	1943.0	1938.7	1934.5	1930.3	1933.5
7.5°	1939.1	1937.3	1935.4	1933.5	1931.6	1927.8	1922.4	1916.8	1911.4	1905.8	1907.6
10°	1924.0	1921.5	1919.0	1916.5	1914.1	1909.7	1903.3	1896.9	1890.6	1884.3	1884.6
12.5°	1902.4	1899.7	1896.8	1894.1	1891.4	1886.1	1878.3	1870.6	1862.8	1855.0	1854.8
15°	1866.8	1862.9	1859.1	1855.1	1851.3	1844.4	1834.5	1824.6	1814.7	1804.9	1803.1
17.5°	1822.0	1817.6	1813.0	1808.5	1804.0	1795.4	1782.9	1770.3	1757.8	1745.2	1741.5
20°	1789.0	1783.4	1777.8	1772.1	1766.5	1757.0	1743.5	1730.1	1716.7	1703.3	1698.7
22.5°	1752.2	1745.7	1739.2	1732.7	1726.3	1715.9	1701.6	1687.4	1673.1	1658.8	1653.1
25°	1698.5	1689.7	1680.9	1672.0	1663.2	1650.7	1634.5	1618.3	1602.0	1585.8	1578.4
27.5°	1633.5	1623.8	1614.0	1604.3	1594.5	1580.6	1562.6	1544.5	1526.4	1508.3	1498.0
30°	1589.0	1578.4	1567.8	1557.2	1546.7	1531.5	1511.8	1492.0	1472.3	1452.5	1440.5
32.5°	1544.6	1532.6	1520.6	1508.5	1496.6	1480.2	1459.3	1438.4	1417.4	1396.6	1383.5
35°	1470.0	1457.2	1444.5	1431.9	1419.2	1401.9	1380.0	1358.2	1336.3	1314.3	1299.2
37.5°	1394.4	1380.3	1366.1	1352.0	1338.0	1319.2	1295.9	1272.5	1249.2	1225.8	1208.6
40°	1346.2	1330.6	1315.0	1299.6	1284.0	1263.7	1238.7	1213.7	1188.6	1163.6	1145.2
42.5°	1291.5	1276.0	1260.5	1245.0	1229.4	1208.7	1182.9	1156.9	1131.0	1105.2	1085.1
45°	1208.0	1192.1	1176.3	1160.4	1144.5	1123.0	1095.8	1068.6	1041.5	1014.3	994.2
47.5°	1124.5	1107.1	1089.6	1072.3	1054.8	1032.5	1005.3	978.2	951.0	923.9	902.0
50°	1063.6	1047.0	1030.4	1013.8	997.2	974.7	946.1	917.6	889.0	860.4	838.5
52.5°	1009.0	991.0	973.0	955.0	937.0	913.8	885.6	857.3	829.0	800.7	778.0
55°	917.6	900.2	882.9	865.7	848.4	824.8	794.8	764.8	734.8	704.8	684.4
57.5°	833.0	814.3	795.4	776.6	757.7	733.3	703.2	673.0	642.9	612.8	593.4
60°	774.7	755.3	735.9	716.5	697.0	672.7	643.4	614.2	584.9	555.6	536.5
62.5°	716.2	696.8	677.4	658.0	638.6	614.3	585.0	555.7	526.4	497.2	479.3
65°	627.0	607.6	588.2	568.9	549.5	525.9	498.5	470.9	443.4	415.9	398.6
67.5°	537.9	518.2	498.6	479.0	459.4	436.4	410.0	383.5	357.2	330.8	317.9
70°	479.4	460.4	441.3	422.2	403.2	381.3	356.7	331.9	307.3	282.6	270.2
72.5°	421.0	402.2	383.4	364.7	345.9	325.3	302.9	280.4	258.0	235.6	225.5
75°	331.7	314.9	297.9	280.9	264.1	245.9	226.5	207.0	187.6	168.2	164.7
77.5°	250.4	235.2	219.8	204.6	189.2	175.3	162.9	150.4	137.8	125.4	123.5
80°	198.4	184.0	169.5	155.0	140.6	129.7	122.2	114.8	107.4	100.0	99.0
82.5°	148.9	136.4	123.9	111.4	99.0	91.0	87.6	84.0	80.6	77.2	76.0
85°	84.1	76.3	68.6	60.9	53.1	48.7	47.7	46.6	45.5	44.4	43.7
87.5°	30.7	28.2	25.5	22.9	20.4	19.4	20.1	20.8	21.5	22.1	22.1
90°	1.2	3.7	6.4	9.0	11.6	14.6	18.0	21.4	24.7	28.2	29.2
92.5°	28.4	30.2	31.9	33.7	35.4	37.4	39.3	41.2	43.1	45.0	45.8
95°	69.3	71.1	72.9	74.7	76.5	78.5	80.6	82.6	84.7	86.8	87.9
97.5°	123.0	124.3	125.7	127.0	128.4	129.9	131.4	132.9	134.3	135.8	137.0
100°	159.6	161.2	162.7	164.3	165.8	167.2	168.5	169.9	171.2	172.5	173.3
102.5°	201.8	202.8	203.7	204.6	205.6	206.9	208.6	210.4	212.1	213.8	214.6
105°	264.0	264.5	265.1	265.6	266.1	267.5	269.8	272.3	274.6	276.9	276.9
107.5°	336.3	336.6	336.9	337.2	337.5	338.2	339.1	340.0	340.9	341.9	342.7
110°	381.3	381.8	382.3	382.9	383.4	384.0	384.5	385.0	385.5	386.1	387.1



TEST NUMBER: P332388-840

CATALOG NUMBER: S123RDIP-S1165D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	428.3	428.6	428.9	429.2	429.5	429.7	429.8	429.9	430.0	430.1	431.4
115°	498.7	499.5	500.2	501.0	501.8	501.9	501.4	500.9	500.4	499.9	500.1
117.5°	569.6	570.1	570.6	571.1	571.6	571.6	570.9	570.2	569.6	568.9	568.8
120°	613.7	615.2	616.8	618.3	620.0	620.1	618.7	617.4	616.1	614.8	614.6
122.5°	659.6	660.8	662.0	663.1	664.3	664.5	663.8	663.1	662.5	661.8	661.1
125°	729.8	730.6	731.3	732.2	733.0	733.1	732.6	732.1	731.5	731.0	729.9
127.5°	794.6	796.3	797.9	799.6	801.2	801.8	801.2	800.6	800.1	799.5	798.1
130°	837.8	839.8	841.9	844.0	846.1	846.8	846.0	845.2	844.4	843.6	842.6
132.5°	880.9	883.0	885.1	887.2	889.3	890.1	889.5	888.9	888.3	887.8	886.5
135°	946.8	948.5	950.0	951.6	953.1	953.8	953.5	953.3	953.0	952.7	951.7
137.5°	1007.9	1009.2	1010.5	1011.8	1013.1	1014.1	1014.8	1015.4	1016.1	1016.8	1015.7
140°	1050.2	1051.5	1052.8	1054.1	1055.3	1056.1	1056.4	1056.6	1056.9	1057.2	1056.9
142.5°	1088.6	1089.9	1091.3	1092.6	1093.9	1094.7	1095.2	1095.7	1096.1	1096.6	1096.3
145°	1148.7	1149.2	1149.7	1150.2	1150.7	1151.4	1152.3	1153.0	1153.8	1154.6	1154.3
147.5°	1201.2	1202.2	1203.2	1204.1	1205.1	1205.9	1206.6	1207.3	1208.0	1208.8	1208.8
150°	1237.9	1238.4	1238.9	1239.4	1240.0	1240.5	1241.0	1241.5	1242.0	1242.5	1242.5
152.5°	1267.9	1268.7	1269.4	1270.1	1270.8	1271.3	1271.6	1272.0	1272.3	1272.6	1273.0
155°	1315.3	1315.3	1315.3	1315.3	1315.3	1315.5	1315.8	1316.0	1316.3	1316.5	1317.6
157.5°	1355.6	1355.3	1355.0	1354.7	1354.4	1354.3	1354.6	1354.8	1355.0	1355.2	1356.3
160°	1381.0	1380.5	1380.0	1379.5	1379.0	1378.7	1378.7	1378.7	1378.7	1378.7	1380.0
162.5°	1403.5	1402.8	1402.1	1401.4	1400.7	1400.4	1400.6	1400.8	1401.0	1401.2	1402.5
165°	1432.7	1431.9	1431.1	1430.3	1429.6	1429.2	1429.2	1429.2	1429.2	1429.2	1430.7
167.5°	1455.9	1454.8	1453.8	1452.8	1451.7	1451.3	1451.5	1451.7	1451.9	1452.1	1453.7
170°	1469.1	1467.9	1466.9	1465.9	1464.8	1464.3	1464.3	1464.3	1464.3	1464.3	1466.1
172.5°	1479.4	1478.3	1477.2	1476.2	1475.2	1474.7	1474.7	1474.7	1474.7	1474.7	1476.3
175°	1490.2	1489.1	1488.0	1487.0	1486.0	1485.4	1485.4	1485.4	1485.4	1485.4	1487.0
177.5°	1494.6	1493.8	1493.0	1492.1	1491.3	1490.9	1490.9	1490.9	1490.9	1490.9	1492.1
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7



TEST NUMBER: P332388-840

CATALOG NUMBER: S123RDIP-S1165D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1949.5	1952.7	1955.7	1957.0	1956.4	1955.9	1955.3	1954.7
5°	1936.6	1939.8	1943.0	1944.2	1943.5	1942.8	1942.1	1941.4
7.5°	1909.4	1911.2	1912.9	1913.2	1912.0	1910.8	1909.6	1908.3
10°	1885.0	1885.3	1885.7	1885.0	1883.2	1881.5	1879.7	1877.9
12.5°	1854.6	1854.4	1854.2	1853.1	1851.1	1849.0	1846.9	1844.9
15°	1801.4	1799.6	1797.9	1795.7	1793.2	1790.8	1788.3	1785.8
17.5°	1737.8	1733.9	1730.2	1726.6	1722.8	1719.2	1715.6	1711.8
20°	1694.1	1689.5	1685.0	1680.5	1676.3	1672.0	1667.9	1663.7
22.5°	1647.4	1641.7	1636.0	1631.1	1627.2	1623.3	1619.3	1615.4
25°	1571.0	1563.6	1556.2	1550.5	1546.7	1542.8	1538.9	1535.0
27.5°	1487.7	1477.4	1467.1	1459.1	1453.1	1447.2	1441.3	1435.3
30°	1428.5	1416.5	1404.5	1395.7	1390.1	1384.4	1378.8	1373.1
32.5°	1370.4	1357.3	1344.1	1334.6	1328.7	1322.7	1316.9	1310.9
35°	1284.0	1268.9	1253.7	1242.9	1236.6	1230.2	1223.9	1217.6
37.5°	1191.3	1174.2	1156.9	1144.4	1136.6	1128.7	1121.0	1113.1
40°	1126.9	1108.5	1090.3	1077.0	1068.8	1060.8	1052.7	1044.5
42.5°	1065.1	1045.0	1025.0	1011.4	1004.1	996.8	989.6	982.3
45°	974.1	954.0	933.9	919.7	911.2	902.7	894.2	885.8
47.5°	880.1	858.3	836.4	821.7	814.2	806.6	799.0	791.5
50°	816.7	794.8	772.8	757.9	749.8	741.6	733.6	725.5
52.5°	755.3	732.6	709.8	694.8	687.5	680.3	673.1	665.8
55°	663.9	643.4	623.0	609.3	602.2	595.1	588.0	581.0
57.5°	574.1	554.7	535.4	522.7	516.7	510.8	504.7	498.8
60°	517.5	498.5	479.4	466.9	460.9	454.8	448.9	442.9
62.5°	461.3	443.4	425.5	413.4	407.1	400.8	394.6	388.3
65°	381.3	364.1	346.8	336.2	332.3	328.4	324.6	320.6
67.5°	305.0	292.1	279.1	270.6	266.5	262.3	258.1	254.0
70°	257.8	245.5	233.2	225.1	221.2	217.3	213.4	209.5
72.5°	215.4	205.3	195.2	189.3	187.7	186.1	184.5	182.9
75°	161.2	157.6	154.1	152.1	151.4	150.7	150.0	149.3
77.5°	121.6	119.7	117.8	116.4	115.7	115.0	114.3	113.6
80°	97.9	96.8	95.7	94.9	94.2	93.5	92.8	92.1
82.5°	75.0	74.0	72.9	72.3	72.2	72.0	71.9	71.8
85°	43.0	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	22.0	21.9	21.8	21.7	21.5	21.4	21.2	21.0
90°	30.3	31.3	32.3	33.1	33.6	34.1	34.6	35.2
92.5°	46.8	47.6	48.4	48.7	48.4	48.1	47.7	47.4
95°	88.9	90.0	91.0	91.5	91.5	91.5	91.5	91.5
97.5°	138.3	139.5	140.7	141.2	141.1	141.0	140.9	140.8
100°	174.0	174.8	175.6	176.2	176.8	177.3	177.8	178.3
102.5°	215.3	216.1	216.9	217.2	217.1	217.0	216.9	216.8
105°	276.9	276.9	276.9	277.2	277.7	278.2	278.7	279.2
107.5°	343.6	344.5	345.3	345.5	345.2	344.9	344.6	344.3
110°	388.1	389.2	390.2	390.4	389.9	389.4	388.9	388.4



TEST NUMBER: P332388-840

CATALOG NUMBER: S123RDIP-S1165D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.6	433.9	435.2	435.8	435.7	435.6	435.5	435.4
115°	500.4	500.6	500.9	500.9	500.6	500.4	500.1	499.9
117.5°	568.8	568.7	568.7	568.3	567.5	566.7	566.0	565.3
120°	614.3	614.1	613.8	613.4	612.9	612.4	611.9	611.3
122.5°	660.5	659.7	659.0	658.3	657.6	656.9	656.1	655.4
125°	728.9	727.9	726.8	725.8	724.8	723.7	722.7	721.6
127.5°	796.6	795.2	793.7	792.3	791.1	789.9	788.7	787.6
130°	841.5	840.5	839.5	838.0	836.2	834.4	832.5	830.7
132.5°	885.2	884.0	882.7	881.4	880.0	878.6	877.2	875.8
135°	950.7	949.6	948.6	947.8	947.3	946.7	946.2	945.7
137.5°	1014.6	1013.5	1012.4	1011.4	1010.4	1009.5	1008.5	1007.4
140°	1056.6	1056.4	1056.1	1055.1	1053.3	1051.5	1049.7	1047.8
142.5°	1096.1	1095.8	1095.6	1094.7	1093.3	1091.9	1090.6	1089.1
145°	1154.1	1153.8	1153.6	1152.9	1151.9	1150.7	1149.7	1148.7
147.5°	1208.8	1208.8	1208.8	1208.0	1206.4	1204.9	1203.3	1201.7
150°	1242.5	1242.5	1242.5	1241.8	1240.2	1238.7	1237.1	1235.6
152.5°	1273.4	1273.8	1274.2	1273.8	1272.4	1271.1	1269.7	1268.4
155°	1318.6	1319.6	1320.7	1320.3	1318.5	1316.7	1314.8	1312.9
157.5°	1357.4	1358.5	1359.6	1359.4	1358.0	1356.5	1355.0	1353.5
160°	1381.3	1382.6	1383.9	1384.0	1383.0	1381.9	1380.9	1379.9
162.5°	1403.8	1405.1	1406.4	1406.2	1404.5	1402.9	1401.2	1399.6
165°	1432.3	1433.8	1435.4	1435.2	1433.4	1431.6	1429.8	1427.9
167.5°	1455.3	1456.9	1458.5	1458.5	1456.9	1455.3	1453.7	1452.1
170°	1467.9	1469.9	1471.7	1471.7	1469.9	1467.9	1466.1	1464.3
172.5°	1477.9	1479.6	1481.2	1481.1	1479.1	1477.3	1475.5	1473.7
175°	1488.5	1490.2	1491.7	1491.6	1489.8	1487.9	1486.1	1484.3
177.5°	1493.4	1494.6	1495.8	1495.7	1494.3	1492.8	1491.4	1490.0
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7

(END OF REPORT)