

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332360-840

Luminaire Tested: **S123RDIP-S1165D365U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020


Test Information

Test Method: LM-79-08
Report Number: P332360-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D365U840-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6082.6 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80	76
1	104	100	97	93	99	96	92	90	87	85	82	79	77	76	72	71	69	66
2	96	89	83	78	91	85	79	75	78	73	70	71	67	65	65	62	60	57
3	88	79	72	66	84	75	69	64	69	64	60	63	59	56	58	55	52	49
4	81	70	63	57	77	68	60	55	62	56	52	57	52	49	52	49	45	43
5	75	63	55	49	71	61	53	48	56	50	45	52	47	43	48	43	40	38
6	69	57	49	43	66	55	48	42	51	45	40	47	42	38	44	39	36	33
7	64	52	44	39	61	50	43	38	47	40	36	43	38	34	40	36	32	30
8	60	48	40	35	57	46	39	34	43	37	32	40	34	31	37	32	29	27
9	56	44	36	31	54	42	35	30	39	33	29	37	31	28	34	30	26	24
10	53	40	33	28	50	39	32	28	37	31	26	34	29	25	32	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19957	19957	19957	19957
5°	23791	20042	17650	20042
10°	29704	19928	15946	19928
15°	34867	19724	14540	19724
20°	38913	19420	13347	19420
25°	38292	19099	12613	19099
30°	27524	18804	11857	18804
35°	18378	18419	11369	18419
40°	13540	17956	10863	17956
45°	11357	17145	10368	17145
50°	10021	16083	9676	16083
55°	8788	14865	8728	14865
60°	7828	13702	7995	13702
65°	6872	12455	7440	12455
70°	5397	11339	6795	11339
75°	4754	9902	6209	9902
80°	4135	8412	6106	8412
85°	3335	6756	6472	6756



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.3	3.0
10°-20°	569.6	9.4
20°-30°	894.9	14.7
30°-40°	933.7	15.4
40°-50°	799.0	13.1
50°-60°	609.0	10.0
60°-70°	390.4	6.4
70°-80°	187.8	3.1
80°-90°	51.0	0.8
90°-100°	17.5	0.3
100°-110°	83.2	1.4
110°-120°	199.9	3.3
120°-130°	254.6	4.2
130°-140°	272.0	4.5
140°-150°	254.4	4.2
150°-160°	205.2	3.4
160°-170°	132.4	2.2
170°-180°	45.6	0.8
0°-30°	1646.9	27.1
0°-40°	2580.6	42.4
0°-60°	3988.6	65.6
0°-90°	4617.8	75.9
90°-120°	300.6	4.9
90°-150°	1081.5	17.8
90°-180°	1465.0	24.1
0°-180°	6082.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1854	1854	1854	1854	1854	
5°	2202	1855	1634	1855	2202	227
15°	3129	1770	1305	1770	3129	887
25°	3224	1608	1062	1608	3224	1386
35°	1399	1402	865	1402	1399	917
45°	746	1126	681	1126	746	587
55°	468	792	465	792	468	423
65°	270	489	292	489	270	265
75°	114	238	149	238	114	123
85°	27	55	52	55	27	31
90°	11	0	11	0	11	6
95°	14	22	14	22	14	11
105°	16	106	16	106	16	36
115°	210	199	210	199	210	194
125°	287	281	287	281	287	256
135°	354	350	354	350	354	273
145°	408	404	408	404	408	255
155°	444	445	444	445	444	205
165°	468	469	468	469	468	132
175°	479	480	479	480	479	46
180°	480	480	480	480	480	



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1974.8	1977.3	1969.0	1967.8	1958.2	1955.7	1955.7	1942.4	1934.1	1923.4	1917.0
5°	2201.8	2214.5	2208.2	2193.8	2170.0	2164.4	2149.4	2125.6	2098.6	2065.3	2049.4
7.5°	2485.3	2502.6	2496.0	2473.9	2448.9	2428.8	2386.2	2346.7	2291.3	2242.7	2201.1
10°	2717.7	2699.5	2685.1	2663.7	2640.7	2603.4	2559.0	2497.8	2427.2	2371.7	2309.8
12.5°	2891.6	2888.7	2870.5	2848.5	2816.0	2780.6	2725.9	2651.5	2569.4	2489.1	2418.3
15°	3128.9	3133.6	3121.7	3098.7	3052.6	2989.9	2907.4	2876.5	2759.0	2671.7	2584.3
17.5°	3293.0	3292.1	3290.4	3258.5	3211.6	3166.9	3090.4	3009.0	2902.7	2779.7	2662.0
20°	3397.1	3389.2	3390.8	3355.1	3320.1	3268.5	3193.9	3075.6	2988.4	2846.3	2724.8
22.5°	3394.6	3393.0	3399.0	3386.8	3361.4	3321.8	3263.2	3163.3	3051.9	2908.5	2771.9
25°	3224.1	3217.7	3255.1	3265.4	3305.9	3313.0	3295.5	3240.8	3135.2	2987.6	2818.5
27.5°	2698.4	2694.8	2764.1	2850.7	2960.6	3046.0	3128.6	3168.4	3135.2	3029.5	2860.1
30°	2214.5	2289.1	2324.0	2449.4	2589.1	2755.8	2901.8	3040.7	3074.8	3028.9	2889.9
32.5°	1838.6	1903.7	1932.9	2040.5	2170.7	2365.9	2585.0	2781.7	2920.6	2955.8	2872.2
35°	1398.6	1399.4	1466.0	1513.6	1634.3	1835.1	2047.8	2311.3	2573.2	2771.7	2792.3
37.5°	1116.0	1119.9	1160.2	1207.7	1298.2	1404.4	1591.7	1810.8	2113.3	2418.0	2596.6
40°	963.6	970.7	1000.9	1047.7	1112.8	1193.0	1339.0	1545.4	1797.8	2136.7	2413.7
42.5°	865.8	877.4	892.9	929.0	969.3	1044.4	1162.5	1321.9	1551.5	1871.9	2191.5
45°	746.1	752.5	764.4	781.0	817.5	869.9	949.3	1056.4	1247.0	1504.9	1824.7
47.5°	658.1	654.8	667.3	680.9	705.2	740.8	794.1	881.5	1017.4	1224.4	1495.7
50°	598.4	597.6	606.4	616.7	639.7	665.9	709.6	775.5	883.4	1054.9	1303.3
52.5°	542.6	545.6	551.8	564.6	581.3	602.5	641.7	689.1	781.8	929.8	1136.9
55°	468.3	470.7	479.4	486.6	498.5	519.9	544.5	584.2	647.7	750.8	921.5
57.5°	405.5	404.3	412.7	414.4	428.0	445.5	464.4	495.2	541.3	618.0	733.0
60°	363.6	361.1	368.3	373.9	381.0	395.3	411.1	441.3	477.9	534.2	632.6
62.5°	325.4	324.3	329.5	335.1	341.0	354.0	367.3	390.5	419.4	466.9	544.9
65°	269.8	272.3	274.6	277.0	280.1	288.1	300.8	316.7	336.6	369.9	426.3
67.5°	212.1	214.5	215.3	220.2	227.0	232.0	239.7	253.9	267.6	295.8	327.8
70°	171.5	170.7	171.5	173.8	182.6	191.3	201.6	212.0	220.7	240.4	267.5
72.5°	147.3	145.9	147.9	148.5	152.7	155.1	161.6	171.3	182.6	196.0	215.4
75°	114.3	114.3	114.3	114.3	117.4	119.1	121.5	123.8	127.7	134.1	148.5
77.5°	84.4	84.6	85.7	86.5	87.2	88.1	89.6	91.9	93.3	96.6	102.9
80°	66.7	67.5	66.7	67.5	67.5	69.1	69.9	72.2	73.0	77.0	79.4
82.5°	50.2	49.7	50.2	51.0	51.0	52.5	52.7	54.4	54.6	56.7	59.1
85°	27.0	25.4	27.0	26.2	27.8	26.2	27.0	28.6	28.6	29.4	32.5
87.5°	8.5	9.7	8.4	9.0	9.0	9.6	9.5	9.5	10.7	10.0	10.4
90°	10.7	10.5	10.4	10.2	10.1	9.8	9.5	9.2	8.9	8.6	7.6
92.5°	11.8	11.7	11.6	11.5	11.5	11.2	10.7	10.2	9.6	9.1	8.4
95°	13.5	13.5	13.5	13.5	13.5	13.3	12.7	12.2	11.6	11.1	10.2
97.5°	14.7	14.6	14.5	14.4	14.3	14.0	13.4	12.7	12.1	11.5	17.2
100°	14.9	14.9	14.8	14.7	14.6	14.3	13.6	13.0	12.4	11.8	24.1
102.5°	15.2	15.1	14.9	14.8	14.7	15.7	17.6	19.6	21.5	23.5	37.0
105°	15.7	15.6	15.3	15.2	15.0	22.0	36.1	50.1	64.1	78.2	85.3
107.5°	49.3	59.9	70.5	81.1	91.6	102.1	112.4	122.7	132.9	143.2	142.1
110°	98.2	109.5	120.8	132.2	143.5	150.5	153.1	155.7	158.3	161.0	160.1



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	168.3	170.8	173.2	175.5	177.9	179.2	179.0	179.0	178.9	178.9	178.0
115°	209.8	209.5	209.2	208.8	208.5	208.0	207.2	206.4	205.6	204.8	204.1
117.5°	233.1	233.1	233.0	232.9	232.9	232.5	231.9	231.3	230.6	229.9	229.6
120°	249.1	249.1	249.1	249.1	249.1	248.7	248.1	247.5	246.9	246.2	246.0
122.5°	264.8	264.7	264.7	264.6	264.5	264.3	263.9	263.4	263.0	262.5	262.2
125°	286.9	286.8	286.6	286.4	286.3	286.1	286.0	285.8	285.7	285.5	285.2
127.5°	308.2	308.3	308.5	308.6	308.8	308.8	308.5	308.2	308.0	307.7	307.4
130°	321.8	322.0	322.2	322.3	322.6	322.4	322.1	321.8	321.4	321.1	320.8
132.5°	334.5	334.7	334.9	335.1	335.4	335.3	335.0	334.7	334.4	334.1	333.8
135°	353.7	353.9	354.2	354.4	354.6	354.6	354.4	354.2	353.9	353.7	353.4
137.5°	371.7	371.8	372.0	372.1	372.3	372.2	371.8	371.4	371.1	370.7	370.5
140°	382.5	382.7	382.8	383.0	383.1	383.1	382.7	382.4	382.1	381.8	381.6
142.5°	392.5	392.7	392.9	393.2	393.4	393.4	393.1	392.9	392.6	392.4	392.1
145°	407.9	407.9	407.9	407.9	407.9	407.8	407.7	407.5	407.4	407.2	407.0
147.5°	419.3	419.7	420.0	420.4	420.8	420.9	420.7	420.5	420.4	420.2	420.1
150°	427.9	428.1	428.4	428.6	428.8	428.9	428.7	428.6	428.4	428.2	428.1
152.5°	434.7	435.0	435.5	435.9	436.2	436.3	436.0	435.7	435.4	435.0	434.9
155°	444.2	444.7	445.2	445.8	446.2	446.3	445.9	445.5	445.0	444.6	444.5
157.5°	452.3	452.9	453.6	454.2	454.8	454.9	454.4	453.9	453.4	453.0	453.0
160°	457.5	458.1	458.6	459.2	459.7	459.8	459.3	458.8	458.3	457.9	458.0
162.5°	462.3	462.8	463.3	463.8	464.3	464.2	463.7	463.2	462.6	462.1	462.2
165°	468.2	468.8	469.3	469.9	470.4	470.4	469.8	469.1	468.5	467.9	467.9
167.5°	472.4	473.0	473.6	474.3	474.9	474.9	474.3	473.6	473.0	472.4	472.4
170°	474.9	475.6	476.3	476.9	477.5	477.5	476.9	476.3	475.6	474.9	474.9
172.5°	476.4	477.1	477.8	478.5	479.2	479.2	478.6	478.0	477.4	476.7	476.7
175°	478.6	479.2	479.8	480.5	481.1	481.1	480.6	480.0	479.5	478.9	478.8
177.5°	479.2	479.8	480.5	481.1	481.7	481.8	481.3	480.8	480.3	479.8	479.7
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1914.5	1912.6	1903.7	1893.5	1880.2	1871.3	1864.3	1860.5	1849.1	1835.1	1825.5
5°	2032.8	2008.9	1983.5	1952.6	1924.0	1894.6	1876.3	1854.9	1828.8	1799.4	1778.8
7.5°	2159.4	2112.7	2062.4	2010.5	1959.2	1913.2	1872.6	1837.8	1796.0	1753.9	1724.4
10°	2256.5	2188.3	2117.7	2045.4	1979.5	1917.6	1870.0	1823.2	1773.2	1724.7	1688.3
12.5°	2344.8	2254.9	2173.5	2084.8	2000.5	1926.5	1857.9	1802.8	1742.7	1691.1	1649.5
15°	2456.6	2364.5	2266.0	2131.1	2019.2	1925.6	1842.2	1770.0	1697.0	1633.5	1593.0
17.5°	2561.0	2422.5	2290.2	2177.7	2032.3	1915.2	1813.5	1727.2	1647.0	1579.6	1529.8
20°	2604.2	2470.0	2326.4	2182.7	2039.8	1908.9	1790.6	1695.4	1612.0	1535.8	1489.9
22.5°	2630.2	2478.3	2327.0	2172.6	2020.8	1884.8	1767.8	1663.0	1572.7	1500.3	1443.5
25°	2660.6	2479.6	2312.9	2160.5	2005.7	1858.2	1719.2	1608.1	1510.5	1433.5	1373.1
27.5°	2680.6	2467.7	2270.7	2101.3	1944.3	1797.3	1670.0	1552.2	1453.2	1371.7	1307.0
30°	2684.3	2458.1	2238.3	2055.0	1895.4	1760.5	1625.6	1512.9	1408.1	1321.5	1261.2
32.5°	2689.5	2434.7	2194.4	1999.7	1836.3	1702.7	1580.4	1472.8	1365.5	1280.3	1218.7
35°	2668.5	2421.7	2128.0	1904.1	1740.6	1611.2	1501.0	1401.7	1296.2	1213.6	1150.9
37.5°	2578.3	2370.1	2059.1	1796.5	1625.6	1505.7	1415.8	1329.3	1232.5	1143.5	1084.4
40°	2487.5	2319.3	2005.7	1731.1	1552.6	1429.5	1348.6	1277.9	1184.3	1100.9	1037.4
42.5°	2352.3	2250.1	1954.9	1662.5	1470.0	1351.4	1283.1	1216.9	1134.7	1050.1	990.4
45°	2104.2	2117.7	1851.0	1553.3	1355.6	1236.6	1172.4	1126.3	1053.3	983.4	922.3
47.5°	1793.0	1919.2	1728.9	1436.9	1235.2	1123.5	1067.2	1027.0	977.9	909.3	853.5
50°	1589.8	1770.0	1631.1	1358.9	1159.6	1048.5	992.9	960.4	917.6	863.5	810.4
52.5°	1402.5	1596.0	1513.0	1271.8	1077.7	976.1	921.8	895.0	861.0	810.2	762.1
55°	1143.8	1339.8	1320.8	1140.5	954.8	863.5	822.3	792.1	769.1	731.0	693.0
57.5°	925.1	1111.1	1120.8	994.5	846.6	756.4	720.8	698.1	683.1	654.4	619.1
60°	787.4	958.1	991.4	896.2	769.1	689.7	654.8	636.5	624.7	601.7	574.6
62.5°	673.1	818.3	856.1	787.5	694.8	620.6	593.2	575.6	567.5	547.6	523.8
65°	515.1	635.8	672.3	634.2	585.7	526.2	504.0	489.0	481.8	470.7	453.2
67.5°	387.4	475.2	515.3	488.5	471.0	433.3	419.2	411.1	404.8	397.2	382.5
70°	311.1	376.2	417.5	410.3	396.1	376.2	365.9	360.3	354.0	347.7	335.0
72.5°	250.1	295.0	333.7	337.3	325.6	321.6	312.6	310.2	306.4	298.7	291.8
75°	165.9	196.8	223.8	234.2	238.9	242.9	238.9	238.1	237.3	231.0	227.0
77.5°	108.8	125.4	142.4	160.1	167.4	172.9	174.1	177.0	174.9	171.6	169.7
80°	83.3	87.4	99.2	114.3	126.2	131.0	134.1	135.7	134.9	134.1	131.0
82.5°	60.5	63.8	69.4	80.0	90.0	98.0	99.9	99.6	101.3	101.8	99.2
85°	32.5	33.3	34.9	36.6	42.1	50.8	53.2	54.7	56.4	56.4	51.6
87.5°	11.4	10.6	11.7	11.5	13.2	13.7	17.4	20.4	21.2	18.8	19.0
90°	6.5	5.5	4.4	3.5	2.7	1.9	1.1	0.4	1.1	1.9	2.7
92.5°	7.6	6.8	6.1	5.8	6.0	6.2	6.5	6.7	6.5	6.2	6.0
95°	9.3	8.5	7.6	8.8	12.0	15.2	18.5	21.8	18.5	15.2	12.0
97.5°	22.9	28.6	34.3	37.9	39.4	40.8	42.3	43.7	42.3	40.8	39.4
100°	36.6	48.9	61.3	66.7	65.0	63.5	61.9	60.3	61.9	63.5	65.0
102.5°	50.5	64.0	77.6	83.7	82.6	81.4	80.3	79.2	80.3	81.4	82.6
105°	92.4	99.6	106.7	109.9	109.0	108.1	107.2	106.3	107.2	108.1	109.0
107.5°	141.0	139.9	138.8	137.8	137.1	136.4	135.7	135.0	135.7	136.4	137.1
110°	159.2	158.3	157.4	156.7	156.0	155.4	154.8	154.2	154.8	155.4	156.0



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	177.2	176.3	175.4	174.7	174.1	173.6	173.0	172.4	173.0	173.6	174.1
115°	203.4	202.7	202.0	201.4	200.9	200.5	200.0	199.4	200.0	200.5	200.9
117.5°	229.2	228.8	228.5	228.0	227.4	226.8	226.3	225.7	226.3	226.8	227.4
120°	245.8	245.5	245.3	244.8	244.1	243.4	242.7	242.0	242.7	243.4	244.1
122.5°	261.9	261.6	261.3	260.8	260.2	259.6	259.1	258.5	259.1	259.6	260.2
125°	284.9	284.6	284.2	283.8	283.1	282.5	281.9	281.2	281.9	282.5	283.1
127.5°	307.0	306.6	306.2	305.7	305.1	304.5	303.9	303.2	303.9	304.5	305.1
130°	320.5	320.2	319.9	319.4	318.8	318.1	317.5	316.9	317.5	318.1	318.8
132.5°	333.6	333.3	333.0	332.5	331.9	331.3	330.6	330.0	330.6	331.3	331.9
135°	353.0	352.6	352.3	351.9	351.5	351.0	350.5	350.1	350.5	351.0	351.5
137.5°	370.3	370.2	370.0	369.6	369.0	368.4	367.8	367.2	367.8	368.4	369.0
140°	381.3	381.1	380.9	380.5	380.0	379.6	379.1	378.6	379.1	379.6	380.0
142.5°	391.9	391.7	391.4	391.1	390.6	390.1	389.7	389.2	389.7	390.1	390.6
145°	406.9	406.7	406.6	406.2	405.7	405.1	404.6	403.9	404.6	405.1	405.7
147.5°	419.9	419.8	419.6	419.3	419.0	418.6	418.3	417.9	418.3	418.6	419.0
150°	427.9	427.8	427.6	427.4	427.2	426.9	426.7	426.5	426.7	426.9	427.2
152.5°	434.8	434.7	434.7	434.5	434.4	434.3	434.2	434.1	434.2	434.3	434.4
155°	444.4	444.4	444.3	444.3	444.5	444.6	444.8	445.0	444.8	444.6	444.5
157.5°	453.1	453.2	453.3	453.3	453.3	453.4	453.4	453.4	453.4	453.4	453.3
160°	458.0	458.1	458.2	458.3	458.3	458.4	458.5	458.6	458.5	458.4	458.3
162.5°	462.3	462.3	462.4	462.6	462.8	463.0	463.2	463.4	463.2	463.0	462.8
165°	468.0	468.1	468.2	468.3	468.6	468.8	469.0	469.3	469.0	468.8	468.6
167.5°	472.4	472.4	472.4	472.5	472.9	473.2	473.5	473.8	473.5	473.2	472.9
170°	474.9	474.9	474.9	475.1	475.4	475.7	476.1	476.4	476.1	475.7	475.4
172.5°	476.6	476.5	476.5	476.6	477.0	477.4	477.8	478.1	477.8	477.4	477.0
175°	478.8	478.7	478.6	478.8	479.2	479.5	479.9	480.3	479.9	479.5	479.2
177.5°	479.6	479.6	479.5	479.6	480.0	480.3	480.6	480.9	480.6	480.3	480.0
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1822.4	1814.1	1808.5	1795.7	1787.5	1778.6	1769.7	1775.4	1774.7	1774.1	1774.1
5°	1761.3	1743.0	1726.4	1705.0	1691.4	1674.8	1662.0	1660.4	1663.7	1652.5	1646.2
7.5°	1700.6	1675.7	1652.0	1628.4	1603.4	1583.4	1570.7	1564.9	1556.8	1549.9	1542.9
10°	1658.1	1628.7	1605.7	1576.3	1549.3	1525.5	1510.5	1500.2	1494.6	1489.0	1478.7
12.5°	1614.3	1585.6	1556.2	1523.0	1497.3	1469.7	1458.3	1446.8	1436.1	1430.0	1415.8
15°	1550.1	1512.9	1481.9	1446.9	1418.4	1391.4	1375.5	1352.5	1349.3	1341.4	1327.1
17.5°	1485.8	1445.3	1402.7	1376.7	1344.5	1316.5	1292.3	1284.5	1261.8	1253.2	1240.9
20°	1435.0	1397.8	1365.2	1331.1	1284.2	1258.1	1239.0	1228.7	1210.4	1199.3	1191.3
22.5°	1391.2	1353.3	1315.7	1275.9	1237.3	1207.9	1194.0	1177.9	1167.9	1152.4	1143.8
25°	1328.7	1287.4	1242.1	1199.3	1171.5	1149.3	1127.1	1112.8	1098.5	1091.4	1075.5
27.5°	1256.0	1212.8	1170.5	1138.0	1103.9	1082.0	1061.9	1049.1	1032.0	1020.0	1011.2
30°	1216.0	1165.2	1128.6	1099.3	1055.6	1035.0	1020.0	1004.1	991.4	978.7	970.0
32.5°	1169.6	1123.3	1088.6	1052.3	1018.9	996.2	976.7	962.8	952.0	939.9	931.2
35°	1096.9	1058.0	1022.3	985.8	961.2	938.2	915.1	903.2	892.9	881.8	873.9
37.5°	1031.2	994.8	960.9	926.2	895.8	877.1	858.5	849.4	835.5	828.0	819.9
40°	990.6	954.8	918.4	885.0	853.2	839.0	822.3	808.8	796.1	790.5	781.8
42.5°	946.1	910.4	879.6	843.7	817.7	798.3	782.9	768.2	758.6	750.5	745.6
45°	880.2	848.5	818.3	782.6	758.0	741.3	723.9	710.3	701.7	696.1	687.3
47.5°	816.3	784.6	753.9	722.8	698.9	679.9	662.5	653.1	641.5	634.7	628.7
50°	769.9	741.3	708.8	680.2	656.4	637.3	623.1	611.2	600.9	592.1	588.1
52.5°	727.4	696.9	668.8	642.1	617.0	595.4	582.4	569.9	562.1	552.1	547.5
55°	657.2	627.8	604.0	577.8	553.2	534.9	519.1	508.0	500.1	489.0	482.6
57.5°	591.3	565.0	536.5	513.8	488.5	473.0	459.9	444.8	435.2	426.4	420.2
60°	546.8	516.7	492.1	470.7	448.5	428.6	416.7	404.8	394.5	385.8	380.2
62.5°	500.5	474.1	450.8	427.5	407.2	389.9	376.1	366.1	357.0	351.4	345.9
65°	429.4	408.8	385.0	365.9	346.9	334.2	323.1	314.3	308.0	304.0	299.2
67.5°	364.0	344.0	323.2	304.5	291.8	282.1	274.8	267.3	264.2	259.0	255.9
70°	321.4	300.8	282.6	268.3	255.6	248.4	243.7	238.1	234.9	228.6	225.4
72.5°	275.1	260.1	247.0	235.3	225.1	218.6	212.6	205.7	200.7	193.7	190.5
75°	216.7	203.2	192.9	184.9	178.5	169.9	161.2	154.0	151.6	149.3	148.5
77.5°	160.5	151.9	144.4	137.7	129.9	123.5	121.6	120.0	119.6	118.3	118.3
80°	126.2	118.3	112.7	104.7	100.0	100.0	100.0	98.5	99.2	99.2	99.2
82.5°	93.8	86.5	83.5	80.7	79.7	80.3	80.3	80.7	80.2	81.4	80.8
85°	48.4	49.2	50.8	50.0	50.8	50.8	52.4	51.6	52.4	50.8	52.4
87.5°	18.5	20.6	21.4	22.2	23.1	22.6	23.3	23.4	24.1	24.2	24.2
90°	3.5	4.4	5.5	6.5	7.6	8.6	8.9	9.2	9.5	9.8	10.1
92.5°	5.8	6.1	6.8	7.6	8.4	9.1	9.6	10.2	10.7	11.2	11.5
95°	8.8	7.6	8.5	9.3	10.2	11.1	11.6	12.2	12.7	13.3	13.5
97.5°	37.9	34.3	28.6	22.9	17.2	11.5	12.1	12.7	13.4	14.0	14.3
100°	66.7	61.3	48.9	36.6	24.1	11.8	12.4	13.0	13.6	14.3	14.6
102.5°	83.7	77.6	64.0	50.5	37.0	23.5	21.5	19.6	17.6	15.7	14.7
105°	109.9	106.7	99.6	92.4	85.3	78.2	64.1	50.1	36.1	22.0	15.0
107.5°	137.8	138.8	139.9	141.0	142.1	143.2	132.9	122.7	112.4	102.1	91.6
110°	156.7	157.4	158.3	159.2	160.1	161.0	158.3	155.7	153.1	150.5	143.5



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	174.7	175.4	176.3	177.2	178.0	178.9	178.9	179.0	179.0	179.2	177.9
115°	201.4	202.0	202.7	203.4	204.1	204.8	205.6	206.4	207.2	208.0	208.5
117.5°	228.0	228.5	228.8	229.2	229.6	229.9	230.6	231.3	231.9	232.5	232.9
120°	244.8	245.3	245.5	245.8	246.0	246.2	246.9	247.5	248.1	248.7	249.1
122.5°	260.8	261.3	261.6	261.9	262.2	262.5	263.0	263.4	263.9	264.3	264.5
125°	283.8	284.2	284.6	284.9	285.2	285.5	285.7	285.8	286.0	286.1	286.3
127.5°	305.7	306.2	306.6	307.0	307.4	307.7	308.0	308.2	308.5	308.8	308.8
130°	319.4	319.9	320.2	320.5	320.8	321.1	321.4	321.8	322.1	322.4	322.6
132.5°	332.5	333.0	333.3	333.6	333.8	334.1	334.4	334.7	335.0	335.3	335.4
135°	351.9	352.3	352.6	353.0	353.4	353.7	353.9	354.2	354.4	354.6	354.6
137.5°	369.6	370.0	370.2	370.3	370.5	370.7	371.1	371.4	371.8	372.2	372.3
140°	380.5	380.9	381.1	381.3	381.6	381.8	382.1	382.4	382.7	383.1	383.1
142.5°	391.1	391.4	391.7	391.9	392.1	392.4	392.6	392.9	393.1	393.4	393.4
145°	406.2	406.6	406.7	406.9	407.0	407.2	407.4	407.5	407.7	407.8	407.9
147.5°	419.3	419.6	419.8	419.9	420.1	420.2	420.4	420.5	420.7	420.9	420.8
150°	427.4	427.6	427.8	427.9	428.1	428.2	428.4	428.6	428.7	428.9	428.8
152.5°	434.5	434.7	434.7	434.8	434.9	435.0	435.4	435.7	436.0	436.3	436.2
155°	444.3	444.3	444.4	444.4	444.5	444.6	445.0	445.5	445.9	446.3	446.2
157.5°	453.3	453.3	453.2	453.1	453.0	453.0	453.4	453.9	454.4	454.9	454.8
160°	458.3	458.2	458.1	458.0	458.0	457.9	458.3	458.8	459.3	459.8	459.7
162.5°	462.6	462.4	462.3	462.3	462.2	462.1	462.6	463.2	463.7	464.2	464.3
165°	468.3	468.2	468.1	468.0	467.9	467.9	468.5	469.1	469.8	470.4	470.4
167.5°	472.5	472.4	472.4	472.4	472.4	472.4	473.0	473.6	474.3	474.9	474.9
170°	475.1	474.9	474.9	474.9	474.9	474.9	475.6	476.3	476.9	477.5	477.5
172.5°	476.6	476.5	476.5	476.6	476.7	476.7	477.4	478.0	478.6	479.2	479.2
175°	478.8	478.6	478.7	478.8	478.8	478.9	479.5	480.0	480.6	481.1	481.1
177.5°	479.6	479.5	479.6	479.6	479.7	479.8	480.3	480.8	481.3	481.8	481.7
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1766.6	1765.8	1766.6	1763.9	1766.6	1765.8	1766.6	1774.1	1774.1	1774.7	1775.4
5°	1643.8	1643.1	1640.6	1633.5	1640.6	1643.1	1643.8	1646.2	1652.5	1663.7	1660.4
7.5°	1536.6	1535.5	1528.5	1528.7	1528.5	1535.5	1536.6	1542.9	1549.9	1556.8	1564.9
10°	1473.2	1473.9	1464.4	1458.9	1464.4	1473.9	1473.2	1478.7	1489.0	1494.6	1500.2
12.5°	1411.6	1408.0	1400.3	1394.1	1400.3	1408.0	1411.6	1415.8	1430.0	1436.1	1446.8
15°	1330.3	1322.3	1303.3	1304.8	1303.3	1322.3	1330.3	1327.1	1341.4	1349.3	1352.5
17.5°	1234.6	1228.7	1228.4	1217.3	1228.4	1228.7	1234.6	1240.9	1253.2	1261.8	1284.5
20°	1178.7	1174.7	1176.3	1165.2	1176.3	1174.7	1178.7	1191.3	1199.3	1210.4	1228.7
22.5°	1134.9	1130.8	1124.2	1120.7	1124.2	1130.8	1134.9	1143.8	1152.4	1167.9	1177.9
25°	1070.8	1064.4	1058.0	1062.0	1058.0	1064.4	1070.8	1075.5	1091.4	1098.5	1112.8
27.5°	1006.6	1001.9	995.5	994.7	995.5	1001.9	1006.6	1011.2	1020.0	1032.0	1049.1
30°	965.9	961.2	958.1	954.0	958.1	961.2	965.9	970.0	978.7	991.4	1004.1
32.5°	924.7	923.7	918.1	917.3	918.1	923.7	924.7	931.2	939.9	952.0	962.8
35°	870.7	866.0	864.3	865.2	864.3	866.0	870.7	873.9	881.8	892.9	903.2
37.5°	819.4	813.0	810.2	807.4	810.2	813.0	819.4	819.9	828.0	835.5	849.4
40°	782.6	776.3	774.7	773.1	774.7	776.3	782.6	781.8	790.5	796.1	808.8
42.5°	741.3	738.8	737.8	735.0	737.8	738.8	741.3	745.6	750.5	758.6	768.2
45°	685.0	684.2	679.4	681.1	679.4	684.2	685.0	687.3	696.1	701.7	710.3
47.5°	625.6	622.1	618.7	621.0	618.7	622.1	625.6	628.7	634.7	641.5	653.1
50°	585.0	583.4	576.2	577.8	576.2	583.4	585.0	588.1	592.1	600.9	611.2
52.5°	544.3	538.3	535.6	534.6	535.6	538.3	544.3	547.5	552.1	562.1	569.9
55°	477.1	469.9	466.7	465.1	466.7	469.9	477.1	482.6	489.0	500.1	508.0
57.5°	411.0	409.1	406.6	408.3	406.6	409.1	411.0	420.2	426.4	435.2	444.8
60°	372.2	372.2	372.2	371.4	372.2	372.2	372.2	380.2	385.8	394.5	404.8
62.5°	342.4	340.5	339.9	341.0	339.9	340.5	342.4	345.9	351.4	357.0	366.1
65°	296.9	296.1	292.9	292.1	292.9	296.1	296.9	299.2	304.0	308.0	314.3
67.5°	253.9	251.0	250.0	248.9	250.0	251.0	253.9	255.9	259.0	264.2	267.3
70°	221.5	219.8	215.1	215.9	215.1	219.8	221.5	225.4	228.6	234.9	238.1
72.5°	186.5	184.9	184.0	182.9	184.0	184.9	186.5	190.5	193.7	200.7	205.7
75°	147.6	146.8	146.0	149.3	146.0	146.8	147.6	148.5	149.3	151.6	154.0
77.5°	118.3	118.3	118.8	117.4	118.8	118.3	118.3	118.3	118.3	119.6	120.0
80°	99.2	99.2	98.5	98.5	98.5	99.2	99.2	99.2	99.2	99.2	98.5
82.5°	79.6	80.2	80.7	79.4	80.7	80.2	79.6	80.8	81.4	80.2	80.7
85°	52.4	51.6	53.2	52.4	53.2	51.6	52.4	52.4	50.8	52.4	51.6
87.5°	25.5	24.3	24.3	25.0	24.3	24.3	25.5	24.2	24.2	24.1	23.4
90°	10.2	10.4	10.5	10.7	10.5	10.4	10.2	10.1	9.8	9.5	9.2
92.5°	11.5	11.6	11.7	11.8	11.7	11.6	11.5	11.5	11.2	10.7	10.2
95°	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.3	12.7	12.2
97.5°	14.4	14.5	14.6	14.7	14.6	14.5	14.4	14.3	14.0	13.4	12.7
100°	14.7	14.8	14.9	14.9	14.9	14.8	14.7	14.6	14.3	13.6	13.0
102.5°	14.8	14.9	15.1	15.2	15.1	14.9	14.8	14.7	15.7	17.6	19.6
105°	15.2	15.3	15.6	15.7	15.6	15.3	15.2	15.0	22.0	36.1	50.1
107.5°	81.1	70.5	59.9	49.3	59.9	70.5	81.1	91.6	102.1	112.4	122.7
110°	132.2	120.8	109.5	98.2	109.5	120.8	132.2	143.5	150.5	153.1	155.7



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	175.5	173.2	170.8	168.3	170.8	173.2	175.5	177.9	179.2	179.0	179.0
115°	208.8	209.2	209.5	209.8	209.5	209.2	208.8	208.5	208.0	207.2	206.4
117.5°	232.9	233.0	233.1	233.1	233.1	233.0	232.9	232.9	232.5	231.9	231.3
120°	249.1	249.1	249.1	249.1	249.1	249.1	249.1	249.1	248.7	248.1	247.5
122.5°	264.6	264.7	264.7	264.8	264.7	264.7	264.6	264.5	264.3	263.9	263.4
125°	286.4	286.6	286.8	286.9	286.8	286.6	286.4	286.3	286.1	286.0	285.8
127.5°	308.6	308.5	308.3	308.2	308.3	308.5	308.6	308.8	308.8	308.5	308.2
130°	322.3	322.2	322.0	321.8	322.0	322.2	322.3	322.6	322.4	322.1	321.8
132.5°	335.1	334.9	334.7	334.5	334.7	334.9	335.1	335.4	335.3	335.0	334.7
135°	354.4	354.2	353.9	353.7	353.9	354.2	354.4	354.6	354.6	354.4	354.2
137.5°	372.1	372.0	371.8	371.7	371.8	372.0	372.1	372.3	372.2	371.8	371.4
140°	383.0	382.8	382.7	382.5	382.7	382.8	383.0	383.1	383.1	382.7	382.4
142.5°	393.2	392.9	392.7	392.5	392.7	392.9	393.2	393.4	393.4	393.1	392.9
145°	407.9	407.9	407.9	407.9	407.9	407.9	407.9	407.9	407.8	407.7	407.5
147.5°	420.4	420.0	419.7	419.3	419.7	420.0	420.4	420.8	420.9	420.7	420.5
150°	428.6	428.4	428.1	427.9	428.1	428.4	428.6	428.8	428.9	428.7	428.6
152.5°	435.9	435.5	435.0	434.7	435.0	435.5	435.9	436.2	436.3	436.0	435.7
155°	445.8	445.2	444.7	444.2	444.7	445.2	445.8	446.2	446.3	445.9	445.5
157.5°	454.2	453.6	452.9	452.3	452.9	453.6	454.2	454.8	454.9	454.4	453.9
160°	459.2	458.6	458.1	457.5	458.1	458.6	459.2	459.7	459.8	459.3	458.8
162.5°	463.8	463.3	462.8	462.3	462.8	463.3	463.8	464.3	464.2	463.7	463.2
165°	469.9	469.3	468.8	468.2	468.8	469.3	469.9	470.4	470.4	469.8	469.1
167.5°	474.3	473.6	473.0	472.4	473.0	473.6	474.3	474.9	474.9	474.3	473.6
170°	476.9	476.3	475.6	474.9	475.6	476.3	476.9	477.5	477.5	476.9	476.3
172.5°	478.5	477.8	477.1	476.4	477.1	477.8	478.5	479.2	479.2	478.6	478.0
175°	480.5	479.8	479.2	478.6	479.2	479.8	480.5	481.1	481.1	480.6	480.0
177.5°	481.1	480.5	479.8	479.2	479.8	480.5	481.1	481.7	481.8	481.3	480.8
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1769.7	1778.6	1787.5	1795.7	1808.5	1814.1	1822.4	1825.5	1835.1	1849.1	1860.5
5°	1662.0	1674.8	1691.4	1705.0	1726.4	1743.0	1761.3	1778.8	1799.4	1828.8	1854.9
7.5°	1570.7	1583.4	1603.4	1628.4	1652.0	1675.7	1700.6	1724.4	1753.9	1796.0	1837.8
10°	1510.5	1525.5	1549.3	1576.3	1605.7	1628.7	1658.1	1688.3	1724.7	1773.2	1823.2
12.5°	1458.3	1469.7	1497.3	1523.0	1556.2	1585.6	1614.3	1649.5	1691.1	1742.7	1802.8
15°	1375.5	1391.4	1418.4	1446.9	1481.9	1512.9	1550.1	1593.0	1633.5	1697.0	1770.0
17.5°	1292.3	1316.5	1344.5	1376.7	1402.7	1445.3	1485.8	1529.8	1579.6	1647.0	1727.2
20°	1239.0	1258.1	1284.2	1331.1	1365.2	1397.8	1435.0	1489.9	1535.8	1612.0	1695.4
22.5°	1194.0	1207.9	1237.3	1275.9	1315.7	1353.3	1391.2	1443.5	1500.3	1572.7	1663.0
25°	1127.1	1149.3	1171.5	1199.3	1242.1	1287.4	1328.7	1373.1	1433.5	1510.5	1608.1
27.5°	1061.9	1082.0	1103.9	1138.0	1170.5	1212.8	1256.0	1307.0	1371.7	1453.2	1552.2
30°	1020.0	1035.0	1055.6	1099.3	1128.6	1165.2	1216.0	1261.2	1321.5	1408.1	1512.9
32.5°	976.7	996.2	1018.9	1052.3	1088.6	1123.3	1169.6	1218.7	1280.3	1365.5	1472.8
35°	915.1	938.2	961.2	985.8	1022.3	1058.0	1096.9	1150.9	1213.6	1296.2	1401.7
37.5°	858.5	877.1	895.8	926.2	960.9	994.8	1031.2	1084.4	1143.5	1232.5	1329.3
40°	822.3	839.0	853.2	885.0	918.4	954.8	990.6	1037.4	1100.9	1184.3	1277.9
42.5°	782.9	798.3	817.7	843.7	879.6	910.4	946.1	990.4	1050.1	1134.7	1216.9
45°	723.9	741.3	758.0	782.6	818.3	848.5	880.2	922.3	983.4	1053.3	1126.3
47.5°	662.5	679.9	698.9	722.8	753.9	784.6	816.3	853.5	909.3	977.9	1027.0
50°	623.1	637.3	656.4	680.2	708.8	741.3	769.9	810.4	863.5	917.6	960.4
52.5°	582.4	595.4	617.0	642.1	668.8	696.9	727.4	762.1	810.2	861.0	895.0
55°	519.1	534.9	553.2	577.8	604.0	627.8	657.2	693.0	731.0	769.1	792.1
57.5°	459.9	473.0	488.5	513.8	536.5	565.0	591.3	619.1	654.4	683.1	698.1
60°	416.7	428.6	448.5	470.7	492.1	516.7	546.8	574.6	601.7	624.7	636.5
62.5°	376.1	389.9	407.2	427.5	450.8	474.1	500.5	523.8	547.6	567.5	575.6
65°	323.1	334.2	346.9	365.9	385.0	408.8	429.4	453.2	470.7	481.8	489.0
67.5°	274.8	282.1	291.8	304.5	323.2	344.0	364.0	382.5	397.2	404.8	411.1
70°	243.7	248.4	255.6	268.3	282.6	300.8	321.4	335.0	347.7	354.0	360.3
72.5°	212.6	218.6	225.1	235.3	247.0	260.1	275.1	291.8	298.7	306.4	310.2
75°	161.2	169.9	178.5	184.9	192.9	203.2	216.7	227.0	231.0	237.3	238.1
77.5°	121.6	123.5	129.9	137.7	144.4	151.9	160.5	169.7	171.6	174.9	177.0
80°	100.0	100.0	100.0	104.7	112.7	118.3	126.2	131.0	134.1	134.9	135.7
82.5°	80.3	80.3	79.7	80.7	83.5	86.5	93.8	99.2	101.8	101.3	99.6
85°	52.4	50.8	50.8	50.0	50.8	49.2	48.4	51.6	56.4	56.4	54.7
87.5°	23.3	22.6	23.1	22.2	21.4	20.6	18.5	19.0	18.8	21.2	20.4
90°	8.9	8.6	7.6	6.5	5.5	4.4	3.5	2.7	1.9	1.1	0.4
92.5°	9.6	9.1	8.4	7.6	6.8	6.1	5.8	6.0	6.2	6.5	6.7
95°	11.6	11.1	10.2	9.3	8.5	7.6	8.8	12.0	15.2	18.5	21.8
97.5°	12.1	11.5	17.2	22.9	28.6	34.3	37.9	39.4	40.8	42.3	43.7
100°	12.4	11.8	24.1	36.6	48.9	61.3	66.7	65.0	63.5	61.9	60.3
102.5°	21.5	23.5	37.0	50.5	64.0	77.6	83.7	82.6	81.4	80.3	79.2
105°	64.1	78.2	85.3	92.4	99.6	106.7	109.9	109.0	108.1	107.2	106.3
107.5°	132.9	143.2	142.1	141.0	139.9	138.8	137.8	137.1	136.4	135.7	135.0
110°	158.3	161.0	160.1	159.2	158.3	157.4	156.7	156.0	155.4	154.8	154.2



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	178.9	178.9	178.0	177.2	176.3	175.4	174.7	174.1	173.6	173.0	172.4
115°	205.6	204.8	204.1	203.4	202.7	202.0	201.4	200.9	200.5	200.0	199.4
117.5°	230.6	229.9	229.6	229.2	228.8	228.5	228.0	227.4	226.8	226.3	225.7
120°	246.9	246.2	246.0	245.8	245.5	245.3	244.8	244.1	243.4	242.7	242.0
122.5°	263.0	262.5	262.2	261.9	261.6	261.3	260.8	260.2	259.6	259.1	258.5
125°	285.7	285.5	285.2	284.9	284.6	284.2	283.8	283.1	282.5	281.9	281.2
127.5°	308.0	307.7	307.4	307.0	306.6	306.2	305.7	305.1	304.5	303.9	303.2
130°	321.4	321.1	320.8	320.5	320.2	319.9	319.4	318.8	318.1	317.5	316.9
132.5°	334.4	334.1	333.8	333.6	333.3	333.0	332.5	331.9	331.3	330.6	330.0
135°	353.9	353.7	353.4	353.0	352.6	352.3	351.9	351.5	351.0	350.5	350.1
137.5°	371.1	370.7	370.5	370.3	370.2	370.0	369.6	369.0	368.4	367.8	367.2
140°	382.1	381.8	381.6	381.3	381.1	380.9	380.5	380.0	379.6	379.1	378.6
142.5°	392.6	392.4	392.1	391.9	391.7	391.4	391.1	390.6	390.1	389.7	389.2
145°	407.4	407.2	407.0	406.9	406.7	406.6	406.2	405.7	405.1	404.6	403.9
147.5°	420.4	420.2	420.1	419.9	419.8	419.6	419.3	419.0	418.6	418.3	417.9
150°	428.4	428.2	428.1	427.9	427.8	427.6	427.4	427.2	426.9	426.7	426.5
152.5°	435.4	435.0	434.9	434.8	434.7	434.7	434.5	434.4	434.3	434.2	434.1
155°	445.0	444.6	444.5	444.4	444.4	444.3	444.3	444.5	444.6	444.8	445.0
157.5°	453.4	453.0	453.0	453.1	453.2	453.3	453.3	453.3	453.4	453.4	453.4
160°	458.3	457.9	458.0	458.0	458.1	458.2	458.3	458.3	458.4	458.5	458.6
162.5°	462.6	462.1	462.2	462.3	462.3	462.4	462.6	462.8	463.0	463.2	463.4
165°	468.5	467.9	467.9	468.0	468.1	468.2	468.3	468.6	468.8	469.0	469.3
167.5°	473.0	472.4	472.4	472.4	472.4	472.4	472.5	472.9	473.2	473.5	473.8
170°	475.6	474.9	474.9	474.9	474.9	474.9	475.1	475.4	475.7	476.1	476.4
172.5°	477.4	476.7	476.7	476.6	476.5	476.5	476.6	477.0	477.4	477.8	478.1
175°	479.5	478.9	478.8	478.8	478.7	478.6	478.8	479.2	479.5	479.9	480.3
177.5°	480.3	479.8	479.7	479.6	479.6	479.5	479.6	480.0	480.3	480.6	480.9
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1864.3	1871.3	1880.2	1893.5	1903.7	1912.6	1914.5	1917.0	1923.4	1934.1	1942.4
5°	1876.3	1894.6	1924.0	1952.6	1983.5	2008.9	2032.8	2049.4	2065.3	2098.6	2125.6
7.5°	1872.6	1913.2	1959.2	2010.5	2062.4	2112.7	2159.4	2201.1	2242.7	2291.3	2346.7
10°	1870.0	1917.6	1979.5	2045.4	2117.7	2188.3	2256.5	2309.8	2371.7	2427.2	2497.8
12.5°	1857.9	1926.5	2000.5	2084.8	2173.5	2254.9	2344.8	2418.3	2489.1	2569.4	2651.5
15°	1842.2	1925.6	2019.2	2131.1	2266.0	2364.5	2456.6	2584.3	2671.7	2759.0	2876.5
17.5°	1813.5	1915.2	2032.3	2177.7	2290.2	2422.5	2561.0	2662.0	2779.7	2902.7	3009.0
20°	1790.6	1908.9	2039.8	2182.7	2326.4	2470.0	2604.2	2724.8	2846.3	2988.4	3075.6
22.5°	1767.8	1884.8	2020.8	2172.6	2327.0	2478.3	2630.2	2771.9	2908.5	3051.9	3163.3
25°	1719.2	1858.2	2005.7	2160.5	2312.9	2479.6	2660.6	2818.5	2987.6	3135.2	3240.8
27.5°	1670.0	1797.3	1944.3	2101.3	2270.7	2467.7	2680.6	2860.1	3029.5	3135.2	3168.4
30°	1625.6	1760.5	1895.4	2055.0	2238.3	2458.1	2684.3	2889.9	3028.9	3074.8	3040.7
32.5°	1580.4	1702.7	1836.3	1999.7	2194.4	2434.7	2689.5	2872.2	2955.8	2920.6	2781.7
35°	1501.0	1611.2	1740.6	1904.1	2128.0	2421.7	2668.5	2792.3	2771.7	2573.2	2311.3
37.5°	1415.8	1505.7	1625.6	1796.5	2059.1	2370.1	2578.3	2596.6	2418.0	2113.3	1810.8
40°	1348.6	1429.5	1552.6	1731.1	2005.7	2319.3	2487.5	2413.7	2136.7	1797.8	1545.4
42.5°	1283.1	1351.4	1470.0	1662.5	1954.9	2250.1	2352.3	2191.5	1871.9	1551.5	1321.9
45°	1172.4	1236.6	1355.6	1553.3	1851.0	2117.7	2104.2	1824.7	1504.9	1247.0	1056.4
47.5°	1067.2	1123.5	1235.2	1436.9	1728.9	1919.2	1793.0	1495.7	1224.4	1017.4	881.5
50°	992.9	1048.5	1159.6	1358.9	1631.1	1770.0	1589.8	1303.3	1054.9	883.4	775.5
52.5°	921.8	976.1	1077.7	1271.8	1513.0	1596.0	1402.5	1136.9	929.8	781.8	689.1
55°	822.3	863.5	954.8	1140.5	1320.8	1339.8	1143.8	921.5	750.8	647.7	584.2
57.5°	720.8	756.4	846.6	994.5	1120.8	1111.1	925.1	733.0	618.0	541.3	495.2
60°	654.8	689.7	769.1	896.2	991.4	958.1	787.4	632.6	534.2	477.9	441.3
62.5°	593.2	620.6	694.8	787.5	856.1	818.3	673.1	544.9	466.9	419.4	390.5
65°	504.0	526.2	585.7	634.2	672.3	635.8	515.1	426.3	369.9	336.6	316.7
67.5°	419.2	433.3	471.0	488.5	515.3	475.2	387.4	327.8	295.8	267.6	253.9
70°	365.9	376.2	396.1	410.3	417.5	376.2	311.1	267.5	240.4	220.7	212.0
72.5°	312.6	321.6	325.6	337.3	333.7	295.0	250.1	215.4	196.0	182.6	171.3
75°	238.9	242.9	238.9	234.2	223.8	196.8	165.9	148.5	134.1	127.7	123.8
77.5°	174.1	172.9	167.4	160.1	142.4	125.4	108.8	102.9	96.6	93.3	91.9
80°	134.1	131.0	126.2	114.3	99.2	87.4	83.3	79.4	77.0	73.0	72.2
82.5°	99.9	98.0	90.0	80.0	69.4	63.8	60.5	59.1	56.7	54.6	54.4
85°	53.2	50.8	42.1	36.6	34.9	33.3	32.5	32.5	29.4	28.6	28.6
87.5°	17.4	13.7	13.2	11.5	11.7	10.6	11.4	10.4	10.0	10.7	9.5
90°	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.6	8.6	8.9	9.2
92.5°	6.5	6.2	6.0	5.8	6.1	6.8	7.6	8.4	9.1	9.6	10.2
95°	18.5	15.2	12.0	8.8	7.6	8.5	9.3	10.2	11.1	11.6	12.2
97.5°	42.3	40.8	39.4	37.9	34.3	28.6	22.9	17.2	11.5	12.1	12.7
100°	61.9	63.5	65.0	66.7	61.3	48.9	36.6	24.1	11.8	12.4	13.0
102.5°	80.3	81.4	82.6	83.7	77.6	64.0	50.5	37.0	23.5	21.5	19.6
105°	107.2	108.1	109.0	109.9	106.7	99.6	92.4	85.3	78.2	64.1	50.1
107.5°	135.7	136.4	137.1	137.8	138.8	139.9	141.0	142.1	143.2	132.9	122.7
110°	154.8	155.4	156.0	156.7	157.4	158.3	159.2	160.1	161.0	158.3	155.7



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.0	173.6	174.1	174.7	175.4	176.3	177.2	178.0	178.9	178.9	179.0
115°	200.0	200.5	200.9	201.4	202.0	202.7	203.4	204.1	204.8	205.6	206.4
117.5°	226.3	226.8	227.4	228.0	228.5	228.8	229.2	229.6	229.9	230.6	231.3
120°	242.7	243.4	244.1	244.8	245.3	245.5	245.8	246.0	246.2	246.9	247.5
122.5°	259.1	259.6	260.2	260.8	261.3	261.6	261.9	262.2	262.5	263.0	263.4
125°	281.9	282.5	283.1	283.8	284.2	284.6	284.9	285.2	285.5	285.7	285.8
127.5°	303.9	304.5	305.1	305.7	306.2	306.6	307.0	307.4	307.7	308.0	308.2
130°	317.5	318.1	318.8	319.4	319.9	320.2	320.5	320.8	321.1	321.4	321.8
132.5°	330.6	331.3	331.9	332.5	333.0	333.3	333.6	333.8	334.1	334.4	334.7
135°	350.5	351.0	351.5	351.9	352.3	352.6	353.0	353.4	353.7	353.9	354.2
137.5°	367.8	368.4	369.0	369.6	370.0	370.2	370.3	370.5	370.7	371.1	371.4
140°	379.1	379.6	380.0	380.5	380.9	381.1	381.3	381.6	381.8	382.1	382.4
142.5°	389.7	390.1	390.6	391.1	391.4	391.7	391.9	392.1	392.4	392.6	392.9
145°	404.6	405.1	405.7	406.2	406.6	406.7	406.9	407.0	407.2	407.4	407.5
147.5°	418.3	418.6	419.0	419.3	419.6	419.8	419.9	420.1	420.2	420.4	420.5
150°	426.7	426.9	427.2	427.4	427.6	427.8	427.9	428.1	428.2	428.4	428.6
152.5°	434.2	434.3	434.4	434.5	434.7	434.7	434.8	434.9	435.0	435.4	435.7
155°	444.8	444.6	444.5	444.3	444.3	444.4	444.4	444.5	444.6	445.0	445.5
157.5°	453.4	453.4	453.3	453.3	453.3	453.2	453.1	453.0	453.0	453.4	453.9
160°	458.5	458.4	458.3	458.3	458.2	458.1	458.0	458.0	457.9	458.3	458.8
162.5°	463.2	463.0	462.8	462.6	462.4	462.3	462.3	462.2	462.1	462.6	463.2
165°	469.0	468.8	468.6	468.3	468.2	468.1	468.0	467.9	467.9	468.5	469.1
167.5°	473.5	473.2	472.9	472.5	472.4	472.4	472.4	472.4	472.4	473.0	473.6
170°	476.1	475.7	475.4	475.1	474.9	474.9	474.9	474.9	474.9	475.6	476.3
172.5°	477.8	477.4	477.0	476.6	476.5	476.5	476.6	476.7	476.7	477.4	478.0
175°	479.9	479.5	479.2	478.8	478.6	478.7	478.8	478.8	478.9	479.5	480.0
177.5°	480.6	480.3	480.0	479.6	479.5	479.6	479.6	479.7	479.8	480.3	480.8
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1955.7	1955.7	1958.2	1967.8	1969.0	1977.3	1974.8
5°	2149.4	2164.4	2170.0	2193.8	2208.2	2214.5	2201.8
7.5°	2386.2	2428.8	2448.9	2473.9	2496.0	2502.6	2485.3
10°	2559.0	2603.4	2640.7	2663.7	2685.1	2699.5	2717.7
12.5°	2725.9	2780.6	2816.0	2848.5	2870.5	2888.7	2891.6
15°	2907.4	2989.9	3052.6	3098.7	3121.7	3133.6	3128.9
17.5°	3090.4	3166.9	3211.6	3258.5	3290.4	3292.1	3293.0
20°	3193.9	3268.5	3320.1	3355.1	3390.8	3389.2	3397.1
22.5°	3263.2	3321.8	3361.4	3386.8	3399.0	3393.0	3394.6
25°	3295.5	3313.0	3305.9	3265.4	3255.1	3217.7	3224.1
27.5°	3128.6	3046.0	2960.6	2850.7	2764.1	2694.8	2698.4
30°	2901.8	2755.8	2589.1	2449.4	2324.0	2289.1	2214.5
32.5°	2585.0	2365.9	2170.7	2040.5	1932.9	1903.7	1838.6
35°	2047.8	1835.1	1634.3	1513.6	1466.0	1399.4	1398.6
37.5°	1591.7	1404.4	1298.2	1207.7	1160.2	1119.9	1116.0
40°	1339.0	1193.0	1112.8	1047.7	1000.9	970.7	963.6
42.5°	1162.5	1044.4	969.3	929.0	892.9	877.4	865.8
45°	949.3	869.9	817.5	781.0	764.4	752.5	746.1
47.5°	794.1	740.8	705.2	680.9	667.3	654.8	658.1
50°	709.6	665.9	639.7	616.7	606.4	597.6	598.4
52.5°	641.7	602.5	581.3	564.6	551.8	545.6	542.6
55°	544.5	519.9	498.5	486.6	479.4	470.7	468.3
57.5°	464.4	445.5	428.0	414.4	412.7	404.3	405.5
60°	411.1	395.3	381.0	373.9	368.3	361.1	363.6
62.5°	367.3	354.0	341.0	335.1	329.5	324.3	325.4
65°	300.8	288.1	280.1	277.0	274.6	272.3	269.8
67.5°	239.7	232.0	227.0	220.2	215.3	214.5	212.1
70°	201.6	191.3	182.6	173.8	171.5	170.7	171.5
72.5°	161.6	155.1	152.7	148.5	147.9	145.9	147.3
75°	121.5	119.1	117.4	114.3	114.3	114.3	114.3
77.5°	89.6	88.1	87.2	86.5	85.7	84.6	84.4
80°	69.9	69.1	67.5	67.5	66.7	67.5	66.7
82.5°	52.7	52.5	51.0	51.0	50.2	49.7	50.2
85°	27.0	26.2	27.8	26.2	27.0	25.4	27.0
87.5°	9.5	9.6	9.0	9.0	8.4	9.7	8.5
90°	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.7	11.2	11.5	11.5	11.6	11.7	11.8
95°	12.7	13.3	13.5	13.5	13.5	13.5	13.5
97.5°	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.6	14.3	14.6	14.7	14.8	14.9	14.9
102.5°	17.6	15.7	14.7	14.8	14.9	15.1	15.2
105°	36.1	22.0	15.0	15.2	15.3	15.6	15.7
107.5°	112.4	102.1	91.6	81.1	70.5	59.9	49.3
110°	153.1	150.5	143.5	132.2	120.8	109.5	98.2



TEST NUMBER: P332360-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	179.0	179.2	177.9	175.5	173.2	170.8	168.3
115°	207.2	208.0	208.5	208.8	209.2	209.5	209.8
117.5°	231.9	232.5	232.9	232.9	233.0	233.1	233.1
120°	248.1	248.7	249.1	249.1	249.1	249.1	249.1
122.5°	263.9	264.3	264.5	264.6	264.7	264.7	264.8
125°	286.0	286.1	286.3	286.4	286.6	286.8	286.9
127.5°	308.5	308.8	308.8	308.6	308.5	308.3	308.2
130°	322.1	322.4	322.6	322.3	322.2	322.0	321.8
132.5°	335.0	335.3	335.4	335.1	334.9	334.7	334.5
135°	354.4	354.6	354.6	354.4	354.2	353.9	353.7
137.5°	371.8	372.2	372.3	372.1	372.0	371.8	371.7
140°	382.7	383.1	383.1	383.0	382.8	382.7	382.5
142.5°	393.1	393.4	393.4	393.2	392.9	392.7	392.5
145°	407.7	407.8	407.9	407.9	407.9	407.9	407.9
147.5°	420.7	420.9	420.8	420.4	420.0	419.7	419.3
150°	428.7	428.9	428.8	428.6	428.4	428.1	427.9
152.5°	436.0	436.3	436.2	435.9	435.5	435.0	434.7
155°	445.9	446.3	446.2	445.8	445.2	444.7	444.2
157.5°	454.4	454.9	454.8	454.2	453.6	452.9	452.3
160°	459.3	459.8	459.7	459.2	458.6	458.1	457.5
162.5°	463.7	464.2	464.3	463.8	463.3	462.8	462.3
165°	469.8	470.4	470.4	469.9	469.3	468.8	468.2
167.5°	474.3	474.9	474.9	474.3	473.6	473.0	472.4
170°	476.9	477.5	477.5	476.9	476.3	475.6	474.9
172.5°	478.6	479.2	479.2	478.5	477.8	477.1	476.4
175°	480.6	481.1	481.1	480.5	479.8	479.2	478.6
177.5°	481.3	481.8	481.7	481.1	480.5	479.8	479.2
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3

(END OF REPORT)