

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332264

Luminaire Tested: **S123RDIP-S340D1195U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332264  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1195U835-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6128.3 lumens  
Efficiency: N/A  
Efficacy: 145.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	101	101	101	101	89	89	89	89	68	68	68	48	48	48	31	31	31	22																				
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26	19																				
2	84	77	71	66	74	68	64	60	53	49	47	38	36	34	24	23	22	16																				
3	76	68	61	55	68	60	55	50	46	43	39	34	31	29	22	20	19	14																				
4	70	60	53	47	62	53	47	42	41	37	34	30	27	25	20	18	17	12																				
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11																				
6	59	48	40	35	52	43	36	32	33	29	25	24	21	19	16	14	13	10																				
7	55	43	36	30	48	39	32	28	30	26	22	22	19	17	15	13	12	9																				
8	50	39	32	27	45	35	29	24	27	23	20	20	17	15	14	12	10	8																				
9	47	35	28	24	42	32	26	21	25	21	17	19	16	13	13	11	9	7																				
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5858	5858	5858	5858
5°	6983	5883	5181	5883
10°	8719	5850	4680	5850
15°	10234	5789	4268	5789
20°	11423	5700	3918	5700
25°	11240	5606	3702	5606
30°	8079	5520	3480	5520
35°	5394	5406	3336	5406
40°	3974	5271	3188	5271
45°	3334	5033	3043	5033
50°	2942	4721	2840	4721
55°	2580	4363	2562	4363
60°	2297	4021	2347	4021
65°	2017	3655	2183	3655
70°	1583	3330	1995	3330
75°	1393	2907	1822	2907
80°	1215	2467	1791	2467
85°	976	1988	1902	1988



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.5	0.9
10°-20°	167.2	2.7
20°-30°	262.7	4.3
30°-40°	274.1	4.5
40°-50°	234.5	3.8
50°-60°	178.8	2.9
60°-70°	114.6	1.9
70°-80°	55.1	0.9
80°-90°	19.0	0.3
90°-100°	56.9	0.9
100°-110°	271.0	4.4
110°-120°	650.9	10.6
120°-130°	828.8	13.5
130°-140°	885.6	14.5
140°-150°	828.1	13.5
150°-160°	668.0	10.9
160°-170°	431.1	7.0
170°-180°	148.6	2.4
0°-30°	483.4	7.9
0°-40°	757.5	12.4
0°-60°	1170.8	19.1
0°-90°	1359.4	22.2
90°-120°	978.7	16.0
90°-150°	3521.2	57.5
90°-180°	4769.0	77.8
0°-180°	6128.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	544	544	544	544	544	
5°	646	544	480	544	646	67
15°	918	520	383	520	918	260
25°	946	472	312	472	946	407
35°	410	411	254	411	410	269
45°	219	331	200	331	219	172
55°	138	232	136	232	138	124
65°	79	144	86	144	79	78
75°	34	70	44	70	34	36
85°	8	16	15	16	8	10
90°	35	1	35	1	35	16
95°	44	71	44	71	44	37
105°	51	346	51	346	51	117
115°	683	650	683	650	683	631
125°	934	916	934	916	934	834
135°	1151	1140	1151	1140	1151	888
145°	1328	1315	1328	1315	1328	829
155°	1446	1449	1446	1449	1446	667
165°	1524	1528	1524	1528	1524	430
175°	1558	1564	1558	1564	1558	148
180°	1564	1564	1564	1564	1564	



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	579.7	580.4	578.0	577.6	574.8	574.1	574.1	570.1	567.7	564.6	562.7
5°	646.3	650.0	648.1	644.0	637.0	635.3	630.9	623.9	616.0	606.2	601.6
7.5°	729.5	734.6	732.6	726.2	718.8	712.9	700.4	688.8	672.6	658.3	646.1
10°	797.7	792.4	788.2	781.9	775.1	764.2	751.1	733.2	712.5	696.1	678.0
12.5°	848.8	847.9	842.6	836.1	826.6	816.2	800.1	778.3	754.2	730.6	709.8
15°	918.4	919.8	916.3	909.6	896.0	877.6	853.4	844.3	809.8	784.2	758.6
17.5°	966.6	966.3	965.8	956.5	942.7	929.6	907.1	883.2	852.0	815.9	781.4
20°	997.2	994.8	995.3	984.8	974.6	959.4	937.5	902.8	877.2	835.5	799.8
22.5°	996.4	995.9	997.7	994.1	986.7	975.1	957.8	928.5	895.8	853.7	813.6
25°	946.4	944.5	955.4	958.5	970.4	972.5	967.3	951.3	920.3	876.9	827.3
27.5°	792.0	791.0	811.3	836.8	869.0	894.1	918.3	930.0	920.3	889.2	839.5
30°	650.0	671.9	682.2	719.0	760.0	808.9	851.8	892.5	902.6	889.0	848.3
32.5°	539.7	558.8	567.4	598.9	637.2	694.5	758.8	816.5	857.3	867.6	843.1
35°	410.5	410.7	430.3	444.3	479.7	538.6	601.1	678.4	755.3	813.6	819.6
37.5°	327.6	328.7	340.6	354.5	381.1	412.2	467.2	531.5	620.3	709.7	762.2
40°	282.8	284.9	293.8	307.5	326.6	350.2	393.0	453.6	527.7	627.2	708.5
42.5°	254.1	257.5	262.1	272.7	284.5	306.6	341.2	388.0	455.4	549.5	643.3
45°	219.0	220.9	224.4	229.3	240.0	255.3	278.6	310.1	366.0	441.7	535.6
47.5°	193.2	192.2	195.9	199.8	207.0	217.5	233.1	258.7	298.6	359.4	439.0
50°	175.7	175.4	178.0	181.0	187.8	195.5	208.3	227.6	259.3	309.6	382.6
52.5°	159.3	160.1	162.0	165.7	170.6	176.8	188.3	202.3	229.5	272.9	333.7
55°	137.5	138.2	140.7	142.8	146.3	152.6	159.8	171.5	190.1	220.4	270.5
57.5°	119.0	118.7	121.1	121.7	125.6	130.7	136.3	145.4	158.9	181.4	215.1
60°	106.7	106.0	108.1	109.7	111.8	116.0	120.7	129.5	140.3	156.8	185.7
62.5°	95.5	95.2	96.7	98.4	100.1	103.9	107.8	114.6	123.1	137.0	160.0
65°	79.2	79.9	80.6	81.3	82.2	84.6	88.3	93.0	98.8	108.6	125.1
67.5°	62.3	63.0	63.2	64.6	66.6	68.1	70.4	74.5	78.6	86.8	96.2
70°	50.3	50.1	50.3	51.0	53.6	56.1	59.2	62.2	64.8	70.6	78.5
72.5°	43.2	42.8	43.4	43.6	44.8	45.5	47.4	50.3	53.6	57.5	63.2
75°	33.5	33.5	33.5	33.5	34.5	34.9	35.6	36.3	37.5	39.4	43.6
77.5°	24.8	24.8	25.2	25.4	25.6	25.9	26.3	27.0	27.4	28.4	30.2
80°	19.6	19.8	19.6	19.8	19.8	20.3	20.5	21.2	21.4	22.6	23.3
82.5°	14.7	14.6	14.7	15.0	15.0	15.4	15.5	16.0	16.0	16.6	17.3
85°	7.9	7.5	7.9	7.7	8.2	7.7	7.9	8.4	8.4	8.6	9.6
87.5°	8.8	9.1	8.6	8.7	8.6	8.6	8.4	8.2	8.4	8.0	7.5
90°	34.9	34.3	33.8	33.3	32.8	32.0	31.0	29.9	28.9	27.9	24.5
92.5°	38.6	38.3	38.0	37.6	37.3	36.4	34.7	33.0	31.4	29.7	27.2
95°	44.1	44.1	44.1	44.1	44.1	43.2	41.4	39.6	37.8	36.0	33.2
97.5°	47.9	47.6	47.4	47.1	46.8	45.7	43.6	41.5	39.5	37.4	35.0
100°	48.8	48.5	48.3	48.0	47.8	46.6	44.5	42.5	40.4	38.3	35.6
102.5°	49.7	49.3	48.8	48.3	47.9	50.8	57.2	63.6	70.0	76.4	120.4
105°	51.1	50.6	50.1	49.6	49.1	71.6	117.3	163.0	208.7	254.4	277.7
107.5°	160.6	195.0	229.4	263.9	298.3	332.3	365.8	399.3	432.8	466.4	462.7
110°	319.5	356.4	393.3	430.3	467.2	489.9	498.4	506.9	515.5	524.0	521.1



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	548.1	555.9	563.7	571.5	579.3	583.2	583.0	582.8	582.7	582.5	579.7
115°	683.1	682.1	681.1	680.0	679.0	677.2	674.6	672.0	669.5	666.9	664.6
117.5°	758.9	758.7	758.5	758.3	758.1	756.9	754.9	752.8	750.7	748.7	747.5
120°	810.9	810.9	810.9	810.9	810.9	809.9	807.8	805.8	803.7	801.6	800.9
122.5°	862.1	861.9	861.6	861.4	861.2	860.4	859.0	857.5	856.1	854.6	853.6
125°	934.1	933.6	933.1	932.5	932.0	931.5	931.0	930.5	930.0	929.4	928.4
127.5°	1003.3	1003.9	1004.4	1004.9	1005.4	1005.2	1004.4	1003.6	1002.8	1001.9	1000.7
130°	1048.0	1048.5	1049.0	1049.5	1050.0	1049.8	1048.7	1047.7	1046.7	1045.6	1044.6
132.5°	1088.8	1089.6	1090.3	1091.0	1091.7	1091.6	1090.6	1089.5	1088.5	1087.5	1086.6
135°	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4	1150.3
137.5°	1210.1	1210.7	1211.2	1211.7	1212.2	1211.8	1210.6	1209.4	1208.1	1206.9	1206.3
140°	1245.5	1246.0	1246.5	1247.0	1247.5	1247.3	1246.2	1245.2	1244.2	1243.1	1242.4
142.5°	1278.0	1278.7	1279.4	1280.2	1280.9	1280.8	1280.0	1279.2	1278.4	1277.5	1276.8
145°	1327.9	1327.9	1327.9	1327.9	1327.9	1327.7	1327.2	1326.7	1326.1	1325.6	1325.1
147.5°	1365.1	1366.3	1367.5	1368.7	1369.9	1370.2	1369.7	1369.2	1368.7	1368.1	1367.6
150°	1393.0	1393.8	1394.6	1395.3	1396.1	1396.2	1395.7	1395.2	1394.7	1394.2	1393.7
152.5°	1415.3	1416.5	1417.7	1418.9	1420.1	1420.2	1419.3	1418.3	1417.4	1416.5	1416.2
155°	1446.5	1448.0	1449.6	1451.1	1452.6	1452.8	1451.5	1450.2	1448.9	1447.6	1447.4
157.5°	1472.7	1474.7	1476.7	1478.8	1480.8	1481.0	1479.4	1477.9	1476.4	1474.8	1475.1
160°	1489.4	1491.2	1493.1	1494.9	1496.7	1496.8	1495.2	1493.7	1492.2	1490.6	1490.9
162.5°	1505.2	1506.8	1508.4	1510.0	1511.6	1511.6	1509.8	1508.1	1506.3	1504.5	1504.8
165°	1524.3	1526.1	1527.9	1529.7	1531.5	1531.4	1529.3	1527.3	1525.2	1523.1	1523.4
167.5°	1538.0	1540.1	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0	1538.0
170°	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4	1546.4
172.5°	1551.0	1553.3	1555.6	1557.8	1560.1	1560.2	1558.1	1556.1	1554.0	1551.9	1551.7
175°	1558.0	1560.1	1562.1	1564.2	1566.2	1566.4	1564.6	1562.8	1561.0	1559.1	1558.9
177.5°	1560.1	1562.1	1564.2	1566.3	1568.3	1568.5	1566.9	1565.2	1563.6	1561.9	1561.7
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	561.9	561.4	558.8	555.8	551.9	549.3	547.2	546.1	542.7	538.6	535.9
5°	596.7	589.7	582.2	573.1	564.7	556.1	550.8	544.5	536.8	528.2	522.1
7.5°	633.8	620.1	605.4	590.1	575.1	561.6	549.6	539.4	527.2	514.8	506.2
10°	662.4	642.3	621.6	600.4	581.1	562.9	548.9	535.2	520.5	506.3	495.5
12.5°	688.3	661.9	638.0	611.9	587.2	565.5	545.4	529.2	511.5	496.4	484.2
15°	721.1	694.0	665.2	625.5	592.7	565.2	540.7	519.5	498.1	479.5	467.6
17.5°	751.7	711.1	672.2	639.2	596.5	562.2	532.3	507.0	483.4	463.7	449.0
20°	764.4	725.0	682.9	640.7	598.8	560.3	525.6	497.6	473.2	450.8	437.3
22.5°	772.0	727.5	683.0	637.7	593.2	553.2	518.9	488.1	461.6	440.4	423.7
25°	780.9	727.8	678.9	634.2	588.7	545.4	504.6	472.0	443.4	420.8	403.1
27.5°	786.8	724.3	666.5	616.8	570.7	527.6	490.2	455.6	426.5	402.6	383.6
30°	787.9	721.5	657.0	603.2	556.4	516.7	477.1	444.1	413.3	387.9	370.2
32.5°	789.4	714.6	644.1	587.0	539.0	499.8	463.9	432.3	400.8	375.8	357.7
35°	783.3	710.8	624.6	558.9	510.9	472.9	440.6	411.4	380.5	356.2	337.8
37.5°	756.8	695.7	604.4	527.3	477.1	442.0	415.6	390.2	361.8	335.6	318.3
40°	730.2	680.8	588.7	508.1	455.7	419.6	395.8	375.1	347.6	323.1	304.5
42.5°	690.5	660.4	573.8	488.0	431.5	396.7	376.6	357.2	333.1	308.2	290.7
45°	617.6	621.6	543.3	455.9	397.9	363.0	344.1	330.6	309.2	288.7	270.7
47.5°	526.3	563.3	507.5	421.8	362.6	329.8	313.3	301.5	287.0	266.9	250.5
50°	466.7	519.5	478.8	398.9	340.4	307.8	291.5	281.9	269.3	253.5	237.9
52.5°	411.7	468.5	444.1	373.3	316.3	286.5	270.6	262.7	252.7	237.8	223.7
55°	335.7	393.3	387.7	334.8	280.3	253.5	241.4	232.5	225.8	214.6	203.4
57.5°	271.6	326.1	329.0	291.9	248.5	222.0	211.6	204.9	200.5	192.1	181.7
60°	231.1	281.2	291.0	263.0	225.8	202.5	192.2	186.8	183.4	176.6	168.7
62.5°	197.6	240.2	251.3	231.2	204.0	182.1	174.1	169.0	166.6	160.8	153.8
65°	151.2	186.6	197.3	186.2	171.9	154.5	147.9	143.5	141.4	138.2	133.0
67.5°	113.7	139.5	151.3	143.4	138.2	127.2	123.1	120.7	118.8	116.6	112.3
70°	91.3	110.4	122.5	120.5	116.3	110.4	107.4	105.8	103.9	102.0	98.3
72.5°	73.4	86.6	97.9	99.0	95.6	94.4	91.7	91.0	89.9	87.7	85.6
75°	48.7	57.8	65.7	68.7	70.1	71.3	70.1	69.9	69.7	67.8	66.6
77.5°	31.9	36.8	41.8	47.0	49.2	50.7	51.1	52.0	51.3	50.4	49.8
80°	24.5	25.6	29.1	33.5	37.0	38.4	39.4	39.8	39.6	39.4	38.4
82.5°	17.8	18.7	20.4	23.5	26.4	28.7	29.3	29.2	29.7	29.9	29.1
85°	9.6	9.8	10.3	10.7	12.3	14.9	15.6	16.1	16.5	16.5	15.1
87.5°	7.2	6.4	6.1	5.5	5.5	5.2	5.8	6.2	6.9	6.7	7.2
90°	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2	3.7	6.3	8.9
92.5°	24.7	22.2	19.6	18.7	19.4	20.2	20.9	21.6	20.9	20.2	19.4
95°	30.3	27.5	24.7	28.5	39.1	49.7	60.3	70.9	60.3	49.7	39.1
97.5°	74.6	93.2	111.8	123.4	128.2	132.9	137.7	142.4	137.7	132.9	128.2
100°	118.9	159.2	199.4	217.0	211.8	206.7	201.5	196.3	201.5	206.7	211.8
102.5°	164.4	208.4	252.4	272.6	268.8	265.1	261.4	257.7	261.4	265.1	268.8
105°	300.9	324.1	347.4	357.6	354.7	351.9	349.1	346.2	349.1	351.9	354.7
107.5°	459.0	455.4	451.7	448.7	446.4	444.2	441.9	439.6	441.9	444.2	446.4
110°	518.3	515.5	512.6	510.2	508.1	506.0	504.0	501.9	504.0	506.0	508.1





TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	576.9	574.0	571.2	568.8	567.0	565.1	563.2	561.4	563.2	565.1	567.0
115°	662.2	659.9	657.6	655.6	654.1	652.5	651.0	649.5	651.0	652.5	654.1
117.5°	746.3	745.1	743.9	742.4	740.5	738.5	736.6	734.7	736.6	738.5	740.5
120°	800.1	799.3	798.6	797.0	794.7	792.4	790.0	787.7	790.0	792.4	794.7
122.5°	852.7	851.7	850.7	849.3	847.3	845.4	843.5	841.6	843.5	845.4	847.3
125°	927.4	926.3	925.3	923.8	921.7	919.6	917.6	915.5	917.6	919.6	921.7
127.5°	999.5	998.2	997.0	995.3	993.3	991.2	989.1	987.1	989.1	991.2	993.3
130°	1043.6	1042.5	1041.5	1039.9	1037.9	1035.8	1033.8	1031.7	1033.8	1035.8	1037.9
132.5°	1085.8	1085.0	1084.1	1082.7	1080.6	1078.6	1076.5	1074.4	1076.5	1078.6	1080.6
135°	1149.3	1148.3	1147.2	1145.9	1144.4	1142.8	1141.3	1139.7	1141.3	1142.8	1144.4
137.5°	1205.8	1205.2	1204.6	1203.4	1201.4	1199.4	1197.5	1195.5	1197.5	1199.4	1201.4
140°	1241.6	1240.8	1240.0	1238.9	1237.3	1235.8	1234.2	1232.7	1234.2	1235.8	1237.3
142.5°	1276.0	1275.2	1274.4	1273.3	1271.7	1270.2	1268.6	1267.1	1268.6	1270.2	1271.7
145°	1324.6	1324.1	1323.6	1322.4	1320.6	1318.8	1317.0	1315.2	1317.0	1318.8	1320.6
147.5°	1367.1	1366.6	1366.1	1365.2	1364.0	1362.9	1361.7	1360.5	1361.7	1362.9	1364.0
150°	1393.1	1392.6	1392.1	1391.5	1390.7	1389.9	1389.1	1388.4	1389.1	1389.9	1390.7
152.5°	1415.9	1415.5	1415.2	1414.9	1414.5	1414.2	1413.8	1413.5	1413.8	1414.2	1414.5
155°	1447.1	1446.8	1446.6	1446.7	1447.2	1447.7	1448.3	1448.8	1448.3	1447.7	1447.2
157.5°	1475.3	1475.6	1475.8	1476.0	1476.0	1476.1	1476.1	1476.2	1476.1	1476.1	1476.0
160°	1491.1	1491.4	1491.6	1491.9	1492.2	1492.4	1492.7	1492.9	1492.7	1492.4	1492.2
162.5°	1505.1	1505.3	1505.6	1506.0	1506.7	1507.4	1508.1	1508.7	1508.1	1507.4	1506.7
165°	1523.6	1523.9	1524.2	1524.7	1525.5	1526.2	1527.0	1527.8	1527.0	1526.2	1525.5
167.5°	1538.0	1538.0	1538.0	1538.5	1539.6	1540.6	1541.6	1542.7	1541.6	1540.6	1539.6
170°	1546.4	1546.4	1546.4	1546.9	1547.9	1549.0	1550.0	1551.0	1550.0	1549.0	1547.9
172.5°	1551.5	1551.3	1551.1	1551.6	1552.9	1554.1	1555.4	1556.6	1555.4	1554.1	1552.9
175°	1558.6	1558.4	1558.1	1558.6	1559.9	1561.2	1562.5	1563.8	1562.5	1561.2	1559.9
177.5°	1561.5	1561.3	1561.1	1561.5	1562.6	1563.6	1564.6	1565.7	1564.6	1563.6	1562.6
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	534.9	532.5	530.8	527.1	524.7	522.1	519.5	521.1	520.9	520.8	520.8
5°	517.0	511.6	506.7	500.4	496.5	491.6	487.9	487.4	488.3	485.1	483.2
7.5°	499.2	491.9	484.9	478.0	470.6	464.7	461.1	459.3	457.0	455.0	452.9
10°	486.7	478.1	471.3	462.7	454.8	447.8	443.4	440.3	438.7	437.1	434.0
12.5°	473.8	465.4	456.8	447.0	439.5	431.4	428.1	424.7	421.6	419.7	415.6
15°	455.0	444.1	435.0	424.7	416.3	408.4	403.8	397.0	396.1	393.7	389.5
17.5°	436.1	424.3	411.7	404.1	394.7	386.4	379.3	377.1	370.4	367.9	364.2
20°	421.2	410.3	400.7	390.7	377.0	369.3	363.7	360.7	355.3	352.0	349.7
22.5°	408.4	397.2	386.2	374.5	363.2	354.5	350.4	345.7	342.8	338.2	335.7
25°	390.0	377.9	364.6	352.0	343.9	337.4	330.8	326.6	322.4	320.3	315.7
27.5°	368.7	356.0	343.6	334.0	324.0	317.6	311.7	308.0	302.9	299.4	296.8
30°	356.9	342.0	331.3	322.7	309.9	303.8	299.4	294.7	291.0	287.3	284.7
32.5°	343.3	329.7	319.6	308.9	299.1	292.4	286.7	282.6	279.4	275.9	273.3
35°	322.0	310.6	300.1	289.4	282.1	275.4	268.6	265.1	262.1	258.8	256.5
37.5°	302.7	292.0	282.0	271.9	262.9	257.4	252.0	249.3	245.2	243.0	240.7
40°	290.8	280.3	269.6	259.8	250.5	246.3	241.4	237.4	233.7	232.0	229.5
42.5°	277.7	267.2	258.2	247.7	240.0	234.3	229.8	225.5	222.7	220.3	218.9
45°	258.4	249.1	240.2	229.7	222.5	217.6	212.5	208.5	206.0	204.3	201.8
47.5°	239.6	230.3	221.3	212.2	205.2	199.6	194.4	191.7	188.3	186.3	184.6
50°	226.0	217.6	208.1	199.7	192.7	187.1	182.9	179.4	176.4	173.8	172.6
52.5°	213.5	204.6	196.3	188.5	181.1	174.8	171.0	167.3	165.0	162.1	160.7
55°	192.9	184.3	177.3	169.6	162.4	157.0	152.4	149.1	146.8	143.5	141.7
57.5°	173.6	165.8	157.5	150.8	143.4	138.9	135.0	130.6	127.7	125.2	123.3
60°	160.5	151.7	144.4	138.2	131.6	125.8	122.3	118.8	115.8	113.2	111.6
62.5°	146.9	139.2	132.3	125.5	119.5	114.4	110.4	107.5	104.8	103.2	101.5
65°	126.0	120.0	113.0	107.4	101.8	98.1	94.8	92.3	90.4	89.2	87.8
67.5°	106.8	101.0	94.9	89.4	85.6	82.8	80.7	78.5	77.5	76.0	75.1
70°	94.4	88.3	82.9	78.7	75.0	72.9	71.5	69.9	69.0	67.1	66.2
72.5°	80.8	76.4	72.5	69.1	66.1	64.2	62.4	60.4	58.9	56.8	55.9
75°	63.6	59.6	56.6	54.3	52.4	49.9	47.3	45.2	44.5	43.8	43.6
77.5°	47.1	44.6	42.4	40.4	38.1	36.3	35.7	35.2	35.1	34.7	34.7
80°	37.0	34.7	33.1	30.8	29.4	29.4	29.4	28.9	29.1	29.1	29.1
82.5°	27.5	25.4	24.5	23.7	23.4	23.6	23.6	23.7	23.5	23.9	23.7
85°	14.2	14.4	14.9	14.7	14.9	14.9	15.4	15.1	15.4	14.9	15.4
87.5°	7.5	8.7	9.5	10.4	11.2	11.7	12.1	12.3	12.7	12.9	13.1
90°	11.5	14.5	17.8	21.2	24.5	27.9	28.9	29.9	31.0	32.0	32.8
92.5°	18.7	19.6	22.2	24.7	27.2	29.7	31.4	33.0	34.7	36.4	37.3
95°	28.5	24.7	27.5	30.3	33.2	36.0	37.8	39.6	41.4	43.2	44.1
97.5°	123.4	111.8	93.2	74.6	56.0	37.4	39.5	41.5	43.6	45.7	46.8
100°	217.0	199.4	159.2	118.9	78.6	38.3	40.4	42.5	44.5	46.6	47.8
102.5°	272.6	252.4	208.4	164.4	120.4	76.4	70.0	63.6	57.2	50.8	47.9
105°	357.6	347.4	324.1	300.9	277.7	254.4	208.7	163.0	117.3	71.6	49.1
107.5°	448.7	451.7	455.4	459.0	462.7	466.4	432.8	399.3	365.8	332.3	298.3
110°	510.2	512.6	515.5	518.3	521.1	524.0	515.5	506.9	498.4	489.9	467.2



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	568.8	571.2	574.0	576.9	579.7	582.5	582.7	582.8	583.0	583.2	579.3
115°	655.6	657.6	659.9	662.2	664.6	666.9	669.5	672.0	674.6	677.2	679.0
117.5°	742.4	743.9	745.1	746.3	747.5	748.7	750.7	752.8	754.9	756.9	758.1
120°	797.0	798.6	799.3	800.1	800.9	801.6	803.7	805.8	807.8	809.9	810.9
122.5°	849.3	850.7	851.7	852.7	853.6	854.6	856.1	857.5	859.0	860.4	861.2
125°	923.8	925.3	926.3	927.4	928.4	929.4	930.0	930.5	931.0	931.5	932.0
127.5°	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8	1003.6	1004.4	1005.2	1005.4
130°	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7	1047.7	1048.7	1049.8	1050.0
132.5°	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5	1089.5	1090.6	1091.6	1091.7
135°	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5
137.5°	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1	1209.4	1210.6	1211.8	1212.2
140°	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2	1245.2	1246.2	1247.3	1247.5
142.5°	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4	1279.2	1280.0	1280.8	1280.9
145°	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1	1326.7	1327.2	1327.7	1327.9
147.5°	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7	1369.2	1369.7	1370.2	1369.9
150°	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7	1395.2	1395.7	1396.2	1396.1
152.5°	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4	1418.3	1419.3	1420.2	1420.1
155°	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9	1450.2	1451.5	1452.8	1452.6
157.5°	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4	1477.9	1479.4	1481.0	1480.8
160°	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2	1493.7	1495.2	1496.8	1496.7
162.5°	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3	1508.1	1509.8	1511.6	1511.6
165°	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2	1527.3	1529.3	1531.4	1531.5
167.5°	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1	1542.1	1544.2	1546.3	1546.3
170°	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6
172.5°	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0	1556.1	1558.1	1560.2	1560.1
175°	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0	1562.8	1564.6	1566.4	1566.2
177.5°	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6	1565.2	1566.9	1568.5	1568.3
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	518.5	518.3	518.5	517.8	518.5	518.3	518.5	520.8	520.8	520.9	521.1
5°	482.5	482.3	481.6	479.5	481.6	482.3	482.5	483.2	485.1	488.3	487.4
7.5°	451.0	450.7	448.7	448.7	448.7	450.7	451.0	452.9	455.0	457.0	459.3
10°	432.4	432.6	429.8	428.2	429.8	432.6	432.4	434.0	437.1	438.7	440.3
12.5°	414.3	413.3	411.0	409.2	411.0	413.3	414.3	415.6	419.7	421.6	424.7
15°	390.5	388.1	382.6	383.0	382.6	388.1	390.5	389.5	393.7	396.1	397.0
17.5°	362.4	360.7	360.6	357.3	360.6	360.7	362.4	364.2	367.9	370.4	377.1
20°	346.0	344.8	345.3	342.0	345.3	344.8	346.0	349.7	352.0	355.3	360.7
22.5°	333.1	331.9	330.0	329.0	330.0	331.9	333.1	335.7	338.2	342.8	345.7
25°	314.3	312.4	310.6	311.7	310.6	312.4	314.3	315.7	320.3	322.4	326.6
27.5°	295.5	294.1	292.2	292.0	292.2	294.1	295.5	296.8	299.4	302.9	308.0
30°	283.5	282.1	281.2	280.0	281.2	282.1	283.5	284.7	287.3	291.0	294.7
32.5°	271.4	271.1	269.5	269.2	269.5	271.1	271.4	273.3	275.9	279.4	282.6
35°	255.6	254.2	253.7	253.9	253.7	254.2	255.6	256.5	258.8	262.1	265.1
37.5°	240.5	238.7	237.8	237.0	237.8	238.7	240.5	240.7	243.0	245.2	249.3
40°	229.7	227.9	227.4	226.9	227.4	227.9	229.7	229.5	232.0	233.7	237.4
42.5°	217.6	216.9	216.6	215.7	216.6	216.9	217.6	218.9	220.3	222.7	225.5
45°	201.1	200.8	199.4	199.9	199.4	200.8	201.1	201.8	204.3	206.0	208.5
47.5°	183.6	182.6	181.6	182.3	181.6	182.6	183.6	184.6	186.3	188.3	191.7
50°	171.7	171.2	169.1	169.6	169.1	171.2	171.7	172.6	173.8	176.4	179.4
52.5°	159.8	158.0	157.2	156.9	157.2	158.0	159.8	160.7	162.1	165.0	167.3
55°	140.0	137.9	137.0	136.5	137.0	137.9	140.0	141.7	143.5	146.8	149.1
57.5°	120.6	120.1	119.3	119.8	119.3	120.1	120.6	123.3	125.2	127.7	130.6
60°	109.3	109.3	109.3	109.0	109.3	109.3	109.3	111.6	113.2	115.8	118.8
62.5°	100.5	99.9	99.8	100.1	99.8	99.9	100.5	101.5	103.2	104.8	107.5
65°	87.1	86.9	86.0	85.7	86.0	86.9	87.1	87.8	89.2	90.4	92.3
67.5°	74.5	73.7	73.4	73.1	73.4	73.7	74.5	75.1	76.0	77.5	78.5
70°	65.0	64.5	63.1	63.4	63.1	64.5	65.0	66.2	67.1	69.0	69.9
72.5°	54.8	54.3	54.0	53.7	54.0	54.3	54.8	55.9	56.8	58.9	60.4
75°	43.3	43.1	42.9	43.8	42.9	43.1	43.3	43.6	43.8	44.5	45.2
77.5°	34.7	34.7	34.9	34.5	34.9	34.7	34.7	34.7	34.7	35.1	35.2
80°	29.1	29.1	28.9	28.9	28.9	29.1	29.1	29.1	29.1	29.1	28.9
82.5°	23.3	23.5	23.7	23.3	23.7	23.5	23.3	23.7	23.9	23.5	23.7
85°	15.4	15.1	15.6	15.4	15.6	15.1	15.4	15.4	14.9	15.4	15.1
87.5°	13.6	13.3	13.4	13.7	13.4	13.3	13.6	13.1	12.9	12.7	12.3
90°	33.3	33.8	34.3	34.9	34.3	33.8	33.3	32.8	32.0	31.0	29.9
92.5°	37.6	38.0	38.3	38.6	38.3	38.0	37.6	37.3	36.4	34.7	33.0
95°	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1	43.2	41.4	39.6
97.5°	47.1	47.4	47.6	47.9	47.6	47.4	47.1	46.8	45.7	43.6	41.5
100°	48.0	48.3	48.5	48.8	48.5	48.3	48.0	47.8	46.6	44.5	42.5
102.5°	48.3	48.8	49.3	49.7	49.3	48.8	48.3	47.9	50.8	57.2	63.6
105°	49.6	50.1	50.6	51.1	50.6	50.1	49.6	49.1	71.6	117.3	163.0
107.5°	263.9	229.4	195.0	160.6	195.0	229.4	263.9	298.3	332.3	365.8	399.3
110°	430.3	393.3	356.4	319.5	356.4	393.3	430.3	467.2	489.9	498.4	506.9



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	571.5	563.7	555.9	548.1	555.9	563.7	571.5	579.3	583.2	583.0	582.8
115°	680.0	681.1	682.1	683.1	682.1	681.1	680.0	679.0	677.2	674.6	672.0
117.5°	758.3	758.5	758.7	758.9	758.7	758.5	758.3	758.1	756.9	754.9	752.8
120°	810.9	810.9	810.9	810.9	810.9	810.9	810.9	810.9	809.9	807.8	805.8
122.5°	861.4	861.6	861.9	862.1	861.9	861.6	861.4	861.2	860.4	859.0	857.5
125°	932.5	933.1	933.6	934.1	933.6	933.1	932.5	932.0	931.5	931.0	930.5
127.5°	1004.9	1004.4	1003.9	1003.3	1003.9	1004.4	1004.9	1005.4	1005.2	1004.4	1003.6
130°	1049.5	1049.0	1048.5	1048.0	1048.5	1049.0	1049.5	1050.0	1049.8	1048.7	1047.7
132.5°	1091.0	1090.3	1089.6	1088.8	1089.6	1090.3	1091.0	1091.7	1091.6	1090.6	1089.5
135°	1153.7	1152.9	1152.1	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9
137.5°	1211.7	1211.2	1210.7	1210.1	1210.7	1211.2	1211.7	1212.2	1211.8	1210.6	1209.4
140°	1247.0	1246.5	1246.0	1245.5	1246.0	1246.5	1247.0	1247.5	1247.3	1246.2	1245.2
142.5°	1280.2	1279.4	1278.7	1278.0	1278.7	1279.4	1280.2	1280.9	1280.8	1280.0	1279.2
145°	1327.9	1327.9	1327.9	1327.9	1327.9	1327.9	1327.9	1327.9	1327.7	1327.2	1326.7
147.5°	1368.7	1367.5	1366.3	1365.1	1366.3	1367.5	1368.7	1369.9	1370.2	1369.7	1369.2
150°	1395.3	1394.6	1393.8	1393.0	1393.8	1394.6	1395.3	1396.1	1396.2	1395.7	1395.2
152.5°	1418.9	1417.7	1416.5	1415.3	1416.5	1417.7	1418.9	1420.1	1420.2	1419.3	1418.3
155°	1451.1	1449.6	1448.0	1446.5	1448.0	1449.6	1451.1	1452.6	1452.8	1451.5	1450.2
157.5°	1478.8	1476.7	1474.7	1472.7	1474.7	1476.7	1478.8	1480.8	1481.0	1479.4	1477.9
160°	1494.9	1493.1	1491.2	1489.4	1491.2	1493.1	1494.9	1496.7	1496.8	1495.2	1493.7
162.5°	1510.0	1508.4	1506.8	1505.2	1506.8	1508.4	1510.0	1511.6	1511.6	1509.8	1508.1
165°	1529.7	1527.9	1526.1	1524.3	1526.1	1527.9	1529.7	1531.5	1531.4	1529.3	1527.3
167.5°	1544.2	1542.1	1540.1	1538.0	1540.1	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1
170°	1552.6	1550.5	1548.4	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5
172.5°	1557.8	1555.6	1553.3	1551.0	1553.3	1555.6	1557.8	1560.1	1560.2	1558.1	1556.1
175°	1564.2	1562.1	1560.1	1558.0	1560.1	1562.1	1564.2	1566.2	1566.4	1564.6	1562.8
177.5°	1566.3	1564.2	1562.1	1560.1	1562.1	1564.2	1566.3	1568.3	1568.5	1566.9	1565.2
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	519.5	522.1	524.7	527.1	530.8	532.5	534.9	535.9	538.6	542.7	546.1
5°	487.9	491.6	496.5	500.4	506.7	511.6	517.0	522.1	528.2	536.8	544.5
7.5°	461.1	464.7	470.6	478.0	484.9	491.9	499.2	506.2	514.8	527.2	539.4
10°	443.4	447.8	454.8	462.7	471.3	478.1	486.7	495.5	506.3	520.5	535.2
12.5°	428.1	431.4	439.5	447.0	456.8	465.4	473.8	484.2	496.4	511.5	529.2
15°	403.8	408.4	416.3	424.7	435.0	444.1	455.0	467.6	479.5	498.1	519.5
17.5°	379.3	386.4	394.7	404.1	411.7	424.3	436.1	449.0	463.7	483.4	507.0
20°	363.7	369.3	377.0	390.7	400.7	410.3	421.2	437.3	450.8	473.2	497.6
22.5°	350.4	354.5	363.2	374.5	386.2	397.2	408.4	423.7	440.4	461.6	488.1
25°	330.8	337.4	343.9	352.0	364.6	377.9	390.0	403.1	420.8	443.4	472.0
27.5°	311.7	317.6	324.0	334.0	343.6	356.0	368.7	383.6	402.6	426.5	455.6
30°	299.4	303.8	309.9	322.7	331.3	342.0	356.9	370.2	387.9	413.3	444.1
32.5°	286.7	292.4	299.1	308.9	319.6	329.7	343.3	357.7	375.8	400.8	432.3
35°	268.6	275.4	282.1	289.4	300.1	310.6	322.0	337.8	356.2	380.5	411.4
37.5°	252.0	257.4	262.9	271.9	282.0	292.0	302.7	318.3	335.6	361.8	390.2
40°	241.4	246.3	250.5	259.8	269.6	280.3	290.8	304.5	323.1	347.6	375.1
42.5°	229.8	234.3	240.0	247.7	258.2	267.2	277.7	290.7	308.2	333.1	357.2
45°	212.5	217.6	222.5	229.7	240.2	249.1	258.4	270.7	288.7	309.2	330.6
47.5°	194.4	199.6	205.2	212.2	221.3	230.3	239.6	250.5	266.9	287.0	301.5
50°	182.9	187.1	192.7	199.7	208.1	217.6	226.0	237.9	253.5	269.3	281.9
52.5°	171.0	174.8	181.1	188.5	196.3	204.6	213.5	223.7	237.8	252.7	262.7
55°	152.4	157.0	162.4	169.6	177.3	184.3	192.9	203.4	214.6	225.8	232.5
57.5°	135.0	138.9	143.4	150.8	157.5	165.8	173.6	181.7	192.1	200.5	204.9
60°	122.3	125.8	131.6	138.2	144.4	151.7	160.5	168.7	176.6	183.4	186.8
62.5°	110.4	114.4	119.5	125.5	132.3	139.2	146.9	153.8	160.8	166.6	169.0
65°	94.8	98.1	101.8	107.4	113.0	120.0	126.0	133.0	138.2	141.4	143.5
67.5°	80.7	82.8	85.6	89.4	94.9	101.0	106.8	112.3	116.6	118.8	120.7
70°	71.5	72.9	75.0	78.7	82.9	88.3	94.4	98.3	102.0	103.9	105.8
72.5°	62.4	64.2	66.1	69.1	72.5	76.4	80.8	85.6	87.7	89.9	91.0
75°	47.3	49.9	52.4	54.3	56.6	59.6	63.6	66.6	67.8	69.7	69.9
77.5°	35.7	36.3	38.1	40.4	42.4	44.6	47.1	49.8	50.4	51.3	52.0
80°	29.4	29.4	29.4	30.8	33.1	34.7	37.0	38.4	39.4	39.6	39.8
82.5°	23.6	23.6	23.4	23.7	24.5	25.4	27.5	29.1	29.9	29.7	29.2
85°	15.4	14.9	14.9	14.7	14.9	14.4	14.2	15.1	16.5	16.5	16.1
87.5°	12.1	11.7	11.2	10.4	9.5	8.7	7.5	7.2	6.7	6.9	6.2
90°	28.9	27.9	24.5	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2
92.5°	31.4	29.7	27.2	24.7	22.2	19.6	18.7	19.4	20.2	20.9	21.6
95°	37.8	36.0	33.2	30.3	27.5	24.7	28.5	39.1	49.7	60.3	70.9
97.5°	39.5	37.4	56.0	74.6	93.2	111.8	123.4	128.2	132.9	137.7	142.4
100°	40.4	38.3	78.6	118.9	159.2	199.4	217.0	211.8	206.7	201.5	196.3
102.5°	70.0	76.4	120.4	164.4	208.4	252.4	272.6	268.8	265.1	261.4	257.7
105°	208.7	254.4	277.7	300.9	324.1	347.4	357.6	354.7	351.9	349.1	346.2
107.5°	432.8	466.4	462.7	459.0	455.4	451.7	448.7	446.4	444.2	441.9	439.6
110°	515.5	524.0	521.1	518.3	515.5	512.6	510.2	508.1	506.0	504.0	501.9



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	582.7	582.5	579.7	576.9	574.0	571.2	568.8	567.0	565.1	563.2	561.4
115°	669.5	666.9	664.6	662.2	659.9	657.6	655.6	654.1	652.5	651.0	649.5
117.5°	750.7	748.7	747.5	746.3	745.1	743.9	742.4	740.5	738.5	736.6	734.7
120°	803.7	801.6	800.9	800.1	799.3	798.6	797.0	794.7	792.4	790.0	787.7
122.5°	856.1	854.6	853.6	852.7	851.7	850.7	849.3	847.3	845.4	843.5	841.6
125°	930.0	929.4	928.4	927.4	926.3	925.3	923.8	921.7	919.6	917.6	915.5
127.5°	1002.8	1001.9	1000.7	999.5	998.2	997.0	995.3	993.3	991.2	989.1	987.1
130°	1046.7	1045.6	1044.6	1043.6	1042.5	1041.5	1039.9	1037.9	1035.8	1033.8	1031.7
132.5°	1088.5	1087.5	1086.6	1085.8	1085.0	1084.1	1082.7	1080.6	1078.6	1076.5	1074.4
135°	1152.1	1151.4	1150.3	1149.3	1148.3	1147.2	1145.9	1144.4	1142.8	1141.3	1139.7
137.5°	1208.1	1206.9	1206.3	1205.8	1205.2	1204.6	1203.4	1201.4	1199.4	1197.5	1195.5
140°	1244.2	1243.1	1242.4	1241.6	1240.8	1240.0	1238.9	1237.3	1235.8	1234.2	1232.7
142.5°	1278.4	1277.5	1276.8	1276.0	1275.2	1274.4	1273.3	1271.7	1270.2	1268.6	1267.1
145°	1326.1	1325.6	1325.1	1324.6	1324.1	1323.6	1322.4	1320.6	1318.8	1317.0	1315.2
147.5°	1368.7	1368.1	1367.6	1367.1	1366.6	1366.1	1365.2	1364.0	1362.9	1361.7	1360.5
150°	1394.7	1394.2	1393.7	1393.1	1392.6	1392.1	1391.5	1390.7	1389.9	1389.1	1388.4
152.5°	1417.4	1416.5	1416.2	1415.9	1415.5	1415.2	1414.9	1414.5	1414.2	1413.8	1413.5
155°	1448.9	1447.6	1447.4	1447.1	1446.8	1446.6	1446.7	1447.2	1447.7	1448.3	1448.8
157.5°	1476.4	1474.8	1475.1	1475.3	1475.6	1475.8	1476.0	1476.0	1476.1	1476.1	1476.2
160°	1492.2	1490.6	1490.9	1491.1	1491.4	1491.6	1491.9	1492.2	1492.4	1492.7	1492.9
162.5°	1506.3	1504.5	1504.8	1505.1	1505.3	1505.6	1506.0	1506.7	1507.4	1508.1	1508.7
165°	1525.2	1523.1	1523.4	1523.6	1523.9	1524.2	1524.7	1525.5	1526.2	1527.0	1527.8
167.5°	1540.1	1538.0	1538.0	1538.0	1538.0	1538.0	1538.5	1539.6	1540.6	1541.6	1542.7
170°	1548.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.9	1547.9	1549.0	1550.0	1551.0
172.5°	1554.0	1551.9	1551.7	1551.5	1551.3	1551.1	1551.6	1552.9	1554.1	1555.4	1556.6
175°	1561.0	1559.1	1558.9	1558.6	1558.4	1558.1	1558.6	1559.9	1561.2	1562.5	1563.8
177.5°	1563.6	1561.9	1561.7	1561.5	1561.3	1561.1	1561.5	1562.6	1563.6	1564.6	1565.7
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	547.2	549.3	551.9	555.8	558.8	561.4	561.9	562.7	564.6	567.7	570.1
5°	550.8	556.1	564.7	573.1	582.2	589.7	596.7	601.6	606.2	616.0	623.9
7.5°	549.6	561.6	575.1	590.1	605.4	620.1	633.8	646.1	658.3	672.6	688.8
10°	548.9	562.9	581.1	600.4	621.6	642.3	662.4	678.0	696.1	712.5	733.2
12.5°	545.4	565.5	587.2	611.9	638.0	661.9	688.3	709.8	730.6	754.2	778.3
15°	540.7	565.2	592.7	625.5	665.2	694.0	721.1	758.6	784.2	809.8	844.3
17.5°	532.3	562.2	596.5	639.2	672.2	711.1	751.7	781.4	815.9	852.0	883.2
20°	525.6	560.3	598.8	640.7	682.9	725.0	764.4	799.8	835.5	877.2	902.8
22.5°	518.9	553.2	593.2	637.7	683.0	727.5	772.0	813.6	853.7	895.8	928.5
25°	504.6	545.4	588.7	634.2	678.9	727.8	780.9	827.3	876.9	920.3	951.3
27.5°	490.2	527.6	570.7	616.8	666.5	724.3	786.8	839.5	889.2	920.3	930.0
30°	477.1	516.7	556.4	603.2	657.0	721.5	787.9	848.3	889.0	902.6	892.5
32.5°	463.9	499.8	539.0	587.0	644.1	714.6	789.4	843.1	867.6	857.3	816.5
35°	440.6	472.9	510.9	558.9	624.6	710.8	783.3	819.6	813.6	755.3	678.4
37.5°	415.6	442.0	477.1	527.3	604.4	695.7	756.8	762.2	709.7	620.3	531.5
40°	395.8	419.6	455.7	508.1	588.7	680.8	730.2	708.5	627.2	527.7	453.6
42.5°	376.6	396.7	431.5	488.0	573.8	660.4	690.5	643.3	549.5	455.4	388.0
45°	344.1	363.0	397.9	455.9	543.3	621.6	617.6	535.6	441.7	366.0	310.1
47.5°	313.3	329.8	362.6	421.8	507.5	563.3	526.3	439.0	359.4	298.6	258.7
50°	291.5	307.8	340.4	398.9	478.8	519.5	466.7	382.6	309.6	259.3	227.6
52.5°	270.6	286.5	316.3	373.3	444.1	468.5	411.7	333.7	272.9	229.5	202.3
55°	241.4	253.5	280.3	334.8	387.7	393.3	335.7	270.5	220.4	190.1	171.5
57.5°	211.6	222.0	248.5	291.9	329.0	326.1	271.6	215.1	181.4	158.9	145.4
60°	192.2	202.5	225.8	263.0	291.0	281.2	231.1	185.7	156.8	140.3	129.5
62.5°	174.1	182.1	204.0	231.2	251.3	240.2	197.6	160.0	137.0	123.1	114.6
65°	147.9	154.5	171.9	186.2	197.3	186.6	151.2	125.1	108.6	98.8	93.0
67.5°	123.1	127.2	138.2	143.4	151.3	139.5	113.7	96.2	86.8	78.6	74.5
70°	107.4	110.4	116.3	120.5	122.5	110.4	91.3	78.5	70.6	64.8	62.2
72.5°	91.7	94.4	95.6	99.0	97.9	86.6	73.4	63.2	57.5	53.6	50.3
75°	70.1	71.3	70.1	68.7	65.7	57.8	48.7	43.6	39.4	37.5	36.3
77.5°	51.1	50.7	49.2	47.0	41.8	36.8	31.9	30.2	28.4	27.4	27.0
80°	39.4	38.4	37.0	33.5	29.1	25.6	24.5	23.3	22.6	21.4	21.2
82.5°	29.3	28.7	26.4	23.5	20.4	18.7	17.8	17.3	16.6	16.0	16.0
85°	15.6	14.9	12.3	10.7	10.3	9.8	9.6	9.6	8.6	8.4	8.4
87.5°	5.8	5.2	5.5	5.5	6.1	6.4	7.2	7.5	8.0	8.4	8.2
90°	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9	29.9
92.5°	20.9	20.2	19.4	18.7	19.6	22.2	24.7	27.2	29.7	31.4	33.0
95°	60.3	49.7	39.1	28.5	24.7	27.5	30.3	33.2	36.0	37.8	39.6
97.5°	137.7	132.9	128.2	123.4	111.8	93.2	74.6	56.0	37.4	39.5	41.5
100°	201.5	206.7	211.8	217.0	199.4	159.2	118.9	78.6	38.3	40.4	42.5
102.5°	261.4	265.1	268.8	272.6	252.4	208.4	164.4	120.4	76.4	70.0	63.6
105°	349.1	351.9	354.7	357.6	347.4	324.1	300.9	277.7	254.4	208.7	163.0
107.5°	441.9	444.2	446.4	448.7	451.7	455.4	459.0	462.7	466.4	432.8	399.3
110°	504.0	506.0	508.1	510.2	512.6	515.5	518.3	521.1	524.0	515.5	506.9





TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	563.2	565.1	567.0	568.8	571.2	574.0	576.9	579.7	582.5	582.7	582.8
115°	651.0	652.5	654.1	655.6	657.6	659.9	662.2	664.6	666.9	669.5	672.0
117.5°	736.6	738.5	740.5	742.4	743.9	745.1	746.3	747.5	748.7	750.7	752.8
120°	790.0	792.4	794.7	797.0	798.6	799.3	800.1	800.9	801.6	803.7	805.8
122.5°	843.5	845.4	847.3	849.3	850.7	851.7	852.7	853.6	854.6	856.1	857.5
125°	917.6	919.6	921.7	923.8	925.3	926.3	927.4	928.4	929.4	930.0	930.5
127.5°	989.1	991.2	993.3	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8	1003.6
130°	1033.8	1035.8	1037.9	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7	1047.7
132.5°	1076.5	1078.6	1080.6	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5	1089.5
135°	1141.3	1142.8	1144.4	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1	1152.9
137.5°	1197.5	1199.4	1201.4	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1	1209.4
140°	1234.2	1235.8	1237.3	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2	1245.2
142.5°	1268.6	1270.2	1271.7	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4	1279.2
145°	1317.0	1318.8	1320.6	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1	1326.7
147.5°	1361.7	1362.9	1364.0	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7	1369.2
150°	1389.1	1389.9	1390.7	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7	1395.2
152.5°	1413.8	1414.2	1414.5	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4	1418.3
155°	1448.3	1447.7	1447.2	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9	1450.2
157.5°	1476.1	1476.1	1476.0	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4	1477.9
160°	1492.7	1492.4	1492.2	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2	1493.7
162.5°	1508.1	1507.4	1506.7	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3	1508.1
165°	1527.0	1526.2	1525.5	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2	1527.3
167.5°	1541.6	1540.6	1539.6	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1	1542.1
170°	1550.0	1549.0	1547.9	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4	1550.5
172.5°	1555.4	1554.1	1552.9	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0	1556.1
175°	1562.5	1561.2	1559.9	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0	1562.8
177.5°	1564.6	1563.6	1562.6	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6	1565.2
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	574.1	574.1	574.8	577.6	578.0	580.4	579.7
5°	630.9	635.3	637.0	644.0	648.1	650.0	646.3
7.5°	700.4	712.9	718.8	726.2	732.6	734.6	729.5
10°	751.1	764.2	775.1	781.9	788.2	792.4	797.7
12.5°	800.1	816.2	826.6	836.1	842.6	847.9	848.8
15°	853.4	877.6	896.0	909.6	916.3	919.8	918.4
17.5°	907.1	929.6	942.7	956.5	965.8	966.3	966.6
20°	937.5	959.4	974.6	984.8	995.3	994.8	997.2
22.5°	957.8	975.1	986.7	994.1	997.7	995.9	996.4
25°	967.3	972.5	970.4	958.5	955.4	944.5	946.4
27.5°	918.3	894.1	869.0	836.8	811.3	791.0	792.0
30°	851.8	808.9	760.0	719.0	682.2	671.9	650.0
32.5°	758.8	694.5	637.2	598.9	567.4	558.8	539.7
35°	601.1	538.6	479.7	444.3	430.3	410.7	410.5
37.5°	467.2	412.2	381.1	354.5	340.6	328.7	327.6
40°	393.0	350.2	326.6	307.5	293.8	284.9	282.8
42.5°	341.2	306.6	284.5	272.7	262.1	257.5	254.1
45°	278.6	255.3	240.0	229.3	224.4	220.9	219.0
47.5°	233.1	217.5	207.0	199.8	195.9	192.2	193.2
50°	208.3	195.5	187.8	181.0	178.0	175.4	175.7
52.5°	188.3	176.8	170.6	165.7	162.0	160.1	159.3
55°	159.8	152.6	146.3	142.8	140.7	138.2	137.5
57.5°	136.3	130.7	125.6	121.7	121.1	118.7	119.0
60°	120.7	116.0	111.8	109.7	108.1	106.0	106.7
62.5°	107.8	103.9	100.1	98.4	96.7	95.2	95.5
65°	88.3	84.6	82.2	81.3	80.6	79.9	79.2
67.5°	70.4	68.1	66.6	64.6	63.2	63.0	62.3
70°	59.2	56.1	53.6	51.0	50.3	50.1	50.3
72.5°	47.4	45.5	44.8	43.6	43.4	42.8	43.2
75°	35.6	34.9	34.5	33.5	33.5	33.5	33.5
77.5°	26.3	25.9	25.6	25.4	25.2	24.8	24.8
80°	20.5	20.3	19.8	19.8	19.6	19.8	19.6
82.5°	15.5	15.4	15.0	15.0	14.7	14.6	14.7
85°	7.9	7.7	8.2	7.7	7.9	7.5	7.9
87.5°	8.4	8.6	8.6	8.7	8.6	9.1	8.8
90°	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	34.7	36.4	37.3	37.6	38.0	38.3	38.6
95°	41.4	43.2	44.1	44.1	44.1	44.1	44.1
97.5°	43.6	45.7	46.8	47.1	47.4	47.6	47.9
100°	44.5	46.6	47.8	48.0	48.3	48.5	48.8
102.5°	57.2	50.8	47.9	48.3	48.8	49.3	49.7
105°	117.3	71.6	49.1	49.6	50.1	50.6	51.1
107.5°	365.8	332.3	298.3	263.9	229.4	195.0	160.6
110°	498.4	489.9	467.2	430.3	393.3	356.4	319.5



TEST NUMBER: P332264

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	583.0	583.2	579.3	571.5	563.7	555.9	548.1
115°	674.6	677.2	679.0	680.0	681.1	682.1	683.1
117.5°	754.9	756.9	758.1	758.3	758.5	758.7	758.9
120°	807.8	809.9	810.9	810.9	810.9	810.9	810.9
122.5°	859.0	860.4	861.2	861.4	861.6	861.9	862.1
125°	931.0	931.5	932.0	932.5	933.1	933.6	934.1
127.5°	1004.4	1005.2	1005.4	1004.9	1004.4	1003.9	1003.3
130°	1048.7	1049.8	1050.0	1049.5	1049.0	1048.5	1048.0
132.5°	1090.6	1091.6	1091.7	1091.0	1090.3	1089.6	1088.8
135°	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4
137.5°	1210.6	1211.8	1212.2	1211.7	1211.2	1210.7	1210.1
140°	1246.2	1247.3	1247.5	1247.0	1246.5	1246.0	1245.5
142.5°	1280.0	1280.8	1280.9	1280.2	1279.4	1278.7	1278.0
145°	1327.2	1327.7	1327.9	1327.9	1327.9	1327.9	1327.9
147.5°	1369.7	1370.2	1369.9	1368.7	1367.5	1366.3	1365.1
150°	1395.7	1396.2	1396.1	1395.3	1394.6	1393.8	1393.0
152.5°	1419.3	1420.2	1420.1	1418.9	1417.7	1416.5	1415.3
155°	1451.5	1452.8	1452.6	1451.1	1449.6	1448.0	1446.5
157.5°	1479.4	1481.0	1480.8	1478.8	1476.7	1474.7	1472.7
160°	1495.2	1496.8	1496.7	1494.9	1493.1	1491.2	1489.4
162.5°	1509.8	1511.6	1511.6	1510.0	1508.4	1506.8	1505.2
165°	1529.3	1531.4	1531.5	1529.7	1527.9	1526.1	1524.3
167.5°	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0
170°	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4
172.5°	1558.1	1560.2	1560.1	1557.8	1555.6	1553.3	1551.0
175°	1564.6	1566.4	1566.2	1564.2	1562.1	1560.1	1558.0
177.5°	1566.9	1568.5	1568.3	1566.3	1564.2	1562.1	1560.1
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8

(END OF REPORT)