

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332269

Luminaire Tested: **S123RDIP-S340D1195U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332269  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1195U835-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5620.5 lumens  
Efficiency: N/A  
Efficacy: 133.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332269

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332269

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	64	60	53	49	47	38	36	34	25	24	23	17
3	76	68	61	55	68	60	54	50	47	43	39	34	31	29	22	21	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6184	6184	6184
5°	6207	6122	6158
10°	6172	6045	6025
15°	6107	5904	5841
20°	6015	5727	5593
25°	5922	5529	5352
30°	5797	5299	5009
35°	5670	5070	4696
40°	5552	4799	4308
45°	5398	4532	3958
50°	5228	4228	3565
55°	5054	3883	3200
60°	4895	3511	2799
65°	4689	3110	2397
70°	4428	2609	1936
75°	4051	2054	1822
80°	3608	1822	1674
85°	3051	1606	1494



TEST NUMBER: P332269

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.0	1.0
10°-20°	150.1	2.7
20°-30°	216.1	3.8
30°-40°	243.5	4.3
40°-50°	232.9	4.1
50°-60°	190.7	3.4
60°-70°	128.7	2.3
70°-80°	64.7	1.2
80°-90°	21.6	0.4
90°-100°	319.4	5.7
100°-110°	904.4	16.1
110°-120°	889.7	15.8
120°-130°	709.7	12.6
130°-140°	559.5	10.0
140°-150°	417.6	7.4
150°-160°	291.1	5.2
160°-170°	171.0	3.0
170°-180°	55.6	1.0
0°-30°	420.2	7.5
0°-40°	663.7	11.8
0°-60°	1087.3	19.3
0°-90°	1302.3	23.2
90°-120°	2113.6	37.6
90°-150°	3800.4	67.6
90°-180°	4318.0	76.8
0°-180°	5620.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	574	574	574	574	574	
5°	574	572	567	570	570	54
15°	548	542	530	527	524	154
25°	499	486	466	456	451	229
35°	432	414	386	366	357	270
45°	355	333	298	272	260	273
55°	269	246	207	181	170	241
65°	184	158	122	100	94	182
75°	97	75	49	45	44	104
85°	25	15	13	12	12	28
90°	2	14	29	33	34	4
95°	40	128	689	201	135	43
105°	135	199	934	1634	1478	143
115°	238	297	714	1567	1797	236
125°	331	391	667	1208	1418	294
135°	388	463	658	995	1149	300
145°	443	507	650	816	898	277
155°	503	543	629	715	745	231
165°	550	565	602	638	650	155
175°	573	573	577	586	584	54
180°	574	574	574	574	574	



TEST NUMBER: P332269

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	576.4	576.0	575.7	575.4	575.1	574.4	573.4	572.4	571.4	570.4	571.3
5°	574.5	574.0	573.5	573.0	572.4	571.6	570.3	569.1	567.8	566.6	567.5
7.5°	569.2	568.6	568.1	567.5	567.0	565.9	564.3	562.7	561.0	559.4	559.9
10°	564.7	564.0	563.3	562.6	561.8	560.5	558.7	556.8	554.9	553.1	553.2
12.5°	558.4	557.6	556.8	556.0	555.2	553.6	551.3	549.1	546.8	544.5	544.4
15°	548.0	546.8	545.7	544.5	543.4	541.4	538.5	535.6	532.7	529.8	529.3
17.5°	534.8	533.5	532.2	530.8	529.5	527.0	523.3	519.6	516.0	512.3	511.2
20°	525.1	523.5	521.8	520.2	518.5	515.7	511.8	507.8	503.9	500.0	498.6
22.5°	514.3	512.4	510.5	508.6	506.7	503.7	499.5	495.3	491.1	486.9	485.2
25°	498.6	496.0	493.4	490.8	488.2	484.5	479.8	475.0	470.2	465.5	463.3
27.5°	479.5	476.6	473.7	470.9	468.0	464.0	458.7	453.3	448.0	442.7	439.7
30°	466.4	463.3	460.2	457.1	454.0	449.5	443.7	437.9	432.1	426.3	422.8
32.5°	453.4	449.8	446.3	442.8	439.3	434.5	428.3	422.2	416.1	409.9	406.1
35°	431.5	427.7	424.0	420.3	416.6	411.5	405.1	398.6	392.2	385.8	381.4
37.5°	409.3	405.1	401.0	396.9	392.7	387.2	380.4	373.5	366.7	359.8	354.8
40°	395.1	390.6	386.0	381.5	376.9	370.9	363.6	356.2	348.9	341.5	336.2
42.5°	379.1	374.5	370.0	365.4	360.9	354.8	347.2	339.6	332.0	324.4	318.5
45°	354.6	349.9	345.3	340.6	335.9	329.6	321.7	313.7	305.7	297.7	291.8
47.5°	330.1	325.0	319.8	314.7	309.6	303.1	295.1	287.1	279.2	271.2	264.8
50°	312.2	307.3	302.5	297.6	292.7	286.1	277.7	269.3	260.9	252.5	246.1
52.5°	296.2	290.9	285.6	280.3	275.0	268.2	259.9	251.6	243.3	235.0	228.4
55°	269.3	264.2	259.2	254.1	249.0	242.1	233.3	224.5	215.7	206.9	200.9
57.5°	244.5	239.0	233.5	227.9	222.4	215.2	206.4	197.5	188.7	179.9	174.2
60°	227.4	221.7	216.0	210.3	204.6	197.5	188.9	180.3	171.7	163.1	157.5
62.5°	210.2	204.5	198.8	193.2	187.5	180.3	171.7	163.1	154.5	145.9	140.7
65°	184.1	178.4	172.7	167.0	161.3	154.4	146.3	138.2	130.2	122.1	117.0
67.5°	157.9	152.1	146.3	140.6	134.8	128.1	120.3	112.6	104.8	97.1	93.3
70°	140.7	135.1	129.5	123.9	118.4	111.9	104.7	97.4	90.2	82.9	79.3
72.5°	123.6	118.1	112.6	107.0	101.5	95.5	88.9	82.3	75.7	69.1	66.2
75°	97.4	92.4	87.4	82.5	77.5	72.2	66.5	60.8	55.1	49.4	48.4
77.5°	73.5	69.0	64.5	60.0	55.6	51.5	47.8	44.1	40.5	36.8	36.3
80°	58.2	54.0	49.8	45.5	41.3	38.1	35.9	33.7	31.5	29.4	29.0
82.5°	43.7	40.0	36.4	32.7	29.0	26.7	25.7	24.7	23.7	22.6	22.3
85°	24.7	22.4	20.1	17.9	15.6	14.3	14.0	13.7	13.4	13.0	12.8
87.5°	9.4	9.0	8.5	8.3	7.9	7.9	8.6	9.3	10.0	10.7	10.3
90°	2.3	4.6	7.0	10.5	12.8	15.1	18.6	22.1	25.6	29.0	27.9
92.5°	14.4	21.4	31.1	40.2	50.0	67.2	97.6	147.6	196.6	178.7	134.8
95°	39.5	43.0	55.8	75.5	105.7	151.0	249.8	422.9	613.5	689.0	558.8
97.5°	67.4	68.5	78.5	95.7	125.5	174.5	268.9	464.0	781.7	1067.7	1142.3
100°	86.0	87.1	95.3	111.5	139.4	184.7	266.1	438.0	743.6	1100.3	1329.2
102.5°	105.5	107.6	114.8	130.1	155.2	196.8	269.8	415.7	687.8	1039.9	1338.4
105°	134.8	138.3	145.2	159.2	181.2	217.3	280.0	399.7	619.3	934.1	1267.6
107.5°	165.9	169.4	176.1	189.8	210.5	244.0	299.1	398.5	575.6	840.7	1143.5
110°	188.2	191.7	197.5	210.3	230.0	262.6	314.9	403.2	558.8	787.7	1065.4



TEST NUMBER: P332269

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	208.7	212.2	218.0	230.7	250.5	282.1	330.7	412.5	549.6	752.4	997.6
115°	238.2	242.8	249.8	261.4	281.2	312.5	356.7	427.6	546.1	714.5	915.5
117.5°	267.7	273.0	278.8	289.5	311.6	340.7	384.3	447.5	548.2	692.2	866.0
120°	288.1	291.6	297.4	309.1	331.1	360.2	402.0	462.4	551.9	682.0	840.0
122.5°	305.8	309.3	315.1	327.6	348.8	379.7	420.6	476.4	558.4	675.5	818.6
125°	331.1	333.5	340.4	353.2	375.3	406.6	447.3	498.4	568.1	666.9	791.2
127.5°	350.4	353.9	362.5	375.5	399.9	431.3	470.5	516.6	579.3	662.7	767.1
130°	362.5	366.0	376.4	390.4	414.8	446.1	484.5	528.6	586.7	659.9	754.0
132.5°	371.8	376.2	387.6	404.3	428.7	459.2	496.6	539.8	592.3	659.0	742.0
135°	388.1	392.7	405.5	422.9	447.3	478.7	514.7	554.2	600.7	657.6	726.2
137.5°	403.4	408.3	420.8	439.4	463.6	492.6	527.2	564.9	606.3	655.0	712.4
140°	413.6	419.4	431.0	449.6	472.9	501.9	535.6	570.5	610.0	654.1	704.1
142.5°	424.8	429.7	442.2	458.9	482.2	509.4	542.1	576.0	612.8	652.3	696.6
145°	442.7	446.1	456.6	474.0	493.8	520.5	550.7	582.1	614.6	649.5	686.7
147.5°	460.8	462.9	473.1	488.2	507.3	530.0	557.7	585.8	614.6	645.1	676.9
150°	472.9	474.0	483.3	498.4	514.7	535.6	562.3	586.7	614.6	641.3	670.4
152.5°	485.0	485.2	494.5	507.7	522.1	542.1	565.1	588.6	611.8	636.7	663.0
155°	503.1	503.1	510.1	521.7	534.4	550.7	570.5	589.1	608.8	628.6	651.8
157.5°	517.5	518.4	524.0	534.2	545.1	557.7	573.5	590.2	604.9	621.4	639.2
160°	528.6	528.6	533.3	542.6	550.7	562.3	576.3	590.2	603.0	615.8	630.9
162.5°	537.0	537.0	540.7	548.2	555.4	565.1	577.2	589.3	599.3	610.2	622.5
165°	549.6	548.4	550.7	556.5	561.2	569.3	578.6	586.7	593.7	601.8	611.1
167.5°	559.1	557.7	558.8	563.3	566.5	571.6	578.4	584.9	588.1	593.5	600.2
170°	564.7	562.3	563.5	567.0	569.3	571.6	577.4	582.1	584.4	587.9	593.7
172.5°	568.4	567.0	567.2	569.8	571.2	572.6	577.4	581.2	581.6	583.2	587.2
175°	572.8	571.6	570.5	572.8	572.8	574.0	576.3	578.6	577.4	577.4	579.8
177.5°	574.9	574.0	573.0	574.0	574.0	574.0	574.9	576.7	574.9	574.0	574.9
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332269

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	572.2	573.1	574.1	574.4	574.3	574.1	573.9	573.8
5°	568.5	569.4	570.3	570.7	570.5	570.3	570.1	569.9
7.5°	560.5	561.0	561.5	561.6	561.2	560.9	560.5	560.2
10°	553.3	553.4	553.5	553.3	552.8	552.3	551.7	551.2
12.5°	544.4	544.3	544.3	543.9	543.3	542.7	542.1	541.5
15°	528.7	528.2	527.7	527.1	526.4	525.6	524.9	524.2
17.5°	510.1	509.0	507.9	506.8	505.7	504.6	503.6	502.5
20°	497.3	495.9	494.6	493.3	492.0	490.8	489.6	488.3
22.5°	483.6	481.9	480.2	478.8	477.6	476.5	475.3	474.2
25°	461.1	459.0	456.8	455.1	454.0	452.9	451.7	450.6
27.5°	436.7	433.7	430.7	428.3	426.5	424.8	423.1	421.3
30°	419.3	415.8	412.3	409.7	408.0	406.4	404.7	403.0
32.5°	402.2	398.4	394.5	391.7	390.0	388.3	386.5	384.8
35°	376.9	372.4	368.0	364.8	363.0	361.1	359.2	357.4
37.5°	349.7	344.6	339.6	335.9	333.6	331.3	329.0	326.7
40°	330.8	325.4	320.0	316.1	313.7	311.4	309.0	306.6
42.5°	312.6	306.8	300.9	296.9	294.7	292.6	290.5	288.3
45°	285.9	280.0	274.1	269.9	267.5	265.0	262.5	260.0
47.5°	258.3	251.9	245.5	241.2	239.0	236.8	234.5	232.3
50°	239.7	233.3	226.9	222.5	220.1	217.7	215.3	212.9
52.5°	221.7	215.0	208.4	204.0	201.8	199.7	197.6	195.4
55°	194.9	188.9	182.9	178.8	176.8	174.7	172.6	170.5
57.5°	168.5	162.8	157.2	153.4	151.7	149.9	148.2	146.4
60°	151.9	146.3	140.7	137.0	135.3	133.5	131.8	130.0
62.5°	135.4	130.2	124.9	121.3	119.5	117.7	115.8	114.0
65°	111.9	106.9	101.8	98.7	97.5	96.4	95.3	94.1
67.5°	89.5	85.7	81.9	79.4	78.2	77.0	75.8	74.6
70°	75.7	72.1	68.4	66.1	64.9	63.8	62.6	61.5
72.5°	63.2	60.3	57.3	55.6	55.1	54.6	54.2	53.7
75°	47.3	46.3	45.2	44.6	44.4	44.2	44.0	43.8
77.5°	35.7	35.1	34.6	34.2	34.0	33.8	33.6	33.4
80°	28.7	28.4	28.1	27.9	27.6	27.4	27.2	27.0
82.5°	22.0	21.7	21.4	21.2	21.2	21.1	21.1	21.1
85°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
87.5°	10.5	10.6	10.8	11.2	10.9	11.0	11.2	10.8
90°	29.0	30.2	31.4	33.7	32.5	33.7	34.9	33.7
92.5°	97.8	77.6	68.5	62.5	60.4	56.9	58.1	56.0
95°	418.3	283.5	221.9	180.1	158.0	147.6	139.4	134.8
97.5°	1042.6	835.1	685.3	546.3	460.6	408.3	376.9	366.9
100°	1369.8	1275.7	1139.8	974.8	857.4	772.6	727.3	728.5
102.5°	1478.6	1475.5	1396.3	1291.7	1200.4	1133.3	1095.4	1068.7
105°	1510.4	1626.6	1648.7	1618.5	1565.0	1520.9	1483.7	1477.9
107.5°	1418.8	1607.5	1709.3	1750.7	1751.6	1736.7	1724.2	1713.5
110°	1331.5	1545.3	1691.7	1773.0	1805.5	1814.8	1812.5	1810.2





TEST NUMBER: P332269

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1245.0	1463.5	1627.5	1732.1	1791.6	1820.4	1829.2	1829.7
115°	1130.5	1332.6	1503.4	1630.1	1717.2	1768.3	1791.6	1797.4
117.5°	1047.5	1222.0	1375.4	1503.9	1594.8	1653.3	1686.8	1694.7
120°	1003.8	1160.7	1300.1	1417.5	1509.2	1574.3	1602.2	1609.2
122.5°	969.4	1111.4	1240.6	1349.6	1431.2	1489.7	1520.4	1529.2
125°	923.7	1050.3	1161.8	1254.8	1329.2	1380.3	1409.3	1417.5
127.5°	883.7	996.6	1097.2	1181.8	1248.1	1291.7	1318.0	1325.4
130°	858.6	963.2	1057.3	1136.3	1197.9	1239.7	1264.1	1273.4
132.5°	835.4	931.6	1019.2	1094.5	1152.3	1194.1	1215.8	1222.3
135°	804.0	886.5	962.0	1028.2	1085.2	1120.0	1140.9	1149.1
137.5°	775.4	843.0	908.1	965.5	1013.4	1048.7	1066.3	1071.7
140°	758.7	817.9	873.7	923.7	967.8	1000.4	1018.9	1017.8
142.5°	742.9	793.8	842.1	885.6	923.2	952.0	968.7	967.6
145°	723.8	762.2	799.4	833.0	862.1	886.5	895.8	898.1
147.5°	708.3	738.7	768.7	792.6	814.7	831.2	840.0	840.9
150°	697.1	723.8	748.2	770.3	787.7	800.5	807.5	807.5
152.5°	686.9	709.9	731.5	749.9	763.6	775.4	779.6	779.6
155°	671.5	690.1	707.6	721.5	732.0	741.3	743.6	744.7
157.5°	655.3	670.9	684.3	695.2	704.3	711.3	713.1	712.9
160°	646.0	658.8	670.4	678.5	686.7	693.6	693.6	692.5
162.5°	634.8	645.8	656.4	663.6	669.0	675.0	675.0	673.9
165°	620.4	627.4	635.5	641.3	646.0	650.6	649.5	649.5
167.5°	607.9	613.2	617.9	622.1	624.1	627.4	626.2	626.2
170°	599.5	603.0	607.6	610.0	611.1	613.5	612.3	612.3
172.5°	592.1	594.6	598.4	599.7	600.0	602.3	600.2	599.3
175°	582.1	583.2	585.6	585.6	585.6	586.7	585.6	584.4
177.5°	575.8	576.7	577.7	577.7	576.7	577.7	575.8	575.8
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0

(END OF REPORT)