

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332375-840

Luminaire Tested: **S123RDIP-S1165D805U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332375-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7665.3 lumens
Efficiency: N/A
Efficacy: 126.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332375-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332375-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73	67	65	63	56	55	54	49
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	83	74	67	61	78	69	63	58	61	56	52	52	49	46	45	42	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	40	37	34	31
5	70	59	51	45	65	55	48	43	49	43	38	42	38	34	36	33	30	27
6	65	53	45	39	60	50	43	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21068	21068	21068
5°	21149	20857	20977
10°	21029	20595	20525
15°	20803	20113	19900
20°	20492	19511	19057
25°	20173	18834	18231
30°	19750	18053	17066
35°	19316	17270	16000
40°	18916	16350	14677
45°	18389	15440	13484
50°	17811	14408	12149
55°	17220	13226	10903
60°	16678	11961	9535
65°	15969	10593	8166
70°	15087	8894	6593
75°	13795	6995	6209
80°	12298	6199	5709
85°	10387	5483	5101



TEST NUMBER: P332375-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	2.4
10°-20°	511.4	6.7
20°-30°	736.4	9.6
30°-40°	829.4	10.8
40°-50°	793.5	10.4
50°-60°	649.8	8.5
60°-70°	438.4	5.7
70°-80°	220.6	2.9
80°-90°	61.3	0.8
90°-100°	38.6	0.5
100°-110°	184.1	2.4
110°-120°	442.3	5.8
120°-130°	563.2	7.3
130°-140°	601.8	7.9
140°-150°	562.7	7.3
150°-160°	453.9	5.9
160°-170°	293.0	3.8
170°-180°	101.0	1.3
0°-30°	1431.6	18.7
0°-40°	2261.0	29.5
0°-60°	3704.3	48.3
0°-90°	4424.6	57.7
90°-120°	665.1	8.7
90°-150°	2392.8	31.2
90°-180°	3241.0	42.3
0°-180°	7665.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1957	1957	1957	1957	1957	
5°	1957	1949	1930	1944	1941	186
15°	1867	1848	1805	1797	1786	526
25°	1698	1657	1586	1553	1535	781
35°	1470	1411	1314	1248	1218	920
45°	1208	1134	1014	927	886	932
55°	918	837	705	616	581	822
65°	627	538	416	342	321	620
75°	332	255	168	153	149	354
85°	84	51	44	41	41	94
90°	1	9	19	22	24	6
95°	48	18	24	30	30	60
105°	235	240	173	41	35	249
115°	441	446	453	461	464	435
125°	622	628	632	633	635	555
135°	774	779	782	784	782	596
145°	894	899	901	902	902	559
155°	984	983	984	987	983	453
165°	1038	1036	1035	1041	1036	293
175°	1063	1059	1060	1064	1059	101
180°	1063	1063	1063	1063	1063	



TEST NUMBER: P332375-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1963.7	1962.5	1961.4	1960.2	1959.1	1956.8	1953.5	1950.0	1946.7	1943.3	1946.4
5°	1957.3	1955.5	1953.8	1952.0	1950.3	1947.2	1943.0	1938.7	1934.5	1930.3	1933.5
7.5°	1939.1	1937.3	1935.4	1933.5	1931.6	1927.8	1922.4	1916.8	1911.4	1905.8	1907.6
10°	1924.0	1921.5	1919.0	1916.5	1914.1	1909.7	1903.3	1896.9	1890.6	1884.3	1884.6
12.5°	1902.4	1899.7	1896.8	1894.1	1891.4	1886.1	1878.3	1870.6	1862.8	1855.0	1854.8
15°	1866.8	1862.9	1859.1	1855.1	1851.3	1844.4	1834.5	1824.6	1814.7	1804.9	1803.1
17.5°	1822.0	1817.6	1813.0	1808.5	1804.0	1795.4	1782.9	1770.3	1757.8	1745.2	1741.5
20°	1789.0	1783.4	1777.8	1772.1	1766.5	1757.0	1743.5	1730.1	1716.7	1703.3	1698.7
22.5°	1752.2	1745.7	1739.2	1732.7	1726.3	1715.9	1701.6	1687.4	1673.1	1658.8	1653.1
25°	1698.5	1689.7	1680.9	1672.0	1663.2	1650.7	1634.5	1618.3	1602.0	1585.8	1578.4
27.5°	1633.5	1623.8	1614.0	1604.3	1594.5	1580.6	1562.6	1544.5	1526.4	1508.3	1498.0
30°	1589.0	1578.4	1567.8	1557.2	1546.7	1531.5	1511.8	1492.0	1472.3	1452.5	1440.5
32.5°	1544.6	1532.6	1520.6	1508.5	1496.6	1480.2	1459.3	1438.4	1417.4	1396.6	1383.5
35°	1470.0	1457.2	1444.5	1431.9	1419.2	1401.9	1380.0	1358.2	1336.3	1314.3	1299.2
37.5°	1394.4	1380.3	1366.1	1352.0	1338.0	1319.2	1295.9	1272.5	1249.2	1225.8	1208.6
40°	1346.2	1330.6	1315.0	1299.6	1284.0	1263.7	1238.7	1213.7	1188.6	1163.6	1145.2
42.5°	1291.5	1276.0	1260.5	1245.0	1229.4	1208.7	1182.9	1156.9	1131.0	1105.2	1085.1
45°	1208.0	1192.1	1176.3	1160.4	1144.5	1123.0	1095.8	1068.6	1041.5	1014.3	994.2
47.5°	1124.5	1107.1	1089.6	1072.3	1054.8	1032.5	1005.3	978.2	951.0	923.9	902.0
50°	1063.6	1047.0	1030.4	1013.8	997.2	974.7	946.1	917.6	889.0	860.4	838.5
52.5°	1009.0	991.0	973.0	955.0	937.0	913.8	885.6	857.3	829.0	800.7	778.0
55°	917.6	900.2	882.9	865.7	848.4	824.8	794.8	764.8	734.8	704.8	684.4
57.5°	833.0	814.3	795.4	776.6	757.7	733.3	703.2	673.0	642.9	612.8	593.4
60°	774.7	755.3	735.9	716.5	697.0	672.7	643.4	614.2	584.9	555.6	536.5
62.5°	716.2	696.8	677.4	658.0	638.6	614.3	585.0	555.7	526.4	497.2	479.3
65°	627.0	607.6	588.2	568.9	549.5	525.9	498.5	470.9	443.4	415.9	398.6
67.5°	537.9	518.2	498.6	479.0	459.4	436.4	410.0	383.5	357.2	330.8	317.9
70°	479.4	460.4	441.3	422.2	403.2	381.3	356.7	331.9	307.3	282.6	270.2
72.5°	421.0	402.2	383.4	364.7	345.9	325.3	302.9	280.4	258.0	235.6	225.5
75°	331.7	314.9	297.9	280.9	264.1	245.9	226.5	207.0	187.6	168.2	164.7
77.5°	250.4	235.2	219.8	204.6	189.2	175.3	162.9	150.4	137.8	125.4	123.5
80°	198.4	184.0	169.5	155.0	140.6	129.7	122.2	114.8	107.4	100.0	99.0
82.5°	148.9	136.4	123.9	111.4	99.0	91.0	87.6	84.0	80.6	77.2	76.0
85°	84.1	76.3	68.6	60.9	53.1	48.7	47.7	46.6	45.5	44.4	43.7
87.5°	30.6	27.9	25.1	22.4	19.6	18.5	18.9	19.4	19.8	20.3	20.2
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.3	16.7	19.0	19.7
92.5°	14.6	14.2	13.7	13.2	12.7	13.3	15.0	16.8	18.5	20.2	21.3
95°	48.2	41.0	33.7	26.6	19.4	16.8	18.7	20.6	22.5	24.4	25.8
97.5°	96.7	93.6	90.4	87.2	83.9	75.9	63.3	50.7	38.1	25.4	26.9
100°	133.4	136.9	140.5	143.9	147.4	135.5	108.2	80.8	53.4	26.1	27.5
102.5°	175.1	177.6	180.2	182.7	185.2	171.6	141.7	111.7	81.8	51.9	47.6
105°	235.3	237.2	239.1	241.1	243.0	236.1	220.3	204.5	188.6	172.9	141.9
107.5°	298.7	300.3	301.8	303.4	304.9	306.9	309.4	311.9	314.4	316.9	294.2
110°	341.0	342.4	343.9	345.3	346.7	348.3	350.3	352.2	354.2	356.1	350.3



TEST NUMBER: P332375-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.5	382.7	384.1	385.3	386.6	388.1	390.1	392.0	393.9	395.9	396.0
115°	441.3	442.4	443.4	444.5	445.6	446.9	448.5	450.0	451.6	453.2	454.9
117.5°	499.3	500.6	501.9	503.2	504.4	505.5	506.3	507.2	508.0	508.8	510.2
120°	535.3	536.8	538.5	540.0	541.6	542.7	543.2	543.7	544.2	544.7	546.1
122.5°	571.9	573.2	574.5	575.8	577.1	578.0	578.8	579.5	580.1	580.8	581.8
125°	622.2	623.5	624.9	626.3	627.7	628.8	629.5	630.2	630.9	631.6	632.0
127.5°	670.8	672.2	673.6	675.0	676.4	677.5	678.3	679.2	680.0	680.9	681.5
130°	701.0	702.5	703.9	705.3	706.7	707.7	708.4	709.1	709.8	710.5	711.2
132.5°	730.1	731.5	733.0	734.4	735.8	736.7	737.3	737.8	738.4	739.0	739.7
135°	774.5	775.6	776.6	777.7	778.7	779.6	780.3	781.0	781.7	782.4	782.9
137.5°	812.4	813.7	815.1	816.4	817.7	818.6	819.0	819.4	819.7	820.1	821.0
140°	837.7	838.7	839.8	840.8	841.9	842.6	843.2	843.7	844.2	844.8	845.5
142.5°	861.0	862.1	863.1	864.2	865.3	866.1	866.6	867.1	867.6	868.2	868.7
145°	893.7	894.9	896.2	897.4	898.7	899.4	899.8	900.1	900.5	900.8	901.2
147.5°	924.5	925.3	926.1	927.0	927.8	928.4	928.7	929.0	929.4	929.7	930.1
150°	943.4	944.0	944.5	945.0	945.5	946.0	946.3	946.7	947.1	947.5	947.8
152.5°	960.5	960.8	961.0	961.3	961.5	961.7	961.9	962.1	962.4	962.6	963.2
155°	984.5	984.2	983.8	983.5	983.1	983.0	983.2	983.4	983.5	983.7	984.6
157.5°	1003.1	1003.1	1003.1	1003.0	1003.0	1002.9	1002.7	1002.6	1002.4	1002.2	1003.3
160°	1014.5	1014.3	1014.2	1014.0	1013.8	1013.6	1013.5	1013.3	1013.1	1012.9	1014.0
162.5°	1025.2	1024.8	1024.3	1023.9	1023.4	1023.1	1022.9	1022.8	1022.6	1022.4	1023.6
165°	1038.2	1037.6	1037.1	1036.6	1036.1	1035.7	1035.6	1035.4	1035.2	1035.0	1036.4
167.5°	1048.3	1047.6	1046.9	1046.2	1045.5	1045.1	1045.1	1045.1	1045.1	1045.1	1046.5
170°	1054.0	1053.3	1052.6	1051.9	1051.2	1050.9	1050.9	1050.9	1050.9	1050.9	1052.3
172.5°	1057.7	1056.9	1056.1	1055.2	1054.4	1054.1	1054.2	1054.3	1054.5	1054.6	1056.0
175°	1062.7	1061.8	1061.0	1060.1	1059.1	1058.8	1058.9	1059.1	1059.3	1059.6	1060.8
177.5°	1063.9	1063.3	1062.6	1061.9	1061.2	1060.9	1061.0	1061.2	1061.3	1061.4	1062.6
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332375-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1949.5	1952.7	1955.7	1957.0	1956.4	1955.9	1955.3	1954.7
5°	1936.6	1939.8	1943.0	1944.2	1943.5	1942.8	1942.1	1941.4
7.5°	1909.4	1911.2	1912.9	1913.2	1912.0	1910.8	1909.6	1908.3
10°	1885.0	1885.3	1885.7	1885.0	1883.2	1881.5	1879.7	1877.9
12.5°	1854.6	1854.4	1854.2	1853.1	1851.1	1849.0	1846.9	1844.9
15°	1801.4	1799.6	1797.9	1795.7	1793.2	1790.8	1788.3	1785.8
17.5°	1737.8	1733.9	1730.2	1726.6	1722.8	1719.2	1715.6	1711.8
20°	1694.1	1689.5	1685.0	1680.5	1676.3	1672.0	1667.9	1663.7
22.5°	1647.4	1641.7	1636.0	1631.1	1627.2	1623.3	1619.3	1615.4
25°	1571.0	1563.6	1556.2	1550.5	1546.7	1542.8	1538.9	1535.0
27.5°	1487.7	1477.4	1467.1	1459.1	1453.1	1447.2	1441.3	1435.3
30°	1428.5	1416.5	1404.5	1395.7	1390.1	1384.4	1378.8	1373.1
32.5°	1370.4	1357.3	1344.1	1334.6	1328.7	1322.7	1316.9	1310.9
35°	1284.0	1268.9	1253.7	1242.9	1236.6	1230.2	1223.9	1217.6
37.5°	1191.3	1174.2	1156.9	1144.4	1136.6	1128.7	1121.0	1113.1
40°	1126.9	1108.5	1090.3	1077.0	1068.8	1060.8	1052.7	1044.5
42.5°	1065.1	1045.0	1025.0	1011.4	1004.1	996.8	989.6	982.3
45°	974.1	954.0	933.9	919.7	911.2	902.7	894.2	885.8
47.5°	880.1	858.3	836.4	821.7	814.2	806.6	799.0	791.5
50°	816.7	794.8	772.8	757.9	749.8	741.6	733.6	725.5
52.5°	755.3	732.6	709.8	694.8	687.5	680.3	673.1	665.8
55°	663.9	643.4	623.0	609.3	602.2	595.1	588.0	581.0
57.5°	574.1	554.7	535.4	522.7	516.7	510.8	504.7	498.8
60°	517.5	498.5	479.4	466.9	460.9	454.8	448.9	442.9
62.5°	461.3	443.4	425.5	413.4	407.1	400.8	394.6	388.3
65°	381.3	364.1	346.8	336.2	332.3	328.4	324.6	320.6
67.5°	305.0	292.1	279.1	270.6	266.5	262.3	258.1	254.0
70°	257.8	245.5	233.2	225.1	221.2	217.3	213.4	209.5
72.5°	215.4	205.3	195.2	189.3	187.7	186.1	184.5	182.9
75°	161.2	157.6	154.1	152.1	151.4	150.7	150.0	149.3
77.5°	121.6	119.7	117.8	116.4	115.7	115.0	114.3	113.6
80°	97.9	96.8	95.7	94.9	94.2	93.5	92.8	92.1
82.5°	75.0	74.0	72.9	72.3	72.2	72.0	71.9	71.8
85°	43.0	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	20.0	19.9	19.7	19.6	19.4	19.1	18.9	18.7
90°	20.4	21.0	21.7	22.3	22.6	23.0	23.3	23.7
92.5°	22.4	23.5	24.7	25.3	25.5	25.8	26.0	26.3
95°	27.0	28.2	29.4	30.0	30.0	30.0	30.0	30.0
97.5°	28.3	29.6	31.0	31.8	32.0	32.2	32.3	32.5
100°	28.9	30.3	31.7	32.4	32.6	32.8	33.0	33.1
102.5°	43.2	38.9	34.5	32.5	32.8	33.1	33.4	33.8
105°	110.8	79.8	48.7	33.3	33.7	34.0	34.4	34.7
107.5°	271.4	248.6	225.8	202.7	179.4	155.9	132.5	109.1
110°	344.5	338.7	333.0	317.5	292.4	267.3	242.2	217.1



TEST NUMBER: P332375-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	396.1	396.2	396.3	393.6	388.4	383.0	377.8	372.5
115°	456.7	458.5	460.2	461.4	462.1	462.8	463.5	464.2
117.5°	511.6	513.0	514.3	515.1	515.3	515.4	515.5	515.7
120°	547.5	549.0	550.4	551.1	551.1	551.1	551.1	551.1
122.5°	582.7	583.7	584.7	585.2	585.4	585.5	585.7	585.8
125°	632.3	632.7	633.0	633.4	633.7	634.1	634.4	634.8
127.5°	682.0	682.6	683.1	683.2	682.9	682.6	682.2	681.9
130°	712.0	712.7	713.4	713.6	713.2	712.9	712.5	712.2
132.5°	740.3	741.0	741.7	741.8	741.4	740.9	740.4	739.9
135°	783.5	784.0	784.5	784.5	784.0	783.5	782.9	782.4
137.5°	821.8	822.6	823.5	823.7	823.4	823.0	822.7	822.3
140°	846.2	846.9	847.6	847.8	847.4	847.1	846.7	846.4
142.5°	869.3	869.8	870.4	870.4	869.9	869.4	869.0	868.5
145°	901.5	901.9	902.2	902.4	902.4	902.4	902.4	902.4
147.5°	930.4	930.8	931.1	930.9	930.1	929.3	928.5	927.7
150°	948.1	948.5	948.8	948.8	948.2	947.7	947.2	946.6
152.5°	963.8	964.4	965.1	965.0	964.2	963.4	962.6	961.8
155°	985.5	986.3	987.2	987.1	986.1	985.0	984.0	982.9
157.5°	1004.3	1005.3	1006.4	1006.2	1004.9	1003.5	1002.2	1000.8
160°	1015.0	1016.1	1017.1	1017.0	1015.8	1014.6	1013.4	1012.2
162.5°	1024.8	1026.0	1027.1	1027.2	1026.1	1025.0	1024.0	1022.9
165°	1037.8	1039.3	1040.7	1040.8	1039.6	1038.2	1037.0	1035.8
167.5°	1047.9	1049.4	1050.8	1050.8	1049.4	1047.9	1046.5	1045.1
170°	1053.6	1055.0	1056.4	1056.4	1055.0	1053.6	1052.3	1050.9
172.5°	1057.4	1058.8	1060.3	1060.2	1058.6	1057.1	1055.5	1054.0
175°	1062.0	1063.2	1064.4	1064.3	1063.0	1061.6	1060.2	1058.7
177.5°	1063.7	1064.8	1065.9	1065.8	1064.4	1063.0	1061.6	1060.2
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7

(END OF REPORT)