

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332240

Luminaire Tested: **S123RDIP-S340D365U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332240
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2806.9 lumens
Efficiency: N/A
Efficacy: 138.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	98	94	90	87	90	87	83	81	73	71	69	61	59	58	49	48	47	42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36
3	82	73	66	61	75	68	62	57	58	53	49	48	45	42	39	37	35	31
4	75	65	57	52	69	60	54	49	51	46	42	43	40	37	36	33	31	27
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	32	29	27	24
6	64	52	45	39	59	49	42	37	42	36	32	35	31	28	29	26	24	21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16
10	48	36	29	25	44	34	28	23	30	24	21	25	21	19	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5858	5858	5858	5858
5°	6983	5883	5181	5883
10°	8719	5850	4680	5850
15°	10234	5789	4268	5789
20°	11423	5700	3918	5700
25°	11240	5606	3702	5606
30°	8079	5520	3480	5520
35°	5394	5406	3336	5406
40°	3974	5271	3188	5271
45°	3334	5033	3043	5033
50°	2942	4721	2840	4721
55°	2580	4363	2562	4363
60°	2297	4021	2347	4021
65°	2017	3655	2183	3655
70°	1583	3330	1995	3330
75°	1393	2907	1822	2907
80°	1215	2467	1791	2467
85°	976	1988	1902	1988



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.5	1.9
10°-20°	167.2	6.0
20°-30°	262.7	9.4
30°-40°	274.1	9.8
40°-50°	234.5	8.4
50°-60°	178.8	6.4
60°-70°	114.6	4.1
70°-80°	55.1	2.0
80°-90°	15.9	0.6
90°-100°	17.3	0.6
100°-110°	82.4	2.9
110°-120°	198.0	7.1
120°-130°	252.1	9.0
130°-140°	269.3	9.6
140°-150°	251.9	9.0
150°-160°	203.2	7.2
160°-170°	131.1	4.7
170°-180°	45.2	1.6
0°-30°	483.4	17.2
0°-40°	757.5	27.0
0°-60°	1170.8	41.7
0°-90°	1356.4	48.3
90°-120°	297.7	10.6
90°-150°	1071.0	38.2
90°-180°	1450.0	51.7
0°-180°	2806.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	544	544	544	544	544	
5°	646	544	480	544	646	67
15°	918	520	383	520	918	260
25°	946	472	312	472	946	407
35°	410	411	254	411	410	269
45°	219	331	200	331	219	172
55°	138	232	136	232	138	124
65°	79	144	86	144	79	78
75°	34	70	44	70	34	36
85°	8	16	15	16	8	9
90°	11	0	11	0	11	5
95°	13	22	13	22	13	11
105°	16	105	16	105	16	36
115°	208	198	208	198	208	192
125°	284	278	284	278	284	254
135°	350	347	350	347	350	270
145°	404	400	404	400	404	252
155°	440	441	440	441	440	203
165°	464	465	464	465	464	131
175°	474	476	474	476	474	45
180°	476	476	476	476	476	



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	579.7	580.4	578.0	577.6	574.8	574.1	574.1	570.1	567.7	564.6	562.7
5°	646.3	650.0	648.1	644.0	637.0	635.3	630.9	623.9	616.0	606.2	601.6
7.5°	729.5	734.6	732.6	726.2	718.8	712.9	700.4	688.8	672.6	658.3	646.1
10°	797.7	792.4	788.2	781.9	775.1	764.2	751.1	733.2	712.5	696.1	678.0
12.5°	848.8	847.9	842.6	836.1	826.6	816.2	800.1	778.3	754.2	730.6	709.8
15°	918.4	919.8	916.3	909.6	896.0	877.6	853.4	844.3	809.8	784.2	758.6
17.5°	966.6	966.3	965.8	956.5	942.7	929.6	907.1	883.2	852.0	815.9	781.4
20°	997.2	994.8	995.3	984.8	974.6	959.4	937.5	902.8	877.2	835.5	799.8
22.5°	996.4	995.9	997.7	994.1	986.7	975.1	957.8	928.5	895.8	853.7	813.6
25°	946.4	944.5	955.4	958.5	970.4	972.5	967.3	951.3	920.3	876.9	827.3
27.5°	792.0	791.0	811.3	836.8	869.0	894.1	918.3	930.0	920.3	889.2	839.5
30°	650.0	671.9	682.2	719.0	760.0	808.9	851.8	892.5	902.6	889.0	848.3
32.5°	539.7	558.8	567.4	598.9	637.2	694.5	758.8	816.5	857.3	867.6	843.1
35°	410.5	410.7	430.3	444.3	479.7	538.6	601.1	678.4	755.3	813.6	819.6
37.5°	327.6	328.7	340.6	354.5	381.1	412.2	467.2	531.5	620.3	709.7	762.2
40°	282.8	284.9	293.8	307.5	326.6	350.2	393.0	453.6	527.7	627.2	708.5
42.5°	254.1	257.5	262.1	272.7	284.5	306.6	341.2	388.0	455.4	549.5	643.3
45°	219.0	220.9	224.4	229.3	240.0	255.3	278.6	310.1	366.0	441.7	535.6
47.5°	193.2	192.2	195.9	199.8	207.0	217.5	233.1	258.7	298.6	359.4	439.0
50°	175.7	175.4	178.0	181.0	187.8	195.5	208.3	227.6	259.3	309.6	382.6
52.5°	159.3	160.1	162.0	165.7	170.6	176.8	188.3	202.3	229.5	272.9	333.7
55°	137.5	138.2	140.7	142.8	146.3	152.6	159.8	171.5	190.1	220.4	270.5
57.5°	119.0	118.7	121.1	121.7	125.6	130.7	136.3	145.4	158.9	181.4	215.1
60°	106.7	106.0	108.1	109.7	111.8	116.0	120.7	129.5	140.3	156.8	185.7
62.5°	95.5	95.2	96.7	98.4	100.1	103.9	107.8	114.6	123.1	137.0	160.0
65°	79.2	79.9	80.6	81.3	82.2	84.6	88.3	93.0	98.8	108.6	125.1
67.5°	62.3	63.0	63.2	64.6	66.6	68.1	70.4	74.5	78.6	86.8	96.2
70°	50.3	50.1	50.3	51.0	53.6	56.1	59.2	62.2	64.8	70.6	78.5
72.5°	43.2	42.8	43.4	43.6	44.8	45.5	47.4	50.3	53.6	57.5	63.2
75°	33.5	33.5	33.5	33.5	34.5	34.9	35.6	36.3	37.5	39.4	43.6
77.5°	24.8	24.8	25.2	25.4	25.6	25.9	26.3	27.0	27.4	28.4	30.2
80°	19.6	19.8	19.6	19.8	19.8	20.3	20.5	21.2	21.4	22.6	23.3
82.5°	14.7	14.6	14.7	15.0	15.0	15.4	15.5	16.0	16.0	16.6	17.3
85°	7.9	7.5	7.9	7.7	8.2	7.7	7.9	8.4	8.4	8.6	9.6
87.5°	4.0	4.3	3.9	4.1	4.0	4.2	4.1	4.1	4.4	4.1	4.1
90°	10.6	10.4	10.3	10.1	10.0	9.7	9.4	9.1	8.8	8.5	7.5
92.5°	11.7	11.6	11.5	11.4	11.4	11.1	10.6	10.1	9.5	9.0	8.3
95°	13.4	13.4	13.4	13.4	13.4	13.2	12.6	12.1	11.5	11.0	10.1
97.5°	14.6	14.5	14.4	14.3	14.2	13.9	13.3	12.6	12.0	11.4	17.0
100°	14.8	14.8	14.7	14.6	14.5	14.2	13.5	12.9	12.3	11.7	23.9
102.5°	15.1	15.0	14.8	14.7	14.6	15.5	17.4	19.4	21.3	23.3	36.6
105°	15.5	15.4	15.2	15.1	14.9	21.8	35.7	49.6	63.5	77.4	84.5
107.5°	48.8	59.3	69.8	80.3	90.7	101.1	111.3	121.5	131.6	141.8	140.7
110°	97.2	108.4	119.6	130.9	142.1	149.0	151.6	154.2	156.8	159.4	158.5



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	166.7	169.1	171.5	173.8	176.2	177.4	177.3	177.3	177.2	177.2	176.3
115°	207.8	207.5	207.2	206.8	206.5	206.0	205.2	204.4	203.6	202.8	202.1
117.5°	230.8	230.8	230.7	230.6	230.6	230.2	229.6	229.0	228.3	227.7	227.4
120°	246.7	246.7	246.7	246.7	246.7	246.3	245.7	245.1	244.5	243.8	243.6
122.5°	262.2	262.1	262.1	262.0	261.9	261.7	261.3	260.8	260.4	259.9	259.6
125°	284.1	284.0	283.8	283.6	283.5	283.3	283.2	283.0	282.9	282.7	282.4
127.5°	305.2	305.3	305.5	305.6	305.8	305.8	305.5	305.2	305.0	304.7	304.4
130°	318.7	318.9	319.1	319.2	319.4	319.3	319.0	318.7	318.3	318.0	317.7
132.5°	331.2	331.4	331.6	331.8	332.1	332.0	331.7	331.4	331.1	330.8	330.5
135°	350.2	350.4	350.7	350.9	351.1	351.1	350.9	350.7	350.4	350.2	349.9
137.5°	368.1	368.2	368.4	368.5	368.7	368.6	368.2	367.8	367.5	367.1	366.9
140°	378.8	379.0	379.1	379.3	379.4	379.4	379.0	378.7	378.4	378.1	377.9
142.5°	388.7	388.9	389.1	389.4	389.6	389.6	389.3	389.1	388.8	388.6	388.3
145°	403.9	403.9	403.9	403.9	403.9	403.8	403.7	403.5	403.4	403.2	403.0
147.5°	415.2	415.6	415.9	416.3	416.7	416.8	416.6	416.4	416.3	416.1	416.0
150°	423.7	423.9	424.2	424.4	424.6	424.7	424.5	424.4	424.2	424.0	423.9
152.5°	430.5	430.8	431.2	431.6	431.9	432.0	431.7	431.4	431.1	430.8	430.7
155°	439.9	440.4	440.9	441.4	441.8	441.9	441.5	441.1	440.7	440.3	440.2
157.5°	447.9	448.5	449.2	449.8	450.4	450.5	450.0	449.5	449.0	448.6	448.6
160°	453.0	453.6	454.1	454.7	455.2	455.3	454.8	454.3	453.8	453.4	453.5
162.5°	457.8	458.3	458.8	459.3	459.8	459.7	459.2	458.7	458.1	457.6	457.7
165°	463.6	464.2	464.7	465.3	465.8	465.8	465.2	464.5	463.9	463.3	463.3
167.5°	467.8	468.4	469.0	469.7	470.3	470.3	469.7	469.0	468.4	467.8	467.8
170°	470.3	471.0	471.6	472.2	472.8	472.8	472.2	471.6	471.0	470.3	470.3
172.5°	471.7	472.4	473.1	473.8	474.5	474.5	473.9	473.3	472.7	472.0	472.0
175°	473.9	474.5	475.1	475.8	476.4	476.4	475.9	475.3	474.8	474.2	474.1
177.5°	474.5	475.1	475.8	476.4	477.0	477.1	476.6	476.1	475.6	475.1	475.0
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	561.9	561.4	558.8	555.8	551.9	549.3	547.2	546.1	542.7	538.6	535.9
5°	596.7	589.7	582.2	573.1	564.7	556.1	550.8	544.5	536.8	528.2	522.1
7.5°	633.8	620.1	605.4	590.1	575.1	561.6	549.6	539.4	527.2	514.8	506.2
10°	662.4	642.3	621.6	600.4	581.1	562.9	548.9	535.2	520.5	506.3	495.5
12.5°	688.3	661.9	638.0	611.9	587.2	565.5	545.4	529.2	511.5	496.4	484.2
15°	721.1	694.0	665.2	625.5	592.7	565.2	540.7	519.5	498.1	479.5	467.6
17.5°	751.7	711.1	672.2	639.2	596.5	562.2	532.3	507.0	483.4	463.7	449.0
20°	764.4	725.0	682.9	640.7	598.8	560.3	525.6	497.6	473.2	450.8	437.3
22.5°	772.0	727.5	683.0	637.7	593.2	553.2	518.9	488.1	461.6	440.4	423.7
25°	780.9	727.8	678.9	634.2	588.7	545.4	504.6	472.0	443.4	420.8	403.1
27.5°	786.8	724.3	666.5	616.8	570.7	527.6	490.2	455.6	426.5	402.6	383.6
30°	787.9	721.5	657.0	603.2	556.4	516.7	477.1	444.1	413.3	387.9	370.2
32.5°	789.4	714.6	644.1	587.0	539.0	499.8	463.9	432.3	400.8	375.8	357.7
35°	783.3	710.8	624.6	558.9	510.9	472.9	440.6	411.4	380.5	356.2	337.8
37.5°	756.8	695.7	604.4	527.3	477.1	442.0	415.6	390.2	361.8	335.6	318.3
40°	730.2	680.8	588.7	508.1	455.7	419.6	395.8	375.1	347.6	323.1	304.5
42.5°	690.5	660.4	573.8	488.0	431.5	396.7	376.6	357.2	333.1	308.2	290.7
45°	617.6	621.6	543.3	455.9	397.9	363.0	344.1	330.6	309.2	288.7	270.7
47.5°	526.3	563.3	507.5	421.8	362.6	329.8	313.3	301.5	287.0	266.9	250.5
50°	466.7	519.5	478.8	398.9	340.4	307.8	291.5	281.9	269.3	253.5	237.9
52.5°	411.7	468.5	444.1	373.3	316.3	286.5	270.6	262.7	252.7	237.8	223.7
55°	335.7	393.3	387.7	334.8	280.3	253.5	241.4	232.5	225.8	214.6	203.4
57.5°	271.6	326.1	329.0	291.9	248.5	222.0	211.6	204.9	200.5	192.1	181.7
60°	231.1	281.2	291.0	263.0	225.8	202.5	192.2	186.8	183.4	176.6	168.7
62.5°	197.6	240.2	251.3	231.2	204.0	182.1	174.1	169.0	166.6	160.8	153.8
65°	151.2	186.6	197.3	186.2	171.9	154.5	147.9	143.5	141.4	138.2	133.0
67.5°	113.7	139.5	151.3	143.4	138.2	127.2	123.1	120.7	118.8	116.6	112.3
70°	91.3	110.4	122.5	120.5	116.3	110.4	107.4	105.8	103.9	102.0	98.3
72.5°	73.4	86.6	97.9	99.0	95.6	94.4	91.7	91.0	89.9	87.7	85.6
75°	48.7	57.8	65.7	68.7	70.1	71.3	70.1	69.9	69.7	67.8	66.6
77.5°	31.9	36.8	41.8	47.0	49.2	50.7	51.1	52.0	51.3	50.4	49.8
80°	24.5	25.6	29.1	33.5	37.0	38.4	39.4	39.8	39.6	39.4	38.4
82.5°	17.8	18.7	20.4	23.5	26.4	28.7	29.3	29.2	29.7	29.9	29.1
85°	9.6	9.8	10.3	10.7	12.3	14.9	15.6	16.1	16.5	16.5	15.1
87.5°	4.3	3.9	4.0	3.9	4.3	4.3	5.3	6.0	6.4	5.8	5.9
90°	6.4	5.4	4.4	3.5	2.7	1.9	1.1	0.4	1.1	1.9	2.7
92.5°	7.5	6.7	6.0	5.7	5.9	6.1	6.4	6.6	6.4	6.1	5.9
95°	9.2	8.4	7.5	8.7	11.9	15.1	18.3	21.6	18.3	15.1	11.9
97.5°	22.7	28.3	34.0	37.5	39.0	40.4	41.9	43.3	41.9	40.4	39.0
100°	36.2	48.4	60.7	66.0	64.4	62.9	61.3	59.7	61.3	62.9	64.4
102.5°	50.0	63.4	76.8	82.9	81.8	80.6	79.5	78.4	79.5	80.6	81.8
105°	91.5	98.6	105.7	108.8	107.9	107.0	106.2	105.3	106.2	107.0	107.9
107.5°	139.6	138.5	137.4	136.5	135.8	135.1	134.4	133.7	134.4	135.1	135.8
110°	157.6	156.8	155.9	155.2	154.5	153.9	153.3	152.7	153.3	153.9	154.5



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	175.5	174.6	173.7	173.0	172.4	171.9	171.3	170.7	171.3	171.9	172.4
115°	201.4	200.7	200.0	199.4	198.9	198.5	198.0	197.5	198.0	198.5	198.9
117.5°	227.0	226.6	226.3	225.8	225.2	224.6	224.1	223.5	224.1	224.6	225.2
120°	243.4	243.1	242.9	242.4	241.7	241.0	240.3	239.6	240.3	241.0	241.7
122.5°	259.3	259.0	258.7	258.3	257.7	257.1	256.6	256.0	256.6	257.1	257.7
125°	282.1	281.8	281.4	281.0	280.3	279.7	279.1	278.5	279.1	279.7	280.3
127.5°	304.0	303.6	303.2	302.7	302.1	301.5	300.9	300.2	300.9	301.5	302.1
130°	317.4	317.1	316.8	316.3	315.7	315.0	314.4	313.8	314.4	315.0	315.7
132.5°	330.3	330.0	329.7	329.3	328.7	328.1	327.4	326.8	327.4	328.1	328.7
135°	349.6	349.2	348.9	348.5	348.1	347.6	347.1	346.7	347.1	347.6	348.1
137.5°	366.7	366.6	366.4	366.0	365.4	364.8	364.2	363.6	364.2	364.8	365.4
140°	377.6	377.4	377.2	376.8	376.3	375.9	375.4	374.9	375.4	375.9	376.3
142.5°	388.1	387.9	387.6	387.3	386.8	386.3	385.9	385.4	385.9	386.3	386.8
145°	402.9	402.7	402.6	402.2	401.7	401.1	400.6	400.0	400.6	401.1	401.7
147.5°	415.8	415.7	415.5	415.2	414.9	414.5	414.2	413.8	414.2	414.5	414.9
150°	423.7	423.6	423.4	423.2	423.0	422.7	422.5	422.3	422.5	422.7	423.0
152.5°	430.6	430.5	430.5	430.3	430.2	430.1	430.0	429.9	430.0	430.1	430.2
155°	440.1	440.1	440.0	440.0	440.2	440.3	440.5	440.7	440.5	440.3	440.2
157.5°	448.7	448.8	448.9	448.9	448.9	449.0	449.0	449.0	449.0	449.0	448.9
160°	453.5	453.6	453.7	453.8	453.8	453.9	454.0	454.1	454.0	453.9	453.8
162.5°	457.8	457.8	457.9	458.1	458.3	458.5	458.7	458.9	458.7	458.5	458.3
165°	463.4	463.5	463.6	463.7	464.0	464.2	464.4	464.7	464.4	464.2	464.0
167.5°	467.8	467.8	467.8	467.9	468.3	468.6	468.9	469.2	468.9	468.6	468.3
170°	470.3	470.3	470.3	470.5	470.8	471.1	471.4	471.7	471.4	471.1	470.8
172.5°	471.9	471.8	471.8	471.9	472.3	472.7	473.1	473.4	473.1	472.7	472.3
175°	474.1	474.0	473.9	474.1	474.5	474.8	475.2	475.6	475.2	474.8	474.5
177.5°	474.9	474.9	474.8	474.9	475.3	475.6	475.9	476.2	475.9	475.6	475.3
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	534.9	532.5	530.8	527.1	524.7	522.1	519.5	521.1	520.9	520.8	520.8
5°	517.0	511.6	506.7	500.4	496.5	491.6	487.9	487.4	488.3	485.1	483.2
7.5°	499.2	491.9	484.9	478.0	470.6	464.7	461.1	459.3	457.0	455.0	452.9
10°	486.7	478.1	471.3	462.7	454.8	447.8	443.4	440.3	438.7	437.1	434.0
12.5°	473.8	465.4	456.8	447.0	439.5	431.4	428.1	424.7	421.6	419.7	415.6
15°	455.0	444.1	435.0	424.7	416.3	408.4	403.8	397.0	396.1	393.7	389.5
17.5°	436.1	424.3	411.7	404.1	394.7	386.4	379.3	377.1	370.4	367.9	364.2
20°	421.2	410.3	400.7	390.7	377.0	369.3	363.7	360.7	355.3	352.0	349.7
22.5°	408.4	397.2	386.2	374.5	363.2	354.5	350.4	345.7	342.8	338.2	335.7
25°	390.0	377.9	364.6	352.0	343.9	337.4	330.8	326.6	322.4	320.3	315.7
27.5°	368.7	356.0	343.6	334.0	324.0	317.6	311.7	308.0	302.9	299.4	296.8
30°	356.9	342.0	331.3	322.7	309.9	303.8	299.4	294.7	291.0	287.3	284.7
32.5°	343.3	329.7	319.6	308.9	299.1	292.4	286.7	282.6	279.4	275.9	273.3
35°	322.0	310.6	300.1	289.4	282.1	275.4	268.6	265.1	262.1	258.8	256.5
37.5°	302.7	292.0	282.0	271.9	262.9	257.4	252.0	249.3	245.2	243.0	240.7
40°	290.8	280.3	269.6	259.8	250.5	246.3	241.4	237.4	233.7	232.0	229.5
42.5°	277.7	267.2	258.2	247.7	240.0	234.3	229.8	225.5	222.7	220.3	218.9
45°	258.4	249.1	240.2	229.7	222.5	217.6	212.5	208.5	206.0	204.3	201.8
47.5°	239.6	230.3	221.3	212.2	205.2	199.6	194.4	191.7	188.3	186.3	184.6
50°	226.0	217.6	208.1	199.7	192.7	187.1	182.9	179.4	176.4	173.8	172.6
52.5°	213.5	204.6	196.3	188.5	181.1	174.8	171.0	167.3	165.0	162.1	160.7
55°	192.9	184.3	177.3	169.6	162.4	157.0	152.4	149.1	146.8	143.5	141.7
57.5°	173.6	165.8	157.5	150.8	143.4	138.9	135.0	130.6	127.7	125.2	123.3
60°	160.5	151.7	144.4	138.2	131.6	125.8	122.3	118.8	115.8	113.2	111.6
62.5°	146.9	139.2	132.3	125.5	119.5	114.4	110.4	107.5	104.8	103.2	101.5
65°	126.0	120.0	113.0	107.4	101.8	98.1	94.8	92.3	90.4	89.2	87.8
67.5°	106.8	101.0	94.9	89.4	85.6	82.8	80.7	78.5	77.5	76.0	75.1
70°	94.4	88.3	82.9	78.7	75.0	72.9	71.5	69.9	69.0	67.1	66.2
72.5°	80.8	76.4	72.5	69.1	66.1	64.2	62.4	60.4	58.9	56.8	55.9
75°	63.6	59.6	56.6	54.3	52.4	49.9	47.3	45.2	44.5	43.8	43.6
77.5°	47.1	44.6	42.4	40.4	38.1	36.3	35.7	35.2	35.1	34.7	34.7
80°	37.0	34.7	33.1	30.8	29.4	29.4	29.4	28.9	29.1	29.1	29.1
82.5°	27.5	25.4	24.5	23.7	23.4	23.6	23.6	23.7	23.5	23.9	23.7
85°	14.2	14.4	14.9	14.7	14.9	14.9	15.4	15.1	15.4	14.9	15.4
87.5°	5.9	6.7	7.0	7.4	7.8	7.8	8.1	8.2	8.4	8.5	8.5
90°	3.5	4.4	5.4	6.4	7.5	8.5	8.8	9.1	9.4	9.7	10.0
92.5°	5.7	6.0	6.7	7.5	8.3	9.0	9.5	10.1	10.6	11.1	11.4
95°	8.7	7.5	8.4	9.2	10.1	11.0	11.5	12.1	12.6	13.2	13.4
97.5°	37.5	34.0	28.3	22.7	17.0	11.4	12.0	12.6	13.3	13.9	14.2
100°	66.0	60.7	48.4	36.2	23.9	11.7	12.3	12.9	13.5	14.2	14.5
102.5°	82.9	76.8	63.4	50.0	36.6	23.3	21.3	19.4	17.4	15.5	14.6
105°	108.8	105.7	98.6	91.5	84.5	77.4	63.5	49.6	35.7	21.8	14.9
107.5°	136.5	137.4	138.5	139.6	140.7	141.8	131.6	121.5	111.3	101.1	90.7
110°	155.2	155.9	156.8	157.6	158.5	159.4	156.8	154.2	151.6	149.0	142.1



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	173.0	173.7	174.6	175.5	176.3	177.2	177.2	177.3	177.3	177.4	176.2
115°	199.4	200.0	200.7	201.4	202.1	202.8	203.6	204.4	205.2	206.0	206.5
117.5°	225.8	226.3	226.6	227.0	227.4	227.7	228.3	229.0	229.6	230.2	230.6
120°	242.4	242.9	243.1	243.4	243.6	243.8	244.5	245.1	245.7	246.3	246.7
122.5°	258.3	258.7	259.0	259.3	259.6	259.9	260.4	260.8	261.3	261.7	261.9
125°	281.0	281.4	281.8	282.1	282.4	282.7	282.9	283.0	283.2	283.3	283.5
127.5°	302.7	303.2	303.6	304.0	304.4	304.7	305.0	305.2	305.5	305.8	305.8
130°	316.3	316.8	317.1	317.4	317.7	318.0	318.3	318.7	319.0	319.3	319.4
132.5°	329.3	329.7	330.0	330.3	330.5	330.8	331.1	331.4	331.7	332.0	332.1
135°	348.5	348.9	349.2	349.6	349.9	350.2	350.4	350.7	350.9	351.1	351.1
137.5°	366.0	366.4	366.6	366.7	366.9	367.1	367.5	367.8	368.2	368.6	368.7
140°	376.8	377.2	377.4	377.6	377.9	378.1	378.4	378.7	379.0	379.4	379.4
142.5°	387.3	387.6	387.9	388.1	388.3	388.6	388.8	389.1	389.3	389.6	389.6
145°	402.2	402.6	402.7	402.9	403.0	403.2	403.4	403.5	403.7	403.8	403.9
147.5°	415.2	415.5	415.7	415.8	416.0	416.1	416.3	416.4	416.6	416.8	416.7
150°	423.2	423.4	423.6	423.7	423.9	424.0	424.2	424.4	424.5	424.7	424.6
152.5°	430.3	430.5	430.5	430.6	430.7	430.8	431.1	431.4	431.7	432.0	431.9
155°	440.0	440.0	440.1	440.1	440.2	440.3	440.7	441.1	441.5	441.9	441.8
157.5°	448.9	448.9	448.8	448.7	448.6	448.6	449.0	449.5	450.0	450.5	450.4
160°	453.8	453.7	453.6	453.5	453.5	453.4	453.8	454.3	454.8	455.3	455.2
162.5°	458.1	457.9	457.8	457.8	457.7	457.6	458.1	458.7	459.2	459.7	459.8
165°	463.7	463.6	463.5	463.4	463.3	463.3	463.9	464.5	465.2	465.8	465.8
167.5°	467.9	467.8	467.8	467.8	467.8	467.8	468.4	469.0	469.7	470.3	470.3
170°	470.5	470.3	470.3	470.3	470.3	470.3	471.0	471.6	472.2	472.8	472.8
172.5°	471.9	471.8	471.8	471.9	472.0	472.0	472.7	473.3	473.9	474.5	474.5
175°	474.1	473.9	474.0	474.1	474.1	474.2	474.8	475.3	475.9	476.4	476.4
177.5°	474.9	474.8	474.9	474.9	475.0	475.1	475.6	476.1	476.6	477.1	477.0
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	518.5	518.3	518.5	517.8	518.5	518.3	518.5	520.8	520.8	520.9	521.1
5°	482.5	482.3	481.6	479.5	481.6	482.3	482.5	483.2	485.1	488.3	487.4
7.5°	451.0	450.7	448.7	448.7	448.7	450.7	451.0	452.9	455.0	457.0	459.3
10°	432.4	432.6	429.8	428.2	429.8	432.6	432.4	434.0	437.1	438.7	440.3
12.5°	414.3	413.3	411.0	409.2	411.0	413.3	414.3	415.6	419.7	421.6	424.7
15°	390.5	388.1	382.6	383.0	382.6	388.1	390.5	389.5	393.7	396.1	397.0
17.5°	362.4	360.7	360.6	357.3	360.6	360.7	362.4	364.2	367.9	370.4	377.1
20°	346.0	344.8	345.3	342.0	345.3	344.8	346.0	349.7	352.0	355.3	360.7
22.5°	333.1	331.9	330.0	329.0	330.0	331.9	333.1	335.7	338.2	342.8	345.7
25°	314.3	312.4	310.6	311.7	310.6	312.4	314.3	315.7	320.3	322.4	326.6
27.5°	295.5	294.1	292.2	292.0	292.2	294.1	295.5	296.8	299.4	302.9	308.0
30°	283.5	282.1	281.2	280.0	281.2	282.1	283.5	284.7	287.3	291.0	294.7
32.5°	271.4	271.1	269.5	269.2	269.5	271.1	271.4	273.3	275.9	279.4	282.6
35°	255.6	254.2	253.7	253.9	253.7	254.2	255.6	256.5	258.8	262.1	265.1
37.5°	240.5	238.7	237.8	237.0	237.8	238.7	240.5	240.7	243.0	245.2	249.3
40°	229.7	227.9	227.4	226.9	227.4	227.9	229.7	229.5	232.0	233.7	237.4
42.5°	217.6	216.9	216.6	215.7	216.6	216.9	217.6	218.9	220.3	222.7	225.5
45°	201.1	200.8	199.4	199.9	199.4	200.8	201.1	201.8	204.3	206.0	208.5
47.5°	183.6	182.6	181.6	182.3	181.6	182.6	183.6	184.6	186.3	188.3	191.7
50°	171.7	171.2	169.1	169.6	169.1	171.2	171.7	172.6	173.8	176.4	179.4
52.5°	159.8	158.0	157.2	156.9	157.2	158.0	159.8	160.7	162.1	165.0	167.3
55°	140.0	137.9	137.0	136.5	137.0	137.9	140.0	141.7	143.5	146.8	149.1
57.5°	120.6	120.1	119.3	119.8	119.3	120.1	120.6	123.3	125.2	127.7	130.6
60°	109.3	109.3	109.3	109.0	109.3	109.3	109.3	111.6	113.2	115.8	118.8
62.5°	100.5	99.9	99.8	100.1	99.8	99.9	100.5	101.5	103.2	104.8	107.5
65°	87.1	86.9	86.0	85.7	86.0	86.9	87.1	87.8	89.2	90.4	92.3
67.5°	74.5	73.7	73.4	73.1	73.4	73.7	74.5	75.1	76.0	77.5	78.5
70°	65.0	64.5	63.1	63.4	63.1	64.5	65.0	66.2	67.1	69.0	69.9
72.5°	54.8	54.3	54.0	53.7	54.0	54.3	54.8	55.9	56.8	58.9	60.4
75°	43.3	43.1	42.9	43.8	42.9	43.1	43.3	43.6	43.8	44.5	45.2
77.5°	34.7	34.7	34.9	34.5	34.9	34.7	34.7	34.7	34.7	35.1	35.2
80°	29.1	29.1	28.9	28.9	28.9	29.1	29.1	29.1	29.1	29.1	28.9
82.5°	23.3	23.5	23.7	23.3	23.7	23.5	23.3	23.7	23.9	23.5	23.7
85°	15.4	15.1	15.6	15.4	15.6	15.1	15.4	15.4	14.9	15.4	15.1
87.5°	8.9	8.6	8.6	8.8	8.6	8.6	8.9	8.5	8.5	8.4	8.2
90°	10.1	10.3	10.4	10.6	10.4	10.3	10.1	10.0	9.7	9.4	9.1
92.5°	11.4	11.5	11.6	11.7	11.6	11.5	11.4	11.4	11.1	10.6	10.1
95°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.2	12.6	12.1
97.5°	14.3	14.4	14.5	14.6	14.5	14.4	14.3	14.2	13.9	13.3	12.6
100°	14.6	14.7	14.8	14.8	14.8	14.7	14.6	14.5	14.2	13.5	12.9
102.5°	14.7	14.8	15.0	15.1	15.0	14.8	14.7	14.6	15.5	17.4	19.4
105°	15.1	15.2	15.4	15.5	15.4	15.2	15.1	14.9	21.8	35.7	49.6
107.5°	80.3	69.8	59.3	48.8	59.3	69.8	80.3	90.7	101.1	111.3	121.5
110°	130.9	119.6	108.4	97.2	108.4	119.6	130.9	142.1	149.0	151.6	154.2



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	173.8	171.5	169.1	166.7	169.1	171.5	173.8	176.2	177.4	177.3	177.3
115°	206.8	207.2	207.5	207.8	207.5	207.2	206.8	206.5	206.0	205.2	204.4
117.5°	230.6	230.7	230.8	230.8	230.8	230.7	230.6	230.6	230.2	229.6	229.0
120°	246.7	246.7	246.7	246.7	246.7	246.7	246.7	246.7	246.3	245.7	245.1
122.5°	262.0	262.1	262.1	262.2	262.1	262.1	262.0	261.9	261.7	261.3	260.8
125°	283.6	283.8	284.0	284.1	284.0	283.8	283.6	283.5	283.3	283.2	283.0
127.5°	305.6	305.5	305.3	305.2	305.3	305.5	305.6	305.8	305.8	305.5	305.2
130°	319.2	319.1	318.9	318.7	318.9	319.1	319.2	319.4	319.3	319.0	318.7
132.5°	331.8	331.6	331.4	331.2	331.4	331.6	331.8	332.1	332.0	331.7	331.4
135°	350.9	350.7	350.4	350.2	350.4	350.7	350.9	351.1	351.1	350.9	350.7
137.5°	368.5	368.4	368.2	368.1	368.2	368.4	368.5	368.7	368.6	368.2	367.8
140°	379.3	379.1	379.0	378.8	379.0	379.1	379.3	379.4	379.4	379.0	378.7
142.5°	389.4	389.1	388.9	388.7	388.9	389.1	389.4	389.6	389.6	389.3	389.1
145°	403.9	403.9	403.9	403.9	403.9	403.9	403.9	403.9	403.8	403.7	403.5
147.5°	416.3	415.9	415.6	415.2	415.6	415.9	416.3	416.7	416.8	416.6	416.4
150°	424.4	424.2	423.9	423.7	423.9	424.2	424.4	424.6	424.7	424.5	424.4
152.5°	431.6	431.2	430.8	430.5	430.8	431.2	431.6	431.9	432.0	431.7	431.4
155°	441.4	440.9	440.4	439.9	440.4	440.9	441.4	441.8	441.9	441.5	441.1
157.5°	449.8	449.2	448.5	447.9	448.5	449.2	449.8	450.4	450.5	450.0	449.5
160°	454.7	454.1	453.6	453.0	453.6	454.1	454.7	455.2	455.3	454.8	454.3
162.5°	459.3	458.8	458.3	457.8	458.3	458.8	459.3	459.8	459.7	459.2	458.7
165°	465.3	464.7	464.2	463.6	464.2	464.7	465.3	465.8	465.8	465.2	464.5
167.5°	469.7	469.0	468.4	467.8	468.4	469.0	469.7	470.3	470.3	469.7	469.0
170°	472.2	471.6	471.0	470.3	471.0	471.6	472.2	472.8	472.8	472.2	471.6
172.5°	473.8	473.1	472.4	471.7	472.4	473.1	473.8	474.5	474.5	473.9	473.3
175°	475.8	475.1	474.5	473.9	474.5	475.1	475.8	476.4	476.4	475.9	475.3
177.5°	476.4	475.8	475.1	474.5	475.1	475.8	476.4	477.0	477.1	476.6	476.1
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	519.5	522.1	524.7	527.1	530.8	532.5	534.9	535.9	538.6	542.7	546.1
5°	487.9	491.6	496.5	500.4	506.7	511.6	517.0	522.1	528.2	536.8	544.5
7.5°	461.1	464.7	470.6	478.0	484.9	491.9	499.2	506.2	514.8	527.2	539.4
10°	443.4	447.8	454.8	462.7	471.3	478.1	486.7	495.5	506.3	520.5	535.2
12.5°	428.1	431.4	439.5	447.0	456.8	465.4	473.8	484.2	496.4	511.5	529.2
15°	403.8	408.4	416.3	424.7	435.0	444.1	455.0	467.6	479.5	498.1	519.5
17.5°	379.3	386.4	394.7	404.1	411.7	424.3	436.1	449.0	463.7	483.4	507.0
20°	363.7	369.3	377.0	390.7	400.7	410.3	421.2	437.3	450.8	473.2	497.6
22.5°	350.4	354.5	363.2	374.5	386.2	397.2	408.4	423.7	440.4	461.6	488.1
25°	330.8	337.4	343.9	352.0	364.6	377.9	390.0	403.1	420.8	443.4	472.0
27.5°	311.7	317.6	324.0	334.0	343.6	356.0	368.7	383.6	402.6	426.5	455.6
30°	299.4	303.8	309.9	322.7	331.3	342.0	356.9	370.2	387.9	413.3	444.1
32.5°	286.7	292.4	299.1	308.9	319.6	329.7	343.3	357.7	375.8	400.8	432.3
35°	268.6	275.4	282.1	289.4	300.1	310.6	322.0	337.8	356.2	380.5	411.4
37.5°	252.0	257.4	262.9	271.9	282.0	292.0	302.7	318.3	335.6	361.8	390.2
40°	241.4	246.3	250.5	259.8	269.6	280.3	290.8	304.5	323.1	347.6	375.1
42.5°	229.8	234.3	240.0	247.7	258.2	267.2	277.7	290.7	308.2	333.1	357.2
45°	212.5	217.6	222.5	229.7	240.2	249.1	258.4	270.7	288.7	309.2	330.6
47.5°	194.4	199.6	205.2	212.2	221.3	230.3	239.6	250.5	266.9	287.0	301.5
50°	182.9	187.1	192.7	199.7	208.1	217.6	226.0	237.9	253.5	269.3	281.9
52.5°	171.0	174.8	181.1	188.5	196.3	204.6	213.5	223.7	237.8	252.7	262.7
55°	152.4	157.0	162.4	169.6	177.3	184.3	192.9	203.4	214.6	225.8	232.5
57.5°	135.0	138.9	143.4	150.8	157.5	165.8	173.6	181.7	192.1	200.5	204.9
60°	122.3	125.8	131.6	138.2	144.4	151.7	160.5	168.7	176.6	183.4	186.8
62.5°	110.4	114.4	119.5	125.5	132.3	139.2	146.9	153.8	160.8	166.6	169.0
65°	94.8	98.1	101.8	107.4	113.0	120.0	126.0	133.0	138.2	141.4	143.5
67.5°	80.7	82.8	85.6	89.4	94.9	101.0	106.8	112.3	116.6	118.8	120.7
70°	71.5	72.9	75.0	78.7	82.9	88.3	94.4	98.3	102.0	103.9	105.8
72.5°	62.4	64.2	66.1	69.1	72.5	76.4	80.8	85.6	87.7	89.9	91.0
75°	47.3	49.9	52.4	54.3	56.6	59.6	63.6	66.6	67.8	69.7	69.9
77.5°	35.7	36.3	38.1	40.4	42.4	44.6	47.1	49.8	50.4	51.3	52.0
80°	29.4	29.4	29.4	30.8	33.1	34.7	37.0	38.4	39.4	39.6	39.8
82.5°	23.6	23.6	23.4	23.7	24.5	25.4	27.5	29.1	29.9	29.7	29.2
85°	15.4	14.9	14.9	14.7	14.9	14.4	14.2	15.1	16.5	16.5	16.1
87.5°	8.1	7.8	7.8	7.4	7.0	6.7	5.9	5.9	5.8	6.4	6.0
90°	8.8	8.5	7.5	6.4	5.4	4.4	3.5	2.7	1.9	1.1	0.4
92.5°	9.5	9.0	8.3	7.5	6.7	6.0	5.7	5.9	6.1	6.4	6.6
95°	11.5	11.0	10.1	9.2	8.4	7.5	8.7	11.9	15.1	18.3	21.6
97.5°	12.0	11.4	17.0	22.7	28.3	34.0	37.5	39.0	40.4	41.9	43.3
100°	12.3	11.7	23.9	36.2	48.4	60.7	66.0	64.4	62.9	61.3	59.7
102.5°	21.3	23.3	36.6	50.0	63.4	76.8	82.9	81.8	80.6	79.5	78.4
105°	63.5	77.4	84.5	91.5	98.6	105.7	108.8	107.9	107.0	106.2	105.3
107.5°	131.6	141.8	140.7	139.6	138.5	137.4	136.5	135.8	135.1	134.4	133.7
110°	156.8	159.4	158.5	157.6	156.8	155.9	155.2	154.5	153.9	153.3	152.7



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	177.2	177.2	176.3	175.5	174.6	173.7	173.0	172.4	171.9	171.3	170.7
115°	203.6	202.8	202.1	201.4	200.7	200.0	199.4	198.9	198.5	198.0	197.5
117.5°	228.3	227.7	227.4	227.0	226.6	226.3	225.8	225.2	224.6	224.1	223.5
120°	244.5	243.8	243.6	243.4	243.1	242.9	242.4	241.7	241.0	240.3	239.6
122.5°	260.4	259.9	259.6	259.3	259.0	258.7	258.3	257.7	257.1	256.6	256.0
125°	282.9	282.7	282.4	282.1	281.8	281.4	281.0	280.3	279.7	279.1	278.5
127.5°	305.0	304.7	304.4	304.0	303.6	303.2	302.7	302.1	301.5	300.9	300.2
130°	318.3	318.0	317.7	317.4	317.1	316.8	316.3	315.7	315.0	314.4	313.8
132.5°	331.1	330.8	330.5	330.3	330.0	329.7	329.3	328.7	328.1	327.4	326.8
135°	350.4	350.2	349.9	349.6	349.2	348.9	348.5	348.1	347.6	347.1	346.7
137.5°	367.5	367.1	366.9	366.7	366.6	366.4	366.0	365.4	364.8	364.2	363.6
140°	378.4	378.1	377.9	377.6	377.4	377.2	376.8	376.3	375.9	375.4	374.9
142.5°	388.8	388.6	388.3	388.1	387.9	387.6	387.3	386.8	386.3	385.9	385.4
145°	403.4	403.2	403.0	402.9	402.7	402.6	402.2	401.7	401.1	400.6	400.0
147.5°	416.3	416.1	416.0	415.8	415.7	415.5	415.2	414.9	414.5	414.2	413.8
150°	424.2	424.0	423.9	423.7	423.6	423.4	423.2	423.0	422.7	422.5	422.3
152.5°	431.1	430.8	430.7	430.6	430.5	430.5	430.3	430.2	430.1	430.0	429.9
155°	440.7	440.3	440.2	440.1	440.1	440.0	440.0	440.2	440.3	440.5	440.7
157.5°	449.0	448.6	448.6	448.7	448.8	448.9	448.9	448.9	449.0	449.0	449.0
160°	453.8	453.4	453.5	453.5	453.6	453.7	453.8	453.8	453.9	454.0	454.1
162.5°	458.1	457.6	457.7	457.8	457.8	457.9	458.1	458.3	458.5	458.7	458.9
165°	463.9	463.3	463.3	463.4	463.5	463.6	463.7	464.0	464.2	464.4	464.7
167.5°	468.4	467.8	467.8	467.8	467.8	467.8	467.9	468.3	468.6	468.9	469.2
170°	471.0	470.3	470.3	470.3	470.3	470.3	470.5	470.8	471.1	471.4	471.7
172.5°	472.7	472.0	472.0	471.9	471.8	471.8	471.9	472.3	472.7	473.1	473.4
175°	474.8	474.2	474.1	474.1	474.0	473.9	474.1	474.5	474.8	475.2	475.6
177.5°	475.6	475.1	475.0	474.9	474.9	474.8	474.9	475.3	475.6	475.9	476.2
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	547.2	549.3	551.9	555.8	558.8	561.4	561.9	562.7	564.6	567.7	570.1
5°	550.8	556.1	564.7	573.1	582.2	589.7	596.7	601.6	606.2	616.0	623.9
7.5°	549.6	561.6	575.1	590.1	605.4	620.1	633.8	646.1	658.3	672.6	688.8
10°	548.9	562.9	581.1	600.4	621.6	642.3	662.4	678.0	696.1	712.5	733.2
12.5°	545.4	565.5	587.2	611.9	638.0	661.9	688.3	709.8	730.6	754.2	778.3
15°	540.7	565.2	592.7	625.5	665.2	694.0	721.1	758.6	784.2	809.8	844.3
17.5°	532.3	562.2	596.5	639.2	672.2	711.1	751.7	781.4	815.9	852.0	883.2
20°	525.6	560.3	598.8	640.7	682.9	725.0	764.4	799.8	835.5	877.2	902.8
22.5°	518.9	553.2	593.2	637.7	683.0	727.5	772.0	813.6	853.7	895.8	928.5
25°	504.6	545.4	588.7	634.2	678.9	727.8	780.9	827.3	876.9	920.3	951.3
27.5°	490.2	527.6	570.7	616.8	666.5	724.3	786.8	839.5	889.2	920.3	930.0
30°	477.1	516.7	556.4	603.2	657.0	721.5	787.9	848.3	889.0	902.6	892.5
32.5°	463.9	499.8	539.0	587.0	644.1	714.6	789.4	843.1	867.6	857.3	816.5
35°	440.6	472.9	510.9	558.9	624.6	710.8	783.3	819.6	813.6	755.3	678.4
37.5°	415.6	442.0	477.1	527.3	604.4	695.7	756.8	762.2	709.7	620.3	531.5
40°	395.8	419.6	455.7	508.1	588.7	680.8	730.2	708.5	627.2	527.7	453.6
42.5°	376.6	396.7	431.5	488.0	573.8	660.4	690.5	643.3	549.5	455.4	388.0
45°	344.1	363.0	397.9	455.9	543.3	621.6	617.6	535.6	441.7	366.0	310.1
47.5°	313.3	329.8	362.6	421.8	507.5	563.3	526.3	439.0	359.4	298.6	258.7
50°	291.5	307.8	340.4	398.9	478.8	519.5	466.7	382.6	309.6	259.3	227.6
52.5°	270.6	286.5	316.3	373.3	444.1	468.5	411.7	333.7	272.9	229.5	202.3
55°	241.4	253.5	280.3	334.8	387.7	393.3	335.7	270.5	220.4	190.1	171.5
57.5°	211.6	222.0	248.5	291.9	329.0	326.1	271.6	215.1	181.4	158.9	145.4
60°	192.2	202.5	225.8	263.0	291.0	281.2	231.1	185.7	156.8	140.3	129.5
62.5°	174.1	182.1	204.0	231.2	251.3	240.2	197.6	160.0	137.0	123.1	114.6
65°	147.9	154.5	171.9	186.2	197.3	186.6	151.2	125.1	108.6	98.8	93.0
67.5°	123.1	127.2	138.2	143.4	151.3	139.5	113.7	96.2	86.8	78.6	74.5
70°	107.4	110.4	116.3	120.5	122.5	110.4	91.3	78.5	70.6	64.8	62.2
72.5°	91.7	94.4	95.6	99.0	97.9	86.6	73.4	63.2	57.5	53.6	50.3
75°	70.1	71.3	70.1	68.7	65.7	57.8	48.7	43.6	39.4	37.5	36.3
77.5°	51.1	50.7	49.2	47.0	41.8	36.8	31.9	30.2	28.4	27.4	27.0
80°	39.4	38.4	37.0	33.5	29.1	25.6	24.5	23.3	22.6	21.4	21.2
82.5°	29.3	28.7	26.4	23.5	20.4	18.7	17.8	17.3	16.6	16.0	16.0
85°	15.6	14.9	12.3	10.7	10.3	9.8	9.6	9.6	8.6	8.4	8.4
87.5°	5.3	4.3	4.3	3.9	4.0	3.9	4.3	4.1	4.1	4.4	4.1
90°	1.1	1.9	2.7	3.5	4.4	5.4	6.4	7.5	8.5	8.8	9.1
92.5°	6.4	6.1	5.9	5.7	6.0	6.7	7.5	8.3	9.0	9.5	10.1
95°	18.3	15.1	11.9	8.7	7.5	8.4	9.2	10.1	11.0	11.5	12.1
97.5°	41.9	40.4	39.0	37.5	34.0	28.3	22.7	17.0	11.4	12.0	12.6
100°	61.3	62.9	64.4	66.0	60.7	48.4	36.2	23.9	11.7	12.3	12.9
102.5°	79.5	80.6	81.8	82.9	76.8	63.4	50.0	36.6	23.3	21.3	19.4
105°	106.2	107.0	107.9	108.8	105.7	98.6	91.5	84.5	77.4	63.5	49.6
107.5°	134.4	135.1	135.8	136.5	137.4	138.5	139.6	140.7	141.8	131.6	121.5
110°	153.3	153.9	154.5	155.2	155.9	156.8	157.6	158.5	159.4	156.8	154.2



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	171.3	171.9	172.4	173.0	173.7	174.6	175.5	176.3	177.2	177.2	177.3
115°	198.0	198.5	198.9	199.4	200.0	200.7	201.4	202.1	202.8	203.6	204.4
117.5°	224.1	224.6	225.2	225.8	226.3	226.6	227.0	227.4	227.7	228.3	229.0
120°	240.3	241.0	241.7	242.4	242.9	243.1	243.4	243.6	243.8	244.5	245.1
122.5°	256.6	257.1	257.7	258.3	258.7	259.0	259.3	259.6	259.9	260.4	260.8
125°	279.1	279.7	280.3	281.0	281.4	281.8	282.1	282.4	282.7	282.9	283.0
127.5°	300.9	301.5	302.1	302.7	303.2	303.6	304.0	304.4	304.7	305.0	305.2
130°	314.4	315.0	315.7	316.3	316.8	317.1	317.4	317.7	318.0	318.3	318.7
132.5°	327.4	328.1	328.7	329.3	329.7	330.0	330.3	330.5	330.8	331.1	331.4
135°	347.1	347.6	348.1	348.5	348.9	349.2	349.6	349.9	350.2	350.4	350.7
137.5°	364.2	364.8	365.4	366.0	366.4	366.6	366.7	366.9	367.1	367.5	367.8
140°	375.4	375.9	376.3	376.8	377.2	377.4	377.6	377.9	378.1	378.4	378.7
142.5°	385.9	386.3	386.8	387.3	387.6	387.9	388.1	388.3	388.6	388.8	389.1
145°	400.6	401.1	401.7	402.2	402.6	402.7	402.9	403.0	403.2	403.4	403.5
147.5°	414.2	414.5	414.9	415.2	415.5	415.7	415.8	416.0	416.1	416.3	416.4
150°	422.5	422.7	423.0	423.2	423.4	423.6	423.7	423.9	424.0	424.2	424.4
152.5°	430.0	430.1	430.2	430.3	430.5	430.5	430.6	430.7	430.8	431.1	431.4
155°	440.5	440.3	440.2	440.0	440.0	440.1	440.1	440.2	440.3	440.7	441.1
157.5°	449.0	449.0	448.9	448.9	448.9	448.8	448.7	448.6	448.6	449.0	449.5
160°	454.0	453.9	453.8	453.8	453.7	453.6	453.5	453.5	453.4	453.8	454.3
162.5°	458.7	458.5	458.3	458.1	457.9	457.8	457.8	457.7	457.6	458.1	458.7
165°	464.4	464.2	464.0	463.7	463.6	463.5	463.4	463.3	463.3	463.9	464.5
167.5°	468.9	468.6	468.3	467.9	467.8	467.8	467.8	467.8	467.8	468.4	469.0
170°	471.4	471.1	470.8	470.5	470.3	470.3	470.3	470.3	470.3	471.0	471.6
172.5°	473.1	472.7	472.3	471.9	471.8	471.8	471.9	472.0	472.0	472.7	473.3
175°	475.2	474.8	474.5	474.1	473.9	474.0	474.1	474.1	474.2	474.8	475.3
177.5°	475.9	475.6	475.3	474.9	474.8	474.9	474.9	475.0	475.1	475.6	476.1
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	574.1	574.1	574.8	577.6	578.0	580.4	579.7
5°	630.9	635.3	637.0	644.0	648.1	650.0	646.3
7.5°	700.4	712.9	718.8	726.2	732.6	734.6	729.5
10°	751.1	764.2	775.1	781.9	788.2	792.4	797.7
12.5°	800.1	816.2	826.6	836.1	842.6	847.9	848.8
15°	853.4	877.6	896.0	909.6	916.3	919.8	918.4
17.5°	907.1	929.6	942.7	956.5	965.8	966.3	966.6
20°	937.5	959.4	974.6	984.8	995.3	994.8	997.2
22.5°	957.8	975.1	986.7	994.1	997.7	995.9	996.4
25°	967.3	972.5	970.4	958.5	955.4	944.5	946.4
27.5°	918.3	894.1	869.0	836.8	811.3	791.0	792.0
30°	851.8	808.9	760.0	719.0	682.2	671.9	650.0
32.5°	758.8	694.5	637.2	598.9	567.4	558.8	539.7
35°	601.1	538.6	479.7	444.3	430.3	410.7	410.5
37.5°	467.2	412.2	381.1	354.5	340.6	328.7	327.6
40°	393.0	350.2	326.6	307.5	293.8	284.9	282.8
42.5°	341.2	306.6	284.5	272.7	262.1	257.5	254.1
45°	278.6	255.3	240.0	229.3	224.4	220.9	219.0
47.5°	233.1	217.5	207.0	199.8	195.9	192.2	193.2
50°	208.3	195.5	187.8	181.0	178.0	175.4	175.7
52.5°	188.3	176.8	170.6	165.7	162.0	160.1	159.3
55°	159.8	152.6	146.3	142.8	140.7	138.2	137.5
57.5°	136.3	130.7	125.6	121.7	121.1	118.7	119.0
60°	120.7	116.0	111.8	109.7	108.1	106.0	106.7
62.5°	107.8	103.9	100.1	98.4	96.7	95.2	95.5
65°	88.3	84.6	82.2	81.3	80.6	79.9	79.2
67.5°	70.4	68.1	66.6	64.6	63.2	63.0	62.3
70°	59.2	56.1	53.6	51.0	50.3	50.1	50.3
72.5°	47.4	45.5	44.8	43.6	43.4	42.8	43.2
75°	35.6	34.9	34.5	33.5	33.5	33.5	33.5
77.5°	26.3	25.9	25.6	25.4	25.2	24.8	24.8
80°	20.5	20.3	19.8	19.8	19.6	19.8	19.6
82.5°	15.5	15.4	15.0	15.0	14.7	14.6	14.7
85°	7.9	7.7	8.2	7.7	7.9	7.5	7.9
87.5°	4.1	4.2	4.0	4.1	3.9	4.3	4.0
90°	9.4	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	10.6	11.1	11.4	11.4	11.5	11.6	11.7
95°	12.6	13.2	13.4	13.4	13.4	13.4	13.4
97.5°	13.3	13.9	14.2	14.3	14.4	14.5	14.6
100°	13.5	14.2	14.5	14.6	14.7	14.8	14.8
102.5°	17.4	15.5	14.6	14.7	14.8	15.0	15.1
105°	35.7	21.8	14.9	15.1	15.2	15.4	15.5
107.5°	111.3	101.1	90.7	80.3	69.8	59.3	48.8
110°	151.6	149.0	142.1	130.9	119.6	108.4	97.2



TEST NUMBER: P332240

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	177.3	177.4	176.2	173.8	171.5	169.1	166.7
115°	205.2	206.0	206.5	206.8	207.2	207.5	207.8
117.5°	229.6	230.2	230.6	230.6	230.7	230.8	230.8
120°	245.7	246.3	246.7	246.7	246.7	246.7	246.7
122.5°	261.3	261.7	261.9	262.0	262.1	262.1	262.2
125°	283.2	283.3	283.5	283.6	283.8	284.0	284.1
127.5°	305.5	305.8	305.8	305.6	305.5	305.3	305.2
130°	319.0	319.3	319.4	319.2	319.1	318.9	318.7
132.5°	331.7	332.0	332.1	331.8	331.6	331.4	331.2
135°	350.9	351.1	351.1	350.9	350.7	350.4	350.2
137.5°	368.2	368.6	368.7	368.5	368.4	368.2	368.1
140°	379.0	379.4	379.4	379.3	379.1	379.0	378.8
142.5°	389.3	389.6	389.6	389.4	389.1	388.9	388.7
145°	403.7	403.8	403.9	403.9	403.9	403.9	403.9
147.5°	416.6	416.8	416.7	416.3	415.9	415.6	415.2
150°	424.5	424.7	424.6	424.4	424.2	423.9	423.7
152.5°	431.7	432.0	431.9	431.6	431.2	430.8	430.5
155°	441.5	441.9	441.8	441.4	440.9	440.4	439.9
157.5°	450.0	450.5	450.4	449.8	449.2	448.5	447.9
160°	454.8	455.3	455.2	454.7	454.1	453.6	453.0
162.5°	459.2	459.7	459.8	459.3	458.8	458.3	457.8
165°	465.2	465.8	465.8	465.3	464.7	464.2	463.6
167.5°	469.7	470.3	470.3	469.7	469.0	468.4	467.8
170°	472.2	472.8	472.8	472.2	471.6	471.0	470.3
172.5°	473.9	474.5	474.5	473.8	473.1	472.4	471.7
175°	475.9	476.4	476.4	475.8	475.1	474.5	473.9
177.5°	476.6	477.1	477.0	476.4	475.8	475.1	474.5
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)