

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332245

Luminaire Tested: **S123RDIP-S340D365U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332245  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D365U835-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2612.6 lumens  
Efficiency: N/A  
Efficacy: 128.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332245

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332245

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48	43
2	90	82	76	71	82	76	71	67	65	61	58	54	51	49	44	42	41	36
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27
5	69	58	50	44	63	54	46	41	46	40	36	39	35	31	32	29	27	23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	25	21	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6184	6184	6184
5°	6207	6122	6158
10°	6172	6045	6025
15°	6107	5904	5841
20°	6015	5727	5593
25°	5922	5529	5352
30°	5797	5299	5009
35°	5670	5070	4696
40°	5552	4799	4308
45°	5398	4532	3958
50°	5228	4228	3565
55°	5054	3883	3200
60°	4895	3511	2799
65°	4689	3110	2397
70°	4428	2609	1936
75°	4051	2054	1822
80°	3608	1822	1674
85°	3051	1606	1494



TEST NUMBER: P332245

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.0	2.1
10°-20°	150.1	5.7
20°-30°	216.1	8.3
30°-40°	243.5	9.3
40°-50°	232.9	8.9
50°-60°	190.7	7.3
60°-70°	128.7	4.9
70°-80°	64.7	2.5
80°-90°	18.5	0.7
90°-100°	97.2	3.7
100°-110°	275.1	10.5
110°-120°	270.6	10.4
120°-130°	215.9	8.3
130°-140°	170.2	6.5
140°-150°	127.0	4.9
150°-160°	88.5	3.4
160°-170°	52.0	2.0
170°-180°	16.9	0.6
0°-30°	420.2	16.1
0°-40°	663.7	25.4
0°-60°	1087.3	41.6
0°-90°	1299.2	49.7
90°-120°	642.9	24.6
90°-150°	1155.9	44.2
90°-180°	1313.0	50.3
0°-180°	2612.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	574	574	574	574	574	
5°	574	572	567	570	570	54
15°	548	542	530	527	524	154
25°	499	486	466	456	451	229
35°	432	414	386	366	357	270
45°	355	333	298	272	260	273
55°	269	246	207	181	170	241
65°	184	158	122	100	94	182
75°	97	75	49	45	44	104
85°	25	15	13	12	12	28
90°	1	4	9	10	10	2
95°	12	39	210	61	41	13
105°	41	61	284	497	450	44
115°	72	90	217	477	547	72
125°	101	119	203	368	431	89
135°	118	141	200	303	350	91
145°	135	154	198	248	273	84
155°	153	165	191	217	226	70
165°	167	172	183	194	198	47
175°	174	174	176	178	178	17
180°	175	175	175	175	175	



TEST NUMBER: P332245

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	576.4	576.0	575.7	575.4	575.1	574.4	573.4	572.4	571.4	570.4	571.3
5°	574.5	574.0	573.5	573.0	572.4	571.6	570.3	569.1	567.8	566.6	567.5
7.5°	569.2	568.6	568.1	567.5	567.0	565.9	564.3	562.7	561.0	559.4	559.9
10°	564.7	564.0	563.3	562.6	561.8	560.5	558.7	556.8	554.9	553.1	553.2
12.5°	558.4	557.6	556.8	556.0	555.2	553.6	551.3	549.1	546.8	544.5	544.4
15°	548.0	546.8	545.7	544.5	543.4	541.4	538.5	535.6	532.7	529.8	529.3
17.5°	534.8	533.5	532.2	530.8	529.5	527.0	523.3	519.6	516.0	512.3	511.2
20°	525.1	523.5	521.8	520.2	518.5	515.7	511.8	507.8	503.9	500.0	498.6
22.5°	514.3	512.4	510.5	508.6	506.7	503.7	499.5	495.3	491.1	486.9	485.2
25°	498.6	496.0	493.4	490.8	488.2	484.5	479.8	475.0	470.2	465.5	463.3
27.5°	479.5	476.6	473.7	470.9	468.0	464.0	458.7	453.3	448.0	442.7	439.7
30°	466.4	463.3	460.2	457.1	454.0	449.5	443.7	437.9	432.1	426.3	422.8
32.5°	453.4	449.8	446.3	442.8	439.3	434.5	428.3	422.2	416.1	409.9	406.1
35°	431.5	427.7	424.0	420.3	416.6	411.5	405.1	398.6	392.2	385.8	381.4
37.5°	409.3	405.1	401.0	396.9	392.7	387.2	380.4	373.5	366.7	359.8	354.8
40°	395.1	390.6	386.0	381.5	376.9	370.9	363.6	356.2	348.9	341.5	336.2
42.5°	379.1	374.5	370.0	365.4	360.9	354.8	347.2	339.6	332.0	324.4	318.5
45°	354.6	349.9	345.3	340.6	335.9	329.6	321.7	313.7	305.7	297.7	291.8
47.5°	330.1	325.0	319.8	314.7	309.6	303.1	295.1	287.1	279.2	271.2	264.8
50°	312.2	307.3	302.5	297.6	292.7	286.1	277.7	269.3	260.9	252.5	246.1
52.5°	296.2	290.9	285.6	280.3	275.0	268.2	259.9	251.6	243.3	235.0	228.4
55°	269.3	264.2	259.2	254.1	249.0	242.1	233.3	224.5	215.7	206.9	200.9
57.5°	244.5	239.0	233.5	227.9	222.4	215.2	206.4	197.5	188.7	179.9	174.2
60°	227.4	221.7	216.0	210.3	204.6	197.5	188.9	180.3	171.7	163.1	157.5
62.5°	210.2	204.5	198.8	193.2	187.5	180.3	171.7	163.1	154.5	145.9	140.7
65°	184.1	178.4	172.7	167.0	161.3	154.4	146.3	138.2	130.2	122.1	117.0
67.5°	157.9	152.1	146.3	140.6	134.8	128.1	120.3	112.6	104.8	97.1	93.3
70°	140.7	135.1	129.5	123.9	118.4	111.9	104.7	97.4	90.2	82.9	79.3
72.5°	123.6	118.1	112.6	107.0	101.5	95.5	88.9	82.3	75.7	69.1	66.2
75°	97.4	92.4	87.4	82.5	77.5	72.2	66.5	60.8	55.1	49.4	48.4
77.5°	73.5	69.0	64.5	60.0	55.6	51.5	47.8	44.1	40.5	36.8	36.3
80°	58.2	54.0	49.8	45.5	41.3	38.1	35.9	33.7	31.5	29.4	29.0
82.5°	43.7	40.0	36.4	32.7	29.0	26.7	25.7	24.7	23.7	22.6	22.3
85°	24.7	22.4	20.1	17.9	15.6	14.3	14.0	13.7	13.4	13.0	12.8
87.5°	9.1	8.3	7.5	6.8	6.1	5.8	6.0	6.2	6.4	6.6	6.5
90°	0.7	1.4	2.1	3.2	3.9	4.6	5.7	6.7	7.8	8.8	8.5
92.5°	4.4	6.5	9.5	12.2	15.2	20.4	29.7	44.9	59.8	54.3	41.0
95°	12.0	13.1	17.0	23.0	32.2	45.9	76.0	128.6	186.6	209.6	170.0
97.5°	20.5	20.8	23.9	29.1	38.2	53.1	81.8	141.1	237.8	324.8	347.4
100°	26.2	26.5	29.0	33.9	42.4	56.2	80.9	133.2	226.2	334.7	404.3
102.5°	32.1	32.7	34.9	39.6	47.2	59.9	82.1	126.4	209.2	316.3	407.1
105°	41.0	42.1	44.2	48.4	55.1	66.1	85.2	121.6	188.4	284.1	385.5
107.5°	50.5	51.5	53.6	57.7	64.0	74.2	91.0	121.2	175.1	255.7	347.8
110°	57.2	58.3	60.1	64.0	70.0	79.9	95.8	122.6	170.0	239.6	324.1



TEST NUMBER: P332245

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	63.5	64.5	66.3	70.2	76.2	85.8	100.6	125.5	167.1	228.8	303.4
115°	72.4	73.9	76.0	79.5	85.5	95.1	108.5	130.0	166.1	217.3	278.5
117.5°	81.4	83.0	84.8	88.1	94.8	103.6	116.9	136.1	166.7	210.5	263.4
120°	87.6	88.7	90.5	94.0	100.7	109.5	122.3	140.6	167.9	207.4	255.5
122.5°	93.0	94.1	95.8	99.7	106.1	115.5	127.9	144.9	169.8	205.5	249.0
125°	100.7	101.4	103.5	107.4	114.1	123.7	136.1	151.6	172.8	202.8	240.7
127.5°	106.6	107.6	110.3	114.2	121.6	131.2	143.1	157.1	176.2	201.6	233.3
130°	110.3	111.3	114.5	118.7	126.2	135.7	147.4	160.8	178.5	200.7	229.3
132.5°	113.1	114.4	117.9	123.0	130.4	139.7	151.0	164.2	180.2	200.4	225.7
135°	118.0	119.4	123.3	128.6	136.1	145.6	156.5	168.6	182.7	200.0	220.9
137.5°	122.7	124.2	128.0	133.6	141.0	149.8	160.4	171.8	184.4	199.2	216.7
140°	125.8	127.6	131.1	136.8	143.8	152.7	162.9	173.5	185.5	199.0	214.1
142.5°	129.2	130.7	134.5	139.6	146.7	154.9	164.9	175.2	186.4	198.4	211.9
145°	134.6	135.7	138.9	144.2	150.2	158.3	167.5	177.0	186.9	197.5	208.8
147.5°	140.2	140.8	143.9	148.5	154.3	161.2	169.6	178.2	186.9	196.2	205.9
150°	143.8	144.2	147.0	151.6	156.5	162.9	171.0	178.5	186.9	195.1	203.9
152.5°	147.5	147.6	150.4	154.4	158.8	164.9	171.9	179.0	186.1	193.7	201.6
155°	153.0	153.0	155.1	158.7	162.6	167.5	173.5	179.2	185.2	191.2	198.2
157.5°	157.4	157.7	159.4	162.5	165.8	169.6	174.4	179.5	184.0	189.0	194.4
160°	160.8	160.8	162.2	165.0	167.5	171.0	175.3	179.5	183.4	187.3	191.9
162.5°	163.3	163.3	164.5	166.7	168.9	171.9	175.6	179.2	182.3	185.6	189.3
165°	167.1	166.8	167.5	169.3	170.7	173.2	176.0	178.5	180.6	183.1	185.9
167.5°	170.0	169.6	170.0	171.3	172.3	173.9	175.9	177.9	178.9	180.5	182.6
170°	171.7	171.0	171.4	172.4	173.2	173.9	175.6	177.0	177.8	178.8	180.6
172.5°	172.9	172.4	172.5	173.3	173.7	174.1	175.6	176.8	176.9	177.4	178.6
175°	174.2	173.9	173.5	174.2	174.2	174.6	175.3	176.0	175.6	175.6	176.3
177.5°	174.9	174.6	174.3	174.6	174.6	174.6	174.9	175.4	174.9	174.6	174.9
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332245

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	572.2	573.1	574.1	574.4	574.3	574.1	573.9	573.8
5°	568.5	569.4	570.3	570.7	570.5	570.3	570.1	569.9
7.5°	560.5	561.0	561.5	561.6	561.2	560.9	560.5	560.2
10°	553.3	553.4	553.5	553.3	552.8	552.3	551.7	551.2
12.5°	544.4	544.3	544.3	543.9	543.3	542.7	542.1	541.5
15°	528.7	528.2	527.7	527.1	526.4	525.6	524.9	524.2
17.5°	510.1	509.0	507.9	506.8	505.7	504.6	503.6	502.5
20°	497.3	495.9	494.6	493.3	492.0	490.8	489.6	488.3
22.5°	483.6	481.9	480.2	478.8	477.6	476.5	475.3	474.2
25°	461.1	459.0	456.8	455.1	454.0	452.9	451.7	450.6
27.5°	436.7	433.7	430.7	428.3	426.5	424.8	423.1	421.3
30°	419.3	415.8	412.3	409.7	408.0	406.4	404.7	403.0
32.5°	402.2	398.4	394.5	391.7	390.0	388.3	386.5	384.8
35°	376.9	372.4	368.0	364.8	363.0	361.1	359.2	357.4
37.5°	349.7	344.6	339.6	335.9	333.6	331.3	329.0	326.7
40°	330.8	325.4	320.0	316.1	313.7	311.4	309.0	306.6
42.5°	312.6	306.8	300.9	296.9	294.7	292.6	290.5	288.3
45°	285.9	280.0	274.1	269.9	267.5	265.0	262.5	260.0
47.5°	258.3	251.9	245.5	241.2	239.0	236.8	234.5	232.3
50°	239.7	233.3	226.9	222.5	220.1	217.7	215.3	212.9
52.5°	221.7	215.0	208.4	204.0	201.8	199.7	197.6	195.4
55°	194.9	188.9	182.9	178.8	176.8	174.7	172.6	170.5
57.5°	168.5	162.8	157.2	153.4	151.7	149.9	148.2	146.4
60°	151.9	146.3	140.7	137.0	135.3	133.5	131.8	130.0
62.5°	135.4	130.2	124.9	121.3	119.5	117.7	115.8	114.0
65°	111.9	106.9	101.8	98.7	97.5	96.4	95.3	94.1
67.5°	89.5	85.7	81.9	79.4	78.2	77.0	75.8	74.6
70°	75.7	72.1	68.4	66.1	64.9	63.8	62.6	61.5
72.5°	63.2	60.3	57.3	55.6	55.1	54.6	54.2	53.7
75°	47.3	46.3	45.2	44.6	44.4	44.2	44.0	43.8
77.5°	35.7	35.1	34.6	34.2	34.0	33.8	33.6	33.4
80°	28.7	28.4	28.1	27.9	27.6	27.4	27.2	27.0
82.5°	22.0	21.7	21.4	21.2	21.2	21.1	21.1	21.1
85°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
87.5°	6.4	6.4	6.4	6.5	6.3	6.3	6.3	6.1
90°	8.8	9.2	9.5	10.2	9.9	10.2	10.6	10.2
92.5°	29.8	23.6	20.8	19.0	18.4	17.3	17.7	17.0
95°	127.2	86.2	67.5	54.8	48.1	44.9	42.4	41.0
97.5°	317.1	254.0	208.4	166.2	140.1	124.2	114.6	111.6
100°	416.6	388.0	346.7	296.5	260.8	235.0	221.2	221.6
102.5°	449.7	448.8	424.7	392.9	365.1	344.7	333.2	325.0
105°	459.4	494.7	501.4	492.3	476.0	462.6	451.3	449.5
107.5°	431.5	488.9	519.9	532.5	532.8	528.2	524.4	521.2
110°	405.0	470.0	514.5	539.3	549.2	552.0	551.3	550.6





TEST NUMBER: P332245

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	378.7	445.1	495.0	526.8	544.9	553.7	556.4	556.5
115°	343.8	405.3	457.3	495.8	522.3	537.8	544.9	546.7
117.5°	318.6	371.7	418.3	457.4	485.1	502.9	513.0	515.4
120°	305.3	353.0	395.4	431.1	459.0	478.8	487.3	489.4
122.5°	294.9	338.0	377.3	410.5	435.3	453.1	462.4	465.1
125°	280.9	319.5	353.4	381.7	404.3	419.8	428.7	431.1
127.5°	268.8	303.1	333.7	359.5	379.6	392.9	400.9	403.1
130°	261.1	293.0	321.6	345.6	364.3	377.1	384.5	387.3
132.5°	254.1	283.3	310.0	332.9	350.5	363.2	369.8	371.8
135°	244.5	269.6	292.6	312.7	330.1	340.7	347.0	349.5
137.5°	235.8	256.4	276.2	293.7	308.2	319.0	324.3	326.0
140°	230.8	248.8	265.7	280.9	294.4	304.3	309.9	309.6
142.5°	226.0	241.4	256.1	269.3	280.8	289.6	294.6	294.3
145°	220.2	231.8	243.1	253.4	262.2	269.6	272.5	273.2
147.5°	215.4	224.7	233.8	241.1	247.8	252.8	255.5	255.8
150°	212.0	220.2	227.6	234.3	239.6	243.5	245.6	245.6
152.5°	208.9	215.9	222.5	228.1	232.2	235.8	237.1	237.1
155°	204.3	209.9	215.2	219.4	222.6	225.5	226.2	226.5
157.5°	199.3	204.0	208.1	211.5	214.2	216.3	216.9	216.8
160°	196.5	200.4	203.9	206.4	208.8	211.0	211.0	210.6
162.5°	193.1	196.4	199.7	201.9	203.5	205.3	205.3	205.0
165°	188.7	190.8	193.3	195.1	196.5	197.9	197.5	197.5
167.5°	184.9	186.5	187.9	189.2	189.8	190.8	190.5	190.5
170°	182.3	183.4	184.8	185.5	185.9	186.6	186.2	186.2
172.5°	180.1	180.9	182.0	182.4	182.5	183.2	182.6	182.3
175°	177.0	177.4	178.1	178.1	178.1	178.5	178.1	177.8
177.5°	175.1	175.4	175.7	175.7	175.4	175.7	175.1	175.1
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6

(END OF REPORT)