

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832015

Luminaire Tested: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832015
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U840-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7805.1 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832015
CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P832015

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64				
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61	56				
2	94	87	81	76	88	82	77	73	73	69	66	64	62	59	57	55	53	49				
3	86	77	71	65	81	73	67	62	65	61	57	58	54	51	51	49	46	43				
4	80	69	62	56	75	66	59	54	59	54	49	53	48	45	47	44	41	38				
5	74	63	55	49	69	60	53	47	54	48	44	48	44	40	43	39	37	34				
6	68	57	49	44	64	54	47	42	49	43	39	44	39	36	39	36	33	30				
7	64	52	44	39	60	50	43	38	45	39	35	41	36	32	36	33	30	28				
8	60	48	40	35	56	46	39	34	41	36	32	38	33	30	34	30	27	25				
9	56	44	37	32	53	42	36	31	38	33	29	35	30	27	32	28	25	23				
10	53	41	34	29	50	39	33	28	36	30	27	33	28	25	30	26	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	40739	40739	40739	40739	40739
5°	48372	46830	40995	33140	30767
10°	43827	47566	40791	26552	22778
15°	30175	40783	40360	21702	18018
20°	20992	31400	39550	18299	15837
25°	15997	23931	38371	16264	14596
30°	13926	19132	36896	15101	13520
35°	12786	16139	34807	14121	12540
40°	11665	14412	32073	13159	11643
45°	10535	13181	29125	12248	10749
50°	9562	12161	25648	11355	9640
55°	8649	11168	22308	10483	8270
60°	7750	10155	19375	9522	7817
65°	7154	9011	16677	8558	7391
70°	5813	7789	14552	7742	6008
75°	5099	6197	12327	6421	5290
80°	4618	5244	10098	5387	5002
85°	4211	4594	7669	4891	4594

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 30731 cd/sqm



TEST NUMBER: P832015

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.0	4.4
10°-20°	798.3	10.2
20°-30°	915.9	11.7
30°-40°	902.8	11.6
40°-50°	796.1	10.2
50°-60°	612.5	7.8
60°-70°	402.7	5.2
70°-80°	195.6	2.5
80°-90°	51.4	0.7
90°-100°	64.7	0.8
100°-110°	195.8	2.5
110°-120°	333.4	4.3
120°-130°	438.6	5.6
130°-140°	493.0	6.3
140°-150°	484.7	6.2
150°-160°	408.0	5.2
160°-170°	271.6	3.5
170°-180°	95.1	1.2
0°-30°	2059.1	26.4
0°-40°	2961.9	37.9
0°-60°	4370.5	56.0
0°-90°	5020.1	64.3
90°-120°	593.9	7.6
90°-150°	2010.1	25.8
90°-180°	2785.0	35.7
0°-180°	7805.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3785	3785	3785	3785	3785	
5°	4477	4334	3794	3067	2848	409
15°	2708	3660	3622	1948	1617	764
25°	1347	2015	3231	1369	1229	636
35°	973	1228	2649	1075	954	607
45°	692	866	1913	805	706	537
55°	461	595	1189	559	441	413
65°	281	354	655	336	290	275
75°	123	149	296	154	127	132
85°	34	37	62	40	37	36
90°	24	19	1	19	24	13
95°	62	58	47	58	62	62
105°	188	186	178	186	188	199
115°	336	336	336	336	336	333
125°	486	492	491	492	486	434
135°	636	641	637	641	636	490
145°	773	777	773	777	773	483
155°	884	886	885	886	884	407
165°	961	962	964	962	961	271
175°	999	1000	1003	1000	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P832015

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8
2.5°	4194.4	4181.2	4168.0	4164.2	4160.3	4147.9	4135.5	4107.5	4079.6	4050.9	4022.2
5°	4476.8	4478.4	4479.9	4476.1	4472.2	4455.9	4439.6	4405.5	4371.3	4334.1	4296.8
7.5°	4389.9	4414.8	4439.6	4444.3	4448.9	4461.3	4473.7	4466.0	4458.2	4444.3	4430.3
10°	4009.8	4008.2	4006.7	4034.6	4062.5	4145.5	4228.6	4271.2	4313.9	4351.9	4389.9
12.5°	3389.1	3391.4	3393.7	3485.3	3576.8	3655.2	3733.5	3842.2	3950.8	4067.9	4185.1
15°	2707.8	2745.8	2783.9	2865.3	2946.8	3064.7	3182.7	3328.5	3474.4	3659.8	3845.3
17.5°	2223.7	2240.0	2256.3	2334.6	2413.0	2524.7	2636.4	2801.7	2967.0	3205.9	3444.9
20°	1832.6	1847.4	1862.1	1918.8	1975.4	2082.5	2189.5	2347.0	2504.5	2741.2	2977.8
22.5°	1530.0	1558.7	1587.5	1625.5	1663.5	1741.1	1818.7	1979.3	2139.9	2355.6	2571.3
25°	1346.9	1360.1	1373.3	1405.9	1438.5	1513.0	1587.5	1693.8	1800.0	2015.0	2229.9
27.5°	1222.8	1226.7	1230.5	1254.6	1278.7	1326.8	1374.9	1473.4	1571.9	1748.8	1925.7
30°	1120.4	1127.4	1134.3	1153.0	1171.6	1206.5	1241.4	1311.2	1381.1	1539.3	1697.6
32.5°	1041.2	1045.1	1049.0	1064.5	1080.0	1105.6	1131.2	1186.3	1241.4	1362.4	1483.5
35°	973.0	973.7	974.5	986.1	997.8	1022.6	1047.4	1093.2	1139.0	1228.2	1317.4
37.5°	895.4	900.8	906.2	914.8	923.3	945.0	966.7	1004.0	1041.2	1114.9	1188.7
40°	830.2	834.8	839.5	849.6	859.7	876.7	893.8	928.0	962.1	1025.7	1089.3
42.5°	765.0	768.1	771.2	781.3	791.4	812.3	833.3	860.5	887.6	940.4	993.1
45°	692.1	699.8	707.6	718.5	729.3	747.2	765.0	793.0	820.9	865.9	910.9
47.5°	631.6	635.4	639.3	648.6	657.9	679.7	701.4	726.2	751.1	793.0	834.8
50°	571.0	572.6	574.2	582.7	591.2	610.6	630.0	658.7	687.4	726.2	765.0
52.5°	513.6	517.5	521.4	529.9	538.5	551.7	564.8	594.3	623.8	661.8	699.8
55°	460.9	463.2	465.5	471.7	477.9	493.5	509.0	534.6	560.2	595.1	630.0
57.5°	411.2	414.3	417.4	422.1	426.7	440.7	454.7	477.2	499.7	534.6	569.5
60°	360.0	363.9	367.8	373.2	378.6	389.5	400.4	420.5	440.7	471.7	502.8
62.5°	322.8	323.5	324.3	329.0	333.6	341.4	349.1	365.4	381.7	412.8	443.8
65°	280.9	283.2	285.5	287.9	290.2	296.4	302.6	316.6	330.5	353.8	377.1
67.5°	237.4	239.7	242.1	246.0	249.8	255.3	260.7	270.0	279.3	301.0	322.8
70°	184.7	184.7	184.7	190.9	197.1	206.4	215.7	222.7	229.7	247.5	265.4
72.5°	150.5	151.3	152.1	152.8	153.6	159.1	164.5	176.1	187.8	198.6	209.5
75°	122.6	123.4	124.1	124.9	125.7	127.2	128.8	132.7	136.6	149.0	161.4
77.5°	97.8	98.5	99.3	100.1	100.9	102.4	104.0	105.5	107.1	111.7	116.4
80°	74.5	75.3	76.0	76.8	77.6	78.4	79.1	80.7	82.2	84.6	86.9
82.5°	54.3	54.3	54.3	54.3	54.3	55.9	57.4	57.4	57.4	59.0	60.5
85°	34.1	34.1	34.1	34.9	35.7	35.7	35.7	36.5	37.2	37.2	37.2
87.5°	15.5	14.7	14.0	14.7	15.5	15.5	15.5	16.3	17.1	17.1	17.1
90°	23.7	23.3	23.0	22.6	22.3	21.8	21.1	20.4	19.7	18.9	16.7
92.5°	34.0	34.3	34.7	35.0	35.4	35.3	34.7	34.2	33.7	33.2	32.1
95°	61.6	61.6	61.6	61.6	61.6	61.2	60.5	59.8	59.1	58.4	57.0
97.5°	88.4	88.6	88.8	89.0	89.1	88.8	87.9	87.0	86.1	85.3	84.2
100°	120.0	119.7	119.3	119.0	118.6	118.2	117.6	117.1	116.6	116.1	115.2
102.5°	152.4	152.6	152.7	152.9	153.1	152.9	152.4	151.9	151.3	150.8	149.6
105°	187.9	187.6	187.2	186.9	186.5	186.3	186.3	186.3	186.3	186.3	184.8
107.5°	224.2	224.4	224.6	224.8	224.9	224.8	224.2	223.7	223.2	222.7	222.0
110°	261.3	261.7	262.0	262.4	262.7	262.6	261.9	261.2	260.5	259.8	259.4



TEST NUMBER: P832015

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	300.8	300.8	300.8	300.8	300.8	300.4	299.5	298.6	297.8	296.9	296.9
115°	336.4	336.5	336.7	336.9	337.1	337.1	336.9	336.7	336.5	336.4	336.7
117.5°	372.7	373.2	373.7	374.2	374.8	375.0	375.0	375.0	375.0	375.0	375.4
120°	411.4	411.7	412.1	412.4	412.8	413.0	413.2	413.4	413.6	413.7	414.6
122.5°	448.5	449.0	449.5	450.0	450.6	451.1	451.6	452.2	452.7	453.2	453.6
125°	485.6	486.3	487.0	487.7	488.4	489.1	489.8	490.5	491.2	491.9	492.2
127.5°	522.7	523.4	524.1	524.8	525.5	526.4	527.4	528.5	529.5	530.6	530.9
130°	559.0	560.2	561.5	562.7	563.9	564.9	565.6	566.3	567.0	567.7	568.2
132.5°	596.9	597.8	598.7	599.5	600.4	601.3	602.2	603.0	603.9	604.8	605.2
135°	636.4	636.7	637.1	637.4	637.8	638.3	639.0	639.7	640.4	641.1	641.3
137.5°	671.1	671.6	672.2	672.7	673.2	673.9	674.8	675.7	676.6	677.4	676.9
140°	705.1	706.3	707.5	708.8	710.0	710.7	710.9	711.0	711.2	711.4	711.2
142.5°	739.8	740.7	741.6	742.4	743.3	743.8	744.0	744.2	744.4	744.6	744.2
145°	773.0	773.7	774.4	775.1	775.8	776.2	776.4	776.6	776.7	776.9	776.4
147.5°	803.0	804.0	805.1	806.1	807.2	807.7	807.7	807.7	807.7	807.7	807.2
150°	831.4	832.5	833.5	834.6	835.6	836.1	836.1	836.1	836.1	836.1	835.8
152.5°	859.0	859.9	860.8	861.7	862.5	862.8	862.5	862.1	861.8	861.4	861.2
155°	883.5	884.7	886.0	887.2	888.4	888.7	888.0	887.3	886.6	885.9	885.7
157.5°	906.4	907.5	908.5	909.6	910.6	910.8	910.1	909.4	908.7	908.0	907.8
160°	928.5	929.2	929.9	930.6	931.3	931.2	930.4	929.5	928.6	927.7	927.7
162.5°	945.1	946.3	947.6	948.8	950.0	950.2	949.3	948.4	947.6	946.7	946.5
165°	960.9	962.1	963.3	964.6	965.8	965.9	964.8	963.8	962.7	961.7	961.7
167.5°	975.1	976.2	977.2	978.3	979.3	979.3	978.3	977.2	976.2	975.1	974.9
170°	985.4	986.6	987.8	989.1	990.3	990.3	989.1	987.8	986.6	985.4	985.4
172.5°	993.3	994.5	995.7	996.9	998.2	998.3	997.2	996.2	995.1	994.1	994.1
175°	998.8	1000.0	1001.2	1002.5	1003.7	1003.8	1002.7	1001.7	1000.6	999.6	999.6
177.5°	1001.9	1003.2	1004.4	1005.6	1006.9	1006.9	1005.9	1004.8	1003.8	1002.7	1002.7
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1

TEST NUMBER: P832015

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8
2.5°	4018.3	4014.4	3977.2	3939.9	3903.5	3867.0	3839.8	3812.7	3766.9	3721.1	3692.4
5°	4267.4	4237.9	4178.9	4119.9	4031.5	3943.0	3868.5	3794.1	3699.4	3604.7	3525.6
7.5°	4406.2	4382.2	4310.8	4239.4	4122.3	4005.1	3888.7	3772.3	3632.7	3493.0	3373.5
10°	4410.1	4430.3	4371.3	4312.4	4180.5	4048.6	3890.3	3732.0	3544.2	3356.5	3202.1
12.5°	4272.0	4358.9	4346.5	4334.1	4199.8	4065.6	3873.2	3680.8	3450.3	3219.9	3026.7
15°	4013.6	4182.0	4231.7	4281.3	4170.4	4059.4	3840.6	3621.8	3351.0	3080.3	2858.3
17.5°	3680.8	3916.7	4047.8	4178.9	4098.2	4017.5	3777.8	3538.0	3233.1	2928.2	2686.9
20°	3286.6	3595.4	3801.0	4006.7	3977.2	3947.7	3700.2	3452.7	3123.7	2794.7	2533.3
22.5°	2897.1	3223.0	3507.0	3791.0	3821.2	3851.5	3601.6	3351.8	2991.8	2631.8	2365.7
25°	2561.2	2892.5	3230.8	3569.1	3637.3	3705.6	3468.2	3230.8	2857.6	2484.4	2219.8
27.5°	2240.7	2555.8	2928.2	3300.6	3424.7	3548.9	3331.6	3114.4	2725.7	2337.0	2073.2
30°	1979.3	2260.9	2641.1	3021.3	3194.3	3367.3	3167.9	2968.5	2582.9	2197.3	1938.9
32.5°	1735.6	1987.8	2369.5	2751.3	2952.2	3153.2	2980.9	2808.7	2437.8	2066.9	1811.7
35°	1543.2	1769.0	2125.1	2481.3	2706.3	2931.3	2790.1	2648.9	2286.5	1924.2	1682.9
37.5°	1378.0	1567.3	1901.7	2236.1	2475.1	2714.0	2596.1	2478.2	2137.6	1796.9	1568.8
40°	1241.4	1393.5	1704.6	2015.7	2250.1	2484.4	2383.5	2282.6	1977.7	1672.8	1459.4
42.5°	1124.3	1255.4	1534.7	1814.0	2028.9	2243.9	2177.1	2110.4	1834.2	1558.0	1360.1
45°	1021.1	1131.2	1377.2	1623.1	1821.0	2018.8	1966.1	1913.3	1675.1	1436.9	1255.4
47.5°	929.5	1024.2	1243.7	1463.3	1641.0	1818.7	1769.8	1720.9	1523.8	1326.8	1161.5
50°	845.7	926.4	1109.5	1292.6	1452.5	1612.3	1571.9	1531.6	1368.7	1205.7	1063.0
52.5°	766.6	833.3	997.8	1162.3	1291.1	1419.9	1388.8	1357.8	1232.1	1106.4	976.8
55°	691.3	752.6	891.5	1030.4	1140.5	1250.7	1219.7	1188.7	1090.9	993.1	879.1
57.5°	623.0	676.6	789.1	901.6	989.2	1076.9	1062.2	1047.4	966.0	884.5	790.6
60°	550.9	599.0	696.0	793.0	863.6	934.2	917.1	900.0	841.8	783.6	702.9
62.5°	486.5	529.2	606.7	684.3	741.7	799.2	786.7	774.3	730.1	685.9	619.2
65°	419.0	460.9	523.7	586.6	631.6	676.6	665.7	654.8	621.5	588.1	534.6
67.5°	357.7	392.6	446.9	501.2	531.5	561.7	555.5	549.3	523.7	498.1	456.2
70°	295.6	325.9	370.9	415.9	436.8	457.8	460.1	462.4	439.1	415.9	384.8
72.5°	233.5	257.6	299.5	341.4	357.7	374.0	373.2	372.4	358.5	344.5	316.6
75°	179.2	197.1	229.7	262.2	276.2	290.2	293.3	296.4	283.2	270.0	254.5
77.5°	128.8	141.2	166.0	190.9	206.4	221.9	223.5	225.0	218.8	212.6	197.8
80°	90.8	94.7	110.2	125.7	142.0	158.3	160.6	162.9	156.7	150.5	141.2
82.5°	62.8	65.2	70.6	76.0	89.2	102.4	105.5	108.6	105.5	102.4	92.3
85°	38.0	38.8	41.1	43.4	49.7	55.9	59.0	62.1	60.5	59.0	53.5
87.5°	17.1	17.1	17.8	18.6	20.2	21.7	25.6	29.5	27.2	24.8	22.5
90°	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	31.1	30.0	29.0	27.9	26.8	25.8	24.7	23.7	24.7	25.8	26.8
95°	55.6	54.2	52.8	51.5	50.3	49.0	47.8	46.6	47.8	49.0	50.3
97.5°	83.2	82.1	81.1	80.1	79.2	78.3	77.5	76.6	77.5	78.3	79.2
100°	114.3	113.4	112.6	111.6	110.5	109.5	108.4	107.4	108.4	109.5	110.5
102.5°	148.3	147.1	145.9	145.0	144.5	144.0	143.4	142.9	143.4	144.0	144.5
105°	183.2	181.6	180.0	179.1	178.7	178.4	178.0	177.7	178.0	178.4	178.7
107.5°	221.3	220.5	219.8	219.4	219.2	219.1	218.9	218.7	218.9	219.1	219.2
110°	259.1	258.7	258.4	258.0	257.7	257.3	257.0	256.6	257.0	257.3	257.7



TEST NUMBER: P832015

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	296.9	296.9	296.9	296.8	296.6	296.4	296.3	296.1	296.3	296.4	296.6
115°	337.1	337.4	337.8	337.7	337.1	336.6	336.1	335.6	336.1	336.6	337.1
117.5°	375.7	376.1	376.4	376.5	376.4	376.2	376.0	375.8	376.0	376.2	376.4
120°	415.5	416.4	417.2	417.1	416.1	415.0	414.0	412.9	414.0	415.0	416.1
122.5°	453.9	454.3	454.6	454.4	453.7	453.0	452.3	451.6	452.3	453.0	453.7
125°	492.6	492.9	493.3	493.2	492.7	492.2	491.6	491.1	491.6	492.2	492.7
127.5°	531.3	531.6	532.0	531.6	530.6	529.5	528.5	527.4	528.5	529.5	530.6
130°	568.7	569.3	569.8	569.4	568.0	566.6	565.1	563.7	565.1	566.6	568.0
132.5°	605.5	605.9	606.2	605.7	604.3	602.9	601.5	600.1	601.5	602.9	604.3
135°	641.5	641.6	641.8	641.4	640.3	639.3	638.2	637.2	638.2	639.3	640.3
137.5°	676.4	675.9	675.3	674.6	673.8	672.9	672.0	671.1	672.0	672.9	673.8
140°	711.0	710.9	710.7	710.2	709.3	708.4	707.5	706.7	707.5	708.4	709.3
142.5°	743.8	743.5	743.1	742.5	741.7	740.8	739.9	739.0	739.9	740.8	741.7
145°	775.9	775.3	774.8	774.4	774.0	773.7	773.3	773.0	773.3	773.7	774.0
147.5°	806.7	806.1	805.6	805.0	804.3	803.6	802.9	802.2	802.9	803.6	804.3
150°	835.4	835.1	834.7	834.4	834.0	833.7	833.3	833.0	833.3	833.7	834.0
152.5°	861.1	860.9	860.7	860.4	859.8	859.3	858.8	858.2	858.8	859.3	859.8
155°	885.5	885.4	885.2	885.1	885.1	885.1	885.1	885.1	885.1	885.1	885.1
157.5°	907.6	907.5	907.3	907.3	907.5	907.6	907.8	908.0	907.8	907.6	907.5
160°	927.7	927.7	927.7	927.9	928.3	928.6	929.0	929.3	929.0	928.6	928.3
162.5°	946.3	946.2	946.0	946.2	946.7	947.2	947.7	948.3	947.7	947.2	946.7
165°	961.7	961.7	961.7	961.9	962.5	963.0	963.5	964.0	963.5	963.0	962.5
167.5°	974.8	974.6	974.4	974.7	975.4	976.1	976.8	977.5	976.8	976.1	975.4
170°	985.4	985.4	985.4	985.7	986.4	987.1	987.8	988.5	987.8	987.1	986.4
172.5°	994.1	994.1	994.1	994.4	995.1	995.8	996.5	997.2	996.5	995.8	995.1
175°	999.6	999.6	999.6	999.9	1000.6	1001.3	1002.0	1002.7	1002.0	1001.3	1000.6
177.5°	1002.7	1002.7	1002.7	1003.1	1003.8	1004.5	1005.2	1005.9	1005.2	1004.5	1003.8
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P832015

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8
2.5°	3663.7	3619.5	3575.3	3543.5	3511.6	3472.1	3432.5	3431.0	3429.4	3399.9	3370.4
5°	3446.5	3369.7	3292.8	3217.6	3142.3	3067.1	2991.8	2974.7	2957.7	2932.1	2906.5
7.5°	3254.0	3131.5	3008.9	2912.7	2816.5	2741.2	2665.9	2614.7	2563.5	2523.9	2484.4
10°	3047.7	2895.6	2743.5	2627.1	2510.8	2429.3	2347.8	2288.9	2229.9	2202.0	2174.0
12.5°	2833.5	2668.3	2503.0	2388.9	2274.9	2177.1	2079.4	2025.8	1972.3	1933.5	1894.7
15°	2636.4	2458.8	2281.1	2160.1	2039.0	1947.5	1855.9	1802.4	1748.8	1710.0	1671.2
17.5°	2445.6	2266.4	2087.1	1964.5	1841.9	1758.9	1675.9	1623.9	1571.9	1547.9	1523.8
20°	2271.8	2091.0	1910.2	1794.6	1679.0	1597.5	1516.1	1488.1	1460.2	1437.7	1415.2
22.5°	2099.5	1925.7	1751.9	1641.0	1530.0	1471.1	1412.1	1389.6	1367.1	1350.0	1333.0
25°	1955.2	1782.2	1609.2	1512.2	1415.2	1369.4	1323.7	1308.9	1294.2	1277.1	1260.0
27.5°	1809.4	1644.9	1480.4	1402.8	1325.2	1288.0	1250.7	1232.1	1213.5	1199.5	1185.5
30°	1680.6	1528.5	1376.4	1312.0	1247.6	1215.0	1182.4	1162.3	1142.1	1128.9	1115.7
32.5°	1556.4	1421.4	1286.4	1231.3	1176.2	1144.4	1112.6	1093.2	1073.8	1058.3	1042.8
35°	1441.6	1324.4	1207.3	1156.8	1106.4	1074.6	1042.8	1023.4	1004.0	988.5	973.0
37.5°	1340.7	1234.4	1128.1	1080.8	1033.5	1005.5	977.6	957.4	937.3	921.0	904.7
40°	1246.1	1152.2	1058.3	1012.5	966.7	936.5	906.2	888.4	870.5	855.8	841.1
42.5°	1162.3	1076.1	990.0	945.0	900.0	871.3	842.6	821.7	800.7	792.2	783.6
45°	1073.8	997.8	921.7	878.3	834.8	804.6	774.3	756.5	738.6	730.9	723.1
47.5°	996.2	925.6	855.0	812.3	769.7	742.5	715.4	701.4	687.4	676.6	665.7
50°	920.2	851.9	783.6	742.5	701.4	678.1	654.8	637.8	620.7	612.9	605.2
52.5°	847.3	785.2	723.1	681.2	639.3	616.8	594.3	579.6	564.8	548.5	532.3
55°	765.0	710.7	656.4	619.2	581.9	558.6	535.4	518.3	501.2	484.2	467.1
57.5°	696.7	643.2	589.7	556.3	522.9	500.4	477.9	459.3	440.7	426.7	412.8
60°	622.3	575.7	529.2	496.6	464.0	442.3	420.5	402.7	384.8	377.9	370.9
62.5°	552.4	509.0	465.5	436.8	408.1	387.2	366.2	354.6	342.9	338.3	333.6
65°	481.0	443.8	406.6	380.2	353.8	336.0	318.1	312.7	307.2	303.4	299.5
67.5°	414.3	382.5	350.7	327.4	304.1	291.7	279.3	273.1	266.9	262.2	257.6
70°	353.8	325.9	297.9	277.8	257.6	246.0	234.3	228.9	223.5	214.9	206.4
72.5°	288.6	266.9	245.2	229.7	214.1	204.1	194.0	183.1	172.2	164.5	156.7
75°	239.0	217.2	195.5	180.8	166.0	154.4	142.8	138.9	135.0	132.7	130.3
77.5°	183.1	164.5	145.9	134.2	122.6	117.2	111.7	109.4	107.1	106.3	105.5
80°	131.9	116.4	100.9	94.7	88.5	86.9	85.3	83.8	82.2	81.5	80.7
82.5°	82.2	74.5	66.7	65.2	63.6	62.8	62.1	61.3	60.5	59.7	59.0
85°	48.1	45.0	41.9	41.1	40.3	39.6	38.8	38.8	38.8	38.8	38.8
87.5°	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2	19.4	18.6
90°	7.8	9.8	12.1	14.4	16.7	18.9	19.7	20.4	21.1	21.8	22.3
92.5°	27.9	29.0	30.0	31.1	32.1	33.2	33.7	34.2	34.7	35.3	35.4
95°	51.5	52.8	54.2	55.6	57.0	58.4	59.1	59.8	60.5	61.2	61.6
97.5°	80.1	81.1	82.1	83.2	84.2	85.3	86.1	87.0	87.9	88.8	89.1
100°	111.6	112.6	113.4	114.3	115.2	116.1	116.6	117.1	117.6	118.2	118.6
102.5°	145.0	145.9	147.1	148.3	149.6	150.8	151.3	151.9	152.4	152.9	153.1
105°	179.1	180.0	181.6	183.2	184.8	186.3	186.3	186.3	186.3	186.3	186.5
107.5°	219.4	219.8	220.5	221.3	222.0	222.7	223.2	223.7	224.2	224.8	224.9
110°	258.0	258.4	258.7	259.1	259.4	259.8	260.5	261.2	261.9	262.6	262.7



TEST NUMBER: P832015

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	296.8	296.9	296.9	296.9	296.9	296.9	297.8	298.6	299.5	300.4	300.8
115°	337.7	337.8	337.4	337.1	336.7	336.4	336.5	336.7	336.9	337.1	337.1
117.5°	376.5	376.4	376.1	375.7	375.4	375.0	375.0	375.0	375.0	375.0	374.8
120°	417.1	417.2	416.4	415.5	414.6	413.7	413.6	413.4	413.2	413.0	412.8
122.5°	454.4	454.6	454.3	453.9	453.6	453.2	452.7	452.2	451.6	451.1	450.6
125°	493.2	493.3	492.9	492.6	492.2	491.9	491.2	490.5	489.8	489.1	488.4
127.5°	531.6	532.0	531.6	531.3	530.9	530.6	529.5	528.5	527.4	526.4	525.5
130°	569.4	569.8	569.3	568.7	568.2	567.7	567.0	566.3	565.6	564.9	563.9
132.5°	605.7	606.2	605.9	605.5	605.2	604.8	603.9	603.0	602.2	601.3	600.4
135°	641.4	641.8	641.6	641.5	641.3	641.1	640.4	639.7	639.0	638.3	637.8
137.5°	674.6	675.3	675.9	676.4	676.9	677.4	676.6	675.7	674.8	673.9	673.2
140°	710.2	710.7	710.9	711.0	711.2	711.4	711.2	711.0	710.9	710.7	710.0
142.5°	742.5	743.1	743.5	743.8	744.2	744.6	744.4	744.2	744.0	743.8	743.3
145°	774.4	774.8	775.3	775.9	776.4	776.9	776.7	776.6	776.4	776.2	775.8
147.5°	805.0	805.6	806.1	806.7	807.2	807.7	807.7	807.7	807.7	807.7	807.2
150°	834.4	834.7	835.1	835.4	835.8	836.1	836.1	836.1	836.1	836.1	835.6
152.5°	860.4	860.7	860.9	861.1	861.2	861.4	861.8	862.1	862.5	862.8	862.5
155°	885.1	885.2	885.4	885.5	885.7	885.9	886.6	887.3	888.0	888.7	888.4
157.5°	907.3	907.3	907.5	907.6	907.8	908.0	908.7	909.4	910.1	910.8	910.6
160°	927.9	927.7	927.7	927.7	927.7	927.7	928.6	929.5	930.4	931.2	931.3
162.5°	946.2	946.0	946.2	946.3	946.5	946.7	947.6	948.4	949.3	950.2	950.0
165°	961.9	961.7	961.7	961.7	961.7	961.7	962.7	963.8	964.8	965.9	965.8
167.5°	974.7	974.4	974.6	974.8	974.9	975.1	976.2	977.2	978.3	979.3	979.3
170°	985.7	985.4	985.4	985.4	985.4	985.4	986.6	987.8	989.1	990.3	990.3
172.5°	994.4	994.1	994.1	994.1	994.1	994.1	995.1	996.2	997.2	998.3	998.2
175°	999.9	999.6	999.6	999.6	999.6	999.6	1000.6	1001.7	1002.7	1003.8	1003.7
177.5°	1003.1	1002.7	1002.7	1002.7	1002.7	1002.7	1003.8	1004.8	1005.9	1006.9	1006.9
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P832015

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3784.8	3784.8	3784.8	3784.8
2.5°	3362.7	3354.9	3351.8	3348.7
5°	2882.4	2858.3	2852.9	2847.5
7.5°	2474.3	2464.2	2430.8	2397.5
10°	2143.0	2112.0	2098.0	2084.0
12.5°	1866.0	1837.3	1832.6	1828.0
15°	1651.1	1630.9	1623.9	1616.9
17.5°	1509.9	1495.9	1487.4	1478.8
20°	1405.1	1395.0	1388.8	1382.6
22.5°	1325.2	1317.4	1312.8	1308.1
25°	1248.4	1236.8	1232.9	1229.0
27.5°	1175.5	1165.4	1161.5	1157.6
30°	1107.2	1098.6	1093.2	1087.8
32.5°	1032.7	1022.6	1019.5	1016.4
35°	966.7	960.5	957.4	954.3
37.5°	896.9	889.2	884.5	879.9
40°	837.2	833.3	831.0	828.6
42.5°	776.7	769.7	768.9	768.1
45°	716.1	709.2	707.6	706.1
47.5°	659.5	653.3	652.5	651.7
50°	596.7	588.1	581.9	575.7
52.5°	524.5	516.7	511.3	505.9
55°	458.5	450.0	445.4	440.7
57.5°	408.9	405.0	402.7	400.4
60°	368.5	366.2	364.7	363.1
62.5°	331.3	329.0	329.0	329.0
65°	297.2	294.8	292.5	290.2
67.5°	252.9	248.3	247.5	246.7
70°	199.4	192.4	191.6	190.9
72.5°	156.0	155.2	153.6	152.1
75°	128.8	127.2	127.2	127.2
77.5°	104.0	102.4	102.4	102.4
80°	79.9	79.1	79.9	80.7
82.5°	59.0	59.0	58.2	57.4
85°	38.0	37.2	37.2	37.2
87.5°	18.6	18.6	18.6	18.6
90°	22.6	23.0	23.3	23.7
92.5°	35.0	34.7	34.3	34.0
95°	61.6	61.6	61.6	61.6
97.5°	89.0	88.8	88.6	88.4
100°	119.0	119.3	119.7	120.0
102.5°	152.9	152.7	152.6	152.4
105°	186.9	187.2	187.6	187.9
107.5°	224.8	224.6	224.4	224.2
110°	262.4	262.0	261.7	261.3



TEST NUMBER: P832015

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	300.8	300.8	300.8	300.8
115°	336.9	336.7	336.5	336.4
117.5°	374.2	373.7	373.2	372.7
120°	412.4	412.1	411.7	411.4
122.5°	450.0	449.5	449.0	448.5
125°	487.7	487.0	486.3	485.6
127.5°	524.8	524.1	523.4	522.7
130°	562.7	561.5	560.2	559.0
132.5°	599.5	598.7	597.8	596.9
135°	637.4	637.1	636.7	636.4
137.5°	672.7	672.2	671.6	671.1
140°	708.8	707.5	706.3	705.1
142.5°	742.4	741.6	740.7	739.8
145°	775.1	774.4	773.7	773.0
147.5°	806.1	805.1	804.0	803.0
150°	834.6	833.5	832.5	831.4
152.5°	861.7	860.8	859.9	859.0
155°	887.2	886.0	884.7	883.5
157.5°	909.6	908.5	907.5	906.4
160°	930.6	929.9	929.2	928.5
162.5°	948.8	947.6	946.3	945.1
165°	964.6	963.3	962.1	960.9
167.5°	978.3	977.2	976.2	975.1
170°	989.1	987.8	986.6	985.4
172.5°	996.9	995.7	994.5	993.3
175°	1002.5	1001.2	1000.0	998.8
177.5°	1005.6	1004.4	1003.2	1001.9
180°	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P832015

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.88	15.81	15.72	16.66	17.71	19.54	20.47	20.38	21.32	22.38
	3H	16.11	16.94	16.96	17.80	18.88	21.05	21.88	21.90	22.74	23.82
	4H	16.49	17.28	17.36	18.14	19.24	21.54	22.33	22.41	23.19	24.29
	6H	16.78	17.50	17.66	18.38	19.48	21.86	22.58	22.74	23.46	24.56
	8H	16.87	17.56	17.76	18.45	19.55	21.94	22.63	22.83	23.52	24.63
	12H	16.93	17.58	17.82	18.46	19.59	21.98	22.63	22.87	23.51	24.65
4H	2H	15.61	16.40	16.48	17.26	18.36	19.55	20.33	20.42	21.20	22.29
	3H	16.99	17.64	17.87	18.54	19.65	21.22	21.87	22.10	22.77	23.87
	4H	17.45	18.04	18.34	18.94	20.07	21.83	22.42	22.72	23.31	24.45
	6H	17.82	18.33	18.73	19.25	20.39	22.27	22.78	23.18	23.70	24.84
	8H	17.95	18.43	18.86	19.34	20.49	22.40	22.88	23.31	23.79	24.94
	12H	18.03	18.46	18.96	19.39	20.55	22.47	22.90	23.40	23.83	24.98
8H	4H	17.77	18.25	18.68	19.16	20.31	21.80	22.28	22.71	23.19	24.34
	6H	18.24	18.63	19.17	19.59	20.74	22.30	22.69	23.24	23.65	24.80
	8H	18.43	18.78	19.38	19.73	20.89	22.49	22.83	23.43	23.78	24.95
	12H	18.58	18.88	19.52	19.82	21.04	22.61	22.91	23.55	23.85	25.07
12H	4H	17.79	18.21	18.72	19.15	20.30	21.76	22.18	22.68	23.11	24.27
	6H	18.30	18.64	19.24	19.59	20.76	22.28	22.62	23.22	23.57	24.74
	8H	18.52	18.82	19.47	19.76	20.98	22.47	22.78	23.42	23.72	24.93