

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332268-840

Luminaire Tested: **S123RDIP-S340D1195U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332268-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1195U840-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5453.5 lumens  
Efficiency: N/A  
Efficacy: 129.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332268-840

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332268-840

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	55	43	35	30	48	39	32	27	30	26	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	20	21	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6245	6245	6245
5°	6269	6183	6218
10°	6233	6105	6084
15°	6167	5962	5899
20°	6074	5783	5648
25°	5980	5583	5404
30°	5854	5351	5059
35°	5727	5119	4742
40°	5606	4846	4350
45°	5451	4576	3997
50°	5280	4270	3600
55°	5104	3920	3232
60°	4943	3546	2827
65°	4735	3140	2420
70°	4472	2634	1954
75°	4092	2075	1838
80°	3645	1841	1692
85°	3075	1618	1507



TEST NUMBER: P332268-840

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.5	1.0
10°-20°	151.6	2.8
20°-30°	218.3	4.0
30°-40°	245.9	4.5
40°-50°	235.2	4.3
50°-60°	192.6	3.5
60°-70°	130.0	2.4
70°-80°	65.4	1.2
80°-90°	21.7	0.4
90°-100°	97.3	1.8
100°-110°	291.2	5.3
110°-120°	495.4	9.1
120°-130°	651.6	11.9
130°-140°	732.3	13.4
140°-150°	719.9	13.2
150°-160°	606.0	11.1
160°-170°	403.4	7.4
170°-180°	141.3	2.6
0°-30°	424.3	7.8
0°-40°	670.2	12.3
0°-60°	1098.1	20.1
0°-90°	1315.1	24.1
90°-120°	883.9	16.2
90°-150°	2987.7	54.8
90°-180°	4138.0	75.9
0°-180°	5453.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	580	580	580	580	580	
5°	580	578	572	576	576	55
15°	553	548	535	533	529	156
25°	504	491	470	460	455	231
35°	436	418	390	370	361	273
45°	358	336	301	275	263	276
55°	272	248	209	183	172	244
65°	186	159	123	101	95	184
75°	98	76	50	45	44	105
85°	25	15	13	12	12	28
90°	1	13	28	33	35	5
95°	69	78	87	91	92	78
105°	264	267	277	277	279	283
115°	499	502	500	501	500	493
125°	730	733	731	726	722	651
135°	947	953	953	948	946	729
145°	1149	1151	1155	1153	1149	717
155°	1315	1315	1316	1320	1313	605
165°	1433	1429	1429	1435	1428	404
175°	1490	1486	1485	1492	1484	141
180°	1494	1494	1494	1494	1494	



TEST NUMBER: P332268-840

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	582.1	581.7	581.4	581.1	580.8	580.1	579.1	578.0	577.0	576.0	576.9
5°	580.2	579.7	579.2	578.7	578.0	577.2	575.9	574.7	573.4	572.2	573.1
7.5°	574.8	574.2	573.7	573.1	572.6	571.5	569.9	568.3	566.5	564.9	565.4
10°	570.3	569.6	568.9	568.2	567.3	566.0	564.2	562.3	560.4	558.6	558.7
12.5°	563.9	563.1	562.3	561.5	560.7	559.1	556.7	554.5	552.2	549.9	549.8
15°	553.4	552.2	551.1	549.9	548.8	546.7	543.8	540.9	538.0	535.0	534.5
17.5°	540.1	538.8	537.5	536.0	534.7	532.2	528.5	524.7	521.1	517.4	516.2
20°	530.3	528.7	526.9	525.3	523.6	520.8	516.8	512.8	508.9	504.9	503.5
22.5°	519.4	517.5	515.5	513.6	511.7	508.7	504.4	500.2	495.9	491.7	490.0
25°	503.5	500.9	498.3	495.6	493.0	489.3	484.5	479.7	474.8	470.1	467.9
27.5°	484.2	481.3	478.4	475.5	472.6	468.6	463.2	457.8	452.4	447.1	444.0
30°	471.0	467.9	464.7	461.6	458.5	453.9	448.1	442.2	436.4	430.5	427.0
32.5°	457.9	454.2	450.7	447.2	443.6	438.8	432.5	426.4	420.2	413.9	410.1
35°	435.8	431.9	428.2	424.4	420.7	415.6	409.1	402.5	396.1	389.6	385.2
37.5°	413.3	409.1	405.0	400.8	396.6	391.0	384.2	377.2	370.3	363.3	358.3
40°	399.0	394.5	389.8	385.3	380.6	374.6	367.2	359.7	352.3	344.9	339.5
42.5°	382.8	378.2	373.7	369.0	364.5	358.3	350.6	343.0	335.3	327.6	321.6
45°	358.1	353.4	348.7	344.0	339.2	332.9	324.9	316.8	308.7	300.6	294.7
47.5°	333.4	328.2	323.0	317.8	312.7	306.1	298.0	289.9	282.0	273.9	267.4
50°	315.3	310.3	305.5	300.5	295.6	288.9	280.4	272.0	263.5	255.0	248.5
52.5°	299.1	293.8	288.4	283.1	277.7	270.8	262.5	254.1	245.7	237.3	230.7
55°	272.0	266.8	261.8	256.6	251.5	244.5	235.6	226.7	217.8	208.9	202.9
57.5°	246.9	241.4	235.8	230.1	224.6	217.3	208.4	199.4	190.6	181.7	175.9
60°	229.6	223.9	218.1	212.4	206.6	199.4	190.8	182.1	173.4	164.7	159.1
62.5°	212.3	206.5	200.8	195.1	189.3	182.1	173.4	164.7	156.0	147.3	142.1
65°	185.9	180.2	174.4	168.6	162.9	155.9	147.7	139.6	131.5	123.3	118.2
67.5°	159.5	153.6	147.7	142.0	136.1	129.4	121.5	113.7	105.8	98.1	94.2
70°	142.1	136.4	130.8	125.1	119.6	113.0	105.7	98.4	91.1	83.7	80.1
72.5°	124.8	119.3	113.7	108.1	102.5	96.4	89.8	83.1	76.4	69.8	66.9
75°	98.4	93.3	88.3	83.3	78.3	72.9	67.2	61.4	55.6	49.9	48.9
77.5°	74.2	69.7	65.1	60.6	56.1	52.0	48.3	44.5	40.9	37.2	36.7
80°	58.8	54.5	50.3	45.9	41.7	38.5	36.3	34.0	31.8	29.7	29.3
82.5°	44.1	40.4	36.8	33.0	29.3	27.0	26.0	24.9	23.9	22.8	22.5
85°	24.9	22.6	20.3	18.1	15.8	14.4	14.1	13.8	13.5	13.1	12.9
87.5°	9.3	8.9	8.5	8.1	7.7	7.8	8.5	9.2	9.9	10.5	10.6
90°	1.2	3.7	6.4	9.0	11.6	14.6	18.0	21.4	24.7	28.2	29.2
92.5°	28.4	30.2	31.9	33.7	35.4	37.4	39.3	41.2	43.1	45.0	45.8
95°	69.3	71.1	72.9	74.7	76.5	78.5	80.6	82.6	84.7	86.8	87.9
97.5°	123.0	124.3	125.7	127.0	128.4	129.9	131.4	132.9	134.3	135.8	137.0
100°	159.6	161.2	162.7	164.3	165.8	167.2	168.5	169.9	171.2	172.5	173.3
102.5°	201.8	202.8	203.7	204.6	205.6	206.9	208.6	210.4	212.1	213.8	214.6
105°	264.0	264.5	265.1	265.6	266.1	267.5	269.8	272.3	274.6	276.9	276.9
107.5°	336.3	336.6	336.9	337.2	337.5	338.2	339.1	340.0	340.9	341.9	342.7
110°	381.3	381.8	382.3	382.9	383.4	384.0	384.5	385.0	385.5	386.1	387.1



TEST NUMBER: P332268-840

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	428.3	428.6	428.9	429.2	429.5	429.7	429.8	429.9	430.0	430.1	431.4
115°	498.7	499.5	500.2	501.0	501.8	501.9	501.4	500.9	500.4	499.9	500.1
117.5°	569.6	570.1	570.6	571.1	571.6	571.6	570.9	570.2	569.6	568.9	568.8
120°	613.7	615.2	616.8	618.3	620.0	620.1	618.7	617.4	616.1	614.8	614.6
122.5°	659.6	660.8	662.0	663.1	664.3	664.5	663.8	663.1	662.5	661.8	661.1
125°	729.8	730.6	731.3	732.2	733.0	733.1	732.6	732.1	731.5	731.0	729.9
127.5°	794.6	796.3	797.9	799.6	801.2	801.8	801.2	800.6	800.1	799.5	798.1
130°	837.8	839.8	841.9	844.0	846.1	846.8	846.0	845.2	844.4	843.6	842.6
132.5°	880.9	883.0	885.1	887.2	889.3	890.1	889.5	888.9	888.3	887.8	886.5
135°	946.8	948.5	950.0	951.6	953.1	953.8	953.5	953.3	953.0	952.7	951.7
137.5°	1007.9	1009.2	1010.5	1011.8	1013.1	1014.1	1014.8	1015.4	1016.1	1016.8	1015.7
140°	1050.2	1051.5	1052.8	1054.1	1055.3	1056.1	1056.4	1056.6	1056.9	1057.2	1056.9
142.5°	1088.6	1089.9	1091.3	1092.6	1093.9	1094.7	1095.2	1095.7	1096.1	1096.6	1096.3
145°	1148.7	1149.2	1149.7	1150.2	1150.7	1151.4	1152.3	1153.0	1153.8	1154.6	1154.3
147.5°	1201.2	1202.2	1203.2	1204.1	1205.1	1205.9	1206.6	1207.3	1208.0	1208.8	1208.8
150°	1237.9	1238.4	1238.9	1239.4	1240.0	1240.5	1241.0	1241.5	1242.0	1242.5	1242.5
152.5°	1267.9	1268.7	1269.4	1270.1	1270.8	1271.3	1271.6	1272.0	1272.3	1272.6	1273.0
155°	1315.3	1315.3	1315.3	1315.3	1315.3	1315.5	1315.8	1316.0	1316.3	1316.5	1317.6
157.5°	1355.6	1355.3	1355.0	1354.7	1354.4	1354.3	1354.6	1354.8	1355.0	1355.2	1356.3
160°	1381.0	1380.5	1380.0	1379.5	1379.0	1378.7	1378.7	1378.7	1378.7	1378.7	1380.0
162.5°	1403.5	1402.8	1402.1	1401.4	1400.7	1400.4	1400.6	1400.8	1401.0	1401.2	1402.5
165°	1432.7	1431.9	1431.1	1430.3	1429.6	1429.2	1429.2	1429.2	1429.2	1429.2	1430.7
167.5°	1455.9	1454.8	1453.8	1452.8	1451.7	1451.3	1451.5	1451.7	1451.9	1452.1	1453.7
170°	1469.1	1467.9	1466.9	1465.9	1464.8	1464.3	1464.3	1464.3	1464.3	1464.3	1466.1
172.5°	1479.4	1478.3	1477.2	1476.2	1475.2	1474.7	1474.7	1474.7	1474.7	1474.7	1476.3
175°	1490.2	1489.1	1488.0	1487.0	1486.0	1485.4	1485.4	1485.4	1485.4	1485.4	1487.0
177.5°	1494.6	1493.8	1493.0	1492.1	1491.3	1490.9	1490.9	1490.9	1490.9	1490.9	1492.1
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7



TEST NUMBER: P332268-840

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	577.8	578.8	579.8	580.1	580.0	579.8	579.6	579.5
5°	574.1	575.0	575.9	576.3	576.1	575.9	575.7	575.5
7.5°	566.0	566.5	567.0	567.1	566.7	566.4	566.0	565.7
10°	558.8	558.9	559.0	558.8	558.3	557.7	557.1	556.6
12.5°	549.8	549.7	549.7	549.3	548.7	548.1	547.4	546.8
15°	533.9	533.4	532.9	532.3	531.6	530.8	530.1	529.4
17.5°	515.1	514.0	512.9	511.8	510.7	509.6	508.6	507.5
20°	502.2	500.8	499.5	498.2	496.9	495.6	494.4	493.1
22.5°	488.4	486.7	484.9	483.5	482.3	481.2	480.0	478.9
25°	465.6	463.5	461.3	459.6	458.5	457.4	456.2	455.0
27.5°	441.0	438.0	434.9	432.5	430.7	429.0	427.3	425.5
30°	423.4	419.9	416.4	413.7	412.0	410.4	408.7	407.0
32.5°	406.2	402.3	398.4	395.6	393.8	392.1	390.3	388.6
35°	380.6	376.1	371.6	368.4	366.6	364.7	362.7	360.9
37.5°	353.1	348.0	343.0	339.2	336.9	334.6	332.2	329.9
40°	334.1	328.6	323.2	319.2	316.8	314.5	312.0	309.6
42.5°	315.7	309.8	303.9	299.8	297.6	295.5	293.4	291.1
45°	288.7	282.8	276.8	272.6	270.1	267.6	265.1	262.6
47.5°	260.8	254.4	247.9	243.6	241.4	239.1	236.8	234.6
50°	242.1	235.6	229.1	224.7	222.3	219.8	217.4	215.0
52.5°	223.9	217.1	210.5	206.0	203.8	201.7	199.5	197.3
55°	196.8	190.8	184.7	180.6	178.5	176.4	174.3	172.2
57.5°	170.2	164.4	158.8	154.9	153.2	151.4	149.7	147.8
60°	153.4	147.7	142.1	138.4	136.6	134.8	133.1	131.3
62.5°	136.7	131.5	126.1	122.5	120.7	118.9	116.9	115.1
65°	113.0	108.0	102.8	99.7	98.5	97.4	96.2	95.0
67.5°	90.4	86.5	82.7	80.2	79.0	77.8	76.5	75.3
70°	76.4	72.8	69.1	66.8	65.5	64.4	63.2	62.1
72.5°	63.8	60.9	57.9	56.1	55.6	55.1	54.7	54.2
75°	47.8	46.8	45.6	45.0	44.8	44.6	44.4	44.2
77.5°	36.1	35.4	34.9	34.5	34.3	34.1	33.9	33.7
80°	29.0	28.7	28.4	28.2	27.9	27.7	27.5	27.3
82.5°	22.2	21.9	21.6	21.4	21.4	21.3	21.3	21.3
85°	12.7	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	10.8	10.9	11.0	11.1	11.1	11.1	11.2	11.2
90°	30.3	31.3	32.3	33.1	33.6	34.1	34.6	35.2
92.5°	46.8	47.6	48.4	48.7	48.4	48.1	47.7	47.4
95°	88.9	90.0	91.0	91.5	91.5	91.5	91.5	91.5
97.5°	138.3	139.5	140.7	141.2	141.1	141.0	140.9	140.8
100°	174.0	174.8	175.6	176.2	176.8	177.3	177.8	178.3
102.5°	215.3	216.1	216.9	217.2	217.1	217.0	216.9	216.8
105°	276.9	276.9	276.9	277.2	277.7	278.2	278.7	279.2
107.5°	343.6	344.5	345.3	345.5	345.2	344.9	344.6	344.3
110°	388.1	389.2	390.2	390.4	389.9	389.4	388.9	388.4





TEST NUMBER: P332268-840

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.6	433.9	435.2	435.8	435.7	435.6	435.5	435.4
115°	500.4	500.6	500.9	500.9	500.6	500.4	500.1	499.9
117.5°	568.8	568.7	568.7	568.3	567.5	566.7	566.0	565.3
120°	614.3	614.1	613.8	613.4	612.9	612.4	611.9	611.3
122.5°	660.5	659.7	659.0	658.3	657.6	656.9	656.1	655.4
125°	728.9	727.9	726.8	725.8	724.8	723.7	722.7	721.6
127.5°	796.6	795.2	793.7	792.3	791.1	789.9	788.7	787.6
130°	841.5	840.5	839.5	838.0	836.2	834.4	832.5	830.7
132.5°	885.2	884.0	882.7	881.4	880.0	878.6	877.2	875.8
135°	950.7	949.6	948.6	947.8	947.3	946.7	946.2	945.7
137.5°	1014.6	1013.5	1012.4	1011.4	1010.4	1009.5	1008.5	1007.4
140°	1056.6	1056.4	1056.1	1055.1	1053.3	1051.5	1049.7	1047.8
142.5°	1096.1	1095.8	1095.6	1094.7	1093.3	1091.9	1090.6	1089.1
145°	1154.1	1153.8	1153.6	1152.9	1151.9	1150.7	1149.7	1148.7
147.5°	1208.8	1208.8	1208.8	1208.0	1206.4	1204.9	1203.3	1201.7
150°	1242.5	1242.5	1242.5	1241.8	1240.2	1238.7	1237.1	1235.6
152.5°	1273.4	1273.8	1274.2	1273.8	1272.4	1271.1	1269.7	1268.4
155°	1318.6	1319.6	1320.7	1320.3	1318.5	1316.7	1314.8	1312.9
157.5°	1357.4	1358.5	1359.6	1359.4	1358.0	1356.5	1355.0	1353.5
160°	1381.3	1382.6	1383.9	1384.0	1383.0	1381.9	1380.9	1379.9
162.5°	1403.8	1405.1	1406.4	1406.2	1404.5	1402.9	1401.2	1399.6
165°	1432.3	1433.8	1435.4	1435.2	1433.4	1431.6	1429.8	1427.9
167.5°	1455.3	1456.9	1458.5	1458.5	1456.9	1455.3	1453.7	1452.1
170°	1467.9	1469.9	1471.7	1471.7	1469.9	1467.9	1466.1	1464.3
172.5°	1477.9	1479.6	1481.2	1481.1	1479.1	1477.3	1475.5	1473.7
175°	1488.5	1490.2	1491.7	1491.6	1489.8	1487.9	1486.1	1484.3
177.5°	1493.4	1494.6	1495.8	1495.7	1494.3	1492.8	1491.4	1490.0
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7

(END OF REPORT)