

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332249-840

Luminaire Tested: **S123RDIP-S340D585U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332249-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D585U840-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3677.1 lumens  
Efficiency: N/A  
Efficacy: 143.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332249-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332249-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	31
2	86	79	74	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	30	28	27	22
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	32	51	41	34	29	34	29	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6245	6245	6245
5°	6269	6183	6218
10°	6233	6105	6084
15°	6167	5962	5899
20°	6074	5783	5648
25°	5980	5583	5404
30°	5854	5351	5059
35°	5727	5119	4742
40°	5606	4846	4350
45°	5451	4576	3997
50°	5280	4270	3600
55°	5104	3920	3232
60°	4943	3546	2827
65°	4735	3140	2420
70°	4472	2634	1954
75°	4092	2075	1838
80°	3645	1841	1692
85°	3075	1618	1507



TEST NUMBER: P332249-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.5	1.5
10°-20°	151.6	4.1
20°-30°	218.3	5.9
30°-40°	245.9	6.7
40°-50°	235.2	6.4
50°-60°	192.6	5.2
60°-70°	130.0	3.5
70°-80°	65.4	1.8
80°-90°	19.5	0.5
90°-100°	28.2	0.8
100°-110°	134.3	3.7
110°-120°	322.7	8.8
120°-130°	410.9	11.2
130°-140°	439.0	11.9
140°-150°	410.5	11.2
150°-160°	331.2	9.0
160°-170°	213.7	5.8
170°-180°	73.7	2.0
0°-30°	424.3	11.5
0°-40°	670.2	18.2
0°-60°	1098.1	29.9
0°-90°	1312.8	35.7
90°-120°	485.2	13.2
90°-150°	1745.7	47.5
90°-180°	2364.0	64.3
0°-180°	3677.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	580	580	580	580	580	
5°	580	578	572	576	576	55
15°	553	548	535	533	529	156
25°	504	491	470	460	455	231
35°	436	418	390	370	361	273
45°	358	336	301	275	263	276
55°	272	248	209	183	172	244
65°	186	159	123	101	95	184
75°	98	76	50	45	44	105
85°	25	15	13	12	12	28
90°	1	6	14	16	17	3
95°	35	13	18	22	22	43
105°	172	175	126	30	25	182
115°	322	326	331	336	339	318
125°	454	458	461	462	463	405
135°	565	568	571	572	571	435
145°	652	656	657	658	658	408
155°	718	717	718	720	717	331
165°	757	756	755	759	756	214
175°	775	773	773	777	772	74
180°	775	775	775	775	775	



TEST NUMBER: P332249-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	582.1	581.7	581.4	581.1	580.8	580.1	579.1	578.0	577.0	576.0	576.9
5°	580.2	579.7	579.2	578.7	578.0	577.2	575.9	574.7	573.4	572.2	573.1
7.5°	574.8	574.2	573.7	573.1	572.6	571.5	569.9	568.3	566.5	564.9	565.4
10°	570.3	569.6	568.9	568.2	567.3	566.0	564.2	562.3	560.4	558.6	558.7
12.5°	563.9	563.1	562.3	561.5	560.7	559.1	556.7	554.5	552.2	549.9	549.8
15°	553.4	552.2	551.1	549.9	548.8	546.7	543.8	540.9	538.0	535.0	534.5
17.5°	540.1	538.8	537.5	536.0	534.7	532.2	528.5	524.7	521.1	517.4	516.2
20°	530.3	528.7	526.9	525.3	523.6	520.8	516.8	512.8	508.9	504.9	503.5
22.5°	519.4	517.5	515.5	513.6	511.7	508.7	504.4	500.2	495.9	491.7	490.0
25°	503.5	500.9	498.3	495.6	493.0	489.3	484.5	479.7	474.8	470.1	467.9
27.5°	484.2	481.3	478.4	475.5	472.6	468.6	463.2	457.8	452.4	447.1	444.0
30°	471.0	467.9	464.7	461.6	458.5	453.9	448.1	442.2	436.4	430.5	427.0
32.5°	457.9	454.2	450.7	447.2	443.6	438.8	432.5	426.4	420.2	413.9	410.1
35°	435.8	431.9	428.2	424.4	420.7	415.6	409.1	402.5	396.1	389.6	385.2
37.5°	413.3	409.1	405.0	400.8	396.6	391.0	384.2	377.2	370.3	363.3	358.3
40°	399.0	394.5	389.8	385.3	380.6	374.6	367.2	359.7	352.3	344.9	339.5
42.5°	382.8	378.2	373.7	369.0	364.5	358.3	350.6	343.0	335.3	327.6	321.6
45°	358.1	353.4	348.7	344.0	339.2	332.9	324.9	316.8	308.7	300.6	294.7
47.5°	333.4	328.2	323.0	317.8	312.7	306.1	298.0	289.9	282.0	273.9	267.4
50°	315.3	310.3	305.5	300.5	295.6	288.9	280.4	272.0	263.5	255.0	248.5
52.5°	299.1	293.8	288.4	283.1	277.7	270.8	262.5	254.1	245.7	237.3	230.7
55°	272.0	266.8	261.8	256.6	251.5	244.5	235.6	226.7	217.8	208.9	202.9
57.5°	246.9	241.4	235.8	230.1	224.6	217.3	208.4	199.4	190.6	181.7	175.9
60°	229.6	223.9	218.1	212.4	206.6	199.4	190.8	182.1	173.4	164.7	159.1
62.5°	212.3	206.5	200.8	195.1	189.3	182.1	173.4	164.7	156.0	147.3	142.1
65°	185.9	180.2	174.4	168.6	162.9	155.9	147.7	139.6	131.5	123.3	118.2
67.5°	159.5	153.6	147.7	142.0	136.1	129.4	121.5	113.7	105.8	98.1	94.2
70°	142.1	136.4	130.8	125.1	119.6	113.0	105.7	98.4	91.1	83.7	80.1
72.5°	124.8	119.3	113.7	108.1	102.5	96.4	89.8	83.1	76.4	69.8	66.9
75°	98.4	93.3	88.3	83.3	78.3	72.9	67.2	61.4	55.6	49.9	48.9
77.5°	74.2	69.7	65.1	60.6	56.1	52.0	48.3	44.5	40.9	37.2	36.7
80°	58.8	54.5	50.3	45.9	41.7	38.5	36.3	34.0	31.8	29.7	29.3
82.5°	44.1	40.4	36.8	33.0	29.3	27.0	26.0	24.9	23.9	22.8	22.5
85°	24.9	22.6	20.3	18.1	15.8	14.4	14.1	13.8	13.5	13.1	12.9
87.5°	9.2	8.5	7.8	7.2	6.5	6.4	6.7	7.0	7.4	7.7	7.7
90°	0.6	1.8	3.1	4.4	5.7	7.2	8.8	10.5	12.1	13.8	14.3
92.5°	10.7	10.4	10.0	9.6	9.3	9.7	11.0	12.2	13.5	14.7	15.6
95°	35.1	29.9	24.6	19.4	14.1	12.2	13.6	15.0	16.5	17.9	18.8
97.5°	70.6	68.3	65.9	63.5	61.2	55.4	46.2	37.0	27.8	18.6	19.6
100°	97.4	99.9	102.5	105.0	107.6	98.9	78.9	59.0	39.0	19.0	20.0
102.5°	127.7	129.6	131.5	133.3	135.1	125.1	103.3	81.5	59.7	37.9	34.7
105°	171.7	173.1	174.5	175.8	177.2	172.2	160.7	149.2	137.6	126.1	103.5
107.5°	217.9	219.0	220.3	221.4	222.5	223.9	225.7	227.5	229.3	231.2	214.6
110°	248.8	249.8	250.9	251.9	252.9	254.2	255.5	256.9	258.3	259.7	255.5



TEST NUMBER: P332249-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	278.3	279.2	280.1	281.0	282.0	283.2	284.6	286.0	287.4	288.8	288.9
115°	321.9	322.8	323.5	324.3	325.1	326.0	327.2	328.3	329.4	330.6	331.9
117.5°	364.3	365.2	366.2	367.1	368.0	368.8	369.4	370.0	370.6	371.1	372.2
120°	390.5	391.6	392.8	393.9	395.2	395.9	396.3	396.7	397.1	397.4	398.5
122.5°	417.3	418.2	419.1	420.1	421.0	421.7	422.2	422.7	423.2	423.7	424.4
125°	453.8	454.9	456.0	457.0	458.0	458.8	459.3	459.8	460.3	460.8	461.0
127.5°	489.4	490.4	491.4	492.4	493.4	494.2	494.8	495.5	496.1	496.8	497.2
130°	511.5	512.5	513.5	514.5	515.5	516.3	516.8	517.4	517.9	518.4	518.9
132.5°	532.7	533.7	534.7	535.7	536.7	537.5	537.9	538.3	538.7	539.2	539.7
135°	565.0	565.8	566.5	567.3	568.2	568.8	569.3	569.8	570.3	570.8	571.2
137.5°	592.7	593.7	594.6	595.6	596.5	597.2	597.4	597.7	598.0	598.3	599.0
140°	611.1	611.9	612.7	613.4	614.2	614.8	615.1	615.5	615.9	616.3	616.8
142.5°	628.1	628.9	629.8	630.5	631.3	631.8	632.2	632.6	633.0	633.4	633.8
145°	652.0	652.9	653.8	654.7	655.6	656.2	656.4	656.7	656.9	657.2	657.4
147.5°	674.5	675.1	675.7	676.2	676.8	677.2	677.5	677.7	678.0	678.3	678.5
150°	688.3	688.7	689.0	689.4	689.8	690.1	690.4	690.6	690.9	691.2	691.5
152.5°	700.7	700.9	701.0	701.3	701.5	701.7	701.8	702.0	702.1	702.3	702.7
155°	718.2	718.0	717.7	717.5	717.2	717.2	717.3	717.4	717.5	717.7	718.3
157.5°	731.8	731.8	731.7	731.7	731.7	731.6	731.5	731.4	731.2	731.1	732.0
160°	740.1	740.0	739.9	739.7	739.6	739.5	739.3	739.2	739.1	739.0	739.7
162.5°	748.0	747.6	747.3	747.0	746.6	746.4	746.3	746.2	746.0	745.9	746.8
165°	757.4	757.0	756.7	756.3	755.9	755.6	755.5	755.4	755.3	755.1	756.2
167.5°	764.8	764.3	763.8	763.3	762.8	762.4	762.4	762.4	762.4	762.4	763.6
170°	768.9	768.4	767.9	767.4	766.9	766.6	766.6	766.6	766.6	766.6	767.7
172.5°	771.7	771.1	770.4	769.8	769.2	769.0	769.1	769.2	769.3	769.4	770.4
175°	775.3	774.7	774.0	773.4	772.7	772.4	772.5	772.7	772.8	773.0	773.9
177.5°	776.2	775.7	775.2	774.7	774.2	774.0	774.1	774.2	774.3	774.4	775.2
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332249-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	577.8	578.8	579.8	580.1	580.0	579.8	579.6	579.5
5°	574.1	575.0	575.9	576.3	576.1	575.9	575.7	575.5
7.5°	566.0	566.5	567.0	567.1	566.7	566.4	566.0	565.7
10°	558.8	558.9	559.0	558.8	558.3	557.7	557.1	556.6
12.5°	549.8	549.7	549.7	549.3	548.7	548.1	547.4	546.8
15°	533.9	533.4	532.9	532.3	531.6	530.8	530.1	529.4
17.5°	515.1	514.0	512.9	511.8	510.7	509.6	508.6	507.5
20°	502.2	500.8	499.5	498.2	496.9	495.6	494.4	493.1
22.5°	488.4	486.7	484.9	483.5	482.3	481.2	480.0	478.9
25°	465.6	463.5	461.3	459.6	458.5	457.4	456.2	455.0
27.5°	441.0	438.0	434.9	432.5	430.7	429.0	427.3	425.5
30°	423.4	419.9	416.4	413.7	412.0	410.4	408.7	407.0
32.5°	406.2	402.3	398.4	395.6	393.8	392.1	390.3	388.6
35°	380.6	376.1	371.6	368.4	366.6	364.7	362.7	360.9
37.5°	353.1	348.0	343.0	339.2	336.9	334.6	332.2	329.9
40°	334.1	328.6	323.2	319.2	316.8	314.5	312.0	309.6
42.5°	315.7	309.8	303.9	299.8	297.6	295.5	293.4	291.1
45°	288.7	282.8	276.8	272.6	270.1	267.6	265.1	262.6
47.5°	260.8	254.4	247.9	243.6	241.4	239.1	236.8	234.6
50°	242.1	235.6	229.1	224.7	222.3	219.8	217.4	215.0
52.5°	223.9	217.1	210.5	206.0	203.8	201.7	199.5	197.3
55°	196.8	190.8	184.7	180.6	178.5	176.4	174.3	172.2
57.5°	170.2	164.4	158.8	154.9	153.2	151.4	149.7	147.8
60°	153.4	147.7	142.1	138.4	136.6	134.8	133.1	131.3
62.5°	136.7	131.5	126.1	122.5	120.7	118.9	116.9	115.1
65°	113.0	108.0	102.8	99.7	98.5	97.4	96.2	95.0
67.5°	90.4	86.5	82.7	80.2	79.0	77.8	76.5	75.3
70°	76.4	72.8	69.1	66.8	65.5	64.4	63.2	62.1
72.5°	63.8	60.9	57.9	56.1	55.6	55.1	54.7	54.2
75°	47.8	46.8	45.6	45.0	44.8	44.6	44.4	44.2
77.5°	36.1	35.4	34.9	34.5	34.3	34.1	33.9	33.7
80°	29.0	28.7	28.4	28.2	27.9	27.7	27.5	27.3
82.5°	22.2	21.9	21.6	21.4	21.4	21.3	21.3	21.3
85°	12.7	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	7.7	7.7	7.8	7.8	7.7	7.7	7.7	7.6
90°	14.8	15.3	15.9	16.3	16.6	16.8	17.1	17.3
92.5°	16.4	17.2	18.0	18.5	18.7	18.8	19.0	19.1
95°	19.7	20.5	21.4	21.9	21.9	21.9	21.9	21.9
97.5°	20.6	21.6	22.6	23.2	23.3	23.4	23.6	23.7
100°	21.0	22.1	23.1	23.6	23.8	23.9	24.0	24.2
102.5°	31.5	28.4	25.2	23.7	23.9	24.2	24.4	24.6
105°	80.8	58.2	35.5	24.3	24.5	24.8	25.0	25.3
107.5°	197.9	181.4	164.7	147.9	130.8	113.7	96.6	79.6
110°	251.4	247.1	242.9	231.6	213.3	195.0	176.7	158.3





TEST NUMBER: P332249-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.9	289.0	289.1	287.2	283.4	279.4	275.6	271.8
115°	333.2	334.5	335.8	336.6	337.1	337.7	338.2	338.7
117.5°	373.2	374.3	375.3	375.9	376.0	376.1	376.2	376.3
120°	399.5	400.5	401.5	402.0	402.0	402.0	402.0	402.0
122.5°	425.2	425.9	426.6	427.0	427.1	427.2	427.3	427.4
125°	461.3	461.5	461.8	462.1	462.3	462.6	462.8	463.1
127.5°	497.6	498.0	498.4	498.5	498.2	498.0	497.7	497.5
130°	519.4	519.9	520.4	520.6	520.3	520.1	519.8	519.6
132.5°	540.2	540.7	541.2	541.3	540.9	540.5	540.2	539.8
135°	571.6	572.0	572.3	572.3	572.0	571.6	571.2	570.8
137.5°	599.6	600.2	600.8	601.0	600.7	600.5	600.2	600.0
140°	617.3	617.8	618.3	618.4	618.2	617.9	617.7	617.4
142.5°	634.2	634.6	635.0	635.0	634.7	634.3	633.9	633.6
145°	657.7	657.9	658.2	658.3	658.3	658.3	658.3	658.3
147.5°	678.8	679.0	679.3	679.1	678.5	677.9	677.4	676.8
150°	691.7	692.0	692.2	692.2	691.8	691.4	690.9	690.6
152.5°	703.2	703.6	704.1	704.0	703.5	702.9	702.3	701.7
155°	718.9	719.6	720.2	720.1	719.4	718.6	717.9	717.1
157.5°	732.7	733.5	734.3	734.1	733.1	732.2	731.1	730.1
160°	740.5	741.2	742.0	741.9	741.1	740.2	739.3	738.4
162.5°	747.6	748.5	749.4	749.4	748.6	747.8	747.0	746.3
165°	757.2	758.2	759.2	759.3	758.4	757.5	756.6	755.7
167.5°	764.6	765.6	766.6	766.6	765.6	764.6	763.6	762.4
170°	768.7	769.7	770.7	770.7	769.7	768.7	767.7	766.6
172.5°	771.4	772.4	773.5	773.5	772.3	771.2	770.0	768.9
175°	774.8	775.7	776.6	776.5	775.5	774.5	773.5	772.3
177.5°	776.0	776.8	777.6	777.5	776.5	775.5	774.5	773.5
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3

(END OF REPORT)