

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332292

Luminaire Tested: **S123RDIP-S560D1025U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332292
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1025U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5658.2 lumens
Efficiency: N/A
Efficacy: 127.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332292

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332292

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	63	59	56	53	47	45	42	35	34	33	27
3	79	70	63	58	72	64	58	53	52	48	45	42	39	36	32	30	28	23
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	46	39	34	38	33	29	30	27	24	23	21	19	16
7	57	45	37	32	51	41	34	30	34	29	25	28	24	21	21	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10167	10167	10167
5°	10205	10065	10122
10°	10147	9939	9905
15°	10038	9706	9604
20°	9889	9415	9196
25°	9734	9089	8797
30°	9531	8712	8236
35°	9320	8335	7720
40°	9128	7890	7082
45°	8873	7451	6506
50°	8594	6953	5863
55°	8310	6382	5262
60°	8047	5772	4600
65°	7707	5112	3940
70°	7279	4293	3182
75°	6658	3377	2994
80°	5938	2994	2752
85°	5014	2643	2458



TEST NUMBER: P332292

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.7	1.6
10°-20°	246.8	4.4
20°-30°	355.3	6.3
30°-40°	400.3	7.1
40°-50°	382.9	6.8
50°-60°	313.6	5.5
60°-70°	211.6	3.7
70°-80°	106.4	1.9
80°-90°	31.9	0.6
90°-100°	82.8	1.5
100°-110°	247.8	4.4
110°-120°	421.4	7.4
120°-130°	554.3	9.8
130°-140°	623.0	11.0
140°-150°	612.4	10.8
150°-160°	515.6	9.1
160°-170°	343.2	6.1
170°-180°	120.2	2.1
0°-30°	690.8	12.2
0°-40°	1091.1	19.3
0°-60°	1787.6	31.6
0°-90°	2137.5	37.8
90°-120°	752.0	13.3
90°-150°	2541.8	44.9
90°-180°	3521.0	62.2
0°-180°	5658.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	944	944	944	944	944	
5°	944	940	932	938	937	90
15°	901	892	871	867	862	254
25°	820	800	765	750	741	377
35°	709	681	634	602	588	444
45°	583	547	490	447	427	450
55°	443	404	340	297	280	397
65°	303	259	201	165	155	299
75°	160	123	81	74	72	171
85°	41	25	21	20	20	46
90°	1	11	24	28	30	6
95°	59	66	74	78	78	66
105°	225	227	236	236	238	241
115°	424	427	425	426	425	420
125°	621	624	622	618	614	553
135°	806	811	810	807	805	621
145°	977	979	982	981	977	610
155°	1119	1119	1120	1123	1117	515
165°	1219	1216	1216	1221	1215	344
175°	1268	1264	1264	1269	1263	120
180°	1271	1271	1271	1271	1271	



TEST NUMBER: P332292

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5
2.5°	947.6	947.0	946.5	945.9	945.4	944.3	942.7	941.0	939.4	937.8	939.3
5°	944.5	943.7	942.8	942.0	941.1	939.7	937.6	935.6	933.5	931.5	933.0
7.5°	935.8	934.9	933.9	933.0	932.1	930.3	927.7	925.0	922.3	919.7	920.5
10°	928.4	927.2	926.0	924.8	923.7	921.5	918.5	915.4	912.3	909.3	909.4
12.5°	918.0	916.7	915.3	914.0	912.7	910.2	906.4	902.7	898.9	895.2	895.1
15°	900.8	899.0	897.1	895.2	893.4	890.0	885.3	880.5	875.7	871.0	870.1
17.5°	879.2	877.1	874.9	872.7	870.5	866.4	860.3	854.3	848.2	842.2	840.4
20°	863.3	860.6	857.9	855.1	852.4	847.8	841.3	834.9	828.4	821.9	819.7
22.5°	845.5	842.4	839.3	836.1	833.0	828.0	821.1	814.2	807.4	800.5	797.7
25°	819.6	815.4	811.1	806.9	802.6	796.6	788.7	780.9	773.1	765.3	761.7
27.5°	788.2	783.5	778.8	774.1	769.4	762.7	754.0	745.3	736.6	727.9	722.9
30°	766.8	761.7	756.6	751.5	746.4	739.0	729.5	720.0	710.4	700.9	695.1
32.5°	745.3	739.6	733.8	728.0	722.2	714.3	704.2	694.1	684.0	673.9	667.6
35°	709.3	703.2	697.1	691.0	684.8	676.5	665.9	655.4	644.8	634.3	626.9
37.5°	672.9	666.1	659.3	652.4	645.6	636.6	625.3	614.1	602.8	591.5	583.2
40°	649.6	642.1	634.6	627.1	619.6	609.8	597.8	585.7	573.6	561.5	552.6
42.5°	623.2	615.7	608.3	600.8	593.3	583.3	570.8	558.3	545.8	533.3	523.6
45°	582.9	575.3	567.6	560.0	552.3	541.9	528.8	515.7	502.6	489.5	479.8
47.5°	542.6	534.2	525.8	517.4	509.0	498.3	485.1	472.0	458.9	445.8	435.3
50°	513.2	505.2	497.2	489.2	481.2	470.3	456.5	442.8	429.0	415.2	404.6
52.5°	486.9	478.2	469.5	460.8	452.2	441.0	427.3	413.7	400.0	386.4	375.4
55°	442.8	434.4	426.1	417.7	409.4	398.0	383.5	369.1	354.6	340.1	330.2
57.5°	402.0	392.9	383.8	374.7	365.6	353.8	339.3	324.8	310.2	295.7	286.4
60°	373.8	364.5	355.1	345.7	336.4	324.6	310.5	296.4	282.2	268.1	258.9
62.5°	345.6	336.3	326.9	317.5	308.2	296.4	282.3	268.2	254.0	239.9	231.3
65°	302.6	293.2	283.9	274.5	265.1	253.8	240.5	227.3	214.0	200.7	192.4
67.5°	259.5	250.1	240.6	231.1	221.7	210.6	197.8	185.1	172.4	159.6	153.4
70°	231.3	222.1	213.0	203.8	194.6	184.0	172.1	160.2	148.3	136.4	130.4
72.5°	203.1	194.1	185.0	176.0	166.9	157.0	146.2	135.3	124.5	113.7	108.8
75°	160.1	151.9	143.8	135.6	127.4	118.6	109.3	99.9	90.6	81.2	79.5
77.5°	120.9	113.5	106.1	98.7	91.3	84.6	78.6	72.6	66.5	60.5	59.6
80°	95.8	88.8	81.8	74.8	67.8	62.6	59.0	55.4	51.8	48.3	47.7
82.5°	71.9	65.8	59.8	53.8	47.7	43.9	42.2	40.6	38.9	37.2	36.7
85°	40.6	36.9	33.1	29.4	25.6	23.5	23.0	22.5	22.0	21.4	21.1
87.5°	14.9	13.9	12.8	11.7	10.7	10.5	11.0	11.6	12.2	12.8	12.8
90°	1.0	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8
92.5°	24.2	25.7	27.2	28.7	30.2	31.8	33.4	35.0	36.7	38.3	39.0
95°	58.9	60.4	62.0	63.6	65.1	66.8	68.5	70.3	72.1	73.9	74.8
97.5°	104.6	105.8	106.9	108.1	109.2	110.4	111.7	113.0	114.3	115.6	116.6
100°	135.8	137.1	138.4	139.7	141.1	142.3	143.4	144.5	145.6	146.7	147.4
102.5°	171.7	172.5	173.3	174.1	174.9	176.0	177.5	178.9	180.4	181.9	182.5
105°	224.6	225.0	225.5	225.9	226.4	227.6	229.6	231.6	233.6	235.6	235.6
107.5°	286.1	286.4	286.6	286.9	287.2	287.7	288.5	289.3	290.1	290.9	291.6
110°	324.4	324.9	325.3	325.7	326.2	326.6	327.1	327.5	328.0	328.4	329.3



TEST NUMBER: P332292

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	364.3	364.6	364.9	365.1	365.4	365.6	365.7	365.8	365.9	365.9	367.0
115°	424.2	424.9	425.6	426.2	426.9	427.0	426.6	426.1	425.7	425.2	425.5
117.5°	484.5	485.0	485.4	485.9	486.3	486.2	485.7	485.1	484.5	483.9	483.9
120°	522.1	523.4	524.7	526.1	527.4	527.5	526.4	525.3	524.2	523.1	522.8
122.5°	561.2	562.2	563.1	564.1	565.1	565.3	564.7	564.1	563.6	563.0	562.4
125°	620.9	621.6	622.2	622.9	623.5	623.7	623.2	622.8	622.3	621.9	621.0
127.5°	676.0	677.4	678.8	680.2	681.7	682.1	681.6	681.2	680.7	680.2	678.9
130°	712.7	714.5	716.3	718.0	719.8	720.4	719.7	719.0	718.4	717.7	716.8
132.5°	749.5	751.2	753.0	754.8	756.6	757.2	756.7	756.2	755.7	755.2	754.2
135°	805.6	806.9	808.2	809.5	810.9	811.4	811.2	811.0	810.8	810.5	809.7
137.5°	857.5	858.6	859.7	860.8	861.9	862.7	863.3	863.9	864.5	865.0	864.1
140°	893.4	894.5	895.6	896.7	897.8	898.5	898.7	898.9	899.2	899.4	899.2
142.5°	926.1	927.2	928.4	929.5	930.6	931.3	931.7	932.1	932.5	932.9	932.7
145°	977.2	977.7	978.1	978.6	979.0	979.6	980.2	980.9	981.6	982.2	982.0
147.5°	1022.0	1022.8	1023.6	1024.4	1025.2	1025.9	1026.5	1027.1	1027.7	1028.4	1028.4
150°	1053.1	1053.6	1054.0	1054.4	1054.9	1055.3	1055.8	1056.2	1056.7	1057.1	1057.1
152.5°	1078.7	1079.3	1079.9	1080.5	1081.1	1081.6	1081.9	1082.1	1082.4	1082.7	1083.0
155°	1119.0	1119.0	1119.0	1119.0	1119.0	1119.1	1119.3	1119.5	1119.8	1120.0	1120.9
157.5°	1153.3	1153.1	1152.8	1152.5	1152.3	1152.2	1152.4	1152.6	1152.8	1152.9	1153.9
160°	1174.9	1174.4	1174.0	1173.6	1173.1	1172.9	1172.9	1172.9	1172.9	1172.9	1174.0
162.5°	1194.1	1193.4	1192.8	1192.2	1191.6	1191.4	1191.5	1191.7	1191.9	1192.1	1193.2
165°	1218.8	1218.1	1217.5	1216.8	1216.2	1215.8	1215.8	1215.8	1215.8	1215.8	1217.1
167.5°	1238.6	1237.7	1236.8	1235.9	1235.0	1234.7	1234.9	1235.0	1235.2	1235.4	1236.8
170°	1249.8	1248.9	1248.0	1247.1	1246.2	1245.8	1245.8	1245.8	1245.8	1245.8	1247.3
172.5°	1258.5	1257.7	1256.8	1255.9	1255.0	1254.5	1254.5	1254.5	1254.5	1254.5	1255.9
175°	1267.7	1266.8	1265.9	1265.1	1264.2	1263.7	1263.7	1263.7	1263.7	1263.7	1265.1
177.5°	1271.5	1270.8	1270.1	1269.4	1268.7	1268.3	1268.3	1268.3	1268.3	1268.3	1269.4
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P332292

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5
2.5°	940.8	942.3	943.8	944.4	944.1	943.8	943.6	943.3
5°	934.5	936.1	937.6	938.2	937.9	937.5	937.2	936.8
7.5°	921.4	922.2	923.1	923.2	922.6	922.1	921.5	920.9
10°	909.6	909.8	909.9	909.6	908.8	907.9	907.1	906.2
12.5°	895.0	894.9	894.8	894.2	893.2	892.2	891.3	890.3
15°	869.3	868.4	867.6	866.5	865.3	864.2	863.0	861.8
17.5°	838.6	836.8	834.9	833.2	831.4	829.6	827.8	826.1
20°	817.5	815.3	813.1	811.0	808.9	806.9	804.8	802.8
22.5°	795.0	792.2	789.5	787.1	785.2	783.3	781.4	779.5
25°	758.1	754.5	751.0	748.2	746.4	744.5	742.6	740.7
27.5°	717.9	713.0	708.0	704.1	701.2	698.4	695.5	692.6
30°	689.3	683.5	677.8	673.5	670.8	668.1	665.3	662.6
32.5°	661.3	654.9	648.6	644.0	641.2	638.3	635.4	632.6
35°	619.6	612.3	605.0	599.8	596.7	593.7	590.6	587.5
37.5°	574.9	566.6	558.3	552.3	548.5	544.7	540.9	537.1
40°	543.8	534.9	526.1	519.7	515.8	511.9	508.0	504.0
42.5°	514.0	504.3	494.6	488.0	484.5	481.0	477.5	474.0
45°	470.1	460.4	450.7	443.8	439.7	435.6	431.5	427.4
47.5°	424.7	414.2	403.6	396.5	392.9	389.2	385.6	381.9
50°	394.1	383.5	373.0	365.7	361.8	357.9	354.0	350.1
52.5°	364.5	353.5	342.5	335.3	331.8	328.3	324.8	321.3
55°	320.4	310.5	300.6	294.0	290.6	287.2	283.8	280.4
57.5°	277.0	267.7	258.4	252.3	249.4	246.5	243.6	240.7
60°	249.7	240.5	231.3	225.3	222.4	219.5	216.6	213.7
62.5°	222.6	214.0	205.3	199.5	196.5	193.4	190.4	187.4
65°	184.0	175.7	167.3	162.2	160.4	158.5	156.6	154.7
67.5°	147.2	140.9	134.7	130.6	128.6	126.6	124.6	122.6
70°	124.4	118.5	112.5	108.6	106.7	104.9	103.0	101.1
72.5°	103.9	99.1	94.2	91.4	90.6	89.8	89.0	88.2
75°	77.8	76.1	74.4	73.4	73.0	72.7	72.3	72.0
77.5°	58.7	57.8	56.8	56.2	55.9	55.5	55.2	54.8
80°	47.2	46.7	46.2	45.8	45.5	45.1	44.8	44.4
82.5°	36.2	35.7	35.2	34.9	34.8	34.8	34.7	34.6
85°	20.8	20.4	20.1	19.9	19.9	19.9	19.9	19.9
87.5°	12.8	12.9	12.9	12.9	12.9	12.8	12.8	12.7
90°	25.7	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	39.8	40.5	41.2	41.4	41.1	40.9	40.6	40.3
95°	75.6	76.5	77.4	77.9	77.9	77.9	77.9	77.9
97.5°	117.6	118.7	119.7	120.1	120.1	120.0	119.9	119.8
100°	148.1	148.7	149.4	150.0	150.4	150.8	151.3	151.7
102.5°	183.2	183.9	184.5	184.8	184.7	184.6	184.6	184.5
105°	235.6	235.6	235.6	235.8	236.2	236.7	237.1	237.6
107.5°	292.3	293.0	293.7	293.9	293.7	293.4	293.1	292.9
110°	330.2	331.1	332.0	332.2	331.7	331.3	330.9	330.4



TEST NUMBER: P332292

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.1	369.1	370.2	370.7	370.6	370.5	370.4	370.3
115°	425.7	425.9	426.1	426.1	425.9	425.7	425.5	425.2
117.5°	483.8	483.8	483.8	483.4	482.8	482.2	481.6	480.9
120°	522.6	522.4	522.2	521.8	521.4	521.0	520.5	520.1
122.5°	561.8	561.3	560.7	560.1	559.5	558.8	558.2	557.6
125°	620.1	619.2	618.3	617.4	616.6	615.7	614.8	613.9
127.5°	677.7	676.5	675.2	674.1	673.1	672.0	671.0	670.0
130°	715.9	715.0	714.2	712.9	711.4	709.8	708.3	706.7
132.5°	753.1	752.1	751.0	749.9	748.7	747.5	746.3	745.1
135°	808.8	807.9	807.0	806.3	805.9	805.4	805.0	804.6
137.5°	863.2	862.3	861.3	860.4	859.6	858.7	857.9	857.1
140°	898.9	898.7	898.5	897.6	896.1	894.5	893.0	891.4
142.5°	932.5	932.3	932.0	931.3	930.1	928.9	927.7	926.5
145°	981.8	981.6	981.3	980.8	979.9	979.0	978.1	977.2
147.5°	1028.4	1028.4	1028.4	1027.7	1026.4	1025.0	1023.7	1022.4
150°	1057.1	1057.1	1057.1	1056.4	1055.1	1053.8	1052.4	1051.1
152.5°	1083.4	1083.7	1084.1	1083.7	1082.5	1081.4	1080.2	1079.1
155°	1121.8	1122.7	1123.5	1123.2	1121.7	1120.1	1118.5	1117.0
157.5°	1154.8	1155.7	1156.7	1156.5	1155.3	1154.0	1152.8	1151.5
160°	1175.1	1176.2	1177.3	1177.4	1176.6	1175.7	1174.8	1173.9
162.5°	1194.3	1195.4	1196.5	1196.3	1194.9	1193.5	1192.1	1190.7
165°	1218.5	1219.8	1221.1	1221.0	1219.5	1217.9	1216.4	1214.8
167.5°	1238.1	1239.5	1240.9	1240.9	1239.5	1238.1	1236.8	1235.4
170°	1248.9	1250.4	1252.0	1252.0	1250.4	1248.9	1247.3	1245.8
172.5°	1257.3	1258.7	1260.0	1260.0	1258.4	1256.9	1255.3	1253.7
175°	1266.4	1267.7	1269.1	1268.9	1267.4	1265.8	1264.3	1262.7
177.5°	1270.5	1271.5	1272.6	1272.5	1271.3	1270.0	1268.8	1267.5
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7

(END OF REPORT)