

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332253-840

Luminaire Tested: **S123RDIP-S340D805U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332253-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4156.2 lumens
Efficiency: N/A
Efficacy: 133.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35	29
2	86	79	73	69	78	72	67	63	58	54	51	45	42	40	32	31	30	25
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	29	27	26	21
4	72	62	55	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	19	18	15
7	57	45	37	32	51	41	34	30	33	28	25	26	23	20	20	18	16	13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5916	5916	5916	5916
5°	7052	5942	5232	5942
10°	8805	5908	4726	5908
15°	10336	5846	4310	5846
20°	11535	5756	3956	5756
25°	11351	5662	3739	5662
30°	8158	5574	3515	5574
35°	5447	5460	3369	5460
40°	4013	5323	3219	5323
45°	3367	5083	3073	5083
50°	2971	4767	2869	4767
55°	2607	4406	2586	4406
60°	2321	4060	2370	4060
65°	2038	3691	2203	3691
70°	1599	3361	2014	3361
75°	1406	2936	1838	2936
80°	1227	2492	1810	2492
85°	988	2013	1927	2013



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	1.3
10°-20°	168.9	4.1
20°-30°	265.3	6.4
30°-40°	276.8	6.7
40°-50°	236.9	5.7
50°-60°	180.5	4.3
60°-70°	115.7	2.8
70°-80°	55.7	1.3
80°-90°	17.7	0.4
90°-100°	65.5	1.6
100°-110°	196.0	4.7
110°-120°	333.3	8.0
120°-130°	438.5	10.5
130°-140°	492.8	11.9
140°-150°	484.4	11.7
150°-160°	407.8	9.8
160°-170°	271.5	6.5
170°-180°	95.1	2.3
0°-30°	488.2	11.7
0°-40°	764.9	18.4
0°-60°	1182.3	28.4
0°-90°	1371.4	33.0
90°-120°	594.8	14.3
90°-150°	2010.5	48.4
90°-180°	2785.0	67.0
0°-180°	4156.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	550	550	550	550	550	
5°	653	550	484	550	653	67
15°	928	525	387	525	928	263
25°	956	477	315	477	956	411
35°	414	416	256	416	414	272
45°	221	334	202	334	221	174
55°	139	235	138	235	139	126
65°	80	145	86	145	80	79
75°	34	71	44	71	34	36
85°	8	16	16	16	8	10
90°	24	1	24	1	24	12
95°	62	47	62	47	62	63
105°	188	178	188	178	188	199
115°	336	336	336	336	336	333
125°	486	491	486	491	486	434
135°	636	637	636	637	636	489
145°	773	773	773	773	773	482
155°	884	885	884	885	884	407
165°	961	964	961	964	961	271
175°	999	1003	999	1003	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	585.4	586.1	583.7	583.3	580.5	579.8	579.8	575.7	573.3	570.2	568.3
5°	652.7	656.4	654.5	650.4	643.3	641.6	637.1	630.1	622.1	612.2	607.5
7.5°	736.7	741.8	739.8	733.4	725.9	719.9	707.3	695.6	679.2	664.8	652.5
10°	805.6	800.2	796.0	789.6	782.7	771.7	758.5	740.4	719.5	703.0	684.7
12.5°	857.2	856.3	850.9	844.3	834.8	824.3	808.0	786.0	761.6	737.8	716.8
15°	927.5	928.9	925.3	918.6	904.8	886.3	861.8	852.6	817.8	791.9	766.1
17.5°	976.1	975.8	975.3	965.9	952.0	938.8	916.0	891.9	860.4	823.9	789.1
20°	1007.0	1004.6	1005.1	994.5	984.2	968.9	946.7	911.7	885.9	843.7	807.7
22.5°	1006.2	1005.7	1007.5	1003.9	996.4	984.7	967.2	937.7	904.6	862.1	821.6
25°	955.7	953.8	964.8	968.0	980.0	982.1	976.8	960.7	929.4	885.6	835.5
27.5°	799.8	798.8	819.3	845.1	877.6	902.9	927.4	939.2	929.4	898.0	847.8
30°	656.4	678.5	688.9	726.1	767.5	816.9	860.2	901.3	911.5	897.8	856.7
32.5°	545.0	564.3	573.0	604.8	643.5	701.4	766.3	824.6	865.8	876.2	851.4
35°	414.5	414.8	434.5	448.7	484.4	543.9	607.0	685.1	762.8	821.6	827.7
37.5°	330.8	331.9	344.0	358.0	384.9	416.3	471.8	536.7	626.4	716.7	769.7
40°	285.6	287.7	296.7	310.5	329.8	353.7	396.9	458.1	532.9	633.4	715.5
42.5°	256.6	260.0	264.7	275.4	287.3	309.6	344.6	391.8	459.9	554.9	649.6
45°	221.2	223.1	226.6	231.6	242.4	257.8	281.3	313.2	369.6	446.1	540.9
47.5°	195.1	194.1	197.8	201.8	209.0	219.6	235.4	261.3	301.5	362.9	443.3
50°	177.4	177.1	179.8	182.8	189.7	197.4	210.4	229.8	261.9	312.7	386.4
52.5°	160.9	161.7	163.6	167.3	172.3	178.5	190.2	204.3	231.8	275.6	337.0
55°	138.9	139.6	142.1	144.2	147.7	154.1	161.4	173.2	192.0	222.6	273.2
57.5°	120.2	119.9	122.3	122.9	126.8	132.0	137.6	146.8	160.5	183.2	217.2
60°	107.8	107.0	109.2	110.8	112.9	117.1	121.9	130.8	141.7	158.3	187.5
62.5°	96.4	96.1	97.7	99.4	101.1	104.9	108.9	115.7	124.3	138.4	161.6
65°	80.0	80.7	81.4	82.1	83.0	85.4	89.2	93.9	99.8	109.7	126.3
67.5°	62.9	63.6	63.8	65.2	67.3	68.8	71.1	75.2	79.4	87.7	97.1
70°	50.8	50.6	50.8	51.5	54.1	56.7	59.8	62.8	65.4	71.3	79.3
72.5°	43.6	43.2	43.8	44.0	45.2	45.9	47.9	50.8	54.1	58.1	63.8
75°	33.8	33.8	33.8	33.8	34.8	35.2	36.0	36.7	37.9	39.8	44.0
77.5°	25.0	25.0	25.4	25.7	25.9	26.2	26.6	27.3	27.7	28.7	30.5
80°	19.8	20.0	19.8	20.0	20.0	20.5	20.7	21.4	21.6	22.8	23.5
82.5°	14.8	14.7	14.8	15.1	15.1	15.6	15.7	16.2	16.2	16.8	17.5
85°	8.0	7.6	8.0	7.8	8.3	7.8	8.0	8.5	8.5	8.7	9.7
87.5°	6.7	7.0	6.5	6.6	6.6	6.6	6.5	6.4	6.6	6.3	6.0
90°	23.7	23.3	23.0	22.6	22.3	21.7	21.0	20.4	19.7	19.0	16.7
92.5°	31.9	32.1	32.3	32.5	32.7	32.5	32.0	31.4	30.9	30.3	29.0
95°	61.6	61.6	61.6	61.6	61.6	61.2	60.5	59.8	59.2	58.5	57.1
97.5°	94.7	94.8	94.9	94.9	95.0	94.6	93.8	93.0	92.2	91.4	90.4
100°	120.0	119.7	119.3	119.0	118.7	118.2	117.6	117.1	116.6	116.0	115.2
102.5°	145.9	146.0	146.0	146.1	146.2	145.9	145.4	144.9	144.4	143.9	142.7
105°	187.9	187.5	187.2	186.8	186.5	186.3	186.3	186.3	186.3	186.3	184.8
107.5°	231.7	231.9	232.1	232.3	232.5	232.4	231.8	231.2	230.7	230.0	229.4
110°	261.4	261.7	262.1	262.4	262.8	262.6	261.9	261.2	260.4	259.7	259.4



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	293.0	293.0	293.1	293.2	293.2	292.9	292.0	291.1	290.3	289.4	289.4
115°	336.4	336.5	336.7	336.9	337.1	337.1	336.9	336.7	336.5	336.4	336.7
117.5°	380.4	380.9	381.4	381.9	382.3	382.6	382.6	382.7	382.7	382.7	383.2
120°	411.3	411.7	412.0	412.4	412.7	413.0	413.2	413.3	413.5	413.7	414.7
122.5°	441.0	441.5	442.0	442.5	443.0	443.5	443.9	444.4	444.8	445.4	445.8
125°	485.5	486.3	487.0	487.7	488.4	489.1	489.8	490.5	491.2	491.9	492.2
127.5°	530.0	530.8	531.6	532.4	533.2	534.1	535.0	536.0	537.0	538.0	538.4
130°	559.0	560.3	561.5	562.7	563.9	564.9	565.6	566.3	566.9	567.6	568.3
132.5°	589.4	590.3	591.2	592.2	593.1	594.0	594.8	595.7	596.5	597.3	597.7
135°	636.4	636.7	637.1	637.4	637.8	638.3	639.0	639.7	640.5	641.2	641.3
137.5°	677.9	678.6	679.2	679.9	680.5	681.3	682.1	682.8	683.5	684.2	683.8
140°	705.1	706.3	707.5	708.7	710.0	710.6	710.8	711.0	711.2	711.3	711.2
142.5°	732.9	733.8	734.8	735.7	736.7	737.2	737.4	737.6	737.7	737.9	737.6
145°	773.0	773.7	774.4	775.1	775.8	776.2	776.4	776.6	776.8	776.9	776.4
147.5°	808.7	809.7	810.7	811.8	812.8	813.4	813.4	813.4	813.4	813.4	812.9
150°	831.4	832.4	833.5	834.6	835.7	836.2	836.2	836.2	836.2	836.2	835.8
152.5°	853.5	854.4	855.4	856.3	857.2	857.5	857.2	856.9	856.7	856.4	856.2
155°	883.5	884.7	886.0	887.2	888.4	888.7	888.0	887.3	886.6	885.9	885.8
157.5°	910.8	911.8	912.8	913.8	914.7	914.8	914.1	913.4	912.7	911.9	911.8
160°	928.5	929.2	929.9	930.6	931.3	931.2	930.4	929.5	928.6	927.8	927.8
162.5°	941.8	942.9	944.0	945.1	946.2	946.4	945.5	944.6	943.7	942.9	942.7
165°	960.9	962.1	963.3	964.6	965.8	965.9	964.8	963.8	962.7	961.7	961.7
167.5°	977.1	978.3	979.4	980.4	981.5	981.5	980.4	979.4	978.3	977.1	977.0
170°	985.3	986.6	987.8	989.1	990.3	990.3	989.1	987.8	986.6	985.3	985.3
172.5°	991.7	992.9	994.1	995.3	996.6	996.6	995.6	994.5	993.4	992.3	992.3
175°	998.8	1000.0	1001.3	1002.5	1003.7	1003.8	1002.7	1001.7	1000.7	999.6	999.6
177.5°	1002.6	1003.6	1004.5	1005.5	1006.5	1006.5	1005.7	1004.9	1004.0	1003.2	1003.2
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	567.4	566.9	564.3	561.3	557.3	554.7	552.6	551.5	548.1	543.9	541.2
5°	602.6	595.5	587.9	578.8	570.3	561.6	556.2	549.9	542.1	533.4	527.3
7.5°	640.1	626.2	611.4	595.9	580.8	567.1	555.0	544.7	532.4	519.9	511.2
10°	668.9	648.6	627.7	606.3	586.8	568.5	554.3	540.5	525.6	511.3	500.4
12.5°	695.1	668.4	644.3	617.9	593.0	571.1	550.8	534.4	516.5	501.3	489.0
15°	728.2	700.8	671.8	631.7	598.5	570.8	546.0	524.6	503.0	484.2	472.2
17.5°	759.1	718.1	678.8	645.5	602.4	567.7	537.6	512.0	488.2	468.3	453.4
20°	771.9	732.2	689.6	647.0	604.7	565.8	530.8	502.5	477.9	455.2	441.6
22.5°	779.6	734.7	689.7	644.0	599.1	558.7	524.0	492.9	466.2	444.7	427.9
25°	788.6	735.0	685.6	640.5	594.5	550.8	509.6	476.7	447.8	425.0	407.1
27.5°	794.6	731.4	673.1	622.9	576.3	532.8	495.0	460.1	430.7	406.6	387.4
30°	795.7	728.6	663.5	609.2	561.9	521.8	481.8	448.5	417.4	391.7	373.9
32.5°	797.2	721.6	650.5	592.8	544.3	504.7	468.5	436.6	404.8	379.5	361.2
35°	791.0	717.8	630.8	564.4	515.9	477.6	444.9	415.5	384.3	359.7	341.1
37.5°	764.3	702.6	610.4	532.5	481.8	446.4	419.7	394.0	365.4	338.9	321.4
40°	737.4	687.5	594.5	513.1	460.2	423.7	399.7	378.8	351.0	326.3	307.5
42.5°	697.3	666.9	579.5	492.8	435.8	400.6	380.3	360.7	336.4	311.2	293.6
45°	623.7	627.7	548.7	460.4	401.8	366.6	347.5	333.9	312.3	291.5	273.4
47.5°	531.5	568.9	512.5	426.0	366.2	333.1	316.4	304.5	289.8	269.5	253.0
50°	471.3	524.6	483.5	402.8	343.8	310.8	294.4	284.7	272.0	256.0	240.2
52.5°	415.8	473.1	448.5	377.0	319.4	289.3	273.3	265.3	255.2	240.1	225.9
55°	339.0	397.2	391.5	338.1	283.1	256.0	243.8	234.8	228.0	216.7	205.4
57.5°	274.3	329.3	332.2	294.8	251.0	224.2	213.7	206.9	202.5	194.0	183.5
60°	233.4	284.0	293.9	265.6	228.0	204.5	194.1	188.6	185.2	178.3	170.4
62.5°	199.5	242.6	253.8	233.5	206.0	183.9	175.8	170.7	168.2	162.4	155.3
65°	152.7	188.4	199.2	188.0	173.6	156.0	149.4	144.9	142.8	139.6	134.3
67.5°	114.8	140.9	152.8	144.8	139.6	128.5	124.3	121.9	120.0	117.8	113.4
70°	92.2	111.5	123.7	121.7	117.4	111.5	108.5	106.8	104.9	103.0	99.3
72.5°	74.1	87.5	98.9	100.0	96.5	95.3	92.6	91.9	90.8	88.6	86.4
75°	49.2	58.4	66.3	69.4	70.8	72.0	70.8	70.6	70.4	68.5	67.3
77.5°	32.2	37.2	42.2	47.5	49.7	51.2	51.6	52.5	51.8	50.9	50.3
80°	24.7	25.9	29.4	33.8	37.4	38.8	39.8	40.2	40.0	39.8	38.8
82.5°	18.0	18.9	20.6	23.7	26.7	29.0	29.6	29.5	30.0	30.2	29.4
85°	9.7	9.9	10.4	10.8	12.4	15.0	15.8	16.3	16.7	16.7	15.2
87.5°	5.9	5.3	5.2	4.7	4.9	4.8	5.6	6.2	6.8	6.4	6.7
90°	14.3	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	27.8	26.5	25.1	23.8	22.7	21.5	20.3	19.1	20.3	21.5	22.7
95°	55.6	54.2	52.8	51.5	50.3	49.1	47.8	46.6	47.8	49.1	50.3
97.5°	89.4	88.4	87.4	86.4	85.4	84.5	83.6	82.7	83.6	84.5	85.4
100°	114.3	113.4	112.6	111.6	110.6	109.5	108.5	107.3	108.5	109.5	110.6
102.5°	141.6	140.4	139.3	138.4	137.7	137.0	136.4	135.8	136.4	137.0	137.7
105°	183.2	181.6	180.1	179.0	178.7	178.3	178.0	177.6	178.0	178.3	178.7
107.5°	228.8	228.2	227.5	227.1	226.9	226.7	226.5	226.3	226.5	226.7	226.9
110°	259.0	258.7	258.3	258.0	257.6	257.3	256.9	256.6	256.9	257.3	257.6



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	289.3	289.2	289.1	289.0	288.8	288.6	288.4	288.2	288.4	288.6	288.8
115°	337.1	337.4	337.8	337.7	337.1	336.6	336.1	335.6	336.1	336.6	337.1
117.5°	383.6	384.2	384.6	384.7	384.3	384.0	383.6	383.2	383.6	384.0	384.3
120°	415.5	416.4	417.3	417.2	416.1	415.1	413.9	412.9	413.9	415.1	416.1
122.5°	446.3	446.7	447.2	447.0	446.2	445.5	444.6	443.9	444.6	445.5	446.2
125°	492.6	492.9	493.3	493.2	492.7	492.1	491.6	491.1	491.6	492.1	492.7
127.5°	538.8	539.2	539.6	539.2	538.1	536.9	535.8	534.7	535.8	536.9	538.1
130°	568.8	569.3	569.8	569.4	567.9	566.5	565.1	563.7	565.1	566.5	567.9
132.5°	598.1	598.5	599.0	598.4	597.0	595.6	594.2	592.8	594.2	595.6	597.0
135°	641.5	641.7	641.9	641.4	640.4	639.2	638.2	637.1	638.2	639.2	640.4
137.5°	683.3	682.9	682.4	681.8	680.9	679.9	679.1	678.2	679.1	679.9	680.9
140°	711.0	710.8	710.6	710.1	709.3	708.4	707.5	706.6	707.5	708.4	709.3
142.5°	737.3	737.0	736.7	736.1	735.2	734.3	733.5	732.6	733.5	734.3	735.2
145°	775.9	775.4	774.8	774.4	774.1	773.7	773.4	773.0	773.4	773.7	774.1
147.5°	812.4	811.9	811.4	810.9	810.2	809.6	809.0	808.4	809.0	809.6	810.2
150°	835.5	835.1	834.8	834.4	834.0	833.6	833.3	832.9	833.3	833.6	834.0
152.5°	856.0	855.8	855.6	855.2	854.6	854.1	853.6	853.2	853.6	854.1	854.6
155°	885.6	885.3	885.1	885.0	885.0	885.0	885.0	885.0	885.0	885.0	885.0
157.5°	911.7	911.5	911.4	911.4	911.6	911.8	912.0	912.2	912.0	911.8	911.6
160°	927.8	927.8	927.8	927.9	928.3	928.6	929.0	929.3	929.0	928.6	928.3
162.5°	942.6	942.5	942.3	942.5	943.0	943.5	944.0	944.4	944.0	943.5	943.0
165°	961.7	961.7	961.7	961.9	962.5	963.0	963.5	964.0	963.5	963.0	962.5
167.5°	976.8	976.7	976.6	976.8	977.5	978.3	979.0	979.7	979.0	978.3	977.5
170°	985.3	985.3	985.3	985.7	986.4	987.1	987.8	988.6	987.8	987.1	986.4
172.5°	992.3	992.3	992.3	992.7	993.4	994.1	994.8	995.4	994.8	994.1	993.4
175°	999.6	999.6	999.6	1000.0	1000.7	1001.4	1002.0	1002.7	1002.0	1001.4	1000.7
177.5°	1003.2	1003.2	1003.2	1003.5	1004.0	1004.6	1005.2	1005.7	1005.2	1004.6	1004.0
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	540.2	537.8	536.0	532.3	529.9	527.3	524.6	526.2	526.0	525.9	525.9
5°	522.1	516.6	511.7	505.3	501.4	496.4	492.7	492.2	493.1	489.9	488.0
7.5°	504.1	496.8	489.7	482.7	475.2	469.3	465.6	463.8	461.5	459.5	457.4
10°	491.5	482.8	475.9	467.3	459.3	452.2	447.8	444.6	443.0	441.4	438.3
12.5°	478.5	470.0	461.3	451.4	443.8	435.7	432.3	428.9	425.8	423.8	419.7
15°	459.5	448.5	439.3	428.9	420.4	412.4	407.8	400.9	400.0	397.6	393.3
17.5°	440.4	428.5	415.8	408.1	398.6	390.2	383.0	380.8	374.1	371.5	367.8
20°	425.4	414.3	404.7	394.6	380.7	372.9	367.3	364.3	358.8	355.5	353.1
22.5°	412.4	401.1	390.0	378.2	366.8	358.0	353.9	349.1	346.2	341.5	339.0
25°	393.8	381.6	368.2	355.5	347.3	340.7	334.1	329.8	325.6	323.5	318.8
27.5°	372.3	359.5	347.0	337.3	327.2	320.7	314.8	311.0	305.9	302.4	299.7
30°	360.4	345.4	334.6	325.9	313.0	306.8	302.4	297.6	293.9	290.1	287.5
32.5°	346.7	333.0	322.8	311.9	302.1	295.3	289.5	285.4	282.2	278.6	276.0
35°	325.2	313.7	303.1	292.3	284.9	278.1	271.2	267.7	264.7	261.4	259.0
37.5°	305.7	294.9	284.8	274.6	265.5	259.9	254.5	251.8	247.6	245.4	243.1
40°	293.7	283.1	272.3	262.4	253.0	248.7	243.8	239.7	236.0	234.3	231.8
42.5°	280.4	269.8	260.7	250.1	242.4	236.6	232.1	227.7	224.9	222.5	221.1
45°	260.9	251.6	242.6	232.0	224.7	219.7	214.6	210.6	208.0	206.3	203.8
47.5°	242.0	232.6	223.5	214.3	207.2	201.6	196.3	193.6	190.2	188.1	186.4
50°	228.2	219.7	210.2	201.7	194.6	188.9	184.7	181.2	178.1	175.5	174.3
52.5°	215.6	206.6	198.2	190.4	182.9	176.5	172.7	169.0	166.6	163.7	162.3
55°	194.8	186.1	179.0	171.3	164.0	158.5	153.9	150.6	148.2	144.9	143.1
57.5°	175.3	167.4	159.1	152.3	144.8	140.3	136.3	131.9	129.0	126.4	124.5
60°	162.1	153.2	145.8	139.6	132.9	127.0	123.5	120.0	116.9	114.3	112.7
62.5°	148.3	140.6	133.6	126.7	120.7	115.5	111.5	108.6	105.8	104.2	102.5
65°	127.2	121.2	114.1	108.5	102.8	99.1	95.7	93.2	91.3	90.1	88.7
67.5°	107.9	102.0	95.8	90.3	86.4	83.6	81.5	79.3	78.3	76.7	75.8
70°	95.3	89.2	83.7	79.5	75.7	73.6	72.2	70.6	69.7	67.8	66.9
72.5°	81.6	77.2	73.2	69.8	66.8	64.8	63.0	61.0	59.5	57.4	56.5
75°	64.2	60.2	57.2	54.8	52.9	50.4	47.8	45.6	44.9	44.2	44.0
77.5°	47.6	45.0	42.8	40.8	38.5	36.7	36.1	35.5	35.4	35.0	35.0
80°	37.4	35.0	33.4	31.1	29.7	29.7	29.7	29.2	29.4	29.4	29.4
82.5°	27.8	25.7	24.7	23.9	23.6	23.8	23.8	23.9	23.7	24.1	23.9
85°	14.3	14.5	15.0	14.8	15.0	15.0	15.6	15.2	15.6	15.0	15.6
87.5°	6.9	7.8	8.5	9.1	9.7	10.0	10.3	10.5	10.8	10.9	11.0
90°	7.8	9.8	12.1	14.3	16.7	19.0	19.7	20.4	21.0	21.7	22.3
92.5°	23.8	25.1	26.5	27.8	29.0	30.3	30.9	31.4	32.0	32.5	32.7
95°	51.5	52.8	54.2	55.6	57.1	58.5	59.2	59.8	60.5	61.2	61.6
97.5°	86.4	87.4	88.4	89.4	90.4	91.4	92.2	93.0	93.8	94.6	95.0
100°	111.6	112.6	113.4	114.3	115.2	116.0	116.6	117.1	117.6	118.2	118.7
102.5°	138.4	139.3	140.4	141.6	142.7	143.9	144.4	144.9	145.4	145.9	146.2
105°	179.0	180.1	181.6	183.2	184.8	186.3	186.3	186.3	186.3	186.3	186.5
107.5°	227.1	227.5	228.2	228.8	229.4	230.0	230.7	231.2	231.8	232.4	232.5
110°	258.0	258.3	258.7	259.0	259.4	259.7	260.4	261.2	261.9	262.6	262.8



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	289.0	289.1	289.2	289.3	289.4	289.4	290.3	291.1	292.0	292.9	293.2
115°	337.7	337.8	337.4	337.1	336.7	336.4	336.5	336.7	336.9	337.1	337.1
117.5°	384.7	384.6	384.2	383.6	383.2	382.7	382.7	382.7	382.6	382.6	382.3
120°	417.2	417.3	416.4	415.5	414.7	413.7	413.5	413.3	413.2	413.0	412.7
122.5°	447.0	447.2	446.7	446.3	445.8	445.4	444.8	444.4	443.9	443.5	443.0
125°	493.2	493.3	492.9	492.6	492.2	491.9	491.2	490.5	489.8	489.1	488.4
127.5°	539.2	539.6	539.2	538.8	538.4	538.0	537.0	536.0	535.0	534.1	533.2
130°	569.4	569.8	569.3	568.8	568.3	567.6	566.9	566.3	565.6	564.9	563.9
132.5°	598.4	599.0	598.5	598.1	597.7	597.3	596.5	595.7	594.8	594.0	593.1
135°	641.4	641.9	641.7	641.5	641.3	641.2	640.5	639.7	639.0	638.3	637.8
137.5°	681.8	682.4	682.9	683.3	683.8	684.2	683.5	682.8	682.1	681.3	680.5
140°	710.1	710.6	710.8	711.0	711.2	711.3	711.2	711.0	710.8	710.6	710.0
142.5°	736.1	736.7	737.0	737.3	737.6	737.9	737.7	737.6	737.4	737.2	736.7
145°	774.4	774.8	775.4	775.9	776.4	776.9	776.8	776.6	776.4	776.2	775.8
147.5°	810.9	811.4	811.9	812.4	812.9	813.4	813.4	813.4	813.4	813.4	812.8
150°	834.4	834.8	835.1	835.5	835.8	836.2	836.2	836.2	836.2	836.2	835.7
152.5°	855.2	855.6	855.8	856.0	856.2	856.4	856.7	856.9	857.2	857.5	857.2
155°	885.0	885.1	885.3	885.6	885.8	885.9	886.6	887.3	888.0	888.7	888.4
157.5°	911.4	911.4	911.5	911.7	911.8	911.9	912.7	913.4	914.1	914.8	914.7
160°	927.9	927.8	927.8	927.8	927.8	927.8	928.6	929.5	930.4	931.2	931.3
162.5°	942.5	942.3	942.5	942.6	942.7	942.9	943.7	944.6	945.5	946.4	946.2
165°	961.9	961.7	961.7	961.7	961.7	961.7	962.7	963.8	964.8	965.9	965.8
167.5°	976.8	976.6	976.7	976.8	977.0	977.1	978.3	979.4	980.4	981.5	981.5
170°	985.7	985.3	985.3	985.3	985.3	985.3	986.6	987.8	989.1	990.3	990.3
172.5°	992.7	992.3	992.3	992.3	992.3	992.3	993.4	994.5	995.6	996.6	996.6
175°	1000.0	999.6	999.6	999.6	999.6	999.6	1000.7	1001.7	1002.7	1003.8	1003.7
177.5°	1003.5	1003.2	1003.2	1003.2	1003.2	1003.2	1004.0	1004.9	1005.7	1006.5	1006.5
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	523.6	523.4	523.6	522.9	523.6	523.4	523.6	525.9	525.9	526.0	526.2
5°	487.3	487.1	486.4	484.2	486.4	487.1	487.3	488.0	489.9	493.1	492.2
7.5°	455.4	455.1	453.1	453.1	453.1	455.1	455.4	457.4	459.5	461.5	463.8
10°	436.7	436.9	434.0	432.4	434.0	436.9	436.7	438.3	441.4	443.0	444.6
12.5°	418.4	417.4	415.1	413.2	415.1	417.4	418.4	419.7	423.8	425.8	428.9
15°	394.4	391.9	386.4	386.8	386.4	391.9	394.4	393.3	397.6	400.0	400.9
17.5°	366.0	364.3	364.2	360.8	364.2	364.3	366.0	367.8	371.5	374.1	380.8
20°	349.4	348.2	348.7	345.4	348.7	348.2	349.4	353.1	355.5	358.8	364.3
22.5°	336.4	335.2	333.3	332.2	333.3	335.2	336.4	339.0	341.5	346.2	349.1
25°	317.4	315.5	313.7	314.8	313.7	315.5	317.4	318.8	323.5	325.6	329.8
27.5°	298.4	297.0	295.1	294.9	295.1	297.0	298.4	299.7	302.4	305.9	311.0
30°	286.3	284.9	284.0	282.8	284.0	284.9	286.3	287.5	290.1	293.9	297.6
32.5°	274.1	273.8	272.2	271.9	272.2	273.8	274.1	276.0	278.6	282.2	285.4
35°	258.1	256.7	256.2	256.4	256.2	256.7	258.1	259.0	261.4	264.7	267.7
37.5°	242.9	241.1	240.1	239.3	240.1	241.1	242.9	243.1	245.4	247.6	251.8
40°	232.0	230.1	229.6	229.1	229.6	230.1	232.0	231.8	234.3	236.0	239.7
42.5°	219.7	219.0	218.7	217.8	218.7	219.0	219.7	221.1	222.5	224.9	227.7
45°	203.1	202.8	201.4	201.9	201.4	202.8	203.1	203.8	206.3	208.0	210.6
47.5°	185.4	184.4	183.4	184.1	183.4	184.4	185.4	186.4	188.1	190.2	193.6
50°	173.4	172.9	170.8	171.3	170.8	172.9	173.4	174.3	175.5	178.1	181.2
52.5°	161.4	159.6	158.8	158.4	158.8	159.6	161.4	162.3	163.7	166.6	169.0
55°	141.4	139.3	138.4	137.8	138.4	139.3	141.4	143.1	144.9	148.2	150.6
57.5°	121.8	121.3	120.5	121.0	120.5	121.3	121.8	124.5	126.4	129.0	131.9
60°	110.4	110.4	110.4	110.1	110.4	110.4	110.4	112.7	114.3	116.9	120.0
62.5°	101.5	100.9	100.8	101.1	100.8	100.9	101.5	102.5	104.2	105.8	108.6
65°	88.0	87.8	86.8	86.5	86.8	87.8	88.0	88.7	90.1	91.3	93.2
67.5°	75.2	74.4	74.1	73.8	74.1	74.4	75.2	75.8	76.7	78.3	79.3
70°	65.6	65.1	63.7	64.0	63.7	65.1	65.6	66.9	67.8	69.7	70.6
72.5°	55.3	54.8	54.5	54.2	54.5	54.8	55.3	56.5	57.4	59.5	61.0
75°	43.7	43.5	43.3	44.2	43.3	43.5	43.7	44.0	44.2	44.9	45.6
77.5°	35.0	35.0	35.2	34.8	35.2	35.0	35.0	35.0	35.0	35.4	35.5
80°	29.4	29.4	29.2	29.2	29.2	29.4	29.4	29.4	29.4	29.4	29.2
82.5°	23.5	23.7	23.9	23.5	23.9	23.7	23.5	23.9	24.1	23.7	23.9
85°	15.6	15.2	15.8	15.6	15.8	15.2	15.6	15.6	15.0	15.6	15.2
87.5°	11.5	11.2	11.2	11.5	11.2	11.2	11.5	11.0	10.9	10.8	10.5
90°	22.6	23.0	23.3	23.7	23.3	23.0	22.6	22.3	21.7	21.0	20.4
92.5°	32.5	32.3	32.1	31.9	32.1	32.3	32.5	32.7	32.5	32.0	31.4
95°	61.6	61.6	61.6	61.6	61.6	61.6	61.6	61.6	61.2	60.5	59.8
97.5°	94.9	94.9	94.8	94.7	94.8	94.9	94.9	95.0	94.6	93.8	93.0
100°	119.0	119.3	119.7	120.0	119.7	119.3	119.0	118.7	118.2	117.6	117.1
102.5°	146.1	146.0	146.0	145.9	146.0	146.0	146.1	146.2	145.9	145.4	144.9
105°	186.8	187.2	187.5	187.9	187.5	187.2	186.8	186.5	186.3	186.3	186.3
107.5°	232.3	232.1	231.9	231.7	231.9	232.1	232.3	232.5	232.4	231.8	231.2
110°	262.4	262.1	261.7	261.4	261.7	262.1	262.4	262.8	262.6	261.9	261.2



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	293.2	293.1	293.0	293.0	293.0	293.1	293.2	293.2	292.9	292.0	291.1
115°	336.9	336.7	336.5	336.4	336.5	336.7	336.9	337.1	337.1	336.9	336.7
117.5°	381.9	381.4	380.9	380.4	380.9	381.4	381.9	382.3	382.6	382.6	382.7
120°	412.4	412.0	411.7	411.3	411.7	412.0	412.4	412.7	413.0	413.2	413.3
122.5°	442.5	442.0	441.5	441.0	441.5	442.0	442.5	443.0	443.5	443.9	444.4
125°	487.7	487.0	486.3	485.5	486.3	487.0	487.7	488.4	489.1	489.8	490.5
127.5°	532.4	531.6	530.8	530.0	530.8	531.6	532.4	533.2	534.1	535.0	536.0
130°	562.7	561.5	560.3	559.0	560.3	561.5	562.7	563.9	564.9	565.6	566.3
132.5°	592.2	591.2	590.3	589.4	590.3	591.2	592.2	593.1	594.0	594.8	595.7
135°	637.4	637.1	636.7	636.4	636.7	637.1	637.4	637.8	638.3	639.0	639.7
137.5°	679.9	679.2	678.6	677.9	678.6	679.2	679.9	680.5	681.3	682.1	682.8
140°	708.7	707.5	706.3	705.1	706.3	707.5	708.7	710.0	710.6	710.8	711.0
142.5°	735.7	734.8	733.8	732.9	733.8	734.8	735.7	736.7	737.2	737.4	737.6
145°	775.1	774.4	773.7	773.0	773.7	774.4	775.1	775.8	776.2	776.4	776.6
147.5°	811.8	810.7	809.7	808.7	809.7	810.7	811.8	812.8	813.4	813.4	813.4
150°	834.6	833.5	832.4	831.4	832.4	833.5	834.6	835.7	836.2	836.2	836.2
152.5°	856.3	855.4	854.4	853.5	854.4	855.4	856.3	857.2	857.5	857.2	856.9
155°	887.2	886.0	884.7	883.5	884.7	886.0	887.2	888.4	888.7	888.0	887.3
157.5°	913.8	912.8	911.8	910.8	911.8	912.8	913.8	914.7	914.8	914.1	913.4
160°	930.6	929.9	929.2	928.5	929.2	929.9	930.6	931.3	931.2	930.4	929.5
162.5°	945.1	944.0	942.9	941.8	942.9	944.0	945.1	946.2	946.4	945.5	944.6
165°	964.6	963.3	962.1	960.9	962.1	963.3	964.6	965.8	965.9	964.8	963.8
167.5°	980.4	979.4	978.3	977.1	978.3	979.4	980.4	981.5	981.5	980.4	979.4
170°	989.1	987.8	986.6	985.3	986.6	987.8	989.1	990.3	990.3	989.1	987.8
172.5°	995.3	994.1	992.9	991.7	992.9	994.1	995.3	996.6	996.6	995.6	994.5
175°	1002.5	1001.3	1000.0	998.8	1000.0	1001.3	1002.5	1003.7	1003.8	1002.7	1001.7
177.5°	1005.5	1004.5	1003.6	1002.6	1003.6	1004.5	1005.5	1006.5	1006.5	1005.7	1004.9
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	524.6	527.3	529.9	532.3	536.0	537.8	540.2	541.2	543.9	548.1	551.5
5°	492.7	496.4	501.4	505.3	511.7	516.6	522.1	527.3	533.4	542.1	549.9
7.5°	465.6	469.3	475.2	482.7	489.7	496.8	504.1	511.2	519.9	532.4	544.7
10°	447.8	452.2	459.3	467.3	475.9	482.8	491.5	500.4	511.3	525.6	540.5
12.5°	432.3	435.7	443.8	451.4	461.3	470.0	478.5	489.0	501.3	516.5	534.4
15°	407.8	412.4	420.4	428.9	439.3	448.5	459.5	472.2	484.2	503.0	524.6
17.5°	383.0	390.2	398.6	408.1	415.8	428.5	440.4	453.4	468.3	488.2	512.0
20°	367.3	372.9	380.7	394.6	404.7	414.3	425.4	441.6	455.2	477.9	502.5
22.5°	353.9	358.0	366.8	378.2	390.0	401.1	412.4	427.9	444.7	466.2	492.9
25°	334.1	340.7	347.3	355.5	368.2	381.6	393.8	407.1	425.0	447.8	476.7
27.5°	314.8	320.7	327.2	337.3	347.0	359.5	372.3	387.4	406.6	430.7	460.1
30°	302.4	306.8	313.0	325.9	334.6	345.4	360.4	373.9	391.7	417.4	448.5
32.5°	289.5	295.3	302.1	311.9	322.8	333.0	346.7	361.2	379.5	404.8	436.6
35°	271.2	278.1	284.9	292.3	303.1	313.7	325.2	341.1	359.7	384.3	415.5
37.5°	254.5	259.9	265.5	274.6	284.8	294.9	305.7	321.4	338.9	365.4	394.0
40°	243.8	248.7	253.0	262.4	272.3	283.1	293.7	307.5	326.3	351.0	378.8
42.5°	232.1	236.6	242.4	250.1	260.7	269.8	280.4	293.6	311.2	336.4	360.7
45°	214.6	219.7	224.7	232.0	242.6	251.6	260.9	273.4	291.5	312.3	333.9
47.5°	196.3	201.6	207.2	214.3	223.5	232.6	242.0	253.0	269.5	289.8	304.5
50°	184.7	188.9	194.6	201.7	210.2	219.7	228.2	240.2	256.0	272.0	284.7
52.5°	172.7	176.5	182.9	190.4	198.2	206.6	215.6	225.9	240.1	255.2	265.3
55°	153.9	158.5	164.0	171.3	179.0	186.1	194.8	205.4	216.7	228.0	234.8
57.5°	136.3	140.3	144.8	152.3	159.1	167.4	175.3	183.5	194.0	202.5	206.9
60°	123.5	127.0	132.9	139.6	145.8	153.2	162.1	170.4	178.3	185.2	188.6
62.5°	111.5	115.5	120.7	126.7	133.6	140.6	148.3	155.3	162.4	168.2	170.7
65°	95.7	99.1	102.8	108.5	114.1	121.2	127.2	134.3	139.6	142.8	144.9
67.5°	81.5	83.6	86.4	90.3	95.8	102.0	107.9	113.4	117.8	120.0	121.9
70°	72.2	73.6	75.7	79.5	83.7	89.2	95.3	99.3	103.0	104.9	106.8
72.5°	63.0	64.8	66.8	69.8	73.2	77.2	81.6	86.4	88.6	90.8	91.9
75°	47.8	50.4	52.9	54.8	57.2	60.2	64.2	67.3	68.5	70.4	70.6
77.5°	36.1	36.7	38.5	40.8	42.8	45.0	47.6	50.3	50.9	51.8	52.5
80°	29.7	29.7	29.7	31.1	33.4	35.0	37.4	38.8	39.8	40.0	40.2
82.5°	23.8	23.8	23.6	23.9	24.7	25.7	27.8	29.4	30.2	30.0	29.5
85°	15.6	15.0	15.0	14.8	15.0	14.5	14.3	15.2	16.7	16.7	16.3
87.5°	10.3	10.0	9.7	9.1	8.5	7.8	6.9	6.7	6.4	6.8	6.2
90°	19.7	19.0	16.7	14.3	12.1	9.8	7.8	6.1	4.3	2.5	0.8
92.5°	30.9	30.3	29.0	27.8	26.5	25.1	23.8	22.7	21.5	20.3	19.1
95°	59.2	58.5	57.1	55.6	54.2	52.8	51.5	50.3	49.1	47.8	46.6
97.5°	92.2	91.4	90.4	89.4	88.4	87.4	86.4	85.4	84.5	83.6	82.7
100°	116.6	116.0	115.2	114.3	113.4	112.6	111.6	110.6	109.5	108.5	107.3
102.5°	144.4	143.9	142.7	141.6	140.4	139.3	138.4	137.7	137.0	136.4	135.8
105°	186.3	186.3	184.8	183.2	181.6	180.1	179.0	178.7	178.3	178.0	177.6
107.5°	230.7	230.0	229.4	228.8	228.2	227.5	227.1	226.9	226.7	226.5	226.3
110°	260.4	259.7	259.4	259.0	258.7	258.3	258.0	257.6	257.3	256.9	256.6



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	290.3	289.4	289.4	289.3	289.2	289.1	289.0	288.8	288.6	288.4	288.2
115°	336.5	336.4	336.7	337.1	337.4	337.8	337.7	337.1	336.6	336.1	335.6
117.5°	382.7	382.7	383.2	383.6	384.2	384.6	384.7	384.3	384.0	383.6	383.2
120°	413.5	413.7	414.7	415.5	416.4	417.3	417.2	416.1	415.1	413.9	412.9
122.5°	444.8	445.4	445.8	446.3	446.7	447.2	447.0	446.2	445.5	444.6	443.9
125°	491.2	491.9	492.2	492.6	492.9	493.3	493.2	492.7	492.1	491.6	491.1
127.5°	537.0	538.0	538.4	538.8	539.2	539.6	539.2	538.1	536.9	535.8	534.7
130°	566.9	567.6	568.3	568.8	569.3	569.8	569.4	567.9	566.5	565.1	563.7
132.5°	596.5	597.3	597.7	598.1	598.5	599.0	598.4	597.0	595.6	594.2	592.8
135°	640.5	641.2	641.3	641.5	641.7	641.9	641.4	640.4	639.2	638.2	637.1
137.5°	683.5	684.2	683.8	683.3	682.9	682.4	681.8	680.9	679.9	679.1	678.2
140°	711.2	711.3	711.2	711.0	710.8	710.6	710.1	709.3	708.4	707.5	706.6
142.5°	737.7	737.9	737.6	737.3	737.0	736.7	736.1	735.2	734.3	733.5	732.6
145°	776.8	776.9	776.4	775.9	775.4	774.8	774.4	774.1	773.7	773.4	773.0
147.5°	813.4	813.4	812.9	812.4	811.9	811.4	810.9	810.2	809.6	809.0	808.4
150°	836.2	836.2	835.8	835.5	835.1	834.8	834.4	834.0	833.6	833.3	832.9
152.5°	856.7	856.4	856.2	856.0	855.8	855.6	855.2	854.6	854.1	853.6	853.2
155°	886.6	885.9	885.8	885.6	885.3	885.1	885.0	885.0	885.0	885.0	885.0
157.5°	912.7	911.9	911.8	911.7	911.5	911.4	911.4	911.6	911.8	912.0	912.2
160°	928.6	927.8	927.8	927.8	927.8	927.8	927.9	928.3	928.6	929.0	929.3
162.5°	943.7	942.9	942.7	942.6	942.5	942.3	942.5	943.0	943.5	944.0	944.4
165°	962.7	961.7	961.7	961.7	961.7	961.7	961.9	962.5	963.0	963.5	964.0
167.5°	978.3	977.1	977.0	976.8	976.7	976.6	976.8	977.5	978.3	979.0	979.7
170°	986.6	985.3	985.3	985.3	985.3	985.3	985.7	986.4	987.1	987.8	988.6
172.5°	993.4	992.3	992.3	992.3	992.3	992.3	992.7	993.4	994.1	994.8	995.4
175°	1000.7	999.6	999.6	999.6	999.6	999.6	1000.0	1000.7	1001.4	1002.0	1002.7
177.5°	1004.0	1003.2	1003.2	1003.2	1003.2	1003.2	1003.5	1004.0	1004.6	1005.2	1005.7
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	552.6	554.7	557.3	561.3	564.3	566.9	567.4	568.3	570.2	573.3	575.7
5°	556.2	561.6	570.3	578.8	587.9	595.5	602.6	607.5	612.2	622.1	630.1
7.5°	555.0	567.1	580.8	595.9	611.4	626.2	640.1	652.5	664.8	679.2	695.6
10°	554.3	568.5	586.8	606.3	627.7	648.6	668.9	684.7	703.0	719.5	740.4
12.5°	550.8	571.1	593.0	617.9	644.3	668.4	695.1	716.8	737.8	761.6	786.0
15°	546.0	570.8	598.5	631.7	671.8	700.8	728.2	766.1	791.9	817.8	852.6
17.5°	537.6	567.7	602.4	645.5	678.8	718.1	759.1	789.1	823.9	860.4	891.9
20°	530.8	565.8	604.7	647.0	689.6	732.2	771.9	807.7	843.7	885.9	911.7
22.5°	524.0	558.7	599.1	644.0	689.7	734.7	779.6	821.6	862.1	904.6	937.7
25°	509.6	550.8	594.5	640.5	685.6	735.0	788.6	835.5	885.6	929.4	960.7
27.5°	495.0	532.8	576.3	622.9	673.1	731.4	794.6	847.8	898.0	929.4	939.2
30°	481.8	521.8	561.9	609.2	663.5	728.6	795.7	856.7	897.8	911.5	901.3
32.5°	468.5	504.7	544.3	592.8	650.5	721.6	797.2	851.4	876.2	865.8	824.6
35°	444.9	477.6	515.9	564.4	630.8	717.8	791.0	827.7	821.6	762.8	685.1
37.5°	419.7	446.4	481.8	532.5	610.4	702.6	764.3	769.7	716.7	626.4	536.7
40°	399.7	423.7	460.2	513.1	594.5	687.5	737.4	715.5	633.4	532.9	458.1
42.5°	380.3	400.6	435.8	492.8	579.5	666.9	697.3	649.6	554.9	459.9	391.8
45°	347.5	366.6	401.8	460.4	548.7	627.7	623.7	540.9	446.1	369.6	313.2
47.5°	316.4	333.1	366.2	426.0	512.5	568.9	531.5	443.3	362.9	301.5	261.3
50°	294.4	310.8	343.8	402.8	483.5	524.6	471.3	386.4	312.7	261.9	229.8
52.5°	273.3	289.3	319.4	377.0	448.5	473.1	415.8	337.0	275.6	231.8	204.3
55°	243.8	256.0	283.1	338.1	391.5	397.2	339.0	273.2	222.6	192.0	173.2
57.5°	213.7	224.2	251.0	294.8	332.2	329.3	274.3	217.2	183.2	160.5	146.8
60°	194.1	204.5	228.0	265.6	293.9	284.0	233.4	187.5	158.3	141.7	130.8
62.5°	175.8	183.9	206.0	233.5	253.8	242.6	199.5	161.6	138.4	124.3	115.7
65°	149.4	156.0	173.6	188.0	199.2	188.4	152.7	126.3	109.7	99.8	93.9
67.5°	124.3	128.5	139.6	144.8	152.8	140.9	114.8	97.1	87.7	79.4	75.2
70°	108.5	111.5	117.4	121.7	123.7	111.5	92.2	79.3	71.3	65.4	62.8
72.5°	92.6	95.3	96.5	100.0	98.9	87.5	74.1	63.8	58.1	54.1	50.8
75°	70.8	72.0	70.8	69.4	66.3	58.4	49.2	44.0	39.8	37.9	36.7
77.5°	51.6	51.2	49.7	47.5	42.2	37.2	32.2	30.5	28.7	27.7	27.3
80°	39.8	38.8	37.4	33.8	29.4	25.9	24.7	23.5	22.8	21.6	21.4
82.5°	29.6	29.0	26.7	23.7	20.6	18.9	18.0	17.5	16.8	16.2	16.2
85°	15.8	15.0	12.4	10.8	10.4	9.9	9.7	9.7	8.7	8.5	8.5
87.5°	5.6	4.8	4.9	4.7	5.2	5.3	5.9	6.0	6.3	6.6	6.4
90°	2.5	4.3	6.1	7.8	9.8	12.1	14.3	16.7	19.0	19.7	20.4
92.5°	20.3	21.5	22.7	23.8	25.1	26.5	27.8	29.0	30.3	30.9	31.4
95°	47.8	49.1	50.3	51.5	52.8	54.2	55.6	57.1	58.5	59.2	59.8
97.5°	83.6	84.5	85.4	86.4	87.4	88.4	89.4	90.4	91.4	92.2	93.0
100°	108.5	109.5	110.6	111.6	112.6	113.4	114.3	115.2	116.0	116.6	117.1
102.5°	136.4	137.0	137.7	138.4	139.3	140.4	141.6	142.7	143.9	144.4	144.9
105°	178.0	178.3	178.7	179.0	180.1	181.6	183.2	184.8	186.3	186.3	186.3
107.5°	226.5	226.7	226.9	227.1	227.5	228.2	228.8	229.4	230.0	230.7	231.2
110°	256.9	257.3	257.6	258.0	258.3	258.7	259.0	259.4	259.7	260.4	261.2



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	288.4	288.6	288.8	289.0	289.1	289.2	289.3	289.4	289.4	290.3	291.1
115°	336.1	336.6	337.1	337.7	337.8	337.4	337.1	336.7	336.4	336.5	336.7
117.5°	383.6	384.0	384.3	384.7	384.6	384.2	383.6	383.2	382.7	382.7	382.7
120°	413.9	415.1	416.1	417.2	417.3	416.4	415.5	414.7	413.7	413.5	413.3
122.5°	444.6	445.5	446.2	447.0	447.2	446.7	446.3	445.8	445.4	444.8	444.4
125°	491.6	492.1	492.7	493.2	493.3	492.9	492.6	492.2	491.9	491.2	490.5
127.5°	535.8	536.9	538.1	539.2	539.6	539.2	538.8	538.4	538.0	537.0	536.0
130°	565.1	566.5	567.9	569.4	569.8	569.3	568.8	568.3	567.6	566.9	566.3
132.5°	594.2	595.6	597.0	598.4	599.0	598.5	598.1	597.7	597.3	596.5	595.7
135°	638.2	639.2	640.4	641.4	641.9	641.7	641.5	641.3	641.2	640.5	639.7
137.5°	679.1	679.9	680.9	681.8	682.4	682.9	683.3	683.8	684.2	683.5	682.8
140°	707.5	708.4	709.3	710.1	710.6	710.8	711.0	711.2	711.3	711.2	711.0
142.5°	733.5	734.3	735.2	736.1	736.7	737.0	737.3	737.6	737.9	737.7	737.6
145°	773.4	773.7	774.1	774.4	774.8	775.4	775.9	776.4	776.9	776.8	776.6
147.5°	809.0	809.6	810.2	810.9	811.4	811.9	812.4	812.9	813.4	813.4	813.4
150°	833.3	833.6	834.0	834.4	834.8	835.1	835.5	835.8	836.2	836.2	836.2
152.5°	853.6	854.1	854.6	855.2	855.6	855.8	856.0	856.2	856.4	856.7	856.9
155°	885.0	885.0	885.0	885.0	885.1	885.3	885.6	885.8	885.9	886.6	887.3
157.5°	912.0	911.8	911.6	911.4	911.4	911.5	911.7	911.8	911.9	912.7	913.4
160°	929.0	928.6	928.3	927.9	927.8	927.8	927.8	927.8	927.8	928.6	929.5
162.5°	944.0	943.5	943.0	942.5	942.3	942.5	942.6	942.7	942.9	943.7	944.6
165°	963.5	963.0	962.5	961.9	961.7	961.7	961.7	961.7	961.7	962.7	963.8
167.5°	979.0	978.3	977.5	976.8	976.6	976.7	976.8	977.0	977.1	978.3	979.4
170°	987.8	987.1	986.4	985.7	985.3	985.3	985.3	985.3	985.3	986.6	987.8
172.5°	994.8	994.1	993.4	992.7	992.3	992.3	992.3	992.3	992.3	993.4	994.5
175°	1002.0	1001.4	1000.7	1000.0	999.6	999.6	999.6	999.6	999.6	1000.7	1001.7
177.5°	1005.2	1004.6	1004.0	1003.5	1003.2	1003.2	1003.2	1003.2	1003.2	1004.0	1004.9
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	579.8	579.8	580.5	583.3	583.7	586.1	585.4
5°	637.1	641.6	643.3	650.4	654.5	656.4	652.7
7.5°	707.3	719.9	725.9	733.4	739.8	741.8	736.7
10°	758.5	771.7	782.7	789.6	796.0	800.2	805.6
12.5°	808.0	824.3	834.8	844.3	850.9	856.3	857.2
15°	861.8	886.3	904.8	918.6	925.3	928.9	927.5
17.5°	916.0	938.8	952.0	965.9	975.3	975.8	976.1
20°	946.7	968.9	984.2	994.5	1005.1	1004.6	1007.0
22.5°	967.2	984.7	996.4	1003.9	1007.5	1005.7	1006.2
25°	976.8	982.1	980.0	968.0	964.8	953.8	955.7
27.5°	927.4	902.9	877.6	845.1	819.3	798.8	799.8
30°	860.2	816.9	767.5	726.1	688.9	678.5	656.4
32.5°	766.3	701.4	643.5	604.8	573.0	564.3	545.0
35°	607.0	543.9	484.4	448.7	434.5	414.8	414.5
37.5°	471.8	416.3	384.9	358.0	344.0	331.9	330.8
40°	396.9	353.7	329.8	310.5	296.7	287.7	285.6
42.5°	344.6	309.6	287.3	275.4	264.7	260.0	256.6
45°	281.3	257.8	242.4	231.6	226.6	223.1	221.2
47.5°	235.4	219.6	209.0	201.8	197.8	194.1	195.1
50°	210.4	197.4	189.7	182.8	179.8	177.1	177.4
52.5°	190.2	178.5	172.3	167.3	163.6	161.7	160.9
55°	161.4	154.1	147.7	144.2	142.1	139.6	138.9
57.5°	137.6	132.0	126.8	122.9	122.3	119.9	120.2
60°	121.9	117.1	112.9	110.8	109.2	107.0	107.8
62.5°	108.9	104.9	101.1	99.4	97.7	96.1	96.4
65°	89.2	85.4	83.0	82.1	81.4	80.7	80.0
67.5°	71.1	68.8	67.3	65.2	63.8	63.6	62.9
70°	59.8	56.7	54.1	51.5	50.8	50.6	50.8
72.5°	47.9	45.9	45.2	44.0	43.8	43.2	43.6
75°	36.0	35.2	34.8	33.8	33.8	33.8	33.8
77.5°	26.6	26.2	25.9	25.7	25.4	25.0	25.0
80°	20.7	20.5	20.0	20.0	19.8	20.0	19.8
82.5°	15.7	15.6	15.1	15.1	14.8	14.7	14.8
85°	8.0	7.8	8.3	7.8	8.0	7.6	8.0
87.5°	6.5	6.6	6.6	6.6	6.5	7.0	6.7
90°	21.0	21.7	22.3	22.6	23.0	23.3	23.7
92.5°	32.0	32.5	32.7	32.5	32.3	32.1	31.9
95°	60.5	61.2	61.6	61.6	61.6	61.6	61.6
97.5°	93.8	94.6	95.0	94.9	94.9	94.8	94.7
100°	117.6	118.2	118.7	119.0	119.3	119.7	120.0
102.5°	145.4	145.9	146.2	146.1	146.0	146.0	145.9
105°	186.3	186.3	186.5	186.8	187.2	187.5	187.9
107.5°	231.8	232.4	232.5	232.3	232.1	231.9	231.7
110°	261.9	262.6	262.8	262.4	262.1	261.7	261.4



TEST NUMBER: P332253-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	292.0	292.9	293.2	293.2	293.1	293.0	293.0
115°	336.9	337.1	337.1	336.9	336.7	336.5	336.4
117.5°	382.6	382.6	382.3	381.9	381.4	380.9	380.4
120°	413.2	413.0	412.7	412.4	412.0	411.7	411.3
122.5°	443.9	443.5	443.0	442.5	442.0	441.5	441.0
125°	489.8	489.1	488.4	487.7	487.0	486.3	485.5
127.5°	535.0	534.1	533.2	532.4	531.6	530.8	530.0
130°	565.6	564.9	563.9	562.7	561.5	560.3	559.0
132.5°	594.8	594.0	593.1	592.2	591.2	590.3	589.4
135°	639.0	638.3	637.8	637.4	637.1	636.7	636.4
137.5°	682.1	681.3	680.5	679.9	679.2	678.6	677.9
140°	710.8	710.6	710.0	708.7	707.5	706.3	705.1
142.5°	737.4	737.2	736.7	735.7	734.8	733.8	732.9
145°	776.4	776.2	775.8	775.1	774.4	773.7	773.0
147.5°	813.4	813.4	812.8	811.8	810.7	809.7	808.7
150°	836.2	836.2	835.7	834.6	833.5	832.4	831.4
152.5°	857.2	857.5	857.2	856.3	855.4	854.4	853.5
155°	888.0	888.7	888.4	887.2	886.0	884.7	883.5
157.5°	914.1	914.8	914.7	913.8	912.8	911.8	910.8
160°	930.4	931.2	931.3	930.6	929.9	929.2	928.5
162.5°	945.5	946.4	946.2	945.1	944.0	942.9	941.8
165°	964.8	965.9	965.8	964.6	963.3	962.1	960.9
167.5°	980.4	981.5	981.5	980.4	979.4	978.3	977.1
170°	989.1	990.3	990.3	989.1	987.8	986.6	985.3
172.5°	995.6	996.6	996.6	995.3	994.1	992.9	991.7
175°	1002.7	1003.8	1003.7	1002.5	1001.3	1000.0	998.8
177.5°	1005.7	1006.5	1006.5	1005.5	1004.5	1003.6	1002.6
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1

(END OF REPORT)