

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832150

Luminaire Tested: S123RDIP-S340D805U840-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832150
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U840-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4274.5 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 33
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832150

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P832150

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				
1	95	91	87	84	86	82	79	77	66	64	62	52	50	49	38	37	37	30				
2	87	80	74	70	78	73	68	64	59	55	53	46	44	42	34	33	32	26				
3	80	71	64	59	72	64	59	54	52	48	45	41	39	36	31	29	28	23				
4	73	63	56	50	66	58	51	46	47	42	39	37	34	32	28	26	24	20				
5	67	57	49	43	61	52	45	40	42	38	34	34	30	28	26	24	22	18				
6	62	51	43	38	56	47	40	35	38	34	30	31	27	25	24	21	20	16				
7	58	46	39	33	52	42	36	31	35	30	27	28	25	22	22	19	18	15				
8	54	42	35	30	49	39	32	28	32	27	24	26	22	20	20	18	16	14				
9	50	38	31	27	45	35	29	25	30	25	22	24	21	18	19	16	15	13				
10	47	35	29	24	43	33	27	23	27	23	20	22	19	17	18	15	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	12076	12076	12076	12076	12076
5°	14338	13881	12151	9823	9121
10°	12991	14100	12091	7871	6753
15°	8945	12090	11964	6433	5341
20°	6222	9308	11724	5424	4694
25°	4742	7094	11374	4821	4327
30°	4128	5671	10936	4477	4007
35°	3790	4784	10318	4185	3717
40°	3458	4272	9507	3901	3451
45°	3124	3908	8634	3631	3186
50°	2835	3605	7603	3366	2858
55°	2563	3310	6611	3108	2451
60°	2297	3010	5744	2822	2316
65°	2122	2672	4944	2537	2190
70°	1721	2310	4315	2294	1781
75°	1510	1838	3656	1905	1568
80°	1370	1556	2994	1599	1481
85°	1247	1359	2272	1445	1359

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 9109 cd/sqm



TEST NUMBER: P832150

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	2.4
10°-20°	236.6	5.5
20°-30°	271.5	6.4
30°-40°	267.6	6.3
40°-50°	236.0	5.5
50°-60°	181.6	4.2
60°-70°	119.4	2.8
70°-80°	58.0	1.4
80°-90°	16.7	0.4
90°-100°	64.7	1.5
100°-110°	195.8	4.6
110°-120°	333.4	7.8
120°-130°	438.6	10.3
130°-140°	493.0	11.5
140°-150°	484.7	11.3
150°-160°	408.0	9.5
160°-170°	271.6	6.4
170°-180°	95.1	2.2
0°-30°	610.4	14.3
0°-40°	878.0	20.5
0°-60°	1295.5	30.3
0°-90°	1489.6	34.8
90°-120°	593.9	13.9
90°-150°	2010.1	47.0
90°-180°	2785.0	65.2
0°-180°	4274.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1122	1122	1122	1122	1122	
5°	1327	1285	1125	909	844	121
15°	803	1085	1074	577	479	227
25°	399	597	958	406	364	189
35°	288	364	785	318	283	180
45°	205	257	567	238	209	159
55°	137	176	352	166	131	123
65°	83	105	194	100	86	82
75°	36	44	88	46	38	39
85°	10	11	18	12	11	11
90°	24	19	1	19	24	12
95°	62	58	47	58	62	62
105°	188	186	178	186	188	199
115°	336	336	336	336	336	333
125°	486	492	491	492	486	434
135°	636	641	637	641	636	490
145°	773	777	773	777	773	483
155°	884	886	885	886	884	407
165°	961	962	964	962	961	271
175°	999	1000	1003	1000	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P832150

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9
2.5°	1243.3	1239.4	1235.5	1234.4	1233.2	1229.5	1225.8	1217.6	1209.3	1200.8	1192.3
5°	1327.0	1327.5	1328.0	1326.8	1325.7	1320.8	1316.0	1305.9	1295.8	1284.7	1273.7
7.5°	1301.3	1308.6	1316.0	1317.4	1318.8	1322.4	1326.1	1323.8	1321.5	1317.4	1313.2
10°	1188.6	1188.1	1187.7	1195.9	1204.2	1228.8	1253.4	1266.1	1278.7	1290.0	1301.3
12.5°	1004.6	1005.3	1006.0	1033.1	1060.3	1083.5	1106.7	1138.9	1171.1	1205.8	1240.6
15°	802.7	813.9	825.2	849.4	873.5	908.5	943.4	986.7	1029.9	1084.9	1139.8
17.5°	659.1	664.0	668.8	692.0	715.3	748.4	781.5	830.5	879.5	950.3	1021.2
20°	543.2	547.6	552.0	568.8	585.6	617.3	649.0	695.7	742.4	812.6	882.7
22.5°	453.5	462.0	470.6	481.8	493.1	516.1	539.1	586.7	634.3	698.2	762.2
25°	399.3	403.2	407.1	416.7	426.4	448.5	470.6	502.1	533.6	597.3	661.0
27.5°	362.5	363.6	364.8	371.9	379.0	393.3	407.5	436.7	466.0	518.4	570.8
30°	332.1	334.2	336.2	341.8	347.3	357.6	368.0	388.7	409.4	456.3	503.2
32.5°	308.6	309.8	310.9	315.5	320.1	327.7	335.3	351.7	368.0	403.9	439.7
35°	288.4	288.6	288.9	292.3	295.8	303.1	310.5	324.1	337.6	364.1	390.5
37.5°	265.4	267.0	268.6	271.2	273.7	280.1	286.6	297.6	308.6	330.5	352.3
40°	246.1	247.5	248.8	251.8	254.8	259.9	264.9	275.1	285.2	304.0	322.9
42.5°	226.8	227.7	228.6	231.6	234.6	240.8	247.0	255.1	263.1	278.7	294.4
45°	205.2	207.5	209.8	213.0	216.2	221.5	226.8	235.0	243.3	256.7	270.0
47.5°	187.2	188.4	189.5	192.3	195.0	201.5	207.9	215.3	222.6	235.0	247.5
50°	169.3	169.7	170.2	172.7	175.3	181.0	186.8	195.3	203.8	215.3	226.8
52.5°	152.3	153.4	154.6	157.1	159.6	163.5	167.4	176.2	184.9	196.2	207.5
55°	136.6	137.3	138.0	139.8	141.7	146.3	150.9	158.5	166.1	176.4	186.8
57.5°	121.9	122.8	123.7	125.1	126.5	130.6	134.8	141.4	148.1	158.5	168.8
60°	106.7	107.9	109.0	110.6	112.2	115.5	118.7	124.7	130.6	139.8	149.0
62.5°	95.7	95.9	96.1	97.5	98.9	101.2	103.5	108.3	113.2	122.4	131.6
65°	83.3	83.9	84.6	85.3	86.0	87.9	89.7	93.8	98.0	104.9	111.8
67.5°	70.4	71.1	71.8	72.9	74.1	75.7	77.3	80.0	82.8	89.2	95.7
70°	54.7	54.7	54.7	56.6	58.4	61.2	63.9	66.0	68.1	73.4	78.7
72.5°	44.6	44.8	45.1	45.3	45.5	47.1	48.8	52.2	55.7	58.9	62.1
75°	36.3	36.6	36.8	37.0	37.3	37.7	38.2	39.3	40.5	44.2	47.8
77.5°	29.0	29.2	29.4	29.7	29.9	30.4	30.8	31.3	31.7	33.1	34.5
80°	22.1	22.3	22.5	22.8	23.0	23.2	23.5	23.9	24.4	25.1	25.8
82.5°	16.1	16.1	16.1	16.1	16.1	16.6	17.0	17.0	17.0	17.5	17.9
85°	10.1	10.1	10.1	10.3	10.6	10.6	10.6	10.8	11.0	11.0	11.0
87.5°	4.6	4.4	4.1	4.4	4.6	4.6	4.6	4.8	5.1	5.1	5.1
90°	23.7	23.3	23.0	22.6	22.3	21.8	21.1	20.4	19.7	18.9	16.7
92.5°	34.0	34.3	34.7	35.0	35.4	35.3	34.7	34.2	33.7	33.2	32.1
95°	61.6	61.6	61.6	61.6	61.6	61.2	60.5	59.8	59.1	58.4	57.0
97.5°	88.4	88.6	88.8	89.0	89.1	88.8	87.9	87.0	86.1	85.3	84.2
100°	120.0	119.7	119.3	119.0	118.6	118.2	117.6	117.1	116.6	116.1	115.2
102.5°	152.4	152.6	152.7	152.9	153.1	152.9	152.4	151.9	151.3	150.8	149.6
105°	187.9	187.6	187.2	186.9	186.5	186.3	186.3	186.3	186.3	186.3	184.8
107.5°	224.2	224.4	224.6	224.8	224.9	224.8	224.2	223.7	223.2	222.7	222.0
110°	261.3	261.7	262.0	262.4	262.7	262.6	261.9	261.2	260.5	259.8	259.4



TEST NUMBER: P832150

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	300.8	300.8	300.8	300.8	300.8	300.4	299.5	298.6	297.8	296.9	296.9
115°	336.4	336.5	336.7	336.9	337.1	337.1	336.9	336.7	336.5	336.4	336.7
117.5°	372.7	373.2	373.7	374.2	374.8	375.0	375.0	375.0	375.0	375.0	375.4
120°	411.4	411.7	412.1	412.4	412.8	413.0	413.2	413.4	413.6	413.7	414.6
122.5°	448.5	449.0	449.5	450.0	450.6	451.1	451.6	452.2	452.7	453.2	453.6
125°	485.6	486.3	487.0	487.7	488.4	489.1	489.8	490.5	491.2	491.9	492.2
127.5°	522.7	523.4	524.1	524.8	525.5	526.4	527.4	528.5	529.5	530.6	530.9
130°	559.0	560.2	561.5	562.7	563.9	564.9	565.6	566.3	567.0	567.7	568.2
132.5°	596.9	597.8	598.7	599.5	600.4	601.3	602.2	603.0	603.9	604.8	605.2
135°	636.4	636.7	637.1	637.4	637.8	638.3	639.0	639.7	640.4	641.1	641.3
137.5°	671.1	671.6	672.2	672.7	673.2	673.9	674.8	675.7	676.6	677.4	676.9
140°	705.1	706.3	707.5	708.8	710.0	710.7	710.9	711.0	711.2	711.4	711.2
142.5°	739.8	740.7	741.6	742.4	743.3	743.8	744.0	744.2	744.4	744.6	744.2
145°	773.0	773.7	774.4	775.1	775.8	776.2	776.4	776.6	776.7	776.9	776.4
147.5°	803.0	804.0	805.1	806.1	807.2	807.7	807.7	807.7	807.7	807.7	807.2
150°	831.4	832.5	833.5	834.6	835.6	836.1	836.1	836.1	836.1	836.1	835.8
152.5°	859.0	859.9	860.8	861.7	862.5	862.8	862.5	862.1	861.8	861.4	861.2
155°	883.5	884.7	886.0	887.2	888.4	888.7	888.0	887.3	886.6	885.9	885.7
157.5°	906.4	907.5	908.5	909.6	910.6	910.8	910.1	909.4	908.7	908.0	907.8
160°	928.5	929.2	929.9	930.6	931.3	931.2	930.4	929.5	928.6	927.7	927.7
162.5°	945.1	946.3	947.6	948.8	950.0	950.2	949.3	948.4	947.6	946.7	946.5
165°	960.9	962.1	963.3	964.6	965.8	965.9	964.8	963.8	962.7	961.7	961.7
167.5°	975.1	976.2	977.2	978.3	979.3	979.3	978.3	977.2	976.2	975.1	974.9
170°	985.4	986.6	987.8	989.1	990.3	990.3	989.1	987.8	986.6	985.4	985.4
172.5°	993.3	994.5	995.7	996.9	998.2	998.3	997.2	996.2	995.1	994.1	994.1
175°	998.8	1000.0	1001.2	1002.5	1003.7	1003.8	1002.7	1001.7	1000.6	999.6	999.6
177.5°	1001.9	1003.2	1004.4	1005.6	1006.9	1006.9	1005.9	1004.8	1003.8	1002.7	1002.7
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P832150

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9
2.5°	1191.1	1190.0	1178.9	1167.9	1157.1	1146.3	1138.2	1130.2	1116.6	1103.0	1094.5
5°	1264.9	1256.2	1238.7	1221.2	1195.0	1168.8	1146.7	1124.6	1096.6	1068.5	1045.1
7.5°	1306.1	1299.0	1277.8	1256.7	1221.9	1187.2	1152.7	1118.2	1076.8	1035.4	1000.0
10°	1307.3	1313.2	1295.8	1278.3	1239.2	1200.1	1153.2	1106.2	1050.6	994.9	949.2
12.5°	1266.3	1292.1	1288.4	1284.7	1244.9	1205.1	1148.1	1091.1	1022.8	954.5	897.2
15°	1189.7	1239.6	1254.4	1269.1	1236.2	1203.3	1138.4	1073.6	993.3	913.1	847.3
17.5°	1091.1	1161.0	1199.9	1238.7	1214.8	1190.9	1119.8	1048.8	958.4	868.0	796.5
20°	974.2	1065.8	1126.7	1187.7	1178.9	1170.2	1096.8	1023.5	925.9	828.4	750.9
22.5°	858.8	955.4	1039.6	1123.7	1132.7	1141.7	1067.6	993.6	886.8	780.1	701.2
25°	759.2	857.4	957.7	1058.0	1078.2	1098.4	1028.1	957.7	847.1	736.4	658.0
27.5°	664.2	757.6	868.0	978.4	1015.2	1052.0	987.6	923.2	808.0	692.7	614.5
30°	586.7	670.2	782.9	895.6	946.9	998.2	939.0	879.9	765.6	651.3	574.7
32.5°	514.5	589.2	702.4	815.5	875.1	934.7	883.6	832.6	722.6	612.7	537.0
35°	457.4	524.4	629.9	735.5	802.2	868.9	827.0	785.2	677.8	570.4	498.8
37.5°	408.5	464.6	563.7	662.8	733.7	804.5	769.5	734.6	633.6	532.7	465.0
40°	368.0	413.1	505.3	597.5	667.0	736.4	706.5	676.6	586.2	495.9	432.6
42.5°	333.3	372.1	454.9	537.7	601.4	665.1	645.4	625.6	543.7	461.8	403.2
45°	302.7	335.3	408.2	481.1	539.8	598.4	582.8	567.2	496.5	425.9	372.1
47.5°	275.5	303.6	368.7	433.8	486.4	539.1	524.6	510.1	451.7	393.3	344.3
50°	250.7	274.6	328.9	383.2	430.5	477.9	466.0	454.0	405.7	357.4	315.1
52.5°	227.2	247.0	295.8	344.5	382.7	420.9	411.7	402.5	365.2	328.0	289.6
55°	204.9	223.1	264.3	305.4	338.1	370.7	361.5	352.3	323.4	294.4	260.6
57.5°	184.7	200.6	233.9	267.2	293.2	319.2	314.9	310.5	286.3	262.2	234.4
60°	163.3	177.6	206.3	235.0	256.0	276.9	271.8	266.8	249.5	232.3	208.4
62.5°	144.2	156.9	179.9	202.9	219.9	236.9	233.2	229.5	216.4	203.3	183.5
65°	124.2	136.6	155.2	173.9	187.2	200.6	197.3	194.1	184.2	174.3	158.5
67.5°	106.0	116.4	132.5	148.6	157.5	166.5	164.7	162.8	155.2	147.7	135.2
70°	87.6	96.6	109.9	123.3	129.5	135.7	136.4	137.1	130.2	123.3	114.1
72.5°	69.2	76.4	88.8	101.2	106.0	110.9	110.6	110.4	106.3	102.1	93.8
75°	53.1	58.4	68.1	77.7	81.9	86.0	86.9	87.9	83.9	80.0	75.4
77.5°	38.2	41.9	49.2	56.6	61.2	65.8	66.2	66.7	64.9	63.0	58.6
80°	26.9	28.1	32.7	37.3	42.1	46.9	47.6	48.3	46.5	44.6	41.9
82.5°	18.6	19.3	20.9	22.5	26.4	30.4	31.3	32.2	31.3	30.4	27.4
85°	11.3	11.5	12.2	12.9	14.7	16.6	17.5	18.4	17.9	17.5	15.9
87.5°	5.1	5.1	5.3	5.5	6.0	6.4	7.6	8.7	8.0	7.4	6.7
90°	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	31.1	30.0	29.0	27.9	26.8	25.8	24.7	23.7	24.7	25.8	26.8
95°	55.6	54.2	52.8	51.5	50.3	49.0	47.8	46.6	47.8	49.0	50.3
97.5°	83.2	82.1	81.1	80.1	79.2	78.3	77.5	76.6	77.5	78.3	79.2
100°	114.3	113.4	112.6	111.6	110.5	109.5	108.4	107.4	108.4	109.5	110.5
102.5°	148.3	147.1	145.9	145.0	144.5	144.0	143.4	142.9	143.4	144.0	144.5
105°	183.2	181.6	180.0	179.1	178.7	178.4	178.0	177.7	178.0	178.4	178.7
107.5°	221.3	220.5	219.8	219.4	219.2	219.1	218.9	218.7	218.9	219.1	219.2
110°	259.1	258.7	258.4	258.0	257.7	257.3	257.0	256.6	257.0	257.3	257.7



TEST NUMBER: P832150

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	296.9	296.9	296.9	296.8	296.6	296.4	296.3	296.1	296.3	296.4	296.6
115°	337.1	337.4	337.8	337.7	337.1	336.6	336.1	335.6	336.1	336.6	337.1
117.5°	375.7	376.1	376.4	376.5	376.4	376.2	376.0	375.8	376.0	376.2	376.4
120°	415.5	416.4	417.2	417.1	416.1	415.0	414.0	412.9	414.0	415.0	416.1
122.5°	453.9	454.3	454.6	454.4	453.7	453.0	452.3	451.6	452.3	453.0	453.7
125°	492.6	492.9	493.3	493.2	492.7	492.2	491.6	491.1	491.6	492.2	492.7
127.5°	531.3	531.6	532.0	531.6	530.6	529.5	528.5	527.4	528.5	529.5	530.6
130°	568.7	569.3	569.8	569.4	568.0	566.6	565.1	563.7	565.1	566.6	568.0
132.5°	605.5	605.9	606.2	605.7	604.3	602.9	601.5	600.1	601.5	602.9	604.3
135°	641.5	641.6	641.8	641.4	640.3	639.3	638.2	637.2	638.2	639.3	640.3
137.5°	676.4	675.9	675.3	674.6	673.8	672.9	672.0	671.1	672.0	672.9	673.8
140°	711.0	710.9	710.7	710.2	709.3	708.4	707.5	706.7	707.5	708.4	709.3
142.5°	743.8	743.5	743.1	742.5	741.7	740.8	739.9	739.0	739.9	740.8	741.7
145°	775.9	775.3	774.8	774.4	774.0	773.7	773.3	773.0	773.3	773.7	774.0
147.5°	806.7	806.1	805.6	805.0	804.3	803.6	802.9	802.2	802.9	803.6	804.3
150°	835.4	835.1	834.7	834.4	834.0	833.7	833.3	833.0	833.3	833.7	834.0
152.5°	861.1	860.9	860.7	860.4	859.8	859.3	858.8	858.2	858.8	859.3	859.8
155°	885.5	885.4	885.2	885.1	885.1	885.1	885.1	885.1	885.1	885.1	885.1
157.5°	907.6	907.5	907.3	907.3	907.5	907.6	907.8	908.0	907.8	907.6	907.5
160°	927.7	927.7	927.7	927.9	928.3	928.6	929.0	929.3	929.0	928.6	928.3
162.5°	946.3	946.2	946.0	946.2	946.7	947.2	947.7	948.3	947.7	947.2	946.7
165°	961.7	961.7	961.7	961.9	962.5	963.0	963.5	964.0	963.5	963.0	962.5
167.5°	974.8	974.6	974.4	974.7	975.4	976.1	976.8	977.5	976.8	976.1	975.4
170°	985.4	985.4	985.4	985.7	986.4	987.1	987.8	988.5	987.8	987.1	986.4
172.5°	994.1	994.1	994.1	994.4	995.1	995.8	996.5	997.2	996.5	995.8	995.1
175°	999.6	999.6	999.6	999.9	1000.6	1001.3	1002.0	1002.7	1002.0	1001.3	1000.6
177.5°	1002.7	1002.7	1002.7	1003.1	1003.8	1004.5	1005.2	1005.9	1005.2	1004.5	1003.8
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P832150

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9
2.5°	1086.0	1072.9	1059.8	1050.4	1040.9	1029.2	1017.5	1017.0	1016.6	1007.8	999.1
5°	1021.6	998.8	976.1	953.8	931.5	909.1	886.8	881.8	876.7	869.1	861.5
7.5°	964.6	928.2	891.9	863.4	834.9	812.6	790.2	775.1	759.9	748.2	736.4
10°	903.4	858.3	813.2	778.7	744.2	720.1	695.9	678.5	661.0	652.7	644.4
12.5°	839.9	790.9	741.9	708.1	674.3	645.4	616.4	600.5	584.6	573.1	561.6
15°	781.5	728.8	676.2	640.3	604.4	577.3	550.1	534.3	518.4	506.9	495.4
17.5°	724.9	671.8	618.7	582.3	546.0	521.4	496.8	481.4	466.0	458.8	451.7
20°	673.4	619.8	566.2	532.0	497.7	473.5	449.4	441.1	432.8	426.2	419.5
22.5°	622.4	570.8	519.3	486.4	453.5	436.1	418.6	411.9	405.2	400.2	395.1
25°	579.6	528.3	477.0	448.2	419.5	405.9	392.4	388.0	383.6	378.6	373.5
27.5°	536.3	487.6	438.8	415.8	392.8	381.8	370.7	365.2	359.7	355.6	351.4
30°	498.2	453.1	408.0	388.9	369.8	360.2	350.5	344.5	338.5	334.6	330.7
32.5°	461.4	421.3	381.3	365.0	348.7	339.2	329.8	324.1	318.3	313.7	309.1
35°	427.3	392.6	357.9	342.9	328.0	318.5	309.1	303.4	297.6	293.0	288.4
37.5°	397.4	365.9	334.4	320.4	306.3	298.1	289.8	283.8	277.8	273.0	268.2
40°	369.4	341.5	313.7	300.1	286.6	277.6	268.6	263.3	258.0	253.7	249.3
42.5°	344.5	319.0	293.5	280.1	266.8	258.3	249.8	243.6	237.3	234.8	232.3
45°	318.3	295.8	273.2	260.3	247.5	238.5	229.5	224.2	218.9	216.6	214.4
47.5°	295.3	274.4	253.4	240.8	228.1	220.1	212.1	207.9	203.8	200.6	197.3
50°	272.8	252.5	232.3	220.1	207.9	201.0	194.1	189.1	184.0	181.7	179.4
52.5°	251.1	232.7	214.4	201.9	189.5	182.8	176.2	171.8	167.4	162.6	157.8
55°	226.8	210.7	194.6	183.5	172.5	165.6	158.7	153.6	148.6	143.5	138.5
57.5°	206.5	190.7	174.8	164.9	155.0	148.3	141.7	136.2	130.6	126.5	122.4
60°	184.5	170.7	156.9	147.2	137.5	131.1	124.7	119.4	114.1	112.0	109.9
62.5°	163.8	150.9	138.0	129.5	121.0	114.8	108.6	105.1	101.7	100.3	98.9
65°	142.6	131.6	120.5	112.7	104.9	99.6	94.3	92.7	91.1	89.9	88.8
67.5°	122.8	113.4	104.0	97.1	90.2	86.5	82.8	81.0	79.1	77.7	76.4
70°	104.9	96.6	88.3	82.3	76.4	72.9	69.5	67.8	66.2	63.7	61.2
72.5°	85.6	79.1	72.7	68.1	63.5	60.5	57.5	54.3	51.1	48.8	46.5
75°	70.8	64.4	58.0	53.6	49.2	45.8	42.3	41.2	40.0	39.3	38.6
77.5°	54.3	48.8	43.2	39.8	36.3	34.7	33.1	32.4	31.7	31.5	31.3
80°	39.1	34.5	29.9	28.1	26.2	25.8	25.3	24.8	24.4	24.1	23.9
82.5°	24.4	22.1	19.8	19.3	18.9	18.6	18.4	18.2	17.9	17.7	17.5
85°	14.3	13.3	12.4	12.2	12.0	11.7	11.5	11.5	11.5	11.5	11.5
87.5°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.7	5.5
90°	7.8	9.8	12.1	14.4	16.7	18.9	19.7	20.4	21.1	21.8	22.3
92.5°	27.9	29.0	30.0	31.1	32.1	33.2	33.7	34.2	34.7	35.3	35.4
95°	51.5	52.8	54.2	55.6	57.0	58.4	59.1	59.8	60.5	61.2	61.6
97.5°	80.1	81.1	82.1	83.2	84.2	85.3	86.1	87.0	87.9	88.8	89.1
100°	111.6	112.6	113.4	114.3	115.2	116.1	116.6	117.1	117.6	118.2	118.6
102.5°	145.0	145.9	147.1	148.3	149.6	150.8	151.3	151.9	152.4	152.9	153.1
105°	179.1	180.0	181.6	183.2	184.8	186.3	186.3	186.3	186.3	186.3	186.5
107.5°	219.4	219.8	220.5	221.3	222.0	222.7	223.2	223.7	224.2	224.8	224.9
110°	258.0	258.4	258.7	259.1	259.4	259.8	260.5	261.2	261.9	262.6	262.7



TEST NUMBER: P832150

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	296.8	296.9	296.9	296.9	296.9	296.9	297.8	298.6	299.5	300.4	300.8
115°	337.7	337.8	337.4	337.1	336.7	336.4	336.5	336.7	336.9	337.1	337.1
117.5°	376.5	376.4	376.1	375.7	375.4	375.0	375.0	375.0	375.0	375.0	374.8
120°	417.1	417.2	416.4	415.5	414.6	413.7	413.6	413.4	413.2	413.0	412.8
122.5°	454.4	454.6	454.3	453.9	453.6	453.2	452.7	452.2	451.6	451.1	450.6
125°	493.2	493.3	492.9	492.6	492.2	491.9	491.2	490.5	489.8	489.1	488.4
127.5°	531.6	532.0	531.6	531.3	530.9	530.6	529.5	528.5	527.4	526.4	525.5
130°	569.4	569.8	569.3	568.7	568.2	567.7	567.0	566.3	565.6	564.9	563.9
132.5°	605.7	606.2	605.9	605.5	605.2	604.8	603.9	603.0	602.2	601.3	600.4
135°	641.4	641.8	641.6	641.5	641.3	641.1	640.4	639.7	639.0	638.3	637.8
137.5°	674.6	675.3	675.9	676.4	676.9	677.4	676.6	675.7	674.8	673.9	673.2
140°	710.2	710.7	710.9	711.0	711.2	711.4	711.2	711.0	710.9	710.7	710.0
142.5°	742.5	743.1	743.5	743.8	744.2	744.6	744.4	744.2	744.0	743.8	743.3
145°	774.4	774.8	775.3	775.9	776.4	776.9	776.7	776.6	776.4	776.2	775.8
147.5°	805.0	805.6	806.1	806.7	807.2	807.7	807.7	807.7	807.7	807.7	807.2
150°	834.4	834.7	835.1	835.4	835.8	836.1	836.1	836.1	836.1	836.1	835.6
152.5°	860.4	860.7	860.9	861.1	861.2	861.4	861.8	862.1	862.5	862.8	862.5
155°	885.1	885.2	885.4	885.5	885.7	885.9	886.6	887.3	888.0	888.7	888.4
157.5°	907.3	907.3	907.5	907.6	907.8	908.0	908.7	909.4	910.1	910.8	910.6
160°	927.9	927.7	927.7	927.7	927.7	927.7	928.6	929.5	930.4	931.2	931.3
162.5°	946.2	946.0	946.2	946.3	946.5	946.7	947.6	948.4	949.3	950.2	950.0
165°	961.9	961.7	961.7	961.7	961.7	961.7	962.7	963.8	964.8	965.9	965.8
167.5°	974.7	974.4	974.6	974.8	974.9	975.1	976.2	977.2	978.3	979.3	979.3
170°	985.7	985.4	985.4	985.4	985.4	985.4	986.6	987.8	989.1	990.3	990.3
172.5°	994.4	994.1	994.1	994.1	994.1	994.1	995.1	996.2	997.2	998.3	998.2
175°	999.9	999.6	999.6	999.6	999.6	999.6	1000.6	1001.7	1002.7	1003.8	1003.7
177.5°	1003.1	1002.7	1002.7	1002.7	1002.7	1002.7	1003.8	1004.8	1005.9	1006.9	1006.9
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P832150

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1121.9	1121.9	1121.9	1121.9
2.5°	996.8	994.5	993.6	992.6
5°	854.4	847.3	845.7	844.1
7.5°	733.4	730.4	720.6	710.7
10°	635.2	626.0	621.9	617.8
12.5°	553.1	544.6	543.2	541.9
15°	489.4	483.4	481.4	479.3
17.5°	447.6	443.4	440.9	438.4
20°	416.5	413.5	411.7	409.8
22.5°	392.8	390.5	389.1	387.8
25°	370.1	366.6	365.5	364.3
27.5°	348.4	345.4	344.3	343.1
30°	328.2	325.7	324.1	322.4
32.5°	306.1	303.1	302.2	301.3
35°	286.6	284.7	283.8	282.9
37.5°	265.9	263.6	262.2	260.8
40°	248.2	247.0	246.3	245.6
42.5°	230.2	228.1	227.9	227.7
45°	212.3	210.2	209.8	209.3
47.5°	195.5	193.7	193.4	193.2
50°	176.9	174.3	172.5	170.7
52.5°	155.5	153.2	151.6	150.0
55°	135.9	133.4	132.0	130.6
57.5°	121.2	120.1	119.4	118.7
60°	109.2	108.6	108.1	107.6
62.5°	98.2	97.5	97.5	97.5
65°	88.1	87.4	86.7	86.0
67.5°	75.0	73.6	73.4	73.1
70°	59.1	57.0	56.8	56.6
72.5°	46.2	46.0	45.5	45.1
75°	38.2	37.7	37.7	37.7
77.5°	30.8	30.4	30.4	30.4
80°	23.7	23.5	23.7	23.9
82.5°	17.5	17.5	17.2	17.0
85°	11.3	11.0	11.0	11.0
87.5°	5.5	5.5	5.5	5.5
90°	22.6	23.0	23.3	23.7
92.5°	35.0	34.7	34.3	34.0
95°	61.6	61.6	61.6	61.6
97.5°	89.0	88.8	88.6	88.4
100°	119.0	119.3	119.7	120.0
102.5°	152.9	152.7	152.6	152.4
105°	186.9	187.2	187.6	187.9
107.5°	224.8	224.6	224.4	224.2
110°	262.4	262.0	261.7	261.3



TEST NUMBER: P832150

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	300.8	300.8	300.8	300.8
115°	336.9	336.7	336.5	336.4
117.5°	374.2	373.7	373.2	372.7
120°	412.4	412.1	411.7	411.4
122.5°	450.0	449.5	449.0	448.5
125°	487.7	487.0	486.3	485.6
127.5°	524.8	524.1	523.4	522.7
130°	562.7	561.5	560.2	559.0
132.5°	599.5	598.7	597.8	596.9
135°	637.4	637.1	636.7	636.4
137.5°	672.7	672.2	671.6	671.1
140°	708.8	707.5	706.3	705.1
142.5°	742.4	741.6	740.7	739.8
145°	775.1	774.4	773.7	773.0
147.5°	806.1	805.1	804.0	803.0
150°	834.6	833.5	832.5	831.4
152.5°	861.7	860.8	859.9	859.0
155°	887.2	886.0	884.7	883.5
157.5°	909.6	908.5	907.5	906.4
160°	930.6	929.9	929.2	928.5
162.5°	948.8	947.6	946.3	945.1
165°	964.6	963.3	962.1	960.9
167.5°	978.3	977.2	976.2	975.1
170°	989.1	987.8	986.6	985.4
172.5°	996.9	995.7	994.5	993.3
175°	1002.5	1001.2	1000.0	998.8
177.5°	1005.6	1004.4	1003.2	1001.9
180°	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P832150

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.78	8.49	8.87	9.57	11.04	12.45	13.16	13.54	14.23	15.71
	3H	9.00	9.63	10.09	10.71	12.21	13.94	14.57	15.03	15.66	17.15
	4H	9.37	9.97	10.48	11.06	12.56	14.42	15.02	15.53	16.11	17.61
	6H	9.65	10.20	10.76	11.29	12.80	14.73	15.28	15.84	16.37	17.88
	8H	9.73	10.25	10.85	11.36	12.87	14.80	15.33	15.92	16.44	17.94
	12H	9.78	10.27	10.90	11.38	12.90	14.83	15.33	15.95	16.43	17.96
4H	2H	8.49	9.09	9.60	10.18	11.68	12.43	13.03	13.54	14.12	15.62
	3H	9.85	10.35	10.97	11.46	12.98	14.08	14.57	15.19	15.69	17.20
	4H	10.30	10.76	11.42	11.86	13.40	14.68	15.14	15.80	16.24	17.77
	6H	10.66	11.05	11.79	12.18	13.71	15.11	15.50	16.24	16.63	18.15
	8H	10.79	11.15	11.91	12.27	13.81	15.24	15.60	16.37	16.72	18.26
	12H	10.86	11.19	12.00	12.32	13.86	15.30	15.63	16.44	16.76	18.30
8H	4H	10.61	10.97	11.74	12.09	13.63	14.64	15.00	15.77	16.12	17.66
	6H	11.07	11.37	12.22	12.53	14.07	15.13	15.43	16.28	16.59	18.13
	8H	11.26	11.52	12.42	12.67	14.22	15.32	15.58	16.47	16.72	18.28
	12H	11.40	11.63	12.55	12.77	14.36	15.43	15.66	16.58	16.80	18.39
12H	4H	10.61	10.94	11.76	12.08	13.62	14.58	14.91	15.73	16.04	17.59
	6H	11.13	11.39	12.28	12.53	14.09	15.10	15.37	16.26	16.51	18.07
	8H	11.34	11.57	12.50	12.71	14.30	15.29	15.52	16.45	16.66	18.25