

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332321

Luminaire Tested: **S123RDIP-S775D1025U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332321  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D1025U835-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7017.4 lumens  
Efficiency: N/A  
Efficacy: 135.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332321

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332321

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42				
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36				
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	38	37	35	30				
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26				
4	73	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26	22				
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20				
6	62	50	43	37	57	46	40	34	39	34	30	32	28	25	25	23	20	17				
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	21	18	16	14				
9	50	38	30	26	45	35	28	24	30	24	21	24	21	18	20	17	15	13				
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332321

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.2	1.7
10°-20°	337.3	4.8
20°-30°	485.7	6.9
30°-40°	547.1	7.8
40°-50°	523.4	7.5
50°-60°	428.6	6.1
60°-70°	289.2	4.1
70°-80°	145.5	2.1
80°-90°	42.3	0.6
90°-100°	48.8	0.7
100°-110°	232.8	3.3
110°-120°	559.2	8.0
120°-130°	712.1	10.1
130°-140°	760.8	10.8
140°-150°	711.5	10.1
150°-160°	573.9	8.2
160°-170°	370.4	5.3
170°-180°	127.6	1.8
0°-30°	944.3	13.5
0°-40°	1491.4	21.3
0°-60°	2443.4	34.8
0°-90°	2920.3	41.6
90°-120°	840.8	12.0
90°-150°	3025.2	43.1
90°-180°	4097.0	58.4
0°-180°	7017.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	1	11	24	28	30	6
95°	61	23	31	38	38	75
105°	297	303	219	52	44	315
115°	558	564	573	583	587	551
125°	786	794	798	800	802	702
135°	979	985	989	992	989	754
145°	1130	1137	1139	1141	1141	707
155°	1245	1243	1244	1248	1243	573
165°	1313	1310	1309	1316	1310	371
175°	1344	1339	1340	1346	1338	128
180°	1344	1344	1344	1344	1344	



TEST NUMBER: P332321

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.3	18.7	17.1	15.5	13.9	13.4	14.0	14.5	15.1	15.7	15.7
90°	1.0	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8
92.5°	18.6	17.9	17.3	16.7	16.1	16.9	19.0	21.2	23.4	25.6	27.0
95°	60.9	51.8	42.7	33.6	24.5	21.2	23.6	26.1	28.5	30.9	32.5
97.5°	122.4	118.3	114.2	110.1	106.0	96.0	80.1	64.1	48.1	32.1	33.9
100°	168.7	173.1	177.6	182.0	186.4	171.3	136.7	102.1	67.5	32.9	34.7
102.5°	221.4	224.6	227.8	231.0	234.2	216.9	179.1	141.3	103.5	65.7	60.2
105°	297.4	299.9	302.3	304.8	307.2	298.4	278.5	258.5	238.6	218.6	179.3
107.5°	377.7	379.7	381.6	383.6	385.5	388.1	391.2	394.4	397.5	400.7	371.9
110°	431.2	433.0	434.7	436.5	438.3	440.4	442.8	445.3	447.7	450.2	442.8



TEST NUMBER: P332321

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	482.3	483.9	485.5	487.1	488.7	490.7	493.2	495.6	498.0	500.5	500.6
115°	558.0	559.3	560.6	562.0	563.3	565.0	566.9	568.9	570.9	572.9	575.2
117.5°	631.2	632.9	634.5	636.2	637.8	639.1	640.1	641.2	642.2	643.2	645.0
120°	676.7	678.7	680.7	682.7	684.7	686.1	686.7	687.4	688.1	688.7	690.5
122.5°	723.1	724.7	726.3	728.0	729.6	730.9	731.7	732.6	733.4	734.2	735.5
125°	786.5	788.3	790.1	791.9	793.6	795.0	795.9	796.7	797.6	798.5	799.0
127.5°	848.0	849.8	851.6	853.3	855.1	856.5	857.6	858.7	859.7	860.8	861.5
130°	886.4	888.1	889.9	891.7	893.5	894.8	895.7	896.6	897.4	898.3	899.2
132.5°	923.1	924.9	926.6	928.4	930.2	931.4	932.1	932.8	933.6	934.3	935.2
135°	979.2	980.5	981.8	983.2	984.5	985.6	986.5	987.4	988.3	989.2	989.8
137.5°	1027.1	1028.8	1030.5	1032.2	1033.8	1034.9	1035.4	1035.9	1036.4	1036.9	1037.9
140°	1059.0	1060.4	1061.7	1063.0	1064.4	1065.4	1066.0	1066.7	1067.4	1068.0	1068.9
142.5°	1088.6	1089.9	1091.2	1092.6	1093.9	1094.9	1095.6	1096.2	1096.9	1097.6	1098.3
145°	1129.9	1131.5	1133.0	1134.6	1136.1	1137.1	1137.6	1138.0	1138.4	1138.9	1139.3
147.5°	1168.8	1169.9	1170.9	1171.9	1172.9	1173.6	1174.1	1174.5	1175.0	1175.4	1175.9
150°	1192.8	1193.5	1194.1	1194.8	1195.4	1196.0	1196.4	1196.9	1197.3	1197.8	1198.2
152.5°	1214.3	1214.7	1215.0	1215.3	1215.6	1215.9	1216.1	1216.4	1216.7	1216.9	1217.7
155°	1244.7	1244.2	1243.8	1243.4	1242.9	1242.8	1243.0	1243.2	1243.5	1243.7	1244.8
157.5°	1268.2	1268.2	1268.2	1268.1	1268.1	1267.9	1267.7	1267.5	1267.3	1267.0	1268.4
160°	1282.6	1282.4	1282.2	1282.0	1281.7	1281.5	1281.3	1281.1	1280.8	1280.6	1282.0
162.5°	1296.2	1295.6	1295.0	1294.5	1293.9	1293.5	1293.3	1293.0	1292.8	1292.6	1294.1
165°	1312.6	1311.9	1311.2	1310.6	1309.9	1309.5	1309.2	1309.0	1308.8	1308.6	1310.3
167.5°	1325.3	1324.5	1323.6	1322.7	1321.8	1321.3	1321.3	1321.3	1321.3	1321.3	1323.1
170°	1332.5	1331.6	1330.8	1329.9	1329.0	1328.5	1328.5	1328.5	1328.5	1328.5	1330.3
172.5°	1337.3	1336.3	1335.2	1334.1	1333.1	1332.6	1332.8	1333.0	1333.1	1333.3	1335.1
175°	1343.5	1342.4	1341.3	1340.2	1339.1	1338.6	1338.8	1339.1	1339.3	1339.5	1341.1
177.5°	1345.1	1344.2	1343.3	1342.4	1341.6	1341.2	1341.4	1341.6	1341.7	1341.9	1343.3
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332321

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	15.7	15.7	15.6	15.6	15.5	15.4	15.3	15.2
90°	25.7	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	28.4	29.8	31.2	32.1	32.3	32.6	32.9	33.1
95°	34.0	35.6	37.2	37.9	37.9	37.9	37.9	37.9
97.5°	35.7	37.5	39.2	40.2	40.5	40.7	40.9	41.1
100°	36.5	38.3	40.0	41.0	41.3	41.5	41.7	41.9
102.5°	54.7	49.2	43.7	41.1	41.5	41.9	42.3	42.7
105°	140.1	100.8	61.6	42.1	42.6	43.0	43.5	43.9
107.5°	343.1	314.3	285.5	256.3	226.7	197.1	167.5	137.9
110°	435.5	428.2	420.9	401.4	369.6	337.9	306.2	274.5





TEST NUMBER: P332321

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	500.7	500.9	501.0	497.7	491.0	484.3	477.6	470.9
115°	577.4	579.6	581.8	583.4	584.2	585.1	586.0	586.9
117.5°	646.8	648.5	650.3	651.3	651.5	651.6	651.8	652.0
120°	692.3	694.0	695.8	696.7	696.7	696.7	696.7	696.7
122.5°	736.7	738.0	739.2	739.9	740.1	740.3	740.4	740.6
125°	799.4	799.8	800.3	800.7	801.2	801.6	802.1	802.5
127.5°	862.2	862.9	863.6	863.8	863.3	862.9	862.4	862.0
130°	900.1	901.0	901.9	902.1	901.7	901.2	900.8	900.3
132.5°	936.0	936.9	937.8	937.9	937.3	936.7	936.1	935.5
135°	990.5	991.2	991.8	991.8	991.2	990.5	989.8	989.2
137.5°	1039.0	1040.1	1041.1	1041.4	1041.0	1040.6	1040.1	1039.7
140°	1069.8	1070.7	1071.6	1071.8	1071.3	1070.9	1070.5	1070.0
142.5°	1099.0	1099.7	1100.4	1100.4	1099.8	1099.2	1098.6	1098.0
145°	1139.8	1140.2	1140.7	1140.9	1140.9	1140.9	1140.9	1140.9
147.5°	1176.3	1176.7	1177.2	1176.9	1175.9	1174.9	1173.8	1172.8
150°	1198.7	1199.1	1199.6	1199.4	1198.8	1198.1	1197.4	1196.8
152.5°	1218.5	1219.3	1220.1	1220.0	1219.0	1218.0	1217.0	1215.9
155°	1245.9	1247.0	1248.1	1248.0	1246.7	1245.4	1244.0	1242.7
157.5°	1269.7	1271.0	1272.4	1272.2	1270.4	1268.7	1267.0	1265.3
160°	1283.3	1284.6	1285.9	1285.8	1284.3	1282.7	1281.2	1279.6
162.5°	1295.6	1297.1	1298.6	1298.7	1297.3	1295.9	1294.6	1293.2
165°	1312.1	1313.9	1315.7	1315.8	1314.2	1312.7	1311.1	1309.6
167.5°	1324.9	1326.7	1328.4	1328.4	1326.7	1324.9	1323.1	1321.3
170°	1332.1	1333.9	1335.6	1335.6	1333.9	1332.1	1330.3	1328.5
172.5°	1336.9	1338.6	1340.4	1340.3	1338.4	1336.4	1334.5	1332.5
175°	1342.6	1344.2	1345.7	1345.6	1343.8	1342.1	1340.3	1338.5
177.5°	1344.7	1346.2	1347.6	1347.4	1345.6	1343.9	1342.1	1340.3
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5

(END OF REPORT)