

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332291-840

Luminaire Tested: **S123RDIP-S560D1025U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332291-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1025U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6296.0 lumens
Efficiency: N/A
Efficacy: 141.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332291-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332291-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	103	103	103	103	93	93	93	93	75	75	75		57	57	57		42	42	42	34
1	94	90	87	83	85	82	79	76	66	63	62		51	49	48		37	36	36	29
2	86	79	73	68	78	72	67	62	58	54	51		45	43	41		33	32	30	25
3	79	70	63	57	71	63	57	52	51	47	43		40	37	34		29	28	26	21
4	72	62	54	48	65	56	50	44	45	41	37		36	32	30		26	24	23	18
5	66	55	47	41	60	50	43	38	41	36	32		32	28	26		24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28		29	25	23		22	19	17	14
7	56	44	37	31	51	41	34	29	33	28	24		26	23	20		20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22		24	20	18		18	16	14	11
9	49	37	29	25	44	34	27	23	28	23	19		22	19	16		17	14	13	10
10	45	34	27	22	41	31	25	20	25	21	17		20	17	14		16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10267	10267	10267
5°	10306	10164	10222
10°	10248	10037	10002
15°	10137	9802	9698
20°	9986	9507	9286
25°	9830	9178	8884
30°	9625	8797	8316
35°	9412	8418	7796
40°	9218	7967	7152
45°	8961	7524	6570
50°	8679	7021	5921
55°	8392	6446	5315
60°	8127	5828	4646
65°	7784	5163	3978
70°	7352	4334	3213
75°	6725	3410	3023
80°	5994	3025	2777
85°	5064	2668	2482



TEST NUMBER: P332291-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.4
10°-20°	249.2	4.0
20°-30°	358.8	5.7
30°-40°	404.2	6.4
40°-50°	386.7	6.1
50°-60°	316.7	5.0
60°-70°	213.7	3.4
70°-80°	107.5	1.7
80°-90°	32.2	0.5
90°-100°	49.3	0.8
100°-110°	235.1	3.7
110°-120°	564.7	9.0
120°-130°	719.1	11.4
130°-140°	768.3	12.2
140°-150°	718.5	11.4
150°-160°	579.5	9.2
160°-170°	374.0	5.9
170°-180°	128.9	2.0
0°-30°	697.6	11.1
0°-40°	1101.8	17.5
0°-60°	1805.2	28.7
0°-90°	2158.6	34.3
90°-120°	849.1	13.5
90°-150°	3055.0	48.5
90°-180°	4137.0	65.7
0°-180°	6296.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	954	954	954	954	954	
5°	954	950	941	947	946	90
15°	910	900	880	876	870	256
25°	828	808	773	757	748	381
35°	716	687	641	608	593	448
45°	589	552	494	452	432	454
55°	447	408	344	300	283	401
65°	306	262	203	166	156	302
75°	162	124	82	75	73	172
85°	41	25	22	20	20	46
90°	1	11	24	28	30	5
95°	62	23	31	38	38	76
105°	300	306	221	52	44	318
115°	564	570	579	588	593	556
125°	794	802	806	808	810	709
135°	989	995	999	1002	999	761
145°	1141	1148	1150	1152	1152	714
155°	1257	1255	1256	1260	1255	579
165°	1326	1323	1322	1329	1322	374
175°	1357	1352	1353	1359	1352	129
180°	1357	1357	1357	1357	1357	



TEST NUMBER: P332291-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	956.9	956.3	955.8	955.2	954.7	953.6	952.0	950.3	948.7	947.1	948.6
5°	953.8	953.0	952.1	951.3	950.4	949.0	946.8	944.8	942.7	940.7	942.2
7.5°	945.0	944.1	943.1	942.2	941.3	939.5	936.9	934.1	931.4	928.8	929.6
10°	937.6	936.3	935.1	933.9	932.8	930.6	927.6	924.4	921.3	918.3	918.4
12.5°	927.1	925.7	924.3	923.0	921.7	919.2	915.3	911.6	907.8	904.0	903.9
15°	909.7	907.9	905.9	904.0	902.2	898.8	894.0	889.2	884.3	879.6	878.7
17.5°	887.9	885.8	883.5	881.3	879.1	874.9	868.8	862.7	856.6	850.5	848.7
20°	871.8	869.1	866.4	863.5	860.8	856.2	849.6	843.1	836.6	830.0	827.8
22.5°	853.8	850.7	847.6	844.3	841.2	836.2	829.2	822.2	815.4	808.4	805.6
25°	827.7	823.4	819.1	814.9	810.5	804.5	796.5	788.6	780.7	772.8	769.2
27.5°	796.0	791.2	786.5	781.7	777.0	770.2	761.4	752.7	743.9	735.1	730.0
30°	774.4	769.2	764.1	758.9	753.8	746.3	736.7	727.1	717.4	707.8	702.0
32.5°	752.7	746.9	741.0	735.2	729.3	721.3	711.1	700.9	690.7	680.5	674.2
35°	716.3	710.1	704.0	697.8	691.6	683.2	672.5	661.9	651.2	640.6	633.1
37.5°	679.5	672.7	665.8	658.8	652.0	642.9	631.5	620.2	608.7	597.3	589.0
40°	656.0	648.4	640.9	633.3	625.7	615.8	603.7	591.5	579.3	567.0	558.1
42.5°	629.3	621.8	614.3	606.7	599.2	589.1	576.4	563.8	551.2	538.6	528.8
45°	588.7	581.0	573.2	565.5	557.7	547.2	534.0	520.8	507.6	494.3	484.5
47.5°	548.0	539.5	531.0	522.5	514.0	503.2	489.9	476.7	463.4	450.2	439.6
50°	518.3	510.2	502.1	494.0	485.9	474.9	461.0	447.2	433.2	419.3	408.6
52.5°	491.7	482.9	474.1	465.3	456.7	445.4	431.5	417.8	403.9	390.2	379.1
55°	447.2	438.7	430.3	421.8	413.4	401.9	387.3	372.7	358.1	343.5	333.5
57.5°	406.0	396.8	387.6	378.4	369.2	357.3	342.6	328.0	313.3	298.6	289.2
60°	377.5	368.1	358.6	349.1	339.7	327.8	313.6	299.3	285.0	270.7	261.5
62.5°	349.0	339.6	330.1	320.6	311.2	299.3	285.1	270.8	256.5	242.3	233.6
65°	305.6	296.1	286.7	277.2	267.7	256.3	242.9	229.5	216.1	202.7	194.3
67.5°	262.1	252.6	243.0	233.4	223.9	212.7	199.8	186.9	174.1	161.2	154.9
70°	233.6	224.3	215.1	205.8	196.5	185.8	173.8	161.8	149.8	137.7	131.7
72.5°	205.1	196.0	186.8	177.7	168.5	158.5	147.6	136.6	125.7	114.8	109.9
75°	161.7	153.4	145.2	136.9	128.7	119.8	110.4	100.9	91.5	82.0	80.3
77.5°	122.1	114.6	107.1	99.7	92.2	85.4	79.4	73.3	67.2	61.1	60.2
80°	96.7	89.7	82.6	75.5	68.5	63.2	59.6	55.9	52.3	48.8	48.2
82.5°	72.6	66.4	60.4	54.3	48.2	44.3	42.6	41.0	39.3	37.6	37.1
85°	41.0	37.3	33.4	29.7	25.9	23.7	23.2	22.7	22.2	21.6	21.3
87.5°	15.0	14.0	12.9	11.8	10.8	10.6	11.1	11.7	12.3	12.9	12.9
90°	1.0	3.2	5.5	7.8	10.0	12.5	15.5	18.4	21.3	24.2	25.0
92.5°	18.8	18.1	17.5	16.9	16.3	17.1	19.2	21.4	23.6	25.9	27.3
95°	61.5	52.3	43.1	33.9	24.7	21.4	23.8	26.4	28.8	31.2	32.8
97.5°	123.6	119.5	115.3	111.2	107.0	96.9	80.9	64.7	48.6	32.4	34.2
100°	170.4	174.8	179.4	183.8	188.2	173.0	138.0	103.1	68.2	33.2	35.0
102.5°	223.6	226.8	230.0	233.3	236.5	219.0	180.9	142.7	104.5	66.3	60.8
105°	300.3	302.9	305.3	307.8	310.2	301.3	281.2	261.1	241.0	220.8	181.1
107.5°	381.4	383.4	385.4	387.4	389.3	391.9	395.1	398.3	401.4	404.7	375.6
110°	435.5	437.3	439.0	440.8	442.6	444.7	447.2	449.7	452.1	454.6	447.2



TEST NUMBER: P332291-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.1	488.7	490.3	491.9	493.5	495.5	498.1	500.5	502.9	505.4	505.5
115°	563.5	564.8	566.1	567.5	568.9	570.6	572.5	574.5	576.5	578.6	580.9
117.5°	637.4	639.1	640.8	642.5	644.1	645.4	646.4	647.5	648.5	649.5	651.4
120°	683.4	685.4	687.4	689.4	691.5	692.9	693.5	694.2	694.9	695.5	697.3
122.5°	730.2	731.8	733.5	735.2	736.8	738.1	738.9	739.8	740.6	741.4	742.8
125°	794.3	796.1	797.9	799.7	801.4	802.8	803.8	804.6	805.5	806.4	806.9
127.5°	856.4	858.2	860.0	861.7	863.5	864.9	866.1	867.2	868.2	869.3	870.0
130°	895.1	896.9	898.7	900.5	902.3	903.6	904.5	905.4	906.3	907.2	908.1
132.5°	932.2	934.0	935.7	937.6	939.4	940.6	941.3	942.0	942.8	943.5	944.4
135°	988.9	990.2	991.5	992.9	994.2	995.3	996.2	997.1	998.0	999.0	999.6
137.5°	1037.2	1038.9	1040.7	1042.4	1044.0	1045.1	1045.6	1046.1	1046.6	1047.1	1048.1
140°	1069.4	1070.9	1072.2	1073.5	1074.9	1075.9	1076.5	1077.2	1077.9	1078.5	1079.4
142.5°	1099.3	1100.7	1102.0	1103.4	1104.7	1105.7	1106.4	1107.0	1107.7	1108.4	1109.1
145°	1141.0	1142.7	1144.2	1145.8	1147.3	1148.3	1148.8	1149.2	1149.6	1150.1	1150.5
147.5°	1180.3	1181.4	1182.5	1183.5	1184.5	1185.2	1185.7	1186.1	1186.6	1187.0	1187.5
150°	1204.6	1205.3	1205.9	1206.6	1207.2	1207.8	1208.2	1208.7	1209.1	1209.6	1210.0
152.5°	1226.3	1226.7	1227.0	1227.3	1227.6	1227.9	1228.1	1228.4	1228.7	1228.9	1229.7
155°	1257.0	1256.5	1256.1	1255.7	1255.2	1255.1	1255.3	1255.5	1255.8	1256.0	1257.1
157.5°	1280.7	1280.7	1280.7	1280.6	1280.6	1280.4	1280.2	1280.0	1279.8	1279.5	1280.9
160°	1295.3	1295.1	1294.8	1294.6	1294.3	1294.1	1293.9	1293.7	1293.4	1293.2	1294.6
162.5°	1309.0	1308.4	1307.8	1307.3	1306.7	1306.3	1306.1	1305.8	1305.6	1305.4	1306.9
165°	1325.5	1324.8	1324.1	1323.5	1322.8	1322.4	1322.1	1321.9	1321.7	1321.5	1323.2
167.5°	1338.4	1337.6	1336.7	1335.7	1334.8	1334.3	1334.3	1334.3	1334.3	1334.3	1336.2
170°	1345.6	1344.7	1343.9	1343.0	1342.1	1341.6	1341.6	1341.6	1341.6	1341.6	1343.4
172.5°	1350.5	1349.5	1348.4	1347.3	1346.3	1345.7	1345.9	1346.2	1346.3	1346.5	1348.3
175°	1356.8	1355.6	1354.5	1353.4	1352.3	1351.8	1352.0	1352.3	1352.5	1352.7	1354.3
177.5°	1358.4	1357.5	1356.6	1355.6	1354.8	1354.4	1354.6	1354.8	1354.9	1355.1	1356.6
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8



TEST NUMBER: P332291-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	950.1	951.6	953.1	953.7	953.4	953.1	952.9	952.6
5°	943.7	945.3	946.8	947.5	947.2	946.7	946.4	946.0
7.5°	930.5	931.3	932.2	932.3	931.7	931.2	930.6	930.0
10°	918.6	918.8	918.9	918.6	917.8	916.9	916.0	915.1
12.5°	903.8	903.7	903.6	903.0	902.0	901.0	900.1	899.1
15°	877.9	877.0	876.2	875.0	873.8	872.7	871.5	870.3
17.5°	846.9	845.1	843.1	841.4	839.6	837.8	836.0	834.2
20°	825.6	823.3	821.1	819.0	816.9	814.9	812.7	810.7
22.5°	802.8	800.0	797.3	794.9	792.9	791.0	789.1	787.2
25°	765.6	761.9	758.4	755.6	753.8	751.8	749.9	748.0
27.5°	725.0	720.0	715.0	711.0	708.1	705.3	702.4	699.4
30°	696.1	690.2	684.5	680.1	677.4	674.7	671.9	669.1
32.5°	667.8	661.4	655.0	650.4	647.5	644.6	641.7	638.8
35°	625.7	618.3	611.0	605.7	602.6	599.6	596.4	593.3
37.5°	580.6	572.2	563.8	557.7	553.9	550.1	546.2	542.4
40°	549.2	540.2	531.3	524.8	520.9	516.9	513.0	509.0
42.5°	519.1	509.3	499.5	492.8	489.3	485.7	482.2	478.7
45°	474.7	464.9	455.1	448.2	444.0	439.9	435.8	431.6
47.5°	428.9	418.3	407.6	400.4	396.8	393.0	389.4	385.7
50°	398.0	387.3	376.7	369.3	365.4	361.4	357.5	353.6
52.5°	368.1	357.0	345.9	338.6	335.1	331.5	328.0	324.5
55°	323.6	313.6	303.6	296.9	293.5	290.0	286.6	283.2
57.5°	279.7	270.3	260.9	254.8	251.9	248.9	246.0	243.1
60°	252.2	242.9	233.6	227.5	224.6	221.7	218.7	215.8
62.5°	224.8	216.1	207.3	201.5	198.4	195.3	192.3	189.2
65°	185.8	177.4	169.0	163.8	162.0	160.1	158.1	156.2
67.5°	148.7	142.3	136.0	131.9	129.9	127.8	125.8	123.8
70°	125.6	119.7	113.6	109.7	107.8	105.9	104.0	102.1
72.5°	104.9	100.1	95.1	92.3	91.5	90.7	89.9	89.1
75°	78.6	76.9	75.1	74.1	73.7	73.4	73.0	72.7
77.5°	59.3	58.4	57.4	56.8	56.5	56.0	55.7	55.3
80°	47.7	47.2	46.7	46.3	45.9	45.5	45.2	44.8
82.5°	36.6	36.1	35.5	35.2	35.1	35.1	35.0	34.9
85°	21.0	20.6	20.3	20.1	20.1	20.1	20.1	20.1
87.5°	12.9	13.0	13.0	13.0	13.0	12.9	12.9	12.8
90°	26.0	26.9	27.8	28.5	28.9	29.4	29.8	30.2
92.5°	28.7	30.1	31.5	32.4	32.6	32.9	33.2	33.4
95°	34.3	36.0	37.6	38.3	38.3	38.3	38.3	38.3
97.5°	36.1	37.9	39.6	40.6	40.9	41.1	41.3	41.5
100°	36.9	38.7	40.4	41.4	41.7	41.9	42.1	42.3
102.5°	55.2	49.7	44.1	41.5	41.9	42.3	42.7	43.1
105°	141.5	101.8	62.2	42.5	43.0	43.4	43.9	44.3
107.5°	346.5	317.4	288.3	258.8	228.9	199.0	169.2	139.3
110°	439.8	432.4	425.1	405.4	373.2	341.2	309.2	277.2



TEST NUMBER: P332291-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	505.6	505.8	505.9	502.6	495.8	489.1	482.3	475.5
115°	583.1	585.3	587.5	589.2	590.0	590.9	591.8	592.7
117.5°	653.2	654.9	656.7	657.7	657.9	658.0	658.2	658.4
120°	699.1	700.8	702.7	703.6	703.6	703.6	703.6	703.6
122.5°	744.0	745.3	746.5	747.2	747.4	747.6	747.7	747.9
125°	807.3	807.7	808.2	808.6	809.1	809.5	810.0	810.4
127.5°	870.7	871.4	872.1	872.3	871.8	871.4	870.9	870.5
130°	909.0	909.9	910.8	911.0	910.6	910.1	909.7	909.2
132.5°	945.2	946.1	947.1	947.2	946.5	945.9	945.3	944.7
135°	1000.3	1001.0	1001.6	1001.6	1001.0	1000.3	999.6	999.0
137.5°	1049.2	1050.4	1051.4	1051.7	1051.3	1050.9	1050.4	1050.0
140°	1080.4	1081.3	1082.2	1082.4	1081.9	1081.5	1081.1	1080.6
142.5°	1109.8	1110.5	1111.3	1111.3	1110.6	1110.0	1109.4	1108.8
145°	1151.0	1151.4	1152.0	1152.2	1152.2	1152.2	1152.2	1152.2
147.5°	1187.9	1188.3	1188.8	1188.5	1187.5	1186.5	1185.4	1184.4
150°	1210.5	1210.9	1211.4	1211.2	1210.6	1209.9	1209.2	1208.6
152.5°	1230.5	1231.3	1232.1	1232.0	1231.0	1230.0	1229.0	1227.9
155°	1258.2	1259.3	1260.4	1260.3	1259.0	1257.7	1256.3	1255.0
157.5°	1282.2	1283.5	1285.0	1284.8	1282.9	1281.2	1279.5	1277.8
160°	1296.0	1297.3	1298.6	1298.5	1297.0	1295.4	1293.8	1292.2
162.5°	1308.4	1309.9	1311.4	1311.5	1310.1	1308.7	1307.4	1306.0
165°	1325.0	1326.9	1328.7	1328.8	1327.2	1325.6	1324.0	1322.5
167.5°	1338.0	1339.8	1341.5	1341.5	1339.8	1338.0	1336.2	1334.3
170°	1345.2	1347.1	1348.8	1348.8	1347.1	1345.2	1343.4	1341.6
172.5°	1350.1	1351.8	1353.6	1353.5	1351.6	1349.6	1347.7	1345.6
175°	1355.8	1357.5	1359.0	1358.9	1357.1	1355.3	1353.5	1351.7
177.5°	1358.0	1359.5	1360.9	1360.7	1358.9	1357.2	1355.3	1353.5
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8

(END OF REPORT)