

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332294-840

Luminaire Tested: **S123RDIP-S560D1195U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332294-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1195U840-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7070.0 lumens
Efficiency: N/A
Efficacy: 143.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39	32
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34	28
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	30	29	24
3	79	70	63	57	71	63	57	53	51	46	43	39	36	34	28	27	25	21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22	18
5	66	55	47	42	59	50	43	38	40	36	32	31	28	26	23	21	19	16
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11
9	49	37	30	25	44	34	27	23	28	23	20	22	18	16	16	14	13	10
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9725	9725	9725	9725
5°	11594	9767	8602	9767
10°	14476	9711	7770	9711
15°	16992	9611	7086	9611
20°	18963	9464	6504	9464
25°	18659	9308	6147	9308
30°	13412	9163	5778	9163
35°	8956	8976	5540	8976
40°	6598	8751	5295	8751
45°	5535	8356	5051	8356
50°	4883	7839	4716	7839
55°	4282	7246	4252	7246
60°	3813	6678	3899	6678
65°	3349	6067	3627	6067
70°	2628	5526	3311	5526
75°	2316	4824	3023	4824
80°	2015	4097	2975	4097
85°	1618	3298	3149	3298



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.9	1.3
10°-20°	277.6	3.9
20°-30°	436.1	6.2
30°-40°	455.0	6.4
40°-50°	389.4	5.5
50°-60°	296.8	4.2
60°-70°	190.2	2.7
70°-80°	91.5	1.3
80°-90°	28.6	0.4
90°-100°	57.4	0.8
100°-110°	273.6	3.9
110°-120°	657.3	9.3
120°-130°	837.0	11.8
130°-140°	894.3	12.6
140°-150°	836.3	11.8
150°-160°	674.6	9.5
160°-170°	435.4	6.2
170°-180°	150.0	2.1
0°-30°	802.6	11.4
0°-40°	1257.6	17.8
0°-60°	1943.7	27.5
0°-90°	2254.1	31.9
90°-120°	988.3	14.0
90°-150°	3555.9	50.3
90°-180°	4816.0	68.1
0°-180°	7070.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1073	904	796	904	1073	111
15°	1525	862	636	862	1525	432
25°	1571	784	518	784	1571	675
35°	682	683	422	683	682	447
45°	364	549	332	549	364	286
55°	228	386	227	386	228	206
65°	132	238	142	238	132	129
75°	56	116	73	116	56	60
85°	13	27	26	27	13	16
90°	35	1	35	1	35	16
95°	44	72	44	72	44	37
105°	52	350	52	350	52	118
115°	690	656	690	656	690	637
125°	943	924	943	924	943	842
135°	1163	1151	1163	1151	1163	897
145°	1341	1328	1341	1328	1341	837
155°	1461	1463	1461	1463	1461	674
165°	1539	1543	1539	1543	1539	435
175°	1573	1579	1573	1579	1573	150
180°	1579	1579	1579	1579	1579	



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	962.3	963.6	959.6	959.0	954.3	953.1	953.1	946.5	942.5	937.3	934.2
5°	1073.0	1079.1	1076.1	1069.1	1057.5	1054.8	1047.4	1035.8	1022.7	1006.4	998.8
7.5°	1211.1	1219.6	1216.3	1205.6	1193.5	1183.6	1162.9	1143.6	1116.6	1093.0	1072.7
10°	1324.4	1315.5	1308.6	1298.1	1286.9	1268.7	1247.1	1217.3	1182.9	1155.8	1125.6
12.5°	1409.2	1407.8	1398.9	1388.2	1372.3	1355.0	1328.4	1292.1	1252.1	1212.9	1178.5
15°	1524.8	1527.1	1521.3	1510.1	1487.6	1457.0	1416.8	1401.8	1344.5	1301.9	1259.4
17.5°	1604.8	1604.3	1603.5	1587.9	1565.1	1543.3	1506.0	1466.3	1414.5	1354.5	1297.3
20°	1655.5	1651.6	1652.4	1635.0	1618.0	1592.9	1556.5	1498.8	1456.3	1387.0	1327.9
22.5°	1654.3	1653.5	1656.4	1650.4	1638.1	1618.8	1590.2	1541.6	1487.2	1417.3	1350.8
25°	1571.1	1568.1	1586.3	1591.2	1611.0	1614.5	1606.0	1579.3	1527.8	1455.9	1373.5
27.5°	1314.9	1313.2	1347.0	1389.2	1442.8	1484.4	1524.6	1544.0	1527.8	1476.3	1393.8
30°	1079.1	1115.5	1132.6	1193.7	1261.7	1342.9	1414.1	1481.8	1498.4	1476.0	1408.4
32.5°	896.0	927.7	941.9	994.4	1057.8	1153.0	1259.7	1355.5	1423.3	1440.5	1399.7
35°	681.6	682.0	714.4	737.6	796.4	894.2	997.9	1126.3	1253.9	1350.7	1360.8
37.5°	543.8	545.7	565.4	588.5	632.7	684.4	775.7	882.4	1029.9	1178.3	1265.4
40°	469.6	473.0	487.8	510.6	542.3	581.4	652.6	753.1	876.1	1041.3	1176.3
42.5°	421.9	427.6	435.2	452.7	472.3	509.0	566.5	644.2	756.0	912.2	1067.9
45°	363.6	366.7	372.4	380.6	398.4	423.9	462.6	514.8	607.6	733.4	889.3
47.5°	320.7	319.1	325.2	331.8	343.7	361.0	387.0	429.6	495.8	596.6	728.9
50°	291.6	291.2	295.5	300.5	311.7	324.6	345.8	377.9	430.5	514.0	635.1
52.5°	264.4	265.9	268.9	275.2	283.3	293.6	312.7	335.8	381.0	453.1	554.0
55°	228.2	229.3	233.6	237.1	242.9	253.4	265.4	284.7	315.6	365.9	449.1
57.5°	197.5	197.0	201.2	202.0	208.5	217.0	226.3	241.4	263.8	301.1	357.2
60°	177.1	176.0	179.5	182.2	185.6	192.6	200.4	215.1	232.9	260.3	308.3
62.5°	158.5	158.0	160.6	163.3	166.1	172.5	179.0	190.3	204.4	227.5	265.6
65°	131.5	132.7	133.8	135.0	136.5	140.4	146.6	154.3	164.0	180.3	207.7
67.5°	103.3	104.5	104.9	107.2	110.6	113.0	116.8	123.7	130.5	144.1	159.8
70°	83.5	83.1	83.5	84.7	89.0	93.2	98.3	103.3	107.6	117.2	130.4
72.5°	71.8	71.1	72.1	72.3	74.4	75.5	78.8	83.5	89.0	95.5	105.0
75°	55.7	55.7	55.7	55.7	57.3	58.1	59.2	60.4	62.3	65.3	72.3
77.5°	41.2	41.2	41.8	42.1	42.5	42.9	43.6	44.8	45.4	47.2	50.1
80°	32.5	32.9	32.5	32.9	32.9	33.6	34.0	35.2	35.5	37.6	38.7
82.5°	24.4	24.2	24.4	24.8	24.8	25.7	25.7	26.6	26.7	27.6	28.8
85°	13.1	12.4	13.1	12.7	13.5	12.7	13.1	13.9	13.9	14.3	15.9
87.5°	10.1	10.6	9.9	10.1	10.0	10.2	10.0	9.8	10.2	9.7	9.3
90°	35.2	34.6	34.1	33.6	33.1	32.3	31.3	30.2	29.2	28.2	24.7
92.5°	39.0	38.7	38.4	38.0	37.7	36.8	35.0	33.3	31.7	30.0	27.5
95°	44.5	44.5	44.5	44.5	44.5	43.6	41.8	40.0	38.2	36.4	33.5
97.5°	48.4	48.1	47.9	47.6	47.3	46.2	44.0	41.9	39.9	37.8	56.6
100°	49.3	49.0	48.8	48.5	48.3	47.1	44.9	42.9	40.8	38.7	79.4
102.5°	50.2	49.8	49.3	48.8	48.4	51.3	57.8	64.2	70.7	77.2	121.6
105°	51.6	51.1	50.6	50.1	49.6	72.3	118.5	164.6	210.8	256.9	280.4
107.5°	162.2	196.9	231.7	266.5	301.2	335.6	369.4	403.2	437.1	471.0	467.3
110°	322.7	359.9	397.2	434.5	471.8	494.7	503.3	511.9	520.6	529.2	526.2



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	553.5	561.4	569.3	577.1	585.0	589.0	588.8	588.5	588.4	588.2	585.4
115°	689.8	688.8	687.8	686.7	685.7	683.9	681.3	678.6	676.1	673.5	671.2
117.5°	766.4	766.2	766.0	765.8	765.6	764.4	762.3	760.2	758.1	756.1	754.9
120°	818.9	818.9	818.9	818.9	818.9	817.9	815.8	813.7	811.6	809.5	808.8
122.5°	870.6	870.4	870.1	869.9	869.7	868.9	867.5	866.0	864.5	863.0	862.0
125°	943.3	942.8	942.3	941.7	941.2	940.7	940.2	939.7	939.2	938.6	937.6
127.5°	1013.2	1013.8	1014.3	1014.8	1015.3	1015.1	1014.3	1013.5	1012.7	1011.8	1010.6
130°	1058.3	1058.8	1059.3	1059.9	1060.4	1060.2	1059.0	1058.0	1057.0	1055.9	1054.9
132.5°	1099.5	1100.3	1101.1	1101.8	1102.5	1102.4	1101.4	1100.2	1099.2	1098.2	1097.3
135°	1162.8	1163.5	1164.3	1165.1	1165.9	1165.9	1165.1	1164.3	1163.5	1162.8	1161.6
137.5°	1222.0	1222.6	1223.1	1223.7	1224.2	1223.8	1222.5	1221.3	1220.0	1218.8	1218.2
140°	1257.8	1258.3	1258.8	1259.3	1259.8	1259.6	1258.5	1257.5	1256.5	1255.4	1254.7
142.5°	1290.6	1291.3	1292.0	1292.8	1293.5	1293.4	1292.6	1291.8	1291.0	1290.1	1289.4
145°	1341.0	1341.0	1341.0	1341.0	1341.0	1340.8	1340.3	1339.8	1339.2	1338.7	1338.2
147.5°	1378.6	1379.8	1381.0	1382.2	1383.4	1383.7	1383.2	1382.7	1382.2	1381.6	1381.1
150°	1406.7	1407.5	1408.4	1409.1	1409.9	1410.0	1409.5	1409.0	1408.5	1408.0	1407.4
152.5°	1429.3	1430.5	1431.7	1432.9	1434.1	1434.2	1433.3	1432.3	1431.4	1430.5	1430.2
155°	1460.8	1462.3	1463.9	1465.4	1466.9	1467.1	1465.8	1464.5	1463.2	1461.9	1461.7
157.5°	1487.2	1489.2	1491.3	1493.4	1495.4	1495.6	1494.0	1492.5	1491.0	1489.3	1489.7
160°	1504.1	1505.9	1507.8	1509.6	1511.5	1511.6	1510.0	1508.4	1506.9	1505.3	1505.6
162.5°	1520.0	1521.7	1523.3	1524.9	1526.5	1526.5	1524.7	1523.0	1521.2	1519.3	1519.6
165°	1539.3	1541.2	1543.0	1544.8	1546.6	1546.5	1544.4	1542.4	1540.2	1538.1	1538.4
167.5°	1553.2	1555.3	1557.3	1559.4	1561.6	1561.6	1559.4	1557.3	1555.3	1553.2	1553.2
170°	1561.7	1563.7	1565.8	1567.9	1569.9	1569.9	1567.9	1565.8	1563.7	1561.7	1561.7
172.5°	1566.3	1568.6	1570.9	1573.2	1575.5	1575.6	1573.5	1571.5	1569.3	1567.2	1567.0
175°	1573.4	1575.5	1577.5	1579.6	1581.7	1581.9	1580.0	1578.2	1576.4	1574.5	1574.3
177.5°	1575.5	1577.5	1579.6	1581.8	1583.8	1584.0	1582.4	1580.6	1579.0	1577.3	1577.1
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	932.9	932.0	927.7	922.7	916.3	911.9	908.5	906.7	901.1	894.2	889.6
5°	990.6	979.0	966.6	951.5	937.6	923.3	914.4	903.9	891.2	876.9	866.8
7.5°	1052.3	1029.6	1005.0	979.8	954.7	932.3	912.5	895.5	875.3	854.7	840.3
10°	1099.6	1066.4	1032.0	996.7	964.6	934.5	911.3	888.5	864.1	840.5	822.7
12.5°	1142.7	1098.9	1059.2	1015.9	974.9	938.9	905.4	878.6	849.3	824.2	803.9
15°	1197.1	1152.3	1104.3	1038.5	984.0	938.4	897.8	862.5	827.0	796.1	776.3
17.5°	1248.0	1180.5	1116.1	1061.2	990.4	933.3	883.7	841.6	802.6	769.8	745.5
20°	1269.1	1203.8	1133.7	1063.7	994.1	930.3	872.6	826.2	785.6	748.4	726.0
22.5°	1281.7	1207.7	1134.0	1058.7	984.8	918.5	861.5	810.4	766.4	731.1	703.5
25°	1296.6	1208.3	1127.1	1052.9	977.4	905.4	837.8	783.7	736.1	698.5	669.1
27.5°	1306.3	1202.5	1106.5	1024.0	947.5	875.9	813.9	756.4	708.1	668.4	636.9
30°	1308.2	1197.9	1090.8	1001.4	923.6	857.9	792.1	737.2	686.2	644.0	614.6
32.5°	1310.6	1186.5	1069.4	974.5	894.9	829.8	770.2	717.7	665.4	623.9	593.9
35°	1300.4	1180.1	1037.0	928.0	848.3	785.2	731.4	683.1	631.7	591.4	560.9
37.5°	1256.5	1155.0	1003.4	875.5	792.1	733.8	689.9	647.8	600.7	557.2	528.5
40°	1212.2	1130.2	977.4	843.6	756.6	696.6	657.1	622.8	577.1	536.4	505.5
42.5°	1146.3	1096.5	952.7	810.2	716.3	658.5	625.3	593.0	553.0	511.7	482.6
45°	1025.4	1032.0	902.0	757.0	660.7	602.6	571.3	548.9	513.3	479.3	449.5
47.5°	873.7	935.2	842.5	700.2	602.0	547.4	520.1	500.5	476.6	443.1	416.0
50°	774.8	862.5	794.9	662.2	565.1	511.0	483.9	468.1	447.2	420.8	395.0
52.5°	683.5	777.8	737.3	619.8	525.2	475.6	449.2	436.2	419.6	394.9	371.4
55°	557.3	652.9	643.6	555.8	465.3	420.8	400.7	386.1	374.8	356.3	337.7
57.5°	450.8	541.4	546.2	484.6	412.5	368.6	351.3	340.2	332.9	318.9	301.7
60°	383.7	466.9	483.1	436.7	374.8	336.1	319.1	310.2	304.4	293.2	280.0
62.5°	328.0	398.8	417.2	383.7	338.6	302.4	289.1	280.5	276.6	266.9	255.3
65°	251.1	309.8	327.6	309.0	285.5	256.4	245.6	238.2	234.8	229.3	220.9
67.5°	188.7	231.7	251.2	238.0	229.5	211.2	204.3	200.4	197.2	193.6	186.4
70°	151.6	183.4	203.5	200.0	193.0	183.4	178.3	175.6	172.5	169.5	163.2
72.5°	121.9	143.7	162.6	164.4	158.6	156.7	152.3	151.2	149.3	145.6	142.2
75°	80.9	95.9	109.1	114.1	116.4	118.4	116.4	116.0	115.6	112.6	110.6
77.5°	53.0	61.1	69.4	78.0	81.6	84.2	84.8	86.2	85.2	83.6	82.7
80°	40.6	42.5	48.4	55.7	61.5	63.8	65.3	66.1	65.7	65.3	63.8
82.5°	29.5	31.1	33.8	39.0	43.8	47.8	48.7	48.5	49.4	49.6	48.4
85°	15.9	16.3	17.1	17.8	20.5	24.7	26.0	26.7	27.5	27.5	25.1
87.5°	9.2	8.3	8.2	7.6	8.0	7.8	9.1	10.1	11.0	10.3	10.8
90°	21.4	18.0	14.6	11.6	9.0	6.4	3.7	1.2	3.7	6.4	9.0
92.5°	24.9	22.4	19.8	18.9	19.6	20.4	21.1	21.8	21.1	20.4	19.6
95°	30.6	27.8	24.9	28.8	39.5	50.2	60.9	71.6	60.9	50.2	39.5
97.5°	75.3	94.1	112.9	124.6	129.5	134.2	139.1	143.8	139.1	134.2	129.5
100°	120.1	160.8	201.4	219.1	213.9	208.7	203.5	198.2	203.5	208.7	213.9
102.5°	166.0	210.5	254.9	275.3	271.5	267.7	264.0	260.2	264.0	267.7	271.5
105°	303.9	327.3	350.8	361.1	358.2	355.4	352.5	349.6	352.5	355.4	358.2
107.5°	463.5	459.9	456.2	453.1	450.8	448.6	446.3	443.9	446.3	448.6	450.8
110°	523.4	520.6	517.7	515.2	513.1	511.0	509.0	506.9	509.0	511.0	513.1



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	582.6	579.7	576.8	574.4	572.6	570.7	568.8	566.9	568.8	570.7	572.6
115°	668.7	666.4	664.1	662.1	660.6	658.9	657.4	655.9	657.4	658.9	660.6
117.5°	753.7	752.5	751.2	749.7	747.8	745.8	743.9	741.9	743.9	745.8	747.8
120°	808.0	807.2	806.5	804.9	802.5	800.2	797.8	795.5	797.8	800.2	802.5
122.5°	861.1	860.1	859.1	857.7	855.7	853.7	851.8	849.9	851.8	853.7	855.7
125°	936.5	935.4	934.4	932.9	930.8	928.7	926.7	924.5	926.7	928.7	930.8
127.5°	1009.4	1008.0	1006.8	1005.1	1003.1	1001.0	998.9	996.8	998.9	1001.0	1003.1
130°	1053.9	1052.8	1051.8	1050.2	1048.1	1046.0	1044.0	1041.9	1044.0	1046.0	1048.1
132.5°	1096.5	1095.7	1094.8	1093.4	1091.3	1089.2	1087.1	1085.0	1087.1	1089.2	1091.3
135°	1160.6	1159.6	1158.5	1157.2	1155.7	1154.1	1152.6	1150.9	1152.6	1154.1	1155.7
137.5°	1217.7	1217.1	1216.5	1215.3	1213.3	1211.2	1209.3	1207.3	1209.3	1211.2	1213.3
140°	1253.8	1253.0	1252.2	1251.1	1249.5	1248.0	1246.4	1244.9	1246.4	1248.0	1249.5
142.5°	1288.6	1287.8	1287.0	1285.9	1284.2	1282.7	1281.1	1279.6	1281.1	1282.7	1284.2
145°	1337.7	1337.2	1336.7	1335.4	1333.6	1331.8	1330.0	1328.2	1330.0	1331.8	1333.6
147.5°	1380.6	1380.1	1379.6	1378.7	1377.5	1376.3	1375.1	1373.9	1375.1	1376.3	1377.5
150°	1406.8	1406.3	1405.8	1405.2	1404.4	1403.6	1402.8	1402.1	1402.8	1403.6	1404.4
152.5°	1429.9	1429.5	1429.2	1428.9	1428.5	1428.2	1427.7	1427.4	1427.7	1428.2	1428.5
155°	1461.4	1461.1	1460.9	1461.0	1461.5	1462.0	1462.6	1463.1	1462.6	1462.0	1461.5
157.5°	1489.9	1490.2	1490.4	1490.6	1490.6	1490.7	1490.7	1490.8	1490.7	1490.7	1490.6
160°	1505.8	1506.1	1506.3	1506.6	1506.9	1507.1	1507.4	1507.6	1507.4	1507.1	1506.9
162.5°	1519.9	1520.1	1520.5	1520.9	1521.6	1522.3	1523.0	1523.6	1523.0	1522.3	1521.6
165°	1538.6	1538.9	1539.2	1539.7	1540.5	1541.3	1542.1	1542.9	1542.1	1541.3	1540.5
167.5°	1553.2	1553.2	1553.2	1553.7	1554.8	1555.8	1556.8	1557.9	1556.8	1555.8	1554.8
170°	1561.7	1561.7	1561.7	1562.2	1563.2	1564.3	1565.3	1566.3	1565.3	1564.3	1563.2
172.5°	1566.8	1566.6	1566.4	1566.9	1568.2	1569.4	1570.7	1572.0	1570.7	1569.4	1568.2
175°	1574.0	1573.8	1573.5	1574.0	1575.3	1576.6	1577.9	1579.2	1577.9	1576.6	1575.3
177.5°	1576.9	1576.7	1576.5	1576.9	1578.0	1579.0	1580.0	1581.1	1580.0	1579.0	1578.0
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	888.1	884.0	881.3	875.0	871.1	866.8	862.4	865.2	864.8	864.5	864.5
5°	858.3	849.4	841.3	830.8	824.3	816.2	809.9	809.2	810.7	805.3	802.2
7.5°	828.8	816.6	805.1	793.6	781.3	771.5	765.5	762.7	758.7	755.4	751.8
10°	808.0	793.8	782.4	768.2	755.1	743.5	736.1	731.0	728.3	725.6	720.6
12.5°	786.7	772.6	758.3	742.1	729.6	716.2	710.7	705.1	699.8	696.8	689.9
15°	755.4	737.2	722.2	705.1	691.3	678.0	670.3	659.1	657.5	653.7	646.7
17.5°	724.1	704.4	683.6	671.0	655.2	641.6	629.8	626.0	614.9	610.8	604.7
20°	699.3	681.2	665.3	648.6	625.8	613.1	603.8	598.7	589.9	584.4	580.6
22.5°	678.0	659.4	641.2	621.8	602.9	588.7	581.8	574.0	569.2	561.6	557.3
25°	647.5	627.4	605.3	584.4	570.9	560.1	549.3	542.3	535.3	531.8	524.1
27.5°	612.1	591.1	570.5	554.6	538.0	527.3	517.5	511.3	502.9	497.1	492.8
30°	592.6	567.8	550.1	535.7	514.4	504.4	497.1	489.3	483.1	477.0	472.6
32.5°	570.0	547.3	530.5	512.8	496.4	485.5	475.9	469.2	463.9	458.1	453.8
35°	534.5	515.6	498.2	480.4	468.4	457.2	446.0	440.2	435.2	429.7	425.9
37.5°	502.5	484.8	468.3	451.4	436.6	427.4	418.4	413.9	407.2	403.5	399.6
40°	482.7	465.3	447.6	431.3	415.8	408.9	400.7	394.2	388.0	385.3	381.0
42.5°	461.1	443.6	428.7	411.1	398.5	389.0	381.5	374.4	369.7	365.8	363.3
45°	429.0	413.4	398.8	381.4	369.4	361.2	352.7	346.2	341.9	339.2	335.0
47.5°	397.8	382.3	367.4	352.2	340.6	331.3	322.9	318.2	312.7	309.3	306.4
50°	375.2	361.2	345.4	331.4	319.9	310.6	303.7	297.8	292.8	288.5	286.6
52.5°	354.5	339.6	325.9	313.0	300.7	290.1	283.9	277.7	274.0	269.0	266.8
55°	320.2	306.0	294.4	281.6	269.6	260.7	253.0	247.5	243.7	238.2	235.2
57.5°	288.1	275.3	261.5	250.4	238.0	230.6	224.1	216.7	212.1	207.8	204.8
60°	266.5	251.8	239.8	229.3	218.5	208.8	203.1	197.2	192.3	187.9	185.3
62.5°	243.9	231.1	219.7	208.3	198.4	190.0	183.3	178.3	174.0	171.3	168.5
65°	209.2	199.2	187.6	178.3	169.1	162.9	157.4	153.2	150.1	148.1	145.8
67.5°	177.4	167.6	157.5	148.3	142.2	137.4	133.9	130.3	128.8	126.2	124.7
70°	156.6	146.6	137.7	130.8	124.5	121.1	118.8	116.0	114.5	111.4	109.9
72.5°	134.1	126.8	120.4	114.6	109.7	106.5	103.6	100.3	97.8	94.4	92.8
75°	105.6	99.1	94.0	90.1	87.1	82.8	78.6	75.0	73.9	72.7	72.3
77.5°	78.2	74.0	70.4	67.2	63.3	60.2	59.3	58.5	58.3	57.7	57.7
80°	61.5	57.7	54.9	51.1	48.8	48.8	48.8	48.0	48.4	48.4	48.4
82.5°	45.7	42.1	40.7	39.3	38.9	39.2	39.2	39.3	39.1	39.7	39.4
85°	23.6	23.9	24.7	24.3	24.7	24.7	25.5	25.1	25.5	24.7	25.5
87.5°	11.0	12.5	13.5	14.4	15.5	15.9	16.4	16.6	17.1	17.3	17.5
90°	11.6	14.6	18.0	21.4	24.7	28.2	29.2	30.2	31.3	32.3	33.1
92.5°	18.9	19.8	22.4	24.9	27.5	30.0	31.7	33.3	35.0	36.8	37.7
95°	28.8	24.9	27.8	30.6	33.5	36.4	38.2	40.0	41.8	43.6	44.5
97.5°	124.6	112.9	94.1	75.3	56.6	37.8	39.9	41.9	44.0	46.2	47.3
100°	219.1	201.4	160.8	120.1	79.4	38.7	40.8	42.9	44.9	47.1	48.3
102.5°	275.3	254.9	210.5	166.0	121.6	77.2	70.7	64.2	57.8	51.3	48.4
105°	361.1	350.8	327.3	303.9	280.4	256.9	210.8	164.6	118.5	72.3	49.6
107.5°	453.1	456.2	459.9	463.5	467.3	471.0	437.1	403.2	369.4	335.6	301.2
110°	515.2	517.7	520.6	523.4	526.2	529.2	520.6	511.9	503.3	494.7	471.8



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	574.4	576.8	579.7	582.6	585.4	588.2	588.4	588.5	588.8	589.0	585.0
115°	662.1	664.1	666.4	668.7	671.2	673.5	676.1	678.6	681.3	683.9	685.7
117.5°	749.7	751.2	752.5	753.7	754.9	756.1	758.1	760.2	762.3	764.4	765.6
120°	804.9	806.5	807.2	808.0	808.8	809.5	811.6	813.7	815.8	817.9	818.9
122.5°	857.7	859.1	860.1	861.1	862.0	863.0	864.5	866.0	867.5	868.9	869.7
125°	932.9	934.4	935.4	936.5	937.6	938.6	939.2	939.7	940.2	940.7	941.2
127.5°	1005.1	1006.8	1008.0	1009.4	1010.6	1011.8	1012.7	1013.5	1014.3	1015.1	1015.3
130°	1050.2	1051.8	1052.8	1053.9	1054.9	1055.9	1057.0	1058.0	1059.0	1060.2	1060.4
132.5°	1093.4	1094.8	1095.7	1096.5	1097.3	1098.2	1099.2	1100.2	1101.4	1102.4	1102.5
135°	1157.2	1158.5	1159.6	1160.6	1161.6	1162.8	1163.5	1164.3	1165.1	1165.9	1165.9
137.5°	1215.3	1216.5	1217.1	1217.7	1218.2	1218.8	1220.0	1221.3	1222.5	1223.8	1224.2
140°	1251.1	1252.2	1253.0	1253.8	1254.7	1255.4	1256.5	1257.5	1258.5	1259.6	1259.8
142.5°	1285.9	1287.0	1287.8	1288.6	1289.4	1290.1	1291.0	1291.8	1292.6	1293.4	1293.5
145°	1335.4	1336.7	1337.2	1337.7	1338.2	1338.7	1339.2	1339.8	1340.3	1340.8	1341.0
147.5°	1378.7	1379.6	1380.1	1380.6	1381.1	1381.6	1382.2	1382.7	1383.2	1383.7	1383.4
150°	1405.2	1405.8	1406.3	1406.8	1407.4	1408.0	1408.5	1409.0	1409.5	1410.0	1409.9
152.5°	1428.9	1429.2	1429.5	1429.9	1430.2	1430.5	1431.4	1432.3	1433.3	1434.2	1434.1
155°	1461.0	1460.9	1461.1	1461.4	1461.7	1461.9	1463.2	1464.5	1465.8	1467.1	1466.9
157.5°	1490.6	1490.4	1490.2	1489.9	1489.7	1489.3	1491.0	1492.5	1494.0	1495.6	1495.4
160°	1506.6	1506.3	1506.1	1505.8	1505.6	1505.3	1506.9	1508.4	1510.0	1511.6	1511.5
162.5°	1520.9	1520.5	1520.1	1519.9	1519.6	1519.3	1521.2	1523.0	1524.7	1526.5	1526.5
165°	1539.7	1539.2	1538.9	1538.6	1538.4	1538.1	1540.2	1542.4	1544.4	1546.5	1546.6
167.5°	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1555.3	1557.3	1559.4	1561.6	1561.6
170°	1562.2	1561.7	1561.7	1561.7	1561.7	1561.7	1563.7	1565.8	1567.9	1569.9	1569.9
172.5°	1566.9	1566.4	1566.6	1566.8	1567.0	1567.2	1569.3	1571.5	1573.5	1575.6	1575.5
175°	1574.0	1573.5	1573.8	1574.0	1574.3	1574.5	1576.4	1578.2	1580.0	1581.9	1581.7
177.5°	1576.9	1576.5	1576.7	1576.9	1577.1	1577.3	1579.0	1580.6	1582.4	1584.0	1583.8
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	860.8	860.5	860.8	859.6	860.8	860.5	860.8	864.5	864.5	864.8	865.2
5°	801.0	800.6	799.5	796.1	799.5	800.6	801.0	802.2	805.3	810.7	809.2
7.5°	748.8	748.3	744.9	745.0	744.9	748.3	748.8	751.8	755.4	758.7	762.7
10°	717.9	718.3	713.7	710.9	713.7	718.3	717.9	720.6	725.6	728.3	731.0
12.5°	687.9	686.1	682.4	679.3	682.4	686.1	687.9	689.9	696.8	699.8	705.1
15°	648.2	644.4	635.1	635.9	635.1	644.4	648.2	646.7	653.7	657.5	659.1
17.5°	601.6	598.7	598.6	593.2	598.6	598.7	601.6	604.7	610.8	614.9	626.0
20°	574.4	572.5	573.2	567.8	573.2	572.5	574.4	580.6	584.4	589.9	598.7
22.5°	553.0	551.1	547.9	546.1	547.9	551.1	553.0	557.3	561.6	569.2	574.0
25°	521.8	518.7	515.6	517.6	515.6	518.7	521.8	524.1	531.8	535.3	542.3
27.5°	490.5	488.2	485.1	484.7	485.1	488.2	490.5	492.8	497.1	502.9	511.3
30°	470.7	468.4	466.9	464.9	466.9	468.4	470.7	472.6	477.0	483.1	489.3
32.5°	450.6	450.2	447.4	447.0	447.4	450.2	450.6	453.8	458.1	463.9	469.2
35°	424.3	422.0	421.2	421.6	421.2	422.0	424.3	425.9	429.7	435.2	440.2
37.5°	399.3	396.3	394.9	393.4	394.9	396.3	399.3	399.6	403.5	407.2	413.9
40°	381.4	378.3	377.5	376.8	377.5	378.3	381.4	381.0	385.3	388.0	394.2
42.5°	361.2	360.0	359.6	358.2	359.6	360.0	361.2	363.3	365.8	369.7	374.4
45°	333.8	333.5	331.1	331.8	331.1	333.5	333.8	335.0	339.2	341.9	346.2
47.5°	304.9	303.2	301.5	302.7	301.5	303.2	304.9	306.4	309.3	312.7	318.2
50°	285.1	284.3	280.8	281.6	280.8	284.3	285.1	286.6	288.5	292.8	297.8
52.5°	265.3	262.4	261.1	260.5	261.1	262.4	265.3	266.8	269.0	274.0	277.7
55°	232.5	228.9	227.4	226.6	227.4	228.9	232.5	235.2	238.2	243.7	247.5
57.5°	200.3	199.3	198.1	198.9	198.1	199.3	200.3	204.8	207.8	212.1	216.7
60°	181.4	181.4	181.4	181.1	181.4	181.4	181.4	185.3	187.9	192.3	197.2
62.5°	166.8	165.9	165.6	166.1	165.6	165.9	166.8	168.5	171.3	174.0	178.3
65°	144.6	144.3	142.7	142.4	142.7	144.3	144.6	145.8	148.1	150.1	153.2
67.5°	123.7	122.3	121.9	121.3	121.9	122.3	123.7	124.7	126.2	128.8	130.3
70°	108.0	107.1	104.8	105.2	104.8	107.1	108.0	109.9	111.4	114.5	116.0
72.5°	90.9	90.1	89.7	89.1	89.7	90.1	90.9	92.8	94.4	97.8	100.3
75°	71.9	71.6	71.2	72.7	71.2	71.6	71.9	72.3	72.7	73.9	75.0
77.5°	57.7	57.7	57.9	57.3	57.9	57.7	57.7	57.7	57.7	58.3	58.5
80°	48.4	48.4	48.0	48.0	48.0	48.4	48.4	48.4	48.4	48.4	48.0
82.5°	38.8	39.1	39.3	38.7	39.3	39.1	38.8	39.4	39.7	39.1	39.3
85°	25.5	25.1	26.0	25.5	26.0	25.1	25.5	25.5	24.7	25.5	25.1
87.5°	18.2	17.7	17.8	18.2	17.8	17.7	18.2	17.5	17.3	17.1	16.6
90°	33.6	34.1	34.6	35.2	34.6	34.1	33.6	33.1	32.3	31.3	30.2
92.5°	38.0	38.4	38.7	39.0	38.7	38.4	38.0	37.7	36.8	35.0	33.3
95°	44.5	44.5	44.5	44.5	44.5	44.5	44.5	44.5	43.6	41.8	40.0
97.5°	47.6	47.9	48.1	48.4	48.1	47.9	47.6	47.3	46.2	44.0	41.9
100°	48.5	48.8	49.0	49.3	49.0	48.8	48.5	48.3	47.1	44.9	42.9
102.5°	48.8	49.3	49.8	50.2	49.8	49.3	48.8	48.4	51.3	57.8	64.2
105°	50.1	50.6	51.1	51.6	51.1	50.6	50.1	49.6	72.3	118.5	164.6
107.5°	266.5	231.7	196.9	162.2	196.9	231.7	266.5	301.2	335.6	369.4	403.2
110°	434.5	397.2	359.9	322.7	359.9	397.2	434.5	471.8	494.7	503.3	511.9



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	577.1	569.3	561.4	553.5	561.4	569.3	577.1	585.0	589.0	588.8	588.5
115°	686.7	687.8	688.8	689.8	688.8	687.8	686.7	685.7	683.9	681.3	678.6
117.5°	765.8	766.0	766.2	766.4	766.2	766.0	765.8	765.6	764.4	762.3	760.2
120°	818.9	818.9	818.9	818.9	818.9	818.9	818.9	818.9	817.9	815.8	813.7
122.5°	869.9	870.1	870.4	870.6	870.4	870.1	869.9	869.7	868.9	867.5	866.0
125°	941.7	942.3	942.8	943.3	942.8	942.3	941.7	941.2	940.7	940.2	939.7
127.5°	1014.8	1014.3	1013.8	1013.2	1013.8	1014.3	1014.8	1015.3	1015.1	1014.3	1013.5
130°	1059.9	1059.3	1058.8	1058.3	1058.8	1059.3	1059.9	1060.4	1060.2	1059.0	1058.0
132.5°	1101.8	1101.1	1100.3	1099.5	1100.3	1101.1	1101.8	1102.5	1102.4	1101.4	1100.2
135°	1165.1	1164.3	1163.5	1162.8	1163.5	1164.3	1165.1	1165.9	1165.9	1165.1	1164.3
137.5°	1223.7	1223.1	1222.6	1222.0	1222.6	1223.1	1223.7	1224.2	1223.8	1222.5	1221.3
140°	1259.3	1258.8	1258.3	1257.8	1258.3	1258.8	1259.3	1259.8	1259.6	1258.5	1257.5
142.5°	1292.8	1292.0	1291.3	1290.6	1291.3	1292.0	1292.8	1293.5	1293.4	1292.6	1291.8
145°	1341.0	1341.0	1341.0	1341.0	1341.0	1341.0	1341.0	1341.0	1340.8	1340.3	1339.8
147.5°	1382.2	1381.0	1379.8	1378.6	1379.8	1381.0	1382.2	1383.4	1383.7	1383.2	1382.7
150°	1409.1	1408.4	1407.5	1406.7	1407.5	1408.4	1409.1	1409.9	1410.0	1409.5	1409.0
152.5°	1432.9	1431.7	1430.5	1429.3	1430.5	1431.7	1432.9	1434.1	1434.2	1433.3	1432.3
155°	1465.4	1463.9	1462.3	1460.8	1462.3	1463.9	1465.4	1466.9	1467.1	1465.8	1464.5
157.5°	1493.4	1491.3	1489.2	1487.2	1489.2	1491.3	1493.4	1495.4	1495.6	1494.0	1492.5
160°	1509.6	1507.8	1505.9	1504.1	1505.9	1507.8	1509.6	1511.5	1511.6	1510.0	1508.4
162.5°	1524.9	1523.3	1521.7	1520.0	1521.7	1523.3	1524.9	1526.5	1526.5	1524.7	1523.0
165°	1544.8	1543.0	1541.2	1539.3	1541.2	1543.0	1544.8	1546.6	1546.5	1544.4	1542.4
167.5°	1559.4	1557.3	1555.3	1553.2	1555.3	1557.3	1559.4	1561.6	1561.6	1559.4	1557.3
170°	1567.9	1565.8	1563.7	1561.7	1563.7	1565.8	1567.9	1569.9	1569.9	1567.9	1565.8
172.5°	1573.2	1570.9	1568.6	1566.3	1568.6	1570.9	1573.2	1575.5	1575.6	1573.5	1571.5
175°	1579.6	1577.5	1575.5	1573.4	1575.5	1577.5	1579.6	1581.7	1581.9	1580.0	1578.2
177.5°	1581.8	1579.6	1577.5	1575.5	1577.5	1579.6	1581.8	1583.8	1584.0	1582.4	1580.6
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	862.4	866.8	871.1	875.0	881.3	884.0	888.1	889.6	894.2	901.1	906.7
5°	809.9	816.2	824.3	830.8	841.3	849.4	858.3	866.8	876.9	891.2	903.9
7.5°	765.5	771.5	781.3	793.6	805.1	816.6	828.8	840.3	854.7	875.3	895.5
10°	736.1	743.5	755.1	768.2	782.4	793.8	808.0	822.7	840.5	864.1	888.5
12.5°	710.7	716.2	729.6	742.1	758.3	772.6	786.7	803.9	824.2	849.3	878.6
15°	670.3	678.0	691.3	705.1	722.2	737.2	755.4	776.3	796.1	827.0	862.5
17.5°	629.8	641.6	655.2	671.0	683.6	704.4	724.1	745.5	769.8	802.6	841.6
20°	603.8	613.1	625.8	648.6	665.3	681.2	699.3	726.0	748.4	785.6	826.2
22.5°	581.8	588.7	602.9	621.8	641.2	659.4	678.0	703.5	731.1	766.4	810.4
25°	549.3	560.1	570.9	584.4	605.3	627.4	647.5	669.1	698.5	736.1	783.7
27.5°	517.5	527.3	538.0	554.6	570.5	591.1	612.1	636.9	668.4	708.1	756.4
30°	497.1	504.4	514.4	535.7	550.1	567.8	592.6	614.6	644.0	686.2	737.2
32.5°	475.9	485.5	496.4	512.8	530.5	547.3	570.0	593.9	623.9	665.4	717.7
35°	446.0	457.2	468.4	480.4	498.2	515.6	534.5	560.9	591.4	631.7	683.1
37.5°	418.4	427.4	436.6	451.4	468.3	484.8	502.5	528.5	557.2	600.7	647.8
40°	400.7	408.9	415.8	431.3	447.6	465.3	482.7	505.5	536.4	577.1	622.8
42.5°	381.5	389.0	398.5	411.1	428.7	443.6	461.1	482.6	511.7	553.0	593.0
45°	352.7	361.2	369.4	381.4	398.8	413.4	429.0	449.5	479.3	513.3	548.9
47.5°	322.9	331.3	340.6	352.2	367.4	382.3	397.8	416.0	443.1	476.6	500.5
50°	303.7	310.6	319.9	331.4	345.4	361.2	375.2	395.0	420.8	447.2	468.1
52.5°	283.9	290.1	300.7	313.0	325.9	339.6	354.5	371.4	394.9	419.6	436.2
55°	253.0	260.7	269.6	281.6	294.4	306.0	320.2	337.7	356.3	374.8	386.1
57.5°	224.1	230.6	238.0	250.4	261.5	275.3	288.1	301.7	318.9	332.9	340.2
60°	203.1	208.8	218.5	229.3	239.8	251.8	266.5	280.0	293.2	304.4	310.2
62.5°	183.3	190.0	198.4	208.3	219.7	231.1	243.9	255.3	266.9	276.6	280.5
65°	157.4	162.9	169.1	178.3	187.6	199.2	209.2	220.9	229.3	234.8	238.2
67.5°	133.9	137.4	142.2	148.3	157.5	167.6	177.4	186.4	193.6	197.2	200.4
70°	118.8	121.1	124.5	130.8	137.7	146.6	156.6	163.2	169.5	172.5	175.6
72.5°	103.6	106.5	109.7	114.6	120.4	126.8	134.1	142.2	145.6	149.3	151.2
75°	78.6	82.8	87.1	90.1	94.0	99.1	105.6	110.6	112.6	115.6	116.0
77.5°	59.3	60.2	63.3	67.2	70.4	74.0	78.2	82.7	83.6	85.2	86.2
80°	48.8	48.8	48.8	51.1	54.9	57.7	61.5	63.8	65.3	65.7	66.1
82.5°	39.2	39.2	38.9	39.3	40.7	42.1	45.7	48.4	49.6	49.4	48.5
85°	25.5	24.7	24.7	24.3	24.7	23.9	23.6	25.1	27.5	27.5	26.7
87.5°	16.4	15.9	15.5	14.4	13.5	12.5	11.0	10.8	10.3	11.0	10.1
90°	29.2	28.2	24.7	21.4	18.0	14.6	11.6	9.0	6.4	3.7	1.2
92.5°	31.7	30.0	27.5	24.9	22.4	19.8	18.9	19.6	20.4	21.1	21.8
95°	38.2	36.4	33.5	30.6	27.8	24.9	28.8	39.5	50.2	60.9	71.6
97.5°	39.9	37.8	56.6	75.3	94.1	112.9	124.6	129.5	134.2	139.1	143.8
100°	40.8	38.7	79.4	120.1	160.8	201.4	219.1	213.9	208.7	203.5	198.2
102.5°	70.7	77.2	121.6	166.0	210.5	254.9	275.3	271.5	267.7	264.0	260.2
105°	210.8	256.9	280.4	303.9	327.3	350.8	361.1	358.2	355.4	352.5	349.6
107.5°	437.1	471.0	467.3	463.5	459.9	456.2	453.1	450.8	448.6	446.3	443.9
110°	520.6	529.2	526.2	523.4	520.6	517.7	515.2	513.1	511.0	509.0	506.9



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	588.4	588.2	585.4	582.6	579.7	576.8	574.4	572.6	570.7	568.8	566.9
115°	676.1	673.5	671.2	668.7	666.4	664.1	662.1	660.6	658.9	657.4	655.9
117.5°	758.1	756.1	754.9	753.7	752.5	751.2	749.7	747.8	745.8	743.9	741.9
120°	811.6	809.5	808.8	808.0	807.2	806.5	804.9	802.5	800.2	797.8	795.5
122.5°	864.5	863.0	862.0	861.1	860.1	859.1	857.7	855.7	853.7	851.8	849.9
125°	939.2	938.6	937.6	936.5	935.4	934.4	932.9	930.8	928.7	926.7	924.5
127.5°	1012.7	1011.8	1010.6	1009.4	1008.0	1006.8	1005.1	1003.1	1001.0	998.9	996.8
130°	1057.0	1055.9	1054.9	1053.9	1052.8	1051.8	1050.2	1048.1	1046.0	1044.0	1041.9
132.5°	1099.2	1098.2	1097.3	1096.5	1095.7	1094.8	1093.4	1091.3	1089.2	1087.1	1085.0
135°	1163.5	1162.8	1161.6	1160.6	1159.6	1158.5	1157.2	1155.7	1154.1	1152.6	1150.9
137.5°	1220.0	1218.8	1218.2	1217.7	1217.1	1216.5	1215.3	1213.3	1211.2	1209.3	1207.3
140°	1256.5	1255.4	1254.7	1253.8	1253.0	1252.2	1251.1	1249.5	1248.0	1246.4	1244.9
142.5°	1291.0	1290.1	1289.4	1288.6	1287.8	1287.0	1285.9	1284.2	1282.7	1281.1	1279.6
145°	1339.2	1338.7	1338.2	1337.7	1337.2	1336.7	1335.4	1333.6	1331.8	1330.0	1328.2
147.5°	1382.2	1381.6	1381.1	1380.6	1380.1	1379.6	1378.7	1377.5	1376.3	1375.1	1373.9
150°	1408.5	1408.0	1407.4	1406.8	1406.3	1405.8	1405.2	1404.4	1403.6	1402.8	1402.1
152.5°	1431.4	1430.5	1430.2	1429.9	1429.5	1429.2	1428.9	1428.5	1428.2	1427.7	1427.4
155°	1463.2	1461.9	1461.7	1461.4	1461.1	1460.9	1461.0	1461.5	1462.0	1462.6	1463.1
157.5°	1491.0	1489.3	1489.7	1489.9	1490.2	1490.4	1490.6	1490.6	1490.7	1490.7	1490.8
160°	1506.9	1505.3	1505.6	1505.8	1506.1	1506.3	1506.6	1506.9	1507.1	1507.4	1507.6
162.5°	1521.2	1519.3	1519.6	1519.9	1520.1	1520.5	1520.9	1521.6	1522.3	1523.0	1523.6
165°	1540.2	1538.1	1538.4	1538.6	1538.9	1539.2	1539.7	1540.5	1541.3	1542.1	1542.9
167.5°	1555.3	1553.2	1553.2	1553.2	1553.2	1553.2	1553.7	1554.8	1555.8	1556.8	1557.9
170°	1563.7	1561.7	1561.7	1561.7	1561.7	1561.7	1562.2	1563.2	1564.3	1565.3	1566.3
172.5°	1569.3	1567.2	1567.0	1566.8	1566.6	1566.4	1566.9	1568.2	1569.4	1570.7	1572.0
175°	1576.4	1574.5	1574.3	1574.0	1573.8	1573.5	1574.0	1575.3	1576.6	1577.9	1579.2
177.5°	1579.0	1577.3	1577.1	1576.9	1576.7	1576.5	1576.9	1578.0	1579.0	1580.0	1581.1
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	908.5	911.9	916.3	922.7	927.7	932.0	932.9	934.2	937.3	942.5	946.5
5°	914.4	923.3	937.6	951.5	966.6	979.0	990.6	998.8	1006.4	1022.7	1035.8
7.5°	912.5	932.3	954.7	979.8	1005.0	1029.6	1052.3	1072.7	1093.0	1116.6	1143.6
10°	911.3	934.5	964.6	996.7	1032.0	1066.4	1099.6	1125.6	1155.8	1182.9	1217.3
12.5°	905.4	938.9	974.9	1015.9	1059.2	1098.9	1142.7	1178.5	1212.9	1252.1	1292.1
15°	897.8	938.4	984.0	1038.5	1104.3	1152.3	1197.1	1259.4	1301.9	1344.5	1401.8
17.5°	883.7	933.3	990.4	1061.2	1116.1	1180.5	1248.0	1297.3	1354.5	1414.5	1466.3
20°	872.6	930.3	994.1	1063.7	1133.7	1203.8	1269.1	1327.9	1387.0	1456.3	1498.8
22.5°	861.5	918.5	984.8	1058.7	1134.0	1207.7	1281.7	1350.8	1417.3	1487.2	1541.6
25°	837.8	905.4	977.4	1052.9	1127.1	1208.3	1296.6	1373.5	1455.9	1527.8	1579.3
27.5°	813.9	875.9	947.5	1024.0	1106.5	1202.5	1306.3	1393.8	1476.3	1527.8	1544.0
30°	792.1	857.9	923.6	1001.4	1090.8	1197.9	1308.2	1408.4	1476.0	1498.4	1481.8
32.5°	770.2	829.8	894.9	974.5	1069.4	1186.5	1310.6	1399.7	1440.5	1423.3	1355.5
35°	731.4	785.2	848.3	928.0	1037.0	1180.1	1300.4	1360.8	1350.7	1253.9	1126.3
37.5°	689.9	733.8	792.1	875.5	1003.4	1155.0	1256.5	1265.4	1178.3	1029.9	882.4
40°	657.1	696.6	756.6	843.6	977.4	1130.2	1212.2	1176.3	1041.3	876.1	753.1
42.5°	625.3	658.5	716.3	810.2	952.7	1096.5	1146.3	1067.9	912.2	756.0	644.2
45°	571.3	602.6	660.7	757.0	902.0	1032.0	1025.4	889.3	733.4	607.6	514.8
47.5°	520.1	547.4	602.0	700.2	842.5	935.2	873.7	728.9	596.6	495.8	429.6
50°	483.9	511.0	565.1	662.2	794.9	862.5	774.8	635.1	514.0	430.5	377.9
52.5°	449.2	475.6	525.2	619.8	737.3	777.8	683.5	554.0	453.1	381.0	335.8
55°	400.7	420.8	465.3	555.8	643.6	652.9	557.3	449.1	365.9	315.6	284.7
57.5°	351.3	368.6	412.5	484.6	546.2	541.4	450.8	357.2	301.1	263.8	241.4
60°	319.1	336.1	374.8	436.7	483.1	466.9	383.7	308.3	260.3	232.9	215.1
62.5°	289.1	302.4	338.6	383.7	417.2	398.8	328.0	265.6	227.5	204.4	190.3
65°	245.6	256.4	285.5	309.0	327.6	309.8	251.1	207.7	180.3	164.0	154.3
67.5°	204.3	211.2	229.5	238.0	251.2	231.7	188.7	159.8	144.1	130.5	123.7
70°	178.3	183.4	193.0	200.0	203.5	183.4	151.6	130.4	117.2	107.6	103.3
72.5°	152.3	156.7	158.6	164.4	162.6	143.7	121.9	105.0	95.5	89.0	83.5
75°	116.4	118.4	116.4	114.1	109.1	95.9	80.9	72.3	65.3	62.3	60.4
77.5°	84.8	84.2	81.6	78.0	69.4	61.1	53.0	50.1	47.2	45.4	44.8
80°	65.3	63.8	61.5	55.7	48.4	42.5	40.6	38.7	37.6	35.5	35.2
82.5°	48.7	47.8	43.8	39.0	33.8	31.1	29.5	28.8	27.6	26.7	26.6
85°	26.0	24.7	20.5	17.8	17.1	16.3	15.9	15.9	14.3	13.9	13.9
87.5°	9.1	7.8	8.0	7.6	8.2	8.3	9.2	9.3	9.7	10.2	9.8
90°	3.7	6.4	9.0	11.6	14.6	18.0	21.4	24.7	28.2	29.2	30.2
92.5°	21.1	20.4	19.6	18.9	19.8	22.4	24.9	27.5	30.0	31.7	33.3
95°	60.9	50.2	39.5	28.8	24.9	27.8	30.6	33.5	36.4	38.2	40.0
97.5°	139.1	134.2	129.5	124.6	112.9	94.1	75.3	56.6	37.8	39.9	41.9
100°	203.5	208.7	213.9	219.1	201.4	160.8	120.1	79.4	38.7	40.8	42.9
102.5°	264.0	267.7	271.5	275.3	254.9	210.5	166.0	121.6	77.2	70.7	64.2
105°	352.5	355.4	358.2	361.1	350.8	327.3	303.9	280.4	256.9	210.8	164.6
107.5°	446.3	448.6	450.8	453.1	456.2	459.9	463.5	467.3	471.0	437.1	403.2
110°	509.0	511.0	513.1	515.2	517.7	520.6	523.4	526.2	529.2	520.6	511.9



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	568.8	570.7	572.6	574.4	576.8	579.7	582.6	585.4	588.2	588.4	588.5
115°	657.4	658.9	660.6	662.1	664.1	666.4	668.7	671.2	673.5	676.1	678.6
117.5°	743.9	745.8	747.8	749.7	751.2	752.5	753.7	754.9	756.1	758.1	760.2
120°	797.8	800.2	802.5	804.9	806.5	807.2	808.0	808.8	809.5	811.6	813.7
122.5°	851.8	853.7	855.7	857.7	859.1	860.1	861.1	862.0	863.0	864.5	866.0
125°	926.7	928.7	930.8	932.9	934.4	935.4	936.5	937.6	938.6	939.2	939.7
127.5°	998.9	1001.0	1003.1	1005.1	1006.8	1008.0	1009.4	1010.6	1011.8	1012.7	1013.5
130°	1044.0	1046.0	1048.1	1050.2	1051.8	1052.8	1053.9	1054.9	1055.9	1057.0	1058.0
132.5°	1087.1	1089.2	1091.3	1093.4	1094.8	1095.7	1096.5	1097.3	1098.2	1099.2	1100.2
135°	1152.6	1154.1	1155.7	1157.2	1158.5	1159.6	1160.6	1161.6	1162.8	1163.5	1164.3
137.5°	1209.3	1211.2	1213.3	1215.3	1216.5	1217.1	1217.7	1218.2	1218.8	1220.0	1221.3
140°	1246.4	1248.0	1249.5	1251.1	1252.2	1253.0	1253.8	1254.7	1255.4	1256.5	1257.5
142.5°	1281.1	1282.7	1284.2	1285.9	1287.0	1287.8	1288.6	1289.4	1290.1	1291.0	1291.8
145°	1330.0	1331.8	1333.6	1335.4	1336.7	1337.2	1337.7	1338.2	1338.7	1339.2	1339.8
147.5°	1375.1	1376.3	1377.5	1378.7	1379.6	1380.1	1380.6	1381.1	1381.6	1382.2	1382.7
150°	1402.8	1403.6	1404.4	1405.2	1405.8	1406.3	1406.8	1407.4	1408.0	1408.5	1409.0
152.5°	1427.7	1428.2	1428.5	1428.9	1429.2	1429.5	1429.9	1430.2	1430.5	1431.4	1432.3
155°	1462.6	1462.0	1461.5	1461.0	1460.9	1461.1	1461.4	1461.7	1461.9	1463.2	1464.5
157.5°	1490.7	1490.7	1490.6	1490.6	1490.4	1490.2	1489.9	1489.7	1489.3	1491.0	1492.5
160°	1507.4	1507.1	1506.9	1506.6	1506.3	1506.1	1505.8	1505.6	1505.3	1506.9	1508.4
162.5°	1523.0	1522.3	1521.6	1520.9	1520.5	1520.1	1519.9	1519.6	1519.3	1521.2	1523.0
165°	1542.1	1541.3	1540.5	1539.7	1539.2	1538.9	1538.6	1538.4	1538.1	1540.2	1542.4
167.5°	1556.8	1555.8	1554.8	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1555.3	1557.3
170°	1565.3	1564.3	1563.2	1562.2	1561.7	1561.7	1561.7	1561.7	1561.7	1563.7	1565.8
172.5°	1570.7	1569.4	1568.2	1566.9	1566.4	1566.6	1566.8	1567.0	1567.2	1569.3	1571.5
175°	1577.9	1576.6	1575.3	1574.0	1573.5	1573.8	1574.0	1574.3	1574.5	1576.4	1578.2
177.5°	1580.0	1579.0	1578.0	1576.9	1576.5	1576.7	1576.9	1577.1	1577.3	1579.0	1580.6
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	953.1	953.1	954.3	959.0	959.6	963.6	962.3
5°	1047.4	1054.8	1057.5	1069.1	1076.1	1079.1	1073.0
7.5°	1162.9	1183.6	1193.5	1205.6	1216.3	1219.6	1211.1
10°	1247.1	1268.7	1286.9	1298.1	1308.6	1315.5	1324.4
12.5°	1328.4	1355.0	1372.3	1388.2	1398.9	1407.8	1409.2
15°	1416.8	1457.0	1487.6	1510.1	1521.3	1527.1	1524.8
17.5°	1506.0	1543.3	1565.1	1587.9	1603.5	1604.3	1604.8
20°	1556.5	1592.9	1618.0	1635.0	1652.4	1651.6	1655.5
22.5°	1590.2	1618.8	1638.1	1650.4	1656.4	1653.5	1654.3
25°	1606.0	1614.5	1611.0	1591.2	1586.3	1568.1	1571.1
27.5°	1524.6	1484.4	1442.8	1389.2	1347.0	1313.2	1314.9
30°	1414.1	1342.9	1261.7	1193.7	1132.6	1115.5	1079.1
32.5°	1259.7	1153.0	1057.8	994.4	941.9	927.7	896.0
35°	997.9	894.2	796.4	737.6	714.4	682.0	681.6
37.5°	775.7	684.4	632.7	588.5	565.4	545.7	543.8
40°	652.6	581.4	542.3	510.6	487.8	473.0	469.6
42.5°	566.5	509.0	472.3	452.7	435.2	427.6	421.9
45°	462.6	423.9	398.4	380.6	372.4	366.7	363.6
47.5°	387.0	361.0	343.7	331.8	325.2	319.1	320.7
50°	345.8	324.6	311.7	300.5	295.5	291.2	291.6
52.5°	312.7	293.6	283.3	275.2	268.9	265.9	264.4
55°	265.4	253.4	242.9	237.1	233.6	229.3	228.2
57.5°	226.3	217.0	208.5	202.0	201.2	197.0	197.5
60°	200.4	192.6	185.6	182.2	179.5	176.0	177.1
62.5°	179.0	172.5	166.1	163.3	160.6	158.0	158.5
65°	146.6	140.4	136.5	135.0	133.8	132.7	131.5
67.5°	116.8	113.0	110.6	107.2	104.9	104.5	103.3
70°	98.3	93.2	89.0	84.7	83.5	83.1	83.5
72.5°	78.8	75.5	74.4	72.3	72.1	71.1	71.8
75°	59.2	58.1	57.3	55.7	55.7	55.7	55.7
77.5°	43.6	42.9	42.5	42.1	41.8	41.2	41.2
80°	34.0	33.6	32.9	32.9	32.5	32.9	32.5
82.5°	25.7	25.7	24.8	24.8	24.4	24.2	24.4
85°	13.1	12.7	13.5	12.7	13.1	12.4	13.1
87.5°	10.0	10.2	10.0	10.1	9.9	10.6	10.1
90°	31.3	32.3	33.1	33.6	34.1	34.6	35.2
92.5°	35.0	36.8	37.7	38.0	38.4	38.7	39.0
95°	41.8	43.6	44.5	44.5	44.5	44.5	44.5
97.5°	44.0	46.2	47.3	47.6	47.9	48.1	48.4
100°	44.9	47.1	48.3	48.5	48.8	49.0	49.3
102.5°	57.8	51.3	48.4	48.8	49.3	49.8	50.2
105°	118.5	72.3	49.6	50.1	50.6	51.1	51.6
107.5°	369.4	335.6	301.2	266.5	231.7	196.9	162.2
110°	503.3	494.7	471.8	434.5	397.2	359.9	322.7



TEST NUMBER: P332294-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	588.8	589.0	585.0	577.1	569.3	561.4	553.5
115°	681.3	683.9	685.7	686.7	687.8	688.8	689.8
117.5°	762.3	764.4	765.6	765.8	766.0	766.2	766.4
120°	815.8	817.9	818.9	818.9	818.9	818.9	818.9
122.5°	867.5	868.9	869.7	869.9	870.1	870.4	870.6
125°	940.2	940.7	941.2	941.7	942.3	942.8	943.3
127.5°	1014.3	1015.1	1015.3	1014.8	1014.3	1013.8	1013.2
130°	1059.0	1060.2	1060.4	1059.9	1059.3	1058.8	1058.3
132.5°	1101.4	1102.4	1102.5	1101.8	1101.1	1100.3	1099.5
135°	1165.1	1165.9	1165.9	1165.1	1164.3	1163.5	1162.8
137.5°	1222.5	1223.8	1224.2	1223.7	1223.1	1222.6	1222.0
140°	1258.5	1259.6	1259.8	1259.3	1258.8	1258.3	1257.8
142.5°	1292.6	1293.4	1293.5	1292.8	1292.0	1291.3	1290.6
145°	1340.3	1340.8	1341.0	1341.0	1341.0	1341.0	1341.0
147.5°	1383.2	1383.7	1383.4	1382.2	1381.0	1379.8	1378.6
150°	1409.5	1410.0	1409.9	1409.1	1408.4	1407.5	1406.7
152.5°	1433.3	1434.2	1434.1	1432.9	1431.7	1430.5	1429.3
155°	1465.8	1467.1	1466.9	1465.4	1463.9	1462.3	1460.8
157.5°	1494.0	1495.6	1495.4	1493.4	1491.3	1489.2	1487.2
160°	1510.0	1511.6	1511.5	1509.6	1507.8	1505.9	1504.1
162.5°	1524.7	1526.5	1526.5	1524.9	1523.3	1521.7	1520.0
165°	1544.4	1546.5	1546.6	1544.8	1543.0	1541.2	1539.3
167.5°	1559.4	1561.6	1561.6	1559.4	1557.3	1555.3	1553.2
170°	1567.9	1569.9	1569.9	1567.9	1565.8	1563.7	1561.7
172.5°	1573.5	1575.6	1575.5	1573.2	1570.9	1568.6	1566.3
175°	1580.0	1581.9	1581.7	1579.6	1577.5	1575.5	1573.4
177.5°	1582.4	1584.0	1583.8	1581.8	1579.6	1577.5	1575.5
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2

(END OF REPORT)