

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332297-840

Luminaire Tested: **S123RDIP-S560D1195U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332297-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1195U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6975.1 lumens
Efficiency: N/A
Efficacy: 141.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332297-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332297-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	26
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22
3	78	69	62	57	70	62	56	52	50	46	42	38	35	33	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	65	54	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	15
6	60	49	41	35	54	44	37	33	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	18	16	14	12
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10267	10267	10267
5°	10306	10164	10222
10°	10248	10037	10002
15°	10137	9802	9698
20°	9986	9507	9286
25°	9830	9178	8884
30°	9625	8797	8316
35°	9412	8418	7796
40°	9218	7967	7152
45°	8961	7524	6570
50°	8679	7021	5921
55°	8392	6446	5315
60°	8127	5828	4646
65°	7784	5163	3978
70°	7352	4334	3213
75°	6725	3410	3023
80°	5994	3025	2777
85°	5064	2668	2482



TEST NUMBER: P332297-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.3
10°-20°	249.2	3.6
20°-30°	358.8	5.1
30°-40°	404.2	5.8
40°-50°	386.7	5.5
50°-60°	316.7	4.5
60°-70°	213.7	3.1
70°-80°	107.5	1.5
80°-90°	32.8	0.5
90°-100°	57.4	0.8
100°-110°	273.6	3.9
110°-120°	657.3	9.4
120°-130°	837.0	12.0
130°-140°	894.3	12.8
140°-150°	836.3	12.0
150°-160°	674.6	9.7
160°-170°	435.4	6.2
170°-180°	150.0	2.2
0°-30°	697.6	10.0
0°-40°	1101.8	15.8
0°-60°	1805.2	25.9
0°-90°	2159.2	31.0
90°-120°	988.3	14.2
90°-150°	3555.9	51.0
90°-180°	4816.0	69.0
0°-180°	6975.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	954	954	954	954	954	
5°	954	950	941	947	946	90
15°	910	900	880	876	870	256
25°	828	808	773	757	748	381
35°	716	687	641	608	593	448
45°	589	552	494	452	432	454
55°	447	408	344	300	283	401
65°	306	262	203	166	156	302
75°	162	124	82	75	73	172
85°	41	25	22	20	20	46
90°	1	13	28	33	35	5
95°	72	27	36	44	44	88
105°	350	356	257	61	52	371
115°	656	663	674	685	690	647
125°	924	934	939	941	943	825
135°	1151	1158	1163	1166	1163	886
145°	1328	1336	1339	1341	1341	831
155°	1463	1461	1462	1467	1461	674
165°	1543	1539	1538	1547	1539	436
175°	1579	1574	1574	1582	1573	150
180°	1579	1579	1579	1579	1579	



TEST NUMBER: P332297-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	956.9	956.3	955.8	955.2	954.7	953.6	952.0	950.3	948.7	947.1	948.6
5°	953.8	953.0	952.1	951.3	950.4	949.0	946.8	944.8	942.7	940.7	942.2
7.5°	945.0	944.1	943.1	942.2	941.3	939.5	936.9	934.1	931.4	928.8	929.6
10°	937.6	936.3	935.1	933.9	932.8	930.6	927.6	924.4	921.3	918.3	918.4
12.5°	927.1	925.7	924.3	923.0	921.7	919.2	915.3	911.6	907.8	904.0	903.9
15°	909.7	907.9	905.9	904.0	902.2	898.8	894.0	889.2	884.3	879.6	878.7
17.5°	887.9	885.8	883.5	881.3	879.1	874.9	868.8	862.7	856.6	850.5	848.7
20°	871.8	869.1	866.4	863.5	860.8	856.2	849.6	843.1	836.6	830.0	827.8
22.5°	853.8	850.7	847.6	844.3	841.2	836.2	829.2	822.2	815.4	808.4	805.6
25°	827.7	823.4	819.1	814.9	810.5	804.5	796.5	788.6	780.7	772.8	769.2
27.5°	796.0	791.2	786.5	781.7	777.0	770.2	761.4	752.7	743.9	735.1	730.0
30°	774.4	769.2	764.1	758.9	753.8	746.3	736.7	727.1	717.4	707.8	702.0
32.5°	752.7	746.9	741.0	735.2	729.3	721.3	711.1	700.9	690.7	680.5	674.2
35°	716.3	710.1	704.0	697.8	691.6	683.2	672.5	661.9	651.2	640.6	633.1
37.5°	679.5	672.7	665.8	658.8	652.0	642.9	631.5	620.2	608.7	597.3	589.0
40°	656.0	648.4	640.9	633.3	625.7	615.8	603.7	591.5	579.3	567.0	558.1
42.5°	629.3	621.8	614.3	606.7	599.2	589.1	576.4	563.8	551.2	538.6	528.8
45°	588.7	581.0	573.2	565.5	557.7	547.2	534.0	520.8	507.6	494.3	484.5
47.5°	548.0	539.5	531.0	522.5	514.0	503.2	489.9	476.7	463.4	450.2	439.6
50°	518.3	510.2	502.1	494.0	485.9	474.9	461.0	447.2	433.2	419.3	408.6
52.5°	491.7	482.9	474.1	465.3	456.7	445.4	431.5	417.8	403.9	390.2	379.1
55°	447.2	438.7	430.3	421.8	413.4	401.9	387.3	372.7	358.1	343.5	333.5
57.5°	406.0	396.8	387.6	378.4	369.2	357.3	342.6	328.0	313.3	298.6	289.2
60°	377.5	368.1	358.6	349.1	339.7	327.8	313.6	299.3	285.0	270.7	261.5
62.5°	349.0	339.6	330.1	320.6	311.2	299.3	285.1	270.8	256.5	242.3	233.6
65°	305.6	296.1	286.7	277.2	267.7	256.3	242.9	229.5	216.1	202.7	194.3
67.5°	262.1	252.6	243.0	233.4	223.9	212.7	199.8	186.9	174.1	161.2	154.9
70°	233.6	224.3	215.1	205.8	196.5	185.8	173.8	161.8	149.8	137.7	131.7
72.5°	205.1	196.0	186.8	177.7	168.5	158.5	147.6	136.6	125.7	114.8	109.9
75°	161.7	153.4	145.2	136.9	128.7	119.8	110.4	100.9	91.5	82.0	80.3
77.5°	122.1	114.6	107.1	99.7	92.2	85.4	79.4	73.3	67.2	61.1	60.2
80°	96.7	89.7	82.6	75.5	68.5	63.2	59.6	55.9	52.3	48.8	48.2
82.5°	72.6	66.4	60.4	54.3	48.2	44.3	42.6	41.0	39.3	37.6	37.1
85°	41.0	37.3	33.4	29.7	25.9	23.7	23.2	22.7	22.2	21.6	21.3
87.5°	15.0	14.1	13.1	12.1	11.1	11.0	11.6	12.3	13.0	13.6	13.7
90°	1.2	3.7	6.4	9.0	11.6	14.6	18.0	21.4	24.7	28.2	29.2
92.5°	21.8	21.1	20.4	19.6	18.9	19.8	22.4	24.9	27.5	30.0	31.7
95°	71.6	60.9	50.2	39.5	28.8	24.9	27.8	30.6	33.5	36.4	38.2
97.5°	143.8	139.1	134.2	129.5	124.6	112.9	94.1	75.3	56.6	37.8	39.9
100°	198.2	203.5	208.7	213.9	219.1	201.4	160.8	120.1	79.4	38.7	40.8
102.5°	260.2	264.0	267.7	271.5	275.3	254.9	210.5	166.0	121.6	77.2	70.7
105°	349.6	352.5	355.4	358.2	361.1	350.8	327.3	303.9	280.4	256.9	210.8
107.5°	443.9	446.3	448.6	450.8	453.1	456.2	459.9	463.5	467.3	471.0	437.1
110°	506.9	509.0	511.0	513.1	515.2	517.7	520.6	523.4	526.2	529.2	520.6



TEST NUMBER: P332297-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	566.9	568.8	570.7	572.6	574.4	576.8	579.7	582.6	585.4	588.2	588.4
115°	655.9	657.4	658.9	660.6	662.1	664.1	666.4	668.7	671.2	673.5	676.1
117.5°	741.9	743.9	745.8	747.8	749.7	751.2	752.5	753.7	754.9	756.1	758.1
120°	795.5	797.8	800.2	802.5	804.9	806.5	807.2	808.0	808.8	809.5	811.6
122.5°	849.9	851.8	853.7	855.7	857.7	859.1	860.1	861.1	862.0	863.0	864.5
125°	924.5	926.7	928.7	930.8	932.9	934.4	935.4	936.5	937.6	938.6	939.2
127.5°	996.8	998.9	1001.0	1003.1	1005.1	1006.8	1008.0	1009.4	1010.6	1011.8	1012.7
130°	1041.9	1044.0	1046.0	1048.1	1050.2	1051.8	1052.8	1053.9	1054.9	1055.9	1057.0
132.5°	1085.0	1087.1	1089.2	1091.3	1093.4	1094.8	1095.7	1096.5	1097.3	1098.2	1099.2
135°	1150.9	1152.6	1154.1	1155.7	1157.2	1158.5	1159.6	1160.6	1161.6	1162.8	1163.5
137.5°	1207.3	1209.3	1211.2	1213.3	1215.3	1216.5	1217.1	1217.7	1218.2	1218.8	1220.0
140°	1244.9	1246.4	1248.0	1249.5	1251.1	1252.2	1253.0	1253.8	1254.7	1255.4	1256.5
142.5°	1279.6	1281.1	1282.7	1284.2	1285.9	1287.0	1287.8	1288.6	1289.4	1290.1	1291.0
145°	1328.2	1330.0	1331.8	1333.6	1335.4	1336.7	1337.2	1337.7	1338.2	1338.7	1339.2
147.5°	1373.9	1375.1	1376.3	1377.5	1378.7	1379.6	1380.1	1380.6	1381.1	1381.6	1382.2
150°	1402.1	1402.8	1403.6	1404.4	1405.2	1405.8	1406.3	1406.8	1407.4	1408.0	1408.5
152.5°	1427.4	1427.7	1428.2	1428.5	1428.9	1429.2	1429.5	1429.9	1430.2	1430.5	1431.4
155°	1463.1	1462.6	1462.0	1461.5	1461.0	1460.9	1461.1	1461.4	1461.7	1461.9	1463.2
157.5°	1490.8	1490.7	1490.7	1490.6	1490.6	1490.4	1490.2	1489.9	1489.7	1489.3	1491.0
160°	1507.6	1507.4	1507.1	1506.9	1506.6	1506.3	1506.1	1505.8	1505.6	1505.3	1506.9
162.5°	1523.6	1523.0	1522.3	1521.6	1520.9	1520.5	1520.1	1519.9	1519.6	1519.3	1521.2
165°	1542.9	1542.1	1541.3	1540.5	1539.7	1539.2	1538.9	1538.6	1538.4	1538.1	1540.2
167.5°	1557.9	1556.8	1555.8	1554.8	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1555.3
170°	1566.3	1565.3	1564.3	1563.2	1562.2	1561.7	1561.7	1561.7	1561.7	1561.7	1563.7
172.5°	1572.0	1570.7	1569.4	1568.2	1566.9	1566.4	1566.6	1566.8	1567.0	1567.2	1569.3
175°	1579.2	1577.9	1576.6	1575.3	1574.0	1573.5	1573.8	1574.0	1574.3	1574.5	1576.4
177.5°	1581.1	1580.0	1579.0	1578.0	1576.9	1576.5	1576.7	1576.9	1577.1	1577.3	1579.0
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332297-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	950.1	951.6	953.1	953.7	953.4	953.1	952.9	952.6
5°	943.7	945.3	946.8	947.5	947.2	946.7	946.4	946.0
7.5°	930.5	931.3	932.2	932.3	931.7	931.2	930.6	930.0
10°	918.6	918.8	918.9	918.6	917.8	916.9	916.0	915.1
12.5°	903.8	903.7	903.6	903.0	902.0	901.0	900.1	899.1
15°	877.9	877.0	876.2	875.0	873.8	872.7	871.5	870.3
17.5°	846.9	845.1	843.1	841.4	839.6	837.8	836.0	834.2
20°	825.6	823.3	821.1	819.0	816.9	814.9	812.7	810.7
22.5°	802.8	800.0	797.3	794.9	792.9	791.0	789.1	787.2
25°	765.6	761.9	758.4	755.6	753.8	751.8	749.9	748.0
27.5°	725.0	720.0	715.0	711.0	708.1	705.3	702.4	699.4
30°	696.1	690.2	684.5	680.1	677.4	674.7	671.9	669.1
32.5°	667.8	661.4	655.0	650.4	647.5	644.6	641.7	638.8
35°	625.7	618.3	611.0	605.7	602.6	599.6	596.4	593.3
37.5°	580.6	572.2	563.8	557.7	553.9	550.1	546.2	542.4
40°	549.2	540.2	531.3	524.8	520.9	516.9	513.0	509.0
42.5°	519.1	509.3	499.5	492.8	489.3	485.7	482.2	478.7
45°	474.7	464.9	455.1	448.2	444.0	439.9	435.8	431.6
47.5°	428.9	418.3	407.6	400.4	396.8	393.0	389.4	385.7
50°	398.0	387.3	376.7	369.3	365.4	361.4	357.5	353.6
52.5°	368.1	357.0	345.9	338.6	335.1	331.5	328.0	324.5
55°	323.6	313.6	303.6	296.9	293.5	290.0	286.6	283.2
57.5°	279.7	270.3	260.9	254.8	251.9	248.9	246.0	243.1
60°	252.2	242.9	233.6	227.5	224.6	221.7	218.7	215.8
62.5°	224.8	216.1	207.3	201.5	198.4	195.3	192.3	189.2
65°	185.8	177.4	169.0	163.8	162.0	160.1	158.1	156.2
67.5°	148.7	142.3	136.0	131.9	129.9	127.8	125.8	123.8
70°	125.6	119.7	113.6	109.7	107.8	105.9	104.0	102.1
72.5°	104.9	100.1	95.1	92.3	91.5	90.7	89.9	89.1
75°	78.6	76.9	75.1	74.1	73.7	73.4	73.0	72.7
77.5°	59.3	58.4	57.4	56.8	56.5	56.0	55.7	55.3
80°	47.7	47.2	46.7	46.3	45.9	45.5	45.2	44.8
82.5°	36.6	36.1	35.5	35.2	35.1	35.1	35.0	34.9
85°	21.0	20.6	20.3	20.1	20.1	20.1	20.1	20.1
87.5°	13.8	13.9	13.9	13.9	13.9	13.9	13.8	13.8
90°	30.2	31.3	32.3	33.1	33.6	34.1	34.6	35.2
92.5°	33.3	35.0	36.8	37.7	38.0	38.4	38.7	39.0
95°	40.0	41.8	43.6	44.5	44.5	44.5	44.5	44.5
97.5°	41.9	44.0	46.2	47.3	47.6	47.9	48.1	48.4
100°	42.9	44.9	47.1	48.3	48.5	48.8	49.0	49.3
102.5°	64.2	57.8	51.3	48.4	48.8	49.3	49.8	50.2
105°	164.6	118.5	72.3	49.6	50.1	50.6	51.1	51.6
107.5°	403.2	369.4	335.6	301.2	266.5	231.7	196.9	162.2
110°	511.9	503.3	494.7	471.8	434.5	397.2	359.9	322.7



TEST NUMBER: P332297-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	588.5	588.8	589.0	585.0	577.1	569.3	561.4	553.5
115°	678.6	681.3	683.9	685.7	686.7	687.8	688.8	689.8
117.5°	760.2	762.3	764.4	765.6	765.8	766.0	766.2	766.4
120°	813.7	815.8	817.9	818.9	818.9	818.9	818.9	818.9
122.5°	866.0	867.5	868.9	869.7	869.9	870.1	870.4	870.6
125°	939.7	940.2	940.7	941.2	941.7	942.3	942.8	943.3
127.5°	1013.5	1014.3	1015.1	1015.3	1014.8	1014.3	1013.8	1013.2
130°	1058.0	1059.0	1060.2	1060.4	1059.9	1059.3	1058.8	1058.3
132.5°	1100.2	1101.4	1102.4	1102.5	1101.8	1101.1	1100.3	1099.5
135°	1164.3	1165.1	1165.9	1165.9	1165.1	1164.3	1163.5	1162.8
137.5°	1221.3	1222.5	1223.8	1224.2	1223.7	1223.1	1222.6	1222.0
140°	1257.5	1258.5	1259.6	1259.8	1259.3	1258.8	1258.3	1257.8
142.5°	1291.8	1292.6	1293.4	1293.5	1292.8	1292.0	1291.3	1290.6
145°	1339.8	1340.3	1340.8	1341.0	1341.0	1341.0	1341.0	1341.0
147.5°	1382.7	1383.2	1383.7	1383.4	1382.2	1381.0	1379.8	1378.6
150°	1409.0	1409.5	1410.0	1409.9	1409.1	1408.4	1407.5	1406.7
152.5°	1432.3	1433.3	1434.2	1434.1	1432.9	1431.7	1430.5	1429.3
155°	1464.5	1465.8	1467.1	1466.9	1465.4	1463.9	1462.3	1460.8
157.5°	1492.5	1494.0	1495.6	1495.4	1493.4	1491.3	1489.2	1487.2
160°	1508.4	1510.0	1511.6	1511.5	1509.6	1507.8	1505.9	1504.1
162.5°	1523.0	1524.7	1526.5	1526.5	1524.9	1523.3	1521.7	1520.0
165°	1542.4	1544.4	1546.5	1546.6	1544.8	1543.0	1541.2	1539.3
167.5°	1557.3	1559.4	1561.6	1561.6	1559.4	1557.3	1555.3	1553.2
170°	1565.8	1567.9	1569.9	1569.9	1567.9	1565.8	1563.7	1561.7
172.5°	1571.5	1573.5	1575.6	1575.5	1573.2	1570.9	1568.6	1566.3
175°	1578.2	1580.0	1581.9	1581.7	1579.6	1577.5	1575.5	1573.4
177.5°	1580.6	1582.4	1584.0	1583.8	1581.8	1579.6	1577.5	1575.5
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2

(END OF REPORT)