

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332298-840

Luminaire Tested: **S123RDIP-S560D1195U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332298-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1195U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6297.6 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332298-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332298-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42
1	94	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	36
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	33	32	30
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	28	26
4	72	62	54	48	65	56	50	44	45	41	37	36	32	30	26	24	23
5	66	55	47	41	60	50	43	38	41	36	32	32	28	26	24	22	20
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	17
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	17	16
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	48	37	29	25	44	34	27	23	28	23	19	22	19	16	17	14	13
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10267	10267	10267
5°	10306	10164	10222
10°	10248	10037	10002
15°	10137	9802	9698
20°	9986	9507	9286
25°	9830	9178	8884
30°	9625	8797	8316
35°	9412	8418	7796
40°	9218	7967	7152
45°	8961	7524	6570
50°	8679	7021	5921
55°	8392	6446	5315
60°	8127	5828	4646
65°	7784	5163	3978
70°	7352	4334	3213
75°	6725	3410	3023
80°	5994	3025	2777
85°	5064	2668	2482



TEST NUMBER: P332298-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.4
10°-20°	249.2	4.0
20°-30°	358.8	5.7
30°-40°	404.2	6.4
40°-50°	386.7	6.1
50°-60°	316.7	5.0
60°-70°	213.7	3.4
70°-80°	107.5	1.7
80°-90°	32.8	0.5
90°-100°	97.3	1.5
100°-110°	291.2	4.6
110°-120°	495.4	7.9
120°-130°	651.6	10.3
130°-140°	732.3	11.6
140°-150°	719.9	11.4
150°-160°	606.0	9.6
160°-170°	403.4	6.4
170°-180°	141.3	2.2
0°-30°	697.6	11.1
0°-40°	1101.8	17.5
0°-60°	1805.2	28.7
0°-90°	2159.2	34.3
90°-120°	883.9	14.0
90°-150°	2987.7	47.4
90°-180°	4138.0	65.7
0°-180°	6297.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	954	954	954	954	954	
5°	954	950	941	947	946	90
15°	910	900	880	876	870	256
25°	828	808	773	757	748	381
35°	716	687	641	608	593	448
45°	589	552	494	452	432	454
55°	447	408	344	300	283	401
65°	306	262	203	166	156	302
75°	162	124	82	75	73	172
85°	41	25	22	20	20	46
90°	1	13	28	33	35	6
95°	69	78	87	91	92	78
105°	264	267	277	277	279	283
115°	499	502	500	501	500	493
125°	730	733	731	726	722	651
135°	947	953	953	948	946	729
145°	1149	1151	1155	1153	1149	717
155°	1315	1315	1316	1320	1313	605
165°	1433	1429	1429	1435	1428	404
175°	1490	1486	1485	1492	1484	141
180°	1494	1494	1494	1494	1494	



TEST NUMBER: P332298-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	956.9	956.3	955.8	955.2	954.7	953.6	952.0	950.3	948.7	947.1	948.6
5°	953.8	953.0	952.1	951.3	950.4	949.0	946.8	944.8	942.7	940.7	942.2
7.5°	945.0	944.1	943.1	942.2	941.3	939.5	936.9	934.1	931.4	928.8	929.6
10°	937.6	936.3	935.1	933.9	932.8	930.6	927.6	924.4	921.3	918.3	918.4
12.5°	927.1	925.7	924.3	923.0	921.7	919.2	915.3	911.6	907.8	904.0	903.9
15°	909.7	907.9	905.9	904.0	902.2	898.8	894.0	889.2	884.3	879.6	878.7
17.5°	887.9	885.8	883.5	881.3	879.1	874.9	868.8	862.7	856.6	850.5	848.7
20°	871.8	869.1	866.4	863.5	860.8	856.2	849.6	843.1	836.6	830.0	827.8
22.5°	853.8	850.7	847.6	844.3	841.2	836.2	829.2	822.2	815.4	808.4	805.6
25°	827.7	823.4	819.1	814.9	810.5	804.5	796.5	788.6	780.7	772.8	769.2
27.5°	796.0	791.2	786.5	781.7	777.0	770.2	761.4	752.7	743.9	735.1	730.0
30°	774.4	769.2	764.1	758.9	753.8	746.3	736.7	727.1	717.4	707.8	702.0
32.5°	752.7	746.9	741.0	735.2	729.3	721.3	711.1	700.9	690.7	680.5	674.2
35°	716.3	710.1	704.0	697.8	691.6	683.2	672.5	661.9	651.2	640.6	633.1
37.5°	679.5	672.7	665.8	658.8	652.0	642.9	631.5	620.2	608.7	597.3	589.0
40°	656.0	648.4	640.9	633.3	625.7	615.8	603.7	591.5	579.3	567.0	558.1
42.5°	629.3	621.8	614.3	606.7	599.2	589.1	576.4	563.8	551.2	538.6	528.8
45°	588.7	581.0	573.2	565.5	557.7	547.2	534.0	520.8	507.6	494.3	484.5
47.5°	548.0	539.5	531.0	522.5	514.0	503.2	489.9	476.7	463.4	450.2	439.6
50°	518.3	510.2	502.1	494.0	485.9	474.9	461.0	447.2	433.2	419.3	408.6
52.5°	491.7	482.9	474.1	465.3	456.7	445.4	431.5	417.8	403.9	390.2	379.1
55°	447.2	438.7	430.3	421.8	413.4	401.9	387.3	372.7	358.1	343.5	333.5
57.5°	406.0	396.8	387.6	378.4	369.2	357.3	342.6	328.0	313.3	298.6	289.2
60°	377.5	368.1	358.6	349.1	339.7	327.8	313.6	299.3	285.0	270.7	261.5
62.5°	349.0	339.6	330.1	320.6	311.2	299.3	285.1	270.8	256.5	242.3	233.6
65°	305.6	296.1	286.7	277.2	267.7	256.3	242.9	229.5	216.1	202.7	194.3
67.5°	262.1	252.6	243.0	233.4	223.9	212.7	199.8	186.9	174.1	161.2	154.9
70°	233.6	224.3	215.1	205.8	196.5	185.8	173.8	161.8	149.8	137.7	131.7
72.5°	205.1	196.0	186.8	177.7	168.5	158.5	147.6	136.6	125.7	114.8	109.9
75°	161.7	153.4	145.2	136.9	128.7	119.8	110.4	100.9	91.5	82.0	80.3
77.5°	122.1	114.6	107.1	99.7	92.2	85.4	79.4	73.3	67.2	61.1	60.2
80°	96.7	89.7	82.6	75.5	68.5	63.2	59.6	55.9	52.3	48.8	48.2
82.5°	72.6	66.4	60.4	54.3	48.2	44.3	42.6	41.0	39.3	37.6	37.1
85°	41.0	37.3	33.4	29.7	25.9	23.7	23.2	22.7	22.2	21.6	21.3
87.5°	15.0	14.1	13.1	12.1	11.1	11.0	11.6	12.3	13.0	13.6	13.7
90°	1.2	3.7	6.4	9.0	11.6	14.6	18.0	21.4	24.7	28.2	29.2
92.5°	28.4	30.2	31.9	33.7	35.4	37.4	39.3	41.2	43.1	45.0	45.8
95°	69.3	71.1	72.9	74.7	76.5	78.5	80.6	82.6	84.7	86.8	87.9
97.5°	123.0	124.3	125.7	127.0	128.4	129.9	131.4	132.9	134.3	135.8	137.0
100°	159.6	161.2	162.7	164.3	165.8	167.2	168.5	169.9	171.2	172.5	173.3
102.5°	201.8	202.8	203.7	204.6	205.6	206.9	208.6	210.4	212.1	213.8	214.6
105°	264.0	264.5	265.1	265.6	266.1	267.5	269.8	272.3	274.6	276.9	276.9
107.5°	336.3	336.6	336.9	337.2	337.5	338.2	339.1	340.0	340.9	341.9	342.7
110°	381.3	381.8	382.3	382.9	383.4	384.0	384.5	385.0	385.5	386.1	387.1



TEST NUMBER: P332298-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	428.3	428.6	428.9	429.2	429.5	429.7	429.8	429.9	430.0	430.1	431.4
115°	498.7	499.5	500.2	501.0	501.8	501.9	501.4	500.9	500.4	499.9	500.1
117.5°	569.6	570.1	570.6	571.1	571.6	571.6	570.9	570.2	569.6	568.9	568.8
120°	613.7	615.2	616.8	618.3	620.0	620.1	618.7	617.4	616.1	614.8	614.6
122.5°	659.6	660.8	662.0	663.1	664.3	664.5	663.8	663.1	662.5	661.8	661.1
125°	729.8	730.6	731.3	732.2	733.0	733.1	732.6	732.1	731.5	731.0	729.9
127.5°	794.6	796.3	797.9	799.6	801.2	801.8	801.2	800.6	800.1	799.5	798.1
130°	837.8	839.8	841.9	844.0	846.1	846.8	846.0	845.2	844.4	843.6	842.6
132.5°	880.9	883.0	885.1	887.2	889.3	890.1	889.5	888.9	888.3	887.8	886.5
135°	946.8	948.5	950.0	951.6	953.1	953.8	953.5	953.3	953.0	952.7	951.7
137.5°	1007.9	1009.2	1010.5	1011.8	1013.1	1014.1	1014.8	1015.4	1016.1	1016.8	1015.7
140°	1050.2	1051.5	1052.8	1054.1	1055.3	1056.1	1056.4	1056.6	1056.9	1057.2	1056.9
142.5°	1088.6	1089.9	1091.3	1092.6	1093.9	1094.7	1095.2	1095.7	1096.1	1096.6	1096.3
145°	1148.7	1149.2	1149.7	1150.2	1150.7	1151.4	1152.3	1153.0	1153.8	1154.6	1154.3
147.5°	1201.2	1202.2	1203.2	1204.1	1205.1	1205.9	1206.6	1207.3	1208.0	1208.8	1208.8
150°	1237.9	1238.4	1238.9	1239.4	1240.0	1240.5	1241.0	1241.5	1242.0	1242.5	1242.5
152.5°	1267.9	1268.7	1269.4	1270.1	1270.8	1271.3	1271.6	1272.0	1272.3	1272.6	1273.0
155°	1315.3	1315.3	1315.3	1315.3	1315.3	1315.5	1315.8	1316.0	1316.3	1316.5	1317.6
157.5°	1355.6	1355.3	1355.0	1354.7	1354.4	1354.3	1354.6	1354.8	1355.0	1355.2	1356.3
160°	1381.0	1380.5	1380.0	1379.5	1379.0	1378.7	1378.7	1378.7	1378.7	1378.7	1380.0
162.5°	1403.5	1402.8	1402.1	1401.4	1400.7	1400.4	1400.6	1400.8	1401.0	1401.2	1402.5
165°	1432.7	1431.9	1431.1	1430.3	1429.6	1429.2	1429.2	1429.2	1429.2	1429.2	1430.7
167.5°	1455.9	1454.8	1453.8	1452.8	1451.7	1451.3	1451.5	1451.7	1451.9	1452.1	1453.7
170°	1469.1	1467.9	1466.9	1465.9	1464.8	1464.3	1464.3	1464.3	1464.3	1464.3	1466.1
172.5°	1479.4	1478.3	1477.2	1476.2	1475.2	1474.7	1474.7	1474.7	1474.7	1474.7	1476.3
175°	1490.2	1489.1	1488.0	1487.0	1486.0	1485.4	1485.4	1485.4	1485.4	1485.4	1487.0
177.5°	1494.6	1493.8	1493.0	1492.1	1491.3	1490.9	1490.9	1490.9	1490.9	1490.9	1492.1
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7



TEST NUMBER: P332298-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	950.1	951.6	953.1	953.7	953.4	953.1	952.9	952.6
5°	943.7	945.3	946.8	947.5	947.2	946.7	946.4	946.0
7.5°	930.5	931.3	932.2	932.3	931.7	931.2	930.6	930.0
10°	918.6	918.8	918.9	918.6	917.8	916.9	916.0	915.1
12.5°	903.8	903.7	903.6	903.0	902.0	901.0	900.1	899.1
15°	877.9	877.0	876.2	875.0	873.8	872.7	871.5	870.3
17.5°	846.9	845.1	843.1	841.4	839.6	837.8	836.0	834.2
20°	825.6	823.3	821.1	819.0	816.9	814.9	812.7	810.7
22.5°	802.8	800.0	797.3	794.9	792.9	791.0	789.1	787.2
25°	765.6	761.9	758.4	755.6	753.8	751.8	749.9	748.0
27.5°	725.0	720.0	715.0	711.0	708.1	705.3	702.4	699.4
30°	696.1	690.2	684.5	680.1	677.4	674.7	671.9	669.1
32.5°	667.8	661.4	655.0	650.4	647.5	644.6	641.7	638.8
35°	625.7	618.3	611.0	605.7	602.6	599.6	596.4	593.3
37.5°	580.6	572.2	563.8	557.7	553.9	550.1	546.2	542.4
40°	549.2	540.2	531.3	524.8	520.9	516.9	513.0	509.0
42.5°	519.1	509.3	499.5	492.8	489.3	485.7	482.2	478.7
45°	474.7	464.9	455.1	448.2	444.0	439.9	435.8	431.6
47.5°	428.9	418.3	407.6	400.4	396.8	393.0	389.4	385.7
50°	398.0	387.3	376.7	369.3	365.4	361.4	357.5	353.6
52.5°	368.1	357.0	345.9	338.6	335.1	331.5	328.0	324.5
55°	323.6	313.6	303.6	296.9	293.5	290.0	286.6	283.2
57.5°	279.7	270.3	260.9	254.8	251.9	248.9	246.0	243.1
60°	252.2	242.9	233.6	227.5	224.6	221.7	218.7	215.8
62.5°	224.8	216.1	207.3	201.5	198.4	195.3	192.3	189.2
65°	185.8	177.4	169.0	163.8	162.0	160.1	158.1	156.2
67.5°	148.7	142.3	136.0	131.9	129.9	127.8	125.8	123.8
70°	125.6	119.7	113.6	109.7	107.8	105.9	104.0	102.1
72.5°	104.9	100.1	95.1	92.3	91.5	90.7	89.9	89.1
75°	78.6	76.9	75.1	74.1	73.7	73.4	73.0	72.7
77.5°	59.3	58.4	57.4	56.8	56.5	56.0	55.7	55.3
80°	47.7	47.2	46.7	46.3	45.9	45.5	45.2	44.8
82.5°	36.6	36.1	35.5	35.2	35.1	35.1	35.0	34.9
85°	21.0	20.6	20.3	20.1	20.1	20.1	20.1	20.1
87.5°	13.8	13.9	13.9	13.9	13.9	13.9	13.8	13.8
90°	30.3	31.3	32.3	33.1	33.6	34.1	34.6	35.2
92.5°	46.8	47.6	48.4	48.7	48.4	48.1	47.7	47.4
95°	88.9	90.0	91.0	91.5	91.5	91.5	91.5	91.5
97.5°	138.3	139.5	140.7	141.2	141.1	141.0	140.9	140.8
100°	174.0	174.8	175.6	176.2	176.8	177.3	177.8	178.3
102.5°	215.3	216.1	216.9	217.2	217.1	217.0	216.9	216.8
105°	276.9	276.9	276.9	277.2	277.7	278.2	278.7	279.2
107.5°	343.6	344.5	345.3	345.5	345.2	344.9	344.6	344.3
110°	388.1	389.2	390.2	390.4	389.9	389.4	388.9	388.4



TEST NUMBER: P332298-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.6	433.9	435.2	435.8	435.7	435.6	435.5	435.4
115°	500.4	500.6	500.9	500.9	500.6	500.4	500.1	499.9
117.5°	568.8	568.7	568.7	568.3	567.5	566.7	566.0	565.3
120°	614.3	614.1	613.8	613.4	612.9	612.4	611.9	611.3
122.5°	660.5	659.7	659.0	658.3	657.6	656.9	656.1	655.4
125°	728.9	727.9	726.8	725.8	724.8	723.7	722.7	721.6
127.5°	796.6	795.2	793.7	792.3	791.1	789.9	788.7	787.6
130°	841.5	840.5	839.5	838.0	836.2	834.4	832.5	830.7
132.5°	885.2	884.0	882.7	881.4	880.0	878.6	877.2	875.8
135°	950.7	949.6	948.6	947.8	947.3	946.7	946.2	945.7
137.5°	1014.6	1013.5	1012.4	1011.4	1010.4	1009.5	1008.5	1007.4
140°	1056.6	1056.4	1056.1	1055.1	1053.3	1051.5	1049.7	1047.8
142.5°	1096.1	1095.8	1095.6	1094.7	1093.3	1091.9	1090.6	1089.1
145°	1154.1	1153.8	1153.6	1152.9	1151.9	1150.7	1149.7	1148.7
147.5°	1208.8	1208.8	1208.8	1208.0	1206.4	1204.9	1203.3	1201.7
150°	1242.5	1242.5	1242.5	1241.8	1240.2	1238.7	1237.1	1235.6
152.5°	1273.4	1273.8	1274.2	1273.8	1272.4	1271.1	1269.7	1268.4
155°	1318.6	1319.6	1320.7	1320.3	1318.5	1316.7	1314.8	1312.9
157.5°	1357.4	1358.5	1359.6	1359.4	1358.0	1356.5	1355.0	1353.5
160°	1381.3	1382.6	1383.9	1384.0	1383.0	1381.9	1380.9	1379.9
162.5°	1403.8	1405.1	1406.4	1406.2	1404.5	1402.9	1401.2	1399.6
165°	1432.3	1433.8	1435.4	1435.2	1433.4	1431.6	1429.8	1427.9
167.5°	1455.3	1456.9	1458.5	1458.5	1456.9	1455.3	1453.7	1452.1
170°	1467.9	1469.9	1471.7	1471.7	1469.9	1467.9	1466.1	1464.3
172.5°	1477.9	1479.6	1481.2	1481.1	1479.1	1477.3	1475.5	1473.7
175°	1488.5	1490.2	1491.7	1491.6	1489.8	1487.9	1486.1	1484.3
177.5°	1493.4	1494.6	1495.8	1495.7	1494.3	1492.8	1491.4	1490.0
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7

(END OF REPORT)