

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332282-840

Luminaire Tested: **S123RDIP-S560D805U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332282-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D805U840-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5493.3 lumens
Efficiency: N/A
Efficacy: 143.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	36	30
3	81	72	65	59	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27	23
5	68	57	49	43	62	52	46	40	44	39	35	36	32	29	28	26	24	20
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21	18
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	35	29	49	39	32	28	33	28	24	27	23	20	22	19	17	15
9	50	38	31	26	46	35	29	25	30	25	22	25	21	18	20	17	15	13
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9725	9725	9725	9725
5°	11594	9767	8602	9767
10°	14476	9711	7770	9711
15°	16992	9611	7086	9611
20°	18963	9464	6504	9464
25°	18659	9308	6147	9308
30°	13412	9163	5778	9163
35°	8956	8976	5540	8976
40°	6598	8751	5295	8751
45°	5535	8356	5051	8356
50°	4883	7839	4716	7839
55°	4282	7246	4252	7246
60°	3813	6678	3899	6678
65°	3349	6067	3627	6067
70°	2628	5526	3311	5526
75°	2316	4824	3023	4824
80°	2015	4097	2975	4097
85°	1618	3298	3149	3298



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.9	1.6
10°-20°	277.6	5.1
20°-30°	436.1	7.9
30°-40°	455.0	8.3
40°-50°	389.4	7.1
50°-60°	296.8	5.4
60°-70°	190.2	3.5
70°-80°	91.5	1.7
80°-90°	27.2	0.5
90°-100°	38.6	0.7
100°-110°	184.1	3.4
110°-120°	442.3	8.1
120°-130°	563.2	10.3
130°-140°	601.8	11.0
140°-150°	562.7	10.2
150°-160°	453.9	8.3
160°-170°	293.0	5.3
170°-180°	101.0	1.8
0°-30°	802.6	14.6
0°-40°	1257.6	22.9
0°-60°	1943.7	35.4
0°-90°	2252.7	41.0
90°-120°	665.1	12.1
90°-150°	2392.8	43.6
90°-180°	3241.0	59.0
0°-180°	5493.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1073	904	796	904	1073	111
15°	1525	862	636	862	1525	432
25°	1571	784	518	784	1571	675
35°	682	683	422	683	682	447
45°	364	549	332	549	364	286
55°	228	386	227	386	228	206
65°	132	238	142	238	132	129
75°	56	116	73	116	56	60
85°	13	27	26	27	13	16
90°	24	1	24	1	24	11
95°	30	48	30	48	30	25
105°	35	235	35	235	35	79
115°	464	441	464	441	464	429
125°	635	622	635	622	635	567
135°	782	774	782	774	782	603
145°	902	894	902	894	902	563
155°	983	984	983	984	983	453
165°	1036	1038	1036	1038	1036	292
175°	1059	1063	1059	1063	1059	101
180°	1063	1063	1063	1063	1063	



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	962.3	963.6	959.6	959.0	954.3	953.1	953.1	946.5	942.5	937.3	934.2
5°	1073.0	1079.1	1076.1	1069.1	1057.5	1054.8	1047.4	1035.8	1022.7	1006.4	998.8
7.5°	1211.1	1219.6	1216.3	1205.6	1193.5	1183.6	1162.9	1143.6	1116.6	1093.0	1072.7
10°	1324.4	1315.5	1308.6	1298.1	1286.9	1268.7	1247.1	1217.3	1182.9	1155.8	1125.6
12.5°	1409.2	1407.8	1398.9	1388.2	1372.3	1355.0	1328.4	1292.1	1252.1	1212.9	1178.5
15°	1524.8	1527.1	1521.3	1510.1	1487.6	1457.0	1416.8	1401.8	1344.5	1301.9	1259.4
17.5°	1604.8	1604.3	1603.5	1587.9	1565.1	1543.3	1506.0	1466.3	1414.5	1354.5	1297.3
20°	1655.5	1651.6	1652.4	1635.0	1618.0	1592.9	1556.5	1498.8	1456.3	1387.0	1327.9
22.5°	1654.3	1653.5	1656.4	1650.4	1638.1	1618.8	1590.2	1541.6	1487.2	1417.3	1350.8
25°	1571.1	1568.1	1586.3	1591.2	1611.0	1614.5	1606.0	1579.3	1527.8	1455.9	1373.5
27.5°	1314.9	1313.2	1347.0	1389.2	1442.8	1484.4	1524.6	1544.0	1527.8	1476.3	1393.8
30°	1079.1	1115.5	1132.6	1193.7	1261.7	1342.9	1414.1	1481.8	1498.4	1476.0	1408.4
32.5°	896.0	927.7	941.9	994.4	1057.8	1153.0	1259.7	1355.5	1423.3	1440.5	1399.7
35°	681.6	682.0	714.4	737.6	796.4	894.2	997.9	1126.3	1253.9	1350.7	1360.8
37.5°	543.8	545.7	565.4	588.5	632.7	684.4	775.7	882.4	1029.9	1178.3	1265.4
40°	469.6	473.0	487.8	510.6	542.3	581.4	652.6	753.1	876.1	1041.3	1176.3
42.5°	421.9	427.6	435.2	452.7	472.3	509.0	566.5	644.2	756.0	912.2	1067.9
45°	363.6	366.7	372.4	380.6	398.4	423.9	462.6	514.8	607.6	733.4	889.3
47.5°	320.7	319.1	325.2	331.8	343.7	361.0	387.0	429.6	495.8	596.6	728.9
50°	291.6	291.2	295.5	300.5	311.7	324.6	345.8	377.9	430.5	514.0	635.1
52.5°	264.4	265.9	268.9	275.2	283.3	293.6	312.7	335.8	381.0	453.1	554.0
55°	228.2	229.3	233.6	237.1	242.9	253.4	265.4	284.7	315.6	365.9	449.1
57.5°	197.5	197.0	201.2	202.0	208.5	217.0	226.3	241.4	263.8	301.1	357.2
60°	177.1	176.0	179.5	182.2	185.6	192.6	200.4	215.1	232.9	260.3	308.3
62.5°	158.5	158.0	160.6	163.3	166.1	172.5	179.0	190.3	204.4	227.5	265.6
65°	131.5	132.7	133.8	135.0	136.5	140.4	146.6	154.3	164.0	180.3	207.7
67.5°	103.3	104.5	104.9	107.2	110.6	113.0	116.8	123.7	130.5	144.1	159.8
70°	83.5	83.1	83.5	84.7	89.0	93.2	98.3	103.3	107.6	117.2	130.4
72.5°	71.8	71.1	72.1	72.3	74.4	75.5	78.8	83.5	89.0	95.5	105.0
75°	55.7	55.7	55.7	55.7	57.3	58.1	59.2	60.4	62.3	65.3	72.3
77.5°	41.2	41.2	41.8	42.1	42.5	42.9	43.6	44.8	45.4	47.2	50.1
80°	32.5	32.9	32.5	32.9	32.9	33.6	34.0	35.2	35.5	37.6	38.7
82.5°	24.4	24.2	24.4	24.8	24.8	25.7	25.7	26.6	26.7	27.6	28.8
85°	13.1	12.4	13.1	12.7	13.5	12.7	13.1	13.9	13.9	14.3	15.9
87.5°	7.9	8.4	7.7	8.0	7.9	8.1	7.9	7.8	8.3	7.8	7.7
90°	23.7	23.3	23.0	22.6	22.3	21.7	21.0	20.4	19.7	19.0	16.7
92.5°	26.3	26.0	25.8	25.5	25.3	24.7	23.5	22.4	21.3	20.2	18.5
95°	30.0	30.0	30.0	30.0	30.0	29.4	28.2	27.0	25.8	24.4	22.5
97.5°	32.5	32.3	32.2	32.0	31.8	31.0	29.6	28.3	26.9	25.4	38.1
100°	33.1	33.0	32.8	32.6	32.4	31.7	30.3	28.9	27.5	26.1	53.4
102.5°	33.8	33.4	33.1	32.8	32.5	34.5	38.9	43.2	47.6	51.9	81.8
105°	34.7	34.4	34.0	33.7	33.3	48.7	79.8	110.8	141.9	172.9	188.6
107.5°	109.1	132.5	155.9	179.4	202.7	225.8	248.6	271.4	294.2	316.9	314.4
110°	217.1	242.2	267.3	292.4	317.5	333.0	338.7	344.5	350.3	356.1	354.2



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	372.5	377.8	383.0	388.4	393.6	396.3	396.2	396.1	396.0	395.9	393.9
115°	464.2	463.5	462.8	462.1	461.4	460.2	458.5	456.7	454.9	453.2	451.6
117.5°	515.7	515.5	515.4	515.3	515.1	514.3	513.0	511.6	510.2	508.8	508.0
120°	551.1	551.1	551.1	551.1	551.1	550.4	549.0	547.5	546.1	544.7	544.2
122.5°	585.8	585.7	585.5	585.4	585.2	584.7	583.7	582.7	581.8	580.8	580.1
125°	634.8	634.4	634.1	633.7	633.4	633.0	632.7	632.3	632.0	631.6	630.9
127.5°	681.9	682.2	682.6	682.9	683.2	683.1	682.6	682.0	681.5	680.9	680.0
130°	712.2	712.5	712.9	713.2	713.6	713.4	712.7	712.0	711.2	710.5	709.8
132.5°	739.9	740.4	740.9	741.4	741.8	741.7	741.0	740.3	739.7	739.0	738.4
135°	782.4	782.9	783.5	784.0	784.5	784.5	784.0	783.5	782.9	782.4	781.7
137.5°	822.3	822.7	823.0	823.4	823.7	823.5	822.6	821.8	821.0	820.1	819.7
140°	846.4	846.7	847.1	847.4	847.8	847.6	846.9	846.2	845.5	844.8	844.2
142.5°	868.5	869.0	869.4	869.9	870.4	870.4	869.8	869.3	868.7	868.2	867.6
145°	902.4	902.4	902.4	902.4	902.4	902.2	901.9	901.5	901.2	900.8	900.5
147.5°	927.7	928.5	929.3	930.1	930.9	931.1	930.8	930.4	930.1	929.7	929.4
150°	946.6	947.2	947.7	948.2	948.8	948.8	948.5	948.1	947.8	947.5	947.1
152.5°	961.8	962.6	963.4	964.2	965.0	965.1	964.4	963.8	963.2	962.6	962.4
155°	982.9	984.0	985.0	986.1	987.1	987.2	986.3	985.5	984.6	983.7	983.5
157.5°	1000.8	1002.2	1003.5	1004.9	1006.2	1006.4	1005.3	1004.3	1003.3	1002.2	1002.4
160°	1012.2	1013.4	1014.6	1015.8	1017.0	1017.1	1016.1	1015.0	1014.0	1012.9	1013.1
162.5°	1022.9	1024.0	1025.0	1026.1	1027.2	1027.1	1026.0	1024.8	1023.6	1022.4	1022.6
165°	1035.8	1037.0	1038.2	1039.6	1040.8	1040.7	1039.3	1037.8	1036.4	1035.0	1035.2
167.5°	1045.1	1046.5	1047.9	1049.4	1050.8	1050.8	1049.4	1047.9	1046.5	1045.1	1045.1
170°	1050.9	1052.3	1053.6	1055.0	1056.4	1056.4	1055.0	1053.6	1052.3	1050.9	1050.9
172.5°	1054.0	1055.5	1057.1	1058.6	1060.2	1060.3	1058.8	1057.4	1056.0	1054.6	1054.5
175°	1058.7	1060.2	1061.6	1063.0	1064.3	1064.4	1063.2	1062.0	1060.8	1059.6	1059.3
177.5°	1060.2	1061.6	1063.0	1064.4	1065.8	1065.9	1064.8	1063.7	1062.6	1061.4	1061.3
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	932.9	932.0	927.7	922.7	916.3	911.9	908.5	906.7	901.1	894.2	889.6
5°	990.6	979.0	966.6	951.5	937.6	923.3	914.4	903.9	891.2	876.9	866.8
7.5°	1052.3	1029.6	1005.0	979.8	954.7	932.3	912.5	895.5	875.3	854.7	840.3
10°	1099.6	1066.4	1032.0	996.7	964.6	934.5	911.3	888.5	864.1	840.5	822.7
12.5°	1142.7	1098.9	1059.2	1015.9	974.9	938.9	905.4	878.6	849.3	824.2	803.9
15°	1197.1	1152.3	1104.3	1038.5	984.0	938.4	897.8	862.5	827.0	796.1	776.3
17.5°	1248.0	1180.5	1116.1	1061.2	990.4	933.3	883.7	841.6	802.6	769.8	745.5
20°	1269.1	1203.8	1133.7	1063.7	994.1	930.3	872.6	826.2	785.6	748.4	726.0
22.5°	1281.7	1207.7	1134.0	1058.7	984.8	918.5	861.5	810.4	766.4	731.1	703.5
25°	1296.6	1208.3	1127.1	1052.9	977.4	905.4	837.8	783.7	736.1	698.5	669.1
27.5°	1306.3	1202.5	1106.5	1024.0	947.5	875.9	813.9	756.4	708.1	668.4	636.9
30°	1308.2	1197.9	1090.8	1001.4	923.6	857.9	792.1	737.2	686.2	644.0	614.6
32.5°	1310.6	1186.5	1069.4	974.5	894.9	829.8	770.2	717.7	665.4	623.9	593.9
35°	1300.4	1180.1	1037.0	928.0	848.3	785.2	731.4	683.1	631.7	591.4	560.9
37.5°	1256.5	1155.0	1003.4	875.5	792.1	733.8	689.9	647.8	600.7	557.2	528.5
40°	1212.2	1130.2	977.4	843.6	756.6	696.6	657.1	622.8	577.1	536.4	505.5
42.5°	1146.3	1096.5	952.7	810.2	716.3	658.5	625.3	593.0	553.0	511.7	482.6
45°	1025.4	1032.0	902.0	757.0	660.7	602.6	571.3	548.9	513.3	479.3	449.5
47.5°	873.7	935.2	842.5	700.2	602.0	547.4	520.1	500.5	476.6	443.1	416.0
50°	774.8	862.5	794.9	662.2	565.1	511.0	483.9	468.1	447.2	420.8	395.0
52.5°	683.5	777.8	737.3	619.8	525.2	475.6	449.2	436.2	419.6	394.9	371.4
55°	557.3	652.9	643.6	555.8	465.3	420.8	400.7	386.1	374.8	356.3	337.7
57.5°	450.8	541.4	546.2	484.6	412.5	368.6	351.3	340.2	332.9	318.9	301.7
60°	383.7	466.9	483.1	436.7	374.8	336.1	319.1	310.2	304.4	293.2	280.0
62.5°	328.0	398.8	417.2	383.7	338.6	302.4	289.1	280.5	276.6	266.9	255.3
65°	251.1	309.8	327.6	309.0	285.5	256.4	245.6	238.2	234.8	229.3	220.9
67.5°	188.7	231.7	251.2	238.0	229.5	211.2	204.3	200.4	197.2	193.6	186.4
70°	151.6	183.4	203.5	200.0	193.0	183.4	178.3	175.6	172.5	169.5	163.2
72.5°	121.9	143.7	162.6	164.4	158.6	156.7	152.3	151.2	149.3	145.6	142.2
75°	80.9	95.9	109.1	114.1	116.4	118.4	116.4	116.0	115.6	112.6	110.6
77.5°	53.0	61.1	69.4	78.0	81.6	84.2	84.8	86.2	85.2	83.6	82.7
80°	40.6	42.5	48.4	55.7	61.5	63.8	65.3	66.1	65.7	65.3	63.8
82.5°	29.5	31.1	33.8	39.0	43.8	47.8	48.7	48.5	49.4	49.6	48.4
85°	15.9	16.3	17.1	17.8	20.5	24.7	26.0	26.7	27.5	27.5	25.1
87.5°	7.9	7.1	7.3	6.9	7.4	7.4	8.9	10.1	10.7	9.8	10.2
90°	14.3	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	16.8	15.0	13.3	12.7	13.2	13.7	14.2	14.6	14.2	13.7	13.2
95°	20.6	18.7	16.8	19.4	26.6	33.7	41.0	48.2	41.0	33.7	26.6
97.5°	50.7	63.3	75.9	83.9	87.2	90.4	93.6	96.7	93.6	90.4	87.2
100°	80.8	108.2	135.5	147.4	143.9	140.5	136.9	133.4	136.9	140.5	143.9
102.5°	111.7	141.7	171.6	185.2	182.7	180.2	177.6	175.1	177.6	180.2	182.7
105°	204.5	220.3	236.1	243.0	241.1	239.1	237.2	235.3	237.2	239.1	241.1
107.5°	311.9	309.4	306.9	304.9	303.4	301.8	300.3	298.7	300.3	301.8	303.4
110°	352.2	350.3	348.3	346.7	345.3	343.9	342.4	341.0	342.4	343.9	345.3



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	392.0	390.1	388.1	386.6	385.3	384.1	382.7	381.5	382.7	384.1	385.3
115°	450.0	448.5	446.9	445.6	444.5	443.4	442.4	441.3	442.4	443.4	444.5
117.5°	507.2	506.3	505.5	504.4	503.2	501.9	500.6	499.3	500.6	501.9	503.2
120°	543.7	543.2	542.7	541.6	540.0	538.5	536.8	535.3	536.8	538.5	540.0
122.5°	579.5	578.8	578.0	577.1	575.8	574.5	573.2	571.9	573.2	574.5	575.8
125°	630.2	629.5	628.8	627.7	626.3	624.9	623.5	622.2	623.5	624.9	626.3
127.5°	679.2	678.3	677.5	676.4	675.0	673.6	672.2	670.8	672.2	673.6	675.0
130°	709.1	708.4	707.7	706.7	705.3	703.9	702.5	701.0	702.5	703.9	705.3
132.5°	737.8	737.3	736.7	735.8	734.4	733.0	731.5	730.1	731.5	733.0	734.4
135°	781.0	780.3	779.6	778.7	777.7	776.6	775.6	774.5	775.6	776.6	777.7
137.5°	819.4	819.0	818.6	817.7	816.4	815.1	813.7	812.4	813.7	815.1	816.4
140°	843.7	843.2	842.6	841.9	840.8	839.8	838.7	837.7	838.7	839.8	840.8
142.5°	867.1	866.6	866.1	865.3	864.2	863.1	862.1	861.0	862.1	863.1	864.2
145°	900.1	899.8	899.4	898.7	897.4	896.2	894.9	893.7	894.9	896.2	897.4
147.5°	929.0	928.7	928.4	927.8	927.0	926.1	925.3	924.5	925.3	926.1	927.0
150°	946.7	946.3	946.0	945.5	945.0	944.5	944.0	943.4	944.0	944.5	945.0
152.5°	962.1	961.9	961.7	961.5	961.3	961.0	960.8	960.5	960.8	961.0	961.3
155°	983.4	983.2	983.0	983.1	983.5	983.8	984.2	984.5	984.2	983.8	983.5
157.5°	1002.6	1002.7	1002.9	1003.0	1003.0	1003.1	1003.1	1003.1	1003.1	1003.1	1003.0
160°	1013.3	1013.5	1013.6	1013.8	1014.0	1014.2	1014.3	1014.5	1014.3	1014.2	1014.0
162.5°	1022.8	1022.9	1023.1	1023.4	1023.9	1024.3	1024.8	1025.2	1024.8	1024.3	1023.9
165°	1035.4	1035.6	1035.7	1036.1	1036.6	1037.1	1037.6	1038.2	1037.6	1037.1	1036.6
167.5°	1045.1	1045.1	1045.1	1045.5	1046.2	1046.9	1047.6	1048.3	1047.6	1046.9	1046.2
170°	1050.9	1050.9	1050.9	1051.2	1051.9	1052.6	1053.3	1054.0	1053.3	1052.6	1051.9
172.5°	1054.3	1054.2	1054.1	1054.4	1055.2	1056.1	1056.9	1057.7	1056.9	1056.1	1055.2
175°	1059.1	1058.9	1058.8	1059.1	1060.1	1061.0	1061.8	1062.7	1061.8	1061.0	1060.1
177.5°	1061.2	1061.0	1060.9	1061.2	1061.9	1062.6	1063.3	1063.9	1063.3	1062.6	1061.9
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	888.1	884.0	881.3	875.0	871.1	866.8	862.4	865.2	864.8	864.5	864.5
5°	858.3	849.4	841.3	830.8	824.3	816.2	809.9	809.2	810.7	805.3	802.2
7.5°	828.8	816.6	805.1	793.6	781.3	771.5	765.5	762.7	758.7	755.4	751.8
10°	808.0	793.8	782.4	768.2	755.1	743.5	736.1	731.0	728.3	725.6	720.6
12.5°	786.7	772.6	758.3	742.1	729.6	716.2	710.7	705.1	699.8	696.8	689.9
15°	755.4	737.2	722.2	705.1	691.3	678.0	670.3	659.1	657.5	653.7	646.7
17.5°	724.1	704.4	683.6	671.0	655.2	641.6	629.8	626.0	614.9	610.8	604.7
20°	699.3	681.2	665.3	648.6	625.8	613.1	603.8	598.7	589.9	584.4	580.6
22.5°	678.0	659.4	641.2	621.8	602.9	588.7	581.8	574.0	569.2	561.6	557.3
25°	647.5	627.4	605.3	584.4	570.9	560.1	549.3	542.3	535.3	531.8	524.1
27.5°	612.1	591.1	570.5	554.6	538.0	527.3	517.5	511.3	502.9	497.1	492.8
30°	592.6	567.8	550.1	535.7	514.4	504.4	497.1	489.3	483.1	477.0	472.6
32.5°	570.0	547.3	530.5	512.8	496.4	485.5	475.9	469.2	463.9	458.1	453.8
35°	534.5	515.6	498.2	480.4	468.4	457.2	446.0	440.2	435.2	429.7	425.9
37.5°	502.5	484.8	468.3	451.4	436.6	427.4	418.4	413.9	407.2	403.5	399.6
40°	482.7	465.3	447.6	431.3	415.8	408.9	400.7	394.2	388.0	385.3	381.0
42.5°	461.1	443.6	428.7	411.1	398.5	389.0	381.5	374.4	369.7	365.8	363.3
45°	429.0	413.4	398.8	381.4	369.4	361.2	352.7	346.2	341.9	339.2	335.0
47.5°	397.8	382.3	367.4	352.2	340.6	331.3	322.9	318.2	312.7	309.3	306.4
50°	375.2	361.2	345.4	331.4	319.9	310.6	303.7	297.8	292.8	288.5	286.6
52.5°	354.5	339.6	325.9	313.0	300.7	290.1	283.9	277.7	274.0	269.0	266.8
55°	320.2	306.0	294.4	281.6	269.6	260.7	253.0	247.5	243.7	238.2	235.2
57.5°	288.1	275.3	261.5	250.4	238.0	230.6	224.1	216.7	212.1	207.8	204.8
60°	266.5	251.8	239.8	229.3	218.5	208.8	203.1	197.2	192.3	187.9	185.3
62.5°	243.9	231.1	219.7	208.3	198.4	190.0	183.3	178.3	174.0	171.3	168.5
65°	209.2	199.2	187.6	178.3	169.1	162.9	157.4	153.2	150.1	148.1	145.8
67.5°	177.4	167.6	157.5	148.3	142.2	137.4	133.9	130.3	128.8	126.2	124.7
70°	156.6	146.6	137.7	130.8	124.5	121.1	118.8	116.0	114.5	111.4	109.9
72.5°	134.1	126.8	120.4	114.6	109.7	106.5	103.6	100.3	97.8	94.4	92.8
75°	105.6	99.1	94.0	90.1	87.1	82.8	78.6	75.0	73.9	72.7	72.3
77.5°	78.2	74.0	70.4	67.2	63.3	60.2	59.3	58.5	58.3	57.7	57.7
80°	61.5	57.7	54.9	51.1	48.8	48.8	48.8	48.0	48.4	48.4	48.4
82.5°	45.7	42.1	40.7	39.3	38.9	39.2	39.2	39.3	39.1	39.7	39.4
85°	23.6	23.9	24.7	24.3	24.7	24.7	25.5	25.1	25.5	24.7	25.5
87.5°	10.2	11.5	12.3	13.1	13.8	14.0	14.4	14.5	15.0	15.1	15.2
90°	7.8	9.8	12.1	14.3	16.7	19.0	19.7	20.4	21.0	21.7	22.3
92.5°	12.7	13.3	15.0	16.8	18.5	20.2	21.3	22.4	23.5	24.7	25.3
95°	19.4	16.8	18.7	20.6	22.5	24.4	25.8	27.0	28.2	29.4	30.0
97.5°	83.9	75.9	63.3	50.7	38.1	25.4	26.9	28.3	29.6	31.0	31.8
100°	147.4	135.5	108.2	80.8	53.4	26.1	27.5	28.9	30.3	31.7	32.4
102.5°	185.2	171.6	141.7	111.7	81.8	51.9	47.6	43.2	38.9	34.5	32.5
105°	243.0	236.1	220.3	204.5	188.6	172.9	141.9	110.8	79.8	48.7	33.3
107.5°	304.9	306.9	309.4	311.9	314.4	316.9	294.2	271.4	248.6	225.8	202.7
110°	346.7	348.3	350.3	352.2	354.2	356.1	350.3	344.5	338.7	333.0	317.5



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	386.6	388.1	390.1	392.0	393.9	395.9	396.0	396.1	396.2	396.3	393.6
115°	445.6	446.9	448.5	450.0	451.6	453.2	454.9	456.7	458.5	460.2	461.4
117.5°	504.4	505.5	506.3	507.2	508.0	508.8	510.2	511.6	513.0	514.3	515.1
120°	541.6	542.7	543.2	543.7	544.2	544.7	546.1	547.5	549.0	550.4	551.1
122.5°	577.1	578.0	578.8	579.5	580.1	580.8	581.8	582.7	583.7	584.7	585.2
125°	627.7	628.8	629.5	630.2	630.9	631.6	632.0	632.3	632.7	633.0	633.4
127.5°	676.4	677.5	678.3	679.2	680.0	680.9	681.5	682.0	682.6	683.1	683.2
130°	706.7	707.7	708.4	709.1	709.8	710.5	711.2	712.0	712.7	713.4	713.6
132.5°	735.8	736.7	737.3	737.8	738.4	739.0	739.7	740.3	741.0	741.7	741.8
135°	778.7	779.6	780.3	781.0	781.7	782.4	782.9	783.5	784.0	784.5	784.5
137.5°	817.7	818.6	819.0	819.4	819.7	820.1	821.0	821.8	822.6	823.5	823.7
140°	841.9	842.6	843.2	843.7	844.2	844.8	845.5	846.2	846.9	847.6	847.8
142.5°	865.3	866.1	866.6	867.1	867.6	868.2	868.7	869.3	869.8	870.4	870.4
145°	898.7	899.4	899.8	900.1	900.5	900.8	901.2	901.5	901.9	902.2	902.4
147.5°	927.8	928.4	928.7	929.0	929.4	929.7	930.1	930.4	930.8	931.1	930.9
150°	945.5	946.0	946.3	946.7	947.1	947.5	947.8	948.1	948.5	948.8	948.8
152.5°	961.5	961.7	961.9	962.1	962.4	962.6	963.2	963.8	964.4	965.1	965.0
155°	983.1	983.0	983.2	983.4	983.5	983.7	984.6	985.5	986.3	987.2	987.1
157.5°	1003.0	1002.9	1002.7	1002.6	1002.4	1002.2	1003.3	1004.3	1005.3	1006.4	1006.2
160°	1013.8	1013.6	1013.5	1013.3	1013.1	1012.9	1014.0	1015.0	1016.1	1017.1	1017.0
162.5°	1023.4	1023.1	1022.9	1022.8	1022.6	1022.4	1023.6	1024.8	1026.0	1027.1	1027.2
165°	1036.1	1035.7	1035.6	1035.4	1035.2	1035.0	1036.4	1037.8	1039.3	1040.7	1040.8
167.5°	1045.5	1045.1	1045.1	1045.1	1045.1	1045.1	1046.5	1047.9	1049.4	1050.8	1050.8
170°	1051.2	1050.9	1050.9	1050.9	1050.9	1050.9	1052.3	1053.6	1055.0	1056.4	1056.4
172.5°	1054.4	1054.1	1054.2	1054.3	1054.5	1054.6	1056.0	1057.4	1058.8	1060.3	1060.2
175°	1059.1	1058.8	1058.9	1059.1	1059.3	1059.6	1060.8	1062.0	1063.2	1064.4	1064.3
177.5°	1061.2	1060.9	1061.0	1061.2	1061.3	1061.4	1062.6	1063.7	1064.8	1065.9	1065.8
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	860.8	860.5	860.8	859.6	860.8	860.5	860.8	864.5	864.5	864.8	865.2
5°	801.0	800.6	799.5	796.1	799.5	800.6	801.0	802.2	805.3	810.7	809.2
7.5°	748.8	748.3	744.9	745.0	744.9	748.3	748.8	751.8	755.4	758.7	762.7
10°	717.9	718.3	713.7	710.9	713.7	718.3	717.9	720.6	725.6	728.3	731.0
12.5°	687.9	686.1	682.4	679.3	682.4	686.1	687.9	689.9	696.8	699.8	705.1
15°	648.2	644.4	635.1	635.9	635.1	644.4	648.2	646.7	653.7	657.5	659.1
17.5°	601.6	598.7	598.6	593.2	598.6	598.7	601.6	604.7	610.8	614.9	626.0
20°	574.4	572.5	573.2	567.8	573.2	572.5	574.4	580.6	584.4	589.9	598.7
22.5°	553.0	551.1	547.9	546.1	547.9	551.1	553.0	557.3	561.6	569.2	574.0
25°	521.8	518.7	515.6	517.6	515.6	518.7	521.8	524.1	531.8	535.3	542.3
27.5°	490.5	488.2	485.1	484.7	485.1	488.2	490.5	492.8	497.1	502.9	511.3
30°	470.7	468.4	466.9	464.9	466.9	468.4	470.7	472.6	477.0	483.1	489.3
32.5°	450.6	450.2	447.4	447.0	447.4	450.2	450.6	453.8	458.1	463.9	469.2
35°	424.3	422.0	421.2	421.6	421.2	422.0	424.3	425.9	429.7	435.2	440.2
37.5°	399.3	396.3	394.9	393.4	394.9	396.3	399.3	399.6	403.5	407.2	413.9
40°	381.4	378.3	377.5	376.8	377.5	378.3	381.4	381.0	385.3	388.0	394.2
42.5°	361.2	360.0	359.6	358.2	359.6	360.0	361.2	363.3	365.8	369.7	374.4
45°	333.8	333.5	331.1	331.8	331.1	333.5	333.8	335.0	339.2	341.9	346.2
47.5°	304.9	303.2	301.5	302.7	301.5	303.2	304.9	306.4	309.3	312.7	318.2
50°	285.1	284.3	280.8	281.6	280.8	284.3	285.1	286.6	288.5	292.8	297.8
52.5°	265.3	262.4	261.1	260.5	261.1	262.4	265.3	266.8	269.0	274.0	277.7
55°	232.5	228.9	227.4	226.6	227.4	228.9	232.5	235.2	238.2	243.7	247.5
57.5°	200.3	199.3	198.1	198.9	198.1	199.3	200.3	204.8	207.8	212.1	216.7
60°	181.4	181.4	181.4	181.1	181.4	181.4	181.4	185.3	187.9	192.3	197.2
62.5°	166.8	165.9	165.6	166.1	165.6	165.9	166.8	168.5	171.3	174.0	178.3
65°	144.6	144.3	142.7	142.4	142.7	144.3	144.6	145.8	148.1	150.1	153.2
67.5°	123.7	122.3	121.9	121.3	121.9	122.3	123.7	124.7	126.2	128.8	130.3
70°	108.0	107.1	104.8	105.2	104.8	107.1	108.0	109.9	111.4	114.5	116.0
72.5°	90.9	90.1	89.7	89.1	89.7	90.1	90.9	92.8	94.4	97.8	100.3
75°	71.9	71.6	71.2	72.7	71.2	71.6	71.9	72.3	72.7	73.9	75.0
77.5°	57.7	57.7	57.9	57.3	57.9	57.7	57.7	57.7	57.7	58.3	58.5
80°	48.4	48.4	48.0	48.0	48.0	48.4	48.4	48.4	48.4	48.4	48.0
82.5°	38.8	39.1	39.3	38.7	39.3	39.1	38.8	39.4	39.7	39.1	39.3
85°	25.5	25.1	26.0	25.5	26.0	25.1	25.5	25.5	24.7	25.5	25.1
87.5°	16.0	15.5	15.5	15.9	15.5	15.5	16.0	15.2	15.1	15.0	14.5
90°	22.6	23.0	23.3	23.7	23.3	23.0	22.6	22.3	21.7	21.0	20.4
92.5°	25.5	25.8	26.0	26.3	26.0	25.8	25.5	25.3	24.7	23.5	22.4
95°	30.0	30.0	30.0	30.0	30.0	30.0	30.0	30.0	29.4	28.2	27.0
97.5°	32.0	32.2	32.3	32.5	32.3	32.2	32.0	31.8	31.0	29.6	28.3
100°	32.6	32.8	33.0	33.1	33.0	32.8	32.6	32.4	31.7	30.3	28.9
102.5°	32.8	33.1	33.4	33.8	33.4	33.1	32.8	32.5	34.5	38.9	43.2
105°	33.7	34.0	34.4	34.7	34.4	34.0	33.7	33.3	48.7	79.8	110.8
107.5°	179.4	155.9	132.5	109.1	132.5	155.9	179.4	202.7	225.8	248.6	271.4
110°	292.4	267.3	242.2	217.1	242.2	267.3	292.4	317.5	333.0	338.7	344.5



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	388.4	383.0	377.8	372.5	377.8	383.0	388.4	393.6	396.3	396.2	396.1
115°	462.1	462.8	463.5	464.2	463.5	462.8	462.1	461.4	460.2	458.5	456.7
117.5°	515.3	515.4	515.5	515.7	515.5	515.4	515.3	515.1	514.3	513.0	511.6
120°	551.1	551.1	551.1	551.1	551.1	551.1	551.1	551.1	550.4	549.0	547.5
122.5°	585.4	585.5	585.7	585.8	585.7	585.5	585.4	585.2	584.7	583.7	582.7
125°	633.7	634.1	634.4	634.8	634.4	634.1	633.7	633.4	633.0	632.7	632.3
127.5°	682.9	682.6	682.2	681.9	682.2	682.6	682.9	683.2	683.1	682.6	682.0
130°	713.2	712.9	712.5	712.2	712.5	712.9	713.2	713.6	713.4	712.7	712.0
132.5°	741.4	740.9	740.4	739.9	740.4	740.9	741.4	741.8	741.7	741.0	740.3
135°	784.0	783.5	782.9	782.4	782.9	783.5	784.0	784.5	784.5	784.0	783.5
137.5°	823.4	823.0	822.7	822.3	822.7	823.0	823.4	823.7	823.5	822.6	821.8
140°	847.4	847.1	846.7	846.4	846.7	847.1	847.4	847.8	847.6	846.9	846.2
142.5°	869.9	869.4	869.0	868.5	869.0	869.4	869.9	870.4	870.4	869.8	869.3
145°	902.4	902.4	902.4	902.4	902.4	902.4	902.4	902.4	902.2	901.9	901.5
147.5°	930.1	929.3	928.5	927.7	928.5	929.3	930.1	930.9	931.1	930.8	930.4
150°	948.2	947.7	947.2	946.6	947.2	947.7	948.2	948.8	948.8	948.5	948.1
152.5°	964.2	963.4	962.6	961.8	962.6	963.4	964.2	965.0	965.1	964.4	963.8
155°	986.1	985.0	984.0	982.9	984.0	985.0	986.1	987.1	987.2	986.3	985.5
157.5°	1004.9	1003.5	1002.2	1000.8	1002.2	1003.5	1004.9	1006.2	1006.4	1005.3	1004.3
160°	1015.8	1014.6	1013.4	1012.2	1013.4	1014.6	1015.8	1017.0	1017.1	1016.1	1015.0
162.5°	1026.1	1025.0	1024.0	1022.9	1024.0	1025.0	1026.1	1027.2	1027.1	1026.0	1024.8
165°	1039.6	1038.2	1037.0	1035.8	1037.0	1038.2	1039.6	1040.8	1040.7	1039.3	1037.8
167.5°	1049.4	1047.9	1046.5	1045.1	1046.5	1047.9	1049.4	1050.8	1050.8	1049.4	1047.9
170°	1055.0	1053.6	1052.3	1050.9	1052.3	1053.6	1055.0	1056.4	1056.4	1055.0	1053.6
172.5°	1058.6	1057.1	1055.5	1054.0	1055.5	1057.1	1058.6	1060.2	1060.3	1058.8	1057.4
175°	1063.0	1061.6	1060.2	1058.7	1060.2	1061.6	1063.0	1064.3	1064.4	1063.2	1062.0
177.5°	1064.4	1063.0	1061.6	1060.2	1061.6	1063.0	1064.4	1065.8	1065.9	1064.8	1063.7
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	862.4	866.8	871.1	875.0	881.3	884.0	888.1	889.6	894.2	901.1	906.7
5°	809.9	816.2	824.3	830.8	841.3	849.4	858.3	866.8	876.9	891.2	903.9
7.5°	765.5	771.5	781.3	793.6	805.1	816.6	828.8	840.3	854.7	875.3	895.5
10°	736.1	743.5	755.1	768.2	782.4	793.8	808.0	822.7	840.5	864.1	888.5
12.5°	710.7	716.2	729.6	742.1	758.3	772.6	786.7	803.9	824.2	849.3	878.6
15°	670.3	678.0	691.3	705.1	722.2	737.2	755.4	776.3	796.1	827.0	862.5
17.5°	629.8	641.6	655.2	671.0	683.6	704.4	724.1	745.5	769.8	802.6	841.6
20°	603.8	613.1	625.8	648.6	665.3	681.2	699.3	726.0	748.4	785.6	826.2
22.5°	581.8	588.7	602.9	621.8	641.2	659.4	678.0	703.5	731.1	766.4	810.4
25°	549.3	560.1	570.9	584.4	605.3	627.4	647.5	669.1	698.5	736.1	783.7
27.5°	517.5	527.3	538.0	554.6	570.5	591.1	612.1	636.9	668.4	708.1	756.4
30°	497.1	504.4	514.4	535.7	550.1	567.8	592.6	614.6	644.0	686.2	737.2
32.5°	475.9	485.5	496.4	512.8	530.5	547.3	570.0	593.9	623.9	665.4	717.7
35°	446.0	457.2	468.4	480.4	498.2	515.6	534.5	560.9	591.4	631.7	683.1
37.5°	418.4	427.4	436.6	451.4	468.3	484.8	502.5	528.5	557.2	600.7	647.8
40°	400.7	408.9	415.8	431.3	447.6	465.3	482.7	505.5	536.4	577.1	622.8
42.5°	381.5	389.0	398.5	411.1	428.7	443.6	461.1	482.6	511.7	553.0	593.0
45°	352.7	361.2	369.4	381.4	398.8	413.4	429.0	449.5	479.3	513.3	548.9
47.5°	322.9	331.3	340.6	352.2	367.4	382.3	397.8	416.0	443.1	476.6	500.5
50°	303.7	310.6	319.9	331.4	345.4	361.2	375.2	395.0	420.8	447.2	468.1
52.5°	283.9	290.1	300.7	313.0	325.9	339.6	354.5	371.4	394.9	419.6	436.2
55°	253.0	260.7	269.6	281.6	294.4	306.0	320.2	337.7	356.3	374.8	386.1
57.5°	224.1	230.6	238.0	250.4	261.5	275.3	288.1	301.7	318.9	332.9	340.2
60°	203.1	208.8	218.5	229.3	239.8	251.8	266.5	280.0	293.2	304.4	310.2
62.5°	183.3	190.0	198.4	208.3	219.7	231.1	243.9	255.3	266.9	276.6	280.5
65°	157.4	162.9	169.1	178.3	187.6	199.2	209.2	220.9	229.3	234.8	238.2
67.5°	133.9	137.4	142.2	148.3	157.5	167.6	177.4	186.4	193.6	197.2	200.4
70°	118.8	121.1	124.5	130.8	137.7	146.6	156.6	163.2	169.5	172.5	175.6
72.5°	103.6	106.5	109.7	114.6	120.4	126.8	134.1	142.2	145.6	149.3	151.2
75°	78.6	82.8	87.1	90.1	94.0	99.1	105.6	110.6	112.6	115.6	116.0
77.5°	59.3	60.2	63.3	67.2	70.4	74.0	78.2	82.7	83.6	85.2	86.2
80°	48.8	48.8	48.8	51.1	54.9	57.7	61.5	63.8	65.3	65.7	66.1
82.5°	39.2	39.2	38.9	39.3	40.7	42.1	45.7	48.4	49.6	49.4	48.5
85°	25.5	24.7	24.7	24.3	24.7	23.9	23.6	25.1	27.5	27.5	26.7
87.5°	14.4	14.0	13.8	13.1	12.3	11.5	10.2	10.2	9.8	10.7	10.1
90°	19.7	19.0	16.7	14.3	12.1	9.8	7.8	6.1	4.3	2.5	0.8
92.5°	21.3	20.2	18.5	16.8	15.0	13.3	12.7	13.2	13.7	14.2	14.6
95°	25.8	24.4	22.5	20.6	18.7	16.8	19.4	26.6	33.7	41.0	48.2
97.5°	26.9	25.4	38.1	50.7	63.3	75.9	83.9	87.2	90.4	93.6	96.7
100°	27.5	26.1	53.4	80.8	108.2	135.5	147.4	143.9	140.5	136.9	133.4
102.5°	47.6	51.9	81.8	111.7	141.7	171.6	185.2	182.7	180.2	177.6	175.1
105°	141.9	172.9	188.6	204.5	220.3	236.1	243.0	241.1	239.1	237.2	235.3
107.5°	294.2	316.9	314.4	311.9	309.4	306.9	304.9	303.4	301.8	300.3	298.7
110°	350.3	356.1	354.2	352.2	350.3	348.3	346.7	345.3	343.9	342.4	341.0



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	396.0	395.9	393.9	392.0	390.1	388.1	386.6	385.3	384.1	382.7	381.5
115°	454.9	453.2	451.6	450.0	448.5	446.9	445.6	444.5	443.4	442.4	441.3
117.5°	510.2	508.8	508.0	507.2	506.3	505.5	504.4	503.2	501.9	500.6	499.3
120°	546.1	544.7	544.2	543.7	543.2	542.7	541.6	540.0	538.5	536.8	535.3
122.5°	581.8	580.8	580.1	579.5	578.8	578.0	577.1	575.8	574.5	573.2	571.9
125°	632.0	631.6	630.9	630.2	629.5	628.8	627.7	626.3	624.9	623.5	622.2
127.5°	681.5	680.9	680.0	679.2	678.3	677.5	676.4	675.0	673.6	672.2	670.8
130°	711.2	710.5	709.8	709.1	708.4	707.7	706.7	705.3	703.9	702.5	701.0
132.5°	739.7	739.0	738.4	737.8	737.3	736.7	735.8	734.4	733.0	731.5	730.1
135°	782.9	782.4	781.7	781.0	780.3	779.6	778.7	777.7	776.6	775.6	774.5
137.5°	821.0	820.1	819.7	819.4	819.0	818.6	817.7	816.4	815.1	813.7	812.4
140°	845.5	844.8	844.2	843.7	843.2	842.6	841.9	840.8	839.8	838.7	837.7
142.5°	868.7	868.2	867.6	867.1	866.6	866.1	865.3	864.2	863.1	862.1	861.0
145°	901.2	900.8	900.5	900.1	899.8	899.4	898.7	897.4	896.2	894.9	893.7
147.5°	930.1	929.7	929.4	929.0	928.7	928.4	927.8	927.0	926.1	925.3	924.5
150°	947.8	947.5	947.1	946.7	946.3	946.0	945.5	945.0	944.5	944.0	943.4
152.5°	963.2	962.6	962.4	962.1	961.9	961.7	961.5	961.3	961.0	960.8	960.5
155°	984.6	983.7	983.5	983.4	983.2	983.0	983.1	983.5	983.8	984.2	984.5
157.5°	1003.3	1002.2	1002.4	1002.6	1002.7	1002.9	1003.0	1003.0	1003.1	1003.1	1003.1
160°	1014.0	1012.9	1013.1	1013.3	1013.5	1013.6	1013.8	1014.0	1014.2	1014.3	1014.5
162.5°	1023.6	1022.4	1022.6	1022.8	1022.9	1023.1	1023.4	1023.9	1024.3	1024.8	1025.2
165°	1036.4	1035.0	1035.2	1035.4	1035.6	1035.7	1036.1	1036.6	1037.1	1037.6	1038.2
167.5°	1046.5	1045.1	1045.1	1045.1	1045.1	1045.1	1045.5	1046.2	1046.9	1047.6	1048.3
170°	1052.3	1050.9	1050.9	1050.9	1050.9	1050.9	1051.2	1051.9	1052.6	1053.3	1054.0
172.5°	1056.0	1054.6	1054.5	1054.3	1054.2	1054.1	1054.4	1055.2	1056.1	1056.9	1057.7
175°	1060.8	1059.6	1059.3	1059.1	1058.9	1058.8	1059.1	1060.1	1061.0	1061.8	1062.7
177.5°	1062.6	1061.4	1061.3	1061.2	1061.0	1060.9	1061.2	1061.9	1062.6	1063.3	1063.9
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	908.5	911.9	916.3	922.7	927.7	932.0	932.9	934.2	937.3	942.5	946.5
5°	914.4	923.3	937.6	951.5	966.6	979.0	990.6	998.8	1006.4	1022.7	1035.8
7.5°	912.5	932.3	954.7	979.8	1005.0	1029.6	1052.3	1072.7	1093.0	1116.6	1143.6
10°	911.3	934.5	964.6	996.7	1032.0	1066.4	1099.6	1125.6	1155.8	1182.9	1217.3
12.5°	905.4	938.9	974.9	1015.9	1059.2	1098.9	1142.7	1178.5	1212.9	1252.1	1292.1
15°	897.8	938.4	984.0	1038.5	1104.3	1152.3	1197.1	1259.4	1301.9	1344.5	1401.8
17.5°	883.7	933.3	990.4	1061.2	1116.1	1180.5	1248.0	1297.3	1354.5	1414.5	1466.3
20°	872.6	930.3	994.1	1063.7	1133.7	1203.8	1269.1	1327.9	1387.0	1456.3	1498.8
22.5°	861.5	918.5	984.8	1058.7	1134.0	1207.7	1281.7	1350.8	1417.3	1487.2	1541.6
25°	837.8	905.4	977.4	1052.9	1127.1	1208.3	1296.6	1373.5	1455.9	1527.8	1579.3
27.5°	813.9	875.9	947.5	1024.0	1106.5	1202.5	1306.3	1393.8	1476.3	1527.8	1544.0
30°	792.1	857.9	923.6	1001.4	1090.8	1197.9	1308.2	1408.4	1476.0	1498.4	1481.8
32.5°	770.2	829.8	894.9	974.5	1069.4	1186.5	1310.6	1399.7	1440.5	1423.3	1355.5
35°	731.4	785.2	848.3	928.0	1037.0	1180.1	1300.4	1360.8	1350.7	1253.9	1126.3
37.5°	689.9	733.8	792.1	875.5	1003.4	1155.0	1256.5	1265.4	1178.3	1029.9	882.4
40°	657.1	696.6	756.6	843.6	977.4	1130.2	1212.2	1176.3	1041.3	876.1	753.1
42.5°	625.3	658.5	716.3	810.2	952.7	1096.5	1146.3	1067.9	912.2	756.0	644.2
45°	571.3	602.6	660.7	757.0	902.0	1032.0	1025.4	889.3	733.4	607.6	514.8
47.5°	520.1	547.4	602.0	700.2	842.5	935.2	873.7	728.9	596.6	495.8	429.6
50°	483.9	511.0	565.1	662.2	794.9	862.5	774.8	635.1	514.0	430.5	377.9
52.5°	449.2	475.6	525.2	619.8	737.3	777.8	683.5	554.0	453.1	381.0	335.8
55°	400.7	420.8	465.3	555.8	643.6	652.9	557.3	449.1	365.9	315.6	284.7
57.5°	351.3	368.6	412.5	484.6	546.2	541.4	450.8	357.2	301.1	263.8	241.4
60°	319.1	336.1	374.8	436.7	483.1	466.9	383.7	308.3	260.3	232.9	215.1
62.5°	289.1	302.4	338.6	383.7	417.2	398.8	328.0	265.6	227.5	204.4	190.3
65°	245.6	256.4	285.5	309.0	327.6	309.8	251.1	207.7	180.3	164.0	154.3
67.5°	204.3	211.2	229.5	238.0	251.2	231.7	188.7	159.8	144.1	130.5	123.7
70°	178.3	183.4	193.0	200.0	203.5	183.4	151.6	130.4	117.2	107.6	103.3
72.5°	152.3	156.7	158.6	164.4	162.6	143.7	121.9	105.0	95.5	89.0	83.5
75°	116.4	118.4	116.4	114.1	109.1	95.9	80.9	72.3	65.3	62.3	60.4
77.5°	84.8	84.2	81.6	78.0	69.4	61.1	53.0	50.1	47.2	45.4	44.8
80°	65.3	63.8	61.5	55.7	48.4	42.5	40.6	38.7	37.6	35.5	35.2
82.5°	48.7	47.8	43.8	39.0	33.8	31.1	29.5	28.8	27.6	26.7	26.6
85°	26.0	24.7	20.5	17.8	17.1	16.3	15.9	15.9	14.3	13.9	13.9
87.5°	8.9	7.4	7.4	6.9	7.3	7.1	7.9	7.7	7.8	8.3	7.8
90°	2.5	4.3	6.1	7.8	9.8	12.1	14.3	16.7	19.0	19.7	20.4
92.5°	14.2	13.7	13.2	12.7	13.3	15.0	16.8	18.5	20.2	21.3	22.4
95°	41.0	33.7	26.6	19.4	16.8	18.7	20.6	22.5	24.4	25.8	27.0
97.5°	93.6	90.4	87.2	83.9	75.9	63.3	50.7	38.1	25.4	26.9	28.3
100°	136.9	140.5	143.9	147.4	135.5	108.2	80.8	53.4	26.1	27.5	28.9
102.5°	177.6	180.2	182.7	185.2	171.6	141.7	111.7	81.8	51.9	47.6	43.2
105°	237.2	239.1	241.1	243.0	236.1	220.3	204.5	188.6	172.9	141.9	110.8
107.5°	300.3	301.8	303.4	304.9	306.9	309.4	311.9	314.4	316.9	294.2	271.4
110°	342.4	343.9	345.3	346.7	348.3	350.3	352.2	354.2	356.1	350.3	344.5



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	382.7	384.1	385.3	386.6	388.1	390.1	392.0	393.9	395.9	396.0	396.1
115°	442.4	443.4	444.5	445.6	446.9	448.5	450.0	451.6	453.2	454.9	456.7
117.5°	500.6	501.9	503.2	504.4	505.5	506.3	507.2	508.0	508.8	510.2	511.6
120°	536.8	538.5	540.0	541.6	542.7	543.2	543.7	544.2	544.7	546.1	547.5
122.5°	573.2	574.5	575.8	577.1	578.0	578.8	579.5	580.1	580.8	581.8	582.7
125°	623.5	624.9	626.3	627.7	628.8	629.5	630.2	630.9	631.6	632.0	632.3
127.5°	672.2	673.6	675.0	676.4	677.5	678.3	679.2	680.0	680.9	681.5	682.0
130°	702.5	703.9	705.3	706.7	707.7	708.4	709.1	709.8	710.5	711.2	712.0
132.5°	731.5	733.0	734.4	735.8	736.7	737.3	737.8	738.4	739.0	739.7	740.3
135°	775.6	776.6	777.7	778.7	779.6	780.3	781.0	781.7	782.4	782.9	783.5
137.5°	813.7	815.1	816.4	817.7	818.6	819.0	819.4	819.7	820.1	821.0	821.8
140°	838.7	839.8	840.8	841.9	842.6	843.2	843.7	844.2	844.8	845.5	846.2
142.5°	862.1	863.1	864.2	865.3	866.1	866.6	867.1	867.6	868.2	868.7	869.3
145°	894.9	896.2	897.4	898.7	899.4	899.8	900.1	900.5	900.8	901.2	901.5
147.5°	925.3	926.1	927.0	927.8	928.4	928.7	929.0	929.4	929.7	930.1	930.4
150°	944.0	944.5	945.0	945.5	946.0	946.3	946.7	947.1	947.5	947.8	948.1
152.5°	960.8	961.0	961.3	961.5	961.7	961.9	962.1	962.4	962.6	963.2	963.8
155°	984.2	983.8	983.5	983.1	983.0	983.2	983.4	983.5	983.7	984.6	985.5
157.5°	1003.1	1003.1	1003.0	1003.0	1002.9	1002.7	1002.6	1002.4	1002.2	1003.3	1004.3
160°	1014.3	1014.2	1014.0	1013.8	1013.6	1013.5	1013.3	1013.1	1012.9	1014.0	1015.0
162.5°	1024.8	1024.3	1023.9	1023.4	1023.1	1022.9	1022.8	1022.6	1022.4	1023.6	1024.8
165°	1037.6	1037.1	1036.6	1036.1	1035.7	1035.6	1035.4	1035.2	1035.0	1036.4	1037.8
167.5°	1047.6	1046.9	1046.2	1045.5	1045.1	1045.1	1045.1	1045.1	1045.1	1046.5	1047.9
170°	1053.3	1052.6	1051.9	1051.2	1050.9	1050.9	1050.9	1050.9	1050.9	1052.3	1053.6
172.5°	1056.9	1056.1	1055.2	1054.4	1054.1	1054.2	1054.3	1054.5	1054.6	1056.0	1057.4
175°	1061.8	1061.0	1060.1	1059.1	1058.8	1058.9	1059.1	1059.3	1059.6	1060.8	1062.0
177.5°	1063.3	1062.6	1061.9	1061.2	1060.9	1061.0	1061.2	1061.3	1061.4	1062.6	1063.7
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	953.1	953.1	954.3	959.0	959.6	963.6	962.3
5°	1047.4	1054.8	1057.5	1069.1	1076.1	1079.1	1073.0
7.5°	1162.9	1183.6	1193.5	1205.6	1216.3	1219.6	1211.1
10°	1247.1	1268.7	1286.9	1298.1	1308.6	1315.5	1324.4
12.5°	1328.4	1355.0	1372.3	1388.2	1398.9	1407.8	1409.2
15°	1416.8	1457.0	1487.6	1510.1	1521.3	1527.1	1524.8
17.5°	1506.0	1543.3	1565.1	1587.9	1603.5	1604.3	1604.8
20°	1556.5	1592.9	1618.0	1635.0	1652.4	1651.6	1655.5
22.5°	1590.2	1618.8	1638.1	1650.4	1656.4	1653.5	1654.3
25°	1606.0	1614.5	1611.0	1591.2	1586.3	1568.1	1571.1
27.5°	1524.6	1484.4	1442.8	1389.2	1347.0	1313.2	1314.9
30°	1414.1	1342.9	1261.7	1193.7	1132.6	1115.5	1079.1
32.5°	1259.7	1153.0	1057.8	994.4	941.9	927.7	896.0
35°	997.9	894.2	796.4	737.6	714.4	682.0	681.6
37.5°	775.7	684.4	632.7	588.5	565.4	545.7	543.8
40°	652.6	581.4	542.3	510.6	487.8	473.0	469.6
42.5°	566.5	509.0	472.3	452.7	435.2	427.6	421.9
45°	462.6	423.9	398.4	380.6	372.4	366.7	363.6
47.5°	387.0	361.0	343.7	331.8	325.2	319.1	320.7
50°	345.8	324.6	311.7	300.5	295.5	291.2	291.6
52.5°	312.7	293.6	283.3	275.2	268.9	265.9	264.4
55°	265.4	253.4	242.9	237.1	233.6	229.3	228.2
57.5°	226.3	217.0	208.5	202.0	201.2	197.0	197.5
60°	200.4	192.6	185.6	182.2	179.5	176.0	177.1
62.5°	179.0	172.5	166.1	163.3	160.6	158.0	158.5
65°	146.6	140.4	136.5	135.0	133.8	132.7	131.5
67.5°	116.8	113.0	110.6	107.2	104.9	104.5	103.3
70°	98.3	93.2	89.0	84.7	83.5	83.1	83.5
72.5°	78.8	75.5	74.4	72.3	72.1	71.1	71.8
75°	59.2	58.1	57.3	55.7	55.7	55.7	55.7
77.5°	43.6	42.9	42.5	42.1	41.8	41.2	41.2
80°	34.0	33.6	32.9	32.9	32.5	32.9	32.5
82.5°	25.7	25.7	24.8	24.8	24.4	24.2	24.4
85°	13.1	12.7	13.5	12.7	13.1	12.4	13.1
87.5°	7.9	8.1	7.9	8.0	7.7	8.4	7.9
90°	21.0	21.7	22.3	22.6	23.0	23.3	23.7
92.5°	23.5	24.7	25.3	25.5	25.8	26.0	26.3
95°	28.2	29.4	30.0	30.0	30.0	30.0	30.0
97.5°	29.6	31.0	31.8	32.0	32.2	32.3	32.5
100°	30.3	31.7	32.4	32.6	32.8	33.0	33.1
102.5°	38.9	34.5	32.5	32.8	33.1	33.4	33.8
105°	79.8	48.7	33.3	33.7	34.0	34.4	34.7
107.5°	248.6	225.8	202.7	179.4	155.9	132.5	109.1
110°	338.7	333.0	317.5	292.4	267.3	242.2	217.1



TEST NUMBER: P332282-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	396.2	396.3	393.6	388.4	383.0	377.8	372.5
115°	458.5	460.2	461.4	462.1	462.8	463.5	464.2
117.5°	513.0	514.3	515.1	515.3	515.4	515.5	515.7
120°	549.0	550.4	551.1	551.1	551.1	551.1	551.1
122.5°	583.7	584.7	585.2	585.4	585.5	585.7	585.8
125°	632.7	633.0	633.4	633.7	634.1	634.4	634.8
127.5°	682.6	683.1	683.2	682.9	682.6	682.2	681.9
130°	712.7	713.4	713.6	713.2	712.9	712.5	712.2
132.5°	741.0	741.7	741.8	741.4	740.9	740.4	739.9
135°	784.0	784.5	784.5	784.0	783.5	782.9	782.4
137.5°	822.6	823.5	823.7	823.4	823.0	822.7	822.3
140°	846.9	847.6	847.8	847.4	847.1	846.7	846.4
142.5°	869.8	870.4	870.4	869.9	869.4	869.0	868.5
145°	901.9	902.2	902.4	902.4	902.4	902.4	902.4
147.5°	930.8	931.1	930.9	930.1	929.3	928.5	927.7
150°	948.5	948.8	948.8	948.2	947.7	947.2	946.6
152.5°	964.4	965.1	965.0	964.2	963.4	962.6	961.8
155°	986.3	987.2	987.1	986.1	985.0	984.0	982.9
157.5°	1005.3	1006.4	1006.2	1004.9	1003.5	1002.2	1000.8
160°	1016.1	1017.1	1017.0	1015.8	1014.6	1013.4	1012.2
162.5°	1026.0	1027.1	1027.2	1026.1	1025.0	1024.0	1022.9
165°	1039.3	1040.7	1040.8	1039.6	1038.2	1037.0	1035.8
167.5°	1049.4	1050.8	1050.8	1049.4	1047.9	1046.5	1045.1
170°	1055.0	1056.4	1056.4	1055.0	1053.6	1052.3	1050.9
172.5°	1058.8	1060.3	1060.2	1058.6	1057.1	1055.5	1054.0
175°	1063.2	1064.4	1064.3	1063.0	1061.6	1060.2	1058.7
177.5°	1064.8	1065.9	1065.8	1064.4	1063.0	1061.6	1060.2
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7

(END OF REPORT)