

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332303

Luminaire Tested: **S123RDIP-S775D365U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332303
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D365U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4368.4 lumens
Efficiency: N/A
Efficacy: 124.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332303

CATALOG NUMBER: S123RDIP-S775D365U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332303

CATALOG NUMBER: S123RDIP-S775D365U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	79	77	73	71	69	64	63	61	57
2	93	86	80	75	88	81	76	71	72	68	65	64	61	58	57	54	52	49
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	67	60	53	74	64	57	51	57	52	47	51	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	52	46	41	46	41	38	41	37	34	32
6	67	54	46	40	63	52	44	39	47	41	36	42	37	33	38	34	30	28
7	62	49	41	36	58	47	40	34	43	36	32	38	33	30	34	30	27	25
8	57	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22
9	54	41	34	29	51	39	32	28	36	30	26	33	28	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332303

CATALOG NUMBER: S123RDIP-S775D365U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.2	2.8
10°-20°	337.3	7.7
20°-30°	485.7	11.1
30°-40°	547.1	12.5
40°-50°	523.4	12.0
50°-60°	428.6	9.8
60°-70°	289.2	6.6
70°-80°	145.5	3.3
80°-90°	39.8	0.9
90°-100°	17.3	0.4
100°-110°	82.4	1.9
110°-120°	198.0	4.5
120°-130°	252.1	5.8
130°-140°	269.3	6.2
140°-150°	251.9	5.8
150°-160°	203.2	4.7
160°-170°	131.1	3.0
170°-180°	45.2	1.0
0°-30°	944.3	21.6
0°-40°	1491.4	34.1
0°-60°	2443.4	55.9
0°-90°	2917.9	66.8
90°-120°	297.7	6.8
90°-150°	1071.0	24.5
90°-180°	1450.0	33.2
0°-180°	4368.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	0	4	8	10	11	4
95°	22	8	11	13	13	27
105°	105	107	77	18	16	112
115°	198	200	203	206	208	195
125°	278	281	283	283	284	249
135°	347	349	350	351	350	267
145°	400	402	403	404	404	250
155°	441	440	440	442	440	203
165°	465	464	463	466	464	131
175°	476	474	474	476	474	45
180°	476	476	476	476	476	



TEST NUMBER: P332303

CATALOG NUMBER: S123RDIP-S775D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.2	18.3	16.4	14.5	12.6	11.8	12.0	12.2	12.4	12.6	12.5
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.4	6.4	7.5	8.5	8.8
92.5°	6.6	6.4	6.1	5.9	5.7	6.0	6.7	7.5	8.3	9.0	9.5
95°	21.6	18.3	15.1	11.9	8.7	7.5	8.4	9.2	10.1	11.0	11.5
97.5°	43.3	41.9	40.4	39.0	37.5	34.0	28.3	22.7	17.0	11.4	12.0
100°	59.7	61.3	62.9	64.4	66.0	60.7	48.4	36.2	23.9	11.7	12.3
102.5°	78.4	79.5	80.6	81.8	82.9	76.8	63.4	50.0	36.6	23.3	21.3
105°	105.3	106.2	107.0	107.9	108.8	105.7	98.6	91.5	84.5	77.4	63.5
107.5°	133.7	134.4	135.1	135.8	136.5	137.4	138.5	139.6	140.7	141.8	131.6
110°	152.7	153.3	153.9	154.5	155.2	155.9	156.8	157.6	158.5	159.4	156.8



TEST NUMBER: P332303

CATALOG NUMBER: S123RDIP-S775D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.7	171.3	171.9	172.4	173.0	173.7	174.6	175.5	176.3	177.2	177.2
115°	197.5	198.0	198.5	198.9	199.4	200.0	200.7	201.4	202.1	202.8	203.6
117.5°	223.5	224.1	224.6	225.2	225.8	226.3	226.6	227.0	227.4	227.7	228.3
120°	239.6	240.3	241.0	241.7	242.4	242.9	243.1	243.4	243.6	243.8	244.5
122.5°	256.0	256.6	257.1	257.7	258.3	258.7	259.0	259.3	259.6	259.9	260.4
125°	278.5	279.1	279.7	280.3	281.0	281.4	281.8	282.1	282.4	282.7	282.9
127.5°	300.2	300.9	301.5	302.1	302.7	303.2	303.6	304.0	304.4	304.7	305.0
130°	313.8	314.4	315.0	315.7	316.3	316.8	317.1	317.4	317.7	318.0	318.3
132.5°	326.8	327.4	328.1	328.7	329.3	329.7	330.0	330.3	330.5	330.8	331.1
135°	346.7	347.1	347.6	348.1	348.5	348.9	349.2	349.6	349.9	350.2	350.4
137.5°	363.6	364.2	364.8	365.4	366.0	366.4	366.6	366.7	366.9	367.1	367.5
140°	374.9	375.4	375.9	376.3	376.8	377.2	377.4	377.6	377.9	378.1	378.4
142.5°	385.4	385.9	386.3	386.8	387.3	387.6	387.9	388.1	388.3	388.6	388.8
145°	400.0	400.6	401.1	401.7	402.2	402.6	402.7	402.9	403.0	403.2	403.4
147.5°	413.8	414.2	414.5	414.9	415.2	415.5	415.7	415.8	416.0	416.1	416.3
150°	422.3	422.5	422.7	423.0	423.2	423.4	423.6	423.7	423.9	424.0	424.2
152.5°	429.9	430.0	430.1	430.2	430.3	430.5	430.5	430.6	430.7	430.8	431.1
155°	440.7	440.5	440.3	440.2	440.0	440.0	440.1	440.1	440.2	440.3	440.7
157.5°	449.0	449.0	449.0	448.9	448.9	448.9	448.8	448.7	448.6	448.6	449.0
160°	454.1	454.0	453.9	453.8	453.8	453.7	453.6	453.5	453.5	453.4	453.8
162.5°	458.9	458.7	458.5	458.3	458.1	457.9	457.8	457.8	457.7	457.6	458.1
165°	464.7	464.4	464.2	464.0	463.7	463.6	463.5	463.4	463.3	463.3	463.9
167.5°	469.2	468.9	468.6	468.3	467.9	467.8	467.8	467.8	467.8	467.8	468.4
170°	471.7	471.4	471.1	470.8	470.5	470.3	470.3	470.3	470.3	470.3	471.0
172.5°	473.4	473.1	472.7	472.3	471.9	471.8	471.8	471.9	472.0	472.0	472.7
175°	475.6	475.2	474.8	474.5	474.1	473.9	474.0	474.1	474.1	474.2	474.8
177.5°	476.2	475.9	475.6	475.3	474.9	474.8	474.9	474.9	475.0	475.1	475.6
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332303

CATALOG NUMBER: S123RDIP-S775D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	12.3	12.2	12.1	12.0	11.8	11.6	11.5	11.3
90°	9.1	9.4	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	10.1	10.6	11.1	11.4	11.4	11.5	11.6	11.7
95°	12.1	12.6	13.2	13.4	13.4	13.4	13.4	13.4
97.5°	12.6	13.3	13.9	14.2	14.3	14.4	14.5	14.6
100°	12.9	13.5	14.2	14.5	14.6	14.7	14.8	14.8
102.5°	19.4	17.4	15.5	14.6	14.7	14.8	15.0	15.1
105°	49.6	35.7	21.8	14.9	15.1	15.2	15.4	15.5
107.5°	121.5	111.3	101.1	90.7	80.3	69.8	59.3	48.8
110°	154.2	151.6	149.0	142.1	130.9	119.6	108.4	97.2



TEST NUMBER: P332303

CATALOG NUMBER: S123RDIP-S775D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	177.3	177.3	177.4	176.2	173.8	171.5	169.1	166.7
115°	204.4	205.2	206.0	206.5	206.8	207.2	207.5	207.8
117.5°	229.0	229.6	230.2	230.6	230.6	230.7	230.8	230.8
120°	245.1	245.7	246.3	246.7	246.7	246.7	246.7	246.7
122.5°	260.8	261.3	261.7	261.9	262.0	262.1	262.1	262.2
125°	283.0	283.2	283.3	283.5	283.6	283.8	284.0	284.1
127.5°	305.2	305.5	305.8	305.8	305.6	305.5	305.3	305.2
130°	318.7	319.0	319.3	319.4	319.2	319.1	318.9	318.7
132.5°	331.4	331.7	332.0	332.1	331.8	331.6	331.4	331.2
135°	350.7	350.9	351.1	351.1	350.9	350.7	350.4	350.2
137.5°	367.8	368.2	368.6	368.7	368.5	368.4	368.2	368.1
140°	378.7	379.0	379.4	379.4	379.3	379.1	379.0	378.8
142.5°	389.1	389.3	389.6	389.6	389.4	389.1	388.9	388.7
145°	403.5	403.7	403.8	403.9	403.9	403.9	403.9	403.9
147.5°	416.4	416.6	416.8	416.7	416.3	415.9	415.6	415.2
150°	424.4	424.5	424.7	424.6	424.4	424.2	423.9	423.7
152.5°	431.4	431.7	432.0	431.9	431.6	431.2	430.8	430.5
155°	441.1	441.5	441.9	441.8	441.4	440.9	440.4	439.9
157.5°	449.5	450.0	450.5	450.4	449.8	449.2	448.5	447.9
160°	454.3	454.8	455.3	455.2	454.7	454.1	453.6	453.0
162.5°	458.7	459.2	459.7	459.8	459.3	458.8	458.3	457.8
165°	464.5	465.2	465.8	465.8	465.3	464.7	464.2	463.6
167.5°	469.0	469.7	470.3	470.3	469.7	469.0	468.4	467.8
170°	471.6	472.2	472.8	472.8	472.2	471.6	471.0	470.3
172.5°	473.3	473.9	474.5	474.5	473.8	473.1	472.4	471.7
175°	475.3	475.9	476.4	476.4	475.8	475.1	474.5	473.9
177.5°	476.1	476.6	477.1	477.0	476.4	475.8	475.1	474.5
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)