

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332308

Luminaire Tested: **S123RDIP-S775D585U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332308
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D585U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5167.1 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59				
1	100	96	93	89	94	90	87	84	79	76	74	68	66	65	58	57	56	51				
2	92	85	79	74	86	80	75	70	70	66	62	60	58	55	52	50	48	44				
3	84	75	68	63	79	71	64	59	62	57	53	54	50	47	47	44	42	38				
4	78	67	59	54	72	63	56	51	56	50	46	49	44	41	42	39	36	33				
5	72	60	52	46	67	57	50	44	50	44	40	44	40	36	38	35	32	29				
6	66	54	46	41	62	51	44	39	45	40	35	40	35	32	35	31	29	26				
7	61	49	41	36	57	47	39	34	41	36	31	37	32	29	32	28	26	23				
8	57	45	37	32	53	42	36	31	38	32	28	34	29	26	30	26	23	21				
9	53	41	34	29	50	39	32	28	35	29	25	31	26	23	27	24	21	19				
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13164	13164	13164	13164
5°	15692	13220	11642	13220
10°	19593	13144	10518	13144
15°	22998	13010	9591	13010
20°	25668	12810	8804	12810
25°	25258	12598	8320	12598
30°	18155	12403	7822	12403
35°	12122	12150	7499	12150
40°	8931	11844	7165	11844
45°	7491	11309	6838	11309
50°	6611	10608	6382	10608
55°	5797	9805	5758	9805
60°	5162	9040	5274	9040
65°	4534	8214	4908	8214
70°	3559	7481	4482	7481
75°	3136	6534	4092	6534
80°	2727	5548	4023	5548
85°	2198	4458	4273	4458



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.3	2.3
10°-20°	375.7	7.3
20°-30°	590.3	11.4
30°-40°	615.9	11.9
40°-50°	527.1	10.2
50°-60°	401.7	7.8
60°-70°	257.5	5.0
70°-80°	123.9	2.4
80°-90°	35.0	0.7
90°-100°	156.8	3.0
100°-110°	444.0	8.6
110°-120°	436.8	8.5
120°-130°	348.4	6.7
130°-140°	274.7	5.3
140°-150°	205.0	4.0
150°-160°	142.9	2.8
160°-170°	83.9	1.6
170°-180°	27.3	0.5
0°-30°	1086.3	21.0
0°-40°	1702.2	32.9
0°-60°	2631.0	50.9
0°-90°	3047.3	59.0
90°-120°	1037.6	20.1
90°-150°	1865.7	36.1
90°-180°	2120.0	41.0
0°-180°	5167.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1223	1223	1223	1223	1223	
5°	1452	1224	1078	1224	1452	150
15°	2064	1168	861	1168	2064	585
25°	2127	1061	700	1061	2127	914
35°	922	925	571	925	922	605
45°	492	743	449	743	492	387
55°	309	522	307	522	309	279
65°	178	322	193	322	178	175
75°	75	157	98	157	75	81
85°	18	36	35	36	18	21
90°	16	1	16	1	16	9
95°	66	19	66	19	66	119
105°	726	66	726	66	726	716
115°	882	117	882	117	882	857
125°	696	163	696	163	696	631
135°	564	190	564	190	564	438
145°	441	217	441	217	441	280
155°	366	247	366	247	366	171
165°	319	270	319	270	319	91
175°	287	281	287	281	287	28
180°	282	282	282	282	282	



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1302.6	1304.3	1298.8	1298.0	1291.7	1290.0	1290.0	1281.2	1275.8	1268.7	1264.5
5°	1452.3	1460.7	1456.5	1447.1	1431.4	1427.7	1417.8	1402.1	1384.3	1362.3	1351.8
7.5°	1639.3	1650.8	1646.4	1631.8	1615.4	1602.1	1574.0	1547.9	1511.4	1479.3	1451.9
10°	1792.6	1780.6	1771.2	1757.0	1741.9	1717.2	1687.9	1647.6	1601.0	1564.4	1523.5
12.5°	1907.4	1905.4	1893.5	1878.9	1857.5	1834.1	1798.1	1749.0	1694.8	1641.9	1595.2
15°	2063.8	2067.0	2059.1	2043.9	2013.6	1972.2	1917.8	1897.3	1819.9	1762.3	1704.7
17.5°	2172.1	2171.5	2170.4	2149.4	2118.4	2089.0	2038.5	1984.8	1914.6	1833.5	1755.9
20°	2240.8	2235.6	2236.6	2213.0	2190.0	2156.0	2106.8	2028.8	1971.2	1877.5	1797.3
22.5°	2239.1	2238.1	2242.1	2234.0	2217.2	2191.2	2152.4	2086.6	2013.1	1918.5	1828.3
25°	2126.7	2122.5	2147.1	2153.9	2180.6	2185.3	2173.8	2137.7	2068.0	1970.6	1859.1
27.5°	1779.9	1777.6	1823.2	1880.4	1952.8	2009.2	2063.6	2089.9	2068.0	1998.3	1886.6
30°	1460.7	1509.9	1533.0	1615.7	1707.8	1817.8	1914.1	2005.7	2028.2	1997.9	1906.2
32.5°	1212.8	1255.7	1274.9	1345.9	1431.8	1560.6	1705.1	1834.8	1926.5	1949.7	1894.5
35°	922.5	923.0	967.0	998.4	1078.0	1210.4	1350.8	1524.6	1697.3	1828.2	1841.8
37.5°	736.1	738.7	765.3	796.6	856.3	926.4	1049.9	1194.4	1394.0	1594.9	1712.7
40°	635.6	640.3	660.2	691.1	734.0	786.9	883.2	1019.4	1185.8	1409.4	1592.1
42.5°	571.1	578.7	589.0	612.8	639.4	688.9	766.8	871.9	1023.3	1234.7	1445.5
45°	492.1	496.3	504.2	515.2	539.3	573.8	626.2	696.8	822.5	992.7	1203.6
47.5°	434.1	431.9	440.2	449.1	465.1	488.7	523.8	581.5	671.1	807.6	986.6
50°	394.8	394.2	400.0	406.8	422.0	439.3	468.1	511.5	582.7	695.8	859.7
52.5°	357.9	359.9	364.0	372.5	383.4	397.4	423.2	454.5	515.7	613.3	749.9
55°	308.9	310.5	316.2	320.9	328.8	342.9	359.2	385.3	427.2	495.3	607.8
57.5°	267.4	266.7	272.2	273.4	282.3	293.8	306.4	326.7	357.1	407.6	483.4
60°	239.8	238.2	242.9	246.6	251.3	260.7	271.2	291.1	315.2	352.3	417.3
62.5°	214.7	213.9	217.4	221.0	224.9	233.5	242.3	257.6	276.6	308.0	359.5
65°	178.0	179.6	181.1	182.7	184.8	190.0	198.4	208.9	222.0	244.0	281.1
67.5°	139.9	141.5	142.0	145.2	149.7	153.0	158.1	167.4	176.5	195.1	216.2
70°	113.1	112.6	113.1	114.7	120.4	126.2	133.0	139.8	145.5	158.6	176.4
72.5°	97.2	96.2	97.6	97.9	100.7	102.3	106.6	113.0	120.4	129.3	142.1
75°	75.4	75.4	75.4	75.4	77.5	78.5	80.1	81.7	84.3	88.5	97.9
77.5°	55.7	55.8	56.5	57.1	57.5	58.1	59.1	60.6	61.6	63.8	67.9
80°	44.0	44.5	44.0	44.5	44.5	45.5	46.1	47.6	48.2	50.8	52.4
82.5°	33.1	32.8	33.1	33.6	33.6	34.7	34.8	35.9	36.0	37.4	39.0
85°	17.8	16.8	17.8	17.3	18.3	17.3	17.8	18.8	18.8	19.4	21.5
87.5°	7.5	8.4	7.5	7.8	7.9	8.1	8.0	7.9	8.6	8.3	8.4
90°	16.5	17.1	16.5	16.0	16.5	15.4	14.8	14.3	13.7	14.3	12.5
92.5°	27.5	28.5	27.9	29.7	30.7	33.7	38.1	48.0	66.2	87.7	96.5
95°	66.2	68.4	72.4	77.6	88.4	108.9	139.2	205.3	274.3	338.2	301.2
97.5°	180.1	185.0	200.4	226.1	268.2	336.4	410.0	511.9	560.8	524.2	383.7
100°	357.6	357.1	379.3	420.9	478.5	559.5	626.3	672.5	652.5	540.1	365.0
102.5°	524.6	537.7	556.3	589.3	634.1	685.5	724.4	725.9	657.1	510.5	337.7
105°	725.5	728.4	746.6	768.3	794.5	809.4	798.5	741.5	622.3	458.6	304.0
107.5°	841.2	846.4	852.6	859.9	859.4	839.1	789.2	696.5	561.4	412.7	282.6
110°	888.6	889.8	890.9	886.4	870.4	830.5	758.6	653.6	523.0	386.7	274.3



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	898.2	898.0	893.7	879.5	850.3	799.0	718.4	611.2	489.7	369.4	269.8
115°	882.4	879.5	868.1	843.0	800.2	738.1	654.2	555.0	449.5	350.8	268.1
117.5°	831.9	828.1	811.6	782.9	738.3	675.2	599.9	514.2	425.2	339.8	269.1
120°	790.0	786.5	772.9	740.9	695.9	638.2	569.8	492.8	412.4	334.8	270.9
122.5°	750.7	746.4	731.3	702.6	662.5	609.0	545.6	475.9	401.9	331.6	274.1
125°	695.9	691.9	677.6	652.5	616.0	570.4	515.6	453.4	388.4	327.4	278.9
127.5°	650.7	647.0	634.1	612.7	580.2	538.7	489.3	433.8	376.6	325.3	284.4
130°	625.1	620.6	608.6	588.1	557.8	519.0	472.8	421.5	370.2	324.0	288.0
132.5°	600.0	596.8	586.2	565.7	537.3	500.3	457.3	410.1	364.2	323.5	290.8
135°	564.1	560.1	549.8	532.7	504.8	472.3	435.2	394.7	356.5	322.8	294.9
137.5°	526.1	523.5	514.8	497.5	474.0	445.8	413.9	380.7	349.8	321.6	297.6
140°	499.6	500.2	491.1	475.1	453.4	428.9	401.5	372.5	345.6	321.1	299.4
142.5°	475.0	475.6	467.4	453.2	434.7	413.4	389.7	364.7	342.0	320.2	300.8
145°	440.9	439.8	435.2	423.2	409.0	392.4	374.2	355.3	337.1	318.8	301.7
147.5°	412.8	412.4	408.0	399.9	389.1	377.4	362.6	347.7	332.3	316.7	301.7
150°	396.4	396.4	393.0	386.7	378.2	367.3	355.3	342.2	329.1	314.8	301.7
152.5°	382.7	382.7	380.7	374.8	368.1	359.1	348.5	337.2	325.5	312.6	300.4
155°	365.6	365.0	363.9	359.3	354.2	347.4	338.8	329.7	320.0	308.6	298.9
157.5°	350.0	350.1	349.2	345.8	341.3	336.0	329.3	321.7	313.8	305.0	296.9
160°	339.9	340.5	340.5	337.1	333.1	329.1	323.4	317.1	309.7	302.3	296.0
162.5°	330.8	331.4	331.4	328.4	325.8	322.3	317.0	311.7	305.6	299.6	294.2
165°	318.8	318.8	319.4	317.1	314.8	312.0	308.0	304.6	300.0	295.5	291.5
167.5°	307.4	307.4	308.0	306.4	305.4	303.3	301.0	298.4	294.7	291.3	288.7
170°	300.6	300.6	301.2	300.0	299.4	298.3	296.0	294.3	291.5	288.6	286.9
172.5°	294.2	294.7	295.7	294.5	294.4	293.7	291.9	290.7	288.3	286.3	285.5
175°	286.9	287.5	288.0	287.5	287.5	287.5	286.3	285.8	284.6	283.5	283.5
177.5°	282.7	282.7	283.6	283.1	283.6	283.6	283.1	282.7	282.2	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1262.8	1261.5	1255.7	1249.0	1240.2	1234.3	1229.7	1227.2	1219.7	1210.4	1204.2
5°	1340.8	1325.1	1308.4	1287.9	1269.1	1249.7	1237.7	1223.5	1206.3	1186.9	1173.3
7.5°	1424.4	1393.6	1360.4	1326.2	1292.3	1262.0	1235.2	1212.2	1184.7	1156.9	1137.5
10°	1488.5	1443.4	1396.8	1349.2	1305.7	1264.9	1233.5	1202.6	1169.6	1137.7	1113.6
12.5°	1546.7	1487.4	1433.7	1375.2	1319.6	1270.8	1225.5	1189.2	1149.5	1115.5	1088.0
15°	1620.4	1559.7	1494.7	1405.7	1331.9	1270.1	1215.2	1167.5	1119.4	1077.5	1050.8
17.5°	1689.3	1597.9	1510.7	1436.4	1340.5	1263.3	1196.2	1139.2	1086.4	1042.0	1009.1
20°	1717.8	1629.3	1534.5	1439.8	1345.5	1259.1	1181.1	1118.3	1063.3	1013.1	982.7
22.5°	1734.9	1634.7	1534.9	1433.1	1333.0	1243.2	1166.1	1096.9	1037.4	989.6	952.1
25°	1754.9	1635.6	1525.6	1425.1	1323.0	1225.6	1134.0	1060.7	996.3	945.5	905.7
27.5°	1768.1	1627.7	1497.8	1386.0	1282.5	1185.5	1101.5	1023.9	958.5	904.8	862.1
30°	1770.6	1621.4	1476.4	1355.5	1250.2	1161.2	1072.2	997.9	928.8	871.7	831.9
32.5°	1774.0	1605.9	1447.5	1319.0	1211.3	1123.1	1042.5	971.5	900.7	844.5	803.9
35°	1760.2	1597.4	1403.6	1256.0	1148.1	1062.8	990.0	924.6	855.0	800.5	759.1
37.5°	1700.7	1563.3	1358.2	1185.0	1072.2	993.2	933.9	876.8	813.0	754.2	715.3
40°	1640.8	1529.8	1323.0	1141.9	1024.1	942.9	889.5	842.9	781.1	726.2	684.3
42.5°	1551.6	1484.2	1289.5	1096.6	969.6	891.4	846.4	802.7	748.5	692.7	653.3
45°	1387.9	1396.8	1220.9	1024.6	894.2	815.7	773.3	742.9	694.8	648.7	608.4
47.5°	1182.7	1265.9	1140.4	947.8	814.7	741.0	704.0	677.5	645.0	599.8	563.0
50°	1048.7	1167.5	1075.9	896.3	764.9	691.6	655.0	633.5	605.2	569.6	534.5
52.5°	925.1	1052.8	998.0	838.9	710.9	643.9	608.1	590.4	567.9	534.4	502.7
55°	754.4	883.8	871.2	752.3	629.8	569.6	542.4	522.5	507.3	482.2	457.1
57.5°	610.3	732.9	739.4	656.0	558.4	498.9	475.5	460.5	450.6	431.6	408.4
60°	519.4	631.9	653.9	591.1	507.3	455.0	431.9	419.9	412.0	396.9	379.1
62.5°	444.0	539.8	564.7	519.5	458.3	409.3	391.3	379.7	374.3	361.2	345.5
65°	339.8	419.4	443.4	418.3	386.4	347.1	332.5	322.5	317.8	310.5	298.9
67.5°	255.5	313.5	339.9	322.2	310.7	285.9	276.5	271.2	267.0	262.0	252.4
70°	205.2	248.2	275.4	270.7	261.3	248.2	241.4	237.7	233.5	229.3	220.9
72.5°	165.0	194.6	220.1	222.5	214.8	212.1	206.2	204.6	202.1	197.1	192.5
75°	109.4	129.8	147.6	154.4	157.6	160.2	157.6	157.1	156.5	152.4	149.7
77.5°	71.7	82.7	93.9	105.5	110.5	114.0	114.9	116.8	115.4	113.2	111.9
80°	55.0	57.6	65.4	75.4	83.2	86.4	88.5	89.5	89.0	88.5	86.4
82.5°	39.9	42.1	45.8	52.8	59.4	64.6	65.9	65.7	66.8	67.1	65.4
85°	21.5	22.0	23.0	24.1	27.7	33.5	35.1	36.1	37.2	37.2	34.0
87.5°	8.9	8.1	8.6	8.4	9.4	9.5	11.8	13.6	14.3	12.8	13.2
90°	10.8	9.1	7.4	6.3	5.1	3.4	2.3	1.1	2.3	3.4	5.1
92.5°	72.4	47.9	33.0	24.5	19.7	15.3	10.5	7.1	10.5	15.3	19.7
95°	207.6	122.6	74.1	51.9	37.1	27.4	21.1	19.4	21.1	27.4	37.1
97.5°	227.8	132.0	85.7	61.6	47.0	38.6	33.7	33.1	33.7	38.6	47.0
100°	215.0	130.6	90.7	68.4	54.8	46.8	42.8	42.2	42.8	46.8	54.8
102.5°	204.1	132.4	96.6	76.2	63.9	56.4	52.8	51.8	52.8	56.4	63.9
105°	196.2	137.5	106.7	89.0	78.1	71.3	67.9	66.2	67.9	71.3	78.1
107.5°	195.6	146.8	119.8	103.4	93.2	86.5	83.2	81.4	83.2	86.5	93.2
110°	197.9	154.6	128.9	112.9	103.2	97.0	94.1	92.4	94.1	97.0	103.2



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	202.5	162.3	138.5	123.0	113.3	107.0	104.2	102.4	104.2	107.0	113.3
115°	209.9	175.1	153.4	138.0	128.3	122.6	119.2	116.9	119.2	122.6	128.3
117.5°	219.7	188.7	167.2	153.0	142.1	136.9	134.0	131.4	134.0	136.9	142.1
120°	227.0	197.3	176.8	162.6	151.7	146.0	143.2	141.5	143.2	146.0	151.7
122.5°	233.9	206.5	186.4	171.2	160.8	154.7	151.8	150.1	151.8	154.7	160.8
125°	244.7	219.6	199.6	184.2	173.4	167.1	163.7	162.6	163.7	167.1	173.4
127.5°	253.6	231.0	211.7	196.3	184.3	178.0	173.7	172.0	173.7	178.0	184.3
130°	259.5	237.8	219.0	203.6	191.6	184.8	179.7	178.0	179.7	184.8	191.6
132.5°	265.0	243.8	225.4	210.5	198.5	190.3	184.7	182.5	184.7	190.3	198.5
135°	272.1	252.7	235.0	219.6	207.6	199.1	192.8	190.5	192.8	199.1	207.6
137.5°	277.3	258.8	241.8	227.6	215.7	206.6	200.4	198.0	200.4	206.6	215.7
140°	280.1	262.9	246.4	232.1	220.7	211.6	205.9	203.1	205.9	211.6	220.7
142.5°	282.8	266.1	250.1	236.7	225.3	217.1	210.9	208.5	210.9	217.1	225.3
145°	285.8	270.4	255.5	242.4	232.7	224.2	219.0	217.3	219.0	224.2	232.7
147.5°	287.6	273.8	260.2	249.0	239.7	232.3	227.2	226.2	227.2	232.3	239.7
150°	288.0	276.1	262.9	252.7	244.7	237.3	232.7	232.1	232.7	237.3	244.7
152.5°	289.0	277.4	266.1	256.3	249.3	242.8	238.2	238.1	238.2	242.8	249.3
155°	289.2	280.1	270.4	262.4	256.1	250.4	247.0	247.0	247.0	250.4	256.1
157.5°	289.8	281.5	273.8	267.6	262.3	257.2	254.5	254.0	254.5	257.2	262.3
160°	289.8	282.9	276.1	270.4	266.4	261.8	259.5	259.5	259.5	261.8	266.4
162.5°	289.3	283.4	277.4	272.6	269.1	265.5	263.6	263.6	263.6	265.5	269.1
165°	288.0	284.0	279.5	275.5	273.2	270.4	269.2	269.8	269.2	270.4	273.2
167.5°	287.1	283.9	280.6	278.1	276.5	274.3	273.8	274.5	273.8	274.3	276.5
170°	285.8	283.5	280.6	279.5	278.3	276.6	276.1	277.2	276.1	276.6	278.3
172.5°	285.3	283.5	281.1	280.4	279.7	278.5	278.3	279.0	278.3	278.5	279.7
175°	284.0	282.9	281.8	281.2	281.2	280.1	280.6	281.2	280.6	280.1	281.2
177.5°	283.1	282.2	281.8	281.8	281.8	281.3	281.8	282.2	281.8	281.3	281.8
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1202.1	1196.6	1192.9	1184.5	1179.0	1173.2	1167.3	1171.1	1170.7	1170.2	1170.2
5°	1161.8	1149.7	1138.7	1124.6	1115.7	1104.7	1096.3	1095.3	1097.4	1090.0	1085.8
7.5°	1121.8	1105.3	1089.7	1074.1	1057.6	1044.4	1036.1	1032.2	1026.9	1022.4	1017.7
10°	1093.7	1074.3	1059.1	1039.8	1022.0	1006.3	996.3	989.5	985.8	982.2	975.4
12.5°	1064.8	1045.8	1026.5	1004.6	987.6	969.4	962.0	954.3	947.3	943.2	933.9
15°	1022.5	997.9	977.5	954.4	935.6	917.8	907.3	892.1	890.0	884.8	875.4
17.5°	980.1	953.4	925.2	908.2	886.9	868.4	852.4	847.3	832.3	826.7	818.5
20°	946.6	922.0	900.5	878.0	847.1	829.8	817.3	810.5	798.4	791.1	785.8
22.5°	917.7	892.7	867.8	841.6	816.1	796.7	787.5	776.9	770.4	760.1	754.4
25°	876.4	849.2	819.4	791.1	772.8	758.1	743.4	734.0	724.6	719.9	709.4
27.5°	828.5	800.0	772.1	750.7	728.2	713.7	700.4	692.0	680.7	672.8	667.0
30°	802.1	768.6	744.5	725.1	696.3	682.7	672.8	662.3	653.9	645.5	639.8
32.5°	771.5	740.9	718.1	694.1	672.0	657.2	644.3	635.1	627.9	620.0	614.2
35°	723.5	697.9	674.3	650.2	634.0	618.8	603.7	595.8	589.0	581.7	576.4
37.5°	680.2	656.2	633.8	611.0	590.9	578.5	566.3	560.3	551.1	546.2	540.8
40°	653.4	629.8	605.7	583.8	562.8	553.4	542.4	533.5	525.1	521.5	515.7
42.5°	624.1	600.5	580.2	556.5	539.4	526.6	516.4	506.7	500.4	495.1	491.8
45°	580.6	559.7	539.8	516.2	500.0	489.0	477.5	468.6	462.8	459.2	453.4
47.5°	538.4	517.5	497.3	476.7	461.0	448.5	437.0	430.8	423.1	418.6	414.8
50°	507.8	489.0	467.5	448.7	433.0	420.4	411.0	403.1	396.3	390.6	388.0
52.5°	479.8	459.7	441.1	423.6	407.0	392.8	384.2	375.9	370.8	364.2	361.1
55°	433.5	414.1	398.4	381.1	364.9	352.9	342.4	335.1	329.8	322.5	318.3
57.5°	390.0	372.7	353.9	338.9	322.2	312.0	303.3	293.4	287.0	281.3	277.2
60°	360.7	340.8	324.6	310.5	295.8	282.7	274.9	267.0	260.2	254.4	250.8
62.5°	330.2	312.8	297.4	282.0	268.6	257.2	248.1	241.5	235.5	231.8	228.2
65°	283.2	269.6	253.9	241.4	228.8	220.4	213.1	207.3	203.1	200.5	197.4
67.5°	240.1	226.9	213.2	200.8	192.5	186.1	181.3	176.3	174.2	170.9	168.8
70°	212.0	198.4	186.4	177.0	168.6	163.9	160.7	157.1	155.0	150.8	148.7
72.5°	181.5	171.6	162.9	155.2	148.5	144.2	140.2	135.7	132.4	127.7	125.7
75°	142.9	134.0	127.2	122.0	117.8	112.0	106.3	101.6	100.0	98.4	97.9
77.5°	105.9	100.2	95.3	90.9	85.7	81.5	80.2	79.2	78.8	78.0	78.0
80°	83.2	78.0	74.3	69.1	66.0	66.0	66.0	64.9	65.4	65.4	65.4
82.5°	61.9	57.1	55.1	53.2	52.6	53.0	53.0	53.2	52.9	53.7	53.3
85°	31.9	32.5	33.5	33.0	33.5	33.5	34.6	34.0	34.6	33.5	34.6
87.5°	13.0	14.5	15.2	16.0	16.8	16.7	17.0	17.1	17.6	17.7	18.0
90°	6.3	7.4	9.1	10.8	12.5	14.3	13.7	14.3	14.8	15.4	16.5
92.5°	24.5	33.0	47.9	72.4	96.5	87.7	66.2	48.0	38.1	33.7	30.7
95°	51.9	74.1	122.6	207.6	301.2	338.2	274.3	205.3	139.2	108.9	88.4
97.5°	61.6	85.7	132.0	227.8	383.7	524.2	560.8	511.9	410.0	336.4	268.2
100°	68.4	90.7	130.6	215.0	365.0	540.1	652.5	672.5	626.3	559.5	478.5
102.5°	76.2	96.6	132.4	204.1	337.7	510.5	657.1	725.9	724.4	685.5	634.1
105°	89.0	106.7	137.5	196.2	304.0	458.6	622.3	741.5	798.5	809.4	794.5
107.5°	103.4	119.8	146.8	195.6	282.6	412.7	561.4	696.5	789.2	839.1	859.4
110°	112.9	128.9	154.6	197.9	274.3	386.7	523.0	653.6	758.6	830.5	870.4



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	123.0	138.5	162.3	202.5	269.8	369.4	489.7	611.2	718.4	799.0	850.3
115°	138.0	153.4	175.1	209.9	268.1	350.8	449.5	555.0	654.2	738.1	800.2
117.5°	153.0	167.2	188.7	219.7	269.1	339.8	425.2	514.2	599.9	675.2	738.3
120°	162.6	176.8	197.3	227.0	270.9	334.8	412.4	492.8	569.8	638.2	695.9
122.5°	171.2	186.4	206.5	233.9	274.1	331.6	401.9	475.9	545.6	609.0	662.5
125°	184.2	199.6	219.6	244.7	278.9	327.4	388.4	453.4	515.6	570.4	616.0
127.5°	196.3	211.7	231.0	253.6	284.4	325.3	376.6	433.8	489.3	538.7	580.2
130°	203.6	219.0	237.8	259.5	288.0	324.0	370.2	421.5	472.8	519.0	557.8
132.5°	210.5	225.4	243.8	265.0	290.8	323.5	364.2	410.1	457.3	500.3	537.3
135°	219.6	235.0	252.7	272.1	294.9	322.8	356.5	394.7	435.2	472.3	504.8
137.5°	227.6	241.8	258.8	277.3	297.6	321.6	349.8	380.7	413.9	445.8	474.0
140°	232.1	246.4	262.9	280.1	299.4	321.1	345.6	372.5	401.5	428.9	453.4
142.5°	236.7	250.1	266.1	282.8	300.8	320.2	342.0	364.7	389.7	413.4	434.7
145°	242.4	255.5	270.4	285.8	301.7	318.8	337.1	355.3	374.2	392.4	409.0
147.5°	249.0	260.2	273.8	287.6	301.7	316.7	332.3	347.7	362.6	377.4	389.1
150°	252.7	262.9	276.1	288.0	301.7	314.8	329.1	342.2	355.3	367.3	378.2
152.5°	256.3	266.1	277.4	289.0	300.4	312.6	325.5	337.2	348.5	359.1	368.1
155°	262.4	270.4	280.1	289.2	298.9	308.6	320.0	329.7	338.8	347.4	354.2
157.5°	267.6	273.8	281.5	289.8	296.9	305.0	313.8	321.7	329.3	336.0	341.3
160°	270.4	276.1	282.9	289.8	296.0	302.3	309.7	317.1	323.4	329.1	333.1
162.5°	272.6	277.4	283.4	289.3	294.2	299.6	305.6	311.7	317.0	322.3	325.8
165°	275.5	279.5	284.0	288.0	291.5	295.5	300.0	304.6	308.0	312.0	314.8
167.5°	278.1	280.6	283.9	287.1	288.7	291.3	294.7	298.4	301.0	303.3	305.4
170°	279.5	280.6	283.5	285.8	286.9	288.6	291.5	294.3	296.0	298.3	299.4
172.5°	280.4	281.1	283.5	285.3	285.5	286.3	288.3	290.7	291.9	293.7	294.4
175°	281.2	281.8	282.9	284.0	283.5	283.5	284.6	285.8	286.3	287.5	287.5
177.5°	281.8	281.8	282.2	283.1	282.2	281.8	282.2	282.7	283.1	283.6	283.6
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1165.2	1164.8	1165.2	1163.5	1165.2	1164.8	1165.2	1170.2	1170.2	1170.7	1171.1
5°	1084.3	1083.7	1082.2	1077.5	1082.2	1083.7	1084.3	1085.8	1090.0	1097.4	1095.3
7.5°	1013.6	1012.9	1008.3	1008.4	1008.3	1012.9	1013.6	1017.7	1022.4	1026.9	1032.2
10°	971.7	972.2	966.0	962.3	966.0	972.2	971.7	975.4	982.2	985.8	989.5
12.5°	931.1	928.7	923.6	919.6	923.6	928.7	931.1	933.9	943.2	947.3	954.3
15°	877.5	872.2	859.7	860.7	859.7	872.2	877.5	875.4	884.8	890.0	892.1
17.5°	814.3	810.5	810.2	802.9	810.2	810.5	814.3	818.5	826.7	832.3	847.3
20°	777.5	774.9	775.9	768.6	775.9	774.9	777.5	785.8	791.1	798.4	810.5
22.5°	748.6	746.0	741.6	739.3	741.6	746.0	748.6	754.4	760.1	770.4	776.9
25°	706.3	702.1	697.9	700.5	697.9	702.1	706.3	709.4	719.9	724.6	734.0
27.5°	664.0	660.8	656.6	656.1	656.6	660.8	664.0	667.0	672.8	680.7	692.0
30°	637.2	634.0	631.9	629.3	631.9	634.0	637.2	639.8	645.5	653.9	662.3
32.5°	609.9	609.3	605.5	605.0	605.5	609.3	609.9	614.2	620.0	627.9	635.1
35°	574.3	571.2	570.1	570.7	570.1	571.2	574.3	576.4	581.7	589.0	595.8
37.5°	540.5	536.3	534.4	532.6	534.4	536.3	540.5	540.8	546.2	551.1	560.3
40°	516.2	512.0	511.0	509.9	511.0	512.0	516.2	515.7	521.5	525.1	533.5
42.5°	489.0	487.3	486.7	484.8	486.7	487.3	489.0	491.8	495.1	500.4	506.7
45°	451.8	451.3	448.2	449.2	448.2	451.3	451.8	453.4	459.2	462.8	468.6
47.5°	412.7	410.4	408.2	409.6	408.2	410.4	412.7	414.8	418.6	423.1	430.8
50°	385.9	384.8	380.1	381.1	380.1	384.8	385.9	388.0	390.6	396.3	403.1
52.5°	359.1	355.1	353.3	352.7	353.3	355.1	359.1	361.1	364.2	370.8	375.9
55°	314.7	309.9	307.8	306.8	307.8	309.9	314.7	318.3	322.5	329.8	335.1
57.5°	271.1	269.8	268.2	269.3	268.2	269.8	271.1	277.2	281.3	287.0	293.4
60°	245.5	245.5	245.5	245.0	245.5	245.5	245.5	250.8	254.4	260.2	267.0
62.5°	225.9	224.6	224.2	224.9	224.2	224.6	225.9	228.2	231.8	235.5	241.5
65°	195.8	195.3	193.2	192.7	193.2	195.3	195.8	197.4	200.5	203.1	207.3
67.5°	167.4	165.5	164.9	164.2	164.9	165.5	167.4	168.8	170.9	174.2	176.3
70°	146.1	145.0	141.9	142.4	141.9	145.0	146.1	148.7	150.8	155.0	157.1
72.5°	123.0	122.0	121.4	120.6	121.4	122.0	123.0	125.7	127.7	132.4	135.7
75°	97.4	96.9	96.3	98.4	96.3	96.9	97.4	97.9	98.4	100.0	101.6
77.5°	78.0	78.0	78.3	77.5	78.3	78.0	78.0	78.0	78.0	78.8	79.2
80°	65.4	65.4	64.9	64.9	64.9	65.4	65.4	65.4	65.4	65.4	64.9
82.5°	52.5	52.9	53.2	52.4	53.2	52.9	52.5	53.3	53.7	52.9	53.2
85°	34.6	34.0	35.1	34.6	35.1	34.0	34.6	34.6	33.5	34.6	34.0
87.5°	18.7	18.0	18.1	18.4	18.1	18.0	18.7	18.0	17.7	17.6	17.1
90°	16.0	16.5	17.1	16.5	17.1	16.5	16.0	16.5	15.4	14.8	14.3
92.5°	29.7	27.9	28.5	27.5	28.5	27.9	29.7	30.7	33.7	38.1	48.0
95°	77.6	72.4	68.4	66.2	68.4	72.4	77.6	88.4	108.9	139.2	205.3
97.5°	226.1	200.4	185.0	180.1	185.0	200.4	226.1	268.2	336.4	410.0	511.9
100°	420.9	379.3	357.1	357.6	357.1	379.3	420.9	478.5	559.5	626.3	672.5
102.5°	589.3	556.3	537.7	524.6	537.7	556.3	589.3	634.1	685.5	724.4	725.9
105°	768.3	746.6	728.4	725.5	728.4	746.6	768.3	794.5	809.4	798.5	741.5
107.5°	859.9	852.6	846.4	841.2	846.4	852.6	859.9	859.4	839.1	789.2	696.5
110°	886.4	890.9	889.8	888.6	889.8	890.9	886.4	870.4	830.5	758.6	653.6



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	879.5	893.7	898.0	898.2	898.0	893.7	879.5	850.3	799.0	718.4	611.2
115°	843.0	868.1	879.5	882.4	879.5	868.1	843.0	800.2	738.1	654.2	555.0
117.5°	782.9	811.6	828.1	831.9	828.1	811.6	782.9	738.3	675.2	599.9	514.2
120°	740.9	772.9	786.5	790.0	786.5	772.9	740.9	695.9	638.2	569.8	492.8
122.5°	702.6	731.3	746.4	750.7	746.4	731.3	702.6	662.5	609.0	545.6	475.9
125°	652.5	677.6	691.9	695.9	691.9	677.6	652.5	616.0	570.4	515.6	453.4
127.5°	612.7	634.1	647.0	650.7	647.0	634.1	612.7	580.2	538.7	489.3	433.8
130°	588.1	608.6	620.6	625.1	620.6	608.6	588.1	557.8	519.0	472.8	421.5
132.5°	565.7	586.2	596.8	600.0	596.8	586.2	565.7	537.3	500.3	457.3	410.1
135°	532.7	549.8	560.1	564.1	560.1	549.8	532.7	504.8	472.3	435.2	394.7
137.5°	497.5	514.8	523.5	526.1	523.5	514.8	497.5	474.0	445.8	413.9	380.7
140°	475.1	491.1	500.2	499.6	500.2	491.1	475.1	453.4	428.9	401.5	372.5
142.5°	453.2	467.4	475.6	475.0	475.6	467.4	453.2	434.7	413.4	389.7	364.7
145°	423.2	435.2	439.8	440.9	439.8	435.2	423.2	409.0	392.4	374.2	355.3
147.5°	399.9	408.0	412.4	412.8	412.4	408.0	399.9	389.1	377.4	362.6	347.7
150°	386.7	393.0	396.4	396.4	396.4	393.0	386.7	378.2	367.3	355.3	342.2
152.5°	374.8	380.7	382.7	382.7	382.7	380.7	374.8	368.1	359.1	348.5	337.2
155°	359.3	363.9	365.0	365.6	365.0	363.9	359.3	354.2	347.4	338.8	329.7
157.5°	345.8	349.2	350.1	350.0	350.1	349.2	345.8	341.3	336.0	329.3	321.7
160°	337.1	340.5	340.5	339.9	340.5	340.5	337.1	333.1	329.1	323.4	317.1
162.5°	328.4	331.4	331.4	330.8	331.4	331.4	328.4	325.8	322.3	317.0	311.7
165°	317.1	319.4	318.8	318.8	318.8	319.4	317.1	314.8	312.0	308.0	304.6
167.5°	306.4	308.0	307.4	307.4	307.4	308.0	306.4	305.4	303.3	301.0	298.4
170°	300.0	301.2	300.6	300.6	300.6	301.2	300.0	299.4	298.3	296.0	294.3
172.5°	294.5	295.7	294.7	294.2	294.7	295.7	294.5	294.4	293.7	291.9	290.7
175°	287.5	288.0	287.5	286.9	287.5	288.0	287.5	287.5	287.5	286.3	285.8
177.5°	283.1	283.6	282.7	282.7	282.7	283.6	283.1	283.6	283.6	283.1	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1167.3	1173.2	1179.0	1184.5	1192.9	1196.6	1202.1	1204.2	1210.4	1219.7	1227.2
5°	1096.3	1104.7	1115.7	1124.6	1138.7	1149.7	1161.8	1173.3	1186.9	1206.3	1223.5
7.5°	1036.1	1044.4	1057.6	1074.1	1089.7	1105.3	1121.8	1137.5	1156.9	1184.7	1212.2
10°	996.3	1006.3	1022.0	1039.8	1059.1	1074.3	1093.7	1113.6	1137.7	1169.6	1202.6
12.5°	962.0	969.4	987.6	1004.6	1026.5	1045.8	1064.8	1088.0	1115.5	1149.5	1189.2
15°	907.3	917.8	935.6	954.4	977.5	997.9	1022.5	1050.8	1077.5	1119.4	1167.5
17.5°	852.4	868.4	886.9	908.2	925.2	953.4	980.1	1009.1	1042.0	1086.4	1139.2
20°	817.3	829.8	847.1	878.0	900.5	922.0	946.6	982.7	1013.1	1063.3	1118.3
22.5°	787.5	796.7	816.1	841.6	867.8	892.7	917.7	952.1	989.6	1037.4	1096.9
25°	743.4	758.1	772.8	791.1	819.4	849.2	876.4	905.7	945.5	996.3	1060.7
27.5°	700.4	713.7	728.2	750.7	772.1	800.0	828.5	862.1	904.8	958.5	1023.9
30°	672.8	682.7	696.3	725.1	744.5	768.6	802.1	831.9	871.7	928.8	997.9
32.5°	644.3	657.2	672.0	694.1	718.1	740.9	771.5	803.9	844.5	900.7	971.5
35°	603.7	618.8	634.0	650.2	674.3	697.9	723.5	759.1	800.5	855.0	924.6
37.5°	566.3	578.5	590.9	611.0	633.8	656.2	680.2	715.3	754.2	813.0	876.8
40°	542.4	553.4	562.8	583.8	605.7	629.8	653.4	684.3	726.2	781.1	842.9
42.5°	516.4	526.6	539.4	556.5	580.2	600.5	624.1	653.3	692.7	748.5	802.7
45°	477.5	489.0	500.0	516.2	539.8	559.7	580.6	608.4	648.7	694.8	742.9
47.5°	437.0	448.5	461.0	476.7	497.3	517.5	538.4	563.0	599.8	645.0	677.5
50°	411.0	420.4	433.0	448.7	467.5	489.0	507.8	534.5	569.6	605.2	633.5
52.5°	384.2	392.8	407.0	423.6	441.1	459.7	479.8	502.7	534.4	567.9	590.4
55°	342.4	352.9	364.9	381.1	398.4	414.1	433.5	457.1	482.2	507.3	522.5
57.5°	303.3	312.0	322.2	338.9	353.9	372.7	390.0	408.4	431.6	450.6	460.5
60°	274.9	282.7	295.8	310.5	324.6	340.8	360.7	379.1	396.9	412.0	419.9
62.5°	248.1	257.2	268.6	282.0	297.4	312.8	330.2	345.5	361.2	374.3	379.7
65°	213.1	220.4	228.8	241.4	253.9	269.6	283.2	298.9	310.5	317.8	322.5
67.5°	181.3	186.1	192.5	200.8	213.2	226.9	240.1	252.4	262.0	267.0	271.2
70°	160.7	163.9	168.6	177.0	186.4	198.4	212.0	220.9	229.3	233.5	237.7
72.5°	140.2	144.2	148.5	155.2	162.9	171.6	181.5	192.5	197.1	202.1	204.6
75°	106.3	112.0	117.8	122.0	127.2	134.0	142.9	149.7	152.4	156.5	157.1
77.5°	80.2	81.5	85.7	90.9	95.3	100.2	105.9	111.9	113.2	115.4	116.8
80°	66.0	66.0	66.0	69.1	74.3	78.0	83.2	86.4	88.5	89.0	89.5
82.5°	53.0	53.0	52.6	53.2	55.1	57.1	61.9	65.4	67.1	66.8	65.7
85°	34.6	33.5	33.5	33.0	33.5	32.5	31.9	34.0	37.2	37.2	36.1
87.5°	17.0	16.7	16.8	16.0	15.2	14.5	13.0	13.2	12.8	14.3	13.6
90°	13.7	14.3	12.5	10.8	9.1	7.4	6.3	5.1	3.4	2.3	1.1
92.5°	66.2	87.7	96.5	72.4	47.9	33.0	24.5	19.7	15.3	10.5	7.1
95°	274.3	338.2	301.2	207.6	122.6	74.1	51.9	37.1	27.4	21.1	19.4
97.5°	560.8	524.2	383.7	227.8	132.0	85.7	61.6	47.0	38.6	33.7	33.1
100°	652.5	540.1	365.0	215.0	130.6	90.7	68.4	54.8	46.8	42.8	42.2
102.5°	657.1	510.5	337.7	204.1	132.4	96.6	76.2	63.9	56.4	52.8	51.8
105°	622.3	458.6	304.0	196.2	137.5	106.7	89.0	78.1	71.3	67.9	66.2
107.5°	561.4	412.7	282.6	195.6	146.8	119.8	103.4	93.2	86.5	83.2	81.4
110°	523.0	386.7	274.3	197.9	154.6	128.9	112.9	103.2	97.0	94.1	92.4



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	489.7	369.4	269.8	202.5	162.3	138.5	123.0	113.3	107.0	104.2	102.4
115°	449.5	350.8	268.1	209.9	175.1	153.4	138.0	128.3	122.6	119.2	116.9
117.5°	425.2	339.8	269.1	219.7	188.7	167.2	153.0	142.1	136.9	134.0	131.4
120°	412.4	334.8	270.9	227.0	197.3	176.8	162.6	151.7	146.0	143.2	141.5
122.5°	401.9	331.6	274.1	233.9	206.5	186.4	171.2	160.8	154.7	151.8	150.1
125°	388.4	327.4	278.9	244.7	219.6	199.6	184.2	173.4	167.1	163.7	162.6
127.5°	376.6	325.3	284.4	253.6	231.0	211.7	196.3	184.3	178.0	173.7	172.0
130°	370.2	324.0	288.0	259.5	237.8	219.0	203.6	191.6	184.8	179.7	178.0
132.5°	364.2	323.5	290.8	265.0	243.8	225.4	210.5	198.5	190.3	184.7	182.5
135°	356.5	322.8	294.9	272.1	252.7	235.0	219.6	207.6	199.1	192.8	190.5
137.5°	349.8	321.6	297.6	277.3	258.8	241.8	227.6	215.7	206.6	200.4	198.0
140°	345.6	321.1	299.4	280.1	262.9	246.4	232.1	220.7	211.6	205.9	203.1
142.5°	342.0	320.2	300.8	282.8	266.1	250.1	236.7	225.3	217.1	210.9	208.5
145°	337.1	318.8	301.7	285.8	270.4	255.5	242.4	232.7	224.2	219.0	217.3
147.5°	332.3	316.7	301.7	287.6	273.8	260.2	249.0	239.7	232.3	227.2	226.2
150°	329.1	314.8	301.7	288.0	276.1	262.9	252.7	244.7	237.3	232.7	232.1
152.5°	325.5	312.6	300.4	289.0	277.4	266.1	256.3	249.3	242.8	238.2	238.1
155°	320.0	308.6	298.9	289.2	280.1	270.4	262.4	256.1	250.4	247.0	247.0
157.5°	313.8	305.0	296.9	289.8	281.5	273.8	267.6	262.3	257.2	254.5	254.0
160°	309.7	302.3	296.0	289.8	282.9	276.1	270.4	266.4	261.8	259.5	259.5
162.5°	305.6	299.6	294.2	289.3	283.4	277.4	272.6	269.1	265.5	263.6	263.6
165°	300.0	295.5	291.5	288.0	284.0	279.5	275.5	273.2	270.4	269.2	269.8
167.5°	294.7	291.3	288.7	287.1	283.9	280.6	278.1	276.5	274.3	273.8	274.5
170°	291.5	288.6	286.9	285.8	283.5	280.6	279.5	278.3	276.6	276.1	277.2
172.5°	288.3	286.3	285.5	285.3	283.5	281.1	280.4	279.7	278.5	278.3	279.0
175°	284.6	283.5	283.5	284.0	282.9	281.8	281.2	281.2	280.1	280.6	281.2
177.5°	282.2	281.8	282.2	283.1	282.2	281.8	281.8	281.8	281.3	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1229.7	1234.3	1240.2	1249.0	1255.7	1261.5	1262.8	1264.5	1268.7	1275.8	1281.2
5°	1237.7	1249.7	1269.1	1287.9	1308.4	1325.1	1340.8	1351.8	1362.3	1384.3	1402.1
7.5°	1235.2	1262.0	1292.3	1326.2	1360.4	1393.6	1424.4	1451.9	1479.3	1511.4	1547.9
10°	1233.5	1264.9	1305.7	1349.2	1396.8	1443.4	1488.5	1523.5	1564.4	1601.0	1647.6
12.5°	1225.5	1270.8	1319.6	1375.2	1433.7	1487.4	1546.7	1595.2	1641.9	1694.8	1749.0
15°	1215.2	1270.1	1331.9	1405.7	1494.7	1559.7	1620.4	1704.7	1762.3	1819.9	1897.3
17.5°	1196.2	1263.3	1340.5	1436.4	1510.7	1597.9	1689.3	1755.9	1833.5	1914.6	1984.8
20°	1181.1	1259.1	1345.5	1439.8	1534.5	1629.3	1717.8	1797.3	1877.5	1971.2	2028.8
22.5°	1166.1	1243.2	1333.0	1433.1	1534.9	1634.7	1734.9	1828.3	1918.5	2013.1	2086.6
25°	1134.0	1225.6	1323.0	1425.1	1525.6	1635.6	1754.9	1859.1	1970.6	2068.0	2137.7
27.5°	1101.5	1185.5	1282.5	1386.0	1497.8	1627.7	1768.1	1886.6	1998.3	2068.0	2089.9
30°	1072.2	1161.2	1250.2	1355.5	1476.4	1621.4	1770.6	1906.2	1997.9	2028.2	2005.7
32.5°	1042.5	1123.1	1211.3	1319.0	1447.5	1605.9	1774.0	1894.5	1949.7	1926.5	1834.8
35°	990.0	1062.8	1148.1	1256.0	1403.6	1597.4	1760.2	1841.8	1828.2	1697.3	1524.6
37.5°	933.9	993.2	1072.2	1185.0	1358.2	1563.3	1700.7	1712.7	1594.9	1394.0	1194.4
40°	889.5	942.9	1024.1	1141.9	1323.0	1529.8	1640.8	1592.1	1409.4	1185.8	1019.4
42.5°	846.4	891.4	969.6	1096.6	1289.5	1484.2	1551.6	1445.5	1234.7	1023.3	871.9
45°	773.3	815.7	894.2	1024.6	1220.9	1396.8	1387.9	1203.6	992.7	822.5	696.8
47.5°	704.0	741.0	814.7	947.8	1140.4	1265.9	1182.7	986.6	807.6	671.1	581.5
50°	655.0	691.6	764.9	896.3	1075.9	1167.5	1048.7	859.7	695.8	582.7	511.5
52.5°	608.1	643.9	710.9	838.9	998.0	1052.8	925.1	749.9	613.3	515.7	454.5
55°	542.4	569.6	629.8	752.3	871.2	883.8	754.4	607.8	495.3	427.2	385.3
57.5°	475.5	498.9	558.4	656.0	739.4	732.9	610.3	483.4	407.6	357.1	326.7
60°	431.9	455.0	507.3	591.1	653.9	631.9	519.4	417.3	352.3	315.2	291.1
62.5°	391.3	409.3	458.3	519.5	564.7	539.8	444.0	359.5	308.0	276.6	257.6
65°	332.5	347.1	386.4	418.3	443.4	419.4	339.8	281.1	244.0	222.0	208.9
67.5°	276.5	285.9	310.7	322.2	339.9	313.5	255.5	216.2	195.1	176.5	167.4
70°	241.4	248.2	261.3	270.7	275.4	248.2	205.2	176.4	158.6	145.5	139.8
72.5°	206.2	212.1	214.8	222.5	220.1	194.6	165.0	142.1	129.3	120.4	113.0
75°	157.6	160.2	157.6	154.4	147.6	129.8	109.4	97.9	88.5	84.3	81.7
77.5°	114.9	114.0	110.5	105.5	93.9	82.7	71.7	67.9	63.8	61.6	60.6
80°	88.5	86.4	83.2	75.4	65.4	57.6	55.0	52.4	50.8	48.2	47.6
82.5°	65.9	64.6	59.4	52.8	45.8	42.1	39.9	39.0	37.4	36.0	35.9
85°	35.1	33.5	27.7	24.1	23.0	22.0	21.5	21.5	19.4	18.8	18.8
87.5°	11.8	9.5	9.4	8.4	8.6	8.1	8.9	8.4	8.3	8.6	7.9
90°	2.3	3.4	5.1	6.3	7.4	9.1	10.8	12.5	14.3	13.7	14.3
92.5°	10.5	15.3	19.7	24.5	33.0	47.9	72.4	96.5	87.7	66.2	48.0
95°	21.1	27.4	37.1	51.9	74.1	122.6	207.6	301.2	338.2	274.3	205.3
97.5°	33.7	38.6	47.0	61.6	85.7	132.0	227.8	383.7	524.2	560.8	511.9
100°	42.8	46.8	54.8	68.4	90.7	130.6	215.0	365.0	540.1	652.5	672.5
102.5°	52.8	56.4	63.9	76.2	96.6	132.4	204.1	337.7	510.5	657.1	725.9
105°	67.9	71.3	78.1	89.0	106.7	137.5	196.2	304.0	458.6	622.3	741.5
107.5°	83.2	86.5	93.2	103.4	119.8	146.8	195.6	282.6	412.7	561.4	696.5
110°	94.1	97.0	103.2	112.9	128.9	154.6	197.9	274.3	386.7	523.0	653.6



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	104.2	107.0	113.3	123.0	138.5	162.3	202.5	269.8	369.4	489.7	611.2
115°	119.2	122.6	128.3	138.0	153.4	175.1	209.9	268.1	350.8	449.5	555.0
117.5°	134.0	136.9	142.1	153.0	167.2	188.7	219.7	269.1	339.8	425.2	514.2
120°	143.2	146.0	151.7	162.6	176.8	197.3	227.0	270.9	334.8	412.4	492.8
122.5°	151.8	154.7	160.8	171.2	186.4	206.5	233.9	274.1	331.6	401.9	475.9
125°	163.7	167.1	173.4	184.2	199.6	219.6	244.7	278.9	327.4	388.4	453.4
127.5°	173.7	178.0	184.3	196.3	211.7	231.0	253.6	284.4	325.3	376.6	433.8
130°	179.7	184.8	191.6	203.6	219.0	237.8	259.5	288.0	324.0	370.2	421.5
132.5°	184.7	190.3	198.5	210.5	225.4	243.8	265.0	290.8	323.5	364.2	410.1
135°	192.8	199.1	207.6	219.6	235.0	252.7	272.1	294.9	322.8	356.5	394.7
137.5°	200.4	206.6	215.7	227.6	241.8	258.8	277.3	297.6	321.6	349.8	380.7
140°	205.9	211.6	220.7	232.1	246.4	262.9	280.1	299.4	321.1	345.6	372.5
142.5°	210.9	217.1	225.3	236.7	250.1	266.1	282.8	300.8	320.2	342.0	364.7
145°	219.0	224.2	232.7	242.4	255.5	270.4	285.8	301.7	318.8	337.1	355.3
147.5°	227.2	232.3	239.7	249.0	260.2	273.8	287.6	301.7	316.7	332.3	347.7
150°	232.7	237.3	244.7	252.7	262.9	276.1	288.0	301.7	314.8	329.1	342.2
152.5°	238.2	242.8	249.3	256.3	266.1	277.4	289.0	300.4	312.6	325.5	337.2
155°	247.0	250.4	256.1	262.4	270.4	280.1	289.2	298.9	308.6	320.0	329.7
157.5°	254.5	257.2	262.3	267.6	273.8	281.5	289.8	296.9	305.0	313.8	321.7
160°	259.5	261.8	266.4	270.4	276.1	282.9	289.8	296.0	302.3	309.7	317.1
162.5°	263.6	265.5	269.1	272.6	277.4	283.4	289.3	294.2	299.6	305.6	311.7
165°	269.2	270.4	273.2	275.5	279.5	284.0	288.0	291.5	295.5	300.0	304.6
167.5°	273.8	274.3	276.5	278.1	280.6	283.9	287.1	288.7	291.3	294.7	298.4
170°	276.1	276.6	278.3	279.5	280.6	283.5	285.8	286.9	288.6	291.5	294.3
172.5°	278.3	278.5	279.7	280.4	281.1	283.5	285.3	285.5	286.3	288.3	290.7
175°	280.6	280.1	281.2	281.2	281.8	282.9	284.0	283.5	283.5	284.6	285.8
177.5°	281.8	281.3	281.8	281.8	281.8	282.2	283.1	282.2	281.8	282.2	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1290.0	1290.0	1291.7	1298.0	1298.8	1304.3	1302.6
5°	1417.8	1427.7	1431.4	1447.1	1456.5	1460.7	1452.3
7.5°	1574.0	1602.1	1615.4	1631.8	1646.4	1650.8	1639.3
10°	1687.9	1717.2	1741.9	1757.0	1771.2	1780.6	1792.6
12.5°	1798.1	1834.1	1857.5	1878.9	1893.5	1905.4	1907.4
15°	1917.8	1972.2	2013.6	2043.9	2059.1	2067.0	2063.8
17.5°	2038.5	2089.0	2118.4	2149.4	2170.4	2171.5	2172.1
20°	2106.8	2156.0	2190.0	2213.0	2236.6	2235.6	2240.8
22.5°	2152.4	2191.2	2217.2	2234.0	2242.1	2238.1	2239.1
25°	2173.8	2185.3	2180.6	2153.9	2147.1	2122.5	2126.7
27.5°	2063.6	2009.2	1952.8	1880.4	1823.2	1777.6	1779.9
30°	1914.1	1817.8	1707.8	1615.7	1533.0	1509.9	1460.7
32.5°	1705.1	1560.6	1431.8	1345.9	1274.9	1255.7	1212.8
35°	1350.8	1210.4	1078.0	998.4	967.0	923.0	922.5
37.5°	1049.9	926.4	856.3	796.6	765.3	738.7	736.1
40°	883.2	786.9	734.0	691.1	660.2	640.3	635.6
42.5°	766.8	688.9	639.4	612.8	589.0	578.7	571.1
45°	626.2	573.8	539.3	515.2	504.2	496.3	492.1
47.5°	523.8	488.7	465.1	449.1	440.2	431.9	434.1
50°	468.1	439.3	422.0	406.8	400.0	394.2	394.8
52.5°	423.2	397.4	383.4	372.5	364.0	359.9	357.9
55°	359.2	342.9	328.8	320.9	316.2	310.5	308.9
57.5°	306.4	293.8	282.3	273.4	272.2	266.7	267.4
60°	271.2	260.7	251.3	246.6	242.9	238.2	239.8
62.5°	242.3	233.5	224.9	221.0	217.4	213.9	214.7
65°	198.4	190.0	184.8	182.7	181.1	179.6	178.0
67.5°	158.1	153.0	149.7	145.2	142.0	141.5	139.9
70°	133.0	126.2	120.4	114.7	113.1	112.6	113.1
72.5°	106.6	102.3	100.7	97.9	97.6	96.2	97.2
75°	80.1	78.5	77.5	75.4	75.4	75.4	75.4
77.5°	59.1	58.1	57.5	57.1	56.5	55.8	55.7
80°	46.1	45.5	44.5	44.5	44.0	44.5	44.0
82.5°	34.8	34.7	33.6	33.6	33.1	32.8	33.1
85°	17.8	17.3	18.3	17.3	17.8	16.8	17.8
87.5°	8.0	8.1	7.9	7.8	7.5	8.4	7.5
90°	14.8	15.4	16.5	16.0	16.5	17.1	16.5
92.5°	38.1	33.7	30.7	29.7	27.9	28.5	27.5
95°	139.2	108.9	88.4	77.6	72.4	68.4	66.2
97.5°	410.0	336.4	268.2	226.1	200.4	185.0	180.1
100°	626.3	559.5	478.5	420.9	379.3	357.1	357.6
102.5°	724.4	685.5	634.1	589.3	556.3	537.7	524.6
105°	798.5	809.4	794.5	768.3	746.6	728.4	725.5
107.5°	789.2	839.1	859.4	859.9	852.6	846.4	841.2
110°	758.6	830.5	870.4	886.4	890.9	889.8	888.6



TEST NUMBER: P332308

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	718.4	799.0	850.3	879.5	893.7	898.0	898.2
115°	654.2	738.1	800.2	843.0	868.1	879.5	882.4
117.5°	599.9	675.2	738.3	782.9	811.6	828.1	831.9
120°	569.8	638.2	695.9	740.9	772.9	786.5	790.0
122.5°	545.6	609.0	662.5	702.6	731.3	746.4	750.7
125°	515.6	570.4	616.0	652.5	677.6	691.9	695.9
127.5°	489.3	538.7	580.2	612.7	634.1	647.0	650.7
130°	472.8	519.0	557.8	588.1	608.6	620.6	625.1
132.5°	457.3	500.3	537.3	565.7	586.2	596.8	600.0
135°	435.2	472.3	504.8	532.7	549.8	560.1	564.1
137.5°	413.9	445.8	474.0	497.5	514.8	523.5	526.1
140°	401.5	428.9	453.4	475.1	491.1	500.2	499.6
142.5°	389.7	413.4	434.7	453.2	467.4	475.6	475.0
145°	374.2	392.4	409.0	423.2	435.2	439.8	440.9
147.5°	362.6	377.4	389.1	399.9	408.0	412.4	412.8
150°	355.3	367.3	378.2	386.7	393.0	396.4	396.4
152.5°	348.5	359.1	368.1	374.8	380.7	382.7	382.7
155°	338.8	347.4	354.2	359.3	363.9	365.0	365.6
157.5°	329.3	336.0	341.3	345.8	349.2	350.1	350.0
160°	323.4	329.1	333.1	337.1	340.5	340.5	339.9
162.5°	317.0	322.3	325.8	328.4	331.4	331.4	330.8
165°	308.0	312.0	314.8	317.1	319.4	318.8	318.8
167.5°	301.0	303.3	305.4	306.4	308.0	307.4	307.4
170°	296.0	298.3	299.4	300.0	301.2	300.6	300.6
172.5°	291.9	293.7	294.4	294.5	295.7	294.7	294.2
175°	286.3	287.5	287.5	287.5	288.0	287.5	286.9
177.5°	283.1	283.6	283.6	283.1	283.6	282.7	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8

(END OF REPORT)