

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332312

Luminaire Tested: **S123RDIP-S775D805U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332312
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6257.1 lumens
Efficiency: N/A
Efficacy: 136.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	49	48	47	42
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	44	42	41	36
3	82	73	66	61	76	68	62	57	58	53	49	48	45	42	40	37	35	31
4	75	65	58	52	69	60	54	49	52	47	43	43	40	37	36	33	31	27
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	32	30	27	24
6	64	52	45	39	59	49	42	37	42	37	33	36	32	28	30	27	24	21
7	59	47	40	34	55	44	37	33	38	33	29	33	28	25	27	24	22	19
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	40	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18	16
10	48	36	29	25	44	34	28	23	30	25	21	25	21	19	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13164	13164	13164	13164
5°	15692	13220	11642	13220
10°	19593	13144	10518	13144
15°	22998	13010	9591	13010
20°	25668	12810	8804	12810
25°	25258	12598	8320	12598
30°	18155	12403	7822	12403
35°	12122	12150	7499	12150
40°	8931	11844	7165	11844
45°	7491	11309	6838	11309
50°	6611	10608	6382	10608
55°	5797	9805	5758	9805
60°	5162	9040	5274	9040
65°	4534	8214	4908	8214
70°	3559	7481	4482	7481
75°	3136	6534	4092	6534
80°	2727	5548	4023	5548
85°	2198	4458	4273	4458



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.3	1.9
10°-20°	375.7	6.0
20°-30°	590.3	9.4
30°-40°	615.9	9.8
40°-50°	527.1	8.4
50°-60°	401.7	6.4
60°-70°	257.5	4.1
70°-80°	123.9	2.0
80°-90°	35.7	0.6
90°-100°	38.3	0.6
100°-110°	182.3	2.9
110°-120°	438.0	7.0
120°-130°	557.7	8.9
130°-140°	595.9	9.5
140°-150°	557.2	8.9
150°-160°	449.5	7.2
160°-170°	290.1	4.6
170°-180°	100.0	1.6
0°-30°	1086.3	17.4
0°-40°	1702.2	27.2
0°-60°	2631.0	42.0
0°-90°	3048.0	48.7
90°-120°	658.6	10.5
90°-150°	2369.4	37.9
90°-180°	3209.0	51.3
0°-180°	6257.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1223	1223	1223	1223	1223	
5°	1452	1224	1078	1224	1452	150
15°	2064	1168	861	1168	2064	585
25°	2127	1061	700	1061	2127	914
35°	922	925	571	925	922	605
45°	492	743	449	743	492	387
55°	309	522	307	522	309	279
65°	178	322	193	322	178	175
75°	75	157	98	157	75	81
85°	18	36	35	36	18	21
90°	24	1	24	1	24	11
95°	30	48	30	48	30	25
105°	34	233	34	233	34	79
115°	460	437	460	437	460	425
125°	629	616	629	616	629	561
135°	775	767	775	767	775	597
145°	894	885	894	885	894	558
155°	973	975	973	975	973	449
165°	1026	1028	1026	1028	1026	290
175°	1048	1052	1048	1052	1048	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1302.6	1304.3	1298.8	1298.0	1291.7	1290.0	1290.0	1281.2	1275.8	1268.7	1264.5
5°	1452.3	1460.7	1456.5	1447.1	1431.4	1427.7	1417.8	1402.1	1384.3	1362.3	1351.8
7.5°	1639.3	1650.8	1646.4	1631.8	1615.4	1602.1	1574.0	1547.9	1511.4	1479.3	1451.9
10°	1792.6	1780.6	1771.2	1757.0	1741.9	1717.2	1687.9	1647.6	1601.0	1564.4	1523.5
12.5°	1907.4	1905.4	1893.5	1878.9	1857.5	1834.1	1798.1	1749.0	1694.8	1641.9	1595.2
15°	2063.8	2067.0	2059.1	2043.9	2013.6	1972.2	1917.8	1897.3	1819.9	1762.3	1704.7
17.5°	2172.1	2171.5	2170.4	2149.4	2118.4	2089.0	2038.5	1984.8	1914.6	1833.5	1755.9
20°	2240.8	2235.6	2236.6	2213.0	2190.0	2156.0	2106.8	2028.8	1971.2	1877.5	1797.3
22.5°	2239.1	2238.1	2242.1	2234.0	2217.2	2191.2	2152.4	2086.6	2013.1	1918.5	1828.3
25°	2126.7	2122.5	2147.1	2153.9	2180.6	2185.3	2173.8	2137.7	2068.0	1970.6	1859.1
27.5°	1779.9	1777.6	1823.2	1880.4	1952.8	2009.2	2063.6	2089.9	2068.0	1998.3	1886.6
30°	1460.7	1509.9	1533.0	1615.7	1707.8	1817.8	1914.1	2005.7	2028.2	1997.9	1906.2
32.5°	1212.8	1255.7	1274.9	1345.9	1431.8	1560.6	1705.1	1834.8	1926.5	1949.7	1894.5
35°	922.5	923.0	967.0	998.4	1078.0	1210.4	1350.8	1524.6	1697.3	1828.2	1841.8
37.5°	736.1	738.7	765.3	796.6	856.3	926.4	1049.9	1194.4	1394.0	1594.9	1712.7
40°	635.6	640.3	660.2	691.1	734.0	786.9	883.2	1019.4	1185.8	1409.4	1592.1
42.5°	571.1	578.7	589.0	612.8	639.4	688.9	766.8	871.9	1023.3	1234.7	1445.5
45°	492.1	496.3	504.2	515.2	539.3	573.8	626.2	696.8	822.5	992.7	1203.6
47.5°	434.1	431.9	440.2	449.1	465.1	488.7	523.8	581.5	671.1	807.6	986.6
50°	394.8	394.2	400.0	406.8	422.0	439.3	468.1	511.5	582.7	695.8	859.7
52.5°	357.9	359.9	364.0	372.5	383.4	397.4	423.2	454.5	515.7	613.3	749.9
55°	308.9	310.5	316.2	320.9	328.8	342.9	359.2	385.3	427.2	495.3	607.8
57.5°	267.4	266.7	272.2	273.4	282.3	293.8	306.4	326.7	357.1	407.6	483.4
60°	239.8	238.2	242.9	246.6	251.3	260.7	271.2	291.1	315.2	352.3	417.3
62.5°	214.7	213.9	217.4	221.0	224.9	233.5	242.3	257.6	276.6	308.0	359.5
65°	178.0	179.6	181.1	182.7	184.8	190.0	198.4	208.9	222.0	244.0	281.1
67.5°	139.9	141.5	142.0	145.2	149.7	153.0	158.1	167.4	176.5	195.1	216.2
70°	113.1	112.6	113.1	114.7	120.4	126.2	133.0	139.8	145.5	158.6	176.4
72.5°	97.2	96.2	97.6	97.9	100.7	102.3	106.6	113.0	120.4	129.3	142.1
75°	75.4	75.4	75.4	75.4	77.5	78.5	80.1	81.7	84.3	88.5	97.9
77.5°	55.7	55.8	56.5	57.1	57.5	58.1	59.1	60.6	61.6	63.8	67.9
80°	44.0	44.5	44.0	44.5	44.5	45.5	46.1	47.6	48.2	50.8	52.4
82.5°	33.1	32.8	33.1	33.6	33.6	34.7	34.8	35.9	36.0	37.4	39.0
85°	17.8	16.8	17.8	17.3	18.3	17.3	17.8	18.8	18.8	19.4	21.5
87.5°	8.9	9.6	8.7	9.1	9.0	9.3	9.2	9.1	9.8	9.2	9.2
90°	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2	19.5	18.8	16.5
92.5°	26.0	25.7	25.5	25.3	25.1	24.5	23.3	22.2	21.1	20.0	18.3
95°	29.7	29.7	29.7	29.7	29.7	29.1	27.9	26.7	25.5	24.2	22.3
97.5°	32.2	32.0	31.9	31.7	31.5	30.7	29.3	28.0	26.6	25.2	37.7
100°	32.8	32.7	32.5	32.3	32.1	31.4	30.0	28.6	27.2	25.8	52.9
102.5°	33.5	33.1	32.8	32.5	32.2	34.2	38.5	42.8	47.1	51.4	81.0
105°	34.4	34.1	33.7	33.4	33.0	48.2	79.0	109.7	140.5	171.2	186.8
107.5°	108.0	131.2	154.4	177.6	200.7	223.6	246.2	268.7	291.3	313.8	311.3
110°	215.0	239.8	264.7	289.5	314.4	329.7	335.4	341.1	346.9	352.6	350.7



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	368.9	374.1	379.3	384.6	389.8	392.4	392.3	392.2	392.1	392.0	390.1
115°	459.7	459.0	458.3	457.6	456.9	455.7	454.0	452.2	450.5	448.8	447.2
117.5°	510.7	510.5	510.4	510.3	510.1	509.3	508.0	506.6	505.2	503.8	503.0
120°	545.7	545.7	545.7	545.7	545.7	545.0	543.6	542.2	540.8	539.4	538.9
122.5°	580.1	580.0	579.8	579.7	579.5	579.0	578.0	577.0	576.1	575.1	574.4
125°	628.6	628.2	627.9	627.5	627.2	626.8	626.5	626.1	625.8	625.4	624.7
127.5°	675.2	675.5	675.9	676.2	676.5	676.4	675.9	675.3	674.8	674.2	673.4
130°	705.2	705.5	705.9	706.2	706.6	706.4	705.7	705.0	704.3	703.6	702.9
132.5°	732.7	733.2	733.7	734.2	734.6	734.5	733.8	733.1	732.5	731.8	731.2
135°	774.8	775.3	775.8	776.3	776.8	776.8	776.3	775.8	775.3	774.8	774.1
137.5°	814.3	814.7	815.0	815.4	815.7	815.5	814.6	813.8	813.0	812.1	811.7
140°	838.1	838.4	838.8	839.1	839.5	839.3	838.6	837.9	837.2	836.5	836.0
142.5°	860.0	860.5	860.9	861.4	861.9	861.9	861.3	860.8	860.2	859.7	859.1
145°	893.6	893.6	893.6	893.6	893.6	893.4	893.1	892.7	892.4	892.0	891.7
147.5°	918.6	919.4	920.2	921.0	921.8	922.0	921.7	921.3	921.0	920.6	920.3
150°	937.4	937.9	938.4	938.9	939.5	939.5	939.2	938.8	938.5	938.2	937.8
152.5°	952.4	953.2	954.0	954.8	955.6	955.7	955.0	954.4	953.8	953.2	953.0
155°	973.3	974.4	975.4	976.5	977.5	977.6	976.7	975.9	975.0	974.1	973.9
157.5°	991.0	992.4	993.7	995.1	996.4	996.6	995.5	994.5	993.5	992.4	992.6
160°	1002.3	1003.5	1004.7	1005.9	1007.1	1007.2	1006.2	1005.1	1004.1	1003.0	1003.2
162.5°	1012.9	1014.0	1015.0	1016.1	1017.2	1017.1	1016.0	1014.8	1013.6	1012.4	1012.6
165°	1025.7	1026.9	1028.1	1029.4	1030.6	1030.5	1029.1	1027.7	1026.3	1024.9	1025.1
167.5°	1034.9	1036.3	1037.7	1039.1	1040.5	1040.5	1039.1	1037.7	1036.3	1034.9	1034.9
170°	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1	1044.7	1043.3	1042.0	1040.6	1040.6
172.5°	1043.7	1045.2	1046.8	1048.3	1049.8	1049.9	1048.5	1047.1	1045.7	1044.3	1044.2
175°	1048.4	1049.8	1051.2	1052.6	1053.9	1054.0	1052.8	1051.6	1050.4	1049.2	1049.0
177.5°	1049.8	1051.2	1052.6	1054.0	1055.4	1055.5	1054.4	1053.3	1052.2	1051.0	1050.9
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1262.8	1261.5	1255.7	1249.0	1240.2	1234.3	1229.7	1227.2	1219.7	1210.4	1204.2
5°	1340.8	1325.1	1308.4	1287.9	1269.1	1249.7	1237.7	1223.5	1206.3	1186.9	1173.3
7.5°	1424.4	1393.6	1360.4	1326.2	1292.3	1262.0	1235.2	1212.2	1184.7	1156.9	1137.5
10°	1488.5	1443.4	1396.8	1349.2	1305.7	1264.9	1233.5	1202.6	1169.6	1137.7	1113.6
12.5°	1546.7	1487.4	1433.7	1375.2	1319.6	1270.8	1225.5	1189.2	1149.5	1115.5	1088.0
15°	1620.4	1559.7	1494.7	1405.7	1331.9	1270.1	1215.2	1167.5	1119.4	1077.5	1050.8
17.5°	1689.3	1597.9	1510.7	1436.4	1340.5	1263.3	1196.2	1139.2	1086.4	1042.0	1009.1
20°	1717.8	1629.3	1534.5	1439.8	1345.5	1259.1	1181.1	1118.3	1063.3	1013.1	982.7
22.5°	1734.9	1634.7	1534.9	1433.1	1333.0	1243.2	1166.1	1096.9	1037.4	989.6	952.1
25°	1754.9	1635.6	1525.6	1425.1	1323.0	1225.6	1134.0	1060.7	996.3	945.5	905.7
27.5°	1768.1	1627.7	1497.8	1386.0	1282.5	1185.5	1101.5	1023.9	958.5	904.8	862.1
30°	1770.6	1621.4	1476.4	1355.5	1250.2	1161.2	1072.2	997.9	928.8	871.7	831.9
32.5°	1774.0	1605.9	1447.5	1319.0	1211.3	1123.1	1042.5	971.5	900.7	844.5	803.9
35°	1760.2	1597.4	1403.6	1256.0	1148.1	1062.8	990.0	924.6	855.0	800.5	759.1
37.5°	1700.7	1563.3	1358.2	1185.0	1072.2	993.2	933.9	876.8	813.0	754.2	715.3
40°	1640.8	1529.8	1323.0	1141.9	1024.1	942.9	889.5	842.9	781.1	726.2	684.3
42.5°	1551.6	1484.2	1289.5	1096.6	969.6	891.4	846.4	802.7	748.5	692.7	653.3
45°	1387.9	1396.8	1220.9	1024.6	894.2	815.7	773.3	742.9	694.8	648.7	608.4
47.5°	1182.7	1265.9	1140.4	947.8	814.7	741.0	704.0	677.5	645.0	599.8	563.0
50°	1048.7	1167.5	1075.9	896.3	764.9	691.6	655.0	633.5	605.2	569.6	534.5
52.5°	925.1	1052.8	998.0	838.9	710.9	643.9	608.1	590.4	567.9	534.4	502.7
55°	754.4	883.8	871.2	752.3	629.8	569.6	542.4	522.5	507.3	482.2	457.1
57.5°	610.3	732.9	739.4	656.0	558.4	498.9	475.5	460.5	450.6	431.6	408.4
60°	519.4	631.9	653.9	591.1	507.3	455.0	431.9	419.9	412.0	396.9	379.1
62.5°	444.0	539.8	564.7	519.5	458.3	409.3	391.3	379.7	374.3	361.2	345.5
65°	339.8	419.4	443.4	418.3	386.4	347.1	332.5	322.5	317.8	310.5	298.9
67.5°	255.5	313.5	339.9	322.2	310.7	285.9	276.5	271.2	267.0	262.0	252.4
70°	205.2	248.2	275.4	270.7	261.3	248.2	241.4	237.7	233.5	229.3	220.9
72.5°	165.0	194.6	220.1	222.5	214.8	212.1	206.2	204.6	202.1	197.1	192.5
75°	109.4	129.8	147.6	154.4	157.6	160.2	157.6	157.1	156.5	152.4	149.7
77.5°	71.7	82.7	93.9	105.5	110.5	114.0	114.9	116.8	115.4	113.2	111.9
80°	55.0	57.6	65.4	75.4	83.2	86.4	88.5	89.5	89.0	88.5	86.4
82.5°	39.9	42.1	45.8	52.8	59.4	64.6	65.9	65.7	66.8	67.1	65.4
85°	21.5	22.0	23.0	24.1	27.7	33.5	35.1	36.1	37.2	37.2	34.0
87.5°	9.6	8.7	9.1	8.7	9.6	9.6	11.8	13.6	14.3	13.0	13.3
90°	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8	2.5	4.3	6.0
92.5°	16.6	14.9	13.2	12.6	13.1	13.6	14.1	14.5	14.1	13.6	13.1
95°	20.4	18.5	16.6	19.2	26.3	33.4	40.6	47.7	40.6	33.4	26.3
97.5°	50.2	62.7	75.2	83.1	86.3	89.5	92.7	95.8	92.7	89.5	86.3
100°	80.0	107.1	134.2	146.0	142.5	139.1	135.6	132.1	135.6	139.1	142.5
102.5°	110.6	140.3	169.9	183.4	180.9	178.4	175.9	173.4	175.9	178.4	180.9
105°	202.5	218.1	233.8	240.6	238.7	236.8	234.9	233.0	234.9	236.8	238.7
107.5°	308.9	306.4	303.9	301.9	300.4	298.9	297.4	295.8	297.4	298.9	300.4
110°	348.8	346.9	344.9	343.3	341.9	340.5	339.1	337.7	339.1	340.5	341.9



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	388.2	386.3	384.3	382.8	381.5	380.3	379.0	377.8	379.0	380.3	381.5
115°	445.6	444.1	442.5	441.2	440.2	439.1	438.1	437.0	438.1	439.1	440.2
117.5°	502.2	501.4	500.6	499.5	498.3	497.0	495.7	494.4	495.7	497.0	498.3
120°	538.4	537.9	537.4	536.3	534.7	533.2	531.6	530.1	531.6	533.2	534.7
122.5°	573.8	573.1	572.4	571.5	570.2	568.9	567.6	566.3	567.6	568.9	570.2
125°	624.0	623.4	622.7	621.6	620.2	618.8	617.4	616.1	617.4	618.8	620.2
127.5°	672.6	671.7	670.9	669.8	668.4	667.0	665.6	664.2	665.6	667.0	668.4
130°	702.2	701.5	700.8	699.8	698.4	697.0	695.6	694.2	695.6	697.0	698.4
132.5°	730.6	730.1	729.5	728.6	727.2	725.8	724.4	723.0	724.4	725.8	727.2
135°	773.4	772.7	772.0	771.1	770.1	769.0	768.0	766.9	768.0	769.0	770.1
137.5°	811.4	811.0	810.6	809.7	808.4	807.1	805.8	804.5	805.8	807.1	808.4
140°	835.5	835.0	834.4	833.7	832.6	831.6	830.5	829.5	830.5	831.6	832.6
142.5°	858.6	858.1	857.6	856.8	855.8	854.7	853.7	852.6	853.7	854.7	855.8
145°	891.3	891.0	890.6	889.9	888.6	887.4	886.2	885.0	886.2	887.4	888.6
147.5°	919.9	919.6	919.3	918.7	917.9	917.1	916.3	915.5	916.3	917.1	917.9
150°	937.5	937.1	936.8	936.3	935.8	935.3	934.8	934.2	934.8	935.3	935.8
152.5°	952.7	952.5	952.3	952.1	951.9	951.6	951.4	951.1	951.4	951.6	951.9
155°	973.8	973.6	973.4	973.5	973.9	974.2	974.6	974.9	974.6	974.2	973.9
157.5°	992.8	992.9	993.1	993.2	993.2	993.3	993.3	993.3	993.3	993.3	993.2
160°	1003.4	1003.6	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6	1004.4	1004.3	1004.1
162.5°	1012.8	1012.9	1013.1	1013.4	1013.9	1014.3	1014.8	1015.2	1014.8	1014.3	1013.9
165°	1025.3	1025.5	1025.6	1026.0	1026.5	1027.0	1027.5	1028.1	1027.5	1027.0	1026.5
167.5°	1034.9	1034.9	1034.9	1035.3	1036.0	1036.7	1037.4	1038.1	1037.4	1036.7	1036.0
170°	1040.6	1040.6	1040.6	1040.9	1041.6	1042.3	1043.0	1043.7	1043.0	1042.3	1041.6
172.5°	1044.0	1043.9	1043.8	1044.1	1044.9	1045.8	1046.6	1047.4	1046.6	1045.8	1044.9
175°	1048.8	1048.6	1048.5	1048.8	1049.7	1050.6	1051.4	1052.3	1051.4	1050.6	1049.7
177.5°	1050.8	1050.6	1050.5	1050.8	1051.5	1052.2	1052.9	1053.5	1052.9	1052.2	1051.5
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1202.1	1196.6	1192.9	1184.5	1179.0	1173.2	1167.3	1171.1	1170.7	1170.2	1170.2
5°	1161.8	1149.7	1138.7	1124.6	1115.7	1104.7	1096.3	1095.3	1097.4	1090.0	1085.8
7.5°	1121.8	1105.3	1089.7	1074.1	1057.6	1044.4	1036.1	1032.2	1026.9	1022.4	1017.7
10°	1093.7	1074.3	1059.1	1039.8	1022.0	1006.3	996.3	989.5	985.8	982.2	975.4
12.5°	1064.8	1045.8	1026.5	1004.6	987.6	969.4	962.0	954.3	947.3	943.2	933.9
15°	1022.5	997.9	977.5	954.4	935.6	917.8	907.3	892.1	890.0	884.8	875.4
17.5°	980.1	953.4	925.2	908.2	886.9	868.4	852.4	847.3	832.3	826.7	818.5
20°	946.6	922.0	900.5	878.0	847.1	829.8	817.3	810.5	798.4	791.1	785.8
22.5°	917.7	892.7	867.8	841.6	816.1	796.7	787.5	776.9	770.4	760.1	754.4
25°	876.4	849.2	819.4	791.1	772.8	758.1	743.4	734.0	724.6	719.9	709.4
27.5°	828.5	800.0	772.1	750.7	728.2	713.7	700.4	692.0	680.7	672.8	667.0
30°	802.1	768.6	744.5	725.1	696.3	682.7	672.8	662.3	653.9	645.5	639.8
32.5°	771.5	740.9	718.1	694.1	672.0	657.2	644.3	635.1	627.9	620.0	614.2
35°	723.5	697.9	674.3	650.2	634.0	618.8	603.7	595.8	589.0	581.7	576.4
37.5°	680.2	656.2	633.8	611.0	590.9	578.5	566.3	560.3	551.1	546.2	540.8
40°	653.4	629.8	605.7	583.8	562.8	553.4	542.4	533.5	525.1	521.5	515.7
42.5°	624.1	600.5	580.2	556.5	539.4	526.6	516.4	506.7	500.4	495.1	491.8
45°	580.6	559.7	539.8	516.2	500.0	489.0	477.5	468.6	462.8	459.2	453.4
47.5°	538.4	517.5	497.3	476.7	461.0	448.5	437.0	430.8	423.1	418.6	414.8
50°	507.8	489.0	467.5	448.7	433.0	420.4	411.0	403.1	396.3	390.6	388.0
52.5°	479.8	459.7	441.1	423.6	407.0	392.8	384.2	375.9	370.8	364.2	361.1
55°	433.5	414.1	398.4	381.1	364.9	352.9	342.4	335.1	329.8	322.5	318.3
57.5°	390.0	372.7	353.9	338.9	322.2	312.0	303.3	293.4	287.0	281.3	277.2
60°	360.7	340.8	324.6	310.5	295.8	282.7	274.9	267.0	260.2	254.4	250.8
62.5°	330.2	312.8	297.4	282.0	268.6	257.2	248.1	241.5	235.5	231.8	228.2
65°	283.2	269.6	253.9	241.4	228.8	220.4	213.1	207.3	203.1	200.5	197.4
67.5°	240.1	226.9	213.2	200.8	192.5	186.1	181.3	176.3	174.2	170.9	168.8
70°	212.0	198.4	186.4	177.0	168.6	163.9	160.7	157.1	155.0	150.8	148.7
72.5°	181.5	171.6	162.9	155.2	148.5	144.2	140.2	135.7	132.4	127.7	125.7
75°	142.9	134.0	127.2	122.0	117.8	112.0	106.3	101.6	100.0	98.4	97.9
77.5°	105.9	100.2	95.3	90.9	85.7	81.5	80.2	79.2	78.8	78.0	78.0
80°	83.2	78.0	74.3	69.1	66.0	66.0	66.0	64.9	65.4	65.4	65.4
82.5°	61.9	57.1	55.1	53.2	52.6	53.0	53.0	53.2	52.9	53.7	53.3
85°	31.9	32.5	33.5	33.0	33.5	33.5	34.6	34.0	34.6	33.5	34.6
87.5°	13.3	14.9	15.8	16.7	17.5	17.6	18.1	18.3	18.8	19.0	19.1
90°	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2	20.8	21.5	22.1
92.5°	12.6	13.2	14.9	16.6	18.3	20.0	21.1	22.2	23.3	24.5	25.1
95°	19.2	16.6	18.5	20.4	22.3	24.2	25.5	26.7	27.9	29.1	29.7
97.5°	83.1	75.2	62.7	50.2	37.7	25.2	26.6	28.0	29.3	30.7	31.5
100°	146.0	134.2	107.1	80.0	52.9	25.8	27.2	28.6	30.0	31.4	32.1
102.5°	183.4	169.9	140.3	110.6	81.0	51.4	47.1	42.8	38.5	34.2	32.2
105°	240.6	233.8	218.1	202.5	186.8	171.2	140.5	109.7	79.0	48.2	33.0
107.5°	301.9	303.9	306.4	308.9	311.3	313.8	291.3	268.7	246.2	223.6	200.7
110°	343.3	344.9	346.9	348.8	350.7	352.6	346.9	341.1	335.4	329.7	314.4



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	382.8	384.3	386.3	388.2	390.1	392.0	392.1	392.2	392.3	392.4	389.8
115°	441.2	442.5	444.1	445.6	447.2	448.8	450.5	452.2	454.0	455.7	456.9
117.5°	499.5	500.6	501.4	502.2	503.0	503.8	505.2	506.6	508.0	509.3	510.1
120°	536.3	537.4	537.9	538.4	538.9	539.4	540.8	542.2	543.6	545.0	545.7
122.5°	571.5	572.4	573.1	573.8	574.4	575.1	576.1	577.0	578.0	579.0	579.5
125°	621.6	622.7	623.4	624.0	624.7	625.4	625.8	626.1	626.5	626.8	627.2
127.5°	669.8	670.9	671.7	672.6	673.4	674.2	674.8	675.3	675.9	676.4	676.5
130°	699.8	700.8	701.5	702.2	702.9	703.6	704.3	705.0	705.7	706.4	706.6
132.5°	728.6	729.5	730.1	730.6	731.2	731.8	732.5	733.1	733.8	734.5	734.6
135°	771.1	772.0	772.7	773.4	774.1	774.8	775.3	775.8	776.3	776.8	776.8
137.5°	809.7	810.6	811.0	811.4	811.7	812.1	813.0	813.8	814.6	815.5	815.7
140°	833.7	834.4	835.0	835.5	836.0	836.5	837.2	837.9	838.6	839.3	839.5
142.5°	856.8	857.6	858.1	858.6	859.1	859.7	860.2	860.8	861.3	861.9	861.9
145°	889.9	890.6	891.0	891.3	891.7	892.0	892.4	892.7	893.1	893.4	893.6
147.5°	918.7	919.3	919.6	919.9	920.3	920.6	921.0	921.3	921.7	922.0	921.8
150°	936.3	936.8	937.1	937.5	937.8	938.2	938.5	938.8	939.2	939.5	939.5
152.5°	952.1	952.3	952.5	952.7	953.0	953.2	953.8	954.4	955.0	955.7	955.6
155°	973.5	973.4	973.6	973.8	973.9	974.1	975.0	975.9	976.7	977.6	977.5
157.5°	993.2	993.1	992.9	992.8	992.6	992.4	993.5	994.5	995.5	996.6	996.4
160°	1003.9	1003.7	1003.6	1003.4	1003.2	1003.0	1004.1	1005.1	1006.2	1007.2	1007.1
162.5°	1013.4	1013.1	1012.9	1012.8	1012.6	1012.4	1013.6	1014.8	1016.0	1017.1	1017.2
165°	1026.0	1025.6	1025.5	1025.3	1025.1	1024.9	1026.3	1027.7	1029.1	1030.5	1030.6
167.5°	1035.3	1034.9	1034.9	1034.9	1034.9	1034.9	1036.3	1037.7	1039.1	1040.5	1040.5
170°	1040.9	1040.6	1040.6	1040.6	1040.6	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1
172.5°	1044.1	1043.8	1043.9	1044.0	1044.2	1044.3	1045.7	1047.1	1048.5	1049.9	1049.8
175°	1048.8	1048.5	1048.6	1048.8	1049.0	1049.2	1050.4	1051.6	1052.8	1054.0	1053.9
177.5°	1050.8	1050.5	1050.6	1050.8	1050.9	1051.0	1052.2	1053.3	1054.4	1055.5	1055.4
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1165.2	1164.8	1165.2	1163.5	1165.2	1164.8	1165.2	1170.2	1170.2	1170.7	1171.1
5°	1084.3	1083.7	1082.2	1077.5	1082.2	1083.7	1084.3	1085.8	1090.0	1097.4	1095.3
7.5°	1013.6	1012.9	1008.3	1008.4	1008.3	1012.9	1013.6	1017.7	1022.4	1026.9	1032.2
10°	971.7	972.2	966.0	962.3	966.0	972.2	971.7	975.4	982.2	985.8	989.5
12.5°	931.1	928.7	923.6	919.6	923.6	928.7	931.1	933.9	943.2	947.3	954.3
15°	877.5	872.2	859.7	860.7	859.7	872.2	877.5	875.4	884.8	890.0	892.1
17.5°	814.3	810.5	810.2	802.9	810.2	810.5	814.3	818.5	826.7	832.3	847.3
20°	777.5	774.9	775.9	768.6	775.9	774.9	777.5	785.8	791.1	798.4	810.5
22.5°	748.6	746.0	741.6	739.3	741.6	746.0	748.6	754.4	760.1	770.4	776.9
25°	706.3	702.1	697.9	700.5	697.9	702.1	706.3	709.4	719.9	724.6	734.0
27.5°	664.0	660.8	656.6	656.1	656.6	660.8	664.0	667.0	672.8	680.7	692.0
30°	637.2	634.0	631.9	629.3	631.9	634.0	637.2	639.8	645.5	653.9	662.3
32.5°	609.9	609.3	605.5	605.0	605.5	609.3	609.9	614.2	620.0	627.9	635.1
35°	574.3	571.2	570.1	570.7	570.1	571.2	574.3	576.4	581.7	589.0	595.8
37.5°	540.5	536.3	534.4	532.6	534.4	536.3	540.5	540.8	546.2	551.1	560.3
40°	516.2	512.0	511.0	509.9	511.0	512.0	516.2	515.7	521.5	525.1	533.5
42.5°	489.0	487.3	486.7	484.8	486.7	487.3	489.0	491.8	495.1	500.4	506.7
45°	451.8	451.3	448.2	449.2	448.2	451.3	451.8	453.4	459.2	462.8	468.6
47.5°	412.7	410.4	408.2	409.6	408.2	410.4	412.7	414.8	418.6	423.1	430.8
50°	385.9	384.8	380.1	381.1	380.1	384.8	385.9	388.0	390.6	396.3	403.1
52.5°	359.1	355.1	353.3	352.7	353.3	355.1	359.1	361.1	364.2	370.8	375.9
55°	314.7	309.9	307.8	306.8	307.8	309.9	314.7	318.3	322.5	329.8	335.1
57.5°	271.1	269.8	268.2	269.3	268.2	269.8	271.1	277.2	281.3	287.0	293.4
60°	245.5	245.5	245.5	245.0	245.5	245.5	245.5	250.8	254.4	260.2	267.0
62.5°	225.9	224.6	224.2	224.9	224.2	224.6	225.9	228.2	231.8	235.5	241.5
65°	195.8	195.3	193.2	192.7	193.2	195.3	195.8	197.4	200.5	203.1	207.3
67.5°	167.4	165.5	164.9	164.2	164.9	165.5	167.4	168.8	170.9	174.2	176.3
70°	146.1	145.0	141.9	142.4	141.9	145.0	146.1	148.7	150.8	155.0	157.1
72.5°	123.0	122.0	121.4	120.6	121.4	122.0	123.0	125.7	127.7	132.4	135.7
75°	97.4	96.9	96.3	98.4	96.3	96.9	97.4	97.9	98.4	100.0	101.6
77.5°	78.0	78.0	78.3	77.5	78.3	78.0	78.0	78.0	78.0	78.8	79.2
80°	65.4	65.4	64.9	64.9	64.9	65.4	65.4	65.4	65.4	65.4	64.9
82.5°	52.5	52.9	53.2	52.4	53.2	52.9	52.5	53.3	53.7	52.9	53.2
85°	34.6	34.0	35.1	34.6	35.1	34.0	34.6	34.6	33.5	34.6	34.0
87.5°	20.0	19.2	19.3	19.8	19.3	19.2	20.0	19.1	19.0	18.8	18.3
90°	22.4	22.8	23.1	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2
92.5°	25.3	25.5	25.7	26.0	25.7	25.5	25.3	25.1	24.5	23.3	22.2
95°	29.7	29.7	29.7	29.7	29.7	29.7	29.7	29.7	29.1	27.9	26.7
97.5°	31.7	31.9	32.0	32.2	32.0	31.9	31.7	31.5	30.7	29.3	28.0
100°	32.3	32.5	32.7	32.8	32.7	32.5	32.3	32.1	31.4	30.0	28.6
102.5°	32.5	32.8	33.1	33.5	33.1	32.8	32.5	32.2	34.2	38.5	42.8
105°	33.4	33.7	34.1	34.4	34.1	33.7	33.4	33.0	48.2	79.0	109.7
107.5°	177.6	154.4	131.2	108.0	131.2	154.4	177.6	200.7	223.6	246.2	268.7
110°	289.5	264.7	239.8	215.0	239.8	264.7	289.5	314.4	329.7	335.4	341.1



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	384.6	379.3	374.1	368.9	374.1	379.3	384.6	389.8	392.4	392.3	392.2
115°	457.6	458.3	459.0	459.7	459.0	458.3	457.6	456.9	455.7	454.0	452.2
117.5°	510.3	510.4	510.5	510.7	510.5	510.4	510.3	510.1	509.3	508.0	506.6
120°	545.7	545.7	545.7	545.7	545.7	545.7	545.7	545.7	545.0	543.6	542.2
122.5°	579.7	579.8	580.0	580.1	580.0	579.8	579.7	579.5	579.0	578.0	577.0
125°	627.5	627.9	628.2	628.6	628.2	627.9	627.5	627.2	626.8	626.5	626.1
127.5°	676.2	675.9	675.5	675.2	675.5	675.9	676.2	676.5	676.4	675.9	675.3
130°	706.2	705.9	705.5	705.2	705.5	705.9	706.2	706.6	706.4	705.7	705.0
132.5°	734.2	733.7	733.2	732.7	733.2	733.7	734.2	734.6	734.5	733.8	733.1
135°	776.3	775.8	775.3	774.8	775.3	775.8	776.3	776.8	776.8	776.3	775.8
137.5°	815.4	815.0	814.7	814.3	814.7	815.0	815.4	815.7	815.5	814.6	813.8
140°	839.1	838.8	838.4	838.1	838.4	838.8	839.1	839.5	839.3	838.6	837.9
142.5°	861.4	860.9	860.5	860.0	860.5	860.9	861.4	861.9	861.9	861.3	860.8
145°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.4	893.1	892.7
147.5°	921.0	920.2	919.4	918.6	919.4	920.2	921.0	921.8	922.0	921.7	921.3
150°	938.9	938.4	937.9	937.4	937.9	938.4	938.9	939.5	939.5	939.2	938.8
152.5°	954.8	954.0	953.2	952.4	953.2	954.0	954.8	955.6	955.7	955.0	954.4
155°	976.5	975.4	974.4	973.3	974.4	975.4	976.5	977.5	977.6	976.7	975.9
157.5°	995.1	993.7	992.4	991.0	992.4	993.7	995.1	996.4	996.6	995.5	994.5
160°	1005.9	1004.7	1003.5	1002.3	1003.5	1004.7	1005.9	1007.1	1007.2	1006.2	1005.1
162.5°	1016.1	1015.0	1014.0	1012.9	1014.0	1015.0	1016.1	1017.2	1017.1	1016.0	1014.8
165°	1029.4	1028.1	1026.9	1025.7	1026.9	1028.1	1029.4	1030.6	1030.5	1029.1	1027.7
167.5°	1039.1	1037.7	1036.3	1034.9	1036.3	1037.7	1039.1	1040.5	1040.5	1039.1	1037.7
170°	1044.7	1043.3	1042.0	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1	1044.7	1043.3
172.5°	1048.3	1046.8	1045.2	1043.7	1045.2	1046.8	1048.3	1049.8	1049.9	1048.5	1047.1
175°	1052.6	1051.2	1049.8	1048.4	1049.8	1051.2	1052.6	1053.9	1054.0	1052.8	1051.6
177.5°	1054.0	1052.6	1051.2	1049.8	1051.2	1052.6	1054.0	1055.4	1055.5	1054.4	1053.3
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1167.3	1173.2	1179.0	1184.5	1192.9	1196.6	1202.1	1204.2	1210.4	1219.7	1227.2
5°	1096.3	1104.7	1115.7	1124.6	1138.7	1149.7	1161.8	1173.3	1186.9	1206.3	1223.5
7.5°	1036.1	1044.4	1057.6	1074.1	1089.7	1105.3	1121.8	1137.5	1156.9	1184.7	1212.2
10°	996.3	1006.3	1022.0	1039.8	1059.1	1074.3	1093.7	1113.6	1137.7	1169.6	1202.6
12.5°	962.0	969.4	987.6	1004.6	1026.5	1045.8	1064.8	1088.0	1115.5	1149.5	1189.2
15°	907.3	917.8	935.6	954.4	977.5	997.9	1022.5	1050.8	1077.5	1119.4	1167.5
17.5°	852.4	868.4	886.9	908.2	925.2	953.4	980.1	1009.1	1042.0	1086.4	1139.2
20°	817.3	829.8	847.1	878.0	900.5	922.0	946.6	982.7	1013.1	1063.3	1118.3
22.5°	787.5	796.7	816.1	841.6	867.8	892.7	917.7	952.1	989.6	1037.4	1096.9
25°	743.4	758.1	772.8	791.1	819.4	849.2	876.4	905.7	945.5	996.3	1060.7
27.5°	700.4	713.7	728.2	750.7	772.1	800.0	828.5	862.1	904.8	958.5	1023.9
30°	672.8	682.7	696.3	725.1	744.5	768.6	802.1	831.9	871.7	928.8	997.9
32.5°	644.3	657.2	672.0	694.1	718.1	740.9	771.5	803.9	844.5	900.7	971.5
35°	603.7	618.8	634.0	650.2	674.3	697.9	723.5	759.1	800.5	855.0	924.6
37.5°	566.3	578.5	590.9	611.0	633.8	656.2	680.2	715.3	754.2	813.0	876.8
40°	542.4	553.4	562.8	583.8	605.7	629.8	653.4	684.3	726.2	781.1	842.9
42.5°	516.4	526.6	539.4	556.5	580.2	600.5	624.1	653.3	692.7	748.5	802.7
45°	477.5	489.0	500.0	516.2	539.8	559.7	580.6	608.4	648.7	694.8	742.9
47.5°	437.0	448.5	461.0	476.7	497.3	517.5	538.4	563.0	599.8	645.0	677.5
50°	411.0	420.4	433.0	448.7	467.5	489.0	507.8	534.5	569.6	605.2	633.5
52.5°	384.2	392.8	407.0	423.6	441.1	459.7	479.8	502.7	534.4	567.9	590.4
55°	342.4	352.9	364.9	381.1	398.4	414.1	433.5	457.1	482.2	507.3	522.5
57.5°	303.3	312.0	322.2	338.9	353.9	372.7	390.0	408.4	431.6	450.6	460.5
60°	274.9	282.7	295.8	310.5	324.6	340.8	360.7	379.1	396.9	412.0	419.9
62.5°	248.1	257.2	268.6	282.0	297.4	312.8	330.2	345.5	361.2	374.3	379.7
65°	213.1	220.4	228.8	241.4	253.9	269.6	283.2	298.9	310.5	317.8	322.5
67.5°	181.3	186.1	192.5	200.8	213.2	226.9	240.1	252.4	262.0	267.0	271.2
70°	160.7	163.9	168.6	177.0	186.4	198.4	212.0	220.9	229.3	233.5	237.7
72.5°	140.2	144.2	148.5	155.2	162.9	171.6	181.5	192.5	197.1	202.1	204.6
75°	106.3	112.0	117.8	122.0	127.2	134.0	142.9	149.7	152.4	156.5	157.1
77.5°	80.2	81.5	85.7	90.9	95.3	100.2	105.9	111.9	113.2	115.4	116.8
80°	66.0	66.0	66.0	69.1	74.3	78.0	83.2	86.4	88.5	89.0	89.5
82.5°	53.0	53.0	52.6	53.2	55.1	57.1	61.9	65.4	67.1	66.8	65.7
85°	34.6	33.5	33.5	33.0	33.5	32.5	31.9	34.0	37.2	37.2	36.1
87.5°	18.1	17.6	17.5	16.7	15.8	14.9	13.3	13.3	13.0	14.3	13.6
90°	19.5	18.8	16.5	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8
92.5°	21.1	20.0	18.3	16.6	14.9	13.2	12.6	13.1	13.6	14.1	14.5
95°	25.5	24.2	22.3	20.4	18.5	16.6	19.2	26.3	33.4	40.6	47.7
97.5°	26.6	25.2	37.7	50.2	62.7	75.2	83.1	86.3	89.5	92.7	95.8
100°	27.2	25.8	52.9	80.0	107.1	134.2	146.0	142.5	139.1	135.6	132.1
102.5°	47.1	51.4	81.0	110.6	140.3	169.9	183.4	180.9	178.4	175.9	173.4
105°	140.5	171.2	186.8	202.5	218.1	233.8	240.6	238.7	236.8	234.9	233.0
107.5°	291.3	313.8	311.3	308.9	306.4	303.9	301.9	300.4	298.9	297.4	295.8
110°	346.9	352.6	350.7	348.8	346.9	344.9	343.3	341.9	340.5	339.1	337.7



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	392.1	392.0	390.1	388.2	386.3	384.3	382.8	381.5	380.3	379.0	377.8
115°	450.5	448.8	447.2	445.6	444.1	442.5	441.2	440.2	439.1	438.1	437.0
117.5°	505.2	503.8	503.0	502.2	501.4	500.6	499.5	498.3	497.0	495.7	494.4
120°	540.8	539.4	538.9	538.4	537.9	537.4	536.3	534.7	533.2	531.6	530.1
122.5°	576.1	575.1	574.4	573.8	573.1	572.4	571.5	570.2	568.9	567.6	566.3
125°	625.8	625.4	624.7	624.0	623.4	622.7	621.6	620.2	618.8	617.4	616.1
127.5°	674.8	674.2	673.4	672.6	671.7	670.9	669.8	668.4	667.0	665.6	664.2
130°	704.3	703.6	702.9	702.2	701.5	700.8	699.8	698.4	697.0	695.6	694.2
132.5°	732.5	731.8	731.2	730.6	730.1	729.5	728.6	727.2	725.8	724.4	723.0
135°	775.3	774.8	774.1	773.4	772.7	772.0	771.1	770.1	769.0	768.0	766.9
137.5°	813.0	812.1	811.7	811.4	811.0	810.6	809.7	808.4	807.1	805.8	804.5
140°	837.2	836.5	836.0	835.5	835.0	834.4	833.7	832.6	831.6	830.5	829.5
142.5°	860.2	859.7	859.1	858.6	858.1	857.6	856.8	855.8	854.7	853.7	852.6
145°	892.4	892.0	891.7	891.3	891.0	890.6	889.9	888.6	887.4	886.2	885.0
147.5°	921.0	920.6	920.3	919.9	919.6	919.3	918.7	917.9	917.1	916.3	915.5
150°	938.5	938.2	937.8	937.5	937.1	936.8	936.3	935.8	935.3	934.8	934.2
152.5°	953.8	953.2	953.0	952.7	952.5	952.3	952.1	951.9	951.6	951.4	951.1
155°	975.0	974.1	973.9	973.8	973.6	973.4	973.5	973.9	974.2	974.6	974.9
157.5°	993.5	992.4	992.6	992.8	992.9	993.1	993.2	993.2	993.3	993.3	993.3
160°	1004.1	1003.0	1003.2	1003.4	1003.6	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6
162.5°	1013.6	1012.4	1012.6	1012.8	1012.9	1013.1	1013.4	1013.9	1014.3	1014.8	1015.2
165°	1026.3	1024.9	1025.1	1025.3	1025.5	1025.6	1026.0	1026.5	1027.0	1027.5	1028.1
167.5°	1036.3	1034.9	1034.9	1034.9	1034.9	1034.9	1035.3	1036.0	1036.7	1037.4	1038.1
170°	1042.0	1040.6	1040.6	1040.6	1040.6	1040.6	1040.9	1041.6	1042.3	1043.0	1043.7
172.5°	1045.7	1044.3	1044.2	1044.0	1043.9	1043.8	1044.1	1044.9	1045.8	1046.6	1047.4
175°	1050.4	1049.2	1049.0	1048.8	1048.6	1048.5	1048.8	1049.7	1050.6	1051.4	1052.3
177.5°	1052.2	1051.0	1050.9	1050.8	1050.6	1050.5	1050.8	1051.5	1052.2	1052.9	1053.5
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1229.7	1234.3	1240.2	1249.0	1255.7	1261.5	1262.8	1264.5	1268.7	1275.8	1281.2
5°	1237.7	1249.7	1269.1	1287.9	1308.4	1325.1	1340.8	1351.8	1362.3	1384.3	1402.1
7.5°	1235.2	1262.0	1292.3	1326.2	1360.4	1393.6	1424.4	1451.9	1479.3	1511.4	1547.9
10°	1233.5	1264.9	1305.7	1349.2	1396.8	1443.4	1488.5	1523.5	1564.4	1601.0	1647.6
12.5°	1225.5	1270.8	1319.6	1375.2	1433.7	1487.4	1546.7	1595.2	1641.9	1694.8	1749.0
15°	1215.2	1270.1	1331.9	1405.7	1494.7	1559.7	1620.4	1704.7	1762.3	1819.9	1897.3
17.5°	1196.2	1263.3	1340.5	1436.4	1510.7	1597.9	1689.3	1755.9	1833.5	1914.6	1984.8
20°	1181.1	1259.1	1345.5	1439.8	1534.5	1629.3	1717.8	1797.3	1877.5	1971.2	2028.8
22.5°	1166.1	1243.2	1333.0	1433.1	1534.9	1634.7	1734.9	1828.3	1918.5	2013.1	2086.6
25°	1134.0	1225.6	1323.0	1425.1	1525.6	1635.6	1754.9	1859.1	1970.6	2068.0	2137.7
27.5°	1101.5	1185.5	1282.5	1386.0	1497.8	1627.7	1768.1	1886.6	1998.3	2068.0	2089.9
30°	1072.2	1161.2	1250.2	1355.5	1476.4	1621.4	1770.6	1906.2	1997.9	2028.2	2005.7
32.5°	1042.5	1123.1	1211.3	1319.0	1447.5	1605.9	1774.0	1894.5	1949.7	1926.5	1834.8
35°	990.0	1062.8	1148.1	1256.0	1403.6	1597.4	1760.2	1841.8	1828.2	1697.3	1524.6
37.5°	933.9	993.2	1072.2	1185.0	1358.2	1563.3	1700.7	1712.7	1594.9	1394.0	1194.4
40°	889.5	942.9	1024.1	1141.9	1323.0	1529.8	1640.8	1592.1	1409.4	1185.8	1019.4
42.5°	846.4	891.4	969.6	1096.6	1289.5	1484.2	1551.6	1445.5	1234.7	1023.3	871.9
45°	773.3	815.7	894.2	1024.6	1220.9	1396.8	1387.9	1203.6	992.7	822.5	696.8
47.5°	704.0	741.0	814.7	947.8	1140.4	1265.9	1182.7	986.6	807.6	671.1	581.5
50°	655.0	691.6	764.9	896.3	1075.9	1167.5	1048.7	859.7	695.8	582.7	511.5
52.5°	608.1	643.9	710.9	838.9	998.0	1052.8	925.1	749.9	613.3	515.7	454.5
55°	542.4	569.6	629.8	752.3	871.2	883.8	754.4	607.8	495.3	427.2	385.3
57.5°	475.5	498.9	558.4	656.0	739.4	732.9	610.3	483.4	407.6	357.1	326.7
60°	431.9	455.0	507.3	591.1	653.9	631.9	519.4	417.3	352.3	315.2	291.1
62.5°	391.3	409.3	458.3	519.5	564.7	539.8	444.0	359.5	308.0	276.6	257.6
65°	332.5	347.1	386.4	418.3	443.4	419.4	339.8	281.1	244.0	222.0	208.9
67.5°	276.5	285.9	310.7	322.2	339.9	313.5	255.5	216.2	195.1	176.5	167.4
70°	241.4	248.2	261.3	270.7	275.4	248.2	205.2	176.4	158.6	145.5	139.8
72.5°	206.2	212.1	214.8	222.5	220.1	194.6	165.0	142.1	129.3	120.4	113.0
75°	157.6	160.2	157.6	154.4	147.6	129.8	109.4	97.9	88.5	84.3	81.7
77.5°	114.9	114.0	110.5	105.5	93.9	82.7	71.7	67.9	63.8	61.6	60.6
80°	88.5	86.4	83.2	75.4	65.4	57.6	55.0	52.4	50.8	48.2	47.6
82.5°	65.9	64.6	59.4	52.8	45.8	42.1	39.9	39.0	37.4	36.0	35.9
85°	35.1	33.5	27.7	24.1	23.0	22.0	21.5	21.5	19.4	18.8	18.8
87.5°	11.8	9.6	9.6	8.7	9.1	8.7	9.6	9.2	9.2	9.8	9.1
90°	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2
92.5°	14.1	13.6	13.1	12.6	13.2	14.9	16.6	18.3	20.0	21.1	22.2
95°	40.6	33.4	26.3	19.2	16.6	18.5	20.4	22.3	24.2	25.5	26.7
97.5°	92.7	89.5	86.3	83.1	75.2	62.7	50.2	37.7	25.2	26.6	28.0
100°	135.6	139.1	142.5	146.0	134.2	107.1	80.0	52.9	25.8	27.2	28.6
102.5°	175.9	178.4	180.9	183.4	169.9	140.3	110.6	81.0	51.4	47.1	42.8
105°	234.9	236.8	238.7	240.6	233.8	218.1	202.5	186.8	171.2	140.5	109.7
107.5°	297.4	298.9	300.4	301.9	303.9	306.4	308.9	311.3	313.8	291.3	268.7
110°	339.1	340.5	341.9	343.3	344.9	346.9	348.8	350.7	352.6	346.9	341.1



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	379.0	380.3	381.5	382.8	384.3	386.3	388.2	390.1	392.0	392.1	392.2
115°	438.1	439.1	440.2	441.2	442.5	444.1	445.6	447.2	448.8	450.5	452.2
117.5°	495.7	497.0	498.3	499.5	500.6	501.4	502.2	503.0	503.8	505.2	506.6
120°	531.6	533.2	534.7	536.3	537.4	537.9	538.4	538.9	539.4	540.8	542.2
122.5°	567.6	568.9	570.2	571.5	572.4	573.1	573.8	574.4	575.1	576.1	577.0
125°	617.4	618.8	620.2	621.6	622.7	623.4	624.0	624.7	625.4	625.8	626.1
127.5°	665.6	667.0	668.4	669.8	670.9	671.7	672.6	673.4	674.2	674.8	675.3
130°	695.6	697.0	698.4	699.8	700.8	701.5	702.2	702.9	703.6	704.3	705.0
132.5°	724.4	725.8	727.2	728.6	729.5	730.1	730.6	731.2	731.8	732.5	733.1
135°	768.0	769.0	770.1	771.1	772.0	772.7	773.4	774.1	774.8	775.3	775.8
137.5°	805.8	807.1	808.4	809.7	810.6	811.0	811.4	811.7	812.1	813.0	813.8
140°	830.5	831.6	832.6	833.7	834.4	835.0	835.5	836.0	836.5	837.2	837.9
142.5°	853.7	854.7	855.8	856.8	857.6	858.1	858.6	859.1	859.7	860.2	860.8
145°	886.2	887.4	888.6	889.9	890.6	891.0	891.3	891.7	892.0	892.4	892.7
147.5°	916.3	917.1	917.9	918.7	919.3	919.6	919.9	920.3	920.6	921.0	921.3
150°	934.8	935.3	935.8	936.3	936.8	937.1	937.5	937.8	938.2	938.5	938.8
152.5°	951.4	951.6	951.9	952.1	952.3	952.5	952.7	953.0	953.2	953.8	954.4
155°	974.6	974.2	973.9	973.5	973.4	973.6	973.8	973.9	974.1	975.0	975.9
157.5°	993.3	993.3	993.2	993.2	993.1	992.9	992.8	992.6	992.4	993.5	994.5
160°	1004.4	1004.3	1004.1	1003.9	1003.7	1003.6	1003.4	1003.2	1003.0	1004.1	1005.1
162.5°	1014.8	1014.3	1013.9	1013.4	1013.1	1012.9	1012.8	1012.6	1012.4	1013.6	1014.8
165°	1027.5	1027.0	1026.5	1026.0	1025.6	1025.5	1025.3	1025.1	1024.9	1026.3	1027.7
167.5°	1037.4	1036.7	1036.0	1035.3	1034.9	1034.9	1034.9	1034.9	1034.9	1036.3	1037.7
170°	1043.0	1042.3	1041.6	1040.9	1040.6	1040.6	1040.6	1040.6	1040.6	1042.0	1043.3
172.5°	1046.6	1045.8	1044.9	1044.1	1043.8	1043.9	1044.0	1044.2	1044.3	1045.7	1047.1
175°	1051.4	1050.6	1049.7	1048.8	1048.5	1048.6	1048.8	1049.0	1049.2	1050.4	1051.6
177.5°	1052.9	1052.2	1051.5	1050.8	1050.5	1050.6	1050.8	1050.9	1051.0	1052.2	1053.3
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1290.0	1290.0	1291.7	1298.0	1298.8	1304.3	1302.6
5°	1417.8	1427.7	1431.4	1447.1	1456.5	1460.7	1452.3
7.5°	1574.0	1602.1	1615.4	1631.8	1646.4	1650.8	1639.3
10°	1687.9	1717.2	1741.9	1757.0	1771.2	1780.6	1792.6
12.5°	1798.1	1834.1	1857.5	1878.9	1893.5	1905.4	1907.4
15°	1917.8	1972.2	2013.6	2043.9	2059.1	2067.0	2063.8
17.5°	2038.5	2089.0	2118.4	2149.4	2170.4	2171.5	2172.1
20°	2106.8	2156.0	2190.0	2213.0	2236.6	2235.6	2240.8
22.5°	2152.4	2191.2	2217.2	2234.0	2242.1	2238.1	2239.1
25°	2173.8	2185.3	2180.6	2153.9	2147.1	2122.5	2126.7
27.5°	2063.6	2009.2	1952.8	1880.4	1823.2	1777.6	1779.9
30°	1914.1	1817.8	1707.8	1615.7	1533.0	1509.9	1460.7
32.5°	1705.1	1560.6	1431.8	1345.9	1274.9	1255.7	1212.8
35°	1350.8	1210.4	1078.0	998.4	967.0	923.0	922.5
37.5°	1049.9	926.4	856.3	796.6	765.3	738.7	736.1
40°	883.2	786.9	734.0	691.1	660.2	640.3	635.6
42.5°	766.8	688.9	639.4	612.8	589.0	578.7	571.1
45°	626.2	573.8	539.3	515.2	504.2	496.3	492.1
47.5°	523.8	488.7	465.1	449.1	440.2	431.9	434.1
50°	468.1	439.3	422.0	406.8	400.0	394.2	394.8
52.5°	423.2	397.4	383.4	372.5	364.0	359.9	357.9
55°	359.2	342.9	328.8	320.9	316.2	310.5	308.9
57.5°	306.4	293.8	282.3	273.4	272.2	266.7	267.4
60°	271.2	260.7	251.3	246.6	242.9	238.2	239.8
62.5°	242.3	233.5	224.9	221.0	217.4	213.9	214.7
65°	198.4	190.0	184.8	182.7	181.1	179.6	178.0
67.5°	158.1	153.0	149.7	145.2	142.0	141.5	139.9
70°	133.0	126.2	120.4	114.7	113.1	112.6	113.1
72.5°	106.6	102.3	100.7	97.9	97.6	96.2	97.2
75°	80.1	78.5	77.5	75.4	75.4	75.4	75.4
77.5°	59.1	58.1	57.5	57.1	56.5	55.8	55.7
80°	46.1	45.5	44.5	44.5	44.0	44.5	44.0
82.5°	34.8	34.7	33.6	33.6	33.1	32.8	33.1
85°	17.8	17.3	18.3	17.3	17.8	16.8	17.8
87.5°	9.2	9.3	9.0	9.1	8.7	9.6	8.9
90°	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	23.3	24.5	25.1	25.3	25.5	25.7	26.0
95°	27.9	29.1	29.7	29.7	29.7	29.7	29.7
97.5°	29.3	30.7	31.5	31.7	31.9	32.0	32.2
100°	30.0	31.4	32.1	32.3	32.5	32.7	32.8
102.5°	38.5	34.2	32.2	32.5	32.8	33.1	33.5
105°	79.0	48.2	33.0	33.4	33.7	34.1	34.4
107.5°	246.2	223.6	200.7	177.6	154.4	131.2	108.0
110°	335.4	329.7	314.4	289.5	264.7	239.8	215.0



TEST NUMBER: P332312

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	392.3	392.4	389.8	384.6	379.3	374.1	368.9
115°	454.0	455.7	456.9	457.6	458.3	459.0	459.7
117.5°	508.0	509.3	510.1	510.3	510.4	510.5	510.7
120°	543.6	545.0	545.7	545.7	545.7	545.7	545.7
122.5°	578.0	579.0	579.5	579.7	579.8	580.0	580.1
125°	626.5	626.8	627.2	627.5	627.9	628.2	628.6
127.5°	675.9	676.4	676.5	676.2	675.9	675.5	675.2
130°	705.7	706.4	706.6	706.2	705.9	705.5	705.2
132.5°	733.8	734.5	734.6	734.2	733.7	733.2	732.7
135°	776.3	776.8	776.8	776.3	775.8	775.3	774.8
137.5°	814.6	815.5	815.7	815.4	815.0	814.7	814.3
140°	838.6	839.3	839.5	839.1	838.8	838.4	838.1
142.5°	861.3	861.9	861.9	861.4	860.9	860.5	860.0
145°	893.1	893.4	893.6	893.6	893.6	893.6	893.6
147.5°	921.7	922.0	921.8	921.0	920.2	919.4	918.6
150°	939.2	939.5	939.5	938.9	938.4	937.9	937.4
152.5°	955.0	955.7	955.6	954.8	954.0	953.2	952.4
155°	976.7	977.6	977.5	976.5	975.4	974.4	973.3
157.5°	995.5	996.6	996.4	995.1	993.7	992.4	991.0
160°	1006.2	1007.2	1007.1	1005.9	1004.7	1003.5	1002.3
162.5°	1016.0	1017.1	1017.2	1016.1	1015.0	1014.0	1012.9
165°	1029.1	1030.5	1030.6	1029.4	1028.1	1026.9	1025.7
167.5°	1039.1	1040.5	1040.5	1039.1	1037.7	1036.3	1034.9
170°	1044.7	1046.1	1046.1	1044.7	1043.3	1042.0	1040.6
172.5°	1048.5	1049.9	1049.8	1048.3	1046.8	1045.2	1043.7
175°	1052.8	1054.0	1053.9	1052.6	1051.2	1049.8	1048.4
177.5°	1054.4	1055.5	1055.4	1054.0	1052.6	1051.2	1049.8
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3

(END OF REPORT)