

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332286-840

Luminaire Tested: **S123RDIP-S560D805U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332286-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D805U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4942.5 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332286-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332286-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37
3	81	71	64	59	74	66	60	55	55	50	47	45	42	39	36	33	31
4	74	63	56	50	67	58	52	46	49	44	40	40	36	34	32	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	26	23	21
7	58	46	38	33	53	42	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	18	15
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10267	10267	10267
5°	10306	10164	10222
10°	10248	10037	10002
15°	10137	9802	9698
20°	9986	9507	9286
25°	9830	9178	8884
30°	9625	8797	8316
35°	9412	8418	7796
40°	9218	7967	7152
45°	8961	7524	6570
50°	8679	7021	5921
55°	8392	6446	5315
60°	8127	5828	4646
65°	7784	5163	3978
70°	7352	4334	3213
75°	6725	3410	3023
80°	5994	3025	2777
85°	5064	2668	2482



TEST NUMBER: P332286-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.8
10°-20°	249.2	5.0
20°-30°	358.8	7.3
30°-40°	404.2	8.2
40°-50°	386.7	7.8
50°-60°	316.7	6.4
60°-70°	213.7	4.3
70°-80°	107.5	2.2
80°-90°	31.4	0.6
90°-100°	65.5	1.3
100°-110°	196.0	4.0
110°-120°	333.3	6.7
120°-130°	438.5	8.9
130°-140°	492.8	10.0
140°-150°	484.4	9.8
150°-160°	407.8	8.3
160°-170°	271.5	5.5
170°-180°	95.1	1.9
0°-30°	697.6	14.1
0°-40°	1101.8	22.3
0°-60°	1805.2	36.5
0°-90°	2157.7	43.7
90°-120°	594.8	12.0
90°-150°	2010.5	40.7
90°-180°	2785.0	56.3
0°-180°	4942.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	954	954	954	954	954	
5°	954	950	941	947	946	90
15°	910	900	880	876	870	256
25°	828	808	773	757	748	381
35°	716	687	641	608	593	448
45°	589	552	494	452	432	454
55°	447	408	344	300	283	401
65°	306	262	203	166	156	302
75°	162	124	82	75	73	172
85°	41	25	22	20	20	46
90°	1	9	19	22	24	5
95°	47	52	58	61	62	52
105°	178	180	186	186	188	190
115°	336	338	336	337	336	332
125°	491	493	492	489	486	438
135°	637	642	641	638	636	491
145°	773	775	777	776	773	483
155°	885	885	886	889	884	407
165°	964	962	962	966	961	272
175°	1003	1000	1000	1004	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P332286-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	956.9	956.3	955.8	955.2	954.7	953.6	952.0	950.3	948.7	947.1	948.6
5°	953.8	953.0	952.1	951.3	950.4	949.0	946.8	944.8	942.7	940.7	942.2
7.5°	945.0	944.1	943.1	942.2	941.3	939.5	936.9	934.1	931.4	928.8	929.6
10°	937.6	936.3	935.1	933.9	932.8	930.6	927.6	924.4	921.3	918.3	918.4
12.5°	927.1	925.7	924.3	923.0	921.7	919.2	915.3	911.6	907.8	904.0	903.9
15°	909.7	907.9	905.9	904.0	902.2	898.8	894.0	889.2	884.3	879.6	878.7
17.5°	887.9	885.8	883.5	881.3	879.1	874.9	868.8	862.7	856.6	850.5	848.7
20°	871.8	869.1	866.4	863.5	860.8	856.2	849.6	843.1	836.6	830.0	827.8
22.5°	853.8	850.7	847.6	844.3	841.2	836.2	829.2	822.2	815.4	808.4	805.6
25°	827.7	823.4	819.1	814.9	810.5	804.5	796.5	788.6	780.7	772.8	769.2
27.5°	796.0	791.2	786.5	781.7	777.0	770.2	761.4	752.7	743.9	735.1	730.0
30°	774.4	769.2	764.1	758.9	753.8	746.3	736.7	727.1	717.4	707.8	702.0
32.5°	752.7	746.9	741.0	735.2	729.3	721.3	711.1	700.9	690.7	680.5	674.2
35°	716.3	710.1	704.0	697.8	691.6	683.2	672.5	661.9	651.2	640.6	633.1
37.5°	679.5	672.7	665.8	658.8	652.0	642.9	631.5	620.2	608.7	597.3	589.0
40°	656.0	648.4	640.9	633.3	625.7	615.8	603.7	591.5	579.3	567.0	558.1
42.5°	629.3	621.8	614.3	606.7	599.2	589.1	576.4	563.8	551.2	538.6	528.8
45°	588.7	581.0	573.2	565.5	557.7	547.2	534.0	520.8	507.6	494.3	484.5
47.5°	548.0	539.5	531.0	522.5	514.0	503.2	489.9	476.7	463.4	450.2	439.6
50°	518.3	510.2	502.1	494.0	485.9	474.9	461.0	447.2	433.2	419.3	408.6
52.5°	491.7	482.9	474.1	465.3	456.7	445.4	431.5	417.8	403.9	390.2	379.1
55°	447.2	438.7	430.3	421.8	413.4	401.9	387.3	372.7	358.1	343.5	333.5
57.5°	406.0	396.8	387.6	378.4	369.2	357.3	342.6	328.0	313.3	298.6	289.2
60°	377.5	368.1	358.6	349.1	339.7	327.8	313.6	299.3	285.0	270.7	261.5
62.5°	349.0	339.6	330.1	320.6	311.2	299.3	285.1	270.8	256.5	242.3	233.6
65°	305.6	296.1	286.7	277.2	267.7	256.3	242.9	229.5	216.1	202.7	194.3
67.5°	262.1	252.6	243.0	233.4	223.9	212.7	199.8	186.9	174.1	161.2	154.9
70°	233.6	224.3	215.1	205.8	196.5	185.8	173.8	161.8	149.8	137.7	131.7
72.5°	205.1	196.0	186.8	177.7	168.5	158.5	147.6	136.6	125.7	114.8	109.9
75°	161.7	153.4	145.2	136.9	128.7	119.8	110.4	100.9	91.5	82.0	80.3
77.5°	122.1	114.6	107.1	99.7	92.2	85.4	79.4	73.3	67.2	61.1	60.2
80°	96.7	89.7	82.6	75.5	68.5	63.2	59.6	55.9	52.3	48.8	48.2
82.5°	72.6	66.4	60.4	54.3	48.2	44.3	42.6	41.0	39.3	37.6	37.1
85°	41.0	37.3	33.4	29.7	25.9	23.7	23.2	22.7	22.2	21.6	21.3
87.5°	15.0	13.8	12.7	11.5	10.4	10.0	10.5	10.9	11.4	11.8	11.8
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.3	16.7	19.0	19.7
92.5°	19.1	20.3	21.5	22.7	23.8	25.1	26.5	27.8	29.0	30.3	30.9
95°	46.6	47.8	49.1	50.3	51.5	52.8	54.2	55.6	57.1	58.5	59.2
97.5°	82.7	83.6	84.5	85.4	86.4	87.4	88.4	89.4	90.4	91.4	92.2
100°	107.3	108.5	109.5	110.6	111.6	112.6	113.4	114.3	115.2	116.0	116.6
102.5°	135.8	136.4	137.0	137.7	138.4	139.3	140.4	141.6	142.7	143.9	144.4
105°	177.6	178.0	178.3	178.7	179.0	180.1	181.6	183.2	184.8	186.3	186.3
107.5°	226.3	226.5	226.7	226.9	227.1	227.5	228.2	228.8	229.4	230.0	230.7
110°	256.6	256.9	257.3	257.6	258.0	258.3	258.7	259.0	259.4	259.7	260.4



TEST NUMBER: P332286-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.2	288.4	288.6	288.8	289.0	289.1	289.2	289.3	289.4	289.4	290.3
115°	335.6	336.1	336.6	337.1	337.7	337.8	337.4	337.1	336.7	336.4	336.5
117.5°	383.2	383.6	384.0	384.3	384.7	384.6	384.2	383.6	383.2	382.7	382.7
120°	412.9	413.9	415.1	416.1	417.2	417.3	416.4	415.5	414.7	413.7	413.5
122.5°	443.9	444.6	445.5	446.2	447.0	447.2	446.7	446.3	445.8	445.4	444.8
125°	491.1	491.6	492.1	492.7	493.2	493.3	492.9	492.6	492.2	491.9	491.2
127.5°	534.7	535.8	536.9	538.1	539.2	539.6	539.2	538.8	538.4	538.0	537.0
130°	563.7	565.1	566.5	567.9	569.4	569.8	569.3	568.8	568.3	567.6	566.9
132.5°	592.8	594.2	595.6	597.0	598.4	599.0	598.5	598.1	597.7	597.3	596.5
135°	637.1	638.2	639.2	640.4	641.4	641.9	641.7	641.5	641.3	641.2	640.5
137.5°	678.2	679.1	679.9	680.9	681.8	682.4	682.9	683.3	683.8	684.2	683.5
140°	706.6	707.5	708.4	709.3	710.1	710.6	710.8	711.0	711.2	711.3	711.2
142.5°	732.6	733.5	734.3	735.2	736.1	736.7	737.0	737.3	737.6	737.9	737.7
145°	773.0	773.4	773.7	774.1	774.4	774.8	775.4	775.9	776.4	776.9	776.8
147.5°	808.4	809.0	809.6	810.2	810.9	811.4	811.9	812.4	812.9	813.4	813.4
150°	832.9	833.3	833.6	834.0	834.4	834.8	835.1	835.5	835.8	836.2	836.2
152.5°	853.2	853.6	854.1	854.6	855.2	855.6	855.8	856.0	856.2	856.4	856.7
155°	885.0	885.0	885.0	885.0	885.0	885.1	885.3	885.6	885.8	885.9	886.6
157.5°	912.2	912.0	911.8	911.6	911.4	911.4	911.5	911.7	911.8	911.9	912.7
160°	929.3	929.0	928.6	928.3	927.9	927.8	927.8	927.8	927.8	927.8	928.6
162.5°	944.4	944.0	943.5	943.0	942.5	942.3	942.5	942.6	942.7	942.9	943.7
165°	964.0	963.5	963.0	962.5	961.9	961.7	961.7	961.7	961.7	961.7	962.7
167.5°	979.7	979.0	978.3	977.5	976.8	976.6	976.7	976.8	977.0	977.1	978.3
170°	988.6	987.8	987.1	986.4	985.7	985.3	985.3	985.3	985.3	985.3	986.6
172.5°	995.4	994.8	994.1	993.4	992.7	992.3	992.3	992.3	992.3	992.3	993.4
175°	1002.7	1002.0	1001.4	1000.7	1000.0	999.6	999.6	999.6	999.6	999.6	1000.7
177.5°	1005.7	1005.2	1004.6	1004.0	1003.5	1003.2	1003.2	1003.2	1003.2	1003.2	1004.0
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332286-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	950.1	951.6	953.1	953.7	953.4	953.1	952.9	952.6
5°	943.7	945.3	946.8	947.5	947.2	946.7	946.4	946.0
7.5°	930.5	931.3	932.2	932.3	931.7	931.2	930.6	930.0
10°	918.6	918.8	918.9	918.6	917.8	916.9	916.0	915.1
12.5°	903.8	903.7	903.6	903.0	902.0	901.0	900.1	899.1
15°	877.9	877.0	876.2	875.0	873.8	872.7	871.5	870.3
17.5°	846.9	845.1	843.1	841.4	839.6	837.8	836.0	834.2
20°	825.6	823.3	821.1	819.0	816.9	814.9	812.7	810.7
22.5°	802.8	800.0	797.3	794.9	792.9	791.0	789.1	787.2
25°	765.6	761.9	758.4	755.6	753.8	751.8	749.9	748.0
27.5°	725.0	720.0	715.0	711.0	708.1	705.3	702.4	699.4
30°	696.1	690.2	684.5	680.1	677.4	674.7	671.9	669.1
32.5°	667.8	661.4	655.0	650.4	647.5	644.6	641.7	638.8
35°	625.7	618.3	611.0	605.7	602.6	599.6	596.4	593.3
37.5°	580.6	572.2	563.8	557.7	553.9	550.1	546.2	542.4
40°	549.2	540.2	531.3	524.8	520.9	516.9	513.0	509.0
42.5°	519.1	509.3	499.5	492.8	489.3	485.7	482.2	478.7
45°	474.7	464.9	455.1	448.2	444.0	439.9	435.8	431.6
47.5°	428.9	418.3	407.6	400.4	396.8	393.0	389.4	385.7
50°	398.0	387.3	376.7	369.3	365.4	361.4	357.5	353.6
52.5°	368.1	357.0	345.9	338.6	335.1	331.5	328.0	324.5
55°	323.6	313.6	303.6	296.9	293.5	290.0	286.6	283.2
57.5°	279.7	270.3	260.9	254.8	251.9	248.9	246.0	243.1
60°	252.2	242.9	233.6	227.5	224.6	221.7	218.7	215.8
62.5°	224.8	216.1	207.3	201.5	198.4	195.3	192.3	189.2
65°	185.8	177.4	169.0	163.8	162.0	160.1	158.1	156.2
67.5°	148.7	142.3	136.0	131.9	129.9	127.8	125.8	123.8
70°	125.6	119.7	113.6	109.7	107.8	105.9	104.0	102.1
72.5°	104.9	100.1	95.1	92.3	91.5	90.7	89.9	89.1
75°	78.6	76.9	75.1	74.1	73.7	73.4	73.0	72.7
77.5°	59.3	58.4	57.4	56.8	56.5	56.0	55.7	55.3
80°	47.7	47.2	46.7	46.3	45.9	45.5	45.2	44.8
82.5°	36.6	36.1	35.5	35.2	35.1	35.1	35.0	34.9
85°	21.0	20.6	20.3	20.1	20.1	20.1	20.1	20.1
87.5°	11.8	11.8	11.8	11.8	11.7	11.7	11.6	11.5
90°	20.4	21.0	21.7	22.3	22.6	23.0	23.3	23.7
92.5°	31.4	32.0	32.5	32.7	32.5	32.3	32.1	31.9
95°	59.8	60.5	61.2	61.6	61.6	61.6	61.6	61.6
97.5°	93.0	93.8	94.6	95.0	94.9	94.9	94.8	94.7
100°	117.1	117.6	118.2	118.7	119.0	119.3	119.7	120.0
102.5°	144.9	145.4	145.9	146.2	146.1	146.0	146.0	145.9
105°	186.3	186.3	186.3	186.5	186.8	187.2	187.5	187.9
107.5°	231.2	231.8	232.4	232.5	232.3	232.1	231.9	231.7
110°	261.2	261.9	262.6	262.8	262.4	262.1	261.7	261.4



TEST NUMBER: P332286-840

CATALOG NUMBER: S123RDIP-S560D805U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	291.1	292.0	292.9	293.2	293.2	293.1	293.0	293.0
115°	336.7	336.9	337.1	337.1	336.9	336.7	336.5	336.4
117.5°	382.7	382.6	382.6	382.3	381.9	381.4	380.9	380.4
120°	413.3	413.2	413.0	412.7	412.4	412.0	411.7	411.3
122.5°	444.4	443.9	443.5	443.0	442.5	442.0	441.5	441.0
125°	490.5	489.8	489.1	488.4	487.7	487.0	486.3	485.5
127.5°	536.0	535.0	534.1	533.2	532.4	531.6	530.8	530.0
130°	566.3	565.6	564.9	563.9	562.7	561.5	560.3	559.0
132.5°	595.7	594.8	594.0	593.1	592.2	591.2	590.3	589.4
135°	639.7	639.0	638.3	637.8	637.4	637.1	636.7	636.4
137.5°	682.8	682.1	681.3	680.5	679.9	679.2	678.6	677.9
140°	711.0	710.8	710.6	710.0	708.7	707.5	706.3	705.1
142.5°	737.6	737.4	737.2	736.7	735.7	734.8	733.8	732.9
145°	776.6	776.4	776.2	775.8	775.1	774.4	773.7	773.0
147.5°	813.4	813.4	813.4	812.8	811.8	810.7	809.7	808.7
150°	836.2	836.2	836.2	835.7	834.6	833.5	832.4	831.4
152.5°	856.9	857.2	857.5	857.2	856.3	855.4	854.4	853.5
155°	887.3	888.0	888.7	888.4	887.2	886.0	884.7	883.5
157.5°	913.4	914.1	914.8	914.7	913.8	912.8	911.8	910.8
160°	929.5	930.4	931.2	931.3	930.6	929.9	929.2	928.5
162.5°	944.6	945.5	946.4	946.2	945.1	944.0	942.9	941.8
165°	963.8	964.8	965.9	965.8	964.6	963.3	962.1	960.9
167.5°	979.4	980.4	981.5	981.5	980.4	979.4	978.3	977.1
170°	987.8	989.1	990.3	990.3	989.1	987.8	986.6	985.3
172.5°	994.5	995.6	996.6	996.6	995.3	994.1	992.9	991.7
175°	1001.7	1002.7	1003.8	1003.7	1002.5	1001.3	1000.0	998.8
177.5°	1004.9	1005.7	1006.5	1006.5	1005.5	1004.5	1003.6	1002.6
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1

(END OF REPORT)