

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332314

Luminaire Tested: **S123RDIP-S775D805U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332314
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5953.8 lumens
Efficiency: N/A
Efficacy: 129.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	95	91	88	91	88	84	82	75	72	70	63	61	60	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38
3	83	74	67	61	76	69	62	57	59	54	50	50	46	44	41	39	37	33
4	76	66	58	52	70	61	54	49	53	47	43	45	41	38	37	35	32	29
5	70	59	51	45	65	55	48	43	47	42	38	40	36	33	34	31	28	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	28	25	23	20
8	56	44	36	31	51	41	34	29	36	30	26	31	27	23	26	23	20	18
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	19	17
10	49	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13164	13164	13164	13164
5°	15692	13220	11642	13220
10°	19593	13144	10518	13144
15°	22998	13010	9591	13010
20°	25668	12810	8804	12810
25°	25258	12598	8320	12598
30°	18155	12403	7822	12403
35°	12122	12150	7499	12150
40°	8931	11844	7165	11844
45°	7491	11309	6838	11309
50°	6611	10608	6382	10608
55°	5797	9805	5758	9805
60°	5162	9040	5274	9040
65°	4534	8214	4908	8214
70°	3559	7481	4482	7481
75°	3136	6534	4092	6534
80°	2727	5548	4023	5548
85°	2198	4458	4273	4458



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.3	2.0
10°-20°	375.7	6.3
20°-30°	590.3	9.9
30°-40°	615.9	10.3
40°-50°	527.1	8.9
50°-60°	401.7	6.7
60°-70°	257.5	4.3
70°-80°	123.9	2.1
80°-90°	35.8	0.6
90°-100°	214.9	3.6
100°-110°	608.6	10.2
110°-120°	598.7	10.1
120°-130°	477.5	8.0
130°-140°	376.5	6.3
140°-150°	281.0	4.7
150°-160°	195.9	3.3
160°-170°	115.1	1.9
170°-180°	37.4	0.6
0°-30°	1086.3	18.2
0°-40°	1702.2	28.6
0°-60°	2631.0	44.2
0°-90°	3048.1	51.2
90°-120°	1422.2	23.9
90°-150°	2557.3	43.0
90°-180°	2906.0	48.8
0°-180°	5953.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1223	1223	1223	1223	1223	
5°	1452	1224	1078	1224	1452	150
15°	2064	1168	861	1168	2064	585
25°	2127	1061	700	1061	2127	914
35°	922	925	571	925	922	605
45°	492	743	449	743	492	387
55°	309	522	307	522	309	279
65°	178	322	193	322	178	175
75°	75	157	98	157	75	81
85°	18	36	35	36	18	21
90°	23	2	23	2	23	13
95°	91	27	91	27	91	163
105°	994	91	994	91	994	981
115°	1210	160	1210	160	1210	1175
125°	954	223	954	223	954	864
135°	773	261	773	261	773	600
145°	604	298	604	298	604	384
155°	501	338	501	338	501	234
165°	437	370	437	370	437	125
175°	393	385	393	385	393	38
180°	386	386	386	386	386	



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1302.6	1304.3	1298.8	1298.0	1291.7	1290.0	1290.0	1281.2	1275.8	1268.7	1264.5
5°	1452.3	1460.7	1456.5	1447.1	1431.4	1427.7	1417.8	1402.1	1384.3	1362.3	1351.8
7.5°	1639.3	1650.8	1646.4	1631.8	1615.4	1602.1	1574.0	1547.9	1511.4	1479.3	1451.9
10°	1792.6	1780.6	1771.2	1757.0	1741.9	1717.2	1687.9	1647.6	1601.0	1564.4	1523.5
12.5°	1907.4	1905.4	1893.5	1878.9	1857.5	1834.1	1798.1	1749.0	1694.8	1641.9	1595.2
15°	2063.8	2067.0	2059.1	2043.9	2013.6	1972.2	1917.8	1897.3	1819.9	1762.3	1704.7
17.5°	2172.1	2171.5	2170.4	2149.4	2118.4	2089.0	2038.5	1984.8	1914.6	1833.5	1755.9
20°	2240.8	2235.6	2236.6	2213.0	2190.0	2156.0	2106.8	2028.8	1971.2	1877.5	1797.3
22.5°	2239.1	2238.1	2242.1	2234.0	2217.2	2191.2	2152.4	2086.6	2013.1	1918.5	1828.3
25°	2126.7	2122.5	2147.1	2153.9	2180.6	2185.3	2173.8	2137.7	2068.0	1970.6	1859.1
27.5°	1779.9	1777.6	1823.2	1880.4	1952.8	2009.2	2063.6	2089.9	2068.0	1998.3	1886.6
30°	1460.7	1509.9	1533.0	1615.7	1707.8	1817.8	1914.1	2005.7	2028.2	1997.9	1906.2
32.5°	1212.8	1255.7	1274.9	1345.9	1431.8	1560.6	1705.1	1834.8	1926.5	1949.7	1894.5
35°	922.5	923.0	967.0	998.4	1078.0	1210.4	1350.8	1524.6	1697.3	1828.2	1841.8
37.5°	736.1	738.7	765.3	796.6	856.3	926.4	1049.9	1194.4	1394.0	1594.9	1712.7
40°	635.6	640.3	660.2	691.1	734.0	786.9	883.2	1019.4	1185.8	1409.4	1592.1
42.5°	571.1	578.7	589.0	612.8	639.4	688.9	766.8	871.9	1023.3	1234.7	1445.5
45°	492.1	496.3	504.2	515.2	539.3	573.8	626.2	696.8	822.5	992.7	1203.6
47.5°	434.1	431.9	440.2	449.1	465.1	488.7	523.8	581.5	671.1	807.6	986.6
50°	394.8	394.2	400.0	406.8	422.0	439.3	468.1	511.5	582.7	695.8	859.7
52.5°	357.9	359.9	364.0	372.5	383.4	397.4	423.2	454.5	515.7	613.3	749.9
55°	308.9	310.5	316.2	320.9	328.8	342.9	359.2	385.3	427.2	495.3	607.8
57.5°	267.4	266.7	272.2	273.4	282.3	293.8	306.4	326.7	357.1	407.6	483.4
60°	239.8	238.2	242.9	246.6	251.3	260.7	271.2	291.1	315.2	352.3	417.3
62.5°	214.7	213.9	217.4	221.0	224.9	233.5	242.3	257.6	276.6	308.0	359.5
65°	178.0	179.6	181.1	182.7	184.8	190.0	198.4	208.9	222.0	244.0	281.1
67.5°	139.9	141.5	142.0	145.2	149.7	153.0	158.1	167.4	176.5	195.1	216.2
70°	113.1	112.6	113.1	114.7	120.4	126.2	133.0	139.8	145.5	158.6	176.4
72.5°	97.2	96.2	97.6	97.9	100.7	102.3	106.6	113.0	120.4	129.3	142.1
75°	75.4	75.4	75.4	75.4	77.5	78.5	80.1	81.7	84.3	88.5	97.9
77.5°	55.7	55.8	56.5	57.1	57.5	58.1	59.1	60.6	61.6	63.8	67.9
80°	44.0	44.5	44.0	44.5	44.5	45.5	46.1	47.6	48.2	50.8	52.4
82.5°	33.1	32.8	33.1	33.6	33.6	34.7	34.8	35.9	36.0	37.4	39.0
85°	17.8	16.8	17.8	17.3	18.3	17.3	17.8	18.8	18.8	19.4	21.5
87.5°	8.7	9.7	8.7	9.0	9.1	9.2	9.1	8.9	9.6	9.4	9.3
90°	22.7	23.5	22.7	21.9	22.7	21.1	20.3	19.5	18.8	19.5	17.2
92.5°	37.7	39.1	38.3	40.7	42.1	46.1	52.2	65.8	90.7	120.2	132.3
95°	90.7	93.8	99.3	106.3	121.2	149.3	190.8	281.5	376.1	463.6	412.8
97.5°	246.9	253.6	274.7	309.9	367.6	461.1	562.0	701.6	768.7	718.5	526.0
100°	490.2	489.4	519.9	577.0	655.9	767.0	858.4	921.8	894.4	740.4	500.4
102.5°	719.1	737.1	762.6	807.8	869.2	939.6	992.9	994.9	900.7	699.7	462.8
105°	994.5	998.4	1023.4	1053.1	1089.1	1109.4	1094.5	1016.4	853.0	628.6	416.7
107.5°	1153.0	1160.2	1168.7	1178.7	1178.0	1150.2	1081.7	954.8	769.5	565.7	387.3
110°	1218.1	1219.6	1221.2	1214.9	1193.1	1138.3	1039.8	896.0	716.9	530.1	376.1



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1231.2	1230.9	1225.0	1205.6	1165.5	1095.2	984.8	837.8	671.3	506.3	369.8
115°	1209.5	1205.6	1189.9	1155.5	1096.9	1011.7	896.7	760.7	616.1	480.8	367.5
117.5°	1140.4	1135.0	1112.5	1073.1	1012.0	925.5	822.3	704.9	582.8	465.8	368.9
120°	1082.8	1078.1	1059.4	1015.6	953.8	874.9	781.0	675.5	565.3	458.9	371.4
122.5°	1029.0	1023.1	1002.4	963.0	908.2	834.8	747.9	652.4	550.9	454.6	375.7
125°	953.8	948.3	928.8	894.4	844.4	781.8	706.8	621.5	532.4	448.8	382.3
127.5°	891.9	886.9	869.2	839.8	795.3	738.4	670.6	594.7	516.2	446.0	389.8
130°	856.9	850.6	834.2	806.1	764.6	711.5	648.1	577.8	507.4	444.1	394.8
132.5°	822.5	818.1	803.6	775.4	736.5	685.8	626.9	562.1	499.3	443.4	398.6
135°	773.2	767.7	753.7	730.2	691.9	647.3	596.5	541.0	488.6	442.5	404.2
137.5°	721.2	717.6	705.7	681.9	649.7	611.1	567.3	521.8	479.4	440.8	408.0
140°	684.9	685.7	673.1	651.3	621.5	587.9	550.4	510.5	473.8	440.2	410.5
142.5°	651.1	651.9	640.6	621.2	595.9	566.7	534.1	499.9	468.8	438.9	412.3
145°	604.3	602.8	596.5	580.1	560.6	537.9	512.9	487.1	462.1	437.0	413.6
147.5°	565.9	565.3	559.3	548.2	533.4	517.3	497.1	476.6	455.5	434.1	413.6
150°	543.4	543.4	538.7	530.1	518.3	503.5	487.1	469.1	451.1	431.6	413.6
152.5°	524.6	524.6	521.8	513.8	504.6	492.2	477.7	462.2	446.1	428.4	411.7
155°	501.1	500.4	498.8	492.5	485.5	476.1	464.4	451.9	438.6	423.0	409.7
157.5°	479.7	479.9	478.6	473.9	467.8	460.5	451.4	440.9	430.2	418.1	407.0
160°	466.0	466.7	466.7	462.1	456.6	451.1	443.3	434.7	424.5	414.4	405.8
162.5°	453.5	454.2	454.2	450.2	446.6	441.7	434.5	427.2	418.9	410.6	403.3
165°	437.0	437.0	437.8	434.7	431.6	427.7	422.2	417.5	411.2	405.0	399.5
167.5°	421.4	421.4	422.2	420.0	418.6	415.8	412.6	409.0	403.9	399.4	395.8
170°	412.0	412.0	412.8	411.2	410.5	408.9	405.8	403.4	399.5	395.6	393.3
172.5°	403.3	403.9	405.3	403.7	403.6	402.6	400.1	398.4	395.1	392.5	391.4
175°	393.3	394.0	394.8	394.0	394.0	394.0	392.5	391.7	390.1	388.6	388.6
177.5°	387.5	387.5	388.7	388.1	388.7	388.7	388.1	387.5	386.8	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1262.8	1261.5	1255.7	1249.0	1240.2	1234.3	1229.7	1227.2	1219.7	1210.4	1204.2
5°	1340.8	1325.1	1308.4	1287.9	1269.1	1249.7	1237.7	1223.5	1206.3	1186.9	1173.3
7.5°	1424.4	1393.6	1360.4	1326.2	1292.3	1262.0	1235.2	1212.2	1184.7	1156.9	1137.5
10°	1488.5	1443.4	1396.8	1349.2	1305.7	1264.9	1233.5	1202.6	1169.6	1137.7	1113.6
12.5°	1546.7	1487.4	1433.7	1375.2	1319.6	1270.8	1225.5	1189.2	1149.5	1115.5	1088.0
15°	1620.4	1559.7	1494.7	1405.7	1331.9	1270.1	1215.2	1167.5	1119.4	1077.5	1050.8
17.5°	1689.3	1597.9	1510.7	1436.4	1340.5	1263.3	1196.2	1139.2	1086.4	1042.0	1009.1
20°	1717.8	1629.3	1534.5	1439.8	1345.5	1259.1	1181.1	1118.3	1063.3	1013.1	982.7
22.5°	1734.9	1634.7	1534.9	1433.1	1333.0	1243.2	1166.1	1096.9	1037.4	989.6	952.1
25°	1754.9	1635.6	1525.6	1425.1	1323.0	1225.6	1134.0	1060.7	996.3	945.5	905.7
27.5°	1768.1	1627.7	1497.8	1386.0	1282.5	1185.5	1101.5	1023.9	958.5	904.8	862.1
30°	1770.6	1621.4	1476.4	1355.5	1250.2	1161.2	1072.2	997.9	928.8	871.7	831.9
32.5°	1774.0	1605.9	1447.5	1319.0	1211.3	1123.1	1042.5	971.5	900.7	844.5	803.9
35°	1760.2	1597.4	1403.6	1256.0	1148.1	1062.8	990.0	924.6	855.0	800.5	759.1
37.5°	1700.7	1563.3	1358.2	1185.0	1072.2	993.2	933.9	876.8	813.0	754.2	715.3
40°	1640.8	1529.8	1323.0	1141.9	1024.1	942.9	889.5	842.9	781.1	726.2	684.3
42.5°	1551.6	1484.2	1289.5	1096.6	969.6	891.4	846.4	802.7	748.5	692.7	653.3
45°	1387.9	1396.8	1220.9	1024.6	894.2	815.7	773.3	742.9	694.8	648.7	608.4
47.5°	1182.7	1265.9	1140.4	947.8	814.7	741.0	704.0	677.5	645.0	599.8	563.0
50°	1048.7	1167.5	1075.9	896.3	764.9	691.6	655.0	633.5	605.2	569.6	534.5
52.5°	925.1	1052.8	998.0	838.9	710.9	643.9	608.1	590.4	567.9	534.4	502.7
55°	754.4	883.8	871.2	752.3	629.8	569.6	542.4	522.5	507.3	482.2	457.1
57.5°	610.3	732.9	739.4	656.0	558.4	498.9	475.5	460.5	450.6	431.6	408.4
60°	519.4	631.9	653.9	591.1	507.3	455.0	431.9	419.9	412.0	396.9	379.1
62.5°	444.0	539.8	564.7	519.5	458.3	409.3	391.3	379.7	374.3	361.2	345.5
65°	339.8	419.4	443.4	418.3	386.4	347.1	332.5	322.5	317.8	310.5	298.9
67.5°	255.5	313.5	339.9	322.2	310.7	285.9	276.5	271.2	267.0	262.0	252.4
70°	205.2	248.2	275.4	270.7	261.3	248.2	241.4	237.7	233.5	229.3	220.9
72.5°	165.0	194.6	220.1	222.5	214.8	212.1	206.2	204.6	202.1	197.1	192.5
75°	109.4	129.8	147.6	154.4	157.6	160.2	157.6	157.1	156.5	152.4	149.7
77.5°	71.7	82.7	93.9	105.5	110.5	114.0	114.9	116.8	115.4	113.2	111.9
80°	55.0	57.6	65.4	75.4	83.2	86.4	88.5	89.5	89.0	88.5	86.4
82.5°	39.9	42.1	45.8	52.8	59.4	64.6	65.9	65.7	66.8	67.1	65.4
85°	21.5	22.0	23.0	24.1	27.7	33.5	35.1	36.1	37.2	37.2	34.0
87.5°	9.7	8.8	9.2	8.8	9.8	9.7	11.9	13.7	14.4	13.1	13.6
90°	14.9	12.5	10.2	8.6	7.0	4.7	3.1	1.6	3.1	4.7	7.0
92.5°	99.3	65.7	45.2	33.6	27.1	21.0	14.4	9.7	14.4	21.0	27.1
95°	284.6	168.1	101.6	71.1	50.8	37.5	28.9	26.6	28.9	37.5	50.8
97.5°	312.3	180.9	117.4	84.4	64.4	52.9	46.1	45.3	46.1	52.9	64.4
100°	294.7	179.0	124.3	93.8	75.1	64.1	58.6	57.9	58.6	64.1	75.1
102.5°	279.7	181.5	132.4	104.5	87.6	77.2	72.4	71.0	72.4	77.2	87.6
105°	268.9	188.4	146.2	122.0	107.1	97.7	93.0	90.7	93.0	97.7	107.1
107.5°	268.2	201.2	164.2	141.7	127.7	118.5	114.0	111.6	114.0	118.5	127.7
110°	271.3	211.9	176.7	154.8	141.5	132.9	129.0	126.7	129.0	132.9	141.5



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	277.5	222.5	189.8	168.6	155.3	146.7	142.8	140.4	142.8	146.7	155.3
115°	287.7	240.0	210.3	189.2	175.9	168.1	163.4	160.3	163.4	168.1	175.9
117.5°	301.2	258.6	229.2	209.7	194.8	187.6	183.7	180.1	183.7	187.6	194.8
120°	311.2	270.5	242.4	222.8	208.0	200.1	196.2	193.9	196.2	200.1	208.0
122.5°	320.5	283.0	255.5	234.7	220.5	212.0	208.1	205.8	208.1	212.0	220.5
125°	335.4	301.0	273.6	252.5	237.7	229.1	224.4	222.8	224.4	229.1	237.7
127.5°	347.6	316.6	290.2	269.1	252.7	243.9	238.1	235.8	238.1	243.9	252.7
130°	355.7	326.0	300.2	279.1	262.7	253.3	246.3	243.9	246.3	253.3	262.7
132.5°	363.2	334.1	309.0	288.5	272.1	260.8	253.2	250.2	253.2	260.8	272.1
135°	372.9	346.3	322.1	301.0	284.6	272.9	264.3	261.1	264.3	272.9	284.6
137.5°	380.1	354.8	331.5	311.9	295.7	283.2	274.7	271.4	274.7	283.2	295.7
140°	383.9	360.4	337.7	318.2	302.6	290.1	282.2	278.3	282.2	290.1	302.6
142.5°	387.6	364.8	342.7	324.5	308.8	297.6	289.1	285.8	289.1	297.6	308.8
145°	391.7	370.6	350.3	332.3	319.0	307.3	300.2	297.9	300.2	307.3	319.0
147.5°	394.2	375.3	356.7	341.3	328.5	318.4	311.5	310.1	311.5	318.4	328.5
150°	394.8	378.4	360.4	346.3	335.4	325.2	319.0	318.2	319.0	325.2	335.4
152.5°	396.1	380.3	364.8	351.3	341.7	332.7	326.5	326.3	326.5	332.7	341.7
155°	396.4	383.9	370.6	359.6	351.0	343.2	338.5	338.5	338.5	343.2	351.0
157.5°	397.2	385.9	375.3	366.8	359.5	352.6	348.8	348.2	348.8	352.6	359.5
160°	397.2	387.8	378.4	370.6	365.1	358.9	355.7	355.7	355.7	358.9	365.1
162.5°	396.5	388.4	380.3	373.7	368.9	363.9	361.4	361.4	361.4	363.9	368.9
165°	394.8	389.3	383.1	377.6	374.5	370.6	369.0	369.8	369.0	370.6	374.5
167.5°	393.6	389.2	384.7	381.2	379.0	376.1	375.3	376.2	375.3	376.1	379.0
170°	391.7	388.6	384.7	383.1	381.5	379.2	378.4	380.0	378.4	379.2	381.5
172.5°	391.1	388.6	385.3	384.3	383.4	381.7	381.5	382.5	381.5	381.7	383.4
175°	389.3	387.8	386.2	385.4	385.4	383.9	384.7	385.4	384.7	383.9	385.4
177.5°	388.1	386.8	386.2	386.2	386.2	385.6	386.2	386.8	386.2	385.6	386.2
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1202.1	1196.6	1192.9	1184.5	1179.0	1173.2	1167.3	1171.1	1170.7	1170.2	1170.2
5°	1161.8	1149.7	1138.7	1124.6	1115.7	1104.7	1096.3	1095.3	1097.4	1090.0	1085.8
7.5°	1121.8	1105.3	1089.7	1074.1	1057.6	1044.4	1036.1	1032.2	1026.9	1022.4	1017.7
10°	1093.7	1074.3	1059.1	1039.8	1022.0	1006.3	996.3	989.5	985.8	982.2	975.4
12.5°	1064.8	1045.8	1026.5	1004.6	987.6	969.4	962.0	954.3	947.3	943.2	933.9
15°	1022.5	997.9	977.5	954.4	935.6	917.8	907.3	892.1	890.0	884.8	875.4
17.5°	980.1	953.4	925.2	908.2	886.9	868.4	852.4	847.3	832.3	826.7	818.5
20°	946.6	922.0	900.5	878.0	847.1	829.8	817.3	810.5	798.4	791.1	785.8
22.5°	917.7	892.7	867.8	841.6	816.1	796.7	787.5	776.9	770.4	760.1	754.4
25°	876.4	849.2	819.4	791.1	772.8	758.1	743.4	734.0	724.6	719.9	709.4
27.5°	828.5	800.0	772.1	750.7	728.2	713.7	700.4	692.0	680.7	672.8	667.0
30°	802.1	768.6	744.5	725.1	696.3	682.7	672.8	662.3	653.9	645.5	639.8
32.5°	771.5	740.9	718.1	694.1	672.0	657.2	644.3	635.1	627.9	620.0	614.2
35°	723.5	697.9	674.3	650.2	634.0	618.8	603.7	595.8	589.0	581.7	576.4
37.5°	680.2	656.2	633.8	611.0	590.9	578.5	566.3	560.3	551.1	546.2	540.8
40°	653.4	629.8	605.7	583.8	562.8	553.4	542.4	533.5	525.1	521.5	515.7
42.5°	624.1	600.5	580.2	556.5	539.4	526.6	516.4	506.7	500.4	495.1	491.8
45°	580.6	559.7	539.8	516.2	500.0	489.0	477.5	468.6	462.8	459.2	453.4
47.5°	538.4	517.5	497.3	476.7	461.0	448.5	437.0	430.8	423.1	418.6	414.8
50°	507.8	489.0	467.5	448.7	433.0	420.4	411.0	403.1	396.3	390.6	388.0
52.5°	479.8	459.7	441.1	423.6	407.0	392.8	384.2	375.9	370.8	364.2	361.1
55°	433.5	414.1	398.4	381.1	364.9	352.9	342.4	335.1	329.8	322.5	318.3
57.5°	390.0	372.7	353.9	338.9	322.2	312.0	303.3	293.4	287.0	281.3	277.2
60°	360.7	340.8	324.6	310.5	295.8	282.7	274.9	267.0	260.2	254.4	250.8
62.5°	330.2	312.8	297.4	282.0	268.6	257.2	248.1	241.5	235.5	231.8	228.2
65°	283.2	269.6	253.9	241.4	228.8	220.4	213.1	207.3	203.1	200.5	197.4
67.5°	240.1	226.9	213.2	200.8	192.5	186.1	181.3	176.3	174.2	170.9	168.8
70°	212.0	198.4	186.4	177.0	168.6	163.9	160.7	157.1	155.0	150.8	148.7
72.5°	181.5	171.6	162.9	155.2	148.5	144.2	140.2	135.7	132.4	127.7	125.7
75°	142.9	134.0	127.2	122.0	117.8	112.0	106.3	101.6	100.0	98.4	97.9
77.5°	105.9	100.2	95.3	90.9	85.7	81.5	80.2	79.2	78.8	78.0	78.0
80°	83.2	78.0	74.3	69.1	66.0	66.0	66.0	64.9	65.4	65.4	65.4
82.5°	61.9	57.1	55.1	53.2	52.6	53.0	53.0	53.2	52.9	53.7	53.3
85°	31.9	32.5	33.5	33.0	33.5	33.5	34.6	34.0	34.6	33.5	34.6
87.5°	13.4	15.0	15.9	16.8	17.7	17.7	18.0	18.1	18.7	18.9	19.2
90°	8.6	10.2	12.5	14.9	17.2	19.5	18.8	19.5	20.3	21.1	22.7
92.5°	33.6	45.2	65.7	99.3	132.3	120.2	90.7	65.8	52.2	46.1	42.1
95°	71.1	101.6	168.1	284.6	412.8	463.6	376.1	281.5	190.8	149.3	121.2
97.5°	84.4	117.4	180.9	312.3	526.0	718.5	768.7	701.6	562.0	461.1	367.6
100°	93.8	124.3	179.0	294.7	500.4	740.4	894.4	921.8	858.4	767.0	655.9
102.5°	104.5	132.4	181.5	279.7	462.8	699.7	900.7	994.9	992.9	939.6	869.2
105°	122.0	146.2	188.4	268.9	416.7	628.6	853.0	1016.4	1094.5	1109.4	1089.1
107.5°	141.7	164.2	201.2	268.2	387.3	565.7	769.5	954.8	1081.7	1150.2	1178.0
110°	154.8	176.7	211.9	271.3	376.1	530.1	716.9	896.0	1039.8	1138.3	1193.1



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	168.6	189.8	222.5	277.5	369.8	506.3	671.3	837.8	984.8	1095.2	1165.5
115°	189.2	210.3	240.0	287.7	367.5	480.8	616.1	760.7	896.7	1011.7	1096.9
117.5°	209.7	229.2	258.6	301.2	368.9	465.8	582.8	704.9	822.3	925.5	1012.0
120°	222.8	242.4	270.5	311.2	371.4	458.9	565.3	675.5	781.0	874.9	953.8
122.5°	234.7	255.5	283.0	320.5	375.7	454.6	550.9	652.4	747.9	834.8	908.2
125°	252.5	273.6	301.0	335.4	382.3	448.8	532.4	621.5	706.8	781.8	844.4
127.5°	269.1	290.2	316.6	347.6	389.8	446.0	516.2	594.7	670.6	738.4	795.3
130°	279.1	300.2	326.0	355.7	394.8	444.1	507.4	577.8	648.1	711.5	764.6
132.5°	288.5	309.0	334.1	363.2	398.6	443.4	499.3	562.1	626.9	685.8	736.5
135°	301.0	322.1	346.3	372.9	404.2	442.5	488.6	541.0	596.5	647.3	691.9
137.5°	311.9	331.5	354.8	380.1	408.0	440.8	479.4	521.8	567.3	611.1	649.7
140°	318.2	337.7	360.4	383.9	410.5	440.2	473.8	510.5	550.4	587.9	621.5
142.5°	324.5	342.7	364.8	387.6	412.3	438.9	468.8	499.9	534.1	566.7	595.9
145°	332.3	350.3	370.6	391.7	413.6	437.0	462.1	487.1	512.9	537.9	560.6
147.5°	341.3	356.7	375.3	394.2	413.6	434.1	455.5	476.6	497.1	517.3	533.4
150°	346.3	360.4	378.4	394.8	413.6	431.6	451.1	469.1	487.1	503.5	518.3
152.5°	351.3	364.8	380.3	396.1	411.7	428.4	446.1	462.2	477.7	492.2	504.6
155°	359.6	370.6	383.9	396.4	409.7	423.0	438.6	451.9	464.4	476.1	485.5
157.5°	366.8	375.3	385.9	397.2	407.0	418.1	430.2	440.9	451.4	460.5	467.8
160°	370.6	378.4	387.8	397.2	405.8	414.4	424.5	434.7	443.3	451.1	456.6
162.5°	373.7	380.3	388.4	396.5	403.3	410.6	418.9	427.2	434.5	441.7	446.6
165°	377.6	383.1	389.3	394.8	399.5	405.0	411.2	417.5	422.2	427.7	431.6
167.5°	381.2	384.7	389.2	393.6	395.8	399.4	403.9	409.0	412.6	415.8	418.6
170°	383.1	384.7	388.6	391.7	393.3	395.6	399.5	403.4	405.8	408.9	410.5
172.5°	384.3	385.3	388.6	391.1	391.4	392.5	395.1	398.4	400.1	402.6	403.6
175°	385.4	386.2	387.8	389.3	388.6	388.6	390.1	391.7	392.5	394.0	394.0
177.5°	386.2	386.2	386.8	388.1	386.8	386.2	386.8	387.5	388.1	388.7	388.7
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1165.2	1164.8	1165.2	1163.5	1165.2	1164.8	1165.2	1170.2	1170.2	1170.7	1171.1
5°	1084.3	1083.7	1082.2	1077.5	1082.2	1083.7	1084.3	1085.8	1090.0	1097.4	1095.3
7.5°	1013.6	1012.9	1008.3	1008.4	1008.3	1012.9	1013.6	1017.7	1022.4	1026.9	1032.2
10°	971.7	972.2	966.0	962.3	966.0	972.2	971.7	975.4	982.2	985.8	989.5
12.5°	931.1	928.7	923.6	919.6	923.6	928.7	931.1	933.9	943.2	947.3	954.3
15°	877.5	872.2	859.7	860.7	859.7	872.2	877.5	875.4	884.8	890.0	892.1
17.5°	814.3	810.5	810.2	802.9	810.2	810.5	814.3	818.5	826.7	832.3	847.3
20°	777.5	774.9	775.9	768.6	775.9	774.9	777.5	785.8	791.1	798.4	810.5
22.5°	748.6	746.0	741.6	739.3	741.6	746.0	748.6	754.4	760.1	770.4	776.9
25°	706.3	702.1	697.9	700.5	697.9	702.1	706.3	709.4	719.9	724.6	734.0
27.5°	664.0	660.8	656.6	656.1	656.6	660.8	664.0	667.0	672.8	680.7	692.0
30°	637.2	634.0	631.9	629.3	631.9	634.0	637.2	639.8	645.5	653.9	662.3
32.5°	609.9	609.3	605.5	605.0	605.5	609.3	609.9	614.2	620.0	627.9	635.1
35°	574.3	571.2	570.1	570.7	570.1	571.2	574.3	576.4	581.7	589.0	595.8
37.5°	540.5	536.3	534.4	532.6	534.4	536.3	540.5	540.8	546.2	551.1	560.3
40°	516.2	512.0	511.0	509.9	511.0	512.0	516.2	515.7	521.5	525.1	533.5
42.5°	489.0	487.3	486.7	484.8	486.7	487.3	489.0	491.8	495.1	500.4	506.7
45°	451.8	451.3	448.2	449.2	448.2	451.3	451.8	453.4	459.2	462.8	468.6
47.5°	412.7	410.4	408.2	409.6	408.2	410.4	412.7	414.8	418.6	423.1	430.8
50°	385.9	384.8	380.1	381.1	380.1	384.8	385.9	388.0	390.6	396.3	403.1
52.5°	359.1	355.1	353.3	352.7	353.3	355.1	359.1	361.1	364.2	370.8	375.9
55°	314.7	309.9	307.8	306.8	307.8	309.9	314.7	318.3	322.5	329.8	335.1
57.5°	271.1	269.8	268.2	269.3	268.2	269.8	271.1	277.2	281.3	287.0	293.4
60°	245.5	245.5	245.5	245.0	245.5	245.5	245.5	250.8	254.4	260.2	267.0
62.5°	225.9	224.6	224.2	224.9	224.2	224.6	225.9	228.2	231.8	235.5	241.5
65°	195.8	195.3	193.2	192.7	193.2	195.3	195.8	197.4	200.5	203.1	207.3
67.5°	167.4	165.5	164.9	164.2	164.9	165.5	167.4	168.8	170.9	174.2	176.3
70°	146.1	145.0	141.9	142.4	141.9	145.0	146.1	148.7	150.8	155.0	157.1
72.5°	123.0	122.0	121.4	120.6	121.4	122.0	123.0	125.7	127.7	132.4	135.7
75°	97.4	96.9	96.3	98.4	96.3	96.9	97.4	97.9	98.4	100.0	101.6
77.5°	78.0	78.0	78.3	77.5	78.3	78.0	78.0	78.0	78.0	78.8	79.2
80°	65.4	65.4	64.9	64.9	64.9	65.4	65.4	65.4	65.4	65.4	64.9
82.5°	52.5	52.9	53.2	52.4	53.2	52.9	52.5	53.3	53.7	52.9	53.2
85°	34.6	34.0	35.1	34.6	35.1	34.0	34.6	34.6	33.5	34.6	34.0
87.5°	19.9	19.2	19.4	19.6	19.4	19.2	19.9	19.2	18.9	18.7	18.1
90°	21.9	22.7	23.5	22.7	23.5	22.7	21.9	22.7	21.1	20.3	19.5
92.5°	40.7	38.3	39.1	37.7	39.1	38.3	40.7	42.1	46.1	52.2	65.8
95°	106.3	99.3	93.8	90.7	93.8	99.3	106.3	121.2	149.3	190.8	281.5
97.5°	309.9	274.7	253.6	246.9	253.6	274.7	309.9	367.6	461.1	562.0	701.6
100°	577.0	519.9	489.4	490.2	489.4	519.9	577.0	655.9	767.0	858.4	921.8
102.5°	807.8	762.6	737.1	719.1	737.1	762.6	807.8	869.2	939.6	992.9	994.9
105°	1053.1	1023.4	998.4	994.5	998.4	1023.4	1053.1	1089.1	1109.4	1094.5	1016.4
107.5°	1178.7	1168.7	1160.2	1153.0	1160.2	1168.7	1178.7	1178.0	1150.2	1081.7	954.8
110°	1214.9	1221.2	1219.6	1218.1	1219.6	1221.2	1214.9	1193.1	1138.3	1039.8	896.0



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1205.6	1225.0	1230.9	1231.2	1230.9	1225.0	1205.6	1165.5	1095.2	984.8	837.8
115°	1155.5	1189.9	1205.6	1209.5	1205.6	1189.9	1155.5	1096.9	1011.7	896.7	760.7
117.5°	1073.1	1112.5	1135.0	1140.4	1135.0	1112.5	1073.1	1012.0	925.5	822.3	704.9
120°	1015.6	1059.4	1078.1	1082.8	1078.1	1059.4	1015.6	953.8	874.9	781.0	675.5
122.5°	963.0	1002.4	1023.1	1029.0	1023.1	1002.4	963.0	908.2	834.8	747.9	652.4
125°	894.4	928.8	948.3	953.8	948.3	928.8	894.4	844.4	781.8	706.8	621.5
127.5°	839.8	869.2	886.9	891.9	886.9	869.2	839.8	795.3	738.4	670.6	594.7
130°	806.1	834.2	850.6	856.9	850.6	834.2	806.1	764.6	711.5	648.1	577.8
132.5°	775.4	803.6	818.1	822.5	818.1	803.6	775.4	736.5	685.8	626.9	562.1
135°	730.2	753.7	767.7	773.2	767.7	753.7	730.2	691.9	647.3	596.5	541.0
137.5°	681.9	705.7	717.6	721.2	717.6	705.7	681.9	649.7	611.1	567.3	521.8
140°	651.3	673.1	685.7	684.9	685.7	673.1	651.3	621.5	587.9	550.4	510.5
142.5°	621.2	640.6	651.9	651.1	651.9	640.6	621.2	595.9	566.7	534.1	499.9
145°	580.1	596.5	602.8	604.3	602.8	596.5	580.1	560.6	537.9	512.9	487.1
147.5°	548.2	559.3	565.3	565.9	565.3	559.3	548.2	533.4	517.3	497.1	476.6
150°	530.1	538.7	543.4	543.4	543.4	538.7	530.1	518.3	503.5	487.1	469.1
152.5°	513.8	521.8	524.6	524.6	524.6	521.8	513.8	504.6	492.2	477.7	462.2
155°	492.5	498.8	500.4	501.1	500.4	498.8	492.5	485.5	476.1	464.4	451.9
157.5°	473.9	478.6	479.9	479.7	479.9	478.6	473.9	467.8	460.5	451.4	440.9
160°	462.1	466.7	466.7	466.0	466.7	466.7	462.1	456.6	451.1	443.3	434.7
162.5°	450.2	454.2	454.2	453.5	454.2	454.2	450.2	446.6	441.7	434.5	427.2
165°	434.7	437.8	437.0	437.0	437.0	437.8	434.7	431.6	427.7	422.2	417.5
167.5°	420.0	422.2	421.4	421.4	421.4	422.2	420.0	418.6	415.8	412.6	409.0
170°	411.2	412.8	412.0	412.0	412.0	412.8	411.2	410.5	408.9	405.8	403.4
172.5°	403.7	405.3	403.9	403.3	403.9	405.3	403.7	403.6	402.6	400.1	398.4
175°	394.0	394.8	394.0	393.3	394.0	394.8	394.0	394.0	394.0	392.5	391.7
177.5°	388.1	388.7	387.5	387.5	387.5	388.7	388.1	388.7	388.7	388.1	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1167.3	1173.2	1179.0	1184.5	1192.9	1196.6	1202.1	1204.2	1210.4	1219.7	1227.2
5°	1096.3	1104.7	1115.7	1124.6	1138.7	1149.7	1161.8	1173.3	1186.9	1206.3	1223.5
7.5°	1036.1	1044.4	1057.6	1074.1	1089.7	1105.3	1121.8	1137.5	1156.9	1184.7	1212.2
10°	996.3	1006.3	1022.0	1039.8	1059.1	1074.3	1093.7	1113.6	1137.7	1169.6	1202.6
12.5°	962.0	969.4	987.6	1004.6	1026.5	1045.8	1064.8	1088.0	1115.5	1149.5	1189.2
15°	907.3	917.8	935.6	954.4	977.5	997.9	1022.5	1050.8	1077.5	1119.4	1167.5
17.5°	852.4	868.4	886.9	908.2	925.2	953.4	980.1	1009.1	1042.0	1086.4	1139.2
20°	817.3	829.8	847.1	878.0	900.5	922.0	946.6	982.7	1013.1	1063.3	1118.3
22.5°	787.5	796.7	816.1	841.6	867.8	892.7	917.7	952.1	989.6	1037.4	1096.9
25°	743.4	758.1	772.8	791.1	819.4	849.2	876.4	905.7	945.5	996.3	1060.7
27.5°	700.4	713.7	728.2	750.7	772.1	800.0	828.5	862.1	904.8	958.5	1023.9
30°	672.8	682.7	696.3	725.1	744.5	768.6	802.1	831.9	871.7	928.8	997.9
32.5°	644.3	657.2	672.0	694.1	718.1	740.9	771.5	803.9	844.5	900.7	971.5
35°	603.7	618.8	634.0	650.2	674.3	697.9	723.5	759.1	800.5	855.0	924.6
37.5°	566.3	578.5	590.9	611.0	633.8	656.2	680.2	715.3	754.2	813.0	876.8
40°	542.4	553.4	562.8	583.8	605.7	629.8	653.4	684.3	726.2	781.1	842.9
42.5°	516.4	526.6	539.4	556.5	580.2	600.5	624.1	653.3	692.7	748.5	802.7
45°	477.5	489.0	500.0	516.2	539.8	559.7	580.6	608.4	648.7	694.8	742.9
47.5°	437.0	448.5	461.0	476.7	497.3	517.5	538.4	563.0	599.8	645.0	677.5
50°	411.0	420.4	433.0	448.7	467.5	489.0	507.8	534.5	569.6	605.2	633.5
52.5°	384.2	392.8	407.0	423.6	441.1	459.7	479.8	502.7	534.4	567.9	590.4
55°	342.4	352.9	364.9	381.1	398.4	414.1	433.5	457.1	482.2	507.3	522.5
57.5°	303.3	312.0	322.2	338.9	353.9	372.7	390.0	408.4	431.6	450.6	460.5
60°	274.9	282.7	295.8	310.5	324.6	340.8	360.7	379.1	396.9	412.0	419.9
62.5°	248.1	257.2	268.6	282.0	297.4	312.8	330.2	345.5	361.2	374.3	379.7
65°	213.1	220.4	228.8	241.4	253.9	269.6	283.2	298.9	310.5	317.8	322.5
67.5°	181.3	186.1	192.5	200.8	213.2	226.9	240.1	252.4	262.0	267.0	271.2
70°	160.7	163.9	168.6	177.0	186.4	198.4	212.0	220.9	229.3	233.5	237.7
72.5°	140.2	144.2	148.5	155.2	162.9	171.6	181.5	192.5	197.1	202.1	204.6
75°	106.3	112.0	117.8	122.0	127.2	134.0	142.9	149.7	152.4	156.5	157.1
77.5°	80.2	81.5	85.7	90.9	95.3	100.2	105.9	111.9	113.2	115.4	116.8
80°	66.0	66.0	66.0	69.1	74.3	78.0	83.2	86.4	88.5	89.0	89.5
82.5°	53.0	53.0	52.6	53.2	55.1	57.1	61.9	65.4	67.1	66.8	65.7
85°	34.6	33.5	33.5	33.0	33.5	32.5	31.9	34.0	37.2	37.2	36.1
87.5°	18.0	17.7	17.7	16.8	15.9	15.0	13.4	13.6	13.1	14.4	13.7
90°	18.8	19.5	17.2	14.9	12.5	10.2	8.6	7.0	4.7	3.1	1.6
92.5°	90.7	120.2	132.3	99.3	65.7	45.2	33.6	27.1	21.0	14.4	9.7
95°	376.1	463.6	412.8	284.6	168.1	101.6	71.1	50.8	37.5	28.9	26.6
97.5°	768.7	718.5	526.0	312.3	180.9	117.4	84.4	64.4	52.9	46.1	45.3
100°	894.4	740.4	500.4	294.7	179.0	124.3	93.8	75.1	64.1	58.6	57.9
102.5°	900.7	699.7	462.8	279.7	181.5	132.4	104.5	87.6	77.2	72.4	71.0
105°	853.0	628.6	416.7	268.9	188.4	146.2	122.0	107.1	97.7	93.0	90.7
107.5°	769.5	565.7	387.3	268.2	201.2	164.2	141.7	127.7	118.5	114.0	111.6
110°	716.9	530.1	376.1	271.3	211.9	176.7	154.8	141.5	132.9	129.0	126.7



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	671.3	506.3	369.8	277.5	222.5	189.8	168.6	155.3	146.7	142.8	140.4
115°	616.1	480.8	367.5	287.7	240.0	210.3	189.2	175.9	168.1	163.4	160.3
117.5°	582.8	465.8	368.9	301.2	258.6	229.2	209.7	194.8	187.6	183.7	180.1
120°	565.3	458.9	371.4	311.2	270.5	242.4	222.8	208.0	200.1	196.2	193.9
122.5°	550.9	454.6	375.7	320.5	283.0	255.5	234.7	220.5	212.0	208.1	205.8
125°	532.4	448.8	382.3	335.4	301.0	273.6	252.5	237.7	229.1	224.4	222.8
127.5°	516.2	446.0	389.8	347.6	316.6	290.2	269.1	252.7	243.9	238.1	235.8
130°	507.4	444.1	394.8	355.7	326.0	300.2	279.1	262.7	253.3	246.3	243.9
132.5°	499.3	443.4	398.6	363.2	334.1	309.0	288.5	272.1	260.8	253.2	250.2
135°	488.6	442.5	404.2	372.9	346.3	322.1	301.0	284.6	272.9	264.3	261.1
137.5°	479.4	440.8	408.0	380.1	354.8	331.5	311.9	295.7	283.2	274.7	271.4
140°	473.8	440.2	410.5	383.9	360.4	337.7	318.2	302.6	290.1	282.2	278.3
142.5°	468.8	438.9	412.3	387.6	364.8	342.7	324.5	308.8	297.6	289.1	285.8
145°	462.1	437.0	413.6	391.7	370.6	350.3	332.3	319.0	307.3	300.2	297.9
147.5°	455.5	434.1	413.6	394.2	375.3	356.7	341.3	328.5	318.4	311.5	310.1
150°	451.1	431.6	413.6	394.8	378.4	360.4	346.3	335.4	325.2	319.0	318.2
152.5°	446.1	428.4	411.7	396.1	380.3	364.8	351.3	341.7	332.7	326.5	326.3
155°	438.6	423.0	409.7	396.4	383.9	370.6	359.6	351.0	343.2	338.5	338.5
157.5°	430.2	418.1	407.0	397.2	385.9	375.3	366.8	359.5	352.6	348.8	348.2
160°	424.5	414.4	405.8	397.2	387.8	378.4	370.6	365.1	358.9	355.7	355.7
162.5°	418.9	410.6	403.3	396.5	388.4	380.3	373.7	368.9	363.9	361.4	361.4
165°	411.2	405.0	399.5	394.8	389.3	383.1	377.6	374.5	370.6	369.0	369.8
167.5°	403.9	399.4	395.8	393.6	389.2	384.7	381.2	379.0	376.1	375.3	376.2
170°	399.5	395.6	393.3	391.7	388.6	384.7	383.1	381.5	379.2	378.4	380.0
172.5°	395.1	392.5	391.4	391.1	388.6	385.3	384.3	383.4	381.7	381.5	382.5
175°	390.1	388.6	388.6	389.3	387.8	386.2	385.4	385.4	383.9	384.7	385.4
177.5°	386.8	386.2	386.8	388.1	386.8	386.2	386.2	386.2	385.6	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1229.7	1234.3	1240.2	1249.0	1255.7	1261.5	1262.8	1264.5	1268.7	1275.8	1281.2
5°	1237.7	1249.7	1269.1	1287.9	1308.4	1325.1	1340.8	1351.8	1362.3	1384.3	1402.1
7.5°	1235.2	1262.0	1292.3	1326.2	1360.4	1393.6	1424.4	1451.9	1479.3	1511.4	1547.9
10°	1233.5	1264.9	1305.7	1349.2	1396.8	1443.4	1488.5	1523.5	1564.4	1601.0	1647.6
12.5°	1225.5	1270.8	1319.6	1375.2	1433.7	1487.4	1546.7	1595.2	1641.9	1694.8	1749.0
15°	1215.2	1270.1	1331.9	1405.7	1494.7	1559.7	1620.4	1704.7	1762.3	1819.9	1897.3
17.5°	1196.2	1263.3	1340.5	1436.4	1510.7	1597.9	1689.3	1755.9	1833.5	1914.6	1984.8
20°	1181.1	1259.1	1345.5	1439.8	1534.5	1629.3	1717.8	1797.3	1877.5	1971.2	2028.8
22.5°	1166.1	1243.2	1333.0	1433.1	1534.9	1634.7	1734.9	1828.3	1918.5	2013.1	2086.6
25°	1134.0	1225.6	1323.0	1425.1	1525.6	1635.6	1754.9	1859.1	1970.6	2068.0	2137.7
27.5°	1101.5	1185.5	1282.5	1386.0	1497.8	1627.7	1768.1	1886.6	1998.3	2068.0	2089.9
30°	1072.2	1161.2	1250.2	1355.5	1476.4	1621.4	1770.6	1906.2	1997.9	2028.2	2005.7
32.5°	1042.5	1123.1	1211.3	1319.0	1447.5	1605.9	1774.0	1894.5	1949.7	1926.5	1834.8
35°	990.0	1062.8	1148.1	1256.0	1403.6	1597.4	1760.2	1841.8	1828.2	1697.3	1524.6
37.5°	933.9	993.2	1072.2	1185.0	1358.2	1563.3	1700.7	1712.7	1594.9	1394.0	1194.4
40°	889.5	942.9	1024.1	1141.9	1323.0	1529.8	1640.8	1592.1	1409.4	1185.8	1019.4
42.5°	846.4	891.4	969.6	1096.6	1289.5	1484.2	1551.6	1445.5	1234.7	1023.3	871.9
45°	773.3	815.7	894.2	1024.6	1220.9	1396.8	1387.9	1203.6	992.7	822.5	696.8
47.5°	704.0	741.0	814.7	947.8	1140.4	1265.9	1182.7	986.6	807.6	671.1	581.5
50°	655.0	691.6	764.9	896.3	1075.9	1167.5	1048.7	859.7	695.8	582.7	511.5
52.5°	608.1	643.9	710.9	838.9	998.0	1052.8	925.1	749.9	613.3	515.7	454.5
55°	542.4	569.6	629.8	752.3	871.2	883.8	754.4	607.8	495.3	427.2	385.3
57.5°	475.5	498.9	558.4	656.0	739.4	732.9	610.3	483.4	407.6	357.1	326.7
60°	431.9	455.0	507.3	591.1	653.9	631.9	519.4	417.3	352.3	315.2	291.1
62.5°	391.3	409.3	458.3	519.5	564.7	539.8	444.0	359.5	308.0	276.6	257.6
65°	332.5	347.1	386.4	418.3	443.4	419.4	339.8	281.1	244.0	222.0	208.9
67.5°	276.5	285.9	310.7	322.2	339.9	313.5	255.5	216.2	195.1	176.5	167.4
70°	241.4	248.2	261.3	270.7	275.4	248.2	205.2	176.4	158.6	145.5	139.8
72.5°	206.2	212.1	214.8	222.5	220.1	194.6	165.0	142.1	129.3	120.4	113.0
75°	157.6	160.2	157.6	154.4	147.6	129.8	109.4	97.9	88.5	84.3	81.7
77.5°	114.9	114.0	110.5	105.5	93.9	82.7	71.7	67.9	63.8	61.6	60.6
80°	88.5	86.4	83.2	75.4	65.4	57.6	55.0	52.4	50.8	48.2	47.6
82.5°	65.9	64.6	59.4	52.8	45.8	42.1	39.9	39.0	37.4	36.0	35.9
85°	35.1	33.5	27.7	24.1	23.0	22.0	21.5	21.5	19.4	18.8	18.8
87.5°	11.9	9.7	9.8	8.8	9.2	8.8	9.7	9.3	9.4	9.6	8.9
90°	3.1	4.7	7.0	8.6	10.2	12.5	14.9	17.2	19.5	18.8	19.5
92.5°	14.4	21.0	27.1	33.6	45.2	65.7	99.3	132.3	120.2	90.7	65.8
95°	28.9	37.5	50.8	71.1	101.6	168.1	284.6	412.8	463.6	376.1	281.5
97.5°	46.1	52.9	64.4	84.4	117.4	180.9	312.3	526.0	718.5	768.7	701.6
100°	58.6	64.1	75.1	93.8	124.3	179.0	294.7	500.4	740.4	894.4	921.8
102.5°	72.4	77.2	87.6	104.5	132.4	181.5	279.7	462.8	699.7	900.7	994.9
105°	93.0	97.7	107.1	122.0	146.2	188.4	268.9	416.7	628.6	853.0	1016.4
107.5°	114.0	118.5	127.7	141.7	164.2	201.2	268.2	387.3	565.7	769.5	954.8
110°	129.0	132.9	141.5	154.8	176.7	211.9	271.3	376.1	530.1	716.9	896.0



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	142.8	146.7	155.3	168.6	189.8	222.5	277.5	369.8	506.3	671.3	837.8
115°	163.4	168.1	175.9	189.2	210.3	240.0	287.7	367.5	480.8	616.1	760.7
117.5°	183.7	187.6	194.8	209.7	229.2	258.6	301.2	368.9	465.8	582.8	704.9
120°	196.2	200.1	208.0	222.8	242.4	270.5	311.2	371.4	458.9	565.3	675.5
122.5°	208.1	212.0	220.5	234.7	255.5	283.0	320.5	375.7	454.6	550.9	652.4
125°	224.4	229.1	237.7	252.5	273.6	301.0	335.4	382.3	448.8	532.4	621.5
127.5°	238.1	243.9	252.7	269.1	290.2	316.6	347.6	389.8	446.0	516.2	594.7
130°	246.3	253.3	262.7	279.1	300.2	326.0	355.7	394.8	444.1	507.4	577.8
132.5°	253.2	260.8	272.1	288.5	309.0	334.1	363.2	398.6	443.4	499.3	562.1
135°	264.3	272.9	284.6	301.0	322.1	346.3	372.9	404.2	442.5	488.6	541.0
137.5°	274.7	283.2	295.7	311.9	331.5	354.8	380.1	408.0	440.8	479.4	521.8
140°	282.2	290.1	302.6	318.2	337.7	360.4	383.9	410.5	440.2	473.8	510.5
142.5°	289.1	297.6	308.8	324.5	342.7	364.8	387.6	412.3	438.9	468.8	499.9
145°	300.2	307.3	319.0	332.3	350.3	370.6	391.7	413.6	437.0	462.1	487.1
147.5°	311.5	318.4	328.5	341.3	356.7	375.3	394.2	413.6	434.1	455.5	476.6
150°	319.0	325.2	335.4	346.3	360.4	378.4	394.8	413.6	431.6	451.1	469.1
152.5°	326.5	332.7	341.7	351.3	364.8	380.3	396.1	411.7	428.4	446.1	462.2
155°	338.5	343.2	351.0	359.6	370.6	383.9	396.4	409.7	423.0	438.6	451.9
157.5°	348.8	352.6	359.5	366.8	375.3	385.9	397.2	407.0	418.1	430.2	440.9
160°	355.7	358.9	365.1	370.6	378.4	387.8	397.2	405.8	414.4	424.5	434.7
162.5°	361.4	363.9	368.9	373.7	380.3	388.4	396.5	403.3	410.6	418.9	427.2
165°	369.0	370.6	374.5	377.6	383.1	389.3	394.8	399.5	405.0	411.2	417.5
167.5°	375.3	376.1	379.0	381.2	384.7	389.2	393.6	395.8	399.4	403.9	409.0
170°	378.4	379.2	381.5	383.1	384.7	388.6	391.7	393.3	395.6	399.5	403.4
172.5°	381.5	381.7	383.4	384.3	385.3	388.6	391.1	391.4	392.5	395.1	398.4
175°	384.7	383.9	385.4	385.4	386.2	387.8	389.3	388.6	388.6	390.1	391.7
177.5°	386.2	385.6	386.2	386.2	386.2	386.8	388.1	386.8	386.2	386.8	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1290.0	1290.0	1291.7	1298.0	1298.8	1304.3	1302.6
5°	1417.8	1427.7	1431.4	1447.1	1456.5	1460.7	1452.3
7.5°	1574.0	1602.1	1615.4	1631.8	1646.4	1650.8	1639.3
10°	1687.9	1717.2	1741.9	1757.0	1771.2	1780.6	1792.6
12.5°	1798.1	1834.1	1857.5	1878.9	1893.5	1905.4	1907.4
15°	1917.8	1972.2	2013.6	2043.9	2059.1	2067.0	2063.8
17.5°	2038.5	2089.0	2118.4	2149.4	2170.4	2171.5	2172.1
20°	2106.8	2156.0	2190.0	2213.0	2236.6	2235.6	2240.8
22.5°	2152.4	2191.2	2217.2	2234.0	2242.1	2238.1	2239.1
25°	2173.8	2185.3	2180.6	2153.9	2147.1	2122.5	2126.7
27.5°	2063.6	2009.2	1952.8	1880.4	1823.2	1777.6	1779.9
30°	1914.1	1817.8	1707.8	1615.7	1533.0	1509.9	1460.7
32.5°	1705.1	1560.6	1431.8	1345.9	1274.9	1255.7	1212.8
35°	1350.8	1210.4	1078.0	998.4	967.0	923.0	922.5
37.5°	1049.9	926.4	856.3	796.6	765.3	738.7	736.1
40°	883.2	786.9	734.0	691.1	660.2	640.3	635.6
42.5°	766.8	688.9	639.4	612.8	589.0	578.7	571.1
45°	626.2	573.8	539.3	515.2	504.2	496.3	492.1
47.5°	523.8	488.7	465.1	449.1	440.2	431.9	434.1
50°	468.1	439.3	422.0	406.8	400.0	394.2	394.8
52.5°	423.2	397.4	383.4	372.5	364.0	359.9	357.9
55°	359.2	342.9	328.8	320.9	316.2	310.5	308.9
57.5°	306.4	293.8	282.3	273.4	272.2	266.7	267.4
60°	271.2	260.7	251.3	246.6	242.9	238.2	239.8
62.5°	242.3	233.5	224.9	221.0	217.4	213.9	214.7
65°	198.4	190.0	184.8	182.7	181.1	179.6	178.0
67.5°	158.1	153.0	149.7	145.2	142.0	141.5	139.9
70°	133.0	126.2	120.4	114.7	113.1	112.6	113.1
72.5°	106.6	102.3	100.7	97.9	97.6	96.2	97.2
75°	80.1	78.5	77.5	75.4	75.4	75.4	75.4
77.5°	59.1	58.1	57.5	57.1	56.5	55.8	55.7
80°	46.1	45.5	44.5	44.5	44.0	44.5	44.0
82.5°	34.8	34.7	33.6	33.6	33.1	32.8	33.1
85°	17.8	17.3	18.3	17.3	17.8	16.8	17.8
87.5°	9.1	9.2	9.1	9.0	8.7	9.7	8.7
90°	20.3	21.1	22.7	21.9	22.7	23.5	22.7
92.5°	52.2	46.1	42.1	40.7	38.3	39.1	37.7
95°	190.8	149.3	121.2	106.3	99.3	93.8	90.7
97.5°	562.0	461.1	367.6	309.9	274.7	253.6	246.9
100°	858.4	767.0	655.9	577.0	519.9	489.4	490.2
102.5°	992.9	939.6	869.2	807.8	762.6	737.1	719.1
105°	1094.5	1109.4	1089.1	1053.1	1023.4	998.4	994.5
107.5°	1081.7	1150.2	1178.0	1178.7	1168.7	1160.2	1153.0
110°	1039.8	1138.3	1193.1	1214.9	1221.2	1219.6	1218.1



TEST NUMBER: P332314

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	984.8	1095.2	1165.5	1205.6	1225.0	1230.9	1231.2
115°	896.7	1011.7	1096.9	1155.5	1189.9	1205.6	1209.5
117.5°	822.3	925.5	1012.0	1073.1	1112.5	1135.0	1140.4
120°	781.0	874.9	953.8	1015.6	1059.4	1078.1	1082.8
122.5°	747.9	834.8	908.2	963.0	1002.4	1023.1	1029.0
125°	706.8	781.8	844.4	894.4	928.8	948.3	953.8
127.5°	670.6	738.4	795.3	839.8	869.2	886.9	891.9
130°	648.1	711.5	764.6	806.1	834.2	850.6	856.9
132.5°	626.9	685.8	736.5	775.4	803.6	818.1	822.5
135°	596.5	647.3	691.9	730.2	753.7	767.7	773.2
137.5°	567.3	611.1	649.7	681.9	705.7	717.6	721.2
140°	550.4	587.9	621.5	651.3	673.1	685.7	684.9
142.5°	534.1	566.7	595.9	621.2	640.6	651.9	651.1
145°	512.9	537.9	560.6	580.1	596.5	602.8	604.3
147.5°	497.1	517.3	533.4	548.2	559.3	565.3	565.9
150°	487.1	503.5	518.3	530.1	538.7	543.4	543.4
152.5°	477.7	492.2	504.6	513.8	521.8	524.6	524.6
155°	464.4	476.1	485.5	492.5	498.8	500.4	501.1
157.5°	451.4	460.5	467.8	473.9	478.6	479.9	479.7
160°	443.3	451.1	456.6	462.1	466.7	466.7	466.0
162.5°	434.5	441.7	446.6	450.2	454.2	454.2	453.5
165°	422.2	427.7	431.6	434.7	437.8	437.0	437.0
167.5°	412.6	415.8	418.6	420.0	422.2	421.4	421.4
170°	405.8	408.9	410.5	411.2	412.8	412.0	412.0
172.5°	400.1	402.6	403.6	403.7	405.3	403.9	403.3
175°	392.5	394.0	394.0	394.0	394.8	394.0	393.3
177.5°	388.1	388.7	388.7	388.1	388.7	387.5	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2

(END OF REPORT)