

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332035-935

Luminaire Tested: **S123DIP-S1000D1025U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332035-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D1025U935-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6743.8 lumens  
Efficiency: N/A  
Efficacy: 111.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332035-935

CATALOG NUMBER: S123DIP-S1000D1025U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332035-935

CATALOG NUMBER: S123DIP-S1000D1025U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	98	94	90	86	91	87	84	81	74	72	70	62	61	59	52	50	49	44
2	89	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41	37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	38	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	35	39	34	31	32	29	26	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14670	14670	14670
5°	14738	14536	14638
10°	14641	14410	14499
15°	14469	14247	14273
20°	14269	14014	14027
25°	14001	13737	13709
30°	13706	13430	13326
35°	13397	13104	12935
40°	13075	12745	12546
45°	12718	12415	12113
50°	12363	12010	11675
55°	11898	11590	11237
60°	11427	11102	10747
65°	11013	10565	10236
70°	10401	9958	9514
75°	9503	9162	8771
80°	8573	8207	8133
85°	7534	7237	6941



TEST NUMBER: P332035-935

CATALOG NUMBER: S123DIP-S1000D1025U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.4	1.9
10°-20°	362.5	5.4
20°-30°	535.5	7.9
30°-40°	625.5	9.3
40°-50°	628.8	9.3
50°-60°	552.4	8.2
60°-70°	411.5	6.1
70°-80°	234.5	3.5
80°-90°	70.6	1.0
90°-100°	236.3	3.5
100°-110°	669.0	9.9
110°-120°	658.1	9.8
120°-130°	525.0	7.8
130°-140°	413.9	6.1
140°-150°	308.9	4.6
150°-160°	215.3	3.2
160°-170°	126.5	1.9
170°-180°	41.2	0.6
0°-30°	1026.3	15.2
0°-40°	1651.8	24.5
0°-60°	2833.0	42.0
0°-90°	3549.6	52.6
90°-120°	1563.5	23.2
90°-150°	2811.2	41.7
90°-180°	3194.0	47.4
0°-180°	6743.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1363	1363	1363	1363	1363	
5°	1364	1358	1345	1356	1355	129
15°	1298	1293	1278	1287	1281	366
25°	1179	1171	1157	1158	1154	543
35°	1020	1012	997	990	984	638
45°	836	830	816	802	796	645
55°	634	632	618	605	599	568
65°	432	426	415	406	402	427
75°	228	224	220	215	211	244
85°	61	59	59	56	56	67
90°	2	10	22	24	25	5
95°	29	95	510	149	100	32
105°	100	147	691	1208	1093	106
115°	176	220	529	1159	1330	174
125°	245	289	493	894	1048	217
135°	287	342	486	736	850	222
145°	327	375	480	604	664	205
155°	372	401	465	529	551	171
165°	406	418	445	472	480	115
175°	424	424	427	433	432	40
180°	425	425	425	425	425	



TEST NUMBER: P332035-935

CATALOG NUMBER: S123DIP-S1000D1025U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1367.5	1366.8	1365.9	1365.0	1364.3	1362.6	1360.4	1358.1	1355.8	1353.5	1355.6
5°	1364.0	1362.7	1361.4	1360.1	1358.8	1356.8	1353.9	1351.0	1348.2	1345.3	1347.9
7.5°	1350.7	1349.4	1348.1	1346.8	1345.5	1343.3	1340.4	1337.4	1334.5	1331.5	1333.8
10°	1339.5	1338.2	1336.8	1335.5	1334.2	1331.9	1328.5	1325.1	1321.7	1318.4	1320.7
12.5°	1324.4	1323.4	1322.2	1321.1	1320.1	1317.9	1314.7	1311.6	1308.4	1305.2	1306.9
15°	1298.4	1297.4	1296.3	1295.3	1294.3	1292.0	1288.7	1285.3	1281.9	1278.5	1280.6
17.5°	1268.2	1266.8	1265.5	1264.1	1262.7	1260.4	1257.0	1253.6	1250.3	1246.8	1248.3
20°	1245.7	1244.1	1242.6	1241.0	1239.4	1236.9	1233.6	1230.2	1226.8	1223.4	1224.4
22.5°	1220.4	1218.8	1217.3	1215.6	1214.1	1211.7	1208.2	1204.9	1201.5	1198.1	1198.9
25°	1178.9	1177.3	1175.8	1174.2	1172.6	1170.2	1166.7	1163.4	1160.0	1156.6	1156.8
27.5°	1134.6	1133.1	1131.5	1130.1	1128.5	1125.9	1122.3	1118.7	1115.0	1111.4	1111.6
30°	1102.7	1101.4	1100.1	1098.8	1097.5	1095.0	1091.4	1087.7	1084.1	1080.5	1080.5
32.5°	1070.8	1069.1	1067.4	1065.7	1063.9	1061.7	1058.9	1056.1	1053.3	1050.4	1049.0
35°	1019.5	1018.0	1016.4	1014.9	1013.2	1010.8	1007.4	1004.0	1000.7	997.2	995.7
37.5°	967.0	965.0	963.0	961.0	959.1	956.4	953.0	949.5	946.1	942.6	940.7
40°	930.5	928.8	927.3	925.7	924.2	921.6	917.9	914.3	910.7	907.0	904.9
42.5°	893.9	892.1	890.4	888.6	886.8	884.1	880.5	876.8	873.1	869.5	867.5
45°	835.5	834.5	833.4	832.4	831.4	829.1	825.8	822.3	819.0	815.6	812.5
47.5°	777.7	776.1	774.6	773.1	771.6	769.2	766.1	762.9	759.7	756.6	753.5
50°	738.3	736.9	735.6	734.3	733.1	730.7	727.3	723.9	720.6	717.2	714.3
52.5°	697.0	696.1	695.3	694.4	693.4	691.2	687.7	684.1	680.4	676.8	674.4
55°	634.0	633.7	633.4	633.2	632.9	631.1	627.8	624.3	621.0	617.6	614.7
57.5°	573.9	573.1	572.2	571.4	570.4	568.6	565.9	563.2	560.5	557.8	555.3
60°	530.8	530.5	530.3	530.0	529.8	528.1	525.0	521.9	518.8	515.7	513.2
62.5°	492.4	491.7	491.0	490.3	489.7	487.8	484.7	481.6	478.5	475.3	472.9
65°	432.4	431.1	429.8	428.5	427.2	425.2	422.7	420.1	417.4	414.8	412.8
67.5°	368.9	367.7	366.6	365.5	364.3	362.7	360.8	358.8	356.8	354.8	353.0
70°	330.5	328.9	327.4	325.8	324.3	322.6	321.1	319.5	318.0	316.4	314.6
72.5°	290.2	289.0	287.8	286.7	285.6	284.1	282.3	280.6	278.8	277.0	275.4
75°	228.5	227.5	226.4	225.4	224.4	223.4	222.7	221.9	221.1	220.3	219.0
77.5°	173.9	173.3	172.7	172.2	171.6	170.8	170.0	169.0	168.1	167.1	166.3
80°	138.3	137.5	136.7	136.0	135.2	134.5	134.0	133.5	132.9	132.4	132.2
82.5°	103.6	103.4	103.3	103.1	103.0	102.8	102.7	102.6	102.5	102.5	101.9
85°	61.0	60.4	59.9	59.4	58.9	58.6	58.6	58.6	58.6	58.6	58.0
87.5°	24.7	24.5	24.2	24.0	23.8	23.7	24.0	24.3	24.6	24.9	24.5
90°	1.7	3.4	5.2	7.7	9.5	11.2	13.8	16.4	18.9	21.5	20.7
92.5°	10.7	15.8	23.1	29.7	36.9	49.7	72.2	109.2	145.4	132.2	99.7
95°	29.2	31.8	41.2	55.9	78.2	111.8	184.8	312.8	453.7	509.6	413.4
97.5°	49.9	50.7	58.1	70.8	92.8	129.1	198.9	343.3	578.2	789.8	845.0
100°	63.6	64.5	70.5	82.5	103.1	136.6	196.8	324.0	550.0	813.9	983.2
102.5°	78.0	79.6	84.9	96.3	114.9	145.6	199.6	307.5	508.8	769.2	990.1
105°	99.7	102.3	107.5	117.8	134.1	160.7	207.2	295.7	458.1	691.0	937.6
107.5°	122.7	125.3	130.3	140.4	155.8	180.5	221.2	294.8	425.8	621.9	845.8
110°	139.2	141.8	146.1	155.6	170.1	194.2	232.9	298.3	413.4	582.7	788.1



TEST NUMBER: P332035-935

CATALOG NUMBER: S123DIP-S1000D1025U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	154.4	157.0	161.3	170.7	185.3	208.7	244.6	305.1	406.5	556.6	737.9
115°	176.2	179.6	184.8	193.4	208.0	231.2	263.8	316.2	403.9	528.6	677.3
117.5°	198.0	202.0	206.3	214.1	230.5	252.0	284.3	331.1	405.4	512.0	640.6
120°	213.1	215.7	220.0	228.6	245.0	266.4	297.4	342.1	408.2	504.5	621.4
122.5°	226.2	228.8	233.1	242.4	258.0	280.9	311.1	352.4	413.0	499.6	605.5
125°	245.0	246.7	251.8	261.2	277.6	300.8	330.9	368.7	420.3	493.4	585.3
127.5°	259.2	261.7	268.1	277.8	295.8	319.0	348.1	382.1	428.5	490.3	567.4
130°	268.1	270.7	278.4	288.8	306.8	330.0	358.3	391.1	434.0	488.2	557.8
132.5°	275.0	278.3	286.7	299.1	317.1	339.7	367.3	399.3	438.2	487.5	548.8
135°	287.1	290.5	300.0	312.8	330.9	354.0	380.7	409.9	444.4	486.5	537.2
137.5°	298.4	302.0	311.3	325.0	342.9	364.4	390.0	417.8	448.4	484.6	527.0
140°	306.0	310.2	318.8	332.6	349.8	371.3	396.2	422.0	451.2	483.9	520.8
142.5°	314.2	317.8	327.1	339.5	356.6	376.8	401.1	426.1	453.2	482.5	515.3
145°	327.4	330.0	337.8	350.7	365.2	385.0	407.3	430.6	454.6	480.4	507.9
147.5°	340.9	342.4	350.0	361.1	375.2	392.1	412.5	433.3	454.6	477.2	500.7
150°	349.8	350.7	357.5	368.7	380.7	396.2	415.9	434.0	454.6	474.4	495.8
152.5°	358.7	358.9	365.8	375.6	386.2	401.1	418.0	435.4	452.5	471.0	490.4
155°	372.1	372.1	377.3	385.9	395.4	407.3	422.0	435.8	450.3	464.9	482.2
157.5°	382.8	383.5	387.6	395.2	403.2	412.5	424.2	436.6	447.5	459.6	472.9
160°	391.1	391.1	394.5	401.3	407.3	415.9	426.3	436.6	446.1	455.5	466.7
162.5°	397.3	397.3	400.0	405.4	410.8	418.0	427.0	435.9	443.3	451.3	460.5
165°	406.5	405.6	407.3	411.6	415.1	421.1	428.0	434.0	439.2	445.2	452.0
167.5°	413.5	412.5	413.4	416.6	419.0	422.8	427.8	432.7	435.1	439.0	444.0
170°	417.7	415.9	416.8	419.4	421.1	422.8	427.1	430.6	432.3	434.9	439.2
172.5°	420.4	419.4	419.6	421.5	422.5	423.5	427.1	429.9	430.2	431.4	434.4
175°	423.7	422.8	422.0	423.7	423.7	424.6	426.3	428.0	427.1	427.1	428.9
177.5°	425.2	424.6	423.9	424.6	424.6	424.6	425.2	426.6	425.2	424.6	425.2
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332035-935

CATALOG NUMBER: S123DIP-S1000D1025U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1357.6	1359.8	1361.8	1362.8	1362.5	1362.4	1362.1	1361.9
5°	1350.5	1353.1	1355.7	1356.8	1356.2	1355.7	1355.2	1354.7
7.5°	1336.2	1338.5	1340.8	1341.9	1341.5	1341.3	1340.9	1340.6
10°	1323.0	1325.3	1327.7	1328.6	1328.1	1327.6	1327.1	1326.5
12.5°	1308.6	1310.4	1312.1	1312.8	1312.5	1312.2	1311.8	1311.6
15°	1282.6	1284.7	1286.9	1287.1	1285.6	1283.9	1282.4	1280.8
17.5°	1249.7	1251.2	1252.7	1253.1	1252.6	1252.0	1251.4	1250.9
20°	1225.5	1226.6	1227.6	1227.7	1226.9	1226.2	1225.4	1224.6
22.5°	1199.8	1200.6	1201.4	1201.4	1200.4	1199.4	1198.4	1197.4
25°	1157.1	1157.4	1157.7	1157.4	1156.6	1155.8	1155.0	1154.3
27.5°	1111.8	1112.0	1112.2	1111.8	1110.9	1109.8	1108.9	1107.8
30°	1080.5	1080.5	1080.5	1079.5	1077.7	1075.9	1074.1	1072.2
32.5°	1047.5	1046.1	1044.7	1043.4	1042.4	1041.4	1040.4	1039.4
35°	994.1	992.6	991.0	989.5	988.3	987.0	985.7	984.4
37.5°	938.9	937.0	935.1	933.8	933.0	932.1	931.3	930.5
40°	902.8	900.8	898.7	897.1	896.0	895.0	894.0	892.9
42.5°	865.3	863.2	861.2	859.6	858.6	857.6	856.5	855.5
45°	809.3	806.2	803.1	800.9	799.6	798.3	797.0	795.7
47.5°	750.4	747.3	744.2	742.2	741.0	739.9	738.7	737.5
50°	711.4	708.6	705.7	703.5	702.0	700.3	698.8	697.2
52.5°	671.9	669.5	667.1	665.0	663.5	661.9	660.4	658.8
55°	611.8	609.0	606.1	604.0	602.7	601.4	600.1	598.8
57.5°	552.7	550.2	547.6	545.5	544.1	542.5	541.1	539.5
60°	510.9	508.6	506.3	504.5	503.1	501.8	500.5	499.2
62.5°	470.6	468.3	465.9	464.3	463.4	462.5	461.7	460.8
65°	410.7	408.5	406.5	405.1	404.3	403.6	402.7	401.9
67.5°	351.2	349.4	347.6	346.1	345.0	343.9	342.8	341.7
70°	312.7	310.9	309.1	307.5	306.3	305.0	303.7	302.3
72.5°	273.8	272.2	270.5	269.4	268.7	268.0	267.4	266.7
75°	217.7	216.4	215.1	214.0	213.3	212.5	211.7	210.9
77.5°	165.3	164.5	163.6	163.2	163.2	163.2	163.2	163.2
80°	131.9	131.6	131.4	131.2	131.2	131.2	131.2	131.2
82.5°	101.5	101.0	100.6	100.2	100.0	99.8	99.6	99.4
85°	57.5	57.0	56.5	56.2	56.2	56.2	56.2	56.2
87.5°	24.5	24.5	24.5	24.7	24.5	24.7	24.9	24.7
90°	21.5	22.4	23.2	24.9	24.0	24.9	25.7	24.9
92.5°	72.3	57.4	50.7	46.2	44.7	42.1	43.0	41.4
95°	309.4	209.7	164.2	133.2	116.9	109.2	103.1	99.7
97.5°	771.3	617.8	506.9	404.1	340.7	302.0	278.8	271.4
100°	1013.3	943.7	843.1	721.1	634.3	571.5	538.0	538.9
102.5°	1093.7	1091.5	1032.9	955.5	887.9	838.3	810.3	790.5
105°	1117.2	1203.2	1219.5	1197.2	1157.6	1125.0	1097.5	1093.2
107.5°	1049.6	1189.1	1264.4	1295.0	1295.7	1284.7	1275.4	1267.5
110°	984.9	1143.1	1251.3	1311.5	1335.6	1342.5	1340.7	1339.0





TEST NUMBER: P332035-935

CATALOG NUMBER: S123DIP-S1000D1025U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	920.9	1082.5	1203.9	1281.3	1325.3	1346.5	1353.1	1353.4
115°	836.2	985.8	1112.1	1205.7	1270.2	1308.0	1325.3	1329.6
117.5°	774.9	904.0	1017.4	1112.4	1179.7	1223.0	1247.8	1253.5
120°	742.5	858.6	961.7	1048.5	1116.4	1164.5	1185.2	1190.3
122.5°	717.1	822.2	917.7	998.3	1058.7	1102.0	1124.6	1131.2
125°	683.3	777.0	859.5	928.2	983.2	1021.0	1042.5	1048.5
127.5°	653.7	737.2	811.7	874.2	923.2	955.5	974.9	980.4
130°	635.2	712.5	782.0	840.5	886.1	917.1	935.0	941.9
132.5°	617.9	689.1	753.9	809.6	852.4	883.3	899.3	904.1
135°	594.7	655.7	711.6	760.6	802.7	828.5	844.0	850.0
137.5°	573.6	623.6	671.8	714.2	749.6	775.8	788.8	792.7
140°	561.2	605.0	646.3	683.3	715.9	739.9	753.7	752.9
142.5°	549.5	587.2	622.9	655.0	682.9	704.2	716.6	715.7
145°	535.5	563.8	591.2	616.2	637.7	655.7	662.6	664.3
147.5°	523.9	546.4	568.6	586.3	602.6	614.8	621.4	622.1
150°	515.7	535.5	553.5	569.8	582.7	592.1	597.3	597.3
152.5°	508.1	525.1	541.1	554.7	564.8	573.6	576.7	576.7
155°	496.7	510.5	523.4	533.7	541.5	548.3	550.0	550.9
157.5°	484.7	496.2	506.2	514.3	521.0	526.2	527.5	527.4
160°	477.9	487.3	495.8	501.9	507.9	513.1	513.1	512.2
162.5°	469.6	477.7	485.6	490.9	494.9	499.3	499.3	498.4
165°	458.9	464.1	470.1	474.4	477.9	481.3	480.4	480.4
167.5°	449.6	453.6	457.0	460.1	461.7	464.1	463.2	463.2
170°	443.5	446.1	449.4	451.2	452.0	453.7	452.9	452.9
172.5°	438.0	439.9	442.6	443.7	443.8	445.6	444.0	443.3
175°	430.6	431.4	433.2	433.2	433.2	434.0	433.2	432.3
177.5°	425.9	426.6	427.3	427.3	426.6	427.3	425.9	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6

(END OF REPORT)