

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832340

Luminaire Tested: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832340
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U840-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7705.8 lumens
Efficiency: N/A
Efficacy: 135.4 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832340
CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P832340

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44	38				
2	89	82	76	72	81	75	71	66	63	59	56	51	49	47	41	39	38	33				
3	82	73	66	61	75	67	61	56	56	52	48	46	43	41	37	35	33	29				
4	75	65	58	52	69	60	54	49	50	46	42	42	38	36	33	31	29	26				
5	69	58	51	45	63	54	47	42	46	41	37	38	34	31	31	28	26	23				
6	64	53	45	40	59	49	42	37	41	36	33	35	31	28	28	26	23	21				
7	59	48	40	35	54	44	38	33	38	33	29	32	28	25	26	23	21	19				
8	55	44	36	31	51	41	34	30	35	30	26	29	26	23	24	21	19	17				
9	52	40	33	28	48	37	31	27	32	27	24	27	23	21	23	20	18	16				
10	48	37	30	26	45	35	28	24	30	25	22	25	22	19	21	18	16	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	27137	27137	27137	27137	27137
5°	32222	31194	27308	22075	20495
10°	29194	31685	27172	17687	15173
15°	20100	27167	26885	14456	12003
20°	13984	20916	26345	12190	10550
25°	10656	15941	25560	10834	9723
30°	9276	12745	24577	10060	9006
35°	8516	10750	23186	9406	8353
40°	7770	9601	21365	8765	7756
45°	7018	8780	19401	8159	7159
50°	6370	8102	17084	7564	6422
55°	5761	7439	14859	6983	5510
60°	5162	6764	12906	6342	5208
65°	4765	6003	11110	5700	4923
70°	3871	5190	9693	5155	4000
75°	3398	4126	8210	4275	3527
80°	3075	3490	6726	3589	3335
85°	2803	3063	5101	3260	3063

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 20471 cd/sqm



TEST NUMBER: P832340

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.8	3.0
10°-20°	531.7	6.9
20°-30°	610.1	7.9
30°-40°	601.4	7.8
40°-50°	530.3	6.9
50°-60°	408.0	5.3
60°-70°	268.2	3.5
70°-80°	130.3	1.7
80°-90°	36.0	0.5
90°-100°	314.5	4.1
100°-110°	920.8	11.9
110°-120°	899.2	11.7
120°-130°	716.1	9.3
130°-140°	565.0	7.3
140°-150°	421.5	5.5
150°-160°	293.9	3.8
160°-170°	172.6	2.2
170°-180°	56.2	0.7
0°-30°	1371.6	17.8
0°-40°	1973.0	25.6
0°-60°	2911.3	37.8
0°-90°	3345.8	43.4
90°-120°	2134.6	27.7
90°-150°	3837.3	49.8
90°-180°	4360.0	56.6
0°-180°	7705.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2521	2521	2521	2521	2521	
5°	2982	2887	2527	2043	1897	272
15°	1804	2438	2413	1297	1077	509
25°	897	1342	2152	912	819	424
35°	648	818	1764	716	636	404
45°	461	577	1274	536	470	358
55°	307	396	792	372	294	275
65°	187	236	436	224	193	183
75°	82	99	197	103	85	88
85°	23	25	41	26	25	24
90°	34	29	2	29	34	19
95°	136	696	40	696	136	221
105°	1492	943	136	943	1492	1489
115°	1815	722	240	722	1815	1770
125°	1431	674	334	674	1431	1295
135°	1160	664	392	664	1160	900
145°	907	656	447	656	907	576
155°	752	635	508	635	752	350
165°	656	608	555	608	656	187
175°	590	583	578	583	590	57
180°	580	580	580	580	580	



TEST NUMBER: P832340

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1
2.5°	2794.0	2785.2	2776.4	2773.8	2771.2	2763.0	2754.7	2736.1	2717.5	2698.4	2679.3
5°	2982.1	2983.1	2984.2	2981.6	2979.0	2968.2	2957.3	2934.6	2911.8	2887.0	2862.2
7.5°	2924.2	2940.8	2957.3	2960.4	2963.5	2971.8	2980.0	2974.9	2969.7	2960.4	2951.1
10°	2671.0	2669.9	2668.9	2687.5	2706.1	2761.4	2816.7	2845.2	2873.6	2898.9	2924.2
12.5°	2257.5	2259.1	2260.6	2321.6	2382.6	2434.8	2487.0	2559.3	2631.7	2709.7	2787.8
15°	1803.7	1829.1	1854.4	1908.7	1962.9	2041.5	2120.0	2217.2	2314.4	2437.9	2561.4
17.5°	1481.2	1492.1	1502.9	1555.1	1607.3	1681.8	1756.2	1866.3	1976.4	2135.5	2294.7
20°	1220.8	1230.6	1240.4	1278.1	1315.9	1387.2	1458.5	1563.4	1668.3	1826.0	1983.6
22.5°	1019.2	1038.3	1057.4	1082.8	1108.1	1159.8	1211.5	1318.4	1425.4	1569.1	1712.8
25°	897.2	906.0	914.8	936.5	958.2	1007.8	1057.4	1128.2	1199.0	1342.2	1485.4
27.5°	814.5	817.1	819.7	835.7	851.7	883.8	915.8	981.5	1047.1	1164.9	1282.8
30°	746.3	751.0	755.6	768.0	780.4	803.7	826.9	873.4	920.0	1025.4	1130.8
32.5°	693.6	696.2	698.8	709.1	719.4	736.5	753.5	790.2	826.9	907.6	988.2
35°	648.1	648.6	649.1	656.9	664.6	681.2	697.7	728.2	758.7	818.1	877.6
37.5°	596.4	600.0	603.7	609.3	615.0	629.5	644.0	668.8	693.6	742.7	791.8
40°	553.0	556.1	559.2	565.9	572.6	584.0	595.4	618.1	640.9	683.3	725.6
42.5°	509.6	511.7	513.7	520.4	527.2	541.1	555.1	573.2	591.3	626.4	661.5
45°	461.0	466.2	471.3	478.6	485.8	497.7	509.6	528.2	546.8	576.8	606.8
47.5°	420.7	423.3	425.9	432.1	438.3	452.7	467.2	483.8	500.3	528.2	556.1
50°	380.4	381.4	382.5	388.1	393.8	406.7	419.7	438.8	457.9	483.8	509.6
52.5°	342.1	344.7	347.3	353.0	358.7	367.5	376.3	395.9	415.5	440.9	466.2
55°	307.0	308.5	310.1	314.2	318.4	328.7	339.0	356.1	373.2	396.4	419.7
57.5°	273.9	276.0	278.1	281.2	284.3	293.6	302.9	317.9	332.8	356.1	379.4
60°	239.8	242.4	245.0	248.6	252.2	259.4	266.7	280.1	293.6	314.2	334.9
62.5°	215.0	215.5	216.0	219.1	222.2	227.4	232.6	243.4	254.3	275.0	295.6
65°	187.1	188.6	190.2	191.7	193.3	197.4	201.6	210.9	220.2	235.7	251.2
67.5°	158.2	159.7	161.3	163.8	166.4	170.0	173.7	179.9	186.1	200.5	215.0
70°	123.0	123.0	123.0	127.1	131.3	137.5	143.7	148.3	153.0	164.9	176.8
72.5°	100.3	100.8	101.3	101.8	102.3	106.0	109.6	117.3	125.1	132.3	139.5
75°	81.7	82.2	82.7	83.2	83.7	84.8	85.8	88.4	91.0	99.2	107.5
77.5°	65.1	65.6	66.2	66.7	67.2	68.2	69.3	70.3	71.3	74.4	77.5
80°	49.6	50.1	50.6	51.2	51.7	52.2	52.7	53.8	54.8	56.3	57.9
82.5°	36.2	36.2	36.2	36.2	36.2	37.2	38.2	38.2	38.2	39.3	40.3
85°	22.7	22.7	22.7	23.3	23.8	23.8	23.8	24.3	24.8	24.8	24.8
87.5°	10.3	9.8	9.3	9.8	10.3	10.3	10.3	10.9	11.4	11.4	11.4
90°	34.0	35.2	34.0	32.9	34.0	31.7	30.5	29.3	28.2	29.3	25.8
92.5°	62.2	64.5	63.4	68.1	70.4	78.6	90.3	116.2	163.1	218.2	241.7
95°	136.1	140.8	149.0	159.6	181.9	224.1	286.3	422.4	564.4	695.8	619.5
97.5°	279.2	292.2	320.3	364.9	443.5	577.3	732.1	970.3	1106.4	1070.1	799.0
100°	735.7	734.5	780.3	865.9	984.4	1151.0	1288.3	1383.3	1342.3	1111.1	750.9
102.5°	1165.1	1199.1	1235.5	1298.9	1384.5	1474.9	1540.6	1520.6	1354.0	1034.9	680.5
105°	1492.5	1498.3	1535.9	1580.4	1634.4	1664.9	1642.6	1525.3	1280.1	943.3	625.4
107.5°	1706.0	1718.9	1734.2	1755.3	1762.3	1730.6	1639.1	1454.9	1174.5	862.4	585.5
110°	1828.0	1830.4	1832.7	1823.3	1790.5	1708.3	1560.5	1344.6	1075.9	795.5	564.4



TEST NUMBER: P832340

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1852.7	1851.5	1839.7	1805.7	1738.8	1627.4	1457.3	1235.5	990.3	750.9	552.6
115°	1815.1	1809.2	1785.8	1734.2	1646.2	1518.3	1345.8	1141.6	924.6	721.6	551.5
117.5°	1733.0	1724.8	1689.6	1632.1	1540.6	1408.0	1249.6	1068.9	881.2	701.6	552.6
120°	1625.0	1618.0	1589.8	1524.1	1431.4	1312.9	1172.1	1013.7	848.3	688.7	557.3
122.5°	1524.1	1514.7	1483.1	1425.6	1345.8	1237.8	1110.0	970.3	821.3	680.5	565.5
125°	1431.4	1423.2	1393.9	1342.3	1267.2	1173.3	1060.7	932.8	799.0	673.5	573.7
127.5°	1351.7	1344.6	1317.6	1273.0	1205.0	1118.2	1014.9	898.8	777.9	670.0	583.1
130°	1285.9	1276.6	1251.9	1209.7	1147.5	1067.7	972.7	867.1	761.5	666.4	592.5
132.5°	1221.4	1215.5	1194.4	1152.2	1094.7	1019.6	932.8	837.7	746.2	665.3	599.6
135°	1160.4	1152.2	1131.1	1095.9	1038.4	971.5	895.2	811.9	733.3	664.1	606.6
137.5°	1095.9	1088.8	1071.2	1034.9	985.6	925.7	857.7	787.3	721.6	661.7	611.3
140°	1027.8	1029.0	1010.2	977.4	932.8	882.3	826.0	766.2	711.0	660.6	616.0
142.5°	964.5	965.6	949.2	921.0	884.7	842.4	795.5	746.2	701.6	658.2	619.5
145°	907.0	904.6	895.2	870.6	841.3	807.2	769.7	731.0	693.4	655.9	620.7
147.5°	857.7	856.5	847.1	829.5	806.1	781.4	749.7	718.1	685.2	652.4	620.7
150°	815.5	815.5	808.4	795.5	777.9	755.6	731.0	704.0	677.0	647.7	620.7
152.5°	780.3	780.3	776.7	765.0	752.1	734.5	713.4	691.1	667.6	641.8	617.2
155°	752.1	750.9	748.6	739.2	728.6	714.5	696.9	678.2	658.2	634.8	614.8
157.5°	725.1	725.1	722.8	715.7	706.3	694.6	680.5	664.1	647.7	628.9	611.3
160°	699.3	700.5	700.5	693.4	685.2	677.0	665.3	652.4	637.1	621.9	608.9
162.5°	675.8	677.0	677.0	671.1	666.4	659.4	648.8	638.3	626.5	614.8	604.3
165°	655.9	655.9	657.1	652.4	647.7	641.8	633.6	626.5	617.2	607.8	599.6
167.5°	635.9	635.9	637.1	633.6	631.2	626.5	621.9	616.0	607.8	600.7	594.9
170°	618.3	618.3	619.5	617.2	616.0	613.6	608.9	605.4	599.6	593.7	590.2
172.5°	601.9	603.1	605.4	603.1	603.1	601.9	598.4	596.0	591.3	587.8	586.7
175°	590.2	591.3	592.5	591.3	591.3	591.3	589.0	587.8	585.5	583.1	583.1
177.5°	582.0	582.0	584.3	583.1	584.3	584.3	583.1	582.0	580.8	579.6	580.8
180°	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6



TEST NUMBER: P832340

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1
2.5°	2676.7	2674.1	2649.3	2624.5	2600.2	2575.9	2557.8	2539.7	2509.2	2478.7	2459.6
5°	2842.6	2822.9	2783.7	2744.4	2685.5	2626.5	2576.9	2527.3	2464.3	2401.2	2348.5
7.5°	2935.1	2919.1	2871.5	2824.0	2745.9	2667.9	2590.4	2512.8	2419.8	2326.8	2247.2
10°	2937.7	2951.1	2911.8	2872.5	2784.7	2696.8	2591.4	2486.0	2360.9	2235.8	2133.0
12.5°	2845.7	2903.6	2895.3	2887.0	2797.6	2708.2	2580.0	2451.8	2298.3	2144.8	2016.2
15°	2673.6	2785.7	2818.8	2851.9	2778.0	2704.1	2558.3	2412.6	2232.2	2051.8	1904.0
17.5°	2451.8	2609.0	2696.3	2783.7	2729.9	2676.2	2516.4	2356.7	2153.6	1950.5	1789.8
20°	2189.3	2395.0	2532.0	2668.9	2649.3	2629.6	2464.8	2299.9	2080.8	1861.6	1687.5
22.5°	1929.8	2146.9	2336.1	2525.2	2545.4	2565.5	2399.1	2232.7	1992.9	1753.1	1575.8
25°	1706.1	1926.7	2152.1	2377.4	2422.9	2468.4	2310.2	2152.1	1903.5	1654.9	1478.7
27.5°	1492.6	1702.4	1950.5	2198.6	2281.3	2364.0	2219.3	2074.6	1815.6	1556.7	1381.0
30°	1318.4	1506.0	1759.3	2012.5	2127.8	2243.0	2110.2	1977.4	1720.5	1463.7	1291.6
32.5°	1156.2	1324.1	1578.4	1832.7	1966.5	2100.4	1985.7	1870.9	1623.9	1376.8	1206.8
35°	1028.0	1178.4	1415.6	1652.8	1802.7	1952.6	1858.5	1764.5	1523.1	1281.7	1121.0
37.5°	917.9	1044.0	1266.8	1489.5	1648.7	1807.9	1729.3	1650.8	1423.9	1197.0	1045.0
40°	826.9	928.2	1135.5	1342.7	1498.8	1654.9	1587.7	1520.5	1317.4	1114.3	972.2
42.5°	748.9	836.2	1022.3	1208.4	1351.5	1494.7	1450.2	1405.8	1221.8	1037.8	906.0
45°	680.1	753.5	917.4	1081.2	1213.0	1344.8	1309.6	1274.5	1115.8	957.2	836.2
47.5°	619.2	682.2	828.5	974.7	1093.1	1211.5	1178.9	1146.3	1015.1	883.8	773.7
50°	563.3	617.1	739.1	861.0	967.5	1074.0	1047.1	1020.2	911.7	803.2	708.1
52.5°	510.6	555.1	664.6	774.2	860.0	945.8	925.1	904.5	820.7	737.0	650.7
55°	460.5	501.3	593.8	686.4	759.7	833.1	812.5	791.8	726.7	661.5	585.6
57.5°	415.0	450.7	525.6	600.6	659.0	717.4	707.5	697.7	643.5	589.2	526.7
60°	366.9	399.0	463.6	528.2	575.2	622.3	610.9	599.5	560.8	522.0	468.2
62.5°	324.1	352.5	404.2	455.8	494.1	532.3	524.1	515.8	486.3	456.9	412.4
65°	279.1	307.0	348.9	390.7	420.7	450.7	443.4	436.2	414.0	391.8	356.1
67.5°	238.3	261.5	297.7	333.9	354.0	374.2	370.1	365.9	348.9	331.8	303.9
70°	196.9	217.1	247.0	277.0	291.0	304.9	306.5	308.0	292.5	277.0	256.3
72.5°	155.6	171.6	199.5	227.4	238.3	249.1	248.6	248.1	238.8	229.5	210.9
75°	119.4	131.3	153.0	174.7	184.0	193.3	195.4	197.4	188.6	179.9	169.5
77.5°	85.8	94.1	110.6	127.1	137.5	147.8	148.8	149.9	145.7	141.6	131.8
80°	60.5	63.1	73.4	83.7	94.6	105.4	107.0	108.5	104.4	100.3	94.1
82.5°	41.9	43.4	47.0	50.6	59.4	68.2	70.3	72.4	70.3	68.2	61.5
85°	25.3	25.8	27.4	28.9	33.1	37.2	39.3	41.3	40.3	39.3	35.7
87.5°	11.4	11.4	11.9	12.4	13.4	14.5	17.1	19.6	18.1	16.5	15.0
90°	22.3	18.8	15.3	12.9	10.6	7.0	4.7	2.3	4.7	7.0	10.6
92.5°	180.7	118.5	81.0	59.8	48.1	37.5	25.8	17.6	25.8	37.5	48.1
95°	427.1	252.3	152.5	106.8	76.3	56.3	43.4	39.9	43.4	56.3	76.3
97.5°	475.2	272.2	173.6	123.2	92.7	75.1	64.5	63.4	64.5	75.1	92.7
100°	442.3	268.7	186.6	140.8	112.6	96.2	88.0	86.8	88.0	96.2	112.6
102.5°	414.2	273.4	201.8	160.7	136.1	120.9	113.8	111.5	113.8	120.9	136.1
105°	403.6	282.8	219.4	183.0	160.7	146.7	139.6	136.1	139.6	146.7	160.7
107.5°	401.3	298.0	241.7	207.7	186.6	172.5	165.4	161.9	165.4	172.5	186.6
110°	407.1	318.0	265.2	232.3	212.4	199.5	193.6	190.1	193.6	199.5	212.4



TEST NUMBER: P832340

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	418.9	337.9	289.8	258.1	238.2	225.3	219.4	215.9	219.4	225.3	238.2
115°	431.8	360.2	315.6	283.9	264.0	252.3	245.2	240.5	245.2	252.3	264.0
117.5°	448.2	383.7	339.1	309.8	287.5	276.9	271.0	265.2	271.0	276.9	287.5
120°	467.0	406.0	363.7	334.4	312.1	300.4	294.5	291.0	294.5	300.4	312.1
122.5°	484.6	429.4	388.4	356.7	335.6	322.7	316.8	313.3	316.8	322.7	335.6
125°	503.3	451.7	410.7	379.0	356.7	343.8	336.7	334.4	336.7	343.8	356.7
127.5°	518.6	471.7	431.8	400.1	375.5	362.6	354.3	350.8	354.3	362.6	375.5
130°	533.9	489.3	450.6	418.9	394.2	380.2	369.6	366.1	369.6	380.2	394.2
132.5°	547.9	504.5	467.0	436.5	411.8	394.2	382.5	377.8	382.5	394.2	411.8
135°	559.7	519.8	483.4	451.7	427.1	409.5	396.6	391.9	396.6	409.5	427.1
137.5°	569.1	530.3	495.1	465.8	441.2	422.4	409.5	404.8	409.5	422.4	441.2
140°	576.1	540.9	506.9	477.5	454.1	435.3	423.6	417.7	423.6	435.3	454.1
142.5°	583.1	549.1	516.3	489.3	465.8	449.4	436.5	431.8	436.5	449.4	465.8
145°	587.8	556.1	525.6	498.7	478.7	461.1	450.6	447.0	450.6	461.1	478.7
147.5°	591.3	562.0	533.9	510.4	490.4	475.2	464.6	462.3	464.6	475.2	490.4
150°	592.5	567.9	540.9	519.8	503.3	488.1	478.7	477.5	478.7	488.1	503.3
152.5°	594.9	571.4	549.1	529.2	515.1	502.2	492.8	492.8	492.8	502.2	515.1
155°	594.9	576.1	556.1	539.7	526.8	515.1	508.0	508.0	508.0	515.1	526.8
157.5°	596.0	578.4	562.0	549.1	537.4	526.8	520.9	519.8	520.9	526.8	537.4
160°	596.0	582.0	567.9	556.1	547.9	538.5	533.9	533.9	533.9	538.5	547.9
162.5°	594.9	583.1	571.4	562.0	555.0	547.9	544.4	544.4	544.4	547.9	555.0
165°	592.5	584.3	574.9	566.7	562.0	556.1	553.8	555.0	553.8	556.1	562.0
167.5°	591.3	584.3	577.3	571.4	567.9	563.2	562.0	563.2	562.0	563.2	567.9
170°	587.8	583.1	577.3	574.9	572.6	569.1	567.9	570.2	567.9	569.1	572.6
172.5°	586.7	583.1	578.4	577.3	576.1	573.7	573.7	574.9	573.7	573.7	576.1
175°	584.3	582.0	579.6	578.4	578.4	576.1	577.3	578.4	577.3	576.1	578.4
177.5°	583.1	580.8	579.6	579.6	579.6	578.4	579.6	580.8	579.6	578.4	579.6
180°	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6



TEST NUMBER: P832340

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1
2.5°	2440.5	2411.0	2381.6	2360.4	2339.2	2312.8	2286.5	2285.4	2284.4	2264.8	2245.1
5°	2295.8	2244.6	2193.4	2143.3	2093.2	2043.0	1992.9	1981.5	1970.2	1953.1	1936.0
7.5°	2167.6	2085.9	2004.3	1940.2	1876.1	1826.0	1775.8	1741.7	1707.6	1681.3	1654.9
10°	2030.1	1928.8	1827.5	1750.0	1672.5	1618.2	1563.9	1524.7	1485.4	1466.8	1448.2
12.5°	1887.5	1777.4	1667.3	1591.3	1515.3	1450.2	1385.1	1349.4	1313.8	1287.9	1262.1
15°	1756.2	1637.8	1519.5	1438.9	1358.2	1297.2	1236.3	1200.6	1164.9	1139.1	1113.3
17.5°	1629.1	1509.7	1390.3	1308.6	1227.0	1171.7	1116.4	1081.7	1047.1	1031.1	1015.1
20°	1513.3	1392.9	1272.4	1195.4	1118.4	1064.2	1009.9	991.3	972.7	957.7	942.7
22.5°	1398.5	1282.8	1167.0	1093.1	1019.2	979.9	940.6	925.6	910.7	899.3	887.9
25°	1302.4	1187.2	1071.9	1007.3	942.7	912.2	881.7	871.9	862.1	850.7	839.3
27.5°	1205.2	1095.7	986.1	934.4	882.7	857.9	833.1	820.7	808.3	799.0	789.7
30°	1119.5	1018.2	916.9	874.0	831.1	809.4	787.7	774.2	760.8	752.0	743.2
32.5°	1036.8	946.8	856.9	820.2	783.5	762.3	741.1	728.2	715.3	705.0	694.6
35°	960.3	882.2	804.2	770.6	737.0	715.8	694.6	681.7	668.8	658.4	648.1
37.5°	893.1	822.3	751.5	719.9	688.4	669.8	651.2	637.8	624.3	613.5	602.6
40°	830.0	767.5	705.0	674.5	644.0	623.8	603.7	591.8	579.9	570.1	560.2
42.5°	774.2	716.8	659.5	629.5	599.5	580.4	561.3	547.3	533.4	527.7	522.0
45°	715.3	664.6	614.0	585.1	556.1	536.0	515.8	503.9	492.0	486.9	481.7
47.5°	663.6	616.6	569.5	541.1	512.7	494.6	476.5	467.2	457.9	450.7	443.4
50°	613.0	567.5	522.0	494.6	467.2	451.7	436.2	424.8	413.5	408.3	403.1
52.5°	564.4	523.0	481.7	453.8	425.9	410.9	395.9	386.1	376.3	365.4	354.5
55°	509.6	473.4	437.2	412.4	387.6	372.1	356.6	345.2	333.9	322.5	311.1
57.5°	464.1	428.5	392.8	370.6	348.3	333.4	318.4	306.0	293.6	284.3	275.0
60°	414.5	383.5	352.5	330.8	309.1	294.6	280.1	268.2	256.3	251.7	247.0
62.5°	368.0	339.0	310.1	291.0	271.9	257.9	243.9	236.2	228.4	225.3	222.2
65°	320.4	295.6	270.8	253.2	235.7	223.8	211.9	208.3	204.7	202.1	199.5
67.5°	276.0	254.8	233.6	218.1	202.6	194.3	186.1	181.9	177.8	174.7	171.6
70°	235.7	217.1	198.5	185.0	171.6	163.8	156.1	152.5	148.8	143.2	137.5
72.5°	192.3	177.8	163.3	153.0	142.6	135.9	129.2	122.0	114.7	109.6	104.4
75°	159.2	144.7	130.2	120.4	110.6	102.8	95.1	92.5	89.9	88.4	86.8
77.5°	122.0	109.6	97.2	89.4	81.7	78.0	74.4	72.9	71.3	70.8	70.3
80°	87.9	77.5	67.2	63.1	58.9	57.9	56.9	55.8	54.8	54.3	53.8
82.5°	54.8	49.6	44.4	43.4	42.4	41.9	41.3	40.8	40.3	39.8	39.3
85°	32.0	30.0	27.9	27.4	26.9	26.4	25.8	25.8	25.8	25.8	25.8
87.5°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	12.9	12.4
90°	12.9	15.3	18.8	22.3	25.8	29.3	28.2	29.3	30.5	31.7	34.0
92.5°	59.8	81.0	118.5	180.7	241.7	218.2	163.1	116.2	90.3	78.6	70.4
95°	106.8	152.5	252.3	427.1	619.5	695.8	564.4	422.4	286.3	224.1	181.9
97.5°	123.2	173.6	272.2	475.2	799.0	1070.1	1106.4	970.3	732.1	577.3	443.5
100°	140.8	186.6	268.7	442.3	750.9	1111.1	1342.3	1383.3	1288.3	1151.0	984.4
102.5°	160.7	201.8	273.4	414.2	680.5	1034.9	1354.0	1520.6	1540.6	1474.9	1384.5
105°	183.0	219.4	282.8	403.6	625.4	943.3	1280.1	1525.3	1642.6	1664.9	1634.4
107.5°	207.7	241.7	298.0	401.3	585.5	862.4	1174.5	1454.9	1639.1	1730.6	1762.3
110°	232.3	265.2	318.0	407.1	564.4	795.5	1075.9	1344.6	1560.5	1708.3	1790.5



TEST NUMBER: P832340

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	258.1	289.8	337.9	418.9	552.6	750.9	990.3	1235.5	1457.3	1627.4	1738.8
115°	283.9	315.6	360.2	431.8	551.5	721.6	924.6	1141.6	1345.8	1518.3	1646.2
117.5°	309.8	339.1	383.7	448.2	552.6	701.6	881.2	1068.9	1249.6	1408.0	1540.6
120°	334.4	363.7	406.0	467.0	557.3	688.7	848.3	1013.7	1172.1	1312.9	1431.4
122.5°	356.7	388.4	429.4	484.6	565.5	680.5	821.3	970.3	1110.0	1237.8	1345.8
125°	379.0	410.7	451.7	503.3	573.7	673.5	799.0	932.8	1060.7	1173.3	1267.2
127.5°	400.1	431.8	471.7	518.6	583.1	670.0	777.9	898.8	1014.9	1118.2	1205.0
130°	418.9	450.6	489.3	533.9	592.5	666.4	761.5	867.1	972.7	1067.7	1147.5
132.5°	436.5	467.0	504.5	547.9	599.6	665.3	746.2	837.7	932.8	1019.6	1094.7
135°	451.7	483.4	519.8	559.7	606.6	664.1	733.3	811.9	895.2	971.5	1038.4
137.5°	465.8	495.1	530.3	569.1	611.3	661.7	721.6	787.3	857.7	925.7	985.6
140°	477.5	506.9	540.9	576.1	616.0	660.6	711.0	766.2	826.0	882.3	932.8
142.5°	489.3	516.3	549.1	583.1	619.5	658.2	701.6	746.2	795.5	842.4	884.7
145°	498.7	525.6	556.1	587.8	620.7	655.9	693.4	731.0	769.7	807.2	841.3
147.5°	510.4	533.9	562.0	591.3	620.7	652.4	685.2	718.1	749.7	781.4	806.1
150°	519.8	540.9	567.9	592.5	620.7	647.7	677.0	704.0	731.0	755.6	777.9
152.5°	529.2	549.1	571.4	594.9	617.2	641.8	667.6	691.1	713.4	734.5	752.1
155°	539.7	556.1	576.1	594.9	614.8	634.8	658.2	678.2	696.9	714.5	728.6
157.5°	549.1	562.0	578.4	596.0	611.3	628.9	647.7	664.1	680.5	694.6	706.3
160°	556.1	567.9	582.0	596.0	608.9	621.9	637.1	652.4	665.3	677.0	685.2
162.5°	562.0	571.4	583.1	594.9	604.3	614.8	626.5	638.3	648.8	659.4	666.4
165°	566.7	574.9	584.3	592.5	599.6	607.8	617.2	626.5	633.6	641.8	647.7
167.5°	571.4	577.3	584.3	591.3	594.9	600.7	607.8	616.0	621.9	626.5	631.2
170°	574.9	577.3	583.1	587.8	590.2	593.7	599.6	605.4	608.9	613.6	616.0
172.5°	577.3	578.4	583.1	586.7	586.7	587.8	591.3	596.0	598.4	601.9	603.1
175°	578.4	579.6	582.0	584.3	583.1	583.1	585.5	587.8	589.0	591.3	591.3
177.5°	579.6	579.6	580.8	583.1	580.8	579.6	580.8	582.0	583.1	584.3	584.3
180°	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6

TEST NUMBER: P832340

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2521.1	2521.1	2521.1	2521.1
2.5°	2239.9	2234.8	2232.7	2230.6
5°	1920.0	1904.0	1900.4	1896.8
7.5°	1648.2	1641.5	1619.2	1597.0
10°	1427.5	1406.8	1397.5	1388.2
12.5°	1243.0	1223.9	1220.8	1217.7
15°	1099.8	1086.4	1081.7	1077.1
17.5°	1005.8	996.5	990.8	985.1
20°	936.0	929.3	925.1	921.0
22.5°	882.7	877.6	874.5	871.4
25°	831.6	823.8	821.2	818.7
27.5°	783.0	776.3	773.7	771.1
30°	737.5	731.8	728.2	724.6
32.5°	687.9	681.2	679.1	677.0
35°	644.0	639.8	637.8	635.7
37.5°	597.5	592.3	589.2	586.1
40°	557.7	555.1	553.5	552.0
42.5°	517.3	512.7	512.2	511.7
45°	477.0	472.4	471.3	470.3
47.5°	439.3	435.2	434.7	434.1
50°	397.4	391.8	387.6	383.5
52.5°	349.4	344.2	340.6	337.0
55°	305.4	299.8	296.7	293.6
57.5°	272.4	269.8	268.2	266.7
60°	245.5	243.9	242.9	241.9
62.5°	220.7	219.1	219.1	219.1
65°	197.9	196.4	194.8	193.3
67.5°	168.5	165.4	164.9	164.4
70°	132.8	128.2	127.7	127.1
72.5°	103.9	103.4	102.3	101.3
75°	85.8	84.8	84.8	84.8
77.5°	69.3	68.2	68.2	68.2
80°	53.2	52.7	53.2	53.8
82.5°	39.3	39.3	38.8	38.2
85°	25.3	24.8	24.8	24.8
87.5°	12.4	12.4	12.4	12.4
90°	32.9	34.0	35.2	34.0
92.5°	68.1	63.4	64.5	62.2
95°	159.6	149.0	140.8	136.1
97.5°	364.9	320.3	292.2	279.2
100°	865.9	780.3	734.5	735.7
102.5°	1298.9	1235.5	1199.1	1165.1
105°	1580.4	1535.9	1498.3	1492.5
107.5°	1755.3	1734.2	1718.9	1706.0
110°	1823.3	1832.7	1830.4	1828.0



TEST NUMBER: P832340

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1805.7	1839.7	1851.5	1852.7
115°	1734.2	1785.8	1809.2	1815.1
117.5°	1632.1	1689.6	1724.8	1733.0
120°	1524.1	1589.8	1618.0	1625.0
122.5°	1425.6	1483.1	1514.7	1524.1
125°	1342.3	1393.9	1423.2	1431.4
127.5°	1273.0	1317.6	1344.6	1351.7
130°	1209.7	1251.9	1276.6	1285.9
132.5°	1152.2	1194.4	1215.5	1221.4
135°	1095.9	1131.1	1152.2	1160.4
137.5°	1034.9	1071.2	1088.8	1095.9
140°	977.4	1010.2	1029.0	1027.8
142.5°	921.0	949.2	965.6	964.5
145°	870.6	895.2	904.6	907.0
147.5°	829.5	847.1	856.5	857.7
150°	795.5	808.4	815.5	815.5
152.5°	765.0	776.7	780.3	780.3
155°	739.2	748.6	750.9	752.1
157.5°	715.7	722.8	725.1	725.1
160°	693.4	700.5	700.5	699.3
162.5°	671.1	677.0	677.0	675.8
165°	652.4	657.1	655.9	655.9
167.5°	633.6	637.1	635.9	635.9
170°	617.2	619.5	618.3	618.3
172.5°	603.1	605.4	603.1	601.9
175°	591.3	592.5	591.3	590.2
177.5°	583.1	584.3	582.0	582.0
180°	579.6	579.6	579.6	579.6

TEST NUMBER: P832340

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.56	12.32	12.58	13.35	14.71	16.23	16.99	17.25	18.01	19.38
	3H	12.78	13.46	13.81	14.49	15.88	17.72	18.40	18.75	19.43	20.82
	4H	13.16	13.80	14.20	14.83	16.23	18.21	18.85	19.25	19.88	21.28
	6H	13.43	14.03	14.49	15.06	16.47	18.51	19.11	19.57	20.15	21.55
	8H	13.52	14.08	14.58	15.14	16.54	18.59	19.15	19.65	20.21	21.61
	12H	13.57	14.10	14.63	15.15	16.58	18.62	19.16	19.68	20.20	21.63
4H	2H	12.28	12.92	13.33	13.95	15.35	16.21	16.86	17.26	17.89	19.28
	3H	13.64	14.17	14.70	15.24	16.64	17.86	18.40	18.92	19.46	20.87
	4H	14.09	14.58	15.16	15.64	17.07	18.47	18.96	19.53	20.01	21.44
	6H	14.46	14.88	15.53	15.95	17.38	18.90	19.32	19.98	20.40	21.82
	8H	14.58	14.97	15.65	16.04	17.48	19.03	19.42	20.11	20.49	21.93
	12H	14.65	15.01	15.74	16.09	17.53	19.09	19.44	20.18	20.53	21.97
8H	4H	14.40	14.79	15.48	15.86	17.30	18.43	18.82	19.50	19.89	21.33
	6H	14.86	15.19	15.96	16.30	17.73	18.93	19.25	20.02	20.36	21.80
	8H	15.06	15.34	16.16	16.43	17.89	19.11	19.39	20.21	20.49	21.94
	12H	15.19	15.44	16.30	16.53	18.03	19.22	19.47	20.33	20.56	22.06
12H	4H	14.41	14.76	15.50	15.85	17.29	18.38	18.73	19.47	19.81	21.26
	6H	14.92	15.20	16.03	16.30	17.76	18.90	19.18	20.00	20.28	21.73
	8H	15.14	15.39	16.24	16.48	17.97	19.09	19.34	20.20	20.43	21.92