

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332007-935

Luminaire Tested: **S123DIP-S1000D365U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332007-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D365U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4620.6 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332007-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332007-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	99	95	91	99	95	91	88	86	83	81	78	76	74	71	70	68	64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	63	60	57	54
3	86	76	68	62	82	73	66	60	67	61	56	61	56	52	55	52	49	46
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	50	45	42	39
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	39	48	41	36	44	39	34	41	36	32	30
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	29	25	32	27	23	21
10	50	38	30	25	48	36	29	25	34	28	23	32	26	22	29	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14670	14670	14670
5°	14738	14536	14638
10°	14641	14410	14499
15°	14469	14247	14273
20°	14269	14014	14027
25°	14001	13737	13709
30°	13706	13430	13326
35°	13397	13104	12935
40°	13075	12745	12546
45°	12718	12415	12113
50°	12363	12010	11675
55°	11898	11590	11237
60°	11427	11102	10747
65°	11013	10565	10236
70°	10401	9958	9514
75°	9503	9162	8771
80°	8573	8207	8133
85°	7534	7237	6941



TEST NUMBER: P332007-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	2.8
10°-20°	362.5	7.8
20°-30°	535.5	11.6
30°-40°	625.5	13.5
40°-50°	628.8	13.6
50°-60°	552.4	12.0
60°-70°	411.5	8.9
70°-80°	234.5	5.1
80°-90°	68.4	1.5
90°-100°	25.2	0.5
100°-110°	75.5	1.6
110°-120°	128.5	2.8
120°-130°	169.0	3.7
130°-140°	189.9	4.1
140°-150°	186.7	4.0
150°-160°	157.2	3.4
160°-170°	104.6	2.3
170°-180°	36.6	0.8
0°-30°	1026.3	22.2
0°-40°	1651.8	35.7
0°-60°	2833.0	61.3
0°-90°	3547.4	76.8
90°-120°	229.2	5.0
90°-150°	774.8	16.8
90°-180°	1073.0	23.2
0°-180°	4620.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1363	1363	1363	1363	1363	
5°	1364	1358	1345	1356	1355	129
15°	1298	1293	1278	1287	1281	366
25°	1179	1171	1157	1158	1154	543
35°	1020	1012	997	990	984	638
45°	836	830	816	802	796	645
55°	634	632	618	605	599	568
65°	432	426	415	406	402	427
75°	228	224	220	215	211	244
85°	61	59	59	56	56	67
90°	0	3	7	8	9	4
95°	18	20	23	24	24	20
105°	68	69	72	72	72	73
115°	129	130	130	130	130	128
125°	189	190	190	188	187	169
135°	246	247	247	246	245	189
145°	298	298	299	299	298	186
155°	341	341	341	342	340	157
165°	372	371	371	372	370	105
175°	386	385	385	387	385	37
180°	387	387	387	387	387	



TEST NUMBER: P332007-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1367.5	1366.8	1365.9	1365.0	1364.3	1362.6	1360.4	1358.1	1355.8	1353.5	1355.6
5°	1364.0	1362.7	1361.4	1360.1	1358.8	1356.8	1353.9	1351.0	1348.2	1345.3	1347.9
7.5°	1350.7	1349.4	1348.1	1346.8	1345.5	1343.3	1340.4	1337.4	1334.5	1331.5	1333.8
10°	1339.5	1338.2	1336.8	1335.5	1334.2	1331.9	1328.5	1325.1	1321.7	1318.4	1320.7
12.5°	1324.4	1323.4	1322.2	1321.1	1320.1	1317.9	1314.7	1311.6	1308.4	1305.2	1306.9
15°	1298.4	1297.4	1296.3	1295.3	1294.3	1292.0	1288.7	1285.3	1281.9	1278.5	1280.6
17.5°	1268.2	1266.8	1265.5	1264.1	1262.7	1260.4	1257.0	1253.6	1250.3	1246.8	1248.3
20°	1245.7	1244.1	1242.6	1241.0	1239.4	1236.9	1233.6	1230.2	1226.8	1223.4	1224.4
22.5°	1220.4	1218.8	1217.3	1215.6	1214.1	1211.7	1208.2	1204.9	1201.5	1198.1	1198.9
25°	1178.9	1177.3	1175.8	1174.2	1172.6	1170.2	1166.7	1163.4	1160.0	1156.6	1156.8
27.5°	1134.6	1133.1	1131.5	1130.1	1128.5	1125.9	1122.3	1118.7	1115.0	1111.4	1111.6
30°	1102.7	1101.4	1100.1	1098.8	1097.5	1095.0	1091.4	1087.7	1084.1	1080.5	1080.5
32.5°	1070.8	1069.1	1067.4	1065.7	1063.9	1061.7	1058.9	1056.1	1053.3	1050.4	1049.0
35°	1019.5	1018.0	1016.4	1014.9	1013.2	1010.8	1007.4	1004.0	1000.7	997.2	995.7
37.5°	967.0	965.0	963.0	961.0	959.1	956.4	953.0	949.5	946.1	942.6	940.7
40°	930.5	928.8	927.3	925.7	924.2	921.6	917.9	914.3	910.7	907.0	904.9
42.5°	893.9	892.1	890.4	888.6	886.8	884.1	880.5	876.8	873.1	869.5	867.5
45°	835.5	834.5	833.4	832.4	831.4	829.1	825.8	822.3	819.0	815.6	812.5
47.5°	777.7	776.1	774.6	773.1	771.6	769.2	766.1	762.9	759.7	756.6	753.5
50°	738.3	736.9	735.6	734.3	733.1	730.7	727.3	723.9	720.6	717.2	714.3
52.5°	697.0	696.1	695.3	694.4	693.4	691.2	687.7	684.1	680.4	676.8	674.4
55°	634.0	633.7	633.4	633.2	632.9	631.1	627.8	624.3	621.0	617.6	614.7
57.5°	573.9	573.1	572.2	571.4	570.4	568.6	565.9	563.2	560.5	557.8	555.3
60°	530.8	530.5	530.3	530.0	529.8	528.1	525.0	521.9	518.8	515.7	513.2
62.5°	492.4	491.7	491.0	490.3	489.7	487.8	484.7	481.6	478.5	475.3	472.9
65°	432.4	431.1	429.8	428.5	427.2	425.2	422.7	420.1	417.4	414.8	412.8
67.5°	368.9	367.7	366.6	365.5	364.3	362.7	360.8	358.8	356.8	354.8	353.0
70°	330.5	328.9	327.4	325.8	324.3	322.6	321.1	319.5	318.0	316.4	314.6
72.5°	290.2	289.0	287.8	286.7	285.6	284.1	282.3	280.6	278.8	277.0	275.4
75°	228.5	227.5	226.4	225.4	224.4	223.4	222.7	221.9	221.1	220.3	219.0
77.5°	173.9	173.3	172.7	172.2	171.6	170.8	170.0	169.0	168.1	167.1	166.3
80°	138.3	137.5	136.7	136.0	135.2	134.5	134.0	133.5	132.9	132.4	132.2
82.5°	103.6	103.4	103.3	103.1	103.0	102.8	102.7	102.6	102.5	102.5	101.9
85°	61.0	60.4	59.9	59.4	58.9	58.6	58.6	58.6	58.6	58.6	58.0
87.5°	24.5	23.9	23.4	23.0	22.5	22.2	22.2	22.1	22.1	22.1	22.0
90°	0.3	0.9	1.6	2.3	3.0	3.8	4.6	5.5	6.5	7.3	7.6
92.5°	7.4	7.8	8.3	8.8	9.2	9.6	10.2	10.7	11.2	11.7	11.9
95°	18.0	18.4	18.9	19.4	19.8	20.3	20.9	21.4	22.0	22.6	22.8
97.5°	31.9	32.2	32.6	33.0	33.3	33.7	34.1	34.4	34.9	35.2	35.6
100°	41.4	41.8	42.2	42.6	43.0	43.4	43.7	44.1	44.4	44.7	44.9
102.5°	52.3	52.6	52.8	53.0	53.3	53.6	54.1	54.6	55.0	55.4	55.6
105°	68.4	68.6	68.7	68.9	69.0	69.4	70.0	70.6	71.2	71.8	71.8
107.5°	87.2	87.3	87.4	87.5	87.6	87.6	87.9	88.2	88.4	88.7	88.9
110°	98.9	99.0	99.2	99.3	99.4	99.5	99.7	99.9	100.0	100.1	100.4



TEST NUMBER: P332007-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	111.1	111.2	111.2	111.3	111.4	111.4	111.5	111.5	111.5	111.6	111.8
115°	129.3	129.5	129.8	129.9	130.1	130.2	130.0	129.9	129.8	129.6	129.7
117.5°	147.7	147.8	148.0	148.1	148.3	148.2	148.0	147.8	147.7	147.5	147.5
120°	159.1	159.5	160.0	160.3	160.7	160.7	160.5	160.1	159.8	159.5	159.4
122.5°	171.1	171.3	171.7	171.9	172.3	172.3	172.1	171.9	171.8	171.6	171.4
125°	189.2	189.4	189.7	189.9	190.1	190.1	189.9	189.9	189.7	189.6	189.2
127.5°	206.0	206.5	206.9	207.3	207.8	207.9	207.8	207.6	207.5	207.3	207.0
130°	217.2	217.7	218.3	218.9	219.4	219.6	219.4	219.2	219.0	218.8	218.5
132.5°	228.4	229.0	229.5	230.1	230.6	230.8	230.7	230.5	230.3	230.2	229.9
135°	245.6	246.0	246.3	246.8	247.2	247.4	247.3	247.2	247.1	247.1	246.8
137.5°	261.4	261.7	262.0	262.3	262.7	262.9	263.1	263.3	263.5	263.6	263.4
140°	272.3	272.7	273.0	273.4	273.7	273.9	274.0	274.0	274.1	274.1	274.1
142.5°	282.3	282.7	283.0	283.4	283.6	283.9	284.0	284.1	284.2	284.4	284.3
145°	297.9	298.0	298.2	298.3	298.4	298.6	298.8	299.0	299.2	299.4	299.4
147.5°	311.5	311.8	312.0	312.3	312.5	312.7	312.9	313.1	313.2	313.5	313.5
150°	321.0	321.2	321.2	321.4	321.6	321.7	321.8	321.9	322.1	322.2	322.2
152.5°	328.8	329.0	329.2	329.3	329.6	329.7	329.8	329.8	329.9	330.0	330.1
155°	341.1	341.1	341.1	341.1	341.1	341.1	341.2	341.2	341.3	341.4	341.6
157.5°	351.5	351.5	351.4	351.3	351.2	351.2	351.3	351.3	351.4	351.5	351.7
160°	358.1	358.0	357.8	357.7	357.6	357.5	357.5	357.5	357.5	357.5	357.8
162.5°	363.9	363.8	363.6	363.4	363.2	363.2	363.2	363.3	363.3	363.3	363.7
165°	371.5	371.3	371.1	370.9	370.7	370.6	370.6	370.6	370.6	370.6	371.0
167.5°	377.5	377.3	377.0	376.7	376.4	376.3	376.4	376.4	376.5	376.6	376.9
170°	380.9	380.6	380.4	380.1	379.9	379.7	379.7	379.7	379.7	379.7	380.2
172.5°	383.7	383.3	383.1	382.8	382.5	382.4	382.4	382.4	382.4	382.4	382.8
175°	386.4	386.2	385.9	385.6	385.4	385.2	385.2	385.2	385.2	385.2	385.6
177.5°	387.5	387.4	387.1	386.9	386.7	386.6	386.6	386.6	386.6	386.6	386.9
180°	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4



TEST NUMBER: P332007-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1357.6	1359.8	1361.8	1362.8	1362.5	1362.4	1362.1	1361.9
5°	1350.5	1353.1	1355.7	1356.8	1356.2	1355.7	1355.2	1354.7
7.5°	1336.2	1338.5	1340.8	1341.9	1341.5	1341.3	1340.9	1340.6
10°	1323.0	1325.3	1327.7	1328.6	1328.1	1327.6	1327.1	1326.5
12.5°	1308.6	1310.4	1312.1	1312.8	1312.5	1312.2	1311.8	1311.6
15°	1282.6	1284.7	1286.9	1287.1	1285.6	1283.9	1282.4	1280.8
17.5°	1249.7	1251.2	1252.7	1253.1	1252.6	1252.0	1251.4	1250.9
20°	1225.5	1226.6	1227.6	1227.7	1226.9	1226.2	1225.4	1224.6
22.5°	1199.8	1200.6	1201.4	1201.4	1200.4	1199.4	1198.4	1197.4
25°	1157.1	1157.4	1157.7	1157.4	1156.6	1155.8	1155.0	1154.3
27.5°	1111.8	1112.0	1112.2	1111.8	1110.9	1109.8	1108.9	1107.8
30°	1080.5	1080.5	1080.5	1079.5	1077.7	1075.9	1074.1	1072.2
32.5°	1047.5	1046.1	1044.7	1043.4	1042.4	1041.4	1040.4	1039.4
35°	994.1	992.6	991.0	989.5	988.3	987.0	985.7	984.4
37.5°	938.9	937.0	935.1	933.8	933.0	932.1	931.3	930.5
40°	902.8	900.8	898.7	897.1	896.0	895.0	894.0	892.9
42.5°	865.3	863.2	861.2	859.6	858.6	857.6	856.5	855.5
45°	809.3	806.2	803.1	800.9	799.6	798.3	797.0	795.7
47.5°	750.4	747.3	744.2	742.2	741.0	739.9	738.7	737.5
50°	711.4	708.6	705.7	703.5	702.0	700.3	698.8	697.2
52.5°	671.9	669.5	667.1	665.0	663.5	661.9	660.4	658.8
55°	611.8	609.0	606.1	604.0	602.7	601.4	600.1	598.8
57.5°	552.7	550.2	547.6	545.5	544.1	542.5	541.1	539.5
60°	510.9	508.6	506.3	504.5	503.1	501.8	500.5	499.2
62.5°	470.6	468.3	465.9	464.3	463.4	462.5	461.7	460.8
65°	410.7	408.5	406.5	405.1	404.3	403.6	402.7	401.9
67.5°	351.2	349.4	347.6	346.1	345.0	343.9	342.8	341.7
70°	312.7	310.9	309.1	307.5	306.3	305.0	303.7	302.3
72.5°	273.8	272.2	270.5	269.4	268.7	268.0	267.4	266.7
75°	217.7	216.4	215.1	214.0	213.3	212.5	211.7	210.9
77.5°	165.3	164.5	163.6	163.2	163.2	163.2	163.2	163.2
80°	131.9	131.6	131.4	131.2	131.2	131.2	131.2	131.2
82.5°	101.5	101.0	100.6	100.2	100.0	99.8	99.6	99.4
85°	57.5	57.0	56.5	56.2	56.2	56.2	56.2	56.2
87.5°	21.8	21.6	21.4	21.4	21.4	21.4	21.5	21.5
90°	7.8	8.1	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	12.1	12.3	12.6	12.7	12.6	12.5	12.4	12.3
95°	23.1	23.3	23.6	23.8	23.8	23.8	23.8	23.8
97.5°	35.8	36.2	36.5	36.6	36.6	36.6	36.5	36.5
100°	45.1	45.4	45.5	45.7	45.8	46.0	46.1	46.2
102.5°	55.9	56.1	56.2	56.3	56.3	56.3	56.2	56.2
105°	71.8	71.8	71.8	71.9	72.0	72.2	72.3	72.4
107.5°	89.1	89.3	89.5	89.6	89.5	89.5	89.4	89.3
110°	100.7	100.9	101.2	101.3	101.1	101.0	100.8	100.7



TEST NUMBER: P332007-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	112.2	112.5	112.9	113.0	113.0	113.0	112.9	112.9
115°	129.8	129.8	129.9	129.9	129.8	129.8	129.7	129.6
117.5°	147.5	147.5	147.5	147.3	147.1	147.0	146.8	146.6
120°	159.3	159.2	159.2	159.0	158.9	158.8	158.7	158.5
122.5°	171.3	171.1	170.9	170.7	170.6	170.3	170.1	170.0
125°	189.0	188.7	188.5	188.2	188.0	187.7	187.4	187.1
127.5°	206.6	206.2	205.8	205.4	205.2	204.8	204.6	204.2
130°	218.3	217.9	217.7	217.3	216.9	216.4	215.9	215.4
132.5°	229.5	229.2	228.9	228.6	228.2	227.8	227.5	227.1
135°	246.5	246.2	246.0	245.8	245.6	245.5	245.4	245.2
137.5°	263.1	262.9	262.5	262.3	262.0	261.7	261.5	261.2
140°	274.0	274.0	273.9	273.6	273.1	272.7	272.2	271.7
142.5°	284.2	284.1	284.1	283.9	283.5	283.2	282.8	282.4
145°	299.3	299.2	299.1	298.9	298.7	298.4	298.2	297.9
147.5°	313.5	313.5	313.5	313.2	312.9	312.5	312.0	311.6
150°	322.2	322.2	322.2	322.0	321.6	321.2	320.8	320.4
152.5°	330.2	330.4	330.5	330.3	329.9	329.6	329.2	328.9
155°	341.9	342.2	342.5	342.3	341.9	341.4	341.0	340.4
157.5°	352.0	352.3	352.6	352.5	352.1	351.8	351.4	351.0
160°	358.2	358.5	358.9	358.9	358.6	358.3	358.1	357.8
162.5°	364.0	364.4	364.7	364.6	364.2	363.8	363.3	362.9
165°	371.4	371.8	372.2	372.2	371.7	371.3	370.7	370.3
167.5°	377.4	377.8	378.2	378.2	377.8	377.4	376.9	376.6
170°	380.6	381.2	381.6	381.6	381.2	380.6	380.2	379.7
172.5°	383.2	383.7	384.1	384.1	383.6	383.1	382.6	382.2
175°	386.0	386.4	386.8	386.8	386.3	385.8	385.4	384.9
177.5°	387.3	387.5	387.9	387.9	387.5	387.1	386.8	386.3
180°	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4

(END OF REPORT)