

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332304-840

Luminaire Tested: **S123RDIP-S775D365U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332304-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D365U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4205.4 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332304-840

CATALOG NUMBER: S123RDIP-S775D365U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332304-840

CATALOG NUMBER: S123RDIP-S775D365U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	75	75	75	70
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	80	75	89	82	77	72	74	70	66	66	63	60	59	57	55	51
3	86	77	69	63	81	73	66	61	66	60	56	59	55	51	53	50	47	44
4	79	68	60	54	74	65	58	52	59	53	48	53	48	44	48	44	41	38
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33
6	67	55	47	41	63	52	45	40	48	42	37	43	38	34	39	35	32	29
7	62	50	42	36	59	48	40	35	44	37	33	40	34	31	36	32	28	26
8	58	46	38	32	55	44	36	31	40	34	29	36	31	27	33	29	26	23
9	54	42	34	29	51	40	33	28	37	31	26	34	28	25	31	26	23	21
10	51	38	31	26	48	37	30	26	34	28	24	31	26	23	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14034	14034	14034
5°	14088	13894	13973
10°	14008	13719	13672
15°	13857	13397	13256
20°	13651	12997	12693
25°	13438	12545	12144
30°	13155	12026	11368
35°	12867	11506	10657
40°	12600	10891	9777
45°	12250	10286	8983
50°	11863	9597	8092
55°	11470	8811	7263
60°	11108	7967	6351
65°	10639	7055	5440
70°	10049	5923	4393
75°	9191	4662	4134
80°	8195	4135	3800
85°	6916	3656	3396



TEST NUMBER: P332304-840

CATALOG NUMBER: S123RDIP-S775D365U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	2.9
10°-20°	340.6	8.1
20°-30°	490.5	11.7
30°-40°	552.5	13.1
40°-50°	528.6	12.6
50°-60°	432.9	10.3
60°-70°	292.0	6.9
70°-80°	146.9	3.5
80°-90°	40.2	1.0
90°-100°	29.6	0.7
100°-110°	88.6	2.1
110°-120°	150.7	3.6
120°-130°	198.2	4.7
130°-140°	222.7	5.3
140°-150°	219.0	5.2
150°-160°	184.3	4.4
160°-170°	122.7	2.9
170°-180°	43.0	1.0
0°-30°	953.6	22.7
0°-40°	1506.1	35.8
0°-60°	2467.5	58.7
0°-90°	2946.7	70.1
90°-120°	268.8	6.4
90°-150°	908.7	21.6
90°-180°	1259.0	29.9
0°-180°	4205.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1304	1304	1304	1304	1304	
5°	1304	1298	1286	1295	1293	124
15°	1244	1231	1202	1197	1190	350
25°	1132	1104	1056	1035	1022	520
35°	979	940	876	832	811	613
45°	805	755	676	617	590	621
55°	611	557	470	410	387	548
65°	418	358	277	227	214	413
75°	221	170	112	102	99	236
85°	56	34	30	28	28	63
90°	0	4	9	10	11	4
95°	21	24	26	28	28	24
105°	80	81	84	84	85	86
115°	152	153	152	152	152	150
125°	222	223	222	221	219	198
135°	288	290	290	288	288	222
145°	349	350	351	351	349	218
155°	400	400	400	402	399	184
165°	436	435	435	437	434	123
175°	453	452	452	454	451	43
180°	454	454	454	454	454	



TEST NUMBER: P332304-840

CATALOG NUMBER: S123RDIP-S775D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1308.0	1307.3	1306.5	1305.8	1305.0	1303.5	1301.2	1299.0	1296.8	1294.4	1296.6
5°	1303.8	1302.6	1301.4	1300.3	1299.1	1297.1	1294.2	1291.4	1288.6	1285.9	1287.9
7.5°	1291.7	1290.5	1289.2	1287.9	1286.7	1284.1	1280.5	1276.9	1273.2	1269.5	1270.7
10°	1281.6	1279.9	1278.3	1276.7	1275.0	1272.0	1267.8	1263.6	1259.4	1255.2	1255.4
12.5°	1267.2	1265.4	1263.5	1261.7	1259.9	1256.4	1251.2	1246.1	1240.8	1235.7	1235.6
15°	1243.5	1240.9	1238.3	1235.8	1233.1	1228.6	1222.0	1215.5	1208.8	1202.2	1201.1
17.5°	1213.7	1210.7	1207.7	1204.7	1201.6	1196.0	1187.6	1179.2	1170.8	1162.6	1160.0
20°	1191.7	1187.9	1184.2	1180.4	1176.7	1170.3	1161.3	1152.5	1143.6	1134.6	1131.6
22.5°	1167.2	1162.9	1158.5	1154.2	1149.8	1143.0	1133.5	1124.0	1114.5	1105.0	1101.2
25°	1131.5	1125.6	1119.6	1113.8	1107.9	1099.5	1088.7	1077.9	1067.1	1056.3	1051.4
27.5°	1088.0	1081.6	1075.1	1068.6	1062.2	1052.9	1040.9	1028.9	1016.7	1004.7	997.8
30°	1058.4	1051.4	1044.4	1037.3	1030.3	1020.2	1007.0	993.8	980.7	967.6	959.6
32.5°	1028.9	1020.9	1012.9	1004.9	996.9	985.9	972.0	958.2	944.2	930.3	921.6
35°	979.2	970.7	962.2	953.8	945.3	933.8	919.3	904.6	890.1	875.6	865.5
37.5°	928.9	919.4	910.0	900.6	891.2	878.8	863.2	847.7	832.1	816.6	805.1
40°	896.7	886.4	876.0	865.7	855.4	841.8	825.2	808.5	791.7	775.1	762.9
42.5°	860.3	850.0	839.6	829.3	819.0	805.2	787.9	770.6	753.5	736.2	722.9
45°	804.7	794.2	783.6	773.0	762.3	748.1	729.9	711.9	693.8	675.7	662.3
47.5°	749.1	737.5	725.9	714.3	702.7	687.8	669.7	651.6	633.5	615.4	600.9
50°	708.4	697.4	686.4	675.3	664.3	649.2	630.3	611.2	592.2	573.1	558.6
52.5°	672.1	660.1	648.1	636.1	624.2	608.7	589.9	571.1	552.2	533.3	518.3
55°	611.2	599.7	588.1	576.6	565.1	549.4	529.4	509.5	489.5	469.5	455.9
57.5°	554.9	542.4	529.9	517.3	504.7	488.5	468.4	448.3	428.2	408.2	395.3
60°	516.0	503.1	490.2	477.3	464.3	448.1	428.6	409.1	389.6	370.1	357.4
62.5°	477.1	464.1	451.2	438.3	425.5	409.2	389.7	370.2	350.7	331.1	319.2
65°	417.7	404.8	391.8	378.9	366.0	350.3	332.0	313.7	295.4	277.0	265.5
67.5°	358.3	345.2	332.1	319.0	306.0	290.6	273.1	255.5	237.9	220.4	211.8
70°	319.3	306.7	294.0	281.2	268.6	254.0	237.5	221.2	204.7	188.2	180.0
72.5°	280.4	267.9	255.4	242.9	230.5	216.7	201.8	186.8	171.9	156.9	150.2
75°	221.0	209.7	198.4	187.1	175.9	163.8	150.9	137.9	125.0	112.1	109.8
77.5°	166.8	156.6	146.4	136.2	126.0	116.8	108.5	100.2	91.9	83.5	82.3
80°	132.2	122.5	112.9	103.3	93.6	86.3	81.4	76.4	71.6	66.7	65.9
82.5°	99.2	90.9	82.5	74.2	65.9	60.6	58.3	55.9	53.7	51.4	50.7
85°	56.0	50.9	45.7	40.5	35.3	32.4	31.7	31.0	30.3	29.6	29.2
87.5°	20.4	18.5	16.6	14.6	12.7	11.9	12.1	12.3	12.5	12.7	12.6
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.6	8.6	8.9
92.5°	8.7	9.2	9.7	10.3	10.8	11.3	11.9	12.5	13.1	13.7	13.9
95°	21.1	21.6	22.1	22.7	23.2	23.8	24.5	25.1	25.8	26.5	26.8
97.5°	37.4	37.8	38.3	38.7	39.1	39.5	40.0	40.4	40.9	41.3	41.7
100°	48.6	49.0	49.5	50.0	50.4	50.9	51.3	51.7	52.1	52.4	52.7
102.5°	61.4	61.7	61.9	62.2	62.5	62.9	63.4	64.0	64.5	65.0	65.2
105°	80.3	80.5	80.6	80.8	80.9	81.4	82.1	82.8	83.5	84.2	84.2
107.5°	102.3	102.4	102.5	102.6	102.7	102.8	103.1	103.4	103.7	104.0	104.2
110°	116.0	116.1	116.3	116.4	116.6	116.7	116.9	117.1	117.2	117.4	117.8



TEST NUMBER: P332304-840

CATALOG NUMBER: S123RDIP-S775D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.3	130.4	130.5	130.6	130.7	130.7	130.8	130.8	130.8	130.9	131.2
115°	151.7	151.9	152.2	152.4	152.6	152.7	152.5	152.4	152.2	152.0	152.1
117.5°	173.2	173.4	173.6	173.7	173.9	173.8	173.6	173.4	173.2	173.0	173.0
120°	186.6	187.1	187.6	188.0	188.5	188.5	188.2	187.8	187.4	187.0	186.9
122.5°	200.7	201.0	201.4	201.7	202.1	202.1	201.9	201.7	201.5	201.3	201.1
125°	222.0	222.2	222.5	222.7	223.0	223.0	222.8	222.7	222.5	222.4	222.0
127.5°	241.7	242.2	242.7	243.2	243.7	243.9	243.7	243.5	243.4	243.2	242.8
130°	254.8	255.4	256.1	256.7	257.3	257.5	257.3	257.1	256.8	256.6	256.3
132.5°	267.9	268.6	269.2	269.8	270.4	270.7	270.5	270.3	270.1	270.0	269.6
135°	288.0	288.5	288.9	289.4	289.9	290.1	290.0	289.9	289.8	289.8	289.4
137.5°	306.6	307.0	307.3	307.7	308.1	308.4	308.6	308.8	309.0	309.2	308.9
140°	319.4	319.8	320.2	320.6	321.0	321.2	321.3	321.3	321.4	321.5	321.4
142.5°	331.1	331.5	331.9	332.3	332.6	333.0	333.2	333.3	333.4	333.6	333.5
145°	349.4	349.5	349.7	349.8	350.0	350.2	350.4	350.7	350.9	351.1	351.1
147.5°	365.4	365.7	366.0	366.3	366.5	366.8	367.0	367.2	367.4	367.7	367.7
150°	376.5	376.7	376.8	377.0	377.2	377.3	377.5	377.6	377.8	377.9	377.9
152.5°	385.7	385.9	386.1	386.3	386.6	386.7	386.8	386.9	387.0	387.1	387.2
155°	400.1	400.1	400.1	400.1	400.1	400.1	400.2	400.2	400.3	400.4	400.7
157.5°	412.3	412.2	412.1	412.0	411.9	411.9	412.0	412.0	412.1	412.2	412.5
160°	420.0	419.9	419.7	419.6	419.4	419.3	419.3	419.3	419.3	419.3	419.7
162.5°	426.9	426.7	426.5	426.3	426.0	426.0	426.0	426.1	426.2	426.2	426.6
165°	435.8	435.6	435.3	435.0	434.7	434.6	434.6	434.6	434.6	434.6	435.2
167.5°	442.8	442.5	442.2	441.8	441.5	441.4	441.5	441.5	441.6	441.7	442.1
170°	446.8	446.5	446.2	445.9	445.6	445.4	445.4	445.4	445.4	445.4	446.0
172.5°	450.0	449.6	449.3	449.0	448.7	448.5	448.5	448.5	448.5	448.5	449.0
175°	453.2	452.9	452.6	452.3	452.0	451.8	451.8	451.8	451.8	451.8	452.3
177.5°	454.5	454.3	454.0	453.8	453.5	453.4	453.4	453.4	453.4	453.4	453.8
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3



TEST NUMBER: P332304-840

CATALOG NUMBER: S123RDIP-S775D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1298.6	1300.7	1302.7	1303.6	1303.2	1302.8	1302.4	1302.1
5°	1290.0	1292.1	1294.2	1295.1	1294.6	1294.1	1293.6	1293.2
7.5°	1271.9	1273.0	1274.2	1274.4	1273.6	1272.8	1272.0	1271.2
10°	1255.7	1255.9	1256.1	1255.7	1254.5	1253.2	1252.1	1250.9
12.5°	1235.4	1235.3	1235.2	1234.4	1233.0	1231.6	1230.3	1228.9
15°	1199.9	1198.7	1197.6	1196.2	1194.6	1192.9	1191.2	1189.6
17.5°	1157.5	1155.1	1152.6	1150.1	1147.6	1145.2	1142.8	1140.3
20°	1128.5	1125.4	1122.4	1119.4	1116.6	1113.8	1111.0	1108.1
22.5°	1097.4	1093.6	1089.7	1086.5	1083.9	1081.3	1078.6	1076.0
25°	1046.5	1041.6	1036.6	1032.9	1030.3	1027.6	1025.1	1022.5
27.5°	991.0	984.2	977.3	971.9	968.0	964.0	960.1	956.1
30°	951.6	943.5	935.5	929.7	925.9	922.2	918.4	914.6
32.5°	912.8	904.1	895.3	889.0	885.0	881.1	877.2	873.2
35°	855.4	845.3	835.2	828.0	823.7	819.5	815.3	811.0
37.5°	793.6	782.1	770.6	762.3	757.1	751.8	746.7	741.4
40°	750.6	738.4	726.2	717.4	712.0	706.6	701.1	695.8
42.5°	709.4	696.1	682.8	673.7	668.8	664.0	659.1	654.3
45°	648.9	635.5	622.1	612.6	606.9	601.3	595.7	590.1
47.5°	586.2	571.7	557.1	547.3	542.3	537.2	532.3	527.3
50°	544.0	529.4	514.8	504.8	499.5	494.0	488.7	483.2
52.5°	503.1	488.0	472.8	462.8	458.0	453.1	448.3	443.4
55°	442.2	428.6	415.0	405.8	401.1	396.4	391.7	387.0
57.5°	382.4	369.5	356.7	348.2	344.3	340.2	336.2	332.2
60°	344.7	332.0	319.3	311.0	307.0	303.0	299.0	295.0
62.5°	307.3	295.4	283.5	275.4	271.1	267.0	262.9	258.6
65°	254.0	242.5	231.0	223.9	221.4	218.7	216.2	213.6
67.5°	203.2	194.6	185.9	180.3	177.5	174.7	172.0	169.2
70°	171.8	163.5	155.3	150.0	147.3	144.7	142.2	139.6
72.5°	143.5	136.7	130.1	126.1	125.0	124.0	122.9	121.8
75°	107.3	105.0	102.7	101.3	100.8	100.4	99.9	99.4
77.5°	81.0	79.7	78.5	77.6	77.2	76.6	76.1	75.7
80°	65.2	64.5	63.8	63.2	62.7	62.3	61.8	61.3
82.5°	50.0	49.3	48.6	48.2	48.1	48.0	47.9	47.8
85°	28.7	28.2	27.8	27.5	27.5	27.5	27.5	27.5
87.5°	12.4	12.3	12.2	12.1	11.9	11.7	11.6	11.4
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	14.2	14.4	14.7	14.8	14.7	14.6	14.5	14.4
95°	27.1	27.4	27.7	27.9	27.9	27.9	27.9	27.9
97.5°	42.0	42.4	42.8	42.9	42.9	42.9	42.8	42.8
100°	52.9	53.2	53.4	53.6	53.7	53.9	54.1	54.2
102.5°	65.5	65.7	65.9	66.0	66.0	66.0	65.9	65.9
105°	84.2	84.2	84.2	84.3	84.4	84.6	84.8	84.9
107.5°	104.5	104.7	105.0	105.1	105.0	104.9	104.8	104.7
110°	118.1	118.4	118.7	118.8	118.6	118.5	118.3	118.2



TEST NUMBER: P332304-840

CATALOG NUMBER: S123RDIP-S775D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	131.6	132.0	132.4	132.5	132.5	132.5	132.4	132.4
115°	152.2	152.3	152.4	152.4	152.3	152.2	152.1	152.0
117.5°	173.0	173.0	173.0	172.8	172.6	172.4	172.2	172.0
120°	186.8	186.7	186.7	186.5	186.4	186.2	186.1	185.9
122.5°	200.9	200.7	200.5	200.3	200.1	199.8	199.5	199.3
125°	221.7	221.4	221.1	220.8	220.5	220.2	219.7	219.4
127.5°	242.3	241.9	241.4	241.0	240.7	240.2	239.9	239.5
130°	256.0	255.6	255.3	254.9	254.4	253.8	253.3	252.7
132.5°	269.2	268.8	268.5	268.1	267.6	267.2	266.8	266.4
135°	289.1	288.8	288.5	288.3	288.1	287.9	287.8	287.6
137.5°	308.6	308.3	307.9	307.6	307.3	307.0	306.7	306.4
140°	321.3	321.3	321.2	320.9	320.3	319.8	319.2	318.7
142.5°	333.4	333.3	333.3	333.0	332.5	332.1	331.6	331.2
145°	351.0	350.9	350.8	350.6	350.3	350.0	349.7	349.4
147.5°	367.7	367.7	367.7	367.4	367.0	366.5	366.0	365.5
150°	377.9	377.9	377.9	377.7	377.2	376.8	376.3	375.8
152.5°	387.3	387.5	387.6	387.4	387.0	386.6	386.2	385.8
155°	401.0	401.3	401.7	401.5	401.0	400.4	399.9	399.3
157.5°	412.8	413.2	413.5	413.4	413.0	412.6	412.1	411.7
160°	420.1	420.5	420.9	420.9	420.6	420.3	420.0	419.7
162.5°	427.0	427.4	427.8	427.7	427.2	426.7	426.2	425.7
165°	435.7	436.1	436.6	436.6	436.0	435.5	434.8	434.3
167.5°	442.6	443.1	443.6	443.6	443.1	442.6	442.1	441.7
170°	446.5	447.1	447.6	447.6	447.1	446.5	446.0	445.4
172.5°	449.5	450.0	450.5	450.5	449.9	449.4	448.8	448.3
175°	452.7	453.2	453.7	453.6	453.1	452.5	452.0	451.4
177.5°	454.2	454.5	454.9	454.9	454.5	454.0	453.6	453.1
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3

(END OF REPORT)