

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332017-935

Luminaire Tested: **S123DIP-S1000D585U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332017-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D585U935-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5373.4 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332017-935

CATALOG NUMBER: S123DIP-S1000D585U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332017-935

CATALOG NUMBER: S123DIP-S1000D585U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	63	61	60	55
2	92	85	78	73	87	80	74	69	71	66	63	63	59	56	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	36	31	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	33	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14670	14670	14670
5°	14738	14536	14638
10°	14641	14410	14499
15°	14469	14247	14273
20°	14269	14014	14027
25°	14001	13737	13709
30°	13706	13430	13326
35°	13397	13104	12935
40°	13075	12745	12546
45°	12718	12415	12113
50°	12363	12010	11675
55°	11898	11590	11237
60°	11427	11102	10747
65°	11013	10565	10236
70°	10401	9958	9514
75°	9503	9162	8771
80°	8573	8207	8133
85°	7534	7237	6941



TEST NUMBER: P332017-935

CATALOG NUMBER: S123DIP-S1000D585U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.4	2.4
10°-20°	362.5	6.7
20°-30°	535.5	10.0
30°-40°	625.5	11.6
40°-50°	628.8	11.7
50°-60°	552.4	10.3
60°-70°	411.5	7.7
70°-80°	234.5	4.4
80°-90°	69.2	1.3
90°-100°	135.0	2.5
100°-110°	382.3	7.1
110°-120°	376.1	7.0
120°-130°	300.0	5.6
130°-140°	236.5	4.4
140°-150°	176.5	3.3
150°-160°	123.0	2.3
160°-170°	72.3	1.3
170°-180°	23.5	0.4
0°-30°	1026.3	19.1
0°-40°	1651.8	30.7
0°-60°	2833.0	52.7
0°-90°	3548.2	66.0
90°-120°	893.4	16.6
90°-150°	1606.4	29.9
90°-180°	1825.0	34.0
0°-180°	5373.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1363	1363	1363	1363	1363	
5°	1364	1358	1345	1356	1355	129
15°	1298	1293	1278	1287	1281	366
25°	1179	1171	1157	1158	1154	543
35°	1020	1012	997	990	984	638
45°	836	830	816	802	796	645
55°	634	632	618	605	599	568
65°	432	426	415	406	402	427
75°	228	224	220	215	211	244
85°	61	59	59	56	56	67
90°	1	6	12	14	14	4
95°	17	54	291	85	57	18
105°	57	84	395	690	625	61
115°	101	125	302	662	760	100
125°	140	165	282	511	599	124
135°	164	196	278	421	486	127
145°	187	214	274	345	380	117
155°	213	229	266	302	315	98
165°	232	239	254	270	274	65
175°	242	242	244	248	247	23
180°	243	243	243	243	243	



TEST NUMBER: P332017-935

CATALOG NUMBER: S123DIP-S1000D585U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1367.5	1366.8	1365.9	1365.0	1364.3	1362.6	1360.4	1358.1	1355.8	1353.5	1355.6
5°	1364.0	1362.7	1361.4	1360.1	1358.8	1356.8	1353.9	1351.0	1348.2	1345.3	1347.9
7.5°	1350.7	1349.4	1348.1	1346.8	1345.5	1343.3	1340.4	1337.4	1334.5	1331.5	1333.8
10°	1339.5	1338.2	1336.8	1335.5	1334.2	1331.9	1328.5	1325.1	1321.7	1318.4	1320.7
12.5°	1324.4	1323.4	1322.2	1321.1	1320.1	1317.9	1314.7	1311.6	1308.4	1305.2	1306.9
15°	1298.4	1297.4	1296.3	1295.3	1294.3	1292.0	1288.7	1285.3	1281.9	1278.5	1280.6
17.5°	1268.2	1266.8	1265.5	1264.1	1262.7	1260.4	1257.0	1253.6	1250.3	1246.8	1248.3
20°	1245.7	1244.1	1242.6	1241.0	1239.4	1236.9	1233.6	1230.2	1226.8	1223.4	1224.4
22.5°	1220.4	1218.8	1217.3	1215.6	1214.1	1211.7	1208.2	1204.9	1201.5	1198.1	1198.9
25°	1178.9	1177.3	1175.8	1174.2	1172.6	1170.2	1166.7	1163.4	1160.0	1156.6	1156.8
27.5°	1134.6	1133.1	1131.5	1130.1	1128.5	1125.9	1122.3	1118.7	1115.0	1111.4	1111.6
30°	1102.7	1101.4	1100.1	1098.8	1097.5	1095.0	1091.4	1087.7	1084.1	1080.5	1080.5
32.5°	1070.8	1069.1	1067.4	1065.7	1063.9	1061.7	1058.9	1056.1	1053.3	1050.4	1049.0
35°	1019.5	1018.0	1016.4	1014.9	1013.2	1010.8	1007.4	1004.0	1000.7	997.2	995.7
37.5°	967.0	965.0	963.0	961.0	959.1	956.4	953.0	949.5	946.1	942.6	940.7
40°	930.5	928.8	927.3	925.7	924.2	921.6	917.9	914.3	910.7	907.0	904.9
42.5°	893.9	892.1	890.4	888.6	886.8	884.1	880.5	876.8	873.1	869.5	867.5
45°	835.5	834.5	833.4	832.4	831.4	829.1	825.8	822.3	819.0	815.6	812.5
47.5°	777.7	776.1	774.6	773.1	771.6	769.2	766.1	762.9	759.7	756.6	753.5
50°	738.3	736.9	735.6	734.3	733.1	730.7	727.3	723.9	720.6	717.2	714.3
52.5°	697.0	696.1	695.3	694.4	693.4	691.2	687.7	684.1	680.4	676.8	674.4
55°	634.0	633.7	633.4	633.2	632.9	631.1	627.8	624.3	621.0	617.6	614.7
57.5°	573.9	573.1	572.2	571.4	570.4	568.6	565.9	563.2	560.5	557.8	555.3
60°	530.8	530.5	530.3	530.0	529.8	528.1	525.0	521.9	518.8	515.7	513.2
62.5°	492.4	491.7	491.0	490.3	489.7	487.8	484.7	481.6	478.5	475.3	472.9
65°	432.4	431.1	429.8	428.5	427.2	425.2	422.7	420.1	417.4	414.8	412.8
67.5°	368.9	367.7	366.6	365.5	364.3	362.7	360.8	358.8	356.8	354.8	353.0
70°	330.5	328.9	327.4	325.8	324.3	322.6	321.1	319.5	318.0	316.4	314.6
72.5°	290.2	289.0	287.8	286.7	285.6	284.1	282.3	280.6	278.8	277.0	275.4
75°	228.5	227.5	226.4	225.4	224.4	223.4	222.7	221.9	221.1	220.3	219.0
77.5°	173.9	173.3	172.7	172.2	171.6	170.8	170.0	169.0	168.1	167.1	166.3
80°	138.3	137.5	136.7	136.0	135.2	134.5	134.0	133.5	132.9	132.4	132.2
82.5°	103.6	103.4	103.3	103.1	103.0	102.8	102.7	102.6	102.5	102.5	101.9
85°	61.0	60.4	59.9	59.4	58.9	58.6	58.6	58.6	58.6	58.6	58.0
87.5°	24.5	24.1	23.7	23.4	23.0	22.7	22.8	22.9	23.0	23.1	22.8
90°	0.9	2.0	2.9	4.4	5.4	6.4	7.8	9.3	10.8	12.3	11.8
92.5°	6.1	9.0	13.2	17.0	21.1	28.4	41.2	62.3	83.1	75.5	57.0
95°	16.7	18.2	23.6	31.9	44.7	63.8	105.6	178.7	259.3	291.2	236.2
97.5°	28.5	29.0	33.2	40.5	53.0	73.8	113.7	196.1	330.4	451.3	482.8
100°	36.3	36.9	40.3	47.2	58.9	78.1	112.4	185.1	314.3	465.0	561.8
102.5°	44.6	45.5	48.6	55.0	65.6	83.2	114.0	175.7	290.8	439.5	565.8
105°	57.0	58.5	61.4	67.2	76.6	91.9	118.4	168.9	261.7	394.9	535.8
107.5°	70.1	71.6	74.5	80.2	89.0	103.1	126.4	168.4	243.3	355.3	483.4
110°	79.6	81.0	83.5	88.9	97.2	111.0	133.1	170.4	236.2	332.9	450.3



TEST NUMBER: P332017-935

CATALOG NUMBER: S123DIP-S1000D585U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	88.2	89.7	92.1	97.6	105.9	119.2	139.7	174.4	232.3	318.1	421.6
115°	100.7	102.6	105.6	110.5	118.8	132.1	150.8	180.7	230.8	302.0	387.0
117.5°	113.1	115.4	117.9	122.3	131.7	144.0	162.5	189.2	231.7	292.6	366.1
120°	121.8	123.3	125.7	130.6	140.0	152.2	169.9	195.4	233.2	288.3	355.1
122.5°	129.2	130.7	133.2	138.4	147.4	160.5	177.8	201.4	236.0	285.5	346.0
125°	140.0	140.9	143.9	149.3	158.6	171.9	189.1	210.7	240.1	281.9	334.4
127.5°	148.1	149.6	153.3	158.7	169.0	182.3	198.9	218.3	244.9	280.1	324.3
130°	153.3	154.7	159.1	165.0	175.3	188.6	204.7	223.4	248.0	279.0	318.7
132.5°	157.1	159.0	163.8	170.9	181.2	194.1	209.9	228.2	250.4	278.5	313.6
135°	164.0	166.0	171.4	178.7	189.1	202.3	217.6	234.3	253.9	277.9	306.9
137.5°	170.5	172.5	177.9	185.7	196.0	208.2	222.8	238.8	256.2	276.9	301.2
140°	174.9	177.3	182.2	190.0	199.8	212.2	226.4	241.2	257.8	276.5	297.6
142.5°	179.5	181.6	186.9	194.0	203.8	215.3	229.1	243.5	259.0	275.7	294.5
145°	187.1	188.6	193.0	200.4	208.7	220.0	232.8	246.1	259.8	274.5	290.2
147.5°	194.8	195.6	200.0	206.4	214.4	224.0	235.7	247.6	259.8	272.7	286.1
150°	199.8	200.4	204.3	210.7	217.6	226.4	237.7	248.0	259.8	271.0	283.4
152.5°	205.0	205.1	209.1	214.6	220.7	229.1	238.8	248.8	258.6	269.1	280.3
155°	212.7	212.7	215.6	220.5	225.9	232.8	241.2	249.0	257.4	265.7	275.5
157.5°	218.7	219.1	221.4	225.8	230.4	235.7	242.4	249.5	255.6	262.6	270.2
160°	223.4	223.4	225.4	229.4	232.8	237.7	243.6	249.5	254.9	260.3	266.7
162.5°	227.0	227.0	228.6	231.7	234.7	238.8	244.0	249.1	253.3	258.0	263.1
165°	232.3	231.8	232.8	235.2	237.2	240.6	244.5	248.0	251.0	254.4	258.3
167.5°	236.3	235.7	236.2	238.1	239.4	241.6	244.4	247.2	248.6	250.8	253.7
170°	238.7	237.7	238.2	239.6	240.6	241.6	244.1	246.1	247.0	248.5	251.0
172.5°	240.2	239.6	239.8	240.8	241.4	242.0	244.1	245.6	245.8	246.5	248.2
175°	242.1	241.6	241.2	242.1	242.1	242.6	243.6	244.5	244.1	244.1	245.0
177.5°	243.0	242.6	242.2	242.6	242.6	242.6	243.0	243.7	243.0	242.6	243.0
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332017-935

CATALOG NUMBER: S123DIP-S1000D585U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1357.6	1359.8	1361.8	1362.8	1362.5	1362.4	1362.1	1361.9
5°	1350.5	1353.1	1355.7	1356.8	1356.2	1355.7	1355.2	1354.7
7.5°	1336.2	1338.5	1340.8	1341.9	1341.5	1341.3	1340.9	1340.6
10°	1323.0	1325.3	1327.7	1328.6	1328.1	1327.6	1327.1	1326.5
12.5°	1308.6	1310.4	1312.1	1312.8	1312.5	1312.2	1311.8	1311.6
15°	1282.6	1284.7	1286.9	1287.1	1285.6	1283.9	1282.4	1280.8
17.5°	1249.7	1251.2	1252.7	1253.1	1252.6	1252.0	1251.4	1250.9
20°	1225.5	1226.6	1227.6	1227.7	1226.9	1226.2	1225.4	1224.6
22.5°	1199.8	1200.6	1201.4	1201.4	1200.4	1199.4	1198.4	1197.4
25°	1157.1	1157.4	1157.7	1157.4	1156.6	1155.8	1155.0	1154.3
27.5°	1111.8	1112.0	1112.2	1111.8	1110.9	1109.8	1108.9	1107.8
30°	1080.5	1080.5	1080.5	1079.5	1077.7	1075.9	1074.1	1072.2
32.5°	1047.5	1046.1	1044.7	1043.4	1042.4	1041.4	1040.4	1039.4
35°	994.1	992.6	991.0	989.5	988.3	987.0	985.7	984.4
37.5°	938.9	937.0	935.1	933.8	933.0	932.1	931.3	930.5
40°	902.8	900.8	898.7	897.1	896.0	895.0	894.0	892.9
42.5°	865.3	863.2	861.2	859.6	858.6	857.6	856.5	855.5
45°	809.3	806.2	803.1	800.9	799.6	798.3	797.0	795.7
47.5°	750.4	747.3	744.2	742.2	741.0	739.9	738.7	737.5
50°	711.4	708.6	705.7	703.5	702.0	700.3	698.8	697.2
52.5°	671.9	669.5	667.1	665.0	663.5	661.9	660.4	658.8
55°	611.8	609.0	606.1	604.0	602.7	601.4	600.1	598.8
57.5°	552.7	550.2	547.6	545.5	544.1	542.5	541.1	539.5
60°	510.9	508.6	506.3	504.5	503.1	501.8	500.5	499.2
62.5°	470.6	468.3	465.9	464.3	463.4	462.5	461.7	460.8
65°	410.7	408.5	406.5	405.1	404.3	403.6	402.7	401.9
67.5°	351.2	349.4	347.6	346.1	345.0	343.9	342.8	341.7
70°	312.7	310.9	309.1	307.5	306.3	305.0	303.7	302.3
72.5°	273.8	272.2	270.5	269.4	268.7	268.0	267.4	266.7
75°	217.7	216.4	215.1	214.0	213.3	212.5	211.7	210.9
77.5°	165.3	164.5	163.6	163.2	163.2	163.2	163.2	163.2
80°	131.9	131.6	131.4	131.2	131.2	131.2	131.2	131.2
82.5°	101.5	101.0	100.6	100.2	100.0	99.8	99.6	99.4
85°	57.5	57.0	56.5	56.2	56.2	56.2	56.2	56.2
87.5°	22.6	22.6	22.5	22.6	22.5	22.6	22.6	22.6
90°	12.3	12.7	13.3	14.2	13.8	14.2	14.7	14.2
92.5°	41.3	32.8	29.0	26.4	25.6	24.0	24.5	23.7
95°	176.8	119.9	93.8	76.1	66.8	62.3	58.9	57.0
97.5°	440.7	353.0	289.6	230.9	194.7	172.5	159.3	155.1
100°	579.0	539.2	481.7	412.0	362.4	326.6	307.5	307.9
102.5°	625.0	623.7	590.2	546.0	507.4	479.0	463.0	451.7
105°	638.4	687.5	696.9	684.1	661.5	642.8	627.2	624.7
107.5°	599.7	679.5	722.5	739.9	740.4	734.1	728.8	724.3
110°	562.7	653.2	715.1	749.4	763.2	767.1	766.1	765.1





TEST NUMBER: P332017-935

CATALOG NUMBER: S123DIP-S1000D585U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	526.2	618.5	687.9	732.1	757.2	769.5	773.2	773.4
115°	477.9	563.3	635.5	689.0	725.8	747.4	757.2	759.7
117.5°	442.7	516.5	581.3	635.7	674.1	698.8	713.0	716.3
120°	424.3	490.6	549.5	599.2	637.9	665.5	677.2	680.2
122.5°	409.7	469.8	524.3	570.4	604.9	629.6	642.7	646.4
125°	390.4	443.9	491.1	530.4	561.8	583.4	595.7	599.2
127.5°	373.5	421.3	463.8	499.6	527.5	546.0	557.1	560.3
130°	362.9	407.1	446.9	480.3	506.4	524.0	534.3	538.2
132.5°	353.1	393.7	430.8	462.6	487.1	504.7	513.8	516.6
135°	339.8	374.7	406.7	434.6	458.7	473.4	482.2	485.7
137.5°	327.8	356.4	383.8	408.1	428.3	443.2	450.7	453.0
140°	320.7	345.7	369.3	390.4	409.1	422.8	430.7	430.2
142.5°	314.0	335.5	355.9	374.3	390.2	402.4	409.5	409.0
145°	305.9	322.2	337.9	352.1	364.4	374.7	378.7	379.6
147.5°	299.4	312.2	324.9	335.0	344.3	351.3	355.1	355.4
150°	294.6	305.9	316.2	325.6	332.9	338.4	341.3	341.3
152.5°	290.3	300.1	309.2	316.9	322.7	327.8	329.5	329.5
155°	283.9	291.7	299.1	305.0	309.4	313.3	314.3	314.8
157.5°	277.0	283.5	289.3	293.9	297.7	300.7	301.4	301.4
160°	273.0	278.4	283.4	286.8	290.2	293.2	293.2	292.7
162.5°	268.4	272.9	277.5	280.5	282.8	285.3	285.3	284.8
165°	262.3	265.2	268.6	271.0	273.0	275.0	274.5	274.5
167.5°	256.9	259.2	261.1	262.9	263.8	265.2	264.7	264.7
170°	253.4	254.9	256.8	257.8	258.3	259.3	258.8	258.8
172.5°	250.3	251.3	252.9	253.5	253.6	254.6	253.7	253.3
175°	246.1	246.5	247.5	247.5	247.5	248.0	247.5	247.0
177.5°	243.4	243.7	244.2	244.2	243.7	244.2	243.4	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6

(END OF REPORT)