

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332025-935

Luminaire Tested: **S123DIP-S1000D805U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332025-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5923.1 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332025-935

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332025-935

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	95	92	88	93	89	86	83	78	75	73	67	65	64	58	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	51	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	47	42	38	40	37	34	31
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	31	27	23	27	24	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	22	19	17
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14670	14670	14670
5°	14738	14536	14638
10°	14641	14410	14499
15°	14469	14247	14273
20°	14269	14014	14027
25°	14001	13737	13709
30°	13706	13430	13326
35°	13397	13104	12935
40°	13075	12745	12546
45°	12718	12415	12113
50°	12363	12010	11675
55°	11898	11590	11237
60°	11427	11102	10747
65°	11013	10565	10236
70°	10401	9958	9514
75°	9503	9162	8771
80°	8573	8207	8133
85°	7534	7237	6941



TEST NUMBER: P332025-935

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	2.2
10°-20°	362.5	6.1
20°-30°	535.5	9.0
30°-40°	625.5	10.6
40°-50°	628.8	10.6
50°-60°	552.4	9.3
60°-70°	411.5	6.9
70°-80°	234.5	4.0
80°-90°	69.8	1.2
90°-100°	55.8	0.9
100°-110°	167.1	2.8
110°-120°	284.2	4.8
120°-130°	373.8	6.3
130°-140°	420.2	7.1
140°-150°	413.0	7.0
150°-160°	347.7	5.9
160°-170°	231.4	3.9
170°-180°	81.0	1.4
0°-30°	1026.3	17.3
0°-40°	1651.8	27.9
0°-60°	2833.0	47.8
0°-90°	3548.8	59.9
90°-120°	507.1	8.6
90°-150°	1714.1	28.9
90°-180°	2374.0	40.1
0°-180°	5923.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1363	1363	1363	1363	1363	
5°	1364	1358	1345	1356	1355	129
15°	1298	1293	1278	1287	1281	366
25°	1179	1171	1157	1158	1154	543
35°	1020	1012	997	990	984	638
45°	836	830	816	802	796	645
55°	634	632	618	605	599	568
65°	432	426	415	406	402	427
75°	228	224	220	215	211	244
85°	61	59	59	56	56	67
90°	1	8	16	19	20	6
95°	40	44	50	52	52	45
105°	151	153	159	159	160	162
115°	286	288	287	287	287	283
125°	419	421	419	417	414	373
135°	543	547	547	544	543	418
145°	659	660	662	662	659	411
155°	755	755	755	758	753	347
165°	822	820	820	824	819	232
175°	855	852	852	856	852	81
180°	857	857	857	857	857	



TEST NUMBER: P332025-935

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1367.5	1366.8	1365.9	1365.0	1364.3	1362.6	1360.4	1358.1	1355.8	1353.5	1355.6
5°	1364.0	1362.7	1361.4	1360.1	1358.8	1356.8	1353.9	1351.0	1348.2	1345.3	1347.9
7.5°	1350.7	1349.4	1348.1	1346.8	1345.5	1343.3	1340.4	1337.4	1334.5	1331.5	1333.8
10°	1339.5	1338.2	1336.8	1335.5	1334.2	1331.9	1328.5	1325.1	1321.7	1318.4	1320.7
12.5°	1324.4	1323.4	1322.2	1321.1	1320.1	1317.9	1314.7	1311.6	1308.4	1305.2	1306.9
15°	1298.4	1297.4	1296.3	1295.3	1294.3	1292.0	1288.7	1285.3	1281.9	1278.5	1280.6
17.5°	1268.2	1266.8	1265.5	1264.1	1262.7	1260.4	1257.0	1253.6	1250.3	1246.8	1248.3
20°	1245.7	1244.1	1242.6	1241.0	1239.4	1236.9	1233.6	1230.2	1226.8	1223.4	1224.4
22.5°	1220.4	1218.8	1217.3	1215.6	1214.1	1211.7	1208.2	1204.9	1201.5	1198.1	1198.9
25°	1178.9	1177.3	1175.8	1174.2	1172.6	1170.2	1166.7	1163.4	1160.0	1156.6	1156.8
27.5°	1134.6	1133.1	1131.5	1130.1	1128.5	1125.9	1122.3	1118.7	1115.0	1111.4	1111.6
30°	1102.7	1101.4	1100.1	1098.8	1097.5	1095.0	1091.4	1087.7	1084.1	1080.5	1080.5
32.5°	1070.8	1069.1	1067.4	1065.7	1063.9	1061.7	1058.9	1056.1	1053.3	1050.4	1049.0
35°	1019.5	1018.0	1016.4	1014.9	1013.2	1010.8	1007.4	1004.0	1000.7	997.2	995.7
37.5°	967.0	965.0	963.0	961.0	959.1	956.4	953.0	949.5	946.1	942.6	940.7
40°	930.5	928.8	927.3	925.7	924.2	921.6	917.9	914.3	910.7	907.0	904.9
42.5°	893.9	892.1	890.4	888.6	886.8	884.1	880.5	876.8	873.1	869.5	867.5
45°	835.5	834.5	833.4	832.4	831.4	829.1	825.8	822.3	819.0	815.6	812.5
47.5°	777.7	776.1	774.6	773.1	771.6	769.2	766.1	762.9	759.7	756.6	753.5
50°	738.3	736.9	735.6	734.3	733.1	730.7	727.3	723.9	720.6	717.2	714.3
52.5°	697.0	696.1	695.3	694.4	693.4	691.2	687.7	684.1	680.4	676.8	674.4
55°	634.0	633.7	633.4	633.2	632.9	631.1	627.8	624.3	621.0	617.6	614.7
57.5°	573.9	573.1	572.2	571.4	570.4	568.6	565.9	563.2	560.5	557.8	555.3
60°	530.8	530.5	530.3	530.0	529.8	528.1	525.0	521.9	518.8	515.7	513.2
62.5°	492.4	491.7	491.0	490.3	489.7	487.8	484.7	481.6	478.5	475.3	472.9
65°	432.4	431.1	429.8	428.5	427.2	425.2	422.7	420.1	417.4	414.8	412.8
67.5°	368.9	367.7	366.6	365.5	364.3	362.7	360.8	358.8	356.8	354.8	353.0
70°	330.5	328.9	327.4	325.8	324.3	322.6	321.1	319.5	318.0	316.4	314.6
72.5°	290.2	289.0	287.8	286.7	285.6	284.1	282.3	280.6	278.8	277.0	275.4
75°	228.5	227.5	226.4	225.4	224.4	223.4	222.7	221.9	221.1	220.3	219.0
77.5°	173.9	173.3	172.7	172.2	171.6	170.8	170.0	169.0	168.1	167.1	166.3
80°	138.3	137.5	136.7	136.0	135.2	134.5	134.0	133.5	132.9	132.4	132.2
82.5°	103.6	103.4	103.3	103.1	103.0	102.8	102.7	102.6	102.5	102.5	101.9
85°	61.0	60.4	59.9	59.4	58.9	58.6	58.6	58.6	58.6	58.6	58.0
87.5°	24.5	24.2	23.8	23.5	23.2	23.2	23.3	23.5	23.7	23.8	23.8
90°	0.7	2.2	3.7	5.2	6.6	8.4	10.3	12.2	14.2	16.2	16.8
92.5°	16.3	17.3	18.3	19.4	20.3	21.4	22.6	23.7	24.7	25.8	26.3
95°	39.7	40.7	41.8	42.9	43.9	45.0	46.2	47.4	48.6	49.9	50.5
97.5°	70.5	71.3	72.1	72.8	73.7	74.5	75.3	76.2	77.1	77.9	78.6
100°	91.5	92.5	93.3	94.3	95.1	96.0	96.7	97.5	98.2	98.9	99.4
102.5°	115.8	116.3	116.8	117.4	118.0	118.7	119.7	120.7	121.7	122.7	123.1
105°	151.4	151.8	152.1	152.4	152.7	153.5	154.8	156.2	157.6	158.9	158.9
107.5°	193.0	193.1	193.3	193.5	193.6	194.0	194.6	195.1	195.6	196.1	196.7
110°	218.8	219.0	219.4	219.6	220.0	220.2	220.6	220.8	221.2	221.4	222.1



TEST NUMBER: P332025-935

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.7	245.9	246.1	246.2	246.4	246.5	246.6	246.7	246.8	246.8	247.5
115°	286.1	286.5	287.0	287.4	287.9	288.0	287.7	287.4	287.1	286.8	286.9
117.5°	326.7	327.1	327.4	327.6	328.0	327.9	327.5	327.1	326.7	326.3	326.3
120°	352.1	352.9	353.9	354.7	355.7	355.8	355.0	354.2	353.5	352.8	352.6
122.5°	378.5	379.1	379.8	380.4	381.1	381.3	380.8	380.5	380.0	379.7	379.3
125°	418.7	419.1	419.6	420.1	420.5	420.6	420.3	420.0	419.7	419.4	418.8
127.5°	455.9	456.8	457.8	458.7	459.7	460.0	459.7	459.3	459.0	458.7	457.9
130°	480.6	481.8	483.0	484.2	485.4	485.8	485.3	484.9	484.5	484.0	483.4
132.5°	505.4	506.6	507.8	509.0	510.2	510.7	510.3	510.0	509.6	509.3	508.6
135°	543.2	544.2	545.0	546.0	546.8	547.3	547.1	546.9	546.7	546.6	546.0
137.5°	578.2	579.0	579.7	580.5	581.3	581.8	582.2	582.6	583.0	583.3	582.7
140°	602.4	603.2	604.0	604.8	605.5	605.9	606.1	606.2	606.4	606.5	606.4
142.5°	624.6	625.3	626.0	626.8	627.6	628.1	628.4	628.6	628.9	629.1	629.0
145°	659.0	659.4	659.6	660.0	660.2	660.6	661.1	661.5	661.9	662.4	662.3
147.5°	689.2	689.7	690.3	690.8	691.4	691.8	692.2	692.7	693.1	693.5	693.5
150°	710.2	710.5	710.8	711.1	711.4	711.7	712.0	712.3	712.6	712.9	712.9
152.5°	727.5	727.8	728.2	728.7	729.1	729.4	729.6	729.8	730.0	730.1	730.4
155°	754.6	754.6	754.6	754.6	754.6	754.7	754.8	755.0	755.2	755.3	755.9
157.5°	777.7	777.6	777.4	777.2	777.1	777.1	777.1	777.3	777.4	777.5	778.2
160°	792.3	792.0	791.7	791.4	791.1	791.0	791.0	791.0	791.0	791.0	791.7
162.5°	805.2	804.9	804.4	804.0	803.6	803.4	803.6	803.7	803.7	803.9	804.6
165°	821.9	821.5	821.0	820.6	820.1	819.9	819.9	819.9	819.9	819.9	820.8
167.5°	835.3	834.7	834.1	833.4	832.8	832.7	832.8	832.8	833.0	833.1	834.1
170°	842.8	842.2	841.6	841.0	840.4	840.1	840.1	840.1	840.1	840.1	841.2
172.5°	848.7	848.2	847.6	847.0	846.4	846.0	846.0	846.0	846.0	846.0	847.0
175°	854.9	854.3	853.8	853.2	852.6	852.2	852.2	852.2	852.2	852.2	853.2
177.5°	857.5	857.0	856.5	856.0	855.6	855.3	855.3	855.3	855.3	855.3	856.0
180°	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0



TEST NUMBER: P332025-935

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1357.6	1359.8	1361.8	1362.8	1362.5	1362.4	1362.1	1361.9
5°	1350.5	1353.1	1355.7	1356.8	1356.2	1355.7	1355.2	1354.7
7.5°	1336.2	1338.5	1340.8	1341.9	1341.5	1341.3	1340.9	1340.6
10°	1323.0	1325.3	1327.7	1328.6	1328.1	1327.6	1327.1	1326.5
12.5°	1308.6	1310.4	1312.1	1312.8	1312.5	1312.2	1311.8	1311.6
15°	1282.6	1284.7	1286.9	1287.1	1285.6	1283.9	1282.4	1280.8
17.5°	1249.7	1251.2	1252.7	1253.1	1252.6	1252.0	1251.4	1250.9
20°	1225.5	1226.6	1227.6	1227.7	1226.9	1226.2	1225.4	1224.6
22.5°	1199.8	1200.6	1201.4	1201.4	1200.4	1199.4	1198.4	1197.4
25°	1157.1	1157.4	1157.7	1157.4	1156.6	1155.8	1155.0	1154.3
27.5°	1111.8	1112.0	1112.2	1111.8	1110.9	1109.8	1108.9	1107.8
30°	1080.5	1080.5	1080.5	1079.5	1077.7	1075.9	1074.1	1072.2
32.5°	1047.5	1046.1	1044.7	1043.4	1042.4	1041.4	1040.4	1039.4
35°	994.1	992.6	991.0	989.5	988.3	987.0	985.7	984.4
37.5°	938.9	937.0	935.1	933.8	933.0	932.1	931.3	930.5
40°	902.8	900.8	898.7	897.1	896.0	895.0	894.0	892.9
42.5°	865.3	863.2	861.2	859.6	858.6	857.6	856.5	855.5
45°	809.3	806.2	803.1	800.9	799.6	798.3	797.0	795.7
47.5°	750.4	747.3	744.2	742.2	741.0	739.9	738.7	737.5
50°	711.4	708.6	705.7	703.5	702.0	700.3	698.8	697.2
52.5°	671.9	669.5	667.1	665.0	663.5	661.9	660.4	658.8
55°	611.8	609.0	606.1	604.0	602.7	601.4	600.1	598.8
57.5°	552.7	550.2	547.6	545.5	544.1	542.5	541.1	539.5
60°	510.9	508.6	506.3	504.5	503.1	501.8	500.5	499.2
62.5°	470.6	468.3	465.9	464.3	463.4	462.5	461.7	460.8
65°	410.7	408.5	406.5	405.1	404.3	403.6	402.7	401.9
67.5°	351.2	349.4	347.6	346.1	345.0	343.9	342.8	341.7
70°	312.7	310.9	309.1	307.5	306.3	305.0	303.7	302.3
72.5°	273.8	272.2	270.5	269.4	268.7	268.0	267.4	266.7
75°	217.7	216.4	215.1	214.0	213.3	212.5	211.7	210.9
77.5°	165.3	164.5	163.6	163.2	163.2	163.2	163.2	163.2
80°	131.9	131.6	131.4	131.2	131.2	131.2	131.2	131.2
82.5°	101.5	101.0	100.6	100.2	100.0	99.8	99.6	99.4
85°	57.5	57.0	56.5	56.2	56.2	56.2	56.2	56.2
87.5°	23.7	23.6	23.5	23.5	23.5	23.6	23.7	23.8
90°	17.4	17.9	18.5	19.0	19.3	19.6	19.9	20.2
92.5°	26.8	27.3	27.7	27.9	27.7	27.6	27.4	27.2
95°	51.0	51.6	52.2	52.5	52.5	52.5	52.5	52.5
97.5°	79.3	80.0	80.7	81.0	80.9	80.9	80.8	80.8
100°	99.9	100.3	100.7	101.2	101.4	101.7	102.0	102.3
102.5°	123.6	124.0	124.4	124.7	124.6	124.5	124.5	124.4
105°	158.9	158.9	158.9	159.0	159.3	159.6	159.9	160.2
107.5°	197.1	197.6	198.1	198.2	198.0	197.9	197.7	197.5
110°	222.7	223.3	223.9	224.0	223.7	223.4	223.1	222.8



TEST NUMBER: P332025-935

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	248.2	248.9	249.7	249.9	249.9	249.9	249.8	249.8
115°	287.1	287.2	287.4	287.4	287.2	287.1	286.9	286.8
117.5°	326.3	326.2	326.2	326.0	325.6	325.2	324.8	324.3
120°	352.4	352.3	352.1	351.9	351.6	351.3	351.0	350.7
122.5°	378.9	378.5	378.2	377.7	377.3	376.9	376.4	376.0
125°	418.2	417.6	417.0	416.4	415.8	415.2	414.6	414.0
127.5°	457.0	456.2	455.4	454.6	453.9	453.2	452.5	451.9
130°	482.8	482.2	481.6	480.8	479.7	478.7	477.7	476.6
132.5°	507.9	507.1	506.4	505.7	504.9	504.0	503.3	502.5
135°	545.4	544.8	544.2	543.8	543.5	543.2	542.9	542.6
137.5°	582.1	581.5	580.8	580.2	579.7	579.1	578.6	578.0
140°	606.2	606.1	605.9	605.4	604.2	603.2	602.2	601.2
142.5°	628.9	628.7	628.5	628.1	627.2	626.5	625.6	624.8
145°	662.1	661.9	661.8	661.4	660.8	660.2	659.6	659.0
147.5°	693.5	693.5	693.5	693.0	692.2	691.2	690.3	689.5
150°	712.9	712.9	712.9	712.5	711.5	710.7	709.7	708.9
152.5°	730.6	730.8	731.1	730.8	730.0	729.3	728.5	727.7
155°	756.5	757.1	757.7	757.4	756.4	755.4	754.3	753.3
157.5°	778.8	779.4	780.0	779.9	779.1	778.3	777.4	776.5
160°	792.5	793.2	793.9	794.0	793.4	792.8	792.2	791.6
162.5°	805.4	806.2	806.9	806.8	805.8	804.9	803.9	803.0
165°	821.7	822.6	823.5	823.5	822.4	821.3	820.3	819.2
167.5°	835.0	835.9	836.8	836.8	835.9	835.0	834.1	833.1
170°	842.2	843.3	844.3	844.3	843.3	842.2	841.2	840.1
172.5°	847.9	848.9	849.7	849.7	848.6	847.6	846.5	845.5
175°	854.0	854.9	855.8	855.7	854.7	853.7	852.6	851.5
177.5°	856.8	857.5	858.2	858.2	857.3	856.4	855.7	854.8
180°	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0

(END OF REPORT)