

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332307-840

Luminaire Tested: **S123RDIP-S775D585U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332307-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D585U840-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5108.9 lumens  
Efficiency: N/A  
Efficacy: 126.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	101	97	93	90	94	91	87	84	79	77	75	69	67	65	59	58	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45
3	85	76	68	63	79	71	65	60	63	58	54	55	51	48	47	45	42	39
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37	34
5	72	60	52	47	67	57	50	45	51	45	41	45	40	37	39	35	33	30
6	66	55	47	41	62	52	44	39	46	40	36	40	36	32	36	32	29	27
7	62	49	42	36	58	47	40	35	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	33	28	34	29	26	30	26	24	21
9	53	41	34	29	50	39	32	28	35	30	26	31	27	24	28	24	21	19
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13295	13295	13295	13295
5°	15847	13351	11757	13351
10°	19787	13274	10622	13274
15°	23226	13138	9686	13138
20°	25921	12936	8891	12936
25°	25508	12722	8402	12722
30°	18334	12525	7899	12525
35°	12242	12269	7573	12269
40°	9020	11960	7235	11960
45°	7566	11420	6905	11420
50°	6677	10712	6445	10712
55°	5853	9903	5814	9903
60°	5214	9128	5326	9128
65°	4579	8295	4956	8295
70°	3594	7553	4526	7553
75°	3165	6596	4134	6596
80°	2752	5604	4060	5604
85°	2223	4508	4310	4508



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.5	2.4
10°-20°	379.5	7.4
20°-30°	596.1	11.7
30°-40°	621.9	12.2
40°-50°	532.3	10.4
50°-60°	405.7	7.9
60°-70°	260.0	5.1
70°-80°	125.1	2.4
80°-90°	35.3	0.7
90°-100°	47.8	0.9
100°-110°	143.0	2.8
110°-120°	243.2	4.8
120°-130°	319.9	6.3
130°-140°	359.5	7.0
140°-150°	353.4	6.9
150°-160°	297.5	5.8
160°-170°	198.0	3.9
170°-180°	69.3	1.4
0°-30°	1097.0	21.5
0°-40°	1719.0	33.6
0°-60°	2656.9	52.0
0°-90°	3077.3	60.2
90°-120°	433.9	8.5
90°-150°	1466.7	28.7
90°-180°	2032.0	39.8
0°-180°	5108.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1235	1235	1235	1235	1235	
5°	1467	1236	1088	1236	1467	151
15°	2084	1179	869	1179	2084	591
25°	2148	1071	707	1071	2148	923
35°	932	934	576	934	932	611
45°	497	750	454	750	497	391
55°	312	528	310	528	312	282
65°	180	326	195	326	180	177
75°	76	159	99	159	76	82
85°	18	36	35	36	18	21
90°	17	1	17	1	17	9
95°	45	34	45	34	45	46
105°	137	130	137	130	137	145
115°	245	245	245	245	245	243
125°	354	358	354	358	354	317
135°	464	465	464	465	464	357
145°	564	564	564	564	564	352
155°	645	646	645	646	645	297
165°	701	703	701	703	701	198
175°	729	732	729	732	729	69
180°	733	733	733	733	733	



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1315.5	1317.2	1311.6	1310.8	1304.4	1302.7	1302.7	1293.8	1288.4	1281.2	1277.0
5°	1466.6	1475.1	1470.9	1461.4	1445.5	1441.8	1431.8	1415.9	1398.0	1375.7	1365.1
7.5°	1655.5	1667.1	1662.6	1647.9	1631.3	1617.9	1589.5	1563.2	1526.3	1493.9	1466.2
10°	1810.3	1798.2	1788.7	1774.3	1759.1	1734.1	1704.6	1663.9	1616.8	1579.8	1538.5
12.5°	1926.2	1924.2	1912.2	1897.4	1875.8	1852.2	1815.8	1766.3	1711.5	1658.1	1610.9
15°	2084.2	2087.4	2079.4	2064.1	2033.5	1991.7	1936.7	1916.0	1837.9	1779.7	1721.5
17.5°	2193.5	2192.9	2191.8	2170.6	2139.3	2109.6	2058.6	2004.4	1933.5	1851.6	1773.2
20°	2262.9	2257.7	2258.7	2234.8	2211.6	2177.3	2127.6	2048.8	1990.6	1896.0	1815.0
22.5°	2261.2	2260.2	2264.2	2256.0	2239.1	2212.8	2173.6	2107.2	2033.0	1937.4	1846.3
25°	2147.7	2143.4	2168.3	2175.1	2202.1	2206.9	2195.2	2158.8	2088.4	1990.0	1877.4
27.5°	1797.5	1795.1	1841.2	1899.0	1972.1	2029.0	2084.0	2110.5	2088.4	2018.0	1905.2
30°	1475.1	1524.8	1548.1	1631.6	1724.6	1835.7	1933.0	2025.5	2048.2	2017.6	1925.0
32.5°	1224.8	1268.1	1287.5	1359.2	1445.9	1576.0	1721.9	1852.9	1945.5	1968.9	1913.2
35°	931.6	932.1	976.5	1008.2	1088.6	1222.3	1364.1	1539.6	1714.0	1846.2	1860.0
37.5°	743.4	746.0	772.8	804.5	864.7	935.5	1060.3	1206.2	1407.8	1610.6	1729.6
40°	641.9	646.6	666.7	697.9	741.2	794.7	891.9	1029.5	1197.5	1423.3	1607.8
42.5°	576.7	584.4	594.8	618.8	645.7	695.7	774.4	880.5	1033.4	1246.9	1459.8
45°	497.0	501.2	509.2	520.3	544.6	579.5	632.4	703.7	830.6	1002.5	1215.5
47.5°	438.4	436.2	444.5	453.5	469.7	493.5	529.0	587.2	677.7	815.6	996.3
50°	398.7	398.1	403.9	410.8	426.2	443.6	472.7	516.5	588.4	702.7	868.2
52.5°	361.4	363.5	367.6	376.2	387.2	401.3	427.4	459.0	520.8	619.4	757.3
55°	311.9	313.6	319.3	324.1	332.0	346.3	362.7	389.1	431.4	500.2	613.8
57.5°	270.0	269.3	274.9	276.1	285.1	296.7	309.4	329.9	360.6	411.6	488.2
60°	242.2	240.5	245.3	249.0	253.8	263.3	273.9	294.0	318.3	355.8	421.4
62.5°	216.8	216.0	219.5	223.2	227.1	235.8	244.7	260.1	279.3	311.0	363.0
65°	179.8	181.4	182.9	184.5	186.6	191.9	200.4	211.0	224.2	246.4	283.9
67.5°	141.3	142.9	143.4	146.6	151.2	154.5	159.7	169.1	178.2	197.0	218.3
70°	114.2	113.7	114.2	115.8	121.6	127.4	134.3	141.2	146.9	160.2	178.1
72.5°	98.2	97.1	98.6	98.9	101.7	103.3	107.7	114.1	121.6	130.6	143.5
75°	76.1	76.1	76.1	76.1	78.3	79.3	80.9	82.5	85.1	89.4	98.9
77.5°	56.2	56.4	57.1	57.7	58.1	58.7	59.7	61.2	62.2	64.4	68.6
80°	44.4	44.9	44.4	44.9	44.9	45.9	46.6	48.1	48.7	51.3	52.9
82.5°	33.4	33.1	33.4	33.9	33.9	35.0	35.1	36.3	36.4	37.8	39.4
85°	18.0	17.0	18.0	17.5	18.5	17.5	18.0	19.0	19.0	19.6	21.7
87.5°	7.7	8.5	7.6	8.0	7.9	8.3	8.2	8.1	8.8	8.3	8.4
90°	17.3	17.1	16.8	16.6	16.3	15.9	15.3	14.8	14.3	13.8	12.1
92.5°	23.2	23.4	23.5	23.7	23.9	23.7	23.3	22.9	22.5	22.1	21.2
95°	44.9	44.9	44.9	44.9	44.9	44.6	44.1	43.6	43.1	42.6	41.6
97.5°	69.1	69.2	69.2	69.3	69.3	69.1	68.5	67.9	67.3	66.8	65.9
100°	87.6	87.3	87.1	86.7	86.5	86.2	85.8	85.4	85.0	84.6	84.0
102.5°	106.4	106.5	106.5	106.6	106.6	106.4	106.1	105.7	105.3	104.9	104.1
105°	137.1	136.8	136.5	136.3	136.0	135.9	135.9	135.9	135.9	135.9	134.8
107.5°	169.1	169.2	169.4	169.5	169.7	169.5	169.1	168.6	168.2	167.8	167.4
110°	190.7	191.0	191.2	191.5	191.7	191.6	191.1	190.6	190.1	189.6	189.2



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	213.7	213.8	213.8	213.9	213.9	213.6	213.0	212.4	211.8	211.2	211.2
115°	245.4	245.5	245.6	245.8	245.9	245.9	245.8	245.6	245.5	245.4	245.6
117.5°	277.5	277.9	278.2	278.6	278.9	279.1	279.1	279.2	279.2	279.2	279.6
120°	300.1	300.3	300.6	300.8	301.1	301.3	301.4	301.5	301.7	301.8	302.5
122.5°	321.7	322.1	322.4	322.9	323.2	323.6	323.9	324.2	324.6	324.9	325.2
125°	354.3	354.8	355.3	355.8	356.3	356.8	357.3	357.8	358.3	358.9	359.1
127.5°	386.6	387.2	387.8	388.4	389.0	389.6	390.3	391.0	391.8	392.5	392.7
130°	407.8	408.7	409.6	410.5	411.4	412.1	412.6	413.1	413.6	414.1	414.5
132.5°	429.9	430.6	431.3	432.0	432.7	433.3	433.9	434.5	435.2	435.9	436.1
135°	464.2	464.5	464.7	465.0	465.2	465.6	466.2	466.7	467.3	467.8	467.9
137.5°	494.5	495.0	495.5	496.0	496.6	497.1	497.6	498.1	498.7	499.2	498.9
140°	514.4	515.2	516.1	517.1	518.0	518.5	518.6	518.8	518.9	519.0	518.9
142.5°	534.6	535.3	536.0	536.7	537.5	537.9	538.0	538.1	538.3	538.4	538.2
145°	563.9	564.4	564.9	565.4	565.9	566.3	566.4	566.5	566.6	566.8	566.4
147.5°	590.0	590.8	591.5	592.3	593.0	593.4	593.4	593.4	593.4	593.4	593.1
150°	606.5	607.3	608.0	608.8	609.7	610.0	610.0	610.0	610.0	610.0	609.8
152.5°	622.7	623.4	624.0	624.7	625.3	625.6	625.4	625.2	624.9	624.7	624.6
155°	644.6	645.5	646.3	647.2	648.1	648.3	647.8	647.3	646.8	646.3	646.2
157.5°	664.5	665.2	665.9	666.6	667.3	667.4	666.9	666.4	665.8	665.3	665.2
160°	677.4	677.9	678.4	678.9	679.4	679.3	678.7	678.1	677.4	676.8	676.8
162.5°	687.1	687.9	688.7	689.5	690.3	690.4	689.8	689.1	688.5	687.9	687.8
165°	701.0	702.0	702.8	703.7	704.6	704.7	703.9	703.2	702.4	701.6	701.6
167.5°	712.9	713.7	714.5	715.3	716.1	716.1	715.3	714.5	713.7	712.9	712.8
170°	718.8	719.7	720.6	721.5	722.5	722.5	721.5	720.6	719.7	718.8	718.8
172.5°	723.5	724.4	725.3	726.2	727.1	727.1	726.3	725.5	724.8	724.0	724.0
175°	728.6	729.5	730.4	731.3	732.3	732.4	731.5	730.7	730.0	729.2	729.2
177.5°	731.4	732.2	732.9	733.6	734.3	734.4	733.8	733.2	732.5	731.8	731.8
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1275.3	1273.9	1268.1	1261.3	1252.4	1246.5	1241.8	1239.3	1231.7	1222.3	1216.1
5°	1354.0	1338.2	1321.3	1300.6	1281.6	1262.0	1249.9	1235.6	1218.2	1198.6	1184.9
7.5°	1438.5	1407.3	1373.8	1339.3	1305.0	1274.4	1247.4	1224.2	1196.4	1168.3	1148.7
10°	1503.2	1457.6	1410.6	1362.5	1318.6	1277.4	1245.7	1214.5	1181.1	1148.9	1124.6
12.5°	1562.0	1502.1	1447.8	1388.8	1332.6	1283.3	1237.6	1200.9	1160.8	1126.5	1098.7
15°	1636.4	1575.1	1509.4	1419.6	1345.0	1282.6	1227.2	1179.0	1130.4	1088.1	1061.2
17.5°	1706.0	1613.7	1525.6	1450.6	1353.7	1275.8	1208.0	1150.4	1097.1	1052.3	1019.1
20°	1734.7	1645.4	1549.6	1454.0	1358.8	1271.5	1192.8	1129.3	1073.8	1023.1	992.4
22.5°	1752.0	1650.8	1550.0	1447.2	1346.2	1255.5	1177.6	1107.7	1047.6	999.4	961.5
25°	1772.2	1651.7	1540.7	1439.2	1336.1	1237.7	1145.2	1071.2	1006.1	954.8	914.6
27.5°	1785.5	1643.8	1512.6	1399.7	1295.2	1197.2	1112.4	1034.0	968.0	913.7	870.6
30°	1788.1	1637.4	1491.0	1368.9	1262.5	1172.7	1082.8	1007.7	938.0	880.3	840.1
32.5°	1791.5	1621.7	1461.8	1332.0	1223.2	1134.2	1052.8	981.1	909.6	852.8	811.8
35°	1777.6	1613.2	1417.4	1268.4	1159.4	1073.3	999.8	933.7	863.4	808.4	766.6
37.5°	1717.5	1578.7	1371.6	1196.7	1082.8	1003.0	943.1	885.4	821.0	761.6	722.4
40°	1657.0	1544.9	1336.1	1153.2	1034.2	952.2	898.3	851.2	788.8	733.4	691.1
42.5°	1566.9	1498.8	1302.2	1107.4	979.2	900.2	854.7	810.6	755.9	699.5	659.7
45°	1401.6	1410.6	1232.9	1034.7	903.0	823.7	780.9	750.2	701.7	655.1	614.4
47.5°	1194.4	1278.4	1151.7	957.2	822.7	748.3	710.9	684.2	651.4	605.7	568.6
50°	1059.0	1179.0	1086.5	905.1	772.4	698.4	661.5	639.7	611.2	575.2	539.8
52.5°	934.2	1063.2	1007.8	847.2	717.9	650.3	614.1	596.2	573.5	539.7	507.7
55°	761.8	892.5	879.8	759.7	636.0	575.2	547.8	527.7	512.3	487.0	461.6
57.5°	616.3	740.1	746.7	662.5	563.9	503.8	480.2	465.0	455.0	435.9	412.4
60°	524.5	638.1	660.4	596.9	512.3	459.5	436.2	424.0	416.1	400.8	382.8
62.5°	448.4	545.1	570.3	524.6	462.8	413.3	395.2	383.4	378.0	364.8	348.9
65°	343.2	423.5	447.8	422.4	390.2	350.5	335.8	325.7	320.9	313.6	301.8
67.5°	258.0	316.6	343.3	325.4	313.8	288.7	279.2	273.9	269.6	264.6	254.9
70°	207.2	250.6	278.1	273.4	263.9	250.6	243.8	240.0	235.8	231.6	223.1
72.5°	166.6	196.5	222.3	224.7	216.9	214.2	208.2	206.6	204.1	199.0	194.4
75°	110.5	131.1	149.1	155.9	159.2	161.8	159.2	158.6	158.0	153.9	151.2
77.5°	72.4	83.5	94.8	106.5	111.6	115.1	116.0	118.0	116.5	114.3	113.0
80°	55.5	58.2	66.0	76.1	84.0	87.3	89.4	90.4	89.9	89.4	87.3
82.5°	40.3	42.5	46.3	53.3	60.0	65.2	66.6	66.3	67.5	67.8	66.0
85°	21.7	22.2	23.2	24.3	28.0	33.8	35.4	36.5	37.6	37.6	34.3
87.5°	8.9	8.1	8.6	8.3	9.4	9.5	11.8	13.6	14.3	12.9	13.1
90°	10.5	8.8	7.2	5.7	4.4	3.1	1.8	0.6	1.8	3.1	4.4
92.5°	20.2	19.3	18.4	17.5	16.6	15.7	14.8	13.9	14.8	15.7	16.6
95°	40.6	39.6	38.6	37.6	36.7	35.7	34.8	34.0	34.8	35.7	36.7
97.5°	65.2	64.4	63.7	63.0	62.4	61.7	61.0	60.4	61.0	61.7	62.4
100°	83.4	82.7	82.1	81.4	80.7	79.9	79.1	78.4	79.1	79.9	80.7
102.5°	103.3	102.4	101.6	100.9	100.5	100.0	99.6	99.1	99.6	100.0	100.5
105°	133.6	132.5	131.3	130.7	130.4	130.1	129.9	129.6	129.9	130.1	130.4
107.5°	166.9	166.4	166.0	165.7	165.5	165.4	165.2	165.1	165.2	165.4	165.5
110°	189.0	188.7	188.4	188.2	187.9	187.7	187.4	187.2	187.4	187.7	187.9





TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	211.1	211.1	211.0	210.9	210.7	210.6	210.4	210.3	210.4	210.6	210.7
115°	245.9	246.1	246.4	246.3	246.0	245.6	245.2	244.8	245.2	245.6	246.0
117.5°	279.9	280.2	280.5	280.6	280.3	280.1	279.8	279.6	279.8	280.1	280.3
120°	303.2	303.8	304.4	304.4	303.6	302.8	302.1	301.2	302.1	302.8	303.6
122.5°	325.6	325.9	326.2	326.1	325.5	325.0	324.4	323.9	324.4	325.0	325.5
125°	359.4	359.6	359.9	359.8	359.4	359.0	358.7	358.3	358.7	359.0	359.4
127.5°	393.0	393.3	393.6	393.3	392.5	391.7	390.9	390.1	390.9	391.7	392.5
130°	415.0	415.4	415.7	415.4	414.3	413.3	412.3	411.3	412.3	413.3	414.3
132.5°	436.4	436.7	437.0	436.6	435.6	434.5	433.5	432.4	433.5	434.5	435.6
135°	468.0	468.1	468.3	467.9	467.2	466.4	465.6	464.8	465.6	466.4	467.2
137.5°	498.5	498.2	497.9	497.4	496.8	496.0	495.4	494.8	495.4	496.0	496.8
140°	518.8	518.6	518.5	518.1	517.5	516.8	516.1	515.5	516.1	516.8	517.5
142.5°	537.9	537.7	537.5	536.9	536.3	535.7	535.0	534.4	535.0	535.7	536.3
145°	566.0	565.6	565.2	564.9	564.7	564.4	564.2	563.9	564.2	564.4	564.7
147.5°	592.7	592.4	592.0	591.6	591.1	590.7	590.2	589.8	590.2	590.7	591.1
150°	609.5	609.3	608.9	608.7	608.4	608.2	607.9	607.7	607.9	608.2	608.4
152.5°	624.4	624.3	624.1	623.9	623.5	623.2	622.8	622.5	622.8	623.2	623.5
155°	646.0	645.9	645.8	645.7	645.7	645.7	645.7	645.7	645.7	645.7	645.7
157.5°	665.1	665.0	664.9	664.9	665.1	665.2	665.4	665.5	665.4	665.2	665.1
160°	676.8	676.8	676.8	676.9	677.2	677.4	677.7	677.9	677.7	677.4	677.2
162.5°	687.7	687.6	687.5	687.6	687.9	688.3	688.6	689.0	688.6	688.3	687.9
165°	701.6	701.6	701.6	701.8	702.2	702.6	703.0	703.3	703.0	702.6	702.2
167.5°	712.7	712.6	712.5	712.7	713.2	713.7	714.2	714.7	714.2	713.7	713.2
170°	718.8	718.8	718.8	719.1	719.6	720.1	720.6	721.1	720.6	720.1	719.6
172.5°	724.0	724.0	724.0	724.2	724.7	725.2	725.7	726.2	725.7	725.2	724.7
175°	729.2	729.2	729.2	729.5	730.0	730.5	731.0	731.5	731.0	730.5	730.0
177.5°	731.8	731.8	731.8	732.1	732.5	733.0	733.4	733.8	733.4	733.0	732.5
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1214.0	1208.4	1204.7	1196.2	1190.6	1184.8	1178.8	1182.7	1182.2	1181.7	1181.7
5°	1173.3	1161.0	1149.9	1135.7	1126.7	1115.6	1107.1	1106.1	1108.2	1100.8	1096.5
7.5°	1132.9	1116.2	1100.4	1084.7	1068.0	1054.7	1046.3	1042.4	1037.0	1032.5	1027.7
10°	1104.5	1084.9	1069.5	1050.1	1032.1	1016.2	1006.1	999.3	995.5	991.9	985.0
12.5°	1075.3	1056.1	1036.6	1014.5	997.3	979.0	971.5	963.7	956.6	952.5	943.1
15°	1032.6	1007.7	987.1	963.8	944.8	926.9	916.3	900.9	898.8	893.5	884.0
17.5°	989.8	962.8	934.3	917.2	895.6	877.0	860.8	855.7	840.5	834.9	826.6
20°	955.9	931.1	909.4	886.7	855.5	838.0	825.4	818.5	806.3	798.9	793.6
22.5°	926.8	901.5	876.4	849.9	824.2	804.6	795.3	784.6	778.0	767.6	761.8
25°	885.0	857.6	827.5	798.9	780.4	765.6	750.7	741.2	731.7	727.0	716.4
27.5°	836.7	807.9	779.7	758.1	735.4	720.7	707.3	698.8	687.4	679.4	673.6
30°	810.0	776.2	751.8	732.3	703.2	689.4	679.4	668.8	660.4	651.9	646.1
32.5°	779.1	748.2	725.2	700.9	678.6	663.7	650.7	641.4	634.1	626.1	620.3
35°	730.6	704.8	681.0	656.6	640.3	624.9	609.7	601.7	594.8	587.4	582.1
37.5°	686.9	662.7	640.1	617.0	596.7	584.2	571.9	565.8	556.5	551.6	546.1
40°	659.8	636.0	611.7	589.6	568.4	558.9	547.8	538.8	530.3	526.6	520.8
42.5°	630.3	606.4	585.9	562.0	544.7	531.8	521.5	511.7	505.3	500.0	496.7
45°	586.3	565.2	545.1	521.3	504.9	493.8	482.2	473.2	467.4	463.7	457.9
47.5°	543.7	522.6	502.2	481.4	465.5	452.9	441.3	435.0	427.3	422.7	418.9
50°	512.8	493.8	472.1	453.1	437.3	424.5	415.1	407.1	400.2	394.5	391.8
52.5°	484.5	464.2	445.5	427.8	411.0	396.7	388.0	379.6	374.5	367.8	364.7
55°	437.8	418.2	402.3	384.9	368.5	356.4	345.8	338.4	333.1	325.7	321.4
57.5°	393.8	376.4	357.4	342.2	325.4	315.1	306.3	296.3	289.8	284.1	279.9
60°	364.3	344.2	327.8	313.6	298.7	285.5	277.6	269.6	262.8	256.9	253.3
62.5°	333.5	315.9	300.3	284.8	271.2	259.7	250.5	243.9	237.8	234.1	230.5
65°	286.0	272.3	256.4	243.8	231.1	222.6	215.2	209.3	205.1	202.5	199.3
67.5°	242.5	229.1	215.3	202.8	194.4	187.9	183.1	178.0	175.9	172.6	170.5
70°	214.1	200.4	188.2	178.7	170.3	165.5	162.3	158.6	156.5	152.3	150.2
72.5°	183.3	173.3	164.5	156.7	150.0	145.6	141.6	137.0	133.7	129.0	126.9
75°	144.3	135.3	128.5	123.2	119.0	113.1	107.3	102.6	101.0	99.4	98.9
77.5°	106.9	101.2	96.2	91.8	86.5	82.3	81.0	80.0	79.6	78.8	78.8
80°	84.0	78.8	75.0	69.8	66.7	66.7	66.7	65.5	66.0	66.0	66.0
82.5°	62.5	57.7	55.6	53.7	53.1	53.5	53.5	53.7	53.4	54.2	53.8
85°	32.2	32.8	33.8	33.3	33.8	33.8	34.9	34.3	34.9	33.8	34.9
87.5°	13.0	14.5	15.3	16.1	16.8	16.8	17.3	17.4	17.9	18.0	18.1
90°	5.7	7.2	8.8	10.5	12.1	13.8	14.3	14.8	15.3	15.9	16.3
92.5°	17.5	18.4	19.3	20.2	21.2	22.1	22.5	22.9	23.3	23.7	23.9
95°	37.6	38.6	39.6	40.6	41.6	42.6	43.1	43.6	44.1	44.6	44.9
97.5°	63.0	63.7	64.4	65.2	65.9	66.8	67.3	67.9	68.5	69.1	69.3
100°	81.4	82.1	82.7	83.4	84.0	84.6	85.0	85.4	85.8	86.2	86.5
102.5°	100.9	101.6	102.4	103.3	104.1	104.9	105.3	105.7	106.1	106.4	106.6
105°	130.7	131.3	132.5	133.6	134.8	135.9	135.9	135.9	135.9	135.9	136.0
107.5°	165.7	166.0	166.4	166.9	167.4	167.8	168.2	168.6	169.1	169.5	169.7
110°	188.2	188.4	188.7	189.0	189.2	189.6	190.1	190.6	191.1	191.6	191.7



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	210.9	211.0	211.1	211.1	211.2	211.2	211.8	212.4	213.0	213.6	213.9
115°	246.3	246.4	246.1	245.9	245.6	245.4	245.5	245.6	245.8	245.9	245.9
117.5°	280.6	280.5	280.2	279.9	279.6	279.2	279.2	279.2	279.1	279.1	278.9
120°	304.4	304.4	303.8	303.2	302.5	301.8	301.7	301.5	301.4	301.3	301.1
122.5°	326.1	326.2	325.9	325.6	325.2	324.9	324.6	324.2	323.9	323.6	323.2
125°	359.8	359.9	359.6	359.4	359.1	358.9	358.3	357.8	357.3	356.8	356.3
127.5°	393.3	393.6	393.3	393.0	392.7	392.5	391.8	391.0	390.3	389.6	389.0
130°	415.4	415.7	415.4	415.0	414.5	414.1	413.6	413.1	412.6	412.1	411.4
132.5°	436.6	437.0	436.7	436.4	436.1	435.9	435.2	434.5	433.9	433.3	432.7
135°	467.9	468.3	468.1	468.0	467.9	467.8	467.3	466.7	466.2	465.6	465.2
137.5°	497.4	497.9	498.2	498.5	498.9	499.2	498.7	498.1	497.6	497.1	496.6
140°	518.1	518.5	518.6	518.8	518.9	519.0	518.9	518.8	518.6	518.5	518.0
142.5°	536.9	537.5	537.7	537.9	538.2	538.4	538.3	538.1	538.0	537.9	537.5
145°	564.9	565.2	565.6	566.0	566.4	566.8	566.6	566.5	566.4	566.3	565.9
147.5°	591.6	592.0	592.4	592.7	593.1	593.4	593.4	593.4	593.4	593.4	593.0
150°	608.7	608.9	609.3	609.5	609.8	610.0	610.0	610.0	610.0	610.0	609.7
152.5°	623.9	624.1	624.3	624.4	624.6	624.7	624.9	625.2	625.4	625.6	625.3
155°	645.7	645.8	645.9	646.0	646.2	646.3	646.8	647.3	647.8	648.3	648.1
157.5°	664.9	664.9	665.0	665.1	665.2	665.3	665.8	666.4	666.9	667.4	667.3
160°	676.9	676.8	676.8	676.8	676.8	676.8	677.4	678.1	678.7	679.3	679.4
162.5°	687.6	687.5	687.6	687.7	687.8	687.9	688.5	689.1	689.8	690.4	690.3
165°	701.8	701.6	701.6	701.6	701.6	701.6	702.4	703.2	703.9	704.7	704.6
167.5°	712.7	712.5	712.6	712.7	712.8	712.9	713.7	714.5	715.3	716.1	716.1
170°	719.1	718.8	718.8	718.8	718.8	718.8	719.7	720.6	721.5	722.5	722.5
172.5°	724.2	724.0	724.0	724.0	724.0	724.0	724.8	725.5	726.3	727.1	727.1
175°	729.5	729.2	729.2	729.2	729.2	729.2	730.0	730.7	731.5	732.4	732.3
177.5°	732.1	731.8	731.8	731.8	731.8	731.8	732.5	733.2	733.8	734.4	734.3
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1176.7	1176.3	1176.7	1175.0	1176.7	1176.3	1176.7	1181.7	1181.7	1182.2	1182.7
5°	1095.0	1094.4	1092.9	1088.1	1092.9	1094.4	1095.0	1096.5	1100.8	1108.2	1106.1
7.5°	1023.6	1022.9	1018.2	1018.3	1018.2	1022.9	1023.6	1027.7	1032.5	1037.0	1042.4
10°	981.3	981.8	975.5	971.8	975.5	981.8	981.3	985.0	991.9	995.5	999.3
12.5°	940.3	937.9	932.7	928.7	932.7	937.9	940.3	943.1	952.5	956.6	963.7
15°	886.2	880.8	868.2	869.2	868.2	880.8	886.2	884.0	893.5	898.8	900.9
17.5°	822.3	818.5	818.2	810.8	818.2	818.5	822.3	826.6	834.9	840.5	855.7
20°	785.2	782.5	783.6	776.2	783.6	782.5	785.2	793.6	798.9	806.3	818.5
22.5°	756.0	753.4	748.9	746.6	748.9	753.4	756.0	761.8	767.6	778.0	784.6
25°	713.3	709.0	704.8	707.4	704.8	709.0	713.3	716.4	727.0	731.7	741.2
27.5°	670.6	667.3	663.1	662.6	663.1	667.3	670.6	673.6	679.4	687.4	698.8
30°	643.5	640.3	638.1	635.5	638.1	640.3	643.5	646.1	651.9	660.4	668.8
32.5°	615.9	615.3	611.5	611.0	611.5	615.3	615.9	620.3	626.1	634.1	641.4
35°	580.0	576.8	575.7	576.3	575.7	576.8	580.0	582.1	587.4	594.8	601.7
37.5°	545.8	541.6	539.7	537.9	539.7	541.6	545.8	546.1	551.6	556.5	565.8
40°	521.3	517.1	516.0	514.9	516.0	517.1	521.3	520.8	526.6	530.3	538.8
42.5°	493.8	492.1	491.5	489.6	491.5	492.1	493.8	496.7	500.0	505.3	511.7
45°	456.3	455.8	452.6	453.6	452.6	455.8	456.3	457.9	463.7	467.4	473.2
47.5°	416.8	414.4	412.2	413.6	412.2	414.4	416.8	418.9	422.7	427.3	435.0
50°	389.7	388.6	383.8	384.9	383.8	388.6	389.7	391.8	394.5	400.2	407.1
52.5°	362.6	358.6	356.8	356.2	356.8	358.6	362.6	364.7	367.8	374.5	379.6
55°	317.8	313.0	310.8	309.8	310.8	313.0	317.8	321.4	325.7	333.1	338.4
57.5°	273.8	272.5	270.8	272.0	270.8	272.5	273.8	279.9	284.1	289.8	296.3
60°	247.9	247.9	247.9	247.4	247.9	247.9	247.9	253.3	256.9	262.8	269.6
62.5°	228.1	226.8	226.4	227.1	226.4	226.8	228.1	230.5	234.1	237.8	243.9
65°	197.7	197.2	195.1	194.6	195.1	197.2	197.7	199.3	202.5	205.1	209.3
67.5°	169.1	167.1	166.5	165.8	166.5	167.1	169.1	170.5	172.6	175.9	178.0
70°	147.5	146.4	143.3	143.8	143.3	146.4	147.5	150.2	152.3	156.5	158.6
72.5°	124.2	123.2	122.6	121.8	122.6	123.2	124.2	126.9	129.0	133.7	137.0
75°	98.4	97.9	97.3	99.4	97.3	97.9	98.4	98.9	99.4	101.0	102.6
77.5°	78.8	78.8	79.1	78.3	79.1	78.8	78.8	78.8	78.8	79.6	80.0
80°	66.0	66.0	65.5	65.5	65.5	66.0	66.0	66.0	66.0	66.0	65.5
82.5°	53.0	53.4	53.7	52.9	53.7	53.4	53.0	53.8	54.2	53.4	53.7
85°	34.9	34.3	35.4	34.9	35.4	34.3	34.9	34.9	33.8	34.9	34.3
87.5°	19.0	18.2	18.2	18.7	18.2	18.2	19.0	18.1	18.0	17.9	17.4
90°	16.6	16.8	17.1	17.3	17.1	16.8	16.6	16.3	15.9	15.3	14.8
92.5°	23.7	23.5	23.4	23.2	23.4	23.5	23.7	23.9	23.7	23.3	22.9
95°	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.6	44.1	43.6
97.5°	69.3	69.2	69.2	69.1	69.2	69.2	69.3	69.3	69.1	68.5	67.9
100°	86.7	87.1	87.3	87.6	87.3	87.1	86.7	86.5	86.2	85.8	85.4
102.5°	106.6	106.5	106.5	106.4	106.5	106.5	106.6	106.6	106.4	106.1	105.7
105°	136.3	136.5	136.8	137.1	136.8	136.5	136.3	136.0	135.9	135.9	135.9
107.5°	169.5	169.4	169.2	169.1	169.2	169.4	169.5	169.7	169.5	169.1	168.6
110°	191.5	191.2	191.0	190.7	191.0	191.2	191.5	191.7	191.6	191.1	190.6



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	213.9	213.8	213.8	213.7	213.8	213.8	213.9	213.9	213.6	213.0	212.4
115°	245.8	245.6	245.5	245.4	245.5	245.6	245.8	245.9	245.9	245.8	245.6
117.5°	278.6	278.2	277.9	277.5	277.9	278.2	278.6	278.9	279.1	279.1	279.2
120°	300.8	300.6	300.3	300.1	300.3	300.6	300.8	301.1	301.3	301.4	301.5
122.5°	322.9	322.4	322.1	321.7	322.1	322.4	322.9	323.2	323.6	323.9	324.2
125°	355.8	355.3	354.8	354.3	354.8	355.3	355.8	356.3	356.8	357.3	357.8
127.5°	388.4	387.8	387.2	386.6	387.2	387.8	388.4	389.0	389.6	390.3	391.0
130°	410.5	409.6	408.7	407.8	408.7	409.6	410.5	411.4	412.1	412.6	413.1
132.5°	432.0	431.3	430.6	429.9	430.6	431.3	432.0	432.7	433.3	433.9	434.5
135°	465.0	464.7	464.5	464.2	464.5	464.7	465.0	465.2	465.6	466.2	466.7
137.5°	496.0	495.5	495.0	494.5	495.0	495.5	496.0	496.6	497.1	497.6	498.1
140°	517.1	516.1	515.2	514.4	515.2	516.1	517.1	518.0	518.5	518.6	518.8
142.5°	536.7	536.0	535.3	534.6	535.3	536.0	536.7	537.5	537.9	538.0	538.1
145°	565.4	564.9	564.4	563.9	564.4	564.9	565.4	565.9	566.3	566.4	566.5
147.5°	592.3	591.5	590.8	590.0	590.8	591.5	592.3	593.0	593.4	593.4	593.4
150°	608.8	608.0	607.3	606.5	607.3	608.0	608.8	609.7	610.0	610.0	610.0
152.5°	624.7	624.0	623.4	622.7	623.4	624.0	624.7	625.3	625.6	625.4	625.2
155°	647.2	646.3	645.5	644.6	645.5	646.3	647.2	648.1	648.3	647.8	647.3
157.5°	666.6	665.9	665.2	664.5	665.2	665.9	666.6	667.3	667.4	666.9	666.4
160°	678.9	678.4	677.9	677.4	677.9	678.4	678.9	679.4	679.3	678.7	678.1
162.5°	689.5	688.7	687.9	687.1	687.9	688.7	689.5	690.3	690.4	689.8	689.1
165°	703.7	702.8	702.0	701.0	702.0	702.8	703.7	704.6	704.7	703.9	703.2
167.5°	715.3	714.5	713.7	712.9	713.7	714.5	715.3	716.1	716.1	715.3	714.5
170°	721.5	720.6	719.7	718.8	719.7	720.6	721.5	722.5	722.5	721.5	720.6
172.5°	726.2	725.3	724.4	723.5	724.4	725.3	726.2	727.1	727.1	726.3	725.5
175°	731.3	730.4	729.5	728.6	729.5	730.4	731.3	732.3	732.4	731.5	730.7
177.5°	733.6	732.9	732.2	731.4	732.2	732.9	733.6	734.3	734.4	733.8	733.2
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1178.8	1184.8	1190.6	1196.2	1204.7	1208.4	1214.0	1216.1	1222.3	1231.7	1239.3
5°	1107.1	1115.6	1126.7	1135.7	1149.9	1161.0	1173.3	1184.9	1198.6	1218.2	1235.6
7.5°	1046.3	1054.7	1068.0	1084.7	1100.4	1116.2	1132.9	1148.7	1168.3	1196.4	1224.2
10°	1006.1	1016.2	1032.1	1050.1	1069.5	1084.9	1104.5	1124.6	1148.9	1181.1	1214.5
12.5°	971.5	979.0	997.3	1014.5	1036.6	1056.1	1075.3	1098.7	1126.5	1160.8	1200.9
15°	916.3	926.9	944.8	963.8	987.1	1007.7	1032.6	1061.2	1088.1	1130.4	1179.0
17.5°	860.8	877.0	895.6	917.2	934.3	962.8	989.8	1019.1	1052.3	1097.1	1150.4
20°	825.4	838.0	855.5	886.7	909.4	931.1	955.9	992.4	1023.1	1073.8	1129.3
22.5°	795.3	804.6	824.2	849.9	876.4	901.5	926.8	961.5	999.4	1047.6	1107.7
25°	750.7	765.6	780.4	798.9	827.5	857.6	885.0	914.6	954.8	1006.1	1071.2
27.5°	707.3	720.7	735.4	758.1	779.7	807.9	836.7	870.6	913.7	968.0	1034.0
30°	679.4	689.4	703.2	732.3	751.8	776.2	810.0	840.1	880.3	938.0	1007.7
32.5°	650.7	663.7	678.6	700.9	725.2	748.2	779.1	811.8	852.8	909.6	981.1
35°	609.7	624.9	640.3	656.6	681.0	704.8	730.6	766.6	808.4	863.4	933.7
37.5°	571.9	584.2	596.7	617.0	640.1	662.7	686.9	722.4	761.6	821.0	885.4
40°	547.8	558.9	568.4	589.6	611.7	636.0	659.8	691.1	733.4	788.8	851.2
42.5°	521.5	531.8	544.7	562.0	585.9	606.4	630.3	659.7	699.5	755.9	810.6
45°	482.2	493.8	504.9	521.3	545.1	565.2	586.3	614.4	655.1	701.7	750.2
47.5°	441.3	452.9	465.5	481.4	502.2	522.6	543.7	568.6	605.7	651.4	684.2
50°	415.1	424.5	437.3	453.1	472.1	493.8	512.8	539.8	575.2	611.2	639.7
52.5°	388.0	396.7	411.0	427.8	445.5	464.2	484.5	507.7	539.7	573.5	596.2
55°	345.8	356.4	368.5	384.9	402.3	418.2	437.8	461.6	487.0	512.3	527.7
57.5°	306.3	315.1	325.4	342.2	357.4	376.4	393.8	412.4	435.9	455.0	465.0
60°	277.6	285.5	298.7	313.6	327.8	344.2	364.3	382.8	400.8	416.1	424.0
62.5°	250.5	259.7	271.2	284.8	300.3	315.9	333.5	348.9	364.8	378.0	383.4
65°	215.2	222.6	231.1	243.8	256.4	272.3	286.0	301.8	313.6	320.9	325.7
67.5°	183.1	187.9	194.4	202.8	215.3	229.1	242.5	254.9	264.6	269.6	273.9
70°	162.3	165.5	170.3	178.7	188.2	200.4	214.1	223.1	231.6	235.8	240.0
72.5°	141.6	145.6	150.0	156.7	164.5	173.3	183.3	194.4	199.0	204.1	206.6
75°	107.3	113.1	119.0	123.2	128.5	135.3	144.3	151.2	153.9	158.0	158.6
77.5°	81.0	82.3	86.5	91.8	96.2	101.2	106.9	113.0	114.3	116.5	118.0
80°	66.7	66.7	66.7	69.8	75.0	78.8	84.0	87.3	89.4	89.9	90.4
82.5°	53.5	53.5	53.1	53.7	55.6	57.7	62.5	66.0	67.8	67.5	66.3
85°	34.9	33.8	33.8	33.3	33.8	32.8	32.2	34.3	37.6	37.6	36.5
87.5°	17.3	16.8	16.8	16.1	15.3	14.5	13.0	13.1	12.9	14.3	13.6
90°	14.3	13.8	12.1	10.5	8.8	7.2	5.7	4.4	3.1	1.8	0.6
92.5°	22.5	22.1	21.2	20.2	19.3	18.4	17.5	16.6	15.7	14.8	13.9
95°	43.1	42.6	41.6	40.6	39.6	38.6	37.6	36.7	35.7	34.8	34.0
97.5°	67.3	66.8	65.9	65.2	64.4	63.7	63.0	62.4	61.7	61.0	60.4
100°	85.0	84.6	84.0	83.4	82.7	82.1	81.4	80.7	79.9	79.1	78.4
102.5°	105.3	104.9	104.1	103.3	102.4	101.6	100.9	100.5	100.0	99.6	99.1
105°	135.9	135.9	134.8	133.6	132.5	131.3	130.7	130.4	130.1	129.9	129.6
107.5°	168.2	167.8	167.4	166.9	166.4	166.0	165.7	165.5	165.4	165.2	165.1
110°	190.1	189.6	189.2	189.0	188.7	188.4	188.2	187.9	187.7	187.4	187.2



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	211.8	211.2	211.2	211.1	211.1	211.0	210.9	210.7	210.6	210.4	210.3
115°	245.5	245.4	245.6	245.9	246.1	246.4	246.3	246.0	245.6	245.2	244.8
117.5°	279.2	279.2	279.6	279.9	280.2	280.5	280.6	280.3	280.1	279.8	279.6
120°	301.7	301.8	302.5	303.2	303.8	304.4	304.4	303.6	302.8	302.1	301.2
122.5°	324.6	324.9	325.2	325.6	325.9	326.2	326.1	325.5	325.0	324.4	323.9
125°	358.3	358.9	359.1	359.4	359.6	359.9	359.8	359.4	359.0	358.7	358.3
127.5°	391.8	392.5	392.7	393.0	393.3	393.6	393.3	392.5	391.7	390.9	390.1
130°	413.6	414.1	414.5	415.0	415.4	415.7	415.4	414.3	413.3	412.3	411.3
132.5°	435.2	435.9	436.1	436.4	436.7	437.0	436.6	435.6	434.5	433.5	432.4
135°	467.3	467.8	467.9	468.0	468.1	468.3	467.9	467.2	466.4	465.6	464.8
137.5°	498.7	499.2	498.9	498.5	498.2	497.9	497.4	496.8	496.0	495.4	494.8
140°	518.9	519.0	518.9	518.8	518.6	518.5	518.1	517.5	516.8	516.1	515.5
142.5°	538.3	538.4	538.2	537.9	537.7	537.5	536.9	536.3	535.7	535.0	534.4
145°	566.6	566.8	566.4	566.0	565.6	565.2	564.9	564.7	564.4	564.2	563.9
147.5°	593.4	593.4	593.1	592.7	592.4	592.0	591.6	591.1	590.7	590.2	589.8
150°	610.0	610.0	609.8	609.5	609.3	608.9	608.7	608.4	608.2	607.9	607.7
152.5°	624.9	624.7	624.6	624.4	624.3	624.1	623.9	623.5	623.2	622.8	622.5
155°	646.8	646.3	646.2	646.0	645.9	645.8	645.7	645.7	645.7	645.7	645.7
157.5°	665.8	665.3	665.2	665.1	665.0	664.9	664.9	665.1	665.2	665.4	665.5
160°	677.4	676.8	676.8	676.8	676.8	676.8	676.9	677.2	677.4	677.7	677.9
162.5°	688.5	687.9	687.8	687.7	687.6	687.5	687.6	687.9	688.3	688.6	689.0
165°	702.4	701.6	701.6	701.6	701.6	701.6	701.8	702.2	702.6	703.0	703.3
167.5°	713.7	712.9	712.8	712.7	712.6	712.5	712.7	713.2	713.7	714.2	714.7
170°	719.7	718.8	718.8	718.8	718.8	718.8	719.1	719.6	720.1	720.6	721.1
172.5°	724.8	724.0	724.0	724.0	724.0	724.0	724.2	724.7	725.2	725.7	726.2
175°	730.0	729.2	729.2	729.2	729.2	729.2	729.5	730.0	730.5	731.0	731.5
177.5°	732.5	731.8	731.8	731.8	731.8	731.8	732.1	732.5	733.0	733.4	733.8
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1241.8	1246.5	1252.4	1261.3	1268.1	1273.9	1275.3	1277.0	1281.2	1288.4	1293.8
5°	1249.9	1262.0	1281.6	1300.6	1321.3	1338.2	1354.0	1365.1	1375.7	1398.0	1415.9
7.5°	1247.4	1274.4	1305.0	1339.3	1373.8	1407.3	1438.5	1466.2	1493.9	1526.3	1563.2
10°	1245.7	1277.4	1318.6	1362.5	1410.6	1457.6	1503.2	1538.5	1579.8	1616.8	1663.9
12.5°	1237.6	1283.3	1332.6	1388.8	1447.8	1502.1	1562.0	1610.9	1658.1	1711.5	1766.3
15°	1227.2	1282.6	1345.0	1419.6	1509.4	1575.1	1636.4	1721.5	1779.7	1837.9	1916.0
17.5°	1208.0	1275.8	1353.7	1450.6	1525.6	1613.7	1706.0	1773.2	1851.6	1933.5	2004.4
20°	1192.8	1271.5	1358.8	1454.0	1549.6	1645.4	1734.7	1815.0	1896.0	1990.6	2048.8
22.5°	1177.6	1255.5	1346.2	1447.2	1550.0	1650.8	1752.0	1846.3	1937.4	2033.0	2107.2
25°	1145.2	1237.7	1336.1	1439.2	1540.7	1651.7	1772.2	1877.4	1990.0	2088.4	2158.8
27.5°	1112.4	1197.2	1295.2	1399.7	1512.6	1643.8	1785.5	1905.2	2018.0	2088.4	2110.5
30°	1082.8	1172.7	1262.5	1368.9	1491.0	1637.4	1788.1	1925.0	2017.6	2048.2	2025.5
32.5°	1052.8	1134.2	1223.2	1332.0	1461.8	1621.7	1791.5	1913.2	1968.9	1945.5	1852.9
35°	999.8	1073.3	1159.4	1268.4	1417.4	1613.2	1777.6	1860.0	1846.2	1714.0	1539.6
37.5°	943.1	1003.0	1082.8	1196.7	1371.6	1578.7	1717.5	1729.6	1610.6	1407.8	1206.2
40°	898.3	952.2	1034.2	1153.2	1336.1	1544.9	1657.0	1607.8	1423.3	1197.5	1029.5
42.5°	854.7	900.2	979.2	1107.4	1302.2	1498.8	1566.9	1459.8	1246.9	1033.4	880.5
45°	780.9	823.7	903.0	1034.7	1232.9	1410.6	1401.6	1215.5	1002.5	830.6	703.7
47.5°	710.9	748.3	822.7	957.2	1151.7	1278.4	1194.4	996.3	815.6	677.7	587.2
50°	661.5	698.4	772.4	905.1	1086.5	1179.0	1059.0	868.2	702.7	588.4	516.5
52.5°	614.1	650.3	717.9	847.2	1007.8	1063.2	934.2	757.3	619.4	520.8	459.0
55°	547.8	575.2	636.0	759.7	879.8	892.5	761.8	613.8	500.2	431.4	389.1
57.5°	480.2	503.8	563.9	662.5	746.7	740.1	616.3	488.2	411.6	360.6	329.9
60°	436.2	459.5	512.3	596.9	660.4	638.1	524.5	421.4	355.8	318.3	294.0
62.5°	395.2	413.3	462.8	524.6	570.3	545.1	448.4	363.0	311.0	279.3	260.1
65°	335.8	350.5	390.2	422.4	447.8	423.5	343.2	283.9	246.4	224.2	211.0
67.5°	279.2	288.7	313.8	325.4	343.3	316.6	258.0	218.3	197.0	178.2	169.1
70°	243.8	250.6	263.9	273.4	278.1	250.6	207.2	178.1	160.2	146.9	141.2
72.5°	208.2	214.2	216.9	224.7	222.3	196.5	166.6	143.5	130.6	121.6	114.1
75°	159.2	161.8	159.2	155.9	149.1	131.1	110.5	98.9	89.4	85.1	82.5
77.5°	116.0	115.1	111.6	106.5	94.8	83.5	72.4	68.6	64.4	62.2	61.2
80°	89.4	87.3	84.0	76.1	66.0	58.2	55.5	52.9	51.3	48.7	48.1
82.5°	66.6	65.2	60.0	53.3	46.3	42.5	40.3	39.4	37.8	36.4	36.3
85°	35.4	33.8	28.0	24.3	23.2	22.2	21.7	21.7	19.6	19.0	19.0
87.5°	11.8	9.5	9.4	8.3	8.6	8.1	8.9	8.4	8.3	8.8	8.1
90°	1.8	3.1	4.4	5.7	7.2	8.8	10.5	12.1	13.8	14.3	14.8
92.5°	14.8	15.7	16.6	17.5	18.4	19.3	20.2	21.2	22.1	22.5	22.9
95°	34.8	35.7	36.7	37.6	38.6	39.6	40.6	41.6	42.6	43.1	43.6
97.5°	61.0	61.7	62.4	63.0	63.7	64.4	65.2	65.9	66.8	67.3	67.9
100°	79.1	79.9	80.7	81.4	82.1	82.7	83.4	84.0	84.6	85.0	85.4
102.5°	99.6	100.0	100.5	100.9	101.6	102.4	103.3	104.1	104.9	105.3	105.7
105°	129.9	130.1	130.4	130.7	131.3	132.5	133.6	134.8	135.9	135.9	135.9
107.5°	165.2	165.4	165.5	165.7	166.0	166.4	166.9	167.4	167.8	168.2	168.6
110°	187.4	187.7	187.9	188.2	188.4	188.7	189.0	189.2	189.6	190.1	190.6





TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	210.4	210.6	210.7	210.9	211.0	211.1	211.1	211.2	211.2	211.8	212.4
115°	245.2	245.6	246.0	246.3	246.4	246.1	245.9	245.6	245.4	245.5	245.6
117.5°	279.8	280.1	280.3	280.6	280.5	280.2	279.9	279.6	279.2	279.2	279.2
120°	302.1	302.8	303.6	304.4	304.4	303.8	303.2	302.5	301.8	301.7	301.5
122.5°	324.4	325.0	325.5	326.1	326.2	325.9	325.6	325.2	324.9	324.6	324.2
125°	358.7	359.0	359.4	359.8	359.9	359.6	359.4	359.1	358.9	358.3	357.8
127.5°	390.9	391.7	392.5	393.3	393.6	393.3	393.0	392.7	392.5	391.8	391.0
130°	412.3	413.3	414.3	415.4	415.7	415.4	415.0	414.5	414.1	413.6	413.1
132.5°	433.5	434.5	435.6	436.6	437.0	436.7	436.4	436.1	435.9	435.2	434.5
135°	465.6	466.4	467.2	467.9	468.3	468.1	468.0	467.9	467.8	467.3	466.7
137.5°	495.4	496.0	496.8	497.4	497.9	498.2	498.5	498.9	499.2	498.7	498.1
140°	516.1	516.8	517.5	518.1	518.5	518.6	518.8	518.9	519.0	518.9	518.8
142.5°	535.0	535.7	536.3	536.9	537.5	537.7	537.9	538.2	538.4	538.3	538.1
145°	564.2	564.4	564.7	564.9	565.2	565.6	566.0	566.4	566.8	566.6	566.5
147.5°	590.2	590.7	591.1	591.6	592.0	592.4	592.7	593.1	593.4	593.4	593.4
150°	607.9	608.2	608.4	608.7	608.9	609.3	609.5	609.8	610.0	610.0	610.0
152.5°	622.8	623.2	623.5	623.9	624.1	624.3	624.4	624.6	624.7	624.9	625.2
155°	645.7	645.7	645.7	645.7	645.8	645.9	646.0	646.2	646.3	646.8	647.3
157.5°	665.4	665.2	665.1	664.9	664.9	665.0	665.1	665.2	665.3	665.8	666.4
160°	677.7	677.4	677.2	676.9	676.8	676.8	676.8	676.8	676.8	677.4	678.1
162.5°	688.6	688.3	687.9	687.6	687.5	687.6	687.7	687.8	687.9	688.5	689.1
165°	703.0	702.6	702.2	701.8	701.6	701.6	701.6	701.6	701.6	702.4	703.2
167.5°	714.2	713.7	713.2	712.7	712.5	712.6	712.7	712.8	712.9	713.7	714.5
170°	720.6	720.1	719.6	719.1	718.8	718.8	718.8	718.8	718.8	719.7	720.6
172.5°	725.7	725.2	724.7	724.2	724.0	724.0	724.0	724.0	724.0	724.8	725.5
175°	731.0	730.5	730.0	729.5	729.2	729.2	729.2	729.2	729.2	730.0	730.7
177.5°	733.4	733.0	732.5	732.1	731.8	731.8	731.8	731.8	731.8	732.5	733.2
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1302.7	1302.7	1304.4	1310.8	1311.6	1317.2	1315.5
5°	1431.8	1441.8	1445.5	1461.4	1470.9	1475.1	1466.6
7.5°	1589.5	1617.9	1631.3	1647.9	1662.6	1667.1	1655.5
10°	1704.6	1734.1	1759.1	1774.3	1788.7	1798.2	1810.3
12.5°	1815.8	1852.2	1875.8	1897.4	1912.2	1924.2	1926.2
15°	1936.7	1991.7	2033.5	2064.1	2079.4	2087.4	2084.2
17.5°	2058.6	2109.6	2139.3	2170.6	2191.8	2192.9	2193.5
20°	2127.6	2177.3	2211.6	2234.8	2258.7	2257.7	2262.9
22.5°	2173.6	2212.8	2239.1	2256.0	2264.2	2260.2	2261.2
25°	2195.2	2206.9	2202.1	2175.1	2168.3	2143.4	2147.7
27.5°	2084.0	2029.0	1972.1	1899.0	1841.2	1795.1	1797.5
30°	1933.0	1835.7	1724.6	1631.6	1548.1	1524.8	1475.1
32.5°	1721.9	1576.0	1445.9	1359.2	1287.5	1268.1	1224.8
35°	1364.1	1222.3	1088.6	1008.2	976.5	932.1	931.6
37.5°	1060.3	935.5	864.7	804.5	772.8	746.0	743.4
40°	891.9	794.7	741.2	697.9	666.7	646.6	641.9
42.5°	774.4	695.7	645.7	618.8	594.8	584.4	576.7
45°	632.4	579.5	544.6	520.3	509.2	501.2	497.0
47.5°	529.0	493.5	469.7	453.5	444.5	436.2	438.4
50°	472.7	443.6	426.2	410.8	403.9	398.1	398.7
52.5°	427.4	401.3	387.2	376.2	367.6	363.5	361.4
55°	362.7	346.3	332.0	324.1	319.3	313.6	311.9
57.5°	309.4	296.7	285.1	276.1	274.9	269.3	270.0
60°	273.9	263.3	253.8	249.0	245.3	240.5	242.2
62.5°	244.7	235.8	227.1	223.2	219.5	216.0	216.8
65°	200.4	191.9	186.6	184.5	182.9	181.4	179.8
67.5°	159.7	154.5	151.2	146.6	143.4	142.9	141.3
70°	134.3	127.4	121.6	115.8	114.2	113.7	114.2
72.5°	107.7	103.3	101.7	98.9	98.6	97.1	98.2
75°	80.9	79.3	78.3	76.1	76.1	76.1	76.1
77.5°	59.7	58.7	58.1	57.7	57.1	56.4	56.2
80°	46.6	45.9	44.9	44.9	44.4	44.9	44.4
82.5°	35.1	35.0	33.9	33.9	33.4	33.1	33.4
85°	18.0	17.5	18.5	17.5	18.0	17.0	18.0
87.5°	8.2	8.3	7.9	8.0	7.6	8.5	7.7
90°	15.3	15.9	16.3	16.6	16.8	17.1	17.3
92.5°	23.3	23.7	23.9	23.7	23.5	23.4	23.2
95°	44.1	44.6	44.9	44.9	44.9	44.9	44.9
97.5°	68.5	69.1	69.3	69.3	69.2	69.2	69.1
100°	85.8	86.2	86.5	86.7	87.1	87.3	87.6
102.5°	106.1	106.4	106.6	106.6	106.5	106.5	106.4
105°	135.9	135.9	136.0	136.3	136.5	136.8	137.1
107.5°	169.1	169.5	169.7	169.5	169.4	169.2	169.1
110°	191.1	191.6	191.7	191.5	191.2	191.0	190.7



TEST NUMBER: P332307-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	213.0	213.6	213.9	213.9	213.8	213.8	213.7
115°	245.8	245.9	245.9	245.8	245.6	245.5	245.4
117.5°	279.1	279.1	278.9	278.6	278.2	277.9	277.5
120°	301.4	301.3	301.1	300.8	300.6	300.3	300.1
122.5°	323.9	323.6	323.2	322.9	322.4	322.1	321.7
125°	357.3	356.8	356.3	355.8	355.3	354.8	354.3
127.5°	390.3	389.6	389.0	388.4	387.8	387.2	386.6
130°	412.6	412.1	411.4	410.5	409.6	408.7	407.8
132.5°	433.9	433.3	432.7	432.0	431.3	430.6	429.9
135°	466.2	465.6	465.2	465.0	464.7	464.5	464.2
137.5°	497.6	497.1	496.6	496.0	495.5	495.0	494.5
140°	518.6	518.5	518.0	517.1	516.1	515.2	514.4
142.5°	538.0	537.9	537.5	536.7	536.0	535.3	534.6
145°	566.4	566.3	565.9	565.4	564.9	564.4	563.9
147.5°	593.4	593.4	593.0	592.3	591.5	590.8	590.0
150°	610.0	610.0	609.7	608.8	608.0	607.3	606.5
152.5°	625.4	625.6	625.3	624.7	624.0	623.4	622.7
155°	647.8	648.3	648.1	647.2	646.3	645.5	644.6
157.5°	666.9	667.4	667.3	666.6	665.9	665.2	664.5
160°	678.7	679.3	679.4	678.9	678.4	677.9	677.4
162.5°	689.8	690.4	690.3	689.5	688.7	687.9	687.1
165°	703.9	704.7	704.6	703.7	702.8	702.0	701.0
167.5°	715.3	716.1	716.1	715.3	714.5	713.7	712.9
170°	721.5	722.5	722.5	721.5	720.6	719.7	718.8
172.5°	726.3	727.1	727.1	726.2	725.3	724.4	723.5
175°	731.5	732.4	732.3	731.3	730.4	729.5	728.6
177.5°	733.8	734.4	734.3	733.6	732.9	732.2	731.4
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3

(END OF REPORT)