

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831171

Luminaire Tested: S123DIP-S1000D805U935-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831171  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D805U935-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 805 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6733.2 lumens  
Efficiency: N/A  
Efficacy: 120.9 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 55.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831171

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P831171

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59				
1	100	96	93	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51				
2	92	85	79	74	86	79	74	70	69	66	62	60	57	55	52	50	48	44				
3	84	75	68	63	79	71	64	59	62	57	53	54	50	47	46	44	42	38				
4	78	67	60	54	72	63	56	51	56	50	46	49	45	41	42	39	37	33				
5	72	60	52	47	67	57	50	45	50	45	40	44	40	36	38	35	32	29				
6	66	55	47	41	62	52	44	39	46	40	36	40	36	32	35	32	29	26				
7	62	50	42	37	58	47	40	35	42	36	32	37	33	29	33	29	26	24				
8	58	46	38	33	54	43	36	31	39	33	29	34	30	26	30	27	24	22				
9	54	42	35	30	50	40	33	28	36	30	26	32	27	24	28	25	22	20				
10	50	39	32	27	47	37	30	26	33	28	24	30	25	22	26	23	20	18				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	26579	26579	26579	26579	26579
5°	33613	31726	26817	21610	19859
10°	33940	34967	26639	17227	15054
15°	25563	32465	26457	14588	12730
20°	17811	26270	26119	12757	11564
25°	13581	20202	25543	11738	10846
30°	11749	16051	24623	11016	10268
35°	10901	13550	23563	10494	9862
40°	10321	12156	22073	9999	9725
45°	9977	11251	20180	9611	9663
50°	9805	10535	17941	9259	9614
55°	9439	10010	15739	8923	9655
60°	9102	9449	13567	8609	9496
65°	8550	8917	11703	8273	9309
70°	7896	8239	9951	7717	8762
75°	7149	7386	8530	7170	8006
80°	5895	6465	6750	6248	6750
85°	4668	5236	4952	5311	5372

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 23041 cd/sqm



TEST NUMBER: P831171

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	233.4	3.5
10°-20°	580.8	8.6
20°-30°	687.6	10.2
30°-40°	691.4	10.3
40°-50°	634.3	9.4
50°-60°	523.6	7.8
60°-70°	370.4	5.5
70°-80°	197.7	2.9
80°-90°	52.0	0.8
90°-100°	31.9	0.5
100°-110°	154.4	2.3
110°-120°	378.5	5.6
120°-130°	480.5	7.1
130°-140°	513.3	7.6
140°-150°	480.0	7.1
150°-160°	387.2	5.8
160°-170°	249.9	3.7
170°-180°	86.1	1.3
0°-30°	1501.8	22.3
0°-40°	2193.3	32.6
0°-60°	3351.2	49.8
0°-90°	3971.2	59.0
90°-120°	564.9	8.4
90°-150°	2038.8	30.3
90°-180°	2762.0	41.0
0°-180°	6733.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2469	2469	2469	2469	2469	
5°	3111	2936	2482	2000	1838	296
15°	2294	2913	2374	1309	1142	634
25°	1144	1701	2151	988	913	540
35°	830	1031	1793	799	750	521
45°	655	739	1326	631	635	508
55°	503	533	839	476	514	450
65°	336	350	460	325	366	334
75°	172	178	205	172	192	181
85°	38	42	40	43	44	42
90°	20	16	1	16	20	11
95°	26	21	41	21	26	21
105°	30	147	201	147	30	62
115°	396	386	376	386	396	372
125°	541	538	530	538	541	484
135°	667	667	660	667	667	515
145°	769	768	762	768	769	480
155°	838	839	839	839	838	387
165°	883	882	885	882	883	249
175°	903	903	906	903	903	86
180°	906	906	906	906	906	



TEST NUMBER: P831171

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3
2.5°	2783.2	2780.4	2777.5	2763.2	2748.8	2742.0	2735.1	2714.5	2693.8	2670.9	2648.0
5°	3110.9	3119.0	3127.0	3117.8	3108.6	3080.6	3052.5	3015.3	2978.0	2936.2	2894.4
7.5°	3262.2	3266.8	3271.3	3265.6	3259.9	3252.4	3245.0	3211.8	3178.5	3135.6	3092.6
10°	3105.2	3115.5	3125.8	3148.2	3170.5	3195.7	3220.9	3216.3	3211.8	3199.2	3186.6
12.5°	2760.3	2772.9	2785.5	2830.2	2874.9	2932.2	2989.5	3038.7	3088.0	3122.4	3156.8
15°	2294.0	2328.9	2363.8	2404.5	2445.2	2529.4	2613.6	2717.3	2821.0	2913.3	3005.5
17.5°	1889.5	1902.7	1915.8	1959.4	2002.9	2108.9	2214.9	2334.6	2454.4	2607.3	2760.3
20°	1554.9	1566.9	1579.0	1636.2	1693.5	1776.6	1859.7	1994.3	2129.0	2293.4	2457.8
22.5°	1306.2	1325.2	1344.1	1376.1	1408.2	1487.9	1567.5	1687.2	1807.0	1988.6	2170.2
25°	1143.5	1157.3	1171.0	1190.5	1210.0	1273.6	1337.2	1435.7	1534.3	1701.0	1867.7
27.5°	1032.4	1038.1	1043.9	1063.3	1082.8	1124.1	1165.3	1250.1	1334.9	1476.4	1617.9
30°	945.3	949.3	953.3	970.5	987.7	1015.8	1043.9	1105.2	1166.5	1291.4	1416.2
32.5°	884.6	887.4	890.3	903.5	916.7	936.7	956.8	1001.5	1046.1	1149.3	1252.4
35°	829.6	831.3	833.0	842.8	852.5	867.4	882.3	916.1	949.9	1031.2	1112.6
37.5°	781.5	783.7	786.0	791.8	797.5	810.7	823.9	850.8	877.7	940.2	1002.6
40°	734.5	738.5	742.5	746.5	750.5	761.4	772.3	792.9	813.5	865.1	916.7
42.5°	694.4	698.4	702.4	704.1	705.8	712.1	718.4	737.3	756.2	794.6	833.0
45°	655.4	657.1	658.9	660.6	662.3	667.4	672.6	689.2	705.8	739.1	772.3
47.5°	619.9	619.9	619.9	621.0	622.2	626.8	631.4	643.4	655.4	681.2	707.0
50°	585.5	585.5	585.5	583.8	582.1	584.9	587.8	597.0	606.1	629.1	652.0
52.5°	544.3	544.3	544.3	544.8	545.4	545.4	545.4	553.4	561.5	582.1	602.7
55°	503.0	505.3	507.6	505.9	504.2	505.3	506.5	511.6	516.8	533.4	550.0
57.5°	461.8	462.9	464.1	463.5	462.9	463.5	464.1	468.6	473.2	485.8	498.4
60°	422.8	422.8	422.8	421.7	420.5	421.7	422.8	425.1	427.4	438.9	450.3
62.5°	379.3	379.8	380.4	381.0	381.6	380.4	379.3	382.1	385.0	393.6	402.2
65°	335.7	336.3	336.9	338.6	340.3	339.2	338.0	340.9	343.7	350.1	356.4
67.5°	296.8	295.6	294.5	295.1	295.6	297.3	299.1	299.6	300.2	307.1	314.0
70°	250.9	252.1	253.2	252.7	252.1	252.7	253.2	254.9	256.7	261.8	267.0
72.5°	209.7	210.3	210.8	210.8	210.8	212.0	213.1	214.8	216.6	219.4	222.3
75°	171.9	171.9	171.9	173.0	174.2	174.7	175.3	175.3	175.3	177.6	179.9
77.5°	130.6	133.5	136.4	135.8	135.2	136.4	137.5	139.2	140.9	142.1	143.2
80°	95.1	95.1	95.1	95.7	96.2	98.0	99.7	100.8	102.0	104.3	106.6
82.5°	60.7	61.3	61.9	63.6	65.3	66.5	67.6	69.3	71.0	71.0	71.0
85°	37.8	36.7	35.5	36.7	37.8	39.0	40.1	40.7	41.2	42.4	43.5
87.5°	18.3	18.3	18.3	18.3	18.3	18.9	19.5	19.5	19.5	19.5	19.5
90°	20.2	19.9	19.6	19.3	19.0	18.5	17.9	17.4	16.8	16.2	14.2
92.5°	22.9	22.7	22.6	22.4	22.3	21.7	20.6	19.6	18.5	17.5	16.2
95°	25.6	25.6	25.6	25.6	25.6	25.1	24.0	23.0	21.9	20.9	19.2
97.5°	27.6	27.4	27.3	27.1	27.0	26.3	25.1	23.9	22.7	21.5	20.2
100°	28.3	28.1	28.0	27.8	27.7	27.0	25.8	24.6	23.4	22.2	21.0
102.5°	28.9	28.6	28.3	28.0	27.7	30.1	35.0	39.9	44.9	49.8	55.8
105°	29.6	29.3	29.0	28.7	28.4	41.5	68.0	94.5	120.9	147.4	160.9
107.5°	70.0	89.6	109.2	128.8	148.4	169.7	192.7	215.8	238.8	261.8	259.6
110°	185.1	206.5	227.9	249.3	270.7	283.8	288.8	293.7	298.6	303.6	301.9



TEST NUMBER: P831171

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	350.7	351.0	351.3	351.6	351.9	351.4	350.0	348.7	347.3	346.0	344.3
115°	395.8	395.2	394.6	394.0	393.4	392.4	390.9	389.4	387.9	386.4	385.0
117.5°	432.1	432.0	431.8	431.7	431.5	430.9	429.7	428.5	427.3	426.1	425.3
120°	469.8	469.8	469.8	469.8	469.8	469.2	468.0	466.8	465.7	464.5	464.0
122.5°	506.9	506.7	506.6	506.4	506.3	505.8	505.1	504.3	503.6	502.8	502.2
125°	541.2	540.9	540.6	540.3	540.0	539.7	539.4	539.1	538.8	538.5	537.9
127.5°	574.8	575.1	575.4	575.7	576.0	576.0	575.5	575.1	574.6	574.2	573.4
130°	607.2	607.5	607.8	608.1	608.4	608.2	607.6	607.0	606.4	605.8	605.2
132.5°	636.8	637.2	637.7	638.1	638.6	638.5	637.9	637.3	636.7	636.1	635.7
135°	667.1	667.5	668.0	668.4	668.9	668.9	668.4	668.0	667.5	667.1	666.5
137.5°	696.0	696.3	696.6	696.9	697.2	697.0	696.2	695.5	694.7	694.0	693.7
140°	721.6	721.9	722.2	722.5	722.8	722.6	722.0	721.4	720.8	720.2	719.8
142.5°	745.1	745.6	746.0	746.5	746.9	746.9	746.5	746.0	745.6	745.1	744.7
145°	769.4	769.4	769.4	769.4	769.4	769.2	768.9	768.6	768.3	768.0	767.7
147.5°	786.9	787.6	788.4	789.1	789.9	790.1	789.8	789.5	789.2	788.9	788.6
150°	807.1	807.5	808.0	808.4	808.9	808.9	808.6	808.3	808.0	807.7	807.4
152.5°	823.2	824.0	824.7	825.5	826.2	826.3	825.7	825.1	824.5	823.9	823.8
155°	838.0	838.9	839.8	840.7	841.6	841.7	841.0	840.2	839.5	838.7	838.6
157.5°	850.8	852.0	853.2	854.4	855.6	855.8	854.9	854.0	853.1	852.2	852.3
160°	862.9	864.0	865.0	866.1	867.1	867.2	866.3	865.4	864.5	863.6	863.8
162.5°	874.4	875.3	876.2	877.1	878.0	877.9	876.9	875.8	874.8	873.7	873.9
165°	883.1	884.2	885.2	886.3	887.3	887.3	886.1	884.9	883.7	882.5	882.6
167.5°	889.9	891.1	892.3	893.5	894.7	894.7	893.5	892.3	891.1	889.9	889.9
170°	895.9	897.1	898.3	899.5	900.7	900.7	899.5	898.3	897.1	895.9	895.9
172.5°	899.3	900.6	902.0	903.3	904.7	904.8	903.6	902.4	901.2	900.0	899.8
175°	902.7	903.9	905.1	906.2	907.4	907.5	906.5	905.4	904.4	903.3	903.2
177.5°	903.3	904.8	906.3	907.8	909.3	909.5	908.3	907.1	905.9	904.7	904.5
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P831171

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3
2.5°	2641.1	2634.3	2609.1	2583.8	2555.2	2526.6	2505.4	2484.2	2452.7	2421.1	2395.4
5°	2862.3	2830.2	2776.9	2723.6	2651.5	2579.3	2530.6	2481.9	2416.6	2351.2	2299.1
7.5°	3037.6	2982.6	2908.1	2833.6	2739.1	2644.6	2555.2	2465.8	2366.1	2266.5	2185.1
10°	3149.3	3112.1	3026.1	2940.2	2813.6	2687.0	2562.1	2437.2	2308.8	2180.5	2072.8
12.5°	3160.2	3163.6	3084.6	3005.5	2862.3	2719.1	2567.2	2415.4	2253.8	2092.3	1966.8
15°	3064.5	3123.5	3080.0	3036.5	2892.1	2747.7	2560.9	2374.2	2188.0	2001.8	1856.8
17.5°	2886.9	3013.5	3019.8	3026.1	2881.8	2737.4	2530.6	2323.7	2112.9	1902.1	1749.7
20°	2644.6	2831.3	2895.5	2959.7	2842.2	2724.8	2502.5	2280.2	2044.2	1808.1	1648.3
22.5°	2397.1	2624.0	2741.4	2858.8	2771.8	2684.7	2448.1	2211.5	1962.2	1713.0	1550.9
25°	2115.2	2362.7	2543.2	2723.6	2670.4	2617.1	2383.9	2150.7	1885.5	1620.2	1454.6
27.5°	1869.4	2120.9	2338.6	2556.3	2544.9	2533.4	2302.0	2070.5	1799.0	1527.4	1367.5
30°	1650.6	1884.9	2128.4	2371.9	2399.9	2428.0	2204.6	1981.1	1709.0	1436.9	1282.8
32.5°	1456.9	1661.5	1922.7	2184.0	2239.0	2294.0	2092.3	1890.6	1621.4	1352.1	1203.7
35°	1298.2	1483.9	1745.1	2006.3	2075.1	2143.8	1968.5	1793.2	1530.8	1268.4	1126.9
37.5°	1157.9	1313.1	1568.1	1823.0	1907.2	1991.5	1834.5	1677.5	1431.7	1185.9	1055.9
40°	1041.6	1166.5	1400.8	1635.1	1732.5	1829.9	1700.4	1570.9	1337.8	1104.6	984.8
42.5°	944.2	1055.3	1267.9	1480.4	1573.8	1667.2	1557.8	1448.3	1240.9	1033.5	924.1
45°	861.1	949.9	1143.0	1336.0	1424.8	1513.6	1419.7	1325.7	1143.0	960.2	858.2
47.5°	783.2	859.4	1024.4	1189.4	1268.4	1347.5	1274.2	1200.8	1046.1	891.5	799.2
50°	713.3	774.6	919.0	1063.3	1132.1	1200.8	1136.1	1071.4	944.2	817.0	736.8
52.5°	652.6	702.4	823.3	944.2	1003.2	1062.2	1006.6	951.0	850.2	749.4	679.5
55°	592.4	634.8	739.6	844.5	884.6	924.7	881.7	838.7	757.4	676.0	617.0
57.5°	536.2	574.1	660.0	745.9	776.9	807.8	768.9	729.9	668.6	607.3	558.0
60°	481.2	512.2	583.8	655.4	674.3	693.2	661.7	630.2	587.2	544.3	500.2
62.5°	430.3	458.3	511.6	564.9	577.5	590.1	566.0	542.0	509.3	476.7	442.3
65°	377.6	398.7	442.3	485.8	493.9	501.9	480.7	459.5	434.8	410.2	385.0
67.5°	328.9	343.7	379.3	414.8	415.4	415.9	398.7	381.6	367.8	354.1	334.0
70°	281.3	295.6	319.1	342.6	343.2	343.7	330.0	316.2	305.9	295.6	280.7
72.5°	232.6	242.9	260.7	278.4	277.3	276.1	267.6	259.0	250.9	242.9	232.0
75°	188.5	197.1	209.1	221.1	217.7	214.3	209.7	205.1	198.2	191.4	184.5
77.5°	148.4	153.5	160.4	167.3	165.0	162.7	158.7	154.7	149.5	144.4	141.5
80°	108.9	111.1	115.7	120.3	119.2	118.0	113.4	108.9	107.7	106.6	102.6
82.5°	73.9	76.8	77.9	79.1	78.5	77.9	74.5	71.0	69.9	68.7	68.2
85°	44.1	44.7	45.3	45.8	44.1	42.4	41.2	40.1	40.1	40.1	39.5
87.5°	20.1	20.6	20.6	20.6	20.1	19.5	18.3	17.2	17.8	18.3	18.3
90°	12.3	10.3	8.4	6.7	5.2	3.7	2.2	0.7	2.2	3.7	5.2
92.5°	14.8	13.5	12.1	11.9	12.8	13.7	14.6	15.5	14.6	13.7	12.8
95°	17.6	15.9	14.3	16.5	22.7	28.8	34.9	41.1	34.9	28.8	22.7
97.5°	36.8	44.4	52.1	58.0	62.2	66.3	70.5	74.7	70.5	66.3	62.2
100°	68.9	92.2	115.6	125.7	122.7	119.7	116.7	113.8	116.7	119.7	122.7
102.5°	101.9	127.9	153.9	166.0	164.0	162.1	160.1	158.2	160.1	162.1	164.0
105°	174.3	187.8	201.3	207.2	205.5	203.9	202.2	200.6	202.2	203.9	205.5
107.5°	257.4	255.1	252.9	251.1	249.7	248.4	247.0	245.7	247.0	248.4	249.7
110°	300.3	298.6	297.0	295.6	294.4	293.2	292.0	290.8	292.0	293.2	294.4





TEST NUMBER: P831171

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	342.7	341.0	339.4	338.1	337.0	336.0	334.9	333.9	334.9	336.0	337.0
115°	383.7	382.3	381.0	379.9	379.0	378.1	377.2	376.3	377.2	378.1	379.0
117.5°	424.6	423.8	423.1	422.2	421.2	420.1	419.1	418.0	419.1	420.1	421.2
120°	463.6	463.1	462.7	461.8	460.4	459.1	457.7	456.4	457.7	459.1	460.4
122.5°	501.6	501.0	500.4	499.6	498.6	497.5	496.5	495.4	496.5	497.5	498.6
125°	537.3	536.7	536.1	535.2	534.0	532.8	531.6	530.4	531.6	532.8	534.0
127.5°	572.7	571.9	571.2	570.2	569.0	567.8	566.6	565.4	566.6	567.8	569.0
130°	604.6	604.0	603.4	602.5	601.3	600.1	598.9	597.7	598.9	600.1	601.3
132.5°	635.2	634.8	634.3	633.5	632.3	631.1	629.9	628.7	629.9	631.1	632.3
135°	665.9	665.3	664.7	663.9	663.0	662.1	661.2	660.3	661.2	662.1	663.0
137.5°	693.4	693.1	692.8	692.0	690.8	689.7	688.5	687.3	688.5	689.7	690.8
140°	719.3	718.9	718.4	717.8	716.9	716.0	715.1	714.2	715.1	716.0	716.9
142.5°	744.3	743.8	743.4	742.7	741.8	740.9	740.0	739.1	740.0	740.9	741.8
145°	767.4	767.1	766.8	766.2	765.1	764.1	763.0	762.0	763.0	764.1	765.1
147.5°	788.3	788.0	787.7	787.2	786.4	785.7	784.9	784.2	784.9	785.7	786.4
150°	807.1	806.9	806.6	806.2	805.7	805.3	804.8	804.4	804.8	805.3	805.7
152.5°	823.6	823.5	823.3	823.2	823.0	822.9	822.7	822.6	822.7	822.9	823.0
155°	838.4	838.3	838.1	838.2	838.5	838.8	839.1	839.4	839.1	838.8	838.5
157.5°	852.5	852.6	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8
160°	863.9	864.1	864.2	864.4	864.5	864.7	864.8	865.0	864.8	864.7	864.5
162.5°	874.0	874.2	874.3	874.6	875.1	875.5	876.0	876.4	876.0	875.5	875.1
165°	882.8	882.9	883.1	883.4	883.8	884.3	884.7	885.2	884.7	884.3	883.8
167.5°	889.9	889.9	889.9	890.2	890.8	891.4	892.0	892.6	892.0	891.4	890.8
170°	895.9	895.9	895.9	896.2	896.8	897.4	898.0	898.6	898.0	897.4	896.8
172.5°	899.7	899.5	899.4	899.7	900.4	901.2	901.9	902.7	901.9	901.2	900.4
175°	903.0	902.9	902.7	903.0	903.8	904.5	905.3	906.0	905.3	904.5	903.8
177.5°	904.4	904.2	904.1	904.4	905.1	905.9	906.6	907.4	906.6	905.9	905.1
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P831171

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3
2.5°	2369.6	2347.2	2324.9	2307.7	2290.5	2261.3	2232.1	2225.2	2218.3	2208.6	2198.8
5°	2247.0	2192.0	2137.0	2087.7	2038.4	2000.0	1961.7	1936.5	1911.2	1892.9	1874.6
7.5°	2103.7	2021.2	1938.7	1880.3	1821.9	1766.3	1710.7	1693.0	1675.2	1651.1	1627.1
10°	1965.1	1874.0	1782.9	1706.7	1630.5	1576.1	1521.7	1499.9	1478.1	1447.8	1417.4
12.5°	1841.4	1741.7	1642.0	1565.2	1488.4	1435.7	1383.0	1351.5	1320.0	1302.8	1285.6
15°	1711.9	1605.3	1498.7	1427.7	1356.7	1309.1	1261.6	1234.1	1206.6	1189.9	1173.3
17.5°	1597.3	1491.9	1386.5	1318.3	1250.1	1206.6	1163.0	1139.0	1114.9	1102.3	1089.7
20°	1488.4	1385.3	1282.2	1215.7	1149.3	1113.7	1078.2	1062.8	1047.3	1037.0	1026.7
22.5°	1388.7	1287.3	1185.9	1129.2	1072.5	1043.9	1015.2	1004.3	993.4	984.8	976.2
25°	1289.1	1198.5	1108.0	1059.9	1011.8	988.3	964.8	953.9	943.0	934.4	925.8
27.5°	1207.7	1121.2	1034.7	993.4	952.2	933.9	915.5	906.9	898.3	890.3	882.3
30°	1128.6	1051.3	974.0	938.4	902.9	886.3	869.7	861.1	852.5	845.1	837.6
32.5°	1055.3	988.9	922.4	889.7	857.1	843.3	829.6	819.3	809.0	803.2	797.5
35°	985.4	925.8	866.2	839.3	812.4	798.6	784.9	776.3	767.7	763.1	758.5
37.5°	925.8	872.6	819.3	793.5	767.7	754.5	741.4	733.9	726.5	724.7	723.0
40°	865.1	819.3	773.4	748.2	723.0	711.6	700.1	695.5	690.9	689.8	688.6
42.5°	814.7	770.0	725.3	702.4	679.5	669.7	660.0	657.7	655.4	657.1	658.9
45°	756.2	719.0	681.8	660.6	639.4	631.4	623.3	621.6	619.9	623.3	626.8
47.5°	707.0	672.6	638.2	618.2	598.1	592.4	586.7	586.1	585.5	590.1	594.7
50°	656.6	623.3	590.1	574.1	558.0	552.9	547.7	549.4	551.1	558.6	566.0
52.5°	609.6	578.6	547.7	532.8	517.9	514.5	511.0	515.1	519.1	527.1	535.1
55°	558.0	529.9	501.9	490.4	479.0	475.5	472.1	480.1	488.1	495.6	503.0
57.5°	508.7	484.1	459.5	449.2	438.9	438.3	437.7	445.2	452.6	460.6	468.6
60°	456.0	435.4	414.8	406.8	398.7	399.9	401.0	409.6	418.2	424.5	430.8
62.5°	407.9	390.7	373.5	366.1	358.6	361.5	364.4	373.0	381.6	389.0	396.5
65°	359.8	345.5	331.1	326.0	320.8	324.8	328.9	336.3	343.7	348.9	354.1
67.5°	314.0	301.9	289.9	285.9	281.9	285.9	289.9	297.3	304.8	309.9	315.1
70°	265.8	256.1	246.4	243.5	240.6	245.2	249.8	256.1	262.4	267.6	272.7
72.5°	221.1	213.7	206.2	205.7	205.1	209.1	213.1	219.4	225.7	229.2	232.6
75°	177.6	173.6	169.6	169.0	168.4	172.4	176.5	179.9	183.3	186.2	189.1
77.5°	138.6	135.2	131.8	132.3	132.9	135.8	138.6	142.1	145.5	147.2	149.0
80°	98.5	97.4	96.2	97.4	98.5	100.8	103.1	105.4	107.7	108.9	110.0
82.5°	67.6	66.5	65.3	67.0	68.7	70.5	72.2	73.9	75.6	76.2	76.8
85°	39.0	40.7	42.4	42.4	42.4	43.0	43.5	44.1	44.7	44.1	43.5
87.5°	18.3	18.9	19.5	19.5	19.5	20.1	20.6	20.6	20.6	20.1	19.5
90°	6.7	8.4	10.3	12.3	14.2	16.2	16.8	17.4	17.9	18.5	19.0
92.5°	11.9	12.1	13.5	14.8	16.2	17.5	18.5	19.6	20.6	21.7	22.3
95°	16.5	14.3	15.9	17.6	19.2	20.9	21.9	23.0	24.0	25.1	25.6
97.5°	58.0	52.1	44.4	36.8	29.2	21.5	22.7	23.9	25.1	26.3	27.0
100°	125.7	115.6	92.2	68.9	45.5	22.2	23.4	24.6	25.8	27.0	27.7
102.5°	166.0	153.9	127.9	101.9	75.8	49.8	44.9	39.9	35.0	30.1	27.7
105°	207.2	201.3	187.8	174.3	160.9	147.4	120.9	94.5	68.0	41.5	28.4
107.5°	251.1	252.9	255.1	257.4	259.6	261.8	238.8	215.8	192.7	169.7	148.4
110°	295.6	297.0	298.6	300.3	301.9	303.6	298.6	293.7	288.8	283.8	270.7



TEST NUMBER: P831171

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	338.1	339.4	341.0	342.7	344.3	346.0	347.3	348.7	350.0	351.4	351.9
115°	379.9	381.0	382.3	383.7	385.0	386.4	387.9	389.4	390.9	392.4	393.4
117.5°	422.2	423.1	423.8	424.6	425.3	426.1	427.3	428.5	429.7	430.9	431.5
120°	461.8	462.7	463.1	463.6	464.0	464.5	465.7	466.8	468.0	469.2	469.8
122.5°	499.6	500.4	501.0	501.6	502.2	502.8	503.6	504.3	505.1	505.8	506.3
125°	535.2	536.1	536.7	537.3	537.9	538.5	538.8	539.1	539.4	539.7	540.0
127.5°	570.2	571.2	571.9	572.7	573.4	574.2	574.6	575.1	575.5	576.0	576.0
130°	602.5	603.4	604.0	604.6	605.2	605.8	606.4	607.0	607.6	608.2	608.4
132.5°	633.5	634.3	634.8	635.2	635.7	636.1	636.7	637.3	637.9	638.5	638.6
135°	663.9	664.7	665.3	665.9	666.5	667.1	667.5	668.0	668.4	668.9	668.9
137.5°	692.0	692.8	693.1	693.4	693.7	694.0	694.7	695.5	696.2	697.0	697.2
140°	717.8	718.4	718.9	719.3	719.8	720.2	720.8	721.4	722.0	722.6	722.8
142.5°	742.7	743.4	743.8	744.3	744.7	745.1	745.6	746.0	746.5	746.9	746.9
145°	766.2	766.8	767.1	767.4	767.7	768.0	768.3	768.6	768.9	769.2	769.4
147.5°	787.2	787.7	788.0	788.3	788.6	788.9	789.2	789.5	789.8	790.1	789.9
150°	806.2	806.6	806.9	807.1	807.4	807.7	808.0	808.3	808.6	808.9	808.9
152.5°	823.2	823.3	823.5	823.6	823.8	823.9	824.5	825.1	825.7	826.3	826.2
155°	838.2	838.1	838.3	838.4	838.6	838.7	839.5	840.2	841.0	841.7	841.6
157.5°	852.8	852.8	852.6	852.5	852.3	852.2	853.1	854.0	854.9	855.8	855.6
160°	864.4	864.2	864.1	863.9	863.8	863.6	864.5	865.4	866.3	867.2	867.1
162.5°	874.6	874.3	874.2	874.0	873.9	873.7	874.8	875.8	876.9	877.9	878.0
165°	883.4	883.1	882.9	882.8	882.6	882.5	883.7	884.9	886.1	887.3	887.3
167.5°	890.2	889.9	889.9	889.9	889.9	889.9	891.1	892.3	893.5	894.7	894.7
170°	896.2	895.9	895.9	895.9	895.9	895.9	897.1	898.3	899.5	900.7	900.7
172.5°	899.7	899.4	899.5	899.7	899.8	900.0	901.2	902.4	903.6	904.8	904.7
175°	903.0	902.7	902.9	903.0	903.2	903.3	904.4	905.4	906.5	907.5	907.4
177.5°	904.4	904.1	904.2	904.4	904.5	904.7	905.9	907.1	908.3	909.5	909.3
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P831171

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2469.3	2469.3	2469.3	2469.3
2.5°	2194.8	2190.8	2174.8	2158.7
5°	1860.8	1847.1	1842.5	1837.9
7.5°	1625.9	1624.8	1600.7	1576.7
10°	1419.1	1420.8	1399.1	1377.3
12.5°	1271.3	1257.0	1255.3	1253.5
15°	1160.2	1147.0	1144.7	1142.4
17.5°	1081.7	1073.6	1071.4	1069.1
20°	1022.1	1017.5	1013.5	1009.5
22.5°	970.5	964.8	961.4	957.9
25°	920.7	915.5	914.4	913.2
27.5°	876.0	869.7	869.7	869.7
30°	833.6	829.6	827.9	826.1
32.5°	794.1	790.6	790.6	790.6
35°	756.8	755.1	752.8	750.5
37.5°	723.0	723.0	721.9	720.7
40°	690.4	692.1	692.1	692.1
42.5°	660.6	662.3	662.3	662.3
45°	629.6	632.5	633.6	634.8
47.5°	599.3	603.9	605.0	606.1
50°	569.5	572.9	573.5	574.1
52.5°	539.1	543.1	546.0	548.9
55°	507.0	511.0	512.8	514.5
57.5°	472.7	476.7	477.2	477.8
60°	434.8	438.9	440.0	441.1
62.5°	398.7	401.0	402.2	403.3
65°	357.5	360.9	363.2	365.5
67.5°	318.0	320.8	320.8	320.8
70°	273.9	275.0	276.7	278.4
72.5°	233.2	233.7	233.7	233.7
75°	190.2	191.4	191.9	192.5
77.5°	149.5	150.1	150.1	150.1
80°	109.4	108.9	108.9	108.9
82.5°	75.1	73.3	73.3	73.3
85°	43.0	42.4	43.0	43.5
87.5°	19.5	19.5	19.5	19.5
90°	19.3	19.6	19.9	20.2
92.5°	22.4	22.6	22.7	22.9
95°	25.6	25.6	25.6	25.6
97.5°	27.1	27.3	27.4	27.6
100°	27.8	28.0	28.1	28.3
102.5°	28.0	28.3	28.6	28.9
105°	28.7	29.0	29.3	29.6
107.5°	128.8	109.2	89.6	70.0
110°	249.3	227.9	206.5	185.1



TEST NUMBER: P831171

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	351.6	351.3	351.0	350.7
115°	394.0	394.6	395.2	395.8
117.5°	431.7	431.8	432.0	432.1
120°	469.8	469.8	469.8	469.8
122.5°	506.4	506.6	506.7	506.9
125°	540.3	540.6	540.9	541.2
127.5°	575.7	575.4	575.1	574.8
130°	608.1	607.8	607.5	607.2
132.5°	638.1	637.7	637.2	636.8
135°	668.4	668.0	667.5	667.1
137.5°	696.9	696.6	696.3	696.0
140°	722.5	722.2	721.9	721.6
142.5°	746.5	746.0	745.6	745.1
145°	769.4	769.4	769.4	769.4
147.5°	789.1	788.4	787.6	786.9
150°	808.4	808.0	807.5	807.1
152.5°	825.5	824.7	824.0	823.2
155°	840.7	839.8	838.9	838.0
157.5°	854.4	853.2	852.0	850.8
160°	866.1	865.0	864.0	862.9
162.5°	877.1	876.2	875.3	874.4
165°	886.3	885.2	884.2	883.1
167.5°	893.5	892.3	891.1	889.9
170°	899.5	898.3	897.1	895.9
172.5°	903.3	902.0	900.6	899.3
175°	906.2	905.1	903.9	902.7
177.5°	907.8	906.3	904.8	903.3
180°	906.0	906.0	906.0	906.0



TEST NUMBER: P831171

CATALOG NUMBER: S123DIP-S1000D805U935-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.76	16.67	16.65	17.57	18.71	18.00	18.90	18.89	19.80	20.94
	3H	17.42	18.22	18.31	19.13	20.30	19.43	20.24	20.33	21.15	22.31
	4H	17.99	18.76	18.91	19.67	20.85	19.88	20.65	20.79	21.56	22.74
	6H	18.37	19.07	19.29	19.99	21.18	20.16	20.86	21.08	21.78	22.97
	8H	18.47	19.13	19.40	20.07	21.26	20.22	20.89	21.15	21.83	23.02
	12H	18.51	19.15	19.45	20.08	21.29	20.24	20.88	21.18	21.81	23.02
4H	2H	16.35	17.11	17.26	18.02	19.20	18.17	18.93	19.09	19.85	21.02
	3H	18.18	18.81	19.10	19.76	20.95	19.79	20.43	20.72	21.37	22.56
	4H	18.88	19.46	19.81	20.40	21.61	20.38	20.96	21.32	21.90	23.11
	6H	19.35	19.85	20.31	20.82	22.03	20.79	21.28	21.74	22.25	23.46
	8H	19.49	19.96	20.45	20.92	22.15	20.90	21.36	21.85	22.32	23.55
	12H	19.56	19.98	20.53	20.96	22.19	20.94	21.36	21.92	22.34	23.57
8H	4H	19.15	19.61	20.10	20.57	21.80	20.49	20.95	21.44	21.91	23.14
	6H	19.74	20.12	20.72	21.12	22.35	20.99	21.38	21.97	22.38	23.60
	8H	19.94	20.28	20.93	21.27	22.52	21.17	21.51	22.16	22.50	23.75
	12H	20.07	20.37	21.06	21.35	22.64	21.27	21.57	22.26	22.55	23.85
12H	4H	19.15	19.57	20.12	20.54	21.78	20.46	20.88	21.43	21.86	23.09
	6H	19.79	20.13	20.77	21.12	22.36	21.01	21.34	21.99	22.33	23.58
	8H	20.02	20.32	21.01	21.30	22.60	21.21	21.51	22.20	22.49	23.78