

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332310-840

Luminaire Tested: **S123RDIP-S775D585U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332310-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D585U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4979.1 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332310-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332310-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	56	55	51
2	92	84	78	73	85	79	74	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	27	25
7	60	48	40	35	56	46	38	33	40	35	30	36	31	27	31	27	24	22
8	56	44	36	31	52	42	34	30	37	31	27	33	28	25	29	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14034	14034	14034
5°	14088	13894	13973
10°	14008	13719	13672
15°	13857	13397	13256
20°	13651	12997	12693
25°	13438	12545	12144
30°	13155	12026	11368
35°	12867	11506	10657
40°	12600	10891	9777
45°	12250	10286	8983
50°	11863	9597	8092
55°	11470	8811	7263
60°	11108	7967	6351
65°	10639	7055	5440
70°	10049	5923	4393
75°	9191	4662	4134
80°	8195	4135	3800
85°	6916	3656	3396



TEST NUMBER: P332310-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	2.5
10°-20°	340.6	6.8
20°-30°	490.5	9.9
30°-40°	552.5	11.1
40°-50°	528.6	10.6
50°-60°	432.9	8.7
60°-70°	292.0	5.9
70°-80°	146.9	3.0
80°-90°	41.0	0.8
90°-100°	47.8	1.0
100°-110°	143.0	2.9
110°-120°	243.2	4.9
120°-130°	319.9	6.4
130°-140°	359.5	7.2
140°-150°	353.4	7.1
150°-160°	297.5	6.0
160°-170°	198.0	4.0
170°-180°	69.3	1.4
0°-30°	953.6	19.2
0°-40°	1506.1	30.2
0°-60°	2467.5	49.6
0°-90°	2947.5	59.2
90°-120°	433.9	8.7
90°-150°	1466.7	29.5
90°-180°	2032.0	40.8
0°-180°	4979.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1304	1304	1304	1304	1304	
5°	1304	1298	1286	1295	1293	124
15°	1244	1231	1202	1197	1190	350
25°	1132	1104	1056	1035	1022	520
35°	979	940	876	832	811	613
45°	805	755	676	617	590	621
55°	611	557	470	410	387	548
65°	418	358	277	227	214	413
75°	221	170	112	102	99	236
85°	56	34	30	28	28	63
90°	1	6	14	16	17	5
95°	34	38	43	45	45	38
105°	130	131	136	136	137	139
115°	245	246	245	246	245	242
125°	358	360	359	357	354	319
135°	465	468	468	465	464	358
145°	564	565	567	566	564	352
155°	646	646	646	648	645	297
165°	703	702	702	705	701	198
175°	732	729	729	732	729	69
180°	733	733	733	733	733	



TEST NUMBER: P332310-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1308.0	1307.3	1306.5	1305.8	1305.0	1303.5	1301.2	1299.0	1296.8	1294.4	1296.6
5°	1303.8	1302.6	1301.4	1300.3	1299.1	1297.1	1294.2	1291.4	1288.6	1285.9	1287.9
7.5°	1291.7	1290.5	1289.2	1287.9	1286.7	1284.1	1280.5	1276.9	1273.2	1269.5	1270.7
10°	1281.6	1279.9	1278.3	1276.7	1275.0	1272.0	1267.8	1263.6	1259.4	1255.2	1255.4
12.5°	1267.2	1265.4	1263.5	1261.7	1259.9	1256.4	1251.2	1246.1	1240.8	1235.7	1235.6
15°	1243.5	1240.9	1238.3	1235.8	1233.1	1228.6	1222.0	1215.5	1208.8	1202.2	1201.1
17.5°	1213.7	1210.7	1207.7	1204.7	1201.6	1196.0	1187.6	1179.2	1170.8	1162.6	1160.0
20°	1191.7	1187.9	1184.2	1180.4	1176.7	1170.3	1161.3	1152.5	1143.6	1134.6	1131.6
22.5°	1167.2	1162.9	1158.5	1154.2	1149.8	1143.0	1133.5	1124.0	1114.5	1105.0	1101.2
25°	1131.5	1125.6	1119.6	1113.8	1107.9	1099.5	1088.7	1077.9	1067.1	1056.3	1051.4
27.5°	1088.0	1081.6	1075.1	1068.6	1062.2	1052.9	1040.9	1028.9	1016.7	1004.7	997.8
30°	1058.4	1051.4	1044.4	1037.3	1030.3	1020.2	1007.0	993.8	980.7	967.6	959.6
32.5°	1028.9	1020.9	1012.9	1004.9	996.9	985.9	972.0	958.2	944.2	930.3	921.6
35°	979.2	970.7	962.2	953.8	945.3	933.8	919.3	904.6	890.1	875.6	865.5
37.5°	928.9	919.4	910.0	900.6	891.2	878.8	863.2	847.7	832.1	816.6	805.1
40°	896.7	886.4	876.0	865.7	855.4	841.8	825.2	808.5	791.7	775.1	762.9
42.5°	860.3	850.0	839.6	829.3	819.0	805.2	787.9	770.6	753.5	736.2	722.9
45°	804.7	794.2	783.6	773.0	762.3	748.1	729.9	711.9	693.8	675.7	662.3
47.5°	749.1	737.5	725.9	714.3	702.7	687.8	669.7	651.6	633.5	615.4	600.9
50°	708.4	697.4	686.4	675.3	664.3	649.2	630.3	611.2	592.2	573.1	558.6
52.5°	672.1	660.1	648.1	636.1	624.2	608.7	589.9	571.1	552.2	533.3	518.3
55°	611.2	599.7	588.1	576.6	565.1	549.4	529.4	509.5	489.5	469.5	455.9
57.5°	554.9	542.4	529.9	517.3	504.7	488.5	468.4	448.3	428.2	408.2	395.3
60°	516.0	503.1	490.2	477.3	464.3	448.1	428.6	409.1	389.6	370.1	357.4
62.5°	477.1	464.1	451.2	438.3	425.5	409.2	389.7	370.2	350.7	331.1	319.2
65°	417.7	404.8	391.8	378.9	366.0	350.3	332.0	313.7	295.4	277.0	265.5
67.5°	358.3	345.2	332.1	319.0	306.0	290.6	273.1	255.5	237.9	220.4	211.8
70°	319.3	306.7	294.0	281.2	268.6	254.0	237.5	221.2	204.7	188.2	180.0
72.5°	280.4	267.9	255.4	242.9	230.5	216.7	201.8	186.8	171.9	156.9	150.2
75°	221.0	209.7	198.4	187.1	175.9	163.8	150.9	137.9	125.0	112.1	109.8
77.5°	166.8	156.6	146.4	136.2	126.0	116.8	108.5	100.2	91.9	83.5	82.3
80°	132.2	122.5	112.9	103.3	93.6	86.3	81.4	76.4	71.6	66.7	65.9
82.5°	99.2	90.9	82.5	74.2	65.9	60.6	58.3	55.9	53.7	51.4	50.7
85°	56.0	50.9	45.7	40.5	35.3	32.4	31.7	31.0	30.3	29.6	29.2
87.5°	20.4	18.6	16.8	14.9	13.1	12.4	12.7	13.1	13.4	13.7	13.6
90°	0.6	1.8	3.1	4.4	5.7	7.2	8.8	10.5	12.1	13.8	14.3
92.5°	13.9	14.8	15.7	16.6	17.5	18.4	19.3	20.2	21.2	22.1	22.5
95°	34.0	34.8	35.7	36.7	37.6	38.6	39.6	40.6	41.6	42.6	43.1
97.5°	60.4	61.0	61.7	62.4	63.0	63.7	64.4	65.2	65.9	66.8	67.3
100°	78.4	79.1	79.9	80.7	81.4	82.1	82.7	83.4	84.0	84.6	85.0
102.5°	99.1	99.6	100.0	100.5	100.9	101.6	102.4	103.3	104.1	104.9	105.3
105°	129.6	129.9	130.1	130.4	130.7	131.3	132.5	133.6	134.8	135.9	135.9
107.5°	165.1	165.2	165.4	165.5	165.7	166.0	166.4	166.9	167.4	167.8	168.2
110°	187.2	187.4	187.7	187.9	188.2	188.4	188.7	189.0	189.2	189.6	190.1



TEST NUMBER: P332310-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.3	210.4	210.6	210.7	210.9	211.0	211.1	211.1	211.2	211.2	211.8
115°	244.8	245.2	245.6	246.0	246.3	246.4	246.1	245.9	245.6	245.4	245.5
117.5°	279.6	279.8	280.1	280.3	280.6	280.5	280.2	279.9	279.6	279.2	279.2
120°	301.2	302.1	302.8	303.6	304.4	304.4	303.8	303.2	302.5	301.8	301.7
122.5°	323.9	324.4	325.0	325.5	326.1	326.2	325.9	325.6	325.2	324.9	324.6
125°	358.3	358.7	359.0	359.4	359.8	359.9	359.6	359.4	359.1	358.9	358.3
127.5°	390.1	390.9	391.7	392.5	393.3	393.6	393.3	393.0	392.7	392.5	391.8
130°	411.3	412.3	413.3	414.3	415.4	415.7	415.4	415.0	414.5	414.1	413.6
132.5°	432.4	433.5	434.5	435.6	436.6	437.0	436.7	436.4	436.1	435.9	435.2
135°	464.8	465.6	466.4	467.2	467.9	468.3	468.1	468.0	467.9	467.8	467.3
137.5°	494.8	495.4	496.0	496.8	497.4	497.9	498.2	498.5	498.9	499.2	498.7
140°	515.5	516.1	516.8	517.5	518.1	518.5	518.6	518.8	518.9	519.0	518.9
142.5°	534.4	535.0	535.7	536.3	536.9	537.5	537.7	537.9	538.2	538.4	538.3
145°	563.9	564.2	564.4	564.7	564.9	565.2	565.6	566.0	566.4	566.8	566.6
147.5°	589.8	590.2	590.7	591.1	591.6	592.0	592.4	592.7	593.1	593.4	593.4
150°	607.7	607.9	608.2	608.4	608.7	608.9	609.3	609.5	609.8	610.0	610.0
152.5°	622.5	622.8	623.2	623.5	623.9	624.1	624.3	624.4	624.6	624.7	624.9
155°	645.7	645.7	645.7	645.7	645.7	645.8	645.9	646.0	646.2	646.3	646.8
157.5°	665.5	665.4	665.2	665.1	664.9	664.9	665.0	665.1	665.2	665.3	665.8
160°	677.9	677.7	677.4	677.2	676.9	676.8	676.8	676.8	676.8	676.8	677.4
162.5°	689.0	688.6	688.3	687.9	687.6	687.5	687.6	687.7	687.8	687.9	688.5
165°	703.3	703.0	702.6	702.2	701.8	701.6	701.6	701.6	701.6	701.6	702.4
167.5°	714.7	714.2	713.7	713.2	712.7	712.5	712.6	712.7	712.8	712.9	713.7
170°	721.1	720.6	720.1	719.6	719.1	718.8	718.8	718.8	718.8	718.8	719.7
172.5°	726.2	725.7	725.2	724.7	724.2	724.0	724.0	724.0	724.0	724.0	724.8
175°	731.5	731.0	730.5	730.0	729.5	729.2	729.2	729.2	729.2	729.2	730.0
177.5°	733.8	733.4	733.0	732.5	732.1	731.8	731.8	731.8	731.8	731.8	732.5
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P332310-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1298.6	1300.7	1302.7	1303.6	1303.2	1302.8	1302.4	1302.1
5°	1290.0	1292.1	1294.2	1295.1	1294.6	1294.1	1293.6	1293.2
7.5°	1271.9	1273.0	1274.2	1274.4	1273.6	1272.8	1272.0	1271.2
10°	1255.7	1255.9	1256.1	1255.7	1254.5	1253.2	1252.1	1250.9
12.5°	1235.4	1235.3	1235.2	1234.4	1233.0	1231.6	1230.3	1228.9
15°	1199.9	1198.7	1197.6	1196.2	1194.6	1192.9	1191.2	1189.6
17.5°	1157.5	1155.1	1152.6	1150.1	1147.6	1145.2	1142.8	1140.3
20°	1128.5	1125.4	1122.4	1119.4	1116.6	1113.8	1111.0	1108.1
22.5°	1097.4	1093.6	1089.7	1086.5	1083.9	1081.3	1078.6	1076.0
25°	1046.5	1041.6	1036.6	1032.9	1030.3	1027.6	1025.1	1022.5
27.5°	991.0	984.2	977.3	971.9	968.0	964.0	960.1	956.1
30°	951.6	943.5	935.5	929.7	925.9	922.2	918.4	914.6
32.5°	912.8	904.1	895.3	889.0	885.0	881.1	877.2	873.2
35°	855.4	845.3	835.2	828.0	823.7	819.5	815.3	811.0
37.5°	793.6	782.1	770.6	762.3	757.1	751.8	746.7	741.4
40°	750.6	738.4	726.2	717.4	712.0	706.6	701.1	695.8
42.5°	709.4	696.1	682.8	673.7	668.8	664.0	659.1	654.3
45°	648.9	635.5	622.1	612.6	606.9	601.3	595.7	590.1
47.5°	586.2	571.7	557.1	547.3	542.3	537.2	532.3	527.3
50°	544.0	529.4	514.8	504.8	499.5	494.0	488.7	483.2
52.5°	503.1	488.0	472.8	462.8	458.0	453.1	448.3	443.4
55°	442.2	428.6	415.0	405.8	401.1	396.4	391.7	387.0
57.5°	382.4	369.5	356.7	348.2	344.3	340.2	336.2	332.2
60°	344.7	332.0	319.3	311.0	307.0	303.0	299.0	295.0
62.5°	307.3	295.4	283.5	275.4	271.1	267.0	262.9	258.6
65°	254.0	242.5	231.0	223.9	221.4	218.7	216.2	213.6
67.5°	203.2	194.6	185.9	180.3	177.5	174.7	172.0	169.2
70°	171.8	163.5	155.3	150.0	147.3	144.7	142.2	139.6
72.5°	143.5	136.7	130.1	126.1	125.0	124.0	122.9	121.8
75°	107.3	105.0	102.7	101.3	100.8	100.4	99.9	99.4
77.5°	81.0	79.7	78.5	77.6	77.2	76.6	76.1	75.7
80°	65.2	64.5	63.8	63.2	62.7	62.3	61.8	61.3
82.5°	50.0	49.3	48.6	48.2	48.1	48.0	47.9	47.8
85°	28.7	28.2	27.8	27.5	27.5	27.5	27.5	27.5
87.5°	13.6	13.5	13.4	13.3	13.1	13.0	12.9	12.7
90°	14.8	15.3	15.9	16.3	16.6	16.8	17.1	17.3
92.5°	22.9	23.3	23.7	23.9	23.7	23.5	23.4	23.2
95°	43.6	44.1	44.6	44.9	44.9	44.9	44.9	44.9
97.5°	67.9	68.5	69.1	69.3	69.3	69.2	69.2	69.1
100°	85.4	85.8	86.2	86.5	86.7	87.1	87.3	87.6
102.5°	105.7	106.1	106.4	106.6	106.6	106.5	106.5	106.4
105°	135.9	135.9	135.9	136.0	136.3	136.5	136.8	137.1
107.5°	168.6	169.1	169.5	169.7	169.5	169.4	169.2	169.1
110°	190.6	191.1	191.6	191.7	191.5	191.2	191.0	190.7



TEST NUMBER: P332310-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	212.4	213.0	213.6	213.9	213.9	213.8	213.8	213.7
115°	245.6	245.8	245.9	245.9	245.8	245.6	245.5	245.4
117.5°	279.2	279.1	279.1	278.9	278.6	278.2	277.9	277.5
120°	301.5	301.4	301.3	301.1	300.8	300.6	300.3	300.1
122.5°	324.2	323.9	323.6	323.2	322.9	322.4	322.1	321.7
125°	357.8	357.3	356.8	356.3	355.8	355.3	354.8	354.3
127.5°	391.0	390.3	389.6	389.0	388.4	387.8	387.2	386.6
130°	413.1	412.6	412.1	411.4	410.5	409.6	408.7	407.8
132.5°	434.5	433.9	433.3	432.7	432.0	431.3	430.6	429.9
135°	466.7	466.2	465.6	465.2	465.0	464.7	464.5	464.2
137.5°	498.1	497.6	497.1	496.6	496.0	495.5	495.0	494.5
140°	518.8	518.6	518.5	518.0	517.1	516.1	515.2	514.4
142.5°	538.1	538.0	537.9	537.5	536.7	536.0	535.3	534.6
145°	566.5	566.4	566.3	565.9	565.4	564.9	564.4	563.9
147.5°	593.4	593.4	593.4	593.0	592.3	591.5	590.8	590.0
150°	610.0	610.0	610.0	609.7	608.8	608.0	607.3	606.5
152.5°	625.2	625.4	625.6	625.3	624.7	624.0	623.4	622.7
155°	647.3	647.8	648.3	648.1	647.2	646.3	645.5	644.6
157.5°	666.4	666.9	667.4	667.3	666.6	665.9	665.2	664.5
160°	678.1	678.7	679.3	679.4	678.9	678.4	677.9	677.4
162.5°	689.1	689.8	690.4	690.3	689.5	688.7	687.9	687.1
165°	703.2	703.9	704.7	704.6	703.7	702.8	702.0	701.0
167.5°	714.5	715.3	716.1	716.1	715.3	714.5	713.7	712.9
170°	720.6	721.5	722.5	722.5	721.5	720.6	719.7	718.8
172.5°	725.5	726.3	727.1	727.1	726.2	725.3	724.4	723.5
175°	730.7	731.5	732.4	732.3	731.3	730.4	729.5	728.6
177.5°	733.2	733.8	734.4	734.3	733.6	732.9	732.2	731.4
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3

(END OF REPORT)