

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832419

Luminaire Tested: S123RDIP-S775D805U840-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832419  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D805U840-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 805 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6584.3 lumens  
Efficiency: N/A  
Efficacy: 141.6 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 46.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832419

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P832419

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	
1	99	95	91	88	91	88	85	82	75	72	70	63	61	60	51	50	50	44	44	44	44	
2	91	84	78	73	84	78	73	69	66	63	60	56	53	51	46	45	43	39	39	39	39	
3	83	74	68	62	77	69	63	58	59	55	51	50	47	44	42	40	38	34	34	34	34	
4	77	67	59	53	71	62	55	50	53	49	45	46	42	39	38	36	33	30	30	30	30	
5	71	60	52	47	65	56	49	44	48	43	39	41	38	34	35	32	30	27	27	27	27	
6	66	54	46	41	61	51	44	39	44	39	35	38	34	31	32	29	27	24	24	24	24	
7	61	49	42	36	56	46	39	35	40	35	31	35	31	28	30	27	24	22	22	22	22	
8	57	45	38	33	53	42	36	31	37	32	28	32	28	25	28	25	22	20	20	20	20	
9	53	42	34	30	49	39	33	28	34	29	26	30	26	23	26	23	20	18	18	18	18	
10	50	38	31	27	46	36	30	26	32	27	23	28	24	21	24	21	19	17	17	17	17	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	27137	27137	27137	27137	27137
5°	32222	31194	27308	22075	20495
10°	29194	31685	27172	17687	15173
15°	20100	27167	26885	14456	12003
20°	13984	20916	26345	12190	10550
25°	10656	15941	25560	10834	9723
30°	9276	12745	24577	10060	9006
35°	8516	10750	23186	9406	8353
40°	7770	9601	21365	8765	7756
45°	7018	8780	19401	8159	7159
50°	6370	8102	17084	7564	6422
55°	5761	7439	14859	6983	5510
60°	5162	6764	12906	6342	5208
65°	4765	6003	11110	5700	4923
70°	3871	5190	9693	5155	4000
75°	3398	4126	8210	4275	3527
80°	3075	3490	6726	3589	3335
85°	2803	3063	5101	3260	3063

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 20471 cd/sqm



TEST NUMBER: P832419

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	229.8	3.5
10°-20°	531.7	8.1
20°-30°	610.1	9.3
30°-40°	601.4	9.1
40°-50°	530.3	8.1
50°-60°	408.0	6.2
60°-70°	268.2	4.1
70°-80°	130.3	2.0
80°-90°	35.0	0.5
90°-100°	37.5	0.6
100°-110°	181.1	2.8
110°-120°	444.0	6.7
120°-130°	563.6	8.6
130°-140°	602.1	9.1
140°-150°	563.0	8.6
150°-160°	454.1	6.9
160°-170°	293.1	4.5
170°-180°	101.0	1.5
0°-30°	1371.6	20.8
0°-40°	1973.0	30.0
0°-60°	2911.3	44.2
0°-90°	3344.7	50.8
90°-120°	662.5	10.1
90°-150°	2391.3	36.3
90°-180°	3240.0	49.2
0°-180°	6584.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2521	2521	2521	2521	2521	
5°	2982	2887	2527	2043	1897	272
15°	1804	2438	2413	1297	1077	509
25°	897	1342	2152	912	819	424
35°	648	818	1764	716	636	404
45°	461	577	1274	536	470	358
55°	307	396	792	372	294	275
65°	187	236	436	224	193	183
75°	82	99	197	103	85	88
85°	23	25	41	26	25	24
90°	24	19	1	19	24	12
95°	30	24	48	24	30	25
105°	35	173	235	173	35	72
115°	464	453	441	453	464	437
125°	635	632	622	632	635	567
135°	782	782	774	782	782	604
145°	902	901	894	901	902	564
155°	983	984	984	984	983	453
165°	1036	1035	1038	1035	1036	293
175°	1059	1060	1063	1060	1059	101
180°	1063	1063	1063	1063	1063	



TEST NUMBER: P832419

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1
2.5°	2794.0	2785.2	2776.4	2773.8	2771.2	2763.0	2754.7	2736.1	2717.5	2698.4	2679.3
5°	2982.1	2983.1	2984.2	2981.6	2979.0	2968.2	2957.3	2934.6	2911.8	2887.0	2862.2
7.5°	2924.2	2940.8	2957.3	2960.4	2963.5	2971.8	2980.0	2974.9	2969.7	2960.4	2951.1
10°	2671.0	2669.9	2668.9	2687.5	2706.1	2761.4	2816.7	2845.2	2873.6	2898.9	2924.2
12.5°	2257.5	2259.1	2260.6	2321.6	2382.6	2434.8	2487.0	2559.3	2631.7	2709.7	2787.8
15°	1803.7	1829.1	1854.4	1908.7	1962.9	2041.5	2120.0	2217.2	2314.4	2437.9	2561.4
17.5°	1481.2	1492.1	1502.9	1555.1	1607.3	1681.8	1756.2	1866.3	1976.4	2135.5	2294.7
20°	1220.8	1230.6	1240.4	1278.1	1315.9	1387.2	1458.5	1563.4	1668.3	1826.0	1983.6
22.5°	1019.2	1038.3	1057.4	1082.8	1108.1	1159.8	1211.5	1318.4	1425.4	1569.1	1712.8
25°	897.2	906.0	914.8	936.5	958.2	1007.8	1057.4	1128.2	1199.0	1342.2	1485.4
27.5°	814.5	817.1	819.7	835.7	851.7	883.8	915.8	981.5	1047.1	1164.9	1282.8
30°	746.3	751.0	755.6	768.0	780.4	803.7	826.9	873.4	920.0	1025.4	1130.8
32.5°	693.6	696.2	698.8	709.1	719.4	736.5	753.5	790.2	826.9	907.6	988.2
35°	648.1	648.6	649.1	656.9	664.6	681.2	697.7	728.2	758.7	818.1	877.6
37.5°	596.4	600.0	603.7	609.3	615.0	629.5	644.0	668.8	693.6	742.7	791.8
40°	553.0	556.1	559.2	565.9	572.6	584.0	595.4	618.1	640.9	683.3	725.6
42.5°	509.6	511.7	513.7	520.4	527.2	541.1	555.1	573.2	591.3	626.4	661.5
45°	461.0	466.2	471.3	478.6	485.8	497.7	509.6	528.2	546.8	576.8	606.8
47.5°	420.7	423.3	425.9	432.1	438.3	452.7	467.2	483.8	500.3	528.2	556.1
50°	380.4	381.4	382.5	388.1	393.8	406.7	419.7	438.8	457.9	483.8	509.6
52.5°	342.1	344.7	347.3	353.0	358.7	367.5	376.3	395.9	415.5	440.9	466.2
55°	307.0	308.5	310.1	314.2	318.4	328.7	339.0	356.1	373.2	396.4	419.7
57.5°	273.9	276.0	278.1	281.2	284.3	293.6	302.9	317.9	332.8	356.1	379.4
60°	239.8	242.4	245.0	248.6	252.2	259.4	266.7	280.1	293.6	314.2	334.9
62.5°	215.0	215.5	216.0	219.1	222.2	227.4	232.6	243.4	254.3	275.0	295.6
65°	187.1	188.6	190.2	191.7	193.3	197.4	201.6	210.9	220.2	235.7	251.2
67.5°	158.2	159.7	161.3	163.8	166.4	170.0	173.7	179.9	186.1	200.5	215.0
70°	123.0	123.0	123.0	127.1	131.3	137.5	143.7	148.3	153.0	164.9	176.8
72.5°	100.3	100.8	101.3	101.8	102.3	106.0	109.6	117.3	125.1	132.3	139.5
75°	81.7	82.2	82.7	83.2	83.7	84.8	85.8	88.4	91.0	99.2	107.5
77.5°	65.1	65.6	66.2	66.7	67.2	68.2	69.3	70.3	71.3	74.4	77.5
80°	49.6	50.1	50.6	51.2	51.7	52.2	52.7	53.8	54.8	56.3	57.9
82.5°	36.2	36.2	36.2	36.2	36.2	37.2	38.2	38.2	38.2	39.3	40.3
85°	22.7	22.7	22.7	23.3	23.8	23.8	23.8	24.3	24.8	24.8	24.8
87.5°	10.3	9.8	9.3	9.8	10.3	10.3	10.3	10.9	11.4	11.4	11.4
90°	23.7	23.3	23.0	22.6	22.3	21.8	21.1	20.4	19.6	18.9	16.7
92.5°	26.8	26.7	26.5	26.3	26.1	25.4	24.2	23.0	21.8	20.5	18.9
95°	30.0	30.0	30.0	30.0	30.0	29.4	28.2	26.9	25.7	24.5	22.5
97.5°	32.4	32.2	32.0	31.8	31.7	30.9	29.5	28.1	26.7	25.3	34.2
100°	33.2	33.0	32.8	32.6	32.5	31.7	30.3	28.9	27.5	26.1	53.4
102.5°	33.9	33.6	33.2	32.9	32.5	35.3	41.1	46.8	52.6	58.4	89.0
105°	34.7	34.4	34.0	33.7	33.3	48.7	79.7	110.8	141.8	172.9	188.7
107.5°	82.1	105.1	128.1	151.1	174.0	199.0	226.1	253.1	280.1	307.1	304.5
110°	217.1	242.2	267.3	292.4	317.5	332.9	338.7	344.5	350.3	356.1	354.1



TEST NUMBER: P832419

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	411.3	411.7	412.0	412.4	412.7	412.1	410.5	409.0	407.4	405.8	403.9
115°	464.2	463.5	462.8	462.1	461.4	460.2	458.4	456.7	454.9	453.2	451.6
117.5°	506.9	506.7	506.5	506.3	506.2	505.4	504.0	502.6	501.2	499.8	498.9
120°	551.1	551.1	551.1	551.1	551.1	550.4	549.0	547.6	546.2	544.8	544.2
122.5°	594.5	594.3	594.1	594.0	593.8	593.3	592.4	591.5	590.6	589.8	589.1
125°	634.8	634.4	634.1	633.7	633.4	633.0	632.7	632.3	632.0	631.6	630.9
127.5°	674.2	674.6	674.9	675.3	675.6	675.6	675.0	674.5	674.0	673.4	672.6
130°	712.1	712.5	712.8	713.2	713.5	713.4	712.7	712.0	711.3	710.6	709.9
132.5°	746.9	747.4	747.9	748.5	749.0	748.9	748.2	747.5	746.8	746.1	745.6
135°	782.4	782.9	783.5	784.0	784.5	784.5	784.0	783.5	782.9	782.4	781.7
137.5°	816.4	816.7	817.1	817.4	817.8	817.5	816.6	815.7	814.9	814.0	813.6
140°	846.4	846.7	847.1	847.4	847.8	847.6	846.9	846.2	845.5	844.8	844.2
142.5°	874.0	874.5	875.0	875.6	876.1	876.1	875.6	875.0	874.5	874.0	873.5
145°	902.4	902.4	902.4	902.4	902.4	902.2	901.9	901.5	901.2	900.8	900.5
147.5°	922.9	923.8	924.7	925.6	926.4	926.7	926.4	926.0	925.7	925.3	925.0
150°	946.6	947.1	947.7	948.2	948.7	948.8	948.5	948.1	947.8	947.4	947.1
152.5°	965.6	966.4	967.3	968.2	969.1	969.2	968.5	967.8	967.1	966.4	966.2
155°	982.9	984.0	985.0	986.1	987.1	987.2	986.4	985.5	984.6	983.7	983.6
157.5°	997.9	999.3	1000.7	1002.1	1003.6	1003.7	1002.7	1001.6	1000.6	999.5	999.7
160°	1012.1	1013.4	1014.6	1015.8	1017.1	1017.1	1016.1	1015.0	1014.0	1012.9	1013.1
162.5°	1025.6	1026.6	1027.7	1028.7	1029.8	1029.7	1028.5	1027.2	1026.0	1024.8	1025.0
165°	1035.8	1037.1	1038.3	1039.5	1040.7	1040.7	1039.3	1037.9	1036.4	1035.0	1035.2
167.5°	1043.7	1045.1	1046.5	1047.9	1049.3	1049.3	1047.9	1046.5	1045.1	1043.7	1043.7
170°	1050.8	1052.2	1053.6	1055.0	1056.4	1056.4	1055.0	1053.6	1052.2	1050.8	1050.8
172.5°	1054.8	1056.4	1057.9	1059.5	1061.1	1061.2	1059.8	1058.4	1057.0	1055.6	1055.4
175°	1058.7	1060.1	1061.5	1062.9	1064.3	1064.4	1063.2	1062.0	1060.7	1059.5	1059.3
177.5°	1059.5	1061.3	1063.0	1064.8	1066.5	1066.7	1065.3	1063.9	1062.5	1061.1	1060.9
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P832419

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1
2.5°	2676.7	2674.1	2649.3	2624.5	2600.2	2575.9	2557.8	2539.7	2509.2	2478.7	2459.6
5°	2842.6	2822.9	2783.7	2744.4	2685.5	2626.5	2576.9	2527.3	2464.3	2401.2	2348.5
7.5°	2935.1	2919.1	2871.5	2824.0	2745.9	2667.9	2590.4	2512.8	2419.8	2326.8	2247.2
10°	2937.7	2951.1	2911.8	2872.5	2784.7	2696.8	2591.4	2486.0	2360.9	2235.8	2133.0
12.5°	2845.7	2903.6	2895.3	2887.0	2797.6	2708.2	2580.0	2451.8	2298.3	2144.8	2016.2
15°	2673.6	2785.7	2818.8	2851.9	2778.0	2704.1	2558.3	2412.6	2232.2	2051.8	1904.0
17.5°	2451.8	2609.0	2696.3	2783.7	2729.9	2676.2	2516.4	2356.7	2153.6	1950.5	1789.8
20°	2189.3	2395.0	2532.0	2668.9	2649.3	2629.6	2464.8	2299.9	2080.8	1861.6	1687.5
22.5°	1929.8	2146.9	2336.1	2525.2	2545.4	2565.5	2399.1	2232.7	1992.9	1753.1	1575.8
25°	1706.1	1926.7	2152.1	2377.4	2422.9	2468.4	2310.2	2152.1	1903.5	1654.9	1478.7
27.5°	1492.6	1702.4	1950.5	2198.6	2281.3	2364.0	2219.3	2074.6	1815.6	1556.7	1381.0
30°	1318.4	1506.0	1759.3	2012.5	2127.8	2243.0	2110.2	1977.4	1720.5	1463.7	1291.6
32.5°	1156.2	1324.1	1578.4	1832.7	1966.5	2100.4	1985.7	1870.9	1623.9	1376.8	1206.8
35°	1028.0	1178.4	1415.6	1652.8	1802.7	1952.6	1858.5	1764.5	1523.1	1281.7	1121.0
37.5°	917.9	1044.0	1266.8	1489.5	1648.7	1807.9	1729.3	1650.8	1423.9	1197.0	1045.0
40°	826.9	928.2	1135.5	1342.7	1498.8	1654.9	1587.7	1520.5	1317.4	1114.3	972.2
42.5°	748.9	836.2	1022.3	1208.4	1351.5	1494.7	1450.2	1405.8	1221.8	1037.8	906.0
45°	680.1	753.5	917.4	1081.2	1213.0	1344.8	1309.6	1274.5	1115.8	957.2	836.2
47.5°	619.2	682.2	828.5	974.7	1093.1	1211.5	1178.9	1146.3	1015.1	883.8	773.7
50°	563.3	617.1	739.1	861.0	967.5	1074.0	1047.1	1020.2	911.7	803.2	708.1
52.5°	510.6	555.1	664.6	774.2	860.0	945.8	925.1	904.5	820.7	737.0	650.7
55°	460.5	501.3	593.8	686.4	759.7	833.1	812.5	791.8	726.7	661.5	585.6
57.5°	415.0	450.7	525.6	600.6	659.0	717.4	707.5	697.7	643.5	589.2	526.7
60°	366.9	399.0	463.6	528.2	575.2	622.3	610.9	599.5	560.8	522.0	468.2
62.5°	324.1	352.5	404.2	455.8	494.1	532.3	524.1	515.8	486.3	456.9	412.4
65°	279.1	307.0	348.9	390.7	420.7	450.7	443.4	436.2	414.0	391.8	356.1
67.5°	238.3	261.5	297.7	333.9	354.0	374.2	370.1	365.9	348.9	331.8	303.9
70°	196.9	217.1	247.0	277.0	291.0	304.9	306.5	308.0	292.5	277.0	256.3
72.5°	155.6	171.6	199.5	227.4	238.3	249.1	248.6	248.1	238.8	229.5	210.9
75°	119.4	131.3	153.0	174.7	184.0	193.3	195.4	197.4	188.6	179.9	169.5
77.5°	85.8	94.1	110.6	127.1	137.5	147.8	148.8	149.9	145.7	141.6	131.8
80°	60.5	63.1	73.4	83.7	94.6	105.4	107.0	108.5	104.4	100.3	94.1
82.5°	41.9	43.4	47.0	50.6	59.4	68.2	70.3	72.4	70.3	68.2	61.5
85°	25.3	25.8	27.4	28.9	33.1	37.2	39.3	41.3	40.3	39.3	35.7
87.5°	11.4	11.4	11.9	12.4	13.4	14.5	17.1	19.6	18.1	16.5	15.0
90°	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	17.4	15.8	14.2	13.9	15.0	16.1	17.1	18.2	17.1	16.1	15.0
95°	20.6	18.7	16.8	19.4	26.6	33.8	41.0	48.2	41.0	33.8	26.6
97.5°	43.2	52.1	61.1	68.0	72.9	77.8	82.7	87.6	82.7	77.8	72.9
100°	80.8	108.2	135.5	147.5	144.0	140.4	136.9	133.4	136.9	140.4	144.0
102.5°	119.5	150.0	180.5	194.7	192.4	190.1	187.8	185.5	187.8	190.1	192.4
105°	204.5	220.3	236.1	243.0	241.1	239.1	237.2	235.3	237.2	239.1	241.1
107.5°	301.9	299.2	296.6	294.5	292.9	291.3	289.7	288.2	289.7	291.3	292.9
110°	352.2	350.3	348.3	346.7	345.3	343.9	342.5	341.1	342.5	343.9	345.3





TEST NUMBER: P832419

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	401.9	400.0	398.1	396.5	395.3	394.1	392.8	391.6	392.8	394.1	395.3
115°	450.0	448.4	446.9	445.5	444.5	443.4	442.4	441.3	442.4	443.4	444.5
117.5°	498.0	497.1	496.2	495.2	494.0	492.7	491.5	490.3	491.5	492.7	494.0
120°	543.7	543.2	542.7	541.6	540.0	538.4	536.9	535.3	536.9	538.4	540.0
122.5°	588.4	587.7	587.0	586.0	584.8	583.5	582.3	581.1	582.3	583.5	584.8
125°	630.2	629.5	628.8	627.7	626.3	624.9	623.5	622.1	623.5	624.9	626.3
127.5°	671.7	670.8	669.9	668.8	667.4	666.0	664.6	663.2	664.6	666.0	667.4
130°	709.2	708.5	707.7	706.7	705.3	703.9	702.5	701.1	702.5	703.9	705.3
132.5°	745.0	744.5	744.0	743.0	741.6	740.2	738.8	737.4	738.8	740.2	741.6
135°	781.0	780.3	779.6	778.7	777.7	776.6	775.6	774.5	775.6	776.6	777.7
137.5°	813.3	812.9	812.6	811.7	810.3	808.9	807.5	806.1	807.5	808.9	810.3
140°	843.7	843.2	842.7	841.9	840.8	839.8	838.7	837.7	838.7	839.8	840.8
142.5°	872.9	872.4	871.9	871.1	870.0	869.0	867.9	866.9	867.9	869.0	870.0
145°	900.1	899.8	899.4	898.6	897.4	896.2	895.0	893.7	895.0	896.2	897.4
147.5°	924.6	924.2	923.9	923.3	922.4	921.5	920.7	919.8	920.7	921.5	922.4
150°	946.7	946.4	946.0	945.6	945.0	944.5	944.0	943.5	944.0	944.5	945.0
152.5°	966.0	965.8	965.7	965.5	965.3	965.1	965.0	964.8	965.0	965.1	965.3
155°	983.4	983.2	983.0	983.1	983.5	983.8	984.2	984.5	984.2	983.8	983.5
157.5°	999.9	1000.0	1000.2	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3
160°	1013.3	1013.5	1013.6	1013.8	1014.0	1014.2	1014.3	1014.5	1014.3	1014.2	1014.0
162.5°	1025.1	1025.3	1025.5	1025.8	1026.4	1026.9	1027.4	1027.9	1027.4	1026.9	1026.4
165°	1035.4	1035.6	1035.7	1036.1	1036.6	1037.1	1037.7	1038.2	1037.7	1037.1	1036.6
167.5°	1043.7	1043.7	1043.7	1044.1	1044.8	1045.5	1046.2	1046.9	1046.2	1045.5	1044.8
170°	1050.8	1050.8	1050.8	1051.2	1051.9	1052.6	1053.3	1054.0	1053.3	1052.6	1051.9
172.5°	1055.2	1055.0	1054.9	1055.2	1056.1	1057.0	1057.9	1058.7	1057.9	1057.0	1056.1
175°	1059.2	1059.0	1058.8	1059.2	1060.0	1060.9	1061.8	1062.7	1061.8	1060.9	1060.0
177.5°	1060.7	1060.6	1060.4	1060.7	1061.6	1062.5	1063.4	1064.3	1063.4	1062.5	1061.6
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P832419

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1	2521.1
2.5°	2440.5	2411.0	2381.6	2360.4	2339.2	2312.8	2286.5	2285.4	2284.4	2264.8	2245.1
5°	2295.8	2244.6	2193.4	2143.3	2093.2	2043.0	1992.9	1981.5	1970.2	1953.1	1936.0
7.5°	2167.6	2085.9	2004.3	1940.2	1876.1	1826.0	1775.8	1741.7	1707.6	1681.3	1654.9
10°	2030.1	1928.8	1827.5	1750.0	1672.5	1618.2	1563.9	1524.7	1485.4	1466.8	1448.2
12.5°	1887.5	1777.4	1667.3	1591.3	1515.3	1450.2	1385.1	1349.4	1313.8	1287.9	1262.1
15°	1756.2	1637.8	1519.5	1438.9	1358.2	1297.2	1236.3	1200.6	1164.9	1139.1	1113.3
17.5°	1629.1	1509.7	1390.3	1308.6	1227.0	1171.7	1116.4	1081.7	1047.1	1031.1	1015.1
20°	1513.3	1392.9	1272.4	1195.4	1118.4	1064.2	1009.9	991.3	972.7	957.7	942.7
22.5°	1398.5	1282.8	1167.0	1093.1	1019.2	979.9	940.6	925.6	910.7	899.3	887.9
25°	1302.4	1187.2	1071.9	1007.3	942.7	912.2	881.7	871.9	862.1	850.7	839.3
27.5°	1205.2	1095.7	986.1	934.4	882.7	857.9	833.1	820.7	808.3	799.0	789.7
30°	1119.5	1018.2	916.9	874.0	831.1	809.4	787.7	774.2	760.8	752.0	743.2
32.5°	1036.8	946.8	856.9	820.2	783.5	762.3	741.1	728.2	715.3	705.0	694.6
35°	960.3	882.2	804.2	770.6	737.0	715.8	694.6	681.7	668.8	658.4	648.1
37.5°	893.1	822.3	751.5	719.9	688.4	669.8	651.2	637.8	624.3	613.5	602.6
40°	830.0	767.5	705.0	674.5	644.0	623.8	603.7	591.8	579.9	570.1	560.2
42.5°	774.2	716.8	659.5	629.5	599.5	580.4	561.3	547.3	533.4	527.7	522.0
45°	715.3	664.6	614.0	585.1	556.1	536.0	515.8	503.9	492.0	486.9	481.7
47.5°	663.6	616.6	569.5	541.1	512.7	494.6	476.5	467.2	457.9	450.7	443.4
50°	613.0	567.5	522.0	494.6	467.2	451.7	436.2	424.8	413.5	408.3	403.1
52.5°	564.4	523.0	481.7	453.8	425.9	410.9	395.9	386.1	376.3	365.4	354.5
55°	509.6	473.4	437.2	412.4	387.6	372.1	356.6	345.2	333.9	322.5	311.1
57.5°	464.1	428.5	392.8	370.6	348.3	333.4	318.4	306.0	293.6	284.3	275.0
60°	414.5	383.5	352.5	330.8	309.1	294.6	280.1	268.2	256.3	251.7	247.0
62.5°	368.0	339.0	310.1	291.0	271.9	257.9	243.9	236.2	228.4	225.3	222.2
65°	320.4	295.6	270.8	253.2	235.7	223.8	211.9	208.3	204.7	202.1	199.5
67.5°	276.0	254.8	233.6	218.1	202.6	194.3	186.1	181.9	177.8	174.7	171.6
70°	235.7	217.1	198.5	185.0	171.6	163.8	156.1	152.5	148.8	143.2	137.5
72.5°	192.3	177.8	163.3	153.0	142.6	135.9	129.2	122.0	114.7	109.6	104.4
75°	159.2	144.7	130.2	120.4	110.6	102.8	95.1	92.5	89.9	88.4	86.8
77.5°	122.0	109.6	97.2	89.4	81.7	78.0	74.4	72.9	71.3	70.8	70.3
80°	87.9	77.5	67.2	63.1	58.9	57.9	56.9	55.8	54.8	54.3	53.8
82.5°	54.8	49.6	44.4	43.4	42.4	41.9	41.3	40.8	40.3	39.8	39.3
85°	32.0	30.0	27.9	27.4	26.9	26.4	25.8	25.8	25.8	25.8	25.8
87.5°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	12.9	12.4
90°	7.8	9.8	12.1	14.4	16.7	18.9	19.6	20.4	21.1	21.8	22.3
92.5°	13.9	14.2	15.8	17.4	18.9	20.5	21.8	23.0	24.2	25.4	26.1
95°	19.4	16.8	18.7	20.6	22.5	24.5	25.7	26.9	28.2	29.4	30.0
97.5°	68.0	61.1	52.1	43.2	34.2	25.3	26.7	28.1	29.5	30.9	31.7
100°	147.5	135.5	108.2	80.8	53.4	26.1	27.5	28.9	30.3	31.7	32.5
102.5°	194.7	180.5	150.0	119.5	89.0	58.4	52.6	46.8	41.1	35.3	32.5
105°	243.0	236.1	220.3	204.5	188.7	172.9	141.8	110.8	79.7	48.7	33.3
107.5°	294.5	296.6	299.2	301.9	304.5	307.1	280.1	253.1	226.1	199.0	174.0
110°	346.7	348.3	350.3	352.2	354.1	356.1	350.3	344.5	338.7	332.9	317.5



TEST NUMBER: P832419

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	396.5	398.1	400.0	401.9	403.9	405.8	407.4	409.0	410.5	412.1	412.7
115°	445.5	446.9	448.4	450.0	451.6	453.2	454.9	456.7	458.4	460.2	461.4
117.5°	495.2	496.2	497.1	498.0	498.9	499.8	501.2	502.6	504.0	505.4	506.2
120°	541.6	542.7	543.2	543.7	544.2	544.8	546.2	547.6	549.0	550.4	551.1
122.5°	586.0	587.0	587.7	588.4	589.1	589.8	590.6	591.5	592.4	593.3	593.8
125°	627.7	628.8	629.5	630.2	630.9	631.6	632.0	632.3	632.7	633.0	633.4
127.5°	668.8	669.9	670.8	671.7	672.6	673.4	674.0	674.5	675.0	675.6	675.6
130°	706.7	707.7	708.5	709.2	709.9	710.6	711.3	712.0	712.7	713.4	713.5
132.5°	743.0	744.0	744.5	745.0	745.6	746.1	746.8	747.5	748.2	748.9	749.0
135°	778.7	779.6	780.3	781.0	781.7	782.4	782.9	783.5	784.0	784.5	784.5
137.5°	811.7	812.6	812.9	813.3	813.6	814.0	814.9	815.7	816.6	817.5	817.8
140°	841.9	842.7	843.2	843.7	844.2	844.8	845.5	846.2	846.9	847.6	847.8
142.5°	871.1	871.9	872.4	872.9	873.5	874.0	874.5	875.0	875.6	876.1	876.1
145°	898.6	899.4	899.8	900.1	900.5	900.8	901.2	901.5	901.9	902.2	902.4
147.5°	923.3	923.9	924.2	924.6	925.0	925.3	925.7	926.0	926.4	926.7	926.4
150°	945.6	946.0	946.4	946.7	947.1	947.4	947.8	948.1	948.5	948.8	948.7
152.5°	965.5	965.7	965.8	966.0	966.2	966.4	967.1	967.8	968.5	969.2	969.1
155°	983.1	983.0	983.2	983.4	983.6	983.7	984.6	985.5	986.4	987.2	987.1
157.5°	1000.3	1000.2	1000.0	999.9	999.7	999.5	1000.6	1001.6	1002.7	1003.7	1003.6
160°	1013.8	1013.6	1013.5	1013.3	1013.1	1012.9	1014.0	1015.0	1016.1	1017.1	1017.1
162.5°	1025.8	1025.5	1025.3	1025.1	1025.0	1024.8	1026.0	1027.2	1028.5	1029.7	1029.8
165°	1036.1	1035.7	1035.6	1035.4	1035.2	1035.0	1036.4	1037.9	1039.3	1040.7	1040.7
167.5°	1044.1	1043.7	1043.7	1043.7	1043.7	1043.7	1045.1	1046.5	1047.9	1049.3	1049.3
170°	1051.2	1050.8	1050.8	1050.8	1050.8	1050.8	1052.2	1053.6	1055.0	1056.4	1056.4
172.5°	1055.2	1054.9	1055.0	1055.2	1055.4	1055.6	1057.0	1058.4	1059.8	1061.2	1061.1
175°	1059.2	1058.8	1059.0	1059.2	1059.3	1059.5	1060.7	1062.0	1063.2	1064.4	1064.3
177.5°	1060.7	1060.4	1060.6	1060.7	1060.9	1061.1	1062.5	1063.9	1065.3	1066.7	1066.5
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P832419

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2521.1	2521.1	2521.1	2521.1
2.5°	2239.9	2234.8	2232.7	2230.6
5°	1920.0	1904.0	1900.4	1896.8
7.5°	1648.2	1641.5	1619.2	1597.0
10°	1427.5	1406.8	1397.5	1388.2
12.5°	1243.0	1223.9	1220.8	1217.7
15°	1099.8	1086.4	1081.7	1077.1
17.5°	1005.8	996.5	990.8	985.1
20°	936.0	929.3	925.1	921.0
22.5°	882.7	877.6	874.5	871.4
25°	831.6	823.8	821.2	818.7
27.5°	783.0	776.3	773.7	771.1
30°	737.5	731.8	728.2	724.6
32.5°	687.9	681.2	679.1	677.0
35°	644.0	639.8	637.8	635.7
37.5°	597.5	592.3	589.2	586.1
40°	557.7	555.1	553.5	552.0
42.5°	517.3	512.7	512.2	511.7
45°	477.0	472.4	471.3	470.3
47.5°	439.3	435.2	434.7	434.1
50°	397.4	391.8	387.6	383.5
52.5°	349.4	344.2	340.6	337.0
55°	305.4	299.8	296.7	293.6
57.5°	272.4	269.8	268.2	266.7
60°	245.5	243.9	242.9	241.9
62.5°	220.7	219.1	219.1	219.1
65°	197.9	196.4	194.8	193.3
67.5°	168.5	165.4	164.9	164.4
70°	132.8	128.2	127.7	127.1
72.5°	103.9	103.4	102.3	101.3
75°	85.8	84.8	84.8	84.8
77.5°	69.3	68.2	68.2	68.2
80°	53.2	52.7	53.2	53.8
82.5°	39.3	39.3	38.8	38.2
85°	25.3	24.8	24.8	24.8
87.5°	12.4	12.4	12.4	12.4
90°	22.6	23.0	23.3	23.7
92.5°	26.3	26.5	26.7	26.8
95°	30.0	30.0	30.0	30.0
97.5°	31.8	32.0	32.2	32.4
100°	32.6	32.8	33.0	33.2
102.5°	32.9	33.2	33.6	33.9
105°	33.7	34.0	34.4	34.7
107.5°	151.1	128.1	105.1	82.1
110°	292.4	267.3	242.2	217.1



TEST NUMBER: P832419

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	412.4	412.0	411.7	411.3
115°	462.1	462.8	463.5	464.2
117.5°	506.3	506.5	506.7	506.9
120°	551.1	551.1	551.1	551.1
122.5°	594.0	594.1	594.3	594.5
125°	633.7	634.1	634.4	634.8
127.5°	675.3	674.9	674.6	674.2
130°	713.2	712.8	712.5	712.1
132.5°	748.5	747.9	747.4	746.9
135°	784.0	783.5	782.9	782.4
137.5°	817.4	817.1	816.7	816.4
140°	847.4	847.1	846.7	846.4
142.5°	875.6	875.0	874.5	874.0
145°	902.4	902.4	902.4	902.4
147.5°	925.6	924.7	923.8	922.9
150°	948.2	947.7	947.1	946.6
152.5°	968.2	967.3	966.4	965.6
155°	986.1	985.0	984.0	982.9
157.5°	1002.1	1000.7	999.3	997.9
160°	1015.8	1014.6	1013.4	1012.1
162.5°	1028.7	1027.7	1026.6	1025.6
165°	1039.5	1038.3	1037.1	1035.8
167.5°	1047.9	1046.5	1045.1	1043.7
170°	1055.0	1053.6	1052.2	1050.8
172.5°	1059.5	1057.9	1056.4	1054.8
175°	1062.9	1061.5	1060.1	1058.7
177.5°	1064.8	1063.0	1061.3	1059.5
180°	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P832419

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.29	13.10	13.25	14.07	15.34	16.95	17.77	17.92	18.74	20.00
	3H	13.51	14.24	14.48	15.21	16.50	18.45	19.18	19.42	20.16	21.44
	4H	13.89	14.58	14.88	15.56	16.86	18.94	19.63	19.93	20.61	21.90
	6H	14.17	14.80	15.17	15.79	17.10	19.25	19.88	20.25	20.87	22.18
	8H	14.26	14.86	15.26	15.86	17.17	19.33	19.93	20.33	20.93	22.24
	12H	14.31	14.88	15.32	15.88	17.20	19.36	19.93	20.37	20.93	22.26
4H	2H	13.01	13.70	14.00	14.68	15.98	16.95	17.63	17.94	18.62	19.91
	3H	14.38	14.95	15.38	15.96	17.27	18.60	19.17	19.60	20.19	21.49
	4H	14.83	15.35	15.84	16.36	17.69	19.21	19.73	20.22	20.73	22.07
	6H	15.20	15.65	16.22	16.67	18.01	19.65	20.09	20.67	21.12	22.45
	8H	15.33	15.74	16.35	16.76	18.11	19.78	20.19	20.80	21.21	22.56
	12H	15.40	15.78	16.44	16.81	18.16	19.84	20.21	20.88	21.25	22.60
8H	4H	15.15	15.56	16.17	16.58	17.93	19.17	19.59	20.20	20.61	21.96
	6H	15.61	15.95	16.65	17.02	18.36	19.67	20.01	20.72	21.08	22.42
	8H	15.80	16.10	16.86	17.15	18.51	19.86	20.16	20.91	21.21	22.57
	12H	15.94	16.21	17.00	17.25	18.65	19.97	20.24	21.03	21.28	22.68
12H	4H	15.16	15.53	16.19	16.57	17.92	19.12	19.50	20.16	20.54	21.89
	6H	15.67	15.97	16.72	17.02	18.38	19.65	19.95	20.70	21.00	22.36
	8H	15.89	16.15	16.94	17.19	18.60	19.84	20.10	20.89	21.15	22.55