

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332081-935

Luminaire Tested: **S123DIP-S1165D1195U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332081-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8325.2 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	51	51	51														
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	51	49	48	43	43	43	43	43	43	43														
2	90	82	76	71	83	76	71	67	65	61	58	55	52	49	45	43	41	37	37	37	37	37	37	37														
3	82	73	65	60	75	67	61	56	58	53	49	48	45	42	40	37	35	31	31	31	31	31	31	31														
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27	27	27	27	27	27	27														
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27	24	24	24	24	24	24	24														
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21	21	21	21	21	21	21														
7	59	47	39	33	54	43	36	31	38	32	28	32	28	24	27	24	21	18	18	18	18	18	18	18														
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17	17	17	17	17	17	17														
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15	15	15	15	15	15	15														
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	14	14	14	14	14	14	14														

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15033	15033	15033	15033
5°	17928	15098	13380	15098
10°	22440	15021	12085	15021
15°	27524	14900	11251	14900
20°	32787	14712	10711	14712
25°	34815	14481	10592	14481
30°	29840	14315	10648	14315
35°	20752	14076	10759	14076
40°	15632	13797	10725	13797
45°	12979	13381	10589	13381
50°	11627	12532	10493	12532
55°	10869	11618	10363	11618
60°	10196	10663	10256	10663
65°	9584	9722	9928	9722
70°	8988	8645	9454	8645
75°	8052	7569	8667	7569
80°	7048	6205	7469	6205
85°	5521	4508	5014	4508



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.6	1.7
10°-20°	441.2	5.3
20°-30°	740.4	8.9
30°-40°	838.4	10.1
40°-50°	751.8	9.0
50°-60°	606.7	7.3
60°-70°	422.8	5.1
70°-80°	222.2	2.7
80°-90°	58.1	0.7
90°-100°	48.9	0.6
100°-110°	233.3	2.8
110°-120°	560.4	6.7
120°-130°	713.6	8.6
130°-140°	762.5	9.2
140°-150°	713.0	8.6
150°-160°	575.1	6.9
160°-170°	371.2	4.5
170°-180°	127.9	1.5
0°-30°	1319.2	15.8
0°-40°	2157.5	25.9
0°-60°	3516.1	42.2
0°-90°	4219.2	50.7
90°-120°	842.6	10.1
90°-150°	3031.7	36.4
90°-180°	4106.0	49.3
0°-180°	8325.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1397	1397	1397	1397	1397	
5°	1659	1397	1238	1397	1659	172
15°	2470	1337	1010	1337	2470	713
25°	2931	1219	892	1219	2931	1286
35°	1579	1071	819	1071	1579	1026
45°	853	879	696	879	853	675
55°	579	619	552	619	579	520
65°	376	382	390	382	376	375
75°	194	182	208	182	194	207
85°	45	36	41	36	45	54
90°	30	1	30	1	30	16
95°	38	61	38	61	38	32
105°	44	298	44	298	44	101
115°	588	559	588	559	588	543
125°	804	788	804	788	804	718
135°	991	981	991	981	991	764
145°	1143	1132	1143	1132	1143	714
155°	1245	1247	1245	1247	1245	574
165°	1312	1315	1312	1315	1312	371
175°	1341	1346	1341	1346	1341	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1482.2	1481.1	1478.4	1480.6	1476.3	1470.2	1469.7	1464.3	1448.6	1447.5	1443.2
5°	1659.2	1653.8	1653.1	1652.4	1643.0	1630.1	1605.8	1603.7	1571.2	1555.0	1535.4
7.5°	1888.4	1891.3	1881.5	1872.8	1843.8	1824.7	1798.6	1765.2	1725.3	1684.8	1657.9
10°	2053.1	2075.4	2047.6	2028.7	2011.1	1977.9	1939.4	1891.3	1843.2	1787.1	1744.5
12.5°	2229.6	2240.5	2234.9	2217.1	2189.7	2139.2	2070.9	2018.0	1973.8	1880.3	1842.5
15°	2469.9	2511.2	2484.8	2423.9	2425.2	2377.1	2287.8	2189.7	2137.6	2055.7	1944.1
17.5°	2725.9	2731.1	2719.8	2669.1	2635.3	2569.2	2486.8	2392.7	2287.2	2188.1	2069.7
20°	2862.3	2858.3	2834.6	2808.2	2750.0	2698.6	2608.6	2503.7	2368.4	2271.0	2141.7
22.5°	2938.2	2931.4	2920.2	2898.0	2849.7	2794.4	2713.6	2599.0	2470.1	2335.9	2186.6
25°	2931.4	2940.1	2941.5	2935.4	2918.5	2885.4	2821.8	2730.4	2601.9	2429.3	2273.6
27.5°	2666.1	2678.6	2714.7	2746.8	2782.7	2819.2	2814.3	2769.0	2673.8	2524.8	2334.5
30°	2400.8	2373.8	2440.8	2525.4	2582.9	2684.3	2741.3	2744.6	2691.1	2563.3	2377.8
32.5°	2032.7	2062.5	2092.1	2196.2	2321.9	2435.9	2549.1	2640.2	2650.6	2565.4	2403.3
35°	1579.3	1616.6	1670.7	1724.8	1860.2	1976.6	2175.5	2348.7	2486.8	2505.1	2405.5
37.5°	1272.7	1291.1	1325.3	1379.6	1468.1	1606.2	1760.1	1979.0	2179.0	2327.8	2334.3
40°	1112.5	1117.8	1156.4	1197.7	1269.5	1383.1	1521.8	1715.4	1954.9	2162.7	2249.3
42.5°	992.3	1004.2	1020.5	1060.2	1117.3	1202.9	1331.9	1491.8	1711.3	1950.4	2119.9
45°	852.6	866.2	876.3	902.7	943.3	1000.8	1090.8	1237.0	1404.1	1651.1	1879.1
47.5°	760.3	761.4	769.0	788.8	816.5	859.6	923.3	1017.2	1170.6	1371.0	1605.1
50°	694.3	705.1	707.8	723.3	745.0	776.8	829.6	909.5	1035.4	1211.3	1426.4
52.5°	647.7	651.0	658.6	669.8	688.7	713.5	759.2	821.7	920.6	1070.5	1268.3
55°	579.2	579.2	586.7	595.5	606.3	628.6	659.1	705.1	780.2	896.6	1060.3
57.5°	515.9	519.3	524.5	527.3	536.5	551.2	576.7	611.6	667.6	757.2	887.4
60°	473.6	479.7	479.1	484.5	492.7	504.1	525.8	554.2	604.2	676.0	785.7
62.5°	436.9	436.4	436.4	442.8	450.9	461.9	476.0	500.6	543.1	606.7	700.1
65°	376.3	374.9	379.6	383.7	386.4	394.5	405.4	427.0	455.4	502.7	575.1
67.5°	322.4	318.5	321.0	322.4	327.0	333.3	343.5	356.9	379.4	417.5	472.1
70°	285.6	282.1	281.5	282.8	286.9	291.6	299.1	311.9	332.9	363.3	403.3
72.5°	247.6	245.4	245.2	248.2	250.1	253.2	258.5	270.3	286.9	309.8	347.0
75°	193.6	193.6	193.6	194.2	196.2	199.0	203.0	209.1	222.0	238.2	263.2
77.5°	145.1	144.9	144.1	144.0	147.0	148.2	149.1	154.8	162.0	173.0	191.2
80°	113.7	110.3	111.7	113.7	115.0	115.7	117.8	119.1	125.2	131.3	144.1
82.5°	84.5	81.6	81.9	85.0	85.2	85.9	88.0	89.9	92.1	97.7	104.6
85°	44.7	44.7	45.4	45.4	46.0	45.4	47.4	48.0	48.0	51.4	55.4
87.5°	22.2	21.1	21.5	22.0	21.4	21.8	22.1	22.5	22.8	23.2	23.2
90°	30.0	29.5	29.1	28.7	28.2	27.6	26.7	25.7	24.9	24.0	21.1
92.5°	33.2	33.0	32.7	32.4	32.1	31.3	29.9	28.4	27.0	25.6	23.4
95°	38.0	38.0	38.0	38.0	38.0	37.2	35.6	34.1	32.5	31.0	28.6
97.5°	41.2	41.0	40.8	40.6	40.3	39.3	37.5	35.7	34.0	32.2	48.2
100°	42.0	41.8	41.6	41.3	41.2	40.1	38.3	36.6	34.8	33.0	67.7
102.5°	42.8	42.4	42.0	41.6	41.2	43.7	49.2	54.8	60.3	65.8	103.7
105°	44.0	43.6	43.1	42.7	42.3	61.6	101.0	140.3	179.7	219.0	239.1
107.5°	138.3	167.9	197.5	227.2	256.8	286.1	315.0	343.8	372.6	401.6	398.4
110°	275.1	306.9	338.6	370.5	402.3	421.8	429.1	436.4	443.8	451.2	448.7



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	471.9	478.6	485.3	492.1	498.8	502.1	502.0	501.8	501.7	501.5	499.1
115°	588.1	587.3	586.4	585.5	584.6	583.1	580.8	578.6	576.4	574.2	572.2
117.5°	653.4	653.2	653.1	652.9	652.7	651.7	650.0	648.2	646.4	644.6	643.6
120°	698.2	698.2	698.2	698.2	698.2	697.3	695.5	693.8	692.0	690.2	689.6
122.5°	742.3	742.1	741.8	741.7	741.5	740.8	739.6	738.3	737.1	735.8	734.9
125°	804.3	803.8	803.4	802.9	802.5	802.0	801.6	801.2	800.7	800.2	799.4
127.5°	863.8	864.4	864.8	865.2	865.6	865.5	864.8	864.1	863.4	862.6	861.6
130°	902.3	902.8	903.2	903.6	904.0	903.9	902.9	902.1	901.2	900.3	899.4
132.5°	937.5	938.1	938.7	939.4	940.0	939.9	939.0	938.1	937.2	936.3	935.6
135°	991.4	992.0	992.6	993.3	994.0	994.0	993.3	992.6	992.0	991.4	990.4
137.5°	1041.9	1042.4	1042.8	1043.3	1043.7	1043.4	1042.3	1041.3	1040.2	1039.1	1038.6
140°	1072.4	1072.8	1073.2	1073.7	1074.1	1073.9	1073.0	1072.1	1071.3	1070.3	1069.7
142.5°	1100.4	1101.0	1101.6	1102.3	1102.9	1102.8	1102.1	1101.4	1100.7	1099.9	1099.3
145°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.1	1142.7	1142.3	1141.8	1141.3	1140.9
147.5°	1175.4	1176.4	1177.4	1178.5	1179.5	1179.7	1179.3	1178.9	1178.5	1177.9	1177.5
150°	1199.4	1200.1	1200.8	1201.4	1202.0	1202.1	1201.7	1201.3	1200.8	1200.4	1200.0
152.5°	1218.6	1219.6	1220.6	1221.7	1222.7	1222.8	1222.0	1221.2	1220.4	1219.6	1219.3
155°	1245.4	1246.7	1248.1	1249.4	1250.7	1250.9	1249.7	1248.6	1247.5	1246.4	1246.2
157.5°	1268.0	1269.7	1271.4	1273.2	1275.0	1275.1	1273.8	1272.5	1271.2	1269.8	1270.1
160°	1282.4	1283.9	1285.6	1287.1	1288.7	1288.7	1287.4	1286.1	1284.8	1283.4	1283.7
162.5°	1296.0	1297.4	1298.7	1300.1	1301.5	1301.5	1299.9	1298.5	1296.9	1295.4	1295.6
165°	1312.4	1314.0	1315.5	1317.1	1318.6	1318.5	1316.7	1315.0	1313.2	1311.4	1311.6
167.5°	1324.2	1326.0	1327.7	1329.6	1331.4	1331.4	1329.6	1327.7	1326.0	1324.2	1324.2
170°	1331.5	1333.2	1335.0	1336.8	1338.5	1338.5	1336.8	1335.0	1333.2	1331.5	1331.5
172.5°	1335.4	1337.4	1339.4	1341.3	1343.2	1343.3	1341.5	1339.8	1338.0	1336.2	1336.0
175°	1341.4	1343.2	1345.0	1346.8	1348.5	1348.7	1347.1	1345.6	1344.0	1342.4	1342.2
177.5°	1343.2	1345.0	1346.8	1348.6	1350.3	1350.5	1349.1	1347.6	1346.3	1344.8	1344.6
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1439.9	1435.6	1431.3	1423.7	1417.2	1408.0	1405.3	1402.1	1392.3	1383.7	1377.2
5°	1527.9	1511.7	1488.0	1466.4	1448.8	1425.1	1411.5	1397.3	1377.0	1358.7	1343.8
7.5°	1620.0	1588.0	1551.2	1511.4	1474.4	1438.6	1409.8	1384.1	1355.6	1328.7	1307.8
10°	1693.1	1647.0	1595.6	1540.2	1492.7	1446.7	1408.2	1374.3	1337.8	1306.0	1279.6
12.5°	1776.4	1708.2	1637.3	1569.9	1513.9	1450.0	1403.3	1360.3	1318.9	1280.6	1250.9
15°	1875.1	1788.5	1704.5	1611.9	1526.6	1446.7	1391.3	1337.1	1289.1	1249.8	1211.9
17.5°	1965.0	1866.8	1756.3	1643.5	1540.7	1446.0	1368.2	1307.1	1247.0	1198.9	1161.1
20°	2015.9	1904.2	1779.0	1661.9	1548.3	1442.7	1357.5	1284.4	1219.3	1168.6	1126.0
22.5°	2059.7	1929.1	1799.6	1674.4	1547.7	1434.0	1337.4	1262.1	1191.8	1142.1	1096.7
25°	2105.1	1948.9	1818.9	1672.1	1530.7	1412.9	1304.7	1219.3	1149.0	1090.8	1044.1
27.5°	2144.1	1947.5	1793.3	1635.4	1503.8	1385.9	1270.2	1178.8	1104.1	1040.9	993.5
30°	2170.1	1950.2	1766.8	1610.5	1477.9	1356.1	1243.7	1151.7	1073.2	1008.9	964.2
32.5°	2186.3	1948.5	1742.4	1575.9	1436.8	1329.0	1215.0	1119.7	1039.1	975.9	932.9
35°	2195.8	1936.6	1700.5	1504.3	1370.3	1265.4	1170.0	1071.2	986.6	927.7	879.0
37.5°	2176.9	1911.6	1651.7	1435.2	1288.6	1185.3	1105.0	1020.8	939.9	875.1	833.1
40°	2147.1	1895.4	1613.9	1386.6	1232.3	1132.7	1064.5	981.9	902.0	840.4	801.2
42.5°	2090.2	1862.3	1572.2	1332.4	1173.8	1074.3	1011.3	942.4	866.9	809.0	769.8
45°	1951.5	1790.4	1509.7	1251.2	1087.4	984.6	929.1	879.0	810.6	754.5	720.7
47.5°	1759.1	1682.4	1419.3	1165.5	997.3	898.4	840.7	800.4	750.4	705.1	672.6
50°	1625.4	1593.5	1358.1	1107.1	937.2	840.4	785.0	748.4	712.6	667.2	637.4
52.5°	1471.1	1490.7	1286.7	1046.4	876.1	780.9	728.7	699.6	667.1	629.8	603.9
55°	1253.9	1324.9	1163.2	944.6	785.0	694.3	644.9	619.1	600.2	572.5	550.2
57.5°	1050.5	1140.9	1029.8	839.7	695.5	617.3	569.9	541.9	529.7	515.2	497.7
60°	929.8	1019.1	934.5	769.4	635.4	560.9	519.0	495.3	483.1	473.0	458.1
62.5°	822.0	912.4	841.4	697.9	576.4	507.4	470.8	447.7	438.2	432.9	420.3
65°	674.0	751.8	704.4	586.7	492.0	431.0	397.9	381.7	372.8	370.8	362.7
67.5°	548.5	607.8	573.3	486.6	412.1	359.5	331.3	317.5	310.7	310.0	303.9
70°	466.2	521.7	495.3	416.8	352.6	311.3	286.9	274.7	270.7	270.0	266.7
72.5°	402.3	441.1	420.1	354.6	304.9	267.4	249.5	236.9	232.2	233.2	230.9
75°	297.7	326.8	314.7	269.3	229.4	205.0	190.1	182.0	178.0	180.0	177.3
77.5°	214.2	232.6	221.7	190.3	165.7	148.1	137.1	132.1	128.5	128.3	127.1
80°	161.7	172.5	166.4	147.5	127.3	112.4	103.5	100.1	98.2	97.5	96.8
82.5°	115.2	124.4	117.2	104.2	90.4	81.5	76.5	72.0	70.5	70.9	70.3
85°	58.2	61.6	58.9	50.7	45.4	41.2	38.6	36.5	35.2	35.9	34.5
87.5°	23.7	23.7	21.4	18.8	17.2	15.2	14.7	13.2	12.6	13.0	12.9
90°	18.3	15.3	12.5	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	21.3	19.1	16.9	16.1	16.7	17.4	18.0	18.6	18.0	17.4	16.7
95°	26.1	23.7	21.3	24.5	33.7	42.8	51.9	61.0	51.9	42.8	33.7
97.5°	64.2	80.2	96.3	106.2	110.4	114.4	118.6	122.6	118.6	114.4	110.4
100°	102.4	137.1	171.7	186.8	182.4	178.0	173.5	169.0	173.5	178.0	182.4
102.5°	141.5	179.4	217.3	234.7	231.4	228.3	225.1	221.9	225.1	228.3	231.4
105°	259.1	279.1	299.1	307.9	305.4	303.0	300.6	298.1	300.6	303.0	305.4
107.5°	395.2	392.1	388.9	386.3	384.4	382.5	380.5	378.5	380.5	382.5	384.4
110°	446.3	443.8	441.3	439.3	437.5	435.7	433.9	432.1	433.9	435.7	437.5



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	496.7	494.2	491.8	489.7	488.2	486.6	484.9	483.4	484.9	486.6	488.2
115°	570.2	568.2	566.2	564.5	563.2	561.8	560.5	559.2	560.5	561.8	563.2
117.5°	642.6	641.5	640.5	639.2	637.6	635.8	634.2	632.6	634.2	635.8	637.6
120°	688.9	688.2	687.6	686.2	684.2	682.3	680.2	678.2	680.2	682.3	684.2
122.5°	734.2	733.3	732.5	731.2	729.5	727.9	726.3	724.6	726.3	727.9	729.5
125°	798.5	797.5	796.7	795.4	793.6	791.8	790.1	788.2	790.1	791.8	793.6
127.5°	860.6	859.5	858.4	857.0	855.2	853.4	851.6	849.9	851.6	853.4	855.2
130°	898.5	897.6	896.7	895.4	893.6	891.8	890.1	888.3	890.1	891.8	893.6
132.5°	934.9	934.2	933.4	932.2	930.4	928.7	926.9	925.1	926.9	928.7	930.4
135°	989.5	988.7	987.7	986.6	985.3	984.0	982.7	981.3	982.7	984.0	985.3
137.5°	1038.2	1037.7	1037.2	1036.1	1034.4	1032.7	1031.0	1029.3	1031.0	1032.7	1034.4
140°	1069.0	1068.3	1067.6	1066.7	1065.3	1064.0	1062.6	1061.4	1062.6	1064.0	1065.3
142.5°	1098.6	1097.9	1097.3	1096.3	1094.9	1093.6	1092.3	1091.0	1092.3	1093.6	1094.9
145°	1140.5	1140.1	1139.6	1138.6	1137.0	1135.5	1133.9	1132.4	1133.9	1135.5	1137.0
147.5°	1177.1	1176.6	1176.2	1175.4	1174.4	1173.5	1172.4	1171.4	1172.4	1173.5	1174.4
150°	1199.5	1199.0	1198.6	1198.1	1197.4	1196.7	1196.0	1195.4	1196.0	1196.7	1197.4
152.5°	1219.1	1218.7	1218.5	1218.2	1217.9	1217.6	1217.3	1217.0	1217.3	1217.6	1217.9
155°	1246.0	1245.7	1245.5	1245.6	1246.0	1246.5	1247.0	1247.4	1247.0	1246.5	1246.0
157.5°	1270.2	1270.5	1270.7	1270.8	1270.8	1270.9	1270.9	1271.0	1270.9	1270.9	1270.8
160°	1283.8	1284.1	1284.3	1284.5	1284.8	1285.0	1285.2	1285.4	1285.2	1285.0	1284.8
162.5°	1295.9	1296.1	1296.3	1296.7	1297.3	1297.9	1298.5	1299.0	1298.5	1297.9	1297.3
165°	1311.8	1312.1	1312.3	1312.8	1313.5	1314.1	1314.7	1315.4	1314.7	1314.1	1313.5
167.5°	1324.2	1324.2	1324.2	1324.6	1325.6	1326.5	1327.3	1328.3	1327.3	1326.5	1325.6
170°	1331.5	1331.5	1331.5	1331.9	1332.7	1333.7	1334.6	1335.4	1334.6	1333.7	1332.7
172.5°	1335.8	1335.7	1335.5	1335.9	1337.0	1338.1	1339.2	1340.2	1339.2	1338.1	1337.0
175°	1342.0	1341.8	1341.5	1342.0	1343.1	1344.2	1345.3	1346.4	1345.3	1344.2	1343.1
177.5°	1344.5	1344.3	1344.1	1344.5	1345.4	1346.3	1347.1	1348.1	1347.1	1346.3	1345.4
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1373.4	1369.6	1364.2	1356.1	1349.5	1339.3	1339.3	1340.9	1340.9	1340.4	1339.3
5°	1331.7	1321.5	1309.4	1295.2	1280.3	1265.4	1262.7	1257.2	1253.2	1250.5	1247.2
7.5°	1287.7	1269.7	1252.0	1232.1	1213.9	1198.9	1188.5	1179.8	1174.3	1168.4	1164.0
10°	1257.9	1235.6	1214.6	1193.7	1170.6	1152.4	1140.9	1132.7	1126.7	1121.3	1118.5
12.5°	1222.8	1197.2	1174.1	1154.2	1128.9	1110.2	1099.2	1095.4	1088.2	1076.9	1070.9
15°	1171.3	1147.6	1119.9	1089.4	1077.3	1054.3	1041.4	1035.4	1031.2	1022.4	1019.8
17.5°	1127.3	1096.3	1065.2	1042.5	1019.9	1001.2	994.0	986.4	981.0	973.9	971.7
20°	1092.2	1064.5	1036.0	1011.7	987.9	967.7	961.6	956.1	950.7	947.4	944.6
22.5°	1056.4	1028.7	1005.1	982.4	957.1	943.8	937.2	931.3	927.5	925.1	922.5
25°	1006.3	981.9	955.5	935.1	914.9	906.0	902.0	898.6	896.0	892.5	891.8
27.5°	961.3	934.8	913.3	894.4	879.9	872.5	868.6	866.9	867.5	868.7	869.5
30°	927.7	903.4	885.8	869.5	856.0	849.2	848.5	848.5	851.3	852.0	853.3
32.5°	896.9	876.8	859.3	843.5	833.3	828.6	831.2	831.2	833.4	835.2	837.6
35°	852.0	834.3	820.8	807.3	798.5	800.5	801.8	803.2	806.6	810.6	813.4
37.5°	809.0	793.8	779.6	769.1	765.1	768.7	772.0	774.8	778.7	781.9	784.5
40°	778.2	766.6	753.1	743.6	745.0	747.1	749.8	753.1	756.6	758.5	761.3
42.5°	749.5	737.4	727.2	719.3	721.2	723.8	725.4	727.2	731.1	734.8	736.3
45°	705.8	696.3	686.8	682.1	683.5	684.8	686.1	688.2	691.6	694.3	694.9
47.5°	656.7	650.1	643.7	639.0	641.2	640.7	642.5	646.8	647.8	649.5	653.2
50°	625.3	619.1	611.7	610.4	610.4	610.4	611.1	616.5	616.5	619.1	621.9
52.5°	590.6	586.7	581.9	579.5	578.4	578.4	581.3	584.0	585.0	588.8	591.6
55°	539.3	535.3	531.2	529.2	527.8	529.2	534.6	535.9	539.3	541.3	543.4
57.5°	485.9	482.8	479.5	478.4	478.1	479.9	482.8	486.9	487.8	494.0	497.1
60°	450.6	445.9	443.2	443.2	441.9	448.0	446.6	453.4	454.7	458.8	463.6
62.5°	414.4	408.0	407.0	407.0	408.9	410.6	412.5	415.5	419.0	424.1	427.8
65°	355.9	352.6	357.3	356.6	355.2	359.3	359.3	362.7	366.8	371.5	378.9
67.5°	300.6	298.9	299.2	299.2	301.3	303.6	305.5	308.4	313.3	318.3	323.2
70°	263.2	265.3	261.9	264.6	266.7	267.3	268.6	272.7	278.1	281.5	286.9
72.5°	227.0	226.8	227.2	228.3	230.3	231.5	232.9	237.5	243.5	246.3	250.6
75°	174.6	173.9	175.9	175.9	179.3	180.6	182.0	184.1	189.5	193.6	196.9
77.5°	127.5	128.3	127.9	130.2	129.2	129.5	133.7	135.8	136.3	144.3	146.0
80°	96.1	97.5	98.2	98.8	99.4	98.2	102.9	104.9	104.9	109.6	113.0
82.5°	69.1	69.8	71.6	72.2	72.4	73.8	74.1	75.7	77.3	79.3	83.8
85°	34.5	36.5	37.2	36.5	37.2	35.9	37.9	38.6	39.3	39.3	39.3
87.5°	12.8	13.9	13.9	15.0	15.1	16.2	16.4	15.4	15.6	17.4	15.4
90°	9.9	12.5	15.3	18.3	21.1	24.0	24.9	25.7	26.7	27.6	28.2
92.5°	16.1	16.9	19.1	21.3	23.4	25.6	27.0	28.4	29.9	31.3	32.1
95°	24.5	21.3	23.7	26.1	28.6	31.0	32.5	34.1	35.6	37.2	38.0
97.5°	106.2	96.3	80.2	64.2	48.2	32.2	34.0	35.7	37.5	39.3	40.3
100°	186.8	171.7	137.1	102.4	67.7	33.0	34.8	36.6	38.3	40.1	41.2
102.5°	234.7	217.3	179.4	141.5	103.7	65.8	60.3	54.8	49.2	43.7	41.2
105°	307.9	299.1	279.1	259.1	239.1	219.0	179.7	140.3	101.0	61.6	42.3
107.5°	386.3	388.9	392.1	395.2	398.4	401.6	372.6	343.8	315.0	286.1	256.8
110°	439.3	441.3	443.8	446.3	448.7	451.2	443.8	436.4	429.1	421.8	402.3



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	489.7	491.8	494.2	496.7	499.1	501.5	501.7	501.8	502.0	502.1	498.8
115°	564.5	566.2	568.2	570.2	572.2	574.2	576.4	578.6	580.8	583.1	584.6
117.5°	639.2	640.5	641.5	642.6	643.6	644.6	646.4	648.2	650.0	651.7	652.7
120°	686.2	687.6	688.2	688.9	689.6	690.2	692.0	693.8	695.5	697.3	698.2
122.5°	731.2	732.5	733.3	734.2	734.9	735.8	737.1	738.3	739.6	740.8	741.5
125°	795.4	796.7	797.5	798.5	799.4	800.2	800.7	801.2	801.6	802.0	802.5
127.5°	857.0	858.4	859.5	860.6	861.6	862.6	863.4	864.1	864.8	865.5	865.6
130°	895.4	896.7	897.6	898.5	899.4	900.3	901.2	902.1	902.9	903.9	904.0
132.5°	932.2	933.4	934.2	934.9	935.6	936.3	937.2	938.1	939.0	939.9	940.0
135°	986.6	987.7	988.7	989.5	990.4	991.4	992.0	992.6	993.3	994.0	994.0
137.5°	1036.1	1037.2	1037.7	1038.2	1038.6	1039.1	1040.2	1041.3	1042.3	1043.4	1043.7
140°	1066.7	1067.6	1068.3	1069.0	1069.7	1070.3	1071.3	1072.1	1073.0	1073.9	1074.1
142.5°	1096.3	1097.3	1097.9	1098.6	1099.3	1099.9	1100.7	1101.4	1102.1	1102.8	1102.9
145°	1138.6	1139.6	1140.1	1140.5	1140.9	1141.3	1141.8	1142.3	1142.7	1143.1	1143.3
147.5°	1175.4	1176.2	1176.6	1177.1	1177.5	1177.9	1178.5	1178.9	1179.3	1179.7	1179.5
150°	1198.1	1198.6	1199.0	1199.5	1200.0	1200.4	1200.8	1201.3	1201.7	1202.1	1202.0
152.5°	1218.2	1218.5	1218.7	1219.1	1219.3	1219.6	1220.4	1221.2	1222.0	1222.8	1222.7
155°	1245.6	1245.5	1245.7	1246.0	1246.2	1246.4	1247.5	1248.6	1249.7	1250.9	1250.7
157.5°	1270.8	1270.7	1270.5	1270.2	1270.1	1269.8	1271.2	1272.5	1273.8	1275.1	1275.0
160°	1284.5	1284.3	1284.1	1283.8	1283.7	1283.4	1284.8	1286.1	1287.4	1288.7	1288.7
162.5°	1296.7	1296.3	1296.1	1295.9	1295.6	1295.4	1296.9	1298.5	1299.9	1301.5	1301.5
165°	1312.8	1312.3	1312.1	1311.8	1311.6	1311.4	1313.2	1315.0	1316.7	1318.5	1318.6
167.5°	1324.6	1324.2	1324.2	1324.2	1324.2	1324.2	1326.0	1327.7	1329.6	1331.4	1331.4
170°	1331.9	1331.5	1331.5	1331.5	1331.5	1331.5	1333.2	1335.0	1336.8	1338.5	1338.5
172.5°	1335.9	1335.5	1335.7	1335.8	1336.0	1336.2	1338.0	1339.8	1341.5	1343.3	1343.2
175°	1342.0	1341.5	1341.8	1342.0	1342.2	1342.4	1344.0	1345.6	1347.1	1348.7	1348.5
177.5°	1344.5	1344.1	1344.3	1344.5	1344.6	1344.8	1346.3	1347.6	1349.1	1350.5	1350.3
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1335.5	1335.0	1338.8	1336.0	1338.8	1335.0	1335.5	1339.3	1340.4	1340.9	1340.9
5°	1243.0	1245.1	1238.3	1238.3	1238.3	1245.1	1243.0	1247.2	1250.5	1253.2	1257.2
7.5°	1160.8	1157.8	1158.0	1154.4	1158.0	1157.8	1160.8	1164.0	1168.4	1174.3	1179.8
10°	1110.4	1106.4	1105.0	1105.7	1105.0	1106.4	1110.4	1118.5	1121.3	1126.7	1132.7
12.5°	1068.8	1067.9	1059.0	1059.1	1059.0	1067.9	1068.8	1070.9	1076.9	1088.2	1095.4
15°	1019.8	1006.9	1005.6	1009.6	1005.6	1006.9	1019.8	1019.8	1022.4	1031.2	1035.4
17.5°	970.6	963.9	964.2	962.3	964.2	963.9	970.6	971.7	973.9	981.0	986.4
20°	944.6	940.6	939.9	935.1	939.9	940.6	944.6	944.6	947.4	950.7	956.1
22.5°	920.8	919.5	919.9	914.6	919.9	919.5	920.8	922.5	925.1	927.5	931.3
25°	891.2	894.6	891.8	891.8	891.8	894.6	891.2	891.8	892.5	896.0	898.6
27.5°	871.2	871.0	869.7	869.7	869.7	871.0	871.2	869.5	868.7	867.5	866.9
30°	856.0	855.3	856.7	856.7	856.7	855.3	856.0	853.3	852.0	851.3	848.5
32.5°	840.9	841.8	842.1	842.6	842.1	841.8	840.9	837.6	835.2	833.4	831.2
35°	817.4	818.1	820.1	818.8	820.1	818.1	817.4	813.4	810.6	806.6	803.2
37.5°	785.7	788.8	788.2	789.3	788.2	788.8	785.7	784.5	781.9	778.7	774.8
40°	761.9	764.0	763.3	763.3	763.3	764.0	761.9	761.3	758.5	756.6	753.1
42.5°	737.6	739.1	737.3	736.2	737.3	739.1	737.6	736.3	734.8	731.1	727.2
45°	697.7	696.3	698.4	695.6	698.4	696.3	697.7	694.9	694.3	691.6	688.2
47.5°	653.0	654.4	654.9	656.9	654.9	654.4	653.0	653.2	649.5	647.8	646.8
50°	623.2	627.2	627.2	626.6	627.2	627.2	623.2	621.9	619.1	616.5	616.5
52.5°	594.0	595.9	598.6	598.5	598.6	595.9	594.0	591.6	588.8	585.0	584.0
55°	548.8	550.2	551.5	552.2	551.5	550.2	548.8	543.4	541.3	539.3	535.9
57.5°	502.0	501.4	504.6	505.6	504.6	501.4	502.0	497.1	494.0	487.8	486.9
60°	468.9	468.9	474.3	476.4	474.3	468.9	468.9	463.6	458.8	454.7	453.4
62.5°	433.8	435.9	441.3	438.5	441.3	435.9	433.8	427.8	424.1	419.0	415.5
65°	382.3	387.7	387.0	389.8	387.0	387.7	382.3	378.9	371.5	366.8	362.7
67.5°	328.6	332.0	336.8	337.3	336.8	332.0	328.6	323.2	318.3	313.3	308.4
70°	292.3	295.7	298.4	300.4	298.4	295.7	292.3	286.9	281.5	278.1	272.7
72.5°	257.2	258.9	265.4	262.5	265.4	258.9	257.2	250.6	246.3	243.5	237.5
75°	201.6	206.4	210.4	208.4	210.4	206.4	201.6	196.9	193.6	189.5	184.1
77.5°	149.1	153.9	155.8	154.0	155.8	153.9	149.1	146.0	144.3	136.3	135.8
80°	117.8	117.1	121.1	120.5	121.1	117.1	117.8	113.0	109.6	104.9	104.9
82.5°	86.4	85.7	87.6	88.0	87.6	85.7	86.4	83.8	79.3	77.3	75.7
85°	41.9	44.0	41.2	40.6	41.2	44.0	41.9	39.3	39.3	39.3	38.6
87.5°	15.5	15.6	15.2	14.6	15.2	15.6	15.5	15.4	17.4	15.6	15.4
90°	28.7	29.1	29.5	30.0	29.5	29.1	28.7	28.2	27.6	26.7	25.7
92.5°	32.4	32.7	33.0	33.2	33.0	32.7	32.4	32.1	31.3	29.9	28.4
95°	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	37.2	35.6	34.1
97.5°	40.6	40.8	41.0	41.2	41.0	40.8	40.6	40.3	39.3	37.5	35.7
100°	41.3	41.6	41.8	42.0	41.8	41.6	41.3	41.2	40.1	38.3	36.6
102.5°	41.6	42.0	42.4	42.8	42.4	42.0	41.6	41.2	43.7	49.2	54.8
105°	42.7	43.1	43.6	44.0	43.6	43.1	42.7	42.3	61.6	101.0	140.3
107.5°	227.2	197.5	167.9	138.3	167.9	197.5	227.2	256.8	286.1	315.0	343.8
110°	370.5	338.6	306.9	275.1	306.9	338.6	370.5	402.3	421.8	429.1	436.4



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	492.1	485.3	478.6	471.9	478.6	485.3	492.1	498.8	502.1	502.0	501.8
115°	585.5	586.4	587.3	588.1	587.3	586.4	585.5	584.6	583.1	580.8	578.6
117.5°	652.9	653.1	653.2	653.4	653.2	653.1	652.9	652.7	651.7	650.0	648.2
120°	698.2	698.2	698.2	698.2	698.2	698.2	698.2	698.2	697.3	695.5	693.8
122.5°	741.7	741.8	742.1	742.3	742.1	741.8	741.7	741.5	740.8	739.6	738.3
125°	802.9	803.4	803.8	804.3	803.8	803.4	802.9	802.5	802.0	801.6	801.2
127.5°	865.2	864.8	864.4	863.8	864.4	864.8	865.2	865.6	865.5	864.8	864.1
130°	903.6	903.2	902.8	902.3	902.8	903.2	903.6	904.0	903.9	902.9	902.1
132.5°	939.4	938.7	938.1	937.5	938.1	938.7	939.4	940.0	939.9	939.0	938.1
135°	993.3	992.6	992.0	991.4	992.0	992.6	993.3	994.0	994.0	993.3	992.6
137.5°	1043.3	1042.8	1042.4	1041.9	1042.4	1042.8	1043.3	1043.7	1043.4	1042.3	1041.3
140°	1073.7	1073.2	1072.8	1072.4	1072.8	1073.2	1073.7	1074.1	1073.9	1073.0	1072.1
142.5°	1102.3	1101.6	1101.0	1100.4	1101.0	1101.6	1102.3	1102.9	1102.8	1102.1	1101.4
145°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.1	1142.7	1142.3
147.5°	1178.5	1177.4	1176.4	1175.4	1176.4	1177.4	1178.5	1179.5	1179.7	1179.3	1178.9
150°	1201.4	1200.8	1200.1	1199.4	1200.1	1200.8	1201.4	1202.0	1202.1	1201.7	1201.3
152.5°	1221.7	1220.6	1219.6	1218.6	1219.6	1220.6	1221.7	1222.7	1222.8	1222.0	1221.2
155°	1249.4	1248.1	1246.7	1245.4	1246.7	1248.1	1249.4	1250.7	1250.9	1249.7	1248.6
157.5°	1273.2	1271.4	1269.7	1268.0	1269.7	1271.4	1273.2	1275.0	1275.1	1273.8	1272.5
160°	1287.1	1285.6	1283.9	1282.4	1283.9	1285.6	1287.1	1288.7	1288.7	1287.4	1286.1
162.5°	1300.1	1298.7	1297.4	1296.0	1297.4	1298.7	1300.1	1301.5	1301.5	1299.9	1298.5
165°	1317.1	1315.5	1314.0	1312.4	1314.0	1315.5	1317.1	1318.6	1318.5	1316.7	1315.0
167.5°	1329.6	1327.7	1326.0	1324.2	1326.0	1327.7	1329.6	1331.4	1331.4	1329.6	1327.7
170°	1336.8	1335.0	1333.2	1331.5	1333.2	1335.0	1336.8	1338.5	1338.5	1336.8	1335.0
172.5°	1341.3	1339.4	1337.4	1335.4	1337.4	1339.4	1341.3	1343.2	1343.3	1341.5	1339.8
175°	1346.8	1345.0	1343.2	1341.4	1343.2	1345.0	1346.8	1348.5	1348.7	1347.1	1345.6
177.5°	1348.6	1346.8	1345.0	1343.2	1345.0	1346.8	1348.6	1350.3	1350.5	1349.1	1347.6
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1339.3	1339.3	1349.5	1356.1	1364.2	1369.6	1373.4	1377.2	1383.7	1392.3	1402.1
5°	1262.7	1265.4	1280.3	1295.2	1309.4	1321.5	1331.7	1343.8	1358.7	1377.0	1397.3
7.5°	1188.5	1198.9	1213.9	1232.1	1252.0	1269.7	1287.7	1307.8	1328.7	1355.6	1384.1
10°	1140.9	1152.4	1170.6	1193.7	1214.6	1235.6	1257.9	1279.6	1306.0	1337.8	1374.3
12.5°	1099.2	1110.2	1128.9	1154.2	1174.1	1197.2	1222.8	1250.9	1280.6	1318.9	1360.3
15°	1041.4	1054.3	1077.3	1089.4	1119.9	1147.6	1171.3	1211.9	1249.8	1289.1	1337.1
17.5°	994.0	1001.2	1019.9	1042.5	1065.2	1096.3	1127.3	1161.1	1198.9	1247.0	1307.1
20°	961.6	967.7	987.9	1011.7	1036.0	1064.5	1092.2	1126.0	1168.6	1219.3	1284.4
22.5°	937.2	943.8	957.1	982.4	1005.1	1028.7	1056.4	1096.7	1142.1	1191.8	1262.1
25°	902.0	906.0	914.9	935.1	955.5	981.9	1006.3	1044.1	1090.8	1149.0	1219.3
27.5°	868.6	872.5	879.9	894.4	913.3	934.8	961.3	993.5	1040.9	1104.1	1178.8
30°	848.5	849.2	856.0	869.5	885.8	903.4	927.7	964.2	1008.9	1073.2	1151.7
32.5°	831.2	828.6	833.3	843.5	859.3	876.8	896.9	932.9	975.9	1039.1	1119.7
35°	801.8	800.5	798.5	807.3	820.8	834.3	852.0	879.0	927.7	986.6	1071.2
37.5°	772.0	768.7	765.1	769.1	779.6	793.8	809.0	833.1	875.1	939.9	1020.8
40°	749.8	747.1	745.0	743.6	753.1	766.6	778.2	801.2	840.4	902.0	981.9
42.5°	725.4	723.8	721.2	719.3	727.2	737.4	749.5	769.8	809.0	866.9	942.4
45°	686.1	684.8	683.5	682.1	686.8	696.3	705.8	720.7	754.5	810.6	879.0
47.5°	642.5	640.7	641.2	639.0	643.7	650.1	656.7	672.6	705.1	750.4	800.4
50°	611.1	610.4	610.4	610.4	611.7	619.1	625.3	637.4	667.2	712.6	748.4
52.5°	581.3	578.4	578.4	579.5	581.9	586.7	590.6	603.9	629.8	667.1	699.6
55°	534.6	529.2	527.8	529.2	531.2	535.3	539.3	550.2	572.5	600.2	619.1
57.5°	482.8	479.9	478.1	478.4	479.5	482.8	485.9	497.7	515.2	529.7	541.9
60°	446.6	448.0	441.9	443.2	443.2	445.9	450.6	458.1	473.0	483.1	495.3
62.5°	412.5	410.6	408.9	407.0	407.0	408.0	414.4	420.3	432.9	438.2	447.7
65°	359.3	359.3	355.2	356.6	357.3	352.6	355.9	362.7	370.8	372.8	381.7
67.5°	305.5	303.6	301.3	299.2	299.2	298.9	300.6	303.9	310.0	310.7	317.5
70°	268.6	267.3	266.7	264.6	261.9	265.3	263.2	266.7	270.0	270.7	274.7
72.5°	232.9	231.5	230.3	228.3	227.2	226.8	227.0	230.9	233.2	232.2	236.9
75°	182.0	180.6	179.3	175.9	175.9	173.9	174.6	177.3	180.0	178.0	182.0
77.5°	133.7	129.5	129.2	130.2	127.9	128.3	127.5	127.1	128.3	128.5	132.1
80°	102.9	98.2	99.4	98.8	98.2	97.5	96.1	96.8	97.5	98.2	100.1
82.5°	74.1	73.8	72.4	72.2	71.6	69.8	69.1	70.3	70.9	70.5	72.0
85°	37.9	35.9	37.2	36.5	37.2	36.5	34.5	34.5	35.9	35.2	36.5
87.5°	16.4	16.2	15.1	15.0	13.9	13.9	12.8	12.9	13.0	12.6	13.2
90°	24.9	24.0	21.1	18.3	15.3	12.5	9.9	7.7	5.4	3.2	1.0
92.5°	27.0	25.6	23.4	21.3	19.1	16.9	16.1	16.7	17.4	18.0	18.6
95°	32.5	31.0	28.6	26.1	23.7	21.3	24.5	33.7	42.8	51.9	61.0
97.5°	34.0	32.2	48.2	64.2	80.2	96.3	106.2	110.4	114.4	118.6	122.6
100°	34.8	33.0	67.7	102.4	137.1	171.7	186.8	182.4	178.0	173.5	169.0
102.5°	60.3	65.8	103.7	141.5	179.4	217.3	234.7	231.4	228.3	225.1	221.9
105°	179.7	219.0	239.1	259.1	279.1	299.1	307.9	305.4	303.0	300.6	298.1
107.5°	372.6	401.6	398.4	395.2	392.1	388.9	386.3	384.4	382.5	380.5	378.5
110°	443.8	451.2	448.7	446.3	443.8	441.3	439.3	437.5	435.7	433.9	432.1



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	501.7	501.5	499.1	496.7	494.2	491.8	489.7	488.2	486.6	484.9	483.4
115°	576.4	574.2	572.2	570.2	568.2	566.2	564.5	563.2	561.8	560.5	559.2
117.5°	646.4	644.6	643.6	642.6	641.5	640.5	639.2	637.6	635.8	634.2	632.6
120°	692.0	690.2	689.6	688.9	688.2	687.6	686.2	684.2	682.3	680.2	678.2
122.5°	737.1	735.8	734.9	734.2	733.3	732.5	731.2	729.5	727.9	726.3	724.6
125°	800.7	800.2	799.4	798.5	797.5	796.7	795.4	793.6	791.8	790.1	788.2
127.5°	863.4	862.6	861.6	860.6	859.5	858.4	857.0	855.2	853.4	851.6	849.9
130°	901.2	900.3	899.4	898.5	897.6	896.7	895.4	893.6	891.8	890.1	888.3
132.5°	937.2	936.3	935.6	934.9	934.2	933.4	932.2	930.4	928.7	926.9	925.1
135°	992.0	991.4	990.4	989.5	988.7	987.7	986.6	985.3	984.0	982.7	981.3
137.5°	1040.2	1039.1	1038.6	1038.2	1037.7	1037.2	1036.1	1034.4	1032.7	1031.0	1029.3
140°	1071.3	1070.3	1069.7	1069.0	1068.3	1067.6	1066.7	1065.3	1064.0	1062.6	1061.4
142.5°	1100.7	1099.9	1099.3	1098.6	1097.9	1097.3	1096.3	1094.9	1093.6	1092.3	1091.0
145°	1141.8	1141.3	1140.9	1140.5	1140.1	1139.6	1138.6	1137.0	1135.5	1133.9	1132.4
147.5°	1178.5	1177.9	1177.5	1177.1	1176.6	1176.2	1175.4	1174.4	1173.5	1172.4	1171.4
150°	1200.8	1200.4	1200.0	1199.5	1199.0	1198.6	1198.1	1197.4	1196.7	1196.0	1195.4
152.5°	1220.4	1219.6	1219.3	1219.1	1218.7	1218.5	1218.2	1217.9	1217.6	1217.3	1217.0
155°	1247.5	1246.4	1246.2	1246.0	1245.7	1245.5	1245.6	1246.0	1246.5	1247.0	1247.4
157.5°	1271.2	1269.8	1270.1	1270.2	1270.5	1270.7	1270.8	1270.8	1270.9	1270.9	1271.0
160°	1284.8	1283.4	1283.7	1283.8	1284.1	1284.3	1284.5	1284.8	1285.0	1285.2	1285.4
162.5°	1296.9	1295.4	1295.6	1295.9	1296.1	1296.3	1296.7	1297.3	1297.9	1298.5	1299.0
165°	1313.2	1311.4	1311.6	1311.8	1312.1	1312.3	1312.8	1313.5	1314.1	1314.7	1315.4
167.5°	1326.0	1324.2	1324.2	1324.2	1324.2	1324.2	1324.6	1325.6	1326.5	1327.3	1328.3
170°	1333.2	1331.5	1331.5	1331.5	1331.5	1331.5	1331.9	1332.7	1333.7	1334.6	1335.4
172.5°	1338.0	1336.2	1336.0	1335.8	1335.7	1335.5	1335.9	1337.0	1338.1	1339.2	1340.2
175°	1344.0	1342.4	1342.2	1342.0	1341.8	1341.5	1342.0	1343.1	1344.2	1345.3	1346.4
177.5°	1346.3	1344.8	1344.6	1344.5	1344.3	1344.1	1344.5	1345.4	1346.3	1347.1	1348.1
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1405.3	1408.0	1417.2	1423.7	1431.3	1435.6	1439.9	1443.2	1447.5	1448.6	1464.3
5°	1411.5	1425.1	1448.8	1466.4	1488.0	1511.7	1527.9	1535.4	1555.0	1571.2	1603.7
7.5°	1409.8	1438.6	1474.4	1511.4	1551.2	1588.0	1620.0	1657.9	1684.8	1725.3	1765.2
10°	1408.2	1446.7	1492.7	1540.2	1595.6	1647.0	1693.1	1744.5	1787.1	1843.2	1891.3
12.5°	1403.3	1450.0	1513.9	1569.9	1637.3	1708.2	1776.4	1842.5	1880.3	1973.8	2018.0
15°	1391.3	1446.7	1526.6	1611.9	1704.5	1788.5	1875.1	1944.1	2055.7	2137.6	2189.7
17.5°	1368.2	1446.0	1540.7	1643.5	1756.3	1866.8	1965.0	2069.7	2188.1	2287.2	2392.7
20°	1357.5	1442.7	1548.3	1661.9	1779.0	1904.2	2015.9	2141.7	2271.0	2368.4	2503.7
22.5°	1337.4	1434.0	1547.7	1674.4	1799.6	1929.1	2059.7	2186.6	2335.9	2470.1	2599.0
25°	1304.7	1412.9	1530.7	1672.1	1818.9	1948.9	2105.1	2273.6	2429.3	2601.9	2730.4
27.5°	1270.2	1385.9	1503.8	1635.4	1793.3	1947.5	2144.1	2334.5	2524.8	2673.8	2769.0
30°	1243.7	1356.1	1477.9	1610.5	1766.8	1950.2	2170.1	2377.8	2563.3	2691.1	2744.6
32.5°	1215.0	1329.0	1436.8	1575.9	1742.4	1948.5	2186.3	2403.3	2565.4	2650.6	2640.2
35°	1170.0	1265.4	1370.3	1504.3	1700.5	1936.6	2195.8	2405.5	2505.1	2486.8	2348.7
37.5°	1105.0	1185.3	1288.6	1435.2	1651.7	1911.6	2176.9	2334.3	2327.8	2179.0	1979.0
40°	1064.5	1132.7	1232.3	1386.6	1613.9	1895.4	2147.1	2249.3	2162.7	1954.9	1715.4
42.5°	1011.3	1074.3	1173.8	1332.4	1572.2	1862.3	2090.2	2119.9	1950.4	1711.3	1491.8
45°	929.1	984.6	1087.4	1251.2	1509.7	1790.4	1951.5	1879.1	1651.1	1404.1	1237.0
47.5°	840.7	898.4	997.3	1165.5	1419.3	1682.4	1759.1	1605.1	1371.0	1170.6	1017.2
50°	785.0	840.4	937.2	1107.1	1358.1	1593.5	1625.4	1426.4	1211.3	1035.4	909.5
52.5°	728.7	780.9	876.1	1046.4	1286.7	1490.7	1471.1	1268.3	1070.5	920.6	821.7
55°	644.9	694.3	785.0	944.6	1163.2	1324.9	1253.9	1060.3	896.6	780.2	705.1
57.5°	569.9	617.3	695.5	839.7	1029.8	1140.9	1050.5	887.4	757.2	667.6	611.6
60°	519.0	560.9	635.4	769.4	934.5	1019.1	929.8	785.7	676.0	604.2	554.2
62.5°	470.8	507.4	576.4	697.9	841.4	912.4	822.0	700.1	606.7	543.1	500.6
65°	397.9	431.0	492.0	586.7	704.4	751.8	674.0	575.1	502.7	455.4	427.0
67.5°	331.3	359.5	412.1	486.6	573.3	607.8	548.5	472.1	417.5	379.4	356.9
70°	286.9	311.3	352.6	416.8	495.3	521.7	466.2	403.3	363.3	332.9	311.9
72.5°	249.5	267.4	304.9	354.6	420.1	441.1	402.3	347.0	309.8	286.9	270.3
75°	190.1	205.0	229.4	269.3	314.7	326.8	297.7	263.2	238.2	222.0	209.1
77.5°	137.1	148.1	165.7	190.3	221.7	232.6	214.2	191.2	173.0	162.0	154.8
80°	103.5	112.4	127.3	147.5	166.4	172.5	161.7	144.1	131.3	125.2	119.1
82.5°	76.5	81.5	90.4	104.2	117.2	124.4	115.2	104.6	97.7	92.1	89.9
85°	38.6	41.2	45.4	50.7	58.9	61.6	58.2	55.4	51.4	48.0	48.0
87.5°	14.7	15.2	17.2	18.8	21.4	23.7	23.7	23.2	23.2	22.8	22.5
90°	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9	25.7
92.5°	18.0	17.4	16.7	16.1	16.9	19.1	21.3	23.4	25.6	27.0	28.4
95°	51.9	42.8	33.7	24.5	21.3	23.7	26.1	28.6	31.0	32.5	34.1
97.5°	118.6	114.4	110.4	106.2	96.3	80.2	64.2	48.2	32.2	34.0	35.7
100°	173.5	178.0	182.4	186.8	171.7	137.1	102.4	67.7	33.0	34.8	36.6
102.5°	225.1	228.3	231.4	234.7	217.3	179.4	141.5	103.7	65.8	60.3	54.8
105°	300.6	303.0	305.4	307.9	299.1	279.1	259.1	239.1	219.0	179.7	140.3
107.5°	380.5	382.5	384.4	386.3	388.9	392.1	395.2	398.4	401.6	372.6	343.8
110°	433.9	435.7	437.5	439.3	441.3	443.8	446.3	448.7	451.2	443.8	436.4



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.9	486.6	488.2	489.7	491.8	494.2	496.7	499.1	501.5	501.7	501.8
115°	560.5	561.8	563.2	564.5	566.2	568.2	570.2	572.2	574.2	576.4	578.6
117.5°	634.2	635.8	637.6	639.2	640.5	641.5	642.6	643.6	644.6	646.4	648.2
120°	680.2	682.3	684.2	686.2	687.6	688.2	688.9	689.6	690.2	692.0	693.8
122.5°	726.3	727.9	729.5	731.2	732.5	733.3	734.2	734.9	735.8	737.1	738.3
125°	790.1	791.8	793.6	795.4	796.7	797.5	798.5	799.4	800.2	800.7	801.2
127.5°	851.6	853.4	855.2	857.0	858.4	859.5	860.6	861.6	862.6	863.4	864.1
130°	890.1	891.8	893.6	895.4	896.7	897.6	898.5	899.4	900.3	901.2	902.1
132.5°	926.9	928.7	930.4	932.2	933.4	934.2	934.9	935.6	936.3	937.2	938.1
135°	982.7	984.0	985.3	986.6	987.7	988.7	989.5	990.4	991.4	992.0	992.6
137.5°	1031.0	1032.7	1034.4	1036.1	1037.2	1037.7	1038.2	1038.6	1039.1	1040.2	1041.3
140°	1062.6	1064.0	1065.3	1066.7	1067.6	1068.3	1069.0	1069.7	1070.3	1071.3	1072.1
142.5°	1092.3	1093.6	1094.9	1096.3	1097.3	1097.9	1098.6	1099.3	1099.9	1100.7	1101.4
145°	1133.9	1135.5	1137.0	1138.6	1139.6	1140.1	1140.5	1140.9	1141.3	1141.8	1142.3
147.5°	1172.4	1173.5	1174.4	1175.4	1176.2	1176.6	1177.1	1177.5	1177.9	1178.5	1178.9
150°	1196.0	1196.7	1197.4	1198.1	1198.6	1199.0	1199.5	1200.0	1200.4	1200.8	1201.3
152.5°	1217.3	1217.6	1217.9	1218.2	1218.5	1218.7	1219.1	1219.3	1219.6	1220.4	1221.2
155°	1247.0	1246.5	1246.0	1245.6	1245.5	1245.7	1246.0	1246.2	1246.4	1247.5	1248.6
157.5°	1270.9	1270.9	1270.8	1270.8	1270.7	1270.5	1270.2	1270.1	1269.8	1271.2	1272.5
160°	1285.2	1285.0	1284.8	1284.5	1284.3	1284.1	1283.8	1283.7	1283.4	1284.8	1286.1
162.5°	1298.5	1297.9	1297.3	1296.7	1296.3	1296.1	1295.9	1295.6	1295.4	1296.9	1298.5
165°	1314.7	1314.1	1313.5	1312.8	1312.3	1312.1	1311.8	1311.6	1311.4	1313.2	1315.0
167.5°	1327.3	1326.5	1325.6	1324.6	1324.2	1324.2	1324.2	1324.2	1324.2	1326.0	1327.7
170°	1334.6	1333.7	1332.7	1331.9	1331.5	1331.5	1331.5	1331.5	1331.5	1333.2	1335.0
172.5°	1339.2	1338.1	1337.0	1335.9	1335.5	1335.7	1335.8	1336.0	1336.2	1338.0	1339.8
175°	1345.3	1344.2	1343.1	1342.0	1341.5	1341.8	1342.0	1342.2	1342.4	1344.0	1345.6
177.5°	1347.1	1346.3	1345.4	1344.5	1344.1	1344.3	1344.5	1344.6	1344.8	1346.3	1347.6
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1469.7	1470.2	1476.3	1480.6	1478.4	1481.1	1482.2
5°	1605.8	1630.1	1643.0	1652.4	1653.1	1653.8	1659.2
7.5°	1798.6	1824.7	1843.8	1872.8	1881.5	1891.3	1888.4
10°	1939.4	1977.9	2011.1	2028.7	2047.6	2075.4	2053.1
12.5°	2070.9	2139.2	2189.7	2217.1	2234.9	2240.5	2229.6
15°	2287.8	2377.1	2425.2	2423.9	2484.8	2511.2	2469.9
17.5°	2486.8	2569.2	2635.3	2669.1	2719.8	2731.1	2725.9
20°	2608.6	2698.6	2750.0	2808.2	2834.6	2858.3	2862.3
22.5°	2713.6	2794.4	2849.7	2898.0	2920.2	2931.4	2938.2
25°	2821.8	2885.4	2918.5	2935.4	2941.5	2940.1	2931.4
27.5°	2814.3	2819.2	2782.7	2746.8	2714.7	2678.6	2666.1
30°	2741.3	2684.3	2582.9	2525.4	2440.8	2373.8	2400.8
32.5°	2549.1	2435.9	2321.9	2196.2	2092.1	2062.5	2032.7
35°	2175.5	1976.6	1860.2	1724.8	1670.7	1616.6	1579.3
37.5°	1760.1	1606.2	1468.1	1379.6	1325.3	1291.1	1272.7
40°	1521.8	1383.1	1269.5	1197.7	1156.4	1117.8	1112.5
42.5°	1331.9	1202.9	1117.3	1060.2	1020.5	1004.2	992.3
45°	1090.8	1000.8	943.3	902.7	876.3	866.2	852.6
47.5°	923.3	859.6	816.5	788.8	769.0	761.4	760.3
50°	829.6	776.8	745.0	723.3	707.8	705.1	694.3
52.5°	759.2	713.5	688.7	669.8	658.6	651.0	647.7
55°	659.1	628.6	606.3	595.5	586.7	579.2	579.2
57.5°	576.7	551.2	536.5	527.3	524.5	519.3	515.9
60°	525.8	504.1	492.7	484.5	479.1	479.7	473.6
62.5°	476.0	461.9	450.9	442.8	436.4	436.4	436.9
65°	405.4	394.5	386.4	383.7	379.6	374.9	376.3
67.5°	343.5	333.3	327.0	322.4	321.0	318.5	322.4
70°	299.1	291.6	286.9	282.8	281.5	282.1	285.6
72.5°	258.5	253.2	250.1	248.2	245.2	245.4	247.6
75°	203.0	199.0	196.2	194.2	193.6	193.6	193.6
77.5°	149.1	148.2	147.0	144.0	144.1	144.9	145.1
80°	117.8	115.7	115.0	113.7	111.7	110.3	113.7
82.5°	88.0	85.9	85.2	85.0	81.9	81.6	84.5
85°	47.4	45.4	46.0	45.4	45.4	44.7	44.7
87.5°	22.1	21.8	21.4	22.0	21.5	21.1	22.2
90°	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	29.9	31.3	32.1	32.4	32.7	33.0	33.2
95°	35.6	37.2	38.0	38.0	38.0	38.0	38.0
97.5°	37.5	39.3	40.3	40.6	40.8	41.0	41.2
100°	38.3	40.1	41.2	41.3	41.6	41.8	42.0
102.5°	49.2	43.7	41.2	41.6	42.0	42.4	42.8
105°	101.0	61.6	42.3	42.7	43.1	43.6	44.0
107.5°	315.0	286.1	256.8	227.2	197.5	167.9	138.3
110°	429.1	421.8	402.3	370.5	338.6	306.9	275.1



TEST NUMBER: P332081-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	502.0	502.1	498.8	492.1	485.3	478.6	471.9
115°	580.8	583.1	584.6	585.5	586.4	587.3	588.1
117.5°	650.0	651.7	652.7	652.9	653.1	653.2	653.4
120°	695.5	697.3	698.2	698.2	698.2	698.2	698.2
122.5°	739.6	740.8	741.5	741.7	741.8	742.1	742.3
125°	801.6	802.0	802.5	802.9	803.4	803.8	804.3
127.5°	864.8	865.5	865.6	865.2	864.8	864.4	863.8
130°	902.9	903.9	904.0	903.6	903.2	902.8	902.3
132.5°	939.0	939.9	940.0	939.4	938.7	938.1	937.5
135°	993.3	994.0	994.0	993.3	992.6	992.0	991.4
137.5°	1042.3	1043.4	1043.7	1043.3	1042.8	1042.4	1041.9
140°	1073.0	1073.9	1074.1	1073.7	1073.2	1072.8	1072.4
142.5°	1102.1	1102.8	1102.9	1102.3	1101.6	1101.0	1100.4
145°	1142.7	1143.1	1143.3	1143.3	1143.3	1143.3	1143.3
147.5°	1179.3	1179.7	1179.5	1178.5	1177.4	1176.4	1175.4
150°	1201.7	1202.1	1202.0	1201.4	1200.8	1200.1	1199.4
152.5°	1222.0	1222.8	1222.7	1221.7	1220.6	1219.6	1218.6
155°	1249.7	1250.9	1250.7	1249.4	1248.1	1246.7	1245.4
157.5°	1273.8	1275.1	1275.0	1273.2	1271.4	1269.7	1268.0
160°	1287.4	1288.7	1288.7	1287.1	1285.6	1283.9	1282.4
162.5°	1299.9	1301.5	1301.5	1300.1	1298.7	1297.4	1296.0
165°	1316.7	1318.5	1318.6	1317.1	1315.5	1314.0	1312.4
167.5°	1329.6	1331.4	1331.4	1329.6	1327.7	1326.0	1324.2
170°	1336.8	1338.5	1338.5	1336.8	1335.0	1333.2	1331.5
172.5°	1341.5	1343.3	1343.2	1341.3	1339.4	1337.4	1335.4
175°	1347.1	1348.7	1348.5	1346.8	1345.0	1343.2	1341.4
177.5°	1349.1	1350.5	1350.3	1348.6	1346.8	1345.0	1343.2
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4

(END OF REPORT)