

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332047-935

Luminaire Tested: **S123DIP-S1165D365U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332047-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D365U935-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5347.4 lumens  
Efficiency: N/A  
Efficacy: 107.4 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79																				
1	105	100	96	93	100	96	93	89	88	85	83	81	79	77	74	72	71	67																				
2	96	88	82	77	91	85	79	74	78	73	69	71	68	65	65	63	60	57																				
3	88	78	70	64	83	75	68	62	69	63	59	63	59	55	58	55	52	49																				
4	80	69	61	55	77	67	59	53	61	55	50	57	52	48	52	48	45	42																				
5	74	62	54	48	71	60	52	46	55	49	44	51	46	42	47	43	39	37																				
6	68	56	48	42	65	54	46	41	50	43	39	46	41	37	43	38	35	32																				
7	63	51	42	37	60	49	41	36	46	39	34	42	37	33	39	35	31	29																				
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	31	28	26																				
9	55	42	35	29	53	41	34	29	38	32	28	36	30	26	33	29	25	23																				
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23	21																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15033	15033	15033	15033
5°	17928	15098	13380	15098
10°	22440	15021	12085	15021
15°	27524	14900	11251	14900
20°	32787	14712	10711	14712
25°	34815	14481	10592	14481
30°	29840	14315	10648	14315
35°	20752	14076	10759	14076
40°	15632	13797	10725	13797
45°	12979	13381	10589	13381
50°	11627	12532	10493	12532
55°	10869	11618	10363	11618
60°	10196	10663	10256	10663
65°	9584	9722	9928	9722
70°	8988	8645	9454	8645
75°	8052	7569	8667	7569
80°	7048	6205	7469	6205
85°	5521	4508	5014	4508



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.6	2.6
10°-20°	441.2	8.3
20°-30°	740.4	13.8
30°-40°	838.4	15.7
40°-50°	751.8	14.1
50°-60°	606.7	11.3
60°-70°	422.8	7.9
70°-80°	222.2	4.2
80°-90°	55.5	1.0
90°-100°	83.7	1.6
100°-110°	236.9	4.4
110°-120°	233.0	4.4
120°-130°	185.8	3.5
130°-140°	146.5	2.7
140°-150°	109.4	2.0
150°-160°	76.2	1.4
160°-170°	44.8	0.8
170°-180°	14.6	0.3
0°-30°	1319.2	24.7
0°-40°	2157.5	40.3
0°-60°	3516.1	65.8
0°-90°	4216.6	78.9
90°-120°	553.5	10.4
90°-150°	995.3	18.6
90°-180°	1131.0	21.2
0°-180°	5347.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1397	1397	1397	1397	1397	
5°	1659	1397	1238	1397	1659	172
15°	2470	1337	1010	1337	2470	713
25°	2931	1219	892	1219	2931	1286
35°	1579	1071	819	1071	1579	1026
45°	853	879	696	879	853	675
55°	579	619	552	619	579	520
65°	376	382	390	382	376	375
75°	194	182	208	182	194	207
85°	45	36	41	36	45	53
90°	9	1	9	1	9	7
95°	35	10	35	10	35	64
105°	387	35	387	35	387	382
115°	471	62	471	62	471	457
125°	371	87	371	87	371	336
135°	301	102	301	102	301	233
145°	235	116	235	116	235	150
155°	195	132	195	132	195	91
165°	170	144	170	144	170	49
175°	153	150	153	150	153	15
180°	150	150	150	150	150	



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1482.2	1481.1	1478.4	1480.6	1476.3	1470.2	1469.7	1464.3	1448.6	1447.5	1443.2
5°	1659.2	1653.8	1653.1	1652.4	1643.0	1630.1	1605.8	1603.7	1571.2	1555.0	1535.4
7.5°	1888.4	1891.3	1881.5	1872.8	1843.8	1824.7	1798.6	1765.2	1725.3	1684.8	1657.9
10°	2053.1	2075.4	2047.6	2028.7	2011.1	1977.9	1939.4	1891.3	1843.2	1787.1	1744.5
12.5°	2229.6	2240.5	2234.9	2217.1	2189.7	2139.2	2070.9	2018.0	1973.8	1880.3	1842.5
15°	2469.9	2511.2	2484.8	2423.9	2425.2	2377.1	2287.8	2189.7	2137.6	2055.7	1944.1
17.5°	2725.9	2731.1	2719.8	2669.1	2635.3	2569.2	2486.8	2392.7	2287.2	2188.1	2069.7
20°	2862.3	2858.3	2834.6	2808.2	2750.0	2698.6	2608.6	2503.7	2368.4	2271.0	2141.7
22.5°	2938.2	2931.4	2920.2	2898.0	2849.7	2794.4	2713.6	2599.0	2470.1	2335.9	2186.6
25°	2931.4	2940.1	2941.5	2935.4	2918.5	2885.4	2821.8	2730.4	2601.9	2429.3	2273.6
27.5°	2666.1	2678.6	2714.7	2746.8	2782.7	2819.2	2814.3	2769.0	2673.8	2524.8	2334.5
30°	2400.8	2373.8	2440.8	2525.4	2582.9	2684.3	2741.3	2744.6	2691.1	2563.3	2377.8
32.5°	2032.7	2062.5	2092.1	2196.2	2321.9	2435.9	2549.1	2640.2	2650.6	2565.4	2403.3
35°	1579.3	1616.6	1670.7	1724.8	1860.2	1976.6	2175.5	2348.7	2486.8	2505.1	2405.5
37.5°	1272.7	1291.1	1325.3	1379.6	1468.1	1606.2	1760.1	1979.0	2179.0	2327.8	2334.3
40°	1112.5	1117.8	1156.4	1197.7	1269.5	1383.1	1521.8	1715.4	1954.9	2162.7	2249.3
42.5°	992.3	1004.2	1020.5	1060.2	1117.3	1202.9	1331.9	1491.8	1711.3	1950.4	2119.9
45°	852.6	866.2	876.3	902.7	943.3	1000.8	1090.8	1237.0	1404.1	1651.1	1879.1
47.5°	760.3	761.4	769.0	788.8	816.5	859.6	923.3	1017.2	1170.6	1371.0	1605.1
50°	694.3	705.1	707.8	723.3	745.0	776.8	829.6	909.5	1035.4	1211.3	1426.4
52.5°	647.7	651.0	658.6	669.8	688.7	713.5	759.2	821.7	920.6	1070.5	1268.3
55°	579.2	579.2	586.7	595.5	606.3	628.6	659.1	705.1	780.2	896.6	1060.3
57.5°	515.9	519.3	524.5	527.3	536.5	551.2	576.7	611.6	667.6	757.2	887.4
60°	473.6	479.7	479.1	484.5	492.7	504.1	525.8	554.2	604.2	676.0	785.7
62.5°	436.9	436.4	436.4	442.8	450.9	461.9	476.0	500.6	543.1	606.7	700.1
65°	376.3	374.9	379.6	383.7	386.4	394.5	405.4	427.0	455.4	502.7	575.1
67.5°	322.4	318.5	321.0	322.4	327.0	333.3	343.5	356.9	379.4	417.5	472.1
70°	285.6	282.1	281.5	282.8	286.9	291.6	299.1	311.9	332.9	363.3	403.3
72.5°	247.6	245.4	245.2	248.2	250.1	253.2	258.5	270.3	286.9	309.8	347.0
75°	193.6	193.6	193.6	194.2	196.2	199.0	203.0	209.1	222.0	238.2	263.2
77.5°	145.1	144.9	144.1	144.0	147.0	148.2	149.1	154.8	162.0	173.0	191.2
80°	113.7	110.3	111.7	113.7	115.0	115.7	117.8	119.1	125.2	131.3	144.1
82.5°	84.5	81.6	81.9	85.0	85.2	85.9	88.0	89.9	92.1	97.7	104.6
85°	44.7	44.7	45.4	45.4	46.0	45.4	47.4	48.0	48.0	51.4	55.4
87.5°	18.0	17.0	17.5	17.9	17.5	17.9	18.3	18.9	19.3	19.9	20.3
90°	8.8	9.1	8.8	8.5	8.8	8.2	7.9	7.6	7.3	7.6	6.7
92.5°	14.6	15.2	14.9	15.8	16.4	17.9	20.3	25.7	35.3	46.8	51.5
95°	35.3	36.5	38.7	41.4	47.2	58.1	74.2	109.5	146.4	180.5	160.7
97.5°	96.1	98.7	106.9	120.6	143.1	179.4	218.7	273.0	299.1	279.7	204.7
100°	190.8	190.5	202.3	224.5	255.3	298.5	334.1	358.7	348.1	288.2	194.8
102.5°	279.8	286.9	296.8	314.4	338.3	365.7	386.4	387.2	350.5	272.3	180.1
105°	387.0	388.6	398.3	409.8	423.9	431.7	425.9	395.5	331.9	244.6	162.2
107.5°	448.8	451.5	454.8	458.7	458.5	447.6	420.9	371.5	299.5	220.2	150.8
110°	474.1	474.7	475.3	472.9	464.3	443.0	404.7	348.7	279.1	206.3	146.4



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	479.1	479.1	476.7	469.2	453.6	426.2	383.2	326.1	261.2	197.0	143.9
115°	470.7	469.2	463.0	449.7	426.9	393.7	349.0	296.0	239.8	187.1	143.0
117.5°	443.8	441.7	433.0	417.7	393.8	360.2	320.0	274.3	226.8	181.2	143.5
120°	421.4	419.6	412.2	395.2	371.2	340.4	303.9	262.9	220.0	178.6	144.6
122.5°	400.5	398.1	390.1	374.8	353.4	324.9	291.0	253.9	214.4	176.9	146.2
125°	371.2	369.1	361.4	348.1	328.6	304.3	275.1	241.9	207.2	174.6	148.8
127.5°	347.1	345.2	338.3	326.8	309.5	287.3	261.0	231.4	200.9	173.6	151.7
130°	333.5	331.1	324.7	313.7	297.6	276.9	252.3	224.8	197.4	172.8	153.7
132.5°	320.1	318.4	312.7	301.8	286.6	266.9	243.9	218.8	194.3	172.5	155.2
135°	300.9	298.8	293.3	284.2	269.2	251.9	232.1	210.5	190.2	172.2	157.3
137.5°	280.7	279.2	274.7	265.4	252.9	237.8	220.8	203.0	186.6	171.5	158.8
140°	266.6	266.8	262.0	253.5	241.9	228.8	214.2	198.7	184.3	171.3	159.7
142.5°	253.4	253.7	249.3	241.8	231.9	220.5	207.8	194.6	182.4	170.8	160.5
145°	235.2	234.6	232.1	225.8	218.2	209.3	199.6	189.6	179.8	170.0	160.9
147.5°	220.2	220.0	217.7	213.4	207.6	201.3	193.5	185.5	177.3	168.9	160.9
150°	211.5	211.5	209.7	206.3	201.7	196.0	189.6	182.5	175.6	168.0	160.9
152.5°	204.1	204.1	203.0	199.9	196.4	191.6	185.9	179.9	173.6	166.8	160.2
155°	195.0	194.8	194.2	191.7	188.9	185.3	180.7	175.9	170.7	164.6	159.5
157.5°	186.7	186.8	186.2	184.4	182.1	179.2	175.6	171.6	167.4	162.7	158.4
160°	181.3	181.7	181.7	179.8	177.7	175.6	172.5	169.2	165.2	161.3	157.9
162.5°	176.5	176.8	176.8	175.2	173.8	171.9	169.1	166.3	163.0	159.8	157.0
165°	170.0	170.0	170.4	169.2	168.0	166.4	164.3	162.5	160.1	157.6	155.5
167.5°	164.0	164.0	164.3	163.4	162.9	161.8	160.6	159.2	157.2	155.4	154.0
170°	160.3	160.3	160.7	160.1	159.7	159.1	157.9	157.0	155.5	153.9	153.1
172.5°	157.0	157.2	157.7	157.1	157.0	156.7	155.8	155.1	153.8	152.7	152.3
175°	153.1	153.3	153.7	153.3	153.3	153.3	152.7	152.4	151.8	151.2	151.2
177.5°	150.8	150.8	151.3	151.0	151.3	151.3	151.0	150.8	150.6	150.3	150.6
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1439.9	1435.6	1431.3	1423.7	1417.2	1408.0	1405.3	1402.1	1392.3	1383.7	1377.2
5°	1527.9	1511.7	1488.0	1466.4	1448.8	1425.1	1411.5	1397.3	1377.0	1358.7	1343.8
7.5°	1620.0	1588.0	1551.2	1511.4	1474.4	1438.6	1409.8	1384.1	1355.6	1328.7	1307.8
10°	1693.1	1647.0	1595.6	1540.2	1492.7	1446.7	1408.2	1374.3	1337.8	1306.0	1279.6
12.5°	1776.4	1708.2	1637.3	1569.9	1513.9	1450.0	1403.3	1360.3	1318.9	1280.6	1250.9
15°	1875.1	1788.5	1704.5	1611.9	1526.6	1446.7	1391.3	1337.1	1289.1	1249.8	1211.9
17.5°	1965.0	1866.8	1756.3	1643.5	1540.7	1446.0	1368.2	1307.1	1247.0	1198.9	1161.1
20°	2015.9	1904.2	1779.0	1661.9	1548.3	1442.7	1357.5	1284.4	1219.3	1168.6	1126.0
22.5°	2059.7	1929.1	1799.6	1674.4	1547.7	1434.0	1337.4	1262.1	1191.8	1142.1	1096.7
25°	2105.1	1948.9	1818.9	1672.1	1530.7	1412.9	1304.7	1219.3	1149.0	1090.8	1044.1
27.5°	2144.1	1947.5	1793.3	1635.4	1503.8	1385.9	1270.2	1178.8	1104.1	1040.9	993.5
30°	2170.1	1950.2	1766.8	1610.5	1477.9	1356.1	1243.7	1151.7	1073.2	1008.9	964.2
32.5°	2186.3	1948.5	1742.4	1575.9	1436.8	1329.0	1215.0	1119.7	1039.1	975.9	932.9
35°	2195.8	1936.6	1700.5	1504.3	1370.3	1265.4	1170.0	1071.2	986.6	927.7	879.0
37.5°	2176.9	1911.6	1651.7	1435.2	1288.6	1185.3	1105.0	1020.8	939.9	875.1	833.1
40°	2147.1	1895.4	1613.9	1386.6	1232.3	1132.7	1064.5	981.9	902.0	840.4	801.2
42.5°	2090.2	1862.3	1572.2	1332.4	1173.8	1074.3	1011.3	942.4	866.9	809.0	769.8
45°	1951.5	1790.4	1509.7	1251.2	1087.4	984.6	929.1	879.0	810.6	754.5	720.7
47.5°	1759.1	1682.4	1419.3	1165.5	997.3	898.4	840.7	800.4	750.4	705.1	672.6
50°	1625.4	1593.5	1358.1	1107.1	937.2	840.4	785.0	748.4	712.6	667.2	637.4
52.5°	1471.1	1490.7	1286.7	1046.4	876.1	780.9	728.7	699.6	667.1	629.8	603.9
55°	1253.9	1324.9	1163.2	944.6	785.0	694.3	644.9	619.1	600.2	572.5	550.2
57.5°	1050.5	1140.9	1029.8	839.7	695.5	617.3	569.9	541.9	529.7	515.2	497.7
60°	929.8	1019.1	934.5	769.4	635.4	560.9	519.0	495.3	483.1	473.0	458.1
62.5°	822.0	912.4	841.4	697.9	576.4	507.4	470.8	447.7	438.2	432.9	420.3
65°	674.0	751.8	704.4	586.7	492.0	431.0	397.9	381.7	372.8	370.8	362.7
67.5°	548.5	607.8	573.3	486.6	412.1	359.5	331.3	317.5	310.7	310.0	303.9
70°	466.2	521.7	495.3	416.8	352.6	311.3	286.9	274.7	270.7	270.0	266.7
72.5°	402.3	441.1	420.1	354.6	304.9	267.4	249.5	236.9	232.2	233.2	230.9
75°	297.7	326.8	314.7	269.3	229.4	205.0	190.1	182.0	178.0	180.0	177.3
77.5°	214.2	232.6	221.7	190.3	165.7	148.1	137.1	132.1	128.5	128.3	127.1
80°	161.7	172.5	166.4	147.5	127.3	112.4	103.5	100.1	98.2	97.5	96.8
82.5°	115.2	124.4	117.2	104.2	90.4	81.5	76.5	72.0	70.5	70.9	70.3
85°	58.2	61.6	58.9	50.7	45.4	41.2	38.6	36.5	35.2	35.9	34.5
87.5°	21.2	21.5	19.7	17.5	16.3	14.5	14.3	13.1	12.1	12.3	11.9
90°	5.8	4.9	4.0	3.4	2.8	1.8	1.2	0.6	1.2	1.8	2.8
92.5°	38.7	25.6	17.6	13.1	10.5	8.2	5.6	3.8	5.6	8.2	10.5
95°	110.7	65.4	39.5	27.7	19.8	14.6	11.3	10.3	11.3	14.6	19.8
97.5°	121.5	70.4	45.7	32.9	25.1	20.6	17.9	17.7	17.9	20.6	25.1
100°	114.7	69.7	48.4	36.5	29.2	25.0	22.8	22.6	22.8	25.0	29.2
102.5°	108.8	70.7	51.6	40.6	34.1	30.0	28.2	27.6	28.2	30.0	34.1
105°	104.7	73.4	56.9	47.4	41.7	38.1	36.2	35.3	36.2	38.1	41.7
107.5°	104.4	78.4	63.9	55.1	49.7	46.1	44.3	43.5	44.3	46.1	49.7
110°	105.6	82.5	68.8	60.3	55.1	51.7	50.2	49.2	50.2	51.7	55.1





TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	108.1	86.6	73.9	65.6	60.4	57.1	55.5	54.7	55.5	57.1	60.4
115°	111.9	93.4	81.9	73.6	68.4	65.4	63.6	62.3	63.6	65.4	68.4
117.5°	117.2	100.7	89.2	81.6	75.9	73.0	71.5	70.1	71.5	73.0	75.9
120°	121.1	105.3	94.3	86.7	80.9	77.9	76.4	75.4	76.4	77.9	80.9
122.5°	124.8	110.1	99.4	91.4	85.8	82.5	81.0	80.1	81.0	82.5	85.8
125°	130.5	117.2	106.5	98.2	92.5	89.1	87.3	86.7	87.3	89.1	92.5
127.5°	135.3	123.2	113.0	104.7	98.3	95.0	92.6	91.8	92.6	95.0	98.3
130°	138.4	126.9	116.8	108.7	102.2	98.6	95.8	95.0	95.8	98.6	102.2
132.5°	141.4	130.0	120.3	112.3	105.9	101.5	98.5	97.4	98.5	101.5	105.9
135°	145.2	134.7	125.4	117.2	110.7	106.2	102.8	101.6	102.8	106.2	110.7
137.5°	147.9	138.1	129.0	121.4	115.0	110.2	106.9	105.6	106.9	110.2	115.0
140°	149.4	140.3	131.5	123.8	117.8	112.9	109.9	108.3	109.9	112.9	117.8
142.5°	150.8	142.0	133.4	126.3	120.2	115.8	112.5	111.2	112.5	115.8	120.2
145°	152.4	144.2	136.3	129.3	124.2	119.6	116.8	115.9	116.8	119.6	124.2
147.5°	153.4	146.0	138.8	132.9	127.9	123.9	121.2	120.7	121.2	123.9	127.9
150°	153.7	147.2	140.3	134.7	130.5	126.6	124.2	123.8	124.2	126.6	130.5
152.5°	154.1	148.0	142.0	136.7	132.9	129.5	127.1	127.0	127.1	129.5	132.9
155°	154.3	149.4	144.2	140.0	136.6	133.5	131.7	131.7	131.7	133.5	136.6
157.5°	154.5	150.2	146.0	142.8	139.9	137.2	135.8	135.5	135.8	137.2	139.9
160°	154.5	150.9	147.2	144.2	142.1	139.7	138.4	138.4	138.4	139.7	142.1
162.5°	154.3	151.2	148.0	145.4	143.5	141.6	140.6	140.6	140.6	141.6	143.5
165°	153.7	151.5	149.1	147.0	145.8	144.2	143.6	143.9	143.6	144.2	145.8
167.5°	153.2	151.4	149.7	148.4	147.5	146.4	146.0	146.4	146.0	146.4	147.5
170°	152.4	151.2	149.7	149.1	148.4	147.6	147.2	147.8	147.2	147.6	148.4
172.5°	152.2	151.2	149.9	149.6	149.2	148.5	148.4	148.9	148.4	148.5	149.2
175°	151.5	150.9	150.3	150.0	150.0	149.4	149.7	150.0	149.7	149.4	150.0
177.5°	151.0	150.6	150.3	150.3	150.3	150.1	150.3	150.6	150.3	150.1	150.3
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1373.4	1369.6	1364.2	1356.1	1349.5	1339.3	1339.3	1340.9	1340.9	1340.4	1339.3
5°	1331.7	1321.5	1309.4	1295.2	1280.3	1265.4	1262.7	1257.2	1253.2	1250.5	1247.2
7.5°	1287.7	1269.7	1252.0	1232.1	1213.9	1198.9	1188.5	1179.8	1174.3	1168.4	1164.0
10°	1257.9	1235.6	1214.6	1193.7	1170.6	1152.4	1140.9	1132.7	1126.7	1121.3	1118.5
12.5°	1222.8	1197.2	1174.1	1154.2	1128.9	1110.2	1099.2	1095.4	1088.2	1076.9	1070.9
15°	1171.3	1147.6	1119.9	1089.4	1077.3	1054.3	1041.4	1035.4	1031.2	1022.4	1019.8
17.5°	1127.3	1096.3	1065.2	1042.5	1019.9	1001.2	994.0	986.4	981.0	973.9	971.7
20°	1092.2	1064.5	1036.0	1011.7	987.9	967.7	961.6	956.1	950.7	947.4	944.6
22.5°	1056.4	1028.7	1005.1	982.4	957.1	943.8	937.2	931.3	927.5	925.1	922.5
25°	1006.3	981.9	955.5	935.1	914.9	906.0	902.0	898.6	896.0	892.5	891.8
27.5°	961.3	934.8	913.3	894.4	879.9	872.5	868.6	866.9	867.5	868.7	869.5
30°	927.7	903.4	885.8	869.5	856.0	849.2	848.5	848.5	851.3	852.0	853.3
32.5°	896.9	876.8	859.3	843.5	833.3	828.6	831.2	831.2	833.4	835.2	837.6
35°	852.0	834.3	820.8	807.3	798.5	800.5	801.8	803.2	806.6	810.6	813.4
37.5°	809.0	793.8	779.6	769.1	765.1	768.7	772.0	774.8	778.7	781.9	784.5
40°	778.2	766.6	753.1	743.6	745.0	747.1	749.8	753.1	756.6	758.5	761.3
42.5°	749.5	737.4	727.2	719.3	721.2	723.8	725.4	727.2	731.1	734.8	736.3
45°	705.8	696.3	686.8	682.1	683.5	684.8	686.1	688.2	691.6	694.3	694.9
47.5°	656.7	650.1	643.7	639.0	641.2	640.7	642.5	646.8	647.8	649.5	653.2
50°	625.3	619.1	611.7	610.4	610.4	610.4	611.1	616.5	616.5	619.1	621.9
52.5°	590.6	586.7	581.9	579.5	578.4	578.4	581.3	584.0	585.0	588.8	591.6
55°	539.3	535.3	531.2	529.2	527.8	529.2	534.6	535.9	539.3	541.3	543.4
57.5°	485.9	482.8	479.5	478.4	478.1	479.9	482.8	486.9	487.8	494.0	497.1
60°	450.6	445.9	443.2	443.2	441.9	448.0	446.6	453.4	454.7	458.8	463.6
62.5°	414.4	408.0	407.0	407.0	408.9	410.6	412.5	415.5	419.0	424.1	427.8
65°	355.9	352.6	357.3	356.6	355.2	359.3	359.3	362.7	366.8	371.5	378.9
67.5°	300.6	298.9	299.2	299.2	301.3	303.6	305.5	308.4	313.3	318.3	323.2
70°	263.2	265.3	261.9	264.6	266.7	267.3	268.6	272.7	278.1	281.5	286.9
72.5°	227.0	226.8	227.2	228.3	230.3	231.5	232.9	237.5	243.5	246.3	250.6
75°	174.6	173.9	175.9	175.9	179.3	180.6	182.0	184.1	189.5	193.6	196.9
77.5°	127.5	128.3	127.9	130.2	129.2	129.5	133.7	135.8	136.3	144.3	146.0
80°	96.1	97.5	98.2	98.8	99.4	98.2	102.9	104.9	104.9	109.6	113.0
82.5°	69.1	69.8	71.6	72.2	72.4	73.8	74.1	75.7	77.3	79.3	83.8
85°	34.5	36.5	37.2	36.5	37.2	35.9	37.9	38.6	39.3	39.3	39.3
87.5°	11.5	12.1	11.8	12.5	12.1	12.9	12.8	11.8	11.9	13.5	11.5
90°	3.4	4.0	4.9	5.8	6.7	7.6	7.3	7.6	7.9	8.2	8.8
92.5°	13.1	17.6	25.6	38.7	51.5	46.8	35.3	25.7	20.3	17.9	16.4
95°	27.7	39.5	65.4	110.7	160.7	180.5	146.4	109.5	74.2	58.1	47.2
97.5°	32.9	45.7	70.4	121.5	204.7	279.7	299.1	273.0	218.7	179.4	143.1
100°	36.5	48.4	69.7	114.7	194.8	288.2	348.1	358.7	334.1	298.5	255.3
102.5°	40.6	51.6	70.7	108.8	180.1	272.3	350.5	387.2	386.4	365.7	338.3
105°	47.4	56.9	73.4	104.7	162.2	244.6	331.9	395.5	425.9	431.7	423.9
107.5°	55.1	63.9	78.4	104.4	150.8	220.2	299.5	371.5	420.9	447.6	458.5
110°	60.3	68.8	82.5	105.6	146.4	206.3	279.1	348.7	404.7	443.0	464.3



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	65.6	73.9	86.6	108.1	143.9	197.0	261.2	326.1	383.2	426.2	453.6
115°	73.6	81.9	93.4	111.9	143.0	187.1	239.8	296.0	349.0	393.7	426.9
117.5°	81.6	89.2	100.7	117.2	143.5	181.2	226.8	274.3	320.0	360.2	393.8
120°	86.7	94.3	105.3	121.1	144.6	178.6	220.0	262.9	303.9	340.4	371.2
122.5°	91.4	99.4	110.1	124.8	146.2	176.9	214.4	253.9	291.0	324.9	353.4
125°	98.2	106.5	117.2	130.5	148.8	174.6	207.2	241.9	275.1	304.3	328.6
127.5°	104.7	113.0	123.2	135.3	151.7	173.6	200.9	231.4	261.0	287.3	309.5
130°	108.7	116.8	126.9	138.4	153.7	172.8	197.4	224.8	252.3	276.9	297.6
132.5°	112.3	120.3	130.0	141.4	155.2	172.5	194.3	218.8	243.9	266.9	286.6
135°	117.2	125.4	134.7	145.2	157.3	172.2	190.2	210.5	232.1	251.9	269.2
137.5°	121.4	129.0	138.1	147.9	158.8	171.5	186.6	203.0	220.8	237.8	252.9
140°	123.8	131.5	140.3	149.4	159.7	171.3	184.3	198.7	214.2	228.8	241.9
142.5°	126.3	133.4	142.0	150.8	160.5	170.8	182.4	194.6	207.8	220.5	231.9
145°	129.3	136.3	144.2	152.4	160.9	170.0	179.8	189.6	199.6	209.3	218.2
147.5°	132.9	138.8	146.0	153.4	160.9	168.9	177.3	185.5	193.5	201.3	207.6
150°	134.7	140.3	147.2	153.7	160.9	168.0	175.6	182.5	189.6	196.0	201.7
152.5°	136.7	142.0	148.0	154.1	160.2	166.8	173.6	179.9	185.9	191.6	196.4
155°	140.0	144.2	149.4	154.3	159.5	164.6	170.7	175.9	180.7	185.3	188.9
157.5°	142.8	146.0	150.2	154.5	158.4	162.7	167.4	171.6	175.6	179.2	182.1
160°	144.2	147.2	150.9	154.5	157.9	161.3	165.2	169.2	172.5	175.6	177.7
162.5°	145.4	148.0	151.2	154.3	157.0	159.8	163.0	166.3	169.1	171.9	173.8
165°	147.0	149.1	151.5	153.7	155.5	157.6	160.1	162.5	164.3	166.4	168.0
167.5°	148.4	149.7	151.4	153.2	154.0	155.4	157.2	159.2	160.6	161.8	162.9
170°	149.1	149.7	151.2	152.4	153.1	153.9	155.5	157.0	157.9	159.1	159.7
172.5°	149.6	149.9	151.2	152.2	152.3	152.7	153.8	155.1	155.8	156.7	157.0
175°	150.0	150.3	150.9	151.5	151.2	151.2	151.8	152.4	152.7	153.3	153.3
177.5°	150.3	150.3	150.6	151.0	150.6	150.3	150.6	150.8	151.0	151.3	151.3
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1335.5	1335.0	1338.8	1336.0	1338.8	1335.0	1335.5	1339.3	1340.4	1340.9	1340.9
5°	1243.0	1245.1	1238.3	1238.3	1238.3	1245.1	1243.0	1247.2	1250.5	1253.2	1257.2
7.5°	1160.8	1157.8	1158.0	1154.4	1158.0	1157.8	1160.8	1164.0	1168.4	1174.3	1179.8
10°	1110.4	1106.4	1105.0	1105.7	1105.0	1106.4	1110.4	1118.5	1121.3	1126.7	1132.7
12.5°	1068.8	1067.9	1059.0	1059.1	1059.0	1067.9	1068.8	1070.9	1076.9	1088.2	1095.4
15°	1019.8	1006.9	1005.6	1009.6	1005.6	1006.9	1019.8	1019.8	1022.4	1031.2	1035.4
17.5°	970.6	963.9	964.2	962.3	964.2	963.9	970.6	971.7	973.9	981.0	986.4
20°	944.6	940.6	939.9	935.1	939.9	940.6	944.6	944.6	947.4	950.7	956.1
22.5°	920.8	919.5	919.9	914.6	919.9	919.5	920.8	922.5	925.1	927.5	931.3
25°	891.2	894.6	891.8	891.8	891.8	894.6	891.2	891.8	892.5	896.0	898.6
27.5°	871.2	871.0	869.7	869.7	869.7	871.0	871.2	869.5	868.7	867.5	866.9
30°	856.0	855.3	856.7	856.7	856.7	855.3	856.0	853.3	852.0	851.3	848.5
32.5°	840.9	841.8	842.1	842.6	842.1	841.8	840.9	837.6	835.2	833.4	831.2
35°	817.4	818.1	820.1	818.8	820.1	818.1	817.4	813.4	810.6	806.6	803.2
37.5°	785.7	788.8	788.2	789.3	788.2	788.8	785.7	784.5	781.9	778.7	774.8
40°	761.9	764.0	763.3	763.3	763.3	764.0	761.9	761.3	758.5	756.6	753.1
42.5°	737.6	739.1	737.3	736.2	737.3	739.1	737.6	736.3	734.8	731.1	727.2
45°	697.7	696.3	698.4	695.6	698.4	696.3	697.7	694.9	694.3	691.6	688.2
47.5°	653.0	654.4	654.9	656.9	654.9	654.4	653.0	653.2	649.5	647.8	646.8
50°	623.2	627.2	627.2	626.6	627.2	627.2	623.2	621.9	619.1	616.5	616.5
52.5°	594.0	595.9	598.6	598.5	598.6	595.9	594.0	591.6	588.8	585.0	584.0
55°	548.8	550.2	551.5	552.2	551.5	550.2	548.8	543.4	541.3	539.3	535.9
57.5°	502.0	501.4	504.6	505.6	504.6	501.4	502.0	497.1	494.0	487.8	486.9
60°	468.9	468.9	474.3	476.4	474.3	468.9	468.9	463.6	458.8	454.7	453.4
62.5°	433.8	435.9	441.3	438.5	441.3	435.9	433.8	427.8	424.1	419.0	415.5
65°	382.3	387.7	387.0	389.8	387.0	387.7	382.3	378.9	371.5	366.8	362.7
67.5°	328.6	332.0	336.8	337.3	336.8	332.0	328.6	323.2	318.3	313.3	308.4
70°	292.3	295.7	298.4	300.4	298.4	295.7	292.3	286.9	281.5	278.1	272.7
72.5°	257.2	258.9	265.4	262.5	265.4	258.9	257.2	250.6	246.3	243.5	237.5
75°	201.6	206.4	210.4	208.4	210.4	206.4	201.6	196.9	193.6	189.5	184.1
77.5°	149.1	153.9	155.8	154.0	155.8	153.9	149.1	146.0	144.3	136.3	135.8
80°	117.8	117.1	121.1	120.5	121.1	117.1	117.8	113.0	109.6	104.9	104.9
82.5°	86.4	85.7	87.6	88.0	87.6	85.7	86.4	83.8	79.3	77.3	75.7
85°	41.9	44.0	41.2	40.6	41.2	44.0	41.9	39.3	39.3	39.3	38.6
87.5°	11.5	11.5	11.0	10.4	11.0	11.5	11.5	11.5	13.5	11.9	11.8
90°	8.5	8.8	9.1	8.8	9.1	8.8	8.5	8.8	8.2	7.9	7.6
92.5°	15.8	14.9	15.2	14.6	15.2	14.9	15.8	16.4	17.9	20.3	25.7
95°	41.4	38.7	36.5	35.3	36.5	38.7	41.4	47.2	58.1	74.2	109.5
97.5°	120.6	106.9	98.7	96.1	98.7	106.9	120.6	143.1	179.4	218.7	273.0
100°	224.5	202.3	190.5	190.8	190.5	202.3	224.5	255.3	298.5	334.1	358.7
102.5°	314.4	296.8	286.9	279.8	286.9	296.8	314.4	338.3	365.7	386.4	387.2
105°	409.8	398.3	388.6	387.0	388.6	398.3	409.8	423.9	431.7	425.9	395.5
107.5°	458.7	454.8	451.5	448.8	451.5	454.8	458.7	458.5	447.6	420.9	371.5
110°	472.9	475.3	474.7	474.1	474.7	475.3	472.9	464.3	443.0	404.7	348.7



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	469.2	476.7	479.1	479.1	479.1	476.7	469.2	453.6	426.2	383.2	326.1
115°	449.7	463.0	469.2	470.7	469.2	463.0	449.7	426.9	393.7	349.0	296.0
117.5°	417.7	433.0	441.7	443.8	441.7	433.0	417.7	393.8	360.2	320.0	274.3
120°	395.2	412.2	419.6	421.4	419.6	412.2	395.2	371.2	340.4	303.9	262.9
122.5°	374.8	390.1	398.1	400.5	398.1	390.1	374.8	353.4	324.9	291.0	253.9
125°	348.1	361.4	369.1	371.2	369.1	361.4	348.1	328.6	304.3	275.1	241.9
127.5°	326.8	338.3	345.2	347.1	345.2	338.3	326.8	309.5	287.3	261.0	231.4
130°	313.7	324.7	331.1	333.5	331.1	324.7	313.7	297.6	276.9	252.3	224.8
132.5°	301.8	312.7	318.4	320.1	318.4	312.7	301.8	286.6	266.9	243.9	218.8
135°	284.2	293.3	298.8	300.9	298.8	293.3	284.2	269.2	251.9	232.1	210.5
137.5°	265.4	274.7	279.2	280.7	279.2	274.7	265.4	252.9	237.8	220.8	203.0
140°	253.5	262.0	266.8	266.6	266.8	262.0	253.5	241.9	228.8	214.2	198.7
142.5°	241.8	249.3	253.7	253.4	253.7	249.3	241.8	231.9	220.5	207.8	194.6
145°	225.8	232.1	234.6	235.2	234.6	232.1	225.8	218.2	209.3	199.6	189.6
147.5°	213.4	217.7	220.0	220.2	220.0	217.7	213.4	207.6	201.3	193.5	185.5
150°	206.3	209.7	211.5	211.5	211.5	209.7	206.3	201.7	196.0	189.6	182.5
152.5°	199.9	203.0	204.1	204.1	204.1	203.0	199.9	196.4	191.6	185.9	179.9
155°	191.7	194.2	194.8	195.0	194.8	194.2	191.7	188.9	185.3	180.7	175.9
157.5°	184.4	186.2	186.8	186.7	186.8	186.2	184.4	182.1	179.2	175.6	171.6
160°	179.8	181.7	181.7	181.3	181.7	181.7	179.8	177.7	175.6	172.5	169.2
162.5°	175.2	176.8	176.8	176.5	176.8	176.8	175.2	173.8	171.9	169.1	166.3
165°	169.2	170.4	170.0	170.0	170.0	170.4	169.2	168.0	166.4	164.3	162.5
167.5°	163.4	164.3	164.0	164.0	164.0	164.3	163.4	162.9	161.8	160.6	159.2
170°	160.1	160.7	160.3	160.3	160.3	160.7	160.1	159.7	159.1	157.9	157.0
172.5°	157.1	157.7	157.2	157.0	157.2	157.7	157.1	157.0	156.7	155.8	155.1
175°	153.3	153.7	153.3	153.1	153.3	153.7	153.3	153.3	153.3	152.7	152.4
177.5°	151.0	151.3	150.8	150.8	150.8	151.3	151.0	151.3	151.3	151.0	150.8
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1339.3	1339.3	1349.5	1356.1	1364.2	1369.6	1373.4	1377.2	1383.7	1392.3	1402.1
5°	1262.7	1265.4	1280.3	1295.2	1309.4	1321.5	1331.7	1343.8	1358.7	1377.0	1397.3
7.5°	1188.5	1198.9	1213.9	1232.1	1252.0	1269.7	1287.7	1307.8	1328.7	1355.6	1384.1
10°	1140.9	1152.4	1170.6	1193.7	1214.6	1235.6	1257.9	1279.6	1306.0	1337.8	1374.3
12.5°	1099.2	1110.2	1128.9	1154.2	1174.1	1197.2	1222.8	1250.9	1280.6	1318.9	1360.3
15°	1041.4	1054.3	1077.3	1089.4	1119.9	1147.6	1171.3	1211.9	1249.8	1289.1	1337.1
17.5°	994.0	1001.2	1019.9	1042.5	1065.2	1096.3	1127.3	1161.1	1198.9	1247.0	1307.1
20°	961.6	967.7	987.9	1011.7	1036.0	1064.5	1092.2	1126.0	1168.6	1219.3	1284.4
22.5°	937.2	943.8	957.1	982.4	1005.1	1028.7	1056.4	1096.7	1142.1	1191.8	1262.1
25°	902.0	906.0	914.9	935.1	955.5	981.9	1006.3	1044.1	1090.8	1149.0	1219.3
27.5°	868.6	872.5	879.9	894.4	913.3	934.8	961.3	993.5	1040.9	1104.1	1178.8
30°	848.5	849.2	856.0	869.5	885.8	903.4	927.7	964.2	1008.9	1073.2	1151.7
32.5°	831.2	828.6	833.3	843.5	859.3	876.8	896.9	932.9	975.9	1039.1	1119.7
35°	801.8	800.5	798.5	807.3	820.8	834.3	852.0	879.0	927.7	986.6	1071.2
37.5°	772.0	768.7	765.1	769.1	779.6	793.8	809.0	833.1	875.1	939.9	1020.8
40°	749.8	747.1	745.0	743.6	753.1	766.6	778.2	801.2	840.4	902.0	981.9
42.5°	725.4	723.8	721.2	719.3	727.2	737.4	749.5	769.8	809.0	866.9	942.4
45°	686.1	684.8	683.5	682.1	686.8	696.3	705.8	720.7	754.5	810.6	879.0
47.5°	642.5	640.7	641.2	639.0	643.7	650.1	656.7	672.6	705.1	750.4	800.4
50°	611.1	610.4	610.4	610.4	611.7	619.1	625.3	637.4	667.2	712.6	748.4
52.5°	581.3	578.4	578.4	579.5	581.9	586.7	590.6	603.9	629.8	667.1	699.6
55°	534.6	529.2	527.8	529.2	531.2	535.3	539.3	550.2	572.5	600.2	619.1
57.5°	482.8	479.9	478.1	478.4	479.5	482.8	485.9	497.7	515.2	529.7	541.9
60°	446.6	448.0	441.9	443.2	443.2	445.9	450.6	458.1	473.0	483.1	495.3
62.5°	412.5	410.6	408.9	407.0	407.0	408.0	414.4	420.3	432.9	438.2	447.7
65°	359.3	359.3	355.2	356.6	357.3	352.6	355.9	362.7	370.8	372.8	381.7
67.5°	305.5	303.6	301.3	299.2	299.2	298.9	300.6	303.9	310.0	310.7	317.5
70°	268.6	267.3	266.7	264.6	261.9	265.3	263.2	266.7	270.0	270.7	274.7
72.5°	232.9	231.5	230.3	228.3	227.2	226.8	227.0	230.9	233.2	232.2	236.9
75°	182.0	180.6	179.3	175.9	175.9	173.9	174.6	177.3	180.0	178.0	182.0
77.5°	133.7	129.5	129.2	130.2	127.9	128.3	127.5	127.1	128.3	128.5	132.1
80°	102.9	98.2	99.4	98.8	98.2	97.5	96.1	96.8	97.5	98.2	100.1
82.5°	74.1	73.8	72.4	72.2	71.6	69.8	69.1	70.3	70.9	70.5	72.0
85°	37.9	35.9	37.2	36.5	37.2	36.5	34.5	34.5	35.9	35.2	36.5
87.5°	12.8	12.9	12.1	12.5	11.8	12.1	11.5	11.9	12.3	12.1	13.1
90°	7.3	7.6	6.7	5.8	4.9	4.0	3.4	2.8	1.8	1.2	0.6
92.5°	35.3	46.8	51.5	38.7	25.6	17.6	13.1	10.5	8.2	5.6	3.8
95°	146.4	180.5	160.7	110.7	65.4	39.5	27.7	19.8	14.6	11.3	10.3
97.5°	299.1	279.7	204.7	121.5	70.4	45.7	32.9	25.1	20.6	17.9	17.7
100°	348.1	288.2	194.8	114.7	69.7	48.4	36.5	29.2	25.0	22.8	22.6
102.5°	350.5	272.3	180.1	108.8	70.7	51.6	40.6	34.1	30.0	28.2	27.6
105°	331.9	244.6	162.2	104.7	73.4	56.9	47.4	41.7	38.1	36.2	35.3
107.5°	299.5	220.2	150.8	104.4	78.4	63.9	55.1	49.7	46.1	44.3	43.5
110°	279.1	206.3	146.4	105.6	82.5	68.8	60.3	55.1	51.7	50.2	49.2



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	261.2	197.0	143.9	108.1	86.6	73.9	65.6	60.4	57.1	55.5	54.7
115°	239.8	187.1	143.0	111.9	93.4	81.9	73.6	68.4	65.4	63.6	62.3
117.5°	226.8	181.2	143.5	117.2	100.7	89.2	81.6	75.9	73.0	71.5	70.1
120°	220.0	178.6	144.6	121.1	105.3	94.3	86.7	80.9	77.9	76.4	75.4
122.5°	214.4	176.9	146.2	124.8	110.1	99.4	91.4	85.8	82.5	81.0	80.1
125°	207.2	174.6	148.8	130.5	117.2	106.5	98.2	92.5	89.1	87.3	86.7
127.5°	200.9	173.6	151.7	135.3	123.2	113.0	104.7	98.3	95.0	92.6	91.8
130°	197.4	172.8	153.7	138.4	126.9	116.8	108.7	102.2	98.6	95.8	95.0
132.5°	194.3	172.5	155.2	141.4	130.0	120.3	112.3	105.9	101.5	98.5	97.4
135°	190.2	172.2	157.3	145.2	134.7	125.4	117.2	110.7	106.2	102.8	101.6
137.5°	186.6	171.5	158.8	147.9	138.1	129.0	121.4	115.0	110.2	106.9	105.6
140°	184.3	171.3	159.7	149.4	140.3	131.5	123.8	117.8	112.9	109.9	108.3
142.5°	182.4	170.8	160.5	150.8	142.0	133.4	126.3	120.2	115.8	112.5	111.2
145°	179.8	170.0	160.9	152.4	144.2	136.3	129.3	124.2	119.6	116.8	115.9
147.5°	177.3	168.9	160.9	153.4	146.0	138.8	132.9	127.9	123.9	121.2	120.7
150°	175.6	168.0	160.9	153.7	147.2	140.3	134.7	130.5	126.6	124.2	123.8
152.5°	173.6	166.8	160.2	154.1	148.0	142.0	136.7	132.9	129.5	127.1	127.0
155°	170.7	164.6	159.5	154.3	149.4	144.2	140.0	136.6	133.5	131.7	131.7
157.5°	167.4	162.7	158.4	154.5	150.2	146.0	142.8	139.9	137.2	135.8	135.5
160°	165.2	161.3	157.9	154.5	150.9	147.2	144.2	142.1	139.7	138.4	138.4
162.5°	163.0	159.8	157.0	154.3	151.2	148.0	145.4	143.5	141.6	140.6	140.6
165°	160.1	157.6	155.5	153.7	151.5	149.1	147.0	145.8	144.2	143.6	143.9
167.5°	157.2	155.4	154.0	153.2	151.4	149.7	148.4	147.5	146.4	146.0	146.4
170°	155.5	153.9	153.1	152.4	151.2	149.7	149.1	148.4	147.6	147.2	147.8
172.5°	153.8	152.7	152.3	152.2	151.2	149.9	149.6	149.2	148.5	148.4	148.9
175°	151.8	151.2	151.2	151.5	150.9	150.3	150.0	150.0	149.4	149.7	150.0
177.5°	150.6	150.3	150.6	151.0	150.6	150.3	150.3	150.3	150.1	150.3	150.6
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1405.3	1408.0	1417.2	1423.7	1431.3	1435.6	1439.9	1443.2	1447.5	1448.6	1464.3
5°	1411.5	1425.1	1448.8	1466.4	1488.0	1511.7	1527.9	1535.4	1555.0	1571.2	1603.7
7.5°	1409.8	1438.6	1474.4	1511.4	1551.2	1588.0	1620.0	1657.9	1684.8	1725.3	1765.2
10°	1408.2	1446.7	1492.7	1540.2	1595.6	1647.0	1693.1	1744.5	1787.1	1843.2	1891.3
12.5°	1403.3	1450.0	1513.9	1569.9	1637.3	1708.2	1776.4	1842.5	1880.3	1973.8	2018.0
15°	1391.3	1446.7	1526.6	1611.9	1704.5	1788.5	1875.1	1944.1	2055.7	2137.6	2189.7
17.5°	1368.2	1446.0	1540.7	1643.5	1756.3	1866.8	1965.0	2069.7	2188.1	2287.2	2392.7
20°	1357.5	1442.7	1548.3	1661.9	1779.0	1904.2	2015.9	2141.7	2271.0	2368.4	2503.7
22.5°	1337.4	1434.0	1547.7	1674.4	1799.6	1929.1	2059.7	2186.6	2335.9	2470.1	2599.0
25°	1304.7	1412.9	1530.7	1672.1	1818.9	1948.9	2105.1	2273.6	2429.3	2601.9	2730.4
27.5°	1270.2	1385.9	1503.8	1635.4	1793.3	1947.5	2144.1	2334.5	2524.8	2673.8	2769.0
30°	1243.7	1356.1	1477.9	1610.5	1766.8	1950.2	2170.1	2377.8	2563.3	2691.1	2744.6
32.5°	1215.0	1329.0	1436.8	1575.9	1742.4	1948.5	2186.3	2403.3	2565.4	2650.6	2640.2
35°	1170.0	1265.4	1370.3	1504.3	1700.5	1936.6	2195.8	2405.5	2505.1	2486.8	2348.7
37.5°	1105.0	1185.3	1288.6	1435.2	1651.7	1911.6	2176.9	2334.3	2327.8	2179.0	1979.0
40°	1064.5	1132.7	1232.3	1386.6	1613.9	1895.4	2147.1	2249.3	2162.7	1954.9	1715.4
42.5°	1011.3	1074.3	1173.8	1332.4	1572.2	1862.3	2090.2	2119.9	1950.4	1711.3	1491.8
45°	929.1	984.6	1087.4	1251.2	1509.7	1790.4	1951.5	1879.1	1651.1	1404.1	1237.0
47.5°	840.7	898.4	997.3	1165.5	1419.3	1682.4	1759.1	1605.1	1371.0	1170.6	1017.2
50°	785.0	840.4	937.2	1107.1	1358.1	1593.5	1625.4	1426.4	1211.3	1035.4	909.5
52.5°	728.7	780.9	876.1	1046.4	1286.7	1490.7	1471.1	1268.3	1070.5	920.6	821.7
55°	644.9	694.3	785.0	944.6	1163.2	1324.9	1253.9	1060.3	896.6	780.2	705.1
57.5°	569.9	617.3	695.5	839.7	1029.8	1140.9	1050.5	887.4	757.2	667.6	611.6
60°	519.0	560.9	635.4	769.4	934.5	1019.1	929.8	785.7	676.0	604.2	554.2
62.5°	470.8	507.4	576.4	697.9	841.4	912.4	822.0	700.1	606.7	543.1	500.6
65°	397.9	431.0	492.0	586.7	704.4	751.8	674.0	575.1	502.7	455.4	427.0
67.5°	331.3	359.5	412.1	486.6	573.3	607.8	548.5	472.1	417.5	379.4	356.9
70°	286.9	311.3	352.6	416.8	495.3	521.7	466.2	403.3	363.3	332.9	311.9
72.5°	249.5	267.4	304.9	354.6	420.1	441.1	402.3	347.0	309.8	286.9	270.3
75°	190.1	205.0	229.4	269.3	314.7	326.8	297.7	263.2	238.2	222.0	209.1
77.5°	137.1	148.1	165.7	190.3	221.7	232.6	214.2	191.2	173.0	162.0	154.8
80°	103.5	112.4	127.3	147.5	166.4	172.5	161.7	144.1	131.3	125.2	119.1
82.5°	76.5	81.5	90.4	104.2	117.2	124.4	115.2	104.6	97.7	92.1	89.9
85°	38.6	41.2	45.4	50.7	58.9	61.6	58.2	55.4	51.4	48.0	48.0
87.5°	14.3	14.5	16.3	17.5	19.7	21.5	21.2	20.3	19.9	19.3	18.9
90°	1.2	1.8	2.8	3.4	4.0	4.9	5.8	6.7	7.6	7.3	7.6
92.5°	5.6	8.2	10.5	13.1	17.6	25.6	38.7	51.5	46.8	35.3	25.7
95°	11.3	14.6	19.8	27.7	39.5	65.4	110.7	160.7	180.5	146.4	109.5
97.5°	17.9	20.6	25.1	32.9	45.7	70.4	121.5	204.7	279.7	299.1	273.0
100°	22.8	25.0	29.2	36.5	48.4	69.7	114.7	194.8	288.2	348.1	358.7
102.5°	28.2	30.0	34.1	40.6	51.6	70.7	108.8	180.1	272.3	350.5	387.2
105°	36.2	38.1	41.7	47.4	56.9	73.4	104.7	162.2	244.6	331.9	395.5
107.5°	44.3	46.1	49.7	55.1	63.9	78.4	104.4	150.8	220.2	299.5	371.5
110°	50.2	51.7	55.1	60.3	68.8	82.5	105.6	146.4	206.3	279.1	348.7





TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	55.5	57.1	60.4	65.6	73.9	86.6	108.1	143.9	197.0	261.2	326.1
115°	63.6	65.4	68.4	73.6	81.9	93.4	111.9	143.0	187.1	239.8	296.0
117.5°	71.5	73.0	75.9	81.6	89.2	100.7	117.2	143.5	181.2	226.8	274.3
120°	76.4	77.9	80.9	86.7	94.3	105.3	121.1	144.6	178.6	220.0	262.9
122.5°	81.0	82.5	85.8	91.4	99.4	110.1	124.8	146.2	176.9	214.4	253.9
125°	87.3	89.1	92.5	98.2	106.5	117.2	130.5	148.8	174.6	207.2	241.9
127.5°	92.6	95.0	98.3	104.7	113.0	123.2	135.3	151.7	173.6	200.9	231.4
130°	95.8	98.6	102.2	108.7	116.8	126.9	138.4	153.7	172.8	197.4	224.8
132.5°	98.5	101.5	105.9	112.3	120.3	130.0	141.4	155.2	172.5	194.3	218.8
135°	102.8	106.2	110.7	117.2	125.4	134.7	145.2	157.3	172.2	190.2	210.5
137.5°	106.9	110.2	115.0	121.4	129.0	138.1	147.9	158.8	171.5	186.6	203.0
140°	109.9	112.9	117.8	123.8	131.5	140.3	149.4	159.7	171.3	184.3	198.7
142.5°	112.5	115.8	120.2	126.3	133.4	142.0	150.8	160.5	170.8	182.4	194.6
145°	116.8	119.6	124.2	129.3	136.3	144.2	152.4	160.9	170.0	179.8	189.6
147.5°	121.2	123.9	127.9	132.9	138.8	146.0	153.4	160.9	168.9	177.3	185.5
150°	124.2	126.6	130.5	134.7	140.3	147.2	153.7	160.9	168.0	175.6	182.5
152.5°	127.1	129.5	132.9	136.7	142.0	148.0	154.1	160.2	166.8	173.6	179.9
155°	131.7	133.5	136.6	140.0	144.2	149.4	154.3	159.5	164.6	170.7	175.9
157.5°	135.8	137.2	139.9	142.8	146.0	150.2	154.5	158.4	162.7	167.4	171.6
160°	138.4	139.7	142.1	144.2	147.2	150.9	154.5	157.9	161.3	165.2	169.2
162.5°	140.6	141.6	143.5	145.4	148.0	151.2	154.3	157.0	159.8	163.0	166.3
165°	143.6	144.2	145.8	147.0	149.1	151.5	153.7	155.5	157.6	160.1	162.5
167.5°	146.0	146.4	147.5	148.4	149.7	151.4	153.2	154.0	155.4	157.2	159.2
170°	147.2	147.6	148.4	149.1	149.7	151.2	152.4	153.1	153.9	155.5	157.0
172.5°	148.4	148.5	149.2	149.6	149.9	151.2	152.2	152.3	152.7	153.8	155.1
175°	149.7	149.4	150.0	150.0	150.3	150.9	151.5	151.2	151.2	151.8	152.4
177.5°	150.3	150.1	150.3	150.3	150.3	150.6	151.0	150.6	150.3	150.6	150.8
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1469.7	1470.2	1476.3	1480.6	1478.4	1481.1	1482.2
5°	1605.8	1630.1	1643.0	1652.4	1653.1	1653.8	1659.2
7.5°	1798.6	1824.7	1843.8	1872.8	1881.5	1891.3	1888.4
10°	1939.4	1977.9	2011.1	2028.7	2047.6	2075.4	2053.1
12.5°	2070.9	2139.2	2189.7	2217.1	2234.9	2240.5	2229.6
15°	2287.8	2377.1	2425.2	2423.9	2484.8	2511.2	2469.9
17.5°	2486.8	2569.2	2635.3	2669.1	2719.8	2731.1	2725.9
20°	2608.6	2698.6	2750.0	2808.2	2834.6	2858.3	2862.3
22.5°	2713.6	2794.4	2849.7	2898.0	2920.2	2931.4	2938.2
25°	2821.8	2885.4	2918.5	2935.4	2941.5	2940.1	2931.4
27.5°	2814.3	2819.2	2782.7	2746.8	2714.7	2678.6	2666.1
30°	2741.3	2684.3	2582.9	2525.4	2440.8	2373.8	2400.8
32.5°	2549.1	2435.9	2321.9	2196.2	2092.1	2062.5	2032.7
35°	2175.5	1976.6	1860.2	1724.8	1670.7	1616.6	1579.3
37.5°	1760.1	1606.2	1468.1	1379.6	1325.3	1291.1	1272.7
40°	1521.8	1383.1	1269.5	1197.7	1156.4	1117.8	1112.5
42.5°	1331.9	1202.9	1117.3	1060.2	1020.5	1004.2	992.3
45°	1090.8	1000.8	943.3	902.7	876.3	866.2	852.6
47.5°	923.3	859.6	816.5	788.8	769.0	761.4	760.3
50°	829.6	776.8	745.0	723.3	707.8	705.1	694.3
52.5°	759.2	713.5	688.7	669.8	658.6	651.0	647.7
55°	659.1	628.6	606.3	595.5	586.7	579.2	579.2
57.5°	576.7	551.2	536.5	527.3	524.5	519.3	515.9
60°	525.8	504.1	492.7	484.5	479.1	479.7	473.6
62.5°	476.0	461.9	450.9	442.8	436.4	436.4	436.9
65°	405.4	394.5	386.4	383.7	379.6	374.9	376.3
67.5°	343.5	333.3	327.0	322.4	321.0	318.5	322.4
70°	299.1	291.6	286.9	282.8	281.5	282.1	285.6
72.5°	258.5	253.2	250.1	248.2	245.2	245.4	247.6
75°	203.0	199.0	196.2	194.2	193.6	193.6	193.6
77.5°	149.1	148.2	147.0	144.0	144.1	144.9	145.1
80°	117.8	115.7	115.0	113.7	111.7	110.3	113.7
82.5°	88.0	85.9	85.2	85.0	81.9	81.6	84.5
85°	47.4	45.4	46.0	45.4	45.4	44.7	44.7
87.5°	18.3	17.9	17.5	17.9	17.5	17.0	18.0
90°	7.9	8.2	8.8	8.5	8.8	9.1	8.8
92.5°	20.3	17.9	16.4	15.8	14.9	15.2	14.6
95°	74.2	58.1	47.2	41.4	38.7	36.5	35.3
97.5°	218.7	179.4	143.1	120.6	106.9	98.7	96.1
100°	334.1	298.5	255.3	224.5	202.3	190.5	190.8
102.5°	386.4	365.7	338.3	314.4	296.8	286.9	279.8
105°	425.9	431.7	423.9	409.8	398.3	388.6	387.0
107.5°	420.9	447.6	458.5	458.7	454.8	451.5	448.8
110°	404.7	443.0	464.3	472.9	475.3	474.7	474.1



TEST NUMBER: P332047-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	383.2	426.2	453.6	469.2	476.7	479.1	479.1
115°	349.0	393.7	426.9	449.7	463.0	469.2	470.7
117.5°	320.0	360.2	393.8	417.7	433.0	441.7	443.8
120°	303.9	340.4	371.2	395.2	412.2	419.6	421.4
122.5°	291.0	324.9	353.4	374.8	390.1	398.1	400.5
125°	275.1	304.3	328.6	348.1	361.4	369.1	371.2
127.5°	261.0	287.3	309.5	326.8	338.3	345.2	347.1
130°	252.3	276.9	297.6	313.7	324.7	331.1	333.5
132.5°	243.9	266.9	286.6	301.8	312.7	318.4	320.1
135°	232.1	251.9	269.2	284.2	293.3	298.8	300.9
137.5°	220.8	237.8	252.9	265.4	274.7	279.2	280.7
140°	214.2	228.8	241.9	253.5	262.0	266.8	266.6
142.5°	207.8	220.5	231.9	241.8	249.3	253.7	253.4
145°	199.6	209.3	218.2	225.8	232.1	234.6	235.2
147.5°	193.5	201.3	207.6	213.4	217.7	220.0	220.2
150°	189.6	196.0	201.7	206.3	209.7	211.5	211.5
152.5°	185.9	191.6	196.4	199.9	203.0	204.1	204.1
155°	180.7	185.3	188.9	191.7	194.2	194.8	195.0
157.5°	175.6	179.2	182.1	184.4	186.2	186.8	186.7
160°	172.5	175.6	177.7	179.8	181.7	181.7	181.3
162.5°	169.1	171.9	173.8	175.2	176.8	176.8	176.5
165°	164.3	166.4	168.0	169.2	170.4	170.0	170.0
167.5°	160.6	161.8	162.9	163.4	164.3	164.0	164.0
170°	157.9	159.1	159.7	160.1	160.7	160.3	160.3
172.5°	155.8	156.7	157.0	157.1	157.7	157.2	157.0
175°	152.7	153.3	153.3	153.3	153.7	153.3	153.1
177.5°	151.0	151.3	151.3	151.0	151.3	150.8	150.8
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3

(END OF REPORT)