

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332011-940

Luminaire Tested: **S123DIP-S1000D585U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332011-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D585U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5672.3 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67
1	102	98	94	90	96	92	89	86	82	79	77	72	71	69	64	62	61	57
2	93	86	80	74	87	81	76	71	72	68	64	64	61	58	57	54	52	48
3	85	76	68	62	80	72	65	60	64	59	54	57	53	49	50	47	45	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	36
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27	24
8	57	45	37	31	54	42	35	30	38	32	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13481	13481	13481	13481
5°	16077	13539	11998	13539
10°	20122	13470	10837	13470
15°	24681	13362	10089	13362
20°	29402	13192	9606	13192
25°	31220	12986	9499	12986
30°	26759	12837	9548	12837
35°	18611	12623	9648	12623
40°	14018	12372	9618	12372
45°	11639	12000	9496	12000
50°	10426	11238	9409	11238
55°	9747	10419	9293	10419
60°	9143	9563	9197	9563
65°	8593	8716	8904	8716
70°	8060	7755	8478	7755
75°	7216	6791	7773	6791
80°	6316	5566	6695	5566
85°	4940	4039	4495	4039



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.4	2.2
10°-20°	395.6	7.0
20°-30°	664.0	11.7
30°-40°	751.8	13.3
40°-50°	674.2	11.9
50°-60°	544.1	9.6
60°-70°	379.1	6.7
70°-80°	199.3	3.5
80°-90°	50.7	0.9
90°-100°	139.8	2.5
100°-110°	395.9	7.0
110°-120°	389.5	6.9
120°-130°	310.7	5.5
130°-140°	244.9	4.3
140°-150°	182.8	3.2
150°-160°	127.4	2.2
160°-170°	74.9	1.3
170°-180°	24.4	0.4
0°-30°	1182.9	20.9
0°-40°	1934.7	34.1
0°-60°	3153.0	55.6
0°-90°	3782.1	66.7
90°-120°	925.2	16.3
90°-150°	1663.7	29.3
90°-180°	1890.0	33.3
0°-180°	5672.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1252	1252	1252	1252	1252	
5°	1488	1253	1110	1253	1488	154
15°	2215	1199	905	1199	2215	639
25°	2629	1093	800	1093	2629	1153
35°	1416	961	734	961	1416	920
45°	765	788	624	788	765	605
55°	519	555	495	555	519	466
65°	337	342	350	342	337	336
75°	174	163	187	163	174	186
85°	40	33	36	33	40	48
90°	15	1	15	1	15	10
95°	59	17	59	17	59	106
105°	647	59	647	59	647	638
115°	787	104	787	104	787	764
125°	620	145	620	145	620	562
135°	503	170	503	170	503	390
145°	393	194	393	194	393	250
155°	326	220	326	220	326	152
165°	284	241	284	241	284	81
175°	256	251	256	251	256	25
180°	251	251	251	251	251	



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1329.1	1328.2	1325.7	1327.7	1323.8	1318.5	1317.9	1313.1	1299.0	1298.1	1294.2
5°	1487.9	1483.0	1482.4	1481.8	1473.3	1461.8	1439.9	1438.2	1409.0	1394.5	1376.8
7.5°	1693.4	1696.0	1687.1	1679.4	1653.4	1636.3	1612.8	1582.9	1547.1	1510.8	1486.7
10°	1841.0	1861.1	1836.2	1819.2	1803.4	1773.7	1739.1	1696.0	1653.0	1602.6	1564.3
12.5°	1999.3	2009.1	2004.1	1988.2	1963.6	1918.3	1857.1	1809.6	1770.0	1686.0	1652.2
15°	2214.8	2251.8	2228.2	2173.5	2174.8	2131.7	2051.6	1963.6	1916.9	1843.4	1743.4
17.5°	2444.4	2449.1	2439.0	2393.4	2363.1	2303.9	2230.0	2145.6	2051.0	1962.1	1856.0
20°	2566.8	2563.1	2541.9	2518.2	2466.0	2419.9	2339.2	2245.1	2123.8	2036.4	1920.6
22.5°	2634.7	2628.7	2618.6	2598.8	2555.4	2505.9	2433.4	2330.6	2215.1	2094.7	1960.8
25°	2628.7	2636.5	2637.8	2632.3	2617.2	2587.4	2530.3	2448.5	2333.2	2178.4	2038.9
27.5°	2390.8	2402.0	2434.4	2463.2	2495.3	2528.1	2523.7	2483.1	2397.7	2264.1	2093.5
30°	2152.9	2128.7	2188.7	2264.6	2316.1	2407.2	2458.2	2461.2	2413.2	2298.6	2132.3
32.5°	1822.8	1849.5	1876.1	1969.4	2082.1	2184.3	2285.8	2367.5	2376.9	2300.5	2155.1
35°	1416.3	1449.7	1498.2	1546.8	1668.1	1772.5	1950.9	2106.2	2230.0	2246.4	2157.1
37.5°	1141.3	1157.8	1188.5	1237.2	1316.5	1440.3	1578.3	1774.7	1954.0	2087.4	2093.2
40°	997.6	1002.5	1037.1	1074.1	1138.4	1240.3	1364.7	1538.2	1753.0	1939.4	2017.0
42.5°	889.8	900.4	915.2	950.7	1001.9	1078.6	1194.3	1337.7	1534.6	1749.0	1900.9
45°	764.6	776.7	785.8	809.5	845.9	897.4	978.2	1109.2	1259.1	1480.6	1685.1
47.5°	681.8	682.8	689.6	707.4	732.2	770.9	828.0	912.1	1049.7	1229.4	1439.3
50°	622.6	632.3	634.7	648.6	668.1	696.6	744.0	815.6	928.4	1086.2	1279.2
52.5°	580.9	583.7	590.6	600.7	617.6	639.8	680.8	736.9	825.5	959.9	1137.4
55°	519.4	519.4	526.1	534.0	543.7	563.7	591.0	632.3	699.6	804.1	950.8
57.5°	462.6	465.7	470.4	472.8	481.1	494.3	517.1	548.4	598.7	679.0	795.8
60°	424.7	430.3	429.6	434.4	441.8	452.1	471.4	497.0	541.9	606.2	704.5
62.5°	391.7	391.4	391.3	397.1	404.4	414.2	426.9	448.9	487.1	544.0	627.8
65°	337.4	336.2	340.5	344.0	346.5	353.7	363.5	382.9	408.4	450.8	515.8
67.5°	289.1	285.5	287.8	289.1	293.2	298.9	308.0	320.0	340.3	374.4	423.3
70°	256.1	253.1	252.4	253.6	257.3	261.5	268.2	279.7	298.5	325.8	361.7
72.5°	222.1	220.0	219.9	222.6	224.3	227.0	231.8	242.4	257.3	277.8	311.2
75°	173.5	173.5	173.5	174.2	175.9	178.4	182.0	187.5	199.0	213.6	236.0
77.5°	130.1	130.0	129.2	129.1	131.8	132.9	133.8	138.8	145.3	155.1	171.5
80°	101.9	98.9	100.1	101.9	103.2	103.8	105.6	106.8	112.3	117.7	129.2
82.5°	75.7	73.2	73.4	76.2	76.4	77.0	78.9	80.6	82.7	87.7	93.8
85°	40.0	40.0	40.7	40.7	41.3	40.7	42.4	43.1	43.1	46.1	49.8
87.5°	17.5	16.7	17.0	17.4	17.0	17.3	17.7	18.1	18.5	19.1	19.3
90°	14.7	15.2	14.7	14.3	14.7	13.7	13.2	12.8	12.2	12.8	11.1
92.5°	24.5	25.4	24.9	26.5	27.4	30.1	34.0	42.8	59.0	78.2	86.1
95°	59.0	61.0	64.6	69.2	78.8	97.1	124.1	183.1	244.6	301.6	268.6
97.5°	160.6	165.0	178.7	201.6	239.2	300.0	365.6	456.5	500.1	467.4	342.1
100°	318.9	318.4	338.2	375.3	426.7	498.9	558.5	599.7	581.8	481.6	325.5
102.5°	467.8	479.5	496.1	525.5	565.4	611.3	646.0	647.3	585.9	455.2	301.1
105°	646.9	649.5	665.8	685.1	708.5	721.8	712.0	661.2	554.9	408.9	271.1
107.5°	750.1	754.7	760.3	766.8	766.3	748.2	703.7	621.1	500.6	368.0	252.0
110°	792.4	793.4	794.4	790.4	776.1	740.6	676.5	582.8	466.4	344.8	244.6



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	800.9	800.8	796.9	784.3	758.2	712.5	640.6	545.0	436.7	329.4	240.6
115°	786.8	784.3	774.1	751.7	713.5	658.2	583.4	494.9	400.8	312.8	239.1
117.5°	741.8	738.4	723.7	698.1	658.4	602.1	534.9	458.5	379.2	303.0	240.0
120°	704.5	701.3	689.2	660.7	620.5	569.1	508.1	439.4	367.7	298.5	241.6
122.5°	669.4	665.6	652.1	626.5	590.8	543.1	486.5	424.4	358.4	295.7	244.4
125°	620.5	617.0	604.2	581.8	549.3	508.6	459.8	404.3	346.3	291.9	248.7
127.5°	580.2	576.9	565.4	546.4	517.4	480.4	436.3	386.8	335.8	290.1	253.6
130°	557.4	553.4	542.7	524.4	497.4	462.8	421.6	375.9	330.1	288.9	256.8
132.5°	535.0	532.2	522.7	504.4	479.1	446.1	407.8	365.7	324.8	288.5	259.3
135°	503.0	499.4	490.3	475.0	450.1	421.2	388.1	352.0	317.9	287.8	263.0
137.5°	469.1	466.8	459.1	443.6	422.7	397.5	369.1	339.5	311.9	286.8	265.4
140°	445.5	446.0	437.9	423.7	404.3	382.5	358.0	332.2	308.2	286.3	267.0
142.5°	423.6	424.1	416.8	404.1	387.6	368.6	347.5	325.2	305.0	285.5	268.2
145°	393.2	392.2	388.1	377.4	364.7	349.9	333.7	316.8	300.6	284.3	269.0
147.5°	368.1	367.7	363.8	356.6	347.0	336.5	323.3	310.0	296.3	282.4	269.0
150°	353.5	353.5	350.4	344.8	337.2	327.5	316.8	305.1	293.5	280.7	269.0
152.5°	341.3	341.3	339.5	334.2	328.2	320.2	310.8	300.7	290.3	278.7	267.9
155°	326.0	325.5	324.5	320.4	315.8	309.8	302.1	294.0	285.3	275.2	266.5
157.5°	312.1	312.2	311.4	308.4	304.3	299.6	293.6	286.9	279.8	272.0	264.7
160°	303.1	303.6	303.6	300.6	297.0	293.5	288.4	282.8	276.2	269.6	263.9
162.5°	295.0	295.5	295.5	292.8	290.5	287.4	282.7	277.9	272.5	267.2	262.3
165°	284.3	284.3	284.8	282.8	280.7	278.2	274.6	271.6	267.5	263.5	259.9
167.5°	274.1	274.1	274.6	273.2	272.3	270.5	268.4	266.1	262.8	259.8	257.4
170°	268.0	268.0	268.6	267.5	267.0	266.0	263.9	262.4	259.9	257.3	255.8
172.5°	262.3	262.8	263.7	262.6	262.5	261.9	260.3	259.2	257.1	255.3	254.6
175°	255.8	256.4	256.8	256.4	256.4	256.4	255.3	254.9	253.8	252.8	252.8
177.5°	252.1	252.1	252.9	252.4	252.9	252.9	252.4	252.1	251.6	251.3	251.6
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1291.3	1287.4	1283.5	1276.8	1270.9	1262.7	1260.2	1257.3	1248.6	1240.8	1234.9
5°	1370.1	1355.6	1334.4	1314.9	1299.1	1277.9	1265.8	1253.0	1234.8	1218.4	1205.1
7.5°	1452.7	1424.1	1391.1	1355.3	1322.1	1290.0	1264.2	1241.2	1215.7	1191.5	1172.7
10°	1518.2	1476.9	1430.8	1381.1	1338.6	1297.4	1262.8	1232.4	1199.6	1171.1	1147.5
12.5°	1593.0	1531.8	1468.2	1407.7	1357.5	1300.3	1258.4	1219.8	1182.7	1148.3	1121.8
15°	1681.4	1603.7	1528.6	1445.4	1369.0	1297.4	1247.6	1199.1	1155.9	1120.8	1086.8
17.5°	1762.0	1674.0	1574.9	1473.8	1381.5	1296.6	1227.0	1172.1	1118.2	1075.1	1041.3
20°	1807.7	1707.5	1595.3	1490.3	1388.4	1293.7	1217.3	1151.7	1093.4	1047.9	1009.7
22.5°	1847.0	1729.8	1613.7	1501.5	1387.9	1285.9	1199.3	1131.8	1068.7	1024.1	983.5
25°	1887.8	1747.6	1631.1	1499.4	1372.6	1267.0	1169.9	1093.4	1030.4	978.2	936.3
27.5°	1922.7	1746.4	1608.1	1466.5	1348.5	1242.7	1139.1	1057.0	990.1	933.4	890.9
30°	1946.0	1748.8	1584.4	1444.2	1325.3	1216.0	1115.3	1032.8	962.4	904.7	864.7
32.5°	1960.6	1747.3	1562.5	1413.1	1288.3	1191.8	1089.6	1004.2	931.8	875.1	836.5
35°	1969.1	1736.7	1524.9	1348.9	1228.8	1134.7	1049.2	960.6	884.8	832.0	788.3
37.5°	1952.0	1714.2	1481.2	1287.0	1155.5	1062.8	990.9	915.4	842.8	784.7	747.1
40°	1925.4	1699.7	1447.2	1243.3	1105.0	1015.7	954.5	880.5	808.9	753.7	718.5
42.5°	1874.4	1670.0	1409.9	1194.8	1052.6	963.3	907.0	845.1	777.3	725.5	690.3
45°	1750.0	1605.6	1353.8	1122.0	975.1	882.9	833.1	788.3	726.9	676.5	646.2
47.5°	1577.4	1508.6	1272.7	1045.2	894.3	805.6	753.9	717.7	673.0	632.3	603.2
50°	1457.5	1429.1	1217.8	992.7	840.4	753.7	703.9	671.1	639.0	598.3	571.6
52.5°	1319.2	1336.8	1153.8	938.3	785.6	700.3	653.4	627.4	598.2	564.8	541.5
55°	1124.4	1188.1	1043.1	847.1	703.9	622.6	578.3	555.2	538.2	513.4	493.3
57.5°	942.0	1023.1	923.5	753.0	623.7	553.5	511.0	485.9	475.0	462.0	446.2
60°	833.7	913.8	838.0	689.9	569.8	503.0	465.4	444.2	433.3	424.2	410.8
62.5°	737.2	818.2	754.5	625.9	516.8	455.0	422.2	401.4	393.0	388.3	376.8
65°	604.4	674.1	631.7	526.1	441.1	386.6	356.8	342.2	334.4	332.5	325.2
67.5°	491.9	545.0	514.1	436.4	369.5	322.4	297.1	284.7	278.7	278.0	272.6
70°	418.1	467.9	444.2	373.8	316.1	279.1	257.3	246.4	242.7	242.1	239.1
72.5°	360.8	395.5	376.7	318.0	273.4	239.8	223.8	212.4	208.2	209.1	207.1
75°	267.0	293.1	282.1	241.5	205.7	183.9	170.5	163.3	159.6	161.4	159.0
77.5°	192.1	208.7	198.8	170.7	148.6	132.8	123.0	118.4	115.2	115.0	114.0
80°	145.0	154.7	149.3	132.2	114.0	100.8	92.8	89.8	88.0	87.4	86.8
82.5°	103.3	111.6	105.1	93.5	81.1	73.0	68.6	64.6	63.2	63.6	63.0
85°	52.2	55.2	52.8	45.5	40.7	37.0	34.6	32.7	31.6	32.2	30.9
87.5°	19.9	20.1	18.3	16.1	15.0	13.2	13.0	11.9	11.1	11.3	11.1
90°	9.6	8.1	6.6	5.6	4.5	3.0	2.1	1.0	2.1	3.0	4.5
92.5°	64.6	42.7	29.4	21.8	17.6	13.6	9.4	6.3	9.4	13.6	17.6
95°	185.1	109.3	66.1	46.3	33.1	24.4	18.8	17.3	18.8	24.4	33.1
97.5°	203.1	117.7	76.4	54.9	41.9	34.4	30.1	29.5	30.1	34.4	41.9
100°	191.7	116.5	80.9	61.0	48.9	41.7	38.2	37.6	38.2	41.7	48.9
102.5°	182.0	118.1	86.1	67.9	57.0	50.3	47.1	46.2	47.1	50.3	57.0
105°	175.0	122.6	95.1	79.4	69.6	63.6	60.5	59.0	60.5	63.6	69.6
107.5°	174.4	130.9	106.8	92.2	83.1	77.1	74.2	72.6	74.2	77.1	83.1
110°	176.5	137.9	114.9	100.7	92.0	86.5	83.9	82.4	83.9	86.5	92.0



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	180.6	144.7	123.5	109.7	101.0	95.4	92.9	91.3	92.9	95.4	101.0
115°	187.2	156.1	136.8	123.1	114.4	109.3	106.3	104.2	106.3	109.3	114.4
117.5°	195.9	168.3	149.1	136.4	126.7	122.1	119.5	117.2	119.5	122.1	126.7
120°	202.4	175.9	157.7	145.0	135.3	130.2	127.7	126.2	127.7	130.2	135.3
122.5°	208.6	184.1	166.2	152.7	143.4	137.9	135.4	133.8	135.4	137.9	143.4
125°	218.2	195.8	178.0	164.3	154.6	149.0	146.0	145.0	146.0	149.0	154.6
127.5°	226.1	206.0	188.8	175.0	164.3	158.7	154.9	153.4	154.9	158.7	164.3
130°	231.4	212.0	195.3	181.6	170.9	164.8	160.2	158.7	160.2	164.8	170.9
132.5°	236.3	217.4	201.0	187.7	177.0	169.7	164.7	162.7	164.7	169.7	177.0
135°	242.6	225.3	209.6	195.8	185.1	177.5	171.9	169.9	171.9	177.5	185.1
137.5°	247.3	230.8	215.6	203.0	192.3	184.2	178.7	176.6	178.7	184.2	192.3
140°	249.8	234.4	219.7	207.0	196.8	188.7	183.6	181.1	183.6	188.7	196.8
142.5°	252.2	237.3	223.0	211.1	200.9	193.6	188.1	185.9	188.1	193.6	200.9
145°	254.9	241.1	227.8	216.2	207.5	199.9	195.3	193.8	195.3	199.9	207.5
147.5°	256.5	244.2	232.0	222.0	213.7	207.1	202.6	201.7	202.6	207.1	213.7
150°	256.8	246.2	234.4	225.3	218.2	211.6	207.5	207.0	207.5	211.6	218.2
152.5°	257.7	247.4	237.3	228.5	222.3	216.5	212.4	212.3	212.4	216.5	222.3
155°	257.9	249.8	241.1	234.0	228.4	223.3	220.3	220.3	220.3	223.3	228.4
157.5°	258.4	251.0	244.2	238.6	233.9	229.3	226.9	226.5	226.9	229.3	233.9
160°	258.4	252.3	246.2	241.1	237.6	233.4	231.4	231.4	231.4	233.4	237.6
162.5°	258.0	252.7	247.4	243.1	240.0	236.7	235.1	235.1	235.1	236.7	240.0
165°	256.8	253.2	249.2	245.7	243.6	241.1	240.0	240.6	240.0	241.1	243.6
167.5°	256.0	253.2	250.2	248.0	246.6	244.6	244.2	244.8	244.2	244.6	246.6
170°	254.9	252.8	250.2	249.2	248.2	246.6	246.2	247.2	246.2	246.6	248.2
172.5°	254.4	252.8	250.7	250.0	249.4	248.3	248.2	248.8	248.2	248.3	249.4
175°	253.2	252.3	251.3	250.7	250.7	249.8	250.2	250.7	250.2	249.8	250.7
177.5°	252.4	251.6	251.3	251.3	251.3	250.8	251.3	251.6	251.3	250.8	251.3
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1231.5	1228.2	1223.3	1216.0	1210.2	1201.0	1201.0	1202.5	1202.5	1201.9	1201.0
5°	1194.2	1185.1	1174.2	1161.5	1148.1	1134.7	1132.3	1127.5	1123.8	1121.3	1118.3
7.5°	1154.8	1138.6	1122.7	1104.8	1088.6	1075.1	1065.8	1058.0	1053.0	1047.7	1043.8
10°	1128.0	1108.0	1089.2	1070.4	1049.7	1033.4	1023.1	1015.7	1010.3	1005.5	1003.1
12.5°	1096.4	1073.5	1052.8	1034.9	1012.4	995.5	985.7	982.3	975.9	965.6	960.3
15°	1050.3	1029.1	1004.2	977.0	966.0	945.4	933.9	928.4	924.8	916.9	914.4
17.5°	1010.9	983.1	955.2	934.9	914.5	897.9	891.4	884.6	879.8	873.3	871.4
20°	979.4	954.5	929.0	907.1	885.9	867.7	862.3	857.4	852.6	849.5	847.1
22.5°	947.4	922.5	901.3	880.9	858.3	846.3	840.4	835.1	831.7	829.6	827.2
25°	902.3	880.5	856.8	838.6	820.4	812.5	808.9	805.8	803.4	800.4	799.8
27.5°	862.0	838.2	819.0	802.1	789.0	782.4	778.9	777.4	777.9	779.0	779.7
30°	832.0	810.1	794.3	779.7	767.6	761.5	760.9	760.9	763.4	763.9	765.2
32.5°	804.2	786.3	770.5	756.4	747.3	743.1	745.4	745.4	747.3	748.9	751.1
35°	763.9	748.1	736.0	723.9	716.0	717.8	719.1	720.2	723.3	726.9	729.4
37.5°	725.5	711.8	699.2	689.6	686.1	689.3	692.2	694.8	698.3	701.1	703.6
40°	697.9	687.5	675.4	666.9	668.1	669.9	672.3	675.4	678.4	680.2	682.7
42.5°	672.1	661.3	652.1	645.1	646.8	649.1	650.5	652.1	655.6	658.9	660.3
45°	632.9	624.4	615.9	611.6	612.9	614.1	615.3	617.2	620.2	622.6	623.2
47.5°	588.8	582.9	577.2	573.1	575.0	574.5	576.1	580.0	580.9	582.4	585.8
50°	560.7	555.2	548.6	547.3	547.3	547.3	548.0	552.8	552.8	555.2	557.7
52.5°	529.6	526.1	521.8	519.7	518.7	518.7	521.2	523.7	524.7	528.1	530.5
55°	483.7	480.0	476.4	474.5	473.3	474.5	479.4	480.5	483.7	485.4	487.2
57.5°	435.7	432.9	430.0	429.0	428.7	430.3	433.0	436.7	437.4	443.0	445.8
60°	404.1	399.8	397.4	397.4	396.3	401.7	400.5	406.5	407.8	411.4	415.6
62.5°	371.6	365.9	364.9	364.9	366.7	368.2	369.9	372.6	375.8	380.3	383.6
65°	319.1	316.1	320.4	319.8	318.6	322.2	322.2	325.2	328.9	333.1	339.8
67.5°	269.6	268.0	268.3	268.3	270.2	272.2	273.9	276.6	281.0	285.4	289.8
70°	236.0	237.9	234.9	237.3	239.1	239.7	240.9	244.5	249.4	252.4	257.3
72.5°	203.5	203.4	203.8	204.7	206.5	207.7	208.8	213.0	218.3	220.9	224.8
75°	156.6	156.0	157.7	157.7	160.8	162.0	163.3	165.1	169.9	173.5	176.6
77.5°	114.3	115.0	114.7	116.7	115.9	116.1	119.9	121.7	122.3	129.4	131.0
80°	86.1	87.4	88.0	88.6	89.2	88.0	92.2	94.1	94.1	98.3	101.3
82.5°	61.9	62.6	64.2	64.8	64.9	66.2	66.5	67.9	69.3	71.2	75.1
85°	30.9	32.7	33.3	32.7	33.3	32.2	34.0	34.6	35.2	35.2	35.2
87.5°	10.8	11.5	11.3	12.1	11.9	12.8	12.7	11.8	11.9	13.5	11.7
90°	5.6	6.6	8.1	9.6	11.1	12.8	12.2	12.8	13.2	13.7	14.7
92.5°	21.8	29.4	42.7	64.6	86.1	78.2	59.0	42.8	34.0	30.1	27.4
95°	46.3	66.1	109.3	185.1	268.6	301.6	244.6	183.1	124.1	97.1	78.8
97.5°	54.9	76.4	117.7	203.1	342.1	467.4	500.1	456.5	365.6	300.0	239.2
100°	61.0	80.9	116.5	191.7	325.5	481.6	581.8	599.7	558.5	498.9	426.7
102.5°	67.9	86.1	118.1	182.0	301.1	455.2	585.9	647.3	646.0	611.3	565.4
105°	79.4	95.1	122.6	175.0	271.1	408.9	554.9	661.2	712.0	721.8	708.5
107.5°	92.2	106.8	130.9	174.4	252.0	368.0	500.6	621.1	703.7	748.2	766.3
110°	100.7	114.9	137.9	176.5	244.6	344.8	466.4	582.8	676.5	740.6	776.1



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	109.7	123.5	144.7	180.6	240.6	329.4	436.7	545.0	640.6	712.5	758.2
115°	123.1	136.8	156.1	187.2	239.1	312.8	400.8	494.9	583.4	658.2	713.5
117.5°	136.4	149.1	168.3	195.9	240.0	303.0	379.2	458.5	534.9	602.1	658.4
120°	145.0	157.7	175.9	202.4	241.6	298.5	367.7	439.4	508.1	569.1	620.5
122.5°	152.7	166.2	184.1	208.6	244.4	295.7	358.4	424.4	486.5	543.1	590.8
125°	164.3	178.0	195.8	218.2	248.7	291.9	346.3	404.3	459.8	508.6	549.3
127.5°	175.0	188.8	206.0	226.1	253.6	290.1	335.8	386.8	436.3	480.4	517.4
130°	181.6	195.3	212.0	231.4	256.8	288.9	330.1	375.9	421.6	462.8	497.4
132.5°	187.7	201.0	217.4	236.3	259.3	288.5	324.8	365.7	407.8	446.1	479.1
135°	195.8	209.6	225.3	242.6	263.0	287.8	317.9	352.0	388.1	421.2	450.1
137.5°	203.0	215.6	230.8	247.3	265.4	286.8	311.9	339.5	369.1	397.5	422.7
140°	207.0	219.7	234.4	249.8	267.0	286.3	308.2	332.2	358.0	382.5	404.3
142.5°	211.1	223.0	237.3	252.2	268.2	285.5	305.0	325.2	347.5	368.6	387.6
145°	216.2	227.8	241.1	254.9	269.0	284.3	300.6	316.8	333.7	349.9	364.7
147.5°	222.0	232.0	244.2	256.5	269.0	282.4	296.3	310.0	323.3	336.5	347.0
150°	225.3	234.4	246.2	256.8	269.0	280.7	293.5	305.1	316.8	327.5	337.2
152.5°	228.5	237.3	247.4	257.7	267.9	278.7	290.3	300.7	310.8	320.2	328.2
155°	234.0	241.1	249.8	257.9	266.5	275.2	285.3	294.0	302.1	309.8	315.8
157.5°	238.6	244.2	251.0	258.4	264.7	272.0	279.8	286.9	293.6	299.6	304.3
160°	241.1	246.2	252.3	258.4	263.9	269.6	276.2	282.8	288.4	293.5	297.0
162.5°	243.1	247.4	252.7	258.0	262.3	267.2	272.5	277.9	282.7	287.4	290.5
165°	245.7	249.2	253.2	256.8	259.9	263.5	267.5	271.6	274.6	278.2	280.7
167.5°	248.0	250.2	253.2	256.0	257.4	259.8	262.8	266.1	268.4	270.5	272.3
170°	249.2	250.2	252.8	254.9	255.8	257.3	259.9	262.4	263.9	266.0	267.0
172.5°	250.0	250.7	252.8	254.4	254.6	255.3	257.1	259.2	260.3	261.9	262.5
175°	250.7	251.3	252.3	253.2	252.8	252.8	253.8	254.9	255.3	256.4	256.4
177.5°	251.3	251.3	251.6	252.4	251.6	251.3	251.6	252.1	252.4	252.9	252.9
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1197.6	1197.1	1200.5	1198.1	1200.5	1197.1	1197.6	1201.0	1201.9	1202.5	1202.5
5°	1114.7	1116.5	1110.4	1110.4	1110.4	1116.5	1114.7	1118.3	1121.3	1123.8	1127.5
7.5°	1040.9	1038.2	1038.5	1035.2	1038.5	1038.2	1040.9	1043.8	1047.7	1053.0	1058.0
10°	995.8	992.1	990.9	991.5	990.9	992.1	995.8	1003.1	1005.5	1010.3	1015.7
12.5°	958.4	957.7	949.7	949.8	949.7	957.7	958.4	960.3	965.6	975.9	982.3
15°	914.4	902.9	901.7	905.4	901.7	902.9	914.4	914.4	916.9	924.8	928.4
17.5°	870.4	864.3	864.7	862.9	864.7	864.3	870.4	871.4	873.3	879.8	884.6
20°	847.1	843.5	842.8	838.6	842.8	843.5	847.1	847.1	849.5	852.6	857.4
22.5°	825.7	824.6	824.9	820.2	824.9	824.6	825.7	827.2	829.6	831.7	835.1
25°	799.2	802.2	799.8	799.8	799.8	802.2	799.2	799.8	800.4	803.4	805.8
27.5°	781.2	781.0	779.9	779.9	779.9	781.0	781.2	779.7	779.0	777.9	777.4
30°	767.6	767.0	768.2	768.2	768.2	767.0	767.6	765.2	763.9	763.4	760.9
32.5°	754.0	754.8	755.1	755.5	755.1	754.8	754.0	751.1	748.9	747.3	745.4
35°	733.0	733.6	735.5	734.2	735.5	733.6	733.0	729.4	726.9	723.3	720.2
37.5°	704.6	707.4	706.8	707.8	706.8	707.4	704.6	703.6	701.1	698.3	694.8
40°	683.2	685.1	684.5	684.5	684.5	685.1	683.2	682.7	680.2	678.4	675.4
42.5°	661.4	662.7	661.2	660.2	661.2	662.7	661.4	660.3	658.9	655.6	652.1
45°	625.6	624.4	626.2	623.8	626.2	624.4	625.6	623.2	622.6	620.2	617.2
47.5°	585.6	586.7	587.3	589.1	587.3	586.7	585.6	585.8	582.4	580.9	580.0
50°	558.8	562.5	562.5	561.9	562.5	562.5	558.8	557.7	555.2	552.8	552.8
52.5°	532.6	534.3	536.8	536.6	536.8	534.3	532.6	530.5	528.1	524.7	523.7
55°	492.1	493.3	494.5	495.2	494.5	493.3	492.1	487.2	485.4	483.7	480.5
57.5°	450.1	449.6	452.5	453.4	452.5	449.6	450.1	445.8	443.0	437.4	436.7
60°	420.5	420.5	425.3	427.2	425.3	420.5	420.5	415.6	411.4	407.8	406.5
62.5°	389.0	390.9	395.7	393.2	395.7	390.9	389.0	383.6	380.3	375.8	372.6
65°	342.9	347.7	347.1	349.6	347.1	347.7	342.9	339.8	333.1	328.9	325.2
67.5°	294.6	297.7	302.0	302.5	302.0	297.7	294.6	289.8	285.4	281.0	276.6
70°	262.2	265.2	267.6	269.4	267.6	265.2	262.2	257.3	252.4	249.4	244.5
72.5°	230.6	232.2	238.0	235.4	238.0	232.2	230.6	224.8	220.9	218.3	213.0
75°	180.8	185.0	188.7	186.9	188.7	185.0	180.8	176.6	173.5	169.9	165.1
77.5°	133.8	137.9	139.6	138.1	139.6	137.9	133.8	131.0	129.4	122.3	121.7
80°	105.6	105.0	108.6	108.0	108.6	105.0	105.6	101.3	98.3	94.1	94.1
82.5°	77.4	76.9	78.6	78.9	78.6	76.9	77.4	75.1	71.2	69.3	67.9
85°	37.6	39.4	37.0	36.4	37.0	39.4	37.6	35.2	35.2	35.2	34.6
87.5°	11.6	11.7	11.3	10.7	11.3	11.7	11.6	11.7	13.5	11.9	11.8
90°	14.3	14.7	15.2	14.7	15.2	14.7	14.3	14.7	13.7	13.2	12.8
92.5°	26.5	24.9	25.4	24.5	25.4	24.9	26.5	27.4	30.1	34.0	42.8
95°	69.2	64.6	61.0	59.0	61.0	64.6	69.2	78.8	97.1	124.1	183.1
97.5°	201.6	178.7	165.0	160.6	165.0	178.7	201.6	239.2	300.0	365.6	456.5
100°	375.3	338.2	318.4	318.9	318.4	338.2	375.3	426.7	498.9	558.5	599.7
102.5°	525.5	496.1	479.5	467.8	479.5	496.1	525.5	565.4	611.3	646.0	647.3
105°	685.1	665.8	649.5	646.9	649.5	665.8	685.1	708.5	721.8	712.0	661.2
107.5°	766.8	760.3	754.7	750.1	754.7	760.3	766.8	766.3	748.2	703.7	621.1
110°	790.4	794.4	793.4	792.4	793.4	794.4	790.4	776.1	740.6	676.5	582.8



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	784.3	796.9	800.8	800.9	800.8	796.9	784.3	758.2	712.5	640.6	545.0
115°	751.7	774.1	784.3	786.8	784.3	774.1	751.7	713.5	658.2	583.4	494.9
117.5°	698.1	723.7	738.4	741.8	738.4	723.7	698.1	658.4	602.1	534.9	458.5
120°	660.7	689.2	701.3	704.5	701.3	689.2	660.7	620.5	569.1	508.1	439.4
122.5°	626.5	652.1	665.6	669.4	665.6	652.1	626.5	590.8	543.1	486.5	424.4
125°	581.8	604.2	617.0	620.5	617.0	604.2	581.8	549.3	508.6	459.8	404.3
127.5°	546.4	565.4	576.9	580.2	576.9	565.4	546.4	517.4	480.4	436.3	386.8
130°	524.4	542.7	553.4	557.4	553.4	542.7	524.4	497.4	462.8	421.6	375.9
132.5°	504.4	522.7	532.2	535.0	532.2	522.7	504.4	479.1	446.1	407.8	365.7
135°	475.0	490.3	499.4	503.0	499.4	490.3	475.0	450.1	421.2	388.1	352.0
137.5°	443.6	459.1	466.8	469.1	466.8	459.1	443.6	422.7	397.5	369.1	339.5
140°	423.7	437.9	446.0	445.5	446.0	437.9	423.7	404.3	382.5	358.0	332.2
142.5°	404.1	416.8	424.1	423.6	424.1	416.8	404.1	387.6	368.6	347.5	325.2
145°	377.4	388.1	392.2	393.2	392.2	388.1	377.4	364.7	349.9	333.7	316.8
147.5°	356.6	363.8	367.7	368.1	367.7	363.8	356.6	347.0	336.5	323.3	310.0
150°	344.8	350.4	353.5	353.5	353.5	350.4	344.8	337.2	327.5	316.8	305.1
152.5°	334.2	339.5	341.3	341.3	341.3	339.5	334.2	328.2	320.2	310.8	300.7
155°	320.4	324.5	325.5	326.0	325.5	324.5	320.4	315.8	309.8	302.1	294.0
157.5°	308.4	311.4	312.2	312.1	312.2	311.4	308.4	304.3	299.6	293.6	286.9
160°	300.6	303.6	303.6	303.1	303.6	303.6	300.6	297.0	293.5	288.4	282.8
162.5°	292.8	295.5	295.5	295.0	295.5	295.5	292.8	290.5	287.4	282.7	277.9
165°	282.8	284.8	284.3	284.3	284.3	284.8	282.8	280.7	278.2	274.6	271.6
167.5°	273.2	274.6	274.1	274.1	274.1	274.6	273.2	272.3	270.5	268.4	266.1
170°	267.5	268.6	268.0	268.0	268.0	268.6	267.5	267.0	266.0	263.9	262.4
172.5°	262.6	263.7	262.8	262.3	262.8	263.7	262.6	262.5	261.9	260.3	259.2
175°	256.4	256.8	256.4	255.8	256.4	256.8	256.4	256.4	256.4	255.3	254.9
177.5°	252.4	252.9	252.1	252.1	252.1	252.9	252.4	252.9	252.9	252.4	252.1
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1201.0	1201.0	1210.2	1216.0	1223.3	1228.2	1231.5	1234.9	1240.8	1248.6	1257.3
5°	1132.3	1134.7	1148.1	1161.5	1174.2	1185.1	1194.2	1205.1	1218.4	1234.8	1253.0
7.5°	1065.8	1075.1	1088.6	1104.8	1122.7	1138.6	1154.8	1172.7	1191.5	1215.7	1241.2
10°	1023.1	1033.4	1049.7	1070.4	1089.2	1108.0	1128.0	1147.5	1171.1	1199.6	1232.4
12.5°	985.7	995.5	1012.4	1034.9	1052.8	1073.5	1096.4	1121.8	1148.3	1182.7	1219.8
15°	933.9	945.4	966.0	977.0	1004.2	1029.1	1050.3	1086.8	1120.8	1155.9	1199.1
17.5°	891.4	897.9	914.5	934.9	955.2	983.1	1010.9	1041.3	1075.1	1118.2	1172.1
20°	862.3	867.7	885.9	907.1	929.0	954.5	979.4	1009.7	1047.9	1093.4	1151.7
22.5°	840.4	846.3	858.3	880.9	901.3	922.5	947.4	983.5	1024.1	1068.7	1131.8
25°	808.9	812.5	820.4	838.6	856.8	880.5	902.3	936.3	978.2	1030.4	1093.4
27.5°	778.9	782.4	789.0	802.1	819.0	838.2	862.0	890.9	933.4	990.1	1057.0
30°	760.9	761.5	767.6	779.7	794.3	810.1	832.0	864.7	904.7	962.4	1032.8
32.5°	745.4	743.1	747.3	756.4	770.5	786.3	804.2	836.5	875.1	931.8	1004.2
35°	719.1	717.8	716.0	723.9	736.0	748.1	763.9	788.3	832.0	884.8	960.6
37.5°	692.2	689.3	686.1	689.6	699.2	711.8	725.5	747.1	784.7	842.8	915.4
40°	672.3	669.9	668.1	666.9	675.4	687.5	697.9	718.5	753.7	808.9	880.5
42.5°	650.5	649.1	646.8	645.1	652.1	661.3	672.1	690.3	725.5	777.3	845.1
45°	615.3	614.1	612.9	611.6	615.9	624.4	632.9	646.2	676.5	726.9	788.3
47.5°	576.1	574.5	575.0	573.1	577.2	582.9	588.8	603.2	632.3	673.0	717.7
50°	548.0	547.3	547.3	547.3	548.6	555.2	560.7	571.6	598.3	639.0	671.1
52.5°	521.2	518.7	518.7	519.7	521.8	526.1	529.6	541.5	564.8	598.2	627.4
55°	479.4	474.5	473.3	474.5	476.4	480.0	483.7	493.3	513.4	538.2	555.2
57.5°	433.0	430.3	428.7	429.0	430.0	432.9	435.7	446.2	462.0	475.0	485.9
60°	400.5	401.7	396.3	397.4	397.4	399.8	404.1	410.8	424.2	433.3	444.2
62.5°	369.9	368.2	366.7	364.9	364.9	365.9	371.6	376.8	388.3	393.0	401.4
65°	322.2	322.2	318.6	319.8	320.4	316.1	319.1	325.2	332.5	334.4	342.2
67.5°	273.9	272.2	270.2	268.3	268.3	268.0	269.6	272.6	278.0	278.7	284.7
70°	240.9	239.7	239.1	237.3	234.9	237.9	236.0	239.1	242.1	242.7	246.4
72.5°	208.8	207.7	206.5	204.7	203.8	203.4	203.5	207.1	209.1	208.2	212.4
75°	163.3	162.0	160.8	157.7	157.7	156.0	156.6	159.0	161.4	159.6	163.3
77.5°	119.9	116.1	115.9	116.7	114.7	115.0	114.3	114.0	115.0	115.2	118.4
80°	92.2	88.0	89.2	88.6	88.0	87.4	86.1	86.8	87.4	88.0	89.8
82.5°	66.5	66.2	64.9	64.8	64.2	62.6	61.9	63.0	63.6	63.2	64.6
85°	34.0	32.2	33.3	32.7	33.3	32.7	30.9	30.9	32.2	31.6	32.7
87.5°	12.7	12.8	11.9	12.1	11.3	11.5	10.8	11.1	11.3	11.1	11.9
90°	12.2	12.8	11.1	9.6	8.1	6.6	5.6	4.5	3.0	2.1	1.0
92.5°	59.0	78.2	86.1	64.6	42.7	29.4	21.8	17.6	13.6	9.4	6.3
95°	244.6	301.6	268.6	185.1	109.3	66.1	46.3	33.1	24.4	18.8	17.3
97.5°	500.1	467.4	342.1	203.1	117.7	76.4	54.9	41.9	34.4	30.1	29.5
100°	581.8	481.6	325.5	191.7	116.5	80.9	61.0	48.9	41.7	38.2	37.6
102.5°	585.9	455.2	301.1	182.0	118.1	86.1	67.9	57.0	50.3	47.1	46.2
105°	554.9	408.9	271.1	175.0	122.6	95.1	79.4	69.6	63.6	60.5	59.0
107.5°	500.6	368.0	252.0	174.4	130.9	106.8	92.2	83.1	77.1	74.2	72.6
110°	466.4	344.8	244.6	176.5	137.9	114.9	100.7	92.0	86.5	83.9	82.4



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	436.7	329.4	240.6	180.6	144.7	123.5	109.7	101.0	95.4	92.9	91.3
115°	400.8	312.8	239.1	187.2	156.1	136.8	123.1	114.4	109.3	106.3	104.2
117.5°	379.2	303.0	240.0	195.9	168.3	149.1	136.4	126.7	122.1	119.5	117.2
120°	367.7	298.5	241.6	202.4	175.9	157.7	145.0	135.3	130.2	127.7	126.2
122.5°	358.4	295.7	244.4	208.6	184.1	166.2	152.7	143.4	137.9	135.4	133.8
125°	346.3	291.9	248.7	218.2	195.8	178.0	164.3	154.6	149.0	146.0	145.0
127.5°	335.8	290.1	253.6	226.1	206.0	188.8	175.0	164.3	158.7	154.9	153.4
130°	330.1	288.9	256.8	231.4	212.0	195.3	181.6	170.9	164.8	160.2	158.7
132.5°	324.8	288.5	259.3	236.3	217.4	201.0	187.7	177.0	169.7	164.7	162.7
135°	317.9	287.8	263.0	242.6	225.3	209.6	195.8	185.1	177.5	171.9	169.9
137.5°	311.9	286.8	265.4	247.3	230.8	215.6	203.0	192.3	184.2	178.7	176.6
140°	308.2	286.3	267.0	249.8	234.4	219.7	207.0	196.8	188.7	183.6	181.1
142.5°	305.0	285.5	268.2	252.2	237.3	223.0	211.1	200.9	193.6	188.1	185.9
145°	300.6	284.3	269.0	254.9	241.1	227.8	216.2	207.5	199.9	195.3	193.8
147.5°	296.3	282.4	269.0	256.5	244.2	232.0	222.0	213.7	207.1	202.6	201.7
150°	293.5	280.7	269.0	256.8	246.2	234.4	225.3	218.2	211.6	207.5	207.0
152.5°	290.3	278.7	267.9	257.7	247.4	237.3	228.5	222.3	216.5	212.4	212.3
155°	285.3	275.2	266.5	257.9	249.8	241.1	234.0	228.4	223.3	220.3	220.3
157.5°	279.8	272.0	264.7	258.4	251.0	244.2	238.6	233.9	229.3	226.9	226.5
160°	276.2	269.6	263.9	258.4	252.3	246.2	241.1	237.6	233.4	231.4	231.4
162.5°	272.5	267.2	262.3	258.0	252.7	247.4	243.1	240.0	236.7	235.1	235.1
165°	267.5	263.5	259.9	256.8	253.2	249.2	245.7	243.6	241.1	240.0	240.6
167.5°	262.8	259.8	257.4	256.0	253.2	250.2	248.0	246.6	244.6	244.2	244.8
170°	259.9	257.3	255.8	254.9	252.8	250.2	249.2	248.2	246.6	246.2	247.2
172.5°	257.1	255.3	254.6	254.4	252.8	250.7	250.0	249.4	248.3	248.2	248.8
175°	253.8	252.8	252.8	253.2	252.3	251.3	250.7	250.7	249.8	250.2	250.7
177.5°	251.6	251.3	251.6	252.4	251.6	251.3	251.3	251.3	250.8	251.3	251.6
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1260.2	1262.7	1270.9	1276.8	1283.5	1287.4	1291.3	1294.2	1298.1	1299.0	1313.1
5°	1265.8	1277.9	1299.1	1314.9	1334.4	1355.6	1370.1	1376.8	1394.5	1409.0	1438.2
7.5°	1264.2	1290.0	1322.1	1355.3	1391.1	1424.1	1452.7	1486.7	1510.8	1547.1	1582.9
10°	1262.8	1297.4	1338.6	1381.1	1430.8	1476.9	1518.2	1564.3	1602.6	1653.0	1696.0
12.5°	1258.4	1300.3	1357.5	1407.7	1468.2	1531.8	1593.0	1652.2	1686.0	1770.0	1809.6
15°	1247.6	1297.4	1369.0	1445.4	1528.6	1603.7	1681.4	1743.4	1843.4	1916.9	1963.6
17.5°	1227.0	1296.6	1381.5	1473.8	1574.9	1674.0	1762.0	1856.0	1962.1	2051.0	2145.6
20°	1217.3	1293.7	1388.4	1490.3	1595.3	1707.5	1807.7	1920.6	2036.4	2123.8	2245.1
22.5°	1199.3	1285.9	1387.9	1501.5	1613.7	1729.8	1847.0	1960.8	2094.7	2215.1	2330.6
25°	1169.9	1267.0	1372.6	1499.4	1631.1	1747.6	1887.8	2038.9	2178.4	2333.2	2448.5
27.5°	1139.1	1242.7	1348.5	1466.5	1608.1	1746.4	1922.7	2093.5	2264.1	2397.7	2483.1
30°	1115.3	1216.0	1325.3	1444.2	1584.4	1748.8	1946.0	2132.3	2298.6	2413.2	2461.2
32.5°	1089.6	1191.8	1288.3	1413.1	1562.5	1747.3	1960.6	2155.1	2300.5	2376.9	2367.5
35°	1049.2	1134.7	1228.8	1348.9	1524.9	1736.7	1969.1	2157.1	2246.4	2230.0	2106.2
37.5°	990.9	1062.8	1155.5	1287.0	1481.2	1714.2	1952.0	2093.2	2087.4	1954.0	1774.7
40°	954.5	1015.7	1105.0	1243.3	1447.2	1699.7	1925.4	2017.0	1939.4	1753.0	1538.2
42.5°	907.0	963.3	1052.6	1194.8	1409.9	1670.0	1874.4	1900.9	1749.0	1534.6	1337.7
45°	833.1	882.9	975.1	1122.0	1353.8	1605.6	1750.0	1685.1	1480.6	1259.1	1109.2
47.5°	753.9	805.6	894.3	1045.2	1272.7	1508.6	1577.4	1439.3	1229.4	1049.7	912.1
50°	703.9	753.7	840.4	992.7	1217.8	1429.1	1457.5	1279.2	1086.2	928.4	815.6
52.5°	653.4	700.3	785.6	938.3	1153.8	1336.8	1319.2	1137.4	959.9	825.5	736.9
55°	578.3	622.6	703.9	847.1	1043.1	1188.1	1124.4	950.8	804.1	699.6	632.3
57.5°	511.0	553.5	623.7	753.0	923.5	1023.1	942.0	795.8	679.0	598.7	548.4
60°	465.4	503.0	569.8	689.9	838.0	913.8	833.7	704.5	606.2	541.9	497.0
62.5°	422.2	455.0	516.8	625.9	754.5	818.2	737.2	627.8	544.0	487.1	448.9
65°	356.8	386.6	441.1	526.1	631.7	674.1	604.4	515.8	450.8	408.4	382.9
67.5°	297.1	322.4	369.5	436.4	514.1	545.0	491.9	423.3	374.4	340.3	320.0
70°	257.3	279.1	316.1	373.8	444.2	467.9	418.1	361.7	325.8	298.5	279.7
72.5°	223.8	239.8	273.4	318.0	376.7	395.5	360.8	311.2	277.8	257.3	242.4
75°	170.5	183.9	205.7	241.5	282.1	293.1	267.0	236.0	213.6	199.0	187.5
77.5°	123.0	132.8	148.6	170.7	198.8	208.7	192.1	171.5	155.1	145.3	138.8
80°	92.8	100.8	114.0	132.2	149.3	154.7	145.0	129.2	117.7	112.3	106.8
82.5°	68.6	73.0	81.1	93.5	105.1	111.6	103.3	93.8	87.7	82.7	80.6
85°	34.6	37.0	40.7	45.5	52.8	55.2	52.2	49.8	46.1	43.1	43.1
87.5°	13.0	13.2	15.0	16.1	18.3	20.1	19.9	19.3	19.1	18.5	18.1
90°	2.1	3.0	4.5	5.6	6.6	8.1	9.6	11.1	12.8	12.2	12.8
92.5°	9.4	13.6	17.6	21.8	29.4	42.7	64.6	86.1	78.2	59.0	42.8
95°	18.8	24.4	33.1	46.3	66.1	109.3	185.1	268.6	301.6	244.6	183.1
97.5°	30.1	34.4	41.9	54.9	76.4	117.7	203.1	342.1	467.4	500.1	456.5
100°	38.2	41.7	48.9	61.0	80.9	116.5	191.7	325.5	481.6	581.8	599.7
102.5°	47.1	50.3	57.0	67.9	86.1	118.1	182.0	301.1	455.2	585.9	647.3
105°	60.5	63.6	69.6	79.4	95.1	122.6	175.0	271.1	408.9	554.9	661.2
107.5°	74.2	77.1	83.1	92.2	106.8	130.9	174.4	252.0	368.0	500.6	621.1
110°	83.9	86.5	92.0	100.7	114.9	137.9	176.5	244.6	344.8	466.4	582.8



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	92.9	95.4	101.0	109.7	123.5	144.7	180.6	240.6	329.4	436.7	545.0
115°	106.3	109.3	114.4	123.1	136.8	156.1	187.2	239.1	312.8	400.8	494.9
117.5°	119.5	122.1	126.7	136.4	149.1	168.3	195.9	240.0	303.0	379.2	458.5
120°	127.7	130.2	135.3	145.0	157.7	175.9	202.4	241.6	298.5	367.7	439.4
122.5°	135.4	137.9	143.4	152.7	166.2	184.1	208.6	244.4	295.7	358.4	424.4
125°	146.0	149.0	154.6	164.3	178.0	195.8	218.2	248.7	291.9	346.3	404.3
127.5°	154.9	158.7	164.3	175.0	188.8	206.0	226.1	253.6	290.1	335.8	386.8
130°	160.2	164.8	170.9	181.6	195.3	212.0	231.4	256.8	288.9	330.1	375.9
132.5°	164.7	169.7	177.0	187.7	201.0	217.4	236.3	259.3	288.5	324.8	365.7
135°	171.9	177.5	185.1	195.8	209.6	225.3	242.6	263.0	287.8	317.9	352.0
137.5°	178.7	184.2	192.3	203.0	215.6	230.8	247.3	265.4	286.8	311.9	339.5
140°	183.6	188.7	196.8	207.0	219.7	234.4	249.8	267.0	286.3	308.2	332.2
142.5°	188.1	193.6	200.9	211.1	223.0	237.3	252.2	268.2	285.5	305.0	325.2
145°	195.3	199.9	207.5	216.2	227.8	241.1	254.9	269.0	284.3	300.6	316.8
147.5°	202.6	207.1	213.7	222.0	232.0	244.2	256.5	269.0	282.4	296.3	310.0
150°	207.5	211.6	218.2	225.3	234.4	246.2	256.8	269.0	280.7	293.5	305.1
152.5°	212.4	216.5	222.3	228.5	237.3	247.4	257.7	267.9	278.7	290.3	300.7
155°	220.3	223.3	228.4	234.0	241.1	249.8	257.9	266.5	275.2	285.3	294.0
157.5°	226.9	229.3	233.9	238.6	244.2	251.0	258.4	264.7	272.0	279.8	286.9
160°	231.4	233.4	237.6	241.1	246.2	252.3	258.4	263.9	269.6	276.2	282.8
162.5°	235.1	236.7	240.0	243.1	247.4	252.7	258.0	262.3	267.2	272.5	277.9
165°	240.0	241.1	243.6	245.7	249.2	253.2	256.8	259.9	263.5	267.5	271.6
167.5°	244.2	244.6	246.6	248.0	250.2	253.2	256.0	257.4	259.8	262.8	266.1
170°	246.2	246.6	248.2	249.2	250.2	252.8	254.9	255.8	257.3	259.9	262.4
172.5°	248.2	248.3	249.4	250.0	250.7	252.8	254.4	254.6	255.3	257.1	259.2
175°	250.2	249.8	250.7	250.7	251.3	252.3	253.2	252.8	252.8	253.8	254.9
177.5°	251.3	250.8	251.3	251.3	251.3	251.6	252.4	251.6	251.3	251.6	252.1
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1317.9	1318.5	1323.8	1327.7	1325.7	1328.2	1329.1
5°	1439.9	1461.8	1473.3	1481.8	1482.4	1483.0	1487.9
7.5°	1612.8	1636.3	1653.4	1679.4	1687.1	1696.0	1693.4
10°	1739.1	1773.7	1803.4	1819.2	1836.2	1861.1	1841.0
12.5°	1857.1	1918.3	1963.6	1988.2	2004.1	2009.1	1999.3
15°	2051.6	2131.7	2174.8	2173.5	2228.2	2251.8	2214.8
17.5°	2230.0	2303.9	2363.1	2393.4	2439.0	2449.1	2444.4
20°	2339.2	2419.9	2466.0	2518.2	2541.9	2563.1	2566.8
22.5°	2433.4	2505.9	2555.4	2598.8	2618.6	2628.7	2634.7
25°	2530.3	2587.4	2617.2	2632.3	2637.8	2636.5	2628.7
27.5°	2523.7	2528.1	2495.3	2463.2	2434.4	2402.0	2390.8
30°	2458.2	2407.2	2316.1	2264.6	2188.7	2128.7	2152.9
32.5°	2285.8	2184.3	2082.1	1969.4	1876.1	1849.5	1822.8
35°	1950.9	1772.5	1668.1	1546.8	1498.2	1449.7	1416.3
37.5°	1578.3	1440.3	1316.5	1237.2	1188.5	1157.8	1141.3
40°	1364.7	1240.3	1138.4	1074.1	1037.1	1002.5	997.6
42.5°	1194.3	1078.6	1001.9	950.7	915.2	900.4	889.8
45°	978.2	897.4	845.9	809.5	785.8	776.7	764.6
47.5°	828.0	770.9	732.2	707.4	689.6	682.8	681.8
50°	744.0	696.6	668.1	648.6	634.7	632.3	622.6
52.5°	680.8	639.8	617.6	600.7	590.6	583.7	580.9
55°	591.0	563.7	543.7	534.0	526.1	519.4	519.4
57.5°	517.1	494.3	481.1	472.8	470.4	465.7	462.6
60°	471.4	452.1	441.8	434.4	429.6	430.3	424.7
62.5°	426.9	414.2	404.4	397.1	391.3	391.4	391.7
65°	363.5	353.7	346.5	344.0	340.5	336.2	337.4
67.5°	308.0	298.9	293.2	289.1	287.8	285.5	289.1
70°	268.2	261.5	257.3	253.6	252.4	253.1	256.1
72.5°	231.8	227.0	224.3	222.6	219.9	220.0	222.1
75°	182.0	178.4	175.9	174.2	173.5	173.5	173.5
77.5°	133.8	132.9	131.8	129.1	129.2	130.0	130.1
80°	105.6	103.8	103.2	101.9	100.1	98.9	101.9
82.5°	78.9	77.0	76.4	76.2	73.4	73.2	75.7
85°	42.4	40.7	41.3	40.7	40.7	40.0	40.0
87.5°	17.7	17.3	17.0	17.4	17.0	16.7	17.5
90°	13.2	13.7	14.7	14.3	14.7	15.2	14.7
92.5°	34.0	30.1	27.4	26.5	24.9	25.4	24.5
95°	124.1	97.1	78.8	69.2	64.6	61.0	59.0
97.5°	365.6	300.0	239.2	201.6	178.7	165.0	160.6
100°	558.5	498.9	426.7	375.3	338.2	318.4	318.9
102.5°	646.0	611.3	565.4	525.5	496.1	479.5	467.8
105°	712.0	721.8	708.5	685.1	665.8	649.5	646.9
107.5°	703.7	748.2	766.3	766.8	760.3	754.7	750.1
110°	676.5	740.6	776.1	790.4	794.4	793.4	792.4



TEST NUMBER: P332011-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	640.6	712.5	758.2	784.3	796.9	800.8	800.9
115°	583.4	658.2	713.5	751.7	774.1	784.3	786.8
117.5°	534.9	602.1	658.4	698.1	723.7	738.4	741.8
120°	508.1	569.1	620.5	660.7	689.2	701.3	704.5
122.5°	486.5	543.1	590.8	626.5	652.1	665.6	669.4
125°	459.8	508.6	549.3	581.8	604.2	617.0	620.5
127.5°	436.3	480.4	517.4	546.4	565.4	576.9	580.2
130°	421.6	462.8	497.4	524.4	542.7	553.4	557.4
132.5°	407.8	446.1	479.1	504.4	522.7	532.2	535.0
135°	388.1	421.2	450.1	475.0	490.3	499.4	503.0
137.5°	369.1	397.5	422.7	443.6	459.1	466.8	469.1
140°	358.0	382.5	404.3	423.7	437.9	446.0	445.5
142.5°	347.5	368.6	387.6	404.1	416.8	424.1	423.6
145°	333.7	349.9	364.7	377.4	388.1	392.2	393.2
147.5°	323.3	336.5	347.0	356.6	363.8	367.7	368.1
150°	316.8	327.5	337.2	344.8	350.4	353.5	353.5
152.5°	310.8	320.2	328.2	334.2	339.5	341.3	341.3
155°	302.1	309.8	315.8	320.4	324.5	325.5	326.0
157.5°	293.6	299.6	304.3	308.4	311.4	312.2	312.1
160°	288.4	293.5	297.0	300.6	303.6	303.6	303.1
162.5°	282.7	287.4	290.5	292.8	295.5	295.5	295.0
165°	274.6	278.2	280.7	282.8	284.8	284.3	284.3
167.5°	268.4	270.5	272.3	273.2	274.6	274.1	274.1
170°	263.9	266.0	267.0	267.5	268.6	268.0	268.0
172.5°	260.3	261.9	262.5	262.6	263.7	262.8	262.3
175°	255.3	256.4	256.4	256.4	256.8	256.4	255.8
177.5°	252.4	252.9	252.9	252.4	252.9	252.1	252.1
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3

(END OF REPORT)