

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332060-935

Luminaire Tested: **S123DIP-S1165D585U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332060-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D585U935-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6113.3 lumens  
Efficiency: N/A  
Efficacy: 110.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332060-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332060-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	97	93	89	95	92	88	85	81	79	76	72	70	68	63	62	60	56
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	56	53	51	47
3	84	74	67	61	79	70	64	58	63	57	53	56	52	48	49	46	43	40
4	77	66	58	52	72	62	55	49	56	50	45	50	45	41	44	40	37	34
5	71	59	50	44	67	56	48	43	50	44	39	45	40	36	40	36	32	30
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25	23
8	56	44	36	30	53	41	34	29	38	31	27	34	29	25	30	26	23	21
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16942	16942	16942
5°	17022	16788	16904
10°	16909	16642	16746
15°	16711	16454	16485
20°	16479	16186	16200
25°	16170	15865	15833
30°	15830	15509	15392
35°	15473	15135	14939
40°	15100	14720	14491
45°	14690	14338	13988
50°	14277	13870	13485
55°	13741	13386	12979
60°	13199	12820	12411
65°	12720	12202	11826
70°	12013	11500	10990
75°	10975	10580	10131
80°	9899	9478	9397
85°	8682	8361	8028



TEST NUMBER: P332060-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.3	2.4
10°-20°	418.7	6.8
20°-30°	618.4	10.1
30°-40°	722.4	11.8
40°-50°	726.3	11.9
50°-60°	638.0	10.4
60°-70°	475.3	7.8
70°-80°	270.8	4.4
80°-90°	79.6	1.3
90°-100°	24.0	0.4
100°-110°	114.5	1.9
110°-120°	275.1	4.5
120°-130°	350.3	5.7
130°-140°	374.3	6.1
140°-150°	350.0	5.7
150°-160°	282.3	4.6
160°-170°	182.2	3.0
170°-180°	62.8	1.0
0°-30°	1185.3	19.4
0°-40°	1907.7	31.2
0°-60°	3272.0	53.5
0°-90°	4097.6	67.0
90°-120°	413.7	6.8
90°-150°	1488.3	24.3
90°-180°	2016.0	33.0
0°-180°	6113.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1554	1566	1564	149
15°	1500	1494	1476	1486	1479	423
25°	1362	1353	1336	1337	1333	627
35°	1178	1169	1152	1144	1137	736
45°	965	959	942	926	919	745
55°	732	730	713	699	692	656
65°	499	492	479	469	464	493
75°	264	259	254	248	244	282
85°	70	68	68	65	65	77
90°	0	5	12	14	15	5
95°	30	11	15	18	19	37
105°	146	149	108	26	22	155
115°	274	278	282	287	289	271
125°	387	391	393	394	395	345
135°	482	485	487	488	487	371
145°	556	559	560	561	561	348
155°	612	612	612	614	611	282
165°	646	644	644	647	644	182
175°	661	659	659	662	658	63
180°	661	661	661	661	661	



TEST NUMBER: P332060-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1579.4	1578.5	1577.5	1576.6	1575.5	1573.7	1571.2	1568.5	1565.8	1563.1	1565.6
5°	1575.4	1573.9	1572.4	1570.9	1569.3	1566.9	1563.7	1560.3	1557.0	1553.7	1556.7
7.5°	1560.0	1558.4	1556.9	1555.4	1553.9	1551.4	1548.0	1544.6	1541.2	1537.7	1540.4
10°	1547.0	1545.4	1543.9	1542.4	1540.9	1538.3	1534.3	1530.4	1526.5	1522.6	1525.3
12.5°	1529.7	1528.4	1527.1	1525.9	1524.6	1522.1	1518.5	1514.8	1511.1	1507.4	1509.4
15°	1499.6	1498.4	1497.2	1496.0	1494.8	1492.2	1488.3	1484.4	1480.5	1476.5	1478.9
17.5°	1464.6	1463.1	1461.5	1460.0	1458.4	1455.7	1451.7	1447.9	1443.9	1440.0	1441.7
20°	1438.6	1436.8	1435.0	1433.2	1431.5	1428.6	1424.7	1420.8	1416.9	1413.0	1414.2
22.5°	1409.5	1407.6	1405.8	1404.0	1402.2	1399.4	1395.4	1391.5	1387.7	1383.7	1384.7
25°	1361.5	1359.7	1357.9	1356.1	1354.4	1351.4	1347.6	1343.7	1339.7	1335.8	1336.1
27.5°	1310.4	1308.6	1306.9	1305.1	1303.4	1300.5	1296.2	1292.0	1287.8	1283.6	1283.8
30°	1273.6	1272.0	1270.6	1269.0	1267.6	1264.7	1260.5	1256.3	1252.1	1247.8	1247.8
32.5°	1236.7	1234.8	1232.8	1230.8	1228.8	1226.2	1223.0	1219.7	1216.4	1213.2	1211.5
35°	1177.5	1175.7	1173.9	1172.1	1170.3	1167.4	1163.5	1159.6	1155.6	1151.8	1150.0
37.5°	1116.8	1114.6	1112.2	1110.0	1107.7	1104.6	1100.6	1096.7	1092.7	1088.6	1086.5
40°	1074.6	1072.8	1071.0	1069.2	1067.4	1064.4	1060.1	1055.9	1051.7	1047.6	1045.2
42.5°	1032.3	1030.4	1028.3	1026.2	1024.2	1021.1	1016.8	1012.6	1008.4	1004.3	1001.9
45°	965.0	963.8	962.6	961.4	960.2	957.6	953.7	949.8	945.9	941.9	938.4
47.5°	898.1	896.4	894.7	892.9	891.1	888.5	884.8	881.1	877.4	873.7	870.2
50°	852.6	851.2	849.6	848.2	846.6	844.0	840.0	836.1	832.2	828.3	825.0
52.5°	805.0	804.0	803.0	801.9	800.9	798.3	794.2	790.1	785.9	781.7	778.9
55°	732.2	731.9	731.6	731.3	731.0	728.9	725.0	721.1	717.1	713.3	710.0
57.5°	662.9	661.9	660.8	659.9	658.8	656.8	653.6	650.5	647.4	644.2	641.3
60°	613.1	612.8	612.5	612.2	611.9	609.9	606.3	602.7	599.1	595.5	592.8
62.5°	568.7	567.9	567.1	566.4	565.6	563.4	559.7	556.1	552.6	549.0	546.2
65°	499.4	497.9	496.4	494.9	493.4	491.1	488.1	485.1	482.1	479.1	476.7
67.5°	426.0	424.7	423.4	422.1	420.8	419.0	416.6	414.4	412.1	409.8	407.7
70°	381.7	379.9	378.1	376.3	374.4	372.6	370.8	369.0	367.2	365.4	363.3
72.5°	335.1	333.8	332.4	331.1	329.8	328.1	326.1	324.0	322.0	319.9	318.1
75°	263.9	262.7	261.5	260.3	259.1	258.0	257.2	256.2	255.4	254.4	253.0
77.5°	200.9	200.2	199.5	198.9	198.2	197.3	196.2	195.2	194.1	193.0	192.0
80°	159.7	158.8	157.9	157.0	156.1	155.3	154.7	154.1	153.5	152.9	152.7
82.5°	119.7	119.4	119.2	119.1	118.9	118.7	118.6	118.6	118.4	118.3	117.8
85°	70.3	69.7	69.1	68.5	67.9	67.7	67.7	67.7	67.7	67.7	67.1
87.5°	28.2	27.7	27.2	26.8	26.3	26.0	26.1	26.1	26.2	26.2	26.0
90°	0.5	1.5	2.7	3.8	4.8	6.1	7.5	9.0	10.3	11.8	12.2
92.5°	9.1	8.9	8.5	8.2	7.9	8.3	9.4	10.4	11.5	12.6	13.3
95°	30.0	25.5	21.0	16.5	12.1	10.4	11.6	12.8	14.0	15.2	16.0
97.5°	60.2	58.2	56.2	54.2	52.2	47.3	39.3	31.5	23.7	15.8	16.7
100°	83.0	85.2	87.4	89.5	91.7	84.3	67.2	50.3	33.2	16.2	17.0
102.5°	108.9	110.5	112.1	113.7	115.2	106.7	88.1	69.5	50.9	32.3	29.6
105°	146.4	147.6	148.8	149.9	151.1	146.8	137.0	127.2	117.4	107.5	88.3
107.5°	185.8	186.8	187.8	188.7	189.7	190.9	192.4	194.0	195.5	197.1	183.0
110°	212.2	213.0	213.9	214.7	215.6	216.7	217.8	219.0	220.2	221.4	217.8



TEST NUMBER: P332060-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	237.3	238.1	238.8	239.6	240.4	241.4	242.6	243.8	245.0	246.2	246.3
115°	274.5	275.2	275.8	276.5	277.2	277.9	279.0	279.9	280.9	281.9	283.0
117.5°	310.6	311.3	312.2	313.0	313.7	314.4	315.0	315.5	316.0	316.4	317.4
120°	332.9	333.9	334.9	335.9	336.9	337.5	337.9	338.2	338.5	338.8	339.8
122.5°	355.8	356.5	357.3	358.2	359.0	359.6	360.0	360.4	360.8	361.3	361.9
125°	386.9	387.9	388.7	389.6	390.5	391.2	391.6	392.0	392.4	392.9	393.0
127.5°	417.2	418.1	419.0	419.8	420.7	421.4	421.9	422.5	423.0	423.5	423.9
130°	436.1	437.0	437.8	438.7	439.5	440.2	440.7	441.1	441.5	442.0	442.4
132.5°	454.2	455.0	455.9	456.8	457.6	458.2	458.6	458.9	459.3	459.7	460.1
135°	481.7	482.4	483.0	483.7	484.4	484.9	485.3	485.8	486.2	486.6	487.0
137.5°	505.3	506.2	507.0	507.8	508.6	509.2	509.4	509.6	509.9	510.1	510.7
140°	521.0	521.7	522.4	523.0	523.7	524.2	524.4	524.8	525.1	525.5	525.9
142.5°	535.5	536.2	536.9	537.5	538.2	538.6	539.0	539.3	539.7	540.0	540.4
145°	555.9	556.6	557.4	558.2	559.0	559.5	559.6	559.9	560.1	560.3	560.5
147.5°	575.1	575.6	576.1	576.5	577.0	577.4	577.6	577.8	578.1	578.3	578.5
150°	586.9	587.2	587.5	587.8	588.1	588.4	588.7	588.8	589.1	589.3	589.5
152.5°	597.4	597.6	597.7	597.9	598.1	598.2	598.3	598.5	598.6	598.7	599.1
155°	612.3	612.2	611.9	611.7	611.5	611.5	611.6	611.7	611.7	611.9	612.4
157.5°	624.0	624.0	623.9	623.9	623.9	623.8	623.7	623.6	623.5	623.4	624.1
160°	631.0	630.9	630.9	630.7	630.6	630.5	630.3	630.3	630.2	630.1	630.7
162.5°	637.7	637.4	637.1	636.9	636.5	636.4	636.3	636.2	636.0	635.9	636.7
165°	645.8	645.4	645.1	644.8	644.5	644.2	644.1	644.0	643.9	643.8	644.7
167.5°	652.0	651.6	651.2	650.7	650.3	650.1	650.1	650.1	650.1	650.1	651.0
170°	655.6	655.1	654.7	654.3	653.8	653.6	653.6	653.6	653.6	653.6	654.5
172.5°	658.0	657.5	656.9	656.3	655.8	655.7	655.7	655.8	655.9	656.0	656.9
175°	661.0	660.5	659.9	659.4	658.8	658.6	658.7	658.8	658.9	659.0	659.8
177.5°	661.8	661.3	660.9	660.5	660.0	659.9	660.0	660.0	660.1	660.2	660.9
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0



TEST NUMBER: P332060-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1568.0	1570.4	1572.8	1573.9	1573.6	1573.4	1573.1	1573.0
5°	1559.7	1562.7	1565.7	1566.9	1566.3	1565.7	1565.1	1564.5
7.5°	1543.2	1545.8	1548.6	1549.7	1549.4	1549.0	1548.7	1548.3
10°	1528.0	1530.7	1533.4	1534.5	1533.9	1533.3	1532.7	1532.1
12.5°	1511.4	1513.4	1515.4	1516.2	1515.8	1515.4	1515.1	1514.8
15°	1481.4	1483.8	1486.2	1486.5	1484.7	1482.9	1481.1	1479.3
17.5°	1443.4	1445.1	1446.7	1447.3	1446.7	1446.0	1445.3	1444.7
20°	1415.4	1416.6	1417.8	1417.9	1417.0	1416.1	1415.2	1414.3
22.5°	1385.7	1386.6	1387.6	1387.5	1386.4	1385.2	1384.1	1382.9
25°	1336.4	1336.7	1337.0	1336.7	1335.8	1334.9	1334.0	1333.1
27.5°	1284.1	1284.3	1284.5	1284.1	1283.0	1281.8	1280.7	1279.5
30°	1247.8	1247.8	1247.8	1246.8	1244.7	1242.6	1240.4	1238.4
32.5°	1209.8	1208.2	1206.4	1205.1	1203.9	1202.7	1201.6	1200.5
35°	1148.1	1146.3	1144.5	1142.9	1141.3	1139.9	1138.3	1136.9
37.5°	1084.3	1082.2	1080.0	1078.5	1077.5	1076.5	1075.6	1074.6
40°	1042.8	1040.3	1037.9	1036.1	1034.9	1033.7	1032.5	1031.3
42.5°	999.4	997.0	994.6	992.8	991.6	990.4	989.2	988.0
45°	934.8	931.2	927.6	925.0	923.5	922.0	920.5	918.9
47.5°	866.7	863.2	859.5	857.1	855.8	854.5	853.2	851.9
50°	821.7	818.4	815.0	812.5	810.7	808.9	807.1	805.3
52.5°	776.1	773.3	770.4	768.1	766.3	764.5	762.7	760.9
55°	706.6	703.4	700.0	697.6	696.1	694.6	693.1	691.6
57.5°	638.3	635.4	632.4	630.1	628.4	626.6	624.8	623.1
60°	590.1	587.4	584.7	582.6	581.1	579.5	578.1	576.5
62.5°	543.5	540.8	538.1	536.2	535.2	534.2	533.2	532.2
65°	474.3	471.9	469.5	467.9	466.9	466.1	465.1	464.3
67.5°	405.6	403.5	401.4	399.7	398.5	397.2	395.9	394.7
70°	361.2	359.1	357.0	355.2	353.7	352.1	350.7	349.2
72.5°	316.2	314.4	312.5	311.2	310.4	309.6	308.8	308.1
75°	251.4	249.9	248.4	247.2	246.3	245.4	244.5	243.6
77.5°	191.0	189.9	188.9	188.4	188.4	188.4	188.4	188.4
80°	152.3	152.1	151.7	151.6	151.6	151.6	151.6	151.6
82.5°	117.2	116.7	116.1	115.7	115.5	115.3	115.0	114.8
85°	66.5	65.9	65.3	65.0	65.0	65.0	65.0	65.0
87.5°	25.8	25.7	25.6	25.5	25.6	25.6	25.7	25.7
90°	12.7	13.1	13.5	13.9	14.1	14.3	14.6	14.7
92.5°	13.9	14.6	15.3	15.8	15.9	16.0	16.2	16.3
95°	16.8	17.5	18.3	18.7	18.7	18.7	18.7	18.7
97.5°	17.6	18.4	19.3	19.8	19.9	20.0	20.1	20.2
100°	17.9	18.9	19.7	20.1	20.3	20.4	20.5	20.7
102.5°	26.9	24.2	21.5	20.2	20.4	20.7	20.8	21.0
105°	68.9	49.6	30.3	20.8	20.9	21.2	21.4	21.6
107.5°	168.8	154.6	140.4	126.1	111.5	96.9	82.4	67.8
110°	214.3	210.7	207.1	197.4	181.8	166.3	150.7	135.0





TEST NUMBER: P332060-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	246.3	246.4	246.5	244.9	241.6	238.2	235.0	231.7
115°	284.0	285.2	286.3	287.0	287.4	287.9	288.3	288.8
117.5°	318.2	319.1	319.9	320.5	320.6	320.6	320.7	320.8
120°	340.6	341.5	342.3	342.8	342.8	342.8	342.8	342.8
122.5°	362.5	363.1	363.7	364.0	364.1	364.2	364.3	364.4
125°	393.3	393.5	393.7	394.0	394.2	394.4	394.6	394.9
127.5°	424.2	424.6	424.9	425.0	424.7	424.6	424.3	424.1
130°	442.8	443.2	443.7	443.8	443.6	443.4	443.2	443.0
132.5°	460.5	461.0	461.4	461.5	461.2	460.8	460.5	460.2
135°	487.3	487.7	487.9	487.9	487.7	487.3	487.0	486.6
137.5°	511.2	511.7	512.2	512.4	512.1	512.0	511.7	511.5
140°	526.3	526.8	527.2	527.3	527.1	526.8	526.7	526.4
142.5°	540.7	541.1	541.4	541.4	541.1	540.8	540.4	540.2
145°	560.8	560.9	561.2	561.3	561.3	561.3	561.3	561.3
147.5°	578.8	578.9	579.2	579.0	578.5	578.0	577.6	577.0
150°	589.7	590.0	590.1	590.1	589.8	589.4	589.1	588.8
152.5°	599.5	599.9	600.3	600.2	599.8	599.3	598.7	598.2
155°	612.9	613.5	614.1	614.0	613.4	612.7	612.1	611.4
157.5°	624.7	625.3	626.0	625.9	625.0	624.2	623.4	622.5
160°	631.4	632.0	632.7	632.6	631.9	631.1	630.3	629.6
162.5°	637.4	638.2	638.9	638.9	638.3	637.6	636.9	636.3
165°	645.6	646.4	647.3	647.4	646.6	645.8	645.1	644.3
167.5°	651.9	652.7	653.6	653.6	652.7	651.9	651.0	650.1
170°	655.4	656.3	657.1	657.1	656.3	655.4	654.5	653.6
172.5°	657.7	658.6	659.4	659.4	658.5	657.5	656.5	655.6
175°	660.6	661.3	662.1	662.0	661.2	660.3	659.4	658.5
177.5°	661.6	662.3	663.0	662.9	662.0	661.2	660.3	659.4
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0

(END OF REPORT)