

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332074-940

Luminaire Tested: **S123DIP-S1165D1025U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332074-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D1025U940-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7677.3 lumens  
Efficiency: N/A  
Efficacy: 114.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57																				
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	53	49																				
2	91	84	78	72	84	78	73	68	68	64	60	58	55	53	49	47	45	41																				
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35																				
4	76	65	58	52	71	61	54	49	53	48	44	46	42	39	39	36	34	30																				
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	26																				
6	65	53	44	39	60	49	42	37	43	37	33	38	33	30	32	29	26	23																				
7	60	48	40	34	56	45	37	32	39	34	29	34	30	26	30	26	23	21																				
8	56	43	35	30	52	41	34	29	36	30	26	31	27	23	27	24	21	19																				
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17																				
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15569	15569	15569	15569
5°	18567	15637	13857	15637
10°	23240	15557	12516	15557
15°	28505	15432	11652	15432
20°	33956	15237	11094	15237
25°	36056	14998	10969	14998
30°	30904	14825	11028	14825
35°	21494	14578	11143	14578
40°	16190	14289	11108	14289
45°	13443	13857	10966	13857
50°	12042	12980	10868	12980
55°	11258	12033	10732	12033
60°	10559	11044	10622	11044
65°	9926	10068	10282	10068
70°	9309	8954	9791	8954
75°	8339	7839	8979	7839
80°	7296	6428	7736	6428
85°	5718	4668	5199	4668



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.5	1.9
10°-20°	456.9	6.0
20°-30°	766.8	10.0
30°-40°	868.3	11.3
40°-50°	778.6	10.1
50°-60°	628.3	8.2
60°-70°	437.9	5.7
70°-80°	230.1	3.0
80°-90°	59.7	0.8
90°-100°	244.7	3.2
100°-110°	692.9	9.0
110°-120°	681.6	8.9
120°-130°	543.7	7.1
130°-140°	428.7	5.6
140°-150°	319.9	4.2
150°-160°	223.0	2.9
160°-170°	131.0	1.7
170°-180°	42.6	0.6
0°-30°	1366.2	17.8
0°-40°	2234.5	29.1
0°-60°	3641.5	47.4
0°-90°	4369.2	56.9
90°-120°	1619.2	21.1
90°-150°	2911.5	37.9
90°-180°	3308.0	43.1
0°-180°	7677.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1446	1446	1446	1446	1446	
5°	1718	1447	1282	1447	1718	178
15°	2558	1385	1046	1385	2558	739
25°	3036	1263	924	1263	3036	1331
35°	1636	1109	848	1109	1636	1063
45°	883	910	720	910	883	699
55°	600	641	572	641	600	538
65°	390	395	404	395	390	388
75°	200	188	216	188	200	215
85°	46	38	42	38	46	55
90°	26	2	26	2	26	16
95°	103	30	103	30	103	186
105°	1132	103	1132	103	1132	1117
115°	1377	182	1377	182	1377	1338
125°	1086	254	1086	254	1086	984
135°	880	297	880	297	880	683
145°	688	339	688	339	688	438
155°	570	385	570	385	570	266
165°	498	421	498	421	498	142
175°	448	439	448	439	448	43
180°	440	440	440	440	440	



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1535.1	1533.9	1531.2	1533.4	1528.9	1522.7	1522.2	1516.5	1500.3	1499.1	1494.7
5°	1718.4	1712.8	1712.1	1711.4	1701.6	1688.3	1663.0	1660.9	1627.3	1610.4	1590.2
7.5°	1955.8	1958.7	1948.6	1939.6	1909.6	1889.8	1862.8	1828.2	1786.8	1744.9	1717.0
10°	2126.3	2149.4	2120.7	2101.0	2082.9	2048.4	2008.6	1958.7	1909.0	1850.8	1806.7
12.5°	2309.1	2320.4	2314.6	2296.2	2267.8	2215.5	2144.7	2090.0	2044.2	1947.3	1908.2
15°	2558.0	2600.8	2573.4	2510.3	2511.7	2461.9	2369.5	2267.8	2213.9	2129.0	2013.5
17.5°	2823.2	2828.5	2816.8	2764.3	2729.3	2660.9	2575.5	2478.1	2368.7	2266.2	2143.5
20°	2964.4	2960.2	2935.7	2908.4	2848.1	2794.9	2701.6	2593.0	2452.8	2352.0	2218.0
22.5°	3043.0	3035.9	3024.3	3001.4	2951.3	2894.0	2810.4	2691.7	2558.2	2419.2	2264.6
25°	3035.9	3045.0	3046.4	3040.1	3022.6	2988.3	2922.4	2827.8	2694.7	2516.0	2354.7
27.5°	2761.2	2774.1	2811.6	2844.7	2881.9	2919.7	2914.6	2867.7	2769.2	2614.9	2417.8
30°	2486.4	2458.4	2527.8	2615.5	2675.0	2780.1	2839.0	2842.5	2787.1	2654.7	2462.6
32.5°	2105.2	2136.1	2166.8	2274.6	2404.8	2522.8	2640.0	2734.3	2745.1	2656.9	2489.0
35°	1635.7	1674.3	1730.3	1786.4	1926.5	2047.1	2253.1	2432.5	2575.5	2594.4	2491.4
37.5°	1318.1	1337.1	1372.6	1428.8	1520.5	1663.5	1822.8	2049.6	2256.7	2410.8	2417.5
40°	1152.2	1157.7	1197.7	1240.5	1314.7	1432.4	1576.1	1776.6	2024.6	2239.8	2329.5
42.5°	1027.7	1040.0	1056.9	1098.1	1157.2	1245.8	1379.4	1545.0	1772.4	2020.0	2195.5
45°	883.1	897.1	907.6	934.9	977.0	1036.5	1129.7	1281.1	1454.2	1709.9	1946.2
47.5°	787.5	788.5	796.4	817.0	845.6	890.3	956.2	1053.5	1212.4	1419.9	1662.3
50°	719.1	730.2	733.1	749.1	771.6	804.5	859.2	941.9	1072.3	1254.5	1477.3
52.5°	670.8	674.2	682.1	693.7	713.3	739.0	786.3	851.0	953.4	1108.7	1313.6
55°	599.9	599.9	607.6	616.7	627.9	651.0	682.6	730.2	808.1	928.5	1098.1
57.5°	534.3	537.8	543.2	546.1	555.6	570.9	597.3	633.4	691.4	784.2	919.1
60°	490.5	496.9	496.1	501.8	510.2	522.1	544.6	574.0	625.8	700.1	813.7
62.5°	452.5	452.0	451.9	458.6	467.0	478.4	492.9	518.4	562.5	628.4	725.1
65°	389.7	388.3	393.2	397.3	400.2	408.6	419.8	442.2	471.6	520.7	595.7
67.5°	333.9	329.8	332.4	333.9	338.7	345.2	355.7	369.6	393.0	432.4	488.9
70°	295.8	292.2	291.5	292.9	297.1	302.0	309.8	323.1	344.8	376.3	417.7
72.5°	256.5	254.1	254.0	257.1	259.0	262.3	267.7	279.9	297.1	320.8	359.4
75°	200.5	200.5	200.5	201.2	203.2	206.1	210.3	216.5	229.9	246.6	272.6
77.5°	150.3	150.1	149.3	149.1	152.2	153.5	154.4	160.3	167.7	179.1	198.0
80°	117.7	114.2	115.7	117.7	119.1	119.8	122.0	123.3	129.7	136.0	149.3
82.5°	87.5	84.5	84.8	88.0	88.3	89.0	91.1	93.1	95.4	101.2	108.3
85°	46.3	46.3	47.0	47.0	47.6	47.0	49.0	49.8	49.8	53.2	57.4
87.5°	22.0	21.0	21.4	21.8	21.4	21.7	22.0	22.4	22.7	23.5	23.5
90°	25.8	26.7	25.8	24.9	25.8	24.1	23.2	22.3	21.4	22.3	19.6
92.5°	42.9	44.5	43.6	46.3	47.9	52.5	59.5	74.9	103.3	136.9	150.6
95°	103.3	106.8	113.1	121.1	137.9	170.0	217.2	320.4	428.1	527.8	469.9
97.5°	281.1	288.7	312.8	352.8	418.5	525.0	639.8	798.8	875.1	818.0	598.9
100°	558.1	557.2	591.9	656.9	746.8	873.2	977.3	1049.5	1018.2	842.9	569.6
102.5°	818.7	839.2	868.2	919.6	989.6	1069.7	1130.4	1132.7	1025.4	796.7	526.9
105°	1132.2	1136.7	1165.1	1198.9	1239.9	1263.0	1246.2	1157.1	971.1	715.6	474.4
107.5°	1312.7	1320.9	1330.5	1341.9	1341.2	1309.5	1231.5	1087.0	876.0	644.1	441.0
110°	1386.8	1388.6	1390.4	1383.2	1358.3	1295.9	1183.8	1020.0	816.2	603.5	428.1



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1401.7	1401.3	1394.5	1372.5	1327.0	1246.8	1121.1	953.8	764.2	576.4	421.0
115°	1377.0	1372.5	1354.7	1315.5	1248.8	1151.7	1020.9	866.0	701.4	547.4	418.3
117.5°	1298.2	1292.3	1266.6	1221.7	1152.1	1053.6	936.2	802.5	663.4	530.3	419.9
120°	1232.8	1227.4	1206.0	1156.2	1085.9	996.0	889.2	769.0	643.5	522.5	422.8
122.5°	1171.5	1164.8	1141.3	1096.4	1033.9	950.5	851.5	742.7	627.1	517.5	427.8
125°	1085.9	1079.7	1057.4	1018.2	961.3	890.1	804.7	707.7	606.2	511.0	435.2
127.5°	1015.4	1009.7	989.6	956.1	905.4	840.6	763.5	677.0	587.6	507.7	443.8
130°	975.5	968.4	949.8	917.7	870.5	809.9	737.9	657.8	577.7	505.6	449.5
132.5°	936.4	931.4	914.8	882.8	838.5	780.8	713.6	640.0	568.4	504.9	453.8
135°	880.3	874.1	858.0	831.3	787.7	737.0	679.1	615.9	556.3	503.8	460.2
137.5°	821.0	816.9	803.4	776.3	739.7	695.7	645.9	594.1	545.8	501.9	464.4
140°	779.7	780.6	766.3	741.5	707.7	669.3	626.6	581.2	539.4	501.1	467.3
142.5°	741.3	742.2	729.3	707.3	678.4	645.2	608.1	569.1	533.7	499.7	469.4
145°	688.0	686.3	679.1	660.4	638.2	612.3	583.9	554.6	526.0	497.6	470.8
147.5°	644.3	643.5	636.8	624.1	607.3	588.9	565.9	542.6	518.5	494.2	470.8
150°	618.6	618.6	613.2	603.5	590.1	573.2	554.6	534.0	513.5	491.3	470.8
152.5°	597.3	597.3	594.1	585.0	574.4	560.4	543.9	526.2	507.9	487.8	468.7
155°	570.5	569.6	567.8	560.8	552.8	542.1	528.7	514.4	499.4	481.5	466.4
157.5°	546.2	546.4	544.9	539.6	532.6	524.2	513.9	502.0	489.7	476.0	463.4
160°	530.5	531.4	531.4	526.0	519.8	513.5	504.7	494.9	483.3	471.7	462.0
162.5°	516.2	517.1	517.1	512.6	508.5	502.9	494.7	486.3	476.9	467.4	459.1
165°	497.6	497.6	498.5	494.9	491.3	486.9	480.6	475.3	468.1	461.1	454.9
167.5°	479.7	479.7	480.6	478.1	476.5	473.3	469.8	465.7	459.9	454.7	450.6
170°	469.0	469.0	469.9	468.1	467.3	465.5	462.0	459.3	454.9	450.4	447.7
172.5°	459.1	459.9	461.5	459.7	459.5	458.4	455.6	453.6	449.9	446.8	445.6
175°	447.7	448.6	449.5	448.6	448.6	448.6	446.8	445.9	444.2	442.4	442.4
177.5°	441.1	441.1	442.6	441.8	442.6	442.6	441.8	441.1	440.4	439.7	440.4
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1491.3	1486.8	1482.4	1474.5	1467.8	1458.2	1455.5	1452.1	1442.0	1433.1	1426.3
5°	1582.4	1565.6	1541.1	1518.7	1500.5	1476.0	1461.9	1447.2	1426.1	1407.2	1391.8
7.5°	1677.8	1644.7	1606.5	1565.3	1527.0	1490.0	1460.1	1433.4	1404.0	1376.1	1354.4
10°	1753.5	1705.8	1652.5	1595.1	1546.0	1498.3	1458.4	1423.3	1385.5	1352.5	1325.3
12.5°	1839.8	1769.2	1695.7	1625.9	1567.9	1501.7	1453.3	1408.8	1365.9	1326.2	1295.6
15°	1942.0	1852.3	1765.3	1669.4	1581.0	1498.3	1440.9	1384.8	1335.1	1294.4	1255.2
17.5°	2035.1	1933.4	1818.9	1702.1	1595.6	1497.5	1417.0	1353.7	1291.5	1241.7	1202.6
20°	2087.8	1972.1	1842.5	1721.2	1603.5	1494.2	1405.9	1330.2	1262.8	1210.3	1166.2
22.5°	2133.2	1997.9	1863.8	1734.1	1602.9	1485.1	1385.1	1307.2	1234.3	1182.9	1135.9
25°	2180.2	2018.4	1883.8	1731.7	1585.3	1463.3	1351.2	1262.8	1190.0	1129.7	1081.4
27.5°	2220.6	2017.0	1857.3	1693.7	1557.5	1435.3	1315.5	1220.8	1143.4	1078.0	1028.9
30°	2247.5	2019.7	1829.8	1667.9	1530.6	1404.4	1288.1	1192.8	1111.5	1044.9	998.6
32.5°	2264.3	2018.0	1804.6	1632.1	1488.0	1376.4	1258.4	1159.7	1076.2	1010.8	966.2
35°	2274.1	2005.7	1761.1	1557.9	1419.2	1310.5	1211.7	1109.4	1021.8	960.8	910.3
37.5°	2254.5	1979.8	1710.7	1486.4	1334.5	1227.5	1144.4	1057.2	973.4	906.3	862.8
40°	2223.7	1963.0	1671.4	1436.0	1276.2	1173.1	1102.4	1016.9	934.2	870.4	829.7
42.5°	2164.8	1928.8	1628.3	1379.9	1215.7	1112.6	1047.4	976.0	897.8	837.9	797.3
45°	2021.2	1854.3	1563.5	1295.8	1126.2	1019.7	962.2	910.3	839.5	781.4	746.4
47.5°	1821.9	1742.4	1469.9	1207.1	1032.9	930.4	870.7	828.9	777.2	730.2	696.6
50°	1683.4	1650.4	1406.5	1146.6	970.6	870.4	813.0	775.1	738.0	691.0	660.1
52.5°	1523.6	1543.9	1332.6	1083.7	907.3	808.8	754.7	724.6	690.9	652.3	625.4
55°	1298.6	1372.2	1204.7	978.3	813.0	719.1	667.9	641.2	621.6	592.9	569.8
57.5°	1088.0	1181.6	1066.5	869.7	720.3	639.3	590.2	561.2	548.6	533.6	515.4
60°	963.0	1055.4	967.9	796.8	658.1	580.9	537.5	513.0	500.3	489.9	474.5
62.5°	851.3	944.9	871.4	722.8	596.9	525.5	487.6	463.7	453.9	448.4	435.2
65°	698.0	778.6	729.5	607.6	509.5	446.4	412.1	395.3	386.1	384.1	375.7
67.5°	568.1	629.5	593.7	504.0	426.8	372.3	343.1	328.9	321.8	321.1	314.8
70°	482.9	540.3	513.0	431.7	365.2	322.4	297.1	284.5	280.4	279.6	276.2
72.5°	416.7	456.8	435.1	367.2	315.8	277.0	258.4	245.3	240.5	241.5	239.2
75°	308.4	338.5	325.9	278.9	237.6	212.3	196.9	188.5	184.3	186.5	183.6
77.5°	221.9	240.9	229.6	197.1	171.6	153.4	142.0	136.8	133.0	132.9	131.6
80°	167.5	178.7	172.4	152.8	131.8	116.4	107.2	103.7	101.7	100.9	100.2
82.5°	119.3	128.9	121.4	107.9	93.6	84.4	79.2	74.5	73.0	73.5	72.8
85°	60.3	63.8	61.0	52.5	47.0	42.7	39.9	37.8	36.5	37.2	35.8
87.5°	24.2	24.2	21.9	19.4	17.8	15.6	15.2	13.8	13.0	13.4	13.4
90°	16.9	14.3	11.6	9.8	8.0	5.4	3.6	1.8	3.6	5.4	8.0
92.5°	113.1	74.7	51.5	38.3	30.8	23.9	16.4	11.1	16.4	23.9	30.8
95°	324.0	191.4	115.7	81.0	57.9	42.7	32.9	30.2	32.9	42.7	57.9
97.5°	355.5	206.0	133.7	96.1	73.3	60.2	52.5	51.6	52.5	60.2	73.3
100°	335.6	203.8	141.5	106.8	85.4	73.0	66.8	65.9	66.8	73.0	85.4
102.5°	318.4	206.7	150.8	119.0	99.7	87.9	82.4	80.8	82.4	87.9	99.7
105°	306.2	214.5	166.5	138.8	122.0	111.3	105.9	103.3	105.9	111.3	122.0
107.5°	305.3	229.1	186.9	161.3	145.4	134.9	129.7	127.1	129.7	134.9	145.4
110°	308.9	241.2	201.2	176.2	161.1	151.3	146.9	144.2	146.9	151.3	161.1





TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	316.0	253.3	216.2	191.9	176.7	167.0	162.6	159.9	162.6	167.0	176.7
115°	327.5	273.2	239.4	215.4	200.3	191.4	186.0	182.4	186.0	191.4	200.3
117.5°	342.9	294.4	261.0	238.7	221.8	213.7	209.2	205.1	209.2	213.7	221.8
120°	354.3	308.0	275.9	253.7	236.7	227.8	223.4	220.7	223.4	227.8	236.7
122.5°	365.0	322.2	290.9	267.2	251.0	241.4	236.9	234.3	236.9	241.4	251.0
125°	381.8	342.7	311.6	287.5	270.5	260.8	255.5	253.7	255.5	260.8	270.5
127.5°	395.7	360.5	330.4	306.4	287.7	277.7	271.1	268.5	271.1	277.7	287.7
130°	405.0	371.1	341.8	317.7	299.1	288.4	280.4	277.7	280.4	288.4	299.1
132.5°	413.6	380.4	351.8	328.4	309.8	296.9	288.2	284.8	288.2	296.9	309.8
135°	424.5	394.3	366.7	342.7	324.0	310.7	300.9	297.3	300.9	310.7	324.0
137.5°	432.7	403.9	377.4	355.2	336.6	322.4	312.8	309.1	312.8	322.4	336.6
140°	437.0	410.4	384.5	362.3	344.5	330.2	321.3	316.9	321.3	330.2	344.5
142.5°	441.3	415.4	390.2	369.3	351.6	338.8	329.1	325.4	329.1	338.8	351.6
145°	445.9	421.9	398.8	378.3	363.2	349.8	341.8	339.1	341.8	349.8	363.2
147.5°	448.8	427.2	406.1	388.6	374.0	362.5	354.6	353.0	354.6	362.5	374.0
150°	449.5	430.8	410.4	394.3	381.8	370.2	363.2	362.3	363.2	370.2	381.8
152.5°	450.9	432.9	415.4	400.0	389.0	378.8	371.7	371.5	371.7	378.8	389.0
155°	451.3	437.0	421.9	409.5	399.7	390.7	385.4	385.4	385.4	390.7	399.7
157.5°	452.2	439.3	427.2	417.6	409.3	401.4	397.2	396.5	397.2	401.4	409.3
160°	452.2	441.5	430.8	421.9	415.6	408.6	405.0	405.0	405.0	408.6	415.6
162.5°	451.5	442.2	432.9	425.4	419.9	414.3	411.4	411.4	411.4	414.3	419.9
165°	449.5	443.3	436.1	429.9	426.3	421.9	420.1	421.0	420.1	421.9	426.3
167.5°	448.1	443.1	437.9	434.0	431.5	428.1	427.2	428.3	427.2	428.1	431.5
170°	445.9	442.4	437.9	436.1	434.4	431.7	430.8	432.6	430.8	431.7	434.4
172.5°	445.2	442.4	438.6	437.6	436.5	434.5	434.4	435.4	434.4	434.5	436.5
175°	443.3	441.5	439.7	438.8	438.8	437.0	437.9	438.8	437.9	437.0	438.8
177.5°	441.8	440.4	439.7	439.7	439.7	439.0	439.7	440.4	439.7	439.0	439.7
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1422.4	1418.4	1412.8	1404.4	1397.7	1387.1	1387.1	1388.8	1388.8	1388.2	1387.1
5°	1379.2	1368.7	1356.1	1341.4	1326.0	1310.5	1307.7	1302.1	1297.9	1295.1	1291.6
7.5°	1333.6	1315.0	1296.6	1276.0	1257.2	1241.7	1230.9	1221.9	1216.2	1210.1	1205.5
10°	1302.8	1279.7	1257.9	1236.3	1212.4	1193.5	1181.6	1173.1	1166.9	1161.3	1158.4
12.5°	1266.4	1239.9	1215.9	1195.3	1169.2	1149.8	1138.4	1134.4	1127.0	1115.3	1109.1
15°	1213.1	1188.6	1159.8	1128.3	1115.7	1091.9	1078.5	1072.3	1068.0	1058.9	1056.1
17.5°	1167.5	1135.4	1103.2	1079.7	1056.2	1036.9	1029.5	1021.6	1016.0	1008.6	1006.4
20°	1131.1	1102.4	1072.9	1047.8	1023.1	1002.2	995.9	990.2	984.6	981.1	978.3
22.5°	1094.1	1065.4	1041.0	1017.4	991.2	977.5	970.6	964.5	960.6	958.1	955.4
25°	1042.1	1016.9	989.5	968.5	947.5	938.3	934.2	930.7	927.9	924.3	923.6
27.5°	995.6	968.1	945.9	926.3	911.2	903.7	899.6	897.9	898.5	899.7	900.5
30°	960.8	935.6	917.4	900.5	886.5	879.5	878.8	878.8	881.6	882.3	883.7
32.5°	928.9	908.1	889.9	873.6	863.0	858.2	860.9	860.9	863.1	865.0	867.5
35°	882.3	864.1	850.1	836.1	827.0	829.0	830.5	831.9	835.4	839.5	842.4
37.5°	837.9	822.1	807.4	796.6	792.4	796.1	799.5	802.5	806.5	809.8	812.5
40°	805.9	794.0	780.0	770.2	771.6	773.7	776.5	780.0	783.5	785.6	788.5
42.5°	776.2	763.8	753.1	744.9	746.9	749.6	751.3	753.1	757.2	761.0	762.6
45°	730.9	721.1	711.3	706.4	707.8	709.3	710.6	712.7	716.2	719.1	719.7
47.5°	680.1	673.2	666.6	661.8	664.1	663.5	665.4	669.9	670.9	672.6	676.5
50°	647.6	641.2	633.6	632.1	632.1	632.1	632.8	638.5	638.5	641.2	644.1
52.5°	611.7	607.6	602.7	600.2	599.1	599.1	602.0	604.8	605.9	609.8	612.7
55°	558.6	554.4	550.1	548.0	546.6	548.0	553.7	555.0	558.6	560.6	562.8
57.5°	503.2	500.0	496.6	495.4	495.2	497.0	500.1	504.3	505.2	511.6	514.8
60°	466.7	461.8	459.1	459.1	457.6	464.0	462.5	469.6	470.9	475.2	480.1
62.5°	429.2	422.6	421.5	421.5	423.5	425.3	427.2	430.3	433.9	439.3	443.1
65°	368.6	365.2	370.1	369.3	367.9	372.1	372.1	375.7	379.9	384.8	392.4
67.5°	311.3	309.5	309.9	309.9	312.0	314.4	316.4	319.4	324.5	329.7	334.7
70°	272.6	274.7	271.3	274.0	276.2	276.8	278.2	282.4	288.0	291.5	297.1
72.5°	235.1	234.9	235.3	236.5	238.5	239.8	241.2	246.0	252.2	255.1	259.6
75°	180.8	180.1	182.2	182.2	185.7	187.1	188.5	190.6	196.3	200.5	203.9
77.5°	132.1	132.9	132.4	134.8	133.8	134.1	138.5	140.6	141.2	149.5	151.2
80°	99.5	100.9	101.7	102.3	103.0	101.7	106.6	108.6	108.6	113.5	117.0
82.5°	71.5	72.3	74.2	74.8	75.0	76.4	76.8	78.4	80.1	82.1	86.8
85°	35.8	37.8	38.5	37.8	38.5	37.2	39.2	39.9	40.7	40.7	40.7
87.5°	13.2	14.1	14.1	15.2	15.2	16.2	16.1	15.1	15.2	17.1	15.2
90°	9.8	11.6	14.3	16.9	19.6	22.3	21.4	22.3	23.2	24.1	25.8
92.5°	38.3	51.5	74.7	113.1	150.6	136.9	103.3	74.9	59.5	52.5	47.9
95°	81.0	115.7	191.4	324.0	469.9	527.8	428.1	320.4	217.2	170.0	137.9
97.5°	96.1	133.7	206.0	355.5	598.9	818.0	875.1	798.8	639.8	525.0	418.5
100°	106.8	141.5	203.8	335.6	569.6	842.9	1018.2	1049.5	977.3	873.2	746.8
102.5°	119.0	150.8	206.7	318.4	526.9	796.7	1025.4	1132.7	1130.4	1069.7	989.6
105°	138.8	166.5	214.5	306.2	474.4	715.6	971.1	1157.1	1246.2	1263.0	1239.9
107.5°	161.3	186.9	229.1	305.3	441.0	644.1	876.0	1087.0	1231.5	1309.5	1341.2
110°	176.2	201.2	241.2	308.9	428.1	603.5	816.2	1020.0	1183.8	1295.9	1358.3



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	191.9	216.2	253.3	316.0	421.0	576.4	764.2	953.8	1121.1	1246.8	1327.0
115°	215.4	239.4	273.2	327.5	418.3	547.4	701.4	866.0	1020.9	1151.7	1248.8
117.5°	238.7	261.0	294.4	342.9	419.9	530.3	663.4	802.5	936.2	1053.6	1152.1
120°	253.7	275.9	308.0	354.3	422.8	522.5	643.5	769.0	889.2	996.0	1085.9
122.5°	267.2	290.9	322.2	365.0	427.8	517.5	627.1	742.7	851.5	950.5	1033.9
125°	287.5	311.6	342.7	381.8	435.2	511.0	606.2	707.7	804.7	890.1	961.3
127.5°	306.4	330.4	360.5	395.7	443.8	507.7	587.6	677.0	763.5	840.6	905.4
130°	317.7	341.8	371.1	405.0	449.5	505.6	577.7	657.8	737.9	809.9	870.5
132.5°	328.4	351.8	380.4	413.6	453.8	504.9	568.4	640.0	713.6	780.8	838.5
135°	342.7	366.7	394.3	424.5	460.2	503.8	556.3	615.9	679.1	737.0	787.7
137.5°	355.2	377.4	403.9	432.7	464.4	501.9	545.8	594.1	645.9	695.7	739.7
140°	362.3	384.5	410.4	437.0	467.3	501.1	539.4	581.2	626.6	669.3	707.7
142.5°	369.3	390.2	415.4	441.3	469.4	499.7	533.7	569.1	608.1	645.2	678.4
145°	378.3	398.8	421.9	445.9	470.8	497.6	526.0	554.6	583.9	612.3	638.2
147.5°	388.6	406.1	427.2	448.8	470.8	494.2	518.5	542.6	565.9	588.9	607.3
150°	394.3	410.4	430.8	449.5	470.8	491.3	513.5	534.0	554.6	573.2	590.1
152.5°	400.0	415.4	432.9	450.9	468.7	487.8	507.9	526.2	543.9	560.4	574.4
155°	409.5	421.9	437.0	451.3	466.4	481.5	499.4	514.4	528.7	542.1	552.8
157.5°	417.6	427.2	439.3	452.2	463.4	476.0	489.7	502.0	513.9	524.2	532.6
160°	421.9	430.8	441.5	452.2	462.0	471.7	483.3	494.9	504.7	513.5	519.8
162.5°	425.4	432.9	442.2	451.5	459.1	467.4	476.9	486.3	494.7	502.9	508.5
165°	429.9	436.1	443.3	449.5	454.9	461.1	468.1	475.3	480.6	486.9	491.3
167.5°	434.0	437.9	443.1	448.1	450.6	454.7	459.9	465.7	469.8	473.3	476.5
170°	436.1	437.9	442.4	445.9	447.7	450.4	454.9	459.3	462.0	465.5	467.3
172.5°	437.6	438.6	442.4	445.2	445.6	446.8	449.9	453.6	455.6	458.4	459.5
175°	438.8	439.7	441.5	443.3	442.4	442.4	444.2	445.9	446.8	448.6	448.6
177.5°	439.7	439.7	440.4	441.8	440.4	439.7	440.4	441.1	441.8	442.6	442.6
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1383.1	1382.6	1386.5	1383.7	1386.5	1382.6	1383.1	1387.1	1388.2	1388.8	1388.8
5°	1287.4	1289.5	1282.5	1282.5	1282.5	1289.5	1287.4	1291.6	1295.1	1297.9	1302.1
7.5°	1202.2	1199.1	1199.4	1195.6	1199.4	1199.1	1202.2	1205.5	1210.1	1216.2	1221.9
10°	1150.0	1145.8	1144.4	1145.1	1144.4	1145.8	1150.0	1158.4	1161.3	1166.9	1173.1
12.5°	1106.9	1106.0	1096.8	1096.9	1096.8	1106.0	1106.9	1109.1	1115.3	1127.0	1134.4
15°	1056.1	1042.9	1041.4	1045.6	1041.4	1042.9	1056.1	1056.1	1058.9	1068.0	1072.3
17.5°	1005.2	998.3	998.6	996.6	998.6	998.3	1005.2	1006.4	1008.6	1016.0	1021.6
20°	978.3	974.1	973.4	968.5	973.4	974.1	978.3	978.3	981.1	984.6	990.2
22.5°	953.7	952.3	952.7	947.3	952.7	952.3	953.7	955.4	958.1	960.6	964.5
25°	923.0	926.5	923.6	923.6	923.6	926.5	923.0	923.6	924.3	927.9	930.7
27.5°	902.2	902.1	900.7	900.7	900.7	902.1	902.2	900.5	899.7	898.5	897.9
30°	886.5	885.8	887.3	887.3	887.3	885.8	886.5	883.7	882.3	881.6	878.8
32.5°	870.8	871.8	872.1	872.6	872.1	871.8	870.8	867.5	865.0	863.1	860.9
35°	846.6	847.3	849.4	848.0	849.4	847.3	846.6	842.4	839.5	835.4	831.9
37.5°	813.8	817.0	816.3	817.4	816.3	817.0	813.8	812.5	809.8	806.5	802.5
40°	789.1	791.2	790.5	790.5	790.5	791.2	789.1	788.5	785.6	783.5	780.0
42.5°	763.9	765.4	763.6	762.5	763.6	765.4	763.9	762.6	761.0	757.2	753.1
45°	722.6	721.1	723.3	720.4	723.3	721.1	722.6	719.7	719.1	716.2	712.7
47.5°	676.3	677.7	678.2	680.4	678.2	677.7	676.3	676.5	672.6	670.9	669.9
50°	645.4	649.6	649.6	649.0	649.6	649.6	645.4	644.1	641.2	638.5	638.5
52.5°	615.2	617.2	619.9	619.8	619.9	617.2	615.2	612.7	609.8	605.9	604.8
55°	568.4	569.8	571.1	571.9	571.1	569.8	568.4	562.8	560.6	558.6	555.0
57.5°	519.9	519.3	522.6	523.6	522.6	519.3	519.9	514.8	511.6	505.2	504.3
60°	485.6	485.6	491.2	493.4	491.2	485.6	485.6	480.1	475.2	470.9	469.6
62.5°	449.2	451.5	457.1	454.1	457.1	451.5	449.2	443.1	439.3	433.9	430.3
65°	395.9	401.5	400.8	403.7	400.8	401.5	395.9	392.4	384.8	379.9	375.7
67.5°	340.3	343.8	348.8	349.3	348.8	343.8	340.3	334.7	329.7	324.5	319.4
70°	302.7	306.2	309.1	311.1	309.1	306.2	302.7	297.1	291.5	288.0	282.4
72.5°	266.4	268.1	274.8	271.9	274.8	268.1	266.4	259.6	255.1	252.2	246.0
75°	208.8	213.7	217.9	215.9	217.9	213.7	208.8	203.9	200.5	196.3	190.6
77.5°	154.4	159.3	161.3	159.5	161.3	159.3	154.4	151.2	149.5	141.2	140.6
80°	122.0	121.3	125.5	124.8	125.5	121.3	122.0	117.0	113.5	108.6	108.6
82.5°	89.4	88.7	90.7	91.1	90.7	88.7	89.4	86.8	82.1	80.1	78.4
85°	43.4	45.6	42.7	42.1	42.7	45.6	43.4	40.7	40.7	40.7	39.9
87.5°	15.1	15.2	14.9	14.1	14.9	15.2	15.1	15.2	17.1	15.2	15.1
90°	24.9	25.8	26.7	25.8	26.7	25.8	24.9	25.8	24.1	23.2	22.3
92.5°	46.3	43.6	44.5	42.9	44.5	43.6	46.3	47.9	52.5	59.5	74.9
95°	121.1	113.1	106.8	103.3	106.8	113.1	121.1	137.9	170.0	217.2	320.4
97.5°	352.8	312.8	288.7	281.1	288.7	312.8	352.8	418.5	525.0	639.8	798.8
100°	656.9	591.9	557.2	558.1	557.2	591.9	656.9	746.8	873.2	977.3	1049.5
102.5°	919.6	868.2	839.2	818.7	839.2	868.2	919.6	989.6	1069.7	1130.4	1132.7
105°	1198.9	1165.1	1136.7	1132.2	1136.7	1165.1	1198.9	1239.9	1263.0	1246.2	1157.1
107.5°	1341.9	1330.5	1320.9	1312.7	1320.9	1330.5	1341.9	1341.2	1309.5	1231.5	1087.0
110°	1383.2	1390.4	1388.6	1386.8	1388.6	1390.4	1383.2	1358.3	1295.9	1183.8	1020.0



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1372.5	1394.5	1401.3	1401.7	1401.3	1394.5	1372.5	1327.0	1246.8	1121.1	953.8
115°	1315.5	1354.7	1372.5	1377.0	1372.5	1354.7	1315.5	1248.8	1151.7	1020.9	866.0
117.5°	1221.7	1266.6	1292.3	1298.2	1292.3	1266.6	1221.7	1152.1	1053.6	936.2	802.5
120°	1156.2	1206.0	1227.4	1232.8	1227.4	1206.0	1156.2	1085.9	996.0	889.2	769.0
122.5°	1096.4	1141.3	1164.8	1171.5	1164.8	1141.3	1096.4	1033.9	950.5	851.5	742.7
125°	1018.2	1057.4	1079.7	1085.9	1079.7	1057.4	1018.2	961.3	890.1	804.7	707.7
127.5°	956.1	989.6	1009.7	1015.4	1009.7	989.6	956.1	905.4	840.6	763.5	677.0
130°	917.7	949.8	968.4	975.5	968.4	949.8	917.7	870.5	809.9	737.9	657.8
132.5°	882.8	914.8	931.4	936.4	931.4	914.8	882.8	838.5	780.8	713.6	640.0
135°	831.3	858.0	874.1	880.3	874.1	858.0	831.3	787.7	737.0	679.1	615.9
137.5°	776.3	803.4	816.9	821.0	816.9	803.4	776.3	739.7	695.7	645.9	594.1
140°	741.5	766.3	780.6	779.7	780.6	766.3	741.5	707.7	669.3	626.6	581.2
142.5°	707.3	729.3	742.2	741.3	742.2	729.3	707.3	678.4	645.2	608.1	569.1
145°	660.4	679.1	686.3	688.0	686.3	679.1	660.4	638.2	612.3	583.9	554.6
147.5°	624.1	636.8	643.5	644.3	643.5	636.8	624.1	607.3	588.9	565.9	542.6
150°	603.5	613.2	618.6	618.6	618.6	613.2	603.5	590.1	573.2	554.6	534.0
152.5°	585.0	594.1	597.3	597.3	597.3	594.1	585.0	574.4	560.4	543.9	526.2
155°	560.8	567.8	569.6	570.5	569.6	567.8	560.8	552.8	542.1	528.7	514.4
157.5°	539.6	544.9	546.4	546.2	546.4	544.9	539.6	532.6	524.2	513.9	502.0
160°	526.0	531.4	531.4	530.5	531.4	531.4	526.0	519.8	513.5	504.7	494.9
162.5°	512.6	517.1	517.1	516.2	517.1	517.1	512.6	508.5	502.9	494.7	486.3
165°	494.9	498.5	497.6	497.6	497.6	498.5	494.9	491.3	486.9	480.6	475.3
167.5°	478.1	480.6	479.7	479.7	479.7	480.6	478.1	476.5	473.3	469.8	465.7
170°	468.1	469.9	469.0	469.0	469.0	469.9	468.1	467.3	465.5	462.0	459.3
172.5°	459.7	461.5	459.9	459.1	459.9	461.5	459.7	459.5	458.4	455.6	453.6
175°	448.6	449.5	448.6	447.7	448.6	449.5	448.6	448.6	448.6	446.8	445.9
177.5°	441.8	442.6	441.1	441.1	441.1	442.6	441.8	442.6	442.6	441.8	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1387.1	1387.1	1397.7	1404.4	1412.8	1418.4	1422.4	1426.3	1433.1	1442.0	1452.1
5°	1307.7	1310.5	1326.0	1341.4	1356.1	1368.7	1379.2	1391.8	1407.2	1426.1	1447.2
7.5°	1230.9	1241.7	1257.2	1276.0	1296.6	1315.0	1333.6	1354.4	1376.1	1404.0	1433.4
10°	1181.6	1193.5	1212.4	1236.3	1257.9	1279.7	1302.8	1325.3	1352.5	1385.5	1423.3
12.5°	1138.4	1149.8	1169.2	1195.3	1215.9	1239.9	1266.4	1295.6	1326.2	1365.9	1408.8
15°	1078.5	1091.9	1115.7	1128.3	1159.8	1188.6	1213.1	1255.2	1294.4	1335.1	1384.8
17.5°	1029.5	1036.9	1056.2	1079.7	1103.2	1135.4	1167.5	1202.6	1241.7	1291.5	1353.7
20°	995.9	1002.2	1023.1	1047.8	1072.9	1102.4	1131.1	1166.2	1210.3	1262.8	1330.2
22.5°	970.6	977.5	991.2	1017.4	1041.0	1065.4	1094.1	1135.9	1182.9	1234.3	1307.2
25°	934.2	938.3	947.5	968.5	989.5	1016.9	1042.1	1081.4	1129.7	1190.0	1262.8
27.5°	899.6	903.7	911.2	926.3	945.9	968.1	995.6	1028.9	1078.0	1143.4	1220.8
30°	878.8	879.5	886.5	900.5	917.4	935.6	960.8	998.6	1044.9	1111.5	1192.8
32.5°	860.9	858.2	863.0	873.6	889.9	908.1	928.9	966.2	1010.8	1076.2	1159.7
35°	830.5	829.0	827.0	836.1	850.1	864.1	882.3	910.3	960.8	1021.8	1109.4
37.5°	799.5	796.1	792.4	796.6	807.4	822.1	837.9	862.8	906.3	973.4	1057.2
40°	776.5	773.7	771.6	770.2	780.0	794.0	805.9	829.7	870.4	934.2	1016.9
42.5°	751.3	749.6	746.9	744.9	753.1	763.8	776.2	797.3	837.9	897.8	976.0
45°	710.6	709.3	707.8	706.4	711.3	721.1	730.9	746.4	781.4	839.5	910.3
47.5°	665.4	663.5	664.1	661.8	666.6	673.2	680.1	696.6	730.2	777.2	828.9
50°	632.8	632.1	632.1	632.1	633.6	641.2	647.6	660.1	691.0	738.0	775.1
52.5°	602.0	599.1	599.1	600.2	602.7	607.6	611.7	625.4	652.3	690.9	724.6
55°	553.7	548.0	546.6	548.0	550.1	554.4	558.6	569.8	592.9	621.6	641.2
57.5°	500.1	497.0	495.2	495.4	496.6	500.0	503.2	515.4	533.6	548.6	561.2
60°	462.5	464.0	457.6	459.1	459.1	461.8	466.7	474.5	489.9	500.3	513.0
62.5°	427.2	425.3	423.5	421.5	421.5	422.6	429.2	435.2	448.4	453.9	463.7
65°	372.1	372.1	367.9	369.3	370.1	365.2	368.6	375.7	384.1	386.1	395.3
67.5°	316.4	314.4	312.0	309.9	309.9	309.5	311.3	314.8	321.1	321.8	328.9
70°	278.2	276.8	276.2	274.0	271.3	274.7	272.6	276.2	279.6	280.4	284.5
72.5°	241.2	239.8	238.5	236.5	235.3	234.9	235.1	239.2	241.5	240.5	245.3
75°	188.5	187.1	185.7	182.2	182.2	180.1	180.8	183.6	186.5	184.3	188.5
77.5°	138.5	134.1	133.8	134.8	132.4	132.9	132.1	131.6	132.9	133.0	136.8
80°	106.6	101.7	103.0	102.3	101.7	100.9	99.5	100.2	100.9	101.7	103.7
82.5°	76.8	76.4	75.0	74.8	74.2	72.3	71.5	72.8	73.5	73.0	74.5
85°	39.2	37.2	38.5	37.8	38.5	37.8	35.8	35.8	37.2	36.5	37.8
87.5°	16.1	16.2	15.2	15.2	14.1	14.1	13.2	13.4	13.4	13.0	13.8
90°	21.4	22.3	19.6	16.9	14.3	11.6	9.8	8.0	5.4	3.6	1.8
92.5°	103.3	136.9	150.6	113.1	74.7	51.5	38.3	30.8	23.9	16.4	11.1
95°	428.1	527.8	469.9	324.0	191.4	115.7	81.0	57.9	42.7	32.9	30.2
97.5°	875.1	818.0	598.9	355.5	206.0	133.7	96.1	73.3	60.2	52.5	51.6
100°	1018.2	842.9	569.6	335.6	203.8	141.5	106.8	85.4	73.0	66.8	65.9
102.5°	1025.4	796.7	526.9	318.4	206.7	150.8	119.0	99.7	87.9	82.4	80.8
105°	971.1	715.6	474.4	306.2	214.5	166.5	138.8	122.0	111.3	105.9	103.3
107.5°	876.0	644.1	441.0	305.3	229.1	186.9	161.3	145.4	134.9	129.7	127.1
110°	816.2	603.5	428.1	308.9	241.2	201.2	176.2	161.1	151.3	146.9	144.2



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	764.2	576.4	421.0	316.0	253.3	216.2	191.9	176.7	167.0	162.6	159.9
115°	701.4	547.4	418.3	327.5	273.2	239.4	215.4	200.3	191.4	186.0	182.4
117.5°	663.4	530.3	419.9	342.9	294.4	261.0	238.7	221.8	213.7	209.2	205.1
120°	643.5	522.5	422.8	354.3	308.0	275.9	253.7	236.7	227.8	223.4	220.7
122.5°	627.1	517.5	427.8	365.0	322.2	290.9	267.2	251.0	241.4	236.9	234.3
125°	606.2	511.0	435.2	381.8	342.7	311.6	287.5	270.5	260.8	255.5	253.7
127.5°	587.6	507.7	443.8	395.7	360.5	330.4	306.4	287.7	277.7	271.1	268.5
130°	577.7	505.6	449.5	405.0	371.1	341.8	317.7	299.1	288.4	280.4	277.7
132.5°	568.4	504.9	453.8	413.6	380.4	351.8	328.4	309.8	296.9	288.2	284.8
135°	556.3	503.8	460.2	424.5	394.3	366.7	342.7	324.0	310.7	300.9	297.3
137.5°	545.8	501.9	464.4	432.7	403.9	377.4	355.2	336.6	322.4	312.8	309.1
140°	539.4	501.1	467.3	437.0	410.4	384.5	362.3	344.5	330.2	321.3	316.9
142.5°	533.7	499.7	469.4	441.3	415.4	390.2	369.3	351.6	338.8	329.1	325.4
145°	526.0	497.6	470.8	445.9	421.9	398.8	378.3	363.2	349.8	341.8	339.1
147.5°	518.5	494.2	470.8	448.8	427.2	406.1	388.6	374.0	362.5	354.6	353.0
150°	513.5	491.3	470.8	449.5	430.8	410.4	394.3	381.8	370.2	363.2	362.3
152.5°	507.9	487.8	468.7	450.9	432.9	415.4	400.0	389.0	378.8	371.7	371.5
155°	499.4	481.5	466.4	451.3	437.0	421.9	409.5	399.7	390.7	385.4	385.4
157.5°	489.7	476.0	463.4	452.2	439.3	427.2	417.6	409.3	401.4	397.2	396.5
160°	483.3	471.7	462.0	452.2	441.5	430.8	421.9	415.6	408.6	405.0	405.0
162.5°	476.9	467.4	459.1	451.5	442.2	432.9	425.4	419.9	414.3	411.4	411.4
165°	468.1	461.1	454.9	449.5	443.3	436.1	429.9	426.3	421.9	420.1	421.0
167.5°	459.9	454.7	450.6	448.1	443.1	437.9	434.0	431.5	428.1	427.2	428.3
170°	454.9	450.4	447.7	445.9	442.4	437.9	436.1	434.4	431.7	430.8	432.6
172.5°	449.9	446.8	445.6	445.2	442.4	438.6	437.6	436.5	434.5	434.4	435.4
175°	444.2	442.4	442.4	443.3	441.5	439.7	438.8	438.8	437.0	437.9	438.8
177.5°	440.4	439.7	440.4	441.8	440.4	439.7	439.7	439.7	439.0	439.7	440.4
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1455.5	1458.2	1467.8	1474.5	1482.4	1486.8	1491.3	1494.7	1499.1	1500.3	1516.5
5°	1461.9	1476.0	1500.5	1518.7	1541.1	1565.6	1582.4	1590.2	1610.4	1627.3	1660.9
7.5°	1460.1	1490.0	1527.0	1565.3	1606.5	1644.7	1677.8	1717.0	1744.9	1786.8	1828.2
10°	1458.4	1498.3	1546.0	1595.1	1652.5	1705.8	1753.5	1806.7	1850.8	1909.0	1958.7
12.5°	1453.3	1501.7	1567.9	1625.9	1695.7	1769.2	1839.8	1908.2	1947.3	2044.2	2090.0
15°	1440.9	1498.3	1581.0	1669.4	1765.3	1852.3	1942.0	2013.5	2129.0	2213.9	2267.8
17.5°	1417.0	1497.5	1595.6	1702.1	1818.9	1933.4	2035.1	2143.5	2266.2	2368.7	2478.1
20°	1405.9	1494.2	1603.5	1721.2	1842.5	1972.1	2087.8	2218.0	2352.0	2452.8	2593.0
22.5°	1385.1	1485.1	1602.9	1734.1	1863.8	1997.9	2133.2	2264.6	2419.2	2558.2	2691.7
25°	1351.2	1463.3	1585.3	1731.7	1883.8	2018.4	2180.2	2354.7	2516.0	2694.7	2827.8
27.5°	1315.5	1435.3	1557.5	1693.7	1857.3	2017.0	2220.6	2417.8	2614.9	2769.2	2867.7
30°	1288.1	1404.4	1530.6	1667.9	1829.8	2019.7	2247.5	2462.6	2654.7	2787.1	2842.5
32.5°	1258.4	1376.4	1488.0	1632.1	1804.6	2018.0	2264.3	2489.0	2656.9	2745.1	2734.3
35°	1211.7	1310.5	1419.2	1557.9	1761.1	2005.7	2274.1	2491.4	2594.4	2575.5	2432.5
37.5°	1144.4	1227.5	1334.5	1486.4	1710.7	1979.8	2254.5	2417.5	2410.8	2256.7	2049.6
40°	1102.4	1173.1	1276.2	1436.0	1671.4	1963.0	2223.7	2329.5	2239.8	2024.6	1776.6
42.5°	1047.4	1112.6	1215.7	1379.9	1628.3	1928.8	2164.8	2195.5	2020.0	1772.4	1545.0
45°	962.2	1019.7	1126.2	1295.8	1563.5	1854.3	2021.2	1946.2	1709.9	1454.2	1281.1
47.5°	870.7	930.4	1032.9	1207.1	1469.9	1742.4	1821.9	1662.3	1419.9	1212.4	1053.5
50°	813.0	870.4	970.6	1146.6	1406.5	1650.4	1683.4	1477.3	1254.5	1072.3	941.9
52.5°	754.7	808.8	907.3	1083.7	1332.6	1543.9	1523.6	1313.6	1108.7	953.4	851.0
55°	667.9	719.1	813.0	978.3	1204.7	1372.2	1298.6	1098.1	928.5	808.1	730.2
57.5°	590.2	639.3	720.3	869.7	1066.5	1181.6	1088.0	919.1	784.2	691.4	633.4
60°	537.5	580.9	658.1	796.8	967.9	1055.4	963.0	813.7	700.1	625.8	574.0
62.5°	487.6	525.5	596.9	722.8	871.4	944.9	851.3	725.1	628.4	562.5	518.4
65°	412.1	446.4	509.5	607.6	729.5	778.6	698.0	595.7	520.7	471.6	442.2
67.5°	343.1	372.3	426.8	504.0	593.7	629.5	568.1	488.9	432.4	393.0	369.6
70°	297.1	322.4	365.2	431.7	513.0	540.3	482.9	417.7	376.3	344.8	323.1
72.5°	258.4	277.0	315.8	367.2	435.1	456.8	416.7	359.4	320.8	297.1	279.9
75°	196.9	212.3	237.6	278.9	325.9	338.5	308.4	272.6	246.6	229.9	216.5
77.5°	142.0	153.4	171.6	197.1	229.6	240.9	221.9	198.0	179.1	167.7	160.3
80°	107.2	116.4	131.8	152.8	172.4	178.7	167.5	149.3	136.0	129.7	123.3
82.5°	79.2	84.4	93.6	107.9	121.4	128.9	119.3	108.3	101.2	95.4	93.1
85°	39.9	42.7	47.0	52.5	61.0	63.8	60.3	57.4	53.2	49.8	49.8
87.5°	15.2	15.6	17.8	19.4	21.9	24.2	24.2	23.5	23.5	22.7	22.4
90°	3.6	5.4	8.0	9.8	11.6	14.3	16.9	19.6	22.3	21.4	22.3
92.5°	16.4	23.9	30.8	38.3	51.5	74.7	113.1	150.6	136.9	103.3	74.9
95°	32.9	42.7	57.9	81.0	115.7	191.4	324.0	469.9	527.8	428.1	320.4
97.5°	52.5	60.2	73.3	96.1	133.7	206.0	355.5	598.9	818.0	875.1	798.8
100°	66.8	73.0	85.4	106.8	141.5	203.8	335.6	569.6	842.9	1018.2	1049.5
102.5°	82.4	87.9	99.7	119.0	150.8	206.7	318.4	526.9	796.7	1025.4	1132.7
105°	105.9	111.3	122.0	138.8	166.5	214.5	306.2	474.4	715.6	971.1	1157.1
107.5°	129.7	134.9	145.4	161.3	186.9	229.1	305.3	441.0	644.1	876.0	1087.0
110°	146.9	151.3	161.1	176.2	201.2	241.2	308.9	428.1	603.5	816.2	1020.0





TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	162.6	167.0	176.7	191.9	216.2	253.3	316.0	421.0	576.4	764.2	953.8
115°	186.0	191.4	200.3	215.4	239.4	273.2	327.5	418.3	547.4	701.4	866.0
117.5°	209.2	213.7	221.8	238.7	261.0	294.4	342.9	419.9	530.3	663.4	802.5
120°	223.4	227.8	236.7	253.7	275.9	308.0	354.3	422.8	522.5	643.5	769.0
122.5°	236.9	241.4	251.0	267.2	290.9	322.2	365.0	427.8	517.5	627.1	742.7
125°	255.5	260.8	270.5	287.5	311.6	342.7	381.8	435.2	511.0	606.2	707.7
127.5°	271.1	277.7	287.7	306.4	330.4	360.5	395.7	443.8	507.7	587.6	677.0
130°	280.4	288.4	299.1	317.7	341.8	371.1	405.0	449.5	505.6	577.7	657.8
132.5°	288.2	296.9	309.8	328.4	351.8	380.4	413.6	453.8	504.9	568.4	640.0
135°	300.9	310.7	324.0	342.7	366.7	394.3	424.5	460.2	503.8	556.3	615.9
137.5°	312.8	322.4	336.6	355.2	377.4	403.9	432.7	464.4	501.9	545.8	594.1
140°	321.3	330.2	344.5	362.3	384.5	410.4	437.0	467.3	501.1	539.4	581.2
142.5°	329.1	338.8	351.6	369.3	390.2	415.4	441.3	469.4	499.7	533.7	569.1
145°	341.8	349.8	363.2	378.3	398.8	421.9	445.9	470.8	497.6	526.0	554.6
147.5°	354.6	362.5	374.0	388.6	406.1	427.2	448.8	470.8	494.2	518.5	542.6
150°	363.2	370.2	381.8	394.3	410.4	430.8	449.5	470.8	491.3	513.5	534.0
152.5°	371.7	378.8	389.0	400.0	415.4	432.9	450.9	468.7	487.8	507.9	526.2
155°	385.4	390.7	399.7	409.5	421.9	437.0	451.3	466.4	481.5	499.4	514.4
157.5°	397.2	401.4	409.3	417.6	427.2	439.3	452.2	463.4	476.0	489.7	502.0
160°	405.0	408.6	415.6	421.9	430.8	441.5	452.2	462.0	471.7	483.3	494.9
162.5°	411.4	414.3	419.9	425.4	432.9	442.2	451.5	459.1	467.4	476.9	486.3
165°	420.1	421.9	426.3	429.9	436.1	443.3	449.5	454.9	461.1	468.1	475.3
167.5°	427.2	428.1	431.5	434.0	437.9	443.1	448.1	450.6	454.7	459.9	465.7
170°	430.8	431.7	434.4	436.1	437.9	442.4	445.9	447.7	450.4	454.9	459.3
172.5°	434.4	434.5	436.5	437.6	438.6	442.4	445.2	445.6	446.8	449.9	453.6
175°	437.9	437.0	438.8	438.8	439.7	441.5	443.3	442.4	442.4	444.2	445.9
177.5°	439.7	439.0	439.7	439.7	439.7	440.4	441.8	440.4	439.7	440.4	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1522.2	1522.7	1528.9	1533.4	1531.2	1533.9	1535.1
5°	1663.0	1688.3	1701.6	1711.4	1712.1	1712.8	1718.4
7.5°	1862.8	1889.8	1909.6	1939.6	1948.6	1958.7	1955.8
10°	2008.6	2048.4	2082.9	2101.0	2120.7	2149.4	2126.3
12.5°	2144.7	2215.5	2267.8	2296.2	2314.6	2320.4	2309.1
15°	2369.5	2461.9	2511.7	2510.3	2573.4	2600.8	2558.0
17.5°	2575.5	2660.9	2729.3	2764.3	2816.8	2828.5	2823.2
20°	2701.6	2794.9	2848.1	2908.4	2935.7	2960.2	2964.4
22.5°	2810.4	2894.0	2951.3	3001.4	3024.3	3035.9	3043.0
25°	2922.4	2988.3	3022.6	3040.1	3046.4	3045.0	3035.9
27.5°	2914.6	2919.7	2881.9	2844.7	2811.6	2774.1	2761.2
30°	2839.0	2780.1	2675.0	2615.5	2527.8	2458.4	2486.4
32.5°	2640.0	2522.8	2404.8	2274.6	2166.8	2136.1	2105.2
35°	2253.1	2047.1	1926.5	1786.4	1730.3	1674.3	1635.7
37.5°	1822.8	1663.5	1520.5	1428.8	1372.6	1337.1	1318.1
40°	1576.1	1432.4	1314.7	1240.5	1197.7	1157.7	1152.2
42.5°	1379.4	1245.8	1157.2	1098.1	1056.9	1040.0	1027.7
45°	1129.7	1036.5	977.0	934.9	907.6	897.1	883.1
47.5°	956.2	890.3	845.6	817.0	796.4	788.5	787.5
50°	859.2	804.5	771.6	749.1	733.1	730.2	719.1
52.5°	786.3	739.0	713.3	693.7	682.1	674.2	670.8
55°	682.6	651.0	627.9	616.7	607.6	599.9	599.9
57.5°	597.3	570.9	555.6	546.1	543.2	537.8	534.3
60°	544.6	522.1	510.2	501.8	496.1	496.9	490.5
62.5°	492.9	478.4	467.0	458.6	451.9	452.0	452.5
65°	419.8	408.6	400.2	397.3	393.2	388.3	389.7
67.5°	355.7	345.2	338.7	333.9	332.4	329.8	333.9
70°	309.8	302.0	297.1	292.9	291.5	292.2	295.8
72.5°	267.7	262.3	259.0	257.1	254.0	254.1	256.5
75°	210.3	206.1	203.2	201.2	200.5	200.5	200.5
77.5°	154.4	153.5	152.2	149.1	149.3	150.1	150.3
80°	122.0	119.8	119.1	117.7	115.7	114.2	117.7
82.5°	91.1	89.0	88.3	88.0	84.8	84.5	87.5
85°	49.0	47.0	47.6	47.0	47.0	46.3	46.3
87.5°	22.0	21.7	21.4	21.8	21.4	21.0	22.0
90°	23.2	24.1	25.8	24.9	25.8	26.7	25.8
92.5°	59.5	52.5	47.9	46.3	43.6	44.5	42.9
95°	217.2	170.0	137.9	121.1	113.1	106.8	103.3
97.5°	639.8	525.0	418.5	352.8	312.8	288.7	281.1
100°	977.3	873.2	746.8	656.9	591.9	557.2	558.1
102.5°	1130.4	1069.7	989.6	919.6	868.2	839.2	818.7
105°	1246.2	1263.0	1239.9	1198.9	1165.1	1136.7	1132.2
107.5°	1231.5	1309.5	1341.2	1341.9	1330.5	1320.9	1312.7
110°	1183.8	1295.9	1358.3	1383.2	1390.4	1388.6	1386.8



TEST NUMBER: P332074-940

CATALOG NUMBER: S123DIP-S1165D1025U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1121.1	1246.8	1327.0	1372.5	1394.5	1401.3	1401.7
115°	1020.9	1151.7	1248.8	1315.5	1354.7	1372.5	1377.0
117.5°	936.2	1053.6	1152.1	1221.7	1266.6	1292.3	1298.2
120°	889.2	996.0	1085.9	1156.2	1206.0	1227.4	1232.8
122.5°	851.5	950.5	1033.9	1096.4	1141.3	1164.8	1171.5
125°	804.7	890.1	961.3	1018.2	1057.4	1079.7	1085.9
127.5°	763.5	840.6	905.4	956.1	989.6	1009.7	1015.4
130°	737.9	809.9	870.5	917.7	949.8	968.4	975.5
132.5°	713.6	780.8	838.5	882.8	914.8	931.4	936.4
135°	679.1	737.0	787.7	831.3	858.0	874.1	880.3
137.5°	645.9	695.7	739.7	776.3	803.4	816.9	821.0
140°	626.6	669.3	707.7	741.5	766.3	780.6	779.7
142.5°	608.1	645.2	678.4	707.3	729.3	742.2	741.3
145°	583.9	612.3	638.2	660.4	679.1	686.3	688.0
147.5°	565.9	588.9	607.3	624.1	636.8	643.5	644.3
150°	554.6	573.2	590.1	603.5	613.2	618.6	618.6
152.5°	543.9	560.4	574.4	585.0	594.1	597.3	597.3
155°	528.7	542.1	552.8	560.8	567.8	569.6	570.5
157.5°	513.9	524.2	532.6	539.6	544.9	546.4	546.2
160°	504.7	513.5	519.8	526.0	531.4	531.4	530.5
162.5°	494.7	502.9	508.5	512.6	517.1	517.1	516.2
165°	480.6	486.9	491.3	494.9	498.5	497.6	497.6
167.5°	469.8	473.3	476.5	478.1	480.6	479.7	479.7
170°	462.0	465.5	467.3	468.1	469.9	469.0	469.0
172.5°	455.6	458.4	459.5	459.7	461.5	459.9	459.1
175°	446.8	448.6	448.6	448.6	449.5	448.6	447.7
177.5°	441.8	442.6	442.6	441.8	442.6	441.1	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7

(END OF REPORT)